

## LM5155EVM-FLY User's Guide

The LM5155EVM-FLY evaluation module showcases the features and performance of the LM5155 as wide input non-synchronous flyback controller. The standard configuration is designed to provide a regulate output of 5V at 4A from an input of 18V to 36V, switching at 250 kHz. This evaluation module is designed for ease of configuration, enabling the user to evaluate many different applications on the same module. The PCB is two layers with components populated only on one side. Functionality includes programmable slope compensation, adjustable soft-start, programmable cycle-by-cycle current limit, hiccup mode short-circuit protection, and programmable line under voltage lockout.

### Contents

1	Introduction .....	2
1.1	Electrical Parameters.....	3
1.2	Configuration Points .....	3
2	Application Schematic.....	4
3	EVM Photo.....	5
4	Test Setup and Procedure.....	5
4.1	EVM Test Setup Schematic .....	5
4.2	Test Equipment .....	5
4.3	Precautions .....	6
5	Test Data and Performance Curves.....	6
5.1	Efficiency Curve .....	6
5.2	Load Regulation.....	7
5.3	Thermal Performance .....	8
5.4	Steady State Waveforms .....	9
5.5	Start-Up Waveforms .....	11
5.6	Load Transient Waveforms .....	12
5.7	Load Short-Circuit .....	13
5.8	AC Loop Response .....	14
6	Design Files .....	15

### List of Figures

1	Application Circuit.....	4
2	EVM Photo .....	5
3	Test Setup .....	5
4	Efficiency vs $I_{LOAD}$ .....	6
5	Load Regulation .....	7
6	$V_{SUPPLY} = 36V$ , $I_{LOAD} = 4A$ , No forced air cooling .....	8
7	Steady State, $V_{SUPPLY} = 18V$ , $I_{LOAD} = 4A$ .....	9
8	Steady State, $V_{SUPPLY} = 24V$ , $I_{LOAD} = 4A$ .....	9
9	Steady State, $V_{SUPPLY} = 36V$ , $I_{LOAD} = 4A$ .....	9
10	Start-Up, $V_{SUPPLY} = 18V$ , $I_{LOAD} = 0A$ .....	11
11	Start-Up, $V_{SUPPLY} = 18V$ , $I_{LOAD} = 4A$ .....	11
12	Start-Up, $V_{SUPPLY} = 24V$ , $I_{LOAD} = 0A$ .....	11
13	Start-Up, $V_{SUPPLY} = 24V$ , $I_{LOAD} = 4A$ .....	11
14	Start-Up, $V_{SUPPLY} = 36V$ , $I_{LOAD} = 0A$ .....	11
15	Start-Up, $V_{SUPPLY} = 36V$ , $I_{LOAD} = 4A$ .....	11

16	Load Transient, $V_{SUPPLY} = 18V$ , $I_{LOAD} = 2A$ to $4A$ .....	12
17	Load Transient, $V_{SUPPLY} = 24V$ , $I_{LOAD} = 2A$ to $4A$ .....	12
18	Load Transient, $V_{SUPPLY} = 36V$ , $I_{LOAD} = 2A$ to $4A$ .....	12
19	Short Circuit Protection .....	13
20	Short Circuit Recovery: $V_{SUPPLY} = 36V$ .....	13
21	Control Loop Response $V_{SUPPLY} = 18V$ , $I_{LOAD} = 4A$ .....	14
22	Control Loop Response $V_{SUPPLY} = 24V$ , $I_{LOAD} = 4A$ .....	14
23	Control Loop Response $V_{SUPPLY} = 36V$ , $I_{LOAD} = 4A$ .....	14
24	Top Silkscreen .....	15
25	Top Layer .....	15
26	Bottom Layer .....	15
27	Bottom Silkscreen .....	15
28	LM5155EVM-FLY Schematic .....	16

### List of Tables

1	Electrical Performance Standard Configuration .....	3
2	Test point description .....	3
3	LM5155EVM-FLY Bill of Materials .....	17

## Trademarks

All trademarks are the property of their respective owners.

## 1 Introduction

The LM5155EVM-FLY supports the following features and performance capabilities:

- Tightly regulated output voltage of 5 V
- High conversion efficiency of > 86% at full load.
- Hiccup mode Short Circuit Protection
- User adjustable secondary side soft-start time
- 10V Auxiliary winding to power VCC pin
- 250kHz Switching frequency
- 2 Layer PCB with components populated on 1 side

## 1.1 Electrical Parameters

**Table 1. Electrical Performance Standard Configuration**

Parameter	Test Conditions	MIN	TYP	MAX	UNIT
<b>INPUT CHARACTERISTICS</b>					
Input voltage Range $V_{IN}$	Operation	18	24	36	V
Input voltage turn on $V_{IN(ON)}$	Adjusted by the UVLO/SYNC resistors	17	16.5		V
Input voltage turn off $V_{IN(OFF)}$					
<b>OUTPUT CHARACTERISTICS</b>					
Output Voltage $V_{OUT}$			5		V
Maximum Output Current $I_{OUT}$			4		A
<b>SYSTEM CHARACTERISTICS</b>					
Switching frequency			250		kHz
Peak efficiency	$V_{IN} = 18V, I_{OUT} = 1.8A$		86.5		%
Junction Temperature, $T_J$		-40		150	C
<b>Transformer Specifications (Wurth 750319733)</b>					
Primary Inductance			21		$\mu H$
Turns Ratio	(3-5):(2-1)		1:1		
	(3-5):(6:10) tie (6+7,9+10)		2:1		
Saturation Current	20% inductance reduction		6.2		A
Leakage Inductance			150	300	nH

## 1.2 Configuration Points


Table 2 indicates the available test points. These points offer simple probe points to evaluate the operation of the LM5155.

**Table 2. Test point description**

Jumper	Name	Description
TP1	VIN	Positive input voltage sense connection
TP2	VOUT+	Positive output voltage sense connection
TP3	PGND	Negative input voltage sense connection
TP4	ISO_GND	Negative isolated output voltage sense connection
TP5	SW	Probe point for the switch node of the LM5155 flyback circuit
TP6	VOUT+	Loop response positive injection point
TP7	VOUT-	Loop response negative injection point
TP8	AGND	Analog ground connection point
TP9	ISO_GND	Isolated ground connection point
J1	-	Input power connections
J2	-	Output power connections
J3	PGND	Power ground connection point
J4	PGOOD (pin 1)	Probe voltage on the PGOOD pin of the LM5155
	COMP (pin 2)	Probe voltage on the COMP pin of the LM5155
	SS (pin 3)	Probe voltage on the SS pin of the LM5155
	VAUX (pin 4)	Auxiliary winding voltage
	PGND (pin 5)	Power ground connection


## 2 Application Schematic

The LM5155EVM-FLY is capable of multiple configurations. [Figure 1](#) shows the standard configuration of the LM5155EVM-FLY for which the parameters in [Table 1](#) are valid.



**Figure 1. Application Circuit**

### 3 EVM Photo




**Figure 2. EVM Photo**

### 4 Test Setup and Procedure

#### 4.1 EVM Test Setup Schematic

The correct equipment connections and measurement points are shown in [Figure 3](#)



**Figure 3. Test Setup**

#### 4.2 Test Equipment

**Power Supply:** The input voltage source (VIN) should be a variable supply capable of 0V to 36V and source at least 5A.

**Multi-meters:**

- Voltmeter 1: Input voltage, connect from VIN to PGND
- Voltmeter 2: Output voltage, connect from VOUT to ISO\_GND
- Ammeter 1: Input current, must be able to handle 5A. Shunt resistor can be used as needed.
- Ammeter 2: Output current, must be able to handle 5A. Shunt resistor can be used as needed.

**Electronic Load:** The load should be constant resistance (CR) or constant current (CC) capable. It should safely handle 4A at 5V.

Oscilloscope: 20-MHz bandwidth and AC coupling. Measure the output voltage ripple directly across an output capacitor with a short ground lead. It is not recommended to use a long-leaded ground connection due to the possibility of noise being coupled into the signal. To measure other waveforms, adjust the oscilloscope as needed.

#### 4.3 Precautions


**CAUTION:**


Prolonged operation with low input at full power will cause heating of the diode (D1).

**Board surface is hot. Do not touch. Contact may cause burns.**

### 5 Test Data and Performance Curves


Figure 4 through Figure 23 present the typical performance of the LM5155EVM-FLY according to the bill of materials and the configuration described in Table 1. Based on measurement techniques and environmental variables measurements might differ slightly than the data presented

#### 5.1 Efficiency Curve



**Figure 4. Efficiency vs I<sub>LOAD</sub>**

## 5.2 Load Regulation



**Figure 5. Load Regulation**

### 5.3 Thermal Performance






Figure 6.  $V_{SUPPLY} = 36V$ ,  $I_{LOAD} = 4A$ , No forced air cooling


## 5.4 Steady State Waveforms



**Figure 7. Steady State,  $V_{SUPPLY} = 18V$ ,  $I_{LOAD} = 4A$**








**Figure 8. Steady State,  $V_{SUPPLY} = 24V$ ,  $I_{LOAD} = 4A$**



**Figure 9. Steady State,  $V_{\text{SUPPLY}} = 36\text{V}$ ,  $I_{\text{LOAD}} = 4\text{A}$**

## 5.5 Start-Up Waveforms



## 5.6 Load Transient Waveforms



**Figure 16. Load Transient,  $V_{SUPPLY} = 18V$ ,  $I_{LOAD} = 2A$  to  $4A$**



**Figure 17. Load Transient,  $V_{SUPPLY} = 24V$ ,  $I_{LOAD} = 2A$  to  $4A$**



**Figure 18. Load Transient,  $V_{SUPPLY} = 36V$ ,  $I_{LOAD} = 2A$  to  $4A$**

## 5.7 Load Short-Circuit




**Figure 19. Short Circuit Protection**




**Figure 20. Short Circuit Recovery:  $V_{SUPPLY} = 36V$**


## 5.8 AC Loop Response



**Figure 21. Control Loop Response  $V_{SUPPLY} = 18V, I_{LOAD} = 4A$**




**Figure 22. Control Loop Response  $V_{SUPPLY} = 24V, I_{LOAD} = 4A$**




**Figure 23. Control Loop Response  $V_{SUPPLY} = 36V, I_{LOAD} = 4A$**


## 6 Design Files




**Figure 24. Top Silkscreen**




**Figure 25. Top Layer**



**Figure 26. Bottom Layer**



**Figure 27. Bottom Silkscreen**



**Figure 28. LM5155EVM-FLY Schematic**

**Table 3. LM5155EVM-FLY Bill of Materials**

Designator	Quan tity	Value	Description	Package Reference	Part Number	Manufacturer
C1	1	680pF	CAP, CERM, 680 pF, 100 V, +/- 10%, X7R, 0603	0603	GRM188R72A68 1KA01D	MuRata
C2	1	100uF	CAP, Polymer Hybrid, 100 uF, 50 V, +/- 20%, 28 ohm, 10x10 SMD	10x10	EEHZC1H101P	Panasonic
C3	1	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 20%, X7R, 0805	0805	08055C104MAT 2A	AVX
C4, C5	2	1uF	CAP, CERM, 1 uF, 50 V, +/- 10%, X7R, 0805	0805	08055C105KAT 2A	AVX
C6	1	4.7uF	CAP, CERM, 4.7 uF, 50 V, +/- 10%, X7R, 1206	1206	C3216X7R1H47 5K160AC	TDK
C7, C8	2	270uF	CAP, Aluminum Polymer, 270 uF, 25 V, +/- 20%, 0.027 ohm, D10xL12.7mm SMD	D10xL12.7mm	PCV1E271MCL1 GS	Nichicon
C9, C10	2	10uF	CAP, CERM, 10 uF, 25 V, +/- 10%, X7R, 1210	1210	885012209028	Wurth Elektronik
C11, C13	2	0.1uF	CAP, CERM, 0.1 uF, 25 V, +/- 10%, X7R, 0603	0603	C1608X7R1E10 4K080AA	TDK
C12	1	1000pF	CAP, CERM, 1000 pF, 25 V, +/- 10%, X7R, 0603	0603	GRM188R71E10 2KA01D	MuRata
C14	1	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71H1 03KA37D	MuRata
C15	1	4.7uF	CAP, CERM, 4.7 uF, 35 V, +/- 10%, X5R, 0603	0603	GRM188R6YA4 75KE15D	MuRata
C16	1	0.33uF	CAP, CERM, 0.33 uF, 100 V, +/- 10%, X7R,		C3216X7R2A33 4K130AA	TDK
C17	1	1uF	CAP, CERM, 1 uF, 16 V, +/- 20%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71C1 05MA64D	MuRata
C18	1	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603	C1608X7R1H10 4K080AA	TDK
C19	1	470pF	CAP, CERM, 470 pF, 50 V, +/- 10%, X7R, 0603	0603	GRM188R71H4 71KA01D	MuRata
C20	1	4.7uF	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X6S, AEC-Q200 Grade 2, 0603	0603	GRT188C81E47 5KE13D	MuRata
C21	1	220pF	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	C0603C221J5G ACTU	Kemet
C22	1	0.01uF	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0603	0603	GRM188R71C1 03KA01D	MuRata
C24, C26	2	0.22uF	CAP, CERM, 0.22 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CL10B224KO8V PNC	Samsung
C28	1	1000pF	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1812	1812	1812GC102K1A	AVX
D1	1	40V	Diode, Schottky, 40 V, 10 A, AEC-Q101, TO-277A	TO-277A	SS10P4-M3/87A	Vishay-Semiconductor
D2	1	100V	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323	MMDL914-TP	Micro Commercial Components
D3	1	150V	Diode, Superfast Rectifier, 150 V, 1 A, SMA	SMA	ES1C-13-F	Diodes Inc.
D4	1	30V	Diode, Schottky, 30 V, 0.2 A, SOT-323	SOT-323	BAT54SWT1G	Fairchild Semiconductor
H1, H2, H3, H4	4		Bumper, Cylindrical, 0.312 X 0.200, Black	Black Bumper	SJ61A1	3M
J1, J2	2		Terminal Block, 5mm, 2-pole, TH	TH, 2-Leads, Body 10x9mm, Pin Spacing 5mm	ED350/2	On-Shore Technology

**Table 3. LM5155EVM-FLY Bill of Materials (continued)**

J3, TP9	2		TEST POINT SLOTTED .118", TH	Test point, TH Slot Test point	1040	Keystone
J4	1		Header, 2.54mm, 5x1, Tin, TH	Header, 2.54mm, 5x1, TH	PEC05SAAN	Sullins Connector Solutions
Q1	1	100V	MOSFET, N-CH, 100 V, 13 A, DQJ0008A (VSONP-8)	DQJ0008A	CSD19533Q5A	Texas Instruments
R1	1	15.0	RES, 15.0, 1%, 0.5 W, 1210	1210	ERJ-14NF15R0U	Panasonic
R2, R11	2	100	RES, 100, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	ERJ-3EKF1000V	Panasonic
R3	1	0	RES, 0, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	RMCF0603ZT0R00	Stackpole Electronics Inc
R4	1	30.1k	RES, 30.1 k, 1%, 1 W, AEC-Q200 Grade 0, 2512	2512	CRCW251230K1FKEG	Vishay-Dale
R5, R8, R10, R24, R26	5	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	ERJ-3GEY0R00V	Panasonic
R6, R9, R13	3	100k	RES, 100 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW0603100KFKEA	Vishay-Dale
R7	1	10.0	RES, 10.0, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060310R0FKEA	Vishay-Dale
R12	1	0.02	RES, 0.02, 1%, 1 W, 0612	0612	PRL1632-R020-F-T1	Susumu Co Ltd
R14	1	1.00k	RES, 1.00 k, 1%, 0.1 W, 0603	0603	ERJ-3EKF1001V	Panasonic
R16, R22	2	9.76k	RES, 9.76 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06039K76FKEA	Vishay-Dale
R17	1	86.6k	RES, 86.6 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060386K6FKEA	Vishay-Dale
R18	1	4.99k	RES, 4.99 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06034K99FKEA	Vishay-Dale
R19	1	30.0k	RES, 30.0 k, 1%, 0.1 W, 0603	0603	RC0603FR-0730KL	Yageo
R20, R21	2	1.00k	RES, 1.00 k, 0.1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	ERA3AEB102V	Panasonic
T1	1	21uH	Transformer, 21 uH, SMT	13.97x18.25mm	750317933	Wurth Elektronik
TP1, TP2	2		Test Point, Miniature, Red, TH	Red Miniature Testpoint	5000	Keystone
TP3, TP4, TP8	3		Test Point, Miniature, Black, TH	Black Miniature Testpoint	5001	Keystone
TP5	1		PC Test Point, SMT	PC Test Point, SMT	5017	Keystone
U1	1		2.2-MHz Wide Input Nonsynchronous Boost, Sepic, Flyback Controller, DSS0012B (WSON-12)	DSS0012B	LM51551DSST	Texas Instruments
U2	1		Optocoupler, 2.5 kV, 100-200% CTR, SMT	PS2811-1	PS2811-1-M-A	California Eastern Laboratories
U3	1		Low-Voltage (1.24V) Adjustable Precision Shunt Regulators, 3-pin SOT-23, Pb-Free	DBZ0003A	LMV431BIMF/NOPB	Texas Instruments

## **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2019, Texas Instruments Incorporated