

说明


此以太网供电 (PoE) 参考设计可通过一条以太网电缆向互联 LED 照明镇流器传输电力和数据。此参考设计采用了 TI 的 TPS2372-4 PoE 供电器件 (PD) 接口、LM3409 降压控制器、LM5165 降压转保护器件、TPS62740 降压转换器、TM4C1292NCPDT 微控制器 (MCU)、TPD4E05U06-Q1 ESD 保护器件和 DP83822I 以太网 PHY 为 LED 光源提供电源，在连接到网络的同时，通过远程方式控制 LED 光源的亮度和调光参数。

资源

TIDA-01463	设计文件夹
TPS2372	产品文件夹
LM3409HV	产品文件夹
LM5165	产品文件夹
TPS62740	产品文件夹
TM4C1292NCPDT	产品文件夹
DP83822I	产品文件夹
TPD4E05U06-Q1	产品文件夹



咨询我们的 E2E 专家



特性

- IEEE802.3bt 兼容型 PD
- 51W 6 类功率级别
- 适用于已联网控制的 IP 可寻址板
- 最低待机功耗为 181mW，支持 EEE (IEEE802.3az)
- 自动维持功率特征
- 高功率可满足广泛照明的需求 应用
- 板尺寸较小，可安装在典型 LED 镇流器外壳内

特色应用

- PoE 照明
- 四对非隔离式 PoE



该 TI 参考设计末尾的重要声明表述了授权使用、知识产权问题和其他重要的免责声明和信息。

1 System Description

The TM4C129x family of MCUs features an integrated Ethernet PHY and MAC with cryptographic modules and many serial interfaces for control and sensor data gain. The TM4C129x adds a layer of intelligence at the remote node when integrated with the PoE design. This addition allows customers to leverage their existing network to communicate and control devices securely. The PoE solution delivers power that reduces the system cost in IoT space, which adds value to the products.


1.1 Key System Specifications

表 1. Key System Specifications

PARAMETER	SPECIFICATIONS
DC input voltage	0 V to 57 V
Maximum sinking current	1.2 A
Maximum output voltage	40 V
Constant output current	1.15 A
Minimum system standby power consumption with EEE enabled	181 mW
MPS overhead power consumption	45 mW
PoE power class	Class 6, 51 W at PD input
System efficiency	90%
Printed circuit board (PCB) size	Rectangular, 1.06" x 6.1" (26.9 mm x 154.9 mm), four-layer PCB

2 System Overview

2.1 Block Diagram



Copyright © 2017, Texas Instruments Incorporated

图 1. PoE Lighting System Block Diagram

2.2 Design Considerations

This design features a non-isolated buck converter that offers *low voltage* (< 60 V) locally to each LED lighting ballast, so an electrician is not required. The approximate 48 V received by the TPS2372 is bucked down to 3.3 V by the LM5165 to power the MCU, which is again bucked down to 1.8 V to power the ultra-low-power DP83822I Ethernet PHY. The remaining approximate 46 W is sent along to the LED ballast.

2.3 Highlighted Products

This reference design features the devices listed in [表 2](#).

表 2. Highlighted Products

PART NUMBER	DESCRIPTION
TPS2372-4	IEEE 802.3bt PoE, high-power PD interface with automatic MPS and autoclass
LM3409HV	PFET buck controller for high-power LED drivers
LM5165	3-V to 65-V, 150-mA synchronous buck converter with ultra-low IQ
TPS62740	Ultra-low-power, 300-mA step-down buck DC/DC converter with 360- μ A IQ
TM4C1292NC PDT	IoT-enabled, high-performance, 32-bit ARM® Cortex®-M4F based MCU
DP83822I	Robust, low-power 10/100 Ethernet physical layer transceiver
TPD4E05U06-Q1	Automotive 4-channel ESD protection solution for SuperSpeed (up to 5 Gbps) interface


2.3.1 TPS2372-4

The TPS2372 contains all of the features required to implement an IEEE802.3at or IEEE802.3bt (draft) (Type 1-4) PD. The low internal switch resistance allows the TPS2372-4 and TPS2372-3 to support high-power applications up to 90 W and 60 W respectively. Assuming usage of 100m CAT5 cable, this translates into 71.3 W and 51 W at PD input.

The TPS2372 operates with enhanced features. The automatic MPS function enables applications that require very low-power standby modes. The TPS2372 automatically generates the necessary pulsed current to maintain the power source equipment (PSE) power. An external resistor is used to enable this functionality and to program the MPS pulsed current amplitude.

The TPS2372 also implements a delay function to allow the remote PSE to complete its inrush phase before releasing the Power Good (PG) output. This ensures that the IEEE802.3bt (draft) startup requirements are met. The autoclass enable input also allows advanced system power optimization modes compliant with IEEE802.3bt (draft) standard.

图 2 shows the TPS2372 block diagram.


图 2. TPS2372 Block Diagram

2.3.2 LM3409HV

The LM3409HV is a P-channel MOSFET (PFET) controller for step-down (buck) current regulators. The device offers a wide input voltage range, high-side differential current sense with low adjustable threshold voltage and fast output enable-disable function, and a thermally enhanced 10-pin, HVSSOP package. These features combine to make the LM3409HV ideal for use as constant current sources for driving the LEDs with a forward current of the necessary 1.15 A.

The LM3409HV device uses constant off-time (COFT) control to regulate an accurate constant current without requiring for external control loop compensation. Analog and pulse width modulation (PWM) dimming are easy to implement and result in a highly-linear dimming range with excellent achievable contrast ratios. Programmable undervoltage lockout (UVLO), low-power shutdown, and thermal shutdown complete the feature set.

图 3 shows the LM3409HV block diagram.




图 3. LM3409HV Block Diagram

2.3.3 LM5165

The LM5165 device is a compact, easy-to-use, 3-V to 65-V, ultra-low IQ synchronous buck converter with high efficiency over wide input voltage and load current ranges. With integrated high-side and low-side power MOSFETs, up to 150 mA of output current can be delivered at fixed output voltages of 3.3 V or 5 V or at an adjustable output. The converter is designed to simplify implementation while providing options to optimize the performance for the target application. Pulse frequency modulation (PFM) mode is selected for optimal light-load efficiency or constant on-time (COT) control for nearly constant operating frequency. Both control schemes do not require loop compensation while providing excellent line and load transient response and short PWM on time for large, step-down conversion ratios.

The high-side, P-channel MOSFET can operate at 100% duty cycle for lowest dropout voltage and does not require a bootstrap capacitor for gate drive. Also, the current limit setpoint is adjustable to optimize inductor selection for a particular output current requirement. Selectable and adjustable start-up timing options include minimum delay (no soft start), internally fixed (900 μ s), and externally programmable soft start using a capacitor. An open-drain, PGOOD indicator can be used for sequencing, fault reporting, and output voltage monitoring.

图 4 shows the LM5165 block diagram.





图 4. LM5165 Block Diagram

2.3.4 TPS62740

The TPS6274x is the industry's first step-down converter featuring typical, $360-\mu\text{A}$ quiescent current and operating with a tiny $2.2-\mu\text{H}$ inductor and $10-\mu\text{F}$ output capacitor. This new DCS-Control™ based device extends the light-load efficiency range below $10-\mu\text{A}$ load currents. TPS62740 supports output currents up to 300 mA , and TPS62742 supports up to 400 mA . The device operates from rechargeable Li-Ion batteries, Li-primary battery chemistries, such as Li-SOCl₂ and Li-MnO₂, and two or three cell alkaline batteries. The input voltage range up to 5.5 V also allows operation from a USB port and thin-film, solar modules. The output voltage is user selectable by four VSEL pins within a range of 1.8 V to 3.3 V in $100-\text{mV}$ steps.

TPS6274x features low-output ripple voltage and low noise with a small-output capacitor. Once the battery voltage comes close to the output voltage (close to 100% duty cycle), the device enters no ripple, 100% mode operation to prevent an increase of output ripple voltage. The device then stops switching, and the output is connected to the input voltage. The integrated slew rate controlled load switch provides typical $0.6-\Omega$ on-resistance and can distribute the selected output voltage to a temporarily used subsystem.

图 5 显示了 TPS62740 块图。



Copyright © 2017, Texas Instruments Incorporated


图 5. TPS62740 Block Diagram

2.3.5 TM4C1292NCPDT

Tiva™ C Series MCUs integrate a large variety of rich communication features to enable a new class of highly-connected designs with the ability to allow critical, real-time control between performance and power. The MCUs feature integrated communication peripherals along with other high-performance analog and digital functions to offer a strong foundation for many different target uses, spanning from human machine interface (HMI) to networked system management controllers.

In addition, Tiva C Series MCUs offer the advantages of ARM's widely available development tools, System-on-Chip (SoC) infrastructure, and a large user community. Additionally, these MCUs use ARM's Thumb®-compatible Thumb-2 instruction set to reduce memory requirements and, thereby, cost. Finally, the TM4C1292NCPDT MCU is code-compatible to all members of the extensive Tiva C Series, which provide flexibility to fit precise needs.

图 6 shows the TM4C1292NCPDT block diagram.



Copyright © 2017, Texas Instruments Incorporated

图 6. TM4C1292NCPDT Block Diagram

2.3.6 DP83822I

The DP83822I is a low-power, single-port 10/100 Mbps Ethernet PHY. The device provides all physical layer functions required to transmit and receive data over both standard, twisted-pair cables or connect to an external, fiber-optic transceiver. Additionally, the DP83822I provides flexibility to connect to a MAC through a standard MII, RMII or RGMII interface.

The DP83822I offers integrated cable diagnostic tools, built-in self-test (BIST), and loopback capabilities for ease of use. The device supports multiple industrial buses with its fast, link-down timing as well as Auto-MDIX in forced modes.

The DP83822I offers an innovative and robust approach for reducing power consumption through EEE, Wake on Lan (WoL), and other programmable energy savings modes.

图 7 shows the DP83822I block diagram.




图 7. DP83822I Block Diagram

2.3.7 TPD4E05U06-Q1

The TPDxE05U06-Q1 is a family of unidirectional transient voltage suppressor (TVS) electrostatic discharge (ESD) protection diodes with ultra-low capacitance. They are rated to dissipate ESD strikes above the maximum level specified in the IEC 61000- 4-2 level 4 international standard. The ultra-low loading capacitance makes these devices ideal for protecting any high-speed signal applications up to 6 Gbps. These devices are also available without automotive qualification: TPDxE05U06.




图 8. TPD4E05U0-Q1 Block Diagram

3 Hardware, Software, Testing Requirements, and Test Results

3.1 Required Hardware and Software

This section provides an overview of the TIDA-01463 design board and all the external connections required to evaluate the reference design.

3.1.1 Hardware

To create the solution, the design board must be used as the base board to which the LED lighting ballast is connected. As the solution is PoE, the user must have a PoE PSE available that powers the board during configuration, a debug probe to load the firmware to run the application, and a computer to run the software.

表 3. Hardware Setup

ITEM	COMMENTS	PART NUMBER
TIDA-01463 PCB with IR sensor	—	TIDA-01463
Two CAT5e Ethernet	Both <100-m length	—
PSE	Must be IEEE 802.3bt compliant and capable of supplying 60 W	TPS23861EVM-612
XDS110 JTAG debug probe	Debugger option one	TMDSEMU110-U
MSP432P401R LaunchPad™	Debugger option two	MSP-EXP432P401R
LED lighting ballast	Must be <40 V and <46 W	—
PC with Ethernet port	For running PMP20537 demonstration	—

3.1.1.1 TIDA-01463 PCB With IR Sensor

The TIDA-01463 reference design kit includes the TIDA-01463 PCB, an IR sensor board, and a 4-pin header for clearance between the capacitor and the sensor board.

The sensor board uses the Panasonic EKMB1301111K passive infrared sensor to detect motion. The use of this board is required for basic operation of the TIDA-01463 reference design. The design files for the IR sensor board are included with the TIDA-01463 design files.



图 9. TIDA-01463 PCB With IR Sensor

To setup the demonstration, configure the headers as in 表 4.

表 4. Header Configurations

DESIGNATOR	CONFIGURATION	DESCRIPTION
J1	—	PoE input
J2	Short	Short to enable autoclass
J3	Open	Open selects 5.4% MPS duty cycle
J4	Open	Open to enable 8.4ms inrush delay
J5	Short	Short to connect PoE input current
J6	Short	Short to enable automatic MPS
J7	—	LED Output
J8	Short	Short to connect 3.3 V to MCU V _{DD}
J9	—	10-Pin JTAG connects to debug probe
J10	—	4-Pin I ₂ C connects to IR sensor
J11	Short middle to low	3-pin connects Ethernet PHY Vcc (middle pin) to 1.8 V (lower pin) or 3.3 V (higher pin)
J12	Short	Connects 3.3 V to MCU V _{DDIO}

图 10 shows these headers.



图 10. TIDA-01463 PCB Headers

3.1.1.2 CAT5e Ethernet Cable

The IEEE802.3bt standard recommends using CAT5e cable at the minimum. Greater cable standards (CAT6, 6A) may reduce cable losses and improve system efficiency. The cable length between the PSE and PD must be less than 100 m.

3.1.1.3 Power Sourcing Equipment (PSE)

To take full advantage of this reference design, the PSE must be compliant with the IEEE 802.3bt standard and must be able to source 60 W from its PoE output (PoE class 6). 图 11 shows a Phihong® midspan PSE that meets these requirements.



图 11. Phihong® Class 6 PSE

3.1.1.4 Debug Probe for Tiva™ C Series

There are two hardware options: using a standalone XDS110 debug probe or using the XDS110 debugger from the MSP432™ LaunchPad (MSP EXP432P401R).

The TI XDS110 connects to the TIDA-01463 design board through a TI 20-pin connector with an attached adapter for the ARM, 10-pin, JTAG cable. The design board then connects to the host PC using USB2.0. 图 12 shows the XDS110 debug probe.



图 12. XDS110 JTAG Debug Probe

The XDS110-ET debug probe above the dotted line on the MSP432P401R LaunchPad will work the same, but the probe must be isolated from the bottom of LaunchPad by depopulating the RST, TMS, TCK, TDO, and TDI headers on the isolation block, J101. A 10-pin JTAG cable can be attached to J102, which then connects to the host PC using a micro USB.

图 13 显示的是 MSP432P401R LaunchPad，带有去装配的 JTAG 头。




图 13. MSP432P401R LaunchPad™

3.1.1.5 LED Lighting Ballast

A CREE LMH2 LED module was used for the demonstration. This module is rated for 39 V, 900 mA.



图 14. CREE LMH2 LED Module

3.1.2 Software

The UniFlash and PMP20537 demonstrations are the required software to run the TIDA-01463 demonstration.

3.1.2.1 UniFlash

UniFlash is used to flash firmware on to the TIDA-01463, assign a MAC address, and perform other debug utilities for the onboard TM4C1292NCPDT MCU.

1. UniFlash can be downloaded from the [UniFlash tool folder](#) by clicking *Get Software* beside the most current version of the software.
2. This link will open the [CCS UniFlash](#) page on processors.wiki.ti.com. There, the desktop version of UniFlash can be downloaded for Windows, Linux, or MacOS.
3. Run the installer. Version 4.2 of UniFlash is installed under *C:\ti\uniflash_4.2* by default.

Instructions for how to use UniFlash can be found in [节 3.2.1.2](#).

3.1.2.2 PMP20537 Demonstration

The PMP20537 demonstration is used to control the LED lighting ballast attached to the TIDA-01463 design PCB on the network.

1. Download PMP20537 demonstration from the TIDA-01463 tools folder.
2. Run the *Setup_PMP20537_DEMO* installer. The program will be installed under *C:\Program Files (x86)\Texas Instruments\PMP20537* by default.

Instructions of how to run PMP20537 demonstration can be found in [节 3.2.1.5](#).

3.2 Testing and Results

3.2.1 Test Setup

This section elaborates on how to flash PCB, connect the system, and run the application software.

3.2.1.1 Attaching Debug Probe From MSP432P410R LaunchPad™ to TIDA-01463 PCB

The standalone XDS110 debug probe has a very simple hardware setup. Attaching the 10-pin ARM JTAG adapter to the debug port and connecting to the TIDA-01463 debug pins, J9, is all that is required.

The XDS110-ET debug probe on the MSP432P410R LaunchPad development kit can externally interface to most ARM Cortex-M devices. This functionality is enabled by the J102, 10-pin, Cortex-M JTAG connector. The 10-pin cable can be purchased from Digi-Key Electronics® (sold separately from the LaunchPad development kit).

If unable to provide power to the TIDA-01463 PCB through its PoE port while using UniFlash, 3.3 V of output power can be sourced from the XDS110-ET when jumper JP102 is connected. This connection allows the XDS110-ET to power the external target at 3.3 V through pin 1. By default JP102 is not populated.

1. Remove jumpers on the JTAG signals on the J101 isolation block including RST, TMS, TCK, TDO, and TDI as seen in [图 15](#).




图 15. MSP432P410R LaunchPad™ Isolation Block

2. Connect the 10-pin JTAG connector from J102 on the LaunchPad to J9 on the TIDA-0163 PCB, and connect the LaunchPad's micro USB to a computer.
3. If power is not sent through JTAG, the PCB must receive power through the PoE input.




图 16. PCB Connected to XDS110-ET on LaunchPad

3.2.1.2 Flashing TIDA-01463 PCB Using UniFlash

UniFlash is a standalone tool used to program on-chip flash memory on many TI MCUs, including the Tiva C. Below are instructions on how use UniFlash to flash firmware and assign a MAC address to the TIDA-01463 PCB.

注: While using UniFlash, do not connect the data side of the PSE into the host computer. UniFlash is a web-based application, so it will need internet access to successfully communicate with the TM4C1292NCPDT through JTAG.

- After starting a new UniFlash session, the detected device will be an MSP432P401R LaunchPad if using the onboard XDS110-ET. A new configuration must be selected. The device is a *Tiva TM4C1292NCPDT*, and the connection is the *Texas Instruments XDS110 USB Debug Probe* (see 图 17).




图 17. Device Configuration in UniFlash

- To flash an image on to the TM4C1292NCPDT, navigate to the *Program* tab on the left sidebar. Browse for the *poe_light.bin* file (downloaded from TIDA-01463 tools folder), then click *Load Image* (see 图 18).





图 18. Flashing the PCB in UniFlash

3. To assign a MAC address to the TM4C1292NCPDT, go to the *Settings & Utilities* tab and scroll to *MAC Address Mode*. If there is an unused board, the MAC address will be *ff-ff-ff-ff-ff-ff* after clicking *Read MAC Address Value*.



4. To permanently assign a MAC address, check *Commit MAC Address* before clicking *Program MAC Address*.




图 19. Assigning MAC Address in UniFlash

5. Once the board is flashed and a MAC address is assigned, the board is ready to use.

3.2.1.3 Connecting TIDA-01463 PCB

1. First, connect the IR sensor board to header J10 on the TIDA-01463 PCB. The board will function without the sensor. For the correct connection, the board must hang over the large capacitor, so an additional 4-pin header is included to ensure height clearance. [图 20](#) shows the orientation of the IR sensor board..




图 20. TIDA-01463 PCB With IR Sensor Attached

2. Connect the LED light to the output terminal, J7. If unsure about the polarity of the terminals, check the bottom of the PCB. The right terminal (+) is connected to the trace, and the left terminal (-) is connected to the ground plane (see [图 21](#)).




图 21. TIDA-01463 LED Output Connection on PCB

3.2.1.4 Powering TIDA-01463

CAUTION

LED ballasts similar to the CREE LMH2 LED module (39 V, 900 mA) are used as down-lights in retail spaces and commercial settings. At maximum brightness, eye exposure at short distance can cause disorientation, vertigo, headaches, and possible eye damage with prolonged exposure.

When testing the light at short distance, it is recommended to cover the LED ballast with a box or filter before initiating the GUI software. A box used to cover the LED is shown in [图 22](#).




图 22. Plastic Box Covering LED Ballast

1. Connect a CAT5e Ethernet cable from the computer into the data input of the PSE.

注： The TIDA-01643 supports Energy Efficient Ethernet (EEE), so the data side of the PSE can be connected to a switch with EEE support to enable the lowest power consumption during its idle state (45 mW).

2. Connect another CAT5e Ethernet cable from the output of the PSE into the PD. The LED will turn on to full brightness after all connections are made, so be sure to cover the light if close by. The fully-connected test setup is shown in [图 23](#).



图 23. Full Test Setup

3. After going to full brightness, the light will eventually dim if the IR sensor does not sense motion. If the user moves near the IR sensor, the LED will increase brightness.
4. To change the behavior of the dimming and the brightness level of the LED, see [节 3.2.1.5](#).

3.2.1.5 Controlling TIDA-01463 With PMP20537 Demonstration

After connecting the test setup to the PC and powering on the light, start *PMP20537 Demo*. The window in [图 24](#) appears.




图 24. PMP20537DEMO Software

The settings for the LED light are described in [表 5](#)

表 5. PMP20537 DEMO Settings

SETTING	DESCRIPTION
Light setting (0 to 100)	Idle brightness
Maximum light setting (0 to 100)	Maximum brightness when in motion is sensed
Ramp up factor (1 to 10)	Transition time from idle to maximum
Hold time (1 to 225)	Time to stay bright if proximity has not been detected
Ramp down factor (1 to 10)	Transition time from maximum to idle

Each of the table entries corresponds to an IP-addressable TIDA-01643 PCB connected to a light. To makes changes to a light:

1. Double click one of the table entries.
2. Make the changes to the settings.
3. Click *Update*.
4. Click *Refresh* to see the settings reflected on [图 24](#).

3.2.2 Test Results

This section highlights the collected data from PD operation.




图 25. PoE Class and Detection




图 26. Auto MPS

4 Design Files

4.1 Schematics

To download the schematics, see the design files at [TIDA-01463](#).

4.2 Bill of Materials

To download the bill of materials (BOM), see the design files at [TIDA-01463](#).

4.3 Layout Prints

To download the layer plots, see the design files at [TIDA-01463](#).

4.4 Altium Files

To download the Altium project files, see the design files at [TIDA-01463](#).

4.5 Gerber Files

To download the Gerber files, see the design files at [TIDA-01463](#).

4.6 Assembly Drawings

To download the assembly drawings, see the design files at [TIDA-01463](#).

5 Software Files

To download the software files, see the design files at [TIDA-01463](#).

6 Related Documentation

1. Texas Instruments, [MSP432P401R SimpleLink™ Microcontroller LaunchPad™ Development Kit \(MSP-EXP432P401R\) User's Guide](#)
2. Texas Instruments, [XDS110 Debug Probe User's Guide](#)

6.1 商标

DCS-Control, Tiva, LaunchPad, MSP432 are trademarks of Texas Instruments.

ARM, Cortex, Thumb are registered trademarks of ARM Limited.

Digi-Key Electronics is a registered trademark of Digi-Key Corporation.

Phihong is a registered trademark of Phihong Technology, Co..

7 About the Author

THOMAS AMLEE is an application engineer at Texas Instruments. He is a part of the PoE team supporting the TPS237x family of PoE powered devices. Thomas earned his Bachelor in Electrical Engineering (BSEE) from The University of Texas at Dallas.

有关 TI 设计信息和资源的重要通知

德州仪器 (TI) 公司提供的技术、应用或其他设计建议、服务或信息，包括但不限于与评估模块有关的参考设计和材料（总称“TI 资源”），旨在帮助设计人员开发整合了 TI 产品的应用；如果您（个人，或如果是代表贵公司，则为贵公司）以任何方式下载、访问或使用了任何特定的 TI 资源，即表示贵方同意仅为该等目标，按照本通知的条款进行使用。

TI 所提供的 TI 资源，并未扩大或以其他方式修改 TI 对 TI 产品的公开适用的质保及质保免责声明；也未导致 TI 承担任何额外的义务或责任。TI 有权对其 TI 资源进行纠正、增强、改进和其他修改。

您理解并同意，在设计应用时应自行实施独立的分析、评价和判断，且应全权负责并确保应用的安全性，以及您的应用（包括应用中使用的所有 TI 产品）应符合所有适用的法律法规及其他相关要求。你就您的应用声明，您具备制订和实施下列保障措施所需的一切必要专业知识，能够（1）预见故障的危险后果，（2）监视故障及其后果，以及（3）降低可能导致危险的故障几率并采取适当措施。您同意，在使用或分发包含 TI 产品的任何应用前，您将彻底测试该等应用和该等应用所用 TI 产品的功能。除特定 TI 资源的公开文档中明确列出的测试外，TI 未进行任何其他测试。

您只有在为开发包含该等 TI 资源所列 TI 产品的应用时，才被授权使用、复制和修改任何相关单项 TI 资源。但并未依据禁止反言原则或其他法理授予您任何 TI 知识产权的任何其他明示或默示的许可，也未授予您 TI 或第三方的任何技术或知识产权的许可，该等产权包括但不限于任何专利权、版权、屏蔽作品权或与使用 TI 产品或服务的任何整合、机器制作、流程相关的其他知识产权。涉及或参考了第三方产品或服务的信息不构成使用此类产品或服务的许可或与其相关的保证或认可。使用 TI 资源可能需要您向第三方获得对该等第三方专利或其他知识产权的许可。

TI 资源系“按原样”提供。TI 兹免除对 TI 资源及其使用作出所有其他明确或默认的保证或陈述，包括但不限于对准确性或完整性、产权保证、无屡发故障保证，以及适销性、适合特定用途和不侵犯任何第三方知识产权的任何默认保证。

TI 不负责任何申索，包括但不限于因组合产品所致或与之有关的申索，也不为您辩护或赔偿，即使该等产品组合已列于 TI 资源或其他地方。对因 TI 资源或其使用引起或与之有关的任何实际的、直接的、特殊的、附带的、间接的、惩罚性的、偶发的、从属或惩戒性损害赔偿，不管 TI 是否获悉可能会产生上述损害赔偿，TI 概不负责。

您同意向 TI 及其代表全额赔偿因您不遵守本通知条款和条件而引起的任何损害、费用、损失和/或责任。

本通知适用于 TI 资源。另有其他条款适用于某些类型的材料、TI 产品和服务的使用和采购。这些条款包括但不限于适用于 TI 的半导体产品 (<http://www.ti.com/sc/docs/stdterms.htm>)、评估模块和样品 (<http://www.ti.com/sc/docs/samptersms.htm>) 的标准条款。

邮寄地址：上海市浦东新区世纪大道 1568 号中建大厦 32 楼，邮政编码：200122
Copyright © 2017 德州仪器半导体技术（上海）有限公司