


# TI OMAP4xxx POP SMT Design Guideline

Michael Chen (TITL PKG)

Kenji Masumoto (HIJI PKG)

Shawn Wu (TITL PKG)

Kurt Wachtler (WTBU PKG)



*We Support* **One Make** <sup>1</sup>

# Index:



## ⌘ Package Introduction



## ⌘ OMAP4 SMT Process sharing

- ✓ Stencil/PCB design guide
- ✓ Memory chip flux/solder dipping in 1-step mounting
- ✓ The example of Pick & Place machine condition setting
- ✓ Reflow profile recommendation
- ✓ SMT experiment examples

## ⌘ Appendix

- ✓ Through molded via solder rework methods
- ✓ X-ray examples
- ✓ Screen print material and tool examples
- ✓ Package warpage affect examples

# OMAP4XXX POP Packages




# Mechanical Drawing of OMAP4xxx CBS (TMV)


OMAP4xxx




Top View




Bottom View






Top View



Bottom View




# OMAP4xxx TMV





# Mechanical Drawing of Memory Chip

216-ball FBGA

Solder ball: Lead free (Sn-Ag-Cu)



Memory Chip



# Agenda:

⌘ Package Introduction

➔ ⌘ OMAP4 SMT Process sharing


- ✓ Stencil/PCB design guide
- ✓ Memory chip flux/solder dipping in 1-step mounting
- ✓ The example of Pick & Place machine condition setting
- ✓ Reflow profile recommendation
- ✓ SMT experiment examples

⌘ Q& A



# Stencil/PCB design guide for P0.4 OMAP4

PWB Land & Stencil aperture design Recommendation for pitch 0.4mm

Solder Mask Defined



Non Solder Mask Defined




<u>Ball Pitch</u>	<u>PWB Design</u>		<u>Stencil Design</u>			
	<u>A</u>	<u>B</u>	<u>Thickness</u>	<u>Opening</u>		
0.4mm	SMD*	0.23	0.28	0.08/0.1	0.25	(Zone C)
				0.08/0.1	0.20	(Zone A+B)
	NSMD	0.28	0.23	0.08/0.1	0.25	(Zone C)
			0.08/0.1	0.20	(Zone A+B)	


- Avoid VIP( Via in Pad) design. If should do it, the plugged via with flatten surface is recommended.
- SMD design is more suggested than NSMD to prevent the solder starvation form trace neck or irregular joint shape.
- Trace design: No big ground with several pads connection or wide trace neck.
- Square opening of Stencil can get more volume for joint print.

# Package on Package (POP) Surface Mount Assembly Process Flow

- Screen print solder paste to PCB
- Pick and place OMAP BGA



- Dip Memory package into flux or paste
- Place on top of OMAP package







- Reflow to form POP stack



# Memory chip flux/solder dipping recommendation in 1-step mounting

“A” memory DC package, is dipped into flux with variable depth





50% is appropriate dipping depth



## Flux/solder past dip depth:

From the evaluation, the optimal results at 50-70 % flux dip and solder paste.

# Memory Paste dipping & SMT Machine Control Setting




Memory Dip too fast + paste suppress by 4 balls and extrude the additional paste up & attached on the bottom of substrate surface.





Balance the in/out transfer speed & dwell time to get optimized solder dipping.

# Flux/Solder Paste Depth Measurement



Flux/paste dipping depth was measured by using height gauge shown in below picture.



The dipping performance contributed the top level soldering yield directly.

# Measurement of flux depth (Example)

**ERICHSEN**  
TESTING EQUIPMENT

## Wet Film Thickness Gauge 433

ISO, BS



One instrument only for 4 measuring ranges: 5 - 100 microns, 100 - 500 microns, 300 - 700 microns, 700 - 1500 microns. This comb-shaped instrument, made of stainless steel, stands out for high accuracy.

## Wet Film Thickness Gauge 234

DIN, ASTM, BS, ISO, NF



A hardened and ground double wheel with an eccentric cam in the middle is rolled over a newly applied film. The wetting line on the middle cam is read off on a scale as wet film thickness. Total measuring range: 1500 microns, available in 8 different sub-ranges.

# Condition of PnP M/C setting (example)

## Placement Parameters:

- ✓ SMT M/C Brand: **Panasonic**
- ✓ Type: **NPM**
- ✓ Device Placement: **OMAP4 + Memory Chip**
- ✓ Placement method: **By 1-step**
- ✓ Fiducial marks recognition for placement:  
**By Board fiducial**
- ✓ Pick up Nozzle type: **1004**
- ✓ Nozzle size: **~8mm (with robber tip)**
- ✓ Memory Vision sequence: **Pickup + Camera vision + Memory Dipping + Placement**
- ✓ Dwell time of memory dipping: **400ms ~1 sec**
- ✓ Placement Force (N) or placement depth (um):  
For OMAP4: **package height+1~2.5N (push down)**  
For Memory Chip: **package height+1~2.5N (push down)**




Nozzle type: 1004



# Bottom and Top BGA Placement



Surface Mounter: Fuji NXT




Memory Package  
Flux Dipping Reservoir



Ideal Flux Depth = 50-60%

# Profile Recommendation for OMAP4xxx (TMV)





## Reflow conditions:


- RT to 150°C 1~3°C/s
- Pre-heat temp(150~200 °C) 60~120sec
- Time above melting 220°C 50~80sec
- Peak temp 240-250°C
- Cool down rate 2~6°C/sec (max.)

- ✓ Evaluated solder paste:
  - ✓ Shenmao PF-606-P (SAC305)
  - ✓ Tamura TLF-204-19A
- ✓ Evaluated Memory dip flux/paste:
  - ✓ Senju M705-TVA03.9F (Paste)
  - ✓ Senju Deltalux-901K3 (Flux)
- ✓ <700 ppm O2 reflow atmosphere is recommended to provide the widest process window.
- ✓ The real profile must be fine-tuned for each product to meet the optimized soldering results


# PCB panel




# POP profile test board example




- Thermal couple test locations: see above picture
- Thermal couple test points:
  - a. The central point btw PCB & OMAP
  - b. The central point btw OMAP & Memory
- Total 6 test points



# 2-pass reflow: Pre-stack tray for FCPOP




To check temperature profile



Pre-stack tray designed for TI OMAP3430

Bottom POP is supported by this rib to depopulated ball area



Pre-stack tray designed for TI OMAP3430

# Agenda:

⌘ Package Introduction

⌘ OMAP4 SMT Process sharing

- ✓ Stencil/PCB design guide
- ✓ Memory chip flux/solder dipping in 1-step mounting
- ✓ The example of Pick & Place machine condition setting
- ✓ Reflow profile recommendation

➔ ✓ SMT experiment examples

⌘ Q& A

# OMAP4xxx SMT Evaluation

Preliminary experiments performed concurrent to package design and material selection

Experiments	1	2	3	4	5	6	7
Dippable mat'l	Senju 529D-1	Senju 529D-1	Senju 529D-1	Senju 529D-1	Senju M705-TVA03.9-F	Senju Deltalux-901K3	Senju Deltalux-901K3
	Flux	Flux	Flux	Flux	Paste	Flux	Flux
Dipping plate depth	170um	170um	170um	170um	140um	170um	160um
Reflow Atmosphere	Air	N2	N2	Air	N2	N2	N2
Reflow preheat time (sec)	80-90	80-90	60-65	60-65	70-80	70-80	70-80
Dwell time for TMV package placement (ms)	300	300	300	300	300	300	300
Dwell time for memory package dipping (ms)	300	300	300	300	600	600	300
Dwell time for memory package placement (ms)	300	300	300	300	500	500	500
Sample Size	1635	204	2310	1700	972	216	700
Rejects	114	0	5	37	0	3	8
Yield	93%	100%	100%	98%	100%	99%	99%

Total Air Atmosphere	
Sample Size	3335
Rejects	151
Yield	95.5%

Total N2 Atmosphere	
Sample Size	4402
Rejects	16
Yield	99.6%

## Summary:

- Nitrogen atmosphere better than air
- Senju 901K3 better in air than Senju 529D-1\*
- Dipping depth too deep\*

\*reference follow up tests in this report

# OMAP4xxx DOE Experiments

# OMAP4xxx DC (TMV) SMT Evaluation DOE1

# DOE1 Set Up


	<b>Flux Dipping</b>	<b>Paste Dipping</b>
<b>OMAP4 Package</b>	OMAP4 CBS Daisy Chain	OMAP4 CBS Daisy Chain
<b>Memory Package</b>	Mock Up	Mock Up
<b>SMT Board</b>	NSMD Pads	SMD Pads
<b>Bottom BGA Paste</b>	Shenmao PF-606-P (SAC305)	Shenmao PF-606-P (SAC305)
<b>Top BGA Flux or Paste</b>	Senju Deltalux-901K3 <b>(No-Clean dipping flux)</b>	Senju M705-TVA03.9F <b>(SAC305, No-Clean dipping paste)</b>
<b>Solder Stencil</b>	Laser and electro-polished	Laser and electro-polished
Thickness (um)	80	80
Shape	Round	Round
Outer Four Rows Diameter (um)	250	250
Inner Rows Diameter (um)	200	200
<b>Memory Package Dipping Depth (um)</b>	120 - 140um	See other table
<b>Reflow Profile</b>		
Pre-heat time	70-80 sec	70-80 sec
Time above Liquid	65 - 75 sec	65 - 75 sec
Peak temp and time	245-250oC	245-250oC
<b>Reflow Atmosphere</b>	Nitrogen (700 O2 ppm)	Nitrogen (700 O2 ppm)
<b>Sample Size</b>	540 packages	270
<b>Yield</b>		
Opens (DC net test)	0/540	See other table
Shorts (X-Ray)	0/540	See other table

# DOE1 Results

	Run 1	Run 2
	<b>Flux Dipping</b>	<b>Paste Dipping</b>
<b>Memory Ball Height</b>	190um	190um
<b>Top BGA Flux or Paste</b>	Senju Deltalux-901K3 (No-Clean dipping flux)	Senju M705-TVA03.9F (SAC305, No-Clean dipping paste)
Warm up time	> 8 hours	See below table
<b>Memory Package Dipping Depth (um)</b>	120 - 140um	See below table
<b>Sample Size</b>	540 ea	270ea
<b>Yield</b>		
Opens (DC net test)	0/540	See below table
Shorts (X-Ray)	0/540	See below table

Run	2-1	2-2	2-3	2-4	2-5
<b>Bottom BGA Paste</b>	Shenmao PF-606-P (SAC305)				
Warm up time	> 18 hours				
<b>Top BGA Paste</b>	Senju M705-TVA03.9F (SAC305, No-Clean dipping paste)				
Warm up time	30 min	> 18 hours			
<b>Memory Package Dipping Depth (um)</b>	140	125	124	122	122
<b>Yield</b>					
Opens (DC net test)	0/54	0/54	0/54	0/54	0/54
Shorts (X-Ray)	54/54	2/54	0/54	0/54	0/54

# Top BGA Typical Solder Joint Defects




**Defect:** Random single or double non-wet solder joints

**Root Causes:**

- Insufficient flux
- OMAP and/or Memory solder ball height and gap variation during the reflow process

**Solution:** Flux volume transfer control



# POP SMT Process Variables



# OMAP4xxx DC (TMV) SMT Evaluation DOE2

# DOE2 Set up: Screen Print Stencil Design & Reflow Process


Stencil Designs	1	2	3	4	5	6	7	8
Shape	Round 80 Variable, Nano	Round 80 Variable	Round 80	Square 80 Uniform	Square 80 Variable	Square 80 variable Nano	Round 100 Uniform	Round 100 Uniform
Thickness (um)	80	80	80	80	80	80	100	100
Zone C	250	250	250	250	250	250	210	255
Zones A & B	200	200	250	250	200	200	210	255
Opening Ratio								
Zones C	0.78	0.78	0.78	0.78	0.78	0.78	0.53	0.64
Zone A & B	0.63	0.63	0.78	0.78	0.63	0.63	0.53	0.64




Reflow Profiles			
	Option 1	Option 2	Option 3
<b>Preheat Zone</b>			
Temperature	R/T-120C	R/T-120C	R/T-120C
Time	70	90	110
<b>Soak Zone</b>			
Temperature	120-180c	120-180c	120-180c
Time	90	110	130
<b>Reflow Zone</b>			
Peak Temperature	235	240-245	245-250
Time above Liquid	60	80	100
<b>Cooling Zone</b>			
	3°/sec	3°/sec	3°/sec

# DOE2: Solder Paste and Flux


Solder paste for POP mount:  
Tamura TLF-204-19A



Flux for memory dipping:  
Senju DELTALUX 901K3



Solder paste for memory dipping:  
Senju M705-TVA03.9-F





# DOE2 Results

Legs	Stencils					POP Memory Process		Reflow Profile			Reflow Atmosphere		Qt'y	Opens		Shorts	Yield				
	1	4	5	7	8	Dipping Material	Dipping Depth (um)	A	B	C	Air	N <sub>2</sub> <700ppm O <sub>2</sub>		Bott om	Top	Any	Bottom	Top			
1						Paste: Senju M705- TVA03.9F	105						216	0	0	0	100%	100%			
2							140							216	0	0	0	100%	100%		
3							180							54	0		54	100%	0%		
4						Flux: Senju 901K3	140						216	0	76	0	100%	65%			
5							130							216	0	0	0	100%	100%		
6							130							216	1	1	0	99.5%	99.5%		
7							130							216	0	1	0	100%	99.5%		
8							130							216	0	0	0	100%	100%		
9							130							216	0	216	0	100%	0%		
10							130							108	0	108	0	100%	0%		
11							130							108	0	1	0	100%	99%		
12							130							216	0	216	0	100%	0%		
13							130							108	0	102	0	100%	6%		
14							130							108	0	0	0	100%	100%		
15 (15 air bake, 150oC, 8 hrs)							130							108	0	108	0	100%	0%		
16 (15 air bake, 150oC, 8 hrs)							130							108	0	0	0	100%	100%		
17-1	N/A (Pre-Stack)						Paste: Senju M705- TVA03.9F	140						108	N/A	N/A	N/A	N/A	N/A		
17-2	N/A (Pre-Stack)						Flux: Senju 901K3	130							108	N/A	N/A	N/A	N/A	N/A	
17-1a							17-1 pre-stack							108	0	0	0	100%	100%		
17-2b						17-2 pre-stack							108	0	0	0	100%	100%			
												Total	2862								


# Memory Dipping Defect Example

Black ring is flux wetting bottom of memory package: pulled flux off solder ball



Flux Legs	Flux Dipping Mat'l	Dipping Depth	Reflow Peak Temp (oC)	Reflow Atmosphere	Package Quantity	Yield
1	Senju Deltalux-901K3	140um	240-245	N <sub>2</sub> (<700ppm O <sub>2</sub> )	216	65%
2	Senju Deltalux-901K3	130um	240-245	N <sub>2</sub> (<700ppm O <sub>2</sub> )	216	100%





Flux viscosity with continuous stirring



**Flux transfer to memory package is critical:**

- Type of flux
- Viscosity of flux
- Dipping depth
- Dwell time of package in flux tray

# Paste Dipping Experiment Result



Paste Legs	Paste Dipping Mat'l	Dipping Depth (um)	Reflow Peak Temp (oC)	Reflow Atmosphere	Package Q'ty	Yield
1	Senju M705-TVA03.9F	105	240-245	N <sub>2</sub> (<700ppm O <sub>2</sub> )	216	100%
2	Senju M705-TVA03.9F	140	240-245	N <sub>2</sub> (<700ppm O <sub>2</sub> )	216	100%
3	Senju M705-TVA03.9F	180	240-245	N <sub>2</sub> (<700ppm O <sub>2</sub> )	54	0%

# DOE2 Result

## Summary:

- Bottom BGA yield robust vs. stencil design
- Top BGA yield sensitive to flux dipping process
  - Depth
  - Viscosity
  - Dwell time
- Top BGA dipping in paste successful: verification required
- Nitrogen atmosphere (<700ppm O<sub>2</sub>) required in this test
- Experiments will continue to define assembly capability in an Air reflow atmosphere

# OMAP4xxx DC (TMV) SMT Evaluation DOE3

# DOE3 Set up:

Reflow Profile	
<b>Preheat Zone</b>	
Temperature	R/T-120C
Time	90
<b>Soak Zone</b>	
Temperature	120-180c
Time	110
<b>Reflow Zone</b>	
Peak Temperature	240-245
Time above Liquid	80
<b>Cooling Zone</b>	
	3°/sec

Stencil Design	
Shape	Round 80 Variable
Surface Finish	Laser Job nano coating
Thickness (um)	80
<b>Opening Diameter(um)</b>	
Zone C	250
Zones A & B	200
<b>100% Volume Transfer Rate</b>	
Zones C (um <sup>3</sup> )	3926991
Zone A & B (um <sup>3</sup> )	2513274
<b>Opening Ratio</b>	
Zones C	0.78
Zone A & B	0.63

Material in DOE3		Recommended reflow atmosphere	Notes
Paste	Senju M705-TVA03.9K	Air	[Halogen Free ROLO (<500ppm) per JSTD-004A, No-Clean Dip Paste]
Paste	Senju TVA 107K	Air	[Halogenated ROL1 per JSTD004A, No-Clean Dip Paste]
Flux	Senju Deltalux 529D-1	Air	[Halogenated ROL1, No-Clean Dip Flux]
Flux	Senju Deltalux-GTN68-HF	Air	[Halogen Free ROLO (<500ppm) per J-STD004A/B, No-Clean Dip Flux]

# DOE3: Results

DOE Leg	Bottom BGA Printing Material	Memory Dipping Mat'l		Dipping Depth (Actual depth)	Dipping Dwell Time (ms)	With EMI Shield	Reflow		Q'ty		# Opens	# Shorts	Yield %
							Air	N2 (O <sub>2</sub> <700 ppm)	Panels	PKGs			
1	Tamura TLF-204-19A	Paste	Senju TVA 107K	130	600	No			4	216	1	0	99.5
2	Tamura TLF-204-19A	Paste	Senju TVA 107K	130	900	No			19	1000	0	0	100
3	Tamura TLF-204-19A	Paste	Senju M705-TVA03.9K	130	600	No			1	54	24	0	56
4	Tamura TLF-204-19A	Paste	Senju M705-TVA03.9K	130	900	No			1	54	19	0	65
5	Tamura TLF-204-19A	Paste	Senju M705-TVA03.9K	130	600	No			1	54	0	0	100
6	Tamura TLF-204-19A	Paste	Senju M705-TVA03.9K	130	900	No			1	54	0	0	100
7	Tamura TLF-204-19A	Flux	Senju Deltalux 529D-1	130	600	No			1	54	13	0	76
8	Tamura TLF-204-19A	Flux	Senju Deltalux 529D-1	130	900	No			1	54	22	0	59
9	Tamura TLF-204-19A	Flux	Senju Deltalux-GTN68HF	130	600	No			4	216	1	0	99.5
10	Tamura TLF-204-19A	Flux	Senju Deltalux-GTN68HF	130	900	No			19	1000	0	0	100
11	Tamura TLF-204-19A	Flux	Senju Deltalux-GTN68HF	130	900	Yes			3	18	0	0	100
12*	Tamura TLF-204-19A	Flux	Senju Deltalux-GTN68HF	130	900	No			2	108	108	0	0
13*	Tamura TLF-204-19A	Paste	Senju TVA 107K	130	900	No			2	108	108	0	0

\*Preconditioned: 150C for 1.5 hrs in Air, followed with 8 hrs at 85RH/85C

Totals 59 2990

# DOE3 Result

## Summary:

- Flux and Paste chemistry and rheology are critical factors for use in an air reflow atmosphere
- Time out of refrigeration and time worked in dipping tray affects coating uniformity
- Dipping time change from 600ms to 900ms improved yield
- A paste that did not work in air worked in nitrogen reflow atmosphere
- Bottom BGA process continues to be robust
- Pre-conditioned parts shifted and yielded zero bottom BGA connections: X-ray of top BGA looked normal but unable to test due to lack of connection through bottom BGA

## Appendix

✓ A1: Through molded via solder rework methods



- **Brush with flux repair method**



- Manual rework method

✓ A2: X-ray examples

✓ A3: Screen print material and reflow equipment examples

✓ A4: Package warpage affect examples

# Brush with flux for repair in TMV level (1)




- Use cotton swab to apply adequate flux at the side-walls of defective POP.
- Reflow then Check in X-ray (see next slide) & O/S test.

Evaluate samples			Test result (Xray, O/S)	
Size	Flux type	Repair level	OK	NG
5	Senju 529D-1	TMV	5	0




# Brush with flux for repair in TMV level (2)



## Non-wet Solder Joint

The non-wetting TMV joints show as 3 balls overlapped with bottom BGA ball in X-ray inspection.



## Repaired Solder Joint

The defect TMV joints are re-healed & show as 2 balls overlapped with bottom BGA ball in X-ray inspection.

## Appendix

✓ A1: Through molded via solder rework methods

- Basic repair method



- **Manual rework method**


**Note: this method is not recommended for product repair due to the number of times the topside solder ball is reflowed**

✓ A2: X-ray examples

✓ A3: Screen print material and reflow equipment examples

✓ A4: Package warpage affect examples


# Process Flow of Manual TMV Rework (1)




# Manual TMV Removal and Re-ball (2)

## Reball Approach


Customer return




Solder up




De-soldering




Re-balling



Bake



Bottom reball process



- Thicker solder contributes better thermal conduction
- More flux help the solder soften and extract out , vacuum pressure  $\sim 80\text{kPa}$

• Paint with flux and place 0.25mm solder ball and reflow

• measure coplanarity by an Equipment

## Appendix

✓ A1: Through molded via solder rework methods


- Basic repair method
- Manual rework method

 ✓ A2: X-ray examples

✓ A3: Screen print material and reflow equipment examples A4:  
Package warpage affect examples

# Solder ball analysis by X-ray -1


1-pass reflow



Picture: POP and Memory mount on PCB. Before reflow.  
Solder paste printing check was good. Memory is mount on POP by flux with good accuracy.

# Solder ball analysis by X-ray -2


1-pass reflow



Picture: Memory mounted by flux, NSMD board, After reflow  
Memory solder ball was jointed with POP showing good barrel shape

# Solder ball analysis by X-ray -3





1-pass reflow



Picture: Memory mounted by flux, SMD board, After reflow  
Memory jointed with POP with good barrel shape.  
No anomaly is found for POP solder balls.

# Solder ball analysis by X-ray -4


1-pass reflow



Picture: Memory mounted by solder paste, SMD board, After reflow  
Excess solder paste caused solder ball short

# Solder ball analysis by X-ray -5

1-pass reflow




Picture: Memory mounted by solder paste, SMD board, After reflow.  
Reduced solder paste dipping depth then solder ball short did not happen



# Solder ball analysis by X-ray -6

1-pass reflow


2<sup>nd</sup> reflow result. Run POP+Memory mount board reflow again



Paste dip, After reflow, SMD pad  
Package upward



Paste dip, After reflow, SMD pad  
Package downward




Memory solder ball joint did not change by 2<sup>nd</sup> reflow

## Appendix


- ✓ A1: Through molded via solder rework methods
  - Basic repair method
  - Manual rework method
- ✓ A2: X-ray examples
-  ✓ A3: Screen print material and reflow equipment examples
- ✓ A4: Package warpage affect examples




Solder Paste



Screen Printing





Solder Stencil



Printed Paste


# Solder Reflow



## Appendix

- ✓ A1: Through molded via solder rework methods
  - Basic repair method
  - Manual rework method
- ✓ A2: X-ray examples
- ✓ A3: Screen print material and reflow equipment examples
-  ✓ A4: Package warpage affect examples

# Calculating Solder Paste Volume to Prevent Shorts in the Center Array



Neutral solder ball at maximum reflow temperature (nominal height)

## Factors affecting location of neutral point:

- Number and location of solder balls
- Solder surface tension
- Pad shape
- Weight of OMAP and Memory packages
- Phone board warpage
- Temperature ramp, uniformity & maximum
- Paste
- Reflow atmosphere

Sketches not to scale

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated