


## Enterprise SSD Backup Power Supply

- Input 5.0V or 12V
- Output 3.3V @ 2.5A, Backup Boost at 28V, Backup Buck 5V @ 2.5A
- Free-Running-Switching Frequency for TPS62130 2.5 MHz, for TPS61170 1.2MHz, for LM43603 500 kHz



## 1. Startup

The startup waveform at 5.0V input voltage and no load on the output is shown in Figure 1.

- Channel Ch1 **5.0V Input Voltage**  
5V/div, 2ms/div
- Channel Ch2 **3.3V Output Voltage**  
2V/div, 2ms/div
- Channel Ch3 **28.0V Output Voltage**  
20V/div, 2ms/div
- Channel Ch4 **V Output Voltage**  
1V/div, 2ms/div




Figure 1

The startup waveform at 12.0V input voltage and no load on the output is shown in Figure 2.

- Channel Ch1 **12.0V Input Voltage**  
2V/div, 2ms/div
- Channel Ch2 **3.3V Output Voltage**  
2V/div, 2ms/div
- Channel Ch3 **28.0V Output Voltage**  
20V/div, 2ms/div
- Channel Ch4 **3.3V Output Voltage**  
1V/div, 2ms/div




Figure 2

## 2. Shutdown

The shutdown waveform at 5.0V input voltage and 2.5A load on the 5V LM43603 output is shown in Figure 3.

- Channel Ch1 **5.0V Input Voltage**  
5V/div, 10ms/div
- Channel Ch2 **3.3V Output Voltage**  
2V/div, 10ms/div
- Channel Ch3 **28.0V Output Voltage**  
20V/div, 10ms/div
- Channel Ch4 **LM43603 Switch Node**  
20V/div, 10ms/div




Figure 3

### 3. Efficiency

The efficiency and load regulation of the 3.3V TPS62130 Buck converter are shown in Figure 4 and Figure 5.




Figure 4




Figure 5

The efficiency and load regulation of the 5.0V LM43603 Buck converter are shown in Figure 6 and Figure 7.




Figure 6




Figure 7

## 4. Transient Response

The response to a load step at 5.0V input voltage is shown in Figure 8.

Channel Ch3 **Output Current**, Load Step 1.25A to 2.5A  
1A/div, 200 $\mu$  s/div

Channel Ch1 **Output Voltage**, -24.8mV undershoot, 16mV overshoot  
20mV/div, 200 $\mu$ s/div, AC coupled




Figure 8

The response to a load step at 28.0V input voltage is shown in Figure 9.

Channel Ch3 **Output Current**, Load Step 0A to 2.5A  
2A/div, 200 $\mu$ s/div

Channel Ch1 **Output Voltage**, -120mV undershoot, 88mV overshoot  
200mV/div, 200 $\mu$ s/div, AC coupled





Figure 9

## 5. Frequency Response

The frequency response of the TPS62130 at 2.5A load is shown in Figure 10.

5.0V Input                    21.2 kHz Bandwidth, 80 deg Phase Margin, -24 dB Gain Margin

12.0V Input                   21.5 kHz Bandwidth, 80 deg Phase Margin, -25 dB Gain Margin



**Figure 10**

The frequency response of the TPS61170 at 0.07A load is shown in Figure 11.

3.3V Input

57.8 Hz Bandwidth, 75 deg Phase Margin, < -50 dB Gain Margin




Figure 11

The frequency response at 16.0A load is shown in Figure 10.

8.0V Input                      27.3 kHz Bandwidth, 81 deg Phase Margin, -14 dB Gain Margin

16.0V Input                    25.1 kHz Bandwidth, 80 deg Phase Margin, -14 dB Gain Margin

28.0V Input                    24.4 kHz Bandwidth, 79 deg Phase Margin, -15 dB Gain Margin




Figure 12

## 6. Output Ripple

The TPS62130 output ripple voltage at 2.5A load is shown in Figure 13.

Channel M1 **Output Voltage @ 5.0V Input**, 192mV peak-peak  
200mV/div, 1us/div

Channel M2 **Output Voltage @ 12.0V Input**, 264mV peak-peak  
200mV/div, 1us/div




Figure 13

The LM43603 output ripple voltage at 2.5A load is shown in Figure 14.

Channel R1 **Output Voltage @ 8.0V Input**, 47.2mV peak-peak  
50mV/div, 4us/div

Channel R2 **Output Voltage @ 16.0V Input**, 40.8mV peak-peak  
50mV/div, 4us/div

Channel R3 **Output Voltage @ 28.0V Input**, 35.2mV peak-peak  
50mV/div, 4us/div




Figure 14

## 7. Switching Node

The drain-source voltage of the TPS62130 low-side FET at 12.0V input voltage and 2.5A load on the output is shown in Figure 15.

Channel Ch1 **Drain-Source Voltage**, -0.8V minimum, 13.4V maximum  
5V/div, 80ns/div




Figure 15

The drain-source voltage of the low-side FET at 28.0V input voltage and 2.5A load on the output is shown in Figure 16.

Channel Ch1 **Drain-Source Voltage**, -1.8V minimum, 29.0V maximum  
5V/div, 400ns/div




Figure 16

## 8. Thermal Image

The thermal image (Figure 17) shows the circuit at an ambient temperature of 20°C with an input voltage of 12.0V and 2.5A load on the 3.3V output.





Figure 17

The thermal image (Figure 18) shows the circuit at an ambient temperature of 20°C with an input voltage of 5.0V and 2.5A load on the 3.3V output.



**Figure 18**

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2021, Texas Instruments Incorporated