

# CDx4HC138、CDx4HCT138、CDx4HC238、CDx4HCT238 ハイスピード CMOS ロジック 3~8 ライン・デコーダ/デマルチプレクサ (反転および非反転)

## 1 特長

- 8 つのデータ出力のいずれかを選択:
  - '138 はアクティブ LOW
  - '238 はアクティブ HIGH
- I/O ポートまたはメモリ・セレクト
- カスケード接続を簡単にするための 3 つのイネーブル入力
- 13ns の伝搬遅延 (標準値、 $V_{CC} = 5V$ 、 $C_L = 15pF$ 、 $T_A = 25^\circ C$ )
- ファンアウト (全温度範囲にわたって)
  - バス・ドライバ出力: 15 の LSTTL 負荷
  - 標準出力: 10 の LSTTL 負荷
- 広い動作温度範囲:  $-55^\circ C \sim 125^\circ C$
- 平衡な伝搬遅延と遷移時間
- LSTTL ロジック IC に比べて消費電力を大幅削減
- HC タイプ
  - 2V~6V で動作
  - 優れたノイズ耐性:  $N_{IL} = V_{CC}$  の 30%、 $N_{IH} = V_{CC}$  の 30% ( $V_{CC} = 5V$  の場合)
- HCT タイプ
  - 4.5V~5.5V で動作
  - LSTTL 入力ロジックと直接互換、 $V_{IL} = 0.8V$  (最大値)、 $V_{IH} = 2V$  (最小値)
  - CMOS 入力互換、 $V_{OL}$ 、 $V_{OH}$  で  $I_L \leq 1\mu A$

## 2 概要


CDx4HC(T)138 および '238 は、1 つの通常の (アクティブ HIGH) 出力ストロブ ( $G_2$ ) と 2 つのアクティブ LOW 出力ストロブ ( $\overline{G}_1$ 、 $\overline{G}_0$ ) を備えた 3~8 デコーダです。いずれかのストロブ入力により出力が無効化されると、すべての出力は HIGH 状態に強制されます。ストロブ入力により出力が無効化されている場合以外は、選択された出力のみが LOW であり、その他のすべての出力は HIGH です。

CDx4HC(T)238 は、1 つの通常の (アクティブ HIGH) 出力ストロブ ( $G_2$ ) と 2 つのアクティブ LOW 出力ストロブ ( $\overline{G}_1$ 、 $\overline{G}_0$ ) を備えた 3~8 デコーダです。いずれかのストロブ入力により出力が無効化されると、すべての出力は LOW 状態に強制されます。ストロブ入力により出力が無効化されている場合以外は、選択された出力のみが HIGH であり、その他のすべての出力は LOW です。

### 製品情報

| 部品番号         | パッケージ <sup>(1)</sup> | 本体サイズ (公称)       |
|--------------|----------------------|------------------|
| CD74HC138E   | PDIP (16)            | 25.40mm × 6.35mm |
| CD74HCT138E  | PDIP (16)            | 25.40mm × 6.35mm |
| CD74HCT238E  | PDIP (16)            | 25.40mm × 6.35mm |
| CD74HC138M   | SOIC (16)            | 9.90mm × 3.90mm  |
| CD74HCT238M  | SOIC (16)            | 9.90mm × 3.90mm  |
| CD74HC238NS  | SO (16)              | 10.20mm × 5.30mm |
| CD74HC238PW  | TSSOP (16)           | 5.00mm × 4.40mm  |
| CD74HCT238PW | TSSOP (16)           | 5.00mm × 4.40mm  |
| CD54HC138F   | CDIP (16)            | 21.34mm × 6.92mm |
| CD54HCT138F  | CDIP (16)            | 21.34mm × 6.92mm |
| CD54HCT238F  | CDIP (16)            | 21.34mm × 6.92mm |

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。



機能ブロック図 '138



## Table of Contents


|                                                    |   |                                                          |    |
|----------------------------------------------------|---|----------------------------------------------------------|----|
| 1 特長.....                                          | 1 | 7.3 Device Functional Modes.....                         | 10 |
| 2 概要.....                                          | 1 | 8 Power Supply Recommendations.....                      | 11 |
| 3 Revision History.....                            | 2 | 9 Layout.....                                            | 11 |
| 4 Pin Configuration and Functions.....             | 3 | 9.1 Layout Guidelines.....                               | 11 |
| 5 Specifications.....                              | 4 | 10 Device and Documentation Support.....                 | 12 |
| 5.1 Absolute Maximum Ratings.....                  | 4 | 10.1 Documentation Support.....                          | 12 |
| 5.2 Recommended Operating Conditions.....          | 4 | 10.2 Receiving Notification of Documentation Updates..   | 12 |
| 5.3 Thermal Information.....                       | 4 | 10.3 サポート・リソース.....                                      | 12 |
| 5.4 Electrical Characteristics.....                | 5 | 10.4 Trademarks.....                                     | 12 |
| 5.5 Switching Characteristics <sup>(2)</sup> ..... | 6 | 10.5 Electrostatic Discharge Caution.....                | 12 |
| 6 Parameter Measurement Information.....           | 7 | 10.6 Glossary.....                                       | 12 |
| 7 Detailed Description.....                        | 8 | 11 Mechanical, Packaging, and Orderable Information..... | 12 |
| 7.1 Overview.....                                  | 8 |                                                          |    |
| 7.2 Functional Block Diagram.....                  | 8 |                                                          |    |

## 3 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| Changes from Revision I (August 2004) to Revision J (November 2021)                                                                     | Page |
|-----------------------------------------------------------------------------------------------------------------------------------------|------|
| • 最新のデータシート規格を反映するように、文書全体の表、図、相互参照の採番と書式設定を更新.....                                                                                     | 1    |
| • 現行の TI の命名規則に合わせてピン名を以下のように更新。E <sub>3</sub> を G <sub>2</sub> 、E <sub>2</sub> を G <sub>1</sub> 、E <sub>1</sub> を G <sub>0</sub> ..... | 1    |

## 4 Pin Configuration and Functions



**J, N, D, NS, or PW package**  
**16-Pin CDIP, PDIP, SOIC, SO, or TSSOP**  
**Top View**

### Pin Functions

| PIN               |                  | I/O <sup>(1)</sup> | DESCRIPTION                 |
|-------------------|------------------|--------------------|-----------------------------|
| SOIC or TSSOP NO. | NAME             |                    |                             |
| 1                 | A <sub>0</sub>   | I                  | Address select 0            |
| 2                 | A <sub>1</sub>   | I                  | Address select 1            |
| 3                 | A <sub>2</sub>   | I                  | Address select 2            |
| 4                 | $\overline{G}_0$ | I                  | Output strobe 0, active low |
| 5                 | $\overline{G}_1$ | I                  | Output strobe 1, active low |
| 6                 | G <sub>2</sub>   | I                  | Output strobe 2             |
| 7                 | Y <sub>7</sub>   | O                  | Output 7                    |
| 8                 | GND              | —                  | Ground                      |
| 9                 | Y <sub>6</sub>   | O                  | Output 6                    |
| 10                | Y <sub>5</sub>   | O                  | Output 5                    |
| 11                | Y <sub>4</sub>   | O                  | Output 4                    |
| 12                | Y <sub>3</sub>   | O                  | Output 3                    |
| 13                | Y <sub>2</sub>   | O                  | Output 2                    |
| 14                | Y <sub>1</sub>   | O                  | Output 1                    |
| 15                | Y <sub>0</sub>   | O                  | Output 0                    |
| 16                | V <sub>CC</sub>  | —                  | Positive supply             |

(1) Signal Types: I = Input, O = Output, I/O = Input or Output.

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|           |                                                          | MIN                                        | MAX | UNIT        |
|-----------|----------------------------------------------------------|--------------------------------------------|-----|-------------|
| $V_{CC}$  | Supply voltage                                           | -0.5                                       | 7   | V           |
| $I_{IK}$  | Input clamp diode current                                | For $V_I < 0.5V$ or $V_I > V_{CC} + 0.5V$  |     | $\pm 20$ mA |
| $I_{OK}$  | Output clamp diode current                               | For $V_O < -0.5V$ or $V_O > V_{CC} + 0.5V$ |     | $\pm 20$ mA |
| $I_O$     | Output source or sink current per output pin             | For $V_O > -0.5V$ or $V_O < V_{CC} + 0.5V$ |     | $\pm 25$ mA |
|           | Continuous current through $V_{CC}$ or GND               |                                            |     | $\pm 50$ mA |
| $T_J$     | Junction temperature                                     |                                            |     | 150 °C      |
| $T_{stg}$ | Storage temperature range                                |                                            |     | -65 150 °C  |
|           | Lead temperature (Soldering 10s) (SOIC - Lead Tips Only) |                                            |     | 300 °C      |

- (1) Stresses beyond those listed under *absolute maximum ratings* may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under *recommended operating conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 5.2 Recommended Operating Conditions

|          |                          |                 | MIN | MAX      | UNIT |
|----------|--------------------------|-----------------|-----|----------|------|
| $V_{CC}$ | Supply voltage range     | HC types        | 2   | 6        | V    |
|          |                          | HCT types       | 4.5 | 5.5      |      |
| $V_I$    | Input voltage            |                 | 0   | $V_{CC}$ | V    |
| $V_O$    | Output voltage           |                 | 0   | $V_{CC}$ | V    |
| $t_t$    | Input rise and fall time | $V_{CC} = 2V$   |     | 1000     | ns   |
|          |                          | $V_{CC} = 4.5V$ |     | 500      |      |
|          |                          | $V_{CC} = 6V$   |     | 400      |      |
| $T_A$    | Temperature range        |                 | -55 | 125      | °C   |

### 5.3 Thermal Information

| THERMAL METRIC  |                                                       | CD74HC(T)138, CD74HC(T)238 |             |             |               | UNIT |
|-----------------|-------------------------------------------------------|----------------------------|-------------|-------------|---------------|------|
|                 |                                                       | N<br>(PDIP)                | D<br>(SOIC) | NS<br>(SOP) | PW<br>(TSSOP) |      |
|                 |                                                       | 16 Pins                    | 16 Pins     | 16 Pins     | 16 Pins       |      |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance <sup>(1)</sup> | 67                         | 73          | 64          | 108           | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics](#) application report.

## 5.4 Electrical Characteristics

| PARAMETER        |                                         | TEST CONDITIONS <sup>(1)</sup>                                           | V <sub>CC</sub> (V) | 25°C    |     |     | -40°C to 85°C |     | -55°C to 125°C |     | UNIT |
|------------------|-----------------------------------------|--------------------------------------------------------------------------|---------------------|---------|-----|-----|---------------|-----|----------------|-----|------|
|                  |                                         |                                                                          |                     | MIN     | TYP | MAX | MIN           | MAX | MIN            | MAX |      |
| HC TYPES         |                                         |                                                                          |                     |         |     |     |               |     |                |     |      |
| V <sub>IH</sub>  | High-level input voltage                |                                                                          | 2                   | 1.5     |     |     | 1.5           |     | 1.5            |     | V    |
|                  |                                         |                                                                          | 4.5                 | 3.15    |     |     | 3.15          |     | 3.15           |     | V    |
|                  |                                         |                                                                          | 6                   | 4.2     |     |     | 4.2           |     | 4.2            |     | V    |
| V <sub>IL</sub>  | Low-level input voltage                 |                                                                          | 2                   | 0.5     |     |     | 0.5           |     | 0.5            |     | V    |
|                  |                                         |                                                                          | 4.5                 | 1.35    |     |     | 1.35          |     | 1.35           |     | V    |
|                  |                                         |                                                                          | 6                   | 1.8     |     |     | 1.8           |     | 1.8            |     | V    |
| V <sub>OH</sub>  | High-level output voltage               | I <sub>OH</sub> = − 20 μA                                                | 2                   | 1.9     |     |     | 1.9           |     | 1.9            |     | V    |
|                  |                                         | I <sub>OH</sub> = − 20 μA                                                | 4.5                 | 4.4     |     |     | 4.4           |     | 4.4            |     | V    |
|                  |                                         | I <sub>OH</sub> = − 20 μA                                                | 6                   | 5.9     |     |     | 5.9           |     | 5.9            |     | V    |
|                  | High-level output voltage               | I <sub>OH</sub> = − 4 mA                                                 | 4.5                 | 3.98    |     |     | 3.84          |     | 3.7            |     | V    |
|                  |                                         | I <sub>OH</sub> = − 5.2 mA                                               | 6                   | 5.48    |     |     | 5.34          |     | 5.2            |     | V    |
| V <sub>OL</sub>  | Low-level output voltage                | I <sub>OL</sub> = 20 μA                                                  | 2                   | 0.1     |     |     | 0.1           |     | 0.1            |     | V    |
|                  |                                         | I <sub>OL</sub> = 20 μA                                                  | 4.5                 | 0.1     |     |     | 0.1           |     | 0.1            |     | V    |
|                  |                                         | I <sub>OL</sub> = 20 μA                                                  | 6                   | 0.1     |     |     | 0.1           |     | 0.1            |     | V    |
|                  | Low-level output voltage                | I <sub>OL</sub> = 4 mA                                                   | 4.5                 | 0.26    |     |     | 0.33          |     | 0.4            |     | V    |
|                  |                                         | I <sub>OL</sub> = 5.2 mA                                                 | 6                   | 0.26    |     |     | 0.33          |     | 0.4            |     | V    |
| I <sub>I</sub>   | Input leakage current                   | V <sub>I</sub> = V <sub>CC</sub> or GND                                  | 6                   | ±0.1    |     |     | ±1            |     | ±1             |     | μA   |
| I <sub>CC</sub>  | Supply current                          | V <sub>I</sub> = V <sub>CC</sub> or GND                                  | 6                   | 8       |     |     | 80            |     | 160            |     | μA   |
| HCT TYPES        |                                         |                                                                          |                     |         |     |     |               |     |                |     |      |
| V <sub>IH</sub>  | High-level input voltage                |                                                                          | 4.5 to 5.5          | 2       |     |     | 2             |     | 2              |     | V    |
| V <sub>IL</sub>  | Low-level input voltage                 |                                                                          | 4.5 to 5.5          | 0.8     |     |     | 0.8           |     | 0.8            |     | V    |
| V <sub>OH</sub>  | High-level output voltage               | I <sub>OH</sub> = − 20 μA                                                | 4.5                 | 4.4     |     |     | 4.4           |     | 4.4            |     | V    |
|                  | High-level output voltage               | I <sub>OH</sub> = − 4 mA                                                 | 4.5                 | 3.98    |     |     | 3.84          |     | 3.7            |     | V    |
| V <sub>OL</sub>  | Low-level output voltage                | I <sub>OL</sub> = 20 μA                                                  | 4.5                 | 0.1     |     |     | 0.1           |     | 0.1            |     | V    |
|                  | Low-level output voltage                | I <sub>OH</sub> = 4 mA                                                   | 4.5                 | 0.26    |     |     | 0.33          |     | 0.4            |     | V    |
| I <sub>I</sub>   | Input leakage current                   | V <sub>I</sub> = V <sub>CC</sub> and GND                                 | 5.5                 | ±0.1    |     |     | ±1            |     | ±1             |     | μA   |
| I <sub>CC</sub>  | Supply current                          | V <sub>I</sub> = V <sub>CC</sub> and GND                                 | 5.5                 | 8       |     |     | 80            |     | 160            |     | μA   |
| ΔI <sub>CC</sub> | Additional supply current per input pin | A <sub>0</sub> - A <sub>2</sub> inputs held at V <sub>CC</sub> − 2.1 V   | 4.5 to 5.5          | 100 540 |     |     | 675           |     | 735            |     | μA   |
|                  |                                         | G <sub>0</sub> and G <sub>1</sub> inputs held at V <sub>CC</sub> − 2.1 V | 4.5 to 5.5          | 100 450 |     |     | 562.5         |     | 612.5          |     | μA   |
|                  |                                         | G <sub>2</sub> input held at V <sub>CC</sub> − 2.1 V                     | 4.5 to 5.5          | 100 360 |     |     | 450           |     | 490            |     | μA   |

(1) V<sub>I</sub> = V<sub>IH</sub> or V<sub>IL</sub>, unless otherwise noted.

## 5.5 Switching Characteristics<sup>(2)</sup>

Input  $t_i = 6\text{ns}$ . (See [Parameter Measurement Information](#))

| PARAMETER       |                                                                                  | TEST CONDITIONS       | V <sub>CC</sub> (V) | 25°C              |     |     | -40°C to 85°C |     | -55°C to 125°C |     | UNIT |    |    |
|-----------------|----------------------------------------------------------------------------------|-----------------------|---------------------|-------------------|-----|-----|---------------|-----|----------------|-----|------|----|----|
|                 |                                                                                  |                       |                     | MIN               | TYP | MAX | MIN           | MAX | MIN            | MAX |      |    |    |
| HC TYPES        |                                                                                  |                       |                     |                   |     |     |               |     |                |     |      |    |    |
| t <sub>pd</sub> | Address to output                                                                | C <sub>L</sub> = 50pF | 2                   | 150               |     |     | 190           |     | 225            |     | ns   |    |    |
|                 |                                                                                  |                       | 4.5                 | 13 <sup>(3)</sup> |     |     | 30            |     | 38             |     |      | 45 |    |
|                 |                                                                                  | C <sub>L</sub> = 50pF | 6                   | 26                |     |     | 33            |     | 38             |     |      |    |    |
|                 | Strobe $\overline{G}_0$ , $\overline{G}_1$ , G <sub>2</sub> to output HC/HCT 138 | C <sub>L</sub> = 50pF | 2                   | 150               |     |     | 190           |     | 265            |     | ns   |    |    |
|                 |                                                                                  |                       | 4.5                 | 30                |     |     | 38            |     | 53             |     |      |    |    |
|                 |                                                                                  |                       | 6                   | 26                |     |     | 33            |     | 45             |     |      |    |    |
| t <sub>t</sub>  | Output transition time                                                           | C <sub>L</sub> = 50pF | 2                   | 75                |     |     | 95            |     | 110            |     | MHz  |    |    |
|                 |                                                                                  |                       | 4.5                 | 15                |     |     | 19            |     | 22             |     |      |    |    |
|                 |                                                                                  |                       | 6                   | 13                |     |     | 16            |     | 19             |     |      |    |    |
| C <sub>pd</sub> | Power dissipation capacitance <sup>(1)</sup>                                     | C <sub>L</sub> = 15pF | 5                   | 67                |     |     |               |     |                |     | pF   |    |    |
| C <sub>i</sub>  | Input capacitance                                                                |                       |                     | 10                |     |     | 10            |     | 10             |     | pF   |    |    |
| HCT TYPES       |                                                                                  |                       |                     |                   |     |     |               |     |                |     |      |    |    |
| t <sub>pd</sub> | Address to output                                                                | C <sub>L</sub> = 50pF | 4.5                 | 14 <sup>(3)</sup> |     |     | 35            |     | 44             |     | 53   |    | ns |
|                 | Strobe G <sub>2</sub> to output HC/HCT138                                        | C <sub>L</sub> = 50pF | 4.5                 |                   |     |     | 35            |     | 44             |     | 53   |    | ns |
|                 | Strobe $\overline{G}_0$ , $\overline{G}_1$ to output HC/HCT238                   | C <sub>L</sub> = 15pF | 4.5                 |                   |     |     | 40            |     | 50             |     | 60   |    | ns |
| t <sub>t</sub>  | Output transition time                                                           | C <sub>L</sub> = 15pF | 4.5                 |                   |     |     | 15            |     | 19             |     | 22   |    |    |
| C <sub>pd</sub> | Power dissipation capacitance <sup>(1)</sup>                                     | C <sub>L</sub> = 15pF | 5                   | 67                |     |     |               |     |                |     |      |    | pF |
| C <sub>i</sub>  | Input capacitance                                                                |                       |                     | 10                |     |     | 10            |     | 10             |     |      |    | pF |

(1)  $C_{PD}$  is used to determine the dynamic power consumption, per gate.

(2) For details on power calculation, see [SCAA035B](#)


(3)  $C_L = 15\text{pF}$  and  $V_{CC} = 5$

## 6 Parameter Measurement Information

Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_t < 6 \text{ ns}$ .


For clock inputs,  $f_{\max}$  is measured when the input duty cycle is 50%.

The outputs are measured one at a time with one input transition per measurement.




(1)  $C_L$  includes probe and test-fixture capacitance.

**FIG 6-1. Load Circuit for Push-Pull Outputs**




(1) The greater between  $t_{PLH}$  and  $t_{PHL}$  is the same as  $t_{pd}$ .

**FIG 6-2. Voltage Waveforms, Propagation Delays for Standard CMOS Inputs**



(1) The greater between  $t_r$  and  $t_f$  is the same as  $t_t$ .

**FIG 6-3. Voltage Waveforms, Input and Output Transition Times for Standard CMOS Inputs**



(1) The greater between  $t_{PLH}$  and  $t_{PHL}$  is the same as  $t_{pd}$ .

**FIG 6-4. Voltage Waveforms, Propagation Delays for TTL-Compatible Inputs**

## 7 Detailed Description

### 7.1 Overview

The CDx4HC(T)138 and '238 are high speed silicon gate CMOS decoders well suited to memory address decoding or data routing applications. They contain a single 3:8 decoder.


The CDx4HC(T)138 and '238 have three address select inputs ( $A_2$ ,  $A_1$ , and  $A_0$ ). The circuit functions as a normal one-of-eight decoder.

Three strobe inputs ( $G_2$ ,  $\overline{G}_1$  and  $\overline{G}_0$ ) are provided to simplify cascading and to facilitate demultiplexing. When any input strobe is active, all outputs are forced into the high state for the '138 function. When any input strobe is active, all outputs are forced into the low state for the '238 function.


The demultiplexing function is accomplished by first using the select inputs to choose the desired output, and then using one of the strobe inputs as the data input.

The outputs for the CDx4HC(T)138 are normally low when selected. The outputs for the CDxHC(T)238 are normally high when selected.

### 7.2 Functional Block Diagram



7-1. Functional Block Diagram '138



7-2. Functional Block Diagram '238

## 7.3 Device Functional Modes

表 7-1. Function Table 'HC138, 'HCT138

| INPUTS |    |    |                |                |                | OUTPUTS        |                |                |                |                |                |                |                |
|--------|----|----|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| STROBE |    |    | ADDRESS        |                |                |                |                |                |                |                |                |                |                |
| G2     | G1 | G0 | A <sub>2</sub> | A <sub>1</sub> | A <sub>0</sub> | Y <sub>0</sub> | Y <sub>1</sub> | Y <sub>2</sub> | Y <sub>3</sub> | Y <sub>4</sub> | Y <sub>5</sub> | Y <sub>6</sub> | Y <sub>7</sub> |
| X      | X  | H  | X              | X              | X              | H              | H              | H              | H              | H              | H              | H              | H              |
| L      | X  | X  | X              | X              | X              | H              | H              | H              | H              | H              | H              | H              | H              |
| X      | H  | X  | X              | X              | X              | H              | H              | H              | H              | H              | H              | H              | H              |
| H      | L  | L  | L              | L              | L              | L              | H              | H              | H              | H              | H              | H              | H              |
| H      | L  | L  | L              | L              | H              | H              | L              | H              | H              | H              | H              | H              | H              |
| H      | L  | L  | L              | H              | L              | H              | H              | L              | H              | H              | H              | H              | H              |
| H      | L  | L  | L              | H              | H              | H              | H              | H              | L              | H              | H              | H              | H              |
| H      | L  | L  | H              | L              | L              | H              | H              | H              | H              | L              | H              | H              | H              |
| H      | L  | L  | H              | L              | H              | H              | H              | H              | H              | H              | L              | H              | H              |
| H      | L  | L  | H              | H              | L              | H              | H              | H              | H              | H              | H              | L              | H              |
| H      | L  | L  | H              | H              | H              | H              | H              | H              | H              | H              | H              | H              | L              |

H = High Voltage Level, L = Low Voltage Level, X = Don't Care

表 7-2. Function Table 'HC238, 'HCT238

| INPUTS |    |    |                |                |                | OUTPUTS        |                |                |                |                |                |                |                |
|--------|----|----|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| STROBE |    |    | ADDRESS        |                |                |                |                |                |                |                |                |                |                |
| G2     | G1 | G0 | A <sub>2</sub> | A <sub>1</sub> | A <sub>0</sub> | Y <sub>0</sub> | Y <sub>1</sub> | Y <sub>2</sub> | Y <sub>3</sub> | Y <sub>4</sub> | Y <sub>5</sub> | Y <sub>6</sub> | Y <sub>7</sub> |
| X      | X  | H  | X              | X              | X              | L              | L              | L              | L              | L              | L              | L              | L              |
| L      | X  | X  | X              | X              | X              | L              | L              | L              | L              | L              | L              | L              | L              |
| X      | H  | X  | X              | X              | X              | L              | L              | L              | L              | L              | L              | L              | L              |
| H      | L  | L  | L              | L              | L              | H              | L              | L              | L              | L              | L              | L              | L              |
| H      | L  | L  | L              | L              | H              | L              | H              | L              | L              | L              | L              | L              | L              |
| H      | L  | L  | L              | H              | L              | L              | L              | H              | L              | L              | L              | L              | L              |
| H      | L  | L  | L              | H              | H              | L              | L              | L              | H              | L              | L              | L              | L              |
| H      | L  | L  | H              | L              | L              | L              | L              | L              | L              | H              | L              | L              | L              |
| H      | L  | L  | H              | L              | H              | L              | L              | L              | L              | L              | H              | L              | L              |
| H      | L  | L  | H              | H              | L              | L              | L              | L              | L              | L              | L              | H              | L              |
| H      | L  | L  | H              | H              | H              | L              | L              | L              | L              | L              | L              | L              | H              |

H = High Voltage Level, L = Low Voltage Level, X = Don't Care

## 8 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Recommended Operating Conditions*. Each  $V_{CC}$  terminal should have a good bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.

## 9 Layout

### 9.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

## 10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 10.1 Documentation Support

#### 10.1.1 Related Documentation

### 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 10.3 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

### 10.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

### 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 10.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)             |
|--------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------------|
| <a href="#">5962-8688401EA</a> | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688401EA<br>CD54HC238F3A  |
| <a href="#">CD54HC138F</a>     | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC138F                      |
| CD54HC138F.A                   | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC138F                      |
| <a href="#">CD54HC138F3A</a>   | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8406201EA<br>CD54HC138F3A       |
| CD54HC138F3A.A                 | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8406201EA<br>CD54HC138F3A       |
| <a href="#">CD54HC238F3A</a>   | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688401EA<br>CD54HC238F3A  |
| CD54HC238F3A.A                 | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8688401EA<br>CD54HC238F3A  |
| <a href="#">CD54HCT138F</a>    | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HCT138F                     |
| CD54HCT138F.A                  | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HCT138F                     |
| <a href="#">CD54HCT138F3A</a>  | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8550401EA<br>CD54HCT138F3A      |
| CD54HCT138F3A.A                | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8550401EA<br>CD54HCT138F3A      |
| <a href="#">CD54HCT238F3A</a>  | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8974501EA<br>CD54HCT238F3A |
| CD54HCT238F3A.A                | Active        | Production           | CDIP (J)   16  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8974501EA<br>CD54HCT238F3A |
| <a href="#">CD74HC138E</a>     | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC138E                      |
| CD74HC138E.A                   | Active        | Production           | PDIP (N)   16  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC138E                      |
| <a href="#">CD74HC138M</a>     | Obsolete      | Production           | SOIC (D)   16  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC138M                          |
| <a href="#">CD74HC138M96</a>   | Active        | Production           | SOIC (D)   16  | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HC138M                          |
| CD74HC138M96.A                 | Active        | Production           | SOIC (D)   16  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC138M                          |
| CD74HC138M96E4                 | Active        | Production           | null (null)    | 2500   LARGE T&R      | -           | Call TI                              | Call TI                           | -55 to 125   |                                 |
| CD74HC138M96G4                 | Active        | Production           | SOIC (D)   16  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC138M                          |
| CD74HC138M96G4.A               | Active        | Production           | SOIC (D)   16  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC138M                          |
| <a href="#">CD74HC138MT</a>    | Obsolete      | Production           | SOIC (D)   16  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC138M                          |

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">CD74HC238E</a>      | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC238E          |
| CD74HC238E.A                    | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC238E          |
| CD74HC238EE4                    | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC238E          |
| <a href="#">CD74HC238M</a>      | Obsolete      | Production           | SOIC (D)   16   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC238M              |
| <a href="#">CD74HC238M96</a>    | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| CD74HC238M96.A                  | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| CD74HC238M961G4                 | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| CD74HC238M961G4.A               | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| <a href="#">CD74HC238MT</a>     | Obsolete      | Production           | SOIC (D)   16   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC238M              |
| <a href="#">CD74HC238NSR</a>    | Active        | Production           | SOP (NS)   16   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| CD74HC238NSR.A                  | Active        | Production           | SOP (NS)   16   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC238M              |
| <a href="#">CD74HC238PW</a>     | Obsolete      | Production           | TSSOP (PW)   16 | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HJ238               |
| <a href="#">CD74HC238PWR</a>    | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HJ238               |
| CD74HC238PWR.A                  | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HJ238               |
| <a href="#">CD74HC238PWR1G4</a> | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HJ238               |
| <a href="#">CD74HC238PWT</a>    | Obsolete      | Production           | TSSOP (PW)   16 | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HJ238               |
| <a href="#">CD74HCT138E</a>     | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT138E         |
| CD74HCT138E.A                   | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT138E         |
| <a href="#">CD74HCT138M</a>     | Obsolete      | Production           | SOIC (D)   16   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HCT138M             |
| <a href="#">CD74HCT138M96</a>   | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HCT138M             |
| CD74HCT138M96.A                 | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT138M             |
| <a href="#">CD74HCT238E</a>     | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT238E         |
| CD74HCT238E.A                   | Active        | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT238E         |
| <a href="#">CD74HCT238M</a>     | Obsolete      | Production           | SOIC (D)   16   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HCT238M             |
| <a href="#">CD74HCT238M96</a>   | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HCT238M             |
| CD74HCT238M96.A                 | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT238M             |
| <a href="#">CD74HCT238PW</a>    | Obsolete      | Production           | TSSOP (PW)   16 | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HK238               |
| <a href="#">CD74HCT238PWR</a>   | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HK238               |
| CD74HCT238PWR.A                 | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HK238               |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

**(2) Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

**(3) RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

**(4) Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**(5) MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

**(6) Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54HC138, CD54HC238, CD54HCT138, CD54HCT238, CD74HC138, CD74HC238, CD74HCT138, CD74HCT238 :**

- Catalog : [CD74HC138](#), [CD74HC238](#), [CD74HCT138](#), [CD74HCT238](#)
- Automotive : [CD74HC138-Q1](#), [CD74HC138-Q1](#)
- Military : [CD54HC138](#), [CD54HC238](#), [CD54HCT138](#), [CD54HCT238](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD74HC138M96    | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC138M96G4  | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC238M96    | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC238M96    | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC238M961G4 | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC238NSR    | SOP          | NS              | 16   | 2000 | 330.0              | 16.4               | 8.1     | 10.4    | 2.5     | 12.0    | 16.0   | Q1            |
| CD74HC238PWR    | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD74HC238PWR1G4 | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD74HCT138M96   | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HCT238M96   | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HCT238PWR   | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HC138M96    | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HC138M96G4  | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HC238M96    | SOIC         | D               | 16   | 2500 | 340.5       | 336.1      | 32.0        |
| CD74HC238M96    | SOIC         | D               | 16   | 2500 | 340.5       | 336.1      | 32.0        |
| CD74HC238M961G4 | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HC238NSR    | SOP          | NS              | 16   | 2000 | 353.0       | 353.0      | 32.0        |
| CD74HC238PWR    | TSSOP        | PW              | 16   | 2000 | 353.0       | 353.0      | 32.0        |
| CD74HC238PWR1G4 | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| CD74HCT138M96   | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HCT238M96   | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HCT238PWR   | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |

**TUBE**


\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HC138E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC138E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC138E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC138E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238EE4  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC238EE4  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT138E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT138E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT138E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT138E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT238E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT238E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT238E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT238E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |



# PACKAGE OUTLINE

NS0016A

SOP - 2.00 mm max height

SOP



4220735/A 12/2021

## NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.

# EXAMPLE BOARD LAYOUT

NS0016A

SOP - 2.00 mm max height

SOP



4220735/A 12/2021

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE  
 BASED ON 0.125 mm THICK STENCIL  
 SCALE:7X

4220735/A 12/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - $\triangle C$  Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  - $\triangle D$  Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AC.

J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.



**PW0016A**

## TSSOP - 1.2 mm max height

## SMALL OUTLINE PACKAGE



1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220204/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220204/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## 重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated