


LM317 3 ピン可変レギュレータ

1 特長

- 出力電圧範囲:
 - 可変: 1.25V ~ 37V
- 出力電流: 1.5A
- ラインレギュレーション: 0.01%/V (標準値)
- 負荷レギュレーション: 0.1% (標準値)
- 内蔵短絡電流制限機能
- 熱過負荷保護機能
- 出力安全領域補償 (新チップ)
- PSRR: $C_{ADJ} = 10\mu\text{F}$ (新チップ) において 120Hz 時 80dB
- パッケージ:
 - 4 ピン SOT-223 (DCY)
 - 3 ピン TO-263 (KTT)
 - 3 ピン TO-220 (KCS、KCT) 従来型チップ

2 アプリケーション

- マルチファンクション プリンタ
- AC ドライブの電力段モジュール
- 電気メーター
- サーボドライブ制御モジュール
- 商用ネットワークとサーバーの電源



*デバイスがフィルタ コンデンサから 6 インチ以上離れている場合に必要。

†オプションで、過渡応答を改善。

†† 式 1 を参照。

$$V_{OUT} = 1.25V \times \left(1 + \frac{R_2}{R_1}\right) + I_{ADJ} \times (R_2) \quad (1)$$

代表的なアプリケーション

3 説明


LM317 は、1.25V ~ 37V の出力電圧範囲で 1.5A を超える電流を供給できる可変 3 ピン正電圧レギュレータです。本デバイスは 2 つの外付け抵抗だけで出力電圧を設定できます。このデバイスはライン レギュレーションが 0.01% (標準値)、負荷レギュレーションが 0.1% (標準値) です。LM317 は電流制限、熱過負荷保護、安全動作領域保護の各機能を内蔵しています。過負荷保護は、ADJUST ピンが接続されていない場合でも動作し続けます。

通常、デバイスが入力フィルタ コンデンサから 6 インチ以上離れていない限り、コンデンサは必要ありません。6 インチ以上離れている場合には、入力バイパス コンデンサが必要です。オプションの出力コンデンサを追加すると、過渡応答を改善できます。調整ピンをバイパスすると、非常に高いリップル除去率を達成できます。これは、標準的な 3 ピンレギュレータでは実現困難です。

パッケージ情報

部品番号	パッケージ (1)	パッケージ サイズ (2)
LM317	DCY (SOT-223、4)	6.5mm × 7mm
	KTT (TO-263、3)	10.16mm × 15.24mm
	KCS、KCT (TO-220、3) (3)	10.16mm × 4.55mm

- 詳細については、[メカニカル](#)、[パッケージ](#)、および[注文情報](#)をご覧ください。
- パッケージ サイズ (長さ × 幅) は公称値であり、該当する場合はピンも含まれます。
- 従来型チップ。



バッテリー充電器の回路



レギュレータは フローティング 状態で、入出力差動電圧のみを検出します。したがって、入出力差動電圧の最大値を超過しない限り、数百ボルトの電源がレギュレートされます。つまり、出力の短絡も回避します。

調整ピンと出力との間に固定の抵抗を接続すると、LM317 は高精度の電流レギュレータとしても使用できます。調整端子をグランドにクランプすることで電子的なシャットダウン機能を持つ電源が実現し、出力が 1.25V にプログラムされるため、ほとんどの負荷がわずかな電流しか消費しません。

Table of Contents

1 特長	1	7.4 Device Functional Modes.....	14
2 アプリケーション	1	8 Application and Implementation	15
3 説明	1	8.1 Application Information.....	15
4 Device Comparison Table	4	8.2 Typical Application.....	15
5 Pin Configuration and Functions	5	8.3 System Examples.....	17
6 Specifications	6	8.4 Power Supply Recommendations.....	23
6.1 Absolute Maximum Ratings.....	6	8.5 Layout.....	23
6.2 ESD Ratings.....	6	9 Device and Documentation Support	28
6.3 Recommended Operating Conditions.....	6	9.1 Device Support.....	28
6.4 Thermal Information (Legacy Chip).....	7	9.2 ドキュメントの更新通知を受け取る方法.....	28
6.5 Thermal Information (New Chip).....	7	9.3 サポート・リソース.....	28
6.6 Electrical Characteristics.....	8	9.4 Trademarks.....	28
6.7 Typical Characteristics.....	9	9.5 静電気放電に関する注意事項.....	28
7 Detailed Description	13	9.6 用語集.....	28
7.1 Overview.....	13	10 Revision History	29
7.2 Functional Block Diagram.....	13	11 Mechanical, Packaging, and Orderable Information	29
7.3 Feature Description.....	13		

4 Device Comparison Table

I _{OUT}	PARAMETER	LM317 (Legacy Chip)	LM317 (New Chip)	LM317-N	LM317A	LM317HV	UNIT
1.5A	Input voltage range	4.25 to 40	4.25 to 40	4.25 to 40	4.25 to 40	4.25 - 60	V
	Load regulation accuracy	1.5	1.5	1.5	1	1.5	%
	PSRR (120Hz)	64	80	80	80	65	dB
	Recommended operating temperature	0 to 125	0 to 125	0 to 125	–40 to 125	0 to 125	°C
	TO-220 (NDE) T _{JA}	23.5		23.2	23.3	23	°C/W
	TO-200 (KCT) T _{JA}	37.9		N/A	N/A		°C/W
	TO-252 T _{JA}	N/A		54	54		°C/W
	TO-263 T _{JA}	38	41	41	N/A		°C/W
	SOT-223 T _{JA}	66.8	59.6	59.6	59.6		°C/W
	TO-92 T _{JA}	N/A		186	186		°C/W
0.5A		LM317M					
	Input voltage range	3.75 to 40					V
	Load regulation accuracy	1.5					%
	PSRR (120Hz)	80					dB
	Recommended operating temperature	–40 to 125					°C
	SOT-223 T _{JA}	60.2					°C/W
	TO-252 T _{JA}	56.9					°C/W
0.1A		LM317L		LM317L-N			
	Input voltage range	3.75 to 40		4.25 to 40			V
	Load regulation accuracy	1		1.5			%
	PSRR (120Hz)	62		80			dB
	Recommended operating temperature	–40 to 125		–40 to 125			°C
	SOT-23 T _{JA}	167.8		N/A			°C/W
	SO-8 T _{JA}	N/A		165			°C/W
	DSBGA T _{JA}	N/A		290			°C/W
	TO-92 T _{JA}	N/A		180			°C/W

5 Pin Configuration and Functions




図 5-1. DCY Package, 4-Pin SOT-223 (Top View)




図 5-2. KCS or KCT Package, 3-Pin TO-220 (Top View), Legacy Chip




図 5-3. KTT Package, 3-Pin TO-263 (Top View)

Pin Functions, Metal Can Packages

NAME	PIN			I/O	DESCRIPTION
	TO-220 (Legacy Chip)	TO-263	SOT-223		
ADJUST	1	1	1	—	Output voltage adjustment pin. Connect to a resistor divider to set V_{OUT} .
INPUT	3	3	3	I	Input voltage pin for the regulator.
OUTPUT	2, TAB	2, TAB	2, TAB	O	Output voltage pin for the regulator.

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)^{(1) (2)}

	MIN	MAX	UNIT
Power dissipation	Internally limited		
Input-output voltage differential	−0.3	40	V
Storage temperature, T_{stg}	−65	150	°C
Operating virtual junction temperature, T_J (legacy chip)	−65	150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/Distributors for availability and specifications.

6.2 ESD Ratings

			VALUE		UNIT
			Legacy Chip	New Chip	
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2500	±3000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	NA	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

		MIN	MAX	UNIT
V_O	Output voltage	1.25	37	V
$V_I - V_O$	Input-to-output differential voltage	3	40	V
I_O	Output current	0.01	1.5	A
T_J	Operating virtual junction temperature	0	125	°C

6.4 Thermal Information (Legacy Chip)

THERMAL METRIC ⁽¹⁾		LM317				UNIT
		DCY (SOT-223)	KCS (TO-220)	KCT (TO-220)	KTT (TO-263)	
		4 PINS	3 PINS	3 PINS	3 PINS	
$R_{\theta(JA)}$	Junction-to-ambient thermal resistance	66.8	23.5	37.9	38.0	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	43.2	15.9	51.1	36.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	16.9	7.9	23.2	18.9	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	3.6	3.0	13.0	6.9	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	16.8	7.8	22.8	17.9	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	NA	0.1	4.2	1.1	°C/W

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics application note](#).

6.5 Thermal Information (New Chip)

THERMAL METRIC ^{(1) (2)}		LM317		UNIT
		DCY (SOT-223)	KTT (TO-263)	
		4 PINS	3 PINS	
$R_{\theta(JA)}$	Junction-to-ambient thermal resistance	59.6	41.0	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	39.3	43.6	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	8.4	23.6	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	1.8	10.4	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	8.3	22.6	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	—	0.9	°C/W

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics application note](#).
- (2) When surface-mount packages are used (SOT-223), the junction to ambient thermal resistance is reduced by increasing the PCB copper area that is thermally connected to the package. See the [Heat Sink Requirements](#) section for heat sink techniques.

6.6 Electrical Characteristics

some specifications apply over the full operating temperature range as noted; unless otherwise specified, $T_J = 25^\circ\text{C}$, $V_{IN} - V_{OUT} = 5\text{V}$, and $I_{OUT} = 10\text{mA}$ ⁽¹⁾

PARAMETER	TEST CONDITIONS ⁽¹⁾		MIN	TYP	MAX	UNIT
Reference voltage	T _J = 25°C			1.25		V
	3V ≤ (V _{IN} - V _{OUT}) ≤ 40V, 10mA ≤ I _{OUT} ≤ 1500mA, P _D ≤ 20W		1.2	1.25	1.3	
Line regulation ⁽²⁾	3V ≤ (V _{IN} - V _{OUT}) ≤ 40V ⁽⁴⁾		T _J = 25°C	0.01	0.04	%V
			(over full operating temperature range)	0.02	0.07	
Load regulation	Legacy chip	I _O = 10mA to 1500mA, C _{ADJ} = 10μF ⁽³⁾ , T _J = 25°C	V _O ≤ 5V		25	mV
			V _O ≥ 5V	0.1	0.5	%V _O
		I _O = 10mA to 1500mA, T _J = 0°C to 125°C	V _O ≤ 5V	20	70	mV
			V _O ≥ 5V	0.3	1.5	%V _O
	New chip	10mA ≤ I _{OUT} ≤ I _{MAX} ⁽⁵⁾	T _J = 25°C	0.1	0.5	
			(over full operating temperature range)	0.3	1.5	
Thermal regulation	20ms pulse			0.04	0.07	%/W
Adjustment pin current	Over full operating temperature range			50	100	μA
Adjustment pin current change	10mA ≤ I _{OUT} ≤ I _{MAX} ⁽⁴⁾ 3V ≤ (V _{IN} - V _{OUT}) ≤ 40V		Over full operating temperature range	0.2	5	μA
Temperature stability	Legacy chip	T _{MIN} ≤ T _J ≤ T _{MAX}	Over full operating temperature range	0.7		%V _O
	New chip			1%		
Minimum load current	(V _{IN} - V _{OUT}) = 40V		Over full operating temperature range	3.5	10	mA
Current limit	(V _{IN} - V _{OUT}) ≤ 15V		P _D < P _{MAX} ⁽³⁾	1.5	2.2	A
	(V _{IN} - V _{OUT}) = 40V		P _D < P _{MAX} ⁽³⁾ , T _J = 25°C	0.15	0.4	
RMS output noise, % of V _{OUT}	10Hz ≤ f ≤ 10kHz			0.003		%
Ripple rejection ratio	Legacy chip	V _{OUT} = 10V, f = 120Hz, C _{ADJ} = 0μF ⁽⁴⁾		57		dB
		V _{OUT} = 10V, f = 120Hz, C _{ADJ} = 10μF ⁽⁴⁾	62	64		
	New chip	V _{OUT} = 10V, f = 120Hz, C _{ADJ} = 0μF (over full operating temperature range)		65		
		V _{OUT} = 10V, f = 120Hz, C _{ADJ} = 10μF (over full operating temperature range)	66	80		
Long-term stability	T _J = 25°C			0.3	1	%/1k hr

- (1) For the legacy chip (unless otherwise noted), the following test conditions apply: $|V_I - V_O| = 5\text{V}$, $I_{OMAX} = 1.5\text{A}$, and $T_J = 0^\circ\text{C}$ to 125°C . Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.
- (2) For the legacy chip, line regulation is expressed as the percentage change in output voltage per 1V change at the input.
- (3) For the legacy chip, maximum power dissipation is a function of $T_{J(max)}$, $R_{\theta JA}$, and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_{J(max)} - T_A) / R_{\theta JA}$. Operating at the absolute maximum T_J of 150°C potentially affects reliability.
- (4) For the legacy chip, C_{ADJ} is connected between the ADJUST pin and GND.
- (5) For the new chip, regulation is measured at a constant junction temperature, using pulse testing with a low duty cycle. Changes in output voltage resulting from heating effects are covered under the specifications for thermal regulation.

6.7 Typical Characteristics




図 6-1. Load Regulation (Legacy Chip)




図 6-2. Load Regulation (Legacy Chip)




図 6-3. Load Regulation (New Chip)




図 6-4. Load Transient Response (Legacy Chip)




図 6-5. Load Transient Response (Legacy Chip)




図 6-6. Load Transient Response (New Chip)

6.7 Typical Characteristics (continued)




図 6-7. Line Regulation (Legacy Chip)




図 6-8. Output Voltage vs Input Voltage, $V_{OUT} = V_{REF}$ (New Chip)




図 6-9. Output Voltage vs Input Voltage, $V_{OUT} = 5V$ (New Chip)




図 6-10. Ripple Rejection vs Output Current (Legacy Chip)




図 6-11. Ripple Rejection vs Output Voltage (Legacy Chip)




図 6-12. Ripple Rejection vs Frequency (Legacy Chip)

6.7 Typical Characteristics (continued)




図 6-13. Ripple Rejection vs Output Voltage (New Chip)




図 6-14. Ripple Rejection vs Frequency (New Chip)




図 6-15. Ripple Rejection vs Output Current (New Chip)




図 6-16. Current Limit Threshold (New Chip)




図 6-17. Adjustment Current vs Temperature (New Chip)




図 6-18. Dropout Voltage vs Temperature (New Chip)

6.7 Typical Characteristics (continued)




図 6-19. Temperature Stability (New Chip)




図 6-20. Minimum Operating Current (New Chip)




図 6-21. Output Impedance vs Frequency (New Chip)




図 6-22. Line Transient Response (New Chip)


7 Detailed Description

7.1 Overview

The LM317 is an adjustable three-pin, positive-voltage regulator capable of supplying up to 1.5A over an output voltage range of 1.25V to 37V. The device requires only two external resistors to set the output voltage. The device features a typical line regulation of 0.01% and typical load regulation of 0.1%. The LM317 includes current limiting, thermal overload protection, and safe operating area protection. Overload protection remains functional even if the ADJUST pin is disconnected.

The LM317 is designed to minimize the I_{ADJUST} current and make this current constant with line and load changes. A 100μA current from the ADJUST pin represents an error term.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 NPN Darlington Output Drive

The NPN Darlington output topology provides naturally low output impedance and an output capacitor is optional. A 3V headroom is recommended ($V_I - V_O$) to support maximum current and lowest temperature.

7.3.2 Overload Block

Overcurrent and overtemperature shutdown protects the device against overload or damage from operating in excessive heat.

7.3.3 Programmable Feedback

An op amp with a 1.25V offset input at the ADJUST pin provides easy output voltage or current programming (but not both). For current regulation applications, use a single resistor whose resistance value is $1.25V / I_O$ and a power rating greater than $(1.25V)^2 / R$. For voltage regulation applications, two resistors set the output voltage.

7.4 Device Functional Modes

7.4.1 Normal Operation

The device OUTPUT pin sources current necessary to make the OUTPUT pin 1.25V greater than ADJUST pin to provide output regulation.

7.4.2 Operation With Low Input Voltage

The device requires up to 3V headroom ($V_I - V_O$) to operate in regulation. The device potentially drops out and OUTPUT voltage becomes the INPUT voltage minus the dropout voltage with less headroom.

7.4.3 Operation at Light Loads

The device passes the bias current to the OUTPUT pin. Make sure the load or feedback consumes this minimum current for regulation or the output is potentially too high. See the [Electrical Characteristics](#) table for the minimum load current needed to maintain regulation.

7.4.4 Operation In Self Protection

When an overload occurs, the device shuts down the Darlington NPN output stage or reduces the output current to prevent device damage. The device automatically resets from the overload. The output is either reduced or alternates between on and off until the overload is removed.

8 Application and Implementation

注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

8.1 Application Information

The flexibility of the LM317 allows the device to be configured to take on many different functions in DC power applications.

8.2 Typical Application




図 8-1. Adjustable Voltage Regulator

8.2.1 Design Requirements

- R1 and R2 are required to set the output voltage.
- Use C_{ADJ} to improve ripple rejection. C_{ADJ} prevents amplification of the ripple when the output voltage is adjusted higher. The impact of C_{ADJ} on the ripple rejection performance is captured in the [Electrical Characteristics](#) table.
- C_I is recommended, particularly if the regulator is not in close proximity to the power-supply filter capacitors. A 0.1 μF or 1 μF ceramic or tantalum capacitor provides sufficient bypassing for most applications, especially when adjustment and output capacitors are used.
- C_O improves transient response, but is not needed for stability.
- Protection diode D2 is recommended if C_{ADJ} is used. The diode provides a low-impedance discharge path to prevent the capacitor from discharging into the output of the regulator.
- Protection diode D1 is recommended if C_O is used. The diode provides a low-impedance discharge path to prevent the capacitor from discharging into the output of the regulator.

8.2.2 Detailed Design Procedure

V_O is calculated as shown in 式 2. I_{ADJ} is typically 50 μ A and negligible in most applications.

$$V_O = V_{REF} (1 + R_2 / R_1) + (I_{ADJ} \times R_2) \quad (2)$$

8.2.3 Application Curves




図 8-2. Line-Transient Response (Legacy Chip)




図 8-3. Line-Transient Response (Legacy Chip)




図 8-4. Line-Transient Response (New Chip)




図 8-5. Load Transient Response (New Chip)

8.3 System Examples

8.3.1 0V to 30V Regulator Circuit

Here, the voltage is determined by:

$$V_{OUT} = V_{REF} \left(1 + \frac{R_2 + R_3}{R_1} \right) - 10V \quad (3)$$

By varying the voltage at the terminal of R3 (–10V in [Figure 8-6](#)), V_{OUT} is varied from 0V to 30V. In the absence of –10V, the V_{OUT} is only regulated to the lowest value of V_{REF} by making $R_2 = 0\Omega$.




図 8-6. 0V to 30V Regulator Circuit

8.3.2 Adjustable Regulator Circuit With Improved Ripple Rejection

As shown in [Figure 8-7](#), C2 helps stabilize the voltage at the ADJUST pin, which helps reject noise. Diode D1 exists to discharge C2 in case the output is shorted to ground.




Figure 8-7. Adjustable Regulator Circuit with Improved Ripple Rejection

8.3.3 Precision Current-Limiter Circuit

This application limits the output current to I_{LIMIT} in [Figure 8-8](#).




Figure 8-8. Precision Current-Limiter Circuit

8.3.4 Tracking Preregulator Circuit

This application keeps a constant voltage across the second LM317 in the circuit of [Figure 8-9](#).




Figure 8-9. Tracking Preregulator Circuit

8.3.5 1.25V to 20V Regulator Circuit With Minimum Program Current

Because the value of V_{REF} is constant, the value of R_1 determines the amount of current that flows through R_1 and R_2 . The size of R_2 determines the IR drop from ADJUSTMENT to GND. Higher values of R_2 translate to higher V_{OUT} . 式 4, 式 5, and 図 8-10 illustrate this relationship.

$$V_{OUT} = V_{REF} \left(1 + \frac{R_2}{R_1} \right) \quad (4)$$

$$(R_1 + R_2)_{min} = Vol_{reg(min)} \quad (5)$$




図 8-10. 1.25V to 20V Regulator Circuit With Minimum Program Current

8.3.6 Battery-Charger Circuit

The series resistor limits the current output of the LM317, minimizing damage to the battery cell.

$$V_{OUT} = 1.25 \text{ V} \times \left(1 + \frac{R_2}{R_1} \right) \quad (6)$$

$$I_{OUT(short)} = \frac{1.25\text{V}}{R_S} \quad (7)$$

$$\text{Output Impedance} = R_S \times \left(1 + \frac{R_2}{R_1} \right) \quad (8)$$




図 8-11. Battery-Charger Circuit

8.3.7 50mA, Constant-Current, Battery-Charger Circuit

Use the current-limit operation mode to trickle charge a battery at a fixed current. $I_{CHG} = 1.25V \div 24\Omega$. Make sure V_I is greater than $V_{BAT} + 4.25V$. ($1.25V [V_{REF}] + 3V [\text{headroom}]$). [Figure 8-12](#) shows a diagram of a battery-charger circuit.




Figure 8-12. 50mA, Constant-Current, Battery-Charger Circuit

8.3.8 Slow Turn-On 15V Regulator Circuit

The capacitor C1, in combination with the PNP transistor, helps the circuit ([Figure 8-13](#)) to slowly start supplying voltage. In the beginning, the capacitor is not charged. Therefore, the output voltage starts at $V_{C1} + V_{BE} + 1.25V = 0V + 0.65V + 1.25V = 1.9V$. When the capacitor voltage rises, V_{OUT} rises at the same rate. When the output voltage reaches the value determined by R1 and R2, the PNP is turned off.




Figure 8-13. Slow Turn-On 15V Regulator Circuit

8.3.9 AC Voltage-Regulator Circuit

[Figure 8-14](#) shows a circuit employing two LM317 devices. These two LM317 devices regulate both the positive and negative swings of a sinusoidal AC input.




Figure 8-14. AC Voltage-Regulator Circuit

☒ 8-15. Current-Limited 6V Charger Circuit

The circuit diagram shows three LM317 regulators connected in a cascaded fashion. The input voltage V_I is applied to the INPUT of the top LM317. The OUTPUT of the top LM317 is connected to the INPUT of the middle LM317 through a $0.2\ \Omega$ resistor. The OUTPUT of the middle LM317 is connected to the INPUT of the bottom LM317 through another $0.2\ \Omega$ resistor. The ADJUST pin of each LM317 is connected to its INPUT. The OUTPUT of the bottom LM317 is connected to the base of a 2N2905 transistor through a $100\ \Omega$ resistor. The emitter of the 2N2905 transistor is connected to ground. The collector of the 2N2905 transistor is connected to the non-inverting input (+) of a TL084 op-amp. The TL084 op-amp is configured as a voltage follower, with its output connected to its inverting input (-). The output of the TL084 is connected to the ADJUST pin of the bottom LM317. A $200\ \text{pF}$ capacitor is connected between the output of the TL084 and ground. A $5\ \text{k}\Omega$ resistor is connected between the output of the bottom LM317 and ground. A $150\ \Omega$ resistor is connected between the output of the TL084 and a $1.5\ \text{k}\Omega$ resistor, which is connected to ground. A $4.5\ \text{V to } 25\ \text{V}$ source is connected to the output of the bottom LM317 through a $5\ \text{k}\Omega$ resistor.

图 8-16. Adjustable 4A Regulator Circuit

8.3.12 High-Current Adjustable Regulator Circuit

The PNP (2N2905) and NPN (2N6486) at the top of [Figure 8-17](#) allow higher currents at V_{OUT} than the LM317 provides. Meanwhile, the output voltage remains at levels determined by the ADJUST pin resistor divider of the LM317.




Figure 8-17. High-Current Adjustable Regulator Circuit

8.4 Power Supply Recommendations

The LM317 is designed to operate from an input voltage supply range between 1.25V to 37V greater than the output voltage. If the device is more than six inches from the input filter capacitors, use an input bypass capacitor of any type for stability. Make sure this capacitor is 0.1µF or greater.

8.5 Layout

8.5.1 Layout Guidelines

- Bypass the input pin to ground with a bypass capacitor.
- The optimum placement is closest to the input pin of the device and the system GND. Take care to minimize the loop area formed by the bypass-capacitor connection, the input pin, and the system GND.
- For operation at full rated load, use wide trace lengths to eliminate $I \times R$ drop and heat dissipation.

8.5.1.1 Thermal Considerations

8.5.1.1.1 Heat Sink Requirements

The LM317 (new chip) regulators have internal thermal shutdown to protect the device from overheating. Under all operating conditions, make sure the device junction temperature does not exceed the rated maximum junction temperature (T_J) of 125°C for the LM317 (new chip). A heat sink is required depending on the maximum device power dissipation and the maximum ambient temperature of the application. To determine if a heat sink is needed, 式 9 calculates the power dissipated by the regulator, P_D .

$$P_D = ((V_{IN} - V_{OUT}) \times I_L) + (V_{IN} \times I_G) \quad (9)$$

図 8-18 shows the voltage and currents that are present in the circuit.

式 10 calculates the next parameter, which is the maximum allowable temperature rise, $T_{R(MAX)}$.

$$T_{R(MAX)} = T_{J(MAX)} - T_{A(MAX)} \quad (10)$$

where:

- $T_{J(MAX)}$ is the maximum allowable junction temperature (125°C for the LM317, new chip)
- $T_{A(MAX)}$ is the maximum ambient temperature encountered in the application

Using the calculated values for $T_{R(MAX)}$ and P_D , 式 11 calculates the maximum allowable value for the junction-to-ambient thermal resistance ($R_{\theta JA}$).

$$R_{\theta JA} = (T_{R(MAX)} / P_D) \quad (11)$$




図 8-18. Power Dissipation Diagram

If the calculated maximum allowable thermal resistance is higher than the actual package rating, then no additional work is needed. If the calculated maximum allowable thermal resistance is lower than the actual package rating, correct this issue. Either reduce P_D or $T_{A(MAX)}$, or lower $R_{\theta JA}$ by adding a heat sink, or some

combination thereof. P_D is the device power dissipation, $T_{A(MAX)}$ is the maximum ambient temperature, and $R_{\theta JA}$ is the device thermal resistance.

式 12 calculates the value if a heat sink is needed.

$$\theta_{HA} \leq (R_{\theta JA} - (\theta_{CH} + R_{\theta JC})) \quad (12)$$

where:

- θ_{CH} is the thermal resistance of the contact area between the device case and the heat sink surface
- $R_{\theta JC}$ is thermal resistance from the junction of the die to the surface of the package case

When a value for θ_{HA} is calculated, select a heat sink with a value that is less than, or equal to, this number.

The θ_{HA} rating is specified numerically by the heat sink manufacturer in the catalog, or given in a curve plotting temperature rise versus power dissipation for the heat sink.

8.5.1.1.2 Heat Sinking Surface-Mount Packages

The TO-263 (KTT), SOT-223 (DCY), and TO-220 (KCS, KCT) packages use a copper plane on the PCB and the PCB as a heat sink. To optimize the heat sinking ability of the plane and PCB, solder the tab of the package to the plane.

8.5.1.1.2.1 Heatsinking the SOT-223 (DCY) Package

図 8-19 and 図 8-20 show information for the SOT-223 package. 図 8-20 assumes a $R_{\theta JA}$ of 74°C/W for 1oz. copper and 59.6°C/W for 2oz. copper (further details are in セクション 6.5) and a maximum junction temperature of 125°C. See the [AN-1028 Maximum Power Enhancement Techniques for Power Packages](#) application note for thermal enhancement techniques to be used with the SOT-223 and TO-252 packages.




図 8-19. $R_{\theta JA}$ vs Copper (2oz.) Area for the SOT-223 Package




図 8-20. Maximum Power Dissipation vs T_{AMB} for the SOT-223 Package

8.5.1.1.2.2 Heat Sinking the TO-263 (KTT) Package

Figure 8-21 shows the TO-263 measured values of $R_{\theta JA}$ for different copper area sizes using a typical PCB with 1oz. copper. This figure also shows no solder mask over the copper area used for heat sinking.

As shown in Figure 8-21, increasing the copper area beyond 1 square inch produces very little improvement. The minimum value of $R_{\theta JA}$ for the TO-263 package mounted to a PCB is 32°C/W.




Figure 8-21. $R_{\theta JA}$ vs Copper (1-oz.) Area for the TO-263 Package

As a design aid, Figure 8-22 shows the maximum allowable power dissipation compared to ambient temperature for the TO-263 device. This figure assumes $R_{\theta JA}$ is 35°C/W and the maximum junction temperature is 125°C.




Figure 8-22. Maximum Power Dissipation vs T_{AMB} for the TO-263 Package

8.5.2 Layout Examples




図 8-23. Layout Example (Legacy Chip)




図 8-24. SOT-223 Layout Example (New Chip)




図 8-25. TO-220 Layout Example (New Chip)

9 Device and Documentation Support

9.1 Device Support

9.1.1 Device Nomenclature

Device Nomenclature

PRODUCT ⁽¹⁾	V _{OUT}
LM317yyyz	yyy is the package designator. z is the package quantity designator. Devices ship with either the legacy chip (CSO: SHE) or the new chip (CSO: FFAB). The reel packaging label provides CSO information to distinguish which chip is used. Device performance for new and legacy chips is denoted throughout the data sheet.

(1) For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder at www.ti.com.

9.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、www.tij.co.jp のデバイス製品フォルダを開いてください。[通知] をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取ることができます。変更の詳細については、改訂されたドキュメントに含まれている改訂履歴をご覧ください。

9.3 サポート・リソース

テキサス・インスツルメンツ E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、各寄稿者により「現状のまま」提供されるものです。これらはテキサス・インスツルメンツの仕様を構成するものではなく、必ずしもテキサス・インスツルメンツの見解を反映したものではありません。テキサス・インスツルメンツの[使用条件](#)を参照してください。

9.4 Trademarks

テキサス・インスツルメンツ E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

9.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

9.6 用語集

テキサス・インスツルメンツ用語集

この用語集には、用語や略語の一覧および定義が記載されています。

10 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Changes from Revision Y (April 2020) to Revision Z (April 2025)	Page
• ドキュメント全体にわたって表、図、相互参照の採番方法を更新.....	1
• ドキュメントに新しいシリコン デバイスを追加.....	1
• 「代表的特性」セクションに新しいシリコン曲線を追加.....	1
• 「特長」、「アプリケーション」、「概要」セクションを変更	1
• Added <i>LM317 (New Chip)</i> column to <i>Device Comparison Table</i>	4
• Changed DCY pinout drawing and INPUT and OUTPUT description in <i>Pin Functions</i> table.....	5
• Added <i>Power dissipation</i> row to <i>Absolute Maximum Ratings</i> table.....	6
• Added new chip information to <i>ESD Ratings</i> table.....	6
• Added <i>Thermal Information (New Chip)</i> table.....	7
• Changed <i>Electrical Characteristics</i> table.....	8
• Changed ADJUST pin current discussion in second paragraph of <i>Overview</i> section.....	13
• Added effect of C_{ADJ} on ripple rejection discussion to second bullet of <i>Design Requirements</i>	15
• Added new silicon curves to <i>Application Curves</i>	16
• Deleted $-10V$ from Equation 2.....	19
• Changed <i>The NPNs</i> to <i>The PNP (2N2905) and NPN (2N6486)</i> in <i>High-Current Adjustable Regulator Circuit</i> section.....	22
• Added <i>Thermal Considerations</i> section and subsections.....	23

Changes from Revision X (September 2016) to Revision Y (April 2020)	Page
• Added <i>Device Comparison Table</i>	4
• Changed V_{IN} to I_{OUT} in <i>Load Transient Response</i> figures.....	9
• Added missing caption to second y-axis in second <i>Load Transient Response</i> figure.....	9
• Changed V_{OUT} and output impedance equations in <i>Battery-Charger Circuit</i> section.....	19

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LM317DCY	Active	Production	SOT-223 (DCY) 4	80 TUBE	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCY.A	Active	Production	SOT-223 (DCY) 4	80 TUBE	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCY.B	Active	Production	SOT-223 (DCY) 4	80 TUBE	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCY.G3	Active	Production	SOT-223 (DCY) 4	80 TUBE	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCYR	Active	Production	SOT-223 (DCY) 4	2500 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCYR.A	Active	Production	SOT-223 (DCY) 4	2500 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCYR.B	Active	Production	SOT-223 (DCY) 4	2500 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317DCYRG3	Active	Production	SOT-223 (DCY) 4	2500 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	0 to 125	L3
LM317KCS	Active	Production	TO-220 (KCS) 3	50 TUBE	Yes	SN	N/A for Pkg Type	0 to 125	LM317
LM317KCS.A	Active	Production	TO-220 (KCS) 3	50 TUBE	Yes	SN	N/A for Pkg Type	0 to 125	LM317
LM317KCS.E3	Active	Production	TO-220 (KCS) 3	50 TUBE	Yes	SN	N/A for Pkg Type	0 to 125	LM317
LM317KTTR	Active	Production	DDPAK/ TO-263 (KTT) 3	500 LARGE T&R	Yes	SN	Level-3-245C-168 HR	0 to 125	LM317
LM317KTTR.A	Active	Production	DDPAK/ TO-263 (KTT) 3	500 LARGE T&R	Yes	SN	Level-3-245C-168 HR	0 to 125	LM317
LM317KTTR.B	Active	Production	DDPAK/ TO-263 (KTT) 3	500 LARGE T&R	Yes	SN	Level-3-245C-168 HR	0 to 125	LM317
LM317KTTR.G3	Active	Production	DDPAK/ TO-263 (KTT) 3	500 LARGE T&R	Yes	SN	Level-3-245C-168 HR	0 to 125	LM317

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM317DCYR	SOT-223	DCY	4	2500	330.0	12.4	7.05	7.4	1.9	8.0	12.0	Q3
LM317DCYR	SOT-223	DCY	4	2500	330.0	12.4	6.55	7.25	1.9	8.0	12.0	Q3
LM317KTTR	DDPAK/ TO-263	KTT	3	500	330.0	24.4	10.8	16.3	5.11	16.0	24.0	Q2

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM317DCYR	SOT-223	DCY	4	2500	340.0	340.0	38.0
LM317DCYR	SOT-223	DCY	4	2500	336.0	336.0	48.0
LM317KTTR	DDPAK/TO-263	KTT	3	500	340.0	340.0	38.0


TUBE


*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
LM317DCY	DCY	SOT-223	4	80	542.9	8.6	3606	2.67
LM317DCY	DCY	SOT-223	4	80	559	8.6	500	3.6
LM317DCY.A	DCY	SOT-223	4	80	559	8.6	500	3.6
LM317DCY.A	DCY	SOT-223	4	80	542.9	8.6	3606	2.67
LM317DCY.B	DCY	SOT-223	4	80	559	8.6	500	3.6
LM317DCY.B	DCY	SOT-223	4	80	542.9	8.6	3606	2.67
LM317DCYG3	DCY	SOT-223	4	80	559	8.6	500	3.6
LM317DCYG3	DCY	SOT-223	4	80	542.9	8.6	3606	2.67
LM317KCS	KCS	TO-220	3	50	532	34.1	700	9.6
LM317KCS.A	KCS	TO-220	3	50	532	34.1	700	9.6
LM317KCSE3	KCS	TO-220	3	50	532	34.1	700	9.6

KTT (R-PSFM-G3)

PLASTIC FLANGE-MOUNT PACKAGE




4200577-3/G 01/13

- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion. Mold flash or protrusion not to exceed 0.005 (0,13) per side.
- Falls within JEDEC TO-263 variation AA, except minimum lead thickness and minimum exposed pad length.


KTT (R-PSFM-G3)

PLASTIC FLANGE-MOUNT PACKAGE




- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Publication IPC-SM-782 is recommended for alternate designs.
 - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525.
 - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.
 - F. This package is designed to be soldered to a thermal pad on the board. Refer to the Product Datasheet for specific thermal information, via requirements, and recommended thermal pad size. For thermal pad sizes larger than shown a solder mask defined pad is recommended in order to maintain the solderable pad geometry while increasing copper area.

PLASTIC SMALL-OUTLINE




DCY (R-PDSO-G4)

PLASTIC SMALL OUTLINE



- NOTES:
- All linear dimensions are in millimeters.
 - This drawing is subject to change without notice.
 - Publication IPC-7351 is recommended for alternate designs.
 - Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil recommendations. Refer to IPC 7525 for stencil design considerations.




PACKAGE OUTLINE

KCS0003B

TO-220 - 19.65 mm max height

TO-220



4222214/B 08/2018

NOTES:


1. Dimensions are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC registration TO-220.

EXAMPLE BOARD LAYOUT

KCS0003B

TO-220 - 19.65 mm max height

TO-220



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE:15X

4222214/B 08/2018

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](https://www.ti.com) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2025, Texas Instruments Incorporated

最終更新日：2025 年 10 月