

ISO723xx 高速、トリプルチャネル デジタルアイソレータ

1 特長

- 25Mbps と 150Mbps の信号速度オプション
 - 低いチャネル間の出力スキュー:
最大値 1ns
 - 低いパルス幅歪み (PWD):
最大値 2ns
 - 低ジッタ成分: 150Mbps で標準値 1ns
- 定格動作電圧で標準寿命 25 年
(「絶縁寿命予測」を参照)
- ESD 保護: 4kV
- 3.3V または 5V の電源で動作
- 3.3V から 5V への電圧レベル変換
- 高い電磁界耐性
(アプリケーションノート『ISO72x デジタルアイソレータの磁界耐性』を参照)
- 40°C ~ 125°C の動作範囲
- 安全関連認証:
 - DIN EN IEC 60747-17 (VDE 0884-17)
 - UL 1577 部品認定プログラム
 - IEC 61010-1 証明書、IEC 62368-1 証明書

2 アプリケーション

- ファクトリ オートメーション
 - Modbus
 - Profibus™
 - DeviceNet™ データバス
- コンピュータ ペリフェラル インターフェイス
- サーボ制御インターフェイス
- データ アクイジション


3 概要

ISO7230 および ISO7231 は、それぞれ複数のチャネル構成と出力イネーブル機能を備えたトリプルチャネルのデジタルアイソレータです。これらのデバイスは、テキサスインスツルメンツ独自の二酸化ケイ素 (SiO₂) 絶縁バリアで分離されたロジック入出力バッファを備えています。これらのデバイスを絶縁型電源と組み合わせて使用すると、高電圧がブロックされ、グラウンドが絶縁されます。また、データバスや他の回路で発生したノイズ電流がローカルグラウンドに入り込み、ノイズに敏感な回路に干渉または損傷を与えることを防止します。

パッケージ情報

部品番号	パッケージ (1)	本体サイズ (公称)	パッケージサイズ (2)
ISO7230C ISO7231C ISO7231M	DW (SOIC、16)	10.30mm × 7.50mm	10.30mm × 10.30mm

- 利用可能なすべてのパッケージについては、データシートの末尾にある注文情報を参照してください。
- パッケージサイズ (長さ × 幅) は公称値であり、該当する場合はピンも含まれます。



- A. VCCI および GNDI は、それぞれ入力チャネルの電源およびグラウンド接続です。
- B. VCCO および GNDO は、それぞれ出力チャネルの電源およびグラウンド接続です。

概略回路図



Table of Contents

1 特長	1	6.16 Switching Characteristics: V_{CC1} at 5-V, V_{CC2} at 3.3-V.....	10
2 アプリケーション	1	6.17 Typical Characteristics.....	11
3 概要	1	7 Parameter Measurement Information	13
4 Device Comparison Table	3	8 Detailed Description	15
5 Pin Configuration and Functions	3	8.1 Overview.....	15
6 Specifications	4	8.2 Functional Block Diagram.....	15
6.1 Absolute Maximum Ratings.....	4	8.3 Feature Description.....	16
6.2 ESD Ratings.....	4	8.4 Device Functional Modes.....	16
6.3 Thermal Information.....	4	9 Application and Implementation	17
6.4 Recommended Operating Conditions.....	4	9.1 Application Information.....	17
6.5 Power Ratings.....	5	9.2 Typical Application.....	17
6.6 Insulation Specifications.....	5	9.3 Power Supply Recommendations.....	18
6.7 Safety-Related Certifications.....	6	9.4 Layout.....	19
6.8 Safety Limiting Values.....	6	10 Device and Documentation Support	20
6.9 Electrical Characteristics: V_{CC1} and V_{CC2} at 3.3 V.....	6	10.1 Documentation Support.....	20
6.10 Electrical Characteristics: V_{CC1} and V_{CC2} at 5-V.....	7	10.2 ドキュメントの更新通知を受け取る方法.....	20
6.11 Electrical Characteristics: V_{CC1} at 3.3-V, V_{CC2} at 5-V.....	7	10.3 サポート・リソース.....	20
6.12 Electrical Characteristics: V_{CC1} at 5-V, V_{CC2} at 3.3-V.....	8	10.4 Trademarks.....	20
6.13 Switching Characteristics: V_{CC1} and V_{CC2} at 3.3-V.....	8	10.5 静電気放電に関する注意事項.....	20
6.14 Switching Characteristics: V_{CC1} and V_{CC2} at 5-V.....	9	10.6 用語集.....	20
6.15 Switching Characteristics: V_{CC1} at 3.3-V and V_{CC2} at 5-V.....	9	11 Revision History	20
		12 Mechanical, Packaging, and Orderable Information	21

4 Device Comparison Table

PRODUCT	SIGNALING RATE	INPUT THRESHOLD	CHANNEL CONFIGURATION	ISOLATION RATING
ISO7230C	25 Mbps	≈ 1.5 V (TTL) (CMOS compatible)	3/0	4000 V _{PK} , 2500 V _{RMS}
ISO7231C	25 Mbps	≈ 1.5 V (TTL) (CMOS compatible)	2/1	
ISO7231M	150 Mbps	V _{CC} /2 (CMOS)		

5 Pin Configuration and Functions




図 5-1. DW Package 16-Pin SOIC Top View

表 5-1. Pin Functions

NAME	PIN		TYPE ⁽¹⁾	DESCRIPTION
	ISO7230	ISO7231		
EN	10	—	I	Enable, channel A, B, and C
EN1	—	7	I	Enable, channel C
EN2	—	10	I	Enable, channel A and B
GND1	2, 8	2, 8	—	Ground connection for V _{CC1}
GND2	9, 15	9, 15	—	Ground connection for V _{CC2}
INA	3	3	I	Input, channel A
INB	4	4	I	Input, channel B
INC	5	12	I	Input, channel C
NC	6, 7, 11	6, 11	—	Not connected
OUTA	14	14	O	Output, channel A
OUTB	13	13	O	Output, channel B
OUTC	12	5	O	Output, channel C
V _{CC1}	1	1	—	Power supply, V _{CC1}
V _{CC2}	16	16	—	Power supply, V _{CC2}

(1) I = Input; O = Output

6 Specifications

6.1 Absolute Maximum Ratings

See⁽¹⁾

		MIN	MAX	UNIT
V_{CC}	Supply voltage ⁽²⁾ , V_{CC1} , V_{CC2}	–0.5	6	V
V_I	Voltage at INx, OUTx, ENx	–0.5	$V_{CC} + 0.5^{(3)}$	V
I_O	Output current	–15	15	mA
T_J	Maximum junction temperature		170	°C
T_{stg}	Storage temperature	–65	150	°C

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) All voltage values are with respect to network ground terminal and are peak voltage values.
- (3) Maximum voltage must not exceed 6 V.

6.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±4000	V
		Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Thermal Information

THERMAL METRIC ⁽¹⁾		ISO7230C, ISO7231C, ISO7231M	UNIT
		DW (SOIC)	
		16 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	168	°C/W
		68.6	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	33.9	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	33.5	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	14.8	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	32.9	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	n/a	°C/W

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application note.

6.4 Recommended Operating Conditions

			MIN	NOM	MAX	UNIT
V_{CC}	Supply voltage ⁽²⁾ , V_{CC1} , V_{CC2}		3.15		5.5	V
I_{OH}	High-level output current		–4			mA
I_{OL}	Low-level output current				4	mA
t_{ui}	Input pulse width ⁽¹⁾	ISO723xC	40			ns
t_{ui}	Input pulse width ⁽¹⁾	ISO723xM	6.67	5		ns
$1/t_{ui}$	Signaling rate ⁽¹⁾	ISO723xC	0	30	25	Mbps
$1/t_{ui}$	Signaling rate ⁽¹⁾	ISO723xM	0	200	150	Mbps
V_{IH}	High-level input voltage	ISO723xM	$0.7 \times V_{CC}$		V_{CC}	V
V_{IL}	Low-level input voltage	ISO723xM	0		$0.3 \times V_{CC}$	V
V_{IH}	High-level input voltage	ISO723xC	2		5.5	V

			MIN	NOM	MAX	UNIT
V _{IL}	Low-level input voltage	ISO723xC	0		0.8	V
T _A	Ambient temperature		-40	25	125	
T _J	Junction temperature				150	°C
H	External magnetic field-strength immunity per IEC 61000-4-8 and IEC 61000-4-9 certification				1000	A/m

- (1) Typical signaling rate and Input pulse width are measured at ideal conditions at 25°C.
- (2) For the 5-V operation, V_{CC1} or V_{CC2} is specified from 4.5 V to 5.5 V.
For the 3.3-V operation, V_{CC1} or V_{CC2} is specified from 3 V to 3.6 V.
For the 2.8-V operation, V_{CC1} or V_{CC2} is specified at 2.8 V.

6.5 Power Ratings

over operating free-air temperature range (unless otherwise noted)

PARAMETER		ISO7230C, ISO7231C, ISO7231M	UNIT
		DW (SOIC)	
		16 PINS	
P _D	Device power dissipation, V _{CC1} = V _{CC2} = 5.5 V, T _J = 150°C, C _L = 15 pF, D Input a 50% duty cycle, 25-Mbps square wave	220	mW

6.6 Insulation Specifications

PARAMETER		TEST CONDITIONS	VALUE	UNIT
GENERAL				
CLR	External clearance ⁽¹⁾	Shortest terminal-to-terminal distance through air	8	mm
CPG	External creepage ⁽¹⁾	Shortest terminal-to-terminal distance across the package surface	8	mm
DTI	Distance through the insulation	Minimum internal gap (internal clearance)	0.008	mm
CTI	Comparative tracking index	DIN EN 60112 (VDE 0303-11); IEC 60112	400	V
	Material group		II	
	Overvoltage category	Rated mains voltage ≤150 V _{RMS}	I-IV	
		Rated mains voltage ≤300 V _{RMS}	I-III	
		Rated mains voltage ≤400 V _{RMS}	I-II	
DIN EN IEC 60747-17 (VDE 0884-17): ⁽²⁾				
V _{IORM}	Maximum repetitive peak isolation voltage	AC voltage (bipolar)	560	V _{PK}
V _{IOTM}	Maximum transient isolation voltage	V _{TEST} = V _{IOTM} , t = 60 s (qualification); V _{TEST} = 1.2 x V _{IOTM} , t= 1 s (100% production)	4000	V _{PK}
q _{pd}	Apparent charge ⁽³⁾	Method a: After I/O safety test subgroup 2/3, V _{ini} = V _{IOTM} , t _{ini} = 60 s; V _{pd(m)} = 1.2 x V _{IORM} , t _m = 10 s	≤5	pC
		Method a: After environmental tests subgroup 1, V _{ini} = V _{IOTM} , t _{ini} = 60 s; V _{pd(m)} = 1.3 x V _{IORM} , t _m = 10 s	≤5	
		Method b: At routine test (100% production); V _{ini} = 1.2 x V _{IOTM} , t _{ini} = 1s; V _{pd(m)} = 1.5 x V _{IORM} , t _m = 1s (method b1) or V _{pd(m)} = V _{ini} , t _m = t _{ini} (method b2)	≤5	
C _{IO}	Barrier capacitance, input to output ⁽⁴⁾	V _{IO} = 0.4 x sin (2πft), f = 1 MHz	1	pF
R _{IO}	Isolation resistance, input to output ⁽⁴⁾	V _{IO} = 500 V, T _A = 25°C	>10 ¹²	Ω
		V _{IO} = 500 V, 100°C ≤ T _A ≤ 125°C	>10 ¹¹	
		V _{IO} = 500 V at T _S = 150°C	>10 ⁹	
	Pollution degree		2	
	Climatic category		40/125/21	
UL 1577				
V _{ISO}	Withstand isolation voltage	V _{TEST} = V _{ISO} = 2500 V _{RMS} , t = 60 s (qualification); V _{TEST} = 1.2 x V _{ISO} = 3000 V _{RMS} , t = 1 s (100% production)	2500	V _{RMS}

- (1) Creepage and clearance requirements should be applied according to the specific equipment isolation standards of an application.
Care should be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the

isolator on the printed-circuit board do not reduce this distance. Creepage and clearance on a printed-circuit board become equal in certain cases. Techniques such as inserting grooves and/or ribs on a printed circuit board are used to help increase these specifications.

- (2) This coupler is suitable for *basic electrical insulation* only within the maximum operating ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.
- (3) Apparent charge is electrical discharge caused by a partial discharge (pd).
- (4) All pins on each side of the barrier tied together creating a two-terminal device

6.7 Safety-Related Certifications

VDE	CSA	UL
Plan to certify according to DIN EN IEC 60747-17 (VDE 0884-17)	Plan to certify according to IEC 62368-1	Plan to certify according to UL 1577 Component Recognition Program
Certificate planned	Certificate planned	Certificate planned

6.8 Safety Limiting Values

Safety limiting⁽¹⁾ intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to overheat the die and damage the isolation barrier, potentially leading to secondary system failures.

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
I _S	Safety input, output, or supply current	R _{θJA} = 212°C/W, V _I = 5.5 V, T _J = 170°C, T _A = 25°C, see セクション 6.3				124	mA
		R _{θJA} = 212°C/W, V _I = 3.6 V, T _J = 170°C, T _A = 25°C, see セクション 6.3				190	
T _S	Safety temperature					150	°C

- (1) The safety-limiting constraint is the maximum junction temperature specified in the data sheet. The power dissipation and junction-to-air thermal impedance of the device installed in the application hardware determines the junction temperature. The assumed junction-to-air [thermal resistance](#) in the table is that of a device installed on a high-K test board for leaded surface-mount packages. The power is the recommended maximum input voltage times the current. The junction temperature is then the ambient temperature plus the power times the junction-to-air thermal resistance.

6.9 Electrical Characteristics: V_{CC1} and V_{CC2} at 3.3 V

over recommended operating conditions (unless otherwise noted)⁽¹⁾

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY CURRENT							
I _{CC1}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V	0.5	1.2	mA	
		25 Mbps		3	5		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V	4.5	7	mA	
		25 Mbps		6.5	11		
I _{CC2}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V	9	15	mA	
		25 Mbps		10	17		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V	8	12	mA	
		25 Mbps		10.5	16		
ELECTRICAL CHARACTERISTICS							
I _{OFF}	Sleep mode output current		ENx at 0 V, single channel	0		μA	
V _{OH}	High-level output voltage		I _{OH} = -4 mA, See Figure 7-1	V _{CCO} - 0.4		V	
			I _{OH} = -20 μA, See Figure 7-1	V _{CCO} - 0.1			
V _{OL}	Low-level output voltage		I _{OL} = 4 mA, See Figure 7-1	0.4		V	
			I _{OL} = 20 μA, See Figure 7-1	0.1			
V _{I(HYS)}	Input voltage hysteresis			150		mV	
I _{IH}	High-level input current		INx at V _{CC1}	10		μA	
I _{IL}	Low-level input current		INx at 0 V	-10			
C _I	Input capacitance to ground		IN at V _{CC} , V _I = 0.4 sin (2πft), f=2MHz	2		pF	
CMTI	Common-mode transient immunity		V _I = V _{CC1} or 0 V, See Figure 7-4	25	50	kV/μs	

- (1) For the 5-V operation, V_{CC1} or V_{CC2} is specified from 4.5 V to 5.5 V.
For the 3.3-V operation, V_{CC1} or V_{CC2} is specified from 3.15 V to 3.6 V.

6.10 Electrical Characteristics: V_{CC1} and V_{CC2} at 5-V

over recommended operating conditions (unless otherwise noted)⁽¹⁾

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY CURRENT							
I _{CC1}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V	1	3	mA	
		25 Mbps		7	9.5		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V	6.5	11	mA	
		25 Mbps		11	17		
I _{CC2}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V	15	22	mA	
		25 Mbps		17	24		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V	13	20	mA	
		25 Mbps		17.5	27		
ELECTRICAL CHARACTERISTICS							
I _{OFF}	Sleep mode output current		ENx at 0 V, single channel	0		μA	
V _{OH}	High-level output voltage		I _{OH} = −4 mA, See 7-1	V _{CCO} − 0.8		V	
			I _{OH} = −20 μA, See 7-1	V _{CCO} − 0.1			
V _{OL}	Low-level output voltage		I _{OL} = 4 mA, See 7-1	0.4		V	
			I _{OL} = 20 μA, See 7-1	0.1			
V _{I(HYS)}	Input voltage hysteresis			150		mV	
I _{IH}	High-level input current		INx at V _{CC1}	10		μA	
I _{IL}	Low-level input current		INx at 0 V	−10			
C _I	Input capacitance to ground		IN at V _{CC} , V _I = 0.4 sin (2πft), f=2MHz	2		pF	
CMTI	Common-mode transient immunity		V _I = V _{CC1} or 0 V, See 7-4	25	50	kV/μs	

- (1) For the 5-V operation, V_{CC1} or V_{CC2} is specified from 4.5 V to 5.5 V.
For the 3.3-V operation, V_{CC1} or V_{CC2} is specified from 3.15 V to 3.6 V.

6.11 Electrical Characteristics: V_{CC1} at 3.3-V, V_{CC2} at 5-V

over recommended operating conditions (unless otherwise noted)⁽¹⁾

PARAMETER			TEST CONDITIONS		MIN	TYP	MAX	UNIT	
SUPPLY CURRENT									
I _{CC1}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V			0.5	1.2	mA	
		25 Mbps				3	5		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V			4.5	7	mA	
		25 Mbps				6.5	11		
I _{CC2}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V			15	22	mA	
		25 Mbps				17	24		
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V			13	20	mA	
		25 Mbps				17.5	27		
ELECTRICAL CHARACTERISTICS									
I _{OFF}	Sleep mode output current		ENx at 0 V, Single channel			0		μA	
V _{OH}	High-level output voltage		I _{OH} = −4 mA, See 7-1		ISO7230	V _{CCO} − 0.4		V	
					ISO7231 (5-V side)	V _{CCO} − 0.8			
			I _{OH} = −20 μA, See 7-1			V _{CCO} − 0.1			
V _{OL}	Low-level output voltage		I _{OL} = 4 mA, See 7-1				0.4	V	
			I _{OL} = 20 μA, See 7-1				0.1		
V _{I(HYS)}	Input voltage hysteresis					150		mV	
I _{IH}	High-level input current		INx at V _{CC1}					10	μA
I _{IL}	Low-level input current		INx at 0 V			−10			
C _I	Input capacitance to ground		IN at V _{CC} , V _I = 0.4 sin (2πft), f=2MHz			2		pF	

over recommended operating conditions (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
CMTI	Common-mode transient immunity	$V_I = V_{CC1}$ or 0 V, See 7-4	25	50		kV/μs

- (1) For the 5-V operation, V_{CC1} or V_{CC2} is specified from 4.5 V to 5.5 V.
For the 3.3-V operation, V_{CC1} or V_{CC2} is specified from 3.15 V to 3.6 V.

6.12 Electrical Characteristics: V_{CC1} at 5-V, V_{CC2} at 3.3-V

over recommended operating conditions (unless otherwise noted)⁽¹⁾

PARAMETER			TEST CONDITIONS		MIN	TYP	MAX	UNIT
SUPPLY CURRENT								
I _{CC1}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V		1		3	mA
		25 Mbps			7		9.5	
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V		6.5		11	mA
		25 Mbps			11		17	
I _{CC2}	ISO7230C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN at 3 V		9		15	mA
		25 Mbps			10		17	
	ISO7231C/M	Quiescent	V _I = V _{CC1} or 0 V, all channels, no load, EN1 at 3 V, EN2 at 3 V		8		12	mA
		25 Mbps			10.5		16	
ELECTRICAL CHARACTERISTICS								
I _{OFF}	Sleep mode output current		ENx at 0 V, Single channel			0		μA
V _{OH}	High-level output voltage		I _{OH} = −4 mA, See 7-1		ISO7230	V _{CC0} − 0.4		V
					ISO7231 (5-V side)	V _{CC0} − 0.8		
			I _{OH} = −20 μA, See 7-1				V _{CC0} − 0.1	
V _{OL}	Low-level output voltage		I _{OL} = 4 mA, See 7-1			0.4		V
			I _{OL} = 20 μA, See 7-1			0.1		
V _{I(HYS)}	Input voltage hysteresis					150		mV
I _{IH}	High-level input current		INx at V _{CC1}			10		μA
I _{IL}	Low-level input current		INx at 0 V			−10		
C _I	Input capacitance to ground		IN at V _{CC} , V _I = 0.4 sin (2πft), f=2MHz			2		pF
CMTI	Common-mode transient immunity		V _I = V _{CC1} or 0 V, See 7-4			25	50	kV/μs

- (1) For the 5-V operation, V_{CC1} or V_{CC2} is specified from 4.5 V to 5.5 V.
For the 3.3-V operation, V_{CC1} or V_{CC2} is specified from 3.15 V to 3.6 V.

6.13 Switching Characteristics: V_{CC1} and V_{CC2} at 3.3-V

over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH} , t _{PHL}	Propagation delay	ISO723xC	See 7-1	25		56	ns
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}				4		
t _{pLH} , t _{pHL}	Propagation delay	ISO723xM		8		34	ns
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}			1	2		
t _{sk(pp)}	Part-to-part skew ⁽²⁾	ISO723xC			10	ns	
		ISO723xM		0	5		
t _{sk(o)}	Channel-to-channel output skew ⁽³⁾	ISO723xC		0	3	ns	
		ISO723xM		0	1		
t _r	Output signal rise time	See 7-1			2.4	ns	
t _f	Output signal fall time				2.3		

over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{PHZ}	Propagation delay, high-level-to-high-impedance output	See 7-2			15	25	ns
t _{PZH}	Propagation delay, high-impedance-to-high-level output				15	25	
t _{PLZ}	Propagation delay, low-level-to-high-impedance output				15	25	
t _{PZL}	Propagation delay, high-impedance-to-low-level output				15	25	
t _{fs}	Failsafe output delay time from input power loss	See 7-3			18		μs
t _{jlt(pp)}	Peak-to-peak eye-pattern jitter	ISO723xM	150 Mbps PRBS NRZ data input, same polarity input on all channels, See 7-5		1		ns

- (1) Also referred to as pulse skew.
- (2) t_{sk(pp)} is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.
- (3) t_{sk(o)} is the skew between specified outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical specified loads.

6.14 Switching Characteristics: V_{CC1} and V_{CC2} at 5-V

over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT	
t _{PLH} , t _{PHL}	Propagation delay	ISO723xC	See 7-1	18		42	ns	
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}				2.5			
t _{PLH} , t _{PHL}	Propagation delay	ISO723xM		8		23	ns	
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}				1	2		
t _{sk(pp)}	Part-to-part skew ⁽²⁾	ISO723xC				8	ns	
		ISO723xM			0	3		
t _{sk(o)}	Channel-to-channel output skew ⁽³⁾	ISO723xC				0	ns	
		ISO723xM			0	1		
t _r	Output signal rise time		See 7-1			2.4	ns	
t _f	Output signal fall time					2.3		
t _{PHZ}	Propagation delay, high-level-to-high-impedance output		See 7-2			15	ns	
t _{PZH}	Propagation delay, high-impedance-to-high-level output					15		25
t _{PLZ}	Propagation delay, low-level-to-high-impedance output					15		25
t _{PZL}	Propagation delay, high-impedance-to-low-level output					15		25
t _{fs}	Failsafe output delay time from input power loss		See 7-3			12	μs	
t _{jlt(pp)}	Peak-to-peak eye-pattern jitter	ISO723xM	150 Mbps PRBS NRZ data input, Same polarity input on all channels, See 7-5			1	ns	

- (1) Also referred to as pulse skew.
- (2) t_{sk(pp)} is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.
- (3) t_{sk(o)} is the skew between specified outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical specified loads.

6.15 Switching Characteristics: V_{CC1} at 3.3-V and V_{CC2} at 5-V

, over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH} , t _{PHL}	Propagation delay	ISO723xC	See 7-1	22		51	ns
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}					3	
t _{PLH} , t _{PHL}	Propagation delay	ISO723xM		8		30	
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}				1	2	

, over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_{sk(pp)}$	Part-to-part skew ⁽²⁾	ISO723xC				10	ns
		ISO723xM			0	5	
$t_{sk(o)}$	Channel-to-channel output skew ⁽³⁾	ISO723xC			0	2.5	ns
		ISO723xM			0	1	
t_r	Output signal rise time	See 7-1			2.4		ns
t_f	Output signal fall time				2.3		
t_{PHZ}	Propagation delay, high-level-to-high-impedance output	See 7-2			15	25	ns
t_{PZH}	Propagation delay, high-impedance-to-high-level output				15	25	
t_{PLZ}	Propagation delay, low-level-to-high-impedance output				15	25	
t_{PZL}	Propagation delay, high-impedance-to-low-level output				15	25	
t_{fs}	Failsafe output delay time from input power loss	See 7-3			12		μ s
$t_{jit(pp)}$	Peak-to-peak eye-pattern jitter	ISO723xM	150 Mbps PRBS NRZ data input, Same polarity input on all channels, See 7-5		1		ns

(1) Also known as pulse skew

(2) $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.

(3) $t_{sk(o)}$ is the skew between specified outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical specified loads.

6.16 Switching Characteristics: V_{CC1} at 5-V, V_{CC2} at 3.3-V

over recommended operating conditions (unless otherwise noted)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH} , t _{PHL}	Propagation delay, low-to-high-level output	ISO723xC	See 7-1	20		50	ns
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}					3	
t _{PLH} , t _{PHL}	Propagation delay, low-to-high-level output	ISO723xM		8		29	ns
PWD	Pulse-width distortion ⁽¹⁾ t _{PHL} – t _{PLH}				1	2	
t _{sk(pp)}	Part-to-part skew ⁽²⁾	ISO723xC				10	ns
		ISO723xM			0	5	
t _{sk(o)}	Channel-to-channel output skew ⁽³⁾	ISO723xC			0	2.5	ns
		ISO723xM			0	1	
t _r	Output signal rise time		See 7-1		2.4		ns
t _f	Output signal fall time				2.3		
t _{PHZ}	Propagation delay, high-level-to-high-impedance output		See 7-2		15	25	ns
t _{PZH}	Propagation delay, high-impedance-to-high-level output				15	25	
t _{PLZ}	Propagation delay, low-level-to-high-impedance output				15	25	
t _{PZL}	Propagation delay, high-impedance-to-low-level output				15	25	
t _{fs}	Failsafe output delay time from input power loss		See 7-3		18		μs
t _{jit(pp)}	Peak-to-peak eye-pattern jitter	ISO723xM	150 Mbps PRBS NRZ data input, Same polarity input on all channels, See 7-5		1		ns

(1) Also known as pulse skew

(2) $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.

(3) $t_{sk(o)}$ is the skew between specified outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical specified loads.

6.17 Typical Characteristics




FIG 6-1. ISO7230C/M RMS Supply Current vs Signaling Rate




FIG 6-2. ISO7231C/M RMS Supply Current vs Signaling Rate




FIG 6-3. Propagation Delay vs Free-Air Temperature




FIG 6-4. Input Threshold Voltage vs Free-Air Temperature




FIG 6-5. VCC1 Fail-Safe Threshold vs Free-Air Temperature




FIG 6-6. High-Level Output Current vs High-Level Output Voltage

6.17 Typical Characteristics (continued)










図 6-7. Low-Level Output Current vs Low-Level Output Voltage

7 Parameter Measurement Information




- A. The input pulse is supplied by a generator having the following characteristics: PRR $\leq$ 50 kHz, 50% duty cycle, $t_r \leq$ 3 ns, $t_f \leq$ 3 ns, $Z_O = 50 \Omega$. At the input, a 50- Ω resistor is required to terminate the Input Generator signal. The 50- Ω is not needed in actual application.
- B. $C_L = 15$ pF and includes instrumentation and fixture capacitance within $\pm 20\%$.

7-1. Switching Characteristic Test Circuit and Voltage Waveforms




- A. The input pulse is supplied by a generator having the following characteristics: PRR $\leq$ 50 kHz, 50% duty cycle, $t_r \leq$ 3 ns, $t_f \leq$ 3 ns, $Z_O = 50 \Omega$.
- B. $C_L = 15$ pF and includes instrumentation and fixture capacitance within $\pm 20\%$.

7-2. Enable/Disable Propagation Delay Time Test Circuit and Waveform




- A. The input pulse is supplied by a generator having the following characteristics: PRR ≤ 50 kHz, 50% duty cycle, $t_r \leq 3$ ns, $t_f \leq 3$ ns, $Z_O = 50 \Omega$.
- B. $C_L = 15$ pF and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 7-3. Failsafe Delay Time Test Circuit and Voltage Waveforms



- A. $C_L = 15$ pF and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 7-4. Common-Mode Transient Immunity Test Circuit



PRBS bit pattern run length is $2^{16} - 1$. Transition time is 800 ps. NRZ data input has no more than five consecutive 1s or 0s.

Figure 7-5. Peak-to-Peak Eye-Pattern Jitter Test Circuit and Voltage Waveform

8 Detailed Description

8.1 Overview

The ISO723x family of devices transmit digital data across a silicon dioxide based isolation barrier. The digital input signal (IN) of the device is sampled by a transmitter and at every data edge the transmitter sends a corresponding differential signal across the isolation barrier. When the input signal is static, the refresh logic periodically sends the necessary differential signal from the transmitter. On the other side of the isolation barrier, the receiver converts the differential signal into a single-ended signal which is output on the OUT pin through a buffer. If the receiver does not receive a data or refresh signal, the timeout logic detects the loss of signal or power from the input side and drives the output to the default level.

8.2 Functional Block Diagram




図 8-1. Conceptual Block Diagram of a Digital Isolator

8.3 Feature Description

The ISO724x-Q1 family of devices is available in multiple channel configurations and default output-state options to enable wide variety of application uses. 表 8-1 lists these device features.

表 8-1. Device Features

PRODUCT ⁽¹⁾	SIGNALING RATE	INPUT THRESHOLD	CHANNEL CONFIGURATION
ISO7240CF	25 Mbps	≈ 1.5 V (TTL)	4/0
ISO7241C	25 Mbps	≈ 1.5 V (TTL)	3/1
ISO7242C	25 Mbps	≈ 1.5 V (TTL)	2/2

8.4 Device Functional Modes

List of ISO7231C-Q1 functional modes.

表 8-2. Device Function Table ISO7231C-Q1

INPUT V_{CC}	OUTPUT V_{CC}	INPUT (IN)	OUTPUT ENABLE (EN)	OUTPUT (OUT)
PU	PU	H	H or Open	H
		L	H or Open	L
		X	L	Z
		Open	H or Open	H
PD	PU	X	H or Open	H
PD	PU	X	L	Z
X	PD	X	X	Undetermined

8.4.1 Device I/O Schematics




図 8-2. Device I/O Schematics

9 Application and Implementation

注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

9.1 Application Information

ISO723x utilize single-ended TTL or CMOS-logic switching technologies. The supply voltage range is from 3.15 V to 5.5 V for both supplies, V_{CC1} and V_{CC2} . When designing with digital isolators keep in mind that due to the single-ended design structure, digital isolators do not conform to any specific interface standard and are only intended for isolating single-ended CMOS or TTL digital signal lines. The isolator is typically placed between the data controller (that is, μ C or UART), and a data converter or a line transceiver, regardless of the interface type or standard.

9.2 Typical Application

ISO7231 combined with Texas Instruments' mixed signal micro-controller, RS-485 transceiver, transformer driver, and voltage regulator can create an isolated RS-485 system as shown in 図 9-1.





図 9-1. Isolated RS-485 Application Circuit

9.2.1 Design Requirements

Unlike optocouplers, which need external components to improve performance, provide bias, or limit current, ISO723x only needs two external bypass capacitors to operate.


9.2.2 Detailed Design Procedure




✎ 9-2. Typical ISO7231-Q1 Circuit Hook-up

9.2.3 Application Performance Plots

9.2.3.1 Insulation Characteristics Curves



✎ 9-3. Isolation Lifetime Projection



✎ 9-4. Thermal Derating Curve for Limiting Current per VDE

9.3 Power Supply Recommendations

To provide reliable operation at all data rates and supply voltages, a 0.1 μF bypass capacitor is recommended at input and output supply pins (V_{CC1} and V_{CC2}). The capacitors must be placed as close to the supply pins as possible. If only a single primary-side power supply is available in an application, isolated power can be generated for the secondary-side with the help of a transformer driver such as Texas Instruments SN6501 data

sheet. For such applications, detailed power supply design and transformer selection recommendations are available in the [SN6501 data sheet](#).

9.4 Layout

9.4.1 Layout Guidelines

A minimum of four layers is required to accomplish a low EMI PCB design (see [Figure 9-5](#)). Layer stacking must be in the following order (top-to-bottom): high-speed signal layer, ground plane, power plane and low-frequency signal layer.

- Routing the high-speed traces on the top layer avoids the use of vias (and the introduction of the inductances) and allows for clean interconnects between the isolator and the transmitter and receiver circuits of the data link.
- Placing a solid ground plane next to the high-speed signal layer establishes controlled impedance for transmission line interconnects and provides an excellent low-inductance path for the return current flow.
- Placing the power plane next to the ground plane creates additional high-frequency bypass capacitance of approximately 100pF/in².
- Routing the slower speed control signals on the bottom layer allows for greater flexibility as these signal links typically have margin to tolerate discontinuities such as vias.

If an additional supply voltage plane or signal layer is needed, add a second power/ground plane system to the stack to keep the planes symmetrical. This makes the stack mechanically stable and prevents warping. Also the power and ground plane of each power system can be placed closer together, thus increasing the high-frequency bypass capacitance significantly. For detailed layout recommendations, see Application Note [SLLA284](#), *Digital Isolator Design Guide*.

9.4.1.1 PCB Material

For digital circuit boards operating below 150 Mbps, (or rise and fall times higher than 1 ns), and trace lengths of up to 10 inches, use standard FR-4 epoxy-glass as PCB material. FR-4 (Flame Retardant 4) meets the requirements of Underwriters Laboratories UL94-V0, and is preferred over cheaper alternatives due to the lower dielectric losses at high frequencies, less moisture absorption, greater strength and stiffness, and the self-extinguishing flammability-characteristics.

9.4.2 Layout Example




Figure 9-5. Recommended Layer Stack

10 Device and Documentation Support

10.1 Documentation Support

10.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [Isolation Glossary](#), application note
- Texas Instruments, [How to use isolation to improve ESD, EFT, and Surge immunity in industrial systems](#), application note
- Texas Instruments, [Digital Isolator Design Guide](#) application report

10.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、www.tij.co.jp のデバイス製品フォルダを開いてください。[通知] をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取ることができます。変更の詳細については、改訂されたドキュメントに含まれている改訂履歴をご覧ください。

10.3 サポート・リソース

テキサス・インスツルメンツ E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、各寄稿者により「現状のまま」提供されるものです。これらはテキサス・インスツルメンツの仕様を構成するものではなく、必ずしもテキサス・インスツルメンツの見解を反映したものではありません。テキサス・インスツルメンツの[使用条件](#)を参照してください。

10.4 Trademarks

Profibus™ is a trademark of Profibus.

DeviceNet™ is a trademark of Open DeviceNet Vendors Association.

テキサス・インスツルメンツ E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

10.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

10.6 用語集

[テキサス・インスツルメンツ用語集](#) この用語集には、用語や略語の一覧および定義が記載されています。

11 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Changes from Revision L (October 2024) to Revision M (February 2025)	Page
• ドキュメント全体にわたって表、図、相互参照の採番方法を更新.....	1
• 「特長」セクションに、安全関連証明書へのリンクを追加.....	1

Changes from Revision K (October 2015) to Revision L (October 2024)	Page
• ドキュメント全体にわたって表、図、相互参照の採番方法を更新.....	1
• ドキュメント全体で VDE V 0884-11 を DIN VDE 0884-17 に更新.....	1

ドキュメント全体を通して容量性絶縁から絶縁バリアに参照を更新.....	1
Updated Thermal Characteristics, Safety Limiting Values, and Thermal Derating Curves to provide more accurate system-level thermal calculations.....	4
Updated the <i>Regulatory Information</i> table.....	6
Updated electrical and switching characteristics to match device performance.....	6
Moved the <i>Insulation Characteristics Curves</i> to the <i>Application Curves</i> section.....	18

Changes from Revision J (May 2015) to Revision K (October 2015)	Page
Added Note 1 to L(I01) and changed the MIN value From: 8.34 To 8 mm in the <i>Insulation Specifications</i> table.....	5
Added Note 1 to L(I02) and changed the MIN value From: 8.1 To 8 mm in the <i>Insulation Specifications</i> table..	5
Deleted Note 1 From the <i>Safety-Related Certifications</i> table.....	6
Changed The ground symbols on the Enable circuit in the Device I/O Schematics images.....	16

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
ISO7230CDW	Obsolete	Production	SOIC (DW) 16	-	-	Call TI	Call TI	-40 to 125	ISO7230C
ISO7230CDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230C
ISO7230CDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230C
ISO7230CDWR.B	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230C
ISO7230MDW	Obsolete	Production	SOIC (DW) 16	-	-	Call TI	Call TI	-40 to 125	ISO7230M
ISO7230MDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230M
ISO7230MDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230M
ISO7230MDWR.B	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7230M
ISO7231CDW	Obsolete	Production	SOIC (DW) 16	-	-	Call TI	Call TI	-40 to 125	ISO7231C
ISO7231CDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231C
ISO7231CDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231C
ISO7231CDWR.B	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231C
ISO7231CDWRG4	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231C
ISO7231MDW	Obsolete	Production	SOIC (DW) 16	-	-	Call TI	Call TI	-40 to 125	ISO7231M
ISO7231MDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231M
ISO7231MDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231M
ISO7231MDWR.B	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231M
ISO7231MDWRG4	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	ISO7231M

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF ISO7231C :

- Automotive : [ISO7231C-Q1](#)

NOTE: Qualified Version Definitions:


- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

TAPE AND REEL INFORMATION


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ISO7230CDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7230MDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7231CDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7231MDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ISO7230CDWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7230MDWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7231CDWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7231MDWR	SOIC	DW	16	2000	350.0	350.0	43.0

GENERIC PACKAGE VIEW


DW 16

SOIC - 2.65 mm max height


7.5 x 10.3, 1.27 mm pitch

SMALL OUTLINE INTEGRATED CIRCUIT

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4224780/A




DW0016B

PACKAGE OUTLINE

SOIC - 2.65 mm max height

SOIC



4221009/B 07/2016

NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
5. Reference JEDEC registration MS-013.

EXAMPLE BOARD LAYOUT


DW0016B

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE
SCALE:4X



SOLDER MASK DETAILS

4221009/B 07/2016

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

DW0016B

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:4X

4221009/B 07/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適したテキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されているテキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかるテキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated