

# SNx4HC374 3 ステート出力、オクタル・エッジ・トリガ D タイプ・フリップ・フロップ

## 1 特長

- 広い動作電圧範囲: 2V~6V
- 大電流 3 ステート出力により最大 15 個の LSTTL 負荷を駆動可能
- 8 個の D タイプ・フリップ・フロップをシングル・パッケージに搭載
- 読み込み時のフル・パラレル・アクセス
- 低消費電力、最大  $I_{CC}$  80 $\mu$ A
- $t_{pd} = 14$ ns (標準値)
- 5V で  $\pm 6$ mA の出力駆動能力
- 低い入力電流: 最大 1 $\mu$ A


## 2 概要

これらの 8 ビット・フリップ・フロップは、容量性負荷または比較的低インピーダンス負荷の駆動用に設計された 3 ステート出力を備えています。特に、バッファ・レジスタ、I/O ポート、双方向バス・ドライバ、作業レジスタの実装に適しています。

### 製品情報

| 部品番号        | パッケージ <sup>(1)</sup> | 本体サイズ (公称)       |
|-------------|----------------------|------------------|
| SN74HC374DW | SOIC (20)            | 12.80mm × 7.50mm |
| SN74HC374DB | SSOP (20)            | 7.20mm × 5.30mm  |
| SN74HC374N  | PDIP (20)            | 25.40mm × 6.35mm |
| SN74HC374NS | SO (20)              | 15.00mm × 5.30mm |
| SN74HC374PW | TSSOP (20)           | 6.50mm × 4.40mm  |
| SN54HC374J  | CDIP (20)            | 26.92mm × 6.92mm |
| SN54HC374FK | LCCC (20)            | 8.89mm × 8.89mm  |
| SN54HC374W  | CFP (20)             | 13.09mm × 6.92mm |

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。



機能ブロック図



## Table of Contents

|                                                           |          |                                                                  |           |
|-----------------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 特長</b> .....                                         | <b>1</b> | 7.1 Overview.....                                                | <b>8</b>  |
| <b>2 概要</b> .....                                         | <b>1</b> | 7.2 Functional Block Diagram.....                                | <b>8</b>  |
| <b>3 Revision History</b> .....                           | <b>2</b> | 7.3 Device Functional Modes.....                                 | <b>8</b>  |
| <b>4 Pin Configuration and Functions</b> .....            | <b>3</b> | <b>8 Power Supply Recommendations</b> .....                      | <b>9</b>  |
| <b>5 Specifications</b> .....                             | <b>4</b> | <b>9 Layout</b> .....                                            | <b>9</b>  |
| 5.1 Absolute Maximum Ratings.....                         | <b>4</b> | 9.1 Layout Guidelines.....                                       | <b>9</b>  |
| 5.2 Recommended Operating Conditions <sup>(1)</sup> ..... | <b>4</b> | <b>10 Device and Documentation Support</b> .....                 | <b>10</b> |
| 5.3 Thermal Information.....                              | <b>4</b> | 10.1 Documentation Support.....                                  | <b>10</b> |
| 5.4 Electrical Characteristics.....                       | <b>5</b> | 10.2 Receiving Notification of Documentation Updates..           | <b>10</b> |
| 5.5 Timing Requirements.....                              | <b>5</b> | 10.3 サポート・リソース.....                                              | <b>10</b> |
| 5.6 Switching Characteristics.....                        | <b>6</b> | 10.4 Trademarks.....                                             | <b>10</b> |
| 5.7 Switching Characteristics.....                        | <b>6</b> | 10.5 Electrostatic Discharge Caution.....                        | <b>10</b> |
| 5.8 Operating Characteristics.....                        | <b>6</b> | 10.6 Glossary.....                                               | <b>10</b> |
| <b>6 Parameter Measurement Information</b> .....          | <b>7</b> | <b>11 Mechanical, Packaging, and Orderable Information</b> ..... | <b>11</b> |
| <b>7 Detailed Description</b> .....                       | <b>8</b> |                                                                  |           |


## 3 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。


| <b>Changes from Revision F (December 2021) to Revision G (April 2022)</b>                                                                                                            | <b>Page</b> |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • Junction-to-ambient thermal resistance values increased. DW was 58 is now 109.1, DB was 70 is now 122.7, N was 69 is now 84.6, NS was 60 is now 113.4, PW was 83 is now 131.8..... | <b>4</b>    |

| <b>Changes from Revision E (August 2003) to Revision F (December 2021)</b> | <b>Page</b> |
|----------------------------------------------------------------------------|-------------|
| • 最新のデータシート規格を反映するように、文書全体の採番、書式設定、表、図、相互参照を更新.....                        | <b>1</b>    |

## 4 Pin Configuration and Functions



J, W, DB, DW, N, NS, or PW package  
20-Pin CDIP, CFP, SSOP, SOIC, PDIP, SO, or TSSOP  
Top View



FK package  
20-Pin LCCC  
Top View

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                                   | MIN                                                    | MAX | UNIT   |
|------------------|---------------------------------------------------|--------------------------------------------------------|-----|--------|
| V <sub>CC</sub>  | Supply voltage range                              | −0.5                                                   | 7   | V      |
| I <sub>IK</sub>  | Input clamp current <sup>(2)</sup>                | V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> |     | ±20 mA |
| I <sub>OK</sub>  | Output clamp current <sup>(2)</sup>               | V <sub>O</sub> < 0 or V <sub>O</sub> > V <sub>CC</sub> |     | ±20 mA |
| I <sub>O</sub>   | Continuous output current                         | V <sub>O</sub> = 0 to V <sub>CC</sub>                  |     | ±35 mA |
|                  | Continuous current through V <sub>CC</sub> or GND |                                                        |     | ±70 mA |
| T <sub>J</sub>   | Junction temperature                              |                                                        |     | 150 °C |
| T <sub>stg</sub> | Storage temperature range                         | −65                                                    | 150 | °C     |

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 5.2 Recommended Operating Conditions<sup>(1)</sup>

|                 |                                     |                         | SN54HC374 |     |                 | SN74HC374 |     |                 | UNIT |
|-----------------|-------------------------------------|-------------------------|-----------|-----|-----------------|-----------|-----|-----------------|------|
|                 |                                     |                         | MIN       | NOM | MAX             | MIN       | NOM | MAX             |      |
| V <sub>CC</sub> | Supply voltage                      |                         | 2         | 5   | 6               | 2         | 5   | 6               | V    |
| V <sub>IH</sub> | High-level input voltage            | V <sub>CC</sub> = 2 V   | 1.5       |     |                 | 1.5       |     |                 | V    |
|                 |                                     | V <sub>CC</sub> = 4.5 V | 3.15      |     |                 | 3.15      |     |                 |      |
|                 |                                     | V <sub>CC</sub> = 6 V   | 4.2       |     |                 | 4.2       |     |                 |      |
| V <sub>IL</sub> | Low-level input voltage             | V <sub>CC</sub> = 2 V   | 0.5       |     |                 | 0.5       |     |                 | V    |
|                 |                                     | V <sub>CC</sub> = 4.5 V | 1.35      |     |                 | 1.35      |     |                 |      |
|                 |                                     | V <sub>CC</sub> = 6 V   | 1.8       |     |                 | 1.8       |     |                 |      |
| V <sub>I</sub>  | Input voltage                       |                         | 0         |     | V <sub>CC</sub> | 0         |     | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                      |                         | 0         |     | V <sub>CC</sub> | 0         |     | V <sub>CC</sub> | V    |
| Δt/Δv           | Input transition rise and fall time | V <sub>CC</sub> = 2 V   | 1000      |     |                 | 1000      |     |                 | ns   |
|                 |                                     | V <sub>CC</sub> = 4.5 V | 500       |     |                 | 500       |     |                 |      |
|                 |                                     | V <sub>CC</sub> = 6 V   | 400       |     |                 | 400       |     |                 |      |
| T <sub>A</sub>  | Operating free-air temperature      |                         | −55       |     | 125             | −40       |     | 85              | °C   |

- (1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number [SCBA004](#).

### 5.3 Thermal Information

| THERMAL METRIC         |                                                       | SN74HC374 |           |          |         |            | UNIT |
|------------------------|-------------------------------------------------------|-----------|-----------|----------|---------|------------|------|
|                        |                                                       | DW (SOIC) | DB (SSOP) | N (PDIP) | NS (SO) | PW (TSSOP) |      |
|                        |                                                       | 20 PINS   | 20 PINS   | 20 PINS  | 20 PINS | 20 PINS    |      |
| R <sub>θJA</sub>       | Junction-to-ambient thermal resistance <sup>(1)</sup> | 109.1     | 122.7     | 84.6     | 113.4   | 131.8      | °C/W |
| R <sub>θJC (top)</sub> | Junction-to-case (top) thermal resistance             | 76        | 81.6      | 72.5     | 78.6    | 72.2       | °C/W |
| R <sub>θJB</sub>       | Junction-to-board thermal resistance                  | 77.6      | 77.5      | 65.3     | 78.4    | 82.8       | °C/W |
| Ψ <sub>JT</sub>        | Junction-to-top characterization parameter            | 51.5      | 46.1      | 55.3     | 47.1    | 21.5       | °C/W |
| Ψ <sub>JB</sub>        | Junction-to-board characterization parameter          | 77.1      | 77.1      | 65.2     | 78.1    | 82.4       | °C/W |

### 5.3 Thermal Information (continued)

| THERMAL METRIC       |                                              | SN74HC374 |           |          |         |            | UNIT |
|----------------------|----------------------------------------------|-----------|-----------|----------|---------|------------|------|
|                      |                                              | DW (SOIC) | DB (SSOP) | N (PDIP) | NS (SO) | PW (TSSOP) |      |
|                      |                                              | 20 PINS   | 20 PINS   | 20 PINS  | 20 PINS | 20 PINS    |      |
| $R_{\theta JC(bot)}$ | Junction-to-case (bottom) thermal resistance | N/A       | N/A       | N/A      | N/A     | N/A        | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics](#) application report.

### 5.4 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS                       |                            | $V_{CC}$   | $T_A = 25^\circ\text{C}$ |            |           | SN54HC374 |            | SN74HC374 |            | UNIT          |
|-----------|---------------------------------------|----------------------------|------------|--------------------------|------------|-----------|-----------|------------|-----------|------------|---------------|
|           |                                       |                            |            | MIN                      | TYP        | MAX       | MIN       | MAX        | MIN       | MAX        |               |
| $V_{OH}$  | $V_I = V_{IH} \text{ or } V_{IL}$     | $I_{OH} = -20 \mu\text{A}$ | 2 V        | 1.9                      | 1.998      |           | 1.9       |            | 1.9       |            | V             |
|           |                                       |                            | 4.5 V      | 4.4                      | 4.499      |           | 4.4       |            | 4.4       |            |               |
|           |                                       |                            | 6 V        | 5.9                      | 5.999      |           | 5.9       |            | 5.9       |            |               |
|           |                                       | $I_{OH} = -6 \text{ mA}$   | 4.5 V      | 3.98                     | 4.3        |           | 3.7       |            | 3.84      |            |               |
|           |                                       | $I_{OH} = -7.8 \text{ mA}$ | 6 V        | 5.48                     | 5.8        |           | 5.2       |            | 5.34      |            |               |
| $V_{OL}$  | $V_I = V_{IH} \text{ or } V_{IL}$     | $I_{OL} = 20 \mu\text{A}$  | 2 V        |                          | 0.002      | 0.1       |           | 0.1        |           | 0.1        | V             |
|           |                                       |                            | 4.5 V      |                          | 0.001      | 0.1       |           | 0.1        |           | 0.1        |               |
|           |                                       |                            | 6 V        |                          | 0.001      | 0.1       |           | 0.1        |           | 0.1        |               |
|           |                                       | $I_{OL} = 6 \text{ mA}$    | 4.5 V      |                          | 0.17       | 0.26      |           | 0.4        |           | 0.33       |               |
|           |                                       | $I_{OL} = 7.8 \text{ mA}$  | 6 V        |                          | 0.15       | 0.26      |           | 0.4        |           | 0.33       |               |
| $I_I$     | $V_I = V_{CC} \text{ or } 0$          |                            | 6 V        |                          | $\pm 0.1$  | $\pm 100$ |           | $\pm 1000$ |           | $\pm 1000$ | nA            |
| $I_{OZ}$  | $V_O = V_{CC} \text{ or } 0$          |                            | 6 V        |                          | $\pm 0.01$ | $\pm 0.5$ |           | $\pm 10$   |           | $\pm 5$    | $\mu\text{A}$ |
| $I_{CC}$  | $V_I = V_{CC} \text{ or } 0, I_O = 0$ |                            | 6 V        |                          |            | 8         |           | 160        |           | 80         | $\mu\text{A}$ |
| $C_i$     |                                       |                            | 2 V to 6 V |                          | 3          | 10        |           | 10         |           | 10         | pF            |

### 5.5 Timing Requirements

over recommended operating free-air temperature range (unless otherwise noted)

|                                                 | $V_{CC}$ | $T_A = 25^\circ\text{C}$ |     | SN54HC374 |     | SN74HC374 |     | UNIT |
|-------------------------------------------------|----------|--------------------------|-----|-----------|-----|-----------|-----|------|
|                                                 |          | MIN                      | MAX | MIN       | MAX | MIN       | MAX |      |
| $f_{\text{clock}}$ Clock frequency              | 2 V      |                          | 6   |           | 4   |           | 5   | MHz  |
|                                                 | 4.5 V    |                          | 30  |           | 20  |           | 24  |      |
|                                                 | 6 V      |                          | 35  |           | 24  |           | 28  |      |
| $t_w$ Pulse duration, CLK high or low           | 2 V      | 80                       |     | 120       |     | 100       |     | ns   |
|                                                 | 4.5 V    | 16                       |     | 24        |     | 20        |     |      |
|                                                 | 6 V      | 14                       |     | 20        |     | 17        |     |      |
| $t_{su}$ Setup time, data before CLK $\uparrow$ | 2 V      | 100                      |     | 150       |     | 125       |     | ns   |
|                                                 | 4.5 V    | 20                       |     | 30        |     | 25        |     |      |
|                                                 | 6 V      | 17                       |     | 25        |     | 21        |     |      |
| $t_h$ Hold time, data after CLK $\uparrow$      | 2 V      | 10                       |     | 13        |     | 12        |     | ns   |
|                                                 | 4.5 V    | 5                        |     | 5         |     | 5         |     |      |
|                                                 | 6 V      | 5                        |     | 5         |     | 5         |     |      |

## 5.6 Switching Characteristics

over recommended operating free-air temperature range,  $C_L = 50$  pF (unless otherwise noted) (see [Figure 6-1](#))

| PARAMETER  | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | $T_A = 25^\circ\text{C}$ |     |     | SN54HC374 |     | SN74HC374 |     | UNIT |
|------------|-----------------|----------------|----------|--------------------------|-----|-----|-----------|-----|-----------|-----|------|
|            |                 |                |          | MIN                      | TYP | MAX | MIN       | MAX | MIN       | MAX |      |
| $f_{\max}$ |                 |                | 2 V      | 6                        | 12  |     | 4         |     | 5         |     | MHz  |
|            |                 |                | 4.5 V    | 30                       | 60  |     | 20        |     | 24        |     |      |
|            |                 |                | 6 V      | 35                       | 70  |     | 24        |     | 28        |     |      |
| $t_{pd}$   | CLK             | Any Q          | 2 V      |                          | 63  | 180 |           | 270 |           | 225 | ns   |
|            |                 |                | 4.5 V    |                          | 17  | 36  |           | 54  |           | 45  |      |
|            |                 |                | 6 V      |                          | 15  | 31  |           | 46  |           | 38  |      |
| $t_{en}$   | $\overline{OE}$ | Any Q          | 2 V      |                          | 60  | 150 |           | 225 |           | 190 | ns   |
|            |                 |                | 4.5 V    |                          | 16  | 30  |           | 45  |           | 38  |      |
|            |                 |                | 6 V      |                          | 14  | 26  |           | 38  |           | 32  |      |
| $t_{dis}$  | $\overline{OE}$ | Any Q          | 2 V      |                          | 36  | 150 |           | 225 |           | 190 | ns   |
|            |                 |                | 4.5 V    |                          | 17  | 30  |           | 45  |           | 38  |      |
|            |                 |                | 6 V      |                          | 16  | 26  |           | 38  |           | 32  |      |
| $t_t$      |                 | Any Q          | 2 V      |                          | 28  | 60  |           | 90  |           | 75  | ns   |
|            |                 |                | 4.5 V    |                          | 8   | 12  |           | 18  |           | 15  |      |
|            |                 |                | 6 V      |                          | 6   | 10  |           | 15  |           | 13  |      |

## 5.7 Switching Characteristics

over recommended operating free-air temperature range,  $C_L = 150$  pF (unless otherwise noted) (see [Figure 6-1](#))


| PARAMETER  | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CC}$ | $T_A = 25^\circ\text{C}$ |     |     | SN54HC374 |     | SN74HC374 |     | UNIT |
|------------|-----------------|----------------|----------|--------------------------|-----|-----|-----------|-----|-----------|-----|------|
|            |                 |                |          | MIN                      | TYP | MAX | MIN       | MAX | MIN       | MAX |      |
| $f_{\max}$ |                 |                | 2 V      | 6                        | 12  |     |           |     | 5         |     | MHz  |
|            |                 |                | 4.5 V    | 30                       | 60  |     |           |     | 24        |     |      |
|            |                 |                | 6 V      | 35                       | 70  |     |           |     | 28        |     |      |
| $t_{pd}$   | CLK             | Any Q          | 2 V      |                          | 80  | 230 |           | 345 |           | 290 | ns   |
|            |                 |                | 4.5 V    |                          | 22  | 46  |           | 69  |           | 58  |      |
|            |                 |                | 6 V      |                          | 19  | 39  |           | 58  |           | 49  |      |
| $t_{en}$   | $\overline{OE}$ | Any Q          | 2 V      |                          | 70  | 200 |           | 300 |           | 250 | ns   |
|            |                 |                | 4.5 V    |                          | 25  | 40  |           | 60  |           | 50  |      |
|            |                 |                | 6 V      |                          | 22  | 34  |           | 51  |           | 43  |      |
| $t_t$      |                 | Any Q          | 2 V      |                          | 45  | 210 |           | 315 |           | 265 | ns   |
|            |                 |                | 4.5 V    |                          | 17  | 42  |           | 63  |           | 53  |      |
|            |                 |                | 6 V      |                          | 13  | 36  |           | 53  |           | 45  |      |

## 5.8 Operating Characteristics





$T_A = 25^\circ\text{C}$

| PARAMETER |                                             | TEST CONDITIONS | TYP | UNIT |
|-----------|---------------------------------------------|-----------------|-----|------|
| $C_{pd}$  | Power dissipation capacitance per flip-flop | No load         | 100 | pF   |

## 6 Parameter Measurement Information



| PARAMETER         |           | $R_L$        | $C_L$           | S1     | S2     |
|-------------------|-----------|--------------|-----------------|--------|--------|
| $t_{en}$          | $t_{PZH}$ | 1 k $\Omega$ | 50 pF or 150 pF | Open   | Closed |
|                   | $t_{PZL}$ |              |                 | Closed | Open   |
| $t_{dis}$         | $t_{PHZ}$ | 1 k $\Omega$ | 50 pF           | Open   | Closed |
|                   | $t_{PLZ}$ |              |                 | Closed | Open   |
| $t_{pd}$ or $t_t$ |           | --           | 50 pF or 150 pF | Open   | Open   |



- NOTES:
- $C_L$  includes probe and test-fixture capacitance.
  - Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
  - Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1$  MHz,  $Z_O = 50 \Omega$ ,  $t_r = 6$  ns,  $t_f = 6$  ns.
  - For clock inputs,  $f_{max}$  is measured when the input duty cycle is 50%.
  - The outputs are measured one at a time with one input transition per measurement.
  - $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .

**6-1. Load Circuit and Voltage Waveforms**

## 7 Detailed Description

### 7.1 Overview

These 8-bit flip-flops feature 3-state outputs designed specifically for driving highly capacitive or relatively low-impedance loads. They are particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers.


The eight flip-flops of the 'HC374 devices are edge-triggered D-type flip-flops. On the positive transition of the clock (CLK) input, the Q outputs are set to the logic levels that were set up at the data (D) inputs.

An output-enable ( $\overline{OE}$ ) input places the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines without interface or pullup components.

$\overline{OE}$  does not affect the internal operations of the flip-flops. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

### 7.2 Functional Block Diagram



### 7.3 Device Functional Modes

表 7-1. Function Table  
(each flip-flop)

| INPUTS          |            |   | OUTPUT |
|-----------------|------------|---|--------|
| $\overline{OE}$ | CLK        | D | Q      |
| L               | $\uparrow$ | H | H      |
| L               | $\uparrow$ | L | L      |
| L               | H or L     | X | $Q_0$  |
| H               | X          | X | Z      |



## 8 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Recommended Operating Conditions*. Each  $V_{CC}$  terminal should have a good bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.

## 9 Layout

### 9.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

## 10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 10.1 Documentation Support

#### 10.1.1 Related Documentation

### 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 10.3 サポート・リソース

[TI E2E™ サポート・フォーラム](#)は、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

### 10.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

### 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 10.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                |
|----------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|------------------------------------|
| <a href="#">5962-8407101VRA</a>  | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8407101VR<br>A<br>SNV54HC374J |
| 5962-8407101VRA.A                | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8407101VR<br>A<br>SNV54HC374J |
| <a href="#">5962-8407101VSA</a>  | Active        | Production           | CFP (W)   20   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8407101VS<br>A<br>SNV54HC374W |
| 5962-8407101VSA.A                | Active        | Production           | CFP (W)   20   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8407101VS<br>A<br>SNV54HC374W |
| <a href="#">84071012A</a>        | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 84071012A<br>SNJ54HC<br>374FK      |
| <a href="#">8407101RA</a>        | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101RA<br>SNJ54HC374J           |
| <a href="#">8407101SA</a>        | Active        | Production           | CFP (W)   20   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101SA<br>SNJ54HC374W           |
| <a href="#">JM38510/65602BRA</a> | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65602BRA               |
| JM38510/65602BRA.A               | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65602BRA               |
| <a href="#">M38510/65602BRA</a>  | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | JM38510/<br>65602BRA               |
| <a href="#">SN54HC374J</a>       | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54HC374J                         |
| SN54HC374J.A                     | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54HC374J                         |
| <a href="#">SN74HC374DBR</a>     | Active        | Production           | SSOP (DB)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                              |
| SN74HC374DBR.A                   | Active        | Production           | SSOP (DB)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                              |
| SN74HC374DBR.B                   | Active        | Production           | SSOP (DB)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                              |
| <a href="#">SN74HC374DW</a>      | Obsolete      | Production           | SOIC (DW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | HC374                              |
| <a href="#">SN74HC374DWR</a>     | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                              |
| SN74HC374DWR.A                   | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                              |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)           |
|------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-------------------------------|
| SN74HC374DWR.B               | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| SN74HC374DWRG4               | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| <a href="#">SN74HC374N</a>   | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC374N                    |
| SN74HC374N.A                 | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC374N                    |
| SN74HC374N.B                 | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC374N                    |
| SN74HC374NE4                 | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74HC374N                    |
| <a href="#">SN74HC374NSR</a> | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| SN74HC374NSR.A               | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| <a href="#">SN74HC374PWR</a> | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| SN74HC374PWR.A               | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| SN74HC374PWR.B               | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | HC374                         |
| <a href="#">SN74HC374PWT</a> | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | HC374                         |
| <a href="#">SNJ54HC374FK</a> | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 84071012A<br>SNJ54HC<br>374FK |
| SNJ54HC374FK.A               | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 84071012A<br>SNJ54HC<br>374FK |
| <a href="#">SNJ54HC374J</a>  | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101RA<br>SNJ54HC374J      |
| SNJ54HC374J.A                | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101RA<br>SNJ54HC374J      |
| <a href="#">SNJ54HC374W</a>  | Active        | Production           | CFP (W)   20    | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101SA<br>SNJ54HC374W      |
| SNJ54HC374W.A                | Active        | Production           | CFP (W)   20    | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8407101SA<br>SNJ54HC374W      |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**OTHER QUALIFIED VERSIONS OF SN54HC374, SN54HC374-SP, SN74HC374 :**

- Catalog : [SN74HC374](#), [SN54HC374](#)
- Military : [SN54HC374](#)
- Space : [SN54HC374-SP](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications
- Space - Radiation tolerant, ceramic packaging and qualified for use in Space-based application


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74HC374DBR | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74HC374DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.9    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74HC374NSR | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74HC374PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |


## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal



| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74HC374DBR | SSOP         | DB              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74HC374DWR | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74HC374NSR | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74HC374PWR | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |



**TUBE**


\*All dimensions are nominal

| Device            | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-8407101VSA   | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| 5962-8407101VSA.A | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| 84071012A         | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| 8407101SA         | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SN74HC374N        | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC374N.A      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC374N.B      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74HC374NE4      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SNJ54HC374FK      | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ54HC374FK.A    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ54HC374W       | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SNJ54HC374W.A     | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |



4214851/B 08/2019

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT



DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4214851/B 08/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



| DIM \ PINS ** | 14    | 16    | 20    | 24    |
|---------------|-------|-------|-------|-------|
| A MAX         | 10,50 | 10,50 | 12,90 | 15,30 |
| A MIN         | 9,90  | 9,90  | 12,30 | 14,70 |


4040062/C 03/03

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.


J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| DIM \ PINS ** | 14                     | 16                     | 18                     | 20                     |
|---------------|------------------------|------------------------|------------------------|------------------------|
| A             | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX         | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN         | —                      | —                      | —                      | —                      |
| C MAX         | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN         | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## GENERIC PACKAGE VIEW


**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.




4229370VA\


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |





14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.





4220724/A 05/2016

## NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

# EXAMPLE BOARD LAYOUT



DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X


4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



W (R-GDFP-F20)

CERAMIC DUAL FLATPACK



## NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within Mil-Std 1835 GDFP2-F20



4220206/A 02/2017

## NOTES:


- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
- This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
- This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## 重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated