

SN74AXCH8T245 構成可能な電圧変換、TRI-STATE出力、バス・ホールド回路を搭載した8ビット・デュアル電源バス・トランシーバ

1 特長

- 認定済みの完全に構成可能なデュアル・レール設計により、各ポートは0.65V～3.6Vの範囲の電源電圧で動作可能
- 動作温度範囲: -40°C～+125°C
- データ入力時のバス・ホールドにより、外部のプルアップまたはプルダウン抵抗が不要
- 複数の方向制御ピンにより、昇圧と降圧の変換を同時に実行
- 最高380Mbpsをサポート（1.8Vから3.3Vへの変換時）
- V_{CC}絶縁機能により、電源オフ時に両方のバスを実質的に絶縁
- 部分的パワーダウン・モードにより、電源オフ時にバックフロー電流を制限
- SN74AVCH8T245および74AVCH8T245レベル・シフタと互換
- JESD 78、Class II準拠で100mA超のラッチアップ性能
- JESD 22を超えるESD保護
 - 人体モデルで8000V
 - 荷電デバイス・モデルで1000V

2 アプリケーション

- エンタープライズおよび通信
- ワイヤレス・インフラ
- ビルディング・オートメーション
- データ・センター向けスイッチ
- エンタープライズ用ソリッド・ステート・ドライバ
- ラック・サーバー
- EPOS

3 概要

SN74AXCH8T245デバイスは、8ビットの非反転バス・トランシーバで、最新の電圧ノード(0.7V、0.8V、0.9V)で動作しているデバイスと、業界標準の電圧ノード(1.8V、2.5V、3.3V)で動作しているデバイスとの間で、電圧レベル不一致の問題を双方向に解決できます。

このデバイスは、2つの独立した電源レール(V_{CCA}とV_{CCB})を使用して動作します。データ・ピンA1～A8はV_{CCA}に追従し、データ・ピンB1～B8はV_{CCB}に追従するよう設計されています。どちらの電源レールも0.65V～3.6Vの任意の電圧で動作します。また、SN74AXCH8T245は単一電源システムとも互換性があります。

SN74AXCH8T245デバイスは、データ・バス間の非同期通信用に設計されています。このデバイスは、方向制御(DIR1およびDIR2)入力の論理レベルに応じて、AバスからBバス、またはBバスからAバスにデータを転送します。出力イネーブル($\overline{OE}$)入力を使用すると、出力をディセーブルにして、バスを実質的に絶縁できます。

SN74AXCH8T245デバイスは、制御ピン(DIRおよび $\overline{OE}$)がV_{CCA}を基準とするよう設計されています。


アクティブなバス・ホールド回路により、使用されていない、または駆動されていないピンは、有効なロジック状態に保持されます。バス・ホールド回路と、プルアップまたはプルダウン抵抗との併用は推奨しません。V_{CCA}またはV_{CCB}に電源が存在する場合、バス・ホールド回路は対応するすべてのAおよびBポートについて、方向制御や出力イネーブルとは独立に、常時アクティブに維持されます。

製品情報⁽¹⁾

型番	パッケージ	本体サイズ(公称)
SN74AXCH8T245PW	TSSOP (24)	7.80mm×4.40mm
SN74AXCH8T245RHL	VQFN (24)	5.50mm×3.50mm

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。

代表的なアプリケーションの回路図



目次

1	特長	1	8	Parameter Measurement Information	18
2	アプリケーション	1	9	Detailed Description	20
3	概要	1	9.1	Overview	20
4	改訂履歴	2	9.2	Functional Block Diagram	20
5	概要 (続き)	2	9.3	Feature Description	21
6	Pin Configuration and Functions	3	9.4	Device Functional Modes	21
7	Specifications	4	10	Application and Implementation	22
7.1	Absolute Maximum Ratings	4	10.1	Application Information	22
7.2	ESD Ratings	4	10.2	Typical Application	22
7.3	Recommended Operating Conditions	5	11	Power Supply Recommendations	24
7.4	Thermal Information	5	12	Layout	24
7.5	Electrical Characteristics	6	12.1	Layout Guidelines	24
7.6	Switching Characteristics, $V_{CCA} = 0.7\text{ V}$	8	12.2	Layout Example	24
7.7	Switching Characteristics, $V_{CCA} = 0.8\text{ V}$	9	13	デバイスおよびドキュメントのサポート	25
7.8	Switching Characteristics, $V_{CCA} = 0.9\text{ V}$	10	13.1	ドキュメントのサポート	25
7.9	Switching Characteristics, $V_{CCA} = 1.2\text{ V}$	11	13.2	ドキュメントの更新通知を受け取る方法	25
7.10	Switching Characteristics, $V_{CCA} = 1.5\text{ V}$	12	13.3	コミュニティ・リソース	25
7.11	Switching Characteristics, $V_{CCA} = 1.8\text{ V}$	13	13.4	商標	25
7.12	Switching Characteristics, $V_{CCA} = 2.5\text{ V}$	14	13.5	静電気放電に関する注意事項	25
7.13	Switching Characteristics, $V_{CCA} = 3.3\text{ V}$	15	13.6	Glossary	25
7.14	Operating Characteristics: $T_A = 25^\circ\text{C}$	16	14	メカニカル、パッケージ、および注文情報	26

4 改訂履歴

から変更 Original (August 2018) to Revision A

Page



• 「製品情報」表に RHL パッケージを 追加	1
• Added RHL package pinout	3
• Added RHL package to Thermal Information table	5

5 概要 (続き)

このデバイスは、 I_{off} を使用する部分的パワーダウン・アプリケーション用に完全に動作が規定されています。 I_{off} 回路は、デバイスの電源がオフになったとき、出力をディセーブルにします。これによってデバイスへの電流の逆流が抑止され、デバイスが損傷から保護されます。

V_{CC} 絶縁機能により、いずれかの V_{CC} 入力電圧が100mV未満になると、すべてのレベル・シフト出力がディセーブルされ、高インピーダンス状態になります。電源投入時または切断時にレベル・シフトI/Oが高インピーダンス状態であることを保証するため、 $\overline{OE}$ はプルアップ抵抗を経由して V_{CCA} に接続する必要があります。この抵抗の最小値は、ドライバの電流シンク能力によって決まります。

6 Pin Configuration and Functions



(1) PAD - may be grounded (recommended) or left floating.

Pin Functions

PIN		I/O	DESCRIPTION
NAME	PW, RHL		
A1	3	I/O	Input/output A1. Referenced to V_{CCA} .
A2	4	I/O	Input/output A2. Referenced to V_{CCA} .
A3	5	I/O	Input/output A3. Referenced to V_{CCA} .
A4	6	I/O	Input/output A4. Referenced to V_{CCA} .
A5	7	I/O	Input/output A5. Referenced to V_{CCA} .
A6	8	I/O	Input/output A6. Referenced to V_{CCA} .
A7	9	I/O	Input/output A7. Referenced to V_{CCA} .
A8	10	I/O	Input/output A8. Referenced to V_{CCA} .
B1	21	I/O	Input/output B1. Referenced to V_{CCB} .
B2	20	I/O	Input/output B2. Referenced to V_{CCB} .
B3	19	I/O	Input/output B3. Referenced to V_{CCB} .
B4	18	I/O	Input/output B4. Referenced to V_{CCB} .
B5	17	I/O	Input/output B5. Referenced to V_{CCB} .
B6	16	I/O	Input/output B6. Referenced to V_{CCB} .
B7	15	I/O	Input/output B7. Referenced to V_{CCB} .
B8	14	I/O	Input/output B8. Referenced to V_{CCB} .
DIR1	2	I	Direction-control signal. Referenced to V_{CCA} .
DIR2	11	I	Direction-control signal. Referenced to V_{CCA} . See Multiple Direction Control Pins for additional details. Tie to GND to maintain backwards compatibility with the SN74AVCH8T245 device.
GND	12	—	Ground
	13	—	Ground
$\overline{OE}$	22	I	Output Enable. Pull to GND to enable all outputs. Pull to V_{CCA} to place all outputs in high-impedance mode. Referenced to V_{CCA} .
V_{CCA}	1	—	A-port supply voltage. $0.65\text{ V} \leq V_{CCA} \leq 3.6\text{ V}$
V_{CCB}	23	—	B-port supply voltage. $0.65\text{ V} \leq V_{CCB} \leq 3.6\text{ V}$
	24	—	B-port supply voltage. $0.65\text{ V} \leq V_{CCB} \leq 3.6\text{ V}$

7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
Supply voltage, V_{CCA}		−0.5	4.2	V
Supply voltage, V_{CCB}		−0.5	4.2	V
Input voltage, V_I ⁽²⁾	I/O ports (A port)	−0.5	4.2	V
	I/O ports (B port)	−0.5	4.2	
	Control inputs	−0.5	4.2	
Voltage applied to any output in the high-impedance or power-off state, V_O ⁽²⁾	A port	−0.5	4.2	V
	B port	−0.5	4.2	
Voltage applied to any output in the high or low state, V_O ^{(2) (3)}	A port	−0.5	$V_{CCA} + 0.2$	V
	B port	−0.5	$V_{CCB} + 0.2$	
Input clamp current, I_{IK}	$V_I < 0$	−50		mA
Output clamp current, I_{OK}	$V_O < 0$	−50		mA
Continuous output current, I_O		−50	50	mA
Continuous current through V_{CCA} , V_{CCB} , or GND		−100	100	mA
Junction Temperature, T_J			150	°C
Storage temperature, T_{stg}		−65	150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input voltage and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) The output positive-voltage rating may be exceeded up to 4.2 V maximum if the output current rating is observed.

7.2 ESD Ratings

		VALUE	UNIT
$V_{(ESD)}$ Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±8000	V
	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±1000	

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾⁽²⁾⁽³⁾

			MIN	MAX	UNIT
V _{CCA}	Supply voltage		0.65	3.6	V
V _{CCB}	Supply voltage		0.65	3.6	V
V _{IH}	High-level input voltage	Data inputs	V _{CCI} = 0.65 V - 0.75 V	V _{CCI} × 0.70	V
			V _{CCI} = 0.76 V - 1 V	V _{CCI} × 0.70	
			V _{CCI} = 1.1 V - 1.95 V	V _{CCI} × 0.65	
			V _{CCI} = 2.3 V - 2.7 V	1.6	
			V _{CCI} = 3 V - 3.6 V	2	
	Control inputs (DIR, $\overline{\text{OE}}$) Referenced to V _{CCA}		V _{CCA} = 0.65 V - 0.75 V	V _{CCA} × 0.70	
			V _{CCA} = 0.76 V - 1 V	V _{CCA} × 0.70	
			V _{CCA} = 1.1 V - 1.95 V	V _{CCA} × 0.65	
			V _{CCA} = 2.3 V - 2.7 V	1.6	
			V _{CCA} = 3 V - 3.6 V	2	
V _{IL}	Low-level input voltage	Data inputs	V _{CCI} = 0.65 V - 0.75 V	V _{CCI} × 0.30	V
			V _{CCI} = 0.76 V - 1 V	V _{CCI} × 0.30	
			V _{CCI} = 1.1 V - 1.95 V	V _{CCI} × 0.35	
			V _{CCI} = 2.3 V - 2.7 V	0.7	
			V _{CCI} = 3 V - 3.6 V	0.8	
	Control inputs (DIR, $\overline{\text{OE}}$) Referenced to V _{CCA}		V _{CCA} = 0.65 V - 0.75 V	V _{CCA} × 0.30	
			V _{CCA} = 0.76 V - 1 V	V _{CCA} × 0.30	
			V _{CCA} = 1.1 V - 1.95 V	V _{CCA} × 0.35	
			V _{CCA} = 2.3 V - 2.7 V	0.7	
			V _{CCA} = 3 V - 3.6 V	0.8	
V _I	Input voltage ⁽³⁾		0	3.6	V
V _O	Output voltage	Active state	0	V _{CCO} ⁽²⁾	V
		Tri-state	0	3.6	
Δt/Δv	Input transition rise or fall rate			10	ns/V
T _A	Operating free-air temperature		–40	125	°C

(1) V_{CCI} is the V_{CC} associated with the input port.

(2) V_{CCO} is the V_{CC} associated with the output port.

(3) All unused data inputs of the device must be held at V_{CCI} or GND to ensure proper device operation. See the [Implications of Slow or Floating CMOS Inputs](#) application report.

7.4 Thermal Information

THERMAL METRIC ⁽¹⁾		SN74AXCH8T245		UNIT
		PW (TSSOP)	RHL (VQFN)	
		24 PINS	24 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	101.7	35	°C/W
R _{θJC(top)}	Junction-to-case (top) thermal resistance	45.4	39.9	°C/W
R _{θJB}	Junction-to-board thermal resistance	56.9	13.8	°C/W
ψ _{JT}	Junction-to-top characterization parameter	7.0	0.3	°C/W
ψ _{JB}	Junction-to-board characterization parameter	56.4	13.8	°C/W
R _{θJC(bot)}	Junction-to-case (bottom) thermal resistance	N/A	1.4	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

7.5 Electrical Characteristics

 Over recommended operating free-air temperature range (unless otherwise noted)⁽¹⁾

PARAMETER	TEST CONDITIONS		V _{CCA}	V _{CCB}	–40°C to 85°C			–40°C to 125°C			UNIT
					MIN	TYP ⁽²⁾	MAX	MIN	TYP ⁽²⁾	MAX	
V _{OH} High-level output voltage	V _I = V _{IH}	I _{OH} = –100 μA	0.7 V - 3.6 V	0.7 V - 3.6 V	V _{CCO} – 0.1			V _{CCO} – 0.1			V
		I _{OH} = –50 μA	0.65 V	0.65 V	0.55			0.55			
		I _{OH} = –200 μA	0.76 V	0.76 V	0.58			0.58			
		I _{OH} = –500 μA	0.85 V	0.85 V	0.65			0.65			
		I _{OH} = -3 mA	1.1 V	1.1 V	0.85			0.85			
		I _{OH} = -6 mA	1.4 V	1.4 V	1.05			1.05			
		I _{OH} = -8 mA	1.65 V	1.65 V	1.2			1.2			
		I _{OH} = -9 mA	2.3 V	2.3 V	1.75			1.75			
		I _{OH} = -12 mA	3 V	3 V	2.3			2.3			
V _{OL} Low-level output voltage	V _I = V _{IL}	I _{OL} = 100 μA	0.7 V - 3.6 V	0.7 V - 3.6 V				0.1			V
		I _{OL} = 50 μA	0.65 V	0.65 V				0.1			
		I _{OL} = 200 μA	0.76 V	0.76 V				0.18			
		I _{OL} = 500 μA	0.85 V	0.85 V				0.2			
		I _{OL} = 3 mA	1.1 V	1.1 V				0.25			
		I _{OL} = 6 mA	1.4 V	1.4 V				0.35			
		I _{OL} = 8 mA	1.65 V	1.65 V				0.45			
		I _{OL} = 9 mA	2.3 V	2.3 V				0.55			
		I _{OL} = 12 mA	3 V	3 V				0.7			
I _{BHL} Bus-hold low sustaining current ⁽³⁾	V _I = 0.20 V		0.65 V	0.65 V	4			4			μA
	V _I = 0.23 V		0.76 V	0.76 V	8			7			
	V _I = 0.26 V		0.85 V	0.85 V	10			10			
	V _I = 0.39 V		1.1 V	1.1 V	20			20			
	V _I = 0.49 V		1.4 V	1.4 V	40			30			
	V _I = 0.58 V		1.65 V	1.65 V	55			45			
	V _I = 0.7 V		2.3 V	2.3 V	90			80			
	V _I = 0.8 V		3 V	3 V	145			135			
I _{BHH} Bus-hold high sustaining current ⁽⁴⁾	V _I = 0.45 V		0.65 V	0.65 V	–4			–4			μA
	V _I = 0.53 V		0.76 V	0.76 V	–8			–7			
	V _I = 0.59 V		0.85 V	0.85 V	–10			–10			
	V _I = 0.71 V		1.1 V	1.1 V	–20			–20			
	V _I = 0.91 V		1.4 V	1.4 V	–40			–30			
	V _I = 1.07 V		1.65 V	1.65 V	–55			–45			
	V _I = 1.6 V		2.3 V	2.3 V	–90			–80			
	V _I = 2.0 V		3 V	3 V	–145			–135			
I _{BHLO} Bus-hold low overdrive current ⁽⁵⁾	V _I = 0 to V _{CC}		0.75 V	0.75 V	40			40			μA
			0.84 V	0.84 V	50			50			
			0.95 V	0.95 V	65			65			
			1.3 V	1.3 V	105			105			
			1.6 V	1.6 V	150			150			
			1.95 V	1.95 V	205			205			
			2.7 V	2.7 V	335			335			
			3.6V	3.6V	480			480			

 (1) V_{CCO} is the V_{CC} associated with the output port.

 (2) All typical values are for T_A = 25°C.

 (3) The bus-hold circuit can sink at least the minimum low sustaining current at V_{IL}(MAX). I_{BHL} should be measured after lowering V_I to GND and then raising it to V_{IL}(MAX).

 (4) The bus-hold circuit can source at least the minimum high sustaining current at V_{IH}(MIN). I_{BHH} should be measured after raising V_I to V_{CC} and then lowering it to V_{IH}(MIN).

 (5) An external driver must source at least I_{BHLO} to switch this node from low to high.

Electrical Characteristics (continued)

Over recommended operating free-air temperature range (unless otherwise noted)⁽¹⁾

PARAMETER	TEST CONDITIONS	V _{CCA}	V _{CCB}	–40°C to 85°C			–40°C to 125°C			UNIT
				MIN	TYP ⁽²⁾	MAX	MIN	TYP ⁽²⁾	MAX	
I _{BHHO} Bus-hold high overdrive current ⁽⁶⁾	V _I = 0 to V _{CC}	0.75 V	0.75 V	–40			–40			μA
		0.84 V	0.84 V	–50			–50			
		0.95 V	0.95 V	–65			–65			
		1.3 V	1.3 V	–105			–105			
		1.6 V	1.6 V	–150			–150			
		1.95 V	1.95 V	–205			–205			
		2.7 V	2.7 V	–335			–335			
		3.6V	3.6V	–480			–480			
I _I Input leakage current	Control Inputs (DIR, $\overline{\text{OE}}$): V _I = V _{CCA} or GND	0.65 V - 3.6 V	0.65 V - 3.6 V	–0.5		0.5	–1		1	μA
I _{off} Partial power down current	A Port: V _I or V _O = 0 V - 3.6 V	0 V	0 V - 3.6 V	–8		8	–12		12	μA
	B Port: V _I or V _O = 0 V - 3.6 V	0 V - 3.6 V	0 V	–8		8	–12		12	
I _{OZ} High- impedance state output current	A Port: V _O = V _{CCO} or GND, V _I = V _{CCI} or GND, $\overline{\text{OE}}$ = V _{IH}	3.6 V	3.6 V	–8		8	–12		12	μA
	B Port: V _O = V _{CCO} or GND, V _I = V _{CCI} or GND, $\overline{\text{OE}}$ = V _{IH}	3.6 V	3.6 V	–8		8	–12		12	
I _{CCA} V _{CCA} supply current	V _I = V _{CCI} or GND, I _O = 0 mA	0.65 V - 3.6 V	0.65 V - 3.6 V			20			42	μA
		0 V	3.6 V	–2			–12			
		3.6 V	0 V			13			27	
I _{CCB} V _{CCB} supply current	V _I = V _{CCI} or GND, I _O = 0 mA	0.65 V - 3.6 V	0.65 V - 3.6 V			20			40	μA
		0 V	3.6 V			13			27	
		3.6 V	0 V	–2			–12			
I _{CCA} + I _{CCB} Combined supply current	V _I = V _{CCI} or GND, I _O = 0 mA	0.65 V - 3.6 V	0.65 V - 3.6 V			30			60	μA
C _i Input capacitance	Control Inputs (DIR, $\overline{\text{OE}}$): V _I = 3.3 V or GND	3.3 V	3.3 V		4.5			4.5		pF
C _{io} Data I/O capacitance	Ports A and B: $\overline{\text{OE}}$ = V _{CCA} , V _O = 1.65V DC + 1 MHz -16 dBm sine wave	3.3 V	3.3 V		7.3			7.3		pF

(6) An external driver must sink at least I_{BHHO} to switch this node from high to low.

7.6 Switching Characteristics, $V_{CCA} = 0.7\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	178	0.5	115	0.5	83	0.5	49	ns
		–40°C to 125°C	0.5	178	0.5	115	0.5	83	0.5	49	
	B input to A output	–40°C to 85°C	0.5	178	0.5	159	0.5	132	0.5	94	
		–40°C to 125°C	0.5	178	0.5	159	0.5	132	0.5	94	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	194	0.5	194	0.5	194	0.5	194	ns
		–40°C to 125°C	0.5	194	0.5	194	0.5	194	0.5	194	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	216	0.5	179	0.5	158	0.5	78	
		–40°C to 125°C	0.5	216	0.5	179	0.5	158	0.5	78	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	240	0.5	240	0.5	240	0.5	240	ns
		–40°C to 125°C	0.5	240	0.5	240	0.5	240	0.5	240	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	292	0.5	180	0.5	125	0.5	76	
		–40°C to 125°C	0.5	292	0.5	180	0.5	125	0.5	76	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	47	0.5	50	0.5	62	0.5	151	ns
		–40°C to 125°C	0.5	47	0.5	50	0.5	62	0.5	151	
	B input to A output	–40°C to 85°C	0.5	89	0.5	88	0.5	87	0.5	86	
		–40°C to 125°C	0.5	89	0.5	88	0.5	87	0.5	86	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	194	0.5	194	0.5	194	0.5	194	ns
		–40°C to 125°C	0.5	194	0.5	194	0.5	194	0.5	194	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	70	0.5	69	0.5	67	0.5	101	
		–40°C to 125°C	0.5	70	0.5	69	0.5	67	0.5	101	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	240	0.5	240	0.5	240	0.5	240	ns
		–40°C to 125°C	0.5	240	0.5	240	0.5	240	0.5	240	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	69	0.5	69	0.5	84	0.5	552	
		–40°C to 125°C	0.5	69	0.5	69	0.5	84	0.5	552	

7.7 Switching Characteristics, $V_{CCA} = 0.8\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	159	0.5	96	0.5	64	0.5	33	ns
		–40°C to 125°C	0.5	159	0.5	96	0.5	64	0.5	33	
	B input to A output	–40°C to 85°C	0.5	117	0.5	97	0.5	79	0.5	54	
		–40°C to 125°C	0.5	117	0.5	97	0.5	79	0.5	54	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	154	0.5	154	0.5	154	0.5	154	ns
		–40°C to 125°C	0.5	154	0.5	154	0.5	154	0.5	154	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	202	0.5	165	0.5	144	0.5	65	
		–40°C to 125°C	0.5	202	0.5	165	0.5	144	0.5	65	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	137	0.5	137	0.5	137	0.5	137	ns
		–40°C to 125°C	0.5	137	0.5	137	0.5	137	0.5	137	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	270	0.5	160	0.5	104	0.5	55	
		–40°C to 125°C	0.5	270	0.5	160	0.5	104	0.5	55	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	27	0.5	26	0.5	26	0.5	35	ns
		–40°C to 125°C	0.5	27	0.5	26	0.5	26	0.5	35	
	B input to A output	–40°C to 85°C	0.5	44	0.5	43	0.5	42	0.5	41	
		–40°C to 125°C	0.5	44	0.5	43	0.5	42	0.5	41	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	154	0.5	154	0.5	154	0.5	154	ns
		–40°C to 125°C	0.5	154	0.5	154	0.5	154	0.5	154	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	57	0.5	55	0.5	50	0.5	52	
		–40°C to 125°C	0.5	57	0.5	55	0.5	50	0.5	52	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	137	0.5	137	0.5	137	0.5	137	ns
		–40°C to 125°C	0.5	137	0.5	137	0.5	137	0.5	137	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	46	0.5	44	0.5	46	0.5	59	
		–40°C to 125°C	0.5	46	0.5	44	0.5	46	0.5	59	

7.8 Switching Characteristics, $V_{CCA} = 0.9\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to output	–40°C to 85°C	0.5	133	0.5	79	0.5	53	0.5	23	ns
		–40°C to 125°C	0.5	133	0.5	79	0.5	53	0.5	23	
	B input to A output	–40°C to 85°C	0.5	84	0.5	64	0.5	53	0.5	41	
		–40°C to 125°C	0.5	84	0.5	64	0.5	53	0.5	41	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	130	0.5	130	0.5	130	0.5	130	ns
		–40°C to 125°C	0.5	130	0.5	130	0.5	130	0.5	130	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	193	0.5	157	0.5	137	0.5	57	
		–40°C to 125°C	0.5	193	0.5	157	0.5	137	0.5	57	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	128	0.5	128	0.5	128	0.5	128	ns
		–40°C to 125°C	0.5	128	0.5	128	0.5	128	0.5	128	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	257	0.5	149	0.5	94	0.5	45	
		–40°C to 125°C	0.5	257	0.5	149	0.5	94	0.5	45	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	18	0.5	16	0.5	15	0.5	18	ns
		–40°C to 125°C	0.5	18	0.5	16	0.5	15	0.5	18	
	B input to A output	–40°C to 85°C	0.5	29	0.5	25	0.5	23	0.5	22	
		–40°C to 125°C	0.5	29	0.5	25	0.5	23	0.5	22	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	130	0.5	130	0.5	130	0.5	130	ns
		–40°C to 125°C	0.5	130	0.5	130	0.5	130	0.5	130	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	50	0.5	48	0.5	42	0.5	43	
		–40°C to 125°C	0.5	50	0.5	48	0.5	42	0.5	43	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	128	0.5	128	0.5	128	0.5	128	ns
		–40°C to 125°C	0.5	128	0.5	128	0.5	128	0.5	128	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	37	0.5	34	0.5	32	0.5	36	
		–40°C to 125°C	0.5	37	0.5	34	0.5	32	0.5	36	

7.9 Switching Characteristics, $V_{CCA} = 1.2\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	−40°C to 85°C	0.5	95	0.5	54	0.5	40	0.5	15	ns
		−40°C to 125°C	0.5	95	0.5	54	0.5	40	0.5	15	
	B input to A output	−40°C to 85°C	0.5	49	0.5	33	0.5	23	0.5	15	
		−40°C to 125°C	0.5	49	0.5	33	0.5	23	0.5	15	
t _{dis} Disable time	OE input to A output	−40°C to 85°C	0.5	47	0.5	47	0.5	47	0.5	47	ns
		−40°C to 125°C	0.5	47	0.5	47	0.5	47	0.5	47	
	OE input to B output	−40°C to 85°C	0.5	181	0.5	147	0.5	127	0.5	49	
		−40°C to 125°C	0.5	181	0.5	147	0.5	127	0.5	49	
t _{en} Enable time	OE input to A output	−40°C to 85°C	0.5	40	0.5	40	0.5	40	0.5	40	ns
		−40°C to 125°C	0.5	40	0.5	40	0.5	40	0.5	40	
	OE input to B output	−40°C to 85°C	0.5	221	0.5	132	0.5	81	0.5	34	
		−40°C to 125°C	0.5	221	0.5	132	0.5	81	0.5	34	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	−40°C to 85°C	0.5	11	0.5	9	0.5	8	0.5	8	ns
		−40°C to 125°C	0.5	11	0.5	9	0.5	8	0.5	8	
	B input to A output	−40°C to 85°C	0.5	12	0.5	10	0.5	8	0.5	8	
		−40°C to 125°C	0.5	12	0.5	10	0.5	8	0.5	8	
t _{dis} Disable time	OE input to A output	−40°C to 85°C	0.5	47	0.5	47	0.5	47	0.5	47	ns
		−40°C to 125°C	0.5	47	0.5	47	0.5	47	0.5	47	
	OE input to B output	−40°C to 85°C	0.5	42	0.5	40	0.5	34	0.5	34	
		−40°C to 125°C	0.5	42	0.5	40	0.5	34	0.5	34	
t _{en} Enable time	OE input to A output	−40°C to 85°C	0.5	39	0.5	40	0.5	40	0.5	40	ns
		−40°C to 125°C	0.5	39	0.5	40	0.5	40	0.5	40	
	OE input to B output	−40°C to 85°C	0.5	25	0.5	22	0.5	20	0.5	19	
		−40°C to 125°C	0.5	25	0.5	22	0.5	20	0.5	19	

7.10 Switching Characteristics, $V_{CCA} = 1.5\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	−40°C to 85°C	0.5	90	0.5	44	0.5	29	0.5	12	ns
		−40°C to 125°C	0.5	90	0.5	44	0.5	29	0.5	12	
	B input to A output	−40°C to 85°C	0.5	47	0.5	27	0.5	18	0.5	11	
		−40°C to 125°C	0.5	47	0.5	27	0.5	18	0.5	11	
t _{dis} Disable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	37	0.5	37	0.5	37	0.5	37	ns
		−40°C to 125°C	0.5	37	0.5	37	0.5	37	0.5	37	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	176	0.5	142	0.5	122	0.5	44	
		−40°C to 125°C	0.5	176	0.5	142	0.5	122	0.5	44	
t _{en} Enable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	25	0.5	25	0.5	25	0.5	25	ns
		−40°C to 125°C	0.5	25	0.5	25	0.5	25	0.5	25	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	214	0.5	114	0.5	71	0.5	29	
		−40°C to 125°C	0.5	214	0.5	114	0.5	71	0.5	29	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	−40°C to 85°C	0.5	9	0.5	8	0.5	6	0.5	6	ns
		−40°C to 125°C	0.5	9	0.5	8	0.5	6	0.5	6	
	B input to A output	−40°C to 85°C	0.5	9	0.5	8	0.5	6	0.5	5	
		−40°C to 125°C	0.5	9	0.5	8	0.5	6	0.5	5	
t _{dis} Disable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	37	0.5	37	0.5	37	0.5	37	ns
		−40°C to 125°C	0.5	37	0.5	37	0.5	37	0.5	37	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	38	0.5	37	0.5	31	0.5	31	
		−40°C to 125°C	0.5	38	0.5	37	0.5	31	0.5	31	
t _{en} Enable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	25	0.5	25	0.5	25	0.5	25	ns
		−40°C to 125°C	0.5	25	0.5	25	0.5	25	0.5	25	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	21	0.5	18	0.5	15	0.5	13	
		−40°C to 125°C	0.5	21	0.5	18	0.5	15	0.5	13	

7.11 Switching Characteristics, $V_{CCA} = 1.8\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	88	0.5	43	0.5	25	0.5	10	ns
		–40°C to 125°C	0.5	88	0.5	43	0.5	25	0.5	10	
	B input to A output	–40°C to 85°C	0.5	50	0.5	26	0.5	16	0.5	9	
		–40°C to 125°C	0.5	50	0.5	26	0.5	16	0.5	9	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	35	0.5	35	0.5	35	0.5	35	ns
		–40°C to 125°C	0.5	35	0.5	35	0.5	35	0.5	35	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	174	0.5	139	0.5	119	0.5	42	
		–40°C to 125°C	0.5	174	0.5	139	0.5	119	0.5	42	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	20	0.5	20	0.5	20	0.5	20	ns
		–40°C to 125°C	0.5	20	0.5	20	0.5	20	0.5	20	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	213	0.5	111	0.5	67	0.5	27	
		–40°C to 125°C	0.5	213	0.5	111	0.5	67	0.5	27	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	8	0.5	7	0.5	6	0.5	5	ns
		–40°C to 125°C	0.5	8	0.5	7	0.5	6	0.5	5	
	B input to A output	–40°C to 85°C	0.5	7	0.5	6	0.5	5	0.5	4	
		–40°C to 125°C	0.5	7	0.5	7	0.5	5	0.5	4	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	35	0.5	35	0.5	35	0.5	35	ns
		–40°C to 125°C	0.5	35	0.5	35	0.5	35	0.5	35	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	36	0.5	35	0.5	30	0.5	29	
		–40°C to 125°C	0.5	36	0.5	35	0.5	30	0.5	29	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	20	0.5	20	0.5	20	0.5	20	ns
		–40°C to 125°C	0.5	20	0.5	20	0.5	20	0.5	20	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	19	0.5	16	0.5	13	0.5	11	
		–40°C to 125°C	0.5	19	0.5	16	0.5	13	0.5	11	

7.12 Switching Characteristics, $V_{CCA} = 2.5\text{ V}$

See [Figure 1](#) and [Figure 2](#) for test circuit and loading conditions. See [Figure 3](#) and [Figure 4](#) for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	−40°C to 85°C	0.5	87	0.5	42	0.5	23	0.5	8	ns
		−40°C to 125°C	0.5	87	0.5	42	0.5	23	0.5	8	
	B input to A output	−40°C to 85°C	0.5	62	0.5	26	0.5	15	0.5	8	
		−40°C to 125°C	0.5	62	0.5	26	0.5	15	0.5	8	
t _{dis} Disable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	28	0.5	28	0.5	28	0.5	28	ns
		−40°C to 125°C	0.5	28	0.5	28	0.5	28	0.5	28	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	173	0.5	137	0.5	117	0.5	40	
		−40°C to 125°C	0.5	173	0.5	137	0.5	117	0.5	40	
t _{en} Enable time	$\overline{OE}$ input to A output	−40°C to 85°C	0.5	13	0.5	13	0.5	13	0.5	13	ns
		−40°C to 125°C	0.5	13	0.5	13	0.5	13	0.5	13	
	$\overline{OE}$ input to B output	−40°C to 85°C	0.5	211	0.5	107	0.5	63	0.5	24	
		−40°C to 125°C	0.5	211	0.5	107	0.5	63	0.5	24	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	6	0.5	6	0.5	5	0.5	5	ns
		–40°C to 125°C	0.5	6	0.5	6	0.5	5	0.5	5	
	B input to A output	–40°C to 85°C	0.5	6	0.5	6	0.5	5	0.5	4	
		–40°C to 125°C	0.5	6	0.5	6	0.5	5	0.5	4	
t _{dis} Disable time	OE input to A output	–40°C to 85°C	0.5	28	0.5	28	0.5	28	0.5	28	ns
		–40°C to 125°C	0.5	28	0.5	28	0.5	28	0.5	28	
	OE input to B output	–40°C to 85°C	0.5	34	0.5	33	0.5	28	0.5	28	
		–40°C to 125°C	0.5	34	0.5	33	0.5	28	0.5	28	
t _{en} Enable time	OE input to A output	–40°C to 85°C	0.5	13	0.5	13	0.5	13	0.5	13	ns
		–40°C to 125°C	0.5	13	0.5	13	0.5	13	0.5	13	
	OE input to B output	–40°C to 85°C	0.5	16	0.5	14	0.5	10	0.5	9	
		–40°C to 125°C	0.5	16	0.5	14	0.5	10	0.5	9	

7.13 Switching Characteristics, $V_{CCA} = 3.3\text{ V}$

See Figure 1 and Figure 2 for test circuit and loading conditions. See Figure 3 and Figure 4 for measurement waveforms.

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			0.7 V ± 0.05 V		0.8 V ± 0.04 V		0.9 V ± 0.045 V		1.2 V ± 0.1 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	87	0.5	41	0.5	22	0.5	8	ns
		–40°C to 125°C	0.5	87	0.5	41	0.5	22	0.5	8	
	B input to A output	–40°C to 85°C	0.5	151	0.5	36	0.5	18	0.5	8	
		–40°C to 125°C	0.5	151	0.5	36	0.5	18	0.5	8	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	27	0.5	27	0.5	27	0.5	27	ns
		–40°C to 125°C	0.5	27	0.5	27	0.5	27	0.5	27	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	172	0.5	136	0.5	116	0.5	39	
		–40°C to 125°C	0.5	172	0.5	136	0.5	116	0.5	39	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	11	0.5	11	0.5	11	0.5	11	ns
		–40°C to 125°C	0.5	11	0.5	11	0.5	11	0.5	11	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	210	0.5	106	0.5	62	0.5	23	
		–40°C to 125°C	0.5	210	0.5	106	0.5	62	0.5	23	

PARAMETER		TEST CONDITION	B-PORT SUPPLY VOLTAGE (V _{CCB})								UNIT
			1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
t _{pd} Propagation delay	A input to B output	–40°C to 85°C	0.5	5	0.5	5	0.5	4	0.5	4	ns
		–40°C to 125°C	0.5	5	0.5	5	0.5	4	0.5	4	
	B input to A output	–40°C to 85°C	0.5	6	0.5	5	0.5	5	0.5	4	
		–40°C to 125°C	0.5	6	0.5	5	0.5	5	0.5	4	
t _{dis} Disable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	27	0.5	27	0.5	27	0.5	27	ns
		–40°C to 125°C	0.5	27	0.5	27	0.5	27	0.5	27	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	33	0.5	32	0.5	27	0.5	27	
		–40°C to 125°C	0.5	33	0.5	32	0.5	27	0.5	27	
t _{en} Enable time	$\overline{OE}$ input to A output	–40°C to 85°C	0.5	11	0.5	11	0.5	11	0.5	11	ns
		–40°C to 125°C	0.5	11	0.5	11	0.5	11	0.5	11	
	$\overline{OE}$ input to B output	–40°C to 85°C	0.5	15	0.5	13	0.5	10	0.5	8	
		–40°C to 125°C	0.5	15	0.5	13	0.5	10	0.5	8	

7.14 Operating Characteristics: $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
C_{pdA} Power dissipation capacitance per transceiver (A to B: outputs enabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	3.0		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	3.0		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	3.0		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	3.1		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	3.0		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	3.2		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	3.7		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	4.4		
C_{pdA} Power dissipation capacitance per transceiver (A to B: outputs disabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	2.5		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	2.5		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	2.6		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	2.6		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	2.6		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	2.7		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	3.2		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	3.9		
C_{pdA} Power dissipation capacitance per transceiver (B to A: outputs enabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	12.6		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	12.3		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	12.4		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	12.4		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	12.7		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	13.6		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	17.4		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	20.9		
C_{pdA} Power dissipation capacitance per transceiver (B to A: outputs disabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	1.2		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	1.1		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	1.1		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	1.0		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	1.0		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	0.9		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	0.9		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	0.9		


Operating Characteristics: $T_A = 25^\circ\text{C}$ (continued)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
C_{pdB} Power dissipation capacitance per transceiver (A to B: outputs enabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	12.6		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	12.4		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	12.4		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	12.4		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	12.6		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	13.6		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	17.2		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	20.8		
C_{pdB} Power dissipation capacitance per transceiver (A to B: outputs disabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	1.4		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	1.3		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	1.3		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	1.2		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	1.1		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	1.1		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	1.1		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	1.0		
C_{pdB} Power dissipation capacitance per transceiver (B to A: outputs enabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	3.3		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	3.3		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	3.3		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	3.2		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	3.2		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	3.3		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	3.6		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	4.4		
C_{pdB} Power dissipation capacitance per transceiver (B to A: outputs disabled)	$C_L = 0$, $R_L = \text{Open}$ $f = 1\text{ MHz}$, $t_r = t_f = 1\text{ ns}$	$V_{CCA} = V_{CCB} = 0.7\text{ V}$	2.8		pF
		$V_{CCA} = V_{CCB} = 0.8\text{ V}$	2.8		
		$V_{CCA} = V_{CCB} = 0.9\text{ V}$	2.8		
		$V_{CCA} = V_{CCB} = 1.2\text{ V}$	2.8		
		$V_{CCA} = V_{CCB} = 1.5\text{ V}$	2.7		
		$V_{CCA} = V_{CCB} = 1.8\text{ V}$	2.8		
		$V_{CCA} = V_{CCB} = 2.5\text{ V}$	3.1		
		$V_{CCA} = V_{CCB} = 3.3\text{ V}$	3.9		

8 Parameter Measurement Information

Unless otherwise noted, all input pulses are supplied by generators having the following characteristics:

- $f = 1 \text{ MHz}$
- $Z_0 = 50 \Omega$
- $dv / dt \leq 1 \text{ ns/V}$




- (1) C_L includes probe and jig capacitance.

图 1. Load Circuit

Parameter	V_{CCO}	R_L	C_L	S1	V_{TP}
t_{pd}	1.1 V - 3.6 V	2 k Ω	15 pF	Open	N/A
	0.65 V - 0.95 V	20 k Ω	15 pF	Open	N/A
$t_{en}^{(1)}, t_{dis}^{(1)}$	3 V - 3.6 V	2 k Ω	15 pF	$2 \times V_{CCO}$	0.3 V
	1.65 V - 2.7 V	2 k Ω	15 pF	$2 \times V_{CCO}$	0.15 V
	1.1 V - 1.6 V	2 k Ω	15 pF	$2 \times V_{CCO}$	0.1 V
	0.65 V - 0.95 V	20 k Ω	15 pF	$2 \times V_{CCO}$	0.1 V
$t_{en}^{(2)}, t_{dis}^{(2)}$	3 V - 3.6 V	2 k Ω	15 pF	GND	0.3 V
	1.65 V - 2.7 V	2 k Ω	15 pF	GND	0.15 V
	1.1 V - 1.6 V	2 k Ω	15 pF	GND	0.1 V
	0.65 V - 0.95 V	20 k Ω	15 pF	GND	0.1 V

- (1) Output waveform on the conditions that input is driven to a valid Logic Low.
 (2) Output waveform on the condition that input is driven to a valid Logic High.


图 2. Load Circuit Conditions



- (1) V_{CCI} is the supply pin associated with the input port.
 (2) V_{OH} and V_{OL} are typical output voltage levels with specified R_L , C_L , and S_1 .

图 3. Propagation Delay

Parameter Measurement Information (continued)



- (1) Output waveform on the condition that input is driven to a valid Logic Low.
- (2) Output waveform on the condition that input is driven to a valid Logic High.
- (3) V_{CCO} is the supply pin associated with the output port.
- (4) V_{OH} and V_{OL} are typical output voltage levels with specified R_L , C_L , and S_1 .

图 4. Enable Time And Disable Time

9 Detailed Description

9.1 Overview

The SN74AXCH8T245 device is an 8-bit, dual-supply non-inverting transceiver with bidirectional voltage level translation. The I/O pins labeled with A and the control pins (DIR1, DIR2, and $\overline{OE}$) are supported by V_{CCA} , and the I/O pins labeled with B are supported by V_{CCB} . Both the A port and the B port are able to accept I/O voltages ranging from 0.65 V to 3.6 V.

9.2 Functional Block Diagram




图 5. Functional Block Diagram

9.3 Feature Description

9.3.1 Up-Translation and Down-Translation From 0.65 V to 3.6 V

Both supply pins are configurable over the full 0.65 V to 3.6 V voltage range, which makes the device suitable for translating between any of the low voltage nodes (0.7 V, 0.8 V, 0.9 V, 1.2 V, 1.8 V, 2.5 V, and 3.3 V).

9.3.2 Multiple Direction Control Pins

Two control pins are used to configure the 8 data I/Os. I/O channels 1 through 4 are grouped together and I/O channels 5 through 8 are banked together. The benefit of this is to permit simultaneous up-translation and down-translation within one device. This eliminates the need for multiple devices, where each device can only provide up-translation or down-translation sequentially. Simultaneous up and down translation is supported when both V_{CCA} and V_{CCB} are at least 1.40 V.

9.3.3 Bus-Hold Circuitry

Active bus-hold circuitry holds unused or undriven data inputs at a valid logic state, which helps with board space savings and reduced component costs. Use of pull-up or pull-down resistors with the bus-hold circuitry is not recommended. See the Bus-Hold Circuit application note for more details. (SCLA015).

Note that the bus-hold circuitry always remains active when the corresponding supply is present (i.e. B port bus-hold circuits are active when V_{CCB} is present, and A port bus-hold circuits are active when V_{CCA} is present). The bus hold circuitry is also active even when the device is in a partial power down state or when the output enable pin is used to place all outputs into high impedance.

9.3.4 I_{off} Supports Partial-Power-Down Mode Operation

This feature is to limit the leakage current of an I/O pin being driven to a voltage as large as 3.6 V while having its corresponding power supply rail powered down. This is represented by the I_{off} parameter in the [Electrical Characteristics](#) table.

9.4 Device Functional Modes

All control inputs are referenced to V_{CCA} and must be driven to a valid Logic High or Logic Low (that is, not floating) to assure proper device operation and to prevent excessive power consumption. 表 1 summarizes the possible modes of device operation based on the configuration of the control inputs.

表 1. Function Table⁽¹⁾

CONTROL INPUTS			Signal Direction	
$\overline{OE}$	DIR1	DIR2	Bits 1:4	Bits 5:8
H	X	X	Disabled (Hi-Z)	
L	L	L	B to A	
L	L	H	B to A	A to B
L	H	L	A to B	
L	H	H	A to B	B to A

(1) Input circuits of the data I/Os are always active and must be driven to a valid logic level.

10 Application and Implementation

注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

10.1 Application Information

The SN74AXCH8T245 device can be used in level-translation applications for interfacing devices or systems operating at different voltage nodes. [Figure 6](#) depicts an application in which the SN74AXCH8T245 device is up-translating a 0.7 V input to a 3.3 V output to interface between a system controller and a peripheral device.

10.2 Typical Application




Figure 6. Typical Application Schematic

Typical Application (continued)

10.2.1 Design Requirements

For this design example, use the parameters listed in 表 2.

表 2. Design Parameters

DESIGN PARAMETERS	EXAMPLE VALUE
Input voltage range	0.65 V to 3.6 V
Output voltage range	0.65 V to 3.6 V

10.2.2 Detailed Design Procedure

To begin the design process, determine the following:

- Input voltage range
 - Use the supply voltage of the device that is driving the SN74AXCH8T245 device to determine the input voltage range. For a valid logic high the value must exceed the V_{IH} of the input port. For a valid logic low the value must be less than the V_{IL} of the input port.
- Output voltage range
 - Use the supply voltage of the device that the SN74AXCH8T245 device is driving to determine the output voltage range.

10.2.3 Application Curve




図 7. Translation Up (0.7 V to 3.3 V) at 2.5 MHz

11 Power Supply Recommendations

Always apply a ground reference to the GND pins first. However, there are no additional requirements for power supply sequencing.

This device was designed with various power supply sequencing methods in mind to help prevent unintended triggering of downstream devices. For more information regarding the power up glitch performance of the AXC family of level translators, see the [Power Sequencing for AXC Family of Devices](#) application report.

12 Layout

12.1 Layout Guidelines

To assure reliability of the device, follow common printed-circuit board layout guidelines.

- Use bypass capacitors on power supplies.
- Use short trace lengths to avoid excessive loading.
- Place pads on the signal paths for loading capacitors or pullup resistors to help adjust rise and fall times of signals depending on the system requirements.

12.2 Layout Example




图 8. SN74AXCH8T245 Device Layout Example

13 デバイスおよびドキュメントのサポート

13.1 ドキュメントのサポート

13.1.1 関連資料

関連資料については、以下を参照してください。

テキサス・インスツルメンツ、『[低速またはフローティングCMOS入力の影響](#)』アプリケーション・レポート

テキサス・インスツルメンツ、『[AXCデバイス・ファミリの電源シーケンス](#)』アプリケーション・レポート

13.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、[ti.com](#)のデバイス製品フォルダを開いてください。右上の「アラートを受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

13.3 コミュニティ・リソース

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

TI E2E™ オンライン・コミュニティ *TIのE2E (Engineer-to-Engineer)* コミュニティ。エンジニア間の共同作業を促進するために開設されたものです。e2e.ti.comでは、他のエンジニアに質問し、知識を共有し、アイデアを検討して、問題解決に役立てることができます。

設計サポート *TIの設計サポート* 役に立つE2Eフォーラムや、設計サポート・ツールをすばやく見つけることができます。技術サポート用の連絡先情報も参照できます。

13.4 商標

E2E is a trademark of Texas Instruments.

13.5 静電気放電に関する注意事項



すべての集積回路は、適切なESD保護方法を用いて、取扱いと保存を行うようにして下さい。

静電気放電はわずかな性能の低下から完全なデバイスの故障に至るまで、様々な損傷を与えます。高精度の集積回路は、損傷に対して敏感であり、極めてわずかなパラメータの変化により、デバイスに規定された仕様に適合しなくなる場合があります。

13.6 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

14 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
74AXCH8T245RHRLRG4	Active	Production	VQFN (RHL) 24	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
74AXCH8T245RHRLRG4.B	Active	Production	VQFN (RHL) 24	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245PWR.B	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245PWRG4	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245PWRG4.B	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245RHRL	Active	Production	VQFN (RHL) 24	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245
SN74AXCH8T245RHRL.B	Active	Production	VQFN (RHL) 24	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	AH8T245

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
74AXCH8T245RHRLRG4	VQFN	RHL	24	3000	330.0	12.4	3.8	5.8	1.2	8.0	12.0	Q1
SN74AXCH8T245RHRLR	VQFN	RHL	24	3000	330.0	12.4	3.8	5.8	1.2	8.0	12.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
74AXCH8T245RHRLRG4	VQFN	RHL	24	3000	367.0	367.0	35.0
SN74AXCH8T245RHRLR	VQFN	RHL	24	3000	367.0	367.0	35.0




NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



NOTES: (continued)

- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sluea271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD
80% PRINTED COVERAGE BY AREA
SCALE: 18X

4225250/B 12/2024

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT


PW0024A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220208/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0024A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220208/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated