

TLC59025 低消費電力の 16 チャンネル、定電流 LED シンク・ドライバ

1 特長

- 16 チャンネルの定電流出力
- 出力電流と外付け抵抗の比が業界標準に適合
- 負荷電圧が変化しても出力電流は一定
- 出力電流精度:
 - チャンネル間: $\pm 5\%$ 未満 (最大値)
 - IC 間: $\pm 6\%$ 未満 (最大値)
- 定出力電流範囲: 3mA~45mA
- 出力電流は外付け抵抗により調整
- 出力電流の高速応答、 $\overline{OE}$ (最小値): 100ns
- クロック周波数: 30MHz
- シュミット・トリガ入力
- 電源電圧: 3.0V~5.5V
- 過熱保護のためのサーマル・シャットダウン
- ESD 性能: 1kV HBM

2 アプリケーション

- ゲーム機 / エンターテインメント
- 汎用 LED アプリケーション
- LED ディスプレイ・システム
- 標識の LED ライティング
- 白物家電

3 概要


TLC59025 デバイスは、LED ディスプレイおよび LED ライティング・アプリケーション用に設計されています。TLC59025 には 16 ビットのシフト・レジスタとデータ・ラッチが搭載されており、シリアル入力データをパラレル出力形式に変換します。TLC59025 の出力段では、16 のレギュレーション電流ポートにより、幅広い VF 変動の範囲内で LED を駆動するための一定の電流を供給します。LED ディスプレイ・アプリケーション (LED パネルなど) のシステム設計に使用される TLC59025 は、優れた柔軟性とデバイス性能を実現します。外付け抵抗 (R_{EXT}) を使用して出力電流を 3mA~45mA の範囲で調整できるため、LED の光強度を柔軟に制御できます。TLC59025 は、出力ポートから最大 17V を供給するように設計されています。高いクロック周波数 (30MHz) により、大量データ送信のシステム要件も満たします。

シリアル・データは、SDI 経由で TLC59025 に転送され、シフト・レジスタにシフト・インされて、SDO 経由で TLC59025 から転送されます。LE は、シフト・レジスタ内のシリアル・データを出カラッチにラッチできます。 $\overline{OE}$ は、出力ドライバが電流をシンクできるようにします。


製品情報 (1)

部品番号	パッケージ	本体サイズ (公称)
TLC59025	SSOP (24)	8.65mm×3.90mm

- (1) 利用可能なパッケージについては、このデータシートの末尾にある注文情報を参照してください。



代表的なアプリケーションの図



I_{OUT} と R_{EXT} の関係



Table of Contents

1 特長	1	8.1 Overview	13
2 アプリケーション	1	8.2 Functional Block Diagram	13
3 概要	1	8.3 Feature Description	13
4 Revision History	2	8.4 Device Functional Modes	13
5 Pin Configuration and Functions	3	9 Application and Implementation	14
6 Specifications	4	9.1 Application Information	14
6.1 Absolute Maximum Ratings.....	4	9.2 Typical Application	15
6.2 ESD Ratings.....	4	10 Power Supply Recommendations	16
6.3 Recommended Operating Conditions.....	4	11 Layout	16
6.4 Thermal Information.....	5	11.1 Layout Guidelines.....	16
6.5 Electrical Characteristics for 3-V Input Voltage.....	5	11.2 Layout Example.....	16
6.6 Electrical Characteristics for 5.5-V Input Voltage.....	6	12 Device and Documentation Support	17
6.7 Power Dissipation Ratings.....	6	12.1 サポート・リソース.....	17
6.8 Timing Requirements.....	7	12.2 Trademarks.....	17
6.9 Switching Characteristics for 3-V Input Voltage.....	8	12.3 静電気放電に関する注意事項.....	17
6.10 Switching Characteristics for 5.5-V Input Voltage.....	9	12.4 用語集.....	17
6.11 Typical Characteristics.....	10	13 Mechanical, Packaging, and Orderable Information	17
7 Parameter Measurement Information	11		
8 Detailed Description	13		

4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Changes from Revision B (February 2015) to Revision C (February 2021)	Page
• 文書全体にわたって表、図、相互参照の採番方法を更新.....	1
• Updated "T _J " to "T _A " in <i>Electrical Characteristics for 3-V Input Voltage</i> table.....	5
• Updated "T _J " to "T _A " in <i>Electrical Characteristics for 5.5-V Input Voltage</i> table.....	6
• Added note to <i>Constant Current</i> section.....	13

Changes from Revision A (March 2013) to Revision B (February 2015)	Page
• 「ピン構成および機能」セクション、「ESD 定格」表、「機能説明」セクション、「デバイスの機能モード」セクション、「アプリケーションと実装」セクション、「電源に関する推奨事項」セクション、「レイアウト」セクション、「デバイスおよびドキュメントのサポート」セクション、「メカニカル、パッケージ、および注文情報」セクションを追加.....	1
• 「注文情報」表を削除.....	1

5 Pin Configuration and Functions




图 5-1. DBQ Package 24-Pin SSOP Top View

表 5-1. Pin Functions

PIN		I/O	DESCRIPTION
NAME	NO.		
CLK	3	I	Clock input for data shift on rising edge
GND	1	—	Ground for control logic and current sink
LE	4	I	Data strobe input Serial data is transferred to the respective latch when LE is high. The data is latched when LE goes low. LE has an internal pulldown resistor.
OE	21	I	Output enable When OE is active (low), the output drivers are enabled. When OE is high, all output drivers are turned OFF (blanked). OE has an internal pullup resistor.
OUT0	5	O	Constant-current output
OUT1	6	O	Constant-current output
OUT2	7	O	Constant-current output
OUT3	8	O	Constant-current output
OUT4	9	O	Constant-current output
OUT5	10	O	Constant-current output
OUT6	11	O	Constant-current output
OUT7	12	O	Constant-current output
OUT8	13	O	Constant-current output
OUT9	14	O	Constant-current output
OUT10	15	O	Constant-current output
OUT11	16	O	Constant-current output
OUT12	17	O	Constant-current output
OUT13	18	O	Constant-current output
OUT14	19	O	Constant-current output
OUT15	20	O	Constant-current output
R-EXT	23	I	Input used to connect an external resistor (R_{ext}) for setting output currents

表 5-1. Pin Functions (continued)

PIN		I/O	DESCRIPTION
NAME	NO.		
SDI	2	I	Serial-data input to the Shift register
SDO	22	O	Serial-data output to the following SDI of next driver IC or to the microcontroller
VDD	24	—	Supply voltage

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

	MIN	MAX	UNIT
V _{DD} Supply voltage	0	7	V
V _I Input voltage	−0.4	V _{DD} + 0.4	V
V _O Output voltage	−0.5	20	V
I _{OUT} Output current		45	mA
I _{GND} GND terminal current		750	mA
T _J Operating virtual-junction temperature	−40	150	°C
T _{stg} Storage temperature	−55	150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

	VALUE	UNIT
V _(ESD) Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±1000
	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±500

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Pins listed as ±1000 V may actually have higher performance.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Pins listed as ±500 V may actually have higher performance.

6.3 Recommended Operating Conditions

Over operating free-air temperature range (unless otherwise noted)

	MIN	MAX	UNIT
V _{DD} Supply voltage	3	5.5	V
V _O Output voltage		17	V
V _{IH} Input voltage	0.7 × V _{DD}	V _{DD} + 0.4	V
V _{IL} Output voltage	GND	0.3 × V _{DD}	V
I _{OUT} Output current	V _O ≥ 0.6 V	3	mA
	V _O ≥ 1.0 V	45	mA
I _{OH} High-level output current, source	−1		mA
I _{OL} Low-level output current, sink	1		mA
T _A Operating free-air temperature	−40	125	°C

6.4 Thermal Information

THERMAL METRIC ⁽¹⁾			TLC59025	UNIT
			DBQ (SSOP)	
			24 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	Mounted on JEDEC 1-layer board (JESD 51-3), No airflow	99.8	°C/W
		Mounted on JEDEC 4-layer board (JESD 51-7), No airflow	61	°C/W

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

6.5 Electrical Characteristics for 3-V Input Voltage

$V_{DD} = 3\text{ V}$, $T_A = -40^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I_{leak}	Output leakage current	$V_{OH} = 17\text{ V}$			0.5	μA
		$T_A = 25^\circ\text{C}$				
		$T_A = 125^\circ\text{C}$			2	
V_{OH}	High-level output voltage	SDO, $I_{OL} = -1\text{ mA}$	$V_{DD} - 0.4$			V
V_{OL}	Low-level output voltage	SDO, $I_{OH} = 1\text{ mA}$			0.4	V
$I_{O(1)}$	Output current 1	$V_{OUT} = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$	13			mA
	Output current error, die-die	$I_{OL} = 13\text{ mA}$, $V_O = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$, $T_A = 25^\circ\text{C}$	$\pm 3\%$		$\pm 6\%$	
	Output current error, channel-to-channel	$I_{OL} = 13\text{ mA}$, $V_O = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$, $T_A = 25^\circ\text{C}$	$\pm 1.5\%$		$\pm 5\%$	
$I_{O(2)}$	Output current 2	$V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$	26			mA
	Output current error, die-die	$I_{OL} = 26\text{ mA}$, $V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$, $T_A = 25^\circ\text{C}$	$\pm 3\%$		$\pm 6\%$	
	Output current error, channel-to-channel	$I_{OL} = 26\text{ mA}$, $V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$, $T_A = 25^\circ\text{C}$	$\pm 1.5\%$		$\pm 5\%$	
I_{OUT} vs V_{OUT}	Output current vs output voltage regulation	$V_O = 1\text{ V}$ to 3 V , $I_O = 13\text{ mA}$	± 0.1			% / V
		$V_{DD} = 3.0\text{ V}$ to 5.5 V , $I_O = 13\text{ mA}$ to 45 mA	± 1			
	Pullup resistance	$\overline{OE}$	500			k Ω
	Pulldown resistance	LE	500			k Ω
T_{sd}	Overtemperature shutdown ⁽¹⁾		150	175	200	°C
T_{hys}	Restart temperature hysteresis		15			°C
I_{DD}	Supply current	$R_{ext} = \text{Open}$	7		10	mA
		$R_{ext} = 1440\ \Omega$	9		12	
		$R_{ext} = 720\ \Omega$	11		13	
C_{IN}	Input capacitance	$V_I = V_{DD}$ or GND, CLK, SDI, SDO, $\overline{OE}$			10	pF

(1) Specified by design

6.6 Electrical Characteristics for 5.5-V Input Voltage

$V_{DD} = 5.5\text{ V}$, $T_A = -40^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
I_{leak}	Output leakage current	$V_{OH} = 17\text{ V}$	$T_A = 25^\circ\text{C}$			0.5	μA
			$T_A = 125^\circ\text{C}$			2	
V_{OH}	High-level output voltage	SDO, $I_{OL} = -1\text{ mA}$		$V_{DD} - 0.4$			V
V_{OL}	Low-level output voltage	SDO, $I_{OH} = 1\text{ mA}$				0.4	V
$I_{O(1)}$	Output current 1	$V_{OUT} = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$		13			mA
	Output current error, die-die	$I_{OL} = 13\text{ mA}$, $V_O = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$, $T_A = 25^\circ\text{C}$		$\pm 3\%$		$\pm 6\%$	
	Output current error, channel-to-channel	$I_{OL} = 13\text{ mA}$, $V_O = 0.6\text{ V}$, $R_{ext} = 1440\ \Omega$, $T_A = 25^\circ\text{C}$		$\pm 1.5\%$		$\pm 5\%$	
$I_{O(2)}$	Output current 2	$V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$		26			mA
	Output current error, die-die	$I_{OL} = 26\text{ mA}$, $V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$, $T_A = 25^\circ\text{C}$		$\pm 3\%$		$\pm 6\%$	
	Output current error, channel-to-channel	$I_{OL} = 26\text{ mA}$, $V_O = 0.8\text{ V}$, $R_{ext} = 720\ \Omega$, $T_A = 25^\circ\text{C}$		$\pm 1.5\%$		$\pm 5\%$	
I_{OUT} vs V_{OUT}	Output current vs output voltage regulation	$V_O = 1\text{ V}$ to 3 V , $I_O = 26\text{ mA}$		± 0.1			% / V
		$V_{DD} = 3.0\text{ V}$ to 5.5 V , $I_O = 13\text{ mA}$ to 45 mA		± 1			
	Pullup resistance	$\overline{OE}$		500			k Ω
	Pulldown resistance	LE		500			k Ω
T_{sd}	Overtemperature shutdown ⁽¹⁾			150	175	200	$^\circ\text{C}$
T_{hys}	Restart temperature hysteresis			15			$^\circ\text{C}$
I_{DD}	Supply current	$R_{ext} = \text{Open}$		9		11	mA
		$R_{ext} = 1440\ \Omega$		12		14	
		$R_{ext} = 720\ \Omega$		14		16	
C_{IN}	Input capacitance	$V_I = V_{DD}$ or GND, CLK, SDI, SDO, $\overline{OE}$				10	pF

(1) Specified by design


6.7 Power Dissipation Ratings

			MIN	MAX	UNIT
P_D	Power dissipation	Mounted on JEDEC 4-layer board (JESD 51-7), No airflow, $T_A = 25^\circ\text{C}$, $T_J = 125^\circ\text{C}$		1.6	W

6.8 Timing Requirements

$V_{DD} = 3\text{ V to }5.5\text{ V}$ (unless otherwise noted)

		MIN	MAX	UNIT
$t_{w(L)}$	LE pulse duration	15		ns
$t_{w(CLK)}$	CLK pulse duration	15		ns
$t_{w(OE)}$	OE pulse duration	300		ns
$t_{su(D)}$	Setup time for SDI	3		ns
$t_{h(D)}$	Hold time for SDI	2		ns
$t_{su(L)}$	Setup time for LE	5		ns
$t_{h(L)}$	Hold time for LE	5		ns
f_{CLK}	Clock frequency		30	MHz
	Cascade operation			



6-1. Timing Diagram

6.9 Switching Characteristics for 3-V Input Voltage

$V_{DD} = 3\text{ V}$, $T_A = -40^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH1}	Low-to-high propagation delay time, CLK to $\overline{OUTn}$	$V_{IH} = V_{DD}$, $V_{IL} = \text{GND}$, $R_{ext} = 720\ \Omega$, $V_L = 4\text{ V}$, $R_L = 88\ \Omega$, $C_L = 10\text{ pF}$	30	45	60	ns
t_{PLH2}	Low-to-high propagation delay time, LE to $\overline{OUTn}$		30	45	60	ns
t_{PLH3}	Low-to-high propagation delay time, $\overline{OE}$ to $\overline{OUTn}$		30	45	60	ns
t_{PLH4}	Low-to-high propagation delay time, CLK to SDO			30	40	ns
t_{PHL1}	High-to-low propagation delay time, CLK to $\overline{OUTn}$		40	65	100	ns
t_{PHL2}	High-to-low propagation delay time, LE to $\overline{OUTn}$		40	65	100	ns
t_{PHL3}	High-to-low propagation delay time, $\overline{OE}$ to $\overline{OUTn}$		40	65	100	ns
t_{PHL4}	High-to-low propagation delay time, CLK to SDO			30	40	ns
$t_{w(\text{CLK})}$	Pulse duration, CLK		15			ns
$t_{w(L)}$	Pulse duration LE		15			ns
$t_{w(\text{OE})}$	Pulse duration, $\overline{OE}$		300			ns
$t_{h(D)}$	Hold time, SDI		2			ns
$t_{su(D)}$	Setup time, SDI		3			ns
$t_{h(L)}$	Hold time, LE		5			ns
$t_{su(L)}$	Setup time, LE		5			ns
t_r	Rise time, CLK ⁽¹⁾				500	ns
t_f	Fall time, CLK ⁽¹⁾				500	ns
t_{or}	Rise time, outputs (off)		35	50	70	ns
t_{of}	Rise time, outputs (on)		15	50	120	ns
f_{CLK}	Clock frequency	Cascade operation			30	MHz

- (1) If the devices are connected in cascade and t_r or t_f is large, it may be critical to achieve the timing required for data transfer between two cascaded devices.

6.10 Switching Characteristics for 5.5-V Input Voltage

 $V_{DD} = 5.5\text{ V}$, $T_A = -40^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH1}	Low-to-high propagation delay time, CLK to $\overline{OUTn}$	$V_{IH} = V_{DD}$, $V_{IL} = \text{GND}$, $R_{ext} = 720\ \Omega$, $V_L = 4\text{ V}$, $R_L = 88\ \Omega$, $C_L = 10\text{ pF}$	20	35	55	ns
t_{PLH2}	Low-to-high propagation delay time, LE to $\overline{OUTn}$		20	35	55	ns
t_{PLH3}	Low-to-high propagation delay time, $\overline{OE}$ to $\overline{OUTn}$		20	35	55	ns
t_{PLH4}	Low-to-high propagation delay time, CLK to SDO			20	30	ns
t_{PHL1}	High-to-low propagation delay time, CLK to $\overline{OUTn}$		15	28	42	ns
t_{PHL2}	High-to-low propagation delay time, LE to $\overline{OUTn}$		15	28	42	ns
t_{PHL3}	High-to-low propagation delay time, $\overline{OE}$ to $\overline{OUTn}$		15	28	42	ns
t_{PHL4}	High-to-low propagation delay time, CLK to SDO			20	30	ns
$t_{w(\text{CLK})}$	Pulse duration, CLK		10			ns
$t_{w(L)}$	Pulse duration LE		10			ns
$t_{w(\text{OE})}$	Pulse duration, $\overline{OE}$		200			ns
$t_{h(D)}$	Hold time, SDI		2			ns
$t_{su(D)}$	Setup time, SDI		3			ns
$t_{h(L)}$	Hold time, LE		5			ns
$t_{su(L)}$	Setup time, LE		5			ns
t_r	Rise time, CLK ⁽¹⁾				500	ns
t_f	Fall time, CLK ⁽¹⁾				500	ns
t_{or}	Rise time, outputs (off)		25	45	65	ns
t_{of}	Rise time, outputs (on)		7	12	20	ns
f_{CLK}	Clock frequency	Cascade operation			30	MHz

- (1) If the devices are connected in cascade and t_r or t_f is large, it may be critical to achieve the timing required for data transfer between two cascaded devices.

6.11 Typical Characteristics




图 6-2. CLK to $\overline{\text{OUT7}}$




图 6-3. $\overline{\text{OE}}$ to $\overline{\text{OUT1}}$




图 6-4. $\overline{\text{OE}}$ to $\overline{\text{OUT7}}$

7 Parameter Measurement Information




图 7-1. Test Circuit for Electrical Characteristics





图 7-2. Test Circuit for Switching Characteristics




7-3. Normal Mode Timing Waveforms

8 Detailed Description

8.1 Overview

The TLC59025 is a 16-channel LED driver designed for LED displays and LED lighting applications. The TLC59025 contains a 16-bit shift register and data latches, which convert serial input data into parallel output format. At the TLC59025 output stage, 16 regulated-current ports provide uniform and constant current for driving LEDs within a wide range of V_F variations. Used in system design for LED display applications (for example, LED panels), the TLC59025 provides great flexibility and device performance. Users can adjust the output current from 3 mA to 45 mA through an external resistor, R_{EXT} , which gives flexibility in controlling the light intensity of LEDs. TLC59025 is designed for up to 17 V at the output port. The high clock frequency, 30 MHz, also satisfies the system requirements of high-volume data transmission.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Constant Current

In LED display applications, TLC59025 provides nearly no current variations from channel to channel and from IC to IC. While $I_{OUT} \leq 45$ mA, the maximum current skew between channels is less than $\pm 5\%$ and between ICs is less than $\pm 6\%$.

注

When the TLC59025 is used in very low current applications, reduced current accuracy can be expected. For example, current accuracy is estimated to degrade to as much as $\pm 10\%$ when $I_{OUT} = 1.7$ mA.

8.4 Device Functional Modes

表 8-1 lists the functional modes for the TLC59025.

表 8-1. Truth Table in Normal Operation

CLK	LE	OE	SDI	OUT0... OUT15... OUT15	SDO
↑	H	L	Dn	Dn...Dn - 7...Dn - 15	Dn - 15
↑	L	L	Dn + 1	No change	Dn - 14
↑	H	L	Dn + 2	Dn + 2...Dn - 5...Dn - 13	Dn - 13
↓	X	L	Dn + 3	Dn + 2...Dn - 5...Dn - 13	Dn - 13
↓	X	H	Dn + 3	off	Dn - 13

9 Application and Implementation

注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。また、お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

9.1 Application Information

9.1.1 Turning on the LEDs

To turn on an LED connected to one of the outputs of the device, the output must be pulled low. To do this, the SDI signal must let the device know which outputs should be activated. Using the rising edge of CLK, the logic level of the SDI signal latches the desired state of each output into the shift register. Once this is complete, the LE signal must be toggled from low to high then back to low. Once /OE is pulled down, the corresponding outputs will be pulled low and the LEDs will be turned on. The below diagram shows outputs 0, 3, 4, 5, 10, 13, and 15 being activated.





図 9-1. Timing Diagram

9.2 Typical Application

This application shows how to calculate the output current for $\overline{\text{OUT0}}$ through $\overline{\text{OUT15}}$.



9-2. Typical Application Diagram

9.2.1 Design Requirements

For the following design procedure, the input voltage (V_{DD}) is between 3 V and 5.5 V.

9.2.2 Detailed Design Procedure

9.2.2.1 Adjusting Output Current


TLC59025 sets I_{OUT} based on the external resistor R_{EXT} . Users can follow the below formula to calculate the target output current $I_{OUT,target}$ in the saturation region:

$$I_{OUT,target} = (1.21 \text{ V} / R_{EXT}) \times 15.5$$

Where R_{EXT} is the external resistance connected between R-EXT and GND. Using this equation, the output current is calculated to be approximately 26 mA at 720 Ω and 13 mA at 1440 Ω .

9.2.3 Application Curve

The default relationship after power on between $I_{OUT,target}$ and R_{EXT} is shown in 9-3.



9-3. Default Relationship Curve Between $I_{OUT,target}$ and R_{ext} After Power Up

10 Power Supply Recommendations

The TLC59025 is designed to operate with a VDD range between 3 V and 5.5 V.

11 Layout


11.1 Layout Guidelines

The SDI, CLK, SDO, LE, and $\overline{OE}$ signals should all be kept from potential noise sources.

All traces carrying power through the LEDs should be wide enough to handle necessary currents.

All LED current passes through the device and into the ground node. There must be a strong connection between the device ground and the circuit board ground.

11.2 Layout Example



✎ 11-1. Layout Recommendation

12 Device and Documentation Support

12.1 サポート・リソース

[TI E2E™ サポート・フォーラム](#)は、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の[使用条件](#)を参照してください。

12.2 Trademarks

TI E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

12.3 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい ESD 対策をとらないと、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

12.4 用語集

[TI 用語集](#) この用語集には、用語や略語の一覧および定義が記載されています。

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TLC59025IDBQR	Active	Production	SSOP (DBQ) 24	2500 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	TLC59025I
TLC59025IDBQR.B	Active	Production	SSOP (DBQ) 24	2500 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	TLC59025I

- ⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).
- ⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- ⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- ⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- ⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- ⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLC59025IDBQR	SSOP	DBQ	24	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLC59025IDBQR	SSOP	DBQ	24	2500	356.0	356.0	35.0

DBQ (R-PDSO-G24)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15) per side.
 - D. Falls within JEDEC MO-137 variation AE.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated