

TPS7B81-Q1 Automotive, 150mA, Off-Battery, Ultra-Low Io (3µA), Low-Dropout Regulator

1 Features

- AEC-Q100 qualified for automotive applications:
 - Temperature grade 1: –40°C to 125°C, T_A
- Device junction temperature range:
- -40°C to 150°C
- 3V to 40V wide V_{IN} input voltage range with up to 45V transient
- Maximum output current: 150mA
- Low quiescent current I_O:
 - 300nA typical when EN = low (shutdown mode)
 - 2.7µA typical at light loads
 - 4.5µA maximum at light loads
- 1.5% output-voltage accuracy over line, load and temperature
- Maximum dropout voltage: 540mV at 150mA load current for fixed 5V output version
- Stable with low-ESR $(0.001\Omega \text{ to } 5\Omega)$ ceramic output-stability capacitor (1µF to 200µF)
- Fixed 5V, 3.3V and 2.5V output voltage
- Integrated fault protection:
 - Thermal shutdown
 - Short-circuit and overcurrent protection
- Functional Safety-Capable
 - Documentation available to aid functional safety system design
- Packages:
 - DGN (8-pin HVSSOP), $R_{\theta JA} = 63.9^{\circ}$ C/W
 - DRV (6-pin WSON), $R_{\theta JA} = 72.8^{\circ}C/W$
 - KVU (5-pin TO-252), $R_{\theta JA} = 38.8^{\circ}C/W$

2 Applications

- Automotive head units
- Headlights
- Battery management systems (BMS)
- Inverter and motor controls

3 Description

In automotive battery-connected applications, low quiescent current (I_O) is important to conserve energy and to extend battery lifetime. Always-on systems must have ultra-low IQ over an extended temperature range to enable sustained operation when the vehicle ignition is off.


The TPS7B81-Q1 is a low-dropout (LDO) linear regulator designed for up to 40V V_{IN} applications. With only a 2.7µA typical quiescent current at light load, the device is an optimal solution for powering microcontrollers and controller area network and local interconnect network (CAN/LIN) transceivers in standby systems.

The device features integrated short-circuit and overcurrent protection. This device operates in ambient temperatures from -40°C to +125°C and with junction temperatures from -40°C to +150°C. Additionally, this device is available in several packages of varying size and thermal conductivity. The small WSON package facilitates the most compact PCB design and the TO-252 package enables sustained operation despite significant dissipation across the device. These features make the device well suited as a power supply for various battery-connected automotive applications.

Package Information

PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE(2)
	DGN (HVSSOP, 8)	3mm × 3mm
TPS7B81-Q1	DRV (WSON, 6)	2mm × 2mm
	KVU (TO-252, 5)	6.1mm × 6.6mm

- For more information, see the Mechanical, Packaging, and Orderable Information.
- The package size (length × width) is a nominal value and includes pins, where applicable.



Typical Application Schematic



Table of Contents

1 Features	1	6.4 Device Functional Modes	13
2 Applications	1	7 Application and Implementation	14
3 Description		7.1 Application Information	14
4 Pin Configuration and Functions	<mark>3</mark>	7.2 Typical Application	
5 Specifications	<mark>5</mark>	7.3 Power Supply Recommendations	
5.1 Absolute Maximum Ratings	<mark>5</mark>	7.4 Layout	
5.2 ESD Ratings		8 Device and Documentation Support	
5.3 Recommended Operating Conditions		8.1 Receiving Notification of Documentation Updates.	21
5.4 Thermal Information		8.2 Support Resources	21
5.5 Electrical Characteristics	6	8.3 Trademarks	
5.6 Typical Characteristics	8	8.4 Electrostatic Discharge Caution	21
6 Detailed Description		8.5 Glossary	21
6.1 Overview		9 Revision History	
6.2 Functional Block Diagram		10 Mechanical, Packaging, and Orderable	
6.3 Feature Description		Information	<mark>2</mark> 1



4 Pin Configuration and Functions




Figure 4-1. DGN Package, 8-Pin HVSSOP PowerPAD™ (Top View)




Figure 4-2. DRV Package, 6-Pin WSON PowerPAD™ (Top View)




Figure 4-3. KVU Package, 5-Pin TO-252 (Top View)

Table 4-1. Pin Functions

		PIN			
NAME		NO.		I/O	DESCRIPTION
NAIVIE	DGN	DRV	KVU		
DNC	_	5	4	_	Do not connect to a biased voltage. Tie this pin to ground or leave floating.
EN	2	2	2	I	Enable input pin. Drive EN greater than V_{IH} to turn on the regulator. Drive EN less than V_{IL} to put the low-dropout (LDO) into shutdown mode.
GND	4, 5, 6	3,4	3, TAB	_	Ground reference
IN	1	1	1	I	Input power-supply pin. For best transient response and to minimize input impedance, use the recommended value or larger ceramic capacitor from IN to ground as listed in the <i>Recommended Operating Conditions</i> table and the <i>Input Capacitor</i> section. Place the input capacitor as close to the output of the device as possible.
NC	3, 7	_	_	_	Not internally connected



Table 4-1. Pin Functions (continued)

		PIN			
NAME	NO.			I/O	DESCRIPTION
INAIVIE	DGN	DRV	KVU		
OUT	8	6	5	0	Regulated output voltage pin. A capacitor is required from OUT to ground for stability. For best transient response, use the nominal recommended value or larger ceramic capacitor from OUT to ground; see the <i>Recommended Operating Conditions</i> table and the <i>Output Capacitor</i> section. Place the output capacitor as close to output of the device as possible.
Thermal pad		_	Connect the thermal pad to a large-area GND plane for improved thermal performance.		

5 Specifications

5.1 Absolute Maximum Ratings

over operating ambient temperature range (unless otherwise noted)(1) (2)

		MIN	MAX	UNIT
V _{IN}	Unregulated input ⁽³⁾	-0.3	45	V
V _{EN}	Enable input ⁽³⁾	-0.3	V _{IN}	V
V _{OUT}	Regulated output	-0.3	7	V
T _J	Junction temperature range	-40	150	°C
T _{stg}	Storage temperature range	-40	150	°C

- (1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values are with respect to GND.
- (3) Absolute maximum voltage, can withstand 45 V for 200 ms.

5.2 ESD Ratings

				VALUE	UNIT
		Human-body model (HBM), per AEC	Q100-002 ⁽¹⁾	±2000	
V _(ESD)	Electrostatic discharge	Charged-device model (CDM), per	Corner pins	±750	V
	a.comange	AEC Q100-011	Other pins	±500	

(1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V _{IN}	Unregulated input voltage	3	40	V
V _{EN}	Enable input voltage	0	V_{IN}	V
C _{OUT}	Output capacitor requirements ⁽¹⁾	1	200	μF
ESR	Output capacitor ESR requirements ⁽²⁾	0.001	5	Ω
T _A	Ambient temperature range	-40	125	°C
T _J	Junction temperature range	-40	150	°C

- (1) The output capacitance range specified in the table is the effective value.
- (2) Relevant ESR value at f = 10 kHz



5.4 Thermal Information

			TPS7B81-Q1			
	THERMAL METRIC(1)	DGN (HVSSOP)	DRV (WSON)	KVU (TO-252)	UNIT	
		8 PINS	6 PINS	5 PINS		
$R_{\theta JA}$	Junction-to-ambient thermal resistance	63.9	72.8	31.1	°C/W	
R _{0JC(top)}	Junction-to-case (top) thermal resistance	50.2	85.8	39.9	°C/W	
$R_{\theta JB}$	Junction-to-board thermal resistance	22.6	37.4	9.9	°C/W	
ΨЈТ	Junction-to-top characterization parameter	1.8	2.7	4.2	°C/W	
Ψ_{JB}	Junction-to-board characterization parameter	22.3	37.3	9.9	°C/W	
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	12.1	13.8	2.8	°C/W	

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

5.5 Electrical Characteristics

over operating ambient temperature range, $T_J = -40^{\circ}\text{C}$ to +150°C, $V_{IN} = 14 \text{ V}$, and 10- μF ceramic output capacitor (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
SUPPL	Y VOLTAGE AND CURRE	ENT (IN)					
V _{IN}	Input voltage			V _{OUT(Nom)} + V _(Dropout)		40	V
I _(SD)	Shutdown current	EN = 0 V			0.3	1	μA
		V_{IN} = 6 V to 40 V, EN \geq 2 V, I_{OUT} = 0 mA			1.9	3.5	
$I_{(Q)}$	Quiescent current	V = 6 V/to 40 V/FN > 2 V/	DGN package		2.7	6.5	μΑ
	$V_{IN} = 6 \text{ V to } 40 \text{ V, EN} \ge 2 \text{ V,}$ $I_{OUT} = 0.2 \text{ mA}$	DRV and KVU packages		2.7	4.5		
V _{(IN,}	V _{IN} undervoltage	Ramp V _{IN} down until the output turns off				2.7	V
UVLO)	detection	Hysteresis			200		mV
ENABL	E INPUT (EN)					'	
V _{IL}	Logic-input low level					0.7	V
V _{IH}	Logic-input high level			2			V
I _{EN}	Enable current				10		nA
REGUL	ATED OUTPUT (OUT)					,	
V _{OUT}	Regulated output	$V_{IN} = V_{OUT} + V_{(Dropout)}$ to 40 V, $I_{OUT} = 1$ mA to 150 mA		-1.5%		1.5%	
V _{(Line-} Reg)	Line regulation	V _{IN} = 6 V to 40 V, I _{OUT} = 10 mA				10	mV
\/			DGN package			20	
V _(Load-Reg) Load regulation	Load regulation	V _{IN} = 14 V, I _{OUT} = 1 mA to 150 mA	DRV and KVU packages			10	mV

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

5.5 Electrical Characteristics (continued)

over operating ambient temperature range, $T_J = -40^{\circ}\text{C}$ to +150°C, $V_{IN} = 14 \text{ V}$, and 10- μF ceramic output capacitor (unless otherwise noted)


	PARAMETER		TEST CONDITIONS	S	MIN	TYP	MAX	UNIT
			DGN package			270	540	
		V _{OUT} = 5 V	I _{OUT} = 150 mA	DRV and KVU packages		325	585	
		V _{OUT} – 3 V		DGN package		180	350	
V _(Dropout)	Dropout voltage ⁽¹⁾		I _{OUT} = 100 mA	DRV and KVU packages		200	390	mV
				DGN package			650	
	V _{OUT} = 3.3 V	I _{OUT} = 150 mA	DRV and KVU packages		345	675		
		I _{OUT} = 100 mA			255	450		
I _{OUT}	Output current	V _{OUT} in regulation, V _I the fixed 3.3-V option	• •	-V option, V _{IN} = 5.8 V for	0		150	mA
I _(CL)	Output current limit	V _{OUT} short to 90% × V	V _{OUT}		180	510	690	mA
PSRR	Power-supply ripple rejection	$V_{(Ripple)} = 0.5 V_{PP}, I_{OU}$ μF	$V_{(Ripple)}$ = 0.5 V_{PP} , I_{OUT} = 10 mA, frequency = 100 Hz, C_{OUT} = 2.2 μF			60		dB
OPERATI	OPERATING TEMPERATURE RANGE							
T _(SD)	Junction shutdown temperature					175		°C
T _(HYST)	Hysteresis of thermal shutdown					20		°C

⁽¹⁾ Dropout is not valid for the 2.5-V output because of the minimum input voltage limits.



5.6 Typical Characteristics

at T_J = -40°C to +150°C, V_{IN} = 14 V, and V_{EN} ≥ 2 V (unless otherwise noted)



5.6 Typical Characteristics (continued)

at $T_J = -40$ °C to +150°C, $V_{IN} = 14$ V, and $V_{EN} \ge 2$ V (unless otherwise noted)




Figure 5-7. Dropout Voltage vs Ambient Temperature




Figure 5-8. Output Voltage vs Ambient Temperature




Figure 5-9. Output Voltage vs Ambient Temperature




Figure 5-10. Temperature Drift Histogram (-40°C to +25°C)




Figure 5-11. Temperature Drift Histogram (25°C to 150°C)





Figure 5-12. Output Voltage vs Input Voltage



5.6 Typical Characteristics (continued)


at $T_J = -40$ °C to +150°C, $V_{IN} = 14$ V, and $V_{EN} \ge 2$ V (unless otherwise noted)





5.6 Typical Characteristics (continued)

at $T_J = -40$ °C to +150°C, $V_{IN} = 14$ V, and $V_{EN} \ge 2$ V (unless otherwise noted)



Frequency (Hz) $C_{IN} = 0.1 \ \mu\text{F, } C_{OUT} = 10 \ \mu\text{F}$

Figure 5-23. Noise vs Frequency


Figure 5-24. Output Capacitance vs ESR Stability

6 Detailed Description

6.1 Overview

The TPS7B81-Q1 is a 40-V, 150-mA, low-dropout (LDO) linear regulator with ultralow quiescent current. This voltage regulator consumes only 3 μ A of quiescent current at light load, and is quite suitable for the automotive always-on application.

6.2 Functional Block Diagram



6.3 Feature Description

6.3.1 Device Enable (EN)

The EN pin is a high-voltage-tolerant pin. A high input activates the device and turns the regulation on. Connect this pin to an external microcontroller or a digital circuit to enable and disable the device, or connect to the IN pin for self-bias applications.

6.3.2 Undervoltage Shutdown

This device has an integrated undervoltage lockout (UVLO) circuit to shut down the output if the input voltage (V_{IN}) falls below an internal UVLO threshold $(V_{(UVLO)})$. This feature ensures that the regulator does not latch into an unknown state during low-input-voltage conditions. If the input voltage has a negative transient that drops below the UVLO threshold and recovers, the regulator shuts down and powers up with a normal power-up sequence when the input voltage is above the required level.

6.3.3 Current Limit

This device features current-limit protection to keep the device in a safe operating area when an overload or output short-to-ground condition occurs. This feature protects the device from excessive power dissipation. For example, during a short-circuit condition on the output, the fault protection limits the current through the pass element to I_(LIM) to protect the device from excessive power dissipation.

6.3.4 Thermal Shutdown

This device incorporates a thermal shutdown (TSD) circuit as protection from overheating. For continuous normal operation, the junction temperature must not exceed the TSD trip point. If the junction temperature exceeds the TSD trip point, the output turns off. When the junction temperature falls below the TSD trip point minus the thermal shutdown hysteresis, the output turns on again.

6.4 Device Functional Modes

6.4.1 Operation With V_{IN} Lower Than 3 V

The device normally operates with input voltages above 3 V. The device can also operate at lower input voltages; the maximum UVLO voltage is 2.7 V. The device does not operate at input voltages below the actual UVLO voltage.

6.4.2 Operation With V_{IN} Larger Than 3 V

When V_{IN} is greater than 3 V, if V_{IN} is also higher than the output set value plus the device dropout voltage, V_{OUT} is equal to the set value. Otherwise, V_{OUT} is equal to V_{IN} minus the dropout voltage.

Table 6-1. Device Functional Mode Comparison

OPERATING MODE	PARAMETER			
Normal mode	$V_{IN} > V_{OUT(nom)} + V_{(Dropout)}$ and $V_{IN} \ge 3 \text{ V}$	$V_{EN} > V_{IH}$	I _{OUT} < I _{CL}	T _J < 160°C
Dropout mode	$3V \le V_{IN} < V_{OUT(nom)} + V_{(Dropout)}$	V _{EN} > V _{IH}	I _{OUT} < I _{CL}	T _J < 160°C
Disabled mode (any true condition disables the device)	V _{IN} < V _(IN, UVLO)	V _{EN} < V _{IL}	_	T _J > 160°C

7 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

7.1 Application Information

The TPS7B81-Q1 is a 150-mA, 40-V, low-dropout (LDO) linear regulator with ultralow quiescent current. The PSpice transient model is available for download on the product folder and can be used to evaluate the basic function of the device.

7.1.1 Power Dissipation

Circuit reliability demands that proper consideration is given to device power dissipation, location of the circuit on the printed circuit board (PCB), and correct sizing of the thermal plane. The PCB area around the regulator must be as free as possible of other heat-generating devices that cause added thermal stresses.

As a first-order approximation, power dissipation in the regulator depends on the input-to-output voltage difference and load conditions. P_D can be approximated using Equation 1:

$$P_{D} = (V_{IN} - V_{OUT}) \times I_{OUT}$$
 (1)

An important note is that power dissipation can be minimized, and thus greater efficiency achieved, by proper selection of the system voltage rails. Proper selection allows the minimum input-to-output voltage differential to be obtained. The low dropout of the device allows for maximum efficiency across a wide range of output voltages.

The main heat conduction path for the device is through the thermal pad on the package. As such, the thermal pad must be soldered to a copper pad area under the device. This pad area contains an array of plated vias that conduct heat to any inner plane areas or to a bottom-side copper plane.

The maximum power dissipation determines the maximum allowable junction temperature (T_J) for the device. Power dissipation and junction temperature are most often related by the junction-to-ambient thermal resistance $(R_{\theta JA})$ of the combined PCB, device package, and the temperature of the ambient air (T_A) , according to Equation 2. The equation is rearranged for output current in Equation 3.

$$T_{J} = T_{A} + R_{\theta JA} \times P_{D} \tag{2}$$

$$I_{OUT} = (T_J - T_A) / [R_{\theta,JA} \times (V_{IN} - V_{OUT})]$$
(3)

Unfortunately, this thermal resistance ($R_{\theta JA}$) is highly dependent on the heat-spreading capability built into the particular PCB design, and therefore varies according to the total copper area, copper weight, and location of the planes. The $R_{\theta JA}$ recorded in the v table is determined by the JEDEC standard, PCB, and copper-spreading area, and is only used as a relative measure of package thermal performance. Note that for a well-designed thermal layout, $R_{\theta JA}$ is actually the sum of the package junction-to-case (bottom) thermal resistance ($R_{\theta JCbot}$) plus the thermal resistance contribution by the PCB copper.

Figure 7-1 through Figure 7-6 show the functions of $R_{\theta JA}$ and ψ_{JB} vs. copper area and thickness. These plots are generated with a 101.6 mm x 101.6 mm x 1.6mm PCB of two and four layers. For the four layer board, inner planes use 1 oz copper thickness. Outer layers are simulated with both 1 oz and 2 oz copper thickness. A 2 x 1 array of thermal vias of 300 μ m drill diameter and 25 μ m Cu plating is located beneath the thermal pad of the device. The thermal vias connect the top layer, the bottom layer and, in the case of the 4-layer board, the first inner GND plane. Each of the layers has a copper plane of equal area.






Figure 7-1. $R_{\theta JA}$ versus Cu Area for the WSON (DRV) Package




Figure 7-2. ψ_{JB} versus Cu Area for the WSON (DRV) Package




Figure 7-3. $R_{\theta JA}$ versus Cu Area for the HVSSOP (DGN) Package




Figure 7-4. ψ_{JB} versus Cu Area for the HVSSOP (DGN) Package






Figure 7-5. $R_{\theta JA}$ versus Cu Area for the TO-252 (KVU) Package




Figure 7-6. ψ_{JB} versus Cu Area for the TO-252 (KVU) Package

7.1.1.1 Estimating Junction Temperature

The JEDEC standard now recommends the use of psi (Ψ) thermal metrics to estimate the junction temperatures of the LDO when in-circuit on a typical PCB board application. These metrics are not strictly speaking thermal resistances, but rather offer practical and relative means of estimating junction temperatures. These psi metrics are determined to be significantly independent of the copper-spreading area. The key thermal metrics (Ψ_{JT} and Ψ_{JB}) are given in the Section 5.4 table and are used in accordance with Equation 4.

$$\Psi_{JT}: T_J = T_T + \Psi_{JT} \times P_D$$

$$\Psi_{JB}: T_J = T_B + \Psi_{JB} \times P_D$$
(4)

where:

- P_D is the power dissipated as explained in Equation 1
- · T_T is the temperature at the center-top of the device package, and
- T_B is the PCB surface temperature measured 1 mm from the device package and centered on the package edge

7.2 Typical Application

Figure 7-7 shows a typical application circuit for the TPS7B81-Q1. Different external component values can be used, depending on the end application. An application may require a larger output capacitor during fast load steps to prevent a large drop on the output voltage. TI recommends using a low-equivalent series resistance (ESR) ceramic capacitor with an X5R- or X7R-type dielectric.




Figure 7-7. TPS7B81-Q1 Typical Application Schematic

7.2.1 Design Requirements

Use the parameters listed in Table 7-1 for this design example.

Table 7-1. Design Requirements Parameters

PARAMETER	VALUE	
Input voltage range	3 V to 40 V	
Output voltage	5 V or 3.3 V	
Output current	150 mA maximum	

7.2.2 Detailed Design Procedure

To begin the design process, determine the following:

- Input voltage range
- Output voltage
- Output current

7.2.2.1 Input Capacitor

Although an input capacitor is not required for stability, good analog design practice is to connect a 10-µF to 22-µF capacitor from IN to GND. This capacitor counteracts reactive input sources and improves transient response, input ripple rejection, and PSRR. The voltage rating must be greater than the maximum input voltage.

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

7.2.2.2 Output Capacitor

To ensure the stability of the TPS7B81-Q1, the device requires an output capacitor with a value in the range from 1 μ F to 200 μ F and with an ESR range between 0.001 Ω and 5 Ω . TI recommends selecting a ceramic capacitor with low ESR to improve the load transient response.

7.2.3 Application Curve




Figure 7-8. TPS7B81-Q1 Power-Up Waveform (5 V)

7.3 Power Supply Recommendations

The device is designed to operate from an input-voltage supply range from 3 V to 40 V. The input supply must be well regulated. If the input supply is located more than a few inches from the TPS7B81-Q1, TI recommends adding a capacitor with a value greater than or equal to 10 μ F with a 0.1- μ F bypass capacitor in parallel at the input.

7.4 Layout

7.4.1 Layout Guidelines

Layout is an important step for LDO power supplies, especially for high-voltage and large-output-current supplies. If the layout is not carefully designed, the regulator can fail to deliver enough output current because of thermal limitations. To improve the thermal performance of the device, and to maximize the current output at high ambient temperature, spread the copper under the thermal pad as far as possible and put enough thermal vias on the copper under the thermal pad. Figure 7-9 shows an example layout.



7.4.2 Layout Example




Figure 7-9. TPSB81-Q1 Example Layout Diagram

8 Device and Documentation Support

8.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.2 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.3 Trademarks

PowerPAD™ and TI E2E™ are trademarks of Texas Instruments. All trademarks are the property of their respective owners.

8.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.5 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision D (June 2020) to Revision E (June 2025)	Page
Added functional safety bullets to Features section	1
Changed power FET from NMOS to PMOS in Functional Block Diagram	
Changes from Revision C (April 2020) to Revision D (June 2020)	Page
• Changed the numbering format for tables, figures, and cross-references throughout the document	1
Added footnote and deleted V _{OUT} = 2.5 V rows from <i>Dropout voltage</i> parameter	6

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com

29-May-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking
	(1)	(2)			(3)	(4)	(5)		(6)
TPS7B8125QDGNRQ1	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	26GX
TPS7B8125QDGNRQ1.A	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	26GX
TPS7B8133QDGNRQ1	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1VTX
TPS7B8133QDGNRQ1.A	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1VTX
TPS7B8133QDRVRQ1	Active	Production	WSON (DRV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 150	1X2H
TPS7B8133QDRVRQ1.A	Active	Production	WSON (DRV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 150	1X2H
TPS7B8133QKVURQ1	Active	Production	TO-252 (KVU) 5	2500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 150	7B8133Q1
TPS7B8133QKVURQ1.A	Active	Production	TO-252 (KVU) 5	2500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 150	7B8133Q1
TPS7B8150QDGNRQ1	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1VUX
TPS7B8150QDGNRQ1.A	Active	Production	HVSSOP (DGN) 8	2500 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1VUX
TPS7B8150QDRVRQ1	Active	Production	WSON (DRV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 150	1WNH
TPS7B8150QDRVRQ1.A	Active	Production	WSON (DRV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 150	1WNH
TPS7B8150QKVURQ1	Active	Production	TO-252 (KVU) 5	2500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 150	7B8150Q1
TPS7B8150QKVURQ1.A	Active	Production	TO-252 (KVU) 5	2500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 150	7B8150Q1

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



PACKAGE OPTION ADDENDUM

www.ti.com 29-May-2025

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS7B81-Q1:

Catalog: TPS7B81


NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Apr-2025

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS7B8125QDGNRQ1	HVSSOP	DGN	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS7B8133QDGNRQ1	HVSSOP	DGN	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS7B8133QDRVRQ1	WSON	DRV	6	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TPS7B8133QKVURQ1	TO-252	KVU	5	2500	330.0	16.4	6.9	10.5	2.7	8.0	16.0	Q2
TPS7B8150QDGNRQ1	HVSSOP	DGN	8	2500	330.0	12.4	5.3	3.4	1.4	8.0	12.0	Q1
TPS7B8150QDRVRQ1	WSON	DRV	6	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
TPS7B8150QKVURQ1	TO-252	KVU	5	2500	330.0	16.4	6.9	10.5	2.7	8.0	16.0	Q2



www.ti.com 3-Apr-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS7B8125QDGNRQ1	HVSSOP	DGN	8	2500	366.0	364.0	50.0
TPS7B8133QDGNRQ1	HVSSOP	DGN	8	2500	366.0	364.0	50.0
TPS7B8133QDRVRQ1	WSON	DRV	6	3000	210.0	185.0	35.0
TPS7B8133QKVURQ1	TO-252	KVU	5	2500	340.0	340.0	38.0
TPS7B8150QDGNRQ1	HVSSOP	DGN	8	2500	366.0	364.0	50.0
TPS7B8150QDRVRQ1	WSON	DRV	6	3000	210.0	185.0	35.0
TPS7B8150QKVURQ1	TO-252	KVU	5	2500	340.0	340.0	38.0



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4206925/F





PLASTIC SMALL OUTLINE - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature
- number SLUA271 (www.ti.com/lit/slua271).

 5. Vias are optional depending on application, refer to device data sheet. If some or all are implemented, recommended via locations are shown.



PLASTIC SMALL OUTLINE - NO LEAD




NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



KVU (R-PSFM-G5)

PLASTIC FLANGE-MOUNT PACKAGE




NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- The center lead is in electrical contact with the exposed thermal tab.
- D. Body Dimensions do not include mold flash or protrusions. Mold flash and protrusion shall not exceed 0.006 (0,15) per side.
- E. Falls within JEDEC TO-252 variation AD.



KVU (R-PSFM-G5)

PLASTIC FLANGE MOUNT PACKAGE



NOTES:

- A. All linear dimensions are in millimeters.
- 3. This drawing is subject to change without notice.
- C. Publication IPC-SM-782 is an alternate information source for PCB land pattern designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for recommended solder mask tolerances and via tenting recommendations for vias placed in thermal pad.



3 x 3, 0.65 mm pitch

SMALL OUTLINE PACKAGE


This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



INSTRUMENTS www.ti.com

PowerPAD[™] HVSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



NOTES:

PowerPAD is a trademark of Texas Instruments.


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-187.



SMALL OUTLINE PACKAGE




NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- 8. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.
- 9. Size of metal pad may vary due to creepage requirement.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 10. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 11. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated