

UC1843A-SP NDD (Neutron Displacement Damage) Characterization



ABSTRACT

This report presents the effect of neutron displacement damage (NDD) on the UC1843A-SP device. The results show that all devices were fully functional and within production test limits after having been irradiated up to $1 \times 10^{12} \text{ n/cm}^2$. A sample size of three units were exposed to radiation testing per (MIL-STD-883, Method 1017 for Neutron Irradiation). Electrical testing was performed at Texas Instruments before and after neutron irradiation using the production test program for 5962P8670409VYC.

Table of Contents

1 Overview	1
2 Test Procedures	2
3 Facility	4
4 Results	4
A Test Results: Parameters	5
B Test Results: NDD Data	7

List of Figures

Figure 2-1. UC1843A-SP Device.....	3
------------------------------------	---

List of Tables

Table 1-1. Overview Information.....	2
Table 2-1. Neutron Irradiation Conditions.....	2
Table A-1. Test List.....	5

Trademarks

All trademarks are the property of their respective owners.

1 Overview

The UC1843A-SP control IC is a radiation hardened pin-for-pin compatible version of the UC184x family. Providing the necessary characteristics to control current-mode switched-mode power supplies, this device has improved features. Start-up current is specified to be less than 0.5 mA and oscillator discharge is trimmed to 8.3 mA. During UVLO, the output stage can sink at least 10 mA at less than 1.2 V for V_{CC} over 5 V.

General device information and testing conditions are listed in [Table 1-1](#).

Table 1-1. Overview Information

TI Part Number	UC1843A-SP
Device Function	Current-mode PWM controller
Die Name	SMEXARC1843VRH
Technology	JI-PWR1
A/T Lot Number / Date Code	6006096MMT/1629A
Biased Quantity Tested	0
Unbiased Quantity Tested	3
Exposure Facility	VPT Rad
Neutron Fluence (1-MeV equivalent)	$1.0 \times 10^{12} \text{ n/cm}^2$
Irradiation Temperature	25°C
TI may provide technical, applications or design advice, quality characterization, and reliability data or service providing these items shall not expand or otherwise affect TI's warranties as set forth in the Texas Instruments Incorporated <i>Standard Terms and Conditions of Sale for Semiconductor Products</i> and no obligation or liability shall arise from Semiconductor Products and no obligation or liability shall arise from TI's provision of such items.	

2 Test Procedures

The UC1843A-SP was electrically pre-tested using the production automated test equipment program. General test procedures were IAW MIL-STD-883, Method 1017 for Neutron Irradiation of UC1843A-SP as modified in [Table 2-1](#).

Table 2-1. Neutron Irradiation Conditions

Group	Sample Qty	Neutron Fluence (n/cm ²)	Bias
A	3	$1.0 \times 10^{12} \text{ n/cm}^2$	Unbiased



Figure 2-1. UC1843A-SP Device

3 Facility

VPT Rad performs all neutron displacement damage irradiations in a Low-Enriched, open-pool, water moderated, thermal neutron reactor. It utilizes flat-plate type fuel, and having a maximum thermal energy output of up to 1 MW. The Fast Neutron Irradiator (FNI) faces one side of the reactor core, its design produces a geometrical planar *beam* of fast neutrons that is approximately uniform over an area of 12 in \times 20 in. Lead and thermal neutron absorbing compounds are combined to filter out both fission gammas and thermal neutrons. The ratio of fast-to-thermal neutrons is approximately 400:1, with a gamma exposure of less than 150 rad(Si) for a 1×10^{12} n/cm² (1-MeV equivalent) exposure. The FNI can accommodate a sample or samples with size up to 30 cm in diameter and 15-cm thick including packaging materials. The minimum neutron fluence rate is 1×10^6 n/cm²-s. The maximum neutron fluence rate is approximately 1.0×10^{11} n/cm²-s (both values are 1-MeV equivalent).

The neutron fluence rate is determined using the previously-measured neutron radiation field for the FNI, performed in accordance with ASTM standards (ASTM F1190 &), and correlated to the measured reactor power level. The neutron dose is timed to meet the customer-specified fluence for the irradiation. Neutron dosimetry meeting ASTM standards (ASTM E265) is utilized to track and ensure irradiations meet the required minimum. The facility retains *source-suitability* with the Defense Logistics Agency (DLA) Laboratory Suitability Program for ASTM Test Method 1017. The DUTS are typically irradiation in an unbiased condition as per TM1017. If bias conditions are required, they can be maintained via dry thimbles connected to the irradiation volume.

4 Results

The device passed all parametric measurements well within all data sheet limits for the exposure level 1.0×10^{12} n/cm². An overview of the largest drifts seen post-test is discussed later in this section. The data sheet parameters that were tested pre- and post-neutron radiation and their corresponding test names are included in [Appendix A](#). [Appendix B](#) has the graphs showing the drift between pre- and post-neutron radiation for these parameters.

The output voltage parameter was reduced after neutron exposure. This parameter is measured with tests 1010.1 and 1010.2. Test 1010.1 showed this parameter drifted downward from an average value of 4.981 V to an average value of 4.962 V. Test 1010.2 showed this parameter drifted downward from an average value of 4.985 V to 4.965 V.

The input bias current parameter was reduced after neutron exposure. This parameter is measured with tests 1020.6, 1020.7, and 1020.8. Test 1020.6 showed this parameter drifted downward from an average value of $-0.103 \mu\text{A}$ to $-0.694 \mu\text{A}$. Test 1020.7 showed downward drift from an average value of $-0.093 \mu\text{A}$ to $-0.612 \mu\text{A}$. Test 1020.8 showed downward drift from an average value of $-0.084 \mu\text{A}$ to $-0.541 \mu\text{A}$.

A Test Results: Parameters

Table A-1 provides the list of tested parameters.

Table A-1. Test List

$V_{CC} = 15 \text{ V}^{(1)}$, $R_T = 10 \text{ k}\Omega$, $C_T = 3.3 \text{ nF}$, $T_A = T_J = -55^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETERS	TEST CONDITIONS	UC1843A-SP DATA SHEET SLUSCI6A – DECEMBER 2016 – REVISED FEBRUARY 2019				TEST# OR NAME
		MIN	TYP	MAX	UNIT	
REFERENCE						
Output voltage	$T_J = 25^\circ\text{C}$, $I_O = 1 \text{ mA}$	4.95	5	5.06	V	1010.1, 1010.2
Line regulation	$V_{IN} = 12$ to 25 V		6	20	mV	1010.3
Load regulation	$I_O = 1$ to 20 mA		6	25	mV	1010.4
Temperature stability ^{(2) (3)}			0.2	0.4	mV/ $^\circ\text{C}$	
Total output variation ⁽²⁾	Over line, load, and temperature	4.9		5.1	V	
Output noise voltage	$10 \text{ Hz} \leq f \leq 10 \text{ kHz}$, $T_J = 25^\circ\text{C}$		50		μV	1010.7
Long-term stability	1000 hours, $T_A = 125^\circ\text{C}^{(2)}$		5	25	mV	
Short-circuit output current		-30	-100	-180	mA	1010.6
OSCILLATOR						
Initial accuracy	$T_J = 25^\circ\text{C}^{(4)}$	47	52	57	kHz	1015.1, 1015.2
Voltage stability	$V_{CC} = 12$ to 25 V		0.2%	1%		1015.3
Temperature stability	$T_J = -55^\circ\text{C}$ to $125^\circ\text{C}^{(2)}$		5%			
Amplitude peak-to-peak	V pin 4 ⁽²⁾		1.7		V	1015.6
Discharge current	V pin 4 = $2 \text{ V}^{(5)}$, $T_J = 25^\circ\text{C}$	7.8	8.3	8.8	mA	1015.7
ERROR AMPLIFIER						
Input voltage	$V_{Comp} = 2.5 \text{ V}$	2.45	2.50	2.55	V	1020.1
Input bias current			-0.3	-1	μA	1020.6, 1020.7, 1020.8
Open-loop voltage gain	$V_O = 2$ to 4 V	65	90		dB	1020.9
Unity-gain bandwidth	$T_J = 25^\circ\text{C}^{(2)}$	0.7	1		MHz	
PSRR	$V_{CC} = 12$ to 25 V	60	70		dB	1020.10
Output sink current	$V_{FB} = 2.7 \text{ V}$, $V_{Comp} = 1.1 \text{ V}$	2	6		mA	1020.5
Output source current	$V_{FB} = 2.3 \text{ V}$, $V_{Comp} = 5 \text{ V}$	-0.5	-0.8		mA	1020.4
High-level output voltage	$V_{FB} = 2.3 \text{ V}$, $R_L = 15 \text{ k}\Omega$ to ground	5	6		V	1020.2
Low-level output voltage	$V_{FB} = 2.7 \text{ V}$, $R_L = 15 \text{ k}\Omega$ to V_{REF}		0.7	1.1	V	1020.3
CURRENT SENSE						
Gain ^{(6) (7)}		2.85	3	3.15	V/V	1025.2
Maximum input signal	$V_{Comp} = 5 \text{ V}^{(6)}$	0.9	1	1.1	V	1025.3
PSRR	$V_{CC} = 12$ to $25 \text{ V}^{(6)}$		70		dB	1020.10
Input bias current			-2	-10	μA	1025.1
Delay to output	$V_{ISENSE} = 0$ to $2 \text{ V}^{(2)}$		150	300	ns	1025.4

Table A-1. Test List (continued)
 $V_{CC} = 15 \text{ V}$ ⁽¹⁾, $R_T = 10 \text{ k}\Omega$, $C_T = 3.3 \text{ nF}$, $T_A = T_J = -55^\circ\text{C}$ to 125°C (unless otherwise noted)

PARAMETERS	TEST CONDITIONS	UC1843A-SP DATA SHEET SLUSCI6A – DECEMBER 2016 – REVISED FEBRUARY 2019				TEST# OR NAME
		MIN	TYP	MAX	UNIT	
OUTPUT						
Output low-level voltage	$I_{SINK} = 20 \text{ mA}$		0.1	0.4	V	1030.6
	$I_{SINK} = 200 \text{ mA}$		1.5	2.2		1030.7
Output high-level voltage	$I_{SOURCE} = -20 \text{ mA}$	13	13.5		V	1030.1
	$I_{SOURCE} = -200 \text{ mA}$	12	13.5			1030.2
Rise time	$C_L = 1 \text{ nF}$, $T_J = 25^\circ\text{C}$ ⁽²⁾		50	150	ns	1030.9
Fall time	$C_L = 1 \text{ nF}$, $T_J = 25^\circ\text{C}$ ⁽²⁾		50	150	ns	1030.10
UVLO saturation	$V_{CC} = 5 \text{ V}$, $I_{SINK} = 10 \text{ mA}$		0.7	1.2	V	1030.5
UNDERVOLTAGE LOCKOUT						
Start threshold		7.8	8.4	9	V	1035.1
Minimum operation voltage after turnon		7	7.6	8.2	V	1035.2
PWM						
Maximum duty cycle		94%	96%	100%		1030.11, 1030.12
Minimum duty cycle				0%		1030.13
TOTAL STANDBY CURRENT						
Start-up current			0.3	0.5	mA	1005.1
Operating supply current	$V_{FB} = V_{ISENSE} = 0 \text{ V}$		11	17	mA	1005.2, 1005.3
V_{CC} Zener voltage	$I_{CC} = 25 \text{ mA}$	30	34		V	1035.4

- (1) Adjust V_{CC} above the start threshold before setting at 15 V.
- (2) Parameters ensured by design and/or characterization, if not production tested.
- (3) Temperature stability, sometimes referred to as average temperature coefficient, is described by the equation: Temperature Stability = $V_{REF(max)} - V_{REF(min)} / TJ_{(max)} - TJ_{(min)}$. $V_{REF(max)}$ and $V_{REF(min)}$ are the maximum and minimum reference voltage measured over the appropriate temperature range. Note that the extremes in voltage do not necessarily occur at the extremes in temperature.
- (4) Output frequency equals oscillator frequency for the UC1842A-SP and UC1843A-SP.
- (5) This parameter is measured with $R_T = 10 \text{ k}\Omega$ to V_{REF} . This contributes approximately 300 μA of current to the measurement. The total current flowing into the RT or CT pin will be approximately 300 μA higher than the measured value.
- (6) Parameter measured at trip point of latch with $V_{FB} = 0 \text{ V}$.
- (7) Gain defined as: $G = \Delta V_{Comp} / \Delta V_{ISENSE}$; $V_{ISENSE} = 0$ to 0.8 V.

B Test Results: NDD Data

[Appendix B](#) shows the detailed test results.


NDD Report - Parametric Drift Graphs

UC1843A-SP


NDD Report - Parametric Drift Graphs

UC1843A-SP

1005.1 __ICC Start Up				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	µA
Max Limit	500	500	Min Limit	0
Min Limit	0	0		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	127.332	122.787	-4.545
1E+12	231	130.379	126.613	-3.766
1E+12	232	126.523	122.120	-4.402
0	233	127.961	127.615	-0.346
	Max	130.379	127.615	-0.346
	Average	128.049	124.784	-3.265
	Min	126.523	122.120	-4.545
	Std Dev	1.661	2.735	1.975




1005.1 __ICC Start Up				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	µA
Max Limit	500	500	Min Limit	0
N/cm ²	0	1E+12		
LL	0.000	0.000		
Min	127.615	122.120		
Average	127.615	123.840		
Max	127.615	126.613		
UL	500.000	500.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1005.2 _ICC @ 15V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	mA	mA		
Min Limit	17	17		
	0	0		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	13.327	13.026	-0.301
1E+12	231	13.517	13.243	-0.275
1E+12	232	13.168	12.833	-0.335
0	233	13.340	13.349	0.009
	Max	13.517	13.349	0.009
	Average	13.338	13.113	-0.226
	Min	13.168	12.833	-0.335
	Std Dev	0.143	0.230	0.158




1005.2 _ICC @ 15V		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	17	mA
Min Limit	0	mA
N/cm ²	0	1E+12
LL	0.000	0.000
Min	13.349	12.833
Average	13.349	13.034
Max	13.349	13.243
UL	17.000	17.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1005.3 _ICC @ 30V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	mA	mA		
Min Limit	17	17		
Delta	0	0		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	14.083	13.786	-0.297
1E+12	231	14.287	13.995	-0.292
1E+12	232	13.933	13.590	-0.343
0	233	14.100	14.113	0.013
	Max	14.287	14.113	0.013
	Average	14.101	13.871	-0.230
	Min	13.933	13.590	-0.343
	Std Dev	0.145	0.231	0.163




1005.3 _ICC @ 30V		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	17	mA
Min Limit	0	mA
N/cm ²	0	1E+12
LL	0.000	0.000
Min	14.114	13.590
Average	14.114	13.790
Max	14.114	13.995
UL	17.000	17.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.1 __VREF @ 15V, 1mA				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	V	V		
Max Limit	5.06	5.06		
Min Limit	4.95	4.95		
N/cm²	Serial #	Pre	Post	Delta
1E+12	230	4.986	4.966	-0.020
1E+12	231	4.966	4.953	-0.013
1E+12	232	4.991	4.965	-0.026
0	233	4.997	4.997	0.000
Max		4.997	4.997	0.000
Average		4.985	4.970	-0.015
Min		4.966	4.953	-0.026
Std Dev		0.013	0.019	0.011




1010.1 __VREF @ 15V, 1mA				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Max Limit	5.06	V		
Min Limit	4.95	V		
N/cm²	0	1E+12		
LL	4.950	4.950		
Min	4.997	4.953		
Average	4.997	4.962		
Max	4.997	4.966		
UL	5.060	5.060		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.2 __VREF @ 32V, 1mA				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	V	V		
Max Limit	5.06	5.06		
Min Limit	4.95	4.95		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	4.990	4.970	-0.020
1E+12	231	4.970	4.956	-0.013
1E+12	232	4.995	4.969	-0.026
0	233	5.000	5.000	0.000
	Max	5.000	5.000	0.000
	Average	4.988	4.974	-0.015
	Min	4.970	4.956	-0.026
	Std Dev	0.013	0.018	0.011




1010.2 __VREF @ 32V, 1mA				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Max Limit	5.06	V		
Min Limit	4.95	V		
N/cm ²	0	1E+12		
LL	4.950	4.950		
Min	5.000	4.956		
Average	5.000	4.965		
Max	5.000	4.970		
UL	5.060	5.060		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.3 __ Line Reg @ 12V to 25V				
Test Site	Junkins Lab	Junkins Lab	Unit	
Tester	ETS364	ETS364	Max Limit	20
Test Number	EF230103	EF230103	mV	mV
Min Limit	-20	-20	Delta	
N/cm ²	Serial #	Pre	Post	
1E+12	230	2.321	2.317	-0.004
1E+12	231	2.303	2.315	0.011
1E+12	232	2.225	2.237	0.013
0	233	2.391	2.331	-0.060
	Max	2.391	2.331	0.013
	Average	2.310	2.300	-0.010
	Min	2.225	2.237	-0.060
	Std Dev	0.068	0.042	0.034




1010.3 __ Line Reg @ 12V to 25V				
Test Site	Junkins Lab		Unit	
Tester	ETS364		Max Limit	20
Test Number	EF230103		mV	mV
Min Limit	-20		mV	mV
N/cm ²	0		1E+12	
LL	-20.000		-20.000	
Min	2.331		2.238	
Average	2.331		2.290	
Max	2.331		2.317	
UL	20.000		20.000	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.4 __ Load Reg @ 1mA to 20mA				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	mV	mV		
Max Limit	20	20		
Min Limit	-20	-20		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	8.448	3.093	-5.355
1E+12	231	14.108	3.002	-11.106
1E+12	232	5.032	2.641	-2.391
0	233	5.110	1.748	-3.362
	Max	14.108	3.093	-2.391
	Average	8.175	2.621	-5.553
	Min	5.032	1.748	-11.106
	Std Dev	4.264	0.614	3.902




1010.4 __ Load Reg @ 1mA to 20mA				
Test Site	Junkins Lab			
Tester	ETS364			
Test Number	EF230103			
Max Limit	20	mV		
Min Limit	-20	mV		
N/cm ²	0		1E+12	
LL	-20.000		-20.000	
Min	1.748		2.641	
Average	1.748		2.912	
Max	1.748		3.093	
UL	20.000		20.000	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.6 __VREF Short Circuit				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	mA	mA		
Max Limit	-30	-30		
Min Limit	-180	-180		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	-112.633	-106.337	6.296
1E+12	231	-112.580	-101.649	10.931
1E+12	232	-111.962	-104.955	7.006
0	233	-107.307	-106.714	0.592
	Max	-107.307	-101.649	10.931
	Average	-111.120	-104.914	6.206
	Min	-112.633	-106.714	0.592
	Std Dev	2.561	2.304	4.262




1010.6 __VREF Short Circuit				
Test Site	Junkins Lab			
Tester	ETS364			
Test Number	EF230103			
Max Limit	-30	mA		
Min Limit	-180	mA		
N/cm ²	0	1E+12		
LL	-180.000	-180.000		
Min	-106.714	-106.337		
Average	-106.714	-104.314		
Max	-106.714	-101.649		
UL	-30.000	-30.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1010.7 __Output Noise Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	190	190	μV	
Min Limit	10	10	μV	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	68.584	72.184	3.600
1E+12	231	71.389	82.623	11.234
1E+12	232	74.098	69.329	-4.769
0	233	86.921	66.913	-20.008
	Max	86.921	82.623	11.234
	Average	75.248	72.762	-2.486
	Min	68.584	66.913	-20.008
	Std Dev	8.101	6.918	13.385




1010.7 __Output Noise Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	190	190	μV	
Min Limit	10	10	μV	
N/cm ²	0	1E+12		
LL	10.000	10.000		
Min	66.913	69.329		
Average	66.913	74.712		
Max	66.913	82.623		
UL	190.000	190.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1015.1 __OSC Freq @ VCC=15V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	57	57		
Min Limit	47	47		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	51.735	51.919	0.184
1E+12	231	51.543	51.728	0.185
1E+12	232	51.675	51.920	0.245
0	233	51.657	51.711	0.055
	Max	51.735	51.920	0.245
	Average	51.652	51.819	0.167
	Min	51.543	51.711	0.055
	Std Dev	0.081	0.116	0.080




1015.1 __OSC Freq @ VCC=15V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	57	57	Unit	
Min Limit	47	47	Unit	
N/cm ²	0	1E+12		
LL	47.000	47.000		
Min	51.711	51.728		
Average	51.711	51.855		
Max	51.711	51.920		
UL	57.000	57.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1015.2 __OSC Freq @ VCC=9.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	57	57		
Min Limit	47	47		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	51.767	51.945	0.178
1E+12	231	51.550	51.724	0.174
1E+12	232	51.688	51.926	0.238
0	233	51.671	51.684	0.013
	Max	51.767	51.945	0.238
	Average	51.669	51.820	0.151
	Min	51.550	51.684	0.013
	Std Dev	0.090	0.135	0.096




1015.2 __OSC Freq @ VCC=9.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	57	57	Unit	
Min Limit	47	47	Unit	
N/cm ²	0	1E+12		
LL	47.000	47.000		
Min	51.684	51.725		
Average	51.684	51.865		
Max	51.684	51.945		
UL	57.000	57.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1015.3 __Voltage Stability				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	%	%		
Max Limit	1	1		
Min Limit	-1	-1		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	0.078	0.082	0.004
1E+12	231	0.074	0.057	-0.017
1E+12	232	0.084	0.066	-0.017
0	233	0.132	0.073	-0.058
	Max	0.132	0.082	0.004
	Average	0.092	0.070	-0.022
	Min	0.074	0.057	-0.058
	Std Dev	0.027	0.011	0.026




1015.3 __Voltage Stability				
Test Site	Junkins Lab			
Tester	ETS364			
Test Number	EF230103			
Max Limit	1	%		
Min Limit	-1	%		
N/cm ²	0	1E+12		
LL	-1.000	-1.000		
Min	0.073	0.057		
Average	0.073	0.068		
Max	0.073	0.082		
UL	1.000	1.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1015.6 __Peak to Peak Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	2.989	2.989	V	V
Min Limit	1.011	1.011		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	1.639	1.622	-0.017
1E+12	231	1.639	1.628	-0.010
1E+12	232	1.635	1.622	-0.014
0	233	1.642	1.635	-0.007
	Max	1.642	1.635	-0.007
	Average	1.639	1.627	-0.012
	Min	1.635	1.622	-0.017
	Std Dev	0.003	0.007	0.004




1015.6 __Peak to Peak Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	EF230103	EF230103	Unit	
Max Limit	2.989	2.989	V	V
Min Limit	1.011	1.011	V	V
N/cm ²	0	1E+12		
LL	1.011	1.011		
Min	1.635	1.622		
Average	1.635	1.624		
Max	1.635	1.629		
UL	2.989	2.989		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1015.7 __Discharge Current				
Test Site	Junkins Lab	Junkins Lab	Unit	
Tester	ETS364	ETS364	Max Limit	8.8
Test Number	EF230103	EF230103	Min Limit	7.8
mA	mA	mA	mA	mA
1E+12	230	8.667	8.623	-0.044
1E+12	231	8.400	8.373	-0.027
1E+12	232	8.419	8.362	-0.057
0	233	8.528	8.527	-0.001
	Max	8.667	8.623	-0.001
	Average	8.504	8.471	-0.033
	Min	8.400	8.362	-0.057
	Std Dev	0.123	0.126	0.024




1015.7 __Discharge Current				
Test Site	Junkins Lab			
Tester	ETS364			
Test Number	EF230103			
Max Limit	8.8	mA		
Min Limit	7.8	mA		
N/cm ²	0		1E+12	
LL	7.800		7.800	
Min	8.527		8.362	
Average	8.527		8.453	
Max	8.527		8.623	
UL	8.800		8.800	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.1 __Vin @ COMP=2.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	2.55	2.55	V	
Min Limit	2.45	2.45	V	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	2.510	2.503	-0.007
1E+12	231	2.496	2.492	-0.003
1E+12	232	2.509	2.499	-0.010
0	233	2.507	2.507	0.000
	Max	2.510	2.507	0.000
	Average	2.505	2.500	-0.005
	Min	2.496	2.492	-0.010
	Std Dev	0.007	0.007	0.004




1020.1 __Vin @ COMP=2.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	2.55	2.55	V	
Min Limit	2.45	2.45	V	
N/cm ²	0	1E+12		
LL	2.450	2.450		
Min	2.507	2.492		
Average	2.507	2.498		
Max	2.507	2.503		
UL	2.550	2.550		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.2 __VOH				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	V	V		
Min Limit	8	8		
	5	5		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	5.683	5.664	-0.019
1E+12	231	5.671	5.659	-0.012
1E+12	232	5.689	5.662	-0.027
0	233	5.696	5.696	0.000
	Max	5.696	5.696	0.000
	Average	5.685	5.670	-0.014
	Min	5.671	5.659	-0.027
	Std Dev	0.011	0.017	0.011




1020.2 __VOH				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	EF230103	EF230103	Unit	
Min Limit	V	V	Unit	
N/cm ²	0	1E+12		
LL	5.000	5.000		
Min	5.696	5.659		
Average	5.696	5.662		
Max	5.696	5.664		
UL	8.000	8.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.3 _VOL				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	V	V		
Max Limit	1.1	1.1		
Min Limit	0	0		
N/cm²	Serial #	Pre	Post	Delta
1E+12	230	0.833	0.837	0.004
1E+12	231	0.830	0.835	0.005
1E+12	232	0.832	0.835	0.003
0	233	0.832	0.832	0.000
Max		0.833	0.837	0.005
Average		0.832	0.834	0.003
Min		0.830	0.832	0.000
Std Dev		0.001	0.002	0.002




1020.3 _VOL				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Max Limit	1.1	V		
Min Limit	0	V		
N/cm²	LL	0	1E+12	
LL	0.000	0.000		
Min	0.832	0.835		
Average	0.832	0.835		
Max	0.832	0.837		
UL	1.100	1.100		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.4 __Isource				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	mA
Max Limit	-0.5	-0.5	Min Limit	-5
Min Limit	-5	-5		
N/cm²	Serial #	Pre	Post	Delta
1E+12	230	-0.887	-0.871	0.016
1E+12	231	-0.959	-0.945	0.014
1E+12	232	-0.874	-0.858	0.016
0	233	-0.892	-0.891	0.001
	Max	-0.874	-0.858	0.016
	Average	-0.903	-0.891	0.012
	Min	-0.959	-0.945	0.001
	Std Dev	0.038	0.038	0.007




1020.4 __Isource				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	mA
Max Limit	-0.5	-0.5	Min Limit	-5
				mA
N/cm²	0	1E+12		
LL	-5.000	-5.000		
Min	-0.891	-0.945		
Average	-0.891	-0.892		
Max	-0.891	-0.858		
UL	-0.500	-0.500		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.5 __Isink				
Test Site	Junkins Lab	Junkins Lab	Unit	
Tester	ETS364	ETS364	Max Limit	20
Test Number	EF230103	EF230103	mA	mA
Unit	mA	mA	Max Limit	20
Max Limit	20	20	Min Limit	2
Min Limit	2	2	Delta	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	6.163	6.060	-0.103
1E+12	231	6.546	6.433	-0.113
1E+12	232	6.209	6.112	-0.097
0	233	6.291	6.301	0.010
	Max	6.546	6.433	0.010
	Average	6.302	6.226	-0.076
	Min	6.163	6.060	-0.113
	Std Dev	0.171	0.172	0.057




1020.5 __Isink	
Test Site	Junkins Lab
Tester	ETS364
Test Number	EF230103
Max Limit	20
Min Limit	2
	mA
	mA
N/cm ²	
LL	0
Min	2.000
Average	6.301
Max	6.301
UL	20.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.6 __Ibias @ VFB=0.0V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	-0.001	-0.001	μA	
Min Limit	-1	-1	μA	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	-0.103	-0.712	-0.609
1E+12	231	-0.101	-0.666	-0.565
1E+12	232	-0.104	-0.705	-0.601
0	233	-0.103	-0.103	0.000
	Max	-0.101	-0.103	0.000
	Average	-0.103	-0.546	-0.444
	Min	-0.104	-0.712	-0.609
	Std Dev	0.001	0.297	0.297




1020.6 __Ibias @ VFB=0.0V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	EF230103	EF230103	μA	
Min Limit	-0.001	-1	μA	
N/cm ²	0	1E+12	μA	
LL	-1.000	-1.000	μA	
Min	-0.103	-0.712	μA	
Average	-0.103	-0.694	μA	
Max	-0.103	-0.666	μA	
UL	-0.001	-0.001	μA	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.7 __Ibias @ VFB=2.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	-0.001	-0.001	μA	
Min Limit	-1	-1	μA	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	-0.094	-0.629	-0.535
1E+12	231	-0.092	-0.585	-0.493
1E+12	232	-0.095	-0.623	-0.528
0	233	-0.094	-0.094	0.000
	Max	-0.092	-0.094	0.000
	Average	-0.094	-0.483	-0.389
	Min	-0.095	-0.629	-0.535
	Std Dev	0.001	0.260	0.260




1020.7 __Ibias @ VFB=2.5V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	EF230103	EF230103	μA	
Min Limit	-0.001	-1	μA	
N/cm ²	0	1E+12	μA	
LL	-1.000	-1.000	μA	
Min	-0.094	-0.629	μA	
Average	-0.094	-0.612	μA	
Max	-0.094	-0.585	μA	
UL	-0.001	-0.001	μA	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.8 __Ibias @ VFB=5.0V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
	μA	μA		
Max Limit	-0.001	-0.001		
Min Limit	-1	-1		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	-0.085	-0.556	-0.472
1E+12	231	-0.083	-0.517	-0.435
1E+12	232	-0.085	-0.551	-0.465
0	233	-0.085	-0.085	0.000
	Max	-0.083	-0.085	0.000
	Average	-0.084	-0.427	-0.343
	Min	-0.085	-0.556	-0.472
	Std Dev	0.001	0.229	0.229




1020.8 __Ibias @ VFB=5.0V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	EF230103	EF230103	Unit	
Max Limit	-0.001	-0.001	μA	μA
Min Limit	-1	-1	μA	μA
N/cm ²	0	1E+12		
LL	-1.000	-1.000		
Min	-0.085	-0.556		
Average	-0.085	-0.541		
Max	-0.085	-0.517		
UL	-0.001	-0.001		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.9 __AVOL				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	dB	dB		
Max Limit	200	200		
Min Limit	65	65		
N/cm²	Serial #	Pre	Post	Delta
1E+12	230	97.804	86.787	-11.016
1E+12	231	82.259	83.950	1.692
1E+12	232	75.491	81.142	5.651
0	233	81.190	99.030	17.839
	Max	97.804	99.030	17.839
	Average	84.186	87.727	3.541
	Min	75.491	81.142	-11.016
	Std Dev	9.552	7.879	11.892




1020.9 __AVOL		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	200	dB
Min Limit	65	dB
N/cm²	0	1E+12
LL	65.000	65.000
Min	99.030	81.142
Average	99.030	83.960
Max	99.030	86.787
UL	200.000	200.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1020.10_PSRR				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	dB	dB		
Min Limit	130	130		
	60	60		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	80.377	81.497	1.120
1E+12	231	82.223	81.514	-0.709
1E+12	232	81.070	82.134	1.064
0	233	82.734	82.222	-0.512
	Max	82.734	82.222	1.120
	Average	81.601	81.842	0.241
	Min	80.377	81.497	-0.709
	Std Dev	1.073	0.390	0.987




1020.10_PSRR	
Test Site	Junkins Lab
Tester	ETS364
Test Number	EF230103
Max Limit	130 dB
Min Limit	60 dB
N/cm ²	0 1E+12
LL	60.000 60.000
Min	82.222 81.497
Average	82.222 81.715
Max	82.222 82.134
UL	130.000 130.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1025.1 __Input Bias Current				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
	μA	μA		
Max Limit	10	10		
Min Limit	-10	-10		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	-1.295	-3.227	-1.932
1E+12	231	-1.293	-3.149	-1.856
1E+12	232	-1.282	-3.149	-1.868
0	233	-1.280	-1.280	0.000
	Max	-1.280	-1.280	0.000
	Average	-1.287	-2.701	-1.414
	Min	-1.295	-3.227	-1.932
	Std Dev	0.008	0.948	0.943




1025.1 __Input Bias Current				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	10	10	μA	
Min Limit	-10	-10	μA	
N/cm ²	0	1E+12	μA	
LL	-10.000	-10.000	μA	
Min	-1.280	-3.227	μA	
Average	-1.280	-3.175	μA	
Max	-1.280	-3.149	μA	
UL	10.000	10.000	μA	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1025.2 __Gain				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	3.15	3.15		
Min Limit	2.85	2.85		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	3.028	3.016	-0.013
1E+12	231	3.016	3.016	0.000
1E+12	232	3.016	3.016	0.000
0	233	3.016	3.016	0.000
	Max	3.028	3.016	0.000
	Average	3.019	3.016	-0.003
	Min	3.016	3.016	-0.013
	Std Dev	0.006	0.000	0.006




1025.2 __Gain				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	3.15	3.15		
Min Limit	2.85	2.85		
N/cm ²	0	1E+12		
LL	2.850	2.850		
Min	3.016	3.016		
Average	3.016	3.016		
Max	3.016	3.016		
UL	3.150	3.150		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1025.3 __Max Input				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	1.1	1.1	Min Limit	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	1.005	1.002	-0.003
1E+12	231	1.002	1.002	0.000
1E+12	232	1.012	1.008	-0.003
0	233	1.008	1.008	0.000
	Max	1.012	1.008	0.000
	Average	1.007	1.005	-0.002
	Min	1.002	1.002	-0.003
	Std Dev	0.004	0.004	0.002




1025.3 __Max Input				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	EF230103	EF230103	Unit	
Max Limit	1.1	V	Min Limit	V
N/cm ²	0	1E+12		
LL	0.900	0.900		
Min	1.008	1.002		
Average	1.008	1.004		
Max	1.008	1.008		
UL	1.100	1.100		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1025.4 __Out Delay				
Test Site	Junkins Lab	Junkins Lab	Tester	
Tester	ETS364	ETS364	Test Number	EF230103
Test Number	EF230103	EF230103	Unit	nS
Unit	nS	nS	Max Limit	300
Max Limit	300	300	Min Limit	50
Min Limit	50	50		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	142.961	141.036	-1.925
1E+12	231	135.297	132.895	-2.403
1E+12	232	145.452	143.174	-2.278
0	233	141.583	141.053	-0.530
	Max	145.452	143.174	-0.530
	Average	141.323	139.540	-1.784
	Min	135.297	132.895	-2.403
	Std Dev	4.325	4.542	0.860




1025.4 __Out Delay		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	300	nS
Min Limit	50	nS
N/cm ²	0	1E+12
LL	50.000	50.000
Min	141.053	132.895
Average	141.053	139.035
Max	141.053	143.174
UL	300.000	300.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.1 __VOH @ -20mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	V	V		
Min Limit	15	15		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	13.545	13.544	-0.001
1E+12	231	13.546	13.548	0.003
1E+12	232	13.547	13.547	0.000
0	233	13.547	13.549	0.003
	Max	13.547	13.549	0.003
	Average	13.546	13.547	0.001
	Min	13.545	13.544	-0.001
	Std Dev	0.001	0.002	0.002




1030.1 __VOH @ -20mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	EF230103	EF230103	Unit	
Min Limit	15	15	Unit	V
N/cm ²	0	1E+12		
LL	13.000	13.000		
Min	13.549	13.544		
Average	13.549	13.546		
Max	13.549	13.548		
UL	15.000	15.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.2 __VOH @ -200mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	15	15	Min Limit	
Min Limit	12	12		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	13.333	13.354	0.021
1E+12	231	13.305	13.369	0.064
1E+12	232	13.341	13.359	0.018
0	233	13.348	13.364	0.016
	Max	13.348	13.369	0.064
	Average	13.332	13.362	0.030
	Min	13.305	13.354	0.016
	Std Dev	0.019	0.006	0.023




1030.2 __VOH @ -200mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	15	V	Min Limit	V
N/cm ²	0	1E+12		
LL	12.000	12.000	Min	
Min	13.364	13.354	Average	
Average	13.364	13.361	Max	
Max	13.364	13.369	UL	
UL	15.000	15.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.5 __ UVLO Vsat				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	V	V		
Min Limit	1.2	1.2		
	0.005	0.005		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	0.173	0.752	0.579
1E+12	231	0.154	0.756	0.602
1E+12	232	0.140	0.663	0.524
0	233	0.154	0.367	0.213
	Max	0.173	0.756	0.602
	Average	0.155	0.635	0.479
	Min	0.140	0.367	0.213
	Std Dev	0.014	0.183	0.181




1030.5 __ UVLO Vsat				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	EF230103	EF230103	Unit	
Max Limit	1.2	V	Min Limit	V
	0.005			
N/cm ²	0	1E+12		
LL	0.005	0.005	Min	0.005
Min	0.367	0.663	Average	0.724
Average	0.367	0.756	Max	0.756
Max	1.200	1.200	UL	1.200




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.6 __VOL @ 20mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Tester	ETS364	ETS364	Test Number	EF230103
Test Number	EF230103	EF230103	Unit	V
Max Limit	0.4	0.4	Min Limit	0.01
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	0.074	0.078	0.004
1E+12	231	0.071	0.073	0.002
1E+12	232	0.074	0.078	0.004
0	233	0.072	0.071	-0.001
	Max	0.074	0.078	0.004
	Average	0.073	0.075	0.002
	Min	0.071	0.071	-0.001
	Std Dev	0.002	0.003	0.002




1030.6 __VOL @ 20mA		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	0.4	V
Min Limit	0.01	V
N/cm ²	0	1E+12
LL	0.010	0.010
Min	0.071	0.073
Average	0.071	0.076
Max	0.071	0.078
UL	0.400	0.400




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.7 __VOL @ 200mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	V	V		
Min Limit	2.2	2.2		
	0.5	0.5		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	1.656	1.656	0.000
1E+12	231	1.617	1.615	-0.001
1E+12	232	1.652	1.653	0.001
0	233	1.640	1.633	-0.007
	Max	1.656	1.656	0.001
	Average	1.641	1.640	-0.002
	Min	1.617	1.615	-0.007
	Std Dev	0.018	0.019	0.003




1030.7 __VOL @ 200mA				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	2.2	V	Min Limit	V
	0.5			
N/cm ²	0	1E+12		
LL	0.500	0.500		
Min	1.633	1.615		
Average	1.633	1.642		
Max	1.633	1.657		
UL	2.200	2.200		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.9 __Rise Time @ 1nF				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	nS
Max Limit	150	150	Min Limit	15
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	47.994	40.882	-7.112
1E+12	231	40.634	33.684	-6.950
1E+12	232	47.269	39.877	-7.392
0	233	45.537	44.778	-0.759
Max		47.994	44.778	-0.759
Average		45.359	39.805	-5.553
Min		40.634	33.684	-7.392
Std Dev		3.314	4.596	3.202




1030.9 __Rise Time @ 1nF		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	150	nS
Min Limit	15	nS
N/cm ²	0	1E+12
LL	15.000	15.000
Min	44.778	33.684
Average	44.778	38.148
Max	44.778	40.882
UL	150.000	150.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.10_Fall time @ 1nF				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	150	150	nS	
Min Limit	15	15	nS	
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	39.609	40.205	0.596
1E+12	231	37.426	37.858	0.432
1E+12	232	40.121	40.900	0.780
0	233	38.999	38.887	-0.111
	Max	40.121	40.900	0.780
	Average	39.038	39.462	0.424
	Min	37.426	37.858	-0.111
	Std Dev	1.169	1.357	0.384




1030.10_Fall time @ 1nF	
Test Site	Junkins Lab
Tester	ETS364
Test Number	EF230103
Max Limit	150
Min Limit	15
N/cm ²	0
LL	15.000
Min	38.887
Average	38.887
Max	38.887
UL	150.000
	15.000
	37.858
	39.654
	40.900
	150.000




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.11_Max Duty Cycle				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103	%	%
Max Limit	100	100	Min Limit	
Min Limit	94	94		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	96.026	96.100	0.073
1E+12	231	96.014	96.095	0.081
1E+12	232	95.932	96.007	0.076
0	233	95.975	95.976	0.000
	Max	96.026	96.100	0.081
	Average	95.987	96.044	0.057
	Min	95.932	95.976	0.000
	Std Dev	0.043	0.062	0.038




1030.11_Max Duty Cycle				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	100	%	Min Limit	%
N/cm ²	0		1E+12	
LL	94.000		94.000	
Min	95.976		96.007	
Average	95.976		96.067	
Max	95.976		96.100	
UL	100.000		100.000	




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.12__Max DC @ VCC=30V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103	%	%
Max Limit	100	100	Min Limit	
Min Limit	94	94		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	96.047	96.139	0.092
1E+12	231	96.057	96.135	0.078
1E+12	232	95.958	96.049	0.090
0	233	96.007	96.004	-0.002
	Max	96.057	96.139	0.092
	Average	96.017	96.082	0.065
	Min	95.958	96.004	-0.002
	Std Dev	0.045	0.066	0.045




1030.12__Max DC @ VCC=30V				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	100	%	Min Limit	%
N/cm ²	0	1E+12		
LL	94.000	94.000	Min	
Min	96.004	96.049	Average	
Average	96.004	96.108	Max	
Max	96.004	96.139	UL	
UL	100.000	100.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1030.13_Min Duty Cycle				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	%	%		
Max Limit	0.01	0.01		
Min Limit	-0.01	-0.01		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	0.000	0.000	0.000
1E+12	231	0.000	0.000	0.000
1E+12	232	0.000	0.000	0.000
0	233	0.000	0.000	0.000
	Max	0.000	0.000	0.000
	Average	0.000	0.000	0.000
	Min	0.000	0.000	0.000
	Std Dev	0.000	0.000	0.000




1030.13_Min Duty Cycle		
Test Site	Junkins Lab	
Tester	ETS364	
Test Number	EF230103	
Max Limit	0.01	%
Min Limit	-0.01	%
N/cm ²	0	1E+12
LL	-0.010	-0.010
Min	0.000	0.000
Average	0.000	0.000
Max	0.000	0.000
UL	0.010	0.010




NDD Report - Parametric Drift Graphs

UC1843A-SP

1035.1 __ UVLO Start				
Test Site	Junkins Lab	Junkins Lab		
Tester	ETS364	ETS364		
Test Number	EF230103	EF230103		
Unit	V	V		
Max Limit	9	9		
Min Limit	7.8	7.8		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	8.534	8.516	-0.018
1E+12	231	8.534	8.510	-0.024
1E+12	232	8.522	8.504	-0.018
0	233	8.522	8.528	0.006
	Max	8.534	8.528	0.006
	Average	8.528	8.515	-0.014
	Min	8.522	8.504	-0.024
	Std Dev	0.007	0.010	0.013




1035.1 __ UVLO Start				
Test Site	Junkins Lab			
Tester	ETS364			
Test Number	EF230103			
Max Limit	9	V		
Min Limit	7.8	V		
N/cm ²	0	1E+12		
LL	7.800	7.800		
Min	8.528	8.504		
Average	8.528	8.510		
Max	8.528	8.516		
UL	9.000	9.000		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1035.2 __ UVLO Stop				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	V
Max Limit	8.2	8.2	Min Limit	7
Min Limit	7	7		
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	7.339	7.350	0.011
1E+12	231	7.350	7.360	0.011
1E+12	232	7.328	7.344	0.016
0	233	7.328	7.339	0.011
	Max	7.350	7.360	0.016
	Average	7.336	7.348	0.012
	Min	7.328	7.339	0.011
	Std Dev	0.010	0.009	0.003




1035.2 __ UVLO Stop				
Test Site	Junkins Lab	Junkins Lab	Tester	ETS364
Test Number	EF230103	EF230103	Unit	V
Max Limit	8.2	8.2	Min Limit	7
N/cm ²	0	1E+12		
LL	7.000	7.000	Min	7.339
Min	7.339	7.344	Average	7.339
Average	7.339	7.351	Max	7.339
Max	7.339	7.360	UL	8.200
UL	8.200	8.200		




NDD Report - Parametric Drift Graphs

UC1843A-SP

1035.4 __VCC Zener Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
	EF230103	EF230103		
Max Limit	44.7	44.7	V	V
Min Limit	30	30	V	V
N/cm ²	Serial #	Pre	Post	Delta
1E+12	230	32.250	32.262	0.011
1E+12	231	32.225	32.227	0.002
1E+12	232	32.225	32.251	0.026
0	233	32.218	32.253	0.035
	Max	32.250	32.262	0.035
	Average	32.230	32.248	0.018
	Min	32.218	32.227	0.002
	Std Dev	0.014	0.015	0.015



1035.4 __VCC Zener Voltage				
Test Site	Junkins Lab	Junkins Lab	Tester	
Test Number	ETS364	ETS364	Unit	
Max Limit	44.7	44.7	V	V
Min Limit	30	30	V	V
N/cm ²	0	1E+12		
LL	30.000	30.000		
Min	32.253	32.227		
Average	32.253	32.246		
Max	32.253	32.262		
UL	44.700	44.700		



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated