



TMUX611x $\pm 17V$ 、低容量、低リーク電流、高精度のクワッド SPST スイッチ

1 特長

- 広い電源電圧範囲: $\pm 5V \sim \pm 17V$ (デュアル)、 $10V \sim 17V$ (シングル)
- すべてのピンで、JESD78 Class II Level A 準拠の 100mA を満たすラッチアップ性能
- 小さいオン容量: 4.2pF
- 低い入力リーク電流: 0.5pA
- 低い電荷注入: 0.6pC
- レール・ツー・レール動作
- 低いオン抵抗: 120 Ω
- 高速なスイッチのターンオン時間: 66ns
- Break-Before-Make のスイッチング動作 (TMUX6113)
- V_{DD} に接続可能な EN ピン
- 低い消費電流: 17 μA
- 人体モデル (HBM) ESD 保護: すべてのピンで ± 2 kV
- 業界標準の TSSOP と小型の WQFN パッケージ

2 アプリケーション

- ファクトリ・オートメーションと産業プロセス制御
- プログラマブル・ロジック・コントローラ (PLC)
- アナログ入力モジュール
- 半導体試験機器
- バッテリ・テスト機器

3 概要

TMUX6111、TMUX6112、TMUX6113 デバイスは、最新の CMOS (相補型金属酸化膜半導体) デバイスで、4 つの SPST (単極単投) スイッチを独立に選択可能です。このデバイスは、デュアル電源 ($\pm 5V \sim \pm 17V$)、シングル電源 ($10V \sim 17V$)、非対称電源のいずれでも適切に動作します。すべてのデジタル入力はスレッシュホールドが TTL (Transistor-Transistor Logic) 互換で、TTL および CMOS 両方のロジックとの互換性が保証されています。


スイッチは、TMUX6111 ではデジタル制御入力のロジック 0 でオンになります。TMUX6112 のスイッチをオンにするには、ロジック 1 が必要です。TMUX6113 のスイッチのうち 2 つは TMUX6111 と同様のデジタル制御ロジックで、もう 2 つのスイッチはロジックが反転しています。TMUX6113 は、Break-Before-Make のスイッチングを行うため、クロスポイントのスイッチング・アプリケーションに使用できます。

製品情報⁽¹⁾

型番	パッケージ	本体サイズ (公称)
TMUX6111	TSSOP (16)	5.00mm $\times$ 4.40mm
TMUX6112	WQFN (16)	3.00mm $\times$ 3.00mm
TMUX6113	WQFN (16)	3.00mm $\times$ 3.00mm

(1) 提供されているすべてのパッケージについては、巻末の注文情報を参照してください。

概略回路図



目次

1	特長	1	10.1	Overview	14
2	アプリケーション	1	10.2	Functional Block Diagram	19
3	概要	1	10.3	Feature Description	19
4	改訂履歴	2	10.4	Device Functional Modes	20
5	概要 (続き)	4	11	Application and Implementation	21
6	Device Comparison Table	5	11.1	Application Information	21
7	Pin Configuration and Functions	5	11.2	Typical Application	21
8	Specifications	6	11.3	Application Curves	22
8.1	Absolute Maximum Ratings	6	12	Power Supply Recommendations	23
8.2	ESD Ratings	6	13	Layout	24
8.3	Thermal Information	6	13.1	Layout Guidelines	24
8.4	Recommended Operating Conditions	6	13.2	Layout Example	24
8.5	Electrical Characteristics (Dual Supplies: ± 15 V)	7	14	デバイスおよびドキュメントのサポート	25
8.6	Switching Characteristics (Dual Supplies: ± 15 V)	8	14.1	ドキュメントのサポート	25
8.7	Electrical Characteristics (Single Supply: 12 V)	8	14.2	関連リンク	25
8.8	Switching Characteristics (Single Supply: 12 V)	9	14.3	ドキュメントの更新通知を受け取る方法	25
8.9	Typical Characteristics	10	14.4	サポート・リソース	25
9	Parameter Measurement Information	13	14.5	商標	25
9.1	Truth Tables	13	14.6	静電気放電に関する注意事項	25
10	Detailed Description	14	14.7	Glossary	25
			15	メカニカル、パッケージ、および注文情報	26

4 改訂履歴

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

Revision D (January 2019) から Revision E に変更	Page
• タイトルの「TMUX611x ± 16.5 V」を「TMUX611x ± 17 V」に変更	1
• 「特長」の「広い電源電圧範囲: ± 5 V $\sim$ ± 16.5 V (デュアル)、10V $\sim$ 16.5V (シングル)」を「広い電源電圧範囲: ± 5 V $\sim$ ± 17 V (デュアル)、10V $\sim$ 17V (シングル)」に変更	1
• 「概要」の「デュアル電源 (± 5 V $\sim$ ± 16.5 V)、シングル電源 (10V $\sim$ 16.5V)」を「デュアル電源 (± 5 V $\sim$ ± 17 V)、シングル電源 (10V $\sim$ 17V)」に変更	1
• Changed ± 16.5 -V to ± 17.5 -V in the Description of the <i>Device Comparison Table</i>	5
• Changed recommended power supply voltage differential from 33 V to 34 V	6
• Changed recommended single supply voltage from 16.5 V to 17 V	6
• Changed positive and negative power supply voltage to +17 V and -17V	6
• The Overview From: dual supplies (± 5 V to ± 16.5 V) or single supply (10 V to 16.5 V) To: dual supplies (± 5 V to ± 17 V) or single supply (10 V to 17 V)	14
• Changed the <i>Application Information</i> From: 16.5 V (single supply) To: 17 V (single supply)	21
• The <i>Power Supply Recommendations</i> From: wide supply range of of ± 5 V to ± 16.5 V (10 V to 16.5 V in single-supply mode) To: wide supply range of of ± 5 V to ± 17 V (10 V to 17 V in single-supply mode)	23

Revision C (December 2018) から Revision D に変更	Page
• Changed descriptions in the <i>Device Comparison Table</i> to match the data sheet title	5
• 変更 図 30 to correct Op-Amp terminal polarities.	21

Revision B (November 2018) から Revision C に変更	Page
• Changed units for channel current and ambient temperature.	7

Revision A (November 2018) から Revision B に変更**Page**

-
- TMUX6111 および TMUX6113 のドキュメント・ステータスを製品プレビューから量産データに変更 [1](#)
-

2018年8月発行のものから更新**Page**

-
- TMUX6112 のドキュメント・ステータスを事前情報から量産データに変更 [1](#)
-



5 概要（続き）

TMUX611xデバイスは、テキサス・インスツルメンツの高精度スイッチおよびマルチプレクサ・ファミリの製品です。これらのデバイスはリーク電流と電荷注入が非常に小さいため、高精度の測定アプリケーションに使用可能です。消費電流が17 μ Aと低いため、携帯型アプリケーションにも使用できます。

6 Device Comparison Table

PRODUCT	DESCRIPTION
TMUX6111	±17-V, Low-Capacitance, Low-Leakage-Current, Precision, Quad SPST Switches (Normally Closed)
TMUX6112	±17-V, Low-Capacitance, Low-Leakage-Current, Precision, Quad SPST Switches (Normally Open)
TMUX6113	±17-V, Low-Capacitance, Low-Leakage-Current, Precision, Quad SPST Switches (Dual Open + Dual Closed)

7 Pin Configuration and Functions



Pin Functions

PIN			TYPE ⁽¹⁾	DESCRIPTION
NAME	TSSOP	WQFN		
SEL1	1	15	I	Logic control input 1.
D1	2	16	I/O	Drain pin 1. Can be an input or output.
S1	3	1	I/O	Source pin 1. Can be an input or output.
V _{SS}	4	2	P	Negative power supply. This pin is the most negative power-supply potential. In single-supply applications, this pin can be connected to ground. For reliable operation, connect a decoupling capacitor ranging from 0.1 µF to 10 µF between V _{SS} and GND.
GND	5	3	P	Ground (0 V) reference
S4	6	4	I/O	Source pin 4. Can be an input or output.
D4	7	5	I/O	Drain pin 4. Can be an input or output.
SEL4	8	6	I	Logic control input 4.
SEL3	9	7	I	Logic control input 3.
D3	10	8	I/O	Drain pin 3. Can be an input or output.
S3	11	9	I/O	Source pin 3. Can be an input or output.
NC	12	10	–	No internal connection.
V _{DD}	13	11	P	Positive power supply. This pin is the most positive power-supply potential. For reliable operation, connect a decoupling capacitor ranging from 0.1 µF to 10 µF between V _{DD} and GND.
S2	14	12	I/O	Source pin 2. Can be an input or output.
D2	15	13	I/O	Drain pin 2. Can be an input or output.
SEL2	16	14	I	Logic control input 2.
–	–	EP	–	Exposed Pad. The exposed pad is electrically connected to V _{SS} internally. Connect EP to V _{SS} to achieve rated thermal and ESD performance.

(1) I = input, O = output, I/O = input and output, P = power

8 Specifications

8.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
V_{DD} to V_{SS}	Supply voltage		36	V
V_{DD} to GND		–0.3	18	V
V_{SS} to GND		–18	0.3	V
V_{DIG}	Digital input pin (SEL1, SEL2, SEL3, SEL4) voltage	GND –0.3	$V_{DD}+0.3$	V
I_{DIG}	Digital input pin (SEL1, SEL2, SEL3, SEL4) current	–30	30	mA
V_{ANA_IN}	Analog input pin (Sx) voltage	$V_{SS}-0.3$	$V_{DD}+0.3$	V
I_{ANA_IN}	Analog input pin (Sx) current	–30	30	mA
V_{ANA_OUT}	Analog output pin (D) voltage	$V_{SS}-0.3$	$V_{DD}+0.3$	V
I_{ANA_OUT}	Analog output pin (D) current	–30	30	mA
T_A	Ambient temperature	–55	140	°C
T_J	Junction temperature		150	°C
T_{stg}	Storage temperature	–65	150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Rating* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Condition*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

8.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±500	

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
 (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

8.3 Thermal Information

THERMAL METRIC		TMUX6111/ TMUX6112/ TMUX6113		UNIT
		PW (TSSOP)	RTE (QFN)	
		16 PINS	16 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	111.0	51.9	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	41.7	53.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	57.2	26.6	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	4.1	1.7	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	56.6	26.6	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	11.6	°C/W

8.4 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_{DD} to V_{SS} ⁽¹⁾	Power supply voltage differential	10		34	V
V_{DD} to GND	Positive power supply voltage (single supply, $V_{SS} = 0$ V)	10		17	V
V_{DD} to GND	Positive power supply voltage (dual supply)	5		17	V
V_{SS} to GND	Negative power supply voltage (dual supply)	–5		–17	V
V_S ⁽²⁾	Source pins voltage	V_{SS}		V_{DD}	V

- (1) V_{DD} and V_{SS} can be any value as long as $10\text{ V} \leq (V_{DD} - V_{SS}) \leq 34\text{ V}$.
 (2) V_S is the voltage on all the S pins.

Recommended Operating Conditions (continued)

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_D	Drain pin voltage	V_{SS}		V_{DD}	V
V_{DIG}	Digital input pin (SEL1, SEL2, SEL3, SEL4) voltage	0		V_{DD}	V
I_{CH}	Channel current ($T_A = 25^\circ\text{C}$)	-25		25	mA
T_A	Ambient temperature	-40		125	$^\circ\text{C}$

8.5 Electrical Characteristics (Dual Supplies: $\pm 15\text{ V}$)

at $T_A = 25^\circ\text{C}$, $V_{DD} = 15\text{ V}$, and $V_{SS} = -15\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT	
ANALOG SWITCH								
V _A	Analog signal range		T _A = −40°C to +125°C	V _{SS}		V _{DD}	V	
R _{ON}	On-resistance	V _S = 0 V, I _S = 1 mA		120	135		Ω	
		V _S = ±10 V, I _S = 1 mA		140	160		Ω	
			T _A = −40°C to +85°C			210		Ω
			T _A = −40°C to +125°C			245		Ω
ΔR _{ON}	On-resistance mismatch between channels	V _S = ±10 V, I _S = 1 mA		2.5	6		Ω	
			T _A = −40°C to +85°C			9		Ω
			T _A = −40°C to +125°C			11		Ω
R _{ON_FLAT}	On-resistance flatness	V _S = −10 V, 0 V, +10 V, I _S = 1 mA		23	33		Ω	
			T _A = −40°C to +85°C			37		Ω
			T _A = −40°C to +125°C			38		Ω
R _{ON_DRIFT}	On-resistance drift	V _S = 0 V		0.52			%/°C	
I _{S(OFF)}	Source off leakage current ⁽¹⁾	Switch state is off, V _S = +10 V/ −10 V, V _D = −10 V/ +10 V		−0.02	0.005	0.02	nA	
			T _A = −40°C to +85°C	−0.14		0.05	nA	
			T _A = −40°C to +125°C	−1.3		0.25	nA	
I _{D(OFF)}	Drain off leakage current ⁽¹⁾	Switch state is off, V _S = +10 V/ −10 V, V _D = −10 V/ +10 V		−0.02	0.005	0.02	nA	
			T _A = −40°C to +85°C	−0.14		0.05	nA	
			T _A = −40°C to +125°C	−1.3		0.25	nA	
I _{D(ON)}	Drain on leakage current	Switch state is on, V _S = +10 V/ −10 V, V _D = −10 V/ +10 V		−0.04	0.01	0.04	nA	
			T _A = −40°C to +85°C	−0.25		0.1	nA	
			T _A = −40°C to +125°C	−1.8		0.5	nA	
DIGITAL INPUT (SELx pins)								
V _{IH}	Logic voltage high			2			V	
V _{IL}	Logic voltage low					0.8	V	
R _{PD(IN)}	Pull-down resistance on SELx pins				6		MΩ	
POWER SUPPLY								
I _{DD}	V _{DD} supply current	V _A = 0 V or 3.3 V, V _S = 0 V		17	21		μA	
			T _A = −40°C to +85°C			22		μA
			T _A = −40°C to +125°C			23		μA
I _{SS}	V _{SS} supply current	V _A = 0 V or 3.3 V, V _S = 0 V		8	10		μA	
			T _A = −40°C to +85°C			11		μA
			T _A = −40°C to +125°C			12		μA

(1) When V_S is positive, V_D is negative, and vice versa.

8.6 Switching Characteristics (Dual Supplies: ± 15 V)

 at $T_A = 25^\circ\text{C}$, $V_{DD} = 15$ V, and $V_{SS} = -15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{ON}	Enable turn-on time	$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF		66	78	ns
		$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$			107	ns
		$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$			117	ns
t_{OFF}	Enable turn-off time	$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF		56	68	ns
		$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$			77	ns
		$V_S = \pm 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$			81	ns
t_{BBM}	Break-before-make time delay (TMUX6113 Only)	$V_S = 10$ V, $R_L = 300\ \Omega$, $C_L = 35$ pF, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$	8	40		ns
Q_J	Charge injection	$V_S = 0$ V, $R_S = 0\ \Omega$, $C_L = 1$ nF		0.6		pC
O_{ISO}	Off-isolation	$R_L = 50\ \Omega$, $C_L = 5$ pF, $f = 1$ MHz		-85		dB
X_{TALK}	Channel-to-channel crosstalk	$R_L = 50\ \Omega$, $C_L = 5$ pF, $f = 1$ MHz, adjacent channel		-100		dB
		$R_L = 50\ \Omega$, $C_L = 5$ pF, $f = 1$ MHz, non-adjacent channel		-115		dB
I_L	Insertion loss	$R_L = 50\ \Omega$, $C_L = 5$ pF, $f = 1$ MHz		-7.0		dB
ACPSRR	AC Power Supply Rejection Ratio	$R_L = 10\ \text{k}\Omega$, $C_L = 5$ pF, $V_{PP} = 0.62$ V on V_{DD} , $f = 1$ MHz		-59		dB
		$R_L = 10\ \text{k}\Omega$, $C_L = 5$ pF, $V_{PP} = 0.62$ V on V_{SS} , $f = 1$ MHz		-59		dB
BW	-3dB Bandwidth	$R_L = 50\ \Omega$, $C_L = 5$ pF		800		MHz
THD	Total harmonic distortion + noise	$R_L = 10\ \text{k}\Omega$, $C_L = 5$ pF, $f = 20\ \text{Hz}$ to $20\ \text{kHz}$		0.08		%
C_{IN}	Digital input capacitance	$V_{IN} = 0$ V or V_{DD}		1.5		pF
$C_{S(OFF)}$	Source off-capacitance	$V_S = 0$ V, $f = 1$ MHz (PW package)		1.9	3.0	pF
		$V_S = 0$ V, $f = 1$ MHz (RTE package)		2.5	3.6	pF
$C_{D(OFF)}$	Drain off-capacitance	$V_S = 0$ V, $f = 1$ MHz		2.4	3.1	pF
$C_{S(ON)}$, $C_{D(ON)}$	Source and drain on-capacitance	$V_S = 0$ V, $f = 1$ MHz		4.2	6.0	pF

8.7 Electrical Characteristics (Single Supply: 12 V)

 at $T_A = 25^\circ\text{C}$, $V_{DD} = 12$ V, and $V_{SS} = 0$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
ANALOG SWITCH						
V_A	Analog signal range	$T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$	V_{SS}		V_{DD}	V
R_{ON}	On-resistance	$V_S = 10$ V, $I_S = 1$ mA		230	265	Ω
			$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$		355	Ω
			$T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$		405	Ω
ΔR_{ON}	On-resistance mismatch between channels	$V_S = 10$ V, $I_S = 1$ mA		5	12	Ω
			$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$		19	Ω
			$T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$		23	Ω
R_{ON_DRIFT}	On-resistance drift	$V_S = 0$ V		0.5		%/ $^\circ\text{C}$
$I_{S(OFF)}$	Source off leakage current ⁽¹⁾	Switch state is off, $V_S = 10$ V/ 1 V, $V_D = 1$ V/ 10 V		-0.02	0.005	nA
			$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$	-0.1	0.04	nA
			$T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$	-1	0.2	nA

 (1) When V_S is positive, V_D is negative, and vice versa.

Electrical Characteristics (Single Supply: 12 V) (continued)

at $T_A = 25^\circ\text{C}$, $V_{DD} = 12\text{ V}$, and $V_{SS} = 0\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
I _{D(OFF)}	Drain off leakage current ⁽¹⁾	Switch state is off, V _S = 10 V/ 1 V, V _D = 1 V/ 10 V		−0.02	0.005	0.02	nA
			T _A = −40°C to +85°C	−0.1		0.04	nA
			T _A = −40°C to +125°C	−1		0.2	nA
I _{D(ON)}	Drain on leakage current	Switch state is on, V _S = floating, V _D = 1 V/ 10 V		−0.04	0.01	0.04	nA
			T _A = −40°C to +85°C	−0.16		0.08	nA
			T _A = −40°C to +125°C	−1.4		0.4	nA
DIGITAL INPUT (SELx pins)							
V _{IH}	Logic voltage high			2			V
V _{IL}	Logic voltage low					0.8	V
R _{PD(EN)}	Pull-down resistance on SELx pins				6		MΩ
POWER SUPPLY							
I _{DD}	V _{DD} supply current	V _A = 0 V or 3.3 V, V _S = 0 V		13		16	μA
			T _A = −40°C to +85°C			17	μA
			T _A = −40°C to +125°C			18	μA

8.8 Switching Characteristics (Single Supply: 12 V)

at $T_A = 25^\circ\text{C}$, $V_{DD} = 12\text{ V}$, and $V_{SS} = 0\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
t_{ON}	Enable turn-on time	$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$			72	84	ns
		$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$				117	ns
		$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$				128	ns
t_{OFF}	Enable turn-off time	$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$			57	66	ns
		$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$, $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$				78	ns
		$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$				84	ns
t_{BBM}	Break-before-make time delay (TMUX6113 only)	$V_S = 8\text{ V}$, $R_L = 300\text{ }\Omega$, $C_L = 35\text{ pF}$, $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$		17	47		ns
Q_J	Charge injection	$V_S = 0\text{ V}$ to 12 V , $R_S = 0\text{ }\Omega$, $C_L = 1\text{ nF}$			0.6		pC
O_{ISO}	Off-isolation	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, $f = 1\text{ MHz}$			–86		dB
X_{TALK}	Channel-to-channel crosstalk	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, $f = 1\text{ MHz}$, adjacent channel			–98		dB
		$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, $f = 1\text{ MHz}$, non-adjacent channel			–117		dB
I_L	Insertion loss	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, $f = 1\text{ MHz}$			–14		dB
ACPSRR	AC Power Supply Rejection Ratio	$R_L = 10\text{ k}\Omega$, $C_L = 5\text{ pF}$, $V_{PP} = 0.62\text{ V}$, $f = 1\text{ MHz}$			–59		dB
BW	–3dB Bandwidth	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$			750		MHz
C_{IN}	Digital input capacitance	$V_{IN} = 0\text{ V}$ or V_{DD}			1.6		pF
$C_{S(OFF)}$	Source off-capacitance	$V_S = 6\text{ V}$, $f = 1\text{ MHz}$ (PW package)			2.2	3.1	pF
		$V_S = 6\text{ V}$, $f = 1\text{ MHz}$ (RTE package)			2.9	4.0	pF
$C_{D(OFF)}$	Drain off-capacitance	$V_S = 6\text{ V}$, $f = 1\text{ MHz}$			2.8	3.5	pF
$C_{S(ON)}$, $C_{D(ON)}$	Source and drain on-capacitance	$V_S = 6\text{ V}$, $f = 1\text{ MHz}$			4.6	6.3	pF

8.9 Typical Characteristics

at $T_A = 25^\circ\text{C}$, $V_{DD} = 15\text{ V}$, and $V_{SS} = -15\text{ V}$ (unless otherwise noted)




FIG 1. On-Resistance vs Source or Drain Voltage




FIG 2. On-Resistance vs Source or Drain Voltage




FIG 3. On-Resistance vs Source or Drain Voltage




FIG 4. On-Resistance vs Source or Drain Voltage




FIG 5. Leakage Current vs Temperature




FIG 6. Leakage Current vs Temperature

Typical Characteristics (continued)

at $T_A = 25^\circ\text{C}$, $V_{DD} = 15\text{ V}$, and $V_{SS} = -15\text{ V}$ (unless otherwise noted)




图 7. Charge Injection vs Source Voltage




图 8. Charge Injection vs Drain Voltage




图 9. Turn-On and Turn-Off Times vs Temperature




图 10. Off Isolation vs Frequency




图 11. Crosstalk vs Frequency




图 12. THD+N vs Frequency

Typical Characteristics (continued)

at $T_A = 25^\circ\text{C}$, $V_{DD} = 15\text{ V}$, and $V_{SS} = -15\text{ V}$ (unless otherwise noted)




图 13. On Response vs Frequency




图 14. ACPSRR vs Frequency




图 15. Capacitance vs Source Voltage




图 16. Capacitance vs Source Voltage

9 Parameter Measurement Information

9.1 Truth Tables

表 1, 表 2, 表 3 and show the truth tables for the TMUX6111, TMUX6112, and TMUX6113, respectively.

表 1. TMUX6111 Truth Table

SELx	STATE
0	All Switch ON
1	All Switch OFF

表 2. TMUX6112 Truth Table

SELx	STATE
0	All Switch OFF
1	All Switch ON

表 3. TUMUX6113 Truth Table

SELx	STATE
0	Switch 1, 4 OFF Switch 2, 3 ON
1	Switch 1, 4 ON Switch 2, 3 OFF

10 Detailed Description

10.1 Overview

The TMUX6111, TMUX6112, and TMUX6113 are 4-channel single-pole/ single-throw (SPDT) switches that supports dual supplies ($\pm 5\text{ V}$ to $\pm 17\text{ V}$) or single supply (10 V to 17 V) operation. Each channel of the switch is turned on or turned off based on the state of its corresponding SELx pin. The [Functional Block Diagram](#) section provides a top-level block diagram of the switches.

10.1.1 On-Resistance

The on-resistance of the TMUX6111, TMUX6112, and TMUX6113 is the ohmic resistance across the source (Sx) and drain (Dx) pins of the device. The on-resistance varies with input voltage and supply voltage. The symbol R_{ON} is used to denote on-resistance. The measurement setup used to measure R_{ON} is shown in [Figure 17](#). Voltage (V) and current (I_{CH}) are measured using this setup, and R_{ON} is computed as shown in [Equation 1](#):




Figure 17. On-Resistance Measurement Setup

$$R_{ON} = V / I_{CH} \quad (1)$$

10.1.2 Off-Leakage Current

There are two types of leakage currents associated with a switch during the off state:

1. Source off-leakage current
2. Drain off-leakage current

Source leakage current is defined as the leakage current flowing into or out of the source pin when the switch is off. This current is denoted by the symbol $I_{S(OFF)}$.

Drain leakage current is defined as the leakage current flowing into or out of the drain pin when the switch is off. This current is denoted by the symbol $I_{D(OFF)}$.

The setup used to measure both off-leakage currents is shown in [Figure 18](#).




Figure 18. Off-Leakage Measurement Setup

Overview (continued)

10.1.3 On-Leakage Current

On-leakage current is defined as the leakage current that flows into or out of the drain pin when the switch is in the on state. The source pin is left floating during the measurement. Figure 19 shows the circuit used for measuring the on-leakage current, denoted by $I_{D(ON)}$.




Figure 19. On-Leakage Measurement Setup

10.1.4 Break-Before-Make Delay

The break-before-make delay is a safety feature of the TMUX6113 switch. The TMUX6113's ON switches first break the connection before the OFF switches make connection. The time delay between the *break* and the *make* is known as break-before-make delay. Figure 20 shows the setup used to measure break-before-make delay, denoted by the symbol t_{BBM} .




Figure 20. Break-Before-Make Delay Measurement Setup

10.1.5 Turn-On and Turn-Off Time

Turn-on time is defined as the time taken by the output of the TMUX6111, TMUX6112, and TMUX6113 to rise to a 90% final value after the SELx signal has risen (for NC switches) or fallen (for NO switches) to a 50% final value. Figure 21 shows the setup used to measure turn-on time. Turn-on time is denoted by the symbol t_{ON} .

Turn off time is defined as the time taken by the output of the TMUX6111, TMUX6112, and TMUX6113 to fall to a 10% initial value after the SELx signal has fallen (for NC switches) or risen (for NO switches) to a 50% initial value. Figure 21 shows the setup used to measure turn-off time. Turn-off time is denoted by the symbol t_{OFF} .

Overview (continued)




Figure 21. Turn-On and Turn-Off Time Measurement Setup

10.1.6 Charge Injection

The TMUX6111, TMUX6112, and TMUX6113 have a simple transmission-gate topology. Any mismatch in capacitance between the NMOS and PMOS transistors results in a charge injected into the drain or source during the falling or rising edge of the gate signal. The amount of charge injected into the source or drain of the device is known as charge injection, and is denoted by the symbol Q_{INJ} . Figure 22 shows the setup used to measure charge injection.




Figure 22. Charge-Injection Measurement Setup

10.1.7 Off Isolation

Off isolation is defined as the voltage at the drain pin (Dx) of the TMUX6111, TMUX6112, and TMUX6113 when a $1-V_{RMS}$ signal is applied to the source pin (Sx) of an OFF switch. Figure 23 shows the setup used to measure off isolation. Use Equation 2 to compute off isolation.

Overview (continued)




Figure 23. Off Isolation Measurement Setup

$$\text{Off Isolation} = 20 \cdot \text{Log} \left(\frac{V_{\text{OUT}}}{V_S} \right) \quad (2)$$

10.1.8 Channel-to-Channel Crosstalk

Channel-to-channel crosstalk is defined as the voltage at the source pin (Sx) of an off-channel, when a 1- V_{RMS} signal is applied at the source pin of an on-channel. Figure 24 shows the setup used to measure, and Equation 3 is the equation used to compute, channel-to-channel crosstalk.




Figure 24. Channel-to-Channel Crosstalk Measurement Setup

$$\text{Channel-to-Channel Crosstalk} = 20 \cdot \text{Log} \left(\frac{V_{\text{OUT}}}{V_S} \right) \quad (3)$$

10.1.9 Bandwidth

Bandwidth is defined as the range of frequencies that are attenuated by < 3 dB when the input is applied to the source pin (Sx) of an on-channel, and the output is measured at the drain pin (Dx) of the TMUX6111, TMUX6112, and TMUX6113. Figure 25 shows the setup used to measure bandwidth of the switch. Use Equation 4 to compute the attenuation.

Overview (continued)




Figure 25. Bandwidth Measurement Setup

$$\text{Attenuation} = 20 \cdot \log \left(\frac{V_2}{V_1} \right) \quad (4)$$

10.1.10 THD + Noise

The total harmonic distortion (THD) of a signal is a measurement of the harmonic distortion, and is defined as the ratio of the sum of the powers of all harmonic components to the power of the fundamental frequency at the mux output. The on-resistance of the TMUX6111, TMUX6112, and TMUX6113 varies with the amplitude of the input signal and results in distortion when the drain pin is connected to a low-impedance load. Total harmonic distortion plus noise is denoted as THD+N. [Figure 26](#) shows the setup used to measure THD+N of the TMUX6111, TMUX6112, and TMUX6113.





Figure 26. THD+N Measurement Setup

10.2 Functional Block Diagram



10.3 Feature Description

10.3.1 Ultra-low Leakage Current

The TMUX6111, TMUX6112, and TMUX6113 provide extremely low on- and off-leakage currents. The devices are capable of switching signals from high source-impedance inputs into a high input-impedance op amp with minimal offset error because of the ultralow leakage currents. [Figure 27](#) shows typical leakage currents of the devices versus temperature.





Figure 27. Leakage Current vs Temperature


10.3.2 Ultra-low Charge Injection

The TMUX6111, TMUX6112, and TMUX6113 are implemented with simple transmission gate topology, as shown in [Figure 28](#). Any mismatch in the stray capacitance associated with the NMOS and PMOS causes an output level change whenever the switch is opened or closed. The devices utilize special charge-injection cancellation circuitry that reduces the source (S_x)-to-drain (D_x) charge injection to as low as 0.6 pC at $V_S = 0$ V, as shown in [Figure 29](#).

Feature Description (continued)



28. Transmission Gate Topology



29. Source-to-Drain Charge Injection vs Source or Drain Voltage

10.3.3 Bidirectional and Rail-to-Rail Operation

The TMUX6111, TMUX6112, and TMUX6113 conduct equally well from source (Sx) to drain (Dx) or from drain (Dx) to source (Sx). Each channel of the switches has very similar characteristics in both directions. The input signal to the devices swings from V_{SS} to V_{DD} without any significant degradation in performance. The on-resistance of these devices varies with input signal.

10.4 Device Functional Modes

Each channel of the TMUX6111, TMUX6112, and TMUX6113 is turned on or turned off based on the state of its corresponding SELx pin. The SELx pins are weakly pulled-down through an internal 6 M Ω resistor, allowing the switches to stay in a determined state when power is applied to the devices. The SELx pins can be connected to V_{DD} .

11 Application and Implementation

注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

11.1 Application Information

The TMUX6111, TMUX6112, and TMUX6113 offer outstanding input/output leakage currents and ultralow charge injection. These devices operate up to 34 (dual supply) or 17 V (single supply), and offer true rail-to-rail input and output. The on-capacitance of the TMUX6111, TMUX6112, and TMUX6113 is low. These features makes the TMUX6111, TMUX6112, and TMUX6113 a family of precision, robust, high-performance analog multiplexer for high-voltage, industrial applications.

11.2 Typical Application

One useful application to take advantage of TMUX6111, TMUX6112, and TMUX6113's precision performance is the sample and hold circuit. A sample and hold circuit can be useful for an analog to digital converter (ADC) to sample a varying input voltage with improved reliability and stability. It can also be used to store the output samples from a single digital-to-analog converter (DAC) in a multi-output application. A simple sample and hold circuit can be realized using an analog switch like one of the TMUX6111, TMUX6112, and TMUX6113 analog switches.




图 30. A 2-output Sample and Hold Circuit Realized Using the TMUX611x Analog Switch

Typical Application (continued)

11.2.1 Design Requirements

The purpose of this precision design is to implement an optimized 2-output sample and hold circuit using a 4-channel SPST switch. The sample and hold circuit needs to be capable of supporting high voltage output swing up to $\pm 15\text{V}$ with minimized pedestal error and fast settling time. The overall system block diagram is illustrated in [Figure 30](#).

11.2.2 Detailed Design Procedure

The TMUX6111, TMUX6112, or TMUX6113 switch is used in conjunction with the voltage holding capacitors (C_H) to implement the sample and hold circuit. The basic operation is:

1. When the switch (SW2 or SW3) is closed, it samples the input voltage and charges the holding capacitors (C_H) to the input voltages values.
2. When the switch (SW2 or SW3) is open, the holding capacitors (C_H) holds its previous value, maintaining stable voltage at the amplifier output (V_{OUT}).

Ideally, the switch delivers only the input signals to the holding capacitors. However, when the switch gets toggled, some amount of charge also gets transferred to the switch output in the form of charge injection, resulting slight sampling error. The TMUX6111, TMUX6112, and TMUX6113 switches have excellent charge injection performance of only 0.6 pC, making them ideal choices for this implementation to minimize sampling error.

Due to switch and capacitor leakage current, the voltage on the hold capacitors droops with time. The TMUX6111, TMUX6112, and TMUX6113 minimize the droops due to its ultra-low leakage performance. At 25°C, the TMUX6111, TMUX6112, and TMUX6113 have extremely tiny leakage current at 1 pA typical and 20 pA max.

The TMUX6111, TMUX6112, and TMUX6113 devices also support high voltage capability. The devices support up to $\pm 17\text{V}$ dual supply operation, making it an ideal solution in this high voltage sample and hold application.

A second switch SW1 (or SW4) is also included to operate in parallel with SW2 (or SW3) to reduce pedestal error during switch toggling. Because both switches are driven at the same potential, they act as common-mode signal to the op-amp, thereby minimizing the charge injection effects caused by the switch toggling action. Compensation network consisting of R_C and C_C is also added to further reduce the pedestal error, while reducing the hold-time glitch and improving the settling time of the circuit.

11.3 Application Curves

TMUX6111, TMUX6112, and TMUX6113 have excellent charge injection performance of only 0.6 pC (typical), making them ideal choices to minimize sampling error for the sample and hold application. [Figure 31](#) shows the plot for the charge injection vs. source input voltage for TMUX6111, TMUX6112, and TMUX6113.




Figure 31. Charge injection vs. Source Voltage for TMUX6111, TMUX6112 and TMUX6113

12 Power Supply Recommendations

The TMUX6111, TMUX6112, and TMUX6113 operate across a wide supply range of ± 5 V to ± 17 V (10 V to 17 V in single-supply mode). They also perform well with asymmetrical supplies such as $V_{DD} = 12$ V and $V_{SS} = -5$ V. For improved supply noise immunity, use a supply decoupling capacitor ranging from 0.1 μ F to 10 μ F at both the V_{DD} and V_{SS} pins to ground. Always ensure the ground (GND) connection is established before supplies are ramped. As a best practice, it is recommended to ramp V_{SS} first before V_{DD} in dual or asymmetrical supply applications.

The on-resistance of the devices varies with supply voltage, as illustrated in [Figure 32](#)




Figure 32. On-Resistance Variation With Supply and Input Voltage


13 Layout

13.1 Layout Guidelines

✎ 33 illustrates an example of a PCB layout with the TMUX6112PW. Some key considerations are:

- Decouple the V_{DD} and V_{SS} pins with a 0.1- μ F capacitor, placed as close to the pin as possible. Make sure that the capacitor voltage rating is sufficient for the V_{DD} and V_{SS} supplies.
- Keep the input lines as short as possible.
- Use a solid ground plane to help distribute heat and reduce electromagnetic interference (EMI) noise pickup.
- Do not run sensitive analog traces in parallel with digital traces. Avoid crossing digital and analog traces if possible, and only make perpendicular crossings when necessary.

13.2 Layout Example



✎ 33. TMUX6112PW Layout Example

14 デバイスおよびドキュメントのサポート

14.1 ドキュメントのサポート

14.1.1 関連資料

- 『[OPAx192 36V](#)、レール・ツー・レール入力/出力、低オフセット電圧、低入力バイアス電流オペアンプ、[e-trim™](#)搭載』(SBOS620E)

14.2 関連リンク

次の表に、クイック・アクセス・リンクを示します。カテゴリには、技術資料、サポートおよびコミュニティ・リソース、ツールとソフトウェア、およびご注文へのクイック・アクセスが含まれます。

表 4. 関連リンク

製品	プロダクト・フォルダ	ご注文はこちら	技術資料	ツールとソフトウェア	サポートとコミュニティ
TMUX6111	ここをクリック	ここをクリック	ここをクリック	ここをクリック	ここをクリック
TMUX6112	ここをクリック	ここをクリック	ここをクリック	ここをクリック	ここをクリック
TMUX6113	ここをクリック	ここをクリック	ここをクリック	ここをクリック	ここをクリック

14.3 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の「アラートを受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

14.4 サポート・リソース

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

14.5 商標

E2E is a trademark of Texas Instruments.

14.6 静電気放電に関する注意事項



すべての集積回路は、適切なESD保護方法を用いて、取扱いと保存を行うようにして下さい。

静電気放電はわずかな性能の低下から完全なデバイスの故障に至るまで、様々な損傷を与えます。高精度の集積回路は、損傷に対して敏感であり、極めてわずかなパラメータの変化により、デバイスに規定された仕様に適合しなくなる場合があります。

14.7 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

15 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TMUX6111PWR	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	MUX6111
TMUX6111PWR.B	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6111
TMUX6111RTER	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6111
TMUX6111RTER.B	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6111
TMUX6112PWR	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6112
TMUX6112PWR.B	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6112
TMUX6112RTER	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6112
TMUX6112RTER.B	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6112
TMUX6112RTERG4.B	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6112
TMUX6113PWR	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6113
TMUX6113PWR.B	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6113
TMUX6113PWRG4.B	Active	Production	TSSOP (PW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	MUX6113
TMUX6113RTER	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6113
TMUX6113RTER.B	Active	Production	WQFN (RTE) 16	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	TM6113

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMUX6111PWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TMUX6111RTER	WQFN	RTE	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TMUX6112PWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TMUX6112RTER	WQFN	RTE	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TMUX6113PWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TMUX6113RTER	WQFN	RTE	16	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TMUX6111PWR	TSSOP	PW	16	2000	356.0	356.0	35.0
TMUX6111RTER	WQFN	RTE	16	3000	367.0	367.0	35.0
TMUX6112PWR	TSSOP	PW	16	2000	356.0	356.0	35.0
TMUX6112RTER	WQFN	RTE	16	3000	367.0	367.0	35.0
TMUX6113PWR	TSSOP	PW	16	2000	367.0	367.0	35.0
TMUX6113RTER	WQFN	RTE	16	3000	367.0	367.0	35.0

GENERIC PACKAGE VIEW


RTE 16


WQFN - 0.8 mm max height

3 x 3, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.





4219117/B 04/2022


NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

RTE0016C

WQFN - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD





SOLDER PASTE EXAMPLE BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD 17:
85% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE
SCALE:25X

4219117/B 04/2022

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



4220204/A 02/2017

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT


PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220204/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220204/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated