

# AMC0381D-Q1 Automotive, Precision, High-Voltage DC Input, Reinforced Isolated Amplifier With Fixed-Gain Differential Output

## 1 Features

- AEC-Q100 qualified for automotive applications:
  - Temperature grade 1:  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ,  $T_A$
- Integrated, high-voltage resistive divider for direct DC voltage sensing without external resistors
- Better than 1% accuracy over temperature and lifetime without system-level calibration
- Differential output
- Supply voltage range:
  - High-side (VDD1): 3.0V to 5.5V
  - Low-side (VDD2): 3.0V to 5.5V
- Low DC errors:
  - Offset error:  $\pm 1.5\text{mV}$  (maximum)
  - Offset drift:  $\pm 20\mu\text{V}/^{\circ}\text{C}$  (maximum)
  - Attenuation error:  $\pm 0.25\%$  (maximum)
  - Attenuation drift:  $\pm 40\text{ppm}/^{\circ}\text{C}$  (maximum)
  - Nonlinearity: 0.05% (maximum)
- High CMTI: 50V/ns (minimum)
- Low EMI: Meets CISPR-11 and CISPR-25 limits
- Available input options:
  - AMC0381D06-Q1: 600V, 10M $\Omega$
  - AMC0381D10-Q1: 1000V, 12.5M $\Omega$
  - AMC0381D16-Q1: 1600V, 33M $\Omega$
- Safety-related certifications:
  - 7000V<sub>PK</sub> reinforced isolation per DIN EN IEC 60747-17 (VDE 0884-17)
  - 5000V<sub>RMS</sub> isolation for 1 minute per UL1577

## 2 Applications

- [Traction inverters](#)
- [Onboard chargers](#)
- [DC/DC converters](#)
- [Battery junction box](#)

## 3 Description

The AMC0381D-Q1 is a precision, galvanically isolated amplifier with a high-voltage DC, high impedance input, and fixed-gain, differential output. The input is designed to connect directly to a high-voltage signal source.

The isolation barrier separates parts of the system that operate on different common-mode voltage levels. The isolation barrier is highly resistant to magnetic interference and is certified to provide reinforced isolation of up to 5kV<sub>RMS</sub> (60s).

The AMC0381D-Q1 outputs a differential signal that is proportional to the input voltage. The differential output is insensitive to ground shifts and enables routing the output signal over long distances.


The AMC0381D-Q1 is available in three linear input voltage ranges: 600V, 1000V, and 1600V. With an integrated precision resistive divider, the AMC0381D-Q1 achieves better than 1% accuracy over the full temperature range, including lifetime drift.

The AMC0381D-Q1 is available in a 15-pin, 0.65mm pitch SSOP package and is fully specified over the temperature range from  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ .

### Package Information

PART NUMBER	PACKAGE <sup>(1)</sup>	PACKAGE SIZE <sup>(2)</sup>
AMC0381D-Q1	DFX (SSOP, 15)	12.8mm × 10.3mm

- (1) For more information, see the *Mechanical, Packaging, and Orderable* addendum.
- (2) The package size (length × width) is a nominal value and includes pins, where applicable.



**Typical Application**



## Table of Contents

<b>1 Features</b> .....	<b>1</b>	6.3 Feature Description.....	<b>11</b>
<b>2 Applications</b> .....	<b>1</b>	6.4 Device Functional Modes.....	<b>13</b>
<b>3 Description</b> .....	<b>1</b>	<b>7 Application and Implementation</b> .....	<b>15</b>
<b>4 Pin Configuration and Functions</b> .....	<b>4</b>	7.1 Application Information.....	<b>15</b>
<b>5 Specifications</b> .....	<b>5</b>	7.2 Best Design Practices.....	<b>15</b>
5.1 Absolute Maximum Ratings.....	<b>5</b>	7.3 Power Supply Recommendations.....	<b>16</b>
5.2 ESD Ratings.....	<b>5</b>	7.4 Layout.....	<b>16</b>
5.3 Recommended Operating Conditions.....	<b>5</b>	<b>8 Device and Documentation Support</b> .....	<b>18</b>
5.4 Thermal Information.....	<b>6</b>	8.1 Documentation Support.....	<b>18</b>
5.5 Power Ratings.....	<b>6</b>	8.2 Receiving Notification of Documentation Updates....	<b>18</b>
5.6 Insulation Specifications .....	<b>7</b>	8.3 Support Resources.....	<b>18</b>
5.7 Safety-Related Certifications .....	<b>8</b>	8.4 Trademarks.....	<b>18</b>
5.8 Safety Limiting Values.....	<b>8</b>	8.5 Electrostatic Discharge Caution.....	<b>18</b>
5.9 Electrical Characteristics .....	<b>9</b>	8.6 Glossary.....	<b>18</b>
5.10 Switching Characteristics .....	<b>10</b>	<b>9 Revision History</b> .....	<b>18</b>
5.11 Timing Diagram.....	<b>10</b>	<b>10 Mechanical, Packaging, and Orderable Information</b> .....	<b>18</b>
<b>6 Detailed Description</b> .....	<b>11</b>	10.1 Mechanical Data.....	<b>19</b>
6.1 Overview.....	<b>11</b>		
6.2 Functional Block Diagram.....	<b>11</b>		

## Device Comparison Table

**Table 4-1. Device Comparison**

DEVICE	R1	R2	DIVIDER RATIO	LINEAR INPUT RANGE	CLIPPING VOLTAGE	ABS MAX INPUT VOLTAGE
AMC0381D06-Q1 <sup>(1)</sup>	10MΩ	16.6kΩ	601:1	600V	769V	900V
AMC0381D10-Q1	12.5MΩ	12.5kΩ	1001:1	1000V	1281V	1500V
AMC0381D16-Q1 <sup>(1)</sup>	33MΩ	21kΩ	1601:1	1600V	2049V	2000V

(1) Product preview.

## 4 Pin Configuration and Functions




Figure 4-1. DFX Package, 15-pin SOIC (Top View)

Table 4-1. Pin Functions

PIN		TYPE	DESCRIPTION
NO.	NAME		
1	HVIN	Analog input	High-voltage input
2	INN	Analog input	Ground sense pin and inverting analog input to the modulator. Connect to GND1.
3, 7, 8, 12, 13, 15	NC	N/A	No internal connection. The pin can be connected to any potential or left floating.
4	SNSP	Analog input	Sense voltage pin and non-inverting analog input to the modulator. Connect to an external filter capacitor or leave floating.
5	VDD1	High-side power	Analog (high-side) power supply <sup>(1)</sup>
6	GND1	High-side ground	High-side ground
9	GND2	Low-side ground	Low-side ground
10	OUTN	Analog output	Inverting analog output
11	OUTP	Analog input	Noninverting analog output
14	VDD2	Low-side power	Low-side power supply <sup>(1)</sup>

(1) See the [Power Supply Recommendations](#) section for power-supply decoupling recommendations.

## 5 Specifications

### 5.1 Absolute Maximum Ratings

see<sup>(1)</sup>

		MIN	MAX	UNIT
Power-supply voltage	High-side, VDD1 to GND1	−0.3	6.5	V
	Low-side, VDD2 to GND2	−0.3	6.5	
Analog input voltage	HVIN to GND1, AMC0381D06-Q1	−150	900	V
	HVIN to GND1, AMC0381D10-Q1	−150	1500	
	HVIN to GND1, AMC0381D16-Q1	−150	2000	
	SNSP, SNSN	GND1 − 0.5	VDD1 + 0.5	
Analog output voltage	OUTP, OUTN	GND2 − 0.5	VDD2 + 0.5	V
Input current	Continuous, any pin except power-supply and HVIN pins	−10	10	mA
Temperature	Junction, T <sub>J</sub>		150	°C
	Storage, T <sub>stg</sub>	−65	150	

- (1) Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. *Absolute Maximum Ratings* do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If used outside the *Recommended Operating Conditions* but within the *Absolute Maximum Ratings*, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime

### 5.2 ESD Ratings

			VALUE	UNIT
V <sub>(ESD)</sub>	Electrostatic discharge	Human-body model (HBM), per AEC Q100-002 <sup>(1)</sup> , HBM ESD classification level 2	±2000	V
		Charged-device model (CDM), per AEC Q100-011, CDM ESD classification level C6	±1000	

- (1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

### 5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
POWER SUPPLY						
VDD1	High-side power supply	VDD1 to GND1	3	5.0	5.5	V
VDD2	Low-side power supply	VDD2 to GND2	3	3.3	5.5	V
ANALOG INPUT						
V <sub>Clipping</sub>	Nominal input voltage before clipping output	Referred to SNSP	1.28			V
		Referred to HVIN, AMC0381D06-Q1	769			
		Referred to HVIN, AMC0381D10-Q1	1281			
		Referred to HVIN, AMC0381D16-Q1	2049			
V <sub>FSR</sub>	Specified linear input voltage	Referred to SNSP	−0.05	1		V
		Referred to HVIN, AMC0381D06-Q1	−30	600		
		Referred to HVIN, AMC0381D10-Q1	−50	1000		
		Referred to HVIN, AMC0381D16-Q1	−80	1600		
TEMPERATURE RANGE						
T <sub>A</sub>	Specified ambient temperature		−40	125		°C

## 5.4 Thermal Information

THERMAL METRIC <sup>(1)</sup>		DFX (SSOP)	UNIT
		15 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	86.9	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	36.7	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	43.5	°C/W
$\Psi_{JT}$	Junction-to-top characterization parameter	17	°C/W
$\Psi_{JB}$	Junction-to-board characterization parameter	41.8	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.5 Power Ratings

PARAMETER		TEST CONDITIONS	VALUE	UNIT
$P_D$	Maximum power dissipation (both sides)	AVDD = DVDD = 5.5V	TBD	mW
$P_{D1}$	Maximum power dissipation (high-side)	AVDD = 3.6V	TBD	mW
		AVDD = 5.5V	TBD	
$P_{D2}$	Maximum power dissipation (low-side)	DVDD = 3.6V	TBD	mW
		DVDD = 5.5V	TBD	

## 5.6 Insulation Specifications

over operating ambient temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	VALUE	UNIT
GENERAL				
CLR	External clearance <sup>(1)</sup>	Shortest pin-to-pin distance through air	≥ 8	mm
CPG	External creepage <sup>(1)</sup>	Shortest pin-to-pin distance across the package surface	≥ 9.2	mm
DTI	Distance through insulation	Minimum internal gap (internal clearance) of the double insulation	≥ 15.4	μm
CTI	Comparative tracking index	DIN EN 60112 (VDE 0303-11); IEC 60112	≥ 600	V
	Material group	According to IEC 60664-1	I	
	Overvoltage category per IEC 60664-1	Rated mains voltage ≤ 600V <sub>RMS</sub>	I-III	
		Rated mains voltage ≤ 1000V <sub>RMS</sub>	I-II	
DIN EN IEC 60747-17 (VDE 0884-17) <sup>(2)</sup>				
V <sub>IORM</sub>	Maximum repetitive peak isolation voltage	At AC voltage	1410	V <sub>PK</sub>
V <sub>IOWM</sub>	Maximum-rated isolation working voltage	At AC voltage (sine wave)	1000	V <sub>RMS</sub>
		At DC voltage	1410	V <sub>DC</sub>
V <sub>IOTM</sub>	Maximum transient isolation voltage	V <sub>TEST</sub> = V <sub>IOTM</sub> , t = 60s (qualification test), V <sub>TEST</sub> = 1.2 × V <sub>IOTM</sub> , t = 1s (100% production test)	7000	V <sub>PK</sub>
V <sub>IMP</sub>	Maximum impulse voltage <sup>(3)</sup>	Tested in air, 1.2/50μs waveform per IEC 62368-1	7700	V <sub>PK</sub>
V <sub>IOSM</sub>	Maximum surge isolation voltage <sup>(4)</sup>	Tested in oil (qualification test), 1.2/50μs waveform per IEC 62368-1	10000	V <sub>PK</sub>
q <sub>pd</sub>	Apparent charge <sup>(5)</sup>	Method a, after input/output safety test subgroups 2 and 3, V <sub>pd(ini)</sub> = V <sub>IOTM</sub> , t <sub>ini</sub> = 60s, V <sub>pd(m)</sub> = 1.2 × V <sub>IORM</sub> , t <sub>m</sub> = 10s	≤ 5	pC
		Method a, after environmental tests subgroup 1, V <sub>pd(ini)</sub> = V <sub>IOTM</sub> , t <sub>ini</sub> = 60s, V <sub>pd(m)</sub> = 1.6 × V <sub>IORM</sub> , t <sub>m</sub> = 10s	≤ 5	
		Method b1, at preconditioning (type test) and routine test, V <sub>pd(ini)</sub> = 1.2 × V <sub>IOTM</sub> , t <sub>ini</sub> = 1s, V <sub>pd(m)</sub> = 1.875 × V <sub>IORM</sub> , t <sub>m</sub> = 1s	≤ 5	
		Method b2, at routine test (100% production) <sup>(7)</sup> V <sub>pd(ini)</sub> = V <sub>pd(m)</sub> = 1.2 × V <sub>IOTM</sub> , t <sub>ini</sub> = t <sub>m</sub> = 1s	≤ 5	
C <sub>IO</sub>	Barrier capacitance, input to output <sup>(6)</sup>	V <sub>IO</sub> = 0.5 V <sub>PP</sub> at 1MHz	~1.5	pF
R <sub>IO</sub>	Insulation resistance, input to output <sup>(6)</sup>	V <sub>IO</sub> = 500V at T <sub>A</sub> = 25°C	> 10 <sup>12</sup>	Ω
		V <sub>IO</sub> = 500V at 100°C ≤ T <sub>A</sub> ≤ 125°C	> 10 <sup>11</sup>	
		V <sub>IO</sub> = 500V at T <sub>S</sub> = 150°C	> 10 <sup>9</sup>	
	Pollution degree		2	
	Climatic category		55/125/21	
UL1577				
V <sub>ISO</sub>	Withstand isolation voltage	V <sub>TEST</sub> = V <sub>ISO</sub> , t = 60s (qualification test), V <sub>TEST</sub> = 1.2 × V <sub>ISO</sub> , t = 1s (100% production test)	5000	V <sub>RMS</sub>

- (1) Apply creepage and clearance requirements according to the specific equipment isolation standards of an application. Care must be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed circuit board (PCB) do not reduce this distance. Creepage and clearance on a PCB become equal in certain cases. Techniques such as inserting grooves, ribs, or both on a PCB are used to help increase these specifications.
- (2) This coupler is suitable for *safe electrical insulation* only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.
- (3) Testing is carried out in air to determine the surge immunity of the package.
- (4) Testing is carried in oil to determine the intrinsic surge immunity of the isolation barrier.
- (5) Apparent charge is electrical discharge caused by a partial discharge (pd).
- (6) All pins on each side of the barrier are tied together, creating a two-pin device.
- (7) Either method b1 or b2 is used in production.

## 5.7 Safety-Related Certifications

VDE	UL
DIN EN IEC 60747-17 (VDE 0884-17), EN IEC 60747-17, DIN EN IEC 62368-1 (VDE 0868-1), EN IEC 62368-1, IEC 62368-1 Clause : 5.4.3 ; 5.4.4.4 ; 5.4.9	Recognized under 1577 component recognition and CSA component acceptance NO 5 programs
Reinforced insulation	Single protection
Certificate number: Pending	File number: Pending

## 5.8 Safety Limiting Values

Safety limiting<sup>(1)</sup> intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to over-heat the die and damage the isolation barrier potentially leading to secondary system failures.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I <sub>S</sub>	Safety input, output, or supply current	R <sub>θJA</sub> = TBD°C/W, VDDx = 5.5V, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C			TBD	mA
I <sub>S</sub>	Safety input, output, or supply current	R <sub>θJA</sub> = TBD°C/W, VDDx = 3.6V, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C			TBD	mA
P <sub>S</sub>	Safety input, output, or total power	R <sub>θJA</sub> = TBD°C/W, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C			TBD	mW
T <sub>S</sub>	Maximum safety temperature				150	°C

- (1) The maximum safety temperature, T<sub>S</sub>, has the same value as the maximum junction temperature, T<sub>J</sub>, specified for the device. The I<sub>S</sub> and P<sub>S</sub> parameters represent the safety current and safety power, respectively. Do not exceed the maximum limits of I<sub>S</sub> and P<sub>S</sub>. These limits vary with the ambient temperature, T<sub>A</sub>.

The junction-to-air thermal resistance, R<sub>θJA</sub>, in the Thermal Information table is that of a device installed on a high-K test board for leaded surface-mount packages. Use these equations to calculate the value for each parameter:

$T_J = T_A + R_{\theta JA} \times P$ , where P is the power dissipated in the device.

$T_{J(max)} = T_S = T_A + R_{\theta JA} \times P_S$ , where T<sub>J(max)</sub> is the maximum junction temperature.

$P_S = I_S \times VDD_{max}$ , where VDD<sub>max</sub> is the maximum supply voltage for high-side and low-side.

## 5.9 Electrical Characteristics

minimum and maximum specifications apply from  $T_A = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $V_{DD1} = 3.0\text{V}$  to  $5.5\text{V}$ ,  $V_{DD2} = 3.0\text{V}$  to  $5.5\text{V}$ ,  $V_{SNSP} = 0\text{V}$  to  $+1\text{V}$ , and  $V_{SNSN} = 0\text{V}$ ; typical specifications are at  $T_A = 25^{\circ}\text{C}$ ,  $V_{DD1} = 5\text{V}$ ,  $V_{DD2} = 3.3\text{V}$  (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
ANALOG INPUT							
R <sub>IN</sub>	Input resistance	AMC0381D06-Q1	TBD	10	TBD	MΩ	
		AMC0381D10-Q1	TBD	12.5	TBD		
		AMC0381D16-Q1	TBD	33	TBD		
	Nominal resistive divider ratio	V <sub>HVIN</sub> / V <sub>SNSP</sub> , AMC0381D06-Q1	601			V/V	
		V <sub>HVIN</sub> / V <sub>SNSP</sub> , AMC0381D10-Q1	1001				
		V <sub>HVIN</sub> / V <sub>SNSP</sub> , AMC0381D16-Q1	1601				
CMTI	Common-mode transient immunity		50			V/ns	
ANALOG OUTPUT							
	Nominal attenuation	V <sub>HVIN</sub> / (V <sub>OUTP</sub> – V <sub>OUTN</sub> ), AMC038D06-Q1	601 : 2			V/V	
		V <sub>HVIN</sub> / (V <sub>OUTP</sub> – V <sub>OUTN</sub> ), AMC038D10-Q1	1001 : 2				
		V <sub>HVIN</sub> / (V <sub>OUTP</sub> – V <sub>OUTN</sub> ), AMC038D16-Q1	1601 : 2				
V <sub>CMout</sub>	Output common-mode voltage		1.39	1.44	1.49	V	
V <sub>CLIPout</sub>	Clipping differential output voltage	V <sub>OUT</sub> = (V <sub>OUTP</sub> – V <sub>OUTN</sub> ); V <sub>IN</sub> > V <sub>Clipping</sub>	2.49			V	
V <sub>FAILSAFE</sub>	Failsafe differential output voltage	VDD1 undervoltage, or VDD1 missing	–2.6			–2.5	V
R <sub>OUT</sub>	Output resistance	OUTP or OUTN	<0.2			Ω	
	Output short-circuit current	On OUTP or OUTN, sourcing or sinking, HVIN = GND1, outputs shorted to either GND or VDD2	11			mA	
DC ACCURACY							
V <sub>OS</sub>	Input offset voltage	Referred to SNSP, T <sub>A</sub> = 25°C, HVIN = GND1	–1.5	±0.4	1.5	mV	
		Referred to HVIN, HVIN = GND1, T <sub>A</sub> = 25°C, AMC038D06-Q1	–900	±240	900		
		Referred to HVIN, HVIN = GND1, T <sub>A</sub> = 25°C, AMC038D10-Q1	–1500	±400	1500		
		Referred to HVIN, HVIN = GND1, T <sub>A</sub> = 25°C, AMC038D16-Q1	–2400	±640	2400		
TCV <sub>OS</sub>	Input offset thermal drift <sup>(3)</sup>	Referred to SNSP, HVIN = GND1	–0.01	±0.003	0.01	mV/°C	
		Referred to HVIN, HVIN = GND1, AMC038D06-Q1	–6	±1.8	6		
		Referred to HVIN, HVIN = GND1, AMC038D10-Q1	–10	±3	10		
		Referred to HVIN, HVIN = GND1, AMC038D16-Q1	–16	±4.8	16		
E <sub>A</sub>	Attenuation error <sup>(1)</sup>	T <sub>A</sub> = 25°C	–0.25	±0.05	0.25	%	
TCE <sub>A</sub>	Attenuation error temperature drift <sup>(4)</sup>		–40	±20	40	ppm/°C	
	Nonlinearity <sup>(2)</sup>		–0.05%	±0.01%	0.05%		
	Output noise	V <sub>IN</sub> = GND1, BW = 100kHz	TBD			μVrms	
PSRR	Power-supply rejection ratio <sup>(5)</sup>	VDD1 DC PSRR, HVIN = GND1, VDD1 from 3V to 5.5V	–80			dB	
		VDD1 AC PSRR, HVIN = GND1, VDD1 with 10kHz / 100mV ripple	–80				
		VDD2 DC PSRR, HVIN = GND1, VDD2 from 3V to 5.5V	–100				
		VDD2 AC PSRR, HVIN = GND1, VDD2 with 10kHz / 100mV ripple	–86				
AC ACCURACY							
BW	Output bandwidth		90	110		kHz	
THD	Total harmonic distortion	V <sub>SNSP</sub> = 1V <sub>PP</sub> , SNSN = GND1, f <sub>IN</sub> = 10kHz, BW = 10kHz	–93			dB	

## 5.9 Electrical Characteristics (continued)

minimum and maximum specifications apply from  $T_A = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $V_{DD1} = 3.0\text{V}$  to  $5.5\text{V}$ ,  $V_{DD2} = 3.0\text{V}$  to  $5.5\text{V}$ ,  $V_{SNSP} = 0\text{V}$  to  $+1\text{V}$ , and  $V_{SNSN} = 0\text{V}$ ; typical specifications are at  $T_A = 25^{\circ}\text{C}$ ,  $V_{DD1} = 5\text{V}$ ,  $V_{DD2} = 3.3\text{V}$  (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
SNR	Signal-to-noise ratio	$V_{SNSP} = 1V_{PP}$ , $SNSN = \text{GND1}$ , $f_{IN} = 1\text{kHz}$ , $BW = 10\text{kHz}$	73	79		dB
SNR	Signal-to-noise ratio	$V_{SNSP} = 1V_{PP}$ , $SNSN = \text{GND1}$ , $f_{IN} = 10\text{kHz}$ , $BW = 100\text{kHz}$		64.9		dB
<b>POWER SUPPLY</b>						
$I_{DD1}$	High-side supply current			5.3	7.5	mA
$I_{DD2}$	Low-side supply current			3.6	5.1	mA
$V_{DD1_{UV}}$	High-side undervoltage detection threshold	VDD1 rising	2.3	2.55	2.75	V
		VDD1 falling	2.15	2.35	2.55	
$V_{DD2_{UV}}$	Low-side undervoltage detection threshold	VDD2 rising	2.3	2.55	2.75	V
		VDD2 falling	2.15	2.35	2.55	

- (1) The typical value includes one sigma statistical variation.
- (2) Integral nonlinearity is defined as the maximum deviation from a straight line passing through the end-points of the ideal ADC transfer function expressed as number of LSBs or as a percent of the specified linear full-scale range FSR.
- (3) Offset error drift is calculated using the box method, as described by the following equation:  

$$TCE_O = (\text{value}_{MAX} - \text{value}_{MIN}) / \text{TempRange}$$
- (4) Gain error drift is calculated using the box method, as described by the following equation:  

$$TCE_G (\text{ppm}) = ((\text{value}_{MAX} - \text{value}_{MIN}) / (\text{value} \times \text{TempRange})) \times 10^6$$
- (5) This parameter is referred to SNSP.

## 5.10 Switching Characteristics

over operating ambient temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_r$	Output signal rise time			1.8		$\mu\text{s}$
$t_f$	Output signal fall time			1.8		$\mu\text{s}$
	$V_{HVIN}$ to $V_{OUTX}$ signal delay (50% – 10%)	Unfiltered output		2.4		$\mu\text{s}$
	$V_{HVIN}$ to $V_{OUTX}$ signal delay (50% – 50%)	Unfiltered output		3.0	3.2	$\mu\text{s}$
	$V_{HVIN}$ to $V_{OUTX}$ signal delay (50% – 90%)	Unfiltered output		4.2		$\mu\text{s}$
$t_{AS}$	Analog settling time	VDD1 step to 3.0V with $V_{DD2} \geq 3.0\text{V}$ , to $V_{OUTP}$ , $V_{OUTN}$ valid, 0.1% settling		50	100	$\mu\text{s}$

## 5.11 Timing Diagram




Figure 5-1. Rise, Fall, and Delay Time Definition

## 6 Detailed Description


### 6.1 Overview

The AMC0381D-Q1 is a precision, galvanically isolated amplifier with a high-voltage DC, high impedance input, and fixed-gain, differential output. The input stage of the device drives a second-order, delta-sigma ( $\Delta\Sigma$ ) modulator. The modulator converts the analog input signal into a digital bitstream that is transferred across the isolation barrier that separates the high side from the low side.

On the low-side, the received bitstream is processed by a fourth-order analog filter that outputs a differential signal at the OUTP and OUTN pins. This differential output signal is proportional to the input signal.

The SiO<sub>2</sub>-based, capacitive isolation barrier supports a high level of magnetic field immunity, as described in the [ISO72x Digital Isolator Magnetic-Field Immunity application note](#). The digital modulation used in the AMC0381D-Q1 transmits data across the isolation barrier. This modulation, and the isolation barrier characteristics, result in high reliability and high common-mode transient immunity.

### 6.2 Functional Block Diagram



### 6.3 Feature Description

#### 6.3.1 Analog Input


The resistive divider at the input of the AMC0381D-Q1 scales down the voltage applied to the HVIN pin to a 1V linear fullscale level. This signal is available on the SNSP pin, which is also the input of the analog signal chain.

The input stage of the AMC0381D-Q1 feeds a second-order, switched-capacitor, feed-forward  $\Delta\Sigma$  modulator. The modulator converts the analog signal into a bitstream that is transferred across the isolation barrier, as described in the [Isolation Channel Signal Transmission](#) section.

### 6.3.2 Isolation Channel Signal Transmission

The AMC0381D-Q1 uses an on-off keying (OOK) modulation scheme, as shown in [Figure 6-1](#), to transmit the modulator output bitstream across the SiO<sub>2</sub>-based isolation barrier. The transmit driver (TX), as illustrated in the [Functional Block Diagram](#), transmits an internally generated, high-frequency carrier across the isolation barrier to represent a digital *one*. However, TX does not send a signal to represent a digital *zero*. The nominal frequency of the carrier used inside the AMC0381D-Q1 is 480MHz.

The receiver (RX) on the other side of the isolation barrier recovers and demodulates the signal and provides the input to the fourth-order analog filter. The AMC0381D-Q1 transmission channel is optimized to achieve the highest level of common-mode transient immunity (CMTI) and the lowest level of radiated emissions. The high-frequency carrier and RX/TX buffer switching cause these emissions.




**Figure 6-1. OOK-Based Modulation Scheme**

### 6.3.3 Analog Output

The AMC0381D-Q1 provides a differential analog output voltage on the OUTP and OUTN pins that is proportional to the input voltage. For input voltages in the range from  $V_{FSR, MIN}$  to  $V_{FSR, MAX}$ , the device has a linear response with an output voltage equal to:

$$(V_{OUTP} - V_{OUTN}) = V_{IN} = V_{HVIN} / \text{Attenuation} - V_{SNSN} \quad (1)$$

At zero input, both pins output the same common-mode output voltage  $V_{CMout}$ , as specified in the *Electrical Characteristics* table. For absolute input voltages greater than  $|V_{FSR}|$  but less than  $|V_{Clipping}|$ , the differential output voltage continues to increase in magnitude, but with reduced linearity performance. The outputs saturate at a differential output voltage of  $V_{CLIPout}$ , as shown in Figure 6-2, if the input voltage exceeds the  $V_{Clipping}$  value.



**Figure 6-2. Input to Output Transfer Curve of the AMC0381D-Q1**

The AMC0381D-Q1 output offers a fail-safe feature that simplifies diagnostics on a system level. Figure 6-2 shows the behavior in fail-safe mode, in which the AMC0381D-Q1 outputs a negative differential output voltage that does not occur under normal operating conditions. The fail-safe output is active:

- When the high-side supply VDD1 of the AMC0381D-Q1 device is missing
- When the high-side supply VDD1 falls below the undervoltage threshold  $VDD1_{UV}$

Use the maximum  $V_{FAILSAFE}$  voltage specified in the *Electrical Characteristics* table as a reference value for fail-safe detection on a system level.

### 6.4 Device Functional Modes

The AMC0381D-Q1 operates in one of the following states:

- OFF-state: The low-side supply (VDD2) is below the  $VDD2_{UV}$  threshold. The device is not responsive. OUTP and OUTN are in Hi-Z state. Internally, OUTP and OUTN are clamped to VDD2 and GND2 by ESD protection diodes.
- Missing high-side supply: The low-side of the device (VDD2) is supplied and within the *Recommended Operating Conditions* section. The high-side supply (VDD1) is below the  $VDD1_{UV}$  threshold. The device outputs the  $V_{FAILSAFE}$  voltage.
- Analog input overrange (positive fullscale input): VDD1 and VDD2 are within recommended operating conditions but the analog input voltage  $V_{IN}$  is above the maximum clipping voltage  $V_{Clipping, MAX}$ . The device outputs positive  $V_{CLIPout}$ .
- Analog input underrange (negative fullscale input): VDD1 and VDD2 are within recommended operating conditions but the analog input voltage  $V_{IN}$  is below the minimum clipping voltage  $V_{Clipping, MIN}$ . The device outputs negative  $V_{CLIPout}$ .
- Normal operation: VDD1, VDD2, and  $V_{IN}$  are within the recommended operating conditions. The device outputs a differential voltage that is proportional to the input voltage.

Table 6-1 lists the operating modes.

**Table 6-1. Device Operational Modes**

OPERATING CONDITION	VDD1	VDD2	V <sub>IN</sub>	DEVICE RESPONSE
OFF	Don't care	VDD2 < VDD2 <sub>UV</sub>	Don't care	OUTP and OUTN are in Hi-Z state. Internally, OUTP and OUTN are clamped to VDD2 and GND2 by ESD protection diodes.
Missing high-side supply	VDD1 < VDD1 <sub>UV</sub>	Valid <sup>(1)</sup>	Don't care	The device outputs the V <sub>FAILSAFE</sub> voltage.
Input overrange	Valid <sup>(1)</sup>	Valid <sup>(1)</sup>	V <sub>IN</sub> > V <sub>Clipping, MAX</sub>	The device outputs positive V <sub>CLIPout</sub> .
Input underrange	Valid <sup>(1)</sup>	Valid <sup>(1)</sup>	V <sub>IN</sub> < V <sub>Clipping, MIN</sub>	The device outputs negative V <sub>CLIPout</sub> .
Normal operation	Valid <sup>(1)</sup>	Valid <sup>(1)</sup>	Valid <sup>(1)</sup>	The device outputs a differential voltage that is proportional to the input voltage.

(1) "Valid" denotes within the recommended operating conditions.

## 7 Application and Implementation

---

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

---

### 7.1 Application Information

The high input impedance, low input bias current, excellent accuracy, and low-temperature drift make the AMC0381D-Q1 a high-performance system for automotive applications where voltage sensing in the presence of high common-mode voltage levels is required.


### 7.2 Best Design Practices

Avoid any kind of leakage current between the INP and SNSP pin. Leakage current potentially introduces significant measurement error. See the [Layout Example](#) for layout recommendations.

## 7.3 Power Supply Recommendations

In a typical application, the high-side power supply (VDD1) for the AMC0381D-Q1 is generated from the low-side supply (VDD2) by an isolated DC/DC converter. A low-cost option is based on the push-pull driver [SN6501-Q1](#) and a transformer that supports the desired isolation voltage ratings.

The AMC0381D-Q1 does not require any specific power-up sequencing. The high-side power supply (VDD1) is decoupled with a low-ESR, 100nF capacitor (C1) parallel to a low-ESR, 1μF capacitor (C2). The low-side power supply (VDD2) is equally decoupled with a low-ESR, 100nF capacitor (C3) parallel to a low-ESR, 1μF capacitor (C4). Place all four capacitors (C1, C2, C3, and C4) as close to the device as possible. [Figure 7-1](#) shows a decoupling diagram for the AMC0381D-Q1.



**Figure 7-1. Decoupling of the AMC0381D-Q1**

Capacitors provide adequate effective capacitance under the applicable DC bias conditions experienced in the application. Multilayer ceramic capacitors (MLCC) typically exhibit only a fraction of the nominal capacitance under real-world conditions. Take into consideration this factor when selecting these capacitors. This issue is especially acute in low-profile capacitors, in which the dielectric field strength is higher than in taller components. Reputable capacitor manufacturers provide capacitance versus DC bias curves that greatly simplify component selection.


## 7.4 Layout

### 7.4.1 Layout Guidelines

The [Layout Example](#) section details a layout recommendation with the critical placement of the decoupling capacitors (as close as possible to the AMC0381D-Q1 supply pins). This example also depicts the placement of other components required by the device. For best performance, place the sense resistor close to the device input pin (INP).

## 7.4.2 Layout Example

**Figure 7-2. Recommended Layout of the AMC0381D-Q1**



## 8 Device and Documentation Support

### 8.1 Documentation Support

#### 8.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [Isolation Glossary application report](#)
- Texas Instruments, [Semiconductor and IC Package Thermal Metrics application report](#)
- Texas Instruments, [ISO72x Digital Isolator Magnetic-Field Immunity application report](#)
- Texas Instruments, [Isolated Amplifier Voltage Sensing Excel Calculator design tool](#)

### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 8.3 Support Resources

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES
October 2024	*	Initial Release

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.


## 10.1 Mechanical Data

**DFX0015A**



**PACKAGE OUTLINE**  
**SSOP - 3.55 mm max height**

SMALL OUTLINE PACKAGE



### NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.

**SSOP - 3.55 mm max height**

## ADVANCE INFORMATION




6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

**DFX0015A**

**SSOP - 3.55 mm max height**

SMALL OUTLINE PACKAGE



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

ADVANCE INFORMATION

## PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
<a href="#">PAMC0381D10QDFXRQ1</a>	Active	Preproduction	SSOP (DFX)   15	750   LARGE T&R	-	Call TI	Call TI	-40 to 125	
PAMC0381D10QDFXRQ1.A	Active	Preproduction	SSOP (DFX)   15	750   LARGE T&R	-	Call TI	Call TI	See PAMC0381D10QDFXRQ	
PAMC0381D10QDFXRQ1.B	Active	Preproduction	SSOP (DFX)   15	750   LARGE T&R	-	Call TI	Call TI	See PAMC0381D10QDFXRQ	

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated