





**AMC1411** SBASAA7A - MAY 2021 - REVISED SEPTEMBER 2021

# AMC1411 High-Impedance, 2-V Input, Reinforced Isolated Amplifier in a 15-mm Stretched SOIC Package

#### 1 Features

- 2-V, high-impedance input voltage range optimized for isolated voltage measurements
- Fixed gain: 1.0 V/V
- Low DC errors:
  - Offset error ±1.5 mV (max)
  - Offset drift: ±10 µV/°C (max)
  - Gain error: ±0.2% (max)
  - Gain drift: ±30 ppm/°C (max)
  - Nonlinearity 0.04% (max)
- 3.3-V or 5-V operation on high-side and low-side
- Missing high-side supply detection feature
- High CMTI: 100 kV/µs (min)
- ≥15.7-mm creepage, stretched SOIC package
- Reinforced isolation:
  - 10600-V<sub>PK</sub> reinforced isolation per DIN VDE V 0884-11: 2017-01
  - 7500-V<sub>RMS</sub> isolation for 1 minute per UL1577
- Fully specified over the extended industrial temperature range: -40°C to +125°C

### 2 Applications

- Isolated voltage sensing in:
  - Motor drives
  - Frequency inverters
  - Solar inverters
  - Wind turbine inverters
  - Rail transport systems

### 3 Description

The AMC1411 is a precision, isolated amplifier with an output separated from the input circuitry by a capacitive isolation barrier that is highly resistant to magnetic interference. This barrier is certified to provide reinforced galvanic isolation of up to 7.5 kV<sub>RMS</sub> according to VDE V 0884-11 and UL1577 and supports a working voltage of up to 1600 V<sub>RMS</sub>.

The isolation barrier separates parts of the system that operate on different common-mode voltage levels and protects the low-voltage side from voltages that can cause electrical damage or be harmful to an operator.


The high-impedance input of the AMC1411 is optimized for connection to high-impedance resistive dividers or other high-impedance voltage signal source. The excellent DC accuracy and low temperature drift support accurate voltage sensing in DC/DC converters, solar or wind turbine inverters, AC motor drives, or other applications that must operate at high voltages, high altitudes, or in environments with high pollution degrees.

The AMC1411 is specified over the extended industrial temperature range from -40°C to +125°C and supports operation down to -55°C.

#### Device Information(1)

PART NUMBER	PACKAGE	BODY SIZE (NOM)
AMC1411	SOIC (8)	6.4 mm × 14.0 mm

For all available packages, see the orderable addendum at the end of the data sheet.





## **Table of Contents**

1 Features		7.2 Functional Block Diagram	
2 Applications	1	7.3 Feature Description	18
3 Description	1	7.4 Device Functional Modes	
4 Revision History	. 2	8 Application and Implementation	21
5 Pin Configuration and Functions	3	8.1 Application Information	21
6 Specifications	. 4	8.2 Typical Application	21
6.1 Absolute Maximum Ratings	. 4	8.3 What To Do and What Not To Do	25
6.2 ESD Ratings	. 4	9 Power Supply Recommendations	25
6.3 Recommended Operating Conditions	4	10 Layout	26
6.4 Thermal Information	5	10.1 Layout Guidelines	
6.5 Power Ratings	5	10.2 Layout Example	26
6.6 Insulation Specifications	. 6	11 Device and Documentation Support	27
6.7 Safety-Related Certifications	. 7	11.1 Documentation Support	27
6.8 Safety Limiting Values	7	11.2 Receiving Notification of Documentation Updates	27
6.9 Electrical Characteristics	8	11.3 Support Resources	27
6.10 Switching Characteristics	10	11.4 Trademarks	27
6.11 Timing Diagram		11.5 Electrostatic Discharge Caution	27
6.12 Insulation Characteristics Curves	11	11.6 Glossary	27
6.13 Typical Characteristics	12	12 Mechanical, Packaging, and Orderable	
7 Detailed Description		Information	27
7.1 Overview			

# **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	hanges from Revision * (May 2021) to Revision A (September 2021)	Page
•	Changed document status from Advanced Information to Production Data	1



# **5 Pin Configuration and Functions**




Figure 5-1. DWL Package, 8-Pin SOIC (Top View)

**Table 5-1. Pin Functions** 

	PIN	TYPE	DESCRIPTION	
NO.	NAME	IIPE	DESCRIPTION	
1	VDD1	High-side power	High-side power supply <sup>(1)</sup>	
2	INP	Analog input	nalog input	
3	SHTDN	Digital input	Shutdown input, active high, with internal pullup resistor (typical value: 100 k $\Omega$ )	
4	GND1	High-side ground	gh-side analog ground	
5	GND2	Low-side ground	Low-side analog ground	
6	OUTN	Analog output	Inverting analog output	
7	OUTP	Analog output	Noninverting analog output	
8	VDD2	Low-side power	Low-side power supply <sup>(1)</sup>	

<sup>(1)</sup> See the *Power Supply Recommendations* section for power-supply decoupling recommendations.



## **6 Specifications**

## **6.1 Absolute Maximum Ratings**

see(1)

		MIN	MAX	UNIT	
Power-supply voltage	High-side VDD1 to GND1	-0.3	6.5	V	
Tower-supply vollage	Low-side VDD2 to GND2	-0.3	6.5	v	
Innut valtage	IN	GND1 – 6		V	
nput voltage	SHTDN	GND1 – 0.5	VDD1 + 0.5	v	
Output voltage	OUTP, OUTN	GND2 – 0.5	VDD2 + 0.5	V	
Input current	Continuous, any pin except power-supply pins	-10	10	mA	
Tomporatura	Junction, T <sub>J</sub>		150	°C	
Temperature	Storage, T <sub>stg</sub>	-65	150	°C	

<sup>(1)</sup> Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. *Absolute Maximum Ratings* do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

#### 6.2 ESD Ratings

	-		VALUE	UNIT
V		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2000	.,
$V_{(ESD)}$	Electrostatic discharge	Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 <sup>(2)</sup>	±1000	·

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## **6.3 Recommended Operating Conditions**

over operating ambient temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
POWER	SUPPLY					
	High-side power supply	VDD1 to GND1	3	5	5.5	V
	Low-side power supply	VDD2 to GND2	3	3.3	5.5	V
ANALOG	NPUT	·				
V <sub>Clipping</sub>	Input voltage before clipping output	IN to GND1		2.516		V
V <sub>FSR</sub>	Specified linear full-scale voltage	IN to GND1	-0.1		2	V
DIGITAL	INPUT					
	Input voltage	SHTDN to GND1	0		VDD1	V
TEMPER	ATURE RANGE	·				
_	Operating ambient temperature		-55		125	°C
T <sub>A</sub>	Specified ambient temperature		-40		125	C

Product Folder Links: AMC1411

Submit Document Feedback



### **6.4 Thermal Information**

		AMC1411	
	THERMAL METRIC <sup>(1)</sup>	DWL (SOIC)	UNIT
		8 PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	63.2	°C/W
R <sub>0</sub> JC(top)	Junction-to-case (top) thermal resistance	26.1	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	28.5	°C/W
ΨЈТ	Junction-to-top characterization parameter	7.8	°C/W
ΨЈВ	Junction-to-board characterization parameter	26.8	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	n/a	°C/W

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

## 6.5 Power Ratings

	PARAMETER	TEST CONDITIONS	VALUE	UNIT
В	Maximum power dissipation (both sides)	VDD1 = VDD2 = 3.6 V	56	mW
P <sub>D</sub>		VDD1 = VDD2 = 5.5 V	98	
В	Maximum power dissipation (high-side)	VDD1 = 3.6 V	30	mW
P <sub>D1</sub>		VDD1 = 5.5 V	53	
_	Maximum power dissipation (low-side)	VDD2 = 3.6 V	26	mW
P <sub>D2</sub>		VDD2 = 5.5 V	45	



#### 6.6 Insulation Specifications

over operating ambient temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	VALUE	UNIT
GENER	AL			
CLR	External clearance <sup>(1)</sup>	Shortest pin-to-pin distance through air	≥ 14.7	mm
CPG	External creepage <sup>(1)</sup>	Shortest pin-to-pin distance across the package surface	≥ 15.7	mm
DTI	Distance through insulation	Minimum internal gap (internal clearance) of the double insulation	≥ 0.021	mm
СТІ	Comparative tracking index	DIN EN 60112 (VDE 0303-11); IEC 60112	≥ 600	V
	Material group	According to IEC 60664-1	I	
	Overvoltage category	Rated mains voltage ≤ 600 V <sub>RMS</sub>	I-IV	
	per IEC 60664-1	Rated mains voltage ≤ 1000 V <sub>RMS</sub>	1-111	
DIN VDE	V 0884-11 (VDE V 0884-11): 2017-01			
V <sub>IORM</sub>	Maximum repetitive peak isolation voltage	At AC voltage	2260	V <sub>PK</sub>
V <sub>IOWM</sub>	Maximum-rated isolation	At AC voltage (sine wave)	1600	V <sub>RMS</sub>
VIOWM	working voltage	At DC voltage	2260	$V_{DC}$
V <sub>IOTM</sub>	Maximum transient isolation voltage	V <sub>TEST</sub> = V <sub>IOTM</sub> , t = 60 s (qualification test)	10600	V <sub>PK</sub>
		V <sub>TEST</sub> = 1.2 × V <sub>IOTM</sub> , t = 1 s (100% production test)	12720	
V <sub>IOSM</sub>	Maximum surge isolation voltage <sup>(2)</sup>	Test method per IEC 60065, 1.2/50- $\mu$ s waveform, $V_{TEST} = 1.6 \times V_{IOSM} = 12800 V_{PK}$ (qualification)	8000	V <sub>PK</sub>
	Apparent charge <sup>(3)</sup>	Method a, after input/output safety test subgroups 2 and 3, $V_{\text{ini}} = V_{\text{IOTM}}, t_{\text{ini}} = 60 \text{ s, } V_{\text{pd(m)}} = 1.2 \times V_{\text{IORM}}, t_{\text{m}} = 10 \text{ s}$	≤ 5	pC
q <sub>pd</sub>		Method a, after environmental tests subgroup 1, $V_{ini} = V_{IOTM}$ , $t_{ini} = 60$ s, $V_{pd(m)} = 1.6 \times V_{IORM}$ , $t_m = 10$ s	≤ 5	
		Method b1, at routine test (100% production) and preconditioning (type test), $V_{\text{ini}} = V_{\text{IOTM}}$ , $t_{\text{ini}} = 1 \text{ s}$ , $V_{\text{pd(m)}} = 1.875 \times V_{\text{IORM}}$ , $t_{\text{m}} = 1 \text{ s}$	≤ 5	
C <sub>IO</sub>	Barrier capacitance, input to output <sup>(4)</sup>	V <sub>IO</sub> = 0.5 V <sub>PP</sub> at 1 MHz	~1.5	pF
		V <sub>IO</sub> = 500 V at T <sub>A</sub> = 25°C	> 10 <sup>12</sup>	
R <sub>IO</sub>	Insulation resistance, input to output <sup>(4)</sup>	V <sub>IO</sub> = 500 V at 100°C ≤ T <sub>A</sub> ≤ 125°C	> 10 <sup>11</sup>	Ω
	input to cutput	V <sub>IO</sub> = 500 V at T <sub>S</sub> = 150°C	> 10 <sup>9</sup>	
	Pollution degree		2	
	Climatic category		55/125/21	
UL1577	'			
V <sub>ISO</sub>	Withstand isolation voltage	$V_{TEST} = V_{ISO} = 7500 V_{RMS}$ or $10600 V_{DC}$ , $t = 60 s$ (qualification), $V_{TEST} = 1.2 \times V_{ISO} = 9000 V_{RMS}$ , $t = 1 s$ ( $100\%$ production test)	7500	V <sub>RMS</sub>

<sup>(1)</sup> Apply creepage and clearance requirements according to the specific equipment isolation standards of an application. Care must be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed circuit board (PCB) do not reduce this distance. Creepage and clearance on a PCB become equal in certain cases. Techniques such as inserting grooves, ribs, or both on a PCB are used to help increase these specifications.

- (2) Testing is carried out in air or oil to determine the intrinsic surge immunity of the isolation barrier.
- (3) Apparent charge is electrical discharge caused by a partial discharge (pd).
- (4) All pins on each side of the barrier are tied together, creating a two-pin device.

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

### 6.7 Safety-Related Certifications

VDE	UL
Certified according to DIN VDE V 0884-11 (VDE V 0884-11): 2017-01, DIN EN 60950-1 (VDE 0805 Teil 1): 2014-08, and DIN EN 60065 (VDE 0860): 2005-11	Recognized under 1577 component recognition and CSA component acceptance NO 5 programs
Reinforced insulation	Single protection
Certificate number: pending	File number: E181974

### 6.8 Safety Limiting Values

Safety limiting<sup>(1)</sup> intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to over-heat the die and damage the isolation barrier potentially leading to secondary system failures.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I <sub>S</sub>	Safety input, output, or supply current	R <sub>θJA</sub> = 63.2°C/W, VDDx = 3.6 V, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C		550		A
		R <sub>θJA</sub> = 63.2°C/W, VDDx = 5.5 V, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C			360	mA
Ps	Safety input, output, or total power	R <sub>0JA</sub> = 63.2°C/W, T <sub>J</sub> = 150°C, T <sub>A</sub> = 25°C			1980	mW
T <sub>S</sub>	Maximum safety temperature			-	150	°C

<sup>(1)</sup> The maximum safety temperature, T<sub>S</sub>, has the same value as the maximum junction temperature, T<sub>J</sub>, specified for the device. The I<sub>S</sub> and P<sub>S</sub> parameters represent the safety current and safety power, respectively. Do not exceed the maximum limits of I<sub>S</sub> and P<sub>S</sub>. These limits vary with the ambient temperature, T<sub>A</sub>.

The junction-to-air thermal resistance,  $R_{\theta JA}$ , in the Thermal Information table is that of a device installed on a high-K test board for leaded surface-mount packages. Use these equations to calculate the value for each parameter:

 $T_J = T_A + R_{\theta JA} \times P$ , where P is the power dissipated in the device.

 $T_{J(max)} = T_S = T_A + R_{\theta JA} \times P_S$ , where  $T_{J(max)}$  is the maximum junction temperature.

 $P_S = I_S \times VDD_{max}$ , where  $VDD_{max}$  is the maximum supply voltage for high-side and low-side.



### **6.9 Electrical Characteristics**

minimum and maximum specifications apply from  $T_A$  =  $-40^{\circ}$ C to +125°C, VDD1 = 3.0 V to 5.5 V, VDD2 = 3.0 V to 5.5 V, VDD1 = -0.1 V to 2 V, and SHTDN = GND1 = 0 V (unless otherwise noted); typical specifications are at  $T_A$  = 25°C, VDD1 = 5 V, and VDD2 = 3.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
ANALOG	INPUT					
V <sub>OS</sub>	Input offset voltage	$T_A = 25^{\circ}C^{(1)}(2)$	-1.5	±0.1	1.5	mV
TCV <sub>OS</sub>	Input offset thermal drift <sup>(1)</sup> (2) (4)		-10	±3	10	μV/°C
R <sub>IN</sub>	Input resistance	T <sub>A</sub> = 25°C		1		GΩ
I <sub>IB</sub>	Input bias current	IN = GND1, T <sub>A</sub> = 25°C	-15	3.5	15	nA
C <sub>IN</sub>	Input capacitance	f <sub>IN</sub> = 275 kHz		7		pF
ANALOG	ОИТРИТ				'	
	Nominal gain			1		V/V
E <sub>G</sub>	Gain error <sup>(1)</sup>	T <sub>A</sub> = 25°C	-0.2	±0.05	0.2	%
TCE <sub>G</sub>	Gain error drift <sup>(1) (5)</sup>		-30	±5	30	ppm/°C
	Nonlineartity <sup>(1)</sup>		-0.04%	±0.01%	0.04%	
THD	Total harmonic distortion <sup>(3)</sup>	V <sub>IN</sub> = 2 V <sub>PP</sub> , V <sub>IN</sub> > 0 V, f <sub>IN</sub> = 10 kHz, BW = 10 kHz		-87		dB
SNR	Cirrol to union untio	V <sub>IN</sub> = 2 V <sub>PP</sub> , f <sub>IN</sub> = 1 kHz, BW = 10 kHz	79	82.6		٩D
SNK	Signal-to-noise ratio	V <sub>IN</sub> = 2 V <sub>PP</sub> , f <sub>IN</sub> = 10 kHz, BW = 100 kHz			dB	
	Output noise	V <sub>IN</sub> = GND1, BW = 100 kHz		220		μVrms
	Power-supply rejection ratio <sup>(2)</sup>	vs VDD1, at DC		-80		
PSRR		vs VDD2, at DC		-85		٩D
		vs VDD1, 10 kHz / 100-mV ripple		-65		dB
		vs VDD2, 10 kHz / 100-mV ripple		-70		
V <sub>CMout</sub>	Output common-mode voltage		1.39	1.44	1.49	V
V <sub>CLIPout</sub>	Clipping differential output voltage	$V_{OUT} = (V_{OUTP} - V_{OUTN});$ $V_{IN} > V_{Clipping}$		2.49		V
V <sub>FAILSAFE</sub>	Failsafe differential output voltage	SHTDN = high, or VDD1 undervoltage, or VDD1 missing		-2.6	-2.5	٧
BW	Output bandwidth		220	275		kHz
R <sub>OUT</sub>	Output resistance	On OUTP or OUTN		<0.2		Ω
	Output short-circuit current	On OUTP or OUTN, sourcing or sinking, IN = GND1, outputs shorted to either GND or VDD2		14		mA
CMTI	Common-mode transient immunity		100	150		kV/μs
DIGITAL I	NPUT				'	
I <sub>IN</sub>	Input current	SHTDN pin, GND1 ≤ SHTDN ≤ VDD1	-70		1	μA
C <sub>IN</sub>	Input capacitance	SHTDN pin		5		pF
V <sub>IH</sub>	High-level input voltage		0.7 × VDD1			V
V <sub>IL</sub>	Low-level input voltage				0.3 × VDD1	V

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

### **6.9 Electrical Characteristics (continued)**

minimum and maximum specifications apply from  $T_A$  =  $-40^{\circ}$ C to +125°C, VDD1 = 3.0 V to 5.5 V, VDD2 = 3.0 V to 5.5 V, VDD1 = -0.1 V to 2 V, and SHTDN = GND1 = 0 V (unless otherwise noted); typical specifications are at  $T_A$  = 25°C, VDD1 = 5 V, and VDD2 = 3.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER S	SUPPLY					
VDD1	VDD1 undervoltage detection	VDD1 rising	2.5	2.7	2.9	V
VDD1 <sub>UV</sub>	threshold	VDD1 falling	2.4	2.6	2.8	V
VDD0	VDD2 undervoltage detection threshold	VDD2 rising	2.2	.2 2.45 2.6		V
VDD2 <sub>UV</sub>		VDD2 falling	1.85	2.0	2.2	\ \ \
	High-side supply current	3.0 V < VDD1 < 3.6 V		6.0	8.4	m Λ
I <sub>DD1</sub>		4.5 V < VDD1 < 5.5 V, SHTDN = low		7.1	9.7	mA
		SHTDN = VDD1		1.3		μA
		3.0 V < VDD2 < 3.6 V		5.3	7.2	Λ
$I_{DD2}$	Low-side supply current	4.5 V < VDD2 < 5.5 V		5.9	8.1	mA

- (1) The typical value includes one standard deviation (sigma) at nominal operating conditions.
- (2) This parameter is input referred.
- (3) THD is the ratio of the rms sum of the amplitudes of first five higher harmonics to the amplitude of the fundamental.
- (4) Offset error temperature drift is calculated using the box method, as described by the following equation:  $TCV_{OS} = (Value_{MAX} Value_{MIN}) / TempRange$
- (5) Gain error temperature drift is calculated using the box method, as described by the following equation:  $TCE_G(ppm) = (Value_{MAX} Value_{MIN}) / (Value_{(T=25\%)} \times TempRange) \times 10^6$



## **6.10 Switching Characteristics**

over operating ambient temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t <sub>r</sub>	Output signal rise time			1.3		μs
t <sub>f</sub>	Output signal fall time			1.3		μs
	IN to OUTx signal delay (50% – 10%)	Unfiltered output		1	1.5	μs
	IN to OUTx signal delay (50% – 50%)	Unfiltered output		1.6	2.1	μs
	IN to OUTx signal delay (50% – 90%)	Unfiltered output		2.5	3	μs
t <sub>AS</sub>	Analog settling time	VDD1 step to 3.0 V with VDD2 ≥ 3.0 V, to V <sub>OUTP</sub> , V <sub>OUTN</sub> valid, 0.1% settling		50	100	μs
t <sub>EN</sub>	Device enable time	SHTDN high to low		50	100	μs
t <sub>SHTDN</sub>	Device shutdown time	SHTDN low to high		3	10	μs

## **6.11 Timing Diagram**





Figure 6-1. Rise, Fall, and Delay Time Definition

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

#### **6.12 Insulation Characteristics Curves**







Figure 6-2. Thermal Derating Curve for Safety-Limiting Current per VDE

Figure 6-3. Thermal Derating Curve for Safety-Limiting Power per VDE





T<sub>A</sub> up to 150°C, stress-voltage frequency = 60 Hz, isolation working voltage = 1600 V<sub>RMS</sub>, projected insulation lifetime = 98 years

Figure 6-4. Reinforced Isolation Capacitor Lifetime Projection




#### **6.13 Typical Characteristics**









at VDD1 = 5 V, VDD2 = 3.3 V, SHTDN = 0 V, f<sub>IN</sub> = 10 kHz, and BW = 100 kHz (unless otherwise noted)






Figure 6-28. Output Bandwidth vs Low-Side Supply Voltage










### 7 Detailed Description

#### 7.1 Overview

The AMC1411 is a precision, single-ended input, isolated amplifier with a high input-impedance and wide input voltage range. The input stage of the device drives a second-order, delta-sigma ( $\Delta\Sigma$ ) modulator. The modulator converts the analog input signal into a digital bitstream that is transferred across the isolation barrier and separates the high-side from the low-side. On the low-side, the received bitstream is processed by a fourth-order analog filter that outputs a differential signal at the OUTP and OUTN pins proportional to the input signal.

The SiO<sub>2</sub>-based, capacitive isolation barrier supports a high level of magnetic field immunity, as described in the *ISO72x Digital Isolator Magnetic-Field Immunity* application report. The digital modulation used in the AMC1411 to transmit data across the isolation barrier, and the isolation barrier characteristics itself, result in high reliability and common-mode transient immunity.

#### 7.2 Functional Block Diagram



#### 7.3 Feature Description

#### 7.3.1 Analog Input

The single-ended, high-impedance input stage of the AMC1411 feeds a second-order, switched-capacitor, feed-forward  $\Delta\Sigma$  modulator. The modulator converts the analog signal into a bitstream that is transferred across the isolation barrier, as described in the *Isolation Channel Signal Transmission* section.

There are two restrictions on the analog input signal IN. First, if the input voltage  $V_{IN}$  exceeds the range specified in the *Absolute Maximum Ratings* table, the input current must be limited to the absolute maximum value, because the electrostatic discharge (ESD) protection turns on. In addition, the linearity and parametric performance of the device is ensured only when the analog input voltage remains within the linear full-scale range ( $V_{FSR}$ ) as specified in the *Recommended Operating Conditions* table.

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

### 7.3.2 Isolation Channel Signal Transmission

The AMC1411 uses an on-off keying (OOK) modulation scheme, as shown in Figure 7-1, to transmit the modulator output bitstream across the SiO<sub>2</sub>-based isolation barrier. The transmit driver (TX) shown in the *Functional Block Diagram* transmits an internally-generated, high-frequency carrier across the isolation barrier to represent a digital *one* and does not send a signal to represent a digital *zero*. The nominal frequency of the carrier used inside the AMC1411 is 480 MHz.

The receiver (RX) on the other side of the isolation barrier recovers and demodulates the signal and provides the input to the fourth-order analog filter. The AMC1411 transmission channel is optimized to achieve the highest level of common-mode transient immunity (CMTI) and lowest level of radiated emissions caused by the high-frequency carrier and RX/TX buffer switching.




Figure 7-1. OOK-Based Modulation Scheme

#### 7.3.3 Analog Output

The AMC1411 provides a differential analog output on the OUTP and OUTN pins. For input voltages  $V_{\text{IN}}$  in the range from -0.1 V to +2 V, the device provides a linear response with a nominal gain of 1. For example, for an input voltage of 2 V, the differential output voltage  $(V_{\text{OUTP}} - V_{\text{OUTN}})$  is 2 V. At zero input (IN shorted to GND1), both pins output the same common-mode output voltage  $V_{\text{CMout}}$ , as specified in the *Electrical Characteristics* table. For input voltages greater than 2 V but less than approximately 2.5 V, the differential output voltage continues to increase but with reduced linearity performance. The outputs saturate at a differential output voltage of  $V_{\text{CLIPout}}$ , as shown in Figure 7-2, if the input voltage exceeds the  $V_{\text{Clipping}}$  value.




Figure 7-2. Output Behavior of the AMC1411

The AMC1411 output offers a fail-safe feature that simplifies diagnostics on system level. Figure 7-2 shows the fail-safe mode, in which the AMC1411 outputs a negative differential output voltage that does not occur under normal operating conditions. The fail-safe output is active in three cases:

- When the high-side supply VDD1 of the AMC1411 device is missing
- When the high-side supply VDD1 falls below the undervoltage threshold VDD1<sub>IIV</sub>
- · When the SHTDN pin is pulled high

Use the maximum V<sub>FAILSAFE</sub> voltage specified in the *Electrical Characteristics* table as a reference value for fail-safe detection on a system level.

#### 7.4 Device Functional Modes

The AMC1411 is operational when the power supplies VDD1 and VDD2 are applied as specified in the *Recommended Operating Conditions* table.

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

## 8 Application and Implementation

#### **Note**

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

#### 8.1 Application Information

The high input impedance, low input bias current, excellent accuracy, and low temperature drift make the AMC1411 a high-performance solution for industrial applications where voltage sensing in the presence of high common-mode voltage levels is required.

#### 8.2 Typical Application

Reinforced isolated amplifiers are commonly offered in SOIC packages with less than 9 mm of clearance and creepage specification. Equipment with working voltages greater than 850 V, impulse voltage requirements greater than 8000 V, systems designed for altitudes greater than 2000 m or for environments with pollution degree 2 or higher, may require clearance and creepage distances greater than 9 mm depending on the overvoltage category the system is designed for. Examples are 690-V unearthed (IT) 3-phase power network for high-reliability industrial applications or corner-earthed, 690-V, 3-phase systems commonly used for high-power AC motor drives.

The AMC1411 comes in a SOIC package with greater than 15 mm of creepage distance and is specifically designed for use in high-voltage systems that require accurate voltage monitoring and reinforced isolation between high-voltage and low-voltage parts of the system.

Figure 8-1 shows a 3-phase motor-drive application that uses the AMC1411 to monitor the 1200-V, DC-link voltage. The DC-link voltage is divided down to an approximate 2-V level across the bottom resistor (RSNS) of a high-impedance resistive divider that is sensed by the AMC1411. The output of the AMC1411 is a differential analog output voltage of the same value as the input voltage but is galvanically isolated from the high-side by a reinforced isolation barrier.

The wide creepage and clearance, high isolation voltage rating, and high common-mode transient immunity (CMTI) of the AMC1411 ensure reliable and accurate operation in harsh and high-noise environments.




Figure 8-1. Using the AMC1411 for DC Link Voltage Sensing in Frequency Inverters



#### 8.2.1 Design Requirements

Table 8-1 lists the parameters for this typical application.

Table 8-1. Design Requirements

PARAMETER	VALUE			
System input voltage	3-phase, 690 V, 50 Hz, IT system			
Overvoltage category	III			
Altitude	≤2000 m			
DC-link voltage	1200 V (maximum)			
High-side supply voltage	3.3 V or 5 V			
Low-side supply voltage	3.3 V or 5 V			
Maximum resistor operating voltage	75 V			
Voltage drop across the sense resistor (RSNS) for a linear response	2 V (maximum)			
Current through the resistive divider, I <sub>CROSS</sub>	300 μΑ			

#### 8.2.2 Detailed Design Procedure

The 300-µA cross-current requirement at the maximum DC-link voltage (1200 V) determines that the total impedance of the resistive divider is 4 M $\Omega$ . The impedance of the resistive divider is dominated by the top portion (shown exemplary as RX1 and RX2 in Figure 8-1) and the voltage drop across RSNS can be neglected for a moment. The maximum allowed voltage drop per unit resistor is specified as 75 V; therefore, the minimum number of unit resistors in the top portion of the resistive divider is 1200 V / 75 V = 16. The calculated unit value is 4 M $\Omega$  / 16 = 250 k $\Omega$  and the next closest value from the E96 series is 249 k $\Omega$ .

RSNS is sized such that the voltage drop across the resistor at the maximum DC-link voltage (1200 V) equals the linear full-scale range input voltage (V<sub>FSR</sub>) of the AMC1411 that is 2 V. This voltage is calculated as RSNS =  $V_{FSR}$  / ( $V_{DC-link, max} - V_{FSR}$ ) x  $R_{TOP}$ , where  $R_{TOP}$  is the total value of the top resistor string (16 x 249 k $\Omega$  = 3984  $k\Omega$ ). RSNS is calculated as 6.65  $k\Omega$  and matches a value from the E96 series.

Table 8-2 summarizes the design of the resistive divider.

**Table 8-2. Resistor Value Example** 

PARAMETER	VALUE
Unit resistor value, RX	249 kΩ
Number of unit resistors	16
Sense resistor value, RSNS	6.65 kΩ
Total resistance value	3990.65 kΩ
Resulting current through resistive divider, I <sub>CROSS</sub>	300.7 μΑ
Resulting full-scale voltage drop across sense resistor RSNS	2.000 V
Power dissipated in unit resistor RX	22.5 mW
Total power dissipated in resistive divider	361 mW

Product Folder Links: AMC1411

#### 8.2.2.1 Insulation Coordination

In this example of a motor drive application, isolation between the high-voltage and low-voltage parts of the system must be checked against the requirements of the IEC61800-5-1 standard for electrical power drive systems. Isolation must be designed to withstand the rated impulse voltage, temporary overvoltage, and the working voltage. In addition, the physical distance between exposed metal parts on the high- and low-voltage side must meet the minimum creepage and clearance requirements.

Table B.1 of the IEC60664-1 standard defines the impulse voltage for a 690-V, 3-phase, unearthed system (such as an IT system, OVC III) as 8000 V. This value matches the  $V_{IOSM}$  (8000  $V_{PK}$ ) rating of the AMC1411.

Table B.1 of the IEC60664-1 standard also defines the system voltage of a 690-V, 3-phase IT system as 1000 V. According to table 7 of the IEC61800-5-1 standard, the temporary overvoltage for a system voltage of 1000 V is  $3110 \text{ V}_{PK}$ , which is lower than the  $V_{\text{IOTM}}$  (10500 V) of the AMC1411.

The working voltage in this example is 1200 V<sub>DC</sub> and is also lower than V<sub>IOWM</sub> (2260 V<sub>DC</sub>) of the AMC1411.

The minimum clearance for a 8000-V impulse voltage according the IEC61800-5-1, table 9, is 14 mm for reinforced isolation. The AMC1411 provides a minimum clearance of 14.7 mm and meets the requirement.

Finally, the minimum creepage distance for a working voltage of 1200  $V_{DC}$ , insulating material group I, pollution degree 2, reinforced isolation is 2 × 6.04 mm = 12.08 mm according to IEC61800-5-1 table 10. 6.04 mm is the interpolated value between the 1000  $V_{RMS}$  and 1250  $V_{RMS}$  and is doubled for reinforced isolation. The AMC1411 provides a minimum creepage of 15.7 mm and provides significant margin against the minimum requirement.

#### 8.2.2.2 Input Filter Design

Placing an RC filter in front of the isolated amplifier improves signal-to-noise performance of the signal path. In practice, however, the impedance of the resistor divider is so high that adding a filter capacitor on the IN pin limits the signal bandwidth to an unacceptable low limit, such that the filter capacitor is omitted. When used, design the input filter such that:

- The cutoff frequency of the filter is at least one order of magnitude lower than the sampling frequency (20 MHz) of the internal  $\Delta\Sigma$  modulator
- The input bias current does not generate significant voltage drop across the DC impedance of the input filter

Most voltage-sensing applications use high-impedance resistor dividers in front of the isolated amplifier to scale down the input voltage. In this case, a single capacitor (as shown in Figure 8-2) is sufficient to filter the input signal.




Figure 8-2. Input Filter



#### 8.2.2.3 Differential-to-Single-Ended Output Conversion

Figure 8-3 shows an example of a TLV6001-based signal conversion and filter circuit for systems using single-ended input ADCs to convert the analog output voltage into digital. With R1 = R2 = R3 = R4, the output voltage equals  $(V_{OUTP} - V_{OUTN}) + V_{REF}$ . Tailor the bandwidth of this filter stage to the bandwidth requirement of the system and use NP0-type capacitors for best performance. For most applications, R1 = R2 = R3 = R4 = 3.3 k $\Omega$  and C1 = C2 = 330 pF yields good performance.




Figure 8-3. Connecting the AMC1411 Output to a Single-Ended Input ADC

For more information on the general procedure to design the filtering and driving stages of SAR ADCs, see the 18-Bit, 1MSPS Data Acquisition Block (DAQ) Optimized for Lowest Distortion and Noise and 18-Bit Data Acquisition Block (DAQ) Optimized for Lowest Power reference guides, available for download at www.ti.com.

#### 8.2.3 Application Curve

One important aspect of system design is the effective detection of an overvoltage condition to protect switching devices and passive components from damage. To power off the system quickly in the event of an overvoltage condition, a low delay caused by the isolated amplifier is required. Figure 8-4 shows the typical full-scale step response of the AMC1411.




Figure 8-4. Step Response of the AMC1411

Submit Document Feedback

#### 8.3 What To Do and What Not To Do

Do not leave the analog input (IN) of the AMC1411 unconnected (floating) when the device is powered up on the high-side. If the device input is left floating, the bias current may generate a negative input voltage that exceeds the specified input voltage range and the output of the device is invalid.

Do not connect protection diodes to the input (IN) of the AMC1411. Diode leakage current can introduce significant measurement error especially at high temperatures. The input pin is protected against high voltages by its ESD protection circuit and the high impedance of the external restive divider.

### 9 Power Supply Recommendations

In a typical application, the high-side (VDD1) of the AMC1411 is powered from an already existing, high-side-ground referenced 3.3-V or 5-V power supply in the system. Alternatively, the high-side supply can be generated from the low-side supply (VDD2) by an isolated DC/DC converter. A low-cost solution is based on the push-pull driver SN6501 and a transformer that supports the desired isolation voltage ratings.

The AMC1411 does not require any specific power-up sequencing. The high-side power supply (VDD1) is decoupled with a low-ESR, 100-nF capacitor (C1) parallel to a low-ESR, 1-µF capacitor (C2). The low-side power supply (VDD2) is equally decoupled with a low-ESR, 100-nF capacitor (C3) parallel to a low-ESR, 1-µF capacitor (C4). Place all four capacitors (C1, C2, C3, and C4) as close to the device as possible. Figure 9-1 shows the proper decoupling layout for the AMC1411.




Figure 9-1. Decoupling of the AMC1411

Capacitors must provide adequate effective capacitance under the applicable DC bias conditions they experience in the application. Multilayer ceramic capacitors (MLCC) typically exhibit only a fraction of their nominal capacitance under real-world conditions and this factor must be taken into consideration when selecting these capacitors. This problem is especially acute in low-profile capacitors, in which the dielectric field strength is higher than in taller components. Reputable capacitor manufacturers provide capacitance versus DC bias curves that greatly simplify component selection.



### 10 Layout

### 10.1 Layout Guidelines

Figure 10-1 shows a layout recommendation with the critical placement of the decoupling capacitors (as close as possible to the AMC1411 supply pins) and placement of the other components required by the device. For best performance, place the sense resistor close to the device input pin (IN).

### 10.2 Layout Example




Figure 10-1. Recommended Layout of the AMC1411

## 11 Device and Documentation Support

#### 11.1 Documentation Support

#### 11.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, Isolation Glossary application report
- Texas Instruments, Semiconductor and IC Package Thermal Metrics application report
- Texas Instruments, ISO72x Digital Isolator Magnetic-Field Immunity application report
- Texas Instruments, TLV600x Low-Power, Rail-to-Rail In/Out, 1-MHz Operational Amplifier for Cost-Sensitive Systems data sheet
- Texas Instrument, SN6501 Transformer Driver for Isolated Power Supplies data sheet
- Texas Instruments, 18-Bit, 1-MSPS Data Acquisition Block (DAQ) Optimized for Lowest Distortion and Noise design guide
- Texas Instruments, 18-Bit, 1-MSPS Data Acquisition Block (DAQ) Optimized for Lowest Power reference quide
- · Texas Instruments, Isolated Amplifier Voltage Sensing Excel Calculator design tool

### 11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 11.3 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 11.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

#### 11.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 11.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

### 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2021 Texas Instruments Incorporated

www.ti.com 9-Nov-2025

#### PACKAGING INFORMATION

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	<b>RoHS</b> (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
AMC1411DWLR	Active	Production	SOIC (DWL)   8	500   LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	1411
AMC1411DWLR.A	Active	Production	SOIC (DWL)   8	500   LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	1411
AMC1411DWLR.B	Active	Production	SOIC (DWL)   8	500   LARGE T&R	-	Call TI	Call TI	-40 to 125	

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF AMC1411:

Automotive : AMC1411-Q1

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 9-Nov-2025

NOTE: Qualified Version Definiti	ons	initio	Defin	ersion	٧	Qualified	F:	10.	١
----------------------------------	-----	--------	-------	--------	---	-----------	----	-----	---

• Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 24-Jul-2025

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
AMC1411DWLR	SOIC	DWL	8	500	330.0	24.4	18.55	7.2	4.5	24.0	24.0	Q1

**PACKAGE MATERIALS INFORMATION** 

www.ti.com 24-Jul-2025




#### \*All dimensions are nominal

Device	Device Package Type		Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
AMC1411DWLR	SOIC	DWL	8	500	356.0	356.0	45.0	



PLASTIC SMALL OUTLINE




#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 mm per side.
- 4. This dimension does not include interlead flash.



PLASTIC SMALL OUTLINE




NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



PLASTIC SMALL OUTLINE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025