

# CDx4HC243, CDx4HCT243 High-Speed CMOS Logic Quad-Bus Transceiver with Three-State Outputs

## 1 Features

- Typical propagation delay (A to B, B to A) of 7ns at  $V_{CC} = 5\text{ V}$ ,  $C_L = 15\text{ pF}$ ,  $T_A = 25^\circ\text{C}$
- Three-state outputs
- Buffered inputs
- Fanout (over temperature range)
  - Standard outputs : 10 LSTTL loads
  - Bus driver outputs : 15 LSTTL loads
- Wide operating temperature range :  $-55^\circ\text{C}$  to  $125^\circ\text{C}$
- Balanced propagation delay and transition times
- Significant power reduction compared to LSTTL logic ICs
- HC types
  - 2 V to 6 V Operation
  - High noise immunity:  $N_{IL} = 30\%$ ,  $N_{IH} = 30\%$  of  $V_{CC}$  at  $V_{CC} = 5\text{ V}$
- HCT types
  - 4.5 V to 5.5 V operation
  - Direct LSTTL input logic compatibility,  $V_{IL} = 0.8\text{ V (Max)}$ ,  $V_{IH} = 2\text{ V (Min)}$
  - CMOS input compatibility,  $I_I \leq 1\mu\text{A}$  at  $V_{OL}$ ,  $V_{OH}$


## 2 Description

The CDx4HC243 and CDx4HCT243 are quad bus transceivers with 3-state outputs. The OEA and  $\overline{\text{OEB}}$  inputs control both the high-impedance state as well as the direction of communication through the device.

### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | BODY SIZE (NOM)    |
|-------------|------------------------|--------------------|
| CD54HC243F  | CDIP (14)              | 19.55 mm × 6.71 mm |
| CD74HC243E  | PDIP (14)              | 19.31 mm × 6.35 mm |
| CD74HC243M  | SOIC (14)              | 8.65 mm × 3.90 mm  |
| CD74HCT243E | PDIP (14)              | 19.31 mm × 6.35 mm |
| CD74HCT243M | SOIC (14)              | 8.65 mm × 3.90 mm  |

(1) For all packages see the orderable addendum at the end of the datasheet.



**Functional Block Diagram**



## Table of Contents


|  |          |  |           |
|--|----------|--|-----------|
| <b>1 Features</b> .....                          | <b>1</b> | 7.3 Device Functional Modes.....                                 | <b>8</b>  |
| <b>2 Description</b> .....                       | <b>1</b> | <b>8 Power Supply Recommendations</b> .....                      | <b>9</b>  |
| <b>3 Revision History</b> .....                  | <b>2</b> | <b>9 Layout</b> .....  | <b>9</b>  |
| <b>4 Pin Configuration and Functions</b> .....   | <b>3</b> | 9.1 Layout Guidelines.....                                       | <b>9</b>  |
| <b>5 Specifications</b> .....                    | <b>4</b> | <b>10 Device and Documentation Support</b> .....                 | <b>10</b> |
| 5.1 Absolute Maximum Ratings.....                | <b>4</b> | 10.1 Documentation Support.....                                  | <b>10</b> |
| 5.2 Recommended Operating Conditions.....        | <b>4</b> | 10.2 Receiving Notification of Documentation Updates..           | <b>10</b> |
| 5.3 Thermal Information.....                     | <b>4</b> | 10.3 Support Resources.....                                      | <b>10</b> |
| 5.4 Electrical Characteristics.....              | <b>5</b> | 10.4 Trademarks.....   | <b>10</b> |
| 5.5 Switching Characteristics.....               | <b>6</b> | 10.5 Electrostatic Discharge Caution.....                        | <b>10</b> |
| <b>6 Parameter Measurement Information</b> ..... | <b>7</b> | 10.6 Glossary.....   | <b>10</b> |
| <b>7 Detailed Description</b> .....              | <b>8</b> | <b>11 Mechanical, Packaging, and Orderable Information</b> ..... | <b>10</b> |
| 7.1 Overview.....                                | <b>8</b> |  |           |
| 7.2 Functional Block Diagram.....                | <b>8</b> |  |           |

## 3 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision D (October 2003) to Revision E (March 2022)</b>   | <b>Page</b> |
|--|-------------|
| <ul style="list-style-type: none"> <li>Updated the numbering, formatting, tables, figures, and cross-references throughout the document to reflect modern data sheet standards.....</li> </ul> | <b>1</b>    |

## 4 Pin Configuration and Functions



**J, N, or D Package**  
**14-Pin CDIP, PDIP, or SOIC**  
**Top View**

## 5 Specifications

### 5.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|           |   |  | MIN  | MAX      | UNIT |
|-----------|---|--|------|----------|------|
| $V_{CC}$  | Supply voltage  |  | -0.5 | 7        | V    |
| $I_{IK}$  | Input diode current                                     | For $V_I < -0.5V$ or $V_O > V_{CC} + 0.5V$ |      | $\pm 20$ | mA   |
| $I_{OK}$  | Output diode current                                    | For $V_C < -0.5V$ or $V_O > V_{CC} + 0.5V$ |      | $\pm 20$ | mA   |
| $I_O$     | Drain Current, per output                               | For $-0.5V < V_O < V_{CC} + 0.5V$          |      | $\pm 35$ | mA   |
| $I_O$     | Output source or sink current per output pin            | For $V_O > -0.5V$ or $V_O < V_{CC} + 0.5V$ |      | $\pm 25$ | mA   |
|           | Continuous current through $V_{CC}$ or GND              |  |      | $\pm 70$ | mA   |
| $T_{stg}$ | Storage temperature range                               |  | -65  | 150      | °C   |
| $T_J$     | Junction temperature                                    |  |      | 150      | °C   |
|           | Lead temperature (Soldering 10s)(SOIC - Lead Tips Only) |  |      | 300      | °C   |

- (1) Stresses beyond those listed under *absolute maximum ratings* may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under *recommended operating conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 5.2 Recommended Operating Conditions

|          |                          |                 | MIN | MAX      | UNIT |
|----------|--------------------------|-----------------|-----|----------|------|
| $V_{CC}$ | Supply voltage range     | HC Types        | 2   | 6        | V    |
|          |                          | HCT Types       | 4.5 | 5.5      |      |
| $V_I$    | Input voltage            |                 | 0   | $V_{CC}$ | V    |
| $V_O$    | Output voltage           |                 | 0   | $V_{CC}$ | V    |
| $t_t$    | Input rise and fall time | $V_{CC} = 2V$   |     | 1000     | ns   |
|          |                          | $V_{CC} = 4.5V$ |     | 500      |      |
|          |                          | $V_{CC} = 6V$   |     | 400      |      |
| $T_A$    | Temperature Range        |                 | -55 | 125      | °C   |

### 5.3 Thermal Information

| THERMAL METRIC  |   | N (PDIP) | D (SOIC) | UNIT |
|-----------------|---|----------|----------|------|
|                 |   | 14 PINS  | 14 PINS  |      |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance <sup>(1)</sup> | 80       | 86       | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.4 Electrical Characteristics

| PARAMETER   |  | TEST CONDITIONS <sup>(1)</sup>     | V <sub>CC</sub> (V) | 25°C |     |     | -40°C to 85°C |     | -55°C to 125°C |     | UNIT |
|---|--|------------------------------------|---------------------|------|-----|-----|---------------|-----|----------------|-----|------|
|   |  |                                    |                     | MIN  | TYP | MAX | MIN           | MAX | MIN            | MAX |      |
| HC TYPES  |  |                                    |                     |      |     |     |               |     |                |     |      |
| V <sub>IH</sub>                                   | High-level input voltage                   |                                    | 2                   | 1.5  |     |     | 1.5           |     | 1.5            |     | V    |
|   |  |                                    | 4.5                 | 3.15 |     |     | 3.15          |     | 3.15           |     |      |
|   |  |                                    | 6                   | 4.2  |     |     | 4.2           |     | 4.2            |     |      |
| V <sub>IL</sub>                                   | Low-level input voltage                    |                                    | 2                   | 0.5  |     |     | 0.5           |     | 0.5            |     | V    |
|   |  |                                    | 4.5                 | 1.35 |     |     | 1.35          |     | 1.35           |     |      |
|   |  |                                    | 6                   | 1.8  |     |     | 1.8           |     | 1.8            |     |      |
| V <sub>OH</sub>                                   | High-level output voltage<br>CMOS loads    | I <sub>OH</sub> = - 20μA           | 2                   | 1.9  |     |     | 1.9           |     | 1.9            |     | V    |
|   |  | I <sub>OH</sub> = - 20μA           | 4.5                 | 4.4  |     |     | 4.4           |     | 4.4            |     |      |
|   |  | I <sub>OH</sub> = - 20μA           | 6                   | 5.9  |     |     | 5.9           |     | 5.9            |     |      |
|   | High-level output voltage<br>TTL loads     | I <sub>OH</sub> = - 6mA            | 4.5                 | 3.98 |     |     | 3.84          |     | 3.7            |     |      |
|   |  | I <sub>OH</sub> = - 7.8mA          | 6                   | 5.48 |     |     | 5.34          |     | 5.2            |     |      |
|   |  |                                    |                     |      |     |     |               |     |                |     |      |
| V <sub>OL</sub>                                   | Low-level output voltage<br>CMOS loads     | I <sub>OL</sub> = 20μA             | 2                   | 0.1  |     |     | 0.1           |     | 0.1            |     | V    |
|   |  | I <sub>OL</sub> = 20μA             | 4.5                 | 0.1  |     |     | 0.1           |     | 0.1            |     |      |
|   |  | I <sub>OL</sub> = 20μA             | 6                   | 0.1  |     |     | 0.1           |     | 0.1            |     |      |
|   | Low-level output voltage<br>TTL            | I <sub>OL</sub> = 6mA              | 4.5                 | 0.26 |     |     | 0.33          |     | 0.4            |     |      |
|   |  | I <sub>OL</sub> = 7.8mA            | 6                   | 0.26 |     |     | 0.33          |     | 0.4            |     |      |
|   |  |                                    |                     |      |     |     |               |     |                |     |      |
| I <sub>I</sub>                                    | Input leakage current                      | V <sub>CC</sub> or GND             | 6                   | ±0.1 |     |     | ±1            |     | ±1             |     | μA   |
| I <sub>CC</sub>                                   | Supply Current                             | V <sub>CC</sub> or GND             | 6                   | 8    |     |     | 80            |     | 160            |     | μA   |
| I <sub>OZ</sub>                                   | Three-state leakage current                | V <sub>IL</sub> or V <sub>IH</sub> | 6                   | ±0.5 |     |     | ±0.5          |     | ±10            |     | μA   |
| HCT TYPES   |  |                                    |                     |      |     |     |               |     |                |     |      |
| V <sub>IH</sub>                                   | High-level input voltage                   |                                    | 4.5 to 5.5          | 2    |     |     | 2             |     | 2              |     | V    |
| V <sub>IL</sub>                                   | Low-level input voltage                    |                                    | 4.5 to 5.5          | 0.8  |     |     | 0.8           |     | 0.8            |     | V    |
| V <sub>OH</sub>                                   | High-level output voltage<br>CMOS loads    | I <sub>OH</sub> = - 20μA           | 4.5                 | 4.4  |     |     | 4.4           |     | 4.4            |     | V    |
|   | High-level output voltage<br>TTL loads     | I <sub>OH</sub> = - 6mA            | 4.5                 | 3.98 |     |     | 3.84          |     | 3.7            |     |      |
| V <sub>OL</sub>                                   | Low-level output voltage<br>CMOS loads     | I <sub>OL</sub> = 20μA             | 4.5                 | 0.1  |     |     | 0.1           |     | 0.1            |     | V    |
|   | Low-level output voltage<br>TTL loads      | I <sub>OL</sub> = 6mA              | 4.5                 | 0.26 |     |     | 0.33          |     | 0.4            |     |      |
| I <sub>I</sub>                                    | Input leakage current                      | V <sub>CC</sub> to GND             | 5.5                 | ±0.1 |     |     | ±1            |     | ±1             |     | μA   |
| I <sub>CC</sub>                                   | Supply current                             | V <sub>CC</sub> or GND             | 5.5                 | 8    |     |     | 80            |     | 160            |     | μA   |
| ΔI <sub>CC</sub> <sup>(2)</sup><br><sup>(3)</sup> | Additional supply current<br>per input pin | One of An or Bn                    | 4.5 to 5.5          | 100  |     |     | 396           |     | 495            |     | μA   |
|   |  | One of OEA or<br>OEB               | 4.5 to 5.5          | 100  |     |     | 216           |     | 270            |     |      |
| I <sub>OZ</sub>                                   | Three-state leakage current                | V <sub>IL</sub> or V <sub>IH</sub> | 5.5                 | ±0.5 |     |     | ±5            |     | ±10            |     | μA   |

(1) V<sub>I</sub> = V<sub>IH</sub> or V<sub>IL</sub>, unless otherwise noted.

(2) For dual-supply systems theoretical worst case (V<sub>I</sub> = 2.4 V, V<sub>CC</sub> = 5.5 V) specification is 1.8 mA.

(3) Inputs held at V<sub>CC</sub> - 2.1.

## 5.5 Switching Characteristics

Input  $t_i = 6\text{ns}$ . Unless otherwise specified,  $C_L = 50\text{pF}$

| PARAMETER                           |   | V <sub>CC</sub> (V) | 25°C |                   | -40°C to 85°C | -55°C to 125°C | UNIT |    |
|-------------------------------------|---|---------------------|------|-------------------|---------------|----------------|------|----|
|                                     |   |                     | TYP  | MAX               | MAX           | MAX            |      |    |
| HC TYPES                            |   |                     |      |                   |               |                |      |    |
| t <sub>pd</sub>                     | Propagation delay data to outputs             | 2                   |      | 90                | 115           | 135            | ns   |    |
|                                     |   | 4.5                 |      | 7 <sup>(1)</sup>  | 18            | 23             |      | 27 |
|                                     |   | 6                   |      | 15                | 20            | 23             |      |    |
| t <sub>PZH</sub> , t <sub>PZH</sub> | Output high-Z, to high level to low level     | 2                   |      | 150               | 190           | 225            | ns   |    |
|                                     |   | 4.5                 |      | 12 <sup>(1)</sup> | 30            | 38             |      | 45 |
|                                     |   | 6                   |      | 26                | 33            | 38             |      |    |
| t <sub>PHZ</sub> , t <sub>PLZ</sub> | Output high level, output low level to high-Z | 2                   |      | 150               | 190           | 225            | ns   |    |
|                                     |   | 4.5                 |      | 12 <sup>(1)</sup> | 30            | 38             |      | 45 |
|                                     |   | 6                   |      | 26                | 33            | 38             |      |    |
| t <sub>t</sub>                      | Output transition times                       | 2                   |      | 60                | 75            | 90             | ns   |    |
|                                     |   | 4.5                 |      | 12                | 15            | 18             |      |    |
|                                     |   | 6                   |      | 10                | 13            | 15             |      |    |
| C <sub>i</sub>                      | Input capacitance                             |                     |      | 10                | 10            | 10             | pF   |    |
| C <sub>O</sub>                      | Three-state output capacitance                |                     |      | 20                | 20            | 20             | pF   |    |
| C <sub>pd</sub> <sup>(2) (3)</sup>  | Power dissipation capacitance                 | 5                   |      | 80                |               |                | pF   |    |
| HCT TYPES                           |   |                     |      |                   |               |                |      |    |
| t <sub>pd</sub>                     | Propagation delay data to outputs             | 4.5                 |      | 9 <sup>(1)</sup>  | 22            | 28             | 33   | ns |
| t <sub>PZH</sub> , t <sub>PLZ</sub> | Output high-Z to high level to low level      | 4.5                 |      | 14 <sup>(1)</sup> | 34            | 43             | 51   | ns |
| t <sub>PHZ</sub> , t <sub>PLZ</sub> | Output high level, output low level to high-Z | 4.5                 |      | 14 <sup>(1)</sup> | 35            | 44             | 53   | ns |
| t <sub>t</sub>                      | Output transition times                       | 4.5                 |      | 12                | 15            | 18             |      | ns |
| C <sub>i</sub>                      | Input capacitance                             |                     |      | 10                | 10            | 10             |      | pF |
| C <sub>O</sub>                      | Three-state output capacitance                |                     |      | 20                | 20            | 20             |      | pF |
| C <sub>pd</sub> <sup>(2) (3)</sup>  | Power dissipation capacitance                 | 5                   |      | 91                |               |                |      | pF |

(1) Typical value tested at 5V,  $C_L = 15\text{pF}$ .

(2)  $C_{PD}$  is used to determine the dynamic power consumption, per channel.

(3)  $P_D = V_{CC}^2 f_i (C_{PD} + C_L)$  where  $f_i$  = Input Frequency,  $f_O$  = Output Frequency,  $C_L$  = Output Load Capacitance,  $V_{CC}$  = Supply Voltage.

## 6 Parameter Measurement Information

$t_{PD}$  is the maximum between  $t_{PLH}$  and  $t_{PHL}$

$t_t$  is the maximum between  $t_{TLH}$  and  $t_{THL}$




Figure 6-1. HC and HCT transition times and propagation delay times, combination logic




Figure 6-2. HCT transition times and propagation delay times, combination logic




Figure 6-3. HC three-state propagation delay waveform





Figure 6-4. HCT three-state propagation delay waveform



NOTE: Open drain waveforms  $t_{PLZ}$  and  $t_{PZL}$  are the same as those for three-state shown on the left. The test circuit is Output  $R_L = 1k\Omega$  to  $V_{CC}$ ,  $C_L = 50pF$ .

Figure 6-5. HC and HCT three-state propagation delay test circuit

## 7 Detailed Description

### 7.1 Overview

The CDx4HC243 and CDx4HCT243 silicon-gate CMOS three-state bidirectional noninverting buffers are intended for two-way asynchronous communication between data buses. They have high-drive-current outputs that enable high-speed operation when driving large bus capacitances. These circuits possess the low power dissipation of CMOS circuits and have speeds comparable to low-power Schottky TTL circuits. They can drive 15 LSTTL loads.

The states of the output-enable ( $\overline{\text{OEB}}$ , OEA) inputs determine both the direction of flow (A to B, B to A), and the three-state mode.

### 7.2 Functional Block Diagram




Figure 7-1. Functional Diagram

### 7.3 Device Functional Modes

Table 7-1. Truth Table<sup>(1)(2)</sup>

| Control Inputs          |     | HC, HCT243 Series |    |
|-------------------------|-----|-------------------|----|
|                         |     | Data port status  |    |
| $\overline{\text{OEB}}$ | OEA | An                | Bn |
| H                       | H   | O                 | I  |
| L                       | H   | Z                 | Z  |
| H                       | L   | Z                 | Z  |
| L                       | L   | I                 | O  |

- (1) H = High voltage level. L = Low voltage level. I = Input. O = Output (Same level as input). Z = High Impedance
- (2) To prevent excess currents in the High Z modes all I/O terminals should be terminated with 10kΩ to 1MΩ resistors.



## 8 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Recommended Operating Conditions*. Each  $V_{CC}$  terminal should have a good bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.

## 9 Layout

### 9.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used or only 3 of the 4 buffer gates are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

## 10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 10.1 Documentation Support

#### 10.1.1 Related Documentation

### 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 10.3 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 10.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 10.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)       |
|--------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------|
| <a href="#">8409001CA</a>      | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8409001CA<br>CD54HC243F3A |
| <a href="#">CD54HC243F</a>     | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC243F                |
| CD54HC243F.A                   | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC243F                |
| <a href="#">CD54HC243F3A</a>   | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8409001CA<br>CD54HC243F3A |
| CD54HC243F3A.A                 | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8409001CA<br>CD54HC243F3A |
| <a href="#">CD74HC243E</a>     | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC243E                |
| CD74HC243E.A                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC243E                |
| CD74HC243EE4                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC243E                |
| <a href="#">CD74HC243M</a>     | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC243M                    |
| <a href="#">CD74HC243M96</a>   | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU   SN   NIPDAU                 | Level-1-260C-UNLIM                | -55 to 125   | HC243M                    |
| CD74HC243M96.A                 | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC243M                    |
| CD74HC243M96.B                 | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | -           | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC243M                    |
| <a href="#">CD74HC243M96G4</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -55 to 125   | HC243M                    |
| CD74HC243M96G4.A               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC243M                    |
| <a href="#">CD74HCT243E</a>    | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT243E               |
| CD74HCT243E.A                  | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT243E               |
| <a href="#">CD74HCT243M</a>    | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT243M                   |
| CD74HCT243M.A                  | Active        | Production           | SOIC (D)   14  | 50   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT243M                   |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54HC243, CD74HC243 :**

- Catalog : [CD74HC243](#)
- Military : [CD54HC243](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD74HC243M96   | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC243M96   | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.6     | 9.3     | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC243M96G4 | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HC243M96   | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HC243M96   | SOIC         | D               | 14   | 2500 | 366.0       | 364.0      | 50.0        |
| CD74HC243M96G4 | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HC243E    | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC243E    | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC243E.A  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC243E.A  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC243EE4  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC243EE4  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT243E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT243E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT243E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT243E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT243M   | D            | SOIC         | 14   | 50  | 506.6  | 8      | 3940   | 4.32   |
| CD74HCT243M.A | D            | SOIC         | 14   | 50  | 506.6  | 8      | 3940   | 4.32   |

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

**NOTES:**

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.



**TEXAS  
INSTRUMENTS**  
www.ti.com




# EXAMPLE BOARD LAYOUT


D0014A

SOIC - 1.75 mm max height


SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



NON SOLDER MASK  
DEFINED



SOLDER MASK  
DEFINED

SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE




Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G

**J0014A****PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

**NOTES:**

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT

J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X



4214771/A 05/2017

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2025, Texas Instruments Incorporated