

## TPS7A20 300mA、超低ノイズ、低 $I_Q$ 、高 PSRR LDO

### 1 特長

- 低い出力電圧ノイズ:  $7\mu V_{RMS}$ 
  - ノイズ バイパス コンデンサが不要
- 高 PSRR: 1kHz 時に 95dB
- 超低  $I_Q$ :  $6.5\mu A$
- 入力電圧範囲: 1.6V~6.0V
- 出力電圧範囲: 0.8V~5.5V
- 出力電圧許容誤差:  $\pm 1.5\%$  (最大値)
- 非常に低いドロップアウト:
  - 300mA で 140mV 以下 ( $V_{OUT} = 3.3V$ )
  - 300mA で 145mV 以下 ( $V_{OUT} = 3.3V, DBV$ )
- 小さい突入電流
- スマート イネーブルのプルダウン
- 最小  $1\mu F$  のセラミック出力コンデンサで安定
- パッケージ:
  - 1mm × 1mm X2SON (DQN)
  - 0.616mm × 0.616mm DSBGA (YCK)
  - 0.612mm × 0.612mm DSBGA (YCJ)
  - 2.9mm × 2.8mm SOT23-5 (DBV)

### 2 アプリケーション

- スマートフォンとタブレット
- IP ネットワーク カメラ
- 携帯医療機器
- スマート メータとフィールド トランスミッタ
- モーター ドライブ
- ウェアラブル

### 3 概要

TPS7A20 は、300mA の出力電流を供給できる超小型の低ドロップアウト (LDO) リニア レギュレータです。TPS7A20 は、RF やその他の敏感なアナログ回路の要件を満たすため、低ノイズ、高 PSRR、および非常に優れた負荷ライン過渡性能を実現できるよう設計されています。革新的な設計手法を採用した TPS7A20 は、ノイズ バイパス コンデンサを追加しなくても超低ノイズ性能を発揮します。TPS7A20 は、静止電流が小さいという利点も備えているため、バッテリー駆動のアプリケーションに理想的です。1.6V~6.0V の入力電圧範囲と 0.8V~5.5V の出力電圧範囲を持つ TPS7A20 は幅広いアプリケーションに使用できます。本デバイスは、負荷、ライン、温度の変化に対して誤差 1.5% 以下の精度を達成するために高精度の基準電圧回路を使用しています。


TPS7A20 は、突入電流を低減させるための内部ソフトスタートを備えているため、スタートアップ時の入力電圧降下を最小限に抑えることができます。このデバイスは小さなセラミック コンデンサでも安定に動作するため、ソリューション全体を小型化できます。

TPS7A20 は、内部的に制御されるプルダウン抵抗を持つスマート イネーブル入力回路を備えています。EN ピンをフローティング状態のままにしても、このプルダウン抵抗が LDO をディセーブル状態に維持するため、EN ピンをプルダウンするために使用する外付け部品は不要です。

#### パッケージ情報

| 部品番号    | パッケージ (1)       | パッケージ サイズ (2)     |
|---------|-----------------|-------------------|
| TPS7A20 | DQN (X2SON, 4)  | 1mm × 1mm         |
|         | YCJ (DSBGA, 4)  | 0.612mm × 0.612mm |
|         | YCK (DSBGA, 4)  | 0.616mm × 0.616mm |
|         | DBV (SOT-23, 5) | 2.9mm × 2.8mm     |

- 詳細については、「[メカニカル、パッケージ、および注文情報](#)」を参照してください。
- パッケージ サイズ (長さ × 幅) は公称値で、該当する場合はピンも含まれます。




アプリケーション回路図




## Table of Contents

|                                                |           |                                                                  |           |
|------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 特長</b> .....                              | <b>1</b>  | <b>7 Application and Implementation</b> .....                    | <b>27</b> |
| <b>2 アプリケーション</b> .....                        | <b>1</b>  | 7.1 Application Information.....                                 | 27        |
| <b>3 概要</b> .....                              | <b>1</b>  | 7.2 Typical Application.....                                     | 30        |
| <b>4 Pin Configuration and Functions</b> ..... | <b>3</b>  | 7.3 Power Supply Recommendations.....                            | 31        |
| <b>5 Specifications</b> .....                  | <b>5</b>  | 7.4 Layout.....                                                  | 31        |
| 5.1 Absolute Maximum Ratings.....              | 5         | <b>8 Device and Documentation Support</b> .....                  | <b>33</b> |
| 5.2 ESD Ratings.....                           | 5         | 8.1 Device Support.....                                          | 33        |
| 5.3 Recommended Operating Conditions.....      | 5         | 8.2 ドキュメントの更新通知を受け取る方法.....                                      | 33        |
| 5.4 Thermal Information.....                   | 6         | 8.3 サポート・リソース.....                                               | 33        |
| 5.5 Electrical Characteristics.....            | 6         | 8.4 Trademarks.....                                              | 33        |
| 5.6 Switching Characteristics.....             | 7         | 8.5 静電気放電に関する注意事項.....                                           | 33        |
| 5.7 Typical Characteristics.....               | 8         | 8.6 用語集.....                                                     | 33        |
| <b>6 Detailed Description</b> .....            | <b>23</b> | <b>9 Revision History</b> .....                                  | <b>34</b> |
| 6.1 Overview.....                              | 23        | <b>10 Mechanical, Packaging, and Orderable Information</b> ..... | <b>34</b> |
| 6.2 Functional Block Diagram.....              | 23        | 10.1 Mechanical Data.....                                        | 35        |
| 6.3 Feature Description.....                   | 24        |                                                                  |           |
| 6.4 Device Functional Modes.....               | 26        |                                                                  |           |

## 4 Pin Configuration and Functions





✎ 4-1. YCJ and YCK Packages,  
4-Pin DSBGA (Top View)



✎ 4-2. YCJ and YCK Packages,  
4-Pin DSBGA (Bottom View)

### Pin Functions: DSBGA

| PIN |      | I/O | DESCRIPTION                                                                                                                                                                                                                                                                                                                                                                                             |
|-----|------|-----|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NO. | NAME |     |                                                                                                                                                                                                                                                                                                                                                                                                         |
| A1  | IN   | I   | Input voltage supply. For best transient response and to minimize input impedance, use the nominal value or larger capacitor from IN to ground as listed in the <i>Recommended Operating Conditions</i> table. Place the input capacitor as close to the IN and GND pins of the device as possible.                                                                                                     |
| A2  | OUT  | O   | Regulated output voltage. A low equivalent series resistance (ESR) capacitor is required from OUT to ground for stability. For best transient response, use the nominal recommended value or larger capacitor listed in the <i>Recommended Operating Conditions</i> table. Place the output capacitor as close to the OUT and GND pins of the device as possible.                                       |
| B1  | EN   | I   | Enable input. A low voltage ( $< V_{EN(LOW)}$ ) on this input turns the regulator off and discharges the output pin to GND. A high voltage ( $> V_{EN(HI)}$ ) on this pin enables the regulator output. This pin has an internal 500k $\Omega$ pulldown resistor to hold the regulator off by default. When $V_{EN} > V_{EN(HI)}$ , the 500k $\Omega$ pulldown is disconnected to reduce input current. |
| B2  | GND  | —   | Common ground.                                                                                                                                                                                                                                                                                                                                                                                          |


 4-3. DQN Package, 4-Pin X2SON (Top View)

 4-4. DBV Package, 5-Pin SOT-23 (Top View)

### Pin Functions: X2SON, SOT-23

| NAME        | PIN   |        | I/O | DESCRIPTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------|-------|--------|-----|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|             | X2SON | SOT-23 |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| IN          | 4     | 1      | I   | Input voltage supply. For best transient response and to minimize input impedance, use the nominal value or larger capacitor from IN to ground as listed in the <i>Recommended Operating Conditions</i> table. Place the input capacitor as close to the IN and GND pins of the device as possible.                                                                                                                                                                                                                             |
| OUT         | 1     | 5      | O   | Regulated output voltage. A low equivalent series resistance (ESR) capacitor is required from OUT to ground for stability. For best transient response, use the nominal recommended value or larger capacitor listed in the <i>Recommended Operating Conditions</i> table. Place the output capacitor as close to the OUT and GND pins of the device as possible. An internal 150Ω (typical) pulldown resistor prevents a charge from remaining on $V_{OUT}$ when the regulator is in shutdown mode ( $V_{EN} < V_{EN(LOW)}$ ). |
| EN          | 3     | 3      | I   | Enable input. A low voltage ( $< V_{EN(LOW)}$ ) on this pin turns the regulator off and discharges the output pin to GND. A high voltage ( $> V_{EN(HI)}$ ) on this pin enables the regulator output. This pin has an internal 500kΩ pulldown resistor to hold the regulator off by default. When $V_{EN} > V_{EN(HI)}$ , the 500kΩ pulldown is disconnected to reduce input current.                                                                                                                                           |
| GND         | 2     | 2      | —   | Common ground.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| N/C         | —     | 4      | —   | No internal electrical connection.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Thermal Pad | 5     | —      | —   | Thermal pad for the X2SON package. Connect this pad to GND or leave floating. Do not connect to any potential other than GND. Connect the thermal pad to a large-area ground plane for best thermal performance.                                                                                                                                                                                                                                                                                                                |

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1) (3)</sup>

|             |                                    | MIN                | MAX                                         | UNIT |
|-------------|------------------------------------|--------------------|---------------------------------------------|------|
| Voltage     | V <sub>IN</sub>                    | –0.3               | 6.5                                         | V    |
|             | V <sub>OUT</sub>                   | –0.3               | 6.5 or V <sub>IN</sub> + 0.3 <sup>(2)</sup> |      |
|             | V <sub>EN</sub>                    | –0.3               | 6.5                                         |      |
| Current     | Maximum output <sup>(4)</sup>      | Internally limited |                                             | A    |
| Temperature | Operating junction, T <sub>J</sub> | –40                | 150                                         | °C   |
|             | Storage, T <sub>stg</sub>          | –65                | 150                                         | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The maximum value of V<sub>OUT</sub> is the lesser of 6.5 V or (V<sub>IN</sub> + 0.3 V).
- (3) All voltages are with respect to the GND pin.
- (4) Internal thermal shutdown circuitry protects the device from permanent damage.

### 5.2 ESD Ratings

|                    |                         |                                                                                | VALUE | UNIT |
|--------------------|-------------------------|--------------------------------------------------------------------------------|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V    |
|                    |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±750  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                              | MIN | NOM | MAX | UNIT |
|------------------|----------------------------------------------|-----|-----|-----|------|
| V <sub>IN</sub>  | Input supply voltage                         | 1.6 |     | 6.0 | V    |
| V <sub>EN</sub>  | Enable input voltage                         | 0   |     | 6.0 | V    |
| V <sub>OUT</sub> | Nominal output voltage range                 | 0.8 |     | 5.5 | V    |
| I <sub>OUT</sub> | Output current                               | 0   |     | 300 | mA   |
| C <sub>IN</sub>  | Input capacitor <sup>(2)</sup>               |     | 1   |     | μF   |
| C <sub>OUT</sub> | Output capacitor <sup>(3)</sup>              | 1   |     | 200 | μF   |
| ESR              | Output capacitor effective series resistance |     |     | 100 | mΩ   |
| T <sub>J</sub>   | Operating junction temperature               | –40 |     | 125 | °C   |

- (1) All voltages are with respect to GND.
- (2) An input capacitor is not required for LDO stability. However, an input capacitor with an effective value of 0.47 μF minimum is recommended to counteract the effect of source resistance and inductance, which may in some cases cause symptoms of system-level instability such as ringing or oscillation, especially in the presence of load transients.
- (3) Effective output capacitance of 0.47 μF minimum and 200 μF maximum is required for stability.

## 5.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | TPS7A20         |                |                |                | UNIT |
|-------------------------------|----------------------------------------------|-----------------|----------------|----------------|----------------|------|
|                               |                                              | DBV<br>(SOT-23) | DQN<br>(X2SON) | YCJ<br>(DSBGA) | YCK<br>(DSBGA) |      |
|                               |                                              | 5 PINS          | 4 PINS         | 4 PINS         | 4 PINS         |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance       | 187.1           | 166.1          | 199.6          | 201.4          | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance    | 85.5            | 103.6          | 2.8            | 2.8            | °C/W |
| R <sub>θJB</sub>              | Junction-to-board thermal resistance         | 54.4            | 110.6          | 67.5           | 69.3           | °C/W |
| ψ <sub>JT</sub>               | Junction-to-top characterization parameter   | 27.1            | 3.0            | 1.4            | 1.4            | °C/W |
| ψ <sub>JB</sub>               | Junction-to-board characterization parameter | 54.1            | 103.3          | 67.4           | 69.2           | °C/W |
| R <sub>θJC(bot)</sub>         | Junction-to-case (bottom) thermal resistance | N/A             | 98.8           | N/A            | N/A            | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 5.5 Electrical Characteristics

at operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$  or  $1.6\text{ V}$ , whichever is greater,  $V_{EN} = 1.0\text{ V}$ ,  $I_{OUT} = 1\text{ mA}$ ,  $C_{IN} = 1\text{ }\mu\text{F}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$  (unless otherwise noted); all typical values are at  $T_J = 25^{\circ}\text{C}$

| PARAMETER        |                          | TEST CONDITIONS                                                                                                                                                       |                                                      | MIN  | TYP  | MAX | UNIT          |
|------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------|------|------|-----|---------------|
| $\Delta V_{OUT}$ | Output voltage tolerance | $V_{IN} = (V_{OUT(NOM)} + 0.3\text{ V})$ to $6.0\text{ V}$ ,<br>$I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ ,<br>$V_{OUT} \geq 1.85\text{ V}$ (DQN, YCJ, YCK packages) |                                                      | -1.5 |      | 1.5 | %             |
|                  |                          | $V_{IN} = (V_{OUT(NOM)} + 0.3\text{ V})$ to $6.0\text{ V}$ ,<br>$I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ ,<br>$V_{OUT} \geq 2.8\text{ V}$ (DBV package)             |                                                      | -1.5 |      | 1.5 |               |
|                  |                          | $V_{IN} = (V_{OUT(NOM)} + 0.5\text{ V})$ to $6.0\text{ V}$ ,<br>$I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ ,<br>$V_{OUT} < 1.85\text{ V}$ (DQN, YCJ, YCK packages)    |                                                      | -30  |      | 30  | mV            |
|                  |                          | $V_{IN} = (V_{OUT(NOM)} + 0.3\text{ V})$ to $6.0\text{ V}$ ,<br>$I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ ,<br>$V_{OUT} < 2.8\text{ V}$ (DBV package)                |                                                      | -40  |      | 40  |               |
| $\Delta V_{OUT}$ | Line regulation          | $V_{IN} = (V_{OUT(NOM)} + 0.3\text{ V})$ to $6.0\text{ V}$ ,<br>$I_{OUT} = 1\text{ mA}$                                                                               |                                                      |      | 0.03 |     | %/V           |
| $\Delta V_{OUT}$ | Load regulation          | $I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ (DQN, YCJ, YCK packages)                                                                                                   |                                                      |      | 13   |     | mV            |
|                  |                          | $I_{OUT} = 1\text{ mA}$ to $300\text{ mA}$ (DBV package)                                                                                                              |                                                      |      | 19   |     |               |
| $I_{GND}$        | Quiescent ground current | $V_{EN} = V_{IN} = 6\text{ V}$ ,<br>$I_{OUT} = 0\text{ mA}$                                                                                                           | $T_J = 25^{\circ}\text{C}$                           |      | 6.5  | 8.5 | $\mu\text{A}$ |
|                  |                          |                                                                                                                                                                       | $T_J = -40^{\circ}\text{C}$ to $85^{\circ}\text{C}$  |      |      | 10  |               |
|                  |                          |                                                                                                                                                                       | $T_J = -40^{\circ}\text{C}$ to $125^{\circ}\text{C}$ |      |      | 15  |               |
|                  |                          | $V_{EN} = V_{IN} = 6\text{ V}$ , $I_{OUT} = 300\text{ mA}$                                                                                                            |                                                      |      | 2000 |     |               |
| $I_{SHDN}$       | Shutdown ground current  | $V_{EN} = 0\text{ V}$ (disabled), $V_{IN} = 6.0\text{ V}$ , $T_J = 25^{\circ}\text{C}$                                                                                |                                                      |      | 0.07 | 0.2 | $\mu\text{A}$ |
| $I_{GND(DO)}$    | $I_{GND}$ in dropout     | $V_{IN} \leq V_{OUT(NOM)}$ , $I_{OUT} = 0\text{ mA}$ , $V_{EN} = V_{IN}$                                                                                              |                                                      |      | 6.5  | 15  | $\mu\text{A}$ |
| $V_{DO}$         | Dropout voltage          | $I_{OUT} = 300\text{ mA}$ ,<br>$V_{OUT} = 95\% \times V_{OUT(NOM)}$ ,<br>(DQN, YCJ, YCK packages<br>unless otherwise noted)                                           | $0.8\text{ V} \leq V_{OUT} < 1.0\text{ V}^{(1)}$     |      |      | 690 | mV            |
|                  |                          |                                                                                                                                                                       | $1.0\text{ V} \leq V_{OUT} < 1.2\text{ V}^{(1)}$     |      |      | 490 |               |
|                  |                          |                                                                                                                                                                       | $1.2\text{ V} \leq V_{OUT} < 1.5\text{ V}^{(1)}$     |      |      | 355 |               |
|                  |                          |                                                                                                                                                                       | $1.5\text{ V} \leq V_{OUT} < 2.5\text{ V}$           |      |      | 200 |               |
|                  |                          |                                                                                                                                                                       | $1.5\text{ V} \leq V_{OUT} < 2.5\text{ V}$<br>(DBV)  |      |      | 205 |               |
|                  |                          |                                                                                                                                                                       | $2.5\text{ V} \leq V_{OUT} < 5.5\text{ V}$           |      |      | 140 |               |
|                  |                          |                                                                                                                                                                       | $2.5\text{ V} \leq V_{OUT} < 5.5\text{ V}$<br>(DBV)  |      |      | 145 |               |

## 5.5 Electrical Characteristics (続き)

at operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$  or  $1.6\text{ V}$ , whichever is greater,  $V_{EN} = 1.0\text{ V}$ ,  $I_{OUT} = 1\text{ mA}$ ,  $C_{IN} = 1\text{ }\mu\text{F}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$  (unless otherwise noted); all typical values are at  $T_J = 25^{\circ}\text{C}$

| PARAMETER           |                                                | TEST CONDITIONS                                                                              |                                                 | MIN  | TYP  | MAX  | UNIT                |
|---------------------|------------------------------------------------|----------------------------------------------------------------------------------------------|-------------------------------------------------|------|------|------|---------------------|
| $I_{CL}$            | Output current limit                           | $V_{OUT} = 0.9 \times V_{OUT(NOM)}$ ,<br>$V_{IN} = V_{OUT(NOM)} + 0.5\text{ V}$              | $V_{OUT} < 1.5\text{ V}$ (YCJ, YCK packages)    | 360  | 520  | 770  | mA                  |
|                     |                                                | $V_{OUT} = 0.9 \times V_{OUT(NOM)}$ ,<br>$V_{IN} = V_{OUT(NOM)} + 0.5\text{ V}$              | $V_{OUT} < 1.5\text{ V}$ (DQN package)          | 360  | 520  | 730  |                     |
|                     |                                                | $V_{OUT} = V_{OUT(NOM)} - 150\text{ mV}$ ,<br>$V_{IN} = V_{OUT(NOM)} + 0.5\text{ V}$         | $V_{OUT} < 1.5\text{ V}$ (DBV package)          | 360  | 520  | 730  |                     |
|                     |                                                | $V_{OUT} = 0.9 \times V_{OUT(NOM)}$ ,<br>$V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$              | $V_{OUT} \geq 1.5\text{ V}$ (YCJ, YCK packages) | 360  | 520  | 770  |                     |
|                     |                                                | $V_{OUT} = 0.9 \times V_{OUT(NOM)}$ ,<br>$V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$              | $V_{OUT} \geq 1.5\text{ V}$ (DQN package)       | 360  | 520  | 730  |                     |
| $I_{SC}$            | Short-circuit current limit                    | $V_{OUT} = 0\text{ V}$                                                                       |                                                 |      | 160  |      | mA                  |
| PSRR                | Power-supply rejection ratio                   | $I_{OUT} = 20\text{ mA}$ ,<br>$V_{IN} = V_{OUT} + 1.0\text{ V}$                              | $f = 100\text{ Hz}$                             |      | 95   |      | dB                  |
|                     |                                                |                                                                                              | $f = 1\text{ kHz}$                              |      | 95   |      |                     |
|                     |                                                |                                                                                              | $f = 10\text{ kHz}$                             |      | 75   |      |                     |
|                     |                                                |                                                                                              | $f = 100\text{ kHz}$                            |      | 75   |      |                     |
|                     |                                                |                                                                                              | $f = 1\text{ MHz}$                              |      | 45   |      |                     |
|                     |                                                | $I_{OUT} = 300\text{ mA}$ ,<br>$V_{IN} = V_{OUT} + 1.0\text{ V}$                             | $f = 100\text{ Hz}$                             |      | 65   |      |                     |
|                     |                                                |                                                                                              | $f = 1\text{ kHz}$                              |      | 92   |      |                     |
|                     |                                                |                                                                                              | $f = 10\text{ kHz}$                             |      | 75   |      |                     |
|                     |                                                |                                                                                              | $f = 100\text{ kHz}$                            |      | 60   |      |                     |
|                     |                                                |                                                                                              | $f = 1\text{ MHz}$                              |      | 40   |      |                     |
| $V_N$               | Output noise voltage                           | BW = 10 Hz to 100 kHz,<br>$V_{OUT} = 2.8\text{ V}$                                           | $I_{OUT} = 300\text{ mA}$                       |      | 7    |      | $\mu\text{V}_{RMS}$ |
|                     |                                                |                                                                                              | $I_{OUT} = 1\text{ mA}$                         |      | 10   |      |                     |
|                     |                                                |                                                                                              |                                                 |      |      |      |                     |
| $R_{PULLDOWN}$      | Output automatic discharge pulldown resistance | $V_{EN} < V_{EN(LOW)}$ (output disabled), $V_{IN} = 3.1\text{ V}$                            |                                                 |      | 150  |      | $\Omega$            |
| $T_{SD}$            | Thermal shutdown                               | $T_J$ rising                                                                                 |                                                 |      | 165  |      | $^{\circ}\text{C}$  |
|                     |                                                | $T_J$ falling                                                                                |                                                 |      | 140  |      |                     |
| $V_{EN(LOW)}$       | Low input threshold                            | $V_{IN} = 1.6\text{ V}$ to $6.0\text{ V}$ ,<br>$V_{EN}$ falling until the output is disabled |                                                 |      |      | 0.3  | V                   |
| $V_{EN(HI)}$        | High input threshold                           | $V_{IN} = 1.6\text{ V}$ to $6.0\text{ V}$ ,<br>$V_{EN}$ rising until the output is enabled   |                                                 | 0.9  |      |      | V                   |
| $V_{UVLO}$          | UVLO threshold                                 | $V_{IN}$ rising (YCJ and YCK packages)                                                       |                                                 | 1.11 | 1.35 | 1.59 | V                   |
|                     |                                                | $V_{IN}$ rising (DBV and DQN packages)                                                       |                                                 | 1.17 | 1.35 | 1.59 |                     |
|                     |                                                | $V_{IN}$ falling (YCJ and YCK packages)                                                      |                                                 | 1.05 | 1.3  | 1.55 |                     |
|                     |                                                | $V_{IN}$ falling (DBV and DQN packages)                                                      |                                                 | 1.11 | 1.3  | 1.55 |                     |
| $V_{UVLO(HYST)}$    | UVLO hysteresis                                |                                                                                              |                                                 |      | 50   |      | mV                  |
| $I_{EN}$            | EN input leakage current                       | $V_{EN} = 6.0\text{ V}$ and $V_{IN} = 6.0\text{ V}$                                          |                                                 |      | 90   | 250  | nA                  |
| $R_{EN(PULL-DOWN)}$ | Smart enable pulldown resistor                 | $V_{EN} = 0.25\text{ V}$                                                                     |                                                 |      | 500  |      | K $\Omega$          |

(1) Design simulation data only

## 5.6 Switching Characteristics

at operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$  or  $1.6\text{ V}$ , whichever is greater,  $V_{EN} = 1.0\text{ V}$ ,  $I_{OUT} = 1\text{ mA}$ ,  $C_{IN} = 1\text{ }\mu\text{F}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$  (unless otherwise noted); all typical values are at  $T_J = 25^{\circ}\text{C}$

| PARAMETER |               | TEST CONDITIONS                                                    | MIN | TYP | MAX  | UNIT          |
|-----------|---------------|--------------------------------------------------------------------|-----|-----|------|---------------|
| $t_{STR}$ | Start-up time | From $V_{EN} > V_{EN(HI)}$ to $V_{OUT} = 95\%$ of $V_{OUT(NOM)}$ , |     | 750 | 1150 | $\mu\text{s}$ |

## 5.7 Typical Characteristics

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




Figure 5-1. Line Regulation vs  $V_{IN}$




Figure 5-2. Line Regulation vs  $V_{IN}$




Figure 5-3. Line Regulation vs  $V_{IN}$




Figure 5-4. Line Regulation vs  $V_{IN}$




Figure 5-5. Load Regulation vs  $I_{OUT}$





Figure 5-6. Load Regulation vs  $I_{OUT}$


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{IN} = 2.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

5-7. Load Regulation vs  $I_{OUT}$




$V_{IN} = 2.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

5-8. Load Regulation vs  $I_{OUT}$




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-9. Load Regulation vs  $I_{OUT}$




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-10. Load Regulation vs  $I_{OUT}$



$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

5-11. Load Regulation vs  $I_{OUT}$




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

5-12. Load Regulation vs  $I_{OUT}$


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

图 5-13. Output Voltage Accuracy vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

图 5-14. Output Voltage Accuracy vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DBV package

图 5-15. Output Voltage Accuracy vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DBV package

图 5-16. Output Voltage Accuracy vs  $I_{OUT}$



$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

图 5-17. Output Voltage Accuracy vs  $I_{OUT}$




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages


图 5-18. Output Voltage Accuracy vs  $I_{OUT}$

## 5.7 Typical Characteristics (continued)


$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package  
**Figure 5-19. Output Voltage Accuracy vs  $I_{OUT}$**




$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package  
**Figure 5-20. Output Voltage Accuracy vs  $I_{OUT}$**




$V_{EN} = 1 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ , DQN, YCJ, and YCK packages  
**Figure 5-21. Output Voltage Accuracy vs  $V_{IN}$**



$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages  
**Figure 5-22. Output Voltage Accuracy vs  $V_{IN}$**




$V_{EN} = 1 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ , DBV package  
**Figure 5-23. Output Voltage Accuracy vs  $V_{IN}$**



$V_{OUT} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package  
**Figure 5-24. Output Voltage Accuracy vs  $V_{IN}$**


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-25. Dropout Voltage vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-26. Dropout Voltage vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DBV package

5-27. Dropout Voltage vs  $I_{OUT}$




$V_{EN} = 1 \text{ V}$ , DBV package

5-28. Dropout Voltage vs  $I_{OUT}$



$V_{OUT} = 1.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-29. Dropout Voltage vs  $I_{OUT}$




$V_{OUT} = 1.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DQN, YCJ, and YCK packages

5-30. Dropout Voltage vs  $I_{OUT}$


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{OUT} = 1.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

図 5-31. Dropout Voltage vs  $I_{OUT}$




$V_{OUT} = 1.8 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ , DBV package

図 5-32. Dropout Voltage vs  $I_{OUT}$




$I_{OUT} = 300 \text{ mA}$

図 5-33. Dropout Voltage vs  $V_{OUT}$




$V_{EN} = 1 \text{ V}$ ,  $I_{OUT} = 0 \text{ mA}$

図 5-34.  $I_{GND}$  vs  $V_{IN}$



$V_{EN} = V_{IN}$ ,  $I_{OUT} = 0 \text{ mA}$

図 5-35.  $I_{GND}$  vs  $V_{IN}$



$V_{OUT(NOM)} = 5.5 \text{ V}$ ,  $V_{EN} = 1 \text{ V}$ ,  $I_{OUT} = 0 \text{ mA}$

図 5-36.  $I_{GND}$  vs  $V_{IN}$  in the Dropout Region

## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




Figure 5-37.  $I_{GND}$  vs  $V_{IN}$  in the Dropout Region




Figure 5-38.  $I_{GND}$  vs  $I_{OUT}$




Figure 5-39.  $I_{GND}$  vs  $I_{OUT}$




Figure 5-40.  $I_{GND}$  vs  $I_{OUT}$




Figure 5-41. Shutdown Current vs  $V_{IN}$




Figure 5-42. Shutdown Current vs  $V_{IN}$

## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




図 5-43. Enable Pin Leakage Current vs  $V_{EN} - V_{IN}$




図 5-44. Current Limit




図 5-45. Current Limit




図 5-46. UVLO Threshold vs Temperature




図 5-47. Enable Logic High Threshold vs Temperature






図 5-48. Enable Logic Low Threshold vs Temperature

## 5.7 Typical Characteristics (continued)


$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




5-49. Output Pulldown Resistor vs Temperature




5-50. Smart Enable Pulldown Resistor vs Temperature and  $V_{IN}$




5-51. Load Transient



5-52. Load Transient




5-53. Load Transient



5-54. Load Transient


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$I_{OUT} = 0 \text{ mA to } 300 \text{ mA}$ ,  $t_{RISING} = 1 \mu\text{s}$

Figure 5-55. Load Transient




$I_{OUT} = 300 \text{ mA to } 0 \text{ mA}$ ,  $t_{FALLING} = 1 \mu\text{s}$

Figure 5-56. Load Transient




$I_{OUT} = 0 \text{ mA to } 300 \text{ mA}$ ,  $t_{RISING} = 200 \text{ ns}$

Figure 5-57. Load Transient




$I_{OUT} = 300 \text{ mA to } 0 \text{ mA}$ ,  $t_{FALLING} = 200 \text{ ns}$

Figure 5-58. Load Transient



$V_{IN} = 3.1 \text{ V} \rightarrow 4.1 \text{ V} \rightarrow 3.1 \text{ V}$ ,  $V_{IN} t_{RISING} = 5 \mu\text{s}$ ,  $I_{OUT} = 1 \text{ mA}$

Figure 5-59. Line Transient



$V_{IN} = 3.1 \text{ V} \rightarrow 4.1 \text{ V} \rightarrow 3.1 \text{ V}$ ,  $V_{IN} t_{RISING} = 5 \mu\text{s}$ ,  
 $I_{OUT} = 300 \text{ mA}$

Figure 5-60. Line Transient

## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




Figure 5-61. PSRR vs  $V_{IN}$  vs Frequency and  $V_{IN}$




Figure 5-62. PSRR vs Frequency and  $V_{IN}$




Figure 5-63. PSRR vs Frequency and  $I_{OUT}$




Figure 5-64. PSRR vs Frequency and  $C_{OUT}$




Figure 5-65. Noise vs Frequency and  $I_{OUT}$





Figure 5-66. Noise vs Frequency and  $V_{IN}$


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$  or  $1.6\text{ V}$  (whichever is greater),  $V_{OUT} = 2.8\text{ V}$ ,  $I_{OUT} = 1\text{ mA}$ ,  $C_{IN} = 1\text{ }\mu\text{F}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$I_{OUT} = 300\text{ mA}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-67. Noise vs Frequency and  $V_{IN}$




$V_{IN} = 3.8\text{ V}$ ,  $I_{OUT} = 20\text{ mA}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-68. Noise vs Frequency and  $C_{OUT}$




$V_{IN} = 3.8\text{ V}$ ,  $I_{OUT} = 300\text{ mA}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-69. Noise vs Frequency and  $C_{OUT}$




$V_{OUT} = 0.8\text{ V}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-70. Noise vs Frequency and  $I_{OUT}$



$V_{OUT} = 0.8\text{ V}$ ,  $V_{IN} = 1.8\text{ V}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-71. Noise vs Frequency and  $I_{OUT}$




$V_{OUT} = 5.5\text{ V}$ ,  $V_{IN} = 6\text{ V}$ ,  $V_{RMS}$  BW = 10 Hz to 100 kHz

図 5-72. Noise vs Frequency and  $I_{OUT}$


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




From  $V_{EN} = V_{EN(HI)}$  to  $V_{OUT} = 95\%$  of  $V_{OUT(NOM)}$ ,  $I_{OUT} = 0 \text{ mA}$

FIG 5-73. Start-Up Turn-On Time




$V_{OUT} = 0.8 \text{ V}$ ,  $V_{IN} = 0 \text{ V}$  to  $1.8 \text{ V}$ ,  $V_{EN} = 0 \text{ V}$  to  $1.8 \text{ V}$ ,  $V_{EN}$  rises  $500 \mu\text{s}$  behind  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1 \text{ V}/\mu\text{s}$

FIG 5-74. Start-Up




$V_{OUT} = 0.8 \text{ V}$ ,  $V_{IN} = 0 \text{ V}$  to  $1.8 \text{ V}$ ,  $V_{EN} = 0 \text{ V}$  to  $1.8 \text{ V}$ ,  $V_{EN}$  rises  $500 \mu\text{s}$  ahead of  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1 \text{ V}/\mu\text{s}$

FIG 5-75. Start-Up




$V_{OUT} = 0.8 \text{ V}$ ,  $V_{IN} = 0 \text{ V}$  to  $1.8 \text{ V}$ ,  $V_{EN} = V_{IN}$ ,  $V_{IN}$  slew rate =  $1 \text{ V}/\mu\text{s}$

FIG 5-76. Start-Up



$V_{IN} = 0 \text{ V}$  to  $3.8 \text{ V}$ ,  $V_{EN} = 0 \text{ V}$  to  $3.8 \text{ V}$ ,  $V_{EN}$  rises  $500 \mu\text{s}$  behind  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1 \text{ V}/\mu\text{s}$

FIG 5-77. Start-Up




$V_{IN} = 0 \text{ V}$  to  $3.8 \text{ V}$ ,  $V_{EN} = 0 \text{ V}$  to  $3.8 \text{ V}$ ,  $V_{EN}$  rises  $500 \mu\text{s}$  ahead of  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1 \text{ V}/\mu\text{s}$

FIG 5-78. Start-Up


## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3\text{ V}$  or  $1.6\text{ V}$  (whichever is greater),  $V_{OUT} = 2.8\text{ V}$ ,  $I_{OUT} = 1\text{ mA}$ ,  $C_{IN} = 1\text{ }\mu\text{F}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)




$V_{IN} = 0\text{ V}$  to  $3.8\text{ V}$ ,  $V_{EN} = 0\text{ V}$  to  $3.8\text{ V}$ ,  $V_{EN} = V_{IN}$ ,  $V_{IN}$  and slew rate =  $1\text{ V}/\mu\text{s}$

Figure 5-79. Start-Up




$V_{OUT} = 5.5\text{ V}$ ,  $V_{IN} = 0\text{ V}$  to  $6.0\text{ V}$ ,  $V_{EN} = 0\text{ V}$  to  $6.0\text{ V}$ ,  $V_{EN}$  rises  $500\text{ }\mu\text{s}$  behind  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1\text{ V}/\mu\text{s}$

Figure 5-80. Start-Up




$V_{OUT} = 5.5\text{ V}$ ,  $V_{IN} = 0\text{ V}$  to  $6.0\text{ V}$ ,  $V_{EN} = 0\text{ V}$  to  $6.0\text{ V}$ ,  $V_{EN}$  rises  $500\text{ }\mu\text{s}$  ahead of  $V_{IN}$ ,  $V_{IN}$  and  $V_{EN}$  slew rate =  $1\text{ V}/\mu\text{s}$

Figure 5-81. Start-Up




$V_{OUT} = 5.5\text{ V}$ ,  $V_{IN} = 0\text{ V}$  to  $6\text{ V}$ ,  $V_{EN} = V_{IN}$ ,  $V_{IN}$  slew rate =  $1\text{ V}/\mu\text{s}$

Figure 5-82. Start-Up



$V_{OUT} = 0.8\text{ V}$ ,  $V_{IN} = 1.8\text{ V}$ ,  $V_{EN} = 0\text{ V}$  to  $1.8\text{ V}$ ,  $V_{EN}$  slew rate =  $1\text{ V}/\mu\text{s}$ ,  $C_{OUT} = 10\text{ }\mu\text{F}$

Figure 5-83. Inrush Current




$V_{IN} = 3.8\text{ V}$ ,  $V_{EN} = 0\text{ V}$  to  $3.8\text{ V}$ ,  $V_{EN}$  slew rate =  $1\text{ V}/\mu\text{s}$ ,  $C_{OUT} = 10\text{ }\mu\text{F}$

Figure 5-84. Inrush Current

## 5.7 Typical Characteristics (continued)

$V_{IN} = V_{OUT(NOM)} + 0.3 \text{ V}$  or  $1.6 \text{ V}$  (whichever is greater),  $V_{OUT} = 2.8 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 1 \mu\text{F}$ ,  $C_{OUT} = 1 \mu\text{F}$ , and  $T_A = 25^\circ\text{C}$  (unless otherwise noted)



$V_{OUT} = 5.5 \text{ V}$ ,  $V_{IN} = 6.0 \text{ V}$ ,  $V_{EN} = 0 \text{ V to } 6.0 \text{ V}$ ,  
 $V_{EN}$  slew rate =  $1 \text{ V}/\mu\text{s}$ ,  $C_{OUT} = 10 \mu\text{F}$

图 5-85. Inrush Current


## 6 Detailed Description

### 6.1 Overview

Designed to meet the needs of sensitive RF and analog circuits, the TPS7A20 provides low noise, high PSRR, low quiescent current, as well as low line and load transient response figures. Using innovative design techniques, the TPS7A20 offers class-leading noise performance without the need for a separate noise filter capacitor.

The TPS7A20 is designed to operate with a single 1- $\mu\text{F}$  input capacitor and a single 1- $\mu\text{F}$  ceramic output capacitor.

### 6.2 Functional Block Diagram



## 6.3 Feature Description

### 6.3.1 Low Output Noise

Any internal noise at the TPS7A20 reference voltage is reduced by a first-order, low-pass RC filter before being passed to the output buffer stage. The low-pass RC filter has a –3dB cut-off frequency of approximately 0.1Hz.

During start-up, the filter resistor is bypassed to reduce output rise time; the filter begins normal operation after the output voltage reaches the correct value.

### 6.3.2 Smart Enable

The enable (EN) input polarity is active high. The output voltage is enabled when the voltage of the enable input is greater than  $V_{EN(HI)}$  and disabled when the enable input voltage is less than  $V_{EN(LOW)}$ . If independent control of the output voltage is not needed, connect EN to IN.

This device has a smart enable circuit to reduce quiescent current. When the voltage on the enable pin is driven above  $V_{EN(HI)}$ , as listed in the *Electrical Characteristics* table, the device is enabled and the smart enable internal pulldown resistor ( $R_{EN(PULLDOWN)}$ ) is disconnected. When the enable pin is floating, the  $R_{EN(PULLDOWN)}$  is connected and pulls the enable pin low to disable the device. The  $R_{EN(PULLDOWN)}$  value is listed in the *Electrical Characteristics* table.

### 6.3.3 Dropout Voltage

Dropout voltage ( $V_{DO}$ ) is defined as the input voltage minus the output voltage ( $V_{IN} - V_{OUT}$ ) at the rated output current ( $I_{RATED}$ ), where the pass transistor is fully on.  $I_{RATED}$  is the maximum  $I_{OUT}$  listed in the *Recommended Operating Conditions* table. The pass transistor is in the ohmic or triode region of operation, and acts as a switch. The dropout voltage indirectly specifies a minimum input voltage greater than the nominal programmed output voltage at which the output voltage is expected to stay in regulation. If the input voltage falls to less than the value required to maintain output regulation, then the output voltage falls as well.

For a CMOS regulator, the dropout voltage is determined by the drain-source on-state resistance ( $R_{DS(ON)}$ ) of the pass transistor. Therefore, if the linear regulator operates at less than the rated current, the dropout voltage for that current scales accordingly. The following equation calculates the  $R_{DS(ON)}$  of the device.

$$R_{DS(ON)} = \frac{V_{DO}}{I_{RATED}} \quad (1)$$

### 6.3.4 Foldback Current Limit

The device has an internal current limit circuit that protects the regulator during transient high-load current faults or shorting events. The current limit is a hybrid brick-wall-foldback scheme. The current limit transitions from a brick-wall scheme to a foldback scheme at the foldback voltage ( $V_{FOLDBACK}$ ). In a high-load current fault with the output voltage above  $V_{FOLDBACK}$ , the brick-wall scheme limits the output current to the current limit ( $I_{CL}$ ). When the voltage drops below  $V_{FOLDBACK}$ , a foldback current limit activates that scales back the current as the output voltage approaches GND. When the output is shorted, the device supplies a typical current called the short-circuit current limit ( $I_{SC}$ ).  $I_{CL}$  and  $I_{SC}$  are listed in the *Electrical Characteristics* table.

The output voltage is not regulated when the device is in current limit. When a current limit event occurs, the device begins to heat up because of the increase in power dissipation. When the device is in brick-wall current limit, the pass transistor dissipates power  $[(V_{IN} - V_{OUT}) \times I_{CL}]$ . When the device output is shorted and the output is below  $V_{FOLDBACK}$ , the pass transistor dissipates power  $[(V_{IN} - V_{OUT}) \times I_{SC}]$ . If thermal shutdown is triggered, the device turns off. After the device cools down, the internal thermal shutdown circuit turns the device back on. If the output current fault condition continues, the device cycles between current limit and thermal shutdown. For more information on current limits, see the [Know Your Limits application note](#).

図 6-1 shows a diagram of the foldback current limit.




図 6-1. Foldback Current Limit

### 6.3.5 Undervoltage Lockout (UVLO)

The device has an independent undervoltage lockout (UVLO) circuit that monitors the input voltage, allowing a controlled and consistent turn on and off of the output voltage. To prevent the device from turning off if the input drops during turn on, the UVLO has hysteresis as specified in the *Electrical Characteristics* table.

### 6.3.6 Thermal Shutdown

A thermal shutdown protection circuit disables the LDO when the junction temperature ( $T_J$ ) of the pass transistor rises to  $T_{SD(shutdown)}$  (typical). Thermal shutdown hysteresis assures that the device resets (turns on) when the temperature falls to  $T_{SD(reset)}$  (typical).

The thermal time-constant of the semiconductor die is fairly short, thus the device may cycle on and off when thermal shutdown is reached until power dissipation is reduced. Power dissipation during startup can be high from large  $V_{IN} - V_{OUT}$  voltage drops across the device or from high inrush currents charging large output capacitors. Under some conditions, the thermal shutdown protection disables the device before startup completes.

For reliable operation, limit the junction temperature to the maximum listed in the *Recommended Operating Conditions* table. Operation above this maximum temperature causes the device to exceed its operational specifications. Although the internal protection circuitry of the device is designed to protect against thermal overload conditions, this circuitry is not intended to replace proper heat sinking. Continuously running the device into thermal shutdown or above the maximum recommended junction temperature reduces long-term reliability.

### 6.3.7 Active Discharge (P Version Only)

An internal pulldown MOSFET connects a resistor from OUT to ground when the device is disabled to actively discharge the output capacitance. The active discharge circuit is activated by driving EN low or by the voltage on IN falling below the undervoltage lockout (UVLO) threshold.

Do not rely on the active discharge circuit for discharging a large amount of output capacitance after the input supply has collapsed because reverse current can possibly flow from the output to the input. This reverse current flow can cause damage to the device. Limit reverse current to no more than 5% of the device rated current for a short period of time.

## 6.4 Device Functional Modes

### 6.4.1 Device Functional Mode Comparison

表 6-1 shows the conditions that lead to the different modes of operation. See the *Electrical Characteristics* table for parameter values.

表 6-1. Device Functional Mode Comparison

| OPERATING MODE                                       | PARAMETER                                                   |                        |                          |                          |
|------------------------------------------------------|-------------------------------------------------------------|------------------------|--------------------------|--------------------------|
|                                                      | $V_{IN}$                                                    | $V_{EN}$               | $I_{OUT}$                | $T_J$                    |
| Normal operation                                     | $V_{IN} > V_{OUT(nom)} + V_{DO}$ and $V_{IN} > V_{IN(min)}$ | $V_{EN} > V_{EN(HI)}$  | $I_{OUT} < I_{OUT(max)}$ | $T_J < T_{SD(shutdown)}$ |
| Dropout operation                                    | $V_{IN(min)} < V_{IN} < V_{OUT(nom)} + V_{DO}$              | $V_{EN} > V_{EN(HI)}$  | $I_{OUT} < I_{OUT(max)}$ | $T_J < T_{SD(shutdown)}$ |
| Disabled<br>(any true condition disables the device) | $V_{IN} < V_{UVLO}$                                         | $V_{EN} < V_{EN(LOW)}$ | Not applicable           | $T_J > T_{SD(shutdown)}$ |

### 6.4.2 Normal Operation

The device regulates to the nominal output voltage when the following conditions are met:

- The input voltage is greater than the nominal output voltage plus the dropout voltage ( $V_{OUT(nom)} + V_{DO}$ )
- The output current is less than the current limit ( $I_{OUT} < I_{CL}$ )
- The device junction temperature is less than the thermal shutdown temperature ( $T_J < T_{SD}$ )
- The enable voltage has previously exceeded the enable rising threshold voltage and has not yet decreased to less than the enable falling threshold

### 6.4.3 Dropout Operation

If the input voltage is lower than the nominal output voltage plus the specified dropout voltage, but all other conditions are met for normal operation, the device operates in dropout mode. In this mode, the output voltage tracks the input voltage. During this mode, the transient performance of the device becomes significantly degraded because the pass transistor is in the ohmic or triode region, and acts as a switch. Line or load transients in dropout can result in large output-voltage deviations.

When the device is in a steady dropout state (defined as when the device is in dropout,  $V_{IN} < V_{OUT(NOM)} + V_{DO}$ , directly after being in a normal regulation state, but *not* during startup), the pass transistor is driven into the ohmic or triode region. When the input voltage returns to a value greater than or equal to the nominal output voltage plus the dropout voltage ( $V_{OUT(NOM)} + V_{DO}$ ), the output voltage can overshoot for a short period of time while the device pulls the pass transistor back into the linear region.

### 6.4.4 Disabled

The output of the LDO can be shut down by driving EN to less than  $V_{EN(LOW)}$  (see the *Electrical Characteristics* table). When disabled, the pass transistor is turned off, internal circuits are shut down, and the output voltage is actively discharged to ground by an internal discharge circuit between OUT and ground.

## 7 Application and Implementation

### 注

以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

### 7.1 Application Information

#### 7.1.1 Recommended Capacitor Types

The device is designed to be stable using low equivalent series resistance (ESR) ceramic capacitors at the input and output. Multilayer ceramic capacitors have become the industry standard for these types of applications and are recommended, but must be used with good judgment. Ceramic capacitors that employ X7R-, X5R-, and C0G-rated dielectric materials provide relatively good capacitive stability across temperature, whereas the use of Y5V-rated capacitors is discouraged because of large variations in capacitance.

Regardless of the ceramic capacitor type selected, the effective capacitance varies with operating voltage and temperature. As a rule of thumb, expect the effective capacitance to decrease by as much as 50%. The input and output capacitors recommended in the *Recommended Operating Conditions* table account for an effective capacitance of approximately 50% of the nominal value.


#### 7.1.2 Input and Output Capacitor Requirements

Although the LDO itself is stable without an input capacitor, good analog design practice is to connect a capacitor from IN to GND, with a value at least equal to the nominal value specified in the *Recommended Operating Conditions* table. The input capacitor counteracts reactive input sources and improves transient response, input ripple, and PSRR, and is recommended if the source impedance is greater than 0.5  $\Omega$ . When the source resistance and inductance are sufficiently high, especially in the presence of load transients, the overall system may be susceptible to instability (including ringing and sustained oscillation) and other performance degradation if there is insufficient capacitance between IN and GND. A capacitor with a value greater than the minimum may be necessary if large, fast-rise-time load or line transients are anticipated or if the device is located more than a few centimeters from the input power source.

An output capacitor of an appropriate value helps ensure stability and improve dynamic performance. Use an output capacitor within the range specified in the *Recommended Operating Conditions* table.

#### 7.1.3 Load Transient Response

The load-step transient response is the output voltage response by the LDO to a step in load current, whereby output voltage regulation is maintained. There are two key transitions during a load transient response: the transition from a light to a heavy load and the transition from a heavy to a light load. The regions shown in [Figure 7-1](#) are broken down as follows. Regions A, E, and H are where the output voltage is in steady-state.



**図 7-1. Load Transient Waveform**

During transitions from a light load to a heavy load, the:

- Initial voltage dip is a result of the depletion of the output capacitor charge and parasitic impedance to the output capacitor (region B)

- Recovery from the dip results from the LDO increasing its sourcing current, and leads to output voltage regulation (region C)

During transitions from a heavy load to a light load, the:

- Initial voltage rise results from the LDO sourcing a large current, and leads to the output capacitor charge to increase (region F)
- Recovery from the rise results from the LDO decreasing its sourcing current in combination with the load discharging the output capacitor (region G)

A larger output capacitance reduces the peaks during a load transient but slows down the response time of the device. A larger DC load also reduces the peaks because the amplitude of the transition is lowered and a higher current discharge path is provided for the output capacitor.

#### 7.1.4 Undervoltage Lockout (UVLO) Operation

The UVLO circuit ensures that the device stays disabled before its input supply reaches the minimum operational voltage range, and ensures that the device shuts down when the input supply collapses. [Figure 7-2](#) shows the UVLO circuit response to various input voltage events. The diagram can be separated into the following parts:

- Region A: The device does not start until the input reaches the UVLO rising threshold.
- Region B: Normal operation, regulating device.
- Region C: Brownout event above the UVLO falling threshold (UVLO rising threshold – UVLO hysteresis). The output may fall out of regulation but the device remains enabled.
- Region D: Normal operation, regulating device.
- Region E: Brownout event below the UVLO falling threshold. The device is disabled in most cases and the output falls because of the load and active discharge circuit. The device is re-enabled when the UVLO rising threshold is reached by the input voltage and a normal start-up follows.
- Region F: Normal operation followed by the input falling to the UVLO falling threshold.
- Region G: The device is disabled when the input voltage falls below the UVLO falling threshold to 0 V. The output falls because of the load and active discharge circuit.




図 7-2. Typical UVLO Operation

#### 7.1.5 Power Dissipation ( $P_D$ )

Circuit reliability demands that proper consideration be given to device power dissipation, location of the circuit on the printed circuit board (PCB), and correct sizing of the thermal plane. The PCB area around the regulator must be as free as possible of other heat-generating devices that cause added thermal stresses.

As a first-order approximation, power dissipation in the regulator depends on the input-to-output voltage difference and load conditions. Use [Equation 2](#) to approximate  $P_D$ :

$$P_D = (V_{IN} - V_{OUT}) \times I_{OUT} \quad (2)$$

Power dissipation can be minimized, and thus greater efficiency achieved, by proper selection of the system voltage rails. Proper selection allows the minimum input-to-output voltage differential to be obtained. The low dropout of the TPS7A20 allows for maximum efficiency across a wide range of output voltages.

The main heat conduction path for the device is through the thermal pad on the package. As such, the thermal pad must be soldered to a copper pad area under the device. This pad area contains an array of plated vias that conduct heat to any inner plane areas or to a bottom-side copper plane.

The maximum power dissipation determines the maximum allowable junction temperature ( $T_J$ ) for the device. According to 式 3, power dissipation and junction temperature are most often related by the junction-to-ambient thermal resistance ( $R_{\theta JA}$ ) of the combined PCB and device package and the temperature of the ambient air ( $T_A$ ). 式 4 rearranges 式 3 for output current.

$$T_J = T_A + (R_{\theta JA} \times P_D) \quad (3)$$

$$I_{OUT} = (T_J - T_A) / [R_{\theta JA} \times (V_{IN} - V_{OUT})] \quad (4)$$

Unfortunately, this thermal resistance ( $R_{\theta JA}$ ) is highly dependent on the heat-spreading capability built into the particular PCB design, and therefore varies according to the total copper area, copper weight, and location of the planes. The  $R_{\theta JA}$  recorded in the *Thermal Information* table is determined by the JEDEC standard, PCB, and copper-spreading area, and is only used as a relative measure of package thermal performance. For a well-designed thermal layout,  $R_{\theta JA}$  is actually the sum of the X2SON package junction-to-case (bottom) thermal resistance ( $R_{\theta JC(bot)}$ ) plus the thermal resistance contribution by the PCB copper.

#### 7.1.5.1 Estimating Junction Temperature

The JEDEC standard now recommends the use of psi ( $\Psi$ ) thermal metrics to estimate the junction temperatures of the LDO when in-circuit on a typical PCB board application. These metrics are not strictly speaking thermal resistances, but rather offer practical and relative means of estimating junction temperatures. These psi metrics are determined to be significantly independent of the copper-spreading area. The key thermal metrics ( $\Psi_{JT}$  and  $\Psi_{JB}$ ) are used in accordance with 式 5 and are given in the *Thermal Information* table.

$$\Psi_{JT} : T_J = T_T + \Psi_{JT} \times P_D \text{ and } \Psi_{JB} : T_J = T_B + \Psi_{JB} \times P_D \quad (5)$$

where:

- $P_D$  is the power dissipated as explained in 式 2
- $T_T$  is the temperature at the center-top of the device package
- $T_B$  is the PCB surface temperature measured 1 mm from the device package and centered on the package edge

#### 7.1.5.2 Recommended Area for Continuous Operation

The operational area of an LDO is limited by the dropout voltage, output current, junction temperature, and input voltage. The recommended area for continuous operation for a linear regulator is given in 図 7-3 and can be separated into the following parts:

- Dropout voltage limits the minimum differential voltage between the input and the output ( $V_{IN} - V_{OUT}$ ) at a given output current level. See the *Dropout Operation* section for more details.
- The rated output currents limits the maximum recommended output current level. Exceeding this rating causes the device to fall out of specification.
- The rated junction temperature limits the maximum junction temperature of the device. Exceeding this rating causes the device to fall out of specification and reduces long-term reliability.
  - The shape of the slope is given by 式 4. The slope is nonlinear because the maximum-rated junction temperature of the LDO is controlled by the power dissipation across the LDO; thus when  $V_{IN} - V_{OUT}$  increases the output current must decrease.
- The rated input voltage range governs both the minimum and maximum of  $V_{IN} - V_{OUT}$ .

Figure 7-3 shows the recommended area of operation for this device on a JEDEC-standard high-K board with a  $R_{\theta JA}$  as given in the *Thermal Information* table.





Figure 7-3. Region Description of Continuous Operation Regime

## 7.2 Typical Application

Figure 7-4 shows the typical application circuit for the TPS7A20. Input and output capacitances may need to be increased above the 1  $\mu$ F minimum for some applications.



SVA-30180501

Figure 7-4. TPS7A20 Typical Application

### 7.2.1 Design Requirements

Table 7-1 summarizes the design requirements for Figure 7-4.

Table 7-1. Design Parameters

| DESIGN PARAMETER            | EXAMPLE VALUE  |
|-----------------------------|----------------|
| Input voltage range         | 3.1 V to 3.6 V |
| Output voltage              | 2.8 V          |
| Output current              | 200 mA         |
| Maximum ambient temperature | 85°C           |

## 7.2.2 Detailed Design Procedure

For this design example, the 2.8V output version (TPS7A2028) is selected. A nominal 3.3V input supply is assumed. A minimum 1.0μF input capacitor is recommended to minimize the effect of resistance and inductance between the 3.3V source and the LDO input. A minimum 1.0μF output capacitor is also recommended for stability and good load transient response. The dropout voltage ( $V_{DO}$ ) is less than 140mV maximum at a 2.8V output voltage and 300mA output current, so there are no dropout issues with a minimum input voltage of 3.0V and a maximum output current of 200mA.

## 7.2.3 Application Curves




図 7-5. Start-Up




図 7-6. PSRR

## 7.3 Power Supply Recommendations

This device is designed to operate from an input supply voltage range of 1.6V to 6.0V. The input supply must be well regulated and free of spurious noise. To ensure that the output voltage is well regulated and dynamic performance is optimum, the input supply must be at least  $V_{OUT(nom)} + 0.3V$  or 1.6V, whichever is greater. TI highly recommends using a 1μF or greater input capacitor to reduce the impedance of the input supply, especially during transients.

## 7.4 Layout

### 7.4.1 Layout Guidelines

- Place input and output capacitors as close to the device as possible.
- Use copper planes for device connections to optimize thermal performance.
- Place thermal vias around the device to distribute the heat.
- Do not place a thermal via directly beneath the thermal pad of the DQN package. A via can wick solder or solder paste away from the thermal pad joint during the soldering process, leading to a compromised solder joint on the thermal pad.

### 7.4.2 Layout Examples




図 7-7. DBV Package (SOT-23) Typical Layout




図 7-8. DQN Package (X2SON) Typical Layout




図 7-9. YCJ and YCK Package (DSBGA) Typical Layout

## 8 Device and Documentation Support

### 8.1 Device Support

#### 8.1.1 Device Nomenclature

表 8-1. Device Nomenclature

| PRODUCT <sup>(1) (2)</sup> | V <sub>OUT</sub>                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TPS7A20xx(x)Pyyyz          | <p><b>xx(x)</b> is the nominal output voltage. For output voltages with a resolution of 100 mV, two digits are used in the ordering number; otherwise, three digits are used (for example, 28 = 2.8V; 125 = 1.25V).</p> <p><b>P</b> indicates an active output discharge feature.</p> <p><b>yyy</b> is the package designator.</p> <p><b>z</b> is the package quantity. R is for reel (3000 pieces for DQN and DBV; 12000 pieces for YCJ and YCK).</p> |

- (1) For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder on [www.ti.com](http://www.ti.com).
- (2) Output voltages from 0.8V to 5.5V in 25mV increments are available. Contact the factory for details and availability.

### 8.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、[www.tij.co.jp](http://www.tij.co.jp) のデバイス製品フォルダを開いてください。[通知] をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取ることができます。変更の詳細については、改訂されたドキュメントに含まれている改訂履歴をご覧ください。

### 8.3 サポート・リソース

テキサス・インスツルメンツ E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、各寄稿者により「現状のまま」提供されるものです。これらはテキサス・インスツルメンツの仕様を構成するものではなく、必ずしもテキサス・インスツルメンツの見解を反映したものではありません。テキサス・インスツルメンツの[使用条件](#)を参照してください。

### 8.4 Trademarks

テキサス・インスツルメンツ E2E™ is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

### 8.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

### 8.6 用語集

#### テキサス・インスツルメンツ用語集

この用語集には、用語や略語の一覧および定義が記載されています。

## 9 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| <b>Changes from Revision G (May 2022) to Revision H (July 2024)</b>                                                                   | <b>Page</b>        |
|---------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| • 「特長」のパッケージ簡条書き項目を明確化のため変更 .....                                                                                                     | <a href="#">1</a>  |
| • 「アプリケーション回路図」のタイトルを変更 .....                                                                                                         | <a href="#">1</a>  |
| • Deleted discussion of pulldown resistor from OUT pin description in YCJ and YCK package <i>Pin Functions</i> table.....             | <a href="#">3</a>  |
| • Added clarification to <i>Active Discharge (P Version Only)</i> section that this feature only applies to the P device version..... | <a href="#">26</a> |
| • Changed active output discharge feature discussion in <i>Device Nomenclature</i> table.....                                         | <a href="#">33</a> |

| <b>Changes from Revision F (April 2022) to Revision G (May 2022)</b>          | <b>Page</b>       |
|-------------------------------------------------------------------------------|-------------------|
| • Changed UVLO condition from rising to falling for YCJ and YCK packages..... | <a href="#">6</a> |

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## 10.1 Mechanical Data


YCJ0004-C02



### PACKAGE OUTLINE

DSBGA - 0.35 mm max height

DIE SIZE BALL GRID ARRAY




4226216/A 09/2020

#### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

**EXAMPLE BOARD LAYOUT****YCJ0004-C02****DSBGA - 0.35 mm max height**

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 50X



SOLDER MASK DETAILS  
NOT TO SCALE

4226216/A 09/2020

NOTES: (continued)


3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.  
See Texas Instruments Literature No. SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## EXAMPLE STENCIL DESIGN

YCJ0004-C02

DSBGA - 0.35 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.075 mm THICK STENCIL  
SCALE: 50X




4226216/A 09/2020

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

**PACKAGE OUTLINE****YCK0004-C01****DSBGA - 0.33mm MAX HEIGHT**

DIE SIZE BALL GRID ARRAY



D: Max = 0.636 mm, Min = 0.596 mm  
 E: Max = 0.636 mm, Min = 0.596 mm

4228575/A 03/2022

**NOTES:**


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

## EXAMPLE BOARD LAYOUT


**YCK0004-C01**

**DSBGA - 0.33mm MAX HEIGHT**

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:60X



SOLDERMASK DETAILS  
NOT TO SCALE


4228575/A 03/2022

NOTES: (continued)

- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. Refer to Texas Instruments Literature No. SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

**EXAMPLE STENCIL DESIGN****YCK0004-C01****DSBGA - 0.33mm MAX HEIGHT**

DIE SIZE BALL GRID ARRAY



**SOLDERPASTE EXAMPLE**  
 BASED ON 0.075 mm THICK STENCIL  
 SCALE:80X

4228575/A 03/2022

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

## 重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、[テキサス・インスツルメンツの販売条件](#)、または [ti.com](https://www.ti.com) やかかる テキサス・インスツルメンツ製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。テキサス・インスツルメンツがこれらのリソースを提供することは、適用されるテキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated

## PACKAGING INFORMATION

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">PTPS7A2025PDQNR</a> | Active        | Preproduction        | X2SON (DQN)   4  | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| PTPS7A2025PDQNR.A               | Active        | Preproduction        | X2SON (DQN)   4  | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">PTPS7A2045PDQNR</a> | Active        | Preproduction        | X2SON (DQN)   4  | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| PTPS7A2045PDQNR.A               | Active        | Preproduction        | X2SON (DQN)   4  | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS7A2008DQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QH                  |
| TPS7A2008DQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QH                  |
| <a href="#">TPS7A2009PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GBF                |
| TPS7A2009PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GBF                |
| <a href="#">TPS7A2009PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KT                  |
| TPS7A2009PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KT                  |
| <a href="#">TPS7A20105PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KS                  |
| TPS7A20105PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KS                  |
| <a href="#">TPS7A20115PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QE                  |
| TPS7A20115PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QE                  |
| <a href="#">TPS7A2011PYCKR</a>  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Q                   |
| TPS7A2011PYCKR.A                | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Q                   |
| <a href="#">TPS7A2012DQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QI                  |
| TPS7A2012DQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QI                  |
| <a href="#">TPS7A2012PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2ATF                |
| TPS7A2012PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2ATF                |
| TPS7A2012PDBVRG4                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2ATF                |
| TPS7A2012PDBVRG4.A              | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2ATF                |
| <a href="#">TPS7A2012PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JC                  |
| TPS7A2012PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JC                  |
| <a href="#">TPS7A2012PYCJR</a>  | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | M                   |
| TPS7A2012PYCJR.A                | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | M                   |
| <a href="#">TPS7A20135PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | MM                  |
| TPS7A20135PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | MM                  |
| <a href="#">TPS7A2013DQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QJ                  |

| Orderable part number              | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS7A2013DQNR.A                    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QJ                  |
| <a href="#">TPS7A2015PDBVR</a>     | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2DTF                |
| TPS7A2015PDBVR.A                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 2DTF                |
| <a href="#">TPS7A2015PDQNR</a>     | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | JD                  |
| TPS7A2015PDQNR.A                   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JD                  |
| <a href="#">TPS7A2016YCKR</a>      | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Z                   |
| TPS7A2016YCKR.A                    | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Z                   |
| <a href="#">TPS7A201825PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | IQ                  |
| TPS7A201825PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | IQ                  |
| <a href="#">TPS7A201825PDQNRM3</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | IQ                  |
| TPS7A201825PDQNRM3.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | IQ                  |
| <a href="#">TPS7A20185PDBVR</a>    | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2CBF                |
| TPS7A20185PDBVR.A                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 2CBF                |
| TPS7A20185PDBVRG4                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2CBF                |
| TPS7A20185PDBVRG4.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2CBF                |
| <a href="#">TPS7A20185PDQNR</a>    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | JE                  |
| TPS7A20185PDQNR.A                  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JE                  |
| <a href="#">TPS7A20185PDQNRM3</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JE                  |
| TPS7A20185PDQNRM3.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JE                  |
| <a href="#">TPS7A20185PYCKR</a>    | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | T                   |
| TPS7A20185PYCKR.A                  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | T                   |
| <a href="#">TPS7A2018DQNR</a>      | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QK                  |
| TPS7A2018DQNR.A                    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QK                  |
| <a href="#">TPS7A2018PDBVR</a>     | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2AUF                |
| TPS7A2018PDBVR.A                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 2AUF                |
| TPS7A2018PDBVRG4                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AUF                |
| TPS7A2018PDBVRG4.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AUF                |
| <a href="#">TPS7A2018PDQNR</a>     | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | JF                  |
| TPS7A2018PDQNR.A                   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JF                  |
| <a href="#">TPS7A2018PDQNRM3</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JF                  |
| TPS7A2018PDQNRM3.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JF                  |

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS7A2018PYCKR</a>   | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | D                   |
| TPS7A2018PYCKR.A                 | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | D                   |
| <a href="#">TPS7A2018PYCKRM3</a> | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | D                   |
| <a href="#">TPS7A2018YCKR</a>    | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Y                   |
| TPS7A2018YCKR.A                  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | Y                   |
| <a href="#">TPS7A2020PYCKR</a>   | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | S                   |
| TPS7A2020PYCKR.A                 | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | S                   |
| <a href="#">TPS7A20225PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | PX                  |
| TPS7A20225PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | PX                  |
| <a href="#">TPS7A202275PYCKR</a> | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | B                   |
| TPS7A202275PYCKR.A               | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | B                   |
| <a href="#">TPS7A2022PYCKR</a>   | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | K                   |
| TPS7A2022PYCKR.A                 | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | K                   |
| <a href="#">TPS7A2024PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2CCF                |
| TPS7A2024PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2CCF                |
| <a href="#">TPS7A2025DQNR</a>    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QL                  |
| TPS7A2025DQNR.A                  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QL                  |
| <a href="#">TPS7A2025PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2AVF                |
| TPS7A2025PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AVF                |
| TPS7A2025PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AVF                |
| TPS7A2025PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AVF                |
| <a href="#">TPS7A2025PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JG                  |
| TPS7A2025PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JG                  |
| <a href="#">TPS7A2025PYCJR</a>   | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | L                   |
| TPS7A2025PYCJR.A                 | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | L                   |
| <a href="#">TPS7A2027PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KO                  |
| TPS7A2027PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KO                  |
| <a href="#">TPS7A2027PYCJR</a>   | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | N                   |
| TPS7A2027PYCJR.A                 | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | N                   |
| <a href="#">TPS7A20285PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GCF                |
| TPS7A20285PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GCF                |

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS7A20285PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KN                  |
| TPS7A20285PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KN                  |
| <a href="#">TPS7A20285PYCKR</a>  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | P                   |
| TPS7A20285PYCKR.A                | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | P                   |
| <a href="#">TPS7A2028DQNR</a>    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QM                  |
| TPS7A2028DQNR.A                  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QM                  |
| <a href="#">TPS7A2028PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2AWF                |
| TPS7A2028PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AWF                |
| <a href="#">TPS7A2028PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | JH                  |
| TPS7A2028PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JH                  |
| <a href="#">TPS7A2028PDQNRM3</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JH                  |
| TPS7A2028PDQNRM3.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JH                  |
| <a href="#">TPS7A2028PYCJR</a>   | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E                   |
| TPS7A2028PYCJR.A                 | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E                   |
| <a href="#">TPS7A2028PYCKR</a>   | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E                   |
| TPS7A2028PYCKR.A                 | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E                   |
| <a href="#">TPS7A2029PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JI                  |
| TPS7A2029PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JI                  |
| <a href="#">TPS7A2030DQNR</a>    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QN                  |
| TPS7A2030DQNR.A                  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QN                  |
| <a href="#">TPS7A2030PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2AXF                |
| TPS7A2030PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AXF                |
| TPS7A2030PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AXF                |
| TPS7A2030PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AXF                |
| <a href="#">TPS7A2030PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JJ                  |
| TPS7A2030PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JJ                  |
| TPS7A2030PDQNRG4                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JJ                  |
| TPS7A2030PDQNRG4.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JJ                  |
| <a href="#">TPS7A2030YCKR</a>    | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | X                   |
| TPS7A2030YCKR.A                  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | X                   |
| <a href="#">TPS7A2031PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GDF                |

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS7A2031PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GDF                |
| TPS7A2031PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GDF                |
| TPS7A2031PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GDF                |
| <a href="#">TPS7A2032PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GEF                |
| TPS7A2032PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GEF                |
| <a href="#">TPS7A2033DQNR</a>    | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QO                  |
| TPS7A2033DQNR.A                  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | QO                  |
| <a href="#">TPS7A2033PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2AZF                |
| TPS7A2033PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2AZF                |
| <a href="#">TPS7A2033PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | JA                  |
| TPS7A2033PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JA                  |
| <a href="#">TPS7A2033PDQNRM3</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JA                  |
| TPS7A2033PDQNRM3.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JA                  |
| <a href="#">TPS7A2033PYCJR</a>   | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | O                   |
| TPS7A2033PYCJR.A                 | Active        | Production           | DSBGA (YCJ)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | O                   |
| <a href="#">TPS7A2033YCKR</a>    | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | V                   |
| TPS7A2033YCKR.A                  | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | V                   |
| <a href="#">TPS7A2036PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GIF                |
| TPS7A2036PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GIF                |
| <a href="#">TPS7A2036PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KP                  |
| TPS7A2036PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KP                  |
| <a href="#">TPS7A2040PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KQ                  |
| TPS7A2040PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KQ                  |
| TPS7A2040PDQNRG4                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KQ                  |
| TPS7A2040PDQNRG4.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KQ                  |
| <a href="#">TPS7A2042PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GFF                |
| TPS7A2042PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GFF                |
| TPS7A2042PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GFF                |
| TPS7A2042PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GFF                |
| <a href="#">TPS7A2042PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KV                  |
| TPS7A2042PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KV                  |

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS7A2045PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GGF                |
| TPS7A2045PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GGF                |
| <a href="#">TPS7A2045PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JB                  |
| TPS7A2045PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | JB                  |
| <a href="#">TPS7A2050PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2B1F                |
| TPS7A2050PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 2B1F                |
| TPS7A2050PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2B1F                |
| TPS7A2050PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2B1F                |
| <a href="#">TPS7A2050PDQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| TPS7A2050PDQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| TPS7A2050PDQNRG4                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| TPS7A2050PDQNRG4.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| <a href="#">TPS7A2050PDQNRM3</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| TPS7A2050PDQNRM3.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | KR                  |
| <a href="#">TPS7A2050PYCKR</a>   | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | H                   |
| TPS7A2050PYCKR.A                 | Active        | Production           | DSBGA (YCK)   4  | 12000   LARGE T&R     | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | H                   |
| <a href="#">TPS7A2055PDBVR</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 2GHF                |
| TPS7A2055PDBVR.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GHF                |
| TPS7A2055PDBVRG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GHF                |
| TPS7A2055PDBVRG4.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2GHF                |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ   | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|-------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS7A2008DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2009PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2009PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20105PDQNR  | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20115PDQNR  | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2011PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2011PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2012DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2012PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2012PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2012PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2012PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2012PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2012PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A20135PDQNR  | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2013DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |

| Device             | Package Type | Package Drawing | Pins | SPQ   | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------------|--------------|-----------------|------|-------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS7A2015PDBVR     | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2015PDQNR     | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2016YCKR      | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A201825PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A201825PDQNR   | X2SON        | DQN             | 4    | 3000  | 178.0              | 8.4                | 1.13    | 1.13    | 0.53    | 4.0     | 8.0    | Q2            |
| TPS7A201825PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20185PDBVR    | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A20185PDBVR    | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A20185PDBVRG4  | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A20185PDQNR    | X2SON        | DQN             | 4    | 3000  | 178.0              | 8.4                | 1.13    | 1.13    | 0.53    | 4.0     | 8.0    | Q2            |
| TPS7A20185PDQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20185PDQNRM3  | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20185PYCKR    | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2018DQNR      | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2018PDBVR     | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2018PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2018PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2018PDQNR     | X2SON        | DQN             | 4    | 3000  | 178.0              | 8.4                | 1.13    | 1.13    | 0.53    | 4.0     | 8.0    | Q2            |
| TPS7A2018PDQNR     | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2018PDQNRM3   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2018PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2018PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2018PYCKRM3   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2018PYCKRM3   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2018YCKR      | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2020PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2020PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A20225PDQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A202275PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A202275PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2022PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2022PYCKR     | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2025DQNR      | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2025PDBVR     | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2025PDBVR     | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2025PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2025PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2025PDQNR     | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |

| Device           | Package Type | Package Drawing | Pins | SPQ   | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|-------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS7A2025PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2025PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2027PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2027PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2027PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A20285PDBVR  | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A20285PDQNR  | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A20285PYCKR  | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2028DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2028PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2028PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2028PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2028PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2028PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2028PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2028PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2028PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2029PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2030DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2030PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2030PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2030PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2030PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2030PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2030YCKR    | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2031PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2031PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2032PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2033DQNR    | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2033PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2033PDQNR   | X2SON        | DQN             | 4    | 3000  | 178.0              | 8.4                | 1.13    | 1.13    | 0.53    | 4.0     | 8.0    | Q2            |
| TPS7A2033PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2033PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2033PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2033PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2033YCKR    | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2036PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2036PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2040PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2040PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2042PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

| Device           | Package Type | Package Drawing | Pins | SPQ   | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|-------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS7A2042PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2042PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2045PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2045PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2045PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2050PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2050PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2050PDQNR   | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2050PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2050PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TPS7A2050PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2050PYCKR   | DSBGA        | YCK             | 4    | 12000 | 180.0              | 8.4                | 0.71    | 0.71    | 0.42    | 2.0     | 8.0    | Q1            |
| TPS7A2055PDBVR   | SOT-23       | DBV             | 5    | 3000  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2055PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS7A2055PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ   | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|-------|-------------|------------|-------------|
| TPS7A2008DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2009PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2009PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20105PDQNR  | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20115PDQNR  | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2011PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2011PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2012DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2012PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2012PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2012PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2012PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2012PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2012PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 210.0       | 185.0      | 35.0        |
| TPS7A20135PDQNR  | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2013DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2015PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2015PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |

| Device             | Package Type | Package Drawing | Pins | SPQ   | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|-------|-------------|------------|-------------|
| TPS7A2016YCKR      | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A201825PDQNR   | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A201825PDQNR   | X2SON        | DQN             | 4    | 3000  | 205.0       | 200.0      | 33.0        |
| TPS7A201825PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20185PDBVR    | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20185PDBVR    | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20185PDBVRG4  | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20185PDQNR    | X2SON        | DQN             | 4    | 3000  | 205.0       | 200.0      | 33.0        |
| TPS7A20185PDQNR    | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A20185PDQNRM3  | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20185PYCKR    | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2018DQNR      | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2018PDBVR     | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2018PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2018PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2018PDQNR     | X2SON        | DQN             | 4    | 3000  | 205.0       | 200.0      | 33.0        |
| TPS7A2018PDQNR     | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A2018PDQNRM3   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2018PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2018PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2018PYCKRM3   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2018PYCKRM3   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2018YCKR      | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2020PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2020PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A20225PDQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A202275PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A202275PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2022PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2022PYCKR     | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2024PDBVR     | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025DQNR      | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PDBVR     | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PDBVR     | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PDBVRG4   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PDQNR     | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2025PYCJR     | DSBGA        | YCJ             | 4    | 12000 | 210.0       | 185.0      | 35.0        |
| TPS7A2025PYCJR     | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2027PDQNR     | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2027PYCJR     | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |

| Device           | Package Type | Package Drawing | Pins | SPQ   | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|-------|-------------|------------|-------------|
| TPS7A2027PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A20285PDBVR  | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A20285PDQNR  | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A20285PYCKR  | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2028DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2028PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2028PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2028PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2028PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2028PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2028PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2028PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2028PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2029PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2030PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2030YCKR    | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2031PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2031PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2032PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2033DQNR    | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2033PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2033PDQNR   | X2SON        | DQN             | 4    | 3000  | 205.0       | 200.0      | 33.0        |
| TPS7A2033PDQNR   | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A2033PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2033PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2033PYCJR   | DSBGA        | YCJ             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2033YCKR    | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2036PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |
| TPS7A2036PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2040PDQNR   | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A2040PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 184.0       | 184.0      | 19.0        |
| TPS7A2042PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2042PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2042PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2045PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2045PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2045PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2050PDBVR   | SOT-23       | DBV             | 5    | 3000  | 208.0       | 191.0      | 35.0        |

| Device           | Package Type | Package Drawing | Pins | SPQ   | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|-------|-------------|------------|-------------|
| TPS7A2050PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2050PDQNR   | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2050PDQNRG4 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2050PDQNRM3 | X2SON        | DQN             | 4    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2050PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2050PYCKR   | DSBGA        | YCK             | 4    | 12000 | 182.0       | 182.0      | 20.0        |
| TPS7A2055PDBVR   | SOT-23       | DBV             | 5    | 3000  | 180.0       | 180.0      | 18.0        |
| TPS7A2055PDBVR   | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |
| TPS7A2055PDBVRG4 | SOT-23       | DBV             | 5    | 3000  | 210.0       | 185.0      | 35.0        |

**DQN 4**

## GENERIC PACKAGE VIEW


**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.


4210367/F




4215302/E 12/2016

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.
4. Features may not exist. Recommend use of pin 1 marking on top of package for orientation purposes.
5. Shape of exposed side leads may differ.
6. Number and location of exposed tie bars may vary.



LAND PATTERN EXAMPLE  
SCALE: 40X




SOLDER MASK DETAIL

4215302/E 12/2016

NOTES: (continued)

7. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).
8. If any vias are implemented, it is recommended that vias under paste be filled, plugged or tented.



SOLDER PASTE EXAMPLE  
 BASED ON 0.075 - 0.1mm THICK STENCIL

EXPOSED PAD  
 88% PRINTED SOLDER COVERAGE BY AREA  
 SCALE: 60X

4215302/E 12/2016

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



## SOT-23 - 1.45 mm max height

## SMALL OUTLINE TRANSISTOR




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.

# EXAMPLE BOARD LAYOUT


DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## 重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](https://www.ti.com) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月