

# Ten Output High Performance Clock Synchronizer, Jitter Cleaner, and Clock Distributor

Check for Samples: [CDCE72010](#)

## FEATURES

- High Performance LVPECL, LVDS, LVCMOS PLL Clock Synchronizer
- Two Reference Clock Inputs (Primary and Secondary Clock) for Redundancy Support with Manual or Automatic Selection
- Accepts Two Differential Input (LVPECL or LVDS) References up to 500MHz (or Two LVCMOS Inputs up to 250MHz) as PLL Reference
- VCXO\_IN Clock is Synchronized to One of Two Reference Clocks
- VCXO\_IN Frequencies up to 1.5GHz (LVPECL) 800MHz for LVDS and 250MHz for LVCMOS Level Signaling
- Outputs Can be a Combination of LVPECL, LVDS, and LVCMOS (Up to 10 Differential LVPECL or LVDS Outputs or up to 20 LVCMOS Outputs), Output 9 can be Converted to an Auxiliary Input as a 2nd VC(X)O.
- Output Divider is Selectable to Divide by 1, 2, 3, 4, 5, 6, 8, 10, 12, 16, 18, 20, 24, 28, 30, 32, 36, 40, 42, 48, 50, 56, 60, 64, 70, or 80 On Each Output Individually up to Eight Dividers. (Except for Output 0 and 9, Output 0 Follows Output 1 Divider and Output 9 Follows Output 8 Divider)
- SPI Controllable Device Setting
- Individual Output Enable Control via SPI Interface
- Integrated On-Chip Non-Volatile Memory (EEPROM) to Store Settings without the Need to Apply High Voltage to the Device
- Optional Configuration Pins to Select Between Two Default Settings Stored in EEPROM
- Efficient Jitter Cleaning from Low PLL Loop Bandwidth
- Very Low Phase Noise PLL Core
- Programmable Phase Offset (Input Reference to Outputs)
- Wide Charge-Pump Current Range From 200 $\mu$ A to 3mA
- Presets Charge-Pump to  $V_{CC\_CP}/2$  for Fast Center-Frequency Setting of VC(X)O, Controlled Via the SPI Bus
- SERDES Startup Mode (Depending on VCXO Range)
- Auxiliary Input: Output 9 can Serve as 2nd VCXO Input to Drive All Outputs or to Serve as PLL Feedback Signal
- $\overline{RESET}$  or  $\overline{HOLD}$  Input Pin to Serve as Reset or Hold Functions
- REFERENCE SELECT for Manual Select Between Primary and Secondary Reference Clocks
- POWER DOWN ( $\overline{PD}$ ) to Put Device in Standby Mode
- Analog and Digital PLL Lock Indicator
- Internally Generated VBB Bias Voltages for Single-Ended Input Signals
- Frequency Hold-Over Mode Activated by  $\overline{HOLD}$  Pin or SPI Bus to Improve Fail-Safe Operation
- Input to All Outputs Skew Control
- Individual Skew Control for Each Output with Each Output Divider
- Packaged in a QFN-64 Package
- ESD Protection Exceeds 2kV HBM
- Industrial Temperature Range of  $-40^{\circ}\text{C}$  to  $85^{\circ}$

## APPLICATIONS

- Low Jitter Clock Driver for High-End Telecom and Wireless Applications
- High Precision Test Equipment



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## DESCRIPTION

The CDCE72010 is a high-performance, low phase noise, and low skew clock synchronizer that synchronizes a VCXO (Voltage Controlled Crystal Oscillator) or VCO (Voltage Controlled Oscillator) frequency to one of two reference clocks. The clock path is fully programmable providing the user with a high degree of flexibility. The following relationship applies to the dividers:


$$\text{Frequency (VCXO\_IN or AUX\_IN)} / \text{Frequency (PRI\_REF or SEC\_REF)} = (P*N)/(R*M)$$

The VC(X)O\_IN clock operates up to 1.5GHz through the selection of external VC(X)O and loop filter components. The PLL loop bandwidth and damping factor can be adjusted to meet different system requirements.


The CDCE72010 can lock to one of two reference clock inputs (PRI\_REF and SEC\_REF) and supports frequency hold-over mode for fail-safe and system redundancy. The outputs of the CDCE72010 are user definable and can be any combination of up to 10 LVPECL/LVDS outputs or up to 20 LVCMOS outputs. The built-in synchronization latches ensure that all outputs are synchronized for very low output skew.

All device settings, including output signaling, divider value selection, input selection, and many more, are programmable with the SPI (4-wire Serial Peripheral Interface). The SPI allows individual control of the device settings.

The device operates in a 3.3V environment and is characterized for operation from  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .





**Figure 1. High Level Block Diagram of the CDCE72010**



## PACKAGE

The CDCE72010 is available in a 64-pin lead-free “green” plastic quad flatpack package with enhanced bottom thermal pad for heat dissipation. The Texas Instruments package designator is RGC (S-PQFP-N64).



## PIN FUNCTIONS

| PIN                |                                                     | I/O          | DESCRIPTION <sup>(1)</sup>                                                                                                                                                                        |
|--------------------|-----------------------------------------------------|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME               | NO.                                                 |              |                                                                                                                                                                                                   |
| VCC                | 5, 8, 11, 14, 19, 22, 25, 28, 31, 34, 37, 40 and 43 | Power        | 3.3V supply for the output buffers. <sup>(2)</sup>                                                                                                                                                |
| VCC_PLL            | 4, 63                                               | A.<br>Power  | 3.3V PLL supply voltage for the PLL circuitry.                                                                                                                                                    |
| VCC_IN             | 57, 60                                              | A.<br>Power  | 3.3V reference input buffers and circuitry supply voltage.                                                                                                                                        |
| VCC_VCXO           | 51, 54                                              | A.<br>Power  | 3.3V VCXO input buffer and circuitry supply voltage.                                                                                                                                              |
| GND                | 32                                                  | Ground       | Ground connected to thermal pad internally.                                                                                                                                                       |
| GND                | PAD                                                 | Ground       | Ground on thermal pad. See layout recommendations.                                                                                                                                                |
| VCCA               | 48, 49                                              | A.<br>Power  | 3.3V for internal analog circuitry power supply                                                                                                                                                   |
| GND_CP             | 2                                                   | A.<br>Ground | Analog ground for charge pump                                                                                                                                                                     |
| VCC_CP             | 64                                                  | A.<br>Power  | Charge pump power supply pin used to have the same supply as the external VCO/VCXO. It can be set from 2.3V to 3.6V.                                                                              |
| SPI_MISO           | 15                                                  | O            | 3-State LVC MOS output is enabled when SPI_LE is asserted low. It is the serial data output to the SPI bus interface.                                                                             |
| SPI_LE<br>or CD1   | 45                                                  | I            | LVC MOS input, control latch enable for the Serial Programmable Interface (SPI), with hysteresis in SPI mode.<br><i>In configuration default mode this pin becomes CD1.</i>                       |
| SPI_CLK<br>or CD2  | 46                                                  | I            | LVC MOS input, serial control clock input for the SPI bus interface, with hysteresis. <i>In configuration default mode this pin becomes CD2.</i>                                                  |
| SPI_MOSI<br>or CD3 | 44                                                  | I            | LVC MOS input, master out slave in as a serial control data input to CDCE72010 for the SPI bus interface. <i>In configuration default mode this pin becomes CD3 and it should be tied to GND.</i> |

(1) It is recommended to use supply filter to each VCC supply domain independently.

(2) Pin 5 and 8, pin 28 and 31, pin 40 and 43, pin 51 and 54, pin 4 and 63 and pin 60 and 57 are internally connected.

**PIN FUNCTIONS (continued)**

| PIN                                                                                             |                                                                                     | I/O | DESCRIPTION <sup>(1)</sup>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME                                                                                            | NO.                                                                                 |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| MODE_SEL                                                                                        | 16                                                                                  | I   | <b>SPI MODE = H</b> ; when driven high or left unconnected, it defaults to SPI bus interface mode.<br><b>CD (Configuration Default) MODE = L</b> ; If tied low the device goes into configuration default mode which is configured by CD1, CD2, CD3, and AUX_SEL. In configuration default mode the device loads various configuration defaults from the EEPROM into memory at start-up.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| AUX_SEL                                                                                         | 18                                                                                  | I   | <i>This pin is used in CD mode only. If set to "1" or left unconnected, it disables output 9 and enables the AUXILIARY input to drive all outputs from output0 to output8 depending on the EEPROM configuration. If driven low in CD mode, it enables output 9 and makes all outputs driven by the VCXO Input depending on the internal EEPROM configuration.</i>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| REF_SEL                                                                                         | 47                                                                                  | I   | If Auto Reference Select mode is OFF, this pin acts as an External Input Reference Select Pin; The REF_SEL signal selects one of two input clocks:<br>REF_SEL [1]: PRI_REF is selected;<br>REF_SEL [0]: SEC_REF is selected;<br>The input has an internal 150-kΩ pull-up resistor and if left unconnected it will default to logic level "1".<br>If Auto Reference Select mode in ON, this pin not used.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| $\overline{\text{PD}}$                                                                          | 17                                                                                  | I   | This pin is active low and can be activated externally or by the corresponding bit in the SPI register (in case of logic high, the SPI setting is valid).<br>This pin switches the device into powerdown mode<br>The input has an internal 150-kΩ pull-up resistor and if left unconnected it will default to logic level "1".                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| $\overline{\text{RESET}}$ or $\overline{\text{HOLD}}$                                           | 33                                                                                  | I   | This LVCMOS input can be programmed (SPI) to act as $\overline{\text{HOLD}}$ or $\overline{\text{RESET}}$ . $\overline{\text{RESET}}$ is the default function. This pin is active low and can be activated external or via the corresponding bit in the SPI register.<br>In the case of $\overline{\text{RESET}}$ , the CP (Charge Pump) is switched to 3-state and all counters are reset to zero. The LVPECL outputs are static low (N) and high (P) respectively, and the LVCMOS outputs are all low or high if inverted. In the case of $\overline{\text{HOLD}}$ , the CP (Charge Pump) is switched into 3-state mode only. After $\overline{\text{HOLD}}$ is released and with the next valid reference clock cycle, the charge pump is switched back into normal operation (CP stays in 3-state as long as no reference clock is valid). During $\overline{\text{HOLD}}$ , all outputs are at normal operation. This mode allows external control of "frequency hold-over" mode. The input has an internal 150-kΩ pull-up resistor. |
| VCXO_IN+                                                                                        | 53                                                                                  | I   | VCXO input (+) for LVPECL+, LVDS+, and LVCMOS level inputs.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| VCXO_IN–                                                                                        | 52                                                                                  | I   | Complementary VCXO input for LVPECL–, LVDS– inputs. In the case of a LVCMOS level input on VCXO IN+, ground this pin through 1k resistor.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| PRI_REF+                                                                                        | 59                                                                                  | I   | Universal input buffer (LVPECL, LVDS, LVCMOS) positive input for the Primary Reference Clock.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| PRI_REF–                                                                                        | 58                                                                                  | I   | Universal input buffer (LVPECL, LVDS) negative input for the Primary Reference Clock. In the case of LVCMOS signaling, ground this pin through 1k resistor.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| SEC_REF+                                                                                        | 62                                                                                  | I   | Universal input buffer (LVPECL, LVDS, LVCMOS) positive input for the Secondary Reference Clock.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| SEC_REF–                                                                                        | 61                                                                                  | I   | Universal input buffer (LVPECL, LVDS,) negative input for the Secondary Reference Clock. In the case of LVCMOS signaling, ground this pin through 1k resistor.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| TESTOUTA                                                                                        | 1                                                                                   | A   | Analog Test Point for TI internal testing. Connect a 1kΩ pull-down resistor or leave unconnected.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| STATUS                                                                                          | 55                                                                                  | O   | LVCMOS output for TI internal testing. Leave unconnected unless it is configured as the IREF_CP pin. In this case it should be connected to a 12-kΩ resistor to GND.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| CP_OUT                                                                                          | 3                                                                                   | AO  | Charge pump output                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| VBB                                                                                             | 56                                                                                  | AO  | Internal voltage bias analog output                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| PLL_LOCK                                                                                        | 50                                                                                  | AO  | LVCMOS output for PLL_LOCK information. This pin is set high if the PLL is in lock. This output can be programmed to be a digital lock detect or analog lock detect (see description of Analog Lock).                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| U0P:U0N<br>U1P:U1N<br>U2P:U2N<br>U3P:U3N<br>U4P:U4N<br>U5P:U5N<br>U6P:U6N<br>U7P:U7N<br>U8P:U8N | 7, 6<br>10, 9<br>13, 12<br>21, 20<br>24, 23<br>27, 26<br>30, 29<br>36, 35<br>39, 38 | O   | The outputs of the CDCE72010 are user definable and can be any combination of up to 9 LVPECL outputs, 9 LVDS outputs, or up to 18 LVCMOS outputs. The outputs are selectable via the SPI interface. The power-up setting is EEPROM configurable.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |

**PIN FUNCTIONS (continued)**

| PIN           |     | I/O | DESCRIPTION <sup>(1)</sup>                                                                                                                                                                                                                    |
|---------------|-----|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME          | NO. |     |                                                                                                                                                                                                                                               |
| U9P or AUXINP | 42  | I/O | Positive universal output buffer 9 can be 3-stated and used as a positive universal auxiliary input buffer (It requires external termination). The auxiliary input signal can be routed to drive the outputs or the feedback loop to the PLL. |
| U9N or AUXINN | 41  | I/O | Negative universal output buffer 9 can be 3-stated and used as a negative universal auxiliary input buffer (It requires external termination). The auxiliary input signal can be routed to drive the outputs or the feedback loop to the PLL. |

**PACKAGE THERMAL RESISTANCE FOR QFN (RGZ) PACKAGE<sup>(1) (2)</sup>**

| AIRFLOW (LFM) |                                         | $\theta_{JP}$ (°C/W) <sup>(3)</sup> | $\theta_{JA}$ (°C/W) |
|---------------|-----------------------------------------|-------------------------------------|----------------------|
| 0             | JEDEC compliant board (6×6 VIAs on PAD) | 1.5                                 | 28                   |
| 100           | JEDEC compliant board (6×6 VIAs on PAD) | 1.5                                 | 17.6                 |
| 0             | Recommended layout (10×10 VIAs on PAD)  | 1.5                                 | 22.8                 |
| 100           | Recommended layout (10×10 VIAs on PAD)  | 1.5                                 | 13.8                 |

(1) The package thermal impedance is calculated in accordance with JESD 51 and JEDEC2S2P (high-k board).

(2) Connected to GND with 9 thermal vias (0.3 mm diameter).

(3)  $\theta_{JP}$  (Junction – Pad) is used for the QFN package, because the main heat flow is from the junction to the GND-pad of the QFN.

**ABSOLUTE MAXIMUM RATINGS**

over operating free-air temperature range (unless otherwise noted)

|                                                               |                                          |                                                      | MIN  | MAX                   | UNIT |
|---------------------------------------------------------------|------------------------------------------|------------------------------------------------------|------|-----------------------|------|
| V <sub>CC</sub> ,<br>AV <sub>CC</sub> ,<br>V <sub>CC_CP</sub> | Supply voltage range <sup>(1)</sup>      |                                                      | −0.5 | 4.6                   | V    |
| V <sub>I</sub>                                                | Input voltage range <sup>(2)</sup>       |                                                      | −0.5 | V <sub>CC</sub> + 0.5 | V    |
| V <sub>O</sub>                                                | Output voltage range <sup>(2)</sup>      |                                                      | −0.5 | V <sub>CC</sub> + 0.5 | V    |
|                                                               | Input current                            | V <sub>I</sub> < 0, V <sub>I</sub> > V <sub>CC</sub> |      | ±20                   | mA   |
|                                                               | Output current for LVPECL/LVCMOS Outputs | 0 < V <sub>O</sub> < V <sub>CC</sub>                 |      | ±50                   | mA   |
| T <sub>J</sub>                                                | Junction temperature                     |                                                      |      | 125                   | °C   |
| T <sub>std</sub>                                              | Storage temperature range                |                                                      | −65  | 150                   | °C   |

(1) All supply voltages have to be supplied simultaneously.

(2) The input and output negative voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

## RECOMMENDED OPERATING CONDITIONS

for the CDCE72010 device for under the specified industrial temperature range of –40°C to 85°C

|                                                                                                                                                   |                                                            |                                                                                                                                                                                                                                                                                                                                                             | MIN                 | NOM | MAX                   | UNIT |
|---------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|-----|-----------------------|------|
| <b>Power Supply</b>                                                                                                                               |                                                            |                                                                                                                                                                                                                                                                                                                                                             |                     |     |                       |      |
| V <sub>CC</sub>                                                                                                                                   | Supply voltage                                             |                                                                                                                                                                                                                                                                                                                                                             | 3                   | 3.3 | 3.6                   | V    |
| V <sub>CC_PLL</sub> ,<br>V <sub>CC_IN</sub> ,<br>V <sub>CC_VCXO</sub> ,<br>V <sub>CCA</sub>                                                       | Analog supply voltage                                      |                                                                                                                                                                                                                                                                                                                                                             | 3                   | 3.3 | 3.6                   |      |
| V <sub>CC_CP</sub>                                                                                                                                |                                                            |                                                                                                                                                                                                                                                                                                                                                             | 2.3                 |     | V <sub>CC</sub>       | V    |
| P <sub>LVPECL</sub>                                                                                                                               | REF at 30.72MHz VCXO at 491.52MHz Outputs are LVPECL-HS    | Divider 1 set to divide by 8 (DCR 30%) Divider 2 set to divide by 4 (DCR 30%) Divider 3 set to divide by 2 (DCR 30%) Divider 4 set to divide by 2 (DCR 30%) Divider 5 set to divide by 1 (DCR 30%) Divider 6 set to divide by 1 (DCR 0%) Divider 7 set to divide by 1 (DCR 0%) Divider 8 set to divide by 1 (DCR 0%) DCR: Divider Current Reduction Setting |                     | 2.9 |                       | W    |
| P <sub>LVDS</sub>                                                                                                                                 | REF at 30.72MHz VCXO at 491.52MHz Outputs are LVDS-HS      |                                                                                                                                                                                                                                                                                                                                                             |                     | 2.0 |                       | W    |
| P <sub>LVC MOS</sub>                                                                                                                              | REF at 30.72MHz VCXO at 122.88MHz Outputs are LVC MOS      |                                                                                                                                                                                                                                                                                                                                                             |                     | 2.2 |                       | W    |
| P <sub>OFF</sub>                                                                                                                                  | REF at 30.72MHz VCXO at 491.52MHz                          | Dividers are disabled. Outputs are disabled.                                                                                                                                                                                                                                                                                                                |                     | 775 |                       | mW   |
| P <sub>PD</sub>                                                                                                                                   |                                                            | Device is powered down                                                                                                                                                                                                                                                                                                                                      |                     | 30  |                       | mW   |
| Typical Operating Conditions at V <sub>CC</sub> = 3.3V and 25°C unless otherwise specified.                                                       |                                                            |                                                                                                                                                                                                                                                                                                                                                             |                     |     |                       |      |
| <b>Differential Input Mode (PRI_REF, SEC_REF, VCXO_IN and AUX_IN)</b>                                                                             |                                                            |                                                                                                                                                                                                                                                                                                                                                             |                     |     |                       |      |
| V <sub>IN</sub>                                                                                                                                   | Differential input amplitude                               | (V <sub>INP</sub> – V <sub>INN</sub> )                                                                                                                                                                                                                                                                                                                      | 0.1                 |     | 1.3                   | V    |
| V <sub>ICM</sub>                                                                                                                                  | Common-mode input voltage                                  |                                                                                                                                                                                                                                                                                                                                                             | 1.0                 |     | V <sub>CC</sub> – 0.3 | V    |
| I <sub>IH</sub>                                                                                                                                   | Differential input current high ( No internal termination) | V <sub>I</sub> = V <sub>CC</sub> , V <sub>CC</sub> = 3.6 V                                                                                                                                                                                                                                                                                                  |                     |     | 20                    | μA   |
| I <sub>IL</sub>                                                                                                                                   | Differential input current low( No internal termination)   | V <sub>I</sub> = 0 V, V <sub>CC</sub> = 3.6 V                                                                                                                                                                                                                                                                                                               | –20                 |     | 20                    | μA   |
|                                                                                                                                                   | Input capacitance on PRI_REF, SEC_REF and VCXO_REF         |                                                                                                                                                                                                                                                                                                                                                             |                     | 3   |                       | pF   |
|                                                                                                                                                   | Input capacitance on AUX_IN                                |                                                                                                                                                                                                                                                                                                                                                             |                     | 7   |                       | pF   |
| <b>LVC MOS Input Mode (SPI_CLK, SPI_MOSI, SPI_LE, <math>\overline{\text{PD}}</math>, <math>\overline{\text{RESET}}</math>, REF_SEL, MODE_SEL)</b> |                                                            |                                                                                                                                                                                                                                                                                                                                                             |                     |     |                       |      |
| V <sub>IL</sub>                                                                                                                                   | Low-level input voltage LVC MOS                            |                                                                                                                                                                                                                                                                                                                                                             | 0                   |     | 0.3 V <sub>CC</sub>   | V    |
| V <sub>IH</sub>                                                                                                                                   | High-level input voltage LVC MOS                           |                                                                                                                                                                                                                                                                                                                                                             | 0.7 V <sub>CC</sub> |     | V <sub>CC</sub>       | V    |
| V <sub>IK</sub>                                                                                                                                   | LVC MOS input clamp voltage                                | V <sub>CC</sub> = 3 V, I <sub>I</sub> = –18 mA                                                                                                                                                                                                                                                                                                              |                     |     | –1.2                  | V    |
| I <sub>IH</sub>                                                                                                                                   | LVC MOS input current                                      | V <sub>I</sub> = V <sub>CC</sub> , V <sub>CC</sub> = 3.6 V                                                                                                                                                                                                                                                                                                  |                     |     | 20                    | μA   |
| I <sub>IL</sub>                                                                                                                                   | LVC MOS input                                              | V <sub>I</sub> = 0 V, V <sub>CC</sub> = 3.6 V                                                                                                                                                                                                                                                                                                               | –10                 |     | –40                   | μA   |
| C <sub>I</sub>                                                                                                                                    | Input capacitance (LVC MOS signals)                        | V <sub>I</sub> = 0 V or V <sub>CC</sub>                                                                                                                                                                                                                                                                                                                     |                     | 3   |                       | pF   |

## TIMING REQUIREMENTS

over recommended ranges of supply voltage, load, and operating free-air temperature<sup>(1)</sup> <sup>(2)</sup>

| PARAMETER                                                                                               |                                                                                                                                   | MIN | TYP | MAX  | UNIT |
|---------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|-----|-----|------|------|
| <b>PRI_REF/SEC_REF</b>                                                                                  |                                                                                                                                   |     |     |      |      |
| $f_{REF}$ - Single                                                                                      | For single-ended inputs (LVCMOS) on PRI_REF and SEC_REF                                                                           |     |     | 250  | MHz  |
| $f_{REF}$ - Diff                                                                                        | For differential inputs (LVDS and LVPECL) on PRI_REF and SEC_REF (R divider set to DIV2)                                          |     |     | 500  | MHz  |
| Duty Cycle                                                                                              | Duty cycle of PRI_REF or SEC_REF                                                                                                  | 40% |     | 60%  |      |
| $t_{slew}$                                                                                              | Input signal slew rate                                                                                                            | 1   |     |      | V/ns |
| <b>VCXO_IN, AUX_IN</b>                                                                                  |                                                                                                                                   |     |     |      |      |
| $f_{REF}$ - Single                                                                                      | For single-ended inputs (LVCMOS)                                                                                                  |     |     | 250  | MHz  |
| $f_{REF}$ - Diff                                                                                        | For differential inputs (LVDS and LVPECL)                                                                                         |     |     | 1500 | MHz  |
| Duty Cycle                                                                                              | Duty cycle of PRI_REF or SEC_REF                                                                                                  | 40% |     | 60%  |      |
| $t_{slew}$                                                                                              | Input signal slew rate                                                                                                            | 1   |     |      | V/ns |
| <b><math>\overline{PD}</math>, <math>\overline{RESET}</math>, <math>\overline{Hold}</math>, REF_SEL</b> |                                                                                                                                   |     |     |      |      |
| $t_r/t_f$                                                                                               | Rise and fall time of the $\overline{PD}$ , $\overline{RESET}$ , $\overline{Hold}$ , REF_SEL signal from 20% to 80% of the signal |     |     | 4    | ns   |

- (1) From 250MHz to 500MHz is achieved by setting the divide by 2 in the R-divdier
- (2) If the feedback clock (derived from the VCXO input) is less than 2MHz, the device stays in normal operation mode but the frequency detection circuitry resets the STATUS\_VCXO signal and PLL\_LOCK signal to low. Both status signals are no longer relevant. This affects the HOLD-Over-Function as well as the PLL\_LOCK signal is no longer valid.



## AC/DC CHARACTERISTICS

over the specified industrial temperature range of –40°C to 85°C

| PARAMETER                                                                  |                                                                                   | TEST CONDITIONS                                                                  |                           | MIN                  | TYP <sup>(1)</sup> | MAX | UNIT   |
|----------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------|---------------------------|----------------------|--------------------|-----|--------|
| SPI Output (MISO) / PLL_LOCK                                               |                                                                                   |                                                                                  |                           |                      |                    |     |        |
| I <sub>OH</sub>                                                            | High-level output current                                                         | V <sub>CC</sub> = 3.3 V                                                          | V <sub>O</sub> = 1.65 V   | –30                  |                    |     | mA     |
| I <sub>OL</sub>                                                            | Low-level output current                                                          | V <sub>CC</sub> = 3.3 V                                                          | V <sub>O</sub> = 1.65 V   | 33                   |                    |     | mA     |
| V <sub>OH</sub>                                                            | High-level output voltage for LVCMOS outputs                                      | V <sub>CC</sub> = 3 V                                                            | I <sub>OH</sub> = –100 μA | V <sub>CC</sub> –0.5 |                    |     | V      |
| V <sub>OL</sub>                                                            | Low-level output voltage for LVCMOS outputs                                       | V <sub>CC</sub> = 3 V                                                            | I <sub>OL</sub> = 100 μA  |                      |                    | 0.3 | V      |
| C <sub>O</sub>                                                             | Output capacitance on MISO                                                        | V <sub>CC</sub> = 3.3 V; V <sub>O</sub> = 0 V or V <sub>CC</sub>                 |                           | 3                    |                    |     | pF     |
| I <sub>OZH</sub>                                                           | 3-state output current                                                            | V <sub>O</sub> = V <sub>CC</sub><br>V <sub>O</sub> = 0 V                         |                           | 5                    |                    |     | μA     |
| I <sub>OZL</sub>                                                           |                                                                                   |                                                                                  |                           | –5                   |                    |     | μA     |
| EEPROM                                                                     |                                                                                   |                                                                                  |                           |                      |                    |     |        |
| EEcyc                                                                      | Programming cycle of EEPROM                                                       |                                                                                  |                           | 100                  | 1000               |     | Cycles |
| EEret                                                                      | Data retention                                                                    |                                                                                  |                           | 10                   |                    |     | Years  |
| VBB                                                                        |                                                                                   |                                                                                  |                           |                      |                    |     |        |
| VBB                                                                        | VCXO termination voltage depends on the settings of the VCXO/AUX_IN input buffers | IBB = –0.2mA<br>Depending on the setting, Output impedance = 25 Ω                |                           | 0.9                  |                    | 1.9 | V      |
| Input Buffers Internal Termination Resistors (VCXO_IN,PRI_REF and SEC_REF) |                                                                                   |                                                                                  |                           |                      |                    |     |        |
|                                                                            | Termination resistance <sup>(2)</sup>                                             | Single ended                                                                     |                           | 53                   |                    |     | Ω      |
| Phase Detector                                                             |                                                                                   |                                                                                  |                           |                      |                    |     |        |
| f <sub>CPmax</sub>                                                         | Maximum charge pump frequency                                                     | Default PFD pulse width delay                                                    |                           |                      |                    | 100 | MHz    |
| Charge Pump                                                                |                                                                                   |                                                                                  |                           |                      |                    |     |        |
| ICP3St                                                                     | Charge pump 3-state current                                                       | 0.5 V < V <sub>CP</sub> < V <sub>CC_CP</sub> – 0.5 V                             |                           | 15                   |                    |     | nA     |
| ICPA                                                                       | ICP absolute accuracy                                                             | V <sub>CP</sub> = 0.5 V <sub>CC_CP</sub> ; internal reference resistor           |                           | 20%                  |                    |     |        |
| ICPA                                                                       | ICP absolute accuracy                                                             | V <sub>CP</sub> = 0.5 V <sub>CC_CP</sub> ; external reference resistor 12kΩ (1%) |                           | 5%                   |                    |     |        |
| ICPM                                                                       | Sink/source current matching                                                      | 0.5 V < V <sub>CP</sub> < V <sub>CC_CP</sub> – 0.5 V, SPI default settings       |                           | %4                   |                    |     |        |
| IVCPM                                                                      | ICP vs VCP matching                                                               | 0.5 V < V <sub>CP</sub> < V <sub>CC_CP</sub> – 0.5 V                             |                           | 6%                   |                    |     |        |
| V <sub>I_REF_CP</sub>                                                      | Voltage on STATUS PIN when configured as I_REF_CP                                 | 12-kΩ resitor to GND<br>(External current path for accurate charge pump current) |                           | 1.24                 |                    |     | V      |

(1) All typical values are at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C.

(2) Termination resistor can vary by 20%.

**AC/DC CHARACTERISTICS (CONTINUED)**over the specified industrial temperature range of  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ 

| PARAMETER                   |                                                       | TEST CONDITIONS                                                                                                          |                           | MIN                   | TYP <sup>(1)</sup> | MAX | UNIT |
|-----------------------------|-------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|---------------------------|-----------------------|--------------------|-----|------|
| LVCMOS Output               |                                                       |                                                                                                                          |                           |                       |                    |     |      |
| f <sub>clk</sub>            | Output frequency (see Figure 2 )                      | Load = 5 pF to GND                                                                                                       |                           |                       |                    | 250 | MHz  |
| V <sub>OH</sub>             | High-level output voltage for LVCMOS outputs          | V <sub>CC</sub> = min to max                                                                                             | I <sub>OH</sub> = −100 μA | V <sub>CC</sub> − 0.5 |                    |     | V    |
| V <sub>OL</sub>             | Low-level output voltage for LVCMOS outputs           | V <sub>CC</sub> = min to max                                                                                             | I <sub>OL</sub> =100 μA   |                       |                    | 0.3 | V    |
| I <sub>OH</sub>             | High-level output current                             | V <sub>CC</sub> = 3.3 V                                                                                                  | V <sub>O</sub> = 1.65 V   | −30                   |                    |     | mA   |
| I <sub>OL</sub>             | Low-level output current                              | V <sub>CC</sub> = 3.3 V,                                                                                                 | V <sub>O</sub> = 1.65 V   | 33                    |                    |     | mA   |
| t <sub>pho</sub>            | Phase offset without using available delay adjustment | VCXO at 491.52MHz, Output 1 is divide by 16 and reference at 30.72MHz, M and N delays are fixed to one value (set to 0). |                           | 13                    |                    |     | ns   |
| t <sub>pd(LH)/tpd(HL)</sub> | Propagation delay from VCXO_IN to Outputs             | Crosspoint to V <sub>CC</sub> /2, load = 5 pF                                                                            |                           | 3.3                   |                    |     | ns   |
| t <sub>sk(o)</sub>          | Skew, output-to-output LVCMOS single-ended output     | Divide by 1 for all dividers                                                                                             |                           | 75                    |                    | ps  |      |
|                             |                                                       | Divide by 16 for all dividers                                                                                            |                           | 75                    |                    |     |      |
|                             |                                                       | Divide by 1 for divider 1 and divide by 16 for all other dividers                                                        |                           | 1400                  |                    |     |      |
| C <sub>O</sub>              | Output capacitance on Y0 to Y8                        | V <sub>CC</sub> = 3.3 V; V <sub>O</sub> = 0 V or V <sub>CC</sub>                                                         |                           | 5                     |                    |     | pF   |
| C <sub>O</sub>              | Output capacitance on Y9                              | V <sub>CC</sub> = 3.3 V; V <sub>O</sub> = 0 V or V <sub>CC</sub>                                                         |                           | 5                     |                    |     | pF   |
| I <sub>OZH</sub>            | 3-state LVCMOS output current                         | V <sub>O</sub> = V <sub>CC</sub>                                                                                         |                           | 5                     |                    |     | μA   |
| I <sub>OZL</sub>            | 3-state LVCMOS output current                         | V <sub>O</sub> = 0V                                                                                                      |                           | −5                    |                    |     | μA   |
| I <sub>OPDH</sub>           | Power-down output current                             | V <sub>O</sub> = V <sub>CC</sub>                                                                                         |                           |                       |                    | 25  | μA   |
| I <sub>OPDL</sub>           | Power-down output current                             | V <sub>O</sub> = 0V                                                                                                      |                           |                       |                    | 5   | μA   |
| Duty cycle                  | LVCMOS                                                | With 50% / 50% duty cycle of the VCXO input clock                                                                        |                           | 45%                   |                    | 55% |      |
| t <sub>slew-rate</sub>      | Output rise/fall slew rate                            |                                                                                                                          |                           | 3.6                   |                    | 5.2 | V/ns |

(1) All typical values are at  $V_{\text{CC}} = 3.3\ \text{V}$ ,  $T_{\text{A}} = 25^{\circ}\text{C}$ .

## AC/DC CHARACTERISTICS (CONTINUED)

over the specified industrial temperature range of –40°C to 85°C

| PARAMETER                           |                                                                           | TEST CONDITIONS                                                                                                                                       | MIN | TYP <sup>(1)</sup> | MAX | UNIT          |
|-------------------------------------|---------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----|--------------------|-----|---------------|
| <b>LVDS Output</b>                  |                                                                           |                                                                                                                                                       |     |                    |     |               |
| $f_{clk}$                           | Output frequency                                                          |                                                                                                                                                       | 0   |                    | 800 | MHz           |
| $ V_{OD} $                          | Differential output voltage                                               | $R_L = 100\ \Omega$                                                                                                                                   | 160 |                    | 270 | mV            |
| $\Delta V_{OD}$                     | LVDS VOD magnitude change                                                 |                                                                                                                                                       |     |                    | 50  | mV            |
| $V_{OS}$                            | Offset voltage                                                            | –40°C to 85°C                                                                                                                                         |     | 1.24               |     | V             |
| $\Delta V_{OS}$                     | $V_{OS}$ magnitude change                                                 |                                                                                                                                                       |     | 40                 |     | mV            |
|                                     | Short circuit $V_{OUT+}$ to ground                                        | $V_{OUT} = 0$                                                                                                                                         |     |                    | 27  | mA            |
|                                     | Short circuit $V_{OUT-}$ to ground                                        | $V_{OUT} = 0$                                                                                                                                         |     |                    | 27  | mA            |
| $t_{pho}^{(2)}$                     | Reference to output phase offset without using available delay adjustment | VCXO at 491.52MHz, Output 1 is divide by 16 and reference at 30.72MHz, M and N delays are fixed to one value (set to 0), PFD: 240kHz, (M and N = 128) |     | 14                 |     | ns            |
| $t_{pd(LH)}/t_{pd(HL)}$             | Propagation delay time, VCXO_IN to output                                 | Crosspoint to crosspoint, load                                                                                                                        |     | 3.0                |     | ns            |
| $tsk(o)^{(3)}$                      | Skew, output to output LVDS output                                        | Divide by 1 for all dividers                                                                                                                          |     | 45                 |     | ps            |
|                                     |                                                                           | Divide by 16 for all dividers                                                                                                                         |     | 50                 |     |               |
|                                     |                                                                           | Divide by 1 for divider 1<br>Divide by 16 for all other dividers                                                                                      |     | 2800               |     |               |
| $C_O$                               | Output capacitance on Y0 to Y8                                            | $V_{CC} = 3.3\text{ V}; V_O = 0\text{ V or }V_{CC}$                                                                                                   |     | 5                  |     | pF            |
| $C_O$                               | Output capacitance on Y9                                                  | $V_{CC} = 3.3\text{ V}; V_O = 0\text{ V or }V_{CC} 5$                                                                                                 |     | 7                  |     | pF            |
| $I_{OPDH}$                          | Power-down output current                                                 | $V_O = V_{CC}$                                                                                                                                        |     |                    | 25  | $\mu\text{A}$ |
| $I_{OPDL}$                          | Power-down output current                                                 | $V_O = 0\text{V}$                                                                                                                                     |     |                    | 5   | $\mu\text{A}$ |
|                                     | Duty cycle                                                                |                                                                                                                                                       | 45  |                    | 55  | %             |
| $t_r/t_f$                           | Rise and fall time                                                        | 20% to 80% of $V_{outpp}$                                                                                                                             | 110 | 140                | 160 | ps            |
| <b>LVCMOS-TO-LVDS<sup>(4)</sup></b> |                                                                           |                                                                                                                                                       |     |                    |     |               |
| $tsk_{P\_C}$                        | Output skew between LVCMOS and LVDS outputs                               | Crosspoint to $V_{CC}/2$ . Outputs are at the same output frequency and use the same output divider configuration.                                    | 0.9 | 1.4                | 1.9 | ns            |

(1) All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

(2) This is valid only for same REF\_IN clock and Y output clock frequency. It can be adjusted by the SPI controller (reference delay M and VCXO delay N).

(3) The  $tsk(o)$  specification is only valid for equal loading of all outputs.

(4) The phase of LVCMOS is lagging in reference to the phase of LVDS.

**AC/DC CHARACTERISTICS (CONTINUED)**over the specified industrial temperature range of  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ 

| PARAMETER                                   |                                                                           | TEST CONDITIONS                                                                                                                                                          | MIN | TYP <sup>(1)</sup> | MAX | UNIT          |
|---------------------------------------------|---------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|--------------------|-----|---------------|
| <b>LVDS Hi Swing Output</b>                 |                                                                           |                                                                                                                                                                          |     |                    |     |               |
| $f_{\text{clk}}$                            | Output frequency                                                          |                                                                                                                                                                          | 0   |                    | 800 | MHz           |
| $ V_{\text{OD}} $                           | Differential output voltage                                               | $R_L = 100\ \Omega$                                                                                                                                                      | 270 |                    | 550 | mV            |
| $\Delta V_{\text{OD}}$                      | LVDS VOD magnitude change                                                 |                                                                                                                                                                          |     |                    | 50  | mV            |
| $V_{\text{OS}}$                             | Offset voltage                                                            | $-40^{\circ}\text{C}$ to $85^{\circ}\text{C}$                                                                                                                            |     | 1.24               |     | V             |
| $\Delta V_{\text{OS}}$                      | $V_{\text{OS}}$ magnitude change                                          |                                                                                                                                                                          |     | 40                 |     | mV            |
|                                             | Short Circuit $V_{\text{OUT+}}$ to ground                                 | $V_{\text{OUT}} = 0$                                                                                                                                                     |     |                    | 27  | mA            |
|                                             | Short Circuit $V_{\text{OUT-}}$ to ground                                 | $V_{\text{OUT}} = 0$                                                                                                                                                     |     |                    | 27  | mA            |
| $t_{\text{pho}}^{(2)}$                      | Reference to output phase offset without using available delay adjustment | VCXO at 491.52MHz, Output 1 is divide by 16 and reference at 30.72MHz. M and N delays are fixed to one value. (Set to 0) PFD: 240kHz, (M and N = 128)                    |     | 14                 |     | ns            |
| $t_{\text{pd(LH)}}/$<br>$t_{\text{pd(HL)}}$ | Propagation delay time, VCXO_IN to output                                 | Crosspoint to crosspoint                                                                                                                                                 |     | 3.0                |     | ns            |
| $t_{\text{sk(o)}}^{(3)}$                    | LVDS output skew                                                          | Divide by 1 for all dividers                                                                                                                                             |     | 45                 |     | ps            |
|                                             |                                                                           | Divide by 16 for all dividers                                                                                                                                            |     | 50                 |     |               |
|                                             |                                                                           | Divide by 1 for divider 1<br>Divide by 16 for all other dividers                                                                                                         |     | 2800               |     |               |
| $C_{\text{O}}$                              | Output capacitance on Y0 to Y8                                            | $V_{\text{CC}} = 3.3\text{ V}$ ; $V_{\text{O}} = 0\text{ V}$ or $V_{\text{CC}}$                                                                                          |     | 5                  |     | pF            |
| $C_{\text{O}}$                              | Output capacitance on Y9                                                  | $V_{\text{CC}} = 3.3\text{ V}$ ; $V_{\text{O}} = 0\text{ V}$ or $V_{\text{CC}}$                                                                                          |     | 7                  |     | pF            |
| IOPDH                                       | Power-down output current                                                 | $V_{\text{O}} = V_{\text{CC}}$                                                                                                                                           |     |                    | 25  | $\mu\text{A}$ |
| IOPDL                                       | Power-down output current                                                 | $V_{\text{O}} = 0\text{ V}$                                                                                                                                              |     |                    | 5   | $\mu\text{A}$ |
| Duty cycle                                  |                                                                           |                                                                                                                                                                          | 45  |                    | 55  | %             |
| $t_r/t_f$                                   | Rise and fall time                                                        | 20% to 80% of $V_{\text{outpp}}$                                                                                                                                         | 110 | 160                | 190 | ps            |
| <b>LVC MOS-TO-LVDS<sup>(4)</sup></b>        |                                                                           |                                                                                                                                                                          |     |                    |     |               |
| $t_{\text{skP\_C}}$                         | Output skew between LVC MOS and LVDS outputs                              | Crosspoint to $V_{\text{CC}}/2$ . Outputs are at the same output frequency and use the same output divider configuration with same output frequencies and divider values | 0.9 | 1.4                | 1.9 | ns            |

(1) All typical values are at  $V_{\text{CC}} = 3.3\text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

(2) This is valid only for same REF\_IN clock and Y output clock frequency. It can be adjusted by the SPI controller (reference delay M and VCXO delay N).

(3) The  $t_{\text{sk(o)}}$  specification is only valid for equal loading of all outputs.

(4) The phase of LVC MOS is lagging in reference to the phase of LVDS.

## AC/DC CHARACTERISTICS (CONTINUED)

over the specified industrial temperature range of –40°C to 85°C

| PARAMETER                |                                                                           | TEST CONDITIONS                                                                                                                                       | MIN             | TYP <sup>(1)</sup> | MAX             | UNIT |
|--------------------------|---------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------|-----------------|------|
| <b>LVPECL Output</b>     |                                                                           |                                                                                                                                                       |                 |                    |                 |      |
| $f_{clk}$                | Output frequency                                                          |                                                                                                                                                       | 0               |                    | 1500            | MHz  |
| $V_{OH}$                 | LVPECL high-level output voltage                                          | Load, see <a href="#">Figure 5</a>                                                                                                                    | $V_{CC} - 1.06$ |                    | $V_{CC} - 0.88$ | V    |
| $V_{OL}$                 | LVPECL low-level output voltage                                           | Load, see <a href="#">Figure 5</a>                                                                                                                    | $V_{CC} - 2.02$ |                    | $V_{CC} - 1.58$ | V    |
| $ V_{OD} $               | Differential output voltage                                               | Load, see <a href="#">Figure 5</a>                                                                                                                    | 610             |                    | 970             | mV   |
| $t_{pho}^{(2)}$          | Reference to output phase offset without using available delay adjustment | VCXO at 491.52MHz, Output 1 is divide by 16 and reference at 30.72MHz, M and N delays are fixed to one value (set to 0), PFD: 240kHz, (M and N = 128) |                 | 14                 |                 | ns   |
| $t_{pd(LH)}/t_{pd(HL)}$  | Propagation delay time, VCXO_IN to output                                 | Crosspoint to crosspoint, load                                                                                                                        |                 | 3.4                |                 | ns   |
| $t_{sk(o)}^{(3)}$        | LVPECL output skew                                                        | Divide by 1 for all dividers                                                                                                                          |                 | 45                 |                 | ps   |
|                          |                                                                           | Divide by 16 for all dividers                                                                                                                         |                 | 50                 |                 |      |
|                          |                                                                           | Divide by 1 for divider 1                                                                                                                             |                 | 2700               |                 |      |
|                          |                                                                           | Divide by 16 for all other dividers                                                                                                                   |                 |                    |                 |      |
| $C_O$                    | Output capacitance on Y0 to Y8                                            | $V_{CC} = 3.3\text{ V}$ ; $V_O = 0\text{ V}$ or $V_{CC}$                                                                                              |                 | 5                  |                 | pF   |
| $C_O$                    | Output capacitance on Y9                                                  | $V_{CC} = 3.3\text{ V}$ ; $V_O = 0\text{ V}$ or $V_{CC}$                                                                                              |                 | 7                  |                 | pF   |
| IOPDH                    | Power-down output current                                                 | $V_O = V_{CC}$                                                                                                                                        |                 |                    | 25              | μA   |
| IOPDL                    | Power-down output current                                                 | $V_O = 0\text{ V}$                                                                                                                                    |                 |                    | 5               | μA   |
|                          | Duty cycle                                                                |                                                                                                                                                       | 45              |                    | 55              | %    |
| $t_r/t_f$                | Rise and fall time                                                        | 20% to 80% of $V_{outpp}$                                                                                                                             | 55              | 75                 | 135             | ps   |
| <b>LVDS-TO-LVPECL</b>    |                                                                           |                                                                                                                                                       |                 |                    |                 |      |
| $tsk_{P\_C}$             | Output skew between LVDS and LVPECL outputs                               | Crosspoint to Crosspoint with same output frequencies and divider values                                                                              | 0.9             | 1.1                | 1.3             | ns   |
| <b>LVC MOS-TO-LVPECL</b> |                                                                           |                                                                                                                                                       |                 |                    |                 |      |
| $tsk_{P\_C}$             | Output skew between LVC MOS and LVPECL outputs                            | $V_{CC}/2$ to Crosspoint; With same output frequencies and divider values                                                                             | –150            | 260                | 700             | ps   |

(1) All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

(2) This is valid only for same REF\_IN clock and Y output clock frequency. It can be adjusted by the SPI controller (reference delay M and VCXO delay N).

(3) The  $tsk(o)$  specification is only valid for equal loading of all outputs. :

**AC/DC CHARACTERISTICS (CONTINUED)**

over the specified industrial temperature range of –40°C to 85°C

| PARAMETER                                   |                                                                           | TEST CONDITIONS                                                                                                                                       | MIN                    | TYP <sup>(1)</sup> | MAX                    | UNIT          |
|---------------------------------------------|---------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|--------------------|------------------------|---------------|
| <b>LVPECL Hi Swing Output</b>               |                                                                           |                                                                                                                                                       |                        |                    |                        |               |
| $f_{\text{clk}}$                            | Output frequency                                                          |                                                                                                                                                       | 0                      |                    | 1500                   | MHz           |
| $V_{\text{OH}}$                             | LVPECL high-level output voltage                                          | Load, see <a href="#">Figure 5</a>                                                                                                                    | $V_{\text{CC}} - 1.11$ |                    | $V_{\text{CC}} - 0.87$ | V             |
| $V_{\text{OL}}$                             | LVPECL low-level output voltage                                           | Load, see <a href="#">Figure 5</a>                                                                                                                    | $V_{\text{CC}} - 2.06$ |                    | $V_{\text{CC}} - 1.73$ | V             |
| $ V_{\text{OD}} $                           | Differential output voltage                                               | Load, see <a href="#">Figure 5</a>                                                                                                                    | 760                    |                    | 1160                   | mV            |
| $t_{\text{pho}}^{(2)}$                      | Reference to output phase offset without using available delay adjustment | VCXO at 491.52MHz, Output 1 is divide by 16 and reference at 30.72MHz, M and N delays are fixed to one value (set to 0), PFD: 240kHz, (M and N = 128) |                        | 14                 |                        | ns            |
| $t_{\text{pd(LH)}}/$<br>$t_{\text{pd(HL)}}$ | Propagation delay time, VCXO_IN to output                                 | Crosspoint to crosspoint, load                                                                                                                        |                        | 3.4                |                        | ns            |
| $t_{\text{sk(o)}}^{(3)}$                    | LVPECL output skew                                                        | Divide by 1 for all dividers                                                                                                                          |                        | 45                 |                        | ps            |
|                                             |                                                                           | Divide by 16 for all dividers                                                                                                                         |                        | 50                 |                        |               |
|                                             |                                                                           | Divide by 1 for divider 1<br>Divide by 16 for all other dividers                                                                                      |                        | 2700               |                        |               |
| $C_{\text{O}}$                              | Output capacitance on Y0 to Y8                                            | $V_{\text{CC}} = 3.3\text{ V}$ ; $V_{\text{O}} = 0\text{ V}$ or $V_{\text{CC}}$                                                                       |                        | 5                  |                        | pF            |
| $C_{\text{O}}$                              | Output capacitance on Y9                                                  | $V_{\text{CC}} = 3.3\text{ V}$ ; $V_{\text{O}} = 0\text{ V}$ or $V_{\text{CC}}$                                                                       |                        | 7                  |                        | pF            |
| IOPDH                                       | Power-down output current                                                 | $V_{\text{O}} = V_{\text{CC}}$                                                                                                                        |                        |                    | 25                     | $\mu\text{A}$ |
| IOPDL                                       | Power-down output current                                                 | $V_{\text{O}} = 0\text{ V}$                                                                                                                           |                        |                    | 5                      | $\mu\text{A}$ |
|                                             | Duty cycle                                                                |                                                                                                                                                       | 45%                    |                    | 55%                    |               |
| $t_r/t_f$                                   | Rise and fall time                                                        | 20% to 80% of $V_{\text{outpp}}$                                                                                                                      | 55                     | 75                 | 135                    | ps            |
| <b>LVDS-TO-LVPECL</b>                       |                                                                           |                                                                                                                                                       |                        |                    |                        |               |
| $\text{tsk}_{\text{P\_C}}$                  | Output skew between LVDS and LVPECL outputs                               | Crosspoint to Crosspoint; with same output frequencies and divider values                                                                             | 0.9                    | 1.1                | 1.3                    | ns            |
| <b>LVC MOS-TO-LVPECL</b>                    |                                                                           |                                                                                                                                                       |                        |                    |                        |               |
| $\text{tsk}_{\text{P\_C}}$                  | Output skew between LVC MOS and LVPECL outputs <sup>(4)</sup>             | $V_{\text{CC}}/2$ to Crosspoint; With same output frequencies and divider values                                                                      | –150                   | 260                | 700                    | ps            |


(1) All typical values are at  $V_{\text{CC}} = 3.3\text{ V}$ ,  $T_{\text{A}} = 25^\circ\text{C}$ .

(2) This is valid only for same REF\_IN clock and Y output clock frequency. It can be adjusted by the SPI controller (reference delay M and VCXO delay N).


(3) The  $\text{tsk(o)}$  specification is only valid for equal loading of all outputs.

(4) The phase of LVC MOS is lagging in reference to the phase of LVDS and LVPECL.


## PARAMETER MEASUREMENT INFORMATION




**Figure 2. LVC MOS Output Test Setup**



**Figure 4. LVPECL AC Test Setup**



**Figure 3. LVDS DC Test Setup**



**Figure 5. LVPECL DC Test Setup**

## TYPICAL CHARACTERISTICS

LVPECL OUTPUT SWING  
vs  
FREQUENCY




Figure 6.

Hi Swing LVPECL OUTPUT SWING  
vs  
FREQUENCY




Figure 7.

LVDS OUTPUT SWING  
vs  
FREQUENCY




Figure 8.

Hi Swing LVDS OUTPUT SWING  
vs  
FREQUENCY




Figure 9.



**TYPICAL CHARACTERISTICS (continued)**  
LVCMOS OUTPUT WING  
vs  
FREQUENCY




Figure 10.

## APPLICATION INFORMATION

### PHASE NOISE ANALYSIS

Phase noise is measured in a closed loop mode of 491.52MHz VCXO and 30.72MHz reference and a 100Hz loop. Output 1 is measured for divide by one, output 6 for divide by 4, and output 9 for divide by 16.

**Table 1. Phase Noise for LVPECL High Swing**

| Phase Noise Specifications under following configuration: VCXO = 491.52MHz, REF = 30.72MHz, Divide by = 491.52MHz, Divide by 4 = 122.88MHz, Divide by 16 = 30.72MHz, PFD Frequency = 240KHz, Charge Pump Current = 2mA, Loop BW = 100Hz, Output 1 = 491.52 MHz, Output Buffer: LVPECL-HS |                |                    |                       |                       |                        |        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------|-----------------------|-----------------------|------------------------|--------|
| PHASE NOISE AT OFFSET                                                                                                                                                                                                                                                                    | VCXO OPEN LOOP | REFERENCE 30.72MHz | LVPECL-HS DIVIDE BY 1 | LVPECL-HS DIVIDE BY 4 | LVPECL-HS DIVIDE BY 16 | UNIT   |
| 10Hz                                                                                                                                                                                                                                                                                     | -64            | -107               | -80                   | -92                   | -105                   | dBc/Hz |
| 100Hz                                                                                                                                                                                                                                                                                    | -99            | -123               | -92                   | -104                  | -116                   | dBc/Hz |
| 1kHz                                                                                                                                                                                                                                                                                     | -113           | -134               | -115                  | -127                  | -139                   | dBc/Hz |
| 10kHz                                                                                                                                                                                                                                                                                    | -135           | -153               | -135                  | -145                  | -158                   | dBc/Hz |
| 100kHz                                                                                                                                                                                                                                                                                   | -148           | -156               | -146                  | -155                  | -162                   | dBc/Hz |
| 1MHz                                                                                                                                                                                                                                                                                     | -148           | -158               | -146                  | -155                  | -162                   | dBc/Hz |
| 10MHz                                                                                                                                                                                                                                                                                    | -149           |                    | -147                  | -156                  |                        | dBc/Hz |

**Table 2. Phase Noise for LVDS High Swing**

| Phase Noise Specifications under following configuration: VCXO = 491.52MHz, REF = 30.72MHz, Divide by = 491.52MHz, Divide by 4 = 122.88MHz, Divide by 16 = 30.72MHz, PFD Frequency = 240KHz, Charge Pump Current = 2mA Loop BW = 100Hz, Output 1 = 491.52 MHz, Output Buffer: LVDS-HS |                |           |                     |                     |                      |        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-----------|---------------------|---------------------|----------------------|--------|
| PARAMETER                                                                                                                                                                                                                                                                             | VCXO OPEN LOOP | REFERENCE | LVDS-HS DIVIDE BY 1 | LVDS-HS DIVIDE BY 4 | LVDS-HS DIVIDE BY 16 | UNIT   |
| 10Hz                                                                                                                                                                                                                                                                                  | -64            | -107      | -82                 | -94                 | -104                 | dBc/Hz |
| 100Hz                                                                                                                                                                                                                                                                                 | -99            | -123      | -92                 | -105                | -117                 | dBc/Hz |
| 1kHz                                                                                                                                                                                                                                                                                  | -113           | -134      | -114                | -127                | -139                 | dBc/Hz |
| 10kHz                                                                                                                                                                                                                                                                                 | -135           | -153      | -135                | -145                | -151                 | dBc/Hz |
| 100kHz                                                                                                                                                                                                                                                                                | -148           | -156      | -145                | -152                | -153                 | dBc/Hz |
| 1MHz                                                                                                                                                                                                                                                                                  | -148           | -158      | -146                | -152                | -153                 | dBc/Hz |
| 10MHz                                                                                                                                                                                                                                                                                 | -149           |           | -146                | -152                |                      | dBc/Hz |

**Table 3. Phase Noise for LVCMOS**

| Phase Noise Specifications under following configuration: VCXO = 491.52MHz, REF = 30.72MHz, Divide by = 491.52MHz, Divide by 4 = 122.88MHz, Divide by 16 = 30.72MHz, PFD Frequency = 240KHz, Charge Pump Current = 2mA, Loop BW = 100Hz, Output 1 = 491.52 MHz, Output Buffer: LVCMOS |                |           |     |                    |                     |        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-----------|-----|--------------------|---------------------|--------|
| PARAMETER                                                                                                                                                                                                                                                                             | VCXO OPEN LOOP | REFERENCE | N/A | LVCMOS DIVIDE BY 4 | LVCMOS DIVIDE BY 16 | UNIT   |
| 10Hz                                                                                                                                                                                                                                                                                  | -64            | -107      |     | -91                | -105                | dBc/Hz |
| 100Hz                                                                                                                                                                                                                                                                                 | -99            | -123      |     | -104               | -116                | dBc/Hz |
| 1kHz                                                                                                                                                                                                                                                                                  | -113           | -134      |     | -127               | -139                | dBc/Hz |
| 10kHz                                                                                                                                                                                                                                                                                 | -135           | -153      |     | -140               | -151                | dBc/Hz |
| 100kHz                                                                                                                                                                                                                                                                                | -148           | -156      |     | -151               | -159                | dBc/Hz |
| 1MHz                                                                                                                                                                                                                                                                                  | -148           | -158      |     | -153               | -160                | dBc/Hz |
| 10MHz                                                                                                                                                                                                                                                                                 | -149           |           |     | -154               |                     | dBc/Hz |

## INTERFACE AND CONTROL BLOCK

The Interface & Control Block includes a SPI interface, four control pins, a non-volatile memory array in which the device stores default configuration data, and an array of device registers implemented in Static RAM. This RAM, also called the device registers, configures all hardware within the CDCE72010.

### Serial Peripheral Interface (SPI)

The serial interface of CDCE72010 is a simple bidirectional SPI interface for writing and reading to and from the device registers. It implements a low speed serial communications link in a master/slave topology in which the CDCE72010 is a slave. The SPI consists of four signals:

- **SPI\_CLK:** Serial Clock (Output from Master) – the CDCE72010 and the master host clock data in and out on the rising edge of SPI\_CLK. Data transitions therefore occur on the falling edge of the clock. (LVCMOS Input Buffer)
- **SPI\_MOSI:** Master Output Slave Input (LVCMOS Input Buffer) .
- **SPI\_MISO:** Master Input Slave Output
- **SPI\_LE:** Latch Enable (Output from Master). The falling edge of SPI\_LE initiates a transfer. If SPI\_LE is high, no data transfer can take place. (LVCMOS Input Buffer).

The CDCE72010 implements data fields that are 28-bits wide. In addition, it contains 12 registers, each comprising a 28 bit data field. Therefore, accessing the CDCE72010 requires that the host program append a 4-bit address field to the front of the data field as follows:




Figure 11. CDCE72010 SPI Communications Format

### CDCE72010 SPI Command Structure

The CDCE72010 supports four commands issued by the Master via the SPI:

- Write to RAM
- Read Command
- Copy RAM to EEPROM – unlock
- Copy RAM to EEPROM – lock

Table 4 provides a summary of the CDCE72010 SPI command structure. The host (master) constructs a Write to RAM command by specifying the appropriate register address in the address field and appends this value to the beginning of the data field. Therefore, a valid command stream must include 32 bits, transmitted LSB first. The host must issue a Read Command to initiate a data transfer from the CDCE72010 back to the host. This command specifies the address of the register of interest in the data field.

**Table 4. CDCE72010 SPI Command Structure<sup>(1)</sup>**


|             |                |                     | Data Field (28 Bits) |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |   |   |   |   |   |   |   |   |   | Addr Field (4 Bits)* |   |   |   |
|-------------|----------------|---------------------|----------------------|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|---|---|---|---|---|----------------------|---|---|---|
| Register    | Operation      | NVM                 | 27                   | 26 | 25 | 24 | 23 | 22 | 21 | 20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | 3                    | 2 | 1 | 0 |
| 0           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 0 | 0 | 0 |
| 1           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 0 | 0 | 1 |
| 2           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 0 | 1 | 0 |
| 3           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 0 | 1 | 1 |
| 4           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 1 | 0 | 0 |
| 5           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 1 | 0 | 1 |
| 6           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 1 | 1 | 0 |
| 7           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 0                    | 1 | 1 | 1 |
| 8           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 1                    | 0 | 0 | 0 |
| 9           | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 1                    | 0 | 0 | 1 |
| 10          | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 1                    | 0 | 1 | 0 |
| 11          | Write to RAM   | Yes                 | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 1                    | 0 | 1 | 1 |
| 12          | Status/Control | No                  | X                    | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X  | X | X | X | X | X | X | X | X | X | X | 1                    | 1 | 0 | 0 |
| Instruction | Read Command   | No                  | 0                    | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0 | 0 | 0 | 0 | 0 | 0 | 0 | A | A | A | 1                    | 1 | 1 | 0 |
| Instruction | RAM → EEPROM   | Unlock              | 0                    | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 1                    | 1 | 1 | 1 |
| Instruction | RAM → EEPROM   | Lock <sup>(2)</sup> | 0                    | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1  | 0  | 1 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 1 | 1                    | 1 | 1 | 1 |

(1) **CAUTION:** In a read Cycle the Address Field should be ignored when accessing the CDCE72010 device.

(2) After execution of this command, the EEPROM is permanently locked. After locking EEPROM, device configuration can only be changed via Write into RAM after power up; however EEPROM can no longer be changed.

### SPI Interface Master

The Interface master can be designed using a FPGA or a micro controller. The CDCE72010 acts as a slave to the SPI master. The SPI Master should be designed to issue none consecutive read or write commands. The SPI clock should start and stop with respect to the SPI\_LE signal as shown in Figure 12. SPI\_MOSI, SPI\_CLK, and SPI\_LE are generated by the SPI Master. SPI\_MISO is generated by the SPI slave the CDCE72010.

**Figure 12. CDCE72010 SPI Read/Write Command**

### SPI Consecutive Read/Write Cycles to the CDCE72010

Figure 13 illustrates how two consecutive SPI cycles are performed between a SPI Master and the CDCE72010 SPI Slave.




Figure 13. Consecutive Read/Write Cycles

### Writing to the CDCE72010

Figure 14 illustrates a Write to RAM operation. Notice that the latching of the first data bit in the data stream (Bit 0) occurs on the first rising edge of SPI\_CLK after SPI\_LE transitions from a high to a low. For the CDCE72010, data transitions occur on the falling edge of SPI\_CLK. A rising edge on SPI\_LE signals to the CDCE72010 that the transmission of the last bit in the stream (Bit 31) has occurred.




Figure 14. CDCE72010 SPI Write Operation

### Reading from the CDCE72010

Figure 15 shows how the CDCE72010 executes a Read Command. The SPI master first issues a Read Command to initiate a data transfer from the CDCE72010 back to the host (see Table 4). This command specifies the address of the register of interest (marked as AAAA in Table 1). By transitioning SPI\_LE from a low to a high, the CDCE72010 resolves the address specified in the appropriate bits of the data field. The host drives SPI\_LE low and the CDCE72010 presents the data present in the register specified in the Read Command on SPI\_MISO.

**IMPORTANT NOTE:** The read instruction does not return SPI\_MISO Bit 0 properly. This bit is stuck with zero. The host should ignore this bit when accessing the CDCE72010.




Figure 15. CDCE72010 SPI Read Operation

### Writing to EEPROM

After the CDCE72010 detects a power-up and completes a reset cycle, the device copies the contents of the on-board EEPROM into the Device Registers. (SPI\_LE signal has to be HIGH in order for the EEPROM to load correctly during the rising edge of Power\_Down signal).

The host issues one of two special commands shown in Table 4 to copy the contents of Device Registers 0 through 11 (a total of 336 bits) into EEPROM. They include:

- Copy RAM to EEPROM – Unlock, Execution of this command can happen many times.
- Copy RAM to EEPROM – Lock: Execution of this command can happen only once; after which the EEPROM is **permanently locked**.

After either command is initiated, power must remain stable and the host must not access the CDCE72010 for at least 50 ms to allow the EEPROM to complete the write cycle and to avoid the possibility of EEPROM corruption.

## SPI CONTROL INTERFACE TIMING




Figure 16. Timing Diagram for SPI Write Command




Figure 17. Timing Diagram for SPI Read Command

Table 5. SPI Bus Timing Characteristics

| PARAMETER          |                                 | MIN | TYP | MAX | UNIT |
|--------------------|---------------------------------|-----|-----|-----|------|
| $f_{\text{Clock}}$ | Clock Frequency for the SPI_CLK |     |     | 20  | MHz  |
| $t_1$              | SPI_LE to SPI_CLK setup time    | 10  |     |     | ns   |
| $t_2$              | SPI_MOSI to SPI_CLK setup time  | 10  |     |     | ns   |
| $t_3$              | SPI_MOSI to SPI_CLK hold time   | 10  |     |     | ns   |
| $t_4$              | SPI_CLK high duration           | 25  |     |     | ns   |
| $t_5$              | SPI_CLK low duration            | 25  |     |     | ns   |
| $t_6$              | SPI_CLK to SPI_LE Hold time     | 10  |     |     | ns   |
| $t_7$              | SPI_LE Pulse Width              | 20  |     |     | ns   |
| $t_8$              | SPI_CLK to MISO data valid      |     |     | 10  | ns   |
| $t_9$              | SPI_LE to SPI_MISO Data Valid   |     |     | 10  | ns   |

## CDCE72010 Default Configuration

The CDCE72010 on-chip EEPROM has been factory preset to the default settings listed in [Table 6](#)

**Table 6. CDCE72010 Default Configuration Settings**

| REGISTER | DEFAULT SETTING | REGISTER | DEFAULT SETTING |
|----------|-----------------|----------|-----------------|
| REG0000  | 002C0040        | REG0007  | EB040717        |
| REG0001  | 83840051        | REG0008  | 010C0158        |
| REG0002  | 83400002        | REG0009  | 01000049        |
| REG0003  | 83400003        | REG0010  | 0BFC07CA        |
| REG0004  | 81800004        | REG0011  | 8000058B        |
| REG0005  | 81800005        | REG0012  | Undetermined    |
| REG0006  | EB040006        |          |                 |

The default configuration programmed in the EEPROM is: a 10MHz primary reference single ended LVCMOS, a 491.52MHz LVPECL VCXO running at 80kHz PFD with a 10Hz loop bandwidth. Reference Auto Select is off, M divider is set for 125, N divider is set to 768, charge pump current is set to 2.2mA, and feedback divider is set to divide by 8. Divider 1 is set to divide by 4, Dividers 2 and 3 are set to divide by 1, Dividers 4 and 5 are set to divide by 2, Dividers 6 and 7 are set to divide by 8, and Divider 8 is set to divide by 16. Output0:LVCMOS, Output1:Hi-LVPECL, Output2: Hi-LVPECL, Output3:Hi\_LVPECL, Output4:LVPECL, Output5:LVPECL, Output6:Hi-LVDS, Output7:Hi-LVDS, Output8:LVCMOS and Output9:LVCMOS.

**Register 0 Address 0x00: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK               | DESCRIPTION/FUNCTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                   |    |    |    |    | POWER UP CONDITION |        |   |
|--------------|--------------|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|
| 0            | INBUFSELX    | Reference Input Buffers     | Primary and secondary Buffer Type Select (LVPECL,LVDS or LVCMOS)<br>XY(10) LVPECL, (11) LVDS, (00) LVCMOS- Input is Positive pin                                                                                                                                                                                                                                                                                                                                                                                               |                                   |    |    |    |    | EEPROM             |        |   |
| 1            | INBUFSELY    |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                   |    |    |    |    |                    |        |   |
| 2            | PRISEL       | Reference Input Buffer      | When REFSELCTRL is set to 1, the following settings apply:<br>If Bits (2,3): 00 – No input buffer is selected/active<br>If Bits (2,3): 10 – PRI_REF is selected, SEC_REF is powered down<br>If Bits (2,3): 01 – SEC_REF is selected, PRI_REF is powered down <sup>(1)</sup><br>If Bits (2,3): 11 – Auto Select (PRI then SEC).                                                                                                                                                                                                 |                                   |    |    |    |    | EEPROM             |        |   |
| 3            | SECSEL       |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                   |    |    |    |    |                    |        |   |
| 4            | VCXOSEL      | Divider START DETERM-Block  | When set to 0, PRI- or SEC-clock is selected, depending on bits 2 and 3 (default)<br>When set to 1, VCXO/AUX-clock is selected, overwrites bits 2 and 3                                                                                                                                                                                                                                                                                                                                                                        |                                   |    |    |    |    | EEPROM             |        |   |
| 5            | REFSELCTRL   | Reference Selection Control | Reference Select Control to select if the control of the reference is from the internal bit in Register 0 bits 2 and 3 or from the external select pin.<br>- When set to 0: the external pin REF_SEL takes over the selection between PRI and SEC. Autoselect is not available.<br>- When set to 1: The external pin REF_SEL is ignored. The table in (Register 0 <2 and 3> ) describes which reference input clock is selected and available (none, PRI, SEC or Autoselect). In autoselect mode, refer to the timing diagram. |                                   |    |    |    |    | EEPROM             |        |   |
| 6            | DELAY_PFD0   | PFD                         | PFD pulse width PFD bit 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                                   |    |    |    |    | EEPROM             |        |   |
| 7            | DELAY_PFD1   |                             | PFD pulse width PFD bit 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                                   |    |    |    |    |                    |        |   |
| 8            | Reserved     |                             | Must be set 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                                   |    |    |    |    | EEPROM             |        |   |
| 9            | CP_DIR       | Charge Pump                 | Determines which direction CP current will regulate (Reference Clock leads to Feedback Clock, Positive CP output current [0], Negative CP output current [1])                                                                                                                                                                                                                                                                                                                                                                  |                                   |    |    |    |    | EEPROM             |        |   |
| 10           | CP_SRC       | Charge Pump Diagnostics     | Switches the current source in the charge pump on when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                 |                                   |    |    |    |    | EEPROM             |        |   |
| 11           | CP_SNK       |                             | Switches the current sink in the charge pump on when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                   |    |    |    |    | EEPROM             |        |   |
| 12           | CP_OPA       |                             | Switches the charge pump op-amp off when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                   |    |    |    |    | EEPROM             |        |   |
| 13           | CP_PRE       | Charge Pump                 | Preset charge pump output voltage to V <sub>CC_CP</sub> /2, on [1], off [0]                                                                                                                                                                                                                                                                                                                                                                                                                                                    |                                   |    |    |    |    | EEPROM             |        |   |
| 14           | ICP0         |                             | CP current setting bit 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 15           | ICP1         |                             | CP current setting bit 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 16           | ICP2         |                             | CP current setting bit 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 17           | ICP3         |                             | CP current setting bit 3                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 18           | RESERVED     |                             | Must be set to 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                   |    |    |    |    | EEPROM             |        |   |
| 19           | RESERVED     |                             | Must be set to 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                   |    |    |    |    | EEPROM             |        |   |
| 20           | IREFRES      | Charge Pump Diagnostics     | Enables the 12-kΩ pull-down resistor at I_REF_CP pin when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                              |                                   |    |    |    |    | EEPROM             |        |   |
| 21           | PECL0HISWING | Output 0                    | High output voltage swing in LVPECL/LVDS mode if set to 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                                   |    |    |    |    | EEPROM             |        |   |
| 22           | CMOSMODE0PX  | Output 0                    | LVCMOS mode select for OUTPUT 0 positive pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 23           | CMOSMODE0PY  |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                   |    |    |    |    |                    |        |   |
| 24           | CMOSMODE0NX  | Output 0                    | LVCMOS mode select for OUTPUT 0 negative pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                                                                                                                                                                                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 25           | CMOSMODE0NY  |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                                   |    |    |    |    |                    |        |   |
| 26           | OUTBUFSEL0X  | Output 0                    | OUTPUT TYPE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |
|              |              |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |
| LVPECL       |              |                             | 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 0                                 | 0  | 0  | 0  | 1  |                    |        |   |
| 27           | OUTBUFSEL0Y  | Output 0                    | LVDS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |
|              |              |                             | LVCMOS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | See Settings Above <sup>(2)</sup> |    |    |    |    | 0                  |        | 0 |
|              |              |                             | All Outputs Disabled                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |

(1) This setting is only available if the Register 11 Bit 3 is set to 0 (Feedback Divider clock is set to CMOS type).

(2) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs.



**Register 1 Address 0x01: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK  | DESCRIPTION/FUNCTION                                                                                     |                                   |    |    |    |    | POWER UP CONDITION |        |   |
|--------------|--------------|----------------|----------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|
| 0            | ACDCSEL      | Input Buffers  | If set to 0 AC Termination, If set to 1 DC termination                                                   |                                   |    |    |    |    | EEPROM             |        |   |
| 1            | HYSTEN       | Input Buffers  | If set to 1 Input Buffers Hysteresis enabled                                                             |                                   |    |    |    |    | EEPROM             |        |   |
| 2            | TERMSEL      | Input Buffers  | If set to 0 Input Buffer Internal Termination enabled                                                    |                                   |    |    |    |    | EEPROM             |        |   |
| 3            | PRIINVBB     | Input Buffers  | If set to 1 Primary Input Negative pin biased with internal VBB voltage                                  |                                   |    |    |    |    | EEPROM             |        |   |
| 4            | SECINVBB     | Input Buffers  | If set to 1 Secondary Input Negative pin biased with internal VBB voltage                                |                                   |    |    |    |    | EEPROM             |        |   |
| 5            | FAILSAFE     | Input Buffers  | If set to 1 Fail Safe is enabled for all input buffers                                                   |                                   |    |    |    |    | EEPROM             |        |   |
| 6            | PH1ADJC0     | Output 0 and 1 | Coarse phase adjust select for Output Divider 1                                                          |                                   |    |    |    |    | EEPROM             |        |   |
| 7            | PH1ADJC1     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 8            | PH1ADJC2     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 9            | PH1ADJC3     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 10           | PH1ADJC4     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 11           | PH1ADJC5     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 12           | PH1ADJC6     |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 13           | OUT1DIVRSEL0 | Output 0 and 1 | Output Divider 1 ratio select (seeTable 8)                                                               |                                   |    |    |    |    | EEPROM             |        |   |
| 14           | OUT1DIVRSEL1 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 15           | OUT1DIVRSEL2 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 16           | OUT1DIVRSEL3 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 17           | OUT1DIVRSEL4 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 18           | OUT1DIVRSEL5 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 19           | OUT1DIVRSEL6 |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 20           | EN01DIV      | Output 0 and 1 | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                          |                                   |    |    |    |    | EEPROM             |        |   |
| 21           | PECL1HISWING | Output 1       | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                |                                   |    |    |    |    | EEPROM             |        |   |
| 22           | CMOSMODE1PX  | Output 1       | LVCMOS mode select for OUTPUT 1 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State |                                   |    |    |    |    | EEPROM             |        |   |
| 23           | CMOSMODE1PY  |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 24           | CMOSMODE1NX  | Output 1       | LVCMOS mode select for OUTPUT 1 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State |                                   |    |    |    |    | EEPROM             |        |   |
| 25           | CMOSMODE1NY  |                |                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 26           | OUTBUFSEL1X  | Output 1       | OUTPUT TYPE                                                                                              | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |
|              |              |                |                                                                                                          | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |
|              |              |                | LVPECL                                                                                                   | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |
| 27           | OUTBUFSEL1Y  | Output 1       | LVDS                                                                                                     | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |
|              |              |                | LVCMOS                                                                                                   | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        | 0 |
|              |              |                | All Outputs Disabled                                                                                     | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs.

**Register 2 Address 0x01: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                     |                                   |    |    |    |    | POWER UP CONDITION |        |
|--------------|--------------|---------------|----------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|
| 0            | DLYM0        | DELAY M       | Reference phase delay M bit0                                                                             |                                   |    |    |    |    | EEPROM             |        |
| 1            | DLYM1        |               | Reference phase delay M bit1                                                                             |                                   |    |    |    |    |                    |        |
| 2            | DLYM2        |               | Reference phase delay M bit2                                                                             |                                   |    |    |    |    |                    |        |
| 3            | DLYN0        | DELAY N       | Feedback phase delay N bit0                                                                              |                                   |    |    |    |    | EEPROM             |        |
| 4            | DLYN1        |               | Feedback phase delay N bit1                                                                              |                                   |    |    |    |    |                    |        |
| 5            | DLYN2        |               | Feedback phase delay N bit2                                                                              |                                   |    |    |    |    |                    |        |
| 6            | PH2ADJC0     | Output 2      | Coarse phase adjust select for output divider 2                                                          |                                   |    |    |    |    | EEPROM             |        |
| 7            | PH2ADJC1     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 8            | PH2ADJC2     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 9            | PH2ADJC3     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 10           | PH2ADJC4     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 11           | PH2ADJC5     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 12           | PH2ADJC6     |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 13           | OUT2DIVRSEL0 | Output 2      | Output Divider 2 ratio select (seeTable 8)                                                               |                                   |    |    |    |    | EEPROM             |        |
| 14           | OUT2DIVRSEL1 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 15           | OUT2DIVRSEL2 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 16           | OUT2DIVRSEL3 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 17           | OUT2DIVRSEL4 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 18           | OUT2DIVRSEL5 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 19           | OUT2DIVRSEL6 |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 20           | EN2DIV       | Output 2      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                          |                                   |    |    |    |    | EEPROM             |        |
| 21           | PECL2HISWING | Output 2      | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                |                                   |    |    |    |    | EEPROM             |        |
| 22           | CMOSMODE2PX  | Output 2      | LVCMOS mode select for OUTPUT 2 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State |                                   |    |    |    |    | EEPROM             |        |
| 23           | CMOSMODE2PY  |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 24           | CMOSMODE2NX  | Output 2      | LVCMOS mode select for OUTPUT 2 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State |                                   |    |    |    |    | EEPROM             |        |
| 25           | CMOSMODE2NY  |               |                                                                                                          |                                   |    |    |    |    |                    |        |
| 26           | OUTBUFSEL2X  | Output 2      | OUTPUT TYPE                                                                                              | REGISTER BITS                     |    |    |    |    |                    | EEPROM |
|              |              |               |                                                                                                          | 22                                | 23 | 24 | 25 | 26 | 27                 |        |
| 27           | OUTBUFSEL2Y  | Output 2      | LVPECL                                                                                                   | 0                                 | 0  | 0  | 0  | 0  | 1                  | EEPROM |
|              |              |               | LVDS                                                                                                     | 0                                 | 1  | 0  | 1  | 1  | 1                  |        |
|              |              |               | LVCMOS                                                                                                   | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        |
|              |              |               | All Outputs Disabled                                                                                     | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs.

**Register 3 Address 0x03: SPI Mode**

| REGISTER BIT | BIT NAME      | RELATED BLOCK          | DESCRIPTION/FUNCTION                                                                                                                                                                                |                                   |    |    |    |    | POWER UP CONDITION |        |   |   |
|--------------|---------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|---|
| 0            | DIS_FDET_REF  | PLL Freq. Detect       | When set to 0, the REF-clock frequency detector is ON<br>When set to 1, it is switched OFF                                                                                                          |                                   |    |    |    |    | EEPROM             |        |   |   |
| 1            | DIS_FDET_FB   | Diagnostics            | When set to 1, the feedback path frequency detector is switched OFF (TI Test-GTME)                                                                                                                  |                                   |    |    |    |    | EEPROM             |        |   |   |
| 2            | BIAS_DIV01<0> | Output Divider 0 and 1 | When BIAS_DIV01<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30% |                                   |    |    |    |    | EEPROM             |        |   |   |
| 3            | BIAS_DIV01<1> |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 4            | BIAS_DIV23<0> | Output Divider 2 and 3 | When BIAS_DIV23<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30% |                                   |    |    |    |    | EEPROM             |        |   |   |
| 5            | BIAS_DIV23<1> |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 6            | PH3ADJC0      | Output 3               | Coarse phase adjust select for Output Divider 3                                                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |   |   |
| 7            | PH3ADJC1      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 8            | PH3ADJC2      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 9            | PH3ADJC3      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 10           | PH3ADJC4      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 11           | PH3ADJC5      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 12           | PH3ADJC6      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 13           | OUT3DIVRSEL0  | Output 3               | Output Divider 3 ratio select (seeTable 8)                                                                                                                                                          |                                   |    |    |    |    | EEPROM             |        |   |   |
| 14           | OUT3DIVRSEL1  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 15           | OUT3DIVRSEL2  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 16           | OUT3DIVRSEL3  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 17           | OUT3DIVRSEL4  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 18           | OUT3DIVRSEL5  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 19           | OUT3DIVRSEL6  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 20           | EN3DIV        | Output 3               | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |   |   |
| 21           | PECL3HISWING  | Output 3               | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                           |                                   |    |    |    |    | EEPROM             |        |   |   |
| 22           | CMOSMODE3PX   | Output 3               | LVCMOS mode select for OUTPUT 3 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                            |                                   |    |    |    |    | EEPROM             |        |   |   |
| 23           | CMOSMODE3PY   |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 24           | CMOSMODE3NX   | Output 3               | LVCMOS mode select for OUTPUT 3 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                            |                                   |    |    |    |    | EEPROM             |        |   |   |
| 25           | CMOSMODE3NY   |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |   |   |
| 26           | OUTBUFSEL3X   | Output 3               | OUTPUT TYPE                                                                                                                                                                                         | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |   |
|              |               |                        |                                                                                                                                                                                                     | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |   |
|              |               |                        | LVPECL                                                                                                                                                                                              | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |   |
| 27           | OUTBUFSEL3Y   | Output 3               | LVDS                                                                                                                                                                                                | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |   |
|              |               |                        | LVCMOS                                                                                                                                                                                              | See Settings Above <sup>(1)</sup> |    |    |    |    |                    |        | 0 | 0 |
|              |               |                        | All Outputs Disabled                                                                                                                                                                                | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |   |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs

**Register 4 Address 0x04: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                     | POWER UP CONDITION |
|--------------|--------------|---------------|----------------------------------------------------------------------------------------------------------|--------------------|
| 0            | RESERVED     |               | Must be set '0'                                                                                          | EEPROM             |
| 1            | RESERVED     |               | Must be set '0'                                                                                          | EEPROM             |
| 2            | RESERVED     |               | Must be set '0'                                                                                          | EEPROM             |
| 3            | RESERVED     |               | Must be set '0'                                                                                          | EEPROM             |
| 4            | HOLDONLOR    | HOLD_OVER     | If set to 0, CP remains active and will discharge loop filter if input reference clock is lost           | EEPROM             |
| 5            | RESERVED     |               |                                                                                                          | EEPROM             |
| 6            | PH4ADJC0     | Output 4      | Coarse phase adjust select for Output Divider 4                                                          | EEPROM             |
| 7            | PH4ADJC1     |               |                                                                                                          |                    |
| 8            | PH4ADJC2     |               |                                                                                                          |                    |
| 9            | PH4ADJC3     |               |                                                                                                          |                    |
| 10           | PH4ADJC4     |               |                                                                                                          |                    |
| 11           | PH4ADJC5     |               |                                                                                                          |                    |
| 12           | PH4ADJC6     |               |                                                                                                          |                    |
| 13           | OUT4DIVRSEL0 | Output 4      | Output Divider 4 ratio select (see <a href="#">Table 8</a> )                                             | EEPROM             |
| 14           | OUT4DIVRSEL1 |               |                                                                                                          |                    |
| 15           | OUT4DIVRSEL2 |               |                                                                                                          |                    |
| 16           | OUT4DIVRSEL3 |               |                                                                                                          |                    |
| 17           | OUT4DIVRSEL4 |               |                                                                                                          |                    |
| 18           | OUT4DIVRSEL5 |               |                                                                                                          |                    |
| 19           | OUT4DIVRSEL6 |               |                                                                                                          |                    |
| 20           | EN4DIV       | Output 4      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                          | EEPROM             |
| 21           | PECL4HISWING | Output 4      | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                | EEPROM             |
| 22           | CMOSMODE4PX  | Output 4      | LVCMOS mode select for OUTPUT 4 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State | EEPROM             |
| 23           | CMOSMODE4PY  |               |                                                                                                          |                    |
| 24           | CMOSMODE4NX  | Output 4      | LVCMOS mode select for OUTPUT 4 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State | EEPROM             |
| 25           | CMOSMODE4NY  |               |                                                                                                          |                    |
| 26           | OUTBUFSEL4X  | Output 4      | <b>OUTPUT TYPE</b>                                                                                       | EEPROM             |
|              |              |               |                                                                                                          |                    |
| 27           | OUTBUFSEL4Y  | Output 4      |                                                                                                          | EEPROM             |
|              |              |               |                                                                                                          |                    |
|              |              |               |                                                                                                          |                    |
|              |              |               |                                                                                                          |                    |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs

**Register 5 Address 0x05: SPI Mode**

| REGISTER BIT | BIT NAME      | RELATED BLOCK          | DESCRIPTION/FUNCTION                                                                                                                                                                                |                                   |    |    |    |    | POWER UP CONDITION |        |
|--------------|---------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|
| 0            | BIAS_DIV45<0> | Output Divider 4 and 5 | When BIAS_DIV45<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30% |                                   |    |    |    |    | EEPROM             |        |
| 1            | BIAS_DIV45<1> |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 2            | BIAS_DIV67<0> | Output Divider 6 and 7 | When BIAS_DIV67<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30% |                                   |    |    |    |    | EEPROM             |        |
| 3            | BIAS_DIV67<1> |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 4            | RESERVED      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |
| 5            | RESERVED      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |
| 6            | PH5ADJC0      | Output 5               | Coarse phase adjust select for Output Divider 5                                                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |
| 7            | PH5ADJC1      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 8            | PH5ADJC2      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 9            | PH5ADJC3      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 10           | PH5ADJC4      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 11           | PH5ADJC5      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 12           | PH5ADJC6      |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 13           | OUT5DIVRSEL0  | Output 5               | Output Divider 5 ratio select<br>(seeTable 8)                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |
| 14           | OUT5DIVRSEL1  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 15           | OUT5DIVRSEL2  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 16           | OUT5DIVRSEL3  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 17           | OUT5DIVRSEL4  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 18           | OUT5DIVRSEL5  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 19           | OUT5DIVRSEL6  |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 20           | EN5DIV        | Output 5               | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                     |                                   |    |    |    |    | EEPROM             |        |
| 21           | PECL5HISWING  | Output 5               | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                           |                                   |    |    |    |    | EEPROM             |        |
| 22           | CMOSMODE5PX   | Output 5               | LVCMOS mode select for OUTPUT 5 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                            |                                   |    |    |    |    | EEPROM             |        |
| 23           | CMOSMODE5PY   |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 24           | CMOSMODE5NX   | Output 5               | LVCMOS mode select for OUTPUT 5 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                            |                                   |    |    |    |    | EEPROM             |        |
| 25           | CMOSMODE5NY   |                        |                                                                                                                                                                                                     |                                   |    |    |    |    |                    |        |
| 26           | OUTBUFSEL5X   | Output 5               | OUTPUT TYPE                                                                                                                                                                                         | REGISTER BITS                     |    |    |    |    | EEPROM             |        |
|              |               |                        |                                                                                                                                                                                                     | 22                                | 23 | 24 | 25 | 26 |                    | 27     |
| 27           | OUTBUFSEL5Y   | Output 5               | LVPECL                                                                                                                                                                                              | 0                                 | 0  | 0  | 0  | 0  | 1                  | EEPROM |
|              |               |                        | LVDS                                                                                                                                                                                                | 0                                 | 1  | 0  | 1  | 1  | 1                  |        |
|              |               |                        | LVCMOS                                                                                                                                                                                              | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        |
|              |               |                        | All Outputs Disabled                                                                                                                                                                                | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs

**Register 6 Address 0x06: SPI Mode**

| REGISTER BIT | BIT NAME           | RELATED BLOCK                          | DESCRIPTION/FUNCTION                                                                                                                    |                                   |    |    |    |    | POWER UP CONDITION |        |   |   |
|--------------|--------------------|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|---|
| 0            | FB_FD_DESEL        | LOCK-DET                               | 0 Feedback Frequency Detector is connected to the Lock Detector<br>1 Feedback Frequency Detector is disconnected from the Lock Detector |                                   |    |    |    |    | EEPROM             |        |   |   |
| 1            | RESERVED           |                                        | Set to 0                                                                                                                                |                                   |    |    |    |    |                    |        |   |   |
| 2            | FBDETERM_DIV_SE L  | FB-Divider/<br>Deterministic<br>Blocks | 0 FB-Deterministic Clock divided by 1<br>1 FB- Deterministic Clock divided by 2                                                         |                                   |    |    |    |    | EEPROM             |        |   |   |
| 3            | FBDETERM_DIV2_DI S |                                        | 0 FB-Deterministic-DIV2-Block in normal operation<br>1 FB-Deterministic-DIV2 reset (here REG6_RB<2> == 0)                               |                                   |    |    |    |    |                    |        |   |   |
| 4            | FB_START_BYPASS    |                                        | 0 FB-Divider started with delay block (RC), normal operation<br>1 FB-Divider can be started with external REF_SEL-signal (pin)          |                                   |    |    |    |    |                    |        |   |   |
| 5            | DET_START_BYPAS S  | All Output Dividers                    | 0 Output-Dividers started with delay block (RC), normal operation<br>1 Output-Dividers can be started with external NRESET-signal (pin) |                                   |    |    |    |    | EEPROM             |        |   |   |
| 6            | PH6ADJC0           | Output 6                               | Coarse phase adjust select for Output Divider 6                                                                                         |                                   |    |    |    |    | EEPROM             |        |   |   |
| 7            | PH6ADJC1           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 8            | PH6ADJC2           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 9            | PH6ADJC3           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 10           | PH6ADJC4           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 11           | PH6ADJC5           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 12           | PH6ADJC6           |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 13           | OUT6DIVRSEL0       | Output 6                               | Output Divider 6 ratio select<br>(seeTable 8)                                                                                           |                                   |    |    |    |    | EEPROM             |        |   |   |
| 14           | OUT6DIVRSEL1       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 15           | OUT6DIVRSEL2       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 16           | OUT6DIVRSEL3       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 17           | OUT6DIVRSEL4       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 18           | OUT6DIVRSEL5       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 19           | OUT6DIVRSEL6       |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 20           | EN6DIV             | Output 6                               | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                         |                                   |    |    |    |    | EEPROM             |        |   |   |
| 21           | PECL6HISWING       | Output 6                               | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                               |                                   |    |    |    |    | EEPROM             |        |   |   |
| 22           | CMOSMODE6PX        | Output 6                               | LVCMOS mode select for OUTPUT 6 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                |                                   |    |    |    |    | EEPROM             |        |   |   |
| 23           | CMOSMODE6PY        |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 24           | CMOSMODE6NX        | Output 6                               | LVCMOS mode select for OUTPUT 6 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                |                                   |    |    |    |    | EEPROM             |        |   |   |
| 25           | CMOSMODE6NY        |                                        |                                                                                                                                         |                                   |    |    |    |    |                    |        |   |   |
| 26           | OUTBUFSEL6X        | Output 6                               | OUTPUT TYPE                                                                                                                             | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |   |
|              |                    |                                        |                                                                                                                                         | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |   |
|              |                    |                                        | LVPECL                                                                                                                                  | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |   |
| 27           | OUTBUFSEL6Y        | Output 6                               | LVDS                                                                                                                                    | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |   |
|              |                    |                                        | LVCMOS                                                                                                                                  | See Settings Above <sup>(1)</sup> |    |    |    |    |                    |        | 0 | 0 |
|              |                    |                                        | All Outputs Disabled                                                                                                                    | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |   |

(1) Use description for bits 22, 23, 24 and 25 for setting the LVCMOS outputs

**Register 7 Address 0x07: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                  |                                   |    |    |    |    | POWER UP CONDITION |        |   |
|--------------|--------------|---------------|-------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|
| 0            | LOCKW 0      | LOCK-DET      | Lock-detect window Bit 0 (Refer to Reg 9 Bits 6 and 7)                                                |                                   |    |    |    |    | EEPROM             |        |   |
| 1            | LOCKW 1      |               | Lock-detect window Bit 1 (Refer to Reg 9 Bits 6 and 7)                                                |                                   |    |    |    |    | EEPROM             |        |   |
| 2            | RESERVED     |               | Set to 0                                                                                              |                                   |    |    |    |    |                    |        |   |
| 3            | LOCKC0       |               | Number of coherent lock events Bit 0                                                                  |                                   |    |    |    |    |                    |        |   |
| 4            | LOCKC1       |               | Number of coherent lock events Bit 1                                                                  |                                   |    |    |    |    |                    |        |   |
| 5            | ADLOCK       |               | Selects Digital PLL_LOCK 0, Selects Analog PLL_LOCK 1                                                 |                                   |    |    |    |    |                    |        |   |
| 6            | PH7ADJC0     | Output 7      | Coarse phase adjust select for Output Divider 7                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 7            | PH7ADJC1     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 8            | PH7ADJC2     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 9            | PH7ADJC3     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 10           | PH7ADJC4     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 11           | PH7ADJC5     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 12           | PH7ADJC6     |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 13           | OUT7DIVRSEL0 | Output 7      | Output Divider 7 ratio select (seeTable 8)                                                            |                                   |    |    |    |    | EEPROM             |        |   |
| 14           | OUT7DIVRSEL1 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 15           | OUT7DIVRSEL2 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 16           | OUT7DIVRSEL3 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 17           | OUT7DIVRSEL4 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 18           | OUT7DIVRSEL5 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 19           | OUT7DIVRSEL6 |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 20           | EN7DIV       | Output 7      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                       |                                   |    |    |    |    | EEPROM             |        |   |
| 21           | PECL7HISWING | Output 7      | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                             |                                   |    |    |    |    | EEPROM             |        |   |
| 22           | CMOSMODE7PX  | Output 7      | LVCMOS mode select for OUTPUT 7 Positive Pin (X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State  |                                   |    |    |    |    | EEPROM             |        |   |
| 23           | CMOSMODE7PY  |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 24           | CMOSMODE7NX  | Output 7      | LVCMOS mode select for OUTPUT 7 Negative Pin. (X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State |                                   |    |    |    |    | EEPROM             |        |   |
| 25           | CMOSMODE7NY  |               |                                                                                                       |                                   |    |    |    |    |                    |        |   |
| 26           | OUTBUFSEL7X  | Output 7      | OUTPUT TYPE                                                                                           | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |
|              |              |               |                                                                                                       | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |
|              |              |               | LVPECL                                                                                                | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |
| 27           | OUTBUFSEL7Y  | Output 7      | LVDS                                                                                                  | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |
|              |              |               | LVCMOS                                                                                                | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        | 0 |
|              |              |               | All Outputs Disabled                                                                                  | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs

**Register 8 Address 0x08: SPI Mode**

| REGISTER BIT | BIT NAME     | RELATED BLOCK              | DESCRIPTION/FUNCTION                                                                                                       |                                   |    |    |    |    | POWER UP CONDITION |        |   |
|--------------|--------------|----------------------------|----------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|
| 0            | VCXOBUFSELX  | VCXO and AUX Input Buffers | VCXO and AUX Input Buffer Type Select (LVPECL,LVDS or LVCMOS) XY(10) LVPECL, (11) LVDS, (00) LVCMOS- Input is Positive Pin |                                   |    |    |    |    | EEPROM             |        |   |
| 1            | VCXOBUFSELY  |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 2            | VCXOACDCSEL  |                            | If Set to 0 AC Termination, If set to 1 DC Termination                                                                     |                                   |    |    |    |    |                    |        |   |
| 3            | VCXOHYSTEN   |                            | If Set to 1 Input Buffers Hysteresis enabled                                                                               |                                   |    |    |    |    |                    |        |   |
| 4            | VCXOTERMSEL  |                            | If Set to 0 Input Buffer Internal Termination enabled                                                                      |                                   |    |    |    |    |                    |        |   |
| 5            | VCXOINVBB    | VCXO Input Buffer          | If Set to 1 It Biases VCXO Input negative pin with internal VCXOVBB Voltage                                                |                                   |    |    |    |    | EEPROM             |        |   |
| 6            | PH8ADJC0     | Output 8 and 9             | Coarse phase adjust select for Output Divider 8                                                                            |                                   |    |    |    |    | EEPROM             |        |   |
| 7            | PH8ADJC1     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 8            | PH8ADJC2     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 9            | PH8ADJC3     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 10           | PH8ADJC4     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 11           | PH8ADJC5     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 12           | PH8ADJC6     |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 13           | OUT8DIVRSEL0 | Output 8 and 9             | Output Divider 8 ratio select (seeTable 8)                                                                                 |                                   |    |    |    |    | EEPROM             |        |   |
| 14           | OUT8DIVRSEL1 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 15           | OUT8DIVRSEL2 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 16           | OUT8DIVRSEL3 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 17           | OUT8DIVRSEL4 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 18           | OUT8DIVRSEL5 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 19           | OUT8DIVRSEL6 |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 20           | EN89DIV      | Output 8 and 9             | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                            |                                   |    |    |    |    | EEPROM             |        |   |
| 21           | PECL8HISWING | Output 8                   | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                  |                                   |    |    |    |    | EEPROM             |        |   |
| 22           | CMOSMODE8PX  | Output 8                   | LVCMOS mode select for OUTPUT 8 Positive Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                   |                                   |    |    |    |    | EEPROM             |        |   |
| 23           | CMOSMODE8PY  |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 24           | CMOSMODE8NX  | Output 8                   | LVCMOS mode select for OUTPUT 8 Negative Pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                   |                                   |    |    |    |    | EEPROM             |        |   |
| 25           | CMOSMODE8NY  |                            |                                                                                                                            |                                   |    |    |    |    |                    |        |   |
| 26           | OUTBUFSEL8X  | Output 8                   | OUTPUT TYPE                                                                                                                | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |
|              |              |                            |                                                                                                                            | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |
|              |              |                            | LVPECL                                                                                                                     | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |
| 27           | OUTBUFSEL8Y  | Output 8                   | LVDS                                                                                                                       | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |
|              |              |                            | LVC MOS                                                                                                                    | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        | 0 |
|              |              |                            | All Outputs Disabled                                                                                                       | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs



**Register 9 Address 0x09: SPI Mode**

| REGISTER BIT | BIT NAME         | RELATED BLOCK                      | DESCRIPTION/FUNCTION                                                                                                                                                                                                                                              |                                   |    |    |    |    | POWER UP CONDITION |        |   |
|--------------|------------------|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----|----|----|----|--------------------|--------|---|
| 0            | HOLDF            | HOLD-Over                          | Enables the Frequency Hold-Over (External Hold Over Function based on the external circuitry) on 1, off 0                                                                                                                                                         |                                   |    |    |    |    | EEPROM             |        |   |
| 1            | RESERVED         |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 2            | HOLD             |                                    | 3-State Charge Pump 0 - (equal to $\overline{\text{HOLD}}$ pin function)                                                                                                                                                                                          |                                   |    |    |    |    |                    |        |   |
| 3            | HOLDTR           |                                    | HOLD function always activated 1 (recommended for test purposes, only)<br>Triggered by analog PLL Lock detect outputs<br>If analog PLL Lock Signal is [1] (PLL locked), HOLD is activated<br>If analog PLL Lock Signal is [0] (PLL not lock), HOLD is deactivated |                                   |    |    |    |    |                    |        |   |
| 4            | HOLD_CNT0        |                                    | HOLD Function is reactivated after X Ref Clock Cycles. Defined by (HOLD_CNT0,HOLD_CNT1) : X = Number of Clock Cycles.<br>For (00) : X = 64, (01) : X = 128, (10) : X = 256, (11) : X = 512 Clock Cycles                                                           |                                   |    |    |    |    |                    |        |   |
| 5            | HOLD_CNT1        |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 6            | LOCKW 2          | LOCK-DET                           | Extended Lock-detect window Bit 2 (also refer to Reg 7 Bits 0 and 1)                                                                                                                                                                                              |                                   |    |    |    |    | EEPROM             |        |   |
| 7            | LOCKW 3          |                                    | Extended Lock-detect window Bit 3 (also refer to Reg 7 Bits 0 and 1)                                                                                                                                                                                              |                                   |    |    |    |    |                    |        |   |
| 8            | NOINV_RESHOL_INT | Chip CORE                          | When set to 0, SPI/HOLD_INT and SPI/RESET_INT inverted (default)<br>When set to 1, SPI/HOLD_INT and SPI/RESET_INT not inverted                                                                                                                                    |                                   |    |    |    |    | EEPROM             |        |   |
| 9            | DIVSYNC_DIS      | <i>Diagnostic: PLL N/M Divider</i> | When GTME = 0, this Bit has no functionality, But when GTME = 1, then:<br>When set to 0, START-Signal is synchronized to N/M Divider Input Clocks<br>When set to 1, START-Sync N/M Divider in PLL are bypassed                                                    |                                   |    |    |    |    | EEPROM             |        |   |
| 10           | START_BYPASS     | Divider START DETERM-Block         | When set to 0, START-Signal is synchronized to VCXO-Clock<br>When set to 1, START-Sync Block is bypassed                                                                                                                                                          |                                   |    |    |    |    | EEPROM             |        |   |
| 11           | INDET_BP         | Divider START DETERM-Block         | When set to 0, Sync Logic active when VCXO/AUX-Clocks are available<br>When set to 1, Sync Logic is independent from VCXO- and/or AUX-Clocks                                                                                                                      |                                   |    |    |    |    | EEPROM             |        |   |
| 12           | PLL_LOCK_BP      | Divider START DETERM-Block         | When set to 0, Sync Logic waits for 1st PLL_LOCK state<br>When set to 1, Sync Logic independent from 1st PLL_LOCK                                                                                                                                                 |                                   |    |    |    |    | EEPROM             |        |   |
| 13           | LOW_FD_FB_EN     | Divider START DETERM-Block         | When set to 0, Sync Logic is independent from VCXO/DIV_FB freq. (PLL-FD)<br>When set to 1, Sync Logic is started for VCXO/DIV_FB > ~600KHz, stopped for VCXO/DIV_FB < ~600KHz                                                                                     |                                   |    |    |    |    | EEPROM             |        |   |
| 14           | NPRESET_MDIV     | PLL M/FB-Divider                   | When set to 0, M-Divider uses NHOLD as NPRESET<br>When set to 1, M-Divider NOT preseted by NHOLD                                                                                                                                                                  |                                   |    |    |    |    | EEPROM             |        |   |
| 15           | BIAS_DIV_FB<0>   | Feedback Divider                   | When BIAS_DIV_FB<1:0> =<br>00, No current reduction for FB-Divider<br>01, Current reduction for FB-Divider by about 20%<br>10, Current reduction for FB-Divider by about 30%                                                                                      |                                   |    |    |    |    | EEPROM             |        |   |
| 16           | BIAS_DIV_FB<1>   |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 17           | BIAS_DIV89<0>    | Output Divider 8 and 9             | When BIAS_DIV89<1:0> =<br>00, No current reduction for all output-rivder<br>01, Current reduction for all output-dividder by about 20%<br>10, Current reduction for all output-dividder by about 30%                                                              |                                   |    |    |    |    | EEPROM             |        |   |
| 18           | BIAS_DIV89<1>    |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 19           | AUXINVBB         | AUX Input Buffer                   | If set to 1 it biases AUX Input Negative pin with internal VCXOVBB voltage.                                                                                                                                                                                       |                                   |    |    |    |    | EEPROM             |        |   |
| 20           | DIS_AUX_Y9       |                                    | If set to 1 AUX in Input Mode Buffer Is disabled. If set to 0 it follows the behavior of FB_MUX_SEL and OUT_MUX_SEL bits settings.                                                                                                                                |                                   |    |    |    |    |                    |        |   |
| 21           | PECL9HISWING     | Output 9                           | High output voltage swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                                                                         |                                   |    |    |    |    | EEPROM             |        |   |
| 22           | CMOSMODE9PX      | Output 9                           | LVCMOS mode select for OUTPUT 9 Positive pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                                                                                          |                                   |    |    |    |    | EEPROM             |        |   |
| 23           | CMOSMODE9PY      |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 24           | CMOSMODE9NX      | Output 9                           | LVCMOS mode select for OUTPUT 9 Negative pin.<br>(X,Y) = 00: Active, 10: Inverting, 11: Low, 01: 3-State                                                                                                                                                          |                                   |    |    |    |    | EEPROM             |        |   |
| 25           | CMOSMODE9NY      |                                    |                                                                                                                                                                                                                                                                   |                                   |    |    |    |    |                    |        |   |
| 26           | OUTBUFSEL9X      | Output 9                           | OUTPUT TYPE                                                                                                                                                                                                                                                       | REGISTER BITS                     |    |    |    |    |                    | EEPROM |   |
|              |                  |                                    |                                                                                                                                                                                                                                                                   | 22                                | 23 | 24 | 25 | 26 | 27                 |        |   |
|              |                  |                                    | LVPECL                                                                                                                                                                                                                                                            | 0                                 | 0  | 0  | 0  | 0  | 1                  |        |   |
| 27           | OUTBUFSEL9Y      | Output 9                           | LVDS                                                                                                                                                                                                                                                              | 0                                 | 1  | 0  | 1  | 1  | 1                  | EEPROM |   |
|              |                  |                                    | LVCMOS                                                                                                                                                                                                                                                            | See Settings Above <sup>(1)</sup> |    |    |    |    | 0                  |        | 0 |
|              |                  |                                    | All Outputs Disabled                                                                                                                                                                                                                                              | 0                                 | 1  | 0  | 1  | 1  | 0                  |        |   |

(1) Use description for bits 22, 23, 24, and 25 for setting the LVCMOS outputs

**Register 10 Address 0x0A: SPI Mode**

| REGISTER BIT | BIT NAME | RELATED BLOCK                    | DESCRIPTION/FUNCTION       | POWER UP CONDITION |
|--------------|----------|----------------------------------|----------------------------|--------------------|
| 0            | M0       | Reference<br>(PRI/SEC) Divider M | Reference Divider M Bit 0  | EEPROM             |
| 1            | M1       |                                  | Reference Divider M Bit 1  |                    |
| 2            | M2       |                                  | Reference Divider M Bit 2  |                    |
| 3            | M3       |                                  | Reference Divider M Bit 3  |                    |
| 4            | M4       |                                  | Reference Divider M Bit 4  |                    |
| 5            | M5       |                                  | Reference Divider M Bit 5  |                    |
| 6            | M6       |                                  | Reference Divider M Bit 6  |                    |
| 7            | M7       |                                  | Reference Divider M Bit 7  |                    |
| 8            | M8       |                                  | Reference Divider M Bit 8  |                    |
| 9            | M9       |                                  | Reference Divider M Bit 9  |                    |
| 10           | M10      |                                  | Reference Divider M Bit 10 |                    |
| 11           | M11      |                                  | Reference Divider M Bit 11 |                    |
| 12           | M12      |                                  | Reference Divider M Bit 12 |                    |
| 13           | M13      |                                  | Reference Divider M Bit 13 |                    |
| 14           | N0       | VCXO/AUX/SEC<br>Divider N        | VCXO Divider N Bit 0       | EEPROM             |
| 15           | N1       |                                  | VCXO Divider N Bit 1       |                    |
| 16           | N2       |                                  | VCXO Divider N Bit 2       |                    |
| 17           | N3       |                                  | VCXO Divider N Bit 3       |                    |
| 18           | N4       |                                  | VCXO Divider N Bit 4       |                    |
| 19           | N5       |                                  | VCXO Divider N Bit 5       |                    |
| 20           | N6       |                                  | VCXO Divider N Bit 6       |                    |
| 21           | N7       |                                  | VCXO Divider N Bit 7       |                    |
| 22           | N8       |                                  | VCXO Divider N Bit 8       |                    |
| 23           | N9       |                                  | VCXO Divider N Bit 9       |                    |
| 24           | N10      |                                  | VCXO Divider N Bit 10      |                    |
| 25           | N11      |                                  | VCXO Divider N Bit 11      |                    |
| 26           | N12      |                                  | VCXO Divider N Bit 12      |                    |
| 27           | N13      |                                  | VCXO Divider N Bit 13      |                    |

**Register 11 Address 0x0B: SPI Mode**

| REGISTER BIT | BIT NAME                                   | RELATED BLOCK                          | DESCRIPTION/FUNCTION                                                                                                                                              | POWER UP CONDITION |
|--------------|--------------------------------------------|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0            | PRI_DIV2                                   | Input Buffers                          | If set to 1 enables Primary Reference Divide by 2                                                                                                                 | EEPROM             |
| 1            | SEC_DIV2                                   | Input Buffers                          | If set to 1 enables Secondary Reference Divide by 2                                                                                                               | EEPROM             |
| 2            | FB_DIS                                     | FB Path Integer Counter 32             | When set to 0, FB divider is active<br>When set to 1, FB divider is disabled                                                                                      | EEPROM             |
| 3            | FB_CML_SEL                                 | FB Path Integer Counter 32             | When set to 0, FB clock is CMOS type <sup>(1)</sup><br>When set to 1, FB clock is CML type and uses CML2CMOS converter in PLL                                     | EEPROM             |
| 4            | FB_INCLK_INV                               | FB-Divider/<br>Deterministic<br>Blocks | When set to 0, Input clock for FB not inverted (normal mode, low speed)<br>When set to 1, Input clock for FB inverted (higher speed mode)                         | EEPROM             |
| 5            | FB_COUNT32_0                               | FB Path Integer Counter 32             | Feedback Counter Bit0                                                                                                                                             | EEPROM             |
| 6            | FB_COUNT32_1                               |                                        | Feedback Counter Bit1                                                                                                                                             |                    |
| 7            | FB_COUNT32_2                               |                                        | Feedback Counter Bit2                                                                                                                                             |                    |
| 8            | FB_COUNT32_3                               |                                        | Feedback Counter Bit3                                                                                                                                             |                    |
| 9            | FB_COUNT32_4                               |                                        | Feedback Counter Bit4                                                                                                                                             |                    |
| 10           | FB_COUNT32_5                               |                                        | Feedback Counter Bit5                                                                                                                                             |                    |
| 11           | FB_COUNT32_6                               |                                        | Feedback Counter Bit6                                                                                                                                             |                    |
| 12           | FB_PHASE0                                  | FB Path Integer Counter 32             | Feedback Phase Adjust Bit0                                                                                                                                        | EEPROM             |
| 13           | FB_PHASE1                                  |                                        | Feedback Phase Adjust Bit1                                                                                                                                        |                    |
| 14           | FB_PHASE2                                  |                                        | Feedback Phase Adjust Bit2                                                                                                                                        |                    |
| 15           | FB_PHASE3                                  |                                        | Feedback Phase Adjust Bit3                                                                                                                                        |                    |
| 16           | FB_PHASE4                                  |                                        | Feedback Phase Adjust Bit4                                                                                                                                        |                    |
| 17           | FB_PHASE5                                  |                                        | Feedback Phase Adjust Bit5                                                                                                                                        |                    |
| 18           | FB_PHASE6                                  |                                        | Feedback Phase Adjust Bit6                                                                                                                                        |                    |
| 19           | PD_PLL                                     | PLL                                    | If set to 0, PLL is in normal mode<br>If set to 1, PLL is powered down                                                                                            | EEPROM             |
| 20           | FB_MUX_SEL<br>See <a href="#">Table 7</a>  | Clock Tree and Deterministic Block     | When set to 0, the VCXO Clock is selected for the Clock Tree and FB-Div and Det<br>When set to 1, the AUX Clock is selected for the Clock Tree and FB-Div and Det | EEPROM             |
| 21           | OUT_MUX_SEL<br>See <a href="#">Table 7</a> | Clock Tree                             | If Set to 0 it selects the VCXO Clock and if Set to 1 it selects the AUX Clock                                                                                    | EEPROM             |
| 22           | FB_SEL                                     | Diagnostics                            | Feed Back Path Selects FB/VCXO-Path when set to 0 (TI Test-GTME)<br>The Secondary Reference clock input is selected when set to 1 (TI Test-GTME)                  | EEPROM             |
| 23           | NRESHAPE1                                  | Reference Selection Control            | Reshapes the Reference Clock Signal 0, Disable Reshape 1                                                                                                          | EEPROM             |
| 24           | SEL_DEL1                                   |                                        | If set to 0 it enables short delay for fast operation<br>If Set to 1 Long Delay recommended for Input References below 150Mhz                                     | EEPROM             |
| 25           | RESET_HOLD_MODE                            | Reset Circuitry                        | If set to 1 the RESET or HOLD pin acts as $\overline{\text{HOLD}}$ , set to 0 it acts as $\overline{\text{RESET}}$                                                | EEPROM             |
| 26           | EPLOCK                                     | Status                                 | Read only. If EPLOCK reads a 0, the EEPROM is unlocked. If EPLOCK reads a 1, then the EEPROM is locked.                                                           | EEPROM             |
| 27           | Reserved                                   | read only                              | Read only; always reads '1'                                                                                                                                       | EEPROM             |

(1) When Feedback Divider clock is set to CMOS type, only feedback divider values greater than 5 are available.

**Table 7. Output Buffers Source Feed, PLL Source Feed, and AUX IN/OUTPUT 9 Selection**

| FB_MUX_SEL | OUT_MUX_SEL | PLL FEED AND OUTPUTS FEED                          | AUX INPUT OR OUTPUT 9 |
|------------|-------------|----------------------------------------------------|-----------------------|
| 0          | 0           | VCXO::PLL, VCXO::Y0...Y9 and Deterministic Block   | OUTPUT 9 is enabled   |
| 1          | 0           | AUXIN::PLL, VCXO::Y0...Y8 and Deterministic Block  | AUX IN is enabled     |
| 0          | 1           | VCXO::PLL, AUXIN::Y0...Y8 and Deterministic Block  | AUX IN is enabled     |
| 1          | 1           | AUXIN::PLL, AUXIN::Y0...Y8 and Deterministic Block | AUX IN is enabled     |

**Register 12 Address 0x0C: SPI Mode (RAM only Register)**

| REGISTER BIT | BIT NAME    | RELATED BLOCK      | DESCRIPTION/FUNCTION                                                                                                                                                                                                                                 | POR DEFAULT |     |
|--------------|-------------|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-----|
| 0            | RESERVED    |                    | Must be set '0'                                                                                                                                                                                                                                      |             | RAM |
| 1            | RESERVED    |                    | Must be set '0'                                                                                                                                                                                                                                      |             | RAM |
| 2            | RESERVED    |                    | Must be set '0'                                                                                                                                                                                                                                      |             | RAM |
| 3            | RESERVED    |                    | Must be set '0'                                                                                                                                                                                                                                      |             | RAM |
| 4            | INDET_AUX   | Status (Read Only) | It indicates that a clock is present at AUX-input (Y9) , when set to 1                                                                                                                                                                               |             | RAM |
| 5            | INDET_VCXO  | Status (Read Only) | It indicates that a clock is present at VCXO-input , when set to 1                                                                                                                                                                                   |             | RAM |
| 6            | PLL_LOCK    | Status (Read Only) | It indicates that the PLL is locked when set to 1                                                                                                                                                                                                    |             | RAM |
| 7            | SLEEP       | Power Down         | Power-down mode on when set to 0, Off when set to 1                                                                                                                                                                                                  | 1           | RAM |
| 8            | RESET_HOLD  | Reset              | If set to 0 this bit forces "RESET" or "HOLD" depending on the setting of RESET_HOLD_MODE bit in Register 11. If set to 0 RESET or HOLD are asserted. Set for 1 for normal operation.                                                                | 1           | RAM |
| 9            | GTME        | Diagnostics        | General Test Mode Enable, Test Mode is only enabled, if this bit is set to 1 This bit controls many test modes on the device.                                                                                                                        | 0           | RAM |
| 10           | REVISION0   | Status             | Read only: Revision Control Bit 0                                                                                                                                                                                                                    |             | RAM |
| 11           | REVISION1   | Status             | Read only: Revision Control Bit 1                                                                                                                                                                                                                    |             | RAM |
| 12           | REVISION2   | Status             | Read only: Revision Control Bit 2                                                                                                                                                                                                                    |             | RAM |
| 13           | PD_IO       | Diagnostics        | When set to 0, all blocks are on. (TI Test-GTME)<br>When set to 1, the VCXO Input, AUX Input and all output buffers and divider blocks are disabled. This test is done to measure the effect of the I/O circuitry on the Charge Pump. (TI Test-GTME) | 0           | RAM |
| 14           | SXOIREF     | Diagnostics        | If set to 0 that Status pin is used as CMOS output to enable TI test modes. Set to 1 when IREFRES is set to 1 and 12-KΩ resistor is connected. (TI Test-GTME)                                                                                        | 0           | RAM |
| 15           | SHOLD       | Diagnostics        | Routes the HOLD signal to the PLL_LOCK pin when set to 1 (TI Test-GTME)                                                                                                                                                                              | 0           | RAM |
| 16           | RESERVED    |                    | Must be set '0'                                                                                                                                                                                                                                      | 0           | RAM |
| 17           | STATUS0     | Diagnostics        | TI test registers. For TI use only<br>Route internal signals to external STATUS pin.<br>STATUS3, STATUS2, STATUS1, STATUS0 (S3, S2, S1, S0) will select that internal status signal that will be routed to the external STATUS pin.                  | 1           | RAM |
| 18           | STATUS1     |                    |                                                                                                                                                                                                                                                      |             |     |
| 19           | STATUS2     |                    |                                                                                                                                                                                                                                                      |             |     |
| 20           | STATUS3     |                    |                                                                                                                                                                                                                                                      |             |     |
| 21           | TITSTCFG0   | Diagnostics        | TI test registers. For TI use only                                                                                                                                                                                                                   | 0           | RAM |
| 22           | TITSTCFG1   | Diagnostics        | TI test registers. For TI use only                                                                                                                                                                                                                   | 0           | RAM |
| 23           | TITSTCFG2   | Diagnostics        | TI test registers. For TI use only                                                                                                                                                                                                                   | 0           | RAM |
| 24           | TITSTCFG3   | Diagnostics        | TI test registers. For TI use only                                                                                                                                                                                                                   | 0           | RAM |
| 25           | PRIACTIVITY | Status             | It indicates activity on the Primary when set to - (read only bit)                                                                                                                                                                                   |             | RAM |
| 26           | SECACTIVITY | Status             | It indicates activity on the Secondary when set to - (read only bit)                                                                                                                                                                                 |             | RAM |
| 27           | RESERVED    |                    |                                                                                                                                                                                                                                                      |             | RAM |

**NOTE**

If TI test bits (Register 12< bits 17,18,19, 20> are set to 1000, Reference Select from the Smart Mux will show on the STATUS pin ( High = Primary REF is selected and Low = Secondary REF is selected).

When TI test bits are set to 0000 the Reference Clock Frequency Detector shows up on the STATUS pin. In this mode the STATUS pin goes high if a clock is detected and low if a clock is not detected. In this configuration Register 3 Bit 0 should be set to 0.

## OUTPUT DIVIDERS SETTINGS

The CDCE72010 has a complex multi stage output divider. The table below describes the setting of Bits 13:19 of Register 1 to 8 and the setting for the feedback divider bits 5:11 of register 11. The table below describes divider settings and the phase relation of the outputs with respect to divide by one clock. To calculate the phase relation between 2 different dividers see Output Divider and Phase Adjust Section in this document.

**Table 8. Output Dividers and Feedback Divide Settings and Phase Output**

| FOR REGISTER 1 TO 8 BITS {19[BIT6] TO 13[BIT0]}<br>FOR REGISTER 11 BITS {11[BIT6] TO 5[BIT0]} |         |         |         |         |         |         | DIVIDE BY TOTAL |
|-----------------------------------------------------------------------------------------------|---------|---------|---------|---------|---------|---------|-----------------|
| [Bit 6]                                                                                       | [Bit 5] | [Bit 4] | [Bit 3] | [Bit 2] | [Bit 1] | [Bit 0] |                 |
| 0                                                                                             | 1       | 0       | 0       | 0       | 0       | 0       | 1               |
| 1                                                                                             | 0       | 0       | 0       | 0       | 0       | 0       | 2               |
| 1                                                                                             | 0       | 0       | 0       | 0       | 0       | 1       | 3               |
| 1                                                                                             | 0       | 0       | 0       | 0       | 1       | 0       | 4               |
| 1                                                                                             | 0       | 0       | 0       | 0       | 1       | 1       | 5               |
| 0                                                                                             | 0       | 0       | 0       | 0       | 0       | 0       | 4'              |
| 0                                                                                             | 0       | 0       | 0       | 0       | 0       | 1       | 6               |
| 0                                                                                             | 0       | 0       | 0       | 0       | 1       | 0       | 8               |
| 0                                                                                             | 0       | 0       | 0       | 0       | 1       | 1       | 10              |
| 0                                                                                             | 0       | 0       | 0       | 1       | 0       | 0       | 8'              |
| 0                                                                                             | 0       | 0       | 0       | 1       | 0       | 1       | 12              |
| 0                                                                                             | 0       | 0       | 0       | 1       | 1       | 0       | 16              |
| 0                                                                                             | 0       | 0       | 0       | 1       | 1       | 1       | 20              |
| 0                                                                                             | 0       | 0       | 1       | 0       | 0       | 0       | 12'             |
| 0                                                                                             | 0       | 0       | 1       | 0       | 0       | 1       | 18              |
| 0                                                                                             | 0       | 0       | 1       | 0       | 1       | 0       | 24              |
| 0                                                                                             | 0       | 0       | 1       | 0       | 1       | 1       | 30              |
| 0                                                                                             | 0       | 0       | 1       | 1       | 0       | 0       | 16'             |
| 0                                                                                             | 0       | 0       | 1       | 1       | 0       | 1       | 24'             |
| 0                                                                                             | 0       | 0       | 1       | 1       | 1       | 0       | 32              |
| 0                                                                                             | 0       | 0       | 1       | 1       | 1       | 1       | 40              |
| 0                                                                                             | 0       | 1       | 0       | 0       | 0       | 0       | 20'             |
| 0                                                                                             | 0       | 1       | 0       | 0       | 0       | 1       | 30'             |
| 0                                                                                             | 0       | 1       | 0       | 0       | 1       | 0       | 40'             |
| 0                                                                                             | 0       | 1       | 0       | 0       | 1       | 1       | 50              |
| 0                                                                                             | 0       | 1       | 0       | 1       | 0       | 0       | 24'             |
| 0                                                                                             | 0       | 1       | 0       | 1       | 0       | 1       | 36              |
| 0                                                                                             | 0       | 1       | 0       | 1       | 1       | 0       | 48              |
| 0                                                                                             | 0       | 1       | 0       | 1       | 1       | 1       | 60              |
| 0                                                                                             | 0       | 1       | 1       | 0       | 0       | 0       | 28              |
| 0                                                                                             | 0       | 1       | 1       | 0       | 0       | 1       | 42              |
| 0                                                                                             | 0       | 1       | 1       | 0       | 1       | 0       | 56              |
| 0                                                                                             | 0       | 1       | 1       | 0       | 1       | 1       | 70              |
| 0                                                                                             | 0       | 1       | 1       | 1       | 0       | 0       | 32'             |
| 0                                                                                             | 0       | 1       | 1       | 1       | 0       | 1       | 48'             |
| 0                                                                                             | 0       | 1       | 1       | 1       | 1       | 0       | 64              |
| 0                                                                                             | 0       | 1       | 1       | 1       | 1       | 1       | 80              |

## CONFIGURATION DEFAULT MODE (CD MODE)

The CDCE72010 has two modes of operation, SPI Interface and Configuration Default Mode. The Configuration Default mode is selected when MODE\_SEL Pin is driven low and it is used where SPI interface is not available. In the CD Mode configuration, the SPI interface Pins become static control pins CD1, CD2, CD3 and AUX\_SEL as shown in the Pin description. The CD Mode signals are sampled only at power up or after Power Down are asserted.

In CD Mode, CD1 and CD2 are used to switch between EEPROM saved configurations.

- CD1 allows swapping Divider and Phase Adjust value between output couples
- CD2 allows changing the output type for each output.
- AUX\_SEL Controls the Output Mux between VCXO and AUX Input.
- CD3 must be grounded in CD Mode.

Without any interface a single device with a single program can have multiple configurations that can be implemented on more than one socket.




Figure 18. Writing to EEPROM via SPI Bus




Figure 19. Using CD1, CD2 to Control What is Copied From EEPROM Into Registers at Power Up

**Register 0 Address 0x00: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK               | DESCRIPTION/FUNCTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | POWER UP CONDITION |
|---------|--------------|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | INBUFSELX    | Reference Input Buffers     | Primary and Secondary Buffer Type Select (LVPECL, LVDS or LVCMOS) XY(10) LVPECL, (11) LVDS, (00) LVCMOS- Input is Positive Pin                                                                                                                                                                                                                                                                                                                                                                                                                                       | EEPROM             |
| 1       | INBUFSELY    |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                    |
| 2       | PRISEL       | Reference Input Buffer      | When REFSELCTRL is set to 1 the following settings apply:<br>If Bit (2,3): 00 – no Input Buffer is selected/active<br>If Bit (2,3): 10 – PRI_REF is selected, SEC_BUF is powered down<br>If Bit (2,3): 01 – SEC_REF is selected, PRI_BUF is powered down <sup>(1)</sup><br>If Bit (2,3): 11 – Auto Select (PRI then SEC).                                                                                                                                                                                                                                            | EEPROM             |
| 3       | SECSEL       |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                    |
| 4       | VCXOSEL      | Divider START DETERM-Block  | When set to 0, PRI- or SEC-Clocks are selected, depending on Bits 2 and 3 (default)<br>When set to 1, VCXO/AUX-clock selected, overwrites Bits 2 and 3                                                                                                                                                                                                                                                                                                                                                                                                               | EEPROM             |
| 5       | REFSELCTRL   | Reference Selection Control | Reference Select Control to select if the control of the reference is from the internal bit in Register 0 bits 2 and 3 or from the external select pin.<br>– When set to 0: The external pin REF_SEL takes over the selection between PRI and SEC. Autoselect is not available.<br>– When set to 1 R0.2 and R0.3 bits must be set '1': The external pin REF_SEL is ignored. The Table in (Register 0 <2 and 3> ) describes, which reference input clock is selected and available at (none, PRI, SEC or Autoselect). In autoselect mode, refer to the timing diagram | EEPROM             |
| 6       | DELAY_PFD0   | PFD                         | PFD Pulse Width PFD Bit 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | EEPROM             |
| 7       | DELAY_PFD1   | PFD                         | PFD Pulse Width PFD Bit 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | EEPROM             |
| 8       | RESERVED     |                             | Must be set '0'                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 9       | CP_DIR       | Charge Pump                 | Determines in which direction CP current will regulate (Reference Clock leads to Feedback Clock; Positive CP output current [0]; Negative CP output current [1]                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 10      | CP_SRC       | Diagnostics                 | Switches the current source in the Charge Pump on when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | EEPROM             |
| 11      | CP_SNK       |                             | Switches the current sink in the Charge Pump on when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | EEPROM             |
| 12      | CP_OPA       |                             | Switches the Charge Pump op-amp off when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | EEPROM             |
| 13      | CP_PRE       | Charge Pump                 | Preset Charge Pump output voltage to $V_{CC\_CP}/2$ , on [1], off [0]                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | EEPROM             |
| 14      | ICP0         |                             | CP Current Setting Bit 0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | EEPROM             |
| 15      | ICP1         |                             | CP Current Setting Bit 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | EEPROM             |
| 16      | ICP2         |                             | CP Current Setting Bit 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | EEPROM             |
| 17      | ICP3         |                             | CP Current Setting Bit 3                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | EEPROM             |
| 18      | RESERVED     |                             | Must be set '0'                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 19      | RESERVED     |                             | Must be set '0'                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 20      | IREFRES      | Diagnostics                 | Enables the 12k pull-down resistor at I_REF_CP Pin when set to 1 (TI Test-GTME)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 21      | PECL0HISWING | Output 0                    | High output voltage swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | EEPROM             |
| 22      | RESERVED     |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 23      | RESERVED     |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | EEPROM             |
| 24      | OUTBUF0CD2LX | CD2 Low                     | Output Buffer 0 Signaling Selection when CD2 In low (X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                                                                                                                                                                                                                                                                                                                                                                     | EEPROM             |
| 25      | OUTBUF0CD2LY |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                    |
| 26      | OUTBUF0CD2HX | CD2 High                    | Output Buffer 0 Signaling Selection when CD2 in high (X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: output disable                                                                                                                                                                                                                                                                                                                                                                                                                                                    | EEPROM             |
| 27      | OUTBUF0CD2HY |                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                    |

(1) This setting is only available if the Register 11 Bit 3 is set to 0 (Feedback Divider clock is set to CMOS type).

**Register 1 Address 0x01: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK  | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|--------------|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | ACDCSEL      | Input Buffers  | If Set to 0 AC Termination, If set to 1 DC termination                                                                                                                                                                | EEPROM             |
| 1       | HYSTEN       | Input Buffers  | If Set to 1 Input Buffers Hysteresis enabled                                                                                                                                                                          | EEPROM             |
| 2       | TERMSEL      | Input Buffers  | If Set to 0 Input Buffer Internal Termination enabled                                                                                                                                                                 | EEPROM             |
| 3       | PRIINVBB     | Input Buffers  | If Set to 1 Primary Input Negative Pin biased with internal VBB voltage.                                                                                                                                              | EEPROM             |
| 4       | SECINVBB     | Input Buffers  | If Set to 1 Secondary Input Negative Pin biased with internal VBB voltage                                                                                                                                             | EEPROM             |
| 5       | FAILSAFE     | Input Buffers  | If Set to 1 Fail Safe is enabled for all input buffers.                                                                                                                                                               | EEPROM             |
| 6       | PH1ADJC0     | Output 0 and 1 | Coarse phase adjust select for output divider 1                                                                                                                                                                       | EEPROM             |
| 7       | PH1ADJC1     |                |                                                                                                                                                                                                                       |                    |
| 8       | PH1ADJC2     |                |                                                                                                                                                                                                                       |                    |
| 9       | PH1ADJC3     |                |                                                                                                                                                                                                                       |                    |
| 10      | PH1ADJC4     |                |                                                                                                                                                                                                                       |                    |
| 11      | PH1ADJC5     |                |                                                                                                                                                                                                                       |                    |
| 12      | PH1ADJC6     |                |                                                                                                                                                                                                                       |                    |
| 13      | OUT1DIVRSEL0 | Output 0 and 1 | OUTPUT DIVIDER 1 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT1DIVRSEL1 |                |                                                                                                                                                                                                                       |                    |
| 15      | OUT1DIVRSEL2 |                |                                                                                                                                                                                                                       |                    |
| 16      | OUT1DIVRSEL3 |                |                                                                                                                                                                                                                       |                    |
| 17      | OUT1DIVRSEL4 |                |                                                                                                                                                                                                                       |                    |
| 18      | OUT1DIVRSEL5 |                |                                                                                                                                                                                                                       |                    |
| 19      | OUT1DIVRSEL6 |                |                                                                                                                                                                                                                       |                    |
| 20      | EN01DIV      | Output 0 and 1 | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL1HISWING | Output 1       | High output voltage swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA1CD1H  | CD1 High       | CD1 PIN is high and DIVPHA1CD1H is set to low<br>Loads Output Divider 1 and Phase Adjust 1 into OUTPUT 1<br>CD1 PIN is high and DIVPHA1CD1H is set to high<br>Loads Output Divider 2 and Phase Adjust 2 into OUTPUT 1 | EEPROM             |
| 23      | DIVPHA1CD1L  | CD1 Low        | CD1 PIN is low and DIVPHA1CD1L is set to low<br>Loads Output Divider 1 and Phase Adjust 1 into OUTPUT 1<br>CD1 PIN is low and DIVPHA1CD1L is set to high<br>Loads Output Divider 2 and Phase Adjust 2 into OUTPUT 1   | EEPROM             |
| 24      | OUTBUF1CD2LX | CD2 Low        | Output Buffer 1 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF1CD2LY |                |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF1CD2HX | CD2 High       | Output Buffer 1 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF1CD2HY |                |                                                                                                                                                                                                                       |                    |



**Register 1 Address 0x01: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|--------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | DLYM0        | DELAY M       | Reference Phase Delay M Bit0                                                                                                                                                                                          | EEPROM             |
| 1       | DLYM1        |               | Reference Phase Delay M Bit1                                                                                                                                                                                          |                    |
| 2       | DLYM2        |               | Reference Phase Delay M Bit2                                                                                                                                                                                          |                    |
| 3       | DLYN0        | DELAY N       | Feedback Phase Delay N Bit0                                                                                                                                                                                           | EEPROM             |
| 4       | DLYN1        |               | Feedback Phase Delay N Bit1                                                                                                                                                                                           |                    |
| 5       | DLYN2        |               | Feedback Phase Delay N Bit2                                                                                                                                                                                           |                    |
| 6       | PH2ADJC0     | Output 2      | Coarse phase adjust select for output divider 2                                                                                                                                                                       | EEPROM             |
| 7       | PH2ADJC1     |               |                                                                                                                                                                                                                       |                    |
| 8       | PH2ADJC2     |               |                                                                                                                                                                                                                       |                    |
| 9       | PH2ADJC3     |               |                                                                                                                                                                                                                       |                    |
| 10      | PH2ADJC4     |               |                                                                                                                                                                                                                       |                    |
| 11      | PH2ADJC5     |               |                                                                                                                                                                                                                       |                    |
| 12      | PH2ADJC6     |               |                                                                                                                                                                                                                       |                    |
| 13      | OUT2DIVRSEL0 | Output 2      | OUTPUT DIVIDER 2 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT2DIVRSEL1 |               |                                                                                                                                                                                                                       |                    |
| 15      | OUT2DIVRSEL2 |               |                                                                                                                                                                                                                       |                    |
| 16      | OUT2DIVRSEL3 |               |                                                                                                                                                                                                                       |                    |
| 17      | OUT2DIVRSEL4 |               |                                                                                                                                                                                                                       |                    |
| 18      | OUT2DIVRSEL5 |               |                                                                                                                                                                                                                       |                    |
| 19      | OUT2DIVRSEL6 |               |                                                                                                                                                                                                                       |                    |
| 20      | EN2DIV       | Output 2      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL2HISWING | Output 2      | High output voltage swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA2CD1H  | CD1 High      | CD1 PIN is high and DIVPHA2CD1H is set to low<br>Loads Output Divider 2 and Phase Adjust 2 into OUTPUT 2<br>CD1 PIN is high and DIVPHA2CD1H is set to high<br>Loads Output Divider 1 and Phase Adjust 1 into OUTPUT 2 | EEPROM             |
| 23      | DIVPHA2CD1L  | CD1 Low       | CD1 PIN is low and DIVPHA2CD1L is set to low<br>Loads Output Divider 2 and Phase Adjust 2 into OUTPUT 2<br>CD1 PIN is low and DIVPHA2CD1L is set to high<br>Loads Output Divider 1 and Phase Adjust 1 into OUTPUT 2   | EEPROM             |
| 24      | OUTBUF2CD2LX | CD2 Low       | Output Buffer 2 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF2CD2LY |               |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF2CD2HX | CD2 High      | Output Buffer 2 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF2CD2HY |               |                                                                                                                                                                                                                       |                    |

**Register 3 Address 0x03: CD Mode**

| RAM BIT | BIT NAME      | RELATED BLOCK          | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|---------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | DIS_FDET_REF  | PLL Freq. Detect       | When set to 0, the REF-clock frequency detector is ON<br>When set to 1, it is switched OFF                                                                                                                            | EEPROM             |
| 1       | DIS_FDET_FB   | Diagnostics            | When set to 1, the feedback path frequency detector is switched OFF (TI Test-GTME)                                                                                                                                    | EEPROM             |
| 2       | BIAS_DIV01<0> | Output Divider 0 and 1 | When BIAS_DIV01<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30%                   | EEPROM             |
| 3       | BIAS_DIV01<1> |                        |                                                                                                                                                                                                                       | EEPROM             |
| 4       | BIAS_DIV23<0> | Output Divider 2 and 3 | When BIAS_DIV23<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30%                   | EEPROM             |
| 5       | BIAS_DIV23<1> |                        |                                                                                                                                                                                                                       | EEPROM             |
| 6       | PH3ADJC0      | Output 3               | Coarse phase adjust select for output divider 3                                                                                                                                                                       | EEPROM             |
| 7       | PH3ADJC1      |                        |                                                                                                                                                                                                                       |                    |
| 8       | PH3ADJC2      |                        |                                                                                                                                                                                                                       |                    |
| 9       | PH3ADJC3      |                        |                                                                                                                                                                                                                       |                    |
| 10      | PH3ADJC4      |                        |                                                                                                                                                                                                                       |                    |
| 11      | PH3ADJC5      |                        |                                                                                                                                                                                                                       |                    |
| 12      | PH3ADJC6      |                        |                                                                                                                                                                                                                       |                    |
| 13      | OUT3DIVRSEL0  | Output 3               | OUTPUT DIVIDER 3 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT3DIVRSEL1  |                        |                                                                                                                                                                                                                       |                    |
| 15      | OUT3DIVRSEL2  |                        |                                                                                                                                                                                                                       |                    |
| 16      | OUT3DIVRSEL3  |                        |                                                                                                                                                                                                                       |                    |
| 17      | OUT3DIVRSEL4  |                        |                                                                                                                                                                                                                       |                    |
| 18      | OUT3DIVRSEL5  |                        |                                                                                                                                                                                                                       |                    |
| 19      | OUT3DIVRSEL6  |                        |                                                                                                                                                                                                                       |                    |
| 20      | EN3DIV        | Output 3               | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL3HISWING  | Output 3               | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA3CD1H   | CD1 High               | CD1 PIN is high and DIVPHA3CD1H is set to low<br>Loads Output Divider 3 and Phase Adjust 3 into OUTPUT 3<br>CD1 PIN is high and DIVPHA3CD1H is set to high<br>Loads Output Divider 4 and Phase Adjust 4 into OUTPUT 3 | EEPROM             |
| 23      | DIVPHA3CD1L   | CD1 Low                | CD1 PIN is Low and DIVPHA3CD1L is set to low<br>Loads Output Divider 3 and Phase Adjust 3 into OUTPUT 3<br>CD1 PIN is Low and DIVPHA3CD1L is set to high<br>Loads Output Divider 4 and Phase Adjust 4 into OUTPUT 3   | EEPROM             |
| 24      | OUTBUF3CD2LX  | CD2 Low                | Output Buffer 3 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF3CD2LY  |                        |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF3CD2HX  | CD2 High               | Output Buffer 3 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF3CD2HY  |                        |                                                                                                                                                                                                                       |                    |

**Register 4 Address 0x04: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|--------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | RESERVED     |               | Must be set '0'                                                                                                                                                                                                       | EEPROM             |
| 1       | RESERVED     |               | Must be set '0'                                                                                                                                                                                                       | EEPROM             |
| 2       | RESERVED     |               | Must be set '0'                                                                                                                                                                                                       | EEPROM             |
| 3       | RESERVED     |               | Must be set '0'                                                                                                                                                                                                       | EEPROM             |
| 4       | HOLDONLOR    | HOLD_OVER     | If set to 0, CP remains active and will discharge loop filter if input reference clock is lost.<br>If set to 1 it will 3-state the charge pump to act as a HOLD on Loss of Reference Clocks ( Primary and Secondary)  | EEPROM             |
| 5       | RESERVED     |               |                                                                                                                                                                                                                       | EEPROM             |
| 6       | PH4ADJC0     | Output 4      | Coarse phase adjust select for output divider 4                                                                                                                                                                       | EEPROM             |
| 7       | PH4ADJC1     |               |                                                                                                                                                                                                                       |                    |
| 8       | PH4ADJC2     |               |                                                                                                                                                                                                                       |                    |
| 9       | PH4ADJC3     |               |                                                                                                                                                                                                                       |                    |
| 10      | PH4ADJC4     |               |                                                                                                                                                                                                                       |                    |
| 11      | PH4ADJC5     |               |                                                                                                                                                                                                                       |                    |
| 12      | PH4ADJC6     |               |                                                                                                                                                                                                                       |                    |
| 13      | OUT4DIVRSEL0 | Output 4      | OUTPUT DIVIDER 4 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT4DIVRSEL1 |               |                                                                                                                                                                                                                       |                    |
| 15      | OUT4DIVRSEL2 |               |                                                                                                                                                                                                                       |                    |
| 16      | OUT4DIVRSEL3 |               |                                                                                                                                                                                                                       |                    |
| 17      | OUT4DIVRSEL4 |               |                                                                                                                                                                                                                       |                    |
| 18      | OUT4DIVRSEL5 |               |                                                                                                                                                                                                                       |                    |
| 19      | OUT4DIVRSEL6 |               |                                                                                                                                                                                                                       |                    |
| 20      | EN4DIV       | Output 4      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL4HISWING | Output 4      | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA4CD1H  | CD1 High      | CD1 PIN is high and DIVPHA4CD1H is set to low<br>Loads Output Divider 4 and Phase Adjust 4 into OUTPUT 4<br>CD1 PIN is high and DIVPHA4CD1H is set to high<br>Loads Output Divider 3 and Phase Adjust 3 into OUTPUT 4 | EEPROM             |
| 23      | DIVPHA4CD1L  | CD1 Low       | CD1 PIN is low and DIVPHA4CD1L is set to low<br>Loads Output Divider 4 and Phase Adjust 4 into OUTPUT 4<br>CD1 PIN is low and DIVPHA4CD1L is set to high<br>Loads Output Divider 3 and Phase Adjust 3 into OUTPUT 4   | EEPROM             |
| 24      | OUTBUF4CD2LX | CD2 Low       | Output Buffer 4 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF4CD2LY |               |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF4CD2HX | CD2 High      | Output Buffer 4 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF4CD2HY |               |                                                                                                                                                                                                                       |                    |

**Register 5 Address 0x05: CD Mode**

| RAM BIT | BIT NAME      | RELATED BLOCK          | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|---------------|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | BIAS_DIV45<0> | Output Divider 4 and 5 | When BIAS_DIV45<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30%                   | EEPROM             |
| 1       | BIAS_DIV45<1> |                        |                                                                                                                                                                                                                       |                    |
| 2       | BIAS_DIV67<0> | Output Divider 6 and 7 | When BIAS_DIV67<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30%                   | EEPROM             |
| 3       | BIAS_DIV67<1> |                        |                                                                                                                                                                                                                       |                    |
| 4       | RESERVED      |                        |                                                                                                                                                                                                                       | EEPROM             |
| 5       | RESERVED      |                        |                                                                                                                                                                                                                       | EEPROM             |
| 6       | PH5ADJC0      | Output 5               | Coarse phase adjust select for output divider 5                                                                                                                                                                       | EEPROM             |
| 7       | PH5ADJC1      |                        |                                                                                                                                                                                                                       |                    |
| 8       | PH5ADJC2      |                        |                                                                                                                                                                                                                       |                    |
| 9       | PH5ADJC3      |                        |                                                                                                                                                                                                                       |                    |
| 10      | PH5ADJC4      |                        |                                                                                                                                                                                                                       |                    |
| 11      | PH5ADJC5      |                        |                                                                                                                                                                                                                       |                    |
| 12      | PH5ADJC6      |                        |                                                                                                                                                                                                                       |                    |
| 13      | OUT5DIVRSEL0  | Output 5               | OUTPUT DIVIDER 5 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT5DIVRSEL1  |                        |                                                                                                                                                                                                                       |                    |
| 15      | OUT5DIVRSEL2  |                        |                                                                                                                                                                                                                       |                    |
| 16      | OUT5DIVRSEL3  |                        |                                                                                                                                                                                                                       |                    |
| 17      | OUT5DIVRSEL4  |                        |                                                                                                                                                                                                                       |                    |
| 18      | OUT5DIVRSEL5  |                        |                                                                                                                                                                                                                       |                    |
| 19      | OUT5DIVRSEL6  |                        |                                                                                                                                                                                                                       |                    |
| 20      | EN5DIV        | Output 5               | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL5HISWING  | Output 5               | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA5CD1H   | CD1 High               | CD1 PIN is high and DIVPHA5CD1H is set to low<br>Loads Output Divider 5 and Phase Adjust 5 into OUTPUT 5<br>CD1 PIN is high and DIVPHA5CD1H is set to high<br>Loads Output Divider 6 and Phase Adjust 6 into OUTPUT 5 | EEPROM             |
| 23      | DIVPHA5CD1L   | CD1 Low                | CD1 PIN is low and DIVPHA5CD1L is set to low<br>Loads Output Divider 5 and Phase Adjust 5 into OUTPUT 5<br>CD1 PIN is low and DIVPHA5CD1L is set to high<br>Loads Output Divider 6 and Phase Adjust 6 into OUTPUT 5   | EEPROM             |
| 24      | OUTBUF5CD2LX  | CD2 Low                | Output Buffer 5 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF5CD2LY  |                        |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF5CD2HX  | CD2 High               | Output Buffer 5 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF5CD2HY  |                        |                                                                                                                                                                                                                       |                    |

**Register6 Address 0x06: CD Mode**

| RAM BIT | BIT NAME         | RELATED BLOCK                     | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|------------------|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | FB_FD_DESEL      | LOCK-DET                          | 0 Feedback Frequency Detector is connected to the Lock Detector<br>1 Feedback Frequency Detector is disconnected from the Lock Detector                                                                               | EEPROM             |
| 1       | RESERVED         |                                   | Set to "0"                                                                                                                                                                                                            |                    |
| 2       | FBDTERM_DIV_SEL  | FB-Divider / Deterministic Blocks | 0 FB-Deterministic Clock divided by 1<br>1 FB- Deterministic Clock divided by 2                                                                                                                                       | EEPROM             |
| 3       | FBDTERM_DIV2_DIS |                                   | 0 FB-Deterministic-DIV2-Block in normal operation<br>1 FB-Deterministic-DIV2 reset (here REG6_RB<2> == "0")                                                                                                           |                    |
| 4       | FB_START_BYPASS  |                                   | 0 FB-Divider started with delay block (RC), normal operation<br>1 FB-Divider can be started with external REF_SEL-signal (pin)                                                                                        |                    |
| 5       | DET_START_BYPASS | All Output Dividers               | 0 Output-Dividers started with delay block (RC), normal operation<br>1 Output-Dividers can be started with external NRESET-signal (pin)                                                                               | EEPROM             |
| 6       | PH6ADJC0         | Output 6                          | Coarse phase adjust select for output divider 6                                                                                                                                                                       | EEPROM             |
| 7       | PH6ADJC1         |                                   |                                                                                                                                                                                                                       |                    |
| 8       | PH6ADJC2         |                                   |                                                                                                                                                                                                                       |                    |
| 9       | PH6ADJC3         |                                   |                                                                                                                                                                                                                       |                    |
| 10      | PH6ADJC4         |                                   |                                                                                                                                                                                                                       |                    |
| 11      | PH6ADJC5         |                                   |                                                                                                                                                                                                                       |                    |
| 12      | PH6ADJC6         |                                   |                                                                                                                                                                                                                       |                    |
| 13      | OUT6DIVRSEL0     | Output 6                          | OUTPUT DIVIDER 6 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT6DIVRSEL1     |                                   |                                                                                                                                                                                                                       |                    |
| 15      | OUT6DIVRSEL2     |                                   |                                                                                                                                                                                                                       |                    |
| 16      | OUT6DIVRSEL3     |                                   |                                                                                                                                                                                                                       |                    |
| 17      | OUT6DIVRSEL4     |                                   |                                                                                                                                                                                                                       |                    |
| 18      | OUT6DIVRSEL5     |                                   |                                                                                                                                                                                                                       |                    |
| 19      | OUT6DIVRSEL6     |                                   |                                                                                                                                                                                                                       |                    |
| 20      | EN6DIV           | Output 6                          | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL6HISWING     | Output 6                          | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA6CD1H      | CD1 High                          | CD1 PIN is high and DIVPHA6CD1H is set to low<br>Loads Output Divider 6 and Phase Adjust 6 into OUTPUT 6<br>CD1 PIN is high and DIVPHA6CD1H is set to high<br>Loads Output Divider 5 and Phase Adjust 5 into OUTPUT 6 | EEPROM             |
| 23      | DIVPHA6CD1L      | CD1 Low                           | CD1 PIN is low and DIVPHA6CD1L is set to low<br>Loads Output Divider 6 and Phase Adjust 6 into OUTPUT 6<br>CD1 PIN is low and DIVPHA6CD1L is set to high<br>Loads Output Divider 5 and Phase Adjust 5 into OUTPUT 6   | EEPROM             |
| 24      | OUTBUF6CD2LX     | CD2 Low                           | Output Buffer 6 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF6CD2LY     |                                   |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF6CD2HX     | CD2 High                          | Output Buffer 6 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF6CD2HY     |                                   |                                                                                                                                                                                                                       |                    |

**Table 9. Register 7 Address 0x07: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|--------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | LOCKW 0      | LOCK-DET      | Lock-detect window bit 0 (Refer to Reg 9 Bits 6 and 7)                                                                                                                                                                | EEPROM             |
| 1       | LOCKW 1      |               | Lock-detect window bit 1 (Refer to Reg 9 Bits 6 and 7)                                                                                                                                                                |                    |
| 2       | RESERVED     |               | Set to 0                                                                                                                                                                                                              |                    |
| 3       | LOCKC0       |               | Number of coherent lock events bit 0                                                                                                                                                                                  |                    |
| 4       | LOCKC1       |               | Number of coherent lock events bit 1                                                                                                                                                                                  |                    |
| 5       | ADLOCK       |               | Selects Digital PLL_LOCK 0 ,Selects Analog PLL_LOCK 1                                                                                                                                                                 |                    |
| 6       | PH7ADJC0     | Output 7      | Coarse phase adjust select for output divider 7                                                                                                                                                                       | EEPROM             |
| 7       | PH7ADJC1     |               |                                                                                                                                                                                                                       |                    |
| 8       | PH7ADJC2     |               |                                                                                                                                                                                                                       |                    |
| 9       | PH7ADJC3     |               |                                                                                                                                                                                                                       |                    |
| 10      | PH7ADJC4     |               |                                                                                                                                                                                                                       |                    |
| 11      | PH7ADJC5     |               |                                                                                                                                                                                                                       |                    |
| 12      | PH7ADJC6     |               |                                                                                                                                                                                                                       |                    |
| 13      | OUT7DIVRSEL0 | Output 7      | OUTPUT DIVIDER 7 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                       | EEPROM             |
| 14      | OUT7DIVRSEL1 |               |                                                                                                                                                                                                                       |                    |
| 15      | OUT7DIVRSEL2 |               |                                                                                                                                                                                                                       |                    |
| 16      | OUT7DIVRSEL3 |               |                                                                                                                                                                                                                       |                    |
| 17      | OUT7DIVRSEL4 |               |                                                                                                                                                                                                                       |                    |
| 18      | OUT7DIVRSEL5 |               |                                                                                                                                                                                                                       |                    |
| 19      | OUT7DIVRSEL6 |               |                                                                                                                                                                                                                       |                    |
| 20      | EN7DIV       | Output 7      | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL7HISWING | Output 7      | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA7CD1H  | CD1 High      | CD1 PIN is high and DIVPHA7CD1H is set to low<br>Loads Output Divider 7 and Phase Adjust 7 into OUTPUT 7<br>CD1 PIN is high and DIVPHA7CD1H is set to high<br>Loads Output Divider 8 and Phase Adjust 8 into OUTPUT 7 | EEPROM             |
| 23      | DIVPHA7CD1L  | CD1 Low       | CD1 PIN is low and DIVPHA7CD1L is set to low<br>Loads Output Divider 7 and Phase Adjust 7 into OUTPUT 7<br>CD1 PIN is low and DIVPHA7CD1L is set to high<br>Loads Output Divider 8 and Phase Adjust 8 into OUTPUT 7   | EEPROM             |
| 24      | OUTBUF7CD2LX | CD2 Low       | Output Buffer 7 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF7CD2LY |               |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF7CD2HX | CD2 High      | Output Buffer 7 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF7CD2HY |               |                                                                                                                                                                                                                       |                    |

**Register 8 Address 0x08: CD Mode**

| RAM BIT | BIT NAME     | RELATED BLOCK                                   | DESCRIPTION/FUNCTION                                                                                                                                                                                                  | POWER UP CONDITION |
|---------|--------------|-------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | VCXOBUFSELX  | VCXO and AUX Input Buffers<br>VCXO Input Buffer | VCXO and AUX Input Buffer Type Select (LVPECL, LVDS or LVCMOS)                                                                                                                                                        | EEPROM             |
| 1       | VCXOBUFSELY  |                                                 | XY(10) LVPECL, (11) LVDS, (00) LVCMOS- Input is Positive Pin                                                                                                                                                          |                    |
| 2       | VCXOACDCSEL  |                                                 | If Set to 0 AC Termination, If set to 1 DC Termination                                                                                                                                                                |                    |
| 3       | VCXOHYSTEN   |                                                 | If Set to 1 Input Buffers Hysteresis enabled                                                                                                                                                                          |                    |
| 4       | VCXOTERMSEL  |                                                 | If Set to 0 Input Buffer Internal Termination enabled                                                                                                                                                                 |                    |
| 5       | VCXOINVBB    | VCXO Input Buffer                               | If Set to 1 It biases VCXO Input negative pin with internal VCXOVBB voltage                                                                                                                                           | EEPROM             |
| 6       | PH8ADJC0     | Output 8 and 9                                  | Coarse phase adjust select for output divider 8 and 9                                                                                                                                                                 | EEPROM             |
| 7       | PH8ADJC1     |                                                 |                                                                                                                                                                                                                       |                    |
| 8       | PH8ADJC2     |                                                 |                                                                                                                                                                                                                       |                    |
| 9       | PH8ADJC3     |                                                 |                                                                                                                                                                                                                       |                    |
| 10      | PH8ADJC4     |                                                 |                                                                                                                                                                                                                       |                    |
| 11      | PH8ADJC5     |                                                 |                                                                                                                                                                                                                       |                    |
| 12      | PH8ADJC6     |                                                 |                                                                                                                                                                                                                       |                    |
| 13      | OUT8DIVRSEL0 | Output 8 and 9                                  | OUTPUT DIVIDER 8 and 9 Ratio Select<br>(See <a href="#">Table 8</a> )                                                                                                                                                 | EEPROM             |
| 14      | OUT8DIVRSEL1 |                                                 |                                                                                                                                                                                                                       |                    |
| 15      | OUT8DIVRSEL2 |                                                 |                                                                                                                                                                                                                       |                    |
| 16      | OUT8DIVRSEL3 |                                                 |                                                                                                                                                                                                                       |                    |
| 17      | OUT8DIVRSEL4 |                                                 |                                                                                                                                                                                                                       |                    |
| 18      | OUT8DIVRSEL5 |                                                 |                                                                                                                                                                                                                       |                    |
| 19      | OUT8DIVRSEL6 |                                                 |                                                                                                                                                                                                                       |                    |
| 20      | EN89DIV      | Output 8 and 9                                  | When set to 0, the divider is disabled<br>When set to 1, the divider is enabled                                                                                                                                       | EEPROM             |
| 21      | PECL8HISWING | Output 8                                        | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                             | EEPROM             |
| 22      | DIVPHA8CD1H  | CD1 High                                        | CD1 PIN is high and DIVPHA8CD1H is set to low<br>Loads Output Divider 8 and Phase Adjust 8 into OUTPUT 8<br>CD1 PIN is high and DIVPHA8CD1H is set to high<br>Loads Output Divider 7 and Phase Adjust 7 into OUTPUT 8 | EEPROM             |
| 23      | DIVPHA8CD1L  | CD1 Low                                         | CD1 PIN is low and DIVPHA8CD1L is set to low<br>Loads Output Divider 8 and Phase Adjust 8 into OUTPUT 8<br>CD1 PIN is low and DIVPHA8CD1L is set to high<br>Loads Output Divider 7 and Phase Adjust 7 into OUTPUT 8   | EEPROM             |
| 24      | OUTBUF8CD2LX | CD2 Low                                         | Output Buffer 8 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                   | EEPROM             |
| 25      | OUTBUF8CD2LY |                                                 |                                                                                                                                                                                                                       |                    |
| 26      | OUTBUF8CD2HX | CD2 High                                        | Output Buffer 8 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                  | EEPROM             |
| 27      | OUTBUF8CD2HY |                                                 |                                                                                                                                                                                                                       |                    |

**Register 9 Address 0x09: CD Mode**

| RAM BIT | BIT NAME         | RELATED BLOCK                      | DESCRIPTION/FUNCTION                                                                                                                                                                                                                                                | POWER UP CONDITION |
|---------|------------------|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | HOLDF1           | HOLD- Over                         | Enables the Frequency Hold-Over Function 1 on 1, off 0                                                                                                                                                                                                              | EEPROM             |
| 1       | HOLDF2           |                                    | Enables the Frequency Hold-Over Function 2 on 1, off 0                                                                                                                                                                                                              |                    |
| 2       | HOLD             |                                    | 3-State Charge Pump 0 - (equal to HOLD-Pin function)                                                                                                                                                                                                                |                    |
| 3       | HOLDTR           |                                    | HOLD function always activated “1” (recommended for test purposes, only)<br>Triggered by analog PLL Lock detect outputs<br>If analog PLL Lock Signal is [1] (PLL locked), HOLD is activated<br>If analog PLL Lock Signal is [0] (PLL not lock), HOLD is deactivated |                    |
| 4       | HOLD_CNT0        |                                    | HOLD1 Function is reactivated after X Ref Clock Cycles. Defined by (HOLD_CNT0,HOLD_CNT1)::X= Number of Clock Cycles.<br>For (00)::X=64, (01) ::X=128, (10)::X=256, (11)::X=512 Clock Cycles.                                                                        |                    |
| 5       | HOLD_CNT1        |                                    |                                                                                                                                                                                                                                                                     |                    |
| 6       | LOCKW 2          | LOCK-DET                           | Extended Lock-detect window Bit 2 (Also refer to Reg 7 Bits 0 and 1)                                                                                                                                                                                                | EEPROM             |
| 7       | LOCKW 3          |                                    | Extended Lock-detect window Bit 3 (Also refer to Reg 7 Bits 0 and 1)                                                                                                                                                                                                |                    |
| 8       | NOINV_RESHOL_INT | Chip CORE                          | When set to 0, SPI/HOLD_INT and SPI/RESET_INT inverted (default)<br>When set to 1, SPI/HOLD_INT and SPI/RESET_INT not inverted                                                                                                                                      | EEPROM             |
| 9       | DIVSYNC_DIS      | <i>Diagnostic: PLL N/M Divider</i> | <i>When GTME = 0, this bit has no functionality, But when GTME = 1, then:<br/>When set to 0, START-Signal is synchronized to N/M Divider Input Clocks<br/>When set to 1, START-Sync N/M Divider in PLL are bypassed</i>                                             | EEPROM             |
| 10      | START_BYPASS     | Divider START DETERM-Block         | When set to 0, START-Signal is synchronized to VCXO-Clock<br>When set to 1, START-Sync Block is bypassed                                                                                                                                                            | EEPROM             |
| 11      | INDET_BP         | Divider START DETERM-Block         | When set to 0, Sync Logic active when VCXO/AUX-Clocks are available<br>When set to 1, Sync Logic is independent from VCXO- and/or AUX-Clocks                                                                                                                        | EEPROM             |
| 12      | PLL_LOCK_BP      | Divider START DETERM-Block         | When set to 0, Sync Logic waits for 1st PLL_LOCK state<br>When set to 1, Sync Logic independent from 1st PLL_LOCK                                                                                                                                                   | EEPROM             |
| 13      | LOW_FD_FB_EN     | Divider START DETERM-Block         | When set to 0, Sync Logic is independent from VCXO/DIV_FB freq. (PLL-FD)<br>When set to 1, Sync Logic is started for VCXO/DIV_FB > ~600KHz, stopped for VCXO/DIV_FB < ~600KHz                                                                                       | EEPROM             |
| 14      | NPRESET_MDIV     | PLL M/FB-Divider                   | When set to 0, M-Divider uses NHOLD1 as NPRESET<br>When set to 1, M-Divider NOT preseted by NHOLD1                                                                                                                                                                  | EEPROM             |
| 15      | BIAS_DIV_FB<0>   | Feedback Divider                   | When BIAS_DIV_FB<1:0> =<br>00, No current reduction for FB-Divider<br>01, Current reduction for FB-Divider by about 20%<br>10, Current reduction for FB-Divider by about 30%                                                                                        | EEPROM             |
| 16      | BIAS_DIV_FB<1>   |                                    |                                                                                                                                                                                                                                                                     |                    |
| 17      | BIAS_DIV89<0>    | Output Divider 8 and 9             | When BIAS_DIV89<1:0> =<br>00, No current reduction for all output-divider<br>01, Current reduction for all output-divider by about 20%<br>10, Current reduction for all output-divider by about 30%                                                                 | EEPROM             |
| 18      | BIAS_DIV89<1>    |                                    |                                                                                                                                                                                                                                                                     |                    |
| 19      | AUXINVBB         | AUX Buffer                         | If Set to 1 it Biases AUX Input Negative Pin with internal VCXOVBB voltage.                                                                                                                                                                                         | EEPROM             |
| 20      | DIS_AUX_Y9       |                                    | If Set to 1 AUX in input Mode Buffer is disabled. If Set to 0 it follows the behavior of FB_MUX_SEL and OUT_MUX_SEL bits settings.                                                                                                                                  |                    |
| 21      | PECL9HISWING     | Output 9                           | High Output Voltage Swing in LVPECL/LVDS Mode if set to 1                                                                                                                                                                                                           | EEPROM             |
| 22      | RESERVED         |                                    |                                                                                                                                                                                                                                                                     | EEPROM             |
| 23      | RESERVED         |                                    |                                                                                                                                                                                                                                                                     | EEPROM             |
| 24      | OUTBUF9CD2LX     | CD2 Low                            | Output Buffer 9 Signaling Selection when CD2 in low<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                                                                 | EEPROM             |
| 25      | OUTBUF9CD2LY     |                                    |                                                                                                                                                                                                                                                                     |                    |
| 26      | OUTBUF9CD2HX     | CD2 High                           | Output Buffer 9 Signaling Selection when CD2 in high<br>(X,Y) = 01: LVPECL, 11: LVDS, 00: LVCMOS, 10: Output Disable                                                                                                                                                | EEPROM             |
| 27      | OUTBUF9CD2HY     |                                    |                                                                                                                                                                                                                                                                     |                    |



**Register 10 Address 0x0A: CD Mode**

| RAM BIT | BIT NAME | RELATED BLOCK                 | DESCRIPTION/FUNCTION       | POWER UP CONDITION |
|---------|----------|-------------------------------|----------------------------|--------------------|
| 0       | M0       | Reference (PRI/SEC) Divider M | Reference Divider M bit 0  | EEPROM             |
| 1       | M1       |                               | Reference Divider M bit 1  |                    |
| 2       | M2       |                               | Reference Divider M bit 2  |                    |
| 3       | M3       |                               | Reference Divider M bit 3  |                    |
| 4       | M4       |                               | Reference Divider M bit 4  |                    |
| 5       | M5       |                               | Reference Divider M bit 5  |                    |
| 6       | M6       |                               | Reference Divider M bit 6  |                    |
| 7       | M7       |                               | Reference Divider M bit 7  |                    |
| 8       | M8       |                               | Reference Divider M bit 8  |                    |
| 9       | M9       |                               | Reference Divider M bit 9  |                    |
| 10      | M10      |                               | Reference Divider M bit 10 |                    |
| 11      | M11      |                               | Reference Divider M bit 11 |                    |
| 12      | M12      |                               | Reference Divider M bit 12 |                    |
| 13      | M13      |                               | Reference Divider M bit 13 |                    |
| 14      | N0       | VCXO/AUX/SEC Divider N        | VCXO Divider N bit 0       | EEPROM             |
| 15      | N1       |                               | VCXO Divider N bit 1       |                    |
| 16      | N2       |                               | VCXO Divider N bit 2       |                    |
| 17      | N3       |                               | VCXO Divider N bit 3       |                    |
| 18      | N4       |                               | VCXO Divider N bit 4       |                    |
| 19      | N5       |                               | VCXO Divider N Bit 5       |                    |
| 20      | N6       |                               | VCXO Divider N Bit 6       |                    |
| 21      | N7       |                               | VCXO Divider N Bit 7       |                    |
| 22      | N8       |                               | VCXO Divider N Bit 8       |                    |
| 23      | N9       |                               | VCXO Divider N Bit 9       |                    |
| 24      | N10      |                               | VCXO Divider N Bit 10      |                    |
| 25      | N11      |                               | VCXO Divider N Bit 11      |                    |
| 26      | N12      |                               | VCXO Divider N Bit 12      |                    |
| 27      | N13      |                               | VCXO Divider N Bit 13      |                    |

**Register 11 Address 0x0B: CD Mode**

| RAM BIT | BIT NAME                                | RELATED BLOCK                          | DESCRIPTION/FUNCTION                                                                                                                                       | POWER UP CONDITION |
|---------|-----------------------------------------|----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 0       | PRI_DIV2                                | Input Buffers                          | If set to 1 Enables Primary Reference Divide by 2                                                                                                          | EEPROM             |
| 1       | SEC_DIV2                                | Input Buffers                          | If set to 1 Enables Secondary Reference Divide by 2                                                                                                        | EEPROM             |
| 2       | FB_DIS                                  | FB Path Integer Counter 32             | When set to 0, FB divider is active<br>When set to 1, FB divider is disabled                                                                               | EEPROM             |
| 3       | FB_CML_SEL                              | FB Path Integer Counter 32             | When set to 0, FB clock is CMOS type<br>When set to 1, FB clock is CML type and uses CML2CMOS converter in PLL                                             | EEPROM             |
| 4       | FB_INCLK_INV                            | FB-Divider / Deterministic Blocks      | When set to 0, Input clock for FB not inverted (normal mode, low speed)<br>When set to 1, Input clock for FB inverted (higher speed mode)                  | EEPROM             |
| 5       | FB_COUNT32_0                            | FB Path Integer Counter 32 (P divider) | Feedback Counter Bit0                                                                                                                                      | EEPROM             |
| 6       | FB_COUNT32_1                            |                                        | Feedback Counter Bit1                                                                                                                                      |                    |
| 7       | FB_COUNT32_2                            |                                        | Feedback Counter Bit2                                                                                                                                      |                    |
| 8       | FB_COUNT32_3                            |                                        | Feedback Counter Bit3                                                                                                                                      |                    |
| 9       | FB_COUNT32_4                            |                                        | Feedback Counter Bit4                                                                                                                                      |                    |
| 10      | FB_COUNT32_5                            |                                        | Feedback Counter Bit5                                                                                                                                      |                    |
| 11      | FB_COUNT32_6                            |                                        | Feedback Counter Bit6                                                                                                                                      |                    |
| 12      | FB_PHASE0                               | FB Path Integer Counter 32 (P Divider) | Feedback Phase Adjust Bit0                                                                                                                                 | EEPROM             |
| 13      | FB_PHASE1                               |                                        | Feedback Phase Adjust Bit1                                                                                                                                 |                    |
| 14      | FB_PHASE2                               |                                        | Feedback Phase Adjust Bit2                                                                                                                                 |                    |
| 15      | FB_PHASE3                               |                                        | Feedback Phase Adjust Bit3                                                                                                                                 |                    |
| 16      | FB_PHASE4                               |                                        | Feedback Phase Adjust Bit4                                                                                                                                 |                    |
| 17      | FB_PHASE5                               |                                        | Feedback Phase Adjust Bit5                                                                                                                                 |                    |
| 18      | FB_PHASE6                               |                                        | Feedback Phase Adjust Bit6                                                                                                                                 |                    |
| 19      | PD_PLL                                  | PLL                                    | If set to 0, PLL is in normal mode<br>If set to 1, PLL is powered down                                                                                     | EEPROM             |
| 20      | FB_MUX_SEL<br><a href="#">Table 10</a>  | Clock Tree and Deterministic Block     | When set to 0, the VCXO Clock is selected for the Clock Tree and FB-Div/Det<br>When set to 1, the AUX Clock is selected for the Clock Tree and FB-Div/Det. | EEPROM             |
| 21      | OUT_MUX_SEL<br><a href="#">Table 10</a> |                                        | If Set to 0 it selects the VCXO Clock and if Set to 1 it selects the AUX Clock                                                                             | EEPROM             |
| 22      | FB_SEL                                  | Diagnostics                            | Feed Back Path Selects FB/VCXO-Path when set to 0 (TI Test-GTME)<br>The Secondary Reference clock input is selected when set to 1 (TI Test-GTME)           | EEPROM             |
| 23      | NRESHAPE1                               | Reference Selection Control            | Reshapes the Reference Clock Signal 0, Disable Reshape 1                                                                                                   | EEPROM             |
| 24      | SEL_DEL1                                |                                        | If set to 0 it enables short delay for fast operation<br>If Set to 1 Long Delay recommended for input references below 150Mhz.                             |                    |
| 25      | RESET_HOLD                              | Reset Circuitry                        | If set to 1 the RESET or HOLD pin acts as $\overline{\text{HOLD}}$ , set to 0 it acts as $\overline{\text{RESET}}$ .                                       | EEPROM             |
| 26      | EPLOCK                                  | Status                                 | Read only. If EPLOCK reads a 0, the EEPROM is unlocked. If EPLOCK reads a 1, then the EEPROM is locked.                                                    | EEPROM             |
| 27      | EPSTATUS                                | Status                                 | EEPROM Status                                                                                                                                              | EEPROM             |

**Table 10. Output Buffers Source Feed, PLL Source Feed, and AUX IN/OUTPUT 9 Selection**

| FB_MUX_SEL | OUT_MUX_SEL | PLL FEED AND OUTPUT FEED                           | AUX INPUT OR OUTPUT 9              |
|------------|-------------|----------------------------------------------------|------------------------------------|
| 0          | 0           | VCXO::PLL, VCXO::Y0...Y9 and Deterministic Block   | OUTPUT 9 is Enabled <sup>(1)</sup> |
| 1          | 0           | AUXIN::PLL, VCXO::Y0...Y8 and Deterministic Block  | AUX IN is Enabled                  |
| 0          | 1           | VCXO::PLL, AUXIN::Y0...Y8 and Deterministic Block  | AUX IN is Enabled                  |
| 1          | 1           | AUXIN::PLL, AUXIN::Y0...Y8 and Deterministic Block | AUX IN is Enabled                  |

(1) Default


## INTERFACE, CONFIGURATION, AND CONTROL

The CDCE72010 is designed to support various applications with SPI bus interface and without. In the case where systems lack the SPI bus or a Boot up configuration is required at start up before the management layer is up the built in EEPROM is used to provide this function.

The Interface bus takes the serialized address and data and writes to the specified Register bits. The content of the RAM bits are connected to logical functions in the device. Changing the content of the Register bits (high or low) instantly changes the logical functions inside the device.

At power up or after power down is de-asserted the contents of the EEPROM bits are copied to their corresponding Register bits. After that the content of Register can be changed via the SPI bus. When writing to EEPROM commands are detected on the SPI bus the control logic begins writing the content of the Register bits into the corresponding EEPROM bits. This process takes about 50ms. During this time the power supply should be above 3.2V.

The on-chip EEPROM can be operated in its unlocked or locked mode. An unlocked EEPROM indicates that the stored bit values can be changed on another EEPROM write sequence (available for up to a 100 EEPROM write sequences). A locked EEPROM indicates that the stored bit values cannot be changed on another EEPROM write sequence.




**Figure 20. Interface Control**

## UNIVERSAL INPUT AND REFERENCE CLOCK BUFFERS

The CDCE72010 is designed to support what is referred to as a Universal Input Buffer structure. This type of buffer is designed to accept Differential or single ended inputs and it is sensitive enough to act as a LVPECL or LVDS in differential mode and LVCMOS in Single ended mode. With the proper external termination various types of inputs signals can be supported.

The CDCE72010 has two internal voltage biasing circuitries. One to set the termination voltage for references (PRI\_REF and SEC\_REF) and the second biasing circuitry is to set the termination voltage to the VCXO\_IN and AUX\_IN. This means that we can only have one type of differential signal on PRI\_REF and SEC\_REF and only one type of differential signal on VCXO\_IN and AUX\_IN.



**Figure 21. CDCE72010 REF Voltage Biasing Circuitry**

VCXO & AUX Input Buffer Settings

| Settings |     |     |     |     |          | Configuration |         |      |          |      |
|----------|-----|-----|-----|-----|----------|---------------|---------|------|----------|------|
| 8.0      | 8.1 | 8.2 | 8.3 | 8.4 | 8.5/9.19 | Hyst          | Mode    | Coup | Term     | Vbb  |
| 0        | 0   | X   | 1   | X   | X        | ON            | LVC MOS | DC   | N/A      | --   |
| 1        | 0   | 0   | 1   | 0   | 0        | ON            | LVPECL  | AC   | Internal | 1.9V |
| 1        | 0   | 1   | 1   | 0   | 0        | ON            | LVPECL  | DC   | Internal | 1.2V |
| 1        | 0   | X   | 1   | 1   | X        | ON            | LVPECL  | --   | External | --   |
| 1        | 1   | 0   | 1   | 0   | 0        | ON            | LVDS    | AC   | Internal | 1.2V |
| 1        | 1   | 1   | 1   | 0   | 0        | ON            | LVDS    | DC   | Internal | 1.2V |
| 1        | 1   | X   | 1   | 1   | X        | ON            | LVDS    | --   | External | --   |
| X        | X   | X   | 0   | X   | X        | OFF           | --      | --   | --       | --   |
| X        | X   | X   | 1   | X   | X        | ON            | --      | --   | --       | --   |

AUX\_IN Input Buffer Settings

| Register / Bits |     |     |      | Switch |   |     |
|-----------------|-----|-----|------|--------|---|-----|
| 8.0             | 8.1 | 8.4 | 9.19 | P      | N | INV |
| 0               | 0   | X   | X    | O      | O | O   |
| X               | X   | 1   | X    | O      | O | O   |
| X               | 1   | 0   | 0    | C      | C | C   |
| X               | 1   | 0   | 1    | C      | C | O   |

VCXO Input Buffer Settings

| Register / Bits |     |     |     | Switch |   |     |
|-----------------|-----|-----|-----|--------|---|-----|
| 8.0             | 8.1 | 8.4 | 8.5 | P      | N | INV |
| 0               | 0   | X   | X   | O      | O | O   |
| X               | X   | 1   | X   | O      | O | O   |
| X               | 1   | 0   | 0   | C      | C | C   |
| X               | 1   | 0   | 1   | C      | C | O   |

O - OPEN    C - CLOSED

O - OPEN C - CLOSED

NOTE: Using INV switch, negative input can be biased properly (either 1.2V or 1.9V) and single ended clock signal (whose common mode is already set to either 1.2V for LVDS clock or 1.9V for LVPECL clock) can be applied to positive input.

Figure 22. CDCE72010 Inputs Configuration

### AUTOMATIC/MANUAL REFERENCE CLOCK SWITCHING (SMART MUX)

The CDCE72010 supports two reference clock inputs, the primary clock input, PRI\_REF, and the secondary clock input, SEC\_REF. The clocks can be selected manually or automatically. The respective mode is selected by the dedicated register. In the manual mode the external REF\_SEL signal selects one of the two input clocks

In the automatic mode the primary clock is selected by default even if both clocks are available. In case the primary clock is not available or fails, then the input switches to the secondary clock until the primary clock is back. The figure below shows the automatic clock selection.




Figure 23. Automatic Clock Select Timing

In the automatic mode the frequencies of both clock signals has to be similar but may differ by up to 20%. There is no limitation placed on the phase relationship between the two inputs.

The clock input circuitry is designed to suppress glitches during switching between the primary and secondary clock in the manual and automatic mode. This insures that the clock outputs continue to clock reliably when a transition from a clock input occurs.

The phase of the output clock will slowly follow the new input phase. The speed of this transition is determined by the loop bandwidth. However, there is no phase build-out function supported (like in SONET/SDH applications).

## PHASE FREQUENCY DETECTOR

The main function of the CDCE72010 device is to synchronize a Voltage Control Oscillator (VCO) or a Voltage Control Crystal Oscillator (VCXO) output to a reference clock input. The phase detector compares 2 signals and outputs the difference between them. It is symbolized by an XOR. The compared signals are derived from the Reference clock and from the VCO/VCXO clocks. The Reference clock is divided by the “R” Divider (1 or 2) and “M” divider (14 Bits) and presented to the PFD. The VCO/VCXO clock is divided by the Feedback Divider “P” (1 to 80) and the “N” Divider (14 Bits) and presented to the PFD.

$$\text{Frequency (VCXO\_IN or AUX\_IN)} / \text{Frequency (PRI\_REF or SEC\_REF)} = (P*N)/(R*M)$$

The PFD is a classical style with UP and DOWN signals generating flip-flops and a common reset path. Some special functions were implemented:

- Bit CP\_DIR (register 0 bit<9> can swap internally the REF- and FB-CLK inputs to the PFD flip-flops.
- The reset path can be typically delayed with the bits DELAY\_PFD <1:0> (register 0 bit<7:6>) from 1.5ns to 6.0ns.

### PFD Pulse Width Delay (Register 0 Bits [7:6])

The “PFD pulse width delay” gets around the dead zone of the PFD transfer function and reduces phase noise and reference spurs.

Table 11. PFD Pulse Width Delay

| PFD1 | PFD0 | PFD PULSE WIDTH DELAY |
|------|------|-----------------------|
| 0    | 0    | 1.5ns <sup>(1)</sup>  |
| 0    | 1    | 3.0ns                 |
| 1    | 0    | 4.5ns                 |
| 1    | 1    | 6.0ns                 |

(1) Default

The PFD receives two clocks of the similar frequencies and decides if one is lagging or leading. This Lagging/Leading signals are feed to the Charge Pump. The Charge Pump in its turn takes the Lagging/Leading signals and translate them into current pulses that are feed to the external filter. The Output of the external filter is a DC level that controls the Voltage reference of the VCO/VCXO sitting outside and feeding the CDCE72010 at the VCXO Input. The VCO/VCXO drifts its outputs frequency with respect to the voltage applied to its Voltage Control pin. This is how the loop is closed.




Figure 24. Phase Frequency Detection

**Table 12. Feedback Divider Settings**

| FEEDBACK DIVIDER SETTINGS (REGISTER 11: BITS) |    |   |   |   |   |   | DIVIDER<br>SETTING |
|-----------------------------------------------|----|---|---|---|---|---|--------------------|
| 11                                            | 10 | 9 | 8 | 7 | 6 | 5 |                    |
| 0                                             | 1  | 0 | 0 | 0 | 0 | 0 | 1                  |
| 1                                             | 0  | 0 | 0 | 0 | 0 | 0 | 2                  |
| 1                                             | 0  | 0 | 0 | 0 | 0 | 1 | 3                  |
| 1                                             | 0  | 0 | 0 | 0 | 1 | 0 | 4                  |
| 1                                             | 0  | 0 | 0 | 0 | 1 | 1 | 5                  |
| 0                                             | 0  | 0 | 0 | 0 | 0 | 0 | 4'                 |
| 0                                             | 0  | 0 | 0 | 0 | 0 | 1 | 6                  |
| 0                                             | 0  | 0 | 0 | 0 | 1 | 0 | 8                  |
| 0                                             | 0  | 0 | 0 | 0 | 1 | 1 | 10                 |
| 0                                             | 0  | 0 | 0 | 1 | 0 | 0 | 8'                 |
| 0                                             | 0  | 0 | 0 | 1 | 0 | 1 | 12                 |
| 0                                             | 0  | 0 | 0 | 1 | 1 | 0 | 16                 |
| 0                                             | 0  | 0 | 0 | 1 | 1 | 1 | 20                 |
| 0                                             | 0  | 0 | 1 | 0 | 0 | 0 | 12'                |
| 0                                             | 0  | 0 | 1 | 0 | 0 | 1 | 18                 |
| 0                                             | 0  | 0 | 1 | 0 | 1 | 0 | 24                 |
| 0                                             | 0  | 0 | 1 | 0 | 1 | 1 | 30                 |
| 0                                             | 0  | 0 | 1 | 1 | 0 | 0 | 16'                |
| 0                                             | 0  | 0 | 1 | 1 | 0 | 1 | 24'                |
| 0                                             | 0  | 0 | 1 | 1 | 1 | 0 | 32                 |
| 0                                             | 0  | 0 | 1 | 1 | 1 | 1 | 40                 |
| 0                                             | 0  | 1 | 0 | 0 | 0 | 0 | 20'                |
| 0                                             | 0  | 1 | 0 | 0 | 0 | 1 | 30'                |
| 0                                             | 0  | 1 | 0 | 0 | 1 | 0 | 40'                |
| 0                                             | 0  | 1 | 0 | 0 | 1 | 1 | 50                 |
| 0                                             | 0  | 1 | 0 | 1 | 0 | 0 | 24'                |
| 0                                             | 0  | 1 | 0 | 1 | 0 | 1 | 36                 |
| 0                                             | 0  | 1 | 0 | 1 | 1 | 0 | 48                 |
| 0                                             | 0  | 1 | 0 | 1 | 1 | 1 | 60                 |
| 0                                             | 0  | 1 | 1 | 0 | 0 | 0 | 28                 |
| 0                                             | 0  | 1 | 1 | 0 | 0 | 1 | 42                 |
| 0                                             | 0  | 1 | 1 | 0 | 1 | 0 | 56                 |
| 0                                             | 0  | 1 | 1 | 0 | 1 | 1 | 70                 |
| 0                                             | 0  | 1 | 1 | 1 | 0 | 0 | 32'                |
| 0                                             | 0  | 1 | 1 | 1 | 0 | 1 | 48'                |
| 0                                             | 0  | 1 | 1 | 1 | 1 | 0 | 64                 |
| 0                                             | 0  | 1 | 1 | 1 | 1 | 1 | 80                 |

## PHASE DELAY FOR M AND N

### Delay Block in M/N Path

**Table 13. Reference Delay M (PRI\_REF or SEC\_REF) and Feedback Delay N (VCXO) Phase Adjustment (Register 2 Bits [5:0])** <sup>(1)</sup>

| DLYM2/DLYN2 | DLYM1/DLYN1 | DLYM0/DLYN0 | PHASE OFFSET       |
|-------------|-------------|-------------|--------------------|
| 0           | 0           | 0           | 0ps <sup>(2)</sup> |
| 0           | 0           | 1           | ±160ps             |
| 0           | 1           | 0           | ±320ps             |
| 0           | 1           | 1           | ±480ps             |
| 1           | 0           | 0           | ±830ps             |
| 1           | 0           | 1           | ±1130ps            |
| 1           | 1           | 0           | ±1450ps            |
| 1           | 1           | 1           | ±1750ps            |

(1) If Progr Delay M is set, all Yx outputs are lagging to the Reference Clock according to the value set. If Progr Delay N is set, all Yx outputs are leading to the Reference Clock according to the value set. Above are typical values at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C, PECL-output relate to Div4 mode.

(2) Default

**Table 14. Input and Feedback Divider: 14-Bit (Register 10 Bits [13:0] for M and Bits [27:14] for N)**

| N13 | N12 | N11 | N10 | N9 | N8 | N7 | N6 | N5 | N4 | N3 | N2 | N1 | N0 | DIV BY <sup>(1)</sup> |
|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|-----------------------|
| 0   | 0   | 0   | 0   | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1                     |
| 0   | 0   | 0   | 0   | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1  | 2                     |
| 0   | 0   | 0   | 0   | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1  | 0  | 3                     |
| 0   | 0   | 0   | 0   | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 0  | 1  | 1  | 4                     |
|     |     |     |     |    |    |    |    | •  |    |    |    |    |    |                       |
|     |     |     |     |    |    |    |    | •  |    |    |    |    |    |                       |
|     |     |     |     |    |    |    |    | •  |    |    |    |    |    |                       |
| 0   | 0   | 0   | 0   | 0  | 0  | 0  | 1  | 1  | 1  | 1  | 1  | 0  | 0  | 125 <sup>(2)</sup>    |
|     |     |     |     |    |    |    |    | •  |    |    |    |    |    |                       |
|     |     |     |     |    |    |    |    | •  |    |    |    |    |    |                       |
| 1   | 1   | 1   | 1   | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 0  | 1  | 16382                 |
| 1   | 1   | 1   | 1   | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 0  | 16383                 |
| 1   | 1   | 1   | 1   | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 1  | 16384                 |

(1) If the divider value is Q, then the code will be the binary value of (Q - 1).

(2) Factory EEPROM Default values M = 125 and N = 768

## CHARGE PUMP

The Charge Pump drives the loop filter that controls the external VCO/VCXO. The Charge pump operates at the PFD frequency since the function of the charge pump is to translate the UP DOWN signals of the PFD into current pulses that drives the external filter. The Charge pump current is set by the control vector ICP [3:0].

**Table 15. CP, Charge Pump Current (Register 0 RAM Bits [17:14])**

| ICP3 | ICP2 | ICP1 | ICP0 | TYPICAL CHARGE PUMP CURRENT |
|------|------|------|------|-----------------------------|
| 0    | 0    | 0    | 0    | 0 $\mu$ A (3-State)         |
| 0    | 0    | 0    | 1    | 200 $\mu$ A                 |
| 0    | 0    | 1    | 0    | 400 $\mu$ A                 |
| 0    | 0    | 1    | 1    | 600 $\mu$ A                 |
| 0    | 1    | 0    | 0    | 800 $\mu$ A                 |
| 0    | 1    | 0    | 1    | 1.0 mA                      |
| 0    | 1    | 1    | 0    | 1.2 mA                      |
| 0    | 1    | 1    | 1    | 1.4 mA                      |
| 1    | 0    | 0    | 0    | 1.6 mA                      |
| 1    | 0    | 0    | 1    | 1.8 mA                      |
| 1    | 0    | 1    | 0    | 2.0 mA                      |
| 1    | 0    | 1    | 1    | 2.2 mA <sup>(1)</sup>       |
| 1    | 1    | 0    | 0    | 2.4 mA                      |
| 1    | 1    | 0    | 1    | 2.6 mA                      |
| 1    | 1    | 1    | 0    | 2.8 mA                      |
| 1    | 1    | 1    | 1    | 3.0 mA                      |

(1) Default

The CP\_PRE register bit R0.13 is a useful feature to quickly set the center frequency of the VC(X)O after Power-up or Reset. The adequate control voltage for the VC(X)O will be provided to the Charge-Pump output by an internal voltage divider of 1K $\Omega$ /1K $\Omega$  to  $V_{CC\_CP}$  and GND ( $V_{CC\_CP}/2$ ). The CP\_PRE register bit must be reset to "0" in order for the PLL to achieve lock.


This feature helps to get the initial frequency accuracy, i.e. required at CPRI (Common Public Radio Interface) or OBSAI (Open Base Station Architecture Initiative).

The Preset Charge-Pump to  $V_{CC\_CP}/2$  can be set and reset by register.



### Charge-Pump Current Direction

The direction of the charge-pump (CP) current pulse can be changed by the register settings. It determines in which direction CP current will regulate (Reference Clock leads to Feedback Clock). Most applications use the positive CP output current (power-up condition) because of the use of a passive loop filter. The negative CP current is useful when using an active loop filter concept with inverting operational amplifier. The Figure below shows the internal PFD signal and the corresponding CP current.



PFD pulse width delay improves spurious suppression.

**Figure 25. Charge Pump**

## PLL LOCK FOR ANALOG AND DIGITAL DETECT

The CDCE72010 supports two PLL Lock indications: the digital lock signal or the analog lock signal. Both signals indicate logic high-level at PLL\_LOCK if the PLL locks according the selected lock condition.

The PLL is locked (set high), if the rising edge of the Reference Clock (PRI\_REF or SEC\_REF clock) and Feedback Clock (VCXO\_IN clock) at the PFD (Phase Frequency Detect) are inside a predefined lock detect window for a pre-defined number of successive clock cycles.

The PLL is out-of-lock (set low), if the rising edge of the Reference Clock (PRI\_REF or SEC\_REF clock) and Feedback Clock (VCXO\_IN clock) at the PFD are outside the predefined lock detect window.

Both, the lock detect window and the number of successive clock cycles are user definable in the register settings.




Figure 26. PLL Lock

The lock detect window describes the maximum allowed time difference for lock detect between the rising edge of PRI\_REF or SEC\_REF and VCXO\_IN. The time difference is detected at the phase frequency detector. The rising edge of PRI\_REF or SEC\_REF is taken as reference. The rising edge of VCXO\_IN is outside the lock detect window, if there is a phase displacement of more than  $+0.5 \cdot t_{(\text{lockdetect})}$  or  $-0.5 \cdot t_{(\text{lockdetect})}$ .

Table 16. Lock-Detect Window (Register 7 Bits [1:0] and Register 9 Bits [7:6])

| LOCKW3<br>[7] | LOCKW2<br>[6] | LOCKW1<br>[1] | LOCKW0<br>[0] | PHASE-OFFSET AT PFD-INPUT <sup>(1)</sup> |
|---------------|---------------|---------------|---------------|------------------------------------------|
| 0             | 0             | 0             | 0             | 1.5 ns                                   |
| 0             | 0             | 0             | 1             | 5.8 ns <sup>(2)</sup>                    |
| 0             | 0             | 1             | 0             | 15.1 ns                                  |
| 0             | 0             | 1             | 1             | Reserved                                 |
| 0             | 1             | 0             | 0             | 3.4 ns                                   |
| 0             | 1             | 0             | 1             | 7.7 ns                                   |
| 0             | 1             | 1             | 0             | 17.0 ns                                  |
| 0             | 1             | 1             | 1             | Reserved                                 |
| 1             | 0             | 0             | 0             | 5.4 ns                                   |
| 1             | 0             | 0             | 1             | 9.7 ns                                   |
| 1             | 0             | 1             | 0             | 19.0 ns                                  |
| 1             | 0             | 1             | 1             | Reserved                                 |
| 1             | 1             | 0             | 0             | 15.0 ns                                  |
| 1             | 1             | 0             | 1             | 19.3 ns                                  |
| 1             | 1             | 1             | 0             | 28.6 ns                                  |
| 1             | 1             | 1             | 1             | Reserved                                 |

(1) Typical values at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$

(2) Default


**Table 17. Number of Successive Lock Events Inside the Lock Detect Window (Register 7 Bits [4:3]) the PLL Lock Signal is Delayed for Number of FB\_CLK Events**

| LOCKC1 | LOCKC0 | NO. OF SUCCESSIVE LOCK EVENTS |
|--------|--------|-------------------------------|
| 0      | 0      | 1                             |
| 0      | 1      | 16                            |
| 1      | 0      | 64 <sup>(1)</sup>             |
| 1      | 1      | 256                           |

(1) Default

## DIGITAL LOCK DETECT

When selecting the digital PLL lock option, PLL\_LOCK will possibly jitter several times between lock and out of lock until a stable lock is detected. A single “low-to-high” step can be reached with a wide lock detect window and high number of successive clock cycles. PLL\_LOCK will return to out of lock if just one cycle is outside the lock detect window.



**Figure 27. Digital Lock**

## ANALOG LOCK DETECT

When selecting the analog PLL Lock option, the high-pulses load the external capacitor via the internal 110  $\mu\text{A}$  current source until logic high-level is reached. Therefore, more time is needed to detect logic high level, but jittering of PLL\_LOCK will be suppressed like possible in case of digital lock. The time PLL\_LOCK needs to return to out of lock depends on the level of  $V_{\text{OUT}}$ , when the current source starts to unload the external capacitor.




Figure 28. Analog Lock

## FREQUENCY HOLD-OVER MODE

The HOLD-Function is a CDCE72010 feature that helps to improve system reliability. The HOLD-Function holds the output frequency in case the input reference clock fails or is disrupted. During HOLD, the Charge-Pump is switched off (3-State) freezing the last valid output frequency. The Hold-Function will be released after a valid reference clock is reapplied to the clock input and detected by the CDCE72010. For proper HOLD function, the Analog PLL-Lock-Detect mode has to be active. The following settings are involved with the HOLD Function:

- Lock Detect Window: Defines the window in ns in which the Lock is valid. The size is 3.5ns, 8.5ns, 18.5ns. Lock is set if Reference Clock and Feedback Clock are inside this predefined Lock-Detect Window for a pre-selected number of successive cycles.
- Out-of-Lock: Defines the out-of-lock condition: If the Reference Clock and the Feedback Clock at the PFD are outside the predefined Lock Detect Window.
- Number of Clock Cycles: Defines the number of successive PFD cycles which have to occur inside the lock window to set Lock detect. This does not apply for Out-of-Lock condition.
- Hold-Function: Selects HOLD-Function (see more details below).
- Hold-Trigger: Defines whether the HOLD-Function is always activated or whether it is dependent on the state of the analog PLL Lock detect output. In the latter case, HOLD is activated if Lock is set (high) and de-activated if Lock is reset (low).
- Analog PLL Lock Detect: Analog Lock output charges or discharges an external capacitor with every valid Lock cycle. The time constant for Lock detect can be set by the value of the capacitor.


The CDCE72010 supports two types of HOLD functions, one external controllable  $\overline{\text{HOLD}}$  mode and one internal mode, HOLD.

## EXTERNAL/HOLD FUNCTION

The Charge Pump can directly be switched into 3-State. This function is also available via register. If logic low is applied to  $\overline{\text{HOLD}}$  pin the Charge Pump will be switched to 3-State. After  $\overline{\text{HOLD}}$  pin is released, the charge pump is switched back in to normal operation, with the next valid reference clock cycle at PRI\_REF or SEC\_REF and the next valid feedback clock cycle at the PFD. During HOLD, all divider and all outputs are at normal operation.

## INTERNAL/HOLD FUNCTION

In Internal HOLD Function or HOLD-Over-Function the PLL has to be in lock to start the HOLD function. It switches the Charge Pump in to 3-State when an 'out-of-lock' event occurs. It leaves the '3-State Charge Pump' state when the Reference Clock is back. Then it starts a locking sequence of 64 cycles before it goes back to the beginning of the HOLD-Over loop.



**Figure 29. Frequency Hold Over**

## OUTPUT DIVIDERS AND PHASE ADJUST

The CDCE72010 is designed with individual Output Dividers for Outputs 1 to 8. Output Divider 1 drives Output 1 and Output 0 and Output Divider 8 drives Output 8 and Output 9. Each output divider has a bypass function or it is referred to as divide by “one”. Since divide by one bypasses the divider block it can address higher operating frequencies.

The output divider is designed to address divide by 1, 2, 3, 4, 5, 6, 8, 10, 12, 16, 18, 20, 24, 28, 30, 32, 36, 40, 42, 48, 50, 56, 60, 64, 70 and 80. The output divider includes a coarse phase adjust that shifts the divided clock signal. The phase adjust resolution is a function of the divide function. The maximum number of phase steps equals to the divider setting.

If the output is divide by 2, then two phase adjustment settings (0 and 180 degrees) are available. The resolution of phase adjustment is related to the output divider setting by the following: Phase adjust resolution =  $(1/\text{Output Divider settings}) \times 360$  Degrees.

Example: For a 491.52MHz VCXO where one of the outputs of the device is set to divide by 16 for a 30.72MHz desired output, this will mean that the 30.72MHz clock will have  $(1/16) \times 360 = 22.5$  Degrees of phase adjustment resolution.

Output Divide Select (OUT#DIVSEL#) and Coarse Phase Adjust Select (PH#ADJC#) registers are located in Register 1 through 8 for Output 1 through 8 respectively.

The Phase difference between 2 divider settings on different output can be calculated using the following formula and referring to the Phase Lag number in the Output Divider Table ( see [Table 8](#)).

Integer Remainder of  $[(\text{Phase Lag X} - \text{Phase Lag Y}) / \text{Divide X}]$  as an example if we need to calculate the phase difference between divide by 4 and divide by 8 with respect to divide by 4 clock.

The Integer Remainder  $[(28.5 - 0.5)/4] = 0$ . This means there is 0 Cycle phase delay between Divide by 4 and Divide by 8 with respect to Divide by 4 Clock.

If we need to do the same calculation with respect to Divide by 8 we will have Integer Remainder  $[(28.5 - 0.5)/8] = 0.5$  that means that there is 0.5 Cycles between Divide by 4 and divide by 8 with respect to a divide by 8 clock.





Figure 30. Maximum Output Frequency With Phase Alignment

## FREQUENCY DETECTION CIRCUIT

The Frequency detector circuit can detect the input clock signal and provide the indications at STATUS pin depending on Register 12 and 3 settings (see notes in page 33). The STATUS pin will set to HIGH if a valid input clock is detected. And LOW if valid input clock is absent or missing.

The frequency detector circuit is located in between the SMART MUX and the M divider (see [Figure 31](#)).



**Figure 31. Location of the Frequency Detector Circuit**

The detection circuit is RC-based analog circuit. The response time to detect a new clock signal is clock-frequency dependent (min. 3.125µs at 0.8MHz). With higher clock frequency the response time will be faster as well.

If the input clock goes away, the detector reports the event within 5.2 µs independent of clock frequency.

**Table 18. Specifications**


| PARAMETER                                               | MIN   | TYP | MAX | UNIT   |
|---------------------------------------------------------|-------|-----|-----|--------|
| Frequency detection threshold <sup>(1)</sup>            | 800   |     |     | kHz    |
| Response time (clock absence) <sup>(1)</sup>            | 2.62  |     | 5.2 | µs     |
| Response time (clock resumes) at 0.8 MHz <sup>(1)</sup> | 3.125 |     | 29  | µs     |
| Clock cycles (clock resumes) at 0.8 MHz <sup>(2)</sup>  | 2.5   |     | 23  | cycles |

(1) Received values from simulation

(2) Received values from simulation

## DEVICE LAYOUT

The CDCE72010 is a high performance device packaged in a QFN-64. The die has all the ground pins bounded to the thermal PAD on the bottom of the package. Therefore it is essential that the connection from the thermal PAD to the ground layers should be low impedance. In addition, the thermal path in a QFN package is via the thermal PAD on the bottom of the package. Therefore, the layout of the PAD is very important and it will affect the thermal performance as well as the overall performance of the device. The illustration shown provides optimal performance in terms of thermal issues, inductance and power supply bypassing. The 10 X 10 Filled VIA pattern recommended allows for a low inductance connection between the thermal ground pad and the ground plane of the board. This pattern forms a low thermal resistive path for the heat generated by the die to get dissipated through the ground plane and to the exposed bottom side ground pad. It is recommended that solder mask not be used on this bottom side pad to maximize its effectiveness as a thermal heat sink. The recommended layout drives the thermal conductivity to 22.8 C°/W in still air and 13.8 C°/W in a 100LFM air flow if implemented on a JEDEC compliant test thermal board.



**Figure 32. Device Layout**



## DEVICE POWER


The CDCE72010 is designed as a high performance device, therefore careful attention must be paid to device configuration with respect to power consumption. Total power consumption of the device can be estimated by adding up the total power consumed by each block in the device.

The Table below describes the blocks used and power consumed per block. The total power of the device can be calculated by multiplying the number of blocks used by the power consumption per block.

**Table 19. Device Power**

| Internal Block Power at 3.3V (typ.) |                                                                                               | Power Dissipation/ Block                                                       | Number of Blocks |
|-------------------------------------|-----------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|------------------|
| PLL Core, Input and Feedback        |                                                                                               | 530 mW                                                                         | 1                |
| Output Dividers                     | Divider = 1                                                                                   | 82 mW                                                                          | 8                |
|                                     | Divider > 1                                                                                   | 180 mW                                                                         |                  |
| LVPECL Output Buffer                |                                                                                               | 75 mW <sup>(1)</sup>                                                           | 10               |
| LVDS Output Buffer                  |                                                                                               | 75 mW                                                                          | 10               |
| LVCMOS Output Buffer                | Static                                                                                        | 7 mW                                                                           | 20               |
|                                     | Transient, 'C <sub>L</sub> ' load, 'f <sub>OUT</sub> ' MHz output frequency, 'V' output swing | $V_{DD} \times V \times f_{OUT} \times (C_L + 20 \times 10^{-12}) \times 10^3$ | 20               |

(1) Approximately 50 mW power dissipates externally at termination resistors per LVPECL output pair.



**Figure 33. Die Temperature**

## LOOP FILTER

The CDCE72010 is designed to control an external Voltage Controlled Oscillator (VCO) or a Voltage Controlled Crystal Oscillator (VCXO) and to synchronize the controlled oscillators to the input reference. Controlling the Oscillator happens via a DC voltage that is applied to the Voltage control pin. This DC voltage is generated by the CDCE72010 in the form of AC pulses that get filtered by the external loop filter.




Figure 34. Loop Filter

## UNIVERSAL OUTPUT BUFFERS

The CDCE72010 is designed to drive three types of clock signaling, LVPECL, LVDS, and LVCMOS from each of the ten outputs. This super buffer that contains all three drivers is referred to as the Universal Output Buffer. Only one driver can be enabled at one time. Each universal output buffer is made from four independent buffers in parallel. When LVPECL mode is selected, only the LVPECL Buffer is enabled and the rest of the buffers are 3-stated and in low power mode. When Selecting LVDS, only the LVDS Buffer is enabled and the rest of the buffers are 3-stated and in low power mode. When LVCMOS mode is selected, both LVCMOS drivers are enabled. One LVCMOS buffer drives the negative side and the other buffer drives the positive pin.

The LVCMOS drivers are driven from the same output divider but have separate control bits. In SPI Mode, bits 22, 23, 24, and 25 of Registers 0 to 9 are used to put the LVCMOS buffer in active, inverting, low, or 3-state. In CD Mode, those bits are used for different functions and the LVCMOS buffer can be active when selected or 3-state when their not.




Figure 35. Universal Output Buffer

## Output Dividers Synchronization

The CDCE72010 is a 10 output clock device with 8 output dividers and to insure that all the outputs are synchronous a synchronization startup circuitry is used. The synchronization circuitry generates a pulse to reset all the dividers in a way, that a predictable synchronous output is generated. The Synchronization signal can be generated from different sources and can be synchronized to a specific clock. The Block diagram below illustrates the signal path of the Output Divider Sync Signal. This function is assured up to 500 MHz.

### NOTE

The minimum frequency required for the output synchronization block to work properly is 1 MHz.




Figure 36. Output Divider Synchronization Block Diagram

## POWER UP RESET, POWER DOWN MODE AND RESET OR HOLD

The CDCE72010 is designed to address various clock synchronization applications. Some functions can be set to be in automatic and manual mode or some functions can be controlled by software or by the internal circuitry.

[Table 20](#) explains the various functionalities of power up reset internal circuitry functionality, power down functionality and reset functionality. The hold function shares the same block with Reset and one bit in the EEPROM will select either function.

**Table 20. RESET\_HOLD\_STATE**

| RESET_HOLD_MODE<br>(R11.25) | $\overline{\text{SLEEP}}$<br>(R12.7) | RESET_HOLD<br>(R12.8) | RESET/HOLD<br>(pin #33) | $\overline{\text{PD}}$<br>(pin #17) | MODE                                                                                                                                                       |
|-----------------------------|--------------------------------------|-----------------------|-------------------------|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| X                           | X                                    | X                     | X                       | 0                                   | Device in Power down. On Power down exit, register reset to EEPROM defaults.                                                                               |
| X                           | 0                                    | X                     | X                       | 1                                   | Device in SLEEP Mode. It's the same as power down but upon exit of this mode, the registers will retain their previous state (no EEPROM reload).           |
| 0                           | 1                                    |                       | 00<br>01<br>10          | 1                                   | Device in RESET. Power consumption minimized outputs tri-state. Upon exit of this mode, the registers will retain their previous state (no EEPROM reload). |
| 1                           | 1                                    |                       | 00<br>01<br>10          | 1                                   | Device in HOLD mode. The CP output is tri-stated.                                                                                                          |
| X                           | 1                                    |                       | 11                      | 1                                   | Normal Mode.                                                                                                                                               |

## REVISION HISTORY

| Changes from Original (June 2008) to Revision A                                                            | Page |
|------------------------------------------------------------------------------------------------------------|------|
| • Changed Frequency equation result from $(R \cdot M)/(P \cdot N)$ to $(P \cdot N)/(R \cdot M)$ .....      | 2    |
| • Added table note to Register 0: SPI Mode table description .....                                         | 24   |
| • Changed Register 12: SPI Mode (RAM only Register) Note .....                                             | 36   |
| • Added table note to Register 0: CD Mode table description .....                                          | 39   |
| • Added additional information to INTERFACE, CONFIGURATION, AND CONTROL description .....                  | 51   |
| • Changed <a href="#">Figure 22</a> .....                                                                  | 52   |
| • Added "P" to PHASE FREQUENCY DETECTOR feedback divider description .....                                 | 53   |
| • Changed Frequency equation from $(R \cdot M)/(P \cdot N)$ to $(P \cdot N)/(R \cdot M)$ .....             | 53   |
| • Deleted P is the product of X Divider and FB Divider R and X Divider is set to be divide by 1 or 2 ..... | 53   |
| • Changed <a href="#">Figure 24</a> by adding maximum frequency = 250 MHz .....                            | 53   |
| • Added note to Output Dividers Synchronization description .....                                          | 68   |

| Changes from Revision A (June 2008) to Revision B                                                       | Page |
|---------------------------------------------------------------------------------------------------------|------|
| • Changed many instances in rev B of this data sheet (major changes/additions to this data sheet) ..... | 1    |
| • Deleted "Dedicated Charge-Pump.....VCOs" from FEATURES .....                                          | 1    |
| • Changed <a href="#">Figure 1</a> .....                                                                | 2    |
| • Changed Pin Functions table .....                                                                     | 4    |
| • Changed Pin Functions table .....                                                                     | 5    |
| • Changed Pin Functions table .....                                                                     | 6    |
| • Changed Recommended Operating Conditions table .....                                                  | 7    |
| • Changed Timing Requirements table .....                                                               | 8    |
| • Changed AC/DC Characteristics table .....                                                             | 9    |
| • Added new section "INTERFACE AND CONTROL BLOCK" including figures/tables .....                        | 19   |
| • Changed <a href="#">Table 6</a> .....                                                                 | 23   |
| • Changed <a href="#">Table 6</a> .....                                                                 | 23   |
| • Changed text/rows in all Register tables .....                                                        | 24   |
| • Changed $\overline{\text{SLEEP}}$ and $\overline{\text{RESET\_HOLD}}$ .....                           | 36   |
| • Changed "Universal Input and Reference Clock Buffers" section including figures .....                 | 51   |
| • Changed <a href="#">Figure 21</a> .....                                                               | 51   |
| • Changed <a href="#">Figure 22</a> .....                                                               | 52   |
| • Changed tables in "PHASE DELAY for M and N" section .....                                             | 55   |
| • Deleted 0 from N1 and N0 .....                                                                        | 55   |
| • Changed text in "CHARGE PUMP" section .....                                                           | 56   |
| • Changed text in CHARGE PUMP section .....                                                             | 56   |
| • Changed <a href="#">Table 19</a> .....                                                                | 65   |
| • Changed SLEEP in <a href="#">Table 20</a> to active low .....                                         | 69   |

| Changes from Revision B (August 2011) to Revision C               | Page |
|-------------------------------------------------------------------|------|
| • Changed Pin 3 and 58 to Pin 5 and 8 in PIN FUNCTIONS note ..... | 4    |
| • Changed in Table 6, Reg 11 from 81E09B0C to 8000058B .....      | 23   |

## PACKAGING INFORMATION

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">CDCE72010RGCR</a> | Active        | Production           | VQFN (RGC)   64 | 2000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-3-260C-168 HR               | -40 to 85    | CDCE72010           |
| CDCE72010RGCR.B               | Active        | Production           | VQFN (RGC)   64 | 2000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-3-260C-168 HR               | -40 to 85    | CDCE72010           |
| <a href="#">CDCE72010RGCT</a> | Active        | Production           | VQFN (RGC)   64 | 250   SMALL T&R       | Yes         | NIPDAUAG                             | Level-3-260C-168 HR               | -40 to 85    | CDCE72010           |
| CDCE72010RGCT.B               | Active        | Production           | VQFN (RGC)   64 | 250   SMALL T&R       | Yes         | NIPDAUAG                             | Level-3-260C-168 HR               | -40 to 85    | CDCE72010           |
| CDCE72010RGCTG4               | Active        | Production           | VQFN (RGC)   64 | 250   SMALL T&R       | Yes         | NIPDAUAG                             | Level-3-260C-168 HR               | -40 to 85    | CDCE72010           |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CDCE72010RGCR | VQFN         | RGC             | 64   | 2000 | 330.0              | 16.4               | 9.3     | 9.3     | 1.5     | 12.0    | 16.0   | Q2            |
| CDCE72010RGCT | VQFN         | RGC             | 64   | 250  | 330.0              | 16.4               | 9.3     | 9.3     | 1.5     | 12.0    | 16.0   | Q2            |



## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CDCE72010RGCR | VQFN         | RGC             | 64   | 2000 | 367.0       | 367.0      | 38.0        |
| CDCE72010RGCT | VQFN         | RGC             | 64   | 250  | 367.0       | 367.0      | 38.0        |


## GENERIC PACKAGE VIEW

**RGC 64**

**VQFN - 1 mm max height**



9 x 9, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4224597/A



4219011/A 05/2018


## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.


**RG0064H**

### VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4219011/A 05/2018

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).
5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

# EXAMPLE STENCIL DESIGN

RGC0064H

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE  
 BASED ON 0.125 MM THICK STENCIL  
 SCALE: 10X

EXPOSED PAD 65  
 61% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE

4219011/A 05/2018

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025