TPS92391

JAJSKE4 - MARCH 2021

TPS92391 6 チャネルの 200mA を備えた昇圧 / SEPIC 高調光性 LED ドライバ


1 特長

- 入力電圧動作範囲:3V~48V
- 6 つの高精度電流シンク
 - 電流シンクごとに最大 200mA の DC 電流
 - 電流マッチング 1% (標準値)
 - 152Hz の LED 出力 PWM 周波数を使用した 32 000:1 の調光率
 - I2C または PWM 入力により、最大 16 ビットの LED 調光分解能
 - 8 つの構成可能な LED ストリング構成
- 自動位相シフトの PWM 調光
- 12 ビットのアナログ調光
- スイッチング周波数:100kHz~2.2MHz
- 昇圧拡散スペクトラムによる EMI の低減
- 昇圧同期入力により、外部クロックから昇圧スイッチング周波数を設定
- 最高 48V の V_{OUT} 昇圧または SEPIC DC/DC コントローラ
 - スイッチング周波数:100kHz~2.2MHz
 - 昇圧拡散スペクトラムによる EMI の低減
 - 昇圧同期入力により、外部クロックから昇圧スイッチング周波数を設定
- 広範なフォルト診断

2 アプリケーション

次の応用でのバックライト:

- モニタ
- テレビ
- 医療用ディスプレイ
- 制御パネルの産業用バックライト・システム
- 産業用 PC
- 試験および計測機器



3 概要

TPS92391 は昇圧コントローラを備えた車載用、高効率のLEDドライバです。6 つの高精度電流シンクは、使用しているチャネル数に応じて自動調整される位相シフトをサポートしています。LED の輝度は、I²C インターフェイスまたは PWM 入力によりグローバルに制御できます。


この昇圧コントローラは、LED 電流シンクのヘッドルーム 電圧に基づいた適応型出力電圧制御機能を備えていま す。この機能により、すべての条件で、必要最低限のレベ ルに昇圧を調整することで消費電力を最小化できます。 周波数を広範囲に調整できるため、TPS92391 は AM ラ ジオ周波数帯に対する妨害を回避できます。

TPS92391 は組み込みのハイブリッド PWM 調光とアナログ電流調光をサポートしているため、EMI の削減、LED の寿命の延長、総合的な光学効率の向上を実現します。

製品情報

	ANAL 114 114	
部品番号(1)	パッケージ	本体サイズ (公称)
TPS92391	QFN (32)	5mm × 5mm

(1) 利用可能なパッケージについては、このデータシートの末尾にある注文情報を参照してください。



システム効率



Table of Contents

1 特長	1	7.5 Programming	38
2 アプリケーション		7.6 Register Maps	
3 概要		8 Application and Implementation	56
4 Revision History		8.1 Application Information	<u>56</u>
5 Pin Configuration and Functions		8.2 Typical Applications	
6 Specifications		9 Power Supply Recommendations	
6.1 Absolute Maximum Ratings		10 Layout	
6.2 ESD Ratings		10.1 Layout Guidelines	70
6.3 Recommended Operating Conditions		10.2 Layout Example	71
6.4 Thermal Information		11 Device and Documentation Support	72
6.5 Electrical Characteristics		11.1 Device Support	72
6.6 Logic Interface Characteristics		11.2ドキュメントの更新通知を受け取る方法	72
6.7 Timing Requirements for I2C Interface		11.3 サポート・リソース	72
6.8 Typical Characteristics		11.4 Trademarks	72
7 Detailed Description		11.5 静電気放電に関する注意事項	72
7.1 Overview	11	11.6 用語集	72
7.2 Functional Block Diagram		12 Mechanical, Packaging, and Orderable	
7.3 Feature Description	12	Information	73
7.4 Device Functional Modes	37		

4 Revision History

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

DATE	REVISION	NOTES
March 2021	*	Initial Release

5 Pin Configuration and Functions




図 5-1. RHB Package 32-PIN QFN Top View



表 5-1. QFN Pin Functions

PIN			
NO.	NAME	TYPE	DESCRIPTION
1	OUT6	Analog	LED current sink output. If unused tie to ground
2	OUT5	Analog	LED current sink output. If unused tie to ground
3	OUT4	Analog	LED current sink output. If unused tie to ground.
4	LED_GND	GND	LED ground connection.
5	OUT3	Analog	LED current sink output. If unused tie to ground.
6	OUT2	Analog	LED current sink output. If unused tie to ground.
7	OUT1	Analog	LED current sink output. If unused tie to ground.
8	INT	Analog	Device fault interrupt output, open drain. A 10-kΩ pullup resistor is recommended.
9	SDA	Analog	SDA for I2C interface. A 10-kΩ pullup resistor is recommended.
10	SCL	Analog	SCL for I2C interface. A 10-kΩ pullup resistor is recommended.
11	BST_SYNC	Analog	Input for synchronizing boost. When synchronization is not used, connect this pin to ground to disable spread spectrum or to VDD to enable spread spectrum.
12	PWM	Analog	PWM input for brightness control. Tie to GND if unused.
13	SGND	GND	Signal ground.
14	LED_SET	Analog	LED string configuration through external resistor. Do not leave floating.
15	PWM_FSET	Analog	LED dimming frequency setup through external resistor. Do not leave floating.
16	BST_FSET	Analog	Boost switching frequency setup through external resistor. Do not leave floating.
17	MODE	Analog	Dimming mode setup through external resistor. Do not leave floating.
18	UVLO	Analog	Input voltage sense for programming input UVLO threshold through external resistor to VIN.
19	VSENSE_P	Analog	Pin for input voltage detection for OVP protection and positive input for input current sense.
20	VSENSE_N	Analog	Negative input for input current sense. If input current sense is not used, please tie to VSENSE_P pin.
21	SD	Analog	Power line FET control. Open Drain output. If unused, leave this pin floating.
22	VDD	Power	Power supply input for internal analog and digital circuit. Connect a 10-uF capacitor between the VDD pin to GND.
23	EN	Analog	Enable input.
24	C1N	Analog	Negative input for charge pump flying capacitor. If feature not used leave this pin floating.
25	C1P	Analog	Positive input for charge pump flying capacitor. If feature not used leave this pin floating.
26	CPUMP	Power	Charge pump output pin. Connect to VDD if charge pump is not used. A 4.7-µF decoupling capacitor is recommended on CPUMP pin.
27	GD	Analog	Gate driver output for external N-FET.
28	PGND	GND	Power ground.
29	ISNS	Analog	Boost current sense pin.
30	ISNSGND	GND	Current sense resistor GND.
31	ISET	Analog	LED full-scale current setup through external resistor.
32	FB	Analog	Boost feedback input.
DAP	LED_GND	GND	LED ground connection.



6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (2)

		MIN	MAX	UNIT
Voltage on pins	VSENSE_N, SD, UVLO	-0.3	VSENSE _P + 0.3	V
	VSENSE_P, FB , OUT1 to OUT6	-0.3	52	V
Voltage on pins	C1N, C1P, VDD, EN, ISNS, ISNS_GND, INT, MODE, PWM_FSET, BST_FSET, LED_SET, ISET, GD and CPUMP	-0.3	6	V
Voltage on pins	PWM, BST_SYNC, SDA, SCL	-0.3	VDD + 0.3	V
	Continuous power dissipation ⁽³⁾		Internally Limited	W
	Ambient temperature, TA ⁽⁴⁾	-40	125	
Thormal	Junction temperature, TJ ⁽⁴⁾	-40	150	°C
Thermal	Lead temperature (soldering)		260	°C
	Storage temperature, Tstg	-65	150	°C

- (1) Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to the potential at the GND pins.
- (3) Internal thermal shutdown circuitry protects the device from permanent damage. Thermal shutdown engages at $T_J = 165^{\circ}$ C (typical) and disengages at $T_J = 150^{\circ}$ C (typical).
- (4) In applications where high power dissipation and/or poor package thermal resistance is present, the maximum ambient temperature may have to be derated. Maximum ambient temperature (T_{J-MAX}) is dependent on the maximum operating junction temperature (T_{J-MAX} = 150°C), the power dissipation of the device in the application (P), the junction-to-board thermal resistance and the temperature difference between the system board and the ambient (Δt_{BA}), which is given by the following equation: T_{A-MAX} = T_{J-MAX} (Θ_{JB} × P) Δt_{BA}

6.2 ESD Ratings

				VALUE	UNIT
		Human body model (HBM), per AEC Q100-002 ⁽¹⁾		±2000	
V _(ESD)	Electrostatic discharge	Charged device model (CDM), per AEC Q100-011	Corner pins (1, 19, 20 and 38)	±750	V
	alconargo		Other pins	±500	

(1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)(1)

		MIN	NOM	MAX	UNIT
	VSENSE_P, VSENSE_N, SD, UVLO	3	12	48	
	FB , OUT1 to OUT6	0		48	
Voltage on	ISNS, ISNSGND	0		5.5	V
pins	EN, PWM, INT, SDA, SCL, BST_SYNC	0	3.3	5.5	V
	VDD	3	3.3/5	5.5	
	C1N, C1P, CPUMP,GD	0	5	5.5	
Thermal	Ambient temperature, T _A	-40		125	°C

(1) All voltages are with respect to the potential at the GND pins.



6.4 Thermal Information

		Device	
	THERMAL METRIC ⁽¹⁾	QFN	UNIT
		32-PIN	
$R_{\theta JA}$	Junction-to-ambient thermal resistance ⁽²⁾	32.9	
R _{0JC(top)}	Junction-to-case (top) thermal resistance	19.6	
$R_{\theta JB}$	Junction-to-board thermal resistance	6.8	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	0.3	
Ψ_{JB}	Junction-to-board characterization parameter	6.8	
R _{θJC(bot)}	Junction-to-case (bottom) thermal resistance	1.8	

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

6.5 Electrical Characteristics

Limits apply over the full operation temperature range $-40^{\circ}\text{C} \le T_{A} \le +125^{\circ}\text{C}$, unless otherwise speicified, $V_{IN} = 12 \text{ V}$, VDD = 3.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
General I	Electrical Characteristics					
IQ	Shutdown mode current, VDD pin	EN = L		1	5	μA
IQ	Active mode current, VDD pin ⁽¹⁾	FSW = 303 kHz, PWM = H, BOOST-FET IPD25N06S4L-30, Charge Pump Disabled		15	65	mA
IQ	Active mode current, VDD pin ⁽¹⁾	FSW = 2200 kHz, PWM = H, BOOST- FET IPD25N06S4L-30, Charge Pump Disabled		40	75	mA
IQ	Active mode current, VDD pin ⁽¹⁾	FSW = 303 kHz, PWM = H, BOOST-FET IPD25N06S4L-30, Charge Pump Enabled		20	91	mA
IQ	Active mode current, VDD pin ⁽¹⁾	FSW = 2200 kHz, PWM = H, BOOST- FET IPD25N06S4L-30, Charge Pump Enabled		65	104	mA
CPUMP a	nd LDO Electrical Characteristics					
V _{CPUMP}	Voltage accuracy	V _{DD} = 3.0 to 3.6 V; I _{LOAD} = 1 to 50 mA	4.8	5	5.2	V
f _{CP}	CP switching frequency		387	417	447	kHz
V _{CPUMP} _ UVLO	VCPUMP UVLO threshold	V _{CPUMP} falling edge	3.95	4.2	4.4	V
V _{CPUMP} _ UVLO	VCPUMP UVLO threshold	V _{CPUMP} rising edge	4.15	4.4	4.6	V
V _{CPUMP} _ HYS	VCPUMP UVLO hysteresis		0.1	0.2		V
T _{START_U}	Charge pump startup time	C _{CPUMP} = 10 μF		1000	2000	μs
Protectio	n Electrical Characteristics					
VDD _{UVLO} _F	V _{DD} UVLO threshold	V _{DD} falling	2.68	2.8	2.92	V
VDD _{UVLO} _R	V _{DD} UVLO threshold	V _{DD} rising			3.0	V
VDD _{UVLO} _H	V _{DD} UVLO hysteresis			0.1		V
VIN _{UVLO} _	UVLO pin threshold	V _{UVLO} falling	0.753	0.777	0.801	V

⁽²⁾ Junction-to-ambient thermal resistance is highly application and board-layout dependent. In applications where high maximum power dissipation exists, special care must be paid to thermal dissipation issues in board design.

6.5 Electrical Characteristics (continued)

Limits apply over the full operation temperature range $-40^{\circ}\text{C} \le T_{A} \le +125^{\circ}\text{C}$, unless otherwise speicified, $V_{IN} = 12 \text{ V}$, VDD = 2.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
I _{UVLO}	UVLO pin bias current	V _{UVLO} = V _{UVLO_TH} + 50v mV		-5		μA
VIN _{OVP_T}	OVP threshold	VSENSE_P rising	40.8	43	45.2	V
H						
VIN _{OVP_H} ys	OVP hysteresis			1.7		V
VIN _{OCP_T}	Input OCP threshold	R_{ISENSE} = 20 m Ω	187	220	253	mV
T _{SD}	Thermal shutdown threshold ⁽¹⁾	Temperature rising	150	165	180	°C
T _{SD}	Thermal shutdown hysteresis ⁽¹⁾			20		°C
I _{SD_LEAKA} GE	SD leakage current	V _{SD} = 48 V		1		μΑ
I _{SD}	SD pull down current	R_{SD} = 20 k Ω	250	325	400	μΑ
V _{FB_OVPL}	FB pin - Boost OVP low threshold			1.423		V
V _{FB_OVPH}	FB pin - Boost OVP high threshold			1.76		V
V _{FB_UVP}	FB pin - Boost OCP threshold			0.886		V
V _{BST_OVP}	Discharge pin - Boost OVP high threshold		48.5	50	51.8	V
nput PW	M Electrical Characteristics					
PWM_LEA	PWM leakage current	V _{PWM} = 5 V		1		μA
f _{PWM_IN}	PWM input frequency		100		20000	Hz
t _{PWM_MIN} _ON	PWM input minimum on-time	Direct PWM mode			200	ns
t _{PWM_MIN} _ON	PWM input minimum on-time	Phase Shift PWM mode, Hybrid mode, Current Dimming mode		200	220	ns
PWM_IN	PWM input resolution	f _{PWM_IN} = 100 Hz		16		bit
PWM_IN	PWM input resolution	f _{PWM_IN} = 20 kHz		10		bit
LED Curr	ent Sink and LED PWM Electrical Charac	teristics				
LEAKAGE	Leakage current on OUTx	OUTx = V _{OUT} = 45 V, EN= L		0.1	2.5	μΑ
V _{ISET}	ISET voltage		1.17	1.21	1.25	V
I _{MAX}	Maximum LED sink current	OUTx		200		mA
V _{ISET_UVL}	ISET pin undervoltage		0.97	1	1.03	V
R _{ISET}	ISET Resistor range	I _{OUT} = 30 mA to 200 mA	15.6		104	kΩ
LED_LIMIT	LED current limit when ISET pin short to GND			280		mA
I _{ACC}	LED sink current accuracy	R_{ISET} = 15.6 k Ω , I_{OUT} = 150 mA, PWM = 100%	-4		4	%
		R_{ISET} = 15.6 k Ω , I_{OUT} = 150 mA, PWM =				%



6.5 Electrical Characteristics (continued)

Limits apply over the full operation temperature range $-40^{\circ}\text{C} \le T_{A} \le +125^{\circ}\text{C}$, unless otherwise speicified, $V_{IN} = 12 \text{ V}$, VDD = 3.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
f _{DIM}	LED dimming frequency	PWM_FSET = 3.92 kΩ	141	152	163	
f _{DIM}	LED dimming frequency	PWM_FSET = 4.75 kΩ	283	305	327	
f _{DIM}	LED dimming frequency	PWM_FSET = 5.76 kΩ	567	610	653	
f _{DIM}	LED dimming frequency	PWM_FSET = 7.87 kΩ	1135	1221	1307	1.1-
f _{DIM}	LED dimming frequency	PWM_FSET = 11 kΩ	2270	2441	2612	Hz
f _{DIM}	LED dimming frequency	PWM_FSET = 17.8 kΩ	4541	4883	5225	
f _{DIM}	LED dimming frequency	PWM_FSET = 42.4 kΩ	9082	9766	10450	
f _{DIM}	LED dimming frequency	PWM_FSET = 124 kΩ	18163	19531	20899	
DIM	Dimming ratio	f _{PWM_OUT} = 152 Hz		32000:1		
DIM	Dimming ratio	f _{PWM_OUT} = 4.88 kHz		1000:1		
V _{HEADRO}	LED sink headroom			0.7		V
V _{HEADRO} OM_HYS	LED sink headroom hysteresis			0.8		V
V _{LEDSHO} RT	LED internal short threshold			5.4		V
V _{SHORTG}	LED short to ground threshold			0.24		٧
t _{PWM_OUT}	LED output minimum pulse			200		ns
Boost Co	nverter Electrical Characteristics					
f _{SW}	Switching Frequency	BST_FSET = $7.87 \text{ k}\Omega$	93	100	107	kHz
f _{SW}	Switching Frequency	BST_FSET = $4.75 \text{ k}\Omega$	186	200	214	kHz
f _{SW}	Switching Frequency	BST_FSET = 5.76 kΩ	281	303	325	kHz
f _{SW}	Switching Frequency	BST_FSET = 3.92 kΩ	372	400	428	kHz
f _{SW}	Switching Frequency	BST_FSET = 11 kΩ	465	500	535	kHz
f _{SW}	Switching Frequency	BST_FSET = 17.8 kΩ	1690	1818	1946	kHz
f _{SW}	Switching Frequency	BST_FSET = $42.4 \text{ k}\Omega$	1860	2000	2140	kHz
f _{SW}	Switching Frequency	BST_FSET = 124 kΩ	2066	2222	2378	kHz
V _{ISNS}	External FET current limit	V_{ISNS} threshold, R_{SENSE} = 15 to 50 m Ω	180	200	220	mV
I _{SEL_MAX}	IDAC maximum current	V _{DD} = 3.3 V	36.4	38.7	40.2	μΑ
R _{DS_ONH}	R _{DSON} of high-side FET to gate driver	V _{GD} /(R _{DS_ON} + total resistance to gate input of SW FET) must not be higher than 2.5 A		1.4		Ω
R _{DS_ONL}	R _{DSON} of low-side FET to gate driver	V _{GD} /(R _{DS_ON} + total resistance to gate input of SW FET) must not be higher than 2.5 A		0.75		Ω
t _{STARTUP}	Start-up time	Delay from beginning of boost Soft-start to when LED drivers can begin		50		ms
T _{ON}	Minimum switch on-time			150		ns
T _{OFF}	Minimum switch off time			150		ns
	•					

⁽¹⁾ This specification is not ensured by ATE



6.6 Logic Interface Characteristics

Limits apply over the full operation temperature range $-40^{\circ}\text{C} \le T_{A} \le +125^{\circ}\text{C}$, unless otherwise speicified $V_{IN} = 12 \text{ V}$, VDD = 5 V, $V_{EN} = 3.3 \text{ V}$

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT				
LOGIC INPUT EN										
VENIL	EN logic low threshold				0.4	V				
VENIH	EN logic high threshold		1.2			V				
R _{ENPD}	EN pin internal pull down resistance			1		МΩ				
LOGIC IN	PUT SDA, SCL, BST_SYNC and PWM		•							
V _{IL}	Logic low threshold	V _{DD} = 3.3 V and 5 V			0.4	V				
V _{IH}	Logic high threshold	V _{DD} = 3.3 V and 5 V	1.2			V				
LOGIC O	UTPUT SDA, INT									
V _{OL}	Output level low	I = 3 mA		0.2	0.4	V				
I _{LEAKAGE}	Output leakage current	V = 3.3 V			1	μΑ				

6.7 Timing Requirements for I2C Interface

Limits apply over the full operation temperature range $-40^{\circ}\text{C} \le T_{A} \le +125^{\circ}\text{C}$, unless otherwise speicified $V_{IN} = 12 \text{ V}$, VDD = 5 $V_{.}$ V_{EN} = 3.3 V.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
f _{SCLK}	Clock frequency				400	kHz
1	Hold time (repeated) START condition		0.6			μs
2	Clock low time		1.3			μs
3	Clock high time		600			ns
4	Set-up time for a repeated START condition		600			ns
5	Data hold time		50			ns
6	Data setup time		100			ns
7	Rise time of SDA and SCL				300	ns
8	Fall time of SDA and SCL				300	ns
9	Set-up time for STOP condition		600			ns
10	Bus free time between a STOP and a STAF	RT condition	1.3			μs





図 6-1. I2C Timing Diagram



6.8 Typical Characteristics

Unless otherwise specified: $C_{IN} = C_{OUT} = 2 \times 10 - \mu F$ ceramic and $2 \times 33 - \mu F$ electrolytic, $V_{DD} = 3.3$ V, charge pump enabled, $T_A = 25$ °C





7 Detailed Description

7.1 Overview

The TPS92391 device is a high-voltage LED driver for large screen display LED backlight applications. PWM input is used for brightness control by default. Alternatively, the brightness can also be controlled by I2C Interface.

The boost frequency, LED PWM frequency, and LED string current are configured with external resistors through the BST_FSET, PWM_FSET, and ISET pins. The INT pin is used to report faults to the system. Fault interrupt status can be cleared with the I2C interface, or is cleared on the falling edge of the EN pin.

The TPS92391 supports pure PWM dimming. The six LED current drivers provide up to 200 mA per output and can be tied together to support higher current LEDs. The maximum output current of the LED drivers is set with the ISET resistor and can be optionally scaled by the LEDx_CURRENT[11:0] register bits with I2C interface. The LED output PWM frequency is set with a PWM_FSET resistor. The number of connected LED strings is configured by the LED_SET resistor, and the device automatically selects the corresponding phase shift mode. For example, if the device is set to 4-strings mode, each LED output is phase shifted by 90 degrees with each other(= 360 / 4). Unused outputs, which must be connected to GND, will be disabled and excluded from adaptive voltage and won't generate any LED faults.


A resistor divider connected from V_{OUT} to the FB pin sets the maximum voltage of the boost. For best efficiency, the boost voltage is adapted automatically to the minimum necessary level needed to drive the LED strings by monitoring all the LED output voltages continuously. The switching frequency of the boost regulator can be set between 100 kHz and 2.2 MHz by the BST_FSET resistor. The boost has a start-up feature that reduces the peak current from the power-line during start-up. The TPS92391 can also control a power-line FET to reduce battery leakage when disabled and provide isolation and protection in the event of a fault.

Fault detection features of TPS92391 include:

- Open-string and shorted LED detection
 - LED fault detection prevents system overheating in case of open or short in some of the LED strings
- LED short-to-ground detection
- ISET/BST_FSET/PWM_FSET/LED_SET/MODE resistor out-of-range detection
- Boost overcurrent
- · Boost overvoltage
- Device undervoltage protection (VDD UVLO)
 - Threshold sensing from VDD pin
- V_{IN} input overvoltage protection (V_{IN} OVP)
 - Threshold sensing from VSENSE P pin
- V_{IN} input undervoltage protection (V_{IN} UVLO)
 - Threshold sensing from UVLO pin
- V_{IN} input overcurrent protection (V_{IN} OCP)
 - Threshold sensing across voltage between VSENSE P pin and VSENSE N pin
- · Thermal shutdown in case of die overtemperature



7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Control Interface

Device control interface includes:

- EN is the enable input for the TPS92391 device.
- PWM is the default input to control the brightness of all current sinks by duty cycle.
- INT is an open-drain fault output indicating fault condition detection.
- SDA and SCL are data and clock line for I2C interface to control the brightness of all current sinks and read back the fault conditions for diagnosis.
- BST_SYNC is used to input an external clock for the boost switching frequency and control the internal boost clock mode.
 - The external clock is auto detected at start-up and, if missing, the internal clock is used.

Texas

- Optionally, the BST SYNC can be tied to VDD to enable the boost spread spectrum function or tied to GND to disable it.
- ISET pin to set the maximum LED current level per string.

7.3.2 Function Setting

Device parameter setting includes:

- BST FSET pin is used to set the boost switching frequency through a resistor to signal ground.
- PWM FSET pin is used to set the LED output PWM dimming frequency through a resistor to signal ground.
- MODE pin is used to set the dimming mode via an external resistor to signal ground.
- LED SET pin is used to set the LED configuration through a resistor to signal ground.
- ISET pin is used to set the maximum LED current level per OUTx pin.

7.3.3 Device Supply (VDD)

All internal analog and digital blocks of TPS92391 are biased from external supply from VDD pin. Either a typical 5-V or 3.3-V supply rail is able to supply VDD from previous linear regulator or DC/DC converter with at least 200-mA current capability.

7.3.4 Enable (EN)

The TPS92391 only turns on when the input voltage of EN pin is above the voltage threshold (VEN_{IH}) and turns off when the voltage of EN pin is below the threshold (VEN_{IL}). All analog and digital blocks start operating once the TPS92391 is enabled by asserting EN pin. The SD pin is floating, I2C interface and Fault detection are not active if the EN pin is de-asserted.

7.3.5 Charge Pump

An integrated regulated charge pump can be used to supply the gate drive for the external FET of the boost controller. The charge pump is enabled or disabled by automatically detecting whether VDD and CPUMP pin are connected together. If VDD is < 4.5 V then use the charge pump to generate a 5-V gate voltage to drive the external boost switching FET. To use the charge pump, a 2.2-µF capacitor is placed between C1N and C1P. If the charge pump is not required, C1N and C1P could be left unconnected and CPUMP pins tied to VDD. A 4.7μF CPUMP capacitor is used to store energy for the gate driver. The CPUMP capacitor is required to be used in both charge pump enabled and disabled conditions and must be placed as close as possible to the CPUMP pins. Z 7-1and Z 7-2 show required connections for both use cases.




図 7-1. Charge Pump Enabled Circuit






図 7-2. Charge Pump Disabled Circuit

If the charge pump is enabled, the CPCAP_STATUS bit shows whether a fly capacitor was detected and the CP_STATUS bit shows status of any charge pump faults and generates an INT signal. The CP_INT_EN bit can be used to prevent the charge-pump fault from causing an interrupt on the INT pin.

7.3.6 Boost Controller

The TPS92391 current-mode-controlled boost DC/DC controller generates the anode voltage for the LEDs. The boost is a current-mode-controlled topology with a cycle by cycle current limit. The boost converter senses the switch current and across the external sense resistor connected between ISNS and ISNSGND. A 20-m Ω sense resistor results in a 10-A cycle by cycle current limit. The sense resistor value could vary from 15 m Ω to 50 m Ω depending on the application. Maximum boost voltage is configured with external FB-pin resistor divider connected between V_{OUT} and FB. The FB-divider equation is described in $\frac{1}{2}$ 7.3.6.3.




図 7-3. Boost Controller Block Diagram

The boost switching frequency is adjustable from 100 kHz to 2.2 MHz via an external resistor at BST_FSET (see 表 7-1). Resistor with 1% accuracy is needed to ensure proper operation.

表 7-1. Boost Frequency Selection

R_BST_FSET (kΩ)	BOOST FREQUENCY (kHz)
3.92	400
4.75	200
5.76	303
7.87	100
11	500
17.8	1818
42.2	2000
124	2222

7.3.6.1 Boost Cycle-by-Cycle Current Limit

The voltage between ISNS and ISNSGND is used for both boost DC/DC controller's current sensing and cycle-by-cycle current limit settings. When the cycle-by-cycle current limit is reached, the controller will turn off the switching MOSFET immediately and turn on it again in next siwtching cycle. This cycle-by-cycle current limit could be used as a common protection for all related DC/DC components (inductor, schottky diode and switching MOSFET) to avoid current running over their max limit. Cycle-by-Cycle current limit won't trigger any faults of the device.

$$I_{CYCLE_LIMIT} = \frac{V_{ISNS}}{R_{SENSE}}$$
(1)

where

V_{ISNS} = 200 mV

7.3.6.2 Controller Min On/Off Time

The device boost DC/DC controller has minimum on/off time as below table. Minimum off time should be specially taken care in system design. The SW node rising time plus falling time should be higher than minimum off time to avoid controller not turning off the MOSFET.

表 7-2. Controller Minimum On/Off Time

Frequency (kHz)	Minimum Switch OFF Time (ns)	Minimum Switch ON Time (ns)
100 to 500	150	150
1818 to 2222	40	110

7.3.6.3 Boost Adaptive Voltage Control

The TPS92391 boost DC/DC converter generates the anode voltage for the LEDs. During normal operation, boost output voltage is adjusted automatically based on the LED current sink headroom voltages. This is called adaptive boost control. The number of used LED outputs is set by LED_SET pin and only the active LED outputs are monitored to control the adaptive boost voltage. Any LED strings with open or short faults are also removed from the adaptive voltage control loop. The LED driver pin voltages are periodically monitored by the control loop and the boost voltage is raised if any of the LED outputs falls below the $V_{HEADROOM}$ threshold. The boost voltage is lowered until any of the LED outputs touch the $V_{HEADROOM}$ threshold. See $\boxed{2}$ 7-4 for how the boost voltage automatically scales based on the OUTx-pin voltage, $V_{HEADROOM}$ and $V_{HEADROOM}$ Hys.




図 7-4. Adaptive Boost Voltage Control Loop Function

The resistive divider (R_1, R_2) defines both the minimum and maximum adaptive boost voltage levels. The feedback circuit operates the same in boost and SEPIC topologies. Choose maximum boost voltage based on the maximum LED string voltage specification. Before the LED drivers are active, the boost starts up to the initial boost level. The initial boost voltage is approximately in the 88% point of minimum to maximum boost voltage. Once the LED driver channels are active, the boost output voltage is adjusted automatically based on OUTx pin voltages. The FB pin resistor divider also scales the boost OVP, OCP levels and the LED short level in HUD application.

7.3.6.3.1 FB Divider Using Two-Resistor Method

A typical FB-pin circuit uses a two-resistor divider circuit between the boost output voltage and ground.




図 7-5. Two-Resistor FB Divider Circuit

Maximum boost voltage can be calculated with Equation 2. The maximum boost voltage can be reached during OPEN string detection or if all LED strings are left disconnected.

$$V_{BOOST_MAX} = I_{SEL_MAX} \times R_1 + \left(\frac{R_1}{R_2} + 1\right) \times V_{REF}$$
(2)

where

- V_{REF}= 1.21 V
- $I_{SEL\ MAX} = 38.7 \mu A$
- R₁ / R₂ normal recommended range is 7~15

The minimum boost voltage must be less than the minimum LED string voltage. Minimum boost voltage is calculated with Equation 3:

$$V_{BOOST_MIN} = \left(\frac{R_1}{R_2} + 1\right) \times V_{REF}$$
(3)

where

V_{RFF} = 1.21 V

When the boost OVP_LOW level is reached, the boost controller stops switching the boost FET and the BSTOVPL_STATUS bit is set. The LED drivers are still active during this condition, and the boost resumes normal switching operation once the boost output level falls. The boost OVP low voltage threshold changes dynamically with current boost voltage. It is calculated in Equation 4:

$$V_{BOOST_OVPL} = V_{BOOST} + \left(\frac{R_1}{R_2} + 1\right) \times (V_{FB_OVPL} - V_{REF})$$
(4)

where

- V_{FB_OVPL} = 1.423 V
- V_{REF} = 1.21 V

When the boost OVP_HIGH level is reached the boost controller enters fault recovery mode, and the BSTOVPH_STATUS bit is set. The boost OVP high-voltage threshold also changes dynamically with current boost voltage and is calculated in Equation 5:

$$V_{BOOST_OVPH} = V_{BOOST} + \left(\frac{R_1}{R_2} + 1\right) \times (V_{FB_OVPH} - V_{REF})$$
(5)

where

- V_{FB_OVPH} = 1.76 V
- V_{RFF} = 1.21 V

When the boost UVP level is reached the boost controller starts a 110-ms OCP counter. The TPS92391 device enters the fault recovery mode and sets the BSTOCP_STATUS bit if the boost voltage does not rise above the UVP threshold before the timer expires. The boost UVP voltage threshold also changes dynamically with current boost voltage and is calculated in Equation 6:



$$V_{BOOST_UVP} = V_{BOOST} - \left(\frac{R_1}{R_2} + 1\right) \times (V_{REF} - V_{UVP})$$
(6)

where

- V_{UVP} = 0.886 V
- V_{RFF} = 1.21 V

7.3.6.3.2 FB Divider Using Three-Resistor Method

A FB-pin circuit using a three-resistor divider circuit can be used for applications where less than 200-k Ω resistors are required.




図 7-6. Three-Resistor FB Divider Circuit

Maximum boost voltage can be calculated with Equation 7. The maximum boost voltage can be reached during OPEN string detection or if all LED strings are left disconnected.

$$V_{BOOST_MAX} = \left(\frac{R_1 \times R_3}{R_2} + R_1 + R_3\right) \times I_{SEL_MAX} + \left(\frac{R_1}{R_2} + 1\right) \times V_{REF}$$
(7)

where

- V_{REF} = 1.21 V
- $I_{SEL\ MAX} = 38.7 \,\mu A$
- R₁ / R₂ normal recommended range is 7 to 15

The minimum boost voltage must be less than the minimum LED string voltage. Minimum boost voltage is calculated in Equation 8:



$$V_{BOOST_MIN} = \left(\frac{R_1}{R_2} + 1\right) \times V_{REF}$$
(8)

When the boost OVP LOW level is reached the boost controller stops switching the boost FET, and the BSTOVPL STATUS bit is set. The LED drivers are still active during this condition, and the boost resumes normal switching operation once the boost output level falls. The boost OVP low voltage threshold changes dynamically with current boost voltage. It is calculated in Equation 9:

$$V_{BOOST_OVPL} = V_{BOOST} + \left(\frac{R_1}{R_2} + 1\right) \times (V_{FB_OVPL} - V_{REF})$$
(9)

where

- V_{FB_OVPL}= 1.423 V
 V_{REF}= 1.21 V

When the boost OVP LOW level is reached the boost controller enters fault recovery mode, and the BSTOVPH STATUS bit is set. The boost OVP high-voltage threshold also changes dynamically with current boost voltage and is calculated in Equation 10:

$$V_{BOOST_OVPH} = V_{BOOST} + \left(\frac{R_1}{R_2} + 1\right) \times (V_{FB_OVPH} - V_{REF})$$
(10)

where

- $V_{FB_OVPH} = 1.76 V$ $V_{REF} = 1.21 V$

When the boost UVP level is reached the boost controller starts a 110-ms OCP counter. The TPS92391 device enters the fault recovery mode and sets the BSTOCP STATUS bit if the boost voltage does not rise above the UVP threshold before the timer expires. The boost UVP voltage threshold also changes dynamically with current boost voltage and is calculated in Equation 11:

$$V_{BOOST_UVP} = V_{BOOST} - \left(\frac{R_1}{R_2} + 1\right) \times (V_{REF} - V_{UVP})$$
(11)

where

- V_{UVP} = 0.886 V
- V_{RFF}= 1.21 V

7.3.6.3.3 FB Divider Using External Compensation

The device has internal compensation network to keep the DC-DC control loop in good stability in most cases. However, an additional external compensation network could also be added on FB-pin to offer more flexibility in loop design or solving some extreme use-cases.




図 7-7. External Compensation Network

This network will create one additional pole and one additional zero in the loop.

$$f_{POLE_COMP} = \frac{1}{2\pi [(R_1 || R_2) + R_4]C_{COMP}}$$
(12)

$$f_{ZERO_COMP} = \frac{1}{2\pi R_4 C_{COMP}}$$
(13)

It could be noted that R_3 doesn't take part in the compensation. So this external compensation network could be both used in two-divider network and T-divider network with no equation change.

In real application, for example, when DC-DC loop has stability concern, putting the additional pole in 1 kHz and the additional zero in 2 kHz will suppress the loop gain by approximately 6 dB after 2 kHz. This will benefit gain margin and phase margin a lot.

7.3.6.4 Boost Sync and Spread Spectrum

Spread spectrum function could be enabled when BST_SYNC pin is high and disabled when BST_SYNC pin is low.

If an external CLK signal is on the BST_SYNC pin, the boost controller can be clocked by this signal. If the clock disappears later, the boost continues operation at the frequency defined by RBST_FSET resistor, and the spread spectrum function will be enabled or disabled depending on the final pin level of BST_SYNC.

表 7-3. Boost Synchronization Mode

BST_SYNC PIN LEVEL	BOOST CLOCK MODE	
Low (GND)	Spread spectrum disabled	
High (VDDIO)	Spread spectrum enabled	

/ww.ti.com/ja-jp

表 7-3. Boost Synchronization Mode (continued)					
BST_SYNC PIN LEVEL BOOST CLOCK MODE					
100-kHz to 2222-kHz clock frequency Spread spectrum disabled, external synchronization mode					

If using the external BST_SYNC input, the R_{BST_SET} resistor should be chosen the closest boost frequency options with the external frequency.

The spread spectrum function helps to reduce EMI noise around the switching frequency and its harmonic frequencies. The internal spread spectrum function modulates the boost frequency ±3.3% to 7.2% from the central frequency with a 200-Hz to 1.2-kHz modulation frequency. The switching frequency variation is programmable by SPREAD_RANGE register, and the modulation frequency is programmable by SPREAD_MOD_FREQ register. The spread-spectrum function cannot be used when an external synchronization clock is used.

表 7-4. Spread Spectrum Frequency Range

SPREAD_RANGE (Binary)	SWITCHING FREQUENCY VARIATION
00	±3.3%
01	±4.3%
10 (Default)	±5.3%
11	±7.2%

表 7-5. Spread Spectrum Modulation Frequency

SPREAD_MOD_FREQ (Binary)	MODULATION FREQUENCY
00 (Default)	200 Hz
01	500 Hz
10	800 Hz
11	1200 Hz

7.3.6.5 Light Load Mode

The DC-DC controller will enter into light load mode in below condition:

- V_{IN} voltage is very close to V_{OUT}
- Loading current is very low
- · PWM pulse width is very short

When DC-DC converter enters into light load mode, it stops switching occasionally to make sure output voltage won't rise up too much. It could also be called as PFM mode, since the DC-DC converter switching frequency will change in this mode.

7.3.7 LED Current Sinks

7.3.7.1 LED Output Current Setting

The maximum output LED current is set by an external resistor value. For the application only using external resistor R_{ISET} to set the maximum LED current for each string, the Equation 14 is used to calculate the current setting of all strings:

$$I_{LED} = \frac{1.21V}{R_{ISET}} \times 2580$$
(14)

The LEDx_CURRENT[11:0] registers can also be used to adjust strings current down from this maximum. The default value for LEDx_CURRENT[11:0] registers is the maximum 0xFFF(4095). Equation 15 is used to calculate the current setting of an individual string:



$$I_{LED} = \left(\frac{1.21V}{R_{ISET}} \times 2580\right) \times \left(\frac{LED_CURRENT[11:0]}{4095}\right)$$
(15)

For high accuracy of LED current, the ILED current is recommended to set in range from 30 mA to 200 mA. So the R_{ISFT} value is in the range from 15.6 k Ω to 104 k Ω .




図 7-8. LED Driver Current Setting Circuit

7.3.7.2 LED Output String Configuration

The Six LED driver channels of the TPS92391 device is configured by the LED SET resistor, which supports applications using one to Six LED strings. Resistor with 1% accuracy is needed to ensure proper operation. The driver channels can also be tied together in groups of one, two or three. This allows the TPS92391 device to drive three 400-mA LED strings, two 600-mA LED strings, or one 1200-mA LED string. The LED strings are always appropriately phase shifted for their string configuration. This reduces the ripple seen at the boost output, which allows smaller output capacitors and reduces audible ringing in the capacitors. Phase shift increases the load frequency, which can move potential capacitor noise above the audible band while still keeping PWM frequency low to support a higher dimming ratio.

When the TPS92391 device is firstly powered on, the string configuration is configured by the LED SET resistor and the phases of each channel are automatically configured. The LED string configuration must not be changed unless the TPS92391 is powered off in shutdown state. The unused LEDx pins should be tied to ground.

表 7-6. LED Output String Configuration

z · · · · === · · · · · · · · · · · · ·								
R_LED_SET (kΩ)	CONFIGURATION	OUT1	OUT2	ОИТ3	OUT4	OUT5	ОИТ6	AUTOMATIC PHASE SHIFT
3.92	6 Channels	200 mA	200 mA	60°				
4.75	5 Channels	200 mA	(Tied to GND)	72°				
5.76	4 Channels	200 mA	200 mA	200 mA	200 mA	(Tied to GND)	(Tied to GND)	90°

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



表 7-6	. LED (Output	String	Configu	ration	(cont	tinued)

R_LED_SET (kΩ)	CONFIGURATION	OUT1	OUT2	ОПТ3	OUT4	OUT5	ОИТ6	AUTOMATIC PHASE SHIFT
7.87	3 Channels	200 mA	200 mA	200 mA	(Tied to GND)	(Tied to GND)	(Tied to GND)	120°
11	2 Channels	200 mA	200 mA	(Tied to GND)	(Tied to GND)	(Tied to GND)	(Tied to GND)	180°
17.8	3 Channels	400	mA	400	mA	40	0 mA	120°
42.2	2 Channels	600 mA		A	600 mA		180°	
124	1 Channels		1200 mA					None

7.3.7.3 LED Output PWM Clock Generation

The LED PWM frequency is asynchronous from the input PWM frequency. The LED PWM frequency is generated from the internal 20-MHz oscillator and can be set to eight discrete frequencies from 152 Hz to 19.531 kHz. The PWM dimming resolution is highest when the lowest PWM frequency is used. The PWM_FSET resistor determines the LED PWM frequency based on 表 7-8. PWM resolution in 表 7-8 is with PWM dither disabled.

7.3.8 Brightness Control

The TPS92391 supports global brightness control for all LED strings through either duty cycle input on PWM pin or register by I2C bus. An internal 20-MHz clock is used for generating PWM outputs.

7.3.8.1 Brightness Control Signal Path

The BRT_MODE register selects whether the input to the display brightness path is the PWM input pin or DISP_BRT register. PWM input control will be the default setup after power on. The brightness control signal path diagram is shown in ⊠ 7-9

The display brightness path has sloper function that can be enabled. By default the sloper function is enabled. The sloper and dither function also can be programmable by I2C control. The sloper function is described in セクション 7.3.8.7, and the dither function is described in セクション 7.3.8.9.




図 7-9. TPS92391 Brightness Path Diagram

7.3.8.2 Dimming Mode

Dimming mode can be adjusted via an external resistor to MODE pin (see 表 7-7). Resistor with 1% accuracy is needed to ensure proper operation.

表 7-7. Dimming Mode Configuration

R_MODE (kΩ)	MODE	I2C Address
3.92	Phase-shift PWM Mode	0x2B
4.75	Hybrid Mode	0x2B
5.76	Current Dimming Mode	0x2B

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

表 7-7. Dimming Mode Configuration (continued)

R_MODE (kΩ)	MODE	I2C Address
7.87	Direct PWM Mode	0x2B
11	Phase-shift PWM Mode	0x2A
17.8	Hybrid Mode	0x2A
42.2	Current Dimming Mode	0x2A
124	Direct PWM Mode	0x2A

7.3.8.3 LED Dimming Frequency

The LED dimming frequency is asynchronous from the input PWM frequency for phase-shift PWM mode and hybrid dimming mode. The LED dimming frequency is generated from the internal 20-MHz oscillator and can be set to eight discrete frequencies from 152 Hz to 19.531 kHz. The PWM dimming resolution is highest when the lowest PWM frequency is used. The PWM_FSET resistor determines the LED Dimming frequency based on 表 7-8. Resistor with 1% accuracy is needed to ensure proper operation. PWM resolution in 表 7-8 is with PWM dither disabled.

表 7-8. LED PWM Frequency Selection

R_PWM_FSET (kΩ)	LED PWM FREQUENCY (Hz)	PWM DIMMING RESOLUTION (bits)
3.92	152	16
4.75	305	16
5.76	610	15
7.87	1221	14
11	2441	13
17.8	4883	12
42.2	9766	11
124	19531	10

7.3.8.4 Phase-Shift PWM Mode

In Phase-Shift PWM mode, all current active channels are turned on and off at LED dimming frequency with a constant delay. However, the number of used channels or channel groups determine the phase delay time between two neighboring channels as shown in \boxtimes 7-10.

Product Folder Links: TPS92391

Submit Document Feedback




図 7-10. Phase-shift Dimming Diagram

7.3.8.5 Hybrid Mode

In addition to phase-shift PWM dimming, TPS92391 supports a hybrid-dimming mode. Hybrid dimming combines PWM and current modes for brightness control for the display brightness path. By using hybrid dimming, dimming ratio could be increased by another 8 times. In hybrid mode, PWM dimming is used for low brightness range of brightness, and current dimming is used for high brightness levels as shown in 区 7-11. Current dimming control enables improved optical efficiency due to increased LED efficiency at lower currents. PWM dimming control at low brightness levels ensures linear and accurate control. Hybrid mode can be selected through resistor value at MODE pin as 表 7-7. The PWM and current modes transition threshold can be set at 12.5% or at 0% brightness. The latter selection allows for pure current dimming control mode.




図 7-11. Hybrid Dimming Diagram

7.3.8.6 Direct PWM Mode

In direct PWM mode, all active channels are turned on and off and are synchronized with the input PWM signal.




図 7-12. Direct PWM Dimming Diagram

7.3.8.7 Sloper

An optional sloper function makes the transition from one brightness value to another optically smooth. By default the advanced sloper is enabled with a 200-ms linear sloper duration. Transition time between two brightness values is programmed with the SLOPE_SELECT[2:0] bits (when 000, sloper is disabled). With advanced sloper enabled the brightness changes are further smoothed to be more pleasing to the human eye. Advanced slope is enabled with ADV_SLOPE_ENABLE register bit.




図 7-13. Brightness Sloper

7.3.8.8 PWM Detector Hysteresis

PWM detector has an internal hysteresis function. It means when PWM input is used (except direct PWM mode), PWM output duty cycle will change only when PWM input on-time changes by more than 6.4us. This is to avoid the PWM duty cycle sampling error due to the onboard PWM signal's rising/falling time.

7.3.8.9 Dither

The number of brightness steps when using LED output PWM dimming is equal to the 20-MHz oscillator frequency divided by the LED PWM frequency (set by PWM_FSET resistor). The PWM duty cycle dither is a function the TPS92391 uses to increase the number of brightness dimming steps beyond this oscillator clock limitation. The dither function modulates the LED driver output duty cycle over time to create more possible average brightness levels. The DITHER_SELECT[3:0] register bits control the level of dither, disabled, 1, 2, 3 or 4 bits using the I2C interface. By default the dither is disabled.

When the 1-bit dither is selected, to support higher brightness resolution, the width of every second PWM pulse could be increased by one LSB (one 20-MHz clock period). When the 3-bit dither is selected, within a sequence of 8 PWM periods the number of pulses with increased length varies depending on the dither value: dither value 000 - all 8 pulses at default length; 001 - one of the 8 pulses is longer; 010 - two of the 8 pulses are longer, and so forth, until at 111 - seven of the 8 pulses have increased length. $\mbox{ } \mbox{ } \mbo$






図 7-14. PWM Dither Example

The dither block also helps in low brightness scenario when dimming ratio is limited by LED PWM output frequency and the LED output pulse is less than the minimum pulse width (200 ns). In such scenario, the dither block will skip some of the PWM pulses to reduce the brightness further, enabling high dimming ratio. The end result is that the LED PWM frequency is reduced as more and more minimum pulses are skipped or dithered out. At the same time, dither block will also guarantee that the minimum LED PWM frequency is not less than 152 Hz to ensure no brightness flickering. \boxtimes 7-15 shows how the dither works in low brightness scenario.




図 7-15. Minimum Brightness Dither Example

7.3.9 Protection and Fault Detections

The TPS92391 device includes fault detections for LED open, short and short-to-GND conditions, boost input undervoltage, overvoltage and overcurrent, boost output overvoltage and overcurrent, VDD undervoltage, die overtemperature and external components. The host can monitor the status of the faults in registers SUPPLY FAULT STATUS, BOOST FAULT STATUS and LED STATUS.

7.3.9.1 Supply Faults


7.3.9.1.1 V_{IN} Undervoltage Faults (VINUVLO)

The TPS92391 device supports V_{IN} undervoltage and overvoltage protection. The undervoltage threshold is programmable through external resistor divider on UVLO pin. If during operation of the TPS92391 device, the UVLO pin voltage falls below the UVLO falling level (0.787 V typical), the boost, LED outputs, and power-line FET will be turned off, and the device will enter STANDBY mode. The VINUVLO_STATUS bit is also set in the SUPPLY_FAULT_STATUS register, and the INT pin is triggered. When the UVLO voltage rises above the rising threshold level the TPS92391 exits STANDBY and begins the start-up sequence.

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated





☑ 7-16. V_{IN} UVLO Setting Circuit

The following equation is used to calculate the UVLO threshold for VIN rising edge:

$$VIN_{UVLO_RISING} = (\frac{R_4}{R_5} + 1) \times VIN_{UVLO_TH}$$
(16)

where

VIN_{UVLO} TH = 0.787 V

The hysteresis of UVLO threshold can be designed and calculated with the following equation.

$$VIN_{HYST} = R_4 \times I_{UVLO}$$
(17)

where

• I_{UVLO} = 5 μA

So the following equation can be used for UVLO threshold for VIN falling edge:

$$VIN_{UVLO_FALLING} = VIN_{UVLO_RISING} - VIN_{HYST}$$
(18)

The bottom resistors, R_5 of voltage divider is able to be disconnected to the GND through an additional external N-type of FET as \boxtimes 7-17. This design is to minimize the current leakage from VIN in shutdown mode to extend the battery life.




図 7-17. VIN UVLO Setting Circuit Without Current Leakage Path

7.3.9.1.2 V_{IN} Overvoltage Faults (VINOVP)

The overvoltage threshold for V_{IN} rising edge is internal fixed at typical 43 V. If during TPS92391 operation, VSENSE_P pin voltage rises above the OVP rising threshold, boost, LED outputs, and power-line FET will be turned off, and the device will enter STANDBY mode. The VINOVP_STATUS bit will also be set in the SUPPLY_FAULT_STATUS register, and the INT pin will be triggered. When the VSENSE_P pin voltage falls below the falling threshold level, the TPS92391 exits STANDBY and begins the start-up sequence.

7.3.9.1.3 V_{DD} Undervoltage Faults (VDDUVLO)

If during TPS92391 device operation VDD falls below VDDUVLO falling level, boost, power-line FET, and LED outputs are turned off, and the device enters STANDBY mode. The VDDUVLO_STATUS fault bit will be set in the SUPPLY_FAULT_STATUS register, and the INT pin will be triggered. The TPS92391 restarts automatically to ACTIVE mode when V_{DD} rises above VDDUVLO rising threshold.

7.3.9.1.4 V_{IN} OCP Faults (VINOCP)

If during TPS92391 device operation voltage drop on RISENSE resistor rises above 220 mV, boost, power-line FET, and LED outputs are turned off, and the device enters Fault Recovery mode and then attempt to restart 100 ms after fault occurs. The VINOCP_STATUS fault bit are set in the SUPPLY_FAULT_STATUS register, and the INT pin is triggered.

$$I_{VIN_OCP} = \frac{VIN_{OCP_TH}}{R_{ISENSE}}$$
(19)

where

VIN_{OCP TH} = 220 mV

7.3.9.1.4.1 VIN OCP Current Limit vs. Boost Cycle-by-Cycle Current Limit

VIN OCP current limit is totally different from boost cycle-by-cycle current limit.

Boost cycle-by-cycle current limit is to protect the DC/DC components (inductor, schottky diode and switching MOSFET) in normal scenario, avoiding current running over their max limit. The normal scenario means when loading has sharp change or input voltage has sharp change. It won't trigger any device fault.

VIN OCP current limit is to protect system from ciritical system hazard (e.g, inductor short, switching MOSFET short). It will trigger the device to shutdown all the LED channels and enter into fault recovery state.

VIN OCP current limit should be always greater than boost cycle-by-cycle current limit. This means R_{ISENSE} should be always no smaller than R_{SENSE} .

7.3.9.1.5 Charge Pump Faults (CPCAP, CP)

If during TPS92391 device operation voltage of CPUMP pin falls below typical 4.2-V, boost, power-line FET, and LED outputs are turned off, and the device enters Fault Recovery mode and then attempt to restart 100 ms after fault occurs. The CP_STATUS fault bit will beset in the SUPPLY_FAULT_STATUS register, and the INT pin are triggered.

If during TPS92391 device initialization, the charge pump fly capacitor is disconnected or shorted, charge pump are turned off. In result, boost, power-line FET, and LED outputs are turned off, and the device enters Fault Recovery mode and then attempt to restart 100 ms after fault occurs. Both CPCAP_STATUS and CP_STATUS fault bits are set in the SUPPLY_FAULT_STATUS register, and the INT pin are triggered.

7.3.9.1.6 CRC Error Faults (CRCERR)

If during TPS92391 device initialization, the factory default configuration for registers, options and trim bits are not corrected loaded from memory, TPS92391 keeps operating normally, unless other fault criteria is triggered. The CRCERR_STATUS fault bit are set in the SUPPLY_FAULT_STATUS register and the INT pin are triggered.

7.3.9.2 Boost Faults

7.3.9.2.1 Boost Overvoltage Faults (BSTOVPL, BSTOVPH)

Boost overvoltage is detected if the FB pin voltage exceeds the V_{FB_OVPL} threshold. When boost overvoltage is detected, BSTOVPL_STATUS bit will be set in the BOOST_FAULT_STATUS register. The boost FET stops switching, and the output voltage will be automatically limited. If the BSTOVPL_STATUS bit is continually set (that is, reappears after clearing), it may indicate an loop issue in the application. Boost overvoltage low is monitored during device Boost Softstart and Normal mode.

A second boost overvoltage high fault is detected if the FB pin voltage exceeds the V_{FB_OVPH} threshold or the DISCHARGE pin voltage exceeds the V_{BST_OVPH} . The TPS92391 device enters the fault recovery state to protect system damage from a high boost voltage. When boost overvoltage is detected, BSTOVPH_STATUS bit is set in the BOOST_FAULT_STATUS register. A fault interrupt is also generated. The device enters Fault Recovery mode and then attempt to restart after 100 ms. Boost overvoltage high is monitored during Boost Softstart and Normal mode.

7.3.9.2.2 Boost Overcurrent Faults (BSTOCP)

Boost overcurrent is detected if the FB pin voltage drops below the V_{UVP} threshold for 110 ms. If the boost overcurrent timer expires before the output voltage recovers, the BSTOCP_STATUS bit is set in the BOOST_FAULT_STATUS register. The fault recovery state is entered, and a fault interrupt is generated. The device will enter Fault Recovery mode and then attempt to restart after 100 ms. If the BSTOCP_STATUS bit is permanently set, it may indicate an issue in the application. Boost overcurrent is monitored from the boost start, and fault may trigger during boost start-up.

7.3.9.2.3 LEDSET Resistor Missing Faults (LEDSET)

The LEDSET resistor missing or invalid is detected if the resistor is not assembled or not valid value as requested during the initialization. The TPS92391 device defaults to 6-channel/200-mA configuration if the LEDSET resistor is missing or invalid. The LEDSET_STATUS fault bit is set in the BOOST_FAULT_STATUS register. The LEDSET resistor missing or invalid fault will not be monitored after initialization, so that the TPS92391 is operating in the configuration determined during initialization even though the LEDSET resistor is missing or invalid after initialization.

7.3.9.2.4 MODE Resistor Missing Faults (MODESEL)

The MODE resistor missing or invalid is detected if the resistor is not assembled or not valid value as requested during the initialization. TPS92391 defaults to phase-shift PWM mode with I2C address 0x2A if the MODE resistor is missing or invalid. The MODESEL_STATUS fault bit will be set in the BOOST_FAULT_STATUS register. The MODE resistor missing or invalid fault is not monitored after initialization, so that the TPS92391 operates in the mode determined during initialization even though the MODE resistor is missing or invalid after initialization.



7.3.9.2.5 FSET Resistor Missing Faults (FSET)

The FSET resistor missing or invalid for both BOOST_FSET and PWM_FSET is detected if any one of them is not assembled or not a valid value as requested during the initialization. TPS92391 defaults the switching frequency of boost to 400 kHz if BOOST_FSET resistor is missing or invalid, or PWM dimming frequency to 305 Hz if PWM_FSET resistor is missing or invalid. The FSET_STATUS fault bit is set in the BOOST_FAULT_STATUS register. The FSET resistor missing or invalid fault is not monitored after initialization, so that the TPS92391 device operates at the boost switching frequency and the PWM dimming frequency determined during initialization even though the FSET resistor is missing or invalid after initialization.

7.3.9.2.6 ISET Resistor Out of Range Faults (ISET)

If the ISET pin resistor is shorted to GND during normal operation, the maximum current for each LED channel can be calculated in Equation 20:

$$I_{LED_ISET_FAULT} = I_{LED_LIMIT} \times \left(\frac{LED_CURRENT[11:0]}{4095}\right)$$
(20)

where

• I_{LED_LIMIT} = 280 mA

LED_CURRENT[11:0] register will be automatically modified to 1/4 of latest programmed data. if it is not programmed after device enabling, the default value of LED_CURRENT[11:0] register is 0xFFF and automatically modified to 0x3FF after the fault occurs. If ISET pin voltage returns back to above 1.1 V, the LED_CURRENT[11:0] register data automatically returns to latest programmed data. The ISET_STATUS fault bit will be set in the BOOST_FAULT_STATUS register and the INT pin is triggered.

7.3.9.2.7 Thermal Shutdown Faults (TSD)

If the die temperature of TPS92391 reaches the thermal shutdown threshold T_{SD} , the boost, power-line FET, and LED outputs on TPS92391 shuts down to protect the device from damage. Fault status bit TSD_STATUS bit will be set, and the INT pin will be triggered. The device restarts the power-line FET, the boost, and LED outputs when temperature drops by TSD_HYS amount.

7.3.9.3 LED Faults

7.3.9.3.1 Open LED Faults (OPEN_LED)

During normal boost operation, boost voltage is raised if any of the used LED outputs falls below the LED_DRV_HEADROOM threshold level. Open LED fault is detected if boost output voltage has reached the maximum and at least one LED output is still below the threshold. The open string is then disconnected from the boost adaptive control loop and its output is disabled. Any LED fault sets the status bit LED_STATUS and an interrupt is generated unless LED interrupt is disabled. The detail of open LED faults can be read from bits OPEN_LED and LEDx_FAULT (x = 1...6). These bits maintain their value until device power-down. But the LED_STATUS bit could be cleared by the interrupt clearing procedure. If a new LED fault is detected, LED STATUS is set and an interrupt generated again.




図 7-18. LED Open and Short Detection Logic

7.3.9.3.2 Short LED Faults (SHORT_LED)

Short LED fault is detected if one or more LED outputs are above the VLEDSHORT typical 5.4 V and at least one LED output is inside the normal operation window (see 🗵 7-18). Shorted string is disconnected from the boost adaptive control loop and the LED PWM output is disabled. LED STATUS status bit is set and an interrupt generated similarly as in open LED case. Detailed shorted LED fault can be read from bits SHORT_LED and LEDx_FAULT (x = 1...6), indicating the faulty LED) in LED_FAULT_STATUS register.

In HUD application, when output channels are connected as groups and only one or two groups are active, one more special condition will trigger the short LED fault. This is when boost adaptive voltage comes to minimum and one of the LED channels voltage is still higher than V_{HEADROOM} + V_{HEADROOM} HYS.

7.3.9.3.3 LED Short to GND Faults (GND_LED)

During boost soft start and normal boost operation, if LED output is lower than V_{SHORTGND} for 20 ms, device turns off the corresponding LED output channel and output a typical 6-mA current for 300-µs period again. After this operation, if output voltage is still lower than V_{HEADROOM}, LED short to GND fault will be reported.

If LED short to GND is reported, boost, LED outputs and power-line FET is turned off, the device will enter Fault Recovery mode. LED STATUS bit is set and an interrupt generated similarly as in open LED case. LED short to GND fault reason can be read from bits LED GND and LEDx FAULT (x = 1...6) in LED FAULT STATUS register. These bits maintain their value until device powers are down while the LED STATUS bit is cleared by the interrupt clearing procedure.

7.3.9.3.4 Invalid LED String Faults (INVSTRING)

During device initialization, any of un-used LED outputs pins are checked whether connected to GND or not. If they are not connected to GND as expected, the TPS92391 reports invalid string fault and tries to function normally if possible. The INVSTRING_STATUS fault bit is set in the LED_FAULT_STATUS register, and the INT pin is triggered. The LEDSET resistor missing or invalid fault is not detected after initialization, so that the TPS92391 operates in the configuration determined during initialization even though the LEDSET resistor is missing or invalid after initialization.



7.3.9.3.5 I2C Timeout Faults

If chip receives I2C command without STOP signal for 500 ms, I2C communication block auto resets and waits for the next command. I2C_ERROR_STATUS fault bit is set in the LED_FAULT_STATUS register, and the INT pin is triggered.

English Data Sheet: SNVSBY8



7.3.9.4 Overview of the Fault and Protection Schemes

表 7-9. Fault and Protection Schemes

FAULT NAME	STATUS BIT	CONDITION	TRIGGER FAULT INTERRUPT	ENTER FAULT RECOVERY	ACTION
V _{IN} undervoltage	VINUVLO_STATUS	UVLO voltage falls below 0.787 V.	Yes	Yes	Device goes to standby and then attempts to restart once the input voltage rises above threshold.
V _{IN} overvoltage	VINOVP_STATUS	V _{IN} voltage rises above 43 V.	Yes	Yes	Device goes to standby and waits until input voltage falls below threshold before restarting.
V _{DD} undervoltage	VDDUVLO_STATUS	V _{DD} level falls below VDDUVLO threshold.	Yes	No	Device restarts once VDD level rises above VDDUVLO threshold.
V _{IN} overcurrent	VINOCP_STATUS	Voltage across R _{ISENSE} exceeds 220 mV.	Yes	Yes	Device goes to Fault Recovery and then attempts to restart 100 ms after fault occurs.
Charge pump fault	CP_STATUS	Charge pump voltage level is abnormal.	Yes	Yes	Device goes to Fault Recovery and then attempts to restart 100 ms after fault occurs.
Charge pump components missing	CPCAP_STATUS	Charge pump is missing components.	Yes	No	Charge pump is disabled. Charge pump fault will be reported. Device tries to keep normal operation.
Boost sync clock invalid fault	BSTSYNC_STATUS	Device is enabled while a valid external SYNC clock is running. Then SYNC stops or changes to frequency < 75 kHz.	Yes	No	Defaults to internal clock frequency selected by BST_FSET resistor. If BST_SYNC input is held high then spread spectrum is enabled. If BST_SYNC input is held low then spread spectrum is disabled.
CRC error	CRCERR_STATUS	Factory default configuration for registers, options and trim bits are not correctly loaded from memory.	Yes	No	Device functions normally, if possible.
Boost OVP low	BSTOVPLOW_STATUS	FB pin voltage rises above V _{FB_OVPL} level.	No	No	Boost stops switching until boost voltage level falls. The device remains in normal mode with LED drivers operational.
Boost OVP high	BSTOVPH_STATUS	FB pin voltage rises above V _{FB_OVPH} level or DISCHARGE pin voltage rises above V _{BST_OVPH} .	Yes	Yes	Device goes to Fault Recovery and waits until output voltage falls below threshold before restarting.
Boost overcurrent	BSTOCP_STATUS	FB pin voltages falls below V _{UVP} level for 110 ms.	Yes	Yes	Device goes to Fault Recovery and then attempts to start 100 ms after fault occurs.
LEDSET detection fault	LEDSET_STATUS	LEDSET resistor missing or invalid.	No	No	Defaults to 6-channel / 200mA configuration.
MODE detection fault	MODESEL_STATUS	MODE resistor missing or invalid.	No	No	Defaults to phase-shift PWM mode, I2C address is 0x2A.
FSET detection fault	FSET_STATUS	BST_FSET or PWM_FSET resistor are missing or an invalid value.	No	No	Device keeps operating at 400-kHz switching frequency for boost converter and 305 Hz for PWM dimming frequency.

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

35



表 7-9. Fault and Protection Schemes (continued)

FAULT NAME	STATUS BIT	CONDITION	TRIGGER FAULT INTERRUPT	ENTER FAULT RECOVERY	ACTION
ISET resistor fault	ISET_STATUS	ISET pin voltage is pulled down to below 1V due to ISET pin resistor shorted to GND	Yes	No	LED_CURRENT[11:0] is written to 0x3FF. Total LED current limited to 70 mA.
Thermal shutdown	TSD_STATUS	Junction temperature rises above T _{SD} threshold.	Yes	Yes	Device goes to standby and then attempts to restart once die temperature falls below threshold.
Open LED string	LED_STATUS OPEN_LED	Headroom voltage on one or more channels is below minimum level and boost has adapted to maximum level.	Yes	No	Faulted LED string is disabled and removed from adaptive boost control loop. String is re-enabled next power cycle.
LED internal short	LED_STATUS_SHORT_L ED	Headroom voltage on one or more channels is above the SHORTED_LED_THRESHOLD for > 5 ms while the headroom of at least one channel is still below this threshold.	Yes	No	Faulted LED string is disabled and removed from adaptive boost control loop. String is re-enabled next power cycle.
LED short to GND	LED_STATUS_GND_LE D	During PL FET SOFT START, voltage of one or more used LED output is below V _{HEADROOM} when small test current is injected. In BOOST_SU and Normal Stage, voltage of one or more used LED output is below V _{SHORTGND} .and keeps still when the corresponding channel is off and small test current is injected.	Yes	Yes	Device goes to Fault Recovery and then attempts to restart 100 ms after fault occurs.
Invalid LED string detected	INVSTRING_STATUS	Configured unused LED output is detected not short to GND.	Yes	No	Device functions normally, if possible.
I2C timeout	I2C_ERROR_STATUS	Device receives I2C command without STOP signal for 500 ms.	Yes	No	Device functions normally and waits for the next I2C command.

Submit Document Feedback Copyright © 2023 Texas Instruments Incorporated

7.4 Device Functional Modes

7.4.1 State Diagram




図 7-19. State Machine Diagram

7.4.2 Shutdown

When EN is pulled low, boost, power-line FET, and LED outputs are turned off, and the device tries to discharge the boost output for 400 ms. After this, the device is totally turned off.

7.4.3 Device Initialization

After POR is released device initialization begins. During this state the LDO is started up, EEPROM default and trim configurations are loaded, LEDSET, MODE, BOOST_FSET and PWM_FSET resistors are detected.

7.4.4 Standby Mode

Starting from Standby mode, the device can be accessed with I2C to change any configuration registers.

Standby Mode is immediately switched to Power-line FET Soft Start mode if there's no fault.

7.4.5 Power-line FET Soft Start

Power-line FET is gradually enabled during this 25ms long state. Boost input and output capacitors are charged to V_{IN} level. V_{IN} faults for OCP, OVP, and UVP and fault for LED short to GND are enabled.

7.4.6 Boost Start-Up

Boost voltage is ramped to initial boost voltage level with reduced current limit for 50 ms. All boost faults are now enabled.

Product Folder Links: TPS92391

7.4.7 Normal Mode

LED drivers are enabled when brightness is greater than zero. All LED faults are active.



7.4.8 Fault Recovery

Some critical faults can trigger fault recover state. LED drivers, boost converter, and power-line FET are disabled for 100 ms, and the device attempts to restart from standby mode if EN is still high and brightness is greater than zero.

7.4.9 Latch Fault

If all LED strings are disabled due to faults then the TPS92391 enters the latch fault mode. This state can be exited only by pulling the EN pin low.

7.4.10 Start-Up Sequence




図 7-20. Start-Up Sequence Diagram


7.5 Programming

7.5.1 I2C-Compatible Interface

The TPS92391 device supports I2C interface to access and change the configuration. The 7-bit base slave address is 0x2A or 0x2B. The address could be configured through the resistor settings of MODE pin.

Write I2C transactions are made up of 4 bytes. The first byte includes the 7-bit slave address and Write bit. The 7-bit slave address selects the TPS92391 slave device. The second byte is eight bits register address. The last two bytes are the 16-bit register value.

Read I2C transactions are made up of 5 bytes. The first byte includes the 7-bit slave address and Write bit. The 7-bit slave address selects the TPS92391 slave device. The second byte is eight bits register address. The third byte includes the 7-bit slave address and Read bit. The last two bytes are the 16-bit register value returned from the slave.




where



W bit = 1

図 7-21. I2C Write



where

- R bit = 0
- W bit = 1

図 7-22. I2C Read

7.5.2 Programming Examples

7.5.2.1 General Configuration Registers

The TPS92391 does not require any serial interface configuration. It can be simply controlled with the EN pin and PWM pin. Most of the device configuration is accomplished using external resistor values. If I2C interface is available then extended configuration is possible. The configuration registers can be written from standby state to normal state as shown in \pm 7-10.

表 7-10. Configuration Registers

REGISTER NAME	FUNCTION
ADV_SLOPE_ENABLE	Enables advance sloper S-shape smoothing function.
DITHER_SELECT	Selects up to 3 bits of PWM dither for added dimming resolution.
SLOPE_SELECT	Selects duration for linear brightness sloper.
BRT_MODE	Selects PWM pin or DISPLAY_BRT register for brightness control.
SPREAD_RANGE	Selects up to 2 bits boost switching frequency spread spectrum range.
SPREAD_MOD_FREQ	Selects up to 2 bits boost switching frequency spread spectrum modulation frequency.
SPREAD_PSEUDO_EN	Enables pseudo random modulation for boost switching spread spectrum frequency.

7.5.2.2 Clearing Fault Interrupts

The TPS92391 has an INT pin to alert the host when a fault occurs. If I2C interface is available, the Interrupt Fault Status registers can be read back to learn which fault(s) have been detected. These status bits are located in the SUPPLY STATUS, BOOST STATUS and LED STATUS registers. Each interrupt status has a STATUS bit and a CLEAR bit. To clear a fault interrupt status a 1 must be written to both the STATUS bit and CLEAR bit at the same time.

7.5.2.3 Disabling Fault Interrupts

By default, most of the TPS92391 faults trigger the INT pin. Each fault has two INT EN bits. These bits are located in the SUPPLY INT EN, BOOST INT EN, and LED INT EN registers. If the INT EN bit is read and returns 2b'10, the INT pin is triggered when that fault occurs. The fault interrupt can be disabled by writing 2b'01 to its INT EN bits, or it can be enabled by writing 2b'11 to its INT EN bits. There is also a GLOBAL fault interrupt that can be disabled to prevent any faults from triggering the INT pin.

7.5.2.4 Diagnostic Registers

The TPS92391 contains several diagnostic registers than can be read with the serial interface for debugging or additional device information. 表 7-11 is a summary of the available registers.

表 7-11. Diagnostic Registers

REGISTER NAME	FUNCTION
FSM_LIVE_STATUS	Current state of the functional state machine

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback



表 7-11. Diagnostic Registers (continued)

REGISTER NAME	FUNCTION
PWM_INPUT_STATUS	Measured 16-bit duty cycle of the PWM pin input
LED_PWM_STATUS	16-bit LED PWM duty cycle from state machine
LED_CURRENT_STATUS	12-bit LED current DAC value from state machine
VBOOST_STATUS	10-bit value for adaptive boost voltage target — value is linear between VBOOST_MIN and VBOOST_MAX calculations
MODE_SEL_CFG	Dimming mode configuration from MODE detection
LED_STRING_CFG	LED string phase configuration from LEDSET detection
BOOST_FREQ_SEL	Boost switching frequency value from BST_FSET detection
PWM_FREQ_SEL	LED PWM frequency value from PWM_FSET detection



7.6 Register Maps

7.6.1 FullMap Registers

表 7-12 lists the memory-mapped registers for the FullMap registers. All register offset addresses not listed in 表 7-12 should be considered as reserved locations and the register contents should not be modified.

表 7-12. FULLMAP Registers

Offset	Acronym	Register Name	Section
00h	BRT_CONTROL	Display Brightness	Go
02h	LED_CURR_CONFIG	LED Current	Go
04h	USER_CONFIG1	User Config 1	Go
06h	USER_CONFIG2	User Config 2	Go
08h	SUPPLY_INT_EN	Supply Interrupt Enable	Go
0Ah	BOOST_INT_EN	Boost Interrupt Enable	Go
0Ch	LED_INT_EN	LED Interrupt Enable	Go
0Eh	SUPPLY_STATUS	Supply Fault Status	Go
10h	BOOST_STATUS	Boost Fault Status	Go
12h	LED_STATUS	LED Fault Status	Go
14h	FSM_DIAGNOSTICS	Device State Diagnostics	Go
16h	PWM_INPUT_DIAGNOSTICS	PWM Input Diagnostics	Go
18h	PWM_OUTPUT_DIAGNOSTICS	PWM Output Diagnostics	Go
1Ah	LED_CURR_DIAGNOSTICS	LED Current Diagnostics	Go
1Ch	ADAPT_BOOST_DIAGNOSTICS	Adaptive Boost Diagnostics	Go
1Eh	AUTO_DETECT_DIAGNOSTICS	Auto Detect Diagnostics	Go

Complex bit access types are encoded to fit into small table cells. $\frac{1}{2}$ 7-13 shows the codes that are used for access types in this section.

表 7-13. FullMap Access Type Codes

Access Type	Code	Description						
Read Type	Read Type							
R	R	Read						
Write Type								
W	W	Write						
Reset or Default	Value							
-n		Value after reset or the default value						

7.6.1.1 BRT_CONTROL Register (Offset = 00h) [reset = 0h]

BRT_CONTROL is shown in 図 7-23 and described in 表 7-14.

Return to Summary Table.

図 7-23. BRT_CONTROL Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	DISPLAY_BRT														
R/W-0h															

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

表 7-14. BRT_CONTROL Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-0	DISPLAY_BRT	R/W	0h	Display Brightness Register

7.6.1.2 LED_CURR_CONFIG Register (Offset = 02h) [reset = 0FFFh]

LED_CURR_CONFIG is shown in 図 7-24 and described in 表 7-15.

Return to Summary Table.

図 7-24. LED_CURR_CONFIG Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
RESERVED									LED_CL	JRRENT					
R/W-0h									R/W-	FFFh					

表 7-15. LED_CURR_CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-12	RESERVED	R/W	0h	These bits are reserved.
11-0	LED_CURRENT	R/W	FFFh	LED current control for all LED outputs

7.6.1.3 USER_CONFIG1 Register (Offset = 04h) [reset = 8A3h]

USER_CONFIG1 is shown in 図 7-25 and described in 表 7-16.

Return to Summary Table.

図 7-25. GROUPING1 Register

15	14	13	12	11	10	9	8	
RESERVED	SPREAD_PSE UDO_EN	SPREAD_I	MOD_FREQ	SPREAD	_RANGE	BRT_MODE		
R/W-0h	R/W-0h	R/V	V-0h	R/W	/-2h	R/W-0h		
7	6	5	4	3	2	1	0	
	SLOPE_SELECT			DITHER_SELECT	-	ADV_SLOPE_E NABLE	RESERVED	
	R/W-5h			R/W-0h		R/W-1h	R/W-1h	

表 7-16. USER_CONFIG1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
15	RESERVED	R/W	0h	This bit is reserved.
14	SPREAD_PSEUDO_EN	R/W	0h	0h = Pseudo Random SS disabled 1h = Pseudo Random SS enabled
13-12	SPREAD_MOD_FREQ	R/W	Oh	Boost spread spectrum modulation frequency 0h = 200 Hz 1h = 500 Hz 2h = 800 Hz 3h = 1.2 kHz
11-10	SPREAD_RANGE	R/W	2h	OSC_BST spread spectrum range 0h = 3.3% 1h = 4.3% 2h = 5.3% 3h = 7.2%



表 7-16. USER_CONFIG1 Register Field Descriptions (continued)

		LIX_OOM	ri Field Descriptions (continued)		
Bit	Field	Туре	Reset	Description	
9-8	BRT_MODE	R/W	0h	Select PWM pin or DISPLAY_BRT register for brightness controll 0h = Brightness controlled by PWM input 1h = Reserved 2h = Brightness controlled by DISPLAY_BRT register 3h = Reserved	
7-5	SLOPE_SELECT	R/W	5h	Select duration for linear brightness sloper 0h = Disabled 1h = 1 ms 2h = 2 ms 3h = 50 ms 4h = 100 ms 5h = 200 ms 6h = 300 ms 7h = 500 ms Times are for linear slope mode. Advanced sloper will increase durations while adding additional smoothing to brightness transitions. 1 ms and 2 ms sloper times are intended to be used only in linear mode. 50 ms to 500 ms sloper durations may be used with or without advanced sloper function.	
4-2	DITHER_SELECT	R/W	Oh	Dither mode select 0h = Dither Disabled 1h = 1-bit Dither 2h = 2-bit Dither 3h = 3-bit Dither 4h = 4-bit Dither	
1	ADV_SLOPE_ENABLE	R/W	1h	0h = Linear Sloping 1h = Advanced Sloping	
0	RESERVED	R/W	1h	This bit is reserved.	

7.6.1.4 USER_CONFIG2 Register (Offset = 06h) [reset = 100h]

USER_CONFIG2 is shown in 図 7-26 and described in 表 7-17.

Return to Summary Table.

図 7-26. USER CONFIG2 Register

15	14	13	12	11	10	9	8		
	RESERVED								
	R/W-0h								
7	6	5	4	3	2	1	0		
RESE	RVED	LED6_SHORT_ DISABLE	LED5_SHORT_ DISABLE	LED4_SHORT_ DISABLE	LED3_SHORT_ DISABLE	LED2_SHORT_ DISABLE	LED1_SHORT_ DISABLE		
R/V	V-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h		

表 7-17. USER_CONFIG2 Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-9	RESERVED	R/W	0h	These bits are reserved.



表 7-17. USER_CONFIG2 Register Field Descriptions (continued)

Bit	Field	Type	Reset	Description (continued)
8	EN_LED_GND_DETECT	R/W	1h	Enable LED short to ground detection during Boost_SS and normal stage 0h = Disable 1h = Enable
7-6	RESERVED	R/W	0h	These bits must write 0 for normal operation.
5	LED6_SHORT_DISABLE	R/W	Oh	Disable LED string6 internal short fault. 0h = Enable 1h = Disable
4	LED5_SHORT_DISABLE	R/W	Oh	Disable LED string5 internal short fault. 0h = Enable 1h = Disable
3	LED4_SHORT_DISABLE	R/W	Oh	Disable LED string4 internal short fault. 0h = Enable 1h = Disable
2	LED3_SHORT_DISABLE	R/W	Oh	Disable LED string3 internal short fault. 0h = Enable 1h = Disable
1	LED2_SHORT_DISABLE	R/W	Oh	Disable LED string2 internal short fault. 0h = Enable 1h = Disable
0	LED1_SHORT_DISABLE	R/W	Oh	Disable LED string1 internal short fault. 0h = Enable 1h = Disable

7.6.1.5 SUPPLY_INT_EN Register (Offset = 08h) [reset = 2AAAh]

SUPPLY_INT_EN is shown in 図 7-27 and described in 表 7-18.

Return to Summary Table.

図 7-27. SUPPLY_INT_EN Register

15	14	13	12	11	10	9	8	
RESERVED BSTSYNC_INT_EN		C_INT_EN	CP_INT_EN		CPCAP_INT_EN			
R/W-0I	R/W-0h		R/W-2h		R/W-2h		R/W-2h	
7	6	5	4	3	2	1	0	
VINOCP_IN	VINOCP_INT_EN		VDDUVLO_INT_EN		VINOVP_INT_EN		VINUVLO_INT_EN	
R/W-2h		R/V	V-2h	R/W-2h		R/W-2h		

表 7-18. SUPPLY_INT_EN Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-14	RESERVED	R/W	0h	These bits are reserved.
13-1:	BSTSYNC_INT_EN	R/W	2h	Missing boost sync interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt
				3h = Enable interrupt

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

English Data Sheet: SNVSBY8



表 7-18. SUPPLY_INT_EN Register Field Descriptions (continued)

Bit	Field	Type	Reset	Description (Continued)
11-10	CP_INT_EN	R/W	2h	Charge pump interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
9-8	CPCAP_INT_EN	R/W	2h	Charge pump cap missing interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
7-6	VINOCP_INT_EN	R/W	2h	V _{IN} over-current interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
5-4	VDDUVLO_INT_EN	R/W	2h	V _{DD} under-voltage interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
3-2	VINOVP_INT_EN	R/W	2h	V _{IN} over-voltage interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
1-0	VINUVLO_INT_EN	R/W	2h	V _{IN} under-voltage interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt

Product Folder Links: TPS92391

7.6.1.6 BOOST_INT_EN Register (Offset = 0Ah) [reset = A028h]

BOOST_INT_EN is shown in 図 7-28 and described in 表 7-19.

Return to Summary Table.



図 7-28. BOOST_INT_EN Register

13 12	11 10	9 8	
ISET_INT_EN	LEDSET_INT_EN	MODE_INT_EN	
R/W-2h	R/W-2h	R/W-2h	
5 4	3 2	1 0	
BSTOCP_INT_EN	BSTOVPH_INT_EN	Reserved	
R/W-2h	R/W-2h	R/W-0h	
	R/W-2h 5 4 BSTOCP_INT_EN	ISET_INT_EN LEDSET_INT_EN R/W-2h R/W-2h 5 4 3 2 BSTOCP_INT_EN BSTOVPH_INT_EN	

表 7-19. BOOST_INT_EN Register Field Descriptions

		_IN I _EN REGISTER FIEID DESCRIPTIONS			
Bit	Field	Туре	Reset	Description	
15-14	TSD_INT_EN	R/W	2h	Thermal shutdown interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt	
13-12	ISET_INT_EN	R/W	2h	ISET resistor short to ground interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt	
11-10	LEDSET_INT_EN	R/W	Oh	Missing LEDSET resistor interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt	
9-8	MODE_INT_EN	R/W	Oh	Missing MODE resistor interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt	
7-6	FSET_INT_EN	R/W	0h	Missing FSET resistor interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt	

表 7-19. BOOST_INT_EN Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
5-4	BSTOCP_INT_EN	R/W	2h	Boost over-current interrupt enable
				Read:
				0h = Interrupt is currently disabled
				2h = Interrupt is currently enabled
				Write:
				1h = Disable interrupt
				3h = Enable interrupt
3-2	BSTOVPH_INT_EN	R/W	2h	Boost over-voltage high interrupt enable
				Read:
				0h = Interrupt is currently disabled
				2h = Interrupt is currently enabled
				Write:
				1h = Disable interrupt
				3h = Enable interrupt
1-0	Reserved	R/W	0h	These bits are reserved.

7.6.1.7 LED_INT_EN Register (Offset = 0Ch) [reset = AAh]

LED_INT_EN is shown in 図 7-29 and described in 表 7-20.

Return to Summary Table.

☑ 7-29. LED_INT_EN Register




表 7-20. LED_INT_EN Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-8	RESERVED	R/W	0h	These bits are reserved.
7-6	GLOBAL_INT_EN	R/W	2h	Global interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt
5-4	I2C_ERROR_INT_EN	R/W	2h	I2C time out interrupt enable Read: 0h = Interrupt is currently disabled 2h = Interrupt is currently enabled Write: 1h = Disable interrupt 3h = Enable interrupt



表 7-20. LED_INT_EN Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
3-2	INVSTRING_INT_EN	R/W	2h	Invalid LED string configuration interrupt enable
				Read:
				0h = Interrupt is currently disabled
				2h = Interrupt is currently enabled
				Write:
				1h = Disable interrupt
				3h = Enable interrupt
1-0	LED_INT_EN	R/W	2h	LED open/internal short/short to GND interrupt enable
				Read:
				0h = Interrupt is currently disabled
				2h = Interrupt is currently enabled
				Write:
				1h = Disable interrupt
				3h = Enable interrupt

7.6.1.8 SUPPLY_STATUS Register (Offset = 0Eh) [reset = 0h]

SUPPLY_STATUS is shown in 図 7-30 and described in 表 7-21.

Return to Summary Table.

図 7-30. SUPPLY_STATUS Register

15	14	13	12	11	10	9	8
CRCERR_STAT US	CRCERR_CLE AR	BSTSYNC_STA TUS	BSTSYNC_CLE AR	CP_STATUS	CP_CLEAR	CPCAP_STATU S	CPCAP_CLEA R
R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h
7	6	5	4	3	2	1	0
VINOCP_STAT US	VINOCP_CLEA R	VDDUVLO_ST ATUS	VDDUVLO_CL EAR	VINOVP_STAT US	VINOVP_CLEA R	VINUVLO_STA TUS	VINUVLO_CLE AR
R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h

表 7-21. SUPPLY_STATUS Register Field Descriptions

	12.7	-21.0011	LI_UIAIU	3 Register Field Descriptions
Bit	Field	Type	Reset	Description
15	CRCERR_STATUS	R/W	Oh	CRC error fault status 0h = No fault 1h = Fault
14	CRCERR_CLEAR	R/W	0h	CRC error fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
13	BSTSYNC_STATUS	R/W	0h	Missing boost sync fault status 0h = No fault 1h = Fault
12	BSTSYNC_CLEAR	R/W	0h	Missing boost sync fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
11	CP_STATUS	R/W	0h	Charge pump fault status 0h = No fault 1h = Fault

Product Folder Links: TPS92391

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



表 7-21. SUPPLY STATUS Register Field Descriptions (continued)

Bit	Field	Type	Reset	Description (continued)
10	CP_CLEAR	R/W	0h	Charge pump fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
9	CPCAP_STATUS	R/W	0h	Missing charge pump fault status 0h = No fault 1h = Fault
8	CPCAP_CLEAR	R/W	0h	Missing charge pump fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
7	VINOCP_STATUS	R/W	0h	V _{IN} over-current fault status 0h = No fault 1h = Fault
6	VINOCP_CLEAR	R/W	0h	V _{IN} over-current fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
5	VDDUVLO_STATUS	R/W	0h	V _{DD} under-voltage fault status 0h = No fault 1h = Fault
4	VDDUVLO_CLEAR	R/W	0h	V _{DD} under-voltage fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
3	VINOVP_STATUS	R/W	0h	V _{IN} over-voltage fault status 0h = No fault 1h = Fault
2	VINOVP_CLEAR	R/W	0h	V _{IN} over-voltage fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
1	VINUVLO_STATUS	R/W	0h	V _{IN} under-voltage fault status 0h = No fault 1h = Fault
0	VINUVLO_CLEAR	R/W	0h	V _{IN} under-voltage fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status

7.6.1.9 BOOST_STATUS Register (Offset = 10h) [reset = 0h]

BOOST_STATUS is shown in 図 7-31 and described in 表 7-22.

Return to Summary Table.

図 7-31. BOOST_STATUS Register

15	14	13	12	11	10	9	8
TSD_STATUS	TSD_CLEAR	ISET_STATUS	ISET_CLEAR	LEDSET_STAT US	LEDSET_CLEA R	MODESEL_ST ATUS	MODESEL_CL EAR
R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h
7	6	5	4	3	2	1	0
FSET_STATUS	FSET_CLEAR	BSTOCP_STAT US	BSTOCP_CLE AR	BSTOVPH_STA TUS	BSTOVPH_CL EAR	BSTOVPL_STA TUS	BSTOVPL_CLE AR

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

49



図 7-31. BOOST_STATUS Register (continued)

R/W-0h R/W-0h R/W-0h R/W-0h R/W-0h R/W-0h R/W-0h

表 7-22. BOOST_STATUS Register Field Descriptions

Bit	Field	7-22. BOO Type	Reset	S Register Field Descriptions Description
15	TSD STATUS	R/W	0h	Thermal shutdown fault status
15	100_01/100	1000	Off	0h = No fault 1h = Fault
14	TSD_CLEAR	R/W	0h	Thermal shutdown fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
13	ISET_STATUS	R/W	0h	ISET resistor short to ground fault status 0h = No fault 1h = Fault
12	ISET_CLEAR	R/W	0h	ISET resistor short to ground fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
11	LEDSET_STATUS	R/W	0h	Missing LED resistor fault status 0h = No fault 1h = Fault
10	LEDSET_CLEAR	R/W	0h	Missing LED resistor fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
9	MODESEL_STATUS	R/W	0h	Missing MODE SEL resistor fault status 0h = No fault 1h = Fault
8	MODESEL_CLEAR	R/W	0h	Missing MODE SEL resistor fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
7	FSET_STATUS	R/W	0h	Missing boost FSET resistor fault status 0h = No fault 1h = Fault
6	FSET_CLEAR	R/W	0h	Missing boost FSET resistor fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
5	BSTOCP_STATUS	R/W	0h	Boost over-current fault status 0h = No fault 1h = Fault
4	BSTOCP_CLEAR	R/W	0h	Boost over-current fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
3	BSTOVPH_STATUS	R/W	0h	Boost OVP high fault status 0h = No fault 1h = Fault
2	BSTOVPH_CLEAR	R/W	0h	Boost OVP high fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status



表 7-22. BOOST_STATUS Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
1	BSTOVPL_STATUS	R/W	0h	Boost OVP low fault status
				0h = No fault
				1h = Fault
0	BSTOVPL_CLEAR	R/W	0h	Boost OVP low fault clear
				Write "1" to both Status bit and Clear bit at the same time to clear
				interrupt register status

7.6.1.10 LED_STATUS Register (Offset = 12h) [reset = 0h]

LED_STATUS is shown in 図 7-32 and described in 表 7-23.

Return to Summary Table.

図 7-32. LED_STATUS Register

			_				
15	14	13	12	11	10	9	8
RESERVED	I2C_ERROR_S TATUS	I2C_ERROR_C LEAR	INVSTRING_S TATUS	INVSTRING_C LEAR	LED_STATUS	LED_CLEAR	GND_LED
R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R-0h
7	6	5	4	3	2	1	0
SHORT_LED	OPEN_LED	LED6_FAULT	LED5_FAULT	LED4_FAULT	LED3_FAULT	LED2_FAULT	LED1_FAULT
R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h

表 7-23. LED_STATUS Register Field Descriptions

D:4				Register Field Descriptions
Bit	Field	Туре	Reset	Description
15	RESERVED	R/W	0h	This bit is reserved
14	I2C_ERROR_STATUS	R/W	0h	I2C time out fault status 0h = No fault 1h = Fault
13	I2C_ERROR_CLEAR	R/W	0h	I2C time out fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
12	INVSTRING_STATUS	R/W	0h	Invalid string configuration fault status 0h = No fault 1h = Fault
11	INVSTRING_CLEAR	R/W	0h	Invalid string configuration fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
10	LED_STATUS	R/W	0h	LED open/internal short/short to GND fault status 0h = No fault 1h = Fault
9	LED_CLEAR	R/W	0h	LED open/internal short/short to GND fault clear Write "1" to both Status bit and Clear bit at the same time to clear interrupt register status and interrupt pin status
8	GND_LED	R	0h	LED short to GND fault status 0h = No fault 1h = Fault

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback



表 7-23. LED_STATUS Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
7	SHORT_LED	R	Oh	LED internal short Status 0h = No Fault 1h = Fault Status is cleared with LED_STATUS bit
6	OPEN_LED	R	Oh	LED open fault status 0h = No fault 1h = Fault Status is cleared with LED_STATUS bit
5	LED6_FAULT	R	Oh	LED 6 Status 0h = No Fault 1h = Fault
4	LED5_FAULT	R	Oh	LED 5 Status 0h = No Fault 1h = Fault
3	LED4_FAULT	R	Oh	LED 4 Status 0h = No Fault 1h = Fault
2	LED3_FAULT	R	Oh	LED 3 Status 0h = No Fault 1h = Fault
1	LED2_FAULT	R	Oh	LED 2 Status 0h = No Fault 1h = Fault
0	LED1_FAULT	R	Oh	LED 1 Status 0h = No Fault 1h = Fault

7.6.1.11 FSM_DIAGNOSTICS Register (Offset = 14h) [reset = 0h]

Return to Summary Table.

図 7-33. FSM_DIAGNOSTICS Register




表 7-24. FSM_DIAGNOSTICS Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-5	RESERVED	R	0h	These bits are reserved



表 7-24. FSM_DIAGNOSTICS Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
4-0	FSM_LIVE_STATUS	R	0h	Current state of the functional state machine
				0h = DISABLED
				1h = LDO_STARTUP
				2h = OTP_READ
				3h = STANDBY
				4h-Fh = BOOST_STARTUP
				10h = NORMAL
				11h = SHUTDOWN
				12h = FAULT_RECOVERY
				13h = ALL_LED_FAULT

7.6.1.12 PWM_INPUT_DIAGNOSTICS Register (Offset = 16h) [reset = 0h]

PWM_INPUT_DIAGNOSTICS is shown in 図 7-34 and described in 表 7-25.

Return to Summary Table.

図 7-34. PWM_INPUT_DIAGNOSTICS Register




表 7-25. PWM_INPUT_DIAGNOSTICS Register Field Descriptions

ı	Bit	Field	Туре	Reset	Description
1	5-0	PWM_INPUT_STATUS	R	0h	16-bit value for detected duty cycle of PWM input signal.

7.6.1.13 PWM_OUTPUT_DIAGNOSTICS Register (Offset = 18h) [reset = 0h]

PWM_OUTPUT_DIAGNOSTICS is shown in 図 7-35 and described in 表 7-26.

Return to Summary Table.

図 7-35. PWM_OUTPUT_DIAGNOSTICS Register




表 7-26. PWM_OUTPUT_DIAGNOSTICS Register Field Descriptions


Bit	Field	Туре	Reset	Description
15-0	PWM_OUTPUT_STATUS	R	0h	16-bit value for configured duty cycle of PWM output signal.

7.6.1.14 LED_CURR_DIAGNOSTICS Register (Offset = 1Ah) [reset = 0h]

LED_CURR_DIAGNOSTICS is shown in 図 7-36 and described in 表 7-27.

Return to Summary Table.

☑ 7-36. LED_CURR_DIAGNOSTICS Register



Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated

Submit Document Feedback

53



図 7-36. LED CURR DIAGNOSTICS Register (continued)

7	6	5	4	3	2	1	0
LED_CURRENT_STATUS							
			R	-0h			

表 7-27. LED_CURR_DIAGNOSTICS Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-12	RESERVED	R	0h	These bits are reserved.
11-0	LED_CURRENT_STATUS	R	0h	12-bit Current DAC Code that Brightness path is driving to OUT1-6 output.

7.6.1.15 ADAPT_BOOST_DIAGNOSTICS Register (Offset = 1Ch) [reset = 0h]

ADAPT_BOOST_DIAGNOSTICS is shown in 図 7-37 and described in 表 7-28.

Return to Summary Table.

図 7-37. ADAPT BOOST DIAGNOSTICS Register

15	14	13	12	11	10	9	8
		RESERVED	V	/BOOST_STATU	S		
R-0h					R-0h		
7	6	5	4	3	2	1	0
	VBOOST_STATUS						
	R-0h						

表 7-28. ADAPT_BOOST_DIAGNOSTICS Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-11	RESERVED	R	0h	These bits are reserved.
10-0	VBOOST_STATUS	R	0h	11-bit Boost Voltage Code that Adaptive Voltage Control Loop sending to Analog Boost Block. In two-resistor method, Boost Output Voltage =((1+R1/R2)*1.21V)+(R1*18.9nA*VBOOST_STATUS)

7.6.1.16 AUTO_DETECT_DIAGNOSTICS Register (Offset = 1Eh) [reset = 0h]

AUTO_DETECT_DIAGNOSTICS is shown in 図 7-38 and described in 表 7-29.

Return to Summary Table.

図 7-38. AUTO DETECT DIAGNOSTICS Register

	_ · · · · · · · · · · · · · · · · ·						
15	14	13	12	11	10	9	8
RESERVED	AUTO_PWM_FREQ_SEL			RESERVED	AUT	O_LED_STRING_	CFG
R-0h	R-0h			R-0h		R-0h	
7	6	5	4	3	2	1	0
RESE	RVED	AUTO	D_BOOST_FREC	Q_SEL		MODE_SEL	
R-	·0h	•	R-0h			R-0h	

表 7-29. AUTO DETECT DIAGNOSTICS Register Field Descriptions

pt:					
Bit	Field	Туре	Reset	Description	
15	RESERVED	R	0h	This bit is reserved	

English Data Sheet: SNVSBY8



表 7-29. AUTO_DETECT_DIAGNOSTICS Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description Description
14-12	AUTO_PWM_FREQ_SEL	R	0h	LED PWM frequency value from PWM_SEL resistor detection 0h = 152 Hz 1h = 305 Hz 2h = 610 Hz 3h = 1221 Hz 4h = 2441 Hz 5h = 4883 Hz 6h = 9766 Hz 7h = 19531 Hz
11	RESERVED	R	0h	This bit is reserved
10-8	AUTO_LED_STRING_CF G	R	Oh	LED string configuration from LED_SET resistor detection 0h = 6 separate strings 1h = 5 separate strings 2h = 4 separate strings 3h = 3 separate strings 4h = 2 separate strings 5h = 6 channel outputs connected in 3 groups to drive 3 strings 6h = 6 channel outputs connected in 2 groups to drive 2 strings 7h = 6 channel outputs connected together to drive 1 string
7-6	RESERVED	R	0h	These bits are reserved
5-3	AUTO_BOOST_FREQ_S EL	R	Oh	Boost switching frequency value from PWM_FSET resistor detection 0h = 100 kHz 1h = 200 kHz 2h = 303 kHz 3h = 400 kHz 4h = 500 kHz 5h = 1818 kHz 6h = 2000 kHz 7h = 2222 kHz
2-0	MODE_SEL	R	Oh	LED dimming MODE value from MODE detection 0h = PWM mode, I2C address 0x2B 1h = 12.5% hybrid dimming mode, I2C address 0x2B 2h = Constant current mode, I2C address 0x2B 3h = Direct PWM, I2C address 0x2B 4h = PWM mode, I2C address 0x2A 5h = 12.5% hybrid dimming mode, I2C address 0x2A 6h = Constant current mode, I2C address 0x2A 7h = Direct PWM, I2C address 0x2A



8 Application and Implementation

注

以下のアプリケーション情報は、TIの製品仕様に含まれるものではなく、TIではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。また、お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

8.1 Application Information

The TPS92391 device is designed for automotive applications, and an input voltage V_{IN} is intended to be connected to the vehicle battery. Depending on the input voltage, the device may be used in either boost mode or SEPIC mode. The device is internally powered from the VDD pin, and voltage must be in 2.7-V to 5.5-V range. The device has flexible configurability through external components or by an I2C interface. If the VDD voltage is not high enough to drive an external nMOSFET gate, an internal charge pump must be used to power the gate driver (GD pin).

8.2 Typical Applications

8.2.1 Full Feature Application for Display Backlight

⊠ 8-1 shows a full application for the TPS92391 device in a boost topology. It supports 6 LED strings in display mode, each at 150 mA, with an automatic 60° phase shift. Brightness control register is used for LED dimming method through I2C communication. The charge pump is enabled for a 400-kHz boost switching frequency with spread spectrum.




図 8-1. Full Feature Application for Display Backlight

Product Folder Links: TPS92391

8.2.1.1 Design Requirements

This typical LED-driver application is designed to meet the parameters listed in 表 8-1:

Copyright © 2023 Texas Instruments Incorporated

表 8-1.	TPS92391	Full-Feature	Design	Parameters
--------	----------	---------------------	--------	-------------------

DESIGN PARAMETER	VALUE
VIN voltage range	5 Vto 20 V (Quiescent Voltage)
VDD voltage	3.3 V
LED strings configuration	6 strings, 7 LEDs in series
Charge pump	Enabled
Brightness control	I2C
Output configuration	OUT1 to OUT6 are in phase shift mode (60°)
LED string current	150 mA
Boost frequency	400 kHz
Inductor	22 µH at 6.5-A saturation current
R _{ISENSE}	20 mΩ
Power-line FET	Enabled
R _{SENSE}	30 mΩ
Input/Output capacitors	C _{IN} and C _{OUT} : 1 × 33-μF electrolytic + 1 × 10-μF ceramic
Spread spectrum	Enabled

8.2.1.2 Detailed Design Procedure

8.2.1.2.1 Inductor Selection

There are a few things to consider when choosing an inductor: inductance, current rating, and DC resistance (DCR). 表 8-2 shows recommended inductor values for each operating frequency. The TPS92391 device automatically sets internal boost compensation controls depending on the selected switching frequency.

表 8-2. Inductance Values for Boost Switching Frequencies

SW FREQUENCY (kHz)	INDUCTANCE (μH)
100	47
200	33
303	22
400	22
500	22
1818	10
2000	10
2222	10

The current rating of inductor must be at least 25% higher than maximum boost switching current I_{SW(max)}, which can be calculated with Equation 21. TI recommends to use an inductor with low DCR to achieve good efficiency. Efficiency varies with load condition, switching frequency, and components. 80% can be used as a typical estimation. 65% efficiency needs to take into account in extreme condition.

$$I_{SW(max)} = \frac{\Delta I_L}{2} + \frac{I_{OUT(max)}}{1 - D}$$
(21)

Product Folder Links: TPS92391

where

- $\Delta I_L = V_{IN(min)} \times D / f_{SW} \times L$
- D = $1 \dot{V}_{IN(min)} \times \eta / \dot{V}_{OUT}$
- I_{SW(max)}: Maximum switching current
- ΔI_I: Inductor ripple current
- I_{OUT(max)}: Maximum output current
- D: Boost duty cycle

JAJSKE4 - MARCH 2021



- V_{IN(min)}: Minimum input voltage
- f_{SW}: Minimum switching frequency of the converter
- L: Inductance
- V_{OUT}: Output voltage
- η: Efficiency of boost converter

8.2.1.2.2 Output Capacitor Selection

Recommended voltage rating for output capacitors is 50% higher than maximum output voltage level. Capacitance value determines voltage ripple and boost stability. The DC-bias effect can reduce the effective capacitance significantly, by up to 80%, a consideration for capacitance value selection. The conservative target effective capacitance is 50 μ F to achieve good phase and gain margin levels. A design table in product webpage could be refered for the target effective capacitance in a certain application. TI recommends using 33- μ F Alpolymer electrolytic capacitor together with 10- μ F ceramic capacitors in parallel to reduce ripple, increase stability, and reduce ESR effect.

8.2.1.2.3 Input Capacitor Selection

Recommended input capacitance is the same as output capacitance although input capacitors are not as critical to boost operation. Input capacitance can be reduced but must ensure enough filtering for input power.

8.2.1.2.4 Charge Pump Output Capacitor

TI recommends a ceramic capacitor with at least 10-V voltage rating for the output capacitor of the charge pump. A 10-µF capacitor can be used for most applications.

8.2.1.2.5 Charge Pump Flying Capacitor

TI recommends a ceramic capacitor with at least 10-V voltage rating for the flying capacitor of the charge pump. One 2.2-µF capacitor connecting C1P and C1N pins can be used for most applications.

8.2.1.2.6 Output Diode

A Schottky diode must be used for the boost output diode. Current rating must be at least 25% higher than the maximum output current. Schottky diodes with a low forward drop and fast switching speeds are ideal for increasing efficiency. At maximum current, the forward voltage must be as low as possible; less than 0.5 V is recommended. Reverse breakdown voltage of the Schottky diode must be significantly larger than the output voltage, 25% higher voltage rating is recommended. Do not use ordinary rectifier diodes, because slow switching speeds and long recovery times cause efficiency and load regulation to suffer.

8.2.1.2.7 Switching FET

Gate-drive voltage for the FET is 5V. Switching FET is a critical component for determining power efficiency of the boost converter. Several aspects need to be considered when selecting switching FET such as voltage and current rating, R_{DSON} , power dissipation, thermal resistance and rise/fall times. An N type MOSFET with at least 25% higher voltage rating than maximum output voltage must be used. Current rating of switching FET should be same or higher than inductor rating. R_{DSON} must be as low as possible, less than 20 m Ω is recommended. Thermal resistance ($R_{\theta JA}$) must also be low to dissipate heat from power loss on switching FET. In most cases, a resistance is recommended between GD pin and Switching FET's gate terminal. It could be used to control the rising/falling time of the switching FET. This gate resistance could offer the flexibility of balancing between EMC performance and efficiency.

8.2.1.2.8 Boost Sense Resistor

The R_{SENSE} resistor determines the boost overcurrent limit and is sensed every boost switching cycle. A high-power 20-m Ω resistor can be used for sensing the boost SW current and setting maximum current limit at 10 A (typical). R_{SENSE} can be increased to lower this limit and can be calculated with Equation 22. In typical condition, to avoid too much efficiency loss on R_{SENSE} resistor, boost overcurrent limit is recommended to be set above 4A, therefore R_{SENSE} doesn't exceed 50 m Ω . Power rating can be calculated from the inductor current and sense resistor resistance value.

Product Folder Links: TPS92391

Copyright © 2023 Texas Instruments Incorporated



$$R_{SENSE} = \frac{200 \text{ mV}}{I_{BOOST_OCP}}$$
 (22)

where

- R_{SENSE}: boost sense resistor (mΩ)
- I_{BOOST OCP}: boost overcurrent limit

8.2.1.2.9 Power-Line FET

A power line FET can be used to disconnect input power from boost input to protect the TPS92391 device and boost components in case an overcurrent event occurs. A P type MOSFET is used for the power-line FET. Voltage rating must be at least 25% higher than maximum input voltage level. Low R_{DSON} is important to reduce power loss on the FET — less than 20 m Ω is recommended. Current rating for the FET must be at least 25% higher than input peak current. Minimum Gate-to-Source voltage (V_{GS}) to turn on transistor fully must be less than minimum input voltage; use a 20-k Ω resistor between the pFET gate and source.

8.2.1.2.10 Input Current Sense Resistor

A high-power resistor can be used for sensing the boost input current. Overcurrent condition is detected when the voltage across R_{ISENSE} reaches 220 mV. Typical 20-m Ω sense resistor is used to set 11-A input current limit. Sense resistor value can be increased to lower overcurrent limit for application as needed. Power rating can be calculated from the input current and resistance value.

8.2.1.2.11 Feedback Resistor Divider

Feedback resistors R_{FB1} and R_{FB2} determine the maximum boost output level. Output voltage can be calculated as in Equation 23:

$$V_{OUT_MAX} = \left(\frac{V_{BG}}{R_{FB2}} + I_{SEL_MAX}\right) \times R_{FB1} + V_{BG}$$
(23)

where

- V_{BG} = 1.21 V
- I_{SEL_MAX} = 38.7 μA
- R_{FB1} / R_{FB2} normal recommended range is 7~15

8.2.1.2.12 Critical Components for Design

図 8-2 shows the critical part of circuitry: boost components, the TPS92391 internal charge pump for gate-driver powering, and powering/grounding of TPS92391. Schematic example is shown in 図 8-2.





図 8-2. Critical Components for Full Feature Design



表 8-3. Recommended Component Values for Full Feature Design Example

REFERENCE DESIGNATOR	DESCRIPTION	NOTE
R _{ISENSE}	20 mΩ, 3 W	Input current sensing resistor
R _{SD}	20 kΩ, 0.1 W	Power-line FET gate pullup resistor
R _{SENSE}	30 mΩ, 3 W	Boost current sensing resistor
R_{G}	15 Ω, 0.1 W	Gate resistor to control the rising/falling time of nMOSFET for EMC
R _{UVLO1}	76.8 kΩ, 0.1 W	These UVLO resistor settings set the
R _{UVLO2}	20.5 kΩ, 0.1 W	VIN_UVLO rising voltage at 3.75 V, VIN_UVLO falling voltage at 3.35 V
R _{FB3}	0 Ω, 0.1 W	Not needed unless 100-k Ω restrictions on resistors
R _{FB2}	100 kΩ, 0.1 W	Bottom feedback divider resistor
R _{FB1}	910 kΩ, 0.1 W	Top feedback divider resistor
R _{BST_FSET}	3.92 kΩ, 0.1 W	Boost frequency set resistor (400 kHz)
R _{ISET}	20.8 kΩ, 0.1 W	Current set resistor (150 mA per channel)
R _{PWM_FSET}	17.8 kΩ, 0.1 W	Output PWM frequency set resistor (4.88kHz PWM frequency to avoid audible noise)
R _{MODE}	3.92 kΩ, 0.1 W	Mode resistor (Phase-Shift PWM mode with 0x2B I2C address)
R _{LED_SET}	3.92 kΩ, 0.1 W	LED_SET resistor (6channels configuration)
C _{PUMP}	10-μF, 10-V ceramic	Charge-pump output capacitor
C _{2X}	2.2-µF, 10-V ceramic	Flying capacitor
C _{VDD}	4.7-μF + 0.1-μF, 10-V ceramic	VDD bypass capacitor
C _{IN}	1 × 33-μF, 50-V electrolytic + 1 × 10-μF, 50-V ceramic	Boost input capacitor
C _{OUT}	1 × 33-μF, 50-V electrolytic + 1 × 10-μF, 50-V ceramic	Boost output capacitor
L1	22-µH saturation current 6.5 A	Boost inductor
D1	50 V, 6.5-A Schottky diode	Boost Schottky diode
Q1	60-V, 15-A nMOSFET	Boost nMOSFET
Q2	60-V, 15-A pMOSFET	Power-line FET

8.2.1.3 Application Curves





8.2.2 Application With Basic/Minimal Operation

The TPS92391 needs only a few external components for basic functionality if material cost and PCB area for a solution need to be minimized. In this example TPS92391 is configured with external components and no I2C communication. The power-line FET is removed, as is input current sensing. Internal charge pump is not used, and all external synchronization functions and special features are disabled. The 33- μ F Al-polymer electrolytic capacitor is removed for PCB area and height limitation. And boost external compensation is used to compensate the removal of the 33- μ F Al-polymer electrolytic capacitor.




図 8-5. Minimal Solution/Minimum Components Application

8.2.2.1 Design Requirements

This typical LED-driver application is designed to meet the parameters listed in 表 8-4:

表 8-4. TPS92391 Minimal Solution Design Parameters

DESIGN PARAMETER	VALUE
VIN voltage range	3 Vto 20 V (Quiescent Voltage)
VDD voltage	5 V
LED strings configuration	6 strings, 7 LEDs in series
Charge pump	Disabled
Brightness control	PWM
Output configuration	OUT1 to OUT6 are in phase shift mode (60°)
LED string current	120 mA
Boost frequency	400 kHz
Inductor	22 μH at 6.5-A saturation current
R _{ISENSE}	20 mΩ
Power-line FET	Enabled
R _{SENSE}	30 mΩ
Input/Output capacitors	C _{IN} and C _{OUT} : 3 × 10-μF ceramic
Spread spectrum	Enabled
Discharge function	Enabled

Product Folder Links: TPS92391

8.2.2.2 Detailed Design Procedure

See Detailed Design Procedure.

8.2.2.3 Application Curves

See Application Curves.



8.2.3 SEPIC Mode Application

When LED string voltage can be above and below the input voltage level, use the SEPIC configuration. In SEPIC mode, the SW pin detects a maximum voltage equal to the sum of the input and output voltages, a consideration when selecting components.




図 8-6. SEPIC Mode with Three LEDs in Series

8.2.3.1 Design Requirements

This typical LED-driver application is designed to meet the parameters listed in 表 8-5:

表 8-5. TPS92391 SEPIC Mode Design Parameters

DESIGN PARAMETER	VALUE				
V _{IN} voltage range	4.5 V to 20 V (quiescent voltage)				
V _{DD} voltage	3.3 V				
LED strings configuration	5 strings, 3 LEDs in series				
Charge pump	Enabled				
Brightness control	12C				
Output configuration	OUT1 to OUT5 are in phase shift PWM mode				
LED string current	80 mA				
Boost frequency	2.2 MHz				
Inductor	10 μH at 4-A saturation current				
R _{ISENSE}	20 mΩ				
Power-line FET	Enabled				
R _{SENSE}	50 mΩ				
Input/Output capacitors	C _{IN} and C _{OUT} : 1 × 33-μF electrolytic + 1 × 10-μF ceramic				
Spread spectrum	Enabled				
Discharge function	Enabled				

8.2.3.2 Detailed Design Procedure

8.2.3.2.1 Inductor Selection

Inductance for both inductors can be selected from $\frac{1}{2}$ 8-6, depending on operating frequency for the application. Current rating is recommended to be at least 25% higher than maximum inductor peak current. Peak-to-peak ripple current can be estimated to be approximately 40% of the maximum input current and and inductor peak current can be calculated with Equation 24, Equation 25, and Equation 26:

表 8-6. Inductance Values for SEPIC Switching Frequencies

SW FREQUENCY (kHz)	INDUCTANCE (µH)				
100	22				
200	15				
303	10				
400	10				
500	10				
1818	4.7				
2000	4.7				
2222	4.7				



$$I_{L1(peak)} = I_{OUT} \times \frac{V_{OUT} + V_D}{V_{IN(min)}} \times \left(1 + \frac{40\%}{2}\right)$$
(24)

where

I_{L1(peak)}: Peak current for inductor 1

I_{OUT}: Maximum output current

V_{OUT}: Output voltage

V_D: Diode forward voltage drop

V_{IN(min)}: Minimum input voltage

$$I_{L2(peak)} = I_{OUT} \times \left(1 + \frac{40\%}{2}\right)$$
 (25)

where

• I_{L2(peak)}: Peak current for inductor 2

I_{OUT}: Maximum output current

$$\Delta I_{L} = I_{IN} \times 40\% = I_{OUT} \times \frac{V_{OUT}}{V_{IN(min)}} \times 40\%$$
(26)

where

ΔI_L: Inductor ripple current

I_{IN}: Input current

V_{OUT}: Output voltage

V_{IN(min)}: Minimum input voltage

8.2.3.2.2 Coupling Capacitor Selection

The coupling capacitors Cs isolate the input from the output and provide protection against a shorted load. The selection of SEPIC capacitors, Cs, depends mostly on the RMS current, which can be calculated with Equation 27. The capacitors must be rated for a large RMS current relative to the output power; TI recommends at least 25% higher rating for I_{RMS} . When using uncoupled inductors, use one 10- μ F ceramic capacitor in parallel with one 33- μ F electrolytic capacitor and series 2- Ω resistor. If coupled inductors are used, then use only one 10- μ F ceramic capacitor.

$$I_{Cs(rms)} = I_{OUT} \times \sqrt{\frac{V_{OUT} + V_{D}}{V_{IN(min)}}}$$
(27)

where

I_{Cs(rms)}: RMS current of Cs capacitor

I_{OUT}: Óutput current

V_{OUT}: Output voltage

V_D: Diode forward voltage drop

V_{IN(min)}: Minimum input voltage

8.2.3.2.3 Output Capacitor Selection

See Detailed Design Procedure.

8.2.3.2.4 Input Capacitor Selection

See Detailed Design Procedure.

8.2.3.2.5 Charge Pump Output Capacitor

See Detailed Design Procedure.

8.2.3.2.6 Charge Pump Flying Capacitor

See Detailed Design Procedure.

8.2.3.2.7 Switching FET

Gate-drive voltage for the FET is 5V. Use an N-type MOSFET for the switching FET. The switching FET for SEPIC mode sees a maximum voltage of $V_{IN(max)} + V_{OUT}$, 25% higher rating is recommended. Current rating is also recommended to be 25% higher than peak current, which can be calculated with Equation 28. R_{DSON} must be as low as possible — less than 20 m Ω is recommended. Thermal resistance ($R_{\theta JA}$) must also be low to dissipate heat from power loss on switching FET. Typical rise/fall time values recommended are less than 10 ns.

$$I_{Q1(peak)} = I_{L1(peak)} + I_{L2(peak)}$$
(28)

where

- I_{Q1(peak)}: Peak current for switching FET
- I_{L1(peak)}: Peak current for inductor 1
- I_{IL2(peak):} : Peak current for inductor 2 BOOST_OCP

8.2.3.2.8 Output Diode

A Schottky diode must be used for the SEPIC output diode. Current rating must be at least 25% higher than the maximum current, which is the same as switch peak current. Schottky diodes with a low forward drop and fast switching speeds are ideal for increasing efficiency. At maximum current, the forward voltage must be as low as possible; TI recommends less than 0.5 V. Reverse breakdown voltage of the Schottky diode must be able to withstand $V_{IN(max)} + V_{OUT(max)}$; at least 25% higher voltage rating is recommended. Do not use ordinary rectifier diodes, because slow switching speeds and long recovery times cause efficiency and load regulation to suffer.

8.2.3.2.9 Switching Sense Resistor

See Detailed Design Procedure.

8.2.3.2.10 Power-Line FET

See Detailed Design Procedure.

8.2.3.2.11 Input Current Sense Resistor

See Detailed Design Procedure.

8.2.3.2.12 Feedback Resistor Divider

Feedback resistors R_{FB1} and R_{FB2} determine the maximum boost output level. Output voltage can be calculated as follows:

$$V_{OUT_MAX} = \left(\frac{V_{BG}}{R_{FB2}} + I_{SEL_MAX}\right) \times R_{FB1} + V_{BG}$$
(29)

where

- V_{BG} = 1.21 V
- I_{SEL MAX} = 38.7 μA
- R_{FB1} / R_{FB2} normal recommended range is 5~15 (recommended for SEPIC Mode)

8.2.3.2.13 Critical Components for Design

☑ 8-7 shows the critical part of circuitry: SEPIC components, the TPS92391 internal charge pump for gate-driver powering, and powering/grounding of TPS92391. Schematic example is shown below.




図 8-7. SEPIC Mode with Three LEDs in Series

English Data Sheet: SNVSBY8

表 8-7. Recommended Components for SEPIC Design Example

REFERENCE DESIGNATOR	DESCRIPTION	NOTE			
R _{ISENSE}	20 mΩ, 1 W	Input current sensing resistor			
R _{SD}	20 kΩ, 0.1 W	Power-line FET gate pullup resistor			
R _{SENSE}	50 mΩ, 1 W	Boost current sensing resistor			
R _G	15 Ω, 0.1 W	Gate resistor to control the rising/falling time of nMOSFET for EMC			
R _{UVLO1}	76.8 kΩ, 0.1 W	These UVLO resistor settings set the			
R _{UVLO2}	20.5 kΩ, 0.1 W	VIN_UVLO rising voltage at 3.75 V, VIN_UVLO falling voltage at 3.35 V			
R _{FB2}	60 kΩ, 0.1 W	Bottom feedback divider resistor			
R _{FB1}	330 kΩ, 0.1 W	Top feedback divider resistor			
R _{BST_FSET}	124 kΩ, 0.1 W	Boost frequency set resistor (2200 kHz)			
R _{ISET}	38.7 kΩ, 0.1 W	Current set resistor (80 mA per channel)			
R _{PWM_FSET}	4.75 kΩ, 0.1 W	Output PWM frequency set resistor (305-Hz PWM frequency)			
R _{MODE}	3.92 kΩ, 0.1 W	Mode resistor (Phase-Shift PWM mode with 0x2B I2C address)			
R _{LED_SET}	4.75 kΩ, 0.1 W	LED_SET resistor (5 channels configuration)			
C _{PUMP}	10-μF, 10-V ceramic	Charge-pump output capacitor			
C _{2X}	2.2-µF, 10-V ceramic	Flying capacitor			
C _{VDD}	4.7-μF + 0.1-μF, 10-V ceramic	VDD bypass capacitor			
C _{IN}	1 × 33-μF, 50-V electrolytic + 1 × 10-μF, 50-V ceramic	Boost input capacitor			
C _{OUT}	1 × 33-μF, 50-V electrolytic + 1 × 10-μF, 50-V ceramic	Boost output capacitor			
C _{S1}	10-μF, 50-V ceramic	SEPIC coupling capacitor			
C _{S2}	33-μF, 50-V electrolytic	SEPIC coupling capacitor			
RS	2 Ω, 0.125 W	SEPIC resistor			
L1	4.7-μH saturation current 3 A	SEPIC inductor			
L2	4.7-μH saturation current 3 A	SEPIC inductor			
D1	50-V 10-A Schottky diode	SEPIC Schottky diode			
Q1	60-V, 25-A nMOSFET	SEPIC nMOSFET			
Q2	60-V, 30-A pMOSFET	Power-line FET			

8.2.3.3 Application Curves

See Application Curves.

9 Power Supply Recommendations

The TPS92391 is designed to operate from a car battery. The V_{IN} input must be protected from reverse voltage and voltage dump condition over 48 V. The impedance of the input supply rail must be low enough that the input current transient does not cause drop below VIN UVLO level. If the input supply is connected with long wires, additional bulk capacitance may be required in addition to normal input capacitor.

The voltage range for V_{DD} is 3 V to 5.5 V. A ceramic capacitor must be placed as close as possible to the VDD pin. The boost gate driver is powered from the CPUMP pins. A ceramic capacitor must be placed as close to the CPUMP pins as possible.



10 Layout

10.1 Layout Guidelines

☑ 10-1 shows a layout recommendation for the TPS92391 used to illustrate the principles of good layout. This layout can be adapted to the actual application layout if and where possible. It is important that all boost components are close to each other and to the chip; the high-current traces must be wide enough. VDD must be as noise-free as possible. Place a V_{DD} bypass capacitor near the VDD and GND pins. A charge-pump capacitor, boost input capacitors, and boost output capacitors must have closest VIAs to GND. Place the charge-pump capacitors close to the device. The main points to guide the PCB layout design:

- Current loops need to be minimized:
 - For low frequency the minimal current loop can be achieved by placing the boost components as close as
 possible to each other. Input and output capacitor grounds need to be close to each other to minimize
 current loop size.
 - Minimal current loops for high frequencies can be achieved by making sure that the ground plane is intact under the current traces. High frequency return currents follow the route with minimum impedance, which is the route with minimum loop area, not necessarily the shortest path. Minimum loop area is formed when return current flows just under the *positive* current route in the ground plane, if the ground plane is intact under the route.
 - For high frequency the copper area capacitance must be taken into account. For example, the copper area for the drain of boost N-MOSFET is a tradeoff between capacitance and the cooling capacity of the components.
- GND plane must be intact under the high-current-boost traces to provide shortest possible return path and smallest possible current loops for high frequencies.
- Route boost output voltage (V_{OUT}) to LEDs, FB pin & Discharge pin after output capacitors not straight from the diode cathode.
- · FB network should be placed as close as possible to the FB pin, not near boost output
- A small bypass capacitor (TI recommends a 39-pF capacitor) could be placed close to the FB pin and GND to suppress high frequency noise
- VDD line must be separated from the high current supply path to the boost converter to prevent high frequency ripple affecting the chip behavior.
- Capacitor connected to charge pump output CPUMP is recommended to have 10-µF capacitance. This
 capacitor must be as close as possible to CPUMP pin. This capacitor provides a greater peak current for gate
 driver and must be used even if the charge pump is disabled. If the charge pump is disabled, the VDD and
 CPUMP pins must be tied together.
- Input and output capacitors need low-impedance grounding (wide traces with many vias to GND plane).
- Input/output ceramic capacitors have DC-bias effect. If the output capacitance is too low, it can cause boost
 to become unstable under certain load conditions. DC bias characteristics should be obtained from the
 component manufacturer; DC bias is not taken into account on component tolerance.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated

English Data Sheet: SNVSBY8



10.2 Layout Example




図 10-1. TPS92391 Layout Guidelines

11 Device and Documentation Support

11.1 Device Support

11.1.1 サード・パーティ製品に関する免責事項

サード・パーティ製品またはサービスに関するテキサス・インスツルメンツの出版物は、単独またはテキサス・インスツルメンツの製品、サービスと一緒に提供される場合に関係なく、サード・パーティ製品またはサービスの適合性に関する是認、サード・パーティ製品またはサービスの是認の表明を意味するものではありません。

11.2 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.com のデバイス製品フォルダを開いてください。「更新の通知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

11.3 サポート・リソース

TI E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計で必要な支援を迅速に得ることができます。

リンクされているコンテンツは、該当する貢献者により、現状のまま提供されるものです。これらは TI の仕様を構成するものではなく、必ずしも TI の見解を反映したものではありません。TI の使用条件を参照してください。

Product Folder Links: TPS92391

11.4 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

すべての商標は、それぞれの所有者に帰属します。

11.5 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい ESD 対策をとらないと、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

11.6 用語集

TI 用語集 この用語集には、用語や略語の一覧および定義が記載されています。



12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 23-May-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
TPS92391RHBR	Active	Production	VQFN (RHB) 32	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	92391
TPS92391RHBR.A	Active	Production	VQFN (RHB) 32	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	92391
TPS92391RHBRG4.A	Active	Production	VQFN (RHB) 32	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	92391

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

5 x 5, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4224745/A





PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要なお知らせと免責事項

テキサス・インスツルメンツは、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、 テキサス・インスツルメンツ製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した テキサス・インスツルメンツ製品の選定、(2) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとします。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている テキサス・インスツルメンツ製品を使用するアプリケーションの開発の目的でのみ、 テキサス・インスツルメンツはその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。 テキサス・インスツルメンツや第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、 テキサス・インスツルメンツおよびその代理人を完全に補償するものとし、 テキサス・インスツルメンツは一切の責任を拒否します。

テキサス・インスツルメンツの製品は、 テキサス・インスツルメンツの販売条件、または ti.com やかかる テキサス・インスツルメンツ 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。 テキサス・インスツルメンツがこれらのリソ 一スを提供することは、適用される テキサス・インスツルメンツの保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、 テキサス・インスツルメンツはそれらに異議を唱え、拒否します。

郵送先住所: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated