











ISO7310C, ISO7310FC

SLLSEI8D -JUNE 2014-REVISED APRIL 2015

ISO7310x Robust EMC, Low Power, Single Channel Digital Isolator

Features

- Signaling Rate: 25 Mbps
- Integrated Noise Filter at the Input
- Default Output 'High' and 'Low' Options
- Low Power Consumption: Typical I_{CC}
 - 1.9 mA at 1 Mbps, 3.8 mA at 25 Mbps (5V Supplies)
 - 1.4 mA at 1 Mbps, 2.6 mA at 25 Mbps (3.3V) Supplies)
- Low Propagation Delay: 32 ns Typical (5V Supplies)
- 3.3 V and 5 V Level Translation
- Wide T_A Range Specified: -40°C to 125°C
- 65 KV/µs Transient Immunity, Typical (5V Supplies)
- Robust Electromagnetic Compatibility (EMC)
 - System-level ESD, EFT, and Surge Immunity
 - Low Emissions
- Isolation Barrier Life: > 25 Years
- Operates from 3.3 V and 5 V Supplies
- Narrow Body SOIC-8 Package
- Safety and Regulatory Approvals:
 - 4242 V_{PK} Isolation per DIN V VDE V 0884-10 and DIN EN 61010-1
 - 3000 V_{RMS} Isolation for 1 minute per UL 1577
 - CSA Component Acceptance Notice 5A. IEC 60950-1 and IEC 61010-1 End Equipment Standards
 - CQC Certification per GB4943.1-2011

2 Applications

- Opto-Coupler Replacement in:
 - Industrial FieldBus
 - **ProfiBus**
 - ModBus
 - DeviceNet™ Data Buses
 - Servo Control Interface
 - Motor Control
 - **Power Supplies**
 - **Battery Packs**

3 Description


ISO7310x provide galvanic isolation up to 3000 V_{RMS} for 1 minute per UL and 4242 V_{PK} per VDE. These devices have one isolated channel comprised of a logic input and output buffer separated by a silicon dioxide (SiO₂) insulation barrier. Used in conjunction with isolated power supplies, ISO7310x prevent noise currents on a data bus or other circuit from entering the local ground and interfering with or damaging sensitive circuitry. These devices have integrated noise filters for harsh industrial environment where short noise pulses may be present at the device input pins. ISO7310x have TTL input thresholds and operate from 3 V to 5.5 V supply levels. Through innovative chip design and layout techniques, electromagnetic compatibility of ISO7310x has been significantly enhanced to enable system-level ESD, EFT, Surge and Emissions compliance.

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)
ISO7310C	SOIC (8)	4.00mm v. 2.01mm
ISO7310FC		4,90mm x 3,91mm

(1) For all available packages, see the orderable addendum at the end of the datasheet.

Simplified Schematic





1	Га	h	Δ۱	Ωf	Co	nto	nte
	ιа	v		OI.	\mathbf{c}	IIIC	1113

cations 1 iption 1 don History 2 onfiguration and Functions 4 fications 5	8.2 Functional Block Diagram 8.3 Feature Description 8.4 Device Functional Modes 9 Applications and Implementation 9.1 Application Information	12 15 16
iption	8.4 Device Functional Modes 9 Applications and Implementation	19 16
on History	9 Applications and Implementation	16
onfiguration and Functions4	• • • • • • • • • • • • • • • • • • • •	
_	9.1 Application Information	
	TF	10
bsolute Maximum Ratings5	9.2 Typical Application	10
3	10 Power Supply Recommendations	18
•	11 Layout	19
. 6		
	11.2 Layout Guidelines	19
	11.3 Layout Example	19
3		
	12.1 Trademarks	20
	12.2 Electrostatic Discharge Caution	20
	12.3 Glossary	20
ed Description11	13 Mechanical, Packaging, and Orderable	
	SD Ratings	ecommended Operating Conditions 5 hermal Information 5 lectrical Characteristics 6 witching Characteristics 6 lectrical Characteristics 7 witching Characteristics 7 witching Characteristics 7 witching Characteristics 7 witching Characteristics 7 lectrical Characteristics 7 witching Characteristics 7 lectrical Characteristics 12 lectrical Characteristics 12 lectrical Characteristics 12 lectrical Characteristics 13 lectrical Characteristics 14 lectrical Characteristics 15 lectrical Characteristics 16 lectrical Characteristics 17 lectrical Characteristics 17 lectrical Characteristics 18 lectrical Characteristics 19 lectrical

4 Revision History

С	hanges from Revision C (March 2015) to Revision D	Page
•	Added "and DINEN 61010-1" to the 4242 V _{PK} in the <i>Features</i>	
•	Deleted "(Approval Pending)" from the CSA Component Acceptance list item in the Features	<i>'</i>
•	Deleted IEC from the section title: Insulation and Safety-Related Specifications for D-8 Package	12
•	Changed the CTI Test Conditions in Insulation and Safety-Related Specifications for D-8 Package	12
•	Changed V _{ISO} Test Condition in the <i>Insulation Characteristics</i> table	13
•	Changed column CSA in the Regulatory Information table	13

Cł	hanges from Revision B (September 2014) to Revision C	Page
•	Changed Features From: Integrated Noise Filter on the Input pin To: Integrated Noise Filter at the Input	1
•	Added Features - Default Output 'High' and 'Low' Options	1
•	Changed the DIN V VDE 0884-10 To: DIN V VDE V 0884-10 in the Features	1
•	Changed Features From: 3 KV _{RMS} Isolation To: 3000 V _{RMS} Isolation	1
•	Added "(Approval Pending)" to the CSA Component Acceptance list item in the Features	1
•	Changed Features From: GB4943.1-2011 CQC Certification To: CQC Certification per GB4943.1-2011	1
•	Changed the Simplified Schematic: GND1 To: GNDI and GND2 To GNDO	1
•	Changed the Handling Ratings to ESD Ratings table and updated guidelines	5
•	Changed the CTI MIN value in Insulation and Safety-Related Specifications for D-8 Package From: >400 V To: 400	V 12
•	Added "DT1" to the Minimum internal gap in Insulation and Safety-Related Specifications for D-8 Package	12
•	Changed the DTI MIN value in <i>Insulation and Safety-Related Specifications for D-8 Package</i> From: 0.014 mm To: 13 µM	12
•	Changed the R_{IO} Test Condition in <i>Insulation and Safety-Related Specifications for D-8 Package</i> From: $T_A < 100^{\circ}C$ To: $T_A = 25^{\circ}C$	12
•	Changed the R_{IO} Test Condition in <i>Insulation and Safety-Related Specifications for D-8 Package</i> From: $T_A \le max$ To: $T_A = 125^{\circ}C$	12
•	Changed DIN V VDE 0884-10 To: DIN V VDE V 0884-10 in the Insulation Characteristics	13
•	Added V _{IOSM} to the <i>Insulation Characteristics</i> table	13

Submit Documentation Feedback

Copyright © 2014–2015, Texas Instruments Incorporated




www.ti.com

•	Changed R _S Test Conditions in <i>Insulation Characteristics</i> From: T _S To: T _S = 150°C	13
•	Changed the <i>Regulatory Information</i> table, VDE Certified From: DIN V VDE 0884-10 To: DIN V VDE V 0884-10	
	(VDE V 0884-10):2006-12 and DIN EN 61010-1 (VDE 0411-1):2011-07	13
•	Changed the Regulatory Information table, deleted (Approval Pending) statement	13
•	Changed the Regulatory Information table, CQC Certified number From: CQC14001109540 To: CQC15001121656.	13
•	Changed title From: " IEC Safety Limiting Values" To: Safety Limiting Values	14
•	Changed Table 2 Header information to include device number for the OUT column. Added Note 3	15
•	Changed Figure 14 to include a diode at V _{CC1} on the Input circuit	15
•	Changed Figure 15	16
•	Added Figure 16	17
CI	hanges from Revision A (July 2014) to Revision B	Page
•	Added device ISO7310FC	1
•	Changed Feature From: 4242 V _{PK} Isolation per DIN EN 60747-5-5 (VDE 0884-5) To: 4242 V _{PK} Isolation per DIN V VDE 0884-10	1
•	Deleted "All Agencies Approvals Planned" from the Features Safety and Regulatory Approvals:	1
•	Replaced Figure 10	10
•	Changed DIN EN 60747-5-5 To: DIN V VDE 0884-10 in the <i>Insulation Characteristics</i>	13
•	Changed DIN EN 60747-5-5 (VDE 0884-5) To: DIN V VDE 0884-10 in the Regulatory Information table	13
•	Added a NOTE in the Application Information section	16
CI	hanges from Original (March 2014) to Revision A	Page
•	Changed from a 1 page Product Preview to the full data sheet	1
•	Added Features - GB4943.1-2011 CQC Certification	1
•	Changed the Description to include: "Through innovative chip design"	1
•	Changed the Simplified Schematic	1



5 Pin Configuration and Functions



Pin Functions

PIN		1/0	DESCRIPTION		
NAME	NUMBER	1/0	DESCRIPTION		
V _{CC1}	1, 3	-	Power supply, V _{CC1}		
IN	2	1	Input		
GND1	4	-	Ground connection for V _{CC1}		
GND2	5, 7	-	Ground connection for V _{CC2}		
OUT	6	0	Output		
V _{CC2}	8	_	Power supply, V _{CC2}		



6 Specifications

6.1 Absolute Maximum Ratings⁽¹⁾

		MIN	MAX	UNIT
Supply voltage ⁽²⁾	V _{CC1} , V _{CC2}	-0.5	6	V
Voltage (2)	IN, OUT	-0.5	V _{CC} +0.5 ⁽³⁾	V
Output current	Io		±15	mA
Junction temperature	T _J		150	°C
Storage temperature	T _{stg}	-65	150	°C

⁽¹⁾ Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

			MAX	UNIT
	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±4000	\/	
VESD	discharge	Charged device model (CDM), per JEDEC specification JESD22-C101 (2)	±1500	V

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

		MIN	TYP	MAX	UNIT
V _{CC1} , V _{CC2}	Supply voltage	3		5.5	V
I _{OH}	High-level output current	-4			mA
I _{OL}	Low-level output current			4	mA
V _{IH}	High-level input voltage	2		5.5	V
V _{IL}	Low-level input voltage	0		0.8	V
t _{ui}	Input pulse duration	40			ns
1 / t _{ui}	Signaling rate	0		25	Mbps
T _J ⁽¹⁾	Junction temperature			136	°C
T _A	Ambient temperature	-40	25	125	°C

⁽¹⁾ To maintain the recommended operating conditions for T_J, see the *Thermal Information* table.

6.4 Thermal Information

	THERMAL MET	D PACKAGE (8) PINS	UNIT	
$R_{\theta JA}$	Junction-to-ambient thermal resistance		119.9	
$R_{\theta JCtop}$	Junction-to-case (top) thermal resistance		65.2	
$R_{\theta JB}$	Junction-to-board thermal resistance		61.3	90044
Ψлт	Junction-to-top characterization parameter		19.3	°C/W
ΨЈВ	Junction-to-board characterization parameter		60.7	
$R_{\theta JCbot}$	Junction-to-case (bottom) thermal resistance		N/A	
P_D	Maximum power dissipation		34	
P _{D1}	Power dissipation by Side-1	$V_{CC1} = V_{CC2} = 5.5 \text{ V}, T_J = 150^{\circ}\text{C}, C_L = 15 \text{ pF},$ Input a 12.5 MHz 50% duty-cycle square wave	7.9	mW
P _{D2}	Power dissipation by Side-2	input a 12.5 Miliz 50 % duty-cycle square wave	26.1	

⁽¹⁾ For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

⁽²⁾ All voltage values are with respect to network ground terminal and are peak voltage values.

⁽³⁾ Maximum voltage must not exceed 6 V.

⁽²⁾ JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



6.5 Electrical Characteristics

 V_{CC1} and V_{CC2} at 5 V \pm 10% (over recommended operating conditions unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
V	Libert Investment walter	$I_{OH} = -4 \text{ mA}$; se	e Figure 9	V _{CC2} - 0.5	4.7		
V _{OH}	High-level output voltage	$I_{OH} = -20 \mu A; see$	ee Figure 9	V _{CC2} - 0.1	5		V
.,		I _{OL} = 4 mA; see	Figure 9		0.2	0.4	.,
V_{OL}	Low-level output voltage	I _{OL} = 20 μA; see	Figure 9		0	0.1	V
V _{I(HYS)}	Input threshold voltage hysteresis				480		mV
I _{IH}	High-level input current	IN = V _{CC}				10	μA
I _{IL}	Low-level input current	IN = 0 V		-10			μA
CMTI	Common-mode transient immunity	V _I = V _{CC} or 0 V; see Figure 11.		25	65		kV/µs
SUPPL	Y CURRENT (All inputs switching with so	uare wave clock	signal for dynamic I _{CC} measurement	ent)			
I _{CC1}		DO : 4 MI	DC Input: $V_I = V_{CC}$ or 0 V,		0.3	0.6	
I _{CC2}		DC to 1 Mbps	AC Input: C _L = 15pF		1.6	2.4	
I _{CC1}		40.14	0 45 5		0.5	1	
I _{CC2}	Supply current for V _{CC1} and V _{CC2}	10 Mbps	$C_L = 15pF$		2.2	3.2	mA
I _{CC1}		05.14	0 1		0.8	1.3	
I _{CC2}		25 Mbps	$C_L = 15pF$		3	4.2	

6.6 Switching Characteristics

 V_{CC1} and V_{CC2} at 5 V \pm 10% (over recommended operating conditions unless otherwise noted)

001	002	•	,			
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH}, t_{PHL}	Propagation delay time	See Figure 0	20	32	58	ns
PWD ⁽¹⁾	Pulse width distortion t _{PHL} - t _{PLH}	See Figure 9			4	ns
t _{sk(pp)} (2)	Part-to-part skew time				24	ns
t _r	Output signal rise time	See Figure 9		2.5		ns
t _f	Output signal fall time	See Figure 9		2		ns
t _{fs}	Fail-safe output delay time from input power loss	See Figure 10		7.5		μs

⁽¹⁾ Also known as pulse skew.

Submit Documentation Feedback

Copyright © 2014–2015, Texas Instruments Incorporated

t_{sk(pp)} is the magnitude of the difference in propagation delay times between any terminals of different devices switching in the same direction while operating at identical supply voltages, temperature, input signals and loads.



6.7 Electrical Characteristics

 V_{CC1} and V_{CC2} at 3.3 V \pm 10% (over recommended operating conditions unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
	I limb lavel autout valta a	$I_{OH} = -4 \text{ mA}$; see	I _{OH} = -4 mA; see Figure 9		3		
V _{OH}	High-level output voltage	$I_{OH} = -20 \mu A$; see	e Figure 9	V _{CC2} - 0.1	3.3		V
		I _{OL} = 4 mA; see F	Figure 9		0.2	0.4	
V _{OL}	Low-level output voltage	$I_{OL} = 20 \mu A$; see	Figure 9		0	0.1	V
V _{I(HYS)}	Input threshold voltage hysteresis				450		mV
I _{IH}	High-level input current	IN = V _{CC}				10	μΑ
I _{IL}	Low-level input curre	IN = 0 V		-10			μA
CMTI	Common-mode transient immunity	$V_I = V_{CC}$ or 0 V; s	see Figure 11	25	50		kV/µs
SUPPLY	Y CURRENT (All inputs switching with	square wave cloc	k signal for dynamic I _{CC} measureme	ent)			
I _{CC1}		DO to 4 Mb	DC Input: $V_I = V_{CC}$ or 0 V,		0.2	0.4	
I _{CC2}		DC to 1 Mbps	AC Input: $C_L = 15pF$		1.2	1.8	
I _{CC1}	1	40.14	0 45 5		0.3	0.5	
I _{CC2}	Supply current for V _{CC1} and V _{CC2} 10 Mbps	10 Mbps	$C_L = 15pF$		1.6	2.2	mA
I _{CC1}	1				0.5	0.8	
I _{CC2}	1	25 Mbps	$C_L = 15pF$		2.1	3	

6.8 Switching Characteristics

 V_{CC1} and V_{CC2} at 3.3 V \pm 10% (over recommended operating conditions unless otherwise noted)


001	002	9				
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH},t_{PHL}	Propagation delay time	See Figure 0	22	36	67	ns
PWD ⁽¹⁾	Pulse width distortion t _{PHL} - t _{PLH}	See Figure 9			3.5	ns
t _{sk(pp)} (2)	Part-to-part skew time				28	ns
t _r	Output signal rise time	See Figure 9		3.2		ns
t _f	Output signal fall time	See Figure 9		2.7		ns
t _{fs}	Fail-safe output delay time from input power loss	See Figure 10		7.4		μs

⁽¹⁾ Also known as pulse skew.

t_{sk(pp)} is the magnitude of the difference in propagation delay times between any terminals of different devices switching in the same direction while operating at identical supply voltages, temperature, input signals and loads.



6.9 Typical Characteristics





Submit Documentation Feedback


Copyright © 2014–2015, Texas Instruments Incorporated



Typical Characteristics (continued)









TEXAS INSTRUMENTS

7 Parameter Measurement Information




- (1) The input pulse is supplied by a generator having the following characteristics: PRR \leq 50 kHz, 50% duty cycle, $t_f \leq 3$ ns, $t_f \leq 3$ ns, $Z_O = 50 \Omega$. At the input, a 50- Ω resistor is required to terminate the Input Generator signal. It is not needed in actual application.
- (2) $C_L = 15 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 9. Switching Characteristic Test Circuit and Voltage Waveforms



A. $C_L = 15 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 10. Fail-Safe Output Delay-Time Test Circuit and Voltage Waveforms



(1) $C_L = 15 \text{ pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

Figure 11. Common-Mode Transient Immunity Test Circuit

Submit Documentation Feedback



8 Detailed Description

8.1 Overview

The isolator in Figure 12 is based on a capacitive isolation barrier technique. The I/O channel of the device consists of two internal data channels, a high-frequency (HF) channel with a bandwidth from 100 kbps up to 25 Mbps, and a low-frequency (LF) channel covering the range from 100 kbps down to DC.

In principle, a single-ended input signal entering the HF channel is split into a differential signal via the inverter gate at the input. The following capacitor-resistor networks differentiate the signal into transient pulses, which then are converted into CMOS levels by a comparator. The transient pulses at the input of the comparator can be either above or below the common mode voltage VREF depending on whether the input bit transitioned from 0 to 1 or 1 to 0. The comparator threshold is adjusted based on the expected bit transition. A decision logic (DCL) at the output of the HF channel comparator measures the durations between signal transients. If the duration between two consecutive transients exceeds a certain time limit, (as in the case of a low-frequency signal), the DCL forces the output-multiplexer to switch from the high-frequency to the low-frequency channel.

8.2 Functional Block Diagram




Figure 12. Conceptual Block Diagram of a Digital Capacitive Isolator

Because low-frequency input signals require the internal capacitors to assume prohibitively large values, these signals are pulse-width modulated (PWM) with the carrier frequency of an internal oscillator, thus creating a sufficiently high frequency, capable of passing the capacitive barrier. As the input is modulated, a low-pass filter (LPF) is needed to remove the high-frequency carrier from the actual data before passing it on to the output multiplexer.



8.3 Feature Description

PRODUCT	RATED ISOLATION	MAX DATA RATE	DEFAULT OUTPUT
ISO7310C	3000 V _{RMS} / 4242 V _{PK} ⁽¹⁾	25 Mbps	High
ISO7310FC	SUUU V _{RMS} / 4242 V _{PK} (*)	25 Mbps	Low

⁽¹⁾ See the Regulatory Information section for detailed Isolation Ratings

8.3.1 High Voltage Feature Description

8.3.1.1 Insulation and Safety-Related Specifications for D-8 Package

over recommended operating conditions (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
L(I01)	Minimum air gap (clearance)	Shortest terminal-to-terminal distance through air	4			mm
L(102)	Minimum external tracking (creepage)	Shortest terminal-to-terminal distance across the package surface	4			mm
СТІ	Tracking resistance (comparative tracking index)	DIN EN 60112 (VDE 0303-11); IEC 60112	400			V
DTI	Minimum internal gap (internal clearance)	Distance through the insulation	13			μm
Б	Isolation resistance, input to	V _{IO} = 500 V, T _A = 25°C		>10 ¹²		Ω
R _{IO}	output ⁽¹⁾	V _{IO} = 500 V, 100°C ≤ T _A ≤ 125°C		>10 ¹¹		Ω
C _{IO}	Isolation capacitance, input to output (1)	$V_{IO} = 0.4 \sin (2\pi ft), f = 1 \text{ MHz}$		0.5		pF
C _I	Input capacitance ⁽²⁾	$V_I = V_{CC}/2 + 0.4 \sin(2\pi ft)$, f = 1 MHz, $V_{CC} = 5 \text{ V}$		1.6		pF

⁽¹⁾ All pins on each side of the barrier tied together creating a two-terminal device.

NOTE

Creepage and clearance requirements should be applied according to the specific equipment isolation standards of an application. Care should be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed-circuit board do not reduce this distance.

Creepage and clearance on a printed-circuit board become equal in certain cases. Techniques such as inserting grooves and/or ribs on a printed circuit board are used to help increase these specifications.

Submit Documentation Feedback

⁽²⁾ Measured from input pin to ground.



8.3.1.2 Insulation Characteristics

over recommended operating conditions (unless otherwise noted)

	PARAMETER ⁽¹⁾	TEST CONDITIONS	SPECIFICATION	UNIT
V_{IOWM}	Maximum isolation working voltage		400	V_{RMS}
V _{IORM}	Maximum repetitive peak voltage per DIN V VDE V 0884-10		566	V _{PK}
		After Input/Output safety test subgroup 2/3, $V_{PR} = V_{IORM} \times 1.2$, $t = 10 \text{ s}$, Partial discharge < 5 pC	680	
V _{PR}	Input-to-output test voltage per DIN V VDE V 0884-10	Method a, After environmental tests subgroup 1, $V_{PR} = V_{IORM} \times 1.6$, $t = 10 \text{ s}$, Partial Discharge $< 5 \text{ pC}$	906	V _{PK}
Me V _{PF}	Method b1, V _{PR} = V _{IORM} x 1.875, t = 1 s (100% Production test) Partial discharge < 5 pC	1062		
V _{IOTM}	Maximum transient overvoltage per DIN V VDE V 0884-10	V _{TEST} = V _{IOTM} t = 60 sec (qualification) t= 1 sec (100% production)	4242	V _{PK}
V _{IOSM}	Maximum surge isolation voltage per DIN V VDE V 0884-10	Test method per IEC 60065, 1.2/50 μ s waveform, $V_{TEST} = 1.3 \text{ x } V_{IOSM} = 7800 \text{ V}_{PK}$ (qualification)	6000	V _{PK}
V _{ISO}	Withstand isolation voltage per UL 1577	$\begin{array}{l} V_{TEST}=V_{ISO}=3000~V_{RMS},~t=60~sec\\ (qualification);\\ V_{TEST}=1.2~x~V_{ISO}=3600~V_{RMS},~t=1~sec~(100\%\\ production) \end{array}$	3000	V _{RMS}
R _S	Insulation resistance	V _{IO} = 500 V at T _S = 150°C	>10 ⁹	Ω
	Pollution degree		2	

⁽¹⁾ Climatic Classification 40/125/21

Table 1. IEC 60664-1 Ratings Table

PARAMETER	TEST CONDITIONS	SPECIFICATION
Basic isolation group	Material group	H
la stallation plansification	Rated mains voltage ≤ 150 V _{RMS}	I–IV
Installation classification	Rated mains voltage ≤ 300 V _{RMS}	I–III

8.3.1.3 Regulatory Information

VDE	CSA	UL	CQC
Certified according to DIN V VDE V 0884-10 (VDE V 0884-10):2006-12 and DIN EN 61010-1 (VDE 0411-1):2011-07	Approved under CSA Component Acceptance Notice 5A, IEC 60950-1, and IEC 61010-1	Recognized under UL 1577 Component Recognition Program	Certified according to GB4943.1- 2011
Basic Insulation Maximum Transient Overvoltage, 4242 V _{PK} ; Maximum Surge Isolation Voltage, 6000 V _{PK} ; Maximum Repetitive Peak Voltage, 566 V _{PK}	400 V _{RMS} Basic Insulation and 200 V _{RMS} Reinforced Insulation working voltage per CSA 60950-1-07+A1+A2 and IEC 60950-1 2nd Ed.+A1+A2; 300 V _{RMS} Basic Insulation working voltage per CSA 61010-1-12 and IEC 61010-1 3rd Ed.	Single protection, 3000 V _{RMS} ⁽¹⁾	Basic Insulation, Altitude ≤ 5000 m, Tropical Climate, 250 V _{RMS} maximum working voltage
Certificate number: 40016131	Master contract number: 220991	File number: E181974	Certificate number: CQC15001121656

⁽¹⁾ Production tested \geq 3600 V_{RMS} for 1 second in accordance with UL 1577.



8.3.1.4 Safety Limiting Values

Safety limiting intends to prevent potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to overheat the die and damage the isolation barrier, potentially leading to secondary system failures.

	PARAMETER	MIN	TYP	MAX	UNIT	
	Safety input, output, or supply	$R_{\theta JA} = 119.9 \text{ °C/W}, V_I = 5.5 \text{ V}, T_J = 150 \text{ °C}, T_A = 25 \text{ °C}$			190	A
IS	current	$R_{\theta JA} = 119.9 \text{ °C/W}, V_I = 3.6 \text{ V}, T_J = 150 \text{ °C}, T_A = 25 \text{ °C}$			290	mA
T _S	Maximum case temperature				150	°C

The safety-limiting constraint is the absolute-maximum junction temperature specified in the *Absolut Maximun Ratings* table. The power dissipation and junction-to-air thermal impedance of the device installed in the application hardware determines the junction temperature. The assumed junction-to-air thermal resistance in the *Thermal Information* table is that of a device installed on a High-K Test Board for Leaded Surface-Mount Packages. The power is the recommended maximum input voltage times the current. The junction temperature is then the ambient temperature plus the power times the junction-to-air thermal resistance.




Figure 13. θ_{JC} Thermal Derating Curve per DIN V VDE 0884-10

Submit Documentation Feedback

Copyright © 2014–2015, Texas Instruments Incorporated



8.4 Device Functional Modes

Table 2. Function Table⁽¹⁾

V	V	INI		DUT
V _{CC1}	V _{CC2}	IN	ISO7310C	ISO7310FC
		Н	Н	Н
PU	PU	L	L	L
		Open	H ⁽²⁾	L ⁽³⁾
PD	PU	X	H ⁽²⁾	L ⁽³⁾
X	PD	X	Undetermined	Undetermined

- $PU = Powered up (V_{CC} \ge 3 V); PD = Powered down (V_{CC} \le 2.1 V); X = Irrelevant; H = High level; L = Low level In fail-safe condition, output defaults to high level$
- In fail-safe condition, output defaults to low level

8.4.1 Device I/O Schematics




Figure 14. Device I/O Schematics



9 Applications and Implementation

NOTE


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

ISO7310x use single-ended TTL-logic switching technology. The supply voltage range is from 3 V to 5.5 V for both supplies, V_{CC1} and V_{CC2} . When designing with digital isolators, it is important to keep in mind that due to the single-ended design structure, digital isolators do not conform to any specific interface standard and are only intended for isolating single-ended CMOS or TTL digital signal lines. The isolator is typically placed between the data controller (i.e. μ C or UART), and a data converter or a line transceiver, regardless of the interface type or standard.

9.2 Typical Application

ISO7310 can be used with Texas Instruments' microcontroller, CAN transceiver, transformer driver, and low-dropout voltage regulator to create an Isolated CAN Interface as shown in Figure 15.



(1) Multiple pins and capacitors omitted for clarity purpose.

Figure 15. Isolated CAN Interface

Submit Documentation Feedback



Typical Application (continued)

9.2.1 Design Requirements

9.2.1.1 Typical Supply Current Equations

At $V_{CC1} = V_{CC2} = 5 \text{ V}$

- $I_{CC1} = 0.30517 + (0.01983 \times f)$
- $I_{CC2} = 1.40021 + (0.02879 \times f) + (0.0021 \times f \times C_L)$

At $V_{CC1} = V_{CC2} = 3.3 \text{ V}$

- $I_{CC1} = 0.18133 + (0.01166 \times f)$
- $I_{CC2} = 1.053 + (0.01607 \text{ x f}) + (0.001488 \text{ x f x C}_L)$

 I_{CC1} and I_{CC2} are typical supply currents measured in mA, f is data rate measured in Mbps, C_L is the capacitive load measured in pF.

9.2.2 Detailed Design Procedure

Unlike optocouplers, which need external components to improve performance, provide bias, or limit current, ISO7310x only need two external bypass capacitors to operate.




Figure 16. Typical ISO7310 Circuit Hook-up

9.2.2.1 Electromagnetic Compatibility (EMC) Considerations

Many applications in harsh industrial environment are sensitive to disturbances such as electrostatic discharge (ESD), electrical fast transient (EFT), surge and electromagnetic emissions. These electromagnetic disturbances are regulated by international standards such as IEC 61000-4-x and CISPR 22. Although system-level performance and reliability depends, to a large extent, on the application board design and layout, the ISO7310x incorporate many chip-level design improvements for overall system robustness. Some of these improvements include:


- Robust ESD protection cells for input and output signal pins and inter-chip bond pads.
- Low-resistance connectivity of ESD cells to supply and ground pins.
- Enhanced performance of high voltage isolation capacitor for better tolerance of ESD, EFT and surge events.
- Bigger on-chip decoupling capacitors to bypass undesirable high energy signals through a low impedance path.
- PMOS and NMOS devices isolated from each other by using guard rings to avoid triggering of parasitic SCRs.
- Reduced common mode currents across the isolation barrier by ensuring purely differential internal operation.



Typical Application (continued)

9.2.3 Application Performance Curves

Typical eye diagrams of ISO7310x below indicate very low jitter and wide open eye at the maximum data rate of 25 Mbps.



10 Power Supply Recommendations

To ensure reliable operation at all data rates and supply voltages, a 0.1 μ F bypass capacitor is recommended at input and output supply pins (V_{CC1} & V_{CC2}). The capacitors should be placed as close to the supply pins as possible. If only a single primary-side power supply is available in an application, isolated power can be generated for the secondary-side with the help of a transformer driver such as Texas Instruments' SN6501. For such applications, detailed power supply design and transformer selection recommendations are available in SN6501 datasheet (SLLSEA0) .

Submit Documentation Feedback



11 Layout

11.1 PCB Material

For digital circuit boards operating below 150 Mbps, (or rise and fall times higher than 1 ns), and trace lengths of up to 10 inches, use standard FR-4 epoxy-glass as PCB material. FR-4 (Flame Retardant 4) meets the requirements of Underwriters Laboratories UL94-V0, and is preferred over cheaper alternatives due to its lower dielectric losses at high frequencies, less moisture absorption, greater strength and stiffness, and its self-extinguishing flammability-characteristics.

11.2 Layout Guidelines

A minimum of four layers is required to accomplish a low EMI PCB design (see Figure 19). Layer stacking should be in the following order (top-to-bottom): high-speed signal layer, ground plane, power plane and low-frequency signal layer.

- Routing the high-speed traces on the top layer avoids the use of vias (and the introduction of their inductances) and allows for clean interconnects between the isolator and the transmitter and receiver circuits of the data link.
- Placing a solid ground plane next to the high-speed signal layer establishes controlled impedance for transmission line interconnects and provides an excellent low-inductance path for the return current flow.
- Placing the power plane next to the ground plane creates additional high-frequency bypass capacitance of approximately 100pF/in².
- Routing the slower speed control signals on the bottom layer allows for greater flexibility as these signal links
 usually have margin to tolerate discontinuities such as vias.

If an additional supply voltage plane or signal layer is needed, add a second power / ground plane system to the stack to keep it symmetrical. This makes the stack mechanically stable and prevents it from warping. Also the power and ground plane of each power system can be placed closer together, thus increasing the high-frequency bypass capacitance significantly.

For detailed layout recommendations, see Application Note SLLA284, Digital Isolator Design Guide,

11.3 Layout Example




Figure 19. Recommended Layer Stack



12 Device and Documentation Support

12.1 Trademarks

DeviceNet is a trademark of Texas Instruments.

12.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.3 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

Isolation Glossary, SLLA353


13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

0 Submit Documentation Feedback



SOIC




NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15], per side.
- 4. This dimension does not include interlead flash.5. Reference JEDEC registration MS-012, variation AA.



SOIC




NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



www.ti.com 10-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
ISO7310CD	Active	Production	SOIC (D) 8	75 TUBE	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310C
ISO7310CD.A	Active	Production	SOIC (D) 8	75 TUBE	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310C
ISO7310CD.B	Active	Production	SOIC (D) 8	75 TUBE	-	Call TI	Call TI	-40 to 125	
ISO7310CDR	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310C
ISO7310CDR.A	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310C
ISO7310CDR.B	Active	Production	SOIC (D) 8	2500 LARGE T&R	-	Call TI	Call TI	-40 to 125	
ISO7310FCD	Active	Production	SOIC (D) 8	75 TUBE	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310FC
ISO7310FCD.A	Active	Production	SOIC (D) 8	75 TUBE	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310FC
ISO7310FCD.B	Active	Production	SOIC (D) 8	75 TUBE	-	Call TI	Call TI	-40 to 125	
ISO7310FCDR	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310FC
ISO7310FCDR.A	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	FULL NIPDAU	Level-2-260C-1 YEAR	-40 to 125	7310FC
ISO7310FCDR.B	Active	Production	SOIC (D) 8	2500 LARGE T&R	-	Call TI	Call TI	-40 to 125	

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



PACKAGE OPTION ADDENDUM

www.ti.com 10-Nov-2025

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 18-Jul-2025

TAPE AND REEL INFORMATION



TAPE DIMENSIONS + K0 - P1 - B0 W Cavity - A0 -

A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ISO7310CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
ISO7310FCDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

PACKAGE MATERIALS INFORMATION

www.ti.com 18-Jul-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ISO7310CDR	SOIC	D	8	2500	350.0	350.0	43.0
ISO7310FCDR	SOIC	D	8	2500	350.0	350.0	43.0

PACKAGE MATERIALS INFORMATION

www.ti.com 18-Jul-2025

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
ISO7310CD	D	SOIC	8	75	505.46	6.76	3810	4
ISO7310CD.A	D	SOIC	8	75	505.46	6.76	3810	4
ISO7310FCD	D	SOIC	8	75	505.46	6.76	3810	4
ISO7310FCD.A	D	SOIC	8	75	505.46	6.76	3810	4

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025