

## Industry-Standard Dual Operational Amplifiers

### 1 Features

- Wide supply range of 3V to 36V (B, BA versions)
- Quiescent current: 300µA/ch (B, BA versions)
- Unity-gain bandwidth of 1.2MHz (B, BA versions)
- Common-mode input voltage range includes ground, enabling direct sensing near ground
- 2mV input offset voltage maximum at 25°C (BA version)
- 3mV input offset voltage maximum at 25°C (A, B versions)
- Internal RF and EMI filter (B, BA versions)
- On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

### 2 Applications

- Merchant network and server power supply units
- Multi-function printers
- Power supplies and mobile chargers
- Motor control: AC induction, brushed DC, brushless DC, high-voltage, low-voltage, permanent magnet, and stepper motor
- Desktop PC and motherboard
- Indoor and outdoor air conditioners
- Washers, dryers, and refrigerators
- AC inverters, string inverters, central inverters, and voltage frequency drives
- Uninterruptible power supplies
- Electronic point-of-sale systems

### 3 Description

The LM358B and LM2904B devices are the next-generation versions of the industry-standard operational amplifiers (op amps) LM358 and LM2904, which include two high-voltage (36V) op amps. These

devices provide outstanding value for cost-sensitive applications, with features including low offset (300µV, typical), common-mode input range to ground, and high differential input voltage capability.

The LM358B and LM2904B op amps simplify circuit design with enhanced features such as unity-gain stability, lower offset voltage maximum of 3mV (2mV maximum for LM358BA and LM2904BA), and lower quiescent current of 300µA per amplifier (typical). High ESD (2kV, HBM) and integrated EMI and RF filters enable the LM358B and LM2904B devices to be used in the most rugged, environmentally challenging applications.

The LM358B and LM2904B amplifiers are available in micro-sized packaging, such as the SOT23-8, as well as industry standard packages including SOIC, TSSOP, and VSSOP.

#### Package Information

| PART NUMBER <sup>(1)</sup>                                                        | PACKAGE         | PACKAGE SIZE <sup>(2)</sup> |
|-----------------------------------------------------------------------------------|-----------------|-----------------------------|
| LM358B, LM358BA, LM2904B, LM2904BA, LM358, LM358A, LM2904, LM2904V, LM258, LM258A | D (SOIC, 8)     | 4.9mm × 6mm                 |
| LM358B, LM358BA, LM2904B, LM2904BA, LM358, LM358A, LM2904, LM2490V                | PW (TSSOP, 8)   | 3mm × 6.4mm                 |
| LM358B, LM358BA, LM2904B, LM2904BA, LM358, LM358A, LM2904, LM2904V, LM258, LM258A | DGK (VSSOP, 8)  | 3mm × 4.9mm                 |
| LM358B, LM358BA, LM2904B, LM2904BA                                                | DDF (SOT-23, 8) | 2.9mm × 2.8mm               |
| LM358, LM2904                                                                     | PS (SO, 8)      | 6.2mm × 7.8mm               |
| LM358, LM2904, LM358A, LM258, LM258A                                              | P (PDIP, 8)     | 9.81mm × 9.43mm             |
| LM158, LM158A                                                                     | JG (CDIP, 8)    | 9.6mm × 6.67mm              |
| LM158, LM158A                                                                     | FK (LCCC, 20)   | 8.89mm × 8.89mm             |

#### Family Comparison

| Specification                     | LM358B<br>LM358BA | LM2904B<br>LM2904BA | LM358<br>LM358A      | LM2904     | LM2904V<br>LM2904AV | LM258<br>LM258A     | LM158<br>LM158A     | Units |
|-----------------------------------|-------------------|---------------------|----------------------|------------|---------------------|---------------------|---------------------|-------|
| Supply voltage                    | 3 to 36           | 3 to 36             | 3 to 30              | 3 to 26    | 3 to 30             | 3 to 30             | 3 to 30             | V     |
| Offset voltage (max, 25°C)        | ± 3<br>± 2        | ± 3<br>± 2          | ± 7<br>± 3           | ± 7        | ± 7<br>± 2          | ± 5<br>± 3          | ± 5<br>± 2          | mV    |
| Input bias current (typ / max)    | 10 / 35           | 10 / 35             | 20 / 250<br>15 / 100 | 20 / 250   | 20 / 250            | 20 / 150<br>15 / 80 | 20 / 150<br>15 / 50 | nA    |
| Gain bandwidth product            | 1.2               | 1.2                 | 0.7                  | 0.7        | 0.7                 | 0.7                 | 0.7                 | MHz   |
| Supply current (typ, per channel) | 0.3               | 0.3                 | 0.35                 | 0.35       | 0.35                | 0.35                | 0.35                | mA    |
| ESD (HBM)                         | 2000              | 2000                | 500                  | 500        | 500                 | 500                 | 500                 | V     |
| Operating ambient temperature     | –40 to 85         | –40 to 125          | 0 to 70              | –40 to 125 | –40 to 125          | –25 to 85           | –55 to 125          | °C    |


- (1) For all available packages, see the orderable addendum at the end of the data sheet.
- (2) The package size (length × width) is a nominal value and includes pins, where applicable.




## Table of Contents

|                                                                                                           |           |                                                                          |           |
|-----------------------------------------------------------------------------------------------------------|-----------|--------------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                                                                                   | <b>1</b>  | <b>7 Detailed Description</b> .....                                      | <b>25</b> |
| <b>2 Applications</b> .....                                                                               | <b>1</b>  | 7.1 Overview.....                                                        | 25        |
| <b>3 Description</b> .....                                                                                | <b>1</b>  | 7.2 Functional Block Diagram: LM358B, LM358BA,<br>LM2904B, LM2904BA..... | 25        |
| <b>4 Pin Configuration and Functions</b> .....                                                            | <b>3</b>  | 7.3 Feature Description.....                                             | 26        |
| <b>5 Specifications</b> .....                                                                             | <b>4</b>  | 7.4 Device Functional Modes.....                                         | 26        |
| 5.1 Absolute Maximum Ratings.....                                                                         | 4         | <b>8 Application and Implementation</b> .....                            | <b>27</b> |
| 5.2 ESD Ratings.....                                                                                      | 4         | 8.1 Application Information.....                                         | 27        |
| 5.3 Recommended Operating Conditions.....                                                                 | 5         | 8.2 Typical Application.....                                             | 27        |
| 5.4 Thermal Information.....                                                                              | 5         | 8.3 Power Supply Recommendations.....                                    | 28        |
| 5.5 Electrical Characteristics: LM358B and LM358BA.....                                                   | 6         | 8.4 Layout.....                                                          | 28        |
| 5.6 Electrical Characteristics: LM2904B and<br>LM2904BA.....                                              | 8         | <b>9 Device and Documentation Support</b> .....                          | <b>30</b> |
| 5.7 Electrical Characteristics: LM358, LM358A.....                                                        | 10        | 9.1 Receiving Notification of Documentation Updates....                  | 30        |
| 5.8 Electrical Characteristics: LM2904, LM2904V.....                                                      | 11        | 9.2 Support Resources.....                                               | 30        |
| 5.9 Electrical Characteristics: LM158, LM158A.....                                                        | 12        | 9.3 Trademarks.....                                                      | 30        |
| 5.10 Electrical Characteristics: LM258, LM258A.....                                                       | 14        | 9.4 Electrostatic Discharge Caution.....                                 | 30        |
| 5.11 Typical Characteristics: LM358B and LM2904B.....                                                     | 15        | 9.5 Glossary.....                                                        | 30        |
| 5.12 Typical Characteristics: LM158, LM158A,<br>LM258, LM258A, LM358, LM358A, LM2904, and<br>LM2904V..... | 22        | <b>10 Revision History</b> .....                                         | <b>30</b> |
| <b>6 Parameter Measurement Information</b> .....                                                          | <b>24</b> | <b>11 Mechanical, Packaging, and Orderable<br/>Information</b> .....     | <b>32</b> |

## 4 Pin Configuration and Functions



**Figure 4-1. D, DDF, DGK, P, PS, PW, and JG  
Package  
8-Pin SOIC, SOT23-8, VSSOP, PDIP, SO, TSSOP,  
and CDIP  
Top View**



NC - No internal connection

**Figure 4-2. FK Package  
20-Pin LCCC  
Top View**

**Table 4-1. Pin Functions**

| NAME | PIN                                      |                                                                 | I/O | DESCRIPTION                                                      |
|------|------------------------------------------|-----------------------------------------------------------------|-----|------------------------------------------------------------------|
|      | LCCC <sup>(1)</sup>                      | SOIC, SOT23-8, VSSOP, CDIP, PDIP, SO, TSSOP, CFP <sup>(1)</sup> |     |                                                                  |
| IN1– | 5                                        | 2                                                               | I   | Negative input                                                   |
| IN1+ | 7                                        | 3                                                               | I   | Positive input                                                   |
| IN2– | 15                                       | 6                                                               | I   | Negative input                                                   |
| IN2+ | 12                                       | 5                                                               | I   | Positive input                                                   |
| OUT1 | 2                                        | 1                                                               | O   | Output                                                           |
| OUT2 | 17                                       | 7                                                               | O   | Output                                                           |
| V–   | 10                                       | 4                                                               | —   | Negative (lowest) supply or ground (for single-supply operation) |
| NC   | 1, 3, 4, 6, 8, 9, 11, 13, 14, 16, 18, 19 | —                                                               | —   | No internal connection                                           |
| V+   | 20                                       | 8                                                               | —   | Positive (highest) supply                                        |

(1) For a listing of which devices are available in what packages, see [Section 3](#).

## 5 Specifications

### 5.1 Absolute Maximum Ratings

over operating ambient temperature range (unless otherwise noted)<sup>(1)</sup>

|                                                                                                                                                |              |                                                                                                   | MIN  | MAX       | UNIT               |
|------------------------------------------------------------------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------------------|------|-----------|--------------------|
| Supply voltage, $V_S = ([V+] - [V-])$                                                                                                          |              | LM358B, LM358BA,<br>LM2904B, LM2904BA                                                             |      | ±20 or 40 | V                  |
|                                                                                                                                                |              | LM158, LM258, LM358,<br>LM158A, LM258A, LM358A,<br>LM2904V                                        |      | ±16 or 32 |                    |
|                                                                                                                                                |              | LM2904                                                                                            |      | ±13 or 26 |                    |
| Differential input voltage, $V_{ID}$ <sup>(2)</sup>                                                                                            |              | LM358B, LM358BA,<br>LM2904B, LM2904BA, LM158,<br>LM258, LM358, LM158A,<br>LM258A, LM358A, LM2904V | –32  | 32        | V                  |
|                                                                                                                                                |              | LM2904                                                                                            | –26  | 26        |                    |
| Input voltage, $V_I$                                                                                                                           | Either input | LM358B, LM358BA,<br>LM2904B, LM2904BA                                                             | –0.3 | 40        | V                  |
|                                                                                                                                                |              | LM158, LM258, LM358,<br>LM158A, LM258A, LM358A,<br>LM2904V                                        | –0.3 | 32        |                    |
|                                                                                                                                                |              | LM2904                                                                                            | –0.3 | 26        |                    |
| Duration of output short circuit (one amplifier) to ground at (or below) $T_A = 25^{\circ}\text{C}$ ,<br>$V_S \leq 15\text{ V}$ <sup>(3)</sup> |              |                                                                                                   |      | Unlimited | s                  |
| Operating ambient temperature, $T_A$                                                                                                           |              | LM158, LM158A                                                                                     | –55  | 125       | $^{\circ}\text{C}$ |
|                                                                                                                                                |              | LM258, LM258A                                                                                     | –25  | 85        |                    |
|                                                                                                                                                |              | LM358B, LM358BA                                                                                   | –40  | 85        |                    |
|                                                                                                                                                |              | LM358, LM358A                                                                                     | 0    | 70        |                    |
|                                                                                                                                                |              | LM2904B, LM2904BA,<br>LM2904, LM2904V                                                             | –40  | 125       |                    |
| Operating virtual-junction temperature, $T_J$                                                                                                  |              |                                                                                                   |      | 150       | $^{\circ}\text{C}$ |
| Storage temperature, $T_{\text{stg}}$                                                                                                          |              |                                                                                                   | –65  | 150       | $^{\circ}\text{C}$ |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) Differential voltages are at  $IN+$ , with respect to  $IN-$ .
- (3) Short circuits from outputs to  $V_S$  can cause excessive heating and eventual destruction.

### 5.2 ESD Ratings

|                                                                 |                         | VALUE                                                                          | UNIT  |   |
|-----------------------------------------------------------------|-------------------------|--------------------------------------------------------------------------------|-------|---|
| LM358B, LM358BA, LM2904B, AND LM2904BA                          |                         |                                                                                |       |   |
| V <sub>(ESD)</sub>                                              | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V |
|                                                                 |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±1500 |   |
| LM158, LM258, LM358, LM158, LM258A, LM358A, LM2904, AND LM2904V |                         |                                                                                |       |   |
| V <sub>(ESD)</sub>                                              | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±500  | V |
|                                                                 |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±1000 |   |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

|                 |                                                | MIN                                                  | MAX    | UNIT |
|-----------------|------------------------------------------------|------------------------------------------------------|--------|------|
| V <sub>S</sub>  | Supply voltage, V <sub>S</sub> = ([V+] – [V–]) | LM358B, LM358BA, LM2904B, LM2904BA                   | 336    | V    |
|                 |                                                | LM158, LM258, LM358, LM158A, LM258A, LM358A, LM2904V | 330    |      |
|                 |                                                | LM2904                                               | 326    |      |
| V <sub>CM</sub> | Common-mode voltage                            | V–                                                   | V+ – 2 | V    |
| T <sub>A</sub>  | Operating ambient temperature                  | LM358B, LM358BA                                      | –4085  | °C   |
|                 |                                                | LM2904B, LM2904BA, LM2904, LM2904V                   | –40125 |      |
|                 |                                                | LM358, LM358A                                        | 070    |      |
|                 |                                                | LM258, LM258A                                        | –2085  |      |
|                 |                                                | LM158, LM158A                                        | –55125 |      |

### 5.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | LM258, LM258A, LM358, LM358A, LM358B, LM358BA, LM2904, LM2904B, LM2904BA, LM2904V <sup>(2)</sup> |             |          |         |            |              | LM158, LM158A |           | UNIT |
|-------------------------------|----------------------------------------------|--------------------------------------------------------------------------------------------------|-------------|----------|---------|------------|--------------|---------------|-----------|------|
|                               |                                              | D (SOIC)                                                                                         | DGK (VSSOP) | P (PDIP) | PS (SO) | PW (TSSOP) | DDF (SOT-23) | FK (LCCC)     | JG (CDIP) |      |
|                               |                                              | 8 PINS                                                                                           | 8 PINS      | 8 PINS   | 8 PINS  | 8 PINS     | 8PINS        | 20 PINS       | 8 PINS    |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance       | 124.7                                                                                            | 181.4       | 80.9     | 116.9   | 171.7      | 164.3        | 84.0          | 112.4     | °C/W |
| R <sub>θJC(top)</sub>         | Junction-to-case (top) thermal resistance    | 66.9                                                                                             | 69.4        | 70.4     | 62.5    | 68.8       | 98.1         | 56.9          | 63.6      | °C/W |
| R <sub>θJB</sub>              | Junction-to-board thermal resistance         | 67.9                                                                                             | 102.9       | 57.4     | 68.6    | 99.2       | 82.1         | 57.5          | 100.3     | °C/W |
| ψ <sub>JT</sub>               | Junction-to-top characterization parameter   | 19.2                                                                                             | 11.8        | 40       | 21.9    | 11.5       | 11.4         | 51.7          | 35.7      | °C/W |
| ψ <sub>JB</sub>               | Junction-to-board characterization parameter | 67.2                                                                                             | 101.2       | 56.9     | 67.6    | 97.9       | 81.7         | 57.1          | 93.3      | °C/W |
| R <sub>θJC(bot)</sub>         | Junction-to-case (bottom) thermal resistance | —                                                                                                | —           | —        | —       | —          | —            | 10.6          | 22.3      | °C/W |

(1) For more information about traditional and new thermal metrics, see [Semiconductor and IC Package Thermal Metrics](#).

(2) For a listing of which devices are available in what packages, see [Section 3](#).

## 5.5 Electrical Characteristics: LM358B and LM358BA

$V_S = (V+) - (V-) = 5\text{ V} - 36\text{ V} (\pm 2.5\text{ V} - \pm 18\text{ V})$ ,  $T_A = 25^\circ\text{C}$ ,  $V_{CM} = V_{OUT} = V_S / 2$ ,  $R_L = 10\text{k}$  connected to  $V_S / 2$  (unless otherwise noted)

| PARAMETER            |                                   | TEST CONDITIONS                                                                                                                                   |                                 | MIN                                                            | TYP                             | MAX        | UNIT             |       |
|----------------------|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------|------------|------------------|-------|
| OFFSET VOLTAGE       |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| V <sub>OS</sub>      | Input offset voltage              | LM358B                                                                                                                                            |                                 |                                                                | ±0.3                            | ±3.0       | mV               |       |
|                      |                                   |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C                                |                                 | ±4         | mV               |       |
|                      |                                   | LM358BA                                                                                                                                           |                                 |                                                                |                                 | ±2.0       | mV               |       |
|                      |                                   |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C                                |                                 | ±2.5       | mV               |       |
| dV <sub>OS</sub> /dT | Input offset voltage drift        |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C <sup>(1)</sup>                 |                                 | ±3.5       | 11               | μV/°C |
| PSRR                 | Power supply rejection ratio      |                                                                                                                                                   |                                 |                                                                |                                 | ±2         | 15               | μV/V  |
|                      | Channel separation, dc            | f = 1 kHz to 20 kHz                                                                                                                               |                                 |                                                                |                                 | ±1         |                  | μV/V  |
| INPUT VOLTAGE RANGE  |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| V <sub>CM</sub>      | Common-mode voltage range         | V <sub>S</sub> = 3 V to 36 V                                                                                                                      |                                 |                                                                | (V−)                            | (V+) − 1.5 | V                |       |
|                      |                                   | V <sub>S</sub> = 5 V to 36 V                                                                                                                      |                                 | T <sub>A</sub> = −40°C to +85°C                                | (V−)                            | (V+) − 2   | V                |       |
| CMRR                 | Common-mode rejection ratio       | (V−) ≤ V <sub>CM</sub> ≤ (V+) − 1.5 V                                                                                                             | V <sub>S</sub> = 3 V to 36 V    |                                                                | 20                              | 100        | μV/V             |       |
|                      |                                   | (V−) ≤ V <sub>CM</sub> ≤ (V+) − 2.0 V                                                                                                             | V <sub>S</sub> = 5 V to 36 V    | T <sub>A</sub> = −40°C to +85°C                                | 25                              | 316        |                  |       |
| INPUT BIAS CURRENT   |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| I <sub>B</sub>       | Input bias current                |                                                                                                                                                   |                                 |                                                                | −10                             | −35        | nA               |       |
|                      |                                   |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C <sup>(1)</sup>                 |                                 | −50        | nA               |       |
| I <sub>OS</sub>      | Input offset current              |                                                                                                                                                   |                                 |                                                                | 0.5                             | 4          | nA               |       |
|                      |                                   |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C <sup>(1)</sup>                 |                                 | 5          | nA               |       |
| dI <sub>OS</sub> /dT | Input offset current drift        |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C                                |                                 | 10         | pA/°C            |       |
| NOISE                |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| E <sub>n</sub>       | Input voltage noise               | f = 0.1 to 10 Hz                                                                                                                                  |                                 |                                                                | 3                               |            | μV <sub>PP</sub> |       |
| e <sub>n</sub>       | Input voltage noise density       | f = 1 kHz                                                                                                                                         |                                 |                                                                | 40                              |            | nV/√Hz           |       |
| INPUT IMPEDANCE      |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| Z <sub>ID</sub>      | Differential                      |                                                                                                                                                   |                                 |                                                                | 10    0.1                       |            | MΩ   pF          |       |
| Z <sub>IC</sub>      | Common-mode                       |                                                                                                                                                   |                                 |                                                                | 4    1.5                        |            | GΩ   pF          |       |
| OPEN-LOOP GAIN       |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| A <sub>OL</sub>      | Open-loop voltage gain            | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 10 kΩ, connected to (V−)                                                    |                                 |                                                                | 70                              | 140        | V/mV             |       |
|                      |                                   |                                                                                                                                                   |                                 | T <sub>A</sub> = −40°C to +85°C                                | 35                              |            | V/mV             |       |
| FREQUENCY RESPONSE   |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| GBW                  | Gain bandwidth product            |                                                                                                                                                   |                                 |                                                                | 1.2                             |            | MHz              |       |
| SR                   | Slew rate                         | G = + 1                                                                                                                                           |                                 |                                                                | 0.5                             |            | V/μs             |       |
| ∅ <sub>m</sub>       | Phase margin                      | G = + 1, R <sub>L</sub> = 10kΩ, C <sub>L</sub> = 20 pF                                                                                            |                                 |                                                                | 56                              |            | °                |       |
| t <sub>OR</sub>      | Overload recovery time            | V <sub>IN</sub> × gain > V <sub>S</sub>                                                                                                           |                                 |                                                                | 10                              |            | μs               |       |
| t <sub>s</sub>       | Settling time                     | To 0.1%, V <sub>S</sub> = 5 V, 2-V step , G = +1, C <sub>L</sub> = 100 pF                                                                         |                                 |                                                                | 4                               |            | μs               |       |
| THD+N                | Total harmonic distortion + noise | G = + 1, f = 1 kHz, V <sub>O</sub> = 3.53 V <sub>RMS</sub> , V <sub>S</sub> = 36 V, R <sub>L</sub> = 100k, I <sub>OUT</sub> ≤ ±50 μA, BW = 80 kHz |                                 |                                                                | 0.001                           |            | %                |       |
| OUTPUT               |                                   |                                                                                                                                                   |                                 |                                                                |                                 |            |                  |       |
| V <sub>O</sub>       | Voltage output swing from rail    | Positive rail (V+)                                                                                                                                |                                 | I <sub>OUT</sub> = 50 μA                                       | 1.35                            | 1.42       | V                |       |
|                      |                                   |                                                                                                                                                   |                                 | I <sub>OUT</sub> = 1 mA                                        | 1.4                             | 1.48       | V                |       |
|                      |                                   |                                                                                                                                                   |                                 | I <sub>OUT</sub> = 5 mA <sup>(1)</sup>                         | 1.5                             | 1.61       | V                |       |
|                      |                                   | Negative rail (V−)                                                                                                                                |                                 | I <sub>OUT</sub> = 50 μA                                       | 100                             | 150        | mV               |       |
|                      |                                   |                                                                                                                                                   |                                 | I <sub>OUT</sub> = 1 mA                                        | 0.75                            | 1          | V                |       |
|                      |                                   |                                                                                                                                                   |                                 | V <sub>S</sub> = 5 V, R <sub>L</sub> ≤ 10 kΩ connected to (V−) | T <sub>A</sub> = −40°C to +85°C | 5          | 20               | mV    |
| I <sub>O</sub>       | Output current                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = V−; V <sub>ID</sub> = 1 V                                                                                 | Source <sup>(1)</sup>           |                                                                | −20                             | −30        | mA               |       |
|                      |                                   |                                                                                                                                                   | T <sub>A</sub> = −40°C to +85°C | −10                                                            |                                 |            |                  |       |
|                      |                                   | V <sub>S</sub> = 15 V; V <sub>O</sub> = V+; V <sub>ID</sub> = −1 V                                                                                | Sink <sup>(1)</sup>             |                                                                | 10                              | 20         |                  |       |
|                      |                                   |                                                                                                                                                   | T <sub>A</sub> = −40°C to +85°C | 5                                                              |                                 |            |                  |       |
|                      |                                   | V <sub>ID</sub> = −1 V; V <sub>O</sub> = (V−) + 200 mV                                                                                            |                                 | 60                                                             | 100                             |            | μA               |       |
| I <sub>SC</sub>      | Short-circuit current             | V <sub>S</sub> = 20 V, (V+) = 10 V, (V−) = −10 V, V <sub>O</sub> = 0 V                                                                            |                                 |                                                                | ±40                             | ±60        | mA               |       |
| C <sub>LOAD</sub>    | Capacitive load drive             |                                                                                                                                                   |                                 |                                                                | 100                             |            | pF               |       |
| R <sub>O</sub>       | Open-loop output resistance       | f = 1 MHz, I <sub>O</sub> = 0 A                                                                                                                   |                                 |                                                                | 300                             |            | Ω                |       |

## 5.5 Electrical Characteristics: LM358B and LM358BA (continued)

$V_S = (V+) - (V-) = 5\text{ V} - 36\text{ V} (\pm 2.5\text{ V} - \pm 18\text{ V})$ ,  $T_A = 25^\circ\text{C}$ ,  $V_{CM} = V_{OUT} = V_S / 2$ ,  $R_L = 10\text{k}$  connected to  $V_S / 2$   
(unless otherwise noted)

| PARAMETER      |                                 | TEST CONDITIONS                             |                                 | MIN | TYP | MAX | UNIT |
|----------------|---------------------------------|---------------------------------------------|---------------------------------|-----|-----|-----|------|
| POWER SUPPLY   |                                 |                                             |                                 |     |     |     |      |
| I <sub>Q</sub> | Quiescent current per amplifier | V <sub>S</sub> = 5 V; I <sub>O</sub> = 0 A  | T <sub>A</sub> = −40°C to +85°C |     | 300 | 460 | μA   |
| I <sub>Q</sub> | Quiescent current per amplifier | V <sub>S</sub> = 36 V; I <sub>O</sub> = 0 A |                                 |     |     | 800 | μA   |

(1) Specified by characterization only.

## 5.6 Electrical Characteristics: LM2904B and LM2904BA

$V_S = (V+) - (V-) = 5\text{ V} - 36\text{ V} (\pm 2.5\text{ V} - \pm 18\text{ V})$ ,  $T_A = 25^\circ\text{C}$ ,  $V_{CM} = V_{OUT} = V_S/2$ ,  $R_L = 10\text{k}$  connected to  $V_S/2$   
(unless otherwise noted)

| PARAMETER            |                                   |                                                                                                                                                 | TEST CONDITIONS                                                |                                  | MIN        | TYP              | MAX  | UNIT |
|----------------------|-----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|----------------------------------|------------|------------------|------|------|
| OFFSET VOLTAGE       |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| V <sub>OS</sub>      | Input offset voltage              | LM2904B                                                                                                                                         |                                                                |                                  | ±0.3       | ±3.0             | mV   |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               |                                  | ±4         | mV               |      |      |
|                      |                                   | LM2904BA                                                                                                                                        |                                                                |                                  | ±2.0       | mV               |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               |                                  | ±3.0       | mV               |      |      |
| dV <sub>OS</sub> /dT | Input offset voltage drift        |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C <sup>(1)</sup>                | ±3.5                             | 12         | μV/°C            |      |      |
| PSRR                 | Power Supply Rejection Ratio      |                                                                                                                                                 |                                                                | ±2                               | 15         | μV/V             |      |      |
|                      | Channel separation, dc            | f = 1 kHz to 20 kHz                                                                                                                             |                                                                | ±1                               |            | μV/V             |      |      |
| INPUT VOLTAGE RANGE  |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| V <sub>CM</sub>      | Common-mode voltage range         | V <sub>S</sub> = 3 V to 36 V                                                                                                                    |                                                                | (V−)                             | (V+) − 1.5 | V                |      |      |
|                      |                                   | V <sub>S</sub> = 5 V to 36 V                                                                                                                    | T <sub>A</sub> = −40°C to +125°C                               | (V−)                             | (V+) − 2   | V                |      |      |
| CMRR                 | Common-mode rejection ratio       | (V−) ≤ V <sub>CM</sub> ≤ (V+) − 1.5 V                                                                                                           | V <sub>S</sub> = 3 V to 36 V                                   |                                  | 20         | 100              | μV/V |      |
|                      |                                   | (V−) ≤ V <sub>CM</sub> ≤ (V+) − 2.0 V                                                                                                           | V <sub>S</sub> = 5 V to 36 V                                   | T <sub>A</sub> = −40°C to +125°C | 25         | 316              |      |      |
| INPUT BIAS CURRENT   |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| I <sub>B</sub>       | Input bias current                |                                                                                                                                                 |                                                                | −10                              | −35        | nA               |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C <sup>(1)</sup>                |                                  | −50        | nA               |      |      |
| I <sub>OS</sub>      | Input offset current              |                                                                                                                                                 |                                                                | 0.5                              | 4          | nA               |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C <sup>(1)</sup>                |                                  | 5          | nA               |      |      |
| dI <sub>OS</sub> /dT | Input offset current drift        |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               | 10                               |            | pA/°C            |      |      |
| NOISE                |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| E <sub>n</sub>       | Input voltage noise               | f = 0.1 to 10 Hz                                                                                                                                |                                                                | 3                                |            | μV <sub>PP</sub> |      |      |
| e <sub>n</sub>       | Input voltage noise density       | f = 1 kHz                                                                                                                                       |                                                                | 40                               |            | nV/√Hz           |      |      |
| INPUT IMPEDANCE      |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| Z <sub>ID</sub>      | Differential                      |                                                                                                                                                 |                                                                | 10    0.1                        |            | MΩ   pF          |      |      |
| Z <sub>IC</sub>      | Common-mode                       |                                                                                                                                                 |                                                                | 4    1.5                         |            | GΩ   pF          |      |      |
| OPEN-LOOP GAIN       |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| A <sub>OL</sub>      | Open-loop voltage gain            | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 10 kΩ, connected to (V−)                                                  |                                                                | 70                               | 140        | V/mV             |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               | 35                               |            | V/mV             |      |      |
| FREQUENCY RESPONSE   |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| GBW                  | Gain bandwidth product            |                                                                                                                                                 |                                                                | 1.2                              |            | MHz              |      |      |
| SR                   | Slew rate                         | G = + 1                                                                                                                                         |                                                                | 0.5                              |            | V/μs             |      |      |
| Θ <sub>m</sub>       | Phase margin                      | G = + 1, R <sub>L</sub> = 10kΩ, C <sub>L</sub> = 20 pF                                                                                          |                                                                | 56                               |            | °                |      |      |
| t <sub>OR</sub>      | Overload recovery time            | V <sub>IN</sub> × gain > V <sub>S</sub>                                                                                                         |                                                                | 10                               |            | μs               |      |      |
| t <sub>s</sub>       | Settling time                     | To 0.1%, V <sub>S</sub> = 5 V, 2-V Step , G = +1, C <sub>L</sub> = 100 pF                                                                       |                                                                | 4                                |            | μs               |      |      |
| THD+N                | Total harmonic distortion + noise | G = + 1, f = 1 kHz, V <sub>O</sub> = 3.53 V <sub>RMS</sub> , V <sub>S</sub> = 36V, R <sub>L</sub> = 100k, I <sub>OUT</sub> ≤ ±50μA, BW = 80 kHz |                                                                | 0.001                            |            | %                |      |      |
| OUTPUT               |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |
| V <sub>O</sub>       | Voltage output swing from rail    | Positive Rail (V+)                                                                                                                              | I <sub>OUT</sub> = 50 μA                                       | 1.35                             | 1.42       | V                |      |      |
|                      |                                   |                                                                                                                                                 | I <sub>OUT</sub> = 1 mA                                        | 1.4                              | 1.48       | V                |      |      |
|                      |                                   |                                                                                                                                                 | I <sub>OUT</sub> = 5 mA <sup>(1)</sup>                         | 1.5                              | 1.61       | V                |      |      |
|                      |                                   | Negative Rail (V−)                                                                                                                              | I <sub>OUT</sub> = 50 μA                                       | 100                              | 150        | mV               |      |      |
|                      |                                   |                                                                                                                                                 | I <sub>OUT</sub> = 1 mA                                        | 0.75                             | 1          | V                |      |      |
|                      |                                   |                                                                                                                                                 | V <sub>S</sub> = 5 V, R <sub>L</sub> ≤ 10 kΩ connected to (V−) | T <sub>A</sub> = −40°C to +125°C | 5          | 20               | mV   |      |
| I <sub>O</sub>       | Output current                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = V−; V <sub>ID</sub> = 1 V                                                                               | Source <sup>(1)</sup>                                          | −20                              | −30        | mA               |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               | −10                              |            |                  |      |      |
|                      |                                   | V <sub>S</sub> = 15 V; V <sub>O</sub> = V+; V <sub>ID</sub> = −1 V                                                                              | Sink <sup>(1)</sup>                                            | 10                               | 20         |                  |      |      |
|                      |                                   |                                                                                                                                                 | T <sub>A</sub> = −40°C to +125°C                               | 5                                |            |                  |      |      |
|                      |                                   | V <sub>ID</sub> = −1 V; V <sub>O</sub> = (V−) + 200 mV                                                                                          |                                                                | 60                               | 100        | μA               |      |      |
| I <sub>SC</sub>      | Short-circuit current             | V <sub>S</sub> = 20 V, (V+) = 10 V, (V−) = −10 V, V <sub>O</sub> = 0 V                                                                          |                                                                | ±40                              | ±60        | mA               |      |      |
| C <sub>LOAD</sub>    | Capacitive load drive             |                                                                                                                                                 |                                                                | 100                              |            | pF               |      |      |
| R <sub>O</sub>       | Open-loop output resistance       | f = 1 MHz, I <sub>O</sub> = 0 A                                                                                                                 |                                                                | 300                              |            | Ω                |      |      |
| POWER SUPPLY         |                                   |                                                                                                                                                 |                                                                |                                  |            |                  |      |      |

$V_S = (V+) - (V-) = 5\text{ V} - 36\text{ V} (\pm 2.5\text{ V} - \pm 18\text{ V})$ ,  $T_A = 25^\circ\text{C}$ ,  $V_{CM} = V_{OUT} = V_S/2$ ,  $R_L = 10\text{k}$  connected to  $V_S/2$   
(unless otherwise noted)

| PARAMETER |                                 | TEST CONDITIONS                          |                                                   | MIN | TYP | MAX | UNIT          |
|-----------|---------------------------------|------------------------------------------|---------------------------------------------------|-----|-----|-----|---------------|
| $I_Q$     | Quiescent current per amplifier | $V_S = 5\text{ V}$ ; $I_O = 0\text{ A}$  | $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$ |     | 300 | 460 | $\mu\text{A}$ |
| $I_Q$     | Quiescent current per amplifier | $V_S = 36\text{ V}$ ; $I_O = 0\text{ A}$ |                                                   |     |     | 800 | $\mu\text{A}$ |

(1) Specified by characterization only

## 5.7 Electrical Characteristics: LM358, LM358A

For  $V_S = (V_+) - (V_-) = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)

| PARAMETER                         |                                                                           | TEST CONDITIONS <sup>(1)</sup>                                               |                                               | MIN                                          | TYP <sup>(2)</sup>           | MAX        | UNIT    |
|-----------------------------------|---------------------------------------------------------------------------|------------------------------------------------------------------------------|-----------------------------------------------|----------------------------------------------|------------------------------|------------|---------|
| OFFSET VOLTAGE                    |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| V <sub>OS</sub>                   | Input offset voltage                                                      | V <sub>S</sub> = 5 V to 30 V; V <sub>C M</sub> = 0 V; V <sub>O</sub> = 1.4 V | LM358                                         |                                              | 3                            | 7          | mV      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | 9          |         |
|                                   |                                                                           |                                                                              | LM358A                                        |                                              | 2                            | 3          |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | 5          |         |
| dV <sub>OS</sub> /dT              | Input offset voltage drift                                                |                                                                              | LM358                                         | T <sub>A</sub> = 0°C to 70°C                 | 7                            |            | μV/°C   |
|                                   |                                                                           |                                                                              | LM358A                                        | T <sub>A</sub> = 0°C to 70°C                 | 7                            | 20         |         |
| PSRR                              | Input offset voltage vs power supply (ΔV <sub>IO</sub> /ΔV <sub>S</sub> ) | V <sub>S</sub> = 5 V to 30 V                                                 |                                               | 65                                           | 100                          |            | dB      |
| V <sub>O1</sub> / V <sub>O2</sub> | Channel separation                                                        | f = 1 kHz to 20 kHz                                                          |                                               |                                              | 120                          |            | dB      |
| INPUT VOLTAGE RANGE               |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| V <sub>CM</sub>                   | Common-mode voltage range                                                 | V <sub>S</sub> = 5 V to 30 V                                                 | LM358                                         |                                              | (V–)                         | (V+) – 1.5 | V       |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM358A                                        |                                              |                              |            |         |
|                                   |                                                                           | V <sub>S</sub> = 5 V to 30 V                                                 | LM358                                         | T <sub>A</sub> = 0°C to 70°C                 | (V–)                         | (V+) – 2   |         |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM358A                                        |                                              |                              |            |         |
| CMRR                              | Common-mode rejection ratio                                               | V <sub>S</sub> = 5 V to 30 V; V <sub>CM</sub> = 0 V                          |                                               | 65                                           | 80                           |            | dB      |
| INPUT BIAS CURRENT                |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| I <sub>B</sub>                    | Input bias current                                                        | V <sub>O</sub> = 1.4 V                                                       | LM358                                         |                                              | –20                          | –250       | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | –500       |         |
|                                   |                                                                           |                                                                              | LM358A                                        |                                              | –15                          | –100       |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | –200       |         |
| I <sub>OS</sub>                   | Input offset current                                                      | V <sub>O</sub> = 1.4 V                                                       | LM358                                         |                                              | 2                            | 50         | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | 150        |         |
|                                   |                                                                           |                                                                              | LM358A                                        |                                              | 2                            | 30         |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 |                              | 75         |         |
| dI <sub>OS</sub> /dT              | Input offset current drift                                                |                                                                              |                                               |                                              | 10                           |            | pA/°C   |
|                                   |                                                                           |                                                                              | LM358A                                        | T <sub>A</sub> = 0°C to 70°C                 |                              | 300        |         |
| NOISE                             |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| e <sub>n</sub>                    | Input voltage noise density                                               | f = 1 kHz                                                                    |                                               |                                              | 40                           |            | nV/√ Hz |
| OPEN-LOOP GAIN                    |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| A <sub>OL</sub>                   | Open-loop voltage gain                                                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 2 kΩ   |                                               | 25                                           | 100                          |            | V/mV    |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 | 15                           |            |         |
| FREQUENCY RESPONSE                |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| GBW                               | Gain bandwidth product                                                    |                                                                              |                                               |                                              | 0.7                          |            | MHz     |
| SR                                | Slew rate                                                                 | G = +1                                                                       |                                               |                                              | 0.3                          |            | V/μs    |
| OUTPUT                            |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| V <sub>O</sub>                    | Voltage output swing from rail                                            | Positive rail                                                                | V <sub>S</sub> = 30 V; R <sub>L</sub> = 2 kΩ  | T <sub>A</sub> = 0°C to 70°C                 | 4                            |            | V       |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 30 V; R <sub>L</sub> ≥ 10 kΩ |                                              | 2                            | 3          |         |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 5 V; R <sub>L</sub> ≥ 2 kΩ   |                                              |                              | 1.5        |         |
|                                   |                                                                           |                                                                              | Negative rail                                 | V <sub>S</sub> = 5 V; R <sub>L</sub> ≤ 10 kΩ | T <sub>A</sub> = 0°C to 70°C | 5          | 20      |
| I <sub>O</sub>                    | Output current                                                            | Source                                                                       |                                               |                                              | –20                          | –30        | mA      |
|                                   |                                                                           |                                                                              | LM358A                                        |                                              | –60                          |            |         |
|                                   |                                                                           | Sink                                                                         |                                               | T <sub>A</sub> = 0°C to 70°C                 | –10                          |            |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = 0°C to 70°C                 | 10                           | 20         |         |
|                                   | V <sub>S</sub> = 15 V; V <sub>O</sub> = 15 V; V <sub>ID</sub> = –1 V      |                                                                              |                                               | 5                                            |                              |            |         |
|                                   | V <sub>ID</sub> = –1 V; V <sub>O</sub> = 200 mV                           |                                                                              |                                               | 12                                           | 30                           |            | μA      |
| I <sub>SC</sub>                   | Short-circuit current                                                     | V <sub>S</sub> = 10 V; V <sub>O</sub> = V <sub>S</sub> / 2                   |                                               |                                              | ±40                          | ±60        | mA      |
| POWER SUPPLY                      |                                                                           |                                                                              |                                               |                                              |                              |            |         |
| I <sub>Q</sub>                    | Quiescent current per amplifier                                           | V <sub>O</sub> = 2.5 V; I <sub>O</sub> = 0 A                                 |                                               | T <sub>A</sub> = 0°C to 70°C                 | 350                          | 600        | μA      |
|                                   |                                                                           | V <sub>S</sub> = 30 V; V <sub>O</sub> = 15 V; I <sub>O</sub> = 0 A           |                                               |                                              | 500                          | 1000       |         |

- (1) All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. Maximum  $V_S$  for testing purposes is 30 V for LM358 and LM358A.
- (2) All typical values are  $T_A = 25^\circ\text{C}$ .

## 5.8 Electrical Characteristics: LM2904, LM2904V

For  $V_S = (V+) - (V-) = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)

| PARAMETER                                                            |                                                                           | TEST CONDITIONS <sup>(1)</sup>                                                  |                                 | MIN                                                                | TYP <sup>(2)</sup>              | MAX   | UNIT    |     |
|----------------------------------------------------------------------|---------------------------------------------------------------------------|---------------------------------------------------------------------------------|---------------------------------|--------------------------------------------------------------------|---------------------------------|-------|---------|-----|
| OFFSET VOLTAGE                                                       |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| V <sub>OS</sub>                                                      | Input offset voltage                                                      | V <sub>S</sub> = 5 V to maximum; V <sub>C M</sub> = 0 V; V <sub>O</sub> = 1.4 V | Non-A suffix devices            |                                                                    | 3                               | 7     | mV      |     |
|                                                                      |                                                                           |                                                                                 | A-suffix devices                | T <sub>A</sub> = −40°C to 125°C                                    |                                 | 10    |         |     |
|                                                                      |                                                                           |                                                                                 |                                 |                                                                    | 1                               | 2     |         |     |
|                                                                      |                                                                           |                                                                                 |                                 | T <sub>A</sub> = −40°C to 125°C                                    |                                 | 4     |         |     |
| dV <sub>OS</sub> /dT                                                 | Input offset voltage drift                                                |                                                                                 | T <sub>A</sub> = −40°C to 125°C | 7                                                                  |                                 | μV/°C |         |     |
| PSRR                                                                 | Input offset voltage vs power supply (ΔV <sub>IO</sub> /ΔV <sub>S</sub> ) | V <sub>S</sub> = 5 V to 30 V                                                    |                                 | 65                                                                 | 100                             |       | dB      |     |
| V <sub>O1</sub> / V <sub>O2</sub>                                    | Channel separation                                                        | f = 1 kHz to 20 kHz                                                             |                                 |                                                                    | 120                             |       | dB      |     |
| INPUT VOLTAGE RANGE                                                  |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| V <sub>CM</sub>                                                      | Common-mode voltage range                                                 | V <sub>S</sub> = 5 V to maximum                                                 |                                 | (V−)                                                               | (V+) − 1.5                      |       | V       |     |
|                                                                      |                                                                           |                                                                                 | T <sub>A</sub> = −40°C to 125°C | (V−)                                                               | (V+) − 2                        |       |         |     |
| CMRR                                                                 | Common-mode rejection ratio                                               | V <sub>S</sub> = 5 V to maximum; V <sub>CM</sub> = 0 V                          |                                 | 65                                                                 | 80                              |       | dB      |     |
| INPUT BIAS CURRENT                                                   |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| I <sub>B</sub>                                                       | Input bias current                                                        | V <sub>O</sub> = 1.4 V                                                          |                                 | −20                                                                | −250                            |       | nA      |     |
|                                                                      |                                                                           |                                                                                 | T <sub>A</sub> = −40°C to 125°C |                                                                    | −500                            |       |         |     |
| I <sub>OS</sub>                                                      | Input offset current                                                      | V <sub>O</sub> = 1.4 V                                                          | Non-V suffix device             | 2                                                                  | 50                              |       | nA      |     |
|                                                                      |                                                                           |                                                                                 | V-suffix device                 | T <sub>A</sub> = −40°C to 125°C                                    |                                 | 300   |         |     |
|                                                                      |                                                                           |                                                                                 |                                 |                                                                    | 2                               | 50    |         |     |
|                                                                      |                                                                           |                                                                                 |                                 | T <sub>A</sub> = −40°C to 125°C                                    |                                 | 150   |         |     |
| dI <sub>OS</sub> /dT                                                 | Input offset current drift                                                |                                                                                 | T <sub>A</sub> = −40°C to 125°C | 10                                                                 |                                 | pA/°C |         |     |
| NOISE                                                                |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| e <sub>n</sub>                                                       | Input voltage noise density                                               | f = 1 kHz                                                                       |                                 | 40                                                                 |                                 |       | nV/√ Hz |     |
| OPEN-LOOP GAIN                                                       |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| A <sub>OL</sub>                                                      | Open-loop voltage gain                                                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 2 kΩ      |                                 | 25                                                                 | 100                             |       | V/mV    |     |
|                                                                      |                                                                           |                                                                                 | T <sub>A</sub> = −40°C to 125°C | 15                                                                 |                                 |       |         |     |
| FREQUENCY RESPONSE                                                   |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| GBW                                                                  | Gain bandwidth product                                                    |                                                                                 |                                 | 0.7                                                                |                                 |       | MHz     |     |
| SR                                                                   | Slew rate                                                                 | G = +1                                                                          |                                 | 0.3                                                                |                                 |       | V/μs    |     |
| OUTPUT                                                               |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| V <sub>O</sub>                                                       | Voltage output swing from rail                                            | Positive rail                                                                   | R <sub>L</sub> ≥ 10 kΩ          |                                                                    | V <sub>S</sub> − 1.5            |       | V       |     |
|                                                                      |                                                                           |                                                                                 | Non-V suffix device             | V <sub>S</sub> = maximum; R <sub>L</sub> = 2 kΩ                    | T <sub>A</sub> = −40°C to 125°C |       |         | 4   |
|                                                                      |                                                                           |                                                                                 |                                 | V <sub>S</sub> = maximum; R <sub>L</sub> ≥ 10 kΩ                   |                                 | 2     |         | 3   |
|                                                                      |                                                                           |                                                                                 | V-suffix device                 | V <sub>S</sub> = maximum; R <sub>L</sub> = 2 kΩ                    |                                 |       |         | 6   |
|                                                                      |                                                                           |                                                                                 |                                 | V <sub>S</sub> = maximum; R <sub>L</sub> ≥ 10 kΩ                   |                                 | 4     |         | 5   |
|                                                                      |                                                                           | Negative rail                                                                   |                                 | V <sub>S</sub> = 5 V; R <sub>L</sub> ≤ 10 kΩ                       | T <sub>A</sub> = −40°C to 125°C | 5     | 20      | mV  |
|                                                                      |                                                                           | I <sub>O</sub>                                                                  | Output current                  | V <sub>S</sub> = 15 V; V <sub>O</sub> = 0 V; V <sub>ID</sub> = 1 V | Source                          |       | −20     | −30 |
| T <sub>A</sub> = −40°C to 125°C                                      | −10                                                                       |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| V <sub>S</sub> = 15 V; V <sub>O</sub> = 15 V; V <sub>ID</sub> = −1 V | Sink                                                                      |                                                                                 |                                 |                                                                    | 10                              | 20    |         |     |
|                                                                      |                                                                           |                                                                                 |                                 | T <sub>A</sub> = −40°C to 125°C                                    | 5                               |       |         |     |
| V <sub>ID</sub> = -1 V; V <sub>O</sub> = 200 mV                      | Non-V suffix device                                                       |                                                                                 |                                 | 30                                                                 |                                 | μA    |         |     |
|                                                                      | V-suffix device                                                           |                                                                                 |                                 | 12                                                                 | 40                              |       |         |     |
| I <sub>SC</sub>                                                      | Short-circuit current                                                     | V <sub>S</sub> = 10 V; V <sub>O</sub> = V <sub>S</sub> / 2                      |                                 |                                                                    | ±40                             | ±60   | mA      |     |
| POWER SUPPLY                                                         |                                                                           |                                                                                 |                                 |                                                                    |                                 |       |         |     |
| I <sub>Q</sub>                                                       | Quiescent current per amplifier                                           | V <sub>O</sub> = 2.5 V; I <sub>O</sub> = 0 A                                    | T <sub>A</sub> = −40°C to 125°C |                                                                    | 350                             | 600   | μA      |     |
|                                                                      |                                                                           | V <sub>S</sub> = maximum; V <sub>O</sub> = maximum / 2; I <sub>O</sub> = 0 A    |                                 |                                                                    | 500                             | 1000  |         |     |

- (1) All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. Maximum  $V_S$  for testing purposes is 26 V for LM2904 and 32 V for LM2904V.
- (2) All typical values are  $T_A = 25^\circ\text{C}$ .

## 5.9 Electrical Characteristics: LM158, LM158A

For  $V_S = (V_+) - (V_-) = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)

| PARAMETER                         |                                                                           | TEST CONDITIONS <sup>(1)</sup>                                               |                                               |                                 | MIN                             | TYP <sup>(2)</sup> | MAX               | UNIT    |
|-----------------------------------|---------------------------------------------------------------------------|------------------------------------------------------------------------------|-----------------------------------------------|---------------------------------|---------------------------------|--------------------|-------------------|---------|
| OFFSET VOLTAGE                    |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| V <sub>OS</sub>                   | Input offset voltage                                                      | V <sub>S</sub> = 5 V to 30 V; V <sub>C M</sub> = 0 V; V <sub>O</sub> = 1.4 V | LM158                                         |                                 | 3                               |                    | 5                 | mV      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | 7                               |                    |                   |         |
|                                   |                                                                           |                                                                              | LM158A                                        |                                 | 2                               |                    | 4                 |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | 7                               |                    |                   |         |
| dV <sub>OS</sub> /dT              | Input offset voltage drift                                                |                                                                              | LM158                                         | T <sub>A</sub> = –55°C to 125°C | 7                               |                    | 15 <sup>(3)</sup> | μV/°C   |
|                                   |                                                                           |                                                                              | LM158A                                        | T <sub>A</sub> = –55°C to 125°C | 7                               |                    |                   |         |
| PSRR                              | Input offset voltage vs power supply (ΔV <sub>IO</sub> /ΔV <sub>S</sub> ) | V <sub>S</sub> = 5 V to 30 V                                                 |                                               |                                 | 65                              | 100                |                   | dB      |
| V <sub>O1</sub> / V <sub>O2</sub> | Channel separation                                                        | f = 1 kHz to 20 kHz                                                          |                                               |                                 |                                 | 120                |                   | dB      |
| INPUT VOLTAGE RANGE               |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| V <sub>CM</sub>                   | Common-mode voltage range                                                 | V <sub>S</sub> = 5 V to 30 V                                                 | LM158                                         |                                 | (V–)                            | (V+) – 1.5         |                   | V       |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM158A                                        |                                 |                                 |                    |                   |         |
|                                   |                                                                           | V <sub>S</sub> = 5 V to 30 V                                                 | LM158                                         | T <sub>A</sub> = –55°C to 125°C | (V–)                            | (V+) – 2           |                   |         |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM158A                                        |                                 |                                 |                    |                   |         |
| CMRR                              | Common-mode rejection ratio                                               | V <sub>S</sub> = 5 V to 30 V; V <sub>CM</sub> = 0 V                          |                                               |                                 | 70                              | 80                 |                   | dB      |
| INPUT BIAS CURRENT                |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| I <sub>B</sub>                    | Input bias current                                                        | V <sub>O</sub> = 1.4 V                                                       | LM158                                         |                                 | –20                             |                    | –150              | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | –300                            |                    |                   |         |
|                                   |                                                                           |                                                                              | LM158A                                        |                                 | –15                             |                    | –50               |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | –100                            |                    |                   |         |
| I <sub>OS</sub>                   | Input offset current                                                      | V <sub>O</sub> = 1.4 V                                                       | LM158                                         |                                 | 2                               |                    | 30                | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | 100                             |                    |                   |         |
|                                   |                                                                           |                                                                              | LM158A                                        |                                 | 2                               |                    | 10                |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –55°C to 125°C | 30                              |                    |                   |         |
| dI <sub>OS</sub> /dT              | Input offset current drift                                                |                                                                              |                                               |                                 | 10                              |                    | pA/°C             |         |
| LM158A                            | T <sub>A</sub> = –55°C to 125°C                                           | 200                                                                          |                                               |                                 |                                 |                    |                   |         |
| NOISE                             |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| e <sub>n</sub>                    | Input voltage noise density                                               | f = 1 kHz                                                                    |                                               |                                 |                                 | 40                 |                   | nV/√ Hz |
| OPEN-LOOP GAIN                    |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| A <sub>OL</sub>                   | Open-loop voltage gain                                                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 2 kΩ   |                                               |                                 | 50                              | 100                | V/mV              |         |
|                                   |                                                                           |                                                                              | T <sub>A</sub> = –55°C to 125°C               | 25                              |                                 |                    |                   |         |
| FREQUENCY RESPONSE                |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| GBW                               | Gain bandwidth product                                                    |                                                                              |                                               |                                 |                                 | 0.7                |                   | MHz     |
| SR                                | Slew rate                                                                 | G = +1                                                                       |                                               |                                 |                                 | 0.3                |                   | V/μs    |
| OUTPUT                            |                                                                           |                                                                              |                                               |                                 |                                 |                    |                   |         |
| V <sub>O</sub>                    | Voltage output swing from rail                                            | Positive rail                                                                | V <sub>S</sub> = 30 V; R <sub>L</sub> = 2 kΩ  | T <sub>A</sub> = –55°C to 125°C | 4                               |                    | V                 |         |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 30 V; R <sub>L</sub> ≥ 10 kΩ |                                 | 2                               |                    |                   |         |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 5 V; R <sub>L</sub> ≥ 2 kΩ   |                                 | 1.5                             |                    |                   |         |
|                                   |                                                                           | Negative rail                                                                | V <sub>S</sub> = 5 V; R <sub>L</sub> ≤ 10 kΩ  | T <sub>A</sub> = –55°C to 125°C | 5                               | 20                 | mV                |         |
| I <sub>O</sub>                    | Output current                                                            | V <sub>S</sub> = 15 V; V <sub>O</sub> = 0 V; V <sub>ID</sub> = 1 V           | Source                                        | LM158A                          | –60                             |                    | mA                |         |
|                                   |                                                                           |                                                                              |                                               |                                 | T <sub>A</sub> = –55°C to 125°C | –10                |                   |         |
|                                   |                                                                           |                                                                              | Sink                                          |                                 | 10                              |                    |                   | 20      |
|                                   |                                                                           | T <sub>A</sub> = –55°C to 125°C                                              |                                               | 5                               |                                 |                    |                   |         |
|                                   |                                                                           | V <sub>ID</sub> = –1 V; V <sub>O</sub> = 200 mV                              |                                               |                                 |                                 | 12                 |                   | 30      |
| I <sub>SC</sub>                   | Short-circuit current                                                     | V <sub>S</sub> = 10 V; V <sub>O</sub> = V <sub>S</sub> / 2                   |                                               |                                 |                                 | ±40                | ±60               | mA      |

## 5.9 Electrical Characteristics: LM158, LM158A (continued)

For  $V_S = (V_+) - (V_-) = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)

| PARAMETER      |                                 | TEST CONDITIONS <sup>(1)</sup>                                     |                                 | MIN | TYP <sup>(2)</sup> | MAX  | UNIT |
|----------------|---------------------------------|--------------------------------------------------------------------|---------------------------------|-----|--------------------|------|------|
| POWER SUPPLY   |                                 |                                                                    |                                 |     |                    |      |      |
| I <sub>Q</sub> | Quiescent current per amplifier | V <sub>O</sub> = 2.5 V; I <sub>O</sub> = 0 A                       | T <sub>A</sub> = −55°C to 125°C |     | 350                | 600  | μA   |
|                |                                 | V <sub>S</sub> = 30 V; V <sub>O</sub> = 15 V; I <sub>O</sub> = 0 A |                                 |     | 500                | 1000 |      |

- (1) All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. Maximum  $V_S$  for testing purposes is 30 V for LM158 and LM158A.
- (2) All typical values are  $T_A = 25^\circ\text{C}$ .
- (3) On products compliant to MIL-PRF-38535, this parameter is not production tested.

## 5.10 Electrical Characteristics: LM258, LM258A

For  $V_S = (V_+) - (V_-) = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)

| PARAMETER                         |                                                                           | TEST CONDITIONS <sup>(1)</sup>                                               |                                               |                                | MIN  | TYP <sup>(2)</sup> | MAX  | UNIT    |
|-----------------------------------|---------------------------------------------------------------------------|------------------------------------------------------------------------------|-----------------------------------------------|--------------------------------|------|--------------------|------|---------|
| OFFSET VOLTAGE                    |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| V <sub>OS</sub>                   | Input offset voltage                                                      | V <sub>S</sub> = 5 V to 30 V; V <sub>C M</sub> = 0 V; V <sub>O</sub> = 1.4 V | LM258                                         |                                |      | 3                  | 5    | mV      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | 7                  |      |         |
|                                   |                                                                           |                                                                              | LM258A                                        |                                |      | 2                  | 3    |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | 4                  |      |         |
| dV <sub>OS</sub> /dT              | Input offset voltage drift                                                |                                                                              | LM258                                         | T <sub>A</sub> = –25°C to 85°C |      | 7                  |      | µV/°C   |
|                                   |                                                                           |                                                                              | LM258A                                        |                                |      | 7                  | 15   |         |
| PSRR                              | Input offset voltage vs power supply (ΔV <sub>IO</sub> /ΔV <sub>S</sub> ) | V <sub>S</sub> = 5 V to 30 V                                                 |                                               |                                | 65   | 100                |      | dB      |
| V <sub>O1</sub> / V <sub>O2</sub> | Channel separation                                                        | f = 1 kHz to 20 kHz                                                          |                                               |                                |      | 120                |      | dB      |
| INPUT VOLTAGE RANGE               |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| V <sub>CM</sub>                   | Common-mode voltage range                                                 | V <sub>S</sub> = 5 V to 30 V                                                 | LM258                                         |                                | (V–) | (V+) – 1.5         |      | V       |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM258A                                        |                                |      |                    |      |         |
|                                   |                                                                           | V <sub>S</sub> = 5 V to 30 V                                                 | LM258                                         | T <sub>A</sub> = –25°C to 85°C | (V–) | (V+) – 2           |      |         |
|                                   |                                                                           | V <sub>S</sub> = 30 V                                                        | LM258A                                        |                                |      |                    |      |         |
| CMRR                              | Common-mode rejection ratio                                               | V <sub>S</sub> = 5 V to 30 V; V <sub>CM</sub> = 0 V                          |                                               |                                | 70   | 80                 |      | dB      |
| INPUT BIAS CURRENT                |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| I <sub>B</sub>                    | Input bias current                                                        | V <sub>O</sub> = 1.4 V                                                       | LM258                                         |                                |      | –20                | –150 | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | –300               |      |         |
|                                   |                                                                           |                                                                              | LM258A                                        |                                |      | –15                | –80  |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | –100               |      |         |
| I <sub>OS</sub>                   | Input offset current                                                      | V <sub>O</sub> = 1.4 V                                                       | LM258                                         |                                |      | 2                  | 30   | nA      |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | 100                |      |         |
|                                   |                                                                           |                                                                              | LM258A                                        |                                |      | 2                  | 15   |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C |      | 30                 |      |         |
| dI <sub>OS</sub> /dT              | Input offset current drift                                                |                                                                              |                                               |                                |      | 10                 |      | pA/°C   |
|                                   |                                                                           |                                                                              | LM258A                                        | T <sub>A</sub> = –25°C to 85°C |      | 200                |      |         |
| NOISE                             |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| e <sub>n</sub>                    | Input voltage noise density                                               | f = 1 kHz                                                                    |                                               |                                |      | 40                 |      | nV/√ Hz |
| OPEN-LOOP GAIN                    |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| A <sub>OL</sub>                   | Open-loop voltage gain                                                    | V <sub>S</sub> = 15 V; V <sub>O</sub> = 1 V to 11 V; R <sub>L</sub> ≥ 2 kΩ   |                                               |                                | 50   | 100                |      | V/mV    |
|                                   |                                                                           |                                                                              | T <sub>A</sub> = –25°C to 85°C                |                                | 25   |                    |      |         |
| FREQUENCY RESPONSE                |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| GBW                               | Gain bandwidth product                                                    |                                                                              |                                               |                                |      | 0.7                |      | MHz     |
| SR                                | Slew rate                                                                 | G = +1                                                                       |                                               |                                |      | 0.3                |      | V/µs    |
| OUTPUT                            |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| V <sub>O</sub>                    | Voltage output swing from rail                                            | Positive rail                                                                | V <sub>S</sub> = 30 V; R <sub>L</sub> = 2 kΩ  | T <sub>A</sub> = –25°C to 85°C |      | 4                  |      | V       |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 30 V; R <sub>L</sub> ≥ 10 kΩ |                                | 2    | 3                  |      |         |
|                                   |                                                                           |                                                                              | V <sub>S</sub> = 5 V; R <sub>L</sub> ≥ 2 kΩ   |                                |      | 1.5                |      |         |
|                                   |                                                                           | Negative rail                                                                | V <sub>S</sub> = 5 V; R <sub>L</sub> ≤ 10 kΩ  | T <sub>A</sub> = –25°C to 85°C | 5    | 20                 | mV   |         |
| I <sub>O</sub>                    | Output current                                                            | V <sub>S</sub> = 15 V; V <sub>O</sub> = 0 V; V <sub>ID</sub> = 1 V           | Source                                        |                                | –20  | –30                |      | mA      |
|                                   |                                                                           |                                                                              |                                               | LM258A                         |      | –60                |      |         |
|                                   |                                                                           |                                                                              |                                               | T <sub>A</sub> = –25°C to 85°C | –10  |                    |      |         |
|                                   |                                                                           | Sink                                                                         |                                               | 10                             | 20   |                    |      |         |
|                                   |                                                                           |                                                                              | T <sub>A</sub> = –25°C to 85°C                | 5                              |      |                    |      |         |
|                                   | V <sub>ID</sub> = –1 V; V <sub>O</sub> = 200 mV                           |                                                                              |                                               | 12                             | 30   | µA                 |      |         |
| I <sub>SC</sub>                   | Short-circuit current                                                     | V <sub>S</sub> = 10 V; V <sub>O</sub> = V <sub>S</sub> / 2                   |                                               |                                |      | ±40                | ±60  | mA      |
| POWER SUPPLY                      |                                                                           |                                                                              |                                               |                                |      |                    |      |         |
| I <sub>Q</sub>                    | Quiescent current per amplifier                                           | V <sub>O</sub> = 2.5 V; I <sub>O</sub> = 0 A                                 |                                               | T <sub>A</sub> = –25°C to 85°C | 350  | 600                |      | µA      |
|                                   |                                                                           | V <sub>S</sub> = 30 V; V <sub>O</sub> = 15 V; I <sub>O</sub> = 0 A           |                                               |                                | 500  | 1000               |      |         |

- (1) All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. Maximum  $V_S$  for testing purposes is 30 V for LM258 and LM258A.
- (2) All typical values are  $T_A = 25^\circ\text{C}$ .

## 5.11 Typical Characteristics: LM358B and LM2904B

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V } (\pm 18\text{ V})$ ,  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).




Figure 5-1. Offset Voltage Production Distribution




Figure 5-2. Offset Voltage Drift Distribution




Figure 5-3. Offset Voltage vs Temperature




Figure 5-4. Offset Voltage vs Common-Mode Voltage




Figure 5-5. Open-Loop Gain and Phase vs Frequency




Figure 5-6. Closed-Loop Gain vs Frequency

## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).




Figure 5-7. Input Bias Current vs Common-Mode Voltage




Figure 5-8. Input Offset Current vs Common-Mode Voltage




Figure 5-9. Input Bias Current vs Temperature




Figure 5-10. Input Offset Current vs Temperature




Figure 5-11. Output Voltage Swing vs Output Current (Sourcing)




Figure 5-12. Output Voltage Swing vs Output Current (Sinking)

## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).




Figure 5-13. CMRR and PSRR vs Frequency




Figure 5-14. Common-Mode Rejection Ratio vs Temperature (dB)




Figure 5-15. Power Supply Rejection Ratio vs Temperature (dB)




Figure 5-16. 0.1-Hz to 10-Hz Noise






Figure 5-17. Input Voltage Noise Spectral Density vs Frequency



$G = 1$ ,  $f = 1\text{ kHz}$ ,  $BW = 80\text{ kHz}$ ,  
 $V_{OUT} = 10\text{ V}_{PP}$ ,  $R_L$  connected to  $V_-$   
Figure 5-18. THD+N Ratio vs Frequency,  $G = 1$


## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).




$G = -1$ ,  $f = 1\text{ kHz}$ ,  $BW = 80\text{ kHz}$ ,  
 $V_{OUT} = 10\text{ V}_{PP}$ ,  $R_L$  connected to  $V_-$   
See Figure 6-3

Figure 5-19. THD+N Ratio vs Frequency,  $G = -1$



$G = 1$ ,  $f = 1\text{ kHz}$ ,  $BW = 80\text{ kHz}$ ,  
 $R_L$  connected to  $V_-$

Figure 5-20. THD+N vs Output Amplitude,  $G = 1$



$G = -1$ ,  $f = 1\text{ kHz}$ ,  $BW = 80\text{ kHz}$ ,  
 $R_L$  connected to  $V_-$   
See Figure 6-3

Figure 5-21. THD+N vs Output Amplitude,  $G = -1$




Figure 5-22. Quiescent Current vs Supply Voltage




Figure 5-23. Quiescent Current vs Temperature





Figure 5-24. Open-Loop Output Impedance vs Frequency


## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).



$G = 1$ , 100-mV output step,  $R_L = \text{open}$

Figure 5-25. Small-Signal Overshoot vs Capacitive Load



$G = -1$ , 100-mV output step,  $R_L = \text{open}$

Figure 5-26. Small-Signal Overshoot vs Capacitive Load




Figure 5-27. Phase Margin vs Capacitive Load




Figure 5-28. Overload Recovery




Figure 5-29. Small-Signal Step Response,  $G = 1$




Figure 5-30. Small-Signal Step Response,  $G = -1$

## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).




Figure 5-31. Large-Signal Step Response (Rising)




Figure 5-32. Large-Signal Step Response (Falling)




Figure 5-33. Large-Signal Step Response




Figure 5-34. Slew Rate vs Temperature




Figure 5-35. Short-Circuit Current vs Temperature






Figure 5-36. Maximum Output Voltage vs Frequency

## 5.11 Typical Characteristics: LM358B and LM2904B (continued)

This typical characteristics section is applicable for LM358B and LM2904B. Typical characteristics data in this section was taken with  $T_A = 25^\circ\text{C}$ ,  $V_S = 36\text{ V}$  ( $\pm 18\text{ V}$ ),  $V_{CM} = V_S / 2$ ,  $R_{LOAD} = 10\text{ k}\Omega$  connected to  $V_S / 2$  (unless otherwise noted).



**Figure 5-37. Channel Separation vs Frequency**



**Figure 5-38. EMIRR (Electromagnetic Interference Rejection Ratio) vs Frequency**

## 5.12 Typical Characteristics: LM158, LM158A, LM258, LM258A, LM358, LM358A, LM2904, and LM2904V

Typical characteristics section is applicable for LM158, LM158A, LM258, LM258A, LM358, LM358A, LM2904, and LM2904V.




Figure 5-39. Input Current vs Temperature




Figure 5-40. Supply Current vs Supply Voltage




Figure 5-41. Voltage Gain vs Supply Voltage




Figure 5-42. Common-Mode Rejection Ratio vs Frequency




Figure 5-43. Voltage Follower Large Signal Response (50 pF)




Figure 5-44. Voltage Follower Small Signal Response (50 pF)

## 5.12 Typical Characteristics: LM158, LM158A, LM258, LM258A, LM358, LM358A, LM2904, and LM2904V (continued)

Typical characteristics section is applicable for LM158, LM158A, LM258, LM258A, LM358, LM358A, LM2904, and LM2904V.




Figure 5-45. Maximum Output Swing vs Frequency ( $V_{CC} = 15\text{ V}$ )




Figure 5-46. Output Sourcing Characteristics




Figure 5-47. Output Sinking Characteristics




Figure 5-48. Source Current Limiting

## 6 Parameter Measurement Information




Figure 6-1. Unity-Gain Amplifier




Figure 6-2. Noise-Test Circuit




Figure 6-3. Test Circuit,  $G = -1$ , for THD+N and Small-Signal Step Response


## 7 Detailed Description

### 7.1 Overview

These devices consist of two independent, high-gain frequency-compensated operational amplifiers designed to operate from a single supply over a wide range of voltages. Operation from split supplies also is possible if the difference between the two supplies is within the supply voltage range specified in [Recommended Operating Conditions](#) and  $V_S$  is at least 1.5 V more positive than the input common-mode voltage. The low supply-current drain is independent of the magnitude of the supply voltage.

Applications include transducer amplifiers, dc amplification blocks, and all the conventional operational amplifier circuits that now can be implemented more easily in single-supply-voltage systems. For example, these devices can be operated directly from the standard 5-V supply used in digital systems and easily can provide the required interface electronics without additional  $\pm 5$ -V supplies.

### 7.2 Functional Block Diagram: LM358B, LM358BA, LM2904B, LM2904BA



## 7.3 Feature Description

### 7.3.1 Unity-Gain Bandwidth

The unity-gain bandwidth is the frequency up to which an amplifier with a unity gain may be operated without greatly distorting the signal. These devices have a 1.2-MHz unity-gain bandwidth (B Version).

### 7.3.2 Slew Rate

The slew rate is the rate at which an operational amplifier can change its output when there is a change on the input. These devices have a 0.5-V/ $\mu$ s slew rate (B Version).

### 7.3.3 Input Common-Mode Range

The valid common-mode range is from device ground to  $V_S - 1.5$  V ( $V_S - 2$  V across temperature). Inputs may exceed  $V_S$  up to the maximum  $V_S$  without device damage. At least one input must be in the valid input common-mode range for the output to be the correct phase. If both inputs exceed the valid range, then the output phase is undefined. If either input more than 0.3 V below  $V_-$  then input current should be limited to 1 mA and the output phase is undefined.

## 7.4 Device Functional Modes

These devices are powered on when the supply is connected. This device can be operated as a single-supply operational amplifier or dual-supply amplifier, depending on the application.

## 8 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 8.1 Application Information

The LMx58 and LM2904 operational amplifiers are useful in a wide range of signal conditioning applications. Inputs can be powered before  $V_S$  for flexibility in multiple supply circuits.

### 8.2 Typical Application

A typical application for an operational amplifier is an inverting amplifier. This amplifier takes a positive voltage on the input, and makes it a negative voltage of the same magnitude. In the same manner, it also makes negative voltages positive.




Figure 8-1. Application Schematic

#### 8.2.1 Design Requirements

The supply voltage must be chosen such that it is larger than the input voltage range and output range. For instance, this application scales a signal of  $\pm 0.5$  V to  $\pm 1.8$  V. Setting the supply at  $\pm 12$  V is sufficient to accommodate this application.

#### 8.2.2 Detailed Design Procedure

Determine the gain required by the inverting amplifier using [Equation 1](#) and [Equation 2](#):

$$A_V = \frac{V_{OUT}}{V_{IN}} \quad (1)$$

$$A_V = \frac{1.8}{-0.5} = -3.6 \quad (2)$$

Once the desired gain is determined, choose a value for  $R_I$  or  $R_F$ . [Subscripts should be fixed in the accompanying figures and equations also.] Choosing a value in the kilohm range is desirable because the amplifier circuit uses currents in the milliamperage range. This ensures the part does not draw too much current. This example uses 10 k $\Omega$  for  $R_I$  which means 36 k $\Omega$  is used for  $R_F$ . This was determined by [Equation 3](#).

$$A_V = -\frac{R_F}{R_I} \quad (3)$$

### 8.2.3 Application Curve




Figure 8-2. Input and Output Voltages of the Inverting Amplifier

## 8.3 Power Supply Recommendations

### CAUTION

Supply voltages larger than specified in the recommended operating region can permanently damage the device (see [Absolute Maximum Ratings](#)).

Place 0.1- $\mu$ F bypass capacitors close to the power-supply pins to reduce errors coupling in from noisy or high-impedance power supplies. For more detailed information on bypass capacitor placement, see [Section 8.4](#).


## 8.4 Layout

### 8.4.1 Layout Guidelines


For best operational performance of the device, use good PCB layout practices, including:

- Noise can propagate into analog circuitry through the power pins of the circuit as a whole, as well as the operational amplifier. Bypass capacitors are used to reduce the coupled noise by providing low-impedance power sources local to the analog circuitry.
  - Connect low-ESR, 0.1- $\mu$ F ceramic bypass capacitors between each supply pin and ground, placed as close to the device as possible. A single bypass capacitor from V+ to ground is applicable for single-supply applications.
- Separate grounding for analog and digital portions of circuitry is one of the simplest and most-effective methods of noise suppression. One or more layers on multilayer PCBs are usually devoted to ground planes. A ground plane helps distribute heat and reduces EMI noise pickup. Make sure to physically separate digital and analog grounds, paying attention to the flow of the ground current.
- To reduce parasitic coupling, run the input traces as far away from the supply or output traces as possible. If it is not possible to keep them separate, it is much better to cross the sensitive trace perpendicular as opposed to in parallel with the noisy trace.
- Place the external components as close to the device as possible. Keeping  $R_F$  and  $R_G$  close to the inverting input minimizes parasitic capacitance, as shown in [Layout Examples](#).
- Keep the length of input traces as short as possible. Always remember that the input traces are the most sensitive part of the circuit.
- Consider a driven, low-impedance guard ring around the critical traces. A guard ring can significantly reduce leakage currents from nearby traces that are at different potentials.

## 8.4.2 Layout Examples



**Figure 8-3. Operational Amplifier Board Layout for Noninverting Configuration**



**Figure 8-4. Operational Amplifier Schematic for Noninverting Configuration**

## 9 Device and Documentation Support

### 9.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](https://www.ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 9.2 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 9.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.  
All trademarks are the property of their respective owners.

### 9.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 9.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision AA (March 2022) to Revision AB (October 2024)                                                                                 | Page |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Changed <i>Device Information</i> table to <i>Package Information</i> .....                                                                       | 1    |
| • Changed the polarity of the LM358B and LM358BA input bias current value from $\pm$ to $-$ in the <i>Electrical Characteristics</i> section.....   | 6    |
| • Changed the polarity of the LM2904B and LM2904BA input bias current value from $\pm$ to $-$ in the <i>Electrical Characteristics</i> section..... | 8    |

| Changes from Revision Z (July 2021) to Revision AA (March 2022)                                                                                  | Page |
|--------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Added LM358BA and LM2904BA to the <i>Device Information</i> table.....                                                                         | 1    |
| • Added <i>Family Comparison</i> table to the <i>Description</i> section .....                                                                   | 1    |
| • Raised ESD (CDM) for B-versions and BA-versions from 1 kV to 1.5 kV in the <i>ESD Ratings</i> table .....                                      | 4    |
| • Changed Input Offset Voltage Max of LM2904BA from $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$ from $\pm 2.5$ mV to $\pm 3.0$ mV..... | 8    |

| Changes from Revision Y (February 2021) to Revision Z (July 2021)                                        | Page |
|----------------------------------------------------------------------------------------------------------|------|
| • Deleted preview tag from LM358B and LM2904B SOT-23 (8) package in <i>Device Information</i> table..... | 1    |
| • Updated DDF (SOT-23) package thermal information in the <i>Thermal Information</i> table.....          | 5    |
| • Deleted <i>Related Links</i> from the <i>Device and Documentation Support</i> section.....             | 30   |

| Changes from Revision X (June 2020) to Revision Y (February 2021)                                       | Page |
|---------------------------------------------------------------------------------------------------------|------|
| • Updated the numbering format for tables, figures, and cross-references throughout the document.....   | 1    |
| • Added SOT23-8 (DDF) package information throughout data sheet.....                                    | 1    |
| • Deleted preview tag from LM358B and LM2904B VSSOP (8) package in <i>Device Information</i> table..... | 1    |
| • Added SOT23-8 (DDF) package information to the <i>Pin Configuration and Functions</i> section.....    | 3    |
| • Added DDF (SOT-23) package to the <i>Thermal Information</i> table.....                               | 5    |

| Changes from Revision W (October 2019) to Revision X (June 2020)                                         | Page |
|----------------------------------------------------------------------------------------------------------|------|
| • Added application links to <i>Applications</i> section.....                                            | 1    |
| • Deleted preview tag from LM358B and LM2904B TSSOP (8) package in <i>Device Information</i> table ..... | 1    |

| Changes from Revision V (September 2018) to Revision W (October 2019)                                                                | Page |
|--------------------------------------------------------------------------------------------------------------------------------------|------|
| • Changed CDM ESD rating for LM358B and LM2904B in <i>ESD Ratings</i> .....                                                          | 4    |
| • Changed $V_S$ to $V_+$ in <i>Recommended Operating Conditions</i> .....                                                            | 5    |
| • Changed <i>Thermal Information</i> for the LM158FK and LM158JG devices.....                                                        | 5    |
| • Added <i>Typical Characteristics</i> section for the LM358B and LM2490B op amps.....                                               | 15   |
| • Added test circuit for THD+N and small-signal step response, $G = -1$ in the <i>Parameter Measurement Information</i> section..... | 24   |
| • Changed the <i>Functional Block Diagram</i> .....                                                                                  | 25   |

| Changes from Revision U (January 2017) to Revision V (September 2018)                                                                   | Page |
|-----------------------------------------------------------------------------------------------------------------------------------------|------|
| • Changed the data sheet title .....                                                                                                    | 1    |
| • Changed first four items in the <i>Features</i> section .....                                                                         | 1    |
| • Changed the first item in the <i>Applications</i> section and added four new items .....                                              | 1    |
| • Changed voltage values in the first paragraph of the <i>Description</i> section.....                                                  | 1    |
| • Changed text in the second paragraph of the <i>Description</i> section.....                                                           | 1    |
| • Added devices LM358B and LM2904B to data sheet.....                                                                                   | 1    |
| • Changed the first three rows of the <i>Device Information</i> table and added a cross-referenced note for PREVIEW-status devices..... | 1    |
| • Added a table note to the <i>Pin Functions</i> table .....                                                                            | 3    |
| • Changed "free-air temperature" to "ambient temperature" in the <i>Absolute Maximum Ratings</i> condition statement.....               | 4    |
| • Changed all entries in the <i>Absolute Maximum Ratings</i> table except $T_J$ and $T_{stg}$ .....                                     | 4    |
| • Deleted lead temperature and case temperature from <i>Absolute Maximum Ratings</i> .....                                              | 4    |
| • Changed device listings and their voltage values in the <i>ESD Ratings</i> table .....                                                | 4    |
| • Changed "free-air temperature" to "ambient temperature" in the <i>Recommended Operating Conditions</i> condition statement .....      | 5    |
| • Changed table entries for all parameters in the <i>Recommended Operating Conditions</i> table.....                                    | 5    |
| • Added rows to the <i>Thermal Information</i> table, and a table note regarding device-package combinations .....                      | 5    |
| • Deleted the <i>Operating Conditions</i> table.....                                                                                    | 14   |
| • Added a condition statement to the <i>Typical Characteristics</i> section.....                                                        | 22   |
| • Changed specific voltages to a <i>Recommended Operating Conditions</i> reference.....                                                 | 25   |
| • Changed unity-gain bandwidth from 0.7 MHz for all devices to 1.2 MHz for B-version devices.....                                       | 26   |
| • Changed slew rate from 3 V/ $\mu$ s for all devices to 0.5 V/ $\mu$ s for B-version devices.....                                      | 26   |
| • Changed the <i>Input Common-Mode Range</i> section in multiple places throughout.....                                                 | 26   |
| • Changed $V_{CC}$ to $V_S$ in the <i>Application Information</i> section .....                                                         | 27   |
| • Subscripted the suffixes fro $R_I$ and $R_F$ .....                                                                                    | 27   |

|                                                                                                                                   |    |
|-----------------------------------------------------------------------------------------------------------------------------------|----|
| • Changed <i>Operational Amplifier Board Layout for Noninverting Configuration</i> with an image that includes a dual op amp..... | 29 |
|-----------------------------------------------------------------------------------------------------------------------------------|----|

| Changes from Revision T (April 2015) to Revision U (January 2017) | Page |
|-------------------------------------------------------------------|------|
| • Changed data sheet title.....                                   | 1    |

| Changes from Revision S (January 2014) to Revision T (April 2015)                                                                                                                                                                                                                                                                                                                 | Page |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Added <i>Applications</i> section, <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | 1    |

| Changes from Revision R (July 2010) to Revision S (January 2014)                        | Page |
|-----------------------------------------------------------------------------------------|------|
| • Converted this data sheet from the QS format to DocZone using the PDF on the web..... | 1    |
| • Deleted <i>Ordering Information</i> table.....                                        | 1    |
| • Updated <i>Features</i> to include Military Disclaimer.....                           | 1    |
| • Added Typical Characteristics section.....                                            | 22   |

## 11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most-current data available for the designated devices. This data is subject to change without notice and without revision of this document. For browser based versions of this data sheet, see the left-hand navigation pane.

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins     | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)             |
|--------------------------------|---------------|----------------------|--------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------------|
| <a href="#">5962-87710012A</a> | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710012A<br>LM158FKB  |
| <a href="#">5962-8771001PA</a> | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771001PA<br>LM158              |
| <a href="#">5962-87710022A</a> | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710022A<br>LM158AFKB |
| <a href="#">5962-8771002PA</a> | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771002PA<br>LM158A             |
| LM158 MW8                      | Active        | Production           | WAFERSALE (YS)   0 | 1   NOT REQUIRED      | -           | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   |                                 |
| <a href="#">LM158AFKB</a>      | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710022A<br>LM158AFKB |
| LM158AFKB.A                    | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710022A<br>LM158AFKB |
| <a href="#">LM158AJG</a>       | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | LM158AJG                        |
| LM158AJG.A                     | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | LM158AJG                        |
| <a href="#">LM158AJGB</a>      | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771002PA<br>LM158A             |
| LM158AJGB.A                    | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771002PA<br>LM158A             |
| <a href="#">LM158FKB</a>       | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710012A<br>LM158FKB  |
| LM158FKB.A                     | Active        | Production           | LCCC (FK)   20     | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87710012A<br>LM158FKB  |
| <a href="#">LM158JG</a>        | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | LM158JG                         |
| LM158JG.A                      | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | LM158JG                         |
| <a href="#">LM158JGB</a>       | Active        | Production           | CDIP (JG)   8      | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771001PA<br>LM158              |

| Orderable part number      | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)      |
|----------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------|
| LM158JGB.A                 | Active        | Production           | CDIP (JG)   8   | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8771001PA<br>LM158       |
| <a href="#">LM258ADGKR</a> | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | NIPDAU   SN   NIPDAU                 | Level-1-260C-UNLIM                | -25 to 85    | (M3L, M3P, M3S, M3<br>U) |
| LM258ADGKR.A               | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | (M3L, M3P, M3S, M3<br>U) |
| LM258ADGKR.B               | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | (M3L, M3P, M3S, M3<br>U) |
| <a href="#">LM258ADR</a>   | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| LM258ADR.A                 | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| LM258ADR.B                 | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| <a href="#">LM258ADRG4</a> | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| LM258ADRG4.A               | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| LM258ADRG4.B               | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258A                   |
| <a href="#">LM258AP</a>    | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| LM258AP.A                  | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| LM258AP.B                  | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| <a href="#">LM258APE4</a>  | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| LM258APE4.A                | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| LM258APE4.B                | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258AP                  |
| <a href="#">LM258DGKR</a>  | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -25 to 85    | (M2L, M2P, M2S, M2<br>U) |
| LM258DGKR.A                | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -25 to 85    | (M2L, M2P, M2S, M2<br>U) |
| LM258DGKR.B                | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -25 to 85    | (M2L, M2P, M2S, M2<br>U) |
| <a href="#">LM258DR</a>    | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -25 to 85    | LM258                    |
| LM258DR.A                  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258                    |
| LM258DR.B                  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258                    |
| <a href="#">LM258DRG3</a>  | Obsolete      | Production           | SOIC (D)   8    | -                     | -           | Call TI                              | Call TI                           | -25 to 85    | LM258                    |
| <a href="#">LM258DRG4</a>  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -25 to 85    | LM258                    |
| LM258DRG4.A                | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258                    |

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| LM258DRG4.B                    | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | LM258               |
| <a href="#">LM258P</a>         | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU   SN                          | N/A for Pkg Type                  | -25 to 85    | LM258P              |
| LM258P.A                       | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258P              |
| LM258P.B                       | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258P              |
| <a href="#">LM258PE4</a>       | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258P              |
| LM258PE4.B                     | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | LM258P              |
| <a href="#">LM2904AVQDR</a>    | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQDR.A                  | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQDR.B                  | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| <a href="#">LM2904AVQDRG4</a>  | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQDRG4.A                | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQDRG4.B                | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| <a href="#">LM2904AVQPWR</a>   | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQPWR.A                 | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQPWR.B                 | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| <a href="#">LM2904AVQPWRG4</a> | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQPWRG4.A               | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| LM2904AVQPWRG4.B               | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904AV             |
| <a href="#">LM2904BAIDDFR</a>  | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904A               |
| LM2904BAIDDFR.A                | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904A               |
| LM2904BAIDDFR.B                | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904A               |
| <a href="#">LM2904BAIDGKR</a>  | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 28CB                |
| LM2904BAIDGKR.A                | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 28CB                |
| LM2904BAIDGKR.B                | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | 28CB                |
| <a href="#">LM2904BAIDR</a>    | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| LM2904BAIDR.A                  | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| LM2904BAIDR.B                  | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| <a href="#">LM2904BAIPWR</a>   | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| LM2904BAIPWR.A                 | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| LM2904BAIPWR.B                 | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904BA              |
| <a href="#">LM2904BIDDFR</a>   | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904               |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)   |
|------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------|
| LM2904BIDDFR.A               | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904                 |
| LM2904BIDDFR.B               | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904                 |
| <a href="#">LM2904BIDGKR</a> | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | 28BB                  |
| LM2904BIDGKR.A               | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 28BB                  |
| LM2904BIDGKR.B               | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 28BB                  |
| <a href="#">LM2904BIDR</a>   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIDR.A                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIDR.B                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIDRG4                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIDRG4.A               | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIDRG4.B               | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| <a href="#">LM2904BIPWR</a>  | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIPWR.A                | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904BIPWR.B                | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904B                |
| LM2904DE4                    | NRND          | Production           | null (null)           | 75   TUBE             | -           | Call TI                              | Call TI                           | -40 to 125   |                       |
| <a href="#">LM2904DGKR</a>   | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | (MBL, MBP, MBS, MB U) |
| LM2904DGKR.A                 | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | (MBL, MBP, MBS, MB U) |
| LM2904DGKR.B                 | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | (MBL, MBP, MBS, MB U) |
| <a href="#">LM2904DR</a>     | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | LM2904                |
| LM2904DR.A                   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | LM2904                |
| LM2904DR.B                   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | LM2904                |
| <a href="#">LM2904DRG3</a>   | Obsolete      | Production           | SOIC (D)   8          | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | LM2904                |
| <a href="#">LM2904DRG4</a>   | Obsolete      | Production           | SOIC (D)   8          | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | LM2904                |
| <a href="#">LM2904P</a>      | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P               |
| LM2904P.A                    | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P               |
| LM2904P.B                    | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P               |
| <a href="#">LM2904PE4</a>    | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P               |
| LM2904PE4.A                  | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P               |

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)  |
|--------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|----------------------|
| LM2904PE4.B                    | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | LM2904P              |
| <a href="#">LM2904PSR</a>      | Active        | Production           | SO (PS)   8     | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904                |
| LM2904PSR.A                    | Active        | Production           | SO (PS)   8     | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904                |
| <a href="#">LM2904PWR</a>      | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | L2904                |
| LM2904PWR.A                    | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904                |
| <a href="#">LM2904PWRG3</a>    | Obsolete      | Production           | TSSOP (PW)   8  | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | L2904                |
| <a href="#">LM2904PWRG4-JF</a> | Obsolete      | Production           | TSSOP (PW)   8  | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | L2904                |
| <a href="#">LM2904QDR</a>      | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904Q1               |
| LM2904QDR.A                    | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904Q1               |
| LM2904QDR.B                    | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 2904Q1               |
| <a href="#">LM2904QDRG4</a>    | Obsolete      | Production           | SOIC (D)   8    | -                     | -           | Call TI                              | Call TI                           | -40 to 125   | 2904Q1               |
| <a href="#">LM2904VQDR</a>     | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQDR.A                   | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQDR.B                   | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| <a href="#">LM2904VQDRG4</a>   | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQDRG4.A                 | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQDRG4.B                 | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| <a href="#">LM2904VQPWR</a>    | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQPWR.A                  | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQPWR.B                  | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| <a href="#">LM2904VQPWRG4</a>  | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQPWRG4.A                | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM2904VQPWRG4.B                | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | L2904V               |
| LM358ADE4                      | NRND          | Production           | null (null)     | 75   TUBE             | -           | Call TI                              | Call TI                           | 0 to 70      |                      |
| <a href="#">LM358ADGKR</a>     | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | (M6L, M6P, M6S, M6U) |
| LM358ADGKR.A                   | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | (M6L, M6P, M6S, M6U) |
| LM358ADGKR.B                   | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | (M6L, M6P, M6S, M6U) |
| <a href="#">LM358ADR</a>       | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | 0 to 70      | LM358A               |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| LM358ADR.A                   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | LM358A              |
| LM358ADR.B                   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | LM358A              |
| <a href="#">LM358ADRG4</a>   | Obsolete      | Production           | SOIC (D)   8          | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM358A              |
| <a href="#">LM358AP</a>      | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358AP             |
| LM358AP.B                    | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358AP             |
| <a href="#">LM358APE4</a>    | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358AP             |
| LM358APE4.A                  | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358AP             |
| LM358APE4.B                  | Active        | Production           | PDIP (P)   8          | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358AP             |
| <a href="#">LM358APW</a>     | Obsolete      | Production           | TSSOP (PW)   8        | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | L358A               |
| <a href="#">LM358APWR</a>    | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | 0 to 70      | L358A               |
| LM358APWR.A                  | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | L358A               |
| <a href="#">LM358BAIDDFR</a> | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| LM358BAIDDFR.A               | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| LM358BAIDDFR.B               | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| LM358BAIDDFRG4               | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| LM358BAIDDFRG4.A             | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| LM358BAIDDFRG4.B             | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 358BA               |
| <a href="#">LM358BAIDGKR</a> | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | 28DB                |
| LM358BAIDGKR.B               | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | 28DB                |
| <a href="#">LM358BAIDR</a>   | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIDR.A                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIDR.B                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIDRG4                 | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIDRG4.A               | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIDRG4.B               | Active        | Production           | SOIC (D)   8          | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| <a href="#">LM358BAIPWR</a>  | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIPWR.A                | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| LM358BAIPWR.B                | Active        | Production           | TSSOP (PW)   8        | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | L358BA              |
| <a href="#">LM358BIDDFR</a>  | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358               |
| LM358BIDDFR.B                | Active        | Production           | SOT-23-THIN (DDF)   8 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358               |
| <a href="#">LM358BIDGKR</a>  | Active        | Production           | VSSOP (DGK)   8       | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 85    | (1TKR, 358B)        |

| Orderable part number      | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)   |
|----------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------|
| LM358BIDGKR.A              | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (1TKR, 358B)          |
| LM358BIDGKR.B              | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (1TKR, 358B)          |
| <a href="#">LM358BIDR</a>  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIDR.A                | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIDR.B                | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIDRG4                | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIDRG4.A              | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIDRG4.B              | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| <a href="#">LM358BIPWR</a> | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIPWR.A               | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIPWR.B               | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIPWRG4               | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIPWRG4.A             | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| LM358BIPWRG4.B             | Active        | Production           | TSSOP (PW)   8  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | LM358B                |
| <a href="#">LM358D</a>     | Obsolete      | Production           | SOIC (D)   8    | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM358                 |
| <a href="#">LM358DGKR</a>  | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | (M5L, M5P, M5S, M5 U) |
| LM358DGKR.B                | Active        | Production           | VSSOP (DGK)   8 | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | 0 to 70      | (M5L, M5P, M5S, M5 U) |
| <a href="#">LM358DR</a>    | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | LM358                 |
| LM358DR.A                  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | LM358                 |
| LM358DR.B                  | Active        | Production           | SOIC (D)   8    | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | LM358                 |
| <a href="#">LM358DRG3</a>  | Obsolete      | Production           | SOIC (D)   8    | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM358                 |
| <a href="#">LM358DRG4</a>  | Obsolete      | Production           | SOIC (D)   8    | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM358                 |
| <a href="#">LM358P</a>     | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |
| LM358P.A                   | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |
| LM358P.B                   | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |
| <a href="#">LM358PE3</a>   | Obsolete      | Production           | PDIP (P)   8    | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | LM358P                |
| <a href="#">LM358PE4</a>   | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |
| LM358PE4.A                 | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |
| LM358PE4.B                 | Active        | Production           | PDIP (P)   8    | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | LM358P                |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">LM358PSR</a>      | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | L358                |
| LM358PSR.A                    | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | L358                |
| <a href="#">LM358PW</a>       | Obsolete      | Production           | TSSOP (PW)   8 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | L358                |
| <a href="#">LM358PWR</a>      | Active        | Production           | TSSOP (PW)   8 | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | 0 to 70      | L358                |
| LM358PWR.A                    | Active        | Production           | TSSOP (PW)   8 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | L358                |
| <a href="#">LM358PWRG3</a>    | Obsolete      | Production           | TSSOP (PW)   8 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | L358                |
| <a href="#">LM358PWRG4</a>    | Obsolete      | Production           | TSSOP (PW)   8 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | L358                |
| <a href="#">LM358PWRG4-JF</a> | Obsolete      | Production           | TSSOP (PW)   8 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | L358                |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**OTHER QUALIFIED VERSIONS OF LM258A, LM2904, LM2904B, LM2904BA :**

- Automotive : [LM2904-Q1](#), [LM2904B-Q1](#), [LM2904BA-Q1](#)
- Enhanced Product : [LM258A-EP](#), [LM2904-EP](#)

## NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications

## TAPE AND REEL INFORMATION




\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM258ADGKR  | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM258ADR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258ADR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258ADR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258ADRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258ADRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258ADRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DGKR   | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM258DR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DRG4   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DRG4   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DRG4   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM258DRG4   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904AVQDR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM2904AVQDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.5               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904AVQDRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904AVQDRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.5               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904AVQPWR   | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904AVQPWRG4 | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904BAIDDFR  | SOT-23-THIN  | DDF             | 8    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LM2904BAIDGKR  | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| LM2904BAIDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904BAIPWR   | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904BIDDFR   | SOT-23-THIN  | DDF             | 8    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LM2904BIDGKR   | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM2904BIDR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904BIPWR    | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904DGKR     | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM2904DR       | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904DR       | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904PSR      | SO           | PS              | 8    | 2000 | 330.0              | 16.4               | 8.35    | 6.6     | 2.4     | 12.0    | 16.0   | Q1            |
| LM2904PWR      | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904QDR      | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904VQDR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.5               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904VQDRG4   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM2904VQPWR    | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM2904VQPWRG4  | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM358ADGKR     | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| LM358ADR       | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358APWR      | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM358BAIDDFR   | SOT-23-THIN  | DDF             | 8    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LM358BAIDDFRG4 | SOT-23-THIN  | DDF             | 8    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LM358BAIDGKR   | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BAIPWR    | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM358BIDDFR    | SOT-23-THIN  | DDF             | 8    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| LM358BIDGKR    | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BIDR      | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BIDRG4    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358BIDRG4    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LM358BIPWR   | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM358BIPWRG4 | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |
| LM358DGKR    | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LM358DR      | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358DR      | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LM358PSR     | SO           | PS              | 8    | 2000 | 330.0              | 16.4               | 8.35    | 6.6     | 2.4     | 12.0    | 16.0   | Q1            |
| LM358PWR     | TSSOP        | PW              | 8    | 2000 | 330.0              | 12.4               | 7.0     | 3.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM258ADGKR    | VSSOP        | DGK             | 8    | 2500 | 356.0       | 356.0      | 35.0        |
| LM258ADR      | SOIC         | D               | 8    | 2500 | 340.5       | 336.1      | 25.0        |
| LM258ADR      | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM258ADR      | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM258ADRG4    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM258ADRG4    | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM258ADRG4    | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM258DGKR     | VSSOP        | DGK             | 8    | 2500 | 356.0       | 356.0      | 35.0        |
| LM258DR       | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM258DR       | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM258DR       | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM258DR       | SOIC         | D               | 8    | 2500 | 340.5       | 336.1      | 25.0        |
| LM258DRG4     | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM258DRG4     | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM258DRG4     | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904AVQDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM2904AVQDR   | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904AVQDRG4 | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM2904AVQDRG4  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904AVQPWR   | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904AVQPWRG4 | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904BAIDDFR  | SOT-23-THIN  | DDF             | 8    | 3000 | 210.0       | 185.0      | 35.0        |
| LM2904BAIDGKR  | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| LM2904BAIDR    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904BAIPWR   | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904BIDDFR   | SOT-23-THIN  | DDF             | 8    | 3000 | 210.0       | 185.0      | 35.0        |
| LM2904BIDGKR   | VSSOP        | DGK             | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904BIDR     | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904BIPWR    | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904DGKR     | VSSOP        | DGK             | 8    | 2500 | 356.0       | 356.0      | 35.0        |
| LM2904DR       | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM2904DR       | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904PSR      | SO           | PS              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904PWR      | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904QDR      | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904VQDR     | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM2904VQDRG4   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM2904VQPWR    | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM2904VQPWRG4  | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358ADGKR     | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| LM358ADR       | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358APWR      | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358BAIDDFR   | SOT-23-THIN  | DDF             | 8    | 3000 | 210.0       | 185.0      | 35.0        |
| LM358BAIDDFRG4 | SOT-23-THIN  | DDF             | 8    | 3000 | 210.0       | 185.0      | 35.0        |
| LM358BAIDGKR   | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 340.5       | 336.1      | 25.0        |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358BAIDR     | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358BAIPWR    | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358BIDDFR    | SOT-23-THIN  | DDF             | 8    | 3000 | 210.0       | 185.0      | 35.0        |
| LM358BIDGKR    | VSSOP        | DGK             | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358BIDR      | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358BIDRG4    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358BIDRG4    | SOIC         | D               | 8    | 2500 | 340.5       | 336.1      | 25.0        |
| LM358BIPWR     | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358BIPWRG4   | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358DGKR      | VSSOP        | DGK             | 8    | 2500 | 356.0       | 356.0      | 35.0        |
| LM358DR        | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LM358DR        | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| LM358PSR       | SO           | PS              | 8    | 2000 | 353.0       | 353.0      | 32.0        |
| LM358PWR       | TSSOP        | PW              | 8    | 2000 | 353.0       | 353.0      | 32.0        |

## TUBE




\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-87710012A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| 5962-87710022A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| LM158AFKB      | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| LM158AFKB.A    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| LM158FKB       | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| LM158FKB.A     | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| LM258AP        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258AP.A      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258AP.B      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258APE4      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258APE4.A    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258APE4.B    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258P         | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258P         | P            | PDIP         | 8    | 50  | 506.1  | 9      | 600    | 5.4    |
| LM258P.A       | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258P.A       | P            | PDIP         | 8    | 50  | 506.1  | 9      | 600    | 5.4    |
| LM258P.B       | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258P.B       | P            | PDIP         | 8    | 50  | 506.1  | 9      | 600    | 5.4    |
| LM258PE4       | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM258PE4.B     | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904P        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904P.A      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904P.B      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904PE4      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904PE4.A    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM2904PE4.B    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358AP        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358AP        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358AP.B      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| LM358AP.B   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4.B | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358APE4.B | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P.A    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P.A    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P.B    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358P.B    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4.A  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4.A  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4.B  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LM358PE4.B  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |

P (R-PDIP-T8)

PLASTIC DUAL-IN-LINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MS-001 variation BA.


PW0008A



# PACKAGE OUTLINE

## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



4221848/A 02/2015

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153, variation AA.

# EXAMPLE BOARD LAYOUT


PW0008A

TSSOP - 1.2 mm max height


SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
SCALE:10X



NON SOLDER MASK  
DEFINED



SOLDER MASK  
DEFINED

SOLDER MASK DETAILS  
NOT TO SCALE

4221848/A 02/2015

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0008A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:10X

4221848/A 02/2015

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

JG0008A

## PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN-LINE PACKAGE



4230036/A 09/2023

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package can be hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification.
5. Falls within MIL STD 1835 GDIP1-T8

# EXAMPLE BOARD LAYOUT

JG0008A

CDIP - 5.08 mm max height


CERAMIC DUAL IN-LINE PACKAGE



LAND PATTERN EXAMPLE  
NON SOLDER MASK DEFINED  
SCALE: 9X

4230036/A 09/2023


DGK0008A



# PACKAGE OUTLINE

VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



4214862/A 04/2023

## NOTES:

PowerPAD is a trademark of Texas Instruments.


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-187.

# EXAMPLE BOARD LAYOUT



DGK0008A

<sup>TM</sup> VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 15X



SOLDER MASK DETAILS

4214862/A 04/2023

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
8. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.
9. Size of metal pad may vary due to creepage requirement.

## EXAMPLE STENCIL DESIGN

DGK0008A

<sup>TM</sup> VSSOP - 1.1 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
SCALE: 15X

4214862/A 04/2023

NOTES: (continued)

11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
12. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW


**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229370VA\


**DDF0008A**



# PACKAGE OUTLINE

**SOT-23-THIN - 1.1 mm max height**

PLASTIC SMALL OUTLINE



4222047/E 07/2024

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.

# EXAMPLE BOARD LAYOUT



DDF0008A

SOT-23-THIN - 1.1 mm max height

PLASTIC SMALL OUTLINE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4222047/E 07/2024

NOTES: (continued)


4. Publication IPC-7351 may have alternate designs.
5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DDF0008A

SOT-23-THIN - 1.1 mm max height

PLASTIC SMALL OUTLINE




SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4222047/E 07/2024

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
7. Board assembly site may have different recommendations for stencil design.




**D0008A**

# PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019


## NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.


**D0008A**

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



## SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019


NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

PS (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE




4040063/C 03/03

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

## PS (R-PDSO-G8)

## PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated