

TMP9R01-SEP Single-Event Effects (SEE) Radiation Test Report



ABSTRACT

This report characterizes the effects of heavy-ion irradiation on the single-event effect (SEE) performance of the TMP9R01-SEP 1-channel temperature sensor. Heavy ions with a LET_{EFF} of $50.5\text{MeV}\cdot\text{cm}^2/\text{mg}$ was used to irradiate the devices with a fluence of $1 \times 10^7 \text{ ions}/\text{cm}^2$. The results demonstrate that the TMP9R01-SEP is SEL-free up to $\text{LET}_{\text{EFF}} = 50.5\text{MeV}\cdot\text{cm}^2/\text{mg}$ at 125°C , and a dynamic SET cross section is presented.

Table of Contents

1 Introduction.....	3
2 Sample Identification.....	4
3 Irradiation Facility and Setup.....	5
4 Die Micro-section.....	5
5 Test Set-Up.....	6
6 SEL Results.....	11
6.1 TMP9R01-SEP SEL Data.....	12
7 SET Results.....	16
7.1 Summary of SET Results.....	20
7.2 Cross Section Events and Event Rate Calculations.....	38
8 Detailed Results Per Run.....	42
8.1 Detailed Run Raw Data.....	43
9 Summary.....	44
10 Glossary.....	44
11 Revision History.....	45

List of Figures

Figure 2-1. TMP9R01-SEP DGS Package 10-Pin VSSOP Top View - Pinout.....	4
Figure 2-2. TMP9R01 Optical Image.....	4
Figure 2-3. TMP9R01 XRay Image.....	4
Figure 2-4. TMP9R01 XRay Image.....	4
Figure 2-5. Functional Block Diagram of the TMP9R01-SEP.....	4
Figure 4-1. Generalized Cross-Section of the LBC8 Technology BEOL Stack on the TMP9R01-SEP.....	5
Figure 5-1. SEL Setup.....	6
Figure 5-2. SEL Setup.....	7
Figure 5-3. TMP9R01EVM Schematic.....	8
Figure 5-4. Expected Total Quiescent Current with Communication.....	9
Figure 5-5. Full Lab SEL Set Up.....	9
Figure 5-6. TMP9R01 SET PCB Layout.....	10
Figure 5-7. TMP9R01 SET Schematic.....	10
Figure 5-8. Full SET Test Setup.....	11
Figure 6-1. Run Passing SEL Run 4, DUT #2, MSU, 125C, Xe (50.4MeV).....	13
Figure 6-2. Run Passing SEL Run 7, DUT #3, MSU, 125C, Xe (50.4MeV).....	14
Figure 6-3. Run Passing SEL Run 9, DUT #4, MSU, 125C, Xe (50.4MeV).....	15
Figure 7-1. Reset Software Procedure.....	16
Figure 7-2. 12-bit Q4 Format.....	18
Figure 7-3. Alert and Therm Interrupt Operation.....	18
Figure 7-4. Therm and Therm2 Interrupt Operation.....	18
Figure 7-5. TMP9R01 Temperature Reads During 50.5MeV Exposure.....	35
Figure 7-6. TMP9R01 Temperature Reads During 50.5MeV Exposure.....	35

Trademarks

Figure 7-7. Possible Alert Signal Trip During Exposure.....	36
Figure 7-8. Possible Alert Signal Trip During Exposure.....	36
Figure 7-9. Possible Alert Signal Trip During Exposure.....	37
Figure 7-10. Possible Alert Signal Trip During Exposure.....	37
Figure 7-11. Weibull Plot for Local Temperature Accuracy Events.....	38
Figure 7-12. Weibull Plot for Remote Temperature Accuracy Events.....	38
Figure 7-13. Weibull Plot for Bit Flip Events.....	39
Figure 7-14. Weibull Plot for Alert Trip Events.....	39

List of Tables

Table 1-1. Overview Information.....	3
Table 3-1. Ions and LET _{EFF} Used for SEE Characterization.....	5
Table 5-1. TMP9R01 Current Specs.....	8
Table 6-1. TMP9R01-SEP SEL Data.....	12
Table 7-1. Registers Impacting Accuracy Events.....	17
Table 7-2. Registers Impacting Alert/Therm Events.....	19
Table 7-3. Data Comparing SET Results with Resets and No Resets.....	19
Table 7-4. Summary of TMP9R01-SEP SET Results at 25C with Resets.....	20
Table 7-5. Summary of TMP9R01-SEP SET Results at 80C with Resets.....	21
Table 7-6. Number of Bit Flips within Registers 25C.....	22
Table 7-7. Number of Bit Flips within Registers 80C.....	23
Table 7-8. 25C Register Bit Flip Cross Section Summary.....	23
Table 7-9. 80C Register Bit Flip Cross Section Summary.....	29
Table 7-10. 25C SET Event Rate Calculations for Worst-Week LEO and GEO Orbits.....	40
Table 7-11. 80C SET Event Rate Calculations for Worst-Week LEO and GEO Orbits.....	41
Table 8-1. Detailed Run Raw Data.....	43

Trademarks

All trademarks are the property of their respective owners.

1 Introduction

The TMP9R01-SEP device is a radiation tolerant plastic package, high-accuracy, low-power 1-channel remote temperature sensor monitor with a built-in local temperature sensor. The remote temperature sensors are typically low-cost discrete NPN or PNP transistors, or substrate thermal transistors or diodes that are integral parts of microprocessors, analog-to-digital converters (ADC), digital-to-analog converters (DAC), microcontrollers, or field-programmable gate arrays (FPGA). Temperature is represented as a 12-bit digital code for both local and remote sensors, giving a resolution of 0.0625°C. The two-wire serial interface accepts the SMBus communication protocol with up to nine different pin-programmable addresses.

Table 1-1 lists general device information and test conditions. See the [TMP9R01-SEP Product Page](#) for more detailed technical specifications, user-guides, and application notes.

Table 1-1. Overview Information

Description	Device Information ⁽¹⁾
TI Part Number	TMP9R01-SEP
VID Number	V62/24615
Device Function	Remote and Local Digital Temperature Sensor
Technology	LCB8LV
Exposure Facility	Facility for Rare Isotope Beams, Michigan State University
Heavy Ion Fluence per Run	$1 \times 10^6 - 1 \times 10^7$ ions/cm ²
Irradiation Temperature SET	25°C and 80°C
Irradiation Temperature SEL	125°C

- (1) TI can provide technical, application or design advice, quality characterization, and reliability data or service providing these items shall not expand or otherwise affect TI's warranties as set forth in the Texas Instruments Incorporated Standard Terms and Conditions of Sale for Semiconductor Products and no obligation or liability shall arise from Semiconductor Products and no obligation or liability shall arise from TI's provision of such items.

2 Sample Identification

A total of three temperature sensors were verified during SEL testing. A total of one temperature was verified during SET testing. The photos below show the bond wires of a DUT that was tested. All units were decapped before radiation exposure.




Figure 2-1. TMP9R01-SEP DGS Package 10-Pin VSSOP Top View - Pinout




Figure 2-2. TMP9R01 Optical Image




Figure 2-3. TMP9R01 XRay Image




Figure 2-4. TMP9R01 XRay Image




Figure 2-5. Functional Block Diagram of the TMP9R01-SEP

3 Irradiation Facility and Setup

The heavy-ion species used for the SEE studies on this product were provided and delivered by:

- Michigan State University (MSU) Facility for Rare Isotope Beams (FRIB) using a linear accelerator and an advanced electron cyclotron resonance (ECR) ion source. At the fluxes used, ion beams had good flux stability and high irradiation uniformity as the beam is collimated to a maximum of 20mm x 20mm square cross-sectional area for the in-vacuum scintillator. Uniformity is achieved by scattering on a Cu foil and then performing magnetic defocusing. The flux of the beam is regulated over a broad range spanning several orders of magnitude. For these studies, ion flux of 9.36×10^4 to 1.07×10^5 ions/cm² · s was used to provide heavy-ion fluences of 1.00×10^7 ions/cm².

Table 3-1. Ions and LET_{EFF} Used for SEE Characterization

Ion Type	Location	Angle of Incidence	FLUX (ions·cm ² /mg)	FLUENCE (# ions)	LET _{EFF} (MeV-cm ² /mg)
¹²⁹ Xe	MSU	0°	1.00×10^5	1.00×10^7	50.5
⁸⁴ Kr	MSU	0°	1.00×10^4	1.00×10^6	35.4
⁴⁰ Ar	MSU	0°	1.00×10^4	1.00×10^6	7.9

4 Die Micro-section

The TMP9R01-SEP is fabricated in the TI Linear BiCMOS 180-nm process with a back-end-of-line (BEOL) stack consisting of 3 levels of standard thickness aluminum metal on a 0.6μm pitch. The total stack height from the surface of the passivation to the silicon surface is 3.825μm based on nominal layer thickness as shown in [Figure 4-1](#). Accounting for energy loss through the 1mil thick Aramica beam port window, the 40mm air gap, and the BEOL stack over the TMP9R01-SEP, the effective LET (LETEFF) at the surface of the silicon substrate, the depth, and the ion range was determined with the SEUSS 2020 Software (provided by the Texas A&M Cyclotron Institute and based on the latest SRIM-2013 models). The stack was modeled as a homogeneous layer of silicon dioxide (valid since SiO₂ and aluminum density are similar). At MSU, the LETEFF reported is the surface-level LET.




Figure 4-1. Generalized Cross-Section of the LBC8 Technology BEOL Stack on the TMP9R01-SEP

5 Test Set-Up

SEL testing was captured with the TMP9R01EVM. An SMU was used to supply max voltage (3.6V) and measure current through TP2 and GND. The R21 resistor was removed, the Subregulator Switch was switched off, and TP1 and TP2 was supplied at maximum voltage 3.6V.



Figure 5-1. SEL Setup



Figure 5-2. SEL Setup




Figure 5-3. TMP9R01EVM Schematic

Table 5-1. TMP9R01 Current Specs

		TYP (µA)	MAX (µA)
Iq	Active conversion, local sensor	240	375
	Active conversion, remote sensor	400	600
	Standby mode (between conversions)	15	35
	Shutdown mode, serial bus inactive	3	8
	Shutdown mode, serial bus active, fs = 400kHz	90	
	Shutdown mode, serial bus active, fs = 2.17MHz	350	




Figure 5-4. Expected Total Quiescent Current with Communication




Figure 5-5. Full Lab SEL Set Up

SET testing for TMP9R01 has a separate board. The board was designed to capture transient data from the DUT and report the values in an excel sheet. More information about what was captured is presented in the Summary of SET Results Section. The board schematic, layout, and setup is shown below. TMP9R01 SET test setup was combined with other devices to multitask and only the TMP9R01 data is presented in this report.




Figure 5-6. TMP9R01 SET PCB Layout




Figure 5-7. TMP9R01 SET Schematic




Figure 5-8. Full SET Test Setup

6 SEL Results

SEL detection is performed by monitoring the DUT supply current. An SEL event occurs when a device latches and the device current exceeds 600uA. During a latch up event, communication is interfered. A total of three devices were tested and verified at max temperature, max voltage, and at 50.5MeV radiation exposure. Depending on the state the device is in, the output quiescent current can change. The beam start time and end time was taken at different states of the device. The device was heated using forced hot air, maintaining the die temperature at 125°C. All devices where tested before and after SEL exposure to verify the performance of the device. [Table 6-1](#) below shows the details of each device passing with functional behavior after exposing.

6.1 TMP9R01-SEP SEL Data

Table 6-1. TMP9R01-SEP SEL Data

Lot #	Device / Bias	Run #	Pass/ Fail	Temp (°C) Thermo Camera	Distance (mm)	Ion	Initial Energy (MeV/nucleon)	Thetha Table Angle (°)	LETEFF (MeV·cm²/mg)	Target Flux (ions·cm²/s)	Fluence (# of ions·cm²)	VCM Clamp	VS (V)	VS clamp	Measured IS (mA) Before Beam	Measured IS (mA) Post Beam	Measured IS (mA) At Beam
MSU	2	3	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 3.3V	500mA	60-400uA	60-400uA	60-400uA
MSU	2	4	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 3.6V	500mA	60-400uA	60-400uA	60-400uA
MSU	2	5	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 1.7V	500mA	60-400uA	60-400uA	60-400uA
MSU	3	6	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 3.6V	500mA	60-400uA	60-400uA	60-400uA
MSU	3	7	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 3.3V	500mA	60-400uA	60-400uA	60-400uA
MSU	3	8	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1E+07	5mA	Vs1 = Vs2 = 1.7V	500mA	60-400uA	60-400uA	60-400uA
MSU	4	9	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1.5E+07	5mA	Vs1 = Vs2 = 3.6V	500mA	60-400uA	60-400uA	60-400uA
MSU	4	10	Pass	125C	70	Xe	50.4	0	50.4	1E+05	1.5E+07	5mA	Vs1 = Vs2 = 1.7V	500mA	60-400uA	60-400uA	60-400uA




Figure 6-1. Run Passing SEL Run 4, DUT #2, MSU, 125C, Xe (50.4MeV)




Figure 6-2. Run Passing SEL Run 7, DUT #3, MSU, 125C, Xe (50.4MeV)




Figure 6-3. Run Passing SEL Run 9, DUT #4, MSU, 125C, Xe (50.4MeV)

7 SET Results

Transient characterization data was captured while exposing the units to different levels of radiation. The cross-section plots were captured to provide information of the trend of how the device performs under radiation. During the exposure time, all I²C registers were continuously read. A device reset was taken before every read. The data collected in the registers and the alert pin signal was used to understand the complete functionality of the device and support the SET results presented in this report. Data captured in this report is labeled with reset or without resets.

TMP9R01 device supports reset using the two-wire general-call address 00h (0000 0000b). The TMP9R01 device acknowledges the general-call address and responds to the second byte. If the second byte is 06h (0000 0110b), the TMP9R01 device executes a software reset. This software reset restores the power-on reset state to all TMP9R01 registers and aborts any conversion in progress. The TMP9R01 device takes no action in response to other values in the second byte.




Figure 7-1. Reset Software Procedure

Data was read and captured every 50ms. With resets, the max time for the device to recover temperature is 50ms and no temperature value was seen to be stuck longer than 50ms during the exposure. The max time for the TMP461 to read all registers is shown in the following equation:

Where 36 is the number of clock cycles per communication cycle.


$$36 \times \text{clock period} \times \# \text{ of register reads} \quad (1)$$

Without resetting the device, there is a large chance the device performs poorly. TMP9R01 is a digital I²C device and transient/upset events were defined in the following way:



- A remote or local temperature output with an error larger than 1.5C was recorded as a transient. Temperature delta was between the temperature readings during exposure and before. Data was read through I²C SCL and SDA lines and recorded through excel. Local and remote temperature is read through two bytes: high and low byte. The high byte represents the whole portion of the temperature result while the low byte represents the fractional portion of the temperature results. The amount of changed bits and location impact the overall accuracy of the device. The changes in the configuration registers can also affect the accuracy of the temperature result. The bits within the following registers impact temperature accuracy as shown in Table 7-1:

Table 7-1. Registers Impacting Accuracy Events

Pointer (HEX)	Register Description	Potential Accuracy Errors	Event Type
R 00h	Local temperature Register (high byte)	Reading Incorrect Measurement	SET
R 15h	Local temperature Register (low byte)	Reading Incorrect Measurement	SET
R 01h	Remote Temperature Register (high byte)	Reading Incorrect Measurement	SET
R 10h	Remote Temperature Register (low byte)	Reading Incorrect Measurement	SET
R 03h W 09h	Configuration Register	Changing the range from [-40C, 127C] to [-60C, 191C]	SEFI
RW 11h	Remote Temperature Offset Register (high byte)	An unwanted temperature offset is set	SET
RW 12h	Remote Temperature Offset Register (low byte)	An unwanted temperature offset was set	SET
RW 16h	Channel Enable Register	Disabled the temperature conversion of remote and local temperature sensors leading to inaccurate readings	SEFI
RW 23h	η -Factor Correction Register	An unwanted n-Factor calibration was set	SET

**Figure 7-2. 12-bit Q4 Format**

- A SEFI was recorded when the alert/therm signal was tripped. The device was programmed with default settings to where the alert stays off. If the alert is tripped, the number of assurances is recorded. Operation of the ALERT (pin 7) and THERM (pin 4) interrupts is shown in Figure 7-3. Operation of the THERM (pin 4) and THERM2 (pin 7) interrupts is shown in Figure 7-4.

**Figure 7-3. Alert and Therm Interrupt Operation****Figure 7-4. Therm and Therm2 Interrupt Operation**

- Any bit that was changed within any of the I₂C registers outside of the temperature reading registers was recorded as an upset. These events test if any of the configuration settings was changed during exposure. All events are SEU events. No MBU events were present.

The bits within the following registers impact the alert/therm signal as shown in [Table 7-2](#).

Table 7-2. Registers Impacting Alert/Therm Events

Pointer (HEX)	Register Description	Potential Alert/Therm Errors	Event Type
R 02h	Status Register	Mismatch in Status of the Alert Signal	SEU
R 03h W 09h	Configuration Register	Unwanted mask of the alert signal and changing the mode from alert to therm	SEFI
R 05h W 0Bh	Local Temperature High Limit Register	Incorrect limit setting	SEFI
R 06h W 0Ch	Local Temperature Low Limit Register	Incorrect limit setting	SEFI
R 07h W 0Dh	Remote Temperature High Limit Register (high byte)	Incorrect limit setting	SEFI
RW 13h	Remote Temperature High Limit Register (low byte)	Incorrect limit setting	SEFI
R 08h W 0Eh	Remote Temperature Low Limit Register (high byte)	Incorrect limit setting	SEFI
RW 14h	Remote Temperature Low Limit Register (low byte)	Incorrect limit setting	SEFI
RW 19h	Remote Temperature THERM Limit Register	Incorrect limit setting	SEFI
RW 20h	Local Temperature THERM Limit Register	Incorrect limit setting	SEFI
RW 21h	THERM Hysteresis Register	Incorrect hysteresis setting	SEFI
RW 22h	Consecutive ALERT Register	Unwanted number of out-of-limit temperature measurements required for ALERT to be asserted	SEFI

A device reset was taken before every temperature read. All data captured in the report was taken with a temperature reset. *Data was read and captured every 50ms.* With resets, the max time for the device to recover temperature is 50ms and no temperature value was seen to be stuck longer than 50ms during the exposure. Without resetting the device, there is a large chance the device performs poorly. We have tested the results with and without resets and found that with resets the device preforms better.

The following table captures SET data with TMP9R01 in extended mode. Extended mode extends the temperature range to reach the range of -64C to 191C adding more bits to the temperature registers. The data below highlights the benefits of resetting the device before every temperature read.

Table 7-3. Data Comparing SET Results with Resets and No Resets

LetEFF (MeV)	# Events (Reset)	# Events (No Reset)
8.7	24	22
48	26	324
56.36	33	643

7.1 Summary of SET Results

Table 7-4. Summary of TMP9R01-SEP SET Results at 25C with Resets

Run #	Ion Type	Angle	LETEFF (MeV-cm ² /mg)	Flux (ions-cm ⁻² /s)	Fluence (# of ions-cm ⁻²)	VS (V)	Temp (C)	Delta (C)	Total # of Events	Local Channel Temp Delta Events	Local Upper Bound X-Section (cm ²)	Channel 1 Temp Delta Events	Channel 1 Upper Bound X-Section (cm ²)	Bit Flip Events	Bit Flip Upper Bound X-Section (cm ²)	Alert Trip Events	Alert Bound X-Section (cm ²)
1	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	25	1.5	88	36	5.08918E-0	62	8.20614E-0	66	9.82442E-0	19	2.54998E-0
2	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	25	1.5	105	46		6		103		6	
4	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	25	1.5	64	34	3.80529E-0	44	5.64149E-0	64	6.68363E-0	12	1.84525E-0
5	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	25	1.5	61	25		6		47		6	
1	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	25	1.5	66	45	4.5336E-06	47	5.91659E-0	41	4.92288E-0	--	---
2	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	25	1.5	61	27		50		38		6	
4	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	25	1.5	39	23	2.89604E-0	29	3.46627E-0	24	2.83859E-0	6	1.04808E-0
5	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	25	1.5	34	20		6		18		6	
1	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	25	1.5	3	2	5.83417E-0	0	4.38364E-0	1	5.83417E-0	--	---
2	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	25	1.5	4	3		7		4		7	
4	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	25	1.5	1	0	1.84444E-0	0	1.84444E-0	1	2.78582E-0	--	---
5	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	25	1.5	0	0		7		0		7	

Table 7-5. Summary of TMP9R01-SEP SET Results at 80C with Resets

Run #	Ion Type	Angle	LETEFF (MeV-cm ² /mg)	Flux (ions-cm ² /s)	Fluence (# of ions-cm ²)	VS (V)	Temp (C)	Delta (C)	Total # of Events	Local Channel Accuracy	Local Upper Bound X-Section (cm ²)	Channel 1 Accuracy	Channel 1 Upper Bound X-Section (cm ²)	Bit Flip	Bit Flip Upper Bound X-Section (cm ²)	Alert Trip	Alert Upper Bound X-Section (cm ²)
7	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	80	1.5	136	56	5.91659E-0	77	9.23237E-0	136	1.48921E-0	51	6.62899E-0
8	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	80	1.5	148	41		6		128		5	
10	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	80	1.5	200	35	3.86159E-0	183	1.8169E-05	85	9.71688E-0	17	3.01068E-0
11	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	80	1.5	166	25		6		82		6	
7	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	80	1.5	79	36	4.3662E-06	59	6.46493E-0	53	5.86162E-0	--	---
8	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	80	1.5	61	33		48		43		6	
10	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	80	1.5	44	15	2.6079E-06	39	4.75627E-0	24	3.40955E-0	17	2.31721E-0
11	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	80	1.5	42	23		37		28		6	
7	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	80	1.5	2	1	4.38364E-0	1	5.12079E-0	1	5.12079E-0	--	---
8	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	80	1.5	4	2		7		3		7	
10	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	80	1.5	0	0	1.84444E-0	0	1.84444E-0	0	1.84444E-0	--	---
11	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	80	1.5	0	0		7		0		7	

Table 7-6. Number of Bit Flips within Registers 25C

Run #	Ion Type	Angle	LETEFF MeV-cm ² /mg	Flux (ions-cm ⁻² s)	Fluence (# of ions-cm ²)	VS (V)	Temp (C)	Delta (C)	Config.	Remote Temp Offset (h)	Remote Temp Offset (l)	Ch. Enable	n-factor Correction	Local Temp High Limit	Local Temp Low Limit	Remote Temp High Limit (h)	Remote Temp Low Limit (low byte)	Remote Temp High Limit (low byte)	Remote Temp Low Limit (high byte)	Remote Temp THERM Limit	Local Temp THERM Limit	THERM Hysteresis	Consecutive ALERT
1	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	25	1.5	31	11	3	2	7	27	23	23	4	23	4	26	31	6	3
2	¹²⁹ Xe	0	50.5	1E5	1E7	1.7	25	1.5	37	15	5	2	14	35	33	37	4	37	3	32	35	6	2
4	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	25	1.5	35	3	2	1	4	26	31	33	0	33	1	26	28	0	1
5	¹²⁹ Xe	0	50.5	1E5	1E7	3.6	25	1.5	25	4	1	0	3	25	23	22	2	22	1	22	27	0	0
1	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	25	1.5	29	7	1	0	7	22	23	20	0	23	0	19	21	2	1
2	⁸⁴ Kr	0	35.4	1E5	1E7	1.7	25	1.5	21	12	2	2	9	14	18	16	2	17	2	14	15	3	1
4	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	25	1.5	18	2	0	0	2	16	15	12	0	12	1	11	12	0	0
5	⁸⁴ Kr	0	35.4	1E5	1E7	3.6	25	1.5	25	4	1	0	3	25	23	22	2	22	1	22	27	0	0
1	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	25	1.5	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
2	⁴⁰ Ar	0	7.9	1E5	1E7	1.7	25	1.5	3	0	0	0	0	3	3	3	0	3	0	3	3	0	0
4	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	25	1.5	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
5	⁴⁰ Ar	0	7.9	1E5	1E7	3.6	25	1.5	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Table 7-7. Number of Bit Flips within Registers 80C

Run #	Ion Type	Angle	LETEFF MeV-cm ² /mg	Flux (ions-cm ⁻² s)	Fluence (# of ions-cm ²)	VS (V)	Temp (C)	Delta (C)	Config.	Remote Temp Offset (h)	Remote Temp Offset (l)	Ch. Enable	n-factor Correction	Local Temp High Limit	Local Temp Low Limit	Remote Temp High Limit (h)	Remote Temp Low Limit (low byte)	Remote Temp High Limit (low byte)	Remote Temp Low Limit (high byte)	Remote Temp THERM Limit	Local Temp THERM Limit	THERM Hysteresis	Consecutive ALERT
7	¹²⁹ Xe	0	50.5	1E+05	1E+07	1.7	80	1.5	48	9	6	48	4	48	47	51	5	41	128	48	17	4	14
8	¹²⁹ Xe	0	50.5	1E+05	1E+07	1.7	80	1.5	47	18	4	2	10	48	40	48	8	39	7	45	47	17	5
10	¹²⁹ Xe	0	50.5	1E+05	1E+07	3.6	80	1.5	29	7	3	2	10	37	28	33	4	26	2	38	36	9	2
11	¹²⁹ Xe	0	50.5	1E+05	1E+07	3.6	80	1.5	24	7	3	1	7	26	26	29	2	21	3	31	28	4	3
7	⁸⁴ Kr	0	35.4	1E+05	1E+07	1.7	80	1.5	25	10	1	1	11	22	22	23	2	20	1	22	21	3	0
8	⁸⁴ Kr	0	35.4	1E+05	1E+07	1.7	80	1.5	27	8	2	0	8	20	22	14	0	17	1	14	13	2	1
10	⁸⁴ Kr	0	35.4	1E+05	1E+07	3.6	80	1.5	16	3	0	0	2	17	17	17	0	16	0	15	15	1	0
11	⁸⁴ Kr	0	35.4	1E+05	1E+07	3.6	80	1.5	23	3	0	0	1	17	17	17	0	17	0	16	16	1	0
7	⁴⁰ Ar	0	7.9	1E+05	1E+07	1.7	80	1.5	1	0	0	0	0	1	1	1	0	1	0	1	1	0	0
8	⁴⁰ Ar	0	7.9	1E+05	1E+07	1.7	80	1.5	2	0	0	0	0	2	2	2	0	2	0	2	2	0	0
10	⁴⁰ Ar	0	7.9	1E+05	1E+07	3.6	80	1.5	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
11	⁴⁰ Ar	0	7.9	1E+05	1E+07	3.6	80	1.5	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Table 7-8. 25C Register Bit Flip Cross Section Summary

	# of Events	Fluence	LB	Mean	UB
SEL 50 MeV V+1.5 Config	68	20000000	2.64023E-06	0.0000034	4.31031E-06
SEL 50 MeV V+1.5 Remote Temp Offset L	26	20000000	8.49203E-07	0.0000013	1.9048E-06
SEL 50 MeV V+1.5 Remote Temp Offset H	8	20000000	1.72692E-07	0.0000004	7.88159E-07
SEL 50 MeV V+1.5 Ch Enable	4	20000000	5.44933E-08	0.0000002	5.12079E-07
SEL 50 MeV V+1.5 N-Factor Correction	21	20000000	6.49967E-07	0.00000105	1.60504E-06
SEL 50 MeV V+1.5 Local Temp High Limit	62	20000000	2.37675E-06	0.0000031	3.97406E-06
SEL 50 MeV V+1.5 Local Temp Low Limit	56	20000000	2.11509E-06	0.0000028	3.63603E-06

Table 7-8. 25C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 50 MeV V+1.5 Remote Temp High Limit H	60	20000000	2.28932E-06	0.000003	3.86159E-06
SEL 50 MeV V+1.5 Remote Temp High Limit L	8	20000000	1.72692E-07	0.0000004	7.88159E-07
SEL 50 MeV V+1.5 Remote Temp Low Limit H	60	20000000	2.28932E-06	0.000003	3.86159E-06
SEL 50 MeV V+1.5 Remote Temp Low Limit L	7	20000000	1.40718E-07	0.00000035	7.21134E-07
SEL 50 MeV V+1.5 Remote Temp THERM Limit	58	20000000	2.20209E-06	0.0000029	3.74892E-06
SEL 50 MeV V+1.5 Local Temp THERM Limit	66	20000000	2.55222E-06	0.0000033	4.19841E-06
SEL 50 MeV V+1.5 Therm Hysteresis	12	20000000	3.10029E-07	0.0000006	1.04808E-06
SEL 50 MeV V+1.5 Consecutive ALERT	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 50 MeV V+3.6 Config	60	20000000	2.28932E-06	0.000003	3.86159E-06
SEL 50 MeV V+3.6 Remote Temp Offset L	7	20000000	1.40718E-07	0.00000035	7.21134E-07
SEL 50 MeV V+3.6 Remote Temp Offset H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 50 MeV V+3.6 Ch Enable	1	20000000	1.26589E-09	0.00000005	2.78582E-07
SEL 50 MeV V+3.6 N-Factor Correction	7	20000000	1.40718E-07	0.00000035	7.21134E-07
SEL 50 MeV V+3.6 Local Temp High Limit	51	20000000	1.89864E-06	0.00000255	3.35278E-06
SEL 50 MeV V+3.6 Local Temp Low Limit	54	20000000	2.02832E-06	0.0000027	3.52291E-06
SEL 50 MeV V+3.6 Remote Temp High Limit H	55	20000000	2.07168E-06	0.00000275	3.5795E-06
SEL 50 MeV V+3.6 Remote Temp High Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07

Table 7-8. 25C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 50 MeV V+3.6 Remote Temp Low Limit H	55	20000000	2.07168E-06	0.00000275	3.5795E-06
SEL 50 MeV V+3.6 Remote Temp Low Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 50 MeV V+3.6 Remote Temp THERM Limit	48	20000000	1.76957E-06	0.0000024	3.18205E-06
SEL 50 MeV V+3.6 Local Temp THERM Limit	55	20000000	2.07168E-06	0.00000275	3.5795E-06
SEL 50 MeV V+3.6 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 50 MeV V+3.6 Consecutive ALERT	1	20000000	1.26589E-09	0.00000005	2.78582E-07
SEL 35.4 MeV V+1.5 Config	50	20000000	1.85555E-06	0.0000025	3.29594E-06
SEL 35.4 MeV V+1.5 Remote Temp Offset L	19	20000000	5.71962E-07	0.00000095	1.48354E-06
SEL 35.4 MeV V+1.5 Remote Temp Offset H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 35.4 MeV V+1.5 Ch Enable	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+1.5 N-Factor Correction	16	20000000	4.57269E-07	0.0000008	1.29915E-06
SEL 35.4 MeV V+1.5 Local Temp High Limit	36	20000000	1.2607E-06	0.0000018	2.49196E-06
SEL 35.4 MeV V+1.5 Local Temp Low Limit	41	20000000	1.47112E-06	0.00000205	2.78106E-06
SEL 35.4 MeV V+1.5 Remote Temp High Limit H	36	20000000	1.2607E-06	0.0000018	2.49196E-06
SEL 35.4 MeV V+1.5 Remote Temp High Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+1.5 Remote Temp Low Limit H	40	20000000	1.42883E-06	0.000002	2.72343E-06
SEL 35.4 MeV V+1.5 Remote Temp Low Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07

Table 7-8. 25C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 35.4 MeV V+1.5 Remote Temp THERM Limit	33	20000000	1.13578E-06	0.00000165	2.31721E-06
SEL 35.4 MeV V+1.5 Local Temp THERM Limit	36	20000000	1.2607E-06	0.0000018	2.49196E-06
SEL 35.4 MeV V+1.5 Therm Hysteresis	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 35.4 MeV V+1.5 Consecutive ALERT	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+3.6 Config	43	20000000	1.55597E-06	0.00000215	2.89604E-06
SEL 35.4 MeV V+3.6 Remote Temp Offset L	6	20000000	1.10095E-07	0.0000003	6.52974E-07
SEL 35.4 MeV V+3.6 Remote Temp Offset H	1	20000000	1.26589E-09	0.00000005	2.78582E-07
SEL 35.4 MeV V+3.6 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 N-Factor Correction	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 35.4 MeV V+3.6 Local Temp High Limit	41	20000000	1.47112E-06	0.00000205	2.78106E-06
SEL 35.4 MeV V+3.6 Local Temp Low Limit	38	20000000	1.34455E-06	0.0000019	2.6079E-06
SEL 35.4 MeV V+3.6 Remote Temp High Limit H	34	20000000	1.1773E-06	0.0000017	2.37558E-06
SEL 35.4 MeV V+3.6 Remote Temp High Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+3.6 Remote Temp Low Limit H	34	20000000	1.1773E-06	0.0000017	2.37558E-06
SEL 35.4 MeV V+3.6 Remote Temp Low Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+3.6 Remote Temp THERM Limit	33	20000000	1.13578E-06	0.00000165	2.31721E-06
SEL 35.4 MeV V+3.6 Local Temp THERM Limit	39	20000000	1.38664E-06	0.00000195	2.66571E-06

Table 7-8. 25C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 35.4 MeV V+3.6 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 Consecutive ALERT	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Config	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp Offset L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp Offset H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 N-Factor Correction	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Local Temp High Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Local Temp Low Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp High Limit H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp High Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp Low Limit H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp Low Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp THERM Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Local Temp THERM Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Consecutive ALERT	0	20000000	0	0	1.84444E-07

Table 7-8. 25C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 7.9 MeV V+3.6 Config	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Offset L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Offset H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 N-Factor Correction	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp High Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp Low Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp High Limit H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp High Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Low Limit H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Low Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp THERM Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp THERM Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Consecutive ALERT	0	20000000	0	0	1.84444E-07

Table 7-9. 80C Register Bit Flip Cross Section Summary

	# of Events	Fluence	LB	Mean	UB
SEL 50 MeV V+1.5 Config	95	20000000	3.84303E-06	0.00000475	5.80663E-06
SEL 50 MeV V+1.5 Remote Temp Offset L	27	20000000	8.89659E-07	0.00000135	1.96418E-06
SEL 50 MeV V+1.5 Remote Temp Offset H	10	20000000	2.39769E-07	0.0000005	9.19518E-07
SEL 50 MeV V+1.5 Ch Enable	50	20000000	1.85555E-06	0.0000025	3.29594E-06
SEL 50 MeV V+1.5 N-Factor Correction	14	20000000	3.82697E-07	0.0000007	1.17448E-06
SEL 50 MeV V+1.5 Local Temp High Limit	96	20000000	3.88802E-06	0.0000048	5.86162E-06
SEL 50 MeV V+1.5 Local Temp Low Limit	87	20000000	3.48417E-06	0.00000435	5.36571E-06
SEL 50 MeV V+1.5 Remote Temp High Limit H	99	20000000	4.02312E-06	0.00000495	6.02645E-06
SEL 50 MeV V+1.5 Remote Temp High Limit L	13	20000000	3.46098E-07	0.00000065	1.11152E-06
SEL 50 MeV V+1.5 Remote Temp Low Limit H	80	20000000	3.17175E-06	0.000004	4.97835E-06
SEL 50 MeV V+1.5 Remote Temp Low Limit L	135	20000000	5.65944E-06	0.00000675	7.98944E-06
SEL 50 MeV V+1.5 Remote Temp THERM Limit	93	20000000	3.75315E-06	0.00000465	5.69656E-06
SEL 50 MeV V+1.5 Local Temp THERM Limit	64	20000000	2.46439E-06	0.0000032	4.08633E-06
SEL 50 MeV V+1.5 Therm Hysteresis	21	20000000	6.49967E-07	0.00000105	1.60504E-06
SEL 50 MeV V+1.5 Consecutive ALERT	19	20000000	5.71962E-07	0.00000095	1.48354E-06
SEL 50 MeV V+3.6 Config	53	20000000	1.98503E-06	0.00000265	3.46627E-06
SEL 50 MeV V+3.6 Remote Temp Offset L	14	20000000	3.82697E-07	0.0000007	1.17448E-06

Table 7-9. 80C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 50 MeV V+3.6 Remote Temp Offset H	6	20000000	1.10095E-07	0.0000003	6.52974E-07
SEL 50 MeV V+3.6 Ch Enable	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 50 MeV V+3.6 N-Factor Correction	17	20000000	4.95156E-07	0.00000085	1.36093E-06
SEL 50 MeV V+3.6 Local Temp High Limit	63	20000000	2.42055E-06	0.00000315	4.03022E-06
SEL 50 MeV V+3.6 Local Temp Low Limit	54	20000000	2.02832E-06	0.0000027	3.52291E-06
SEL 50 MeV V+3.6 Remote Temp High Limit H	62	20000000	2.37675E-06	0.0000031	3.97406E-06
SEL 50 MeV V+3.6 Remote Temp High Limit L	6	20000000	1.10095E-07	0.0000003	6.52974E-07
SEL 50 MeV V+3.6 Remote Temp Low Limit H	47	20000000	1.72669E-06	0.00000235	3.125E-06
SEL 50 MeV V+3.6 Remote Temp Low Limit L	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 50 MeV V+3.6 Remote Temp THERM Limit	69	20000000	2.68431E-06	0.00000345	4.3662E-06
SEL 50 MeV V+3.6 Local Temp THERM Limit	64	20000000	2.46439E-06	0.0000032	4.08633E-06
SEL 50 MeV V+3.6 Therm Hysteresis	13	20000000	3.46098E-07	0.00000065	1.11152E-06
SEL 50 MeV V+3.6 Consecutive ALERT	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 35.4 MeV V+1.5 Config	52	20000000	1.9418E-06	0.0000026	3.40955E-06
SEL 35.4 MeV V+1.5 Remote Temp Offset L	18	20000000	5.33397E-07	0.0000009	1.42239E-06
SEL 35.4 MeV V+1.5 Remote Temp Offset H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 35.4 MeV V+1.5 Ch Enable	1	20000000	1.26589E-09	0.00000005	2.78582E-07

Table 7-9. 80C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 35.4 MeV V+1.5 N-Factor Correction	19	20000000	5.71962E-07	0.00000095	1.48354E-06
SEL 35.4 MeV V+1.5 Local Temp High Limit	42	20000000	1.5135E-06	0.0000021	2.83859E-06
SEL 35.4 MeV V+1.5 Local Temp Low Limit	44	20000000	1.59852E-06	0.0000022	2.9534E-06
SEL 35.4 MeV V+1.5 Remote Temp High Limit H	37	20000000	1.30257E-06	0.00000185	2.54998E-06
SEL 35.4 MeV V+1.5 Remote Temp High Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+1.5 Remote Temp Low Limit H	37	20000000	1.30257E-06	0.00000185	2.54998E-06
SEL 35.4 MeV V+1.5 Remote Temp Low Limit L	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+1.5 Remote Temp THERM Limit	36	20000000	1.2607E-06	0.0000018	2.49196E-06
SEL 35.4 MeV V+1.5 Local Temp THERM Limit	34	20000000	1.1773E-06	0.0000017	2.37558E-06
SEL 35.4 MeV V+1.5 Therm Hysteresis	5	20000000	8.11743E-08	0.00000025	5.83417E-07
SEL 35.4 MeV V+1.5 Consecutive ALERT	1	20000000	1.26589E-09	0.00000005	2.78582E-07
SEL 35.4 MeV V+3.6 Config	39	20000000	1.38664E-06	0.00000195	2.66571E-06
SEL 35.4 MeV V+3.6 Remote Temp Offset L	6	20000000	1.10095E-07	0.0000003	6.52974E-07
SEL 35.4 MeV V+3.6 Remote Temp Offset H	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 N-Factor Correction	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 35.4 MeV V+3.6 Local Temp High Limit	34	20000000	1.1773E-06	0.0000017	2.37558E-06

Table 7-9. 80C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 35.4 MeV V+3.6 Local Temp Low Limit	34	20000000	1.1773E-06	0.0000017	2.37558E-06
SEL 35.4 MeV V+3.6 Remote Temp High Limit H	34	20000000	1.1773E-06	0.0000017	2.37558E-06
SEL 35.4 MeV V+3.6 Remote Temp High Limit L	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 Remote Temp Low Limit H	33	20000000	1.13578E-06	0.00000165	2.31721E-06
SEL 35.4 MeV V+3.6 Remote Temp Low Limit L	0	20000000	0	0	1.84444E-07
SEL 35.4 MeV V+3.6 Remote Temp THERM Limit	31	20000000	1.05315E-06	0.00000155	2.2001E-06
SEL 35.4 MeV V+3.6 Local Temp THERM Limit	31	20000000	1.05315E-06	0.00000155	2.2001E-06
SEL 35.4 MeV V+3.6 Therm Hysteresis	2	20000000	1.21105E-08	0.0000001	3.61234E-07
SEL 35.4 MeV V+3.6 Consecutive ALERT	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Config	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp Offset L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp Offset H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 N-Factor Correction	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Local Temp High Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Local Temp Low Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp High Limit H	3	20000000	3.09336E-08	0.00000015	4.38364E-07

Table 7-9. 80C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 7.9 MeV V+1.5 Remote Temp High Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp Low Limit H	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Remote Temp Low Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Remote Temp THERM Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Local Temp THERM Limit	3	20000000	3.09336E-08	0.00000015	4.38364E-07
SEL 7.9 MeV V+1.5 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+1.5 Consecutive ALERT	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Config	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Offset L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Offset H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Ch Enable	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 N-Factor Correction	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp High Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp Low Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp High Limit H	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp High Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp Low Limit H	0	20000000	0	0	1.84444E-07

Table 7-9. 80C Register Bit Flip Cross Section Summary (continued)

	# of Events	Fluence	LB	Mean	UB
SEL 7.9 MeV V+3.6 Remote Temp Low Limit L	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Remote Temp THERM Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Local Temp THERM Limit	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Therm Hysteresis	0	20000000	0	0	1.84444E-07
SEL 7.9 MeV V+3.6 Consecutive ALERT	0	20000000	0	0	1.84444E-07

7.1.1 Local Temperature Reads

Figure 7-5 and Figure 7-6 highlight a histogram of local temperature reads during the exposure. This reports only highlights the performance of the local TMP9R01 die hence, only the local histogram information is provided. Only temperature results with a recorded transient were reported in the following plots. You can expect higher numbers of good temperature measurements.

Local Temperature Distribution at Room Temperature




Figure 7-5. TMP9R01 Temperature Reads During 50.5MeV Exposure

Local Temperature Distribution at 80C




Figure 7-6. TMP9R01 Temperature Reads During 50.5MeV Exposure

7.1.1.1 Analog Alert Captures

Scope shots of the alert signal were captured during the exposure. There were 4 common transient captures. The following captures shown below was captured with no resets to highlight to worse case with the alert signal.

- 1) The alert signal can directly switch from off to on.




Figure 7-7. Possible Alert Signal Trip During Exposure

- 2) The alert signal can gradually ramp down with a 0.03ms changing period.




Figure 7-8. Possible Alert Signal Trip During Exposure

3) This plot highlights the recovery of an event.

TMP9R01 Analog Alert Event #3, Run #3




Figure 7-9. Possible Alert Signal Trip During Exposure

4) This plot highlights the largest voltage drop captured during exposure.

TMP9R01 Analog Alert Event #1, Run #7




Figure 7-10. Possible Alert Signal Trip During Exposure

7.2 Cross Section Events and Event Rate Calculations

Event rates were calculated for LEO (ISS) and GEO environments by combining CREME96 orbital integral flux estimations. The Event Rate Calculations was calculated using the upper bound cross section.




Figure 7-11. Weibull Plot for Local Temperature Accuracy Events




Figure 7-12. Weibull Plot for Remote Temperature Accuracy Events

Bit Flip Cross Section vs LET




Figure 7-13. Weibull Plot for Bit Flip Events

Alert Trip Cross Section vs LET




Figure 7-14. Weibull Plot for Alert Trip Events

Table 7-10. 25C SET Event Rate Calculations for Worst-Week LEO and GEO Orbits

Local 1.7V 25C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	5.09E-06	0.000280613	11692.21528	9.763333749
GEO		465.6507132		0.002369781	98740.86619	1.156106933
Local 3.6V 25C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	3.81E-06	0.00020982	8742.509198	13.0574641
GEO		465.6507132		0.001771934	73830.57107	1.546175227
Channel-1 1.7V 25C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	8.21E-06	0.00045248	18853.31463	6.054903461
GEO		465.6507132		0.003821194	159216.4165	0.716980086
Channel-1 3.6V 25C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	5.64E-06	0.000311067	12961.12952	8.80748856
GEO		465.6507132		0.002626965	109456.8588	1.04292231

Table 7-11. 80C SET Event Rate Calculations for Worst-Week LEO and GEO Orbits

Local 1.7V 80C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	5.91659E-06	0.000326236	13593.15536	8.397976556
GEO		465.6507132		0.002755064	114794.3228	0.994430711
Local 3.6V 80C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	3.86159E-06	0.000212925	8871.878537	12.86706074
GEO		465.6507132		0.001798154	74923.09634	1.523628969
Channel-1 1.7V 80C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	9.23237E-06	0.000509065	21211.03633	5.381868109
GEO		465.6507132		0.004299058	179127.3981	0.637283862
Channel-1 3.6V 80C						
Orbit Type	Onset LETeff	CREME96 Integral FLUX	Cross-Saturation	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO	7.9	55.13915962	1.8169E-05	0.001001823	41742.61217	2.734735419
GEO		465.6507132		0.008460402	352516.746	0.323828588

8 Detailed Results Per Run

The data that was captured per run is listed below. Only Events that were considered transients were captured.

- *Elapsed Time (s)*: Total Time of Run
- *Initial Local (C)*: Local Temperature of DUT without radiation exposure before run
- *Initial Remote (C)*: Remote Temperature of DUT without radiation exposure before run
- *Temp Delta Threshold (C)*: Set temperature error threshold to be considered an event for both local and remote channels
- *Current Local (C)*: Current local temperature during exposure
- *Current Remote (C)*: Current remote temperature during exposure
- *Number of Delta Events*: Number of events counted
- *Number of Reset Events*: Number of resets with general-call address
- *TMP119 Temp*: TMP119 was placed on the backside of the board for reference
- *Therm Pins*: Alert and THERM Pin signal captured during the exposure. Data came in as binary values indicating if the alert or THERM signal was turned on
- *Register Map*: Local Hi Byte (0x00), Remote Hi Byte (0x01), Status (0x02), Configuration (0x03), Conversion Rate (0x04), Local Hi Limit (0x05), Local Low Limit (0x06), Rem Hi Limit (0x07) , Rem Low Limit (0x08), Remote Low Byte (0x10), Rem Offset Hi Byte (0x11), Rem Offset Low Byte (0x12), Rem Hi Limit (0x13), Rem Low Limit (0x14), Local Low Byte (0x15), Channel Enable (0x16), Remote THERM Limit (0x19), Local THERM Limit (0x20), THERM Hysteresis (0x21), Consecutive ALERT (0x22), n-factor correction (0x23), Digital Filter (0x24), Manuf. ID (0xFE).

8.1 Detailed Run Raw Data

Table 8-1. Detailed Run Raw Data

Time (s)	Initial Local (C)	Initial Ch1 (C)	Temp (C)	Curre nt Local (C)	Curre nt Ch1 (C)	# Delta Event	# Reset Event	Ther m Pins	0x00	0x01	0x02	0x03	0x04	0x05	0x06	0x07	0x08	0x10	0x11	0x12	0x13	0x14	0x15	0x16	0x19	0x20	0x21	0x22	0x23	0x24	0xFE
0	21.37	21.93	1.5	21.37	21.93	0	0	4	85	85	128	36	8	200	0	200	0	224	0	0	240	0	96	3	200	200	10	1	0	0	85
0.10	21.37	21.93	1.5	21.37	22.31	1	1	4	85	86	0	36	8	200	0	200	0	80	0	0	240	0	96	3	200	200	10	1	0	0	85
10.18	21.37	21.93	1.5	21.37	21.75	2	97	4	85	85	0	36	8	200	0	200	0	192	0	0	240	0	96	3	200	200	10	1	0	0	85
20.21	21.37	21.93	1.5	21.31	21.75	3	193	4	85	85	0	36	8	200	0	200	0	192	0	0	240	0	80	3	200	200	10	1	0	0	85
30.04	21.37	21.93	1.5	149.4	21.5	4	287	4	213	85	0	36	8	200	0	200	0	128	0	0	240	0	96	3	200	200	10	1	0	0	85
30.22	21.37	21.93	1.5	21.37	22.06	5	288	4	85	86	0	36	8	200	0	200	0	16	0	0	240	0	112	3	200	200	10	1	0	0	85
36.73	21.37	21.93	1.5	136.4	21.62	6	350	4	85	85	0	36	8	200	0	200	0	160	0	0	240	0	112	3	200	200	10	1	0	0	85
40.22	21.37	21.93	1.5	21.5	21.81	7	383	4	85	85	0	36	8	200	0	200	0	208	0	0	240	0	128	3	200	200	10	1	0	0	85
50.23	21.37	21.93	1.5	21.5	21.81	8	479	4	85	85	0	36	8	200	0	200	0	208	0	0	240	0	128	3	200	200	10	1	0	0	85
60.29	21.37	21.93	1.5	21.37	21.93	9	575	4	85	85	0	36	8	200	0	200	0	240	0	0	240	0	96	3	200	200	10	1	0	0	85
70.32	21.37	21.93	1.5	21.37	22	10	671	4	85	86	0	36	8	200	0	200	0	0	0	0	240	0	96	3	200	200	10	1	0	0	85
80.35	21.37	21.93	1.5	21.31	21.81	11	767	4	85	85	0	36	8	200	0	200	0	208	0	0	240	0	64	3	200	200	10	1	0	0	85
90.40	21.37	21.93	1.5	21.37	21.56	12	863	4	85	85	0	36	8	200	0	200	0	144	0	0	240	0	96	3	200	200	10	1	0	0	85

9 Summary

This report summarizes all SEE data collected on the TMP9R01-SEP. This document provides the understanding of how the device performs under radiation. The data shows the TMP9R01-SEP is SEL free up to 50.5MeV. A SET study was done by monitoring the temperature readout of the remote and local channels and recording events greater than $\pm 1.5^{\circ}\text{C}$ from the initial recorded temperatures.

10 Glossary

Most of the definitions here below are from JEDEC standard JESD89A.

- **DUT:** Device under test.
- **Fluence** (of particle radiation incident on a surface): The total amount of particle radiant energy incident on a surface in a given period of time, divided by the area of the surface. In this document, Fluence is expressed in ions per cm².
- **Flux:** The time rate of flow of particle radiant energy incident on a surface, divided by the area of that surface. In this document, Flux is expressed in ions per cm²*s.
- **Single-Event Effect (SEE):** Any measurable or observable change in state or performance of a microelectronic device, component, subsystem, or system (digital or analog) resulting from a single energetic particle strike. Single-event effects include single-event upset (SEU), multiple-bit upset (MBU), multiple-cell upset (MCU), single-event functional interrupt (SEFI), single-event latch-up (SEL).
- **Single-Event Transient (SET):** A soft error caused by the transient signal induced by a single energetic particle strike.
- **Single-Event Latch-up (SEL):** An abnormal high-current state in a device caused by the passage of a single energetic particle through sensitive regions of the device structure and resulting in the loss of device functionality. SEL can cause permanent damage to the device. If the device is not permanently damaged, power cycling of the device (off and back on) is necessary to restore normal operation. An example of SEL in a CMOS device is when the passage of a single particle induces the creation of parasitic bipolar (p-n-p-n) shorting of power to ground. Single-Event Latch-up (SEL) cross-section: the number of events per unit fluence. For chip SEL cross-section, the dimensions are cm² per chip.
- **Error cross-section:** the number of errors per unit fluence. For device error cross-section, the dimensions are cm² per device. For bit error cross-section, the dimensions are cm² per bit.
- **Tilt angle:** tilt angle, rotation axis of the DUT board is perpendicular to the beam axis; roll angle, board rotation axis is parallel to the beam axis
- **Weibull Function:** $F(x) = A \left(1 - \exp\{-[(x-x_0)/W]s\}\right)$
 - x = effective LET in MeV-cm² /milligram;
 - F(x) = SEE cross-section in square-cm²/bit;
 - A = limiting or plateau cross-section;
 - x₀ = onset parameter, such that F(x) = 0 for x < x₀;
 - W = width parameter;
 - s = a dimensionless exponent

11 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (April 2025) to Revision B (June 2025)	Page
• Updated data in TMP9R01-SEP SEL Data table.....	12
• Removed SET calculation tables for bit flips and alert signals.....	16
• Added more description to how the data was collected and the timing.....	16
• Added 25C and 80C Register Bit Flip Cross Section Summary tables.....	16

Changes from Revision * (April 2025) to Revision A (April 2025)	Page
• Changed TMP9R01-SP to TMP9R01-SEP.....	44
• Changed 75MeV to 50.5MeV.....	44

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated