www.ti.com

LMP2231 Single Micropower, 1.6V, Precision Operational Amplifier with CMOS Inputs

Check for Samples: LMP2231

FEATURES

(For $V_S = 5V$, $T_A = 25$ °C, Typical Unless Otherwise Noted)

- Supply Current 10 μA
- Operating Voltage Range 1.6V to 5.5V
- TCV_{OS} (LMP2231A) ±0.4 μV/°C (max)
- TCV_{OS} (LMP2231B) ±2.5µV/°C (max)
- V_{os} ±150 μV (max)
- Input Bias Current 20 fA
- PSRR 120 dB
- CMRR 97 dB
- Open Loop Gain 120 dB
- Gain Bandwidth Product 130 kHz
- Slew Rate 58 V/ms
- Input Voltage Noise, f = 1 kHz 60 nV/√Hz
- Temperature Range -40°C to 125°C

APPLICATIONS

- Precision Instrumentation Amplifiers
- Battery Powered Medical Instrumentation
- High Impedance Sensors
- Strain Gauge Bridge Amplifier
- Thermocouple Amplifiers

DESCRIPTION

The LMP2231 is a single micropower precision amplifier designed for battery powered applications. The 1.6V to 5.5V operating supply voltage range and quiescent power consumption of only 16 μW extend the battery life in portable battery operated systems. The LMP2231 is part of the LMPTM precision amplifier family. The high impedance CMOS input makes it ideal for instrumentation and other sensor interface applications.

The LMP2231 has a maximum offset of 150 μ V and maximum offset voltage drift of only 0.4 μ V/°C along with low bias current of only ±20 fA. These precise specifications make the LMP2231 a great choice for maintaining system accuracy and long term stability.

The LMP2231 has a rail-to-rail output that swings 15 mV from the supply voltage, which increases system dynamic range. The common mode input voltage range extends 200 mV below the negative supply, thus the LMP2231 is ideal for use in single supply applications with ground sensing.

The LMP2231 is offered in 5-Pin SOT-23 and 8-pin SOIC packages.

The dual and quad versions of this product are also available. The dual, LMP2232 is offered in 8-pin SOIC and VSSOP. The quad, LMP2234 is offered in 14-pin SOIC and TSSOP.

MA.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

LMP is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.



Typical Application




Figure 1. Strain Gauge Bridge Amplifier



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

Absolute Maximum Ratings(1)(2)

ABOOIGIO Maxiillali		
ESD Tolerance (3)	Human Body Model	2000V
	Machine Model	100V
Differential Input Voltage	•	±300 mV
Supply Voltage (V _S = V ⁺ - '	V ⁻)	6V
Voltage on Input/Output Pi	ns	V ⁺ + 0.3V, V ⁻ – 0.3V
Storage Temperature Rang	ge	-65°C to 150°C
Junction Temperature (4)		150°C
For soldering specifications	s: see product folder at www.ti.com and http://www.ti.com/lit/S	NOA549.

- (1) Absolute Maximum Ratings indicate limits beyond which damage may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and test conditions, see the Electrical Characteristics.
- (2) If Military/Aerospace specified devices are required, please contact the TI Sales Office/ Distributors for availability and specifications.
- (3) Human Body Model, applicable std. MIL-STD-883, Method 3015.7. Machine Model, applicable std. JESD22-A115-A (ESD MM std. of JEDEC)Field-Induced Charge-Device Model, applicable std. JESD22-C101-C (ESD FICDM std. of JEDEC).
- (4) The maximum power dissipation is a function of T_{J(MAX)}, θ_{JA}. The maximum allowable power dissipation at any ambient temperature is P_D = (T_{J(MAX)} T_A)/ θ_{JA}. All numbers apply for packages soldered directly onto a PC Board.

Submit Documentation Feedback

www.ti.com

Operating Ratings⁽¹⁾

Operating Temperature Range (2)	Operating Temperature Range ⁽²⁾		
Supply Voltage $(V_S = V^+ - V^-)$		1.6V to 5.5V	
Package Thermal Resistance (θ _{JA}) ⁽²⁾	5-Pin SOT-23	160.6 °C/W	
	8-Pin SOIC	116.2 °C/W	

- (1) Absolute Maximum Ratings indicate limits beyond which damage may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and test conditions, see the Electrical Characteristics.
- (2) The maximum power dissipation is a function of $T_{J(MAX)}$, θ_{JA} . The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(MAX)} T_A)/\theta_{JA}$. All numbers apply for packages soldered directly onto a PC Board.

5V DC Electrical Characteristics⁽¹⁾

Unless otherwise specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 5V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
V _{OS}	Input Offset Voltage			±10	±150 ±230	μV
TCV _{OS}	Input Offset Voltage Drift	LMP2231A		±0.3	±0.4	μV/°C
		LMP2231B		±0.3	±2.5	
I _{BIAS}	Input Bias Current			0.02	±1 ±50	pA
Ios	Input Offset Current			5		fA
CMRR	Common Mode Rejection Ratio	$0V \le V_{CM} \le 4V$	81 80	97		dB
PSRR	Power Supply Rejection Ratio	$1.6V \le V^{+} \le 5.5V$ $V^{-} = 0V, V_{CM} = 0V$	83 83	120		dB
CMVR	Common Mode Voltage Range	CMRR ≥ 80 dB CMRR ≥ 79 dB	-0.2 - 0.2		4.2 4.2	V
A _{VOL}	Large Signal Voltage Gain	$V_O = 0.3V \text{ to } 4.7V$ $R_L = 10 \text{ k}\Omega \text{ to } V^+/2$	110 108	120		dB
Vo	Output Swing High	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = 100 \text{ mV}$		17	50 50	mV from either
	Output Swing Low	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = -100 \text{ mV}$		17	50 50	rail
I _O	Output Current (4)	Sourcing, V_O to V^- $V_{IN}(diff) = 100 \text{ mV}$	27 19	30		mA
		Sinking, V_O to V^+ $V_{IN}(diff) = -100 \text{ mV}$	17 12	22		
I _S	Supply Current			10	16 18	μΑ

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

(4) The short circuit test is a momentary open loop test.

⁽²⁾ All limits are specified by testing, statistical analysis or design.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.



5V AC Electrical Characteristics(1)

Unless otherwise specified, all limits ensured for $T_A = 25$ °C, $V^+ = 5V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions		Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
GBW	Gain-Bandwidth Product	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			130		kHz
SR	Slew Rate	A _V = +1 Falling Edge		33 32	58		\//
			Rising Edge	33 32	48		V/ms
θm	Phase Margin	C _L = 20 pF, R _L	= 10 kΩ		78		deg
G _m	Gain Margin	C _L = 20 pF, R _L	= 10 kΩ		27		dB
e _n	Input-Referred Voltage Noise Density	f = 1 kHz			60		nV/√ Hz
	Input-Referred Voltage Noise	0.1 Hz to 10 Hz			2.3		μV_{PP}
i _n	Input-Referred Current Noise	f = 1 kHz			10		fA/√ Hz
THD+N	Total Harmonic Distortion + Noise	f = 100 Hz, R _L =	= 10 kΩ		0.002		%

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

2) All limits are specified by testing, statistical analysis or design.

3.3V DC Electrical Characteristics(1)

Unless otherwise specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 3.3V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
V _{OS}	Input Offset Voltage			±10	±160 ±250	μV
TCV _{OS}	Input Offset Voltage Drift	LMP2231A		±0.3	±0.4	μV/°C
		LMP2231B		±0.3	±2.5	
I _{BIAS}	Input Bias Current			0.02	±1 ±50	pA
Ios	Input Offset Current			5		fA
CMRR	Common Mode Rejection Ratio	0V ≤ V _{CM} ≤ 2.3V	79 77	92		dB
PSRR	Power Supply Rejection Ratio	$1.6V \le V^+ \le 5.5V$ $V^- = 0V, V_{CM} = 0V$	83 83	120		dB
CMVR	Common Mode Voltage Range	CMRR ≥ 78 dB CMRR ≥ 77 dB	-0.2 - 0.2		2.5 2.5	V
A _{VOL}	Large Signal Voltage Gain	$V_{O} = 0.3V \text{ to } 3V$ $R_{L} = 10 \text{ k}\Omega \text{ to } V^{+}/2$	108 107	120		dB
Vo	Output Swing High	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = 100 \text{ mV}$		14	50 50	mV from either
	Output Swing Low	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = -100 \text{ mV}$		14	50 50	rail

2) All limits are specified by testing, statistical analysis or design.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.



3.3V DC Electrical Characteristics⁽¹⁾ (continued)

Unless otherwise specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 3.3V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
Io	Output Current (4)	Sourcing, V_O to V^- V_{IN} (diff) = 100 mV	11 8	14		mA
		Sinking, V_O to V^+ V_{IN} (diff) = -100 mV	8 5	11		
I _S	Supply Current			10	15 16	μA

⁽⁴⁾ The short circuit test is a momentary open loop test.

3.3V AC Electrical Characteristics(1)

Unless otherwise is specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 3.3V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions		Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
GBW	Gain-Bandwidth Product	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			128		kHz
SR	Slew Rate	$A_V = +1, C_L = 20 pF$	Falling Edge		58		V/ms
		$R_L = 10 \text{ k}\Omega$	Rising Edge		48		V/IIIS
θ _m	Phase Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			76		deg
G _m	Gain Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ I}$	ς Ω		26		dB
e _n	Input-Referred Voltage Noise Density	f = 1 kHz			60		nV/√ Hz
	Input-Referred Voltage Noise	0.1 Hz to 10 Hz			2.4		μV_{PP}
i _n	Input-Referred Current Noise	f = 1 kHz			10		fA/√Hz
THD+N	Total Harmonic Distortion + Noise	f = 100 Hz, R _L = 10 k	Ω		0.003		%

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

2.5V DC Electrical Characteristics⁽¹⁾

Unless otherwise specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 2.5V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1M\Omega$. Boldface limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
V _{OS}	Input Offset Voltage			±10	±190 ±275	μV
TCV _{OS}	Input Offset Voltage Drift	LMP2231A		±0.3	±0.4	//٥С
		LMP2231B		±0.3	±2.5	μV/°C
I _{BIAS}	Input Bias Current			0.02	±1.0 ± 50	pA
los	Input Offset Current			5		fA
CMRR	Common Mode Rejection Ratio	$0V \le V_{CM} \le 1.5V$	77 76	91		dB

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

⁽²⁾ All limits are specified by testing, statistical analysis or design.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.

⁽²⁾ All limits are specified by testing, statistical analysis or design.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.



2.5V DC Electrical Characteristics⁽¹⁾ (continued)

Unless otherwise specified, all limits ensured for $T_A = 25$ °C, $V^+ = 2.5$ V, $V^- = 0$ V, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
PSRR	Power Supply Rejection Ratio	$1.6V \le V^{+} \le 5.5V$ $V^{-} = 0V, V_{CM} = 0V$	83 83	120		dB
CMVR	Common Mode Voltage Range	CMRR ≥ 77 dB CMRR ≥ 76 dB	-0.2 - 0.2		1.7 1.7	V
A _{VOL}	Large Signal Voltage Gain	$V_{O} = 0.3V$ to 2.2V $R_{L} = 10 \text{ k}\Omega$ to $V^{+}/2$	104 104	120		dB
Vo	Output Swing High	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = 100 \text{ mV}$		12	50 50	mV
	Output Swing Low	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN} \text{ (diff)} = -100 \text{ mV}$		13	50 50	from either rail
Io	Output Current (4)	Sourcing, V_O to V^- V_{IN} (diff) = 100 mV	5 4	8		A
		Sinking, V_O to V^+ V_{IN} (diff) = -100 mV	3.5 2.5	7		- mA
I _S	Supply Current			10	14 15	μΑ

⁽⁴⁾ The short circuit test is a momentary open loop test.

2.5V AC Electrical Characteristics(1)

Unless otherwise specified, all limits ensured for $T_A = 25$ °C, $V^+ = 2.5$ V, $V^- = 0$ V, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions		Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
GBW	Gain-Bandwidth Product	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			128		kHz
SR	Slew Rate			58		V/ms	
			Rising Edge		48		V/IIIS
θ _m	Phase Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			74		deg
G _m	Gain Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ kg}$	Ω		26		dB
e _n	Input-Referred Voltage Noise Density	f = 1 kHz			60		nV/√ Hz
	Input-Referred Voltage Noise	0.1 Hz to 10 Hz			2.5		μV_{PP}
i _n	Input-Referred Current Noise	f = 1 kHz			10		fA/√Hz
THD+N	Total Harmonic Distortion + Noise	f = 100 Hz, R _L = 10 kg)		0.005		%

⁽¹⁾ Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.

(2) All limits are specified by testing, statistical analysis or design.

⁽³⁾ Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.



1.8V DC Electrical Characteristics (1)

Unless otherwise specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 1.8V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
V _{OS}	Input Offset Voltage			±10	±230 ±325	μV
TCV _{OS}	Input Offset Voltage Drift	LMP2231A		±0.3	±0.4	\//00
		LMP2231B		±0.3	±2.5	μV/°C
I _{BIAS}	Input Bias Current			0.02	±1.0 ±50	pA
I _{OS}	Input Offset Current			5		fA
CMRR	Common Mode Rejection Ratio	$0V \le V_{CM} \le 0.8V$	76 75	92		dB
PSRR	Power Supply Rejection Ratio	$1.6V \le V^+ \le 5.5V$ $V^- = 0V, V_{CM} = 0V$	83 83	120		dB
CMVR	Common Mode Voltage Rang	CMRR ≥ 76 dB CMRR ≥ 75 dB	-0.2 0		1.0 1.0	V
A _{VOL}	Large Signal Voltage Gain	$V_O = 0.3V$ to 1.5V $R_L = 10 \text{ k}\Omega$ to $V^+/2$	103 103	120		dB
Vo	Output Swing High	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = 100 \text{ mV}$		12	50 50	mV from either
	Output Swing Low	$R_L = 10 \text{ k}\Omega \text{ to V}^+/2$ $V_{IN}(\text{diff}) = -100 \text{ mV}$		13	50 50	rail
Io	Output Current (4)	Sourcing, V _O to V ⁻ V _{IN} (diff) = 100 mV	2.5 2	5		mA
		Sinking, V_O to V^+ V_{IN} (diff) = -100 mV	2 1.5	5		
Is	Supply Current			10	14 15	μA

- (1) Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.
- (2) All limits are specified by testing, statistical analysis or design.
- (3) Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.
- (4) The short circuit test is a momentary open loop test.

1.8V AC Electrical Characteristics(1)

Unless otherwise is specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 1.8V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions		Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
GBW	Gain-Bandwidth Product	$C_L = 20 \text{ pF}, R_L = 10 \text{ k}\Omega$			127		kHz
SR	Slew Rate	A _V = +1, C _L = 20 pF Falling Edge			58		V/ms
		$R_L = 10 \text{ k}\Omega$	Rising Edge		48		v/ms
θ _m	Phase Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ I}$	kΩ		70		deg
G_{m}	Gain Margin	$C_L = 20 \text{ pF}, R_L = 10 \text{ I}$	kΩ		25		dB
e _n	Input-Referred Voltage Noise Density	f = 1 kHz			60		nV/√ Hz
	Input-Referred Voltage Noise	0.1 Hz to 10 Hz			2.4		μV_{PP}

- (1) Electrical Table values apply only for factory testing conditions at the temperature indicated. Factory testing conditions result in very limited self-heating of the device such that T_J = T_A. No ensured specification of parametric performance is indicated in the electrical tables under conditions of internal self-heating where T_J > T_A. Absolute Maximum Ratings indicate junction temperature limits beyond which the device may be permanently degraded, either mechanically or electrically.
- (2) All limits are specified by testing, statistical analysis or design.
- (3) Typical values represent the most likely parametric norm at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not ensured on shipped production material.



1.8V AC Electrical Characteristics⁽¹⁾ (continued)

Unless otherwise is specified, all limits ensured for $T_A = 25^{\circ}C$, $V^+ = 1.8V$, $V^- = 0V$, $V_{CM} = V_O = V^+/2$, and $R_L > 1$ M Ω . **Boldface** limits apply at the temperature extremes.

Symbol	Parameter	Conditions	Min ⁽²⁾	Typ ⁽³⁾	Max ⁽²⁾	Units
i _n	Input-Referred Current Noise	f = 1 kHz		10		fA/√Hz
THD+N	Total Harmonic Distortion + Noise	$f = 100 \text{ Hz}, R_L = 10 \text{ k}\Omega$		0.005		%

Connection Diagram




Figure 2. 5-Pin SOT-23 (Top View) See Package Number DBV0005A




Figure 3. 8-Pin SOIC (Top View) See Package Number D0008A



Typical Performance Characteristics

Unless otherwise Specified: T_A = 25°C, V_S = 5V, V_{CM} = $V_S/2$, where V_S = V⁺ - V⁻




Figure 4.





Figure 6.






Figure 5.




Figure 7.




Figure 9.



Unless otherwise Specified: $T_A = 25$ °C, $V_S = 5$ V, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$




Figure 10.




Figure 12.




Figure 14.




Figure 11.




Figure 13.




Figure 15.

Submit Documentation Feedback



Unless otherwise Specified: $T_A = 25$ °C, $V_S = 5$ V, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$




Figure 16.




Figure 18.




Figure 20.





Figure 17.



Time Domain Voltage Noise




Figure 21.



Unless otherwise Specified: $T_A = 25$ °C, $V_S = 5$ V, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$




Figure 22.





Figure 24.






Figure 23.




Figure 25.




Figure 27.



Unless otherwise Specified: $T_A = 25^{\circ}C$, $V_S = 5V$, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$





Figure 28.






Figure 29.





Figure 31.


Copyright © 2008–2013, Texas Instruments Incorporated



Unless otherwise Specified: $T_A = 25$ °C, $V_S = 5$ V, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$










Open Loop Frequency Response 100 75 90 50 60 PHASE (°) GAIN (dB) GAIN 25 30 0 R_L $= 10 k\Omega$ $C_{L} = 20 pF$ 11111111 -30 10 100 10k 100k FREQUENCY (Hz)

Figure 36.







Open Loop Frequency Response




Figure 37.

Submit Documentation Feedback



Unless otherwise Specified: $T_A = 25^{\circ}C$, $V_S = 5V$, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$




Figure 38.




Figure 40.




Figure 42.




Figure 39.




Figure 41.




Figure 43.



Unless otherwise Specified: $T_A = 25$ °C, $V_S = 5$ V, $V_{CM} = V_S/2$, where $V_S = V^+ - V^-$





Figure 44.



Small Signal Step Response $V_S = 5V$ $V_S = 5V$ $V_{IN} = 50 \text{ mVpp}$ f = 1 kHz $A_V = +10$ $C_L = 20 \text{ pF}$ $100 \text{ } \mu\text{s/DIV}$

Figure 45.




Figure 47.

Submit Documentation Feedback



APPLICATION INFORMATION

LMP2231

The LMP2231 is a single CMOS precision amplifier that offer low offset voltage and low offset voltage drift, and high gain while only consuming 10 µA of current per channel.

The LMP2231 is a micropower op amp, consuming only 10 μ A of current. Micropower op amps extend the run time of battery powered systems and reduce energy consumption in energy limited systems. The ensured supply voltage range of 1.8V to 5.0V along with the ultra-low supply current extend the battery run time in two ways. The extended ensured power supply voltage range of 1.8V to 5.0V enables the op amp to function when the battery voltage has depleted from its nominal value down to 1.8V. In addition, the lower power consumption increases the life of the battery.

The LMP2231 has an input referred offset voltage of only $\pm 150~\mu V$ maximum at room temperature. This offset is ensured to be less than $\pm 230~\mu V$ over temperature. This minimal offset voltage along with very low TCV_{OS} of only 0.3 $\mu V/^{\circ}$ C typical allows more accurate signal detection and amplification in precision applications.

The low input bias current of only ±20 fA gives the LMP2231 superiority for use in high impedance sensor applications. Bias Current of an amplifier flows through source resistance of the sensor and the voltage resulting from this current flow appears as a noise voltage on the input of the amplifier. The low input bias current enables the LMP2231 to interface with high impedance sensors while generating negligible voltage noise. Thus the LMP2231 provides better signal fidelity and a higher signal-to-noise ration when interfacing with high impedance sensors.

Texas Instruments is heavily committed to precision amplifiers and the market segment they serve. Technical support and extensive characterization data is available for sensitive applications or applications with a constrained error budget.

The operating supply voltage range of 1.8V to 5.5V over the extensive temperature range of −40°C to 125°C makes the LMP2231 an excellent choice for low voltage precision applications with extensive temperature requirements.

The LMP2231 is offered in the space saving 5-Pin SOT-23 and 8-pin SOIC package. These small packages are ideal solutions for area constrained PC boards and portable electronics.

TOTAL NOISE CONTRIBUTION

The LMP2231 has a very low input bias current, very low input current noise, and low input voltage noise for micropower amplifier. As a result, this amplifier makes a great choice for circuits with high impedance sensor applications.

Figure 48 shows the typical input noise of the LMP2231 as a function of source resistance where:

- e_n denotes the input referred voltage noise
- e_i is the voltage drop across source resistance due to input referred current noise or $e_i = R_S * i_n$
- et shows the thermal noise of the source resistance
- e_{ni} shows the total noise on the input.

Where:

$$e_{ni} = \sqrt{e_n^2 + e_i^2 + e_t^2}$$

The input current noise of the LMP2231 is so low that it will not become the dominant factor in the total noise unless source resistance exceeds 300 M Ω , which is an unrealistically high value. As is evident in Figure 48, at lower R $_S$ values, total noise is dominated by the amplifier's input voltage noise. Once R $_S$ is larger than a 100 k Ω , then the dominant noise factor becomes the thermal noise of R $_S$. As mentioned before, the current noise will not be the dominant noise factor for any practical application.






Figure 48. Total Input Noise

VOLTAGE NOISE REDUCTION

The LMP2231 has an input voltage noise of $60 \text{ nV/}\sqrt{\text{Hz}}$. While this value is very low for micropower amplifiers, this input voltage noise can be further reduced by placing N amplifiers in parallel as shown in Figure 49. The total voltage noise on the output of this circuit is divided by the square root of the number of amplifiers used in this parallel combination. This is because each individual amplifier acts as an independent noise source, and the average noise of independent sources is the quadrature sum of the independent sources divided by the number of sources. For N identical amplifiers, this means:

REDUCED INPUT VOLTAGE NOISE =
$$\frac{1}{N}\sqrt{e_{n1}^2+e_{n2}^2+\cdots+e_{nN}^2}$$

= $\frac{1}{N}\sqrt{Ne_n^2}=\frac{\sqrt{N}}{N}$ e_n
= $\frac{1}{\sqrt{N}}$ e_n

Figure 49 shows a schematic of this input voltage noise reduction circuit. Typical resistor values are: $R_G = 10\Omega$, $R_F = 1 \text{ k}\Omega$, and $R_O = 1 \text{ k}\Omega$.

Submit Documentation Feedback






Figure 49. Noise Reduction Circuit

PRECISION INSTRUMENTATION AMPLIFIER

Measurement of very small signals with an amplifier requires close attention to the input impedance of the amplifier, gain of the overall signal on the inputs, and the gain on each input of the amplifier. This is because the difference of the input signal on the two inputs is of the interest and the common signal is considered noise. A classic circuit implementation is an instrumentation amplifier. Instrumentation amplifiers have a finite, accurate, and stable gain. They also have extremely high input impedances and very low output impedances. Finally they have an extremely high CMRR so that the amplifier can only respond to the differential signal. A typical instrumentation amplifier is shown in Figure 50.




Figure 50. Instrumentation Amplifier

There are two stages in this amplifier. The last stage, output stage, is a differential amplifier. In an ideal case the two amplifiers of the first stage, input stage, would be set up as buffers to isolate the inputs. However they cannot be connected as followers because of mismatch of amplifiers. That is why there is a balancing resistor between the two. The product of the two stages of gain will give the gain of the instrumentation amplifier. Ideally, the CMRR should be infinite. However the output stage has a small non-zero common mode gain which results from resistor mismatch.



In the input stage of the circuit, current is the same across all resistors. This is due to the high input impedance and low input bias current of the LMP2231.

$$GIVEN: {}^{1}R_{1} = {}^{1}R_{11}$$
 (1)

By Ohm's Law:

$$V_{O1} - V_{O2} = (2R_1 + R_{11}) I_{R_{11}}$$

$$= (2a + 1) R_{11} \cdot I_{R_{11}}$$

$$= (2a + 1) V_{R_{11}}$$
(2)

However:

$$V_{R_{11}} = V_1 - V_2$$
 (3)

So we have:

$$V_{O1} - V_{O2} = (2a+1)(V_1 - V_2)$$
(4)

Now looking at the output of the instrumentation amplifier:

$$V_{O} = \frac{KR_{2}}{R_{2}} (V_{O2} - V_{O1})$$

$$= -K (V_{O1} - V_{O2})$$
(5)

Substituting from Equation 4:

$$V_O = -K (2a + 1) (V_1 - V_2)$$
 (6)

This shows the gain of the instrumentation amplifier to be:

$$-K(2a+1) \tag{7}$$

Typical values for this circuit can be obtained by setting: a = 12 and K= 4. This results in an overall gain of −100.

SINGLE SUPPLY STRAIN GAGE BRIDGE AMPLIFIER

Strain gauges are popular electrical elements used to measure force or pressure. Strain gauges are subjected to an unknown force which is measured as a the deflection on a previously calibrated scale. Pressure is often measured using the same technique; however this pressure needs to be converted into force using an appropriate transducer. Strain gauges are often resistors which are sensitive to pressure or to flexing. Sense resistor values range from tens of ohms to several hundred kilo ohms. The resistance change which is a result of applied force across the strain gauge might be 1% of its total value. An accurate and reliable system is needed to measure this small resistance change. Bridge configurations offer a reliable method for this measurement.

Bridge sensors are formed of four resistors, connected as a quadrilateral. A voltage source or a current source is used across one of the diagonals to excite the bridge while a voltage detector across the other diagonal measures the output voltage.

Bridges are mainly used as null circuits or to measure a differential voltages. Bridges will have no output voltage if the ratios of two adjacent resistor values are equal. This fact is used in null circuit measurements. These are particularly used in feedback systems which involve electrochemical elements or human interfaces. Null systems force an active resistor, such as a strain gauge, to balance the bridge by influencing the measured parameter.

Often in sensor applications at lease one of the resistors is a variable resistor, or a sensor. The deviation of this active element from its initial value is measured as an indication of change in the measured quantity. A change in output voltage represents the sensor value change. Since the sensor value change is often very small, the resulting output voltage is very small in magnitude as well. This requires an extensive and very precise amplification circuitry so that signal fidelity does not change after amplification.

Sensitivity of a bridge is the ratio of its maximum expected output change to the excitation voltage change.

20 Subn



Figure 51 (a) shows a typical bridge sensor and Figure 51(b) shows the bridge with four sensors. R in Figure 51(b) is the nominal value of the sense resistor and the deviations from R are proportional to the quantity being measured.




Figure 51. Bridge Sensor

Instrumentation amplifiers are great for interfacing with bridge sensors. Bridge sensors often sense a very small differential signal in the presence of a larger common mode voltage. Instrumentation amplifiers reject this common mode signal.

Figure 52 shows a strain gauge bridge amplifier. In this application the LMP2231 is used to buffer the LM4140's precision output voltage. The LM4140A is a precision voltage reference. The other three LMP2231s are used to form an instrumentation amplifier. This instrumentation amplifier uses the LMP2231's high CMRR and low V_{OS} and TCV_{OS} to accurately amplify the small differential signal generated by the output of the bridge sensor. This amplified signal is then fed into the ADC121S021 which is a 12-bit analog to digital converter. This circuit works on a single supply voltage of 5V.




Figure 52. Strain Gauge Bridge Amplifier

Submit Documentation Feedback



PORTABLE GAS DETECTION SENSOR

Gas sensors are used in many different industrial and medical applications. They generate a current which is proportional to the percentage of a particular gas sensed in an air sample. This current goes through a load resistor and the resulting voltage drop is measured. Depending on the sensed gas and sensitivity of the sensor, the output current can be in the order of tens of microamperes to a few milliamperes. Gas sensor datasheets often specify a recommended load resistor value or they suggest a range of load resistors to choose from.

Oxygen sensors are used when air quality or oxygen delivered to a patient needs to be monitored. Fresh air contains 20.9% oxygen. Air samples containing less than 18% oxygen are considered dangerous. Oxygen sensors are also used in industrial applications where the environment must lack oxygen. An example is when food is vacuum packed. There are two main categories of oxygen sensors, those which sense oxygen when it is abundantly present (i.e. in air or near an oxygen tank) and those which detect traces of oxygen in ppm.

Figure 53 shows a typical circuit used to amplify the output of an oxygen detector. The LMP2231 makes an excellent choice for this application as it only draws 10 μ A of current and operates on supply voltages down to 1.8V. This application detects oxygen in air. The oxygen sensor outputs a known current through the load resistor. This value changes with the amount of oxygen present in the air sample. Oxygen sensors usually recommend a particular load resistor value or specify a range of acceptable values for the load resistor. Oxygen sensors typically have a life of one to two years. The use of the micropower LMP2231 means minimal power usage by the op amp and it enhances the battery life. Depending on other components present in the circuit design, the battery could last for the entire life of the oxygen sensor. The precision specifications of the LMP2231, such as its very low offset voltage, low TCV_{OS}, low input bias current, low CMRR, and low PSRR are other factors which make the LMP2231 a great choice for this application.




Figure 53. Precision Oxygen Sensor





REVISION HISTORY

Changes from Revision D (March 2013) to Revision E						
•	Changed layout of National Data Sheet to TI format	2	2			

www.ti.com

11-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
LMP2231AMA/NOPB	Active	Production	SOIC (D) 8	95 TUBE	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMA/NOPB.A	Active	Production	SOIC (D) 8	95 TUBE	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMAE/NOPB	Active	Production	SOIC (D) 8	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMAE/NOPB.A	Active	Production	SOIC (D) 8	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMAX/NOPB	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMAX/NOPB.A	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31AMA
LMP2231AMAX/NOPB.B	Active	Production	SOIC (D) 8	2500 LARGE T&R	-	Call TI	Call TI	-40 to 125	
LMP2231AMF/NOPB	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMF/NOPB.A	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMFE/NOPB	Active	Production	SOT-23 (DBV) 5	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMFE/NOPB.A	Active	Production	SOT-23 (DBV) 5	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMFX/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMFX/NOPB.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5A
LMP2231AMFX/NOPB.B	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	
LMP2231BMA/NOPB	Active	Production	SOIC (D) 8	95 TUBE	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31BMA
LMP2231BMA/NOPB.A	Active	Production	SOIC (D) 8	95 TUBE	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31BMA
LMP2231BMAE/NOPB	Active	Production	SOIC (D) 8	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LMP22 31BMA
LMP2231BMAE/NOPB.A	Active	Production	SOIC (D) 8	250 SMALL T&R	Yes	SN	SN Level-1-260C-UNLIM		LMP22 31BMA
LMP2231BMF/NOPB	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B
LMP2231BMF/NOPB.A	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B
LMP2231BMF/NOPB.B	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	-	Call TI	Call TI	-40 to 125	
LMP2231BMFE/NOPB	Active	Production	SOT-23 (DBV) 5	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B

11-Nov-2025

www.ti.com

Orderable part number	derable part number Status		Package Pins	Package qty Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
LMP2231BMFE/NOPB.A	Active	Production	SOT-23 (DBV) 5	250 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B
LMP2231BMFE/NOPB.B	Active	Production	SOT-23 (DBV) 5	250 SMALL T&R	-	Call TI	Call TI	-40 to 125	
LMP2231BMFX/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B
LMP2231BMFX/NOPB.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	AL5B
LMP2231BMFX/NOPB.B	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	

⁽¹⁾ Status: For more details on status, see our product life cycle.

- (3) RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.
- (4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- (6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.



www.ti.com 5-Sep-2025

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LMP2231AMAE/NOPB	SOIC	D	8	250	177.8	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LMP2231AMAX/NOPB	SOIC	D	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LMP2231AMF/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LMP2231AMFE/NOPB	SOT-23	DBV	5	250	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LMP2231AMFX/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LMP2231BMAE/NOPB	SOIC	D	8	250	177.8	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LMP2231BMF/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LMP2231BMFE/NOPB	SOT-23	DBV	5	250	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LMP2231BMFX/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3



www.ti.com 5-Sep-2025



*All dimensions are nominal

7 ili dimensionis are nominal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LMP2231AMAE/NOPB	SOIC	D	8	250	208.0	191.0	35.0
LMP2231AMAX/NOPB	SOIC	D	8	2500	356.0	356.0	35.0
LMP2231AMF/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LMP2231AMFE/NOPB	SOT-23	DBV	5	250	208.0	191.0	35.0
LMP2231AMFX/NOPB	SOT-23	DBV	5	3000	208.0	191.0	35.0
LMP2231BMAE/NOPB	SOIC	D	8	250	208.0	191.0	35.0
LMP2231BMF/NOPB	SOT-23	DBV	5	1000	208.0	191.0	35.0
LMP2231BMFE/NOPB	SOT-23	DBV	5	250	208.0	191.0	35.0
LMP2231BMFX/NOPB	SOT-23	DBV	5	3000	208.0	191.0	35.0

PACKAGE MATERIALS INFORMATION

www.ti.com 5-Sep-2025

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
LMP2231AMA/NOPB	D	SOIC	8	95	495	8	4064	3.05
LMP2231AMA/NOPB.A	D	SOIC	8	95	495	8	4064	3.05
LMP2231BMA/NOPB	D	SOIC	8	95	495	8	4064	3.05
LMP2231BMA/NOPB.A	D	SOIC	8	95	495	8	4064	3.05



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025