







AMC1351 SBASAA8 - DECEMBER 2021

AMC1351 Precision, 5-V Input, Reinforced Isolated Amplifier

1 Features

Linear input voltage range: -0.25 V to 5 V

High input impedance: 1.25 M Ω (typ)

Fixed gain: 0.4 V/V

Low DC errors:

Offset error ±1.5 mV (max)

Offset drift: ±15 µV/°C (max)

Gain error: ±0.2% (max)

Gain drift: ±35 ppm/°C (max)

Nonlinearity ±0.02% (max)

Operation on high-side and low-side: 3.3 V or 5 V

High CMTI: 100 kV/µs (min)

Fail-safe output

Safety-related certifications:

 7070-V_{PK} reinforced isolation per DIN VDE V 0884-11: 2017-01

5000-V_{RMS} isolation for 1 minute per UL1577

Fully specified over the extended industrial temperature range: -40°C to +125°C

2 Applications

- Isolated DC voltage sensing in:
 - Motor drives
 - Frequency inverters
 - Solar inverters
 - Power supplies

3 Description

The AMC1351 is a precision, isolated amplifier with an output separated from the input circuitry by an isolation barrier that is highly resistant to magnetic interference. This barrier is certified to provide reinforced galvanic isolation of up to 5 kV_{RMS} according to VDE V 0884-11 and UL1577, and supports a working voltage of up to 1.5 kV_{RMS}.


The isolation barrier separates parts of the system that operate on different common-mode voltage levels and protects the low-voltage side from potentially harmful voltages and damage.

The high-impedance input of the AMC1351 is optimized for connection to high-impedance resistive dividers or other voltage signal sources with high output resistance. The excellent accuracy and low temperature drift supports accurate DC voltage sensing in DC/DC converters, frequency inverters, motor-drive, or other applications over the extended industrial temperature range from -40°C to +125°C.

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)		
AMC1351	SOIC (8)	5.85 mm × 7.50 mm		

For all available packages, see the orderable addendum at the end of the data sheet.



Typical Application



Table of Contents

1 Features	1	7.2 Functional Block Diagram	. 19
2 Applications	1	7.3 Feature Description	19
3 Description		7.4 Device Functional Modes	21
4 Revision History	2	8 Application and Implementation	. 22
5 Pin Configuration and Functions		8.1 Application Information	. 22
6 Specifications	4	8.2 Typical Application	. 22
6.1 Absolute Maximum Ratings	4	8.3 What To Do and What Not To Do	25
6.2 ESD Ratings	4	9 Power Supply Recommendations	26
6.3 Recommended Operating Conditions	4	10 Layout	27
6.4 Thermal Information	5	10.1 Layout Guidelines	. 27
6.5 Power Ratings	5	10.2 Layout Example	. 27
6.6 Insulation Specifications	6	11 Device and Documentation Support	28
6.7 Safety-Related Certifications	7	11.1 Documentation Support	. 28
6.8 Safety Limiting Values	7	11.2 Receiving Notification of Documentation Updates.	. 28
6.9 Electrical Characteristics	8	11.3 Support Resources	. 28
6.10 Switching Characteristics	10	11.4 Trademarks	. 28
6.11 Timing Diagram	10	11.5 Electrostatic Discharge Caution	. 28
6.12 Insulation Characteristics Curves	11	11.6 Glossary	. 28
6.13 Typical Characteristics	12	12 Mechanical, Packaging, and Orderable	
7 Detailed Description	19	Information	. 28
7.1 Overview	19		

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES
December 2021	*	Initial Release



5 Pin Configuration and Functions




Figure 5-1. DWV Package, 8-Pin SOIC (Top View)

Table 5-1. Pin Functions

	PIN	TYPE	DESCRIPTION		
NO.	NAME	ITPE	DESCRIPTION		
1	VDD1	High-side power	High-side power supply ⁽¹⁾		
2	IN	Analog input	Analog input		
3	GND1	High-side ground	igh-side analog ground reference for input amplifier. Connect to pin 4. Do not leave nconnected.		
4	GND1	High-side ground	High-side analog ground		
5	GND2	Low-side ground	Low-side analog ground		
6	OUTN	Analog output	Inverting analog output		
7	OUTP	Analog output	Noninverting analog output		
8	VDD2	Low-side power	Low-side power supply ⁽¹⁾		

⁽¹⁾ See the *Power Supply Recommendations* section for power-supply decoupling recommendations.



6 Specifications

6.1 Absolute Maximum Ratings

see(1)

		MIN	MAX	UNIT
Dower aupply voltage	High-side VDD1 to GND1	-0.3	6.5	\/
Power-supply voltage	Low-side VDD2 to GND2	-0.3	6.5	v
Analog input voltage	IN	-1	15	V
Analog output voltage	OUTP, OUTN	GND2 – 0.5	VDD2 + 0.5	V
Input current	Continuous, any pin except power-supply pins	-10	10	mA
Tomporatura	Junction, T _J		150	°C
Temperature	Storage, T _{stg}	-65	150	

⁽¹⁾ Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. *Absolute Maximum Ratings* do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime

6.2 ESD Ratings

				VALUE	UNIT
V		Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	V
V _{(E}	SD)	Lieurostatic discharge	Charged-device model (CDM), per per ANSI/ESDA/JEDEC JS-002 ⁽²⁾	±1000	v

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT	
POWER	SUPPLY				•		
VDD1	High-side power-supply	VDD1 to GND1	3	5	5.5	V	
VDD2	Low-side power-supply	VDD2 to GND2	3	3.3	5.5	V	
ANALOG	INPUT						
V _{Clipping}	Input voltage before clipping output			6.25		V	
V _{FSR}	Specified linear full-scale voltage		-0.25		5	V	
ANALOG	OUTPUT				•		
C	Capacitive load	On OUTP or OUTN to GND2			500	pF	
C _{LOAD}		OUTP to OUTN			250		
R _{LOAD}	Resistive load	On OUTP or OUTN to GND2		10	1	kΩ	
TEMPER	ATURE RANGE						
т	Operating ambient temperature		-55		125	°C	
IA	Specified ambient temperature		-40		125		

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated



6.4 Thermal Information

		AMC1351	
	THERMAL METRIC ⁽¹⁾	DWV (SOIC)	UNIT
		8 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	84.6	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	28.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	41.1	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	4.9	°C/W
ΨЈВ	Junction-to-board characterization parameter	39.1	°C/W
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	n/a	°C/W

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

6.5 Power Ratings

PARAMETER		TEST CONDITIONS	VALUE	UNIT
P _D	Maximum power dissipation (both sides)	VDD1 = VDD2 = 5.5 V	96	mW
Б	Maximum power dissipation (high-side)	VDD1 = 3.6 V	29	mW
P _{D1}		VDD1 = 5.5 V	51	
P _{D2}	Maximum power dissipation (low-side)	VDD2 = 3.6 V	26	m\\/
		VDD2 = 5.5 V	45	mW



6.6 Insulation Specifications

over operating ambient temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	VALUE	UNIT
GENER	AL			
CLR	External clearance ⁽¹⁾	Shortest pin-to-pin distance through air	≥ 8.5	mm
CPG	External creepage ⁽¹⁾	Shortest pin-to-pin distance across the package surface	≥ 8.5	mm
DTI	Distance through insulation	Minimum internal gap (internal clearance) of the double insulation	≥ 0.021	mm
CTI	Comparative tracking index	DIN EN 60112 (VDE 0303-11); IEC 60112	≥ 600	V
	Material group	According to IEC 60664-1	I	
	Overvoltage category	Rated mains voltage ≤ 600 V _{RMS}	I-IV	
	per IEC 60664-1	Rated mains voltage ≤ 1000 V _{RMS}	1-111	
DIN VD	E V 0884-11 (VDE V 0884-11): 2	017-01		<u> </u>
V _{IORM}	Maximum repetitive peak isolation voltage	At AC voltage	2120	V _{PK}
Violen	Maximum-rated isolation	At AC voltage (sine wave)	1500	V _{RMS}
V_{IOWM}	working voltage	At DC voltage	2120	V _{DC}
V _{IOTM}	Maximum transient isolation voltage	V _{TEST} = V _{IOTM} , t = 60 s (qualification test)	7070	V _{PK}
		V _{TEST} = 1.2 × V _{IOTM} , t = 1 s (100% production test)	8480	
V _{IOSM}	Maximum surge isolation voltage ⁽²⁾	Test method per IEC 60065, 1.2/50- μ s waveform, V_{TEST} = 1.6 × V_{IOSM} = 12800 V_{PK} (qualification)	8000	V _{PK}
	Apparent charge ⁽³⁾	Method a, after input/output safety test subgroups 2 and 3, $V_{\text{ini}} = V_{\text{IOTM}}, t_{\text{ini}} = 60 \text{ s}, V_{\text{pd(m)}} = 1.2 \times V_{\text{IORM}}, t_{\text{m}} = 10 \text{ s}$	≤ 5	
q _{pd}		Method a, after environmental tests subgroup 1, $V_{ini} = V_{IOTM}$, $t_{ini} = 60 \text{ s}$, $V_{pd(m)} = 1.6 \times V_{IORM}$, $t_{m} = 10 \text{ s}$	≤ 5	pC
		Method b1, at routine test (100% production) and preconditioning (type test), $V_{ini} = V_{IOTM}$, $t_{ini} = 1$ s, $V_{pd(m)} = 1.875$ × V_{IORM} , $t_m = 1$ s	≤ 5	
C _{IO}	Barrier capacitance, input to output ⁽⁴⁾	V _{IO} = 0.5 V _{PP} at 1 MHz	~1.5	pF
		V _{IO} = 500 V at T _A = 25°C	> 10 ¹²	
R _{IO}	Insulation resistance, input to output ⁽⁴⁾	V _{IO} = 500 V at 100°C ≤ T _A ≤ 125°C	> 10 ¹¹	Ω
	input to output	V _{IO} = 500 V at T _S = 150°C	> 10 ⁹	
	Pollution degree		2	
	Climatic category		55/125/21	
UL1577		· ·		1
V _{ISO}	Withstand isolation voltage	$V_{TEST} = V_{ISO} = 5000 \ V_{RMS}$ or 7071 V_{DC} , $t = 60 \ s$ (qualification), $V_{TEST} = 1.2 \times V_{ISO} = 6000 \ V_{RMS}$, $t = 1 \ s$ (100% production test)	5000	V _{RMS}

⁽¹⁾ Apply creepage and clearance requirements according to the specific equipment isolation standards of an application. Care must be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed circuit board (PCB) do not reduce this distance. Creepage and clearance on a PCB become equal in certain cases. Techniques such as inserting grooves, ribs, or both on a PCB are used to help increase these specifications.

⁽²⁾ Testing is carried out in air or oil to determine the intrinsic surge immunity of the isolation barrier.

⁽³⁾ Apparent charge is electrical discharge caused by a partial discharge (pd).

⁽⁴⁾ All pins on each side of the barrier are tied together, creating a two-pin device.



6.7 Safety-Related Certifications

VDE	UL
Certified according to DIN VDE V 0884-11 (VDE V 0884-11): 2017-01, DIN EN 60950-1 (VDE 0805 Teil 1): 2014-08, and DIN EN 60065 (VDE 0860): 2005-11	Recognized under 1577 component recognition
Reinforced insulation	Single protection
Certificate number: pending	File number: E181974

6.8 Safety Limiting Values

Safety limiting⁽¹⁾ intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to over-heat the die and damage the isolation barrier potentially leading to secondary system failures.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
	Safety input, output, or supply current	$R_{\theta,JA} = 84.6^{\circ}\text{C/W}, VDDx = 5.5 \text{ V},$ $T_J = 150^{\circ}\text{C}, T_A = 25^{\circ}\text{C}$			270	mΛ
IS	Salety Input, output, or supply current	$R_{\theta JA} = 84.6^{\circ}\text{C/W}, VDDx = 3.6 \text{ V},$ $T_J = 150^{\circ}\text{C}, T_A = 25^{\circ}\text{C}$			410	mA
Ps	Safety input, output, or total power	R _{θJA} = 84.6°C/W, T _J = 150°C, T _A = 25°C			1480	mW
T _S	Maximum safety temperature				150	°C

The maximum safety temperature, T_S , has the same value as the maximum junction temperature, T_J , specified for the device. The I_S and P_S parameters represent the safety current and safety power, respectively. Do not exceed the maximum limits of I_S and P_S. These limits vary with the ambient temperature, T_A.

The junction-to-air thermal resistance, $R_{\theta JA}$, in the *Thermal Information* table is that of a device installed on a high-K test board for leaded surface-mount packages. Use these equations to calculate the value for each parameter:

 $T_J = T_A + R_{\theta JA} \times P$, where P is the power dissipated in the device.

 $T_{J(max)} = T_S = T_A + R_{\theta JA} \times P_S$, where $T_{J(max)}$ is the maximum junction temperature. $P_S = I_S \times VDD_{max}$, where VDD_{max} is the maximum supply voltage for high-side and low-side.



6.9 Electrical Characteristics

minimum and maximum specifications apply from $T_A = -40^{\circ}\text{C}$ to +125°C, VDD1 = 3.0 V to 5.5 V, VDD2 = 3.0 V to 5.5 V, IN = -0.25 V to +5 V (unless otherwise noted); typical specifications are at $T_A = 25^{\circ}\text{C}$, VDD1 = 5 V, and VDD2 = 3.3 V

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
ANALOG	INPUT					
V _{OS}	Offset voltage ⁽²⁾	$T_A = 25^{\circ}\text{C}$, IN = GND1, 4.5 V \leq VDD1 \leq 5.5 V ⁽¹⁾	-1.5	±0.3	1.5	mV
• 05	Onest velage	$T_A = 25$ °C, IN = GND1, 3.0 V ≤ VDD1 ≤ 5.5 V ⁽³⁾	-2.5	-0.8	2.5	
ΔV _{OS}	Offset voltage long-term stability	10 years at T _A = 55°C		0 ⁽⁷⁾		mV
TCV _{OS}	Offset voltage thermal drift ⁽⁵⁾	IN = GND1	-15	±3	15	μV/°C
ΔTCV _{OS}	Offset voltage thermal drift long-term stability	10 years at T _A = 55°C, IN = GND1		0 ⁽⁷⁾		mV/°C
R _{IN}	Input resistance		1	1.25	1.5	МΩ
ΔR_{IN}	Input resistance long-term stability	10 years at T _A = 55°C		0 ⁽⁷⁾		ppm
TCR _{IN}	Input resistance thermal drift	-40°C ≤ T _A ≤ 85°C		5		ppm/°C
C _{IN}	Input capacitance	f _{IN} = 275 kHz		4		pF
ANALOG	OUTPUT					
	Nominal gain			0.40		V/V
E _G	Gain error ⁽¹⁾	T _A = 25°C	-0.2%	±0.05%	0.2%	
ΔE_G	Gain error long-term stability	10 years at T _A = 55°C		0 ⁽⁷⁾		
TCE _G	Gain error thermal drift ⁽¹⁾ (6)		-35	±10	35	ppm/°C
ΔTCE _G	Gain error thermal drift long-term stability	10 years at T _A = 55°C		0(7)		ppm/°C
	Nonlineartity ⁽¹⁾		-0.02%	±0.003%	0.02%	
	Nonlinearity thermal drift			0.2		ppm/°C
THD	Total harmonic distortion ⁽⁴⁾	$V_{IN} = 5 V_{PP}, f_{IN} = 10 \text{ kHz},$ BW = 100 kHz		-82		dB
SNR	Signal-to-noise ratio	$V_{IN} = 5 V_{PP}$, $f_{IN} = 1 \text{ kHz}$, BW = 10 kHz	75	79		dB
SNIX	Signal-to-Hoise ratio	V_{IN} = 5 V_{PP} , f_{IN} = 10 kHz, BW = 100 kHz		69		uБ
	Output noise	IN = GND1, BW = 100 kHz		250		μVrms
		PSRR vs VDD1, DC		-67		
		PSRR vs VDD2, DC		-80		
PSRR	Power-supply rejection ratio ⁽²⁾	PSRR vs VDD1 with 10-kHz, 100-mV ripple		-65		dB
		PSRR vs VDD2 with 10-kHz, 100-mV ripple		-64		
V _{CMout}	Output common-mode voltage		1.39	1.44	1.49	V
$V_{CLIPout}$	Clipping differential output voltage	$V_{OUT} = (V_{OUTP} - V_{OUTN}),$ $V_{IN} > V_{Clipping}$		2.49		V
V _{Fail-safe}	Fail-safe differential output voltage	VDD1 undervoltage or VDD1 missing		-2.57	-2.5	V
BW	Output bandwidth		275	300		kHz
R _{OUT}	Output resistance	On OUTP or OUTN		< 0.2		Ω
	Output short-circuit current	On OUTP or OUTN, sourcing or sinking, IN = GND1, outputs shorted to either GND or VDD2		14		mA
CMTI	Common-mode transient immunity		100	150		kV/µs
POWER S	SUPPLY	1				



6.9 Electrical Characteristics (continued)

minimum and maximum specifications apply from $T_A = -40^{\circ}\text{C}$ to +125°C, VDD1 = 3.0 V to 5.5 V, VDD2 = 3.0 V to 5.5 V, IN = -0.25 V to +5 V (unless otherwise noted); typical specifications are at $T_A = 25^{\circ}\text{C}$, VDD1 = 5 V, and VDD2 = 3.3 V

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I VI II I I I I I I I I I I I I I I I I	VDD1 undervoltage detection	VDD1 rising	2.5	2.7	2.9	V
	la	VDD1 falling	2.4	2.6	2.8	V
VDD2 _{UV} VDD2 undervoltage detection threshold	VDD2 undervoltage detection	VDD2 rising	2.2	2.45	2.65	V
	threshold	VDD2 falling	1.85	2.0	2.2	V
	I _{DD1} High-side supply current	3.0 V < VDD1 < 3.6 V		6.0	8.1	mΛ
DD1		4.5 V < VDD1 < 5.5 V		7.0	9.3	mA
I _{DD2}	Low-side supply current	3.0 V < VDD2 < 3.6 V		5.3	7.2	mΛ
		4.5 V < VDD2 < 5.5 V		5.9	8.1	mA

- (1) The typical value includes one standard deviation (sigma) at nominal operating conditions.
- (2) This parameter is input referred.
- (3) The typical value is at VDD1 = 3.3 V.
- (4) THD is the ratio of the rms sum of the amplitues of first five higher harmonics to the amplitude of the fundamental.
- (5) Offset error temperature drift is calculated using the box method, as described by the following equation: TCV_{OS} = (V_{OS,MAX} - V_{OS,MIN}) / TempRange where V_{OS,MAX} and V_{OS,MIN} refer to the maximum and minimum V_{OS} values measured within the temperature range (–40 to 125°C).
- (6) Gain error temperature drift is calculated using the box method, as described by the following equation: $TCE_G(ppm) = ((E_{G,MAX} E_{G,MIN}) / TempRange) \times 10^4$ where $E_{G,MAX}$ and $E_{G,MIN}$ refer to the maximum and minimum E_G values (in %) measured within the temperature range (–40 to 125°C).
- (7) Value is below measurement capability.



6.10 Switching Characteristics

over operating ambient temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _r	Output signal rise time			1.3		μs
t _f	Output signal fall time			1.3		μs
	IN to OUTx signal delay (50% – 10%)	Unfiltered output		1	1.5	μs
	IN to OUTx signal delay (50% – 50%)	Unfiltered output		1.6	2.1	μs
	IN to OUTx signal delay (50% – 90%)	Unfiltered output		2.5	3	μs
t _{AS}	Analog settling time	VDD1 step to 3.0 V with VDD2 ≥ 3.0 V, to V _{OUTP} and V _{OUTN} valid, 0.1% settling		500	800	μs

6.11 Timing Diagram





Figure 6-1. Rise, Fall, and Delay Time Definition



6.12 Insulation Characteristics Curves







Figure 6-2. Thermal Derating Curve for Safety-Limiting Current per VDE

Figure 6-3. Thermal Derating Curve for Safety-Limiting Power per VDE




 T_A up to 150°C, stress-voltage frequency = 60 Hz, isolation working voltage = 1500 V_{RMS} , operating lifetime = 135 years


Figure 6-4. Reinforced Isolation Capacitor Lifetime Projection




6.13 Typical Characteristics


































7 Detailed Description

7.1 Overview

The AMC1351 is a single-ended input, precision, isolated amplifier with a high input-impedance and wide input-voltage range. The input stage of the device drives a second-order, delta-sigma ($\Delta\Sigma$) modulator. The modulator converts the analog input signal into a digital bitstream that is transferred across the isolation barrier that separates the high-side from the low-side. On the low-side, the received bitstream is processed by a fourth-order analog filter that outputs a differential signal at the OUTP and OUTN pins proportional to the input signal.

The SiO₂-based, capacitive isolation barrier supports a high level of magnetic field immunity, as described in the *ISO72x Digital Isolator Magnetic-Field Immunity* application report. The digital modulation used in the AMC1351 to transmit data across the isolation barrier, and the isolation barrier characteristics itself, result in high reliability and common-mode transient immunity.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Analog Input

The single-ended, high-impedance input stage of the AMC1351 feeds a second-order, switched-capacitor, feed-forward $\Delta\Sigma$ modulator. The modulator converts the analog signal into a bitstream that is transferred across the isolation barrier, as described in the *Isolation Channel Signal Transmission* section.

There are two restrictions on the analog input signal IN. First, if the input voltage V_{IN} exceeds the range specified in the *Absolute Maximum Ratings* table, the input current must be limited to the absolute maximum value because the electrostatic discharge (ESD) protection turns on. In addition, the linearity and parametric performance of the device is ensured only when the analog input voltage remains within the linear full-scale range (V_{FSR}) as specified in the *Recommended Operating Conditions* table.



7.3.2 Isolation Channel Signal Transmission

The AMC1351 uses an on-off keying (OOK) modulation scheme, as shown in Figure 7-1, to transmit the modulator output bitstream across the SiO₂-based isolation barrier. The transmit driver (TX) shown in the *Functional Block Diagram* transmits an internally-generated, high-frequency carrier across the isolation barrier to represent a digital *one* and does not send a signal to represent a digital *zero*. The nominal frequency of the carrier used inside the AMC1351 is 480 MHz.

The receiver (RX) on the other side of the isolation barrier recovers and demodulates the signal and provides the input to the fourth-order analog filter. The AMC1351 transmission channel is optimized to achieve the highest level of common-mode transient immunity (CMTI) and lowest level of radiated emissions caused by the high-frequency carrier and RX, TX buffer switching.




Figure 7-1. OOK-Based Modulation Scheme

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated



7.3.3 Analog Output

The AMC1351 provides a differential analog output on the OUTP and OUTN pins. For input voltages (V_{IN}) in the range from -0.25 V to 5 V, the device provides a linear response with a nominal gain of 0.4 V/V. For example, for an input voltage of 5 V, the differential output voltage ($V_{OUTP} - V_{OUTN}$) is 2 V. At zero input (IN shorted to GND1), both pins output the same common-mode output voltage V_{CMout} , as specified in the *Electrical Characteristics* table. For input voltages greater than 5 V but less than approximately 6.25 V, the differential output voltage continues to increase but with reduced linearity performance. The outputs saturate at a differential output voltage of $V_{CLIPout}$, as shown in Figure 7-2, if the input voltage exceeds the $V_{Clipping}$ value.




Figure 7-2. Output Behavior of the AMC1351

The AMC1351 output offers a fail-safe feature that simplifies diagnostics on a system level. Figure 7-2 shows the behavior in fail-safe mode, in which the AMC1351 outputs a negative differential output voltage that does not occur under normal operating conditions. The fail-safe output is active:

- When the high-side supply VDD1 of the AMC1351 device is missing
- When the high-side supply VDD1 falls below the undervoltage threshold VDD1_{IIV}

Use the maximum $V_{\text{Fail-safe}}$ voltage specified in the *Electrical Characteristics* table as a reference value for fail-safe detection on a system level.

7.4 Device Functional Modes

The AMC1351 is operational when the power supplies VDD1 and VDD2 are applied as specified in the *Recommended Operating Conditions* table.



8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

The high input impedance, low input bias current, excellent accuracy, and low temperature drift make the AMC1351 a high-performance solution for industrial applications where voltage sensing in the presence of high common-mode voltage levels is required.

8.2 Typical Application

Isolated amplifiers are widely used for voltage measurements in high-voltage applications that must be isolated from a low-voltage domain. A typical application is the sensing of the DC bus voltage in a frequency inverter.

With its wide, 5-V input voltage range, the AMC1351 is designed for isolated DC voltage-sensing applications where accurate voltage monitoring is required in high-noise environments.

Figure 8-1 shows a simplified schematic of the AMC1351 in a typical motor drive application. The DC bus voltage is divided down to an approximate 5-V level across the bottom resistor (RSNS) of a high-impedance resistor divider that is sensed by the AMC1351. The AMC1351 digitizes the analog input signal on the high-side, transfers the data across the isolation barrier to the low-side, and reconstructs an analog signal that is presented as a differential voltage on the output pins.

The high-impedance input and the high common-mode transient immunity (CMTI) of the AMC1351 ensure reliable and accurate operation even in high-noise environments.




Figure 8-1. Using the AMC1351 for DC Link Voltage Sensing in Frequency Inverters



8.2.1 Design Requirements

Table 8-1 lists the parameters for this typical application.

Table 8-1. Design Requirements

PARAMETER	190-V _{DC} LINE VOLTAGE	360-V _{DC} LINE VOLTAGE
System input voltage	120 V _{RMS} ±10%, 60 Hz	230 V _{RMS} ±10%, 50 Hz
DC bus voltage (max)	190 V	360 V
High-side supply voltage	3.3 V or 5 V	3.3 V or 5 V
Low-side supply voltage	3.3 V or 5 V	3.3 V or 5 V
Maximum resistor operating voltage	75 V	75 V
Voltage drop across the sense resistor (RSNS) for a linear response	5 V (maximum)	5 V (maximum)
Current through the resistive divider (I _{CROSS})	100 μΑ	100 μΑ

8.2.2 Detailed Design Procedure

This discussion covers the 360-V_{DC} example. The procedure for calculating the resistive divider for the 190-V_{DC} use case is identical.

The 100- μ A, cross-current requirement at peak input voltage (360 V) determines that the total impedance of the resistive divider is 3.6 M Ω . The impedance of the resistive divider is dominated by the top resistors (shown exemplary as R1 and R2 in Figure 8-1) and the voltage drop across RSNS can be neglected for a short time. The maximum allowed voltage drop per unit resistor is specified as 75 V; therefore, the total minimum number of unit resistors in the top portion of the resistive divider is 360 V / 75 V = 5. The calculated unit value is 3.6 M Ω / 5 = 720 k Ω and the next closest value from the E96 series is 715 k Ω .

The effective sense resistor value RSNS_{EFF} is the parallel combination of the external resistor RSNS and the input impedance of the AMC1351, R_{IN}. RSNS_{EFF} is sized such that the voltage drop across the impedance at maximum input voltage (360 V) equals the linear full-scale input voltage (V_{FSR}) of the AMC1351 (that is, 5 V). RSNS_{EFF} is calculated as RSNS_{EFF} = V_{FSR} / (V_{Peak} – V_{FSR}) × R_{TOP}, where R_{TOP} is the total value of top resistor string (5 × 715 k Ω = 3575 k Ω). The resulting value for RSNS_{EFF} is 9.96 k Ω . In a final step, RSNS is calculated as RSNS = R_{IN} × RSNS_{EFF} / (R_{IN} – RSNS_{EFF}). With R_{IN} = 1.25 M Ω (typical), RSNS equals 52.47 k Ω and the next closest value from the E96 series is 52.3 k Ω .

Table 8-2 summarizes the design of the resistive divider.

Table 8-2. Resistor Value Examples

190-V _{DC} LINE VOLTAGE	360-V _{DC} LINE VOLTAGE								
634 kΩ	715 kΩ								
3	5								
51.1 kΩ	49.9 kΩ								
1953.1 kΩ	3624.9 kΩ								
97.3 μΑ	99.3 μΑ								
4.971 V	4.956 V								
6 mW	7.1 mW								
18.5 mW	35.8 mW								
	634 kΩ 3 51.1 kΩ 1953.1 kΩ 97.3 μΑ 4.971 V 6 mW								

8.2.2.1 Input Filter Design

Placing an RC filter in front of the isolated amplifier improves signal-to-noise performance of the signal path. In practice, however, the impedance of the resistor divider is so high that adding a filter capacitor on the IN pin limits the signal bandwidth to an unacceptable low limit, such that the filter capacitor is omitted. When used, design the input filter such that:

- The cutoff frequency of the filter is at least one order of magnitude lower than the sampling frequency (20 MHz) of the internal ΔΣ modulator
- The input bias current does not generate significant voltage drop across the DC impedance of the input filter

Most voltage-sensing applications use high-impedance resistor dividers in front of the isolated amplifier to scale down the input voltage. In that case, no additional resistor is needed and a single capacitor (as shown in Figure 8-2) is sufficient to filter the input signal.




Figure 8-2. Input Filter

8.2.2.2 Differential to Single-Ended Output Conversion

Figure 8-3 shows an example of a TLV6001-based signal conversion and filter circuit for systems using single-ended input ADCs to convert the analog output voltage into digital. With R1 = R2 = R3 = R4, the output voltage equals $(V_{OUTP} - V_{OUTN}) + V_{REF}$. Tailor the bandwidth of this filter stage to the bandwidth requirement of the system and use NP0-type capacitors for best performance. For most applications, R1 = R2 = R3 = R4 = 3.3 k Ω and C1 = C2 = 330 pF yields good performance.




Figure 8-3. Connecting the AMC1351 Output to a Single-Ended Input ADC

For more information on the general procedure to design the filtering and driving stages of SAR ADCs, see the 18-Bit, 1MSPS Data Acquisition Block (DAQ) Optimized for Lowest Distortion and Noise and 18-Bit Data Acquisition Block (DAQ) Optimized for Lowest Power reference guides, available for download at www.ti.com.

Submit Document Feedback

Copyright © 2021 Texas Instruments Incorporated

8.2.3 Application Curve

One important aspect of system design is the effective detection of an overvoltage condition to protect switching devices and passive components from damage. To power off the system quickly in the event of an overvoltage condition, a low delay caused by the isolated amplifier is required. Figure 8-4 shows the typical full-scale step response of the AMC1351.




Figure 8-4. Step Response of the AMC1351

8.3 What To Do and What Not To Do

Do not leave the analog input (IN) of the AMC1351 unconnected (floating) when the device is powered up on the high-side. If the device input is left floating, the bias current may generate a positive or negative input voltage and the output of the device is undetermined.

Do not connect protection diodes to the input (IN) of the AMC1351. Diode leakage current can introduce significant measurement error especially at high temperatures. The input pin is protected against high voltages by its ESD protection circuit and the high impedance of the external restive divider

Connect both GND1 pins to the high-side ground potential. Do not leave one of the GND1 pins unconnected.



9 Power Supply Recommendations

In a typical application, the high-side power supply (VDD1) for the AMC1351 is generated either from a gate-driver supply on the high-side (as shown in Figure 8-1), or from the low-side supply (VDD2) by an isolated DC/DC converter. A low-cost solution is based on the push-pull driver SN6501 and a transformer that supports the desired isolation voltage ratings.

The AMC1351 does not require any specific power-up sequencing. The high-side power supply (VDD1) is decoupled with a low-ESR, 100-nF capacitor (C1) parallel to a low-ESR, 1-μF capacitor (C2). The low-side power supply (VDD2) is equally decoupled with a low-ESR, 100-nF capacitor (C3) parallel to a low-ESR, 1-μF capacitor (C4). Place all four capacitors (C1, C2, C3, and C4) as close to the device as possible.




Figure 9-1. Decoupling of the AMC1351

Capacitors must provide adequate effective capacitance under the applicable DC bias conditions they experience in the application. Multilayer ceramic capacitors (MLCC) typically exhibit only a fraction of their nominal capacitance under real-world conditions and this factor must be taken into consideration when selecting these capacitors. This problem is especially acute in low-profile capacitors, in which the dielectric field strength is higher than in taller components. Reputable capacitor manufacturers provide capacitance versus DC bias curves that greatly simplify component selection.

Submit Document Feedback



10 Layout

10.1 Layout Guidelines

Figure 10-1 shows a layout recommendation with the critical placement of the decoupling capacitors (as close as possible to the AMC1351 supply pins) and placement of the other components required by the device. For best performance, place the sense resistor close to the device input pin (IN).

10.2 Layout Example




Figure 10-1. Recommended Layout of the AMC1351



11 Device and Documentation Support

11.1 Documentation Support

11.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, Isolation Glossary application report
- Texas Instruments, Semiconductor and IC Package Thermal Metrics application report
- Texas Instruments, ISO72x Digital Isolator Magnetic-Field Immunity application report
- Texas Instruments, TLV600x Low-Power, Rail-to-Rail In/Out, 1-MHz Operational Amplifier for Cost-Sensitive Systems data sheet
- Texas Instruments, 18-Bit, 1-MSPS Data Acquisition Block (DAQ) Optimized for Lowest Distortion and Noise reference guide
- Texas Instruments, 18-Bit, 1-MSPS Data Acquisition Block (DAQ) Optimized for Lowest Power reference quide
- · Texas Instruments, Isolated Amplifier Voltage Sensing Excel Calculator design tool
- Texas Instruments, Best in Class Radiated Emissions EMI Performance with the AMC1300B-Q1 Isolated Amplifier technical white paper

11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

11.4 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

11.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com

18-Jul-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/			Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
AMC1351DWV	Active	Production	SOIC (DWV) 8	64 TUBE	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWV.A	Active	Production	SOIC (DWV) 8	64 TUBE	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWV.B	Active	Production	SOIC (DWV) 8	64 TUBE	-	Call TI	Call TI	-40 to 125	
AMC1351DWVR	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWVR.A	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWVR.B	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	-	Call TI	Call TI	-40 to 125	
AMC1351DWVRG4	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWVRG4.A	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	Yes	NIPDAU	Level-3-260C-168 HR	-40 to 125	AMC1351
AMC1351DWVRG4.B	Active	Production	SOIC (DWV) 8	1000 LARGE T&R	-	Call TI	Call TI	-40 to 125	

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No. RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

PACKAGE OPTION ADDENDUM

www.ti.com 18-Jul-2025

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF AMC1351:

Automotive : AMC1351-Q1

NOTE: Qualified Version Definitions:

Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

	Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
	AMC1351DWVR	SOIC	DWV	8	1000	330.0	16.4	12.15	6.2	3.05	16.0	16.0	Q1
Α	MC1351DWVRG4	SOIC	DWV	8	1000	330.0	16.4	12.05	6.15	3.3	16.0	16.0	Q1

www.ti.com 24-Jul-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
AMC1351DWVR	SOIC	DWV	8	1000	353.0	353.0	32.0
AMC1351DWVRG4	SOIC	DWV	8	1000	350.0	350.0	43.0

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
AMC1351DWV	DWV	SOIC	8	64	505.46	13.94	4826	6.6
AMC1351DWV.A	DWV	SOIC	8	64	505.46	13.94	4826	6.6



SOIC



NOTES:


- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



SOIC




NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated