

# CMOS Low-Power Monostable/Astable Multivibrator

High Voltage Types (20-Volt Rating)

■ CD4047B consists of a gatable astable multivibrator with logic techniques incorporated to permit positive or negative edge-triggered monostable multivibrator action with retriggering and external counting options.

Inputs include +TRIGGER, -TRIGGER, ASTABLE, ASTABLE, RETRIGGER, and EXTERNAL RESET. Buffered outputs are Q, Q, and OSCILLATOR. In all modes of operation, and external capacitor must be connected between C-Timing and RC-Common terminals, and an external resistor must be connected between the R-Timing and RC-Common terminals.

Astable operation is enabled by a high level on the ASTABLE input or a low level on the ASTABLE input, or both. The period of the square wave at the Q and Q outputs in this mode of operation is a function of the external components employed. "True" input pulses on the ASTABLE input or "Complement" pulses on the ASTABLE input allow the circuit to be used as a gatable multivibrator. The OSCILLATOR output period will be half of the Q terminal output in the astable mode. However, a 50% duty cycle is not guaranteed at this output.

The CD4047B triggers in the monostable mode when a positive-going edge occurs on the +TRIGGER-input while the -TRIGGER is held low. Input pulses may be of any duration relative to the output pulse.

If retrigger capability is desired, the RETRIGGER input is pulsed. The retriggerable mode of operation is limited to positive-going edge. The CD4047B will retrigger as long as the RETRIGGER-input is high, with or without transitions (See Fig. 34).

An external countdown option can be implemented by coupling "Q" to an external "N" counter and resetting the counter with the trigger pulse. The counter output pulse is fed back to the ASTABLE input and has a duration equal to N times the period of the multivibrator.

A high level on the EXTERNAL RESET input assures no output pulse during an "ON" power condition. This input can also be activated to terminate the output pulse at any time. For monostable operation, whenever V<sub>DD</sub> is applied, an internal power-on reset circuit will clock the Q output low within one output period (t<sub>M</sub>).

The CD4047B-Series types are supplied in 14-lead hermetic dual-in-line ceramic packages (F3A suffix), 14-lead dual-in-line plastic packages (E suffix), 14-lead small-outline packages (M, MT, M96, and NSR suffixes), and 14-lead thin shrink small-outline packages (PW and PWR suffixes).

## Features:

- Low power consumption: special CMOS oscillator configuration
- Monostable (one-shot) or astable (free-running) operation
- True and complemented buffered outputs
- Only one external R and C required
- Buffered inputs
- 100% tested for quiescent current at 20 V
- Standardized, symmetrical output characteristics
- 5-V, 10-V, and 15-V parametric ratings
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices"

## Monostable Multivibrator Features:

- Positive- or negative-edge trigger
- Output pulse width independent of trigger pulse duration
- Retriggerable option for pulse width expansion
- Internal power-on reset circuit
- Long pulse widths possible using small RC components by means of external counter provision
- Fast recovery time essentially independent of pulse width
- Pulse-width accuracy maintained at duty cycles approaching 100%

## Astable Multivibrator Features:

- Free-running or gatable operating modes
- 50% duty cycle

- Oscillator output available

- Good astable frequency stability:

Frequency deviation:

= ±2% + 0.03%/°C @ 100 kHz

= ±0.5% + 0.015%/°C @ 10 kHz


(circuits "trimmed" to frequency

V<sub>DD</sub> = 10 V ± 10%)

## Applications:

Digital equipment where low-power dissipation and/or high noise immunity are primary design requirements:

- Envelope detection
- Frequency multiplication
- Frequency division
- Frequency discriminators
- Timing circuits
- Time-delay applications



## RECOMMENDED OPERATING CONDITIONS

For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

| CHARACTERISTIC                                                                                                  | LIMITS |      | UNITS |
|-----------------------------------------------------------------------------------------------------------------|--------|------|-------|
|                                                                                                                 | MIN.   | MAX. |       |
| Supply-Voltage Range (For T <sub>A</sub> = Full Package-Temperature Range)                                      | 3      | 18   | V     |
| NOTE: IF AT 15 V OPERATION A 10 MΩ RESISTOR IS USED THE OPERATING TEMPERATURE SHOULD BE BETWEEN -25°C and 100°C |        |      |       |

## MAXIMUM RATINGS, Absolute-Maximum Values:

### DC SUPPLY-VOLTAGE RANGE, (V<sub>DD</sub>)

Voltages referenced to V<sub>SS</sub> Terminal) ..... -0.5V to +20V

INPUT VOLTAGE RANGE, ALL INPUTS ..... -0.5V to V<sub>DD</sub> + 0.5V

DC INPUT CURRENT, ANY ONE INPUT ..... ±10mA

### POWER DISSIPATION PER PACKAGE (P<sub>D</sub>):

For T<sub>A</sub> = -55°C to +100°C ..... 500mW

For T<sub>A</sub> = +100°C to +125°C ..... Derate Linearly at 12mW/°C to 200mW

### DEVICE DISSIPATION PER OUTPUT TRANSISTOR

FOR T<sub>A</sub> = FULL PACKAGE-TEMPERATURE RANGE (All Package Types) ..... 100mW

OPERATING-TEMPERATURE RANGE (T<sub>A</sub>) ..... -55°C to +125°C

STORAGE TEMPERATURE RANGE (T<sub>stg</sub>) ..... -65°C to +150°C

### LEAD TEMPERATURE (DURING SOLDERING):

At distance 1/16 ± 1/32 inch (1.59 ± 0.79mm) from case for 10s max ..... +265°C

## CD4047B Types

### CD4047B FUNCTIONAL TERMINAL CONNECTIONS

NOTE: IN ALL CASES EXTERNAL RESISTOR BETWEEN TERMINALS 2 AND 3▲  
EXTERNAL CAPACITOR BETWEEN TERMINALS 1 AND 3▲

| FUNCTION                  | TERMINAL CONNECTIONS |                    |          | OUTPUT PULSE FROM | OUTPUT PERIOD OR PULSE WIDTH |
|---------------------------|----------------------|--------------------|----------|-------------------|------------------------------|
|                           | TO V <sub>DD</sub>   | TO V <sub>SS</sub> | INPUT TO |                   |                              |
| Astable Multivibrator:    |                      |                    |          |                   |                              |
| Free Running              | 4,5,6,14             | 7,8,9,12           | —        | 10,11,13          | $t_A(10,11) = 4.40 RC$       |
| True Gating               | 4,6,14               | 7,8,9,12           | 5        | 10,11,13          | $t_A(13) = 2.20 RC^*$        |
| Complement Gating         | 6,14                 | 5,7,8,9,12         | 4        | 10,11,13          |                              |
| Monostable Multivibrator: |                      |                    |          |                   |                              |
| Positive-Edge Trigger     | 4,14                 | 5,6,7,9,12         | 8        | 10,11             | $t_M(10,11) = 2.48 RC$       |
| Negative-Edge Trigger     | 4,8,14               | 5,7,9,12           | 6        | 10,11             |                              |
| Retriggerable             | 4,14                 | 5,6,7,9            | 8,12     | 10,11             |                              |
| External Countdown *      | 14                   | 5,6,7,8,9,12       | —        | 10,11             |                              |

▲ See Text.

\* First positive ½ cycle pulse-width = 2.48 RC, see Note on Page 3-134.

\* Input Pulse to Reset of External Counting Chip External Counting Chip Output To Terminal 4




Fig. 1—CD4047B logic block diagram.

92CS-29071




Fig. 2—CD4047B logic diagram.

92CM-29042RI

# CD4047B Types




Fig. 3—Detail logic diagram for flip-flops FF1 and FF3 (a) and for flip-flops FF2 and FF4 (b).




Fig. 4—Typical output low (sink) current characteristics.




Fig. 5—Minimum output low (sink) current characteristics.

## STATIC ELECTRICAL CHARACTERISTICS

| CHARACTERISTICS                                    | CONDITIONS            |                        |                        | LIMITS AT INDICATED TEMPERATURES (°C) |       |       |       |       |      |      | UNITS |
|----------------------------------------------------|-----------------------|------------------------|------------------------|---------------------------------------|-------|-------|-------|-------|------|------|-------|
|                                                    | V <sub>O</sub><br>(V) | V <sub>IN</sub><br>(V) | V <sub>DD</sub><br>(V) | + 25                                  |       |       |       |       |      |      |       |
|                                                    |                       |                        |                        | −55                                   | −40   | + 85  | + 125 | Min.  | Typ. | Max. |       |
| Quiescent Device Current, I <sub>DD</sub> Max.     | —                     | 0,5                    | 5                      | 1                                     | 1     | 30    | 30    | —     | 0.02 | 1    | μA    |
|                                                    | —                     | 0,10                   | 10                     | 2                                     | 2     | 60    | 60    | —     | 0.02 | 2    |       |
|                                                    | —                     | 0,15                   | 15                     | 4                                     | 4     | 120   | 120   | —     | 0.02 | 4    |       |
|                                                    | —                     | 0,20                   | 20                     | 20                                    | 20    | 600   | 600   | —     | 0.04 | 20   |       |
| Output Low (Sink) Current I <sub>OL</sub> Min.     | 0.4                   | 0,5                    | 5                      | 0.64                                  | 0.61  | 0.42  | 0.36  | 0.51  | 1    | —    | mA    |
|                                                    | 0.5                   | 0,10                   | 10                     | 1.6                                   | 1.5   | 1.1   | 0.9   | 1.3   | 2.6  | —    |       |
|                                                    | 1.5                   | 0,15                   | 15                     | 4.2                                   | 4     | 2.8   | 2.4   | 3.4   | 6.8  | —    |       |
| Output High (Source) Current, I <sub>OH</sub> Min. | 4.6                   | 0,5                    | 5                      | −0.64                                 | −0.61 | −0.42 | −0.36 | −0.51 | −1   | —    | mA    |
|                                                    | 2.5                   | 0,5                    | 5                      | −2                                    | −1.8  | −1.3  | −1.15 | −1.6  | −3.2 | —    |       |
|                                                    | 9.5                   | 0,10                   | 10                     | −1.6                                  | −1.5  | −1.1  | −0.9  | −1.3  | −2.6 | —    |       |
|                                                    | 13.5                  | 0,15                   | 15                     | −4.2                                  | −4    | −2.8  | −2.4  | −3.4  | −6.8 | —    |       |
| Output Voltage: Low-Level V <sub>OL</sub> Max.     | —                     | 0,5                    | 5                      | 0.05                                  |       |       |       | —     | 0    | 0.05 | V     |
|                                                    | —                     | 0,10                   | 10                     | 0.05                                  |       |       |       | —     | 0    | 0.05 |       |
|                                                    | —                     | 0,15                   | 15                     | 0.05                                  |       |       |       | —     | 0    | 0.05 |       |




Fig. 6—Typical output high (source) current characteristics.




Fig. 7—Minimum output high (source) current characteristics.




Fig. 8—Typical propagation delay time as a function of load capacitance (Astable, Astable to Q,  $\bar{Q}$ ).




Fig. 9—Typical propagation delay time as a function of load capacitance (+ or - trigger to Q,  $\bar{Q}$ ).

# CD4047B Types

## STATIC ELECTRICAL CHARACTERISTICS (CONTINUED)

| CHARACTERISTICS                                  | CONDITIONS            |                        |                        | LIMITS AT INDICATED TEMPERATURES (°C) |      |     |      |       |                  |      | UNITS |
|--------------------------------------------------|-----------------------|------------------------|------------------------|---------------------------------------|------|-----|------|-------|------------------|------|-------|
|                                                  | V <sub>O</sub><br>(V) | V <sub>IN</sub><br>(V) | V <sub>DD</sub><br>(V) |                                       |      |     |      | +25   |                  |      |       |
|                                                  |                       |                        |                        | -55                                   | -40  | +85 | +125 | Min.  | Typ.             | Max. |       |
| Output Voltage: High-Level, V <sub>OH</sub> Min. | —                     | 0.5                    | 5                      | 4.95                                  |      |     |      | 4.95  | 5                | —    | V     |
|                                                  | —                     | 0,10                   | 10                     | 9.95                                  |      |     |      | 9.95  | 10               | —    |       |
|                                                  | —                     | 0,15                   | 15                     | 14.95                                 |      |     |      | 14.95 | 15               | —    |       |
| Input Low Voltage, V <sub>IL</sub> Max.          | 0.5,4.5               | —                      | 5                      | 1.5                                   |      |     |      | —     | —                | 1.5  | V     |
|                                                  | 1,9                   | —                      | 10                     | 3                                     |      |     |      | —     | —                | 3    |       |
|                                                  | 1.5,13.5              | —                      | 15                     | 4                                     |      |     |      | —     | —                | 4    |       |
| Input High Voltage, V <sub>IH</sub> Min.         | 0.5,4.5               | —                      | 5                      | 3.5                                   |      |     |      | 3.5   | —                | —    | V     |
|                                                  | 1.9                   | —                      | 10                     | 7                                     |      |     |      | 7     | —                | —    |       |
|                                                  | 1.5,13.5              | —                      | 15                     | 11                                    |      |     |      | 11    | —                | —    |       |
| Input Current I <sub>IN</sub> Max.               | —                     | 0,18                   | 18                     | ±0.1                                  | ±0.1 | ±1  | ±1   | —     | ±10 <sup>5</sup> | ±0.1 | μA    |

**DYNAMIC ELECTRICAL CHARACTERISTICS** at  $T_A = 25^\circ\text{C}$ ; Input  $t_r, t_f = 20\text{ ns}$ ,  
 $C_L = 50\text{ pF}$ ,  $R_L = 200\text{ k}\Omega$

| CHARACTERISTIC                                                                                          | $V_{DD}$ (V) | LIMITS |      |      | UNITS |
|---------------------------------------------------------------------------------------------------------|--------------|--------|------|------|-------|
|                                                                                                         |              | MIN.   | TYP. | MAX. |       |
| Propagation Delay Time, $t_{PHL}, t_{PLH}$<br>Astable, Astable to Osc. Out                              | 5            | —      | 200  | 400  | ns    |
|                                                                                                         | 10           | —      | 100  | 200  |       |
|                                                                                                         | 15           | —      | 80   | 160  |       |
| Astable, Astable to Q, $\bar{Q}$                                                                        | 5            | —      | 350  | 700  |       |
|                                                                                                         | 10           | —      | 175  | 350  |       |
|                                                                                                         | 15           | —      | 125  | 250  |       |
| + or - Trigger to Q, $\bar{Q}$                                                                          | 5            | —      | 500  | 1000 |       |
|                                                                                                         | 10           | —      | 225  | 450  |       |
|                                                                                                         | 15           | —      | 150  | 300  |       |
| Retrigger to Q, $\bar{Q}$                                                                               | 5            | —      | 300  | 600  |       |
|                                                                                                         | 10           | —      | 150  | 300  |       |
|                                                                                                         | 15           | —      | 100  | 200  |       |
| External Reset to Q, $\bar{Q}$                                                                          | 5            | —      | 250  | 500  |       |
|                                                                                                         | 10           | —      | 100  | 200  |       |
|                                                                                                         | 15           | —      | 70   | 140  |       |
| Transition Time, $t_{THL}, t_{TLH}$<br>Osc. Out, Q, $\bar{Q}$                                           | 5            | —      | 100  | 200  |       |
|                                                                                                         | 10           | —      | 50   | 100  |       |
|                                                                                                         | 15           | —      | 40   | 80   |       |
| Minimum Input Pulse Width, $t_w$<br>+ Trigger, - Trigger                                                | 5            | —      | 200  | 400  |       |
|                                                                                                         | 10           | —      | 80   | 160  |       |
|                                                                                                         | 15           | —      | 50   | 100  |       |
| Reset                                                                                                   | 5            | —      | 100  | 200  |       |
|                                                                                                         | 10           | —      | 50   | 100  |       |
|                                                                                                         | 15           | —      | 30   | 60   |       |
| Retrigger                                                                                               | 5            | —      | 300  | 600  |       |
|                                                                                                         | 10           | —      | 115  | 230  |       |
|                                                                                                         | 15           | —      | 75   | 150  |       |
| Input Rise and Fall Time, $t_r, t_f$<br>All Trigger Inputs<br>For + Trigger:<br>$t_r$ only is unlimited | 5            | —      | 270  | —    | μs    |
|                                                                                                         | 10           | —      | 18   | —    |       |
|                                                                                                         | 15           | —      | 9    | —    |       |
|                                                                                                         | 5            | —      | 325  | —    |       |
|                                                                                                         | 10           | —      | 9    | —    |       |
|                                                                                                         | 15           | —      | 4    | —    |       |
| Q or $\bar{Q}$ Deviation from 50% Duty Factor                                                           | 5            | —      | ±0.5 | ±1   | %     |
|                                                                                                         | 10           | —      | ±0.5 | ±1   |       |
|                                                                                                         | 15           | —      | ±0.1 | ±0.5 |       |
| Input Capacitance, $C_{IN}$                                                                             | Any Input    | —      | 5    | 7.7  | pF    |




Fig. 10—Typical transition time as a function of load capacitance.




Fig. 11—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. supply voltage.




Fig. 12—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. supply voltage.




Fig. 13—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. supply voltage.

## CD4047B Types




Fig. 14—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. ambient temperature (ultra-low frequency).




Fig. 15—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. ambient temperature (low frequency).




Fig. 16—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. ambient temperature (medium frequency).




Fig. 17—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. ambient temperature (high-frequency).




Fig. 18—Typical astable oscillator or Q,  $\bar{Q}$  period accuracy vs. ambient temperature.




Fig. 19—Typical output pulse-width variations vs. supply voltage.




Fig. 20—Typical output pulse-width variations vs. supply voltage.




Fig. 21—Typical output pulse-width variations vs. supply voltage.




Fig. 22—Typical output pulse-width variations vs. ambient temperature.




Fig. 23—Typical output pulse-width variations vs. ambient temperature.




Fig. 24—Typical output pulse-width variations vs. ambient temperature.




Fig. 25—Typical output pulse-width variations vs. ambient temperature.

## CD4047B Types




Fig. 26—Typical power dissipation vs. output frequency ( $V_{DD} = 5$  V).




Fig. 27—Typical power dissipation vs. output frequency ( $V_{DD} = 10$  V).




Fig. 28—Typical power dissipation vs. output frequency ( $V_{DD} = 15$  V).




Fig. 29—Quiescent device current test circuit.




Fig. 30—Input-voltage test circuit.




Fig. 31—Input-leakage-current test circuit.

### 1. Astable Mode Design Information

#### A. Unit-to-Unit Transfer-Voltage Variations

The following analysis presents variations from unit to unit as a function of transfer-voltage ( $V_{TR}$ ) shift (33%–67%  $V_{DD}$ ) for free-running (astable) operation.




Fig. 32—Astable mode waveforms.

$$t_1 = -RC \ln \frac{V_{TR}}{V_{DD} + V_{TR}};$$

typically,  $t_1 = 1.1 RC$

$$t_2 = -RC \ln \frac{V_{DD} - V_{TR}}{2V_{DD} - V_{TR}};$$

typically,  $t_2 = 1.1 RC$

$$t_A = 2(t_1 + t_2)$$

$$= -2RC \ln \frac{(V_{TR}V_{DD} - V_{TR})}{(V_{DD} + V_{TR})(2V_{DD} - V_{TR})}$$

Typ:  $V_{TR} = 0.5 V_{DD}$   $t_A = 4.40 RC$   
 Min:  $V_{TR} = 0.33 V_{DD}$   $t_A = 4.62 RC$   
 Max:  $V_{TR} = 0.67 V_{DD}$   $t_A = 4.62 RC$

thus if  $t_A = 4.40 RC$  is used, the variation will be +5%, -0% due to variations in transfer voltage.

**B. Variations Due to  $V_{DD}$  and Temperature Changes** — In addition to variations from unit to unit, the astable period varies with  $V_{DD}$  and temperature. Typical variations are presented in graphical form in Figs. 11 to 18 with 10 V as reference for voltage variation curves and 25°C as reference for temperature variation curves.

### II. Monostable Mode Design Information

The following analysis presents variations from unit to unit as a function of transfer-voltage ( $V_{TR}$ ) shift (33% – 67%  $V_{DD}$ ) for one-shot (monostable) operation.




Fig. 33—Monostable waveforms.

$$t_1' = -RC \ln \frac{V_{TR}}{2V_{DD}}$$

typically,  $t_1' = 1.38 RC$

$$t_M = (t_1' + t_2)$$

$$t_M = -RC \ln \frac{(V_{TR})(V_{DD} - V_{TR})}{(2V_{DD} - V_{TR})(2V_{DD})}$$

where  $t_M$  = Monostable mode pulse width. Values for  $t_M$  are as follows:

Typ:  $V_{TR} = 0.5 V_{DD}$   $t_M = 2.48 RC$   
 Min:  $V_{TR} = 0.33 V_{DD}$   $t_M = 2.71 RC$   
 Max:  $V_{TR} = 0.67 V_{DD}$   $t_M = 2.48 RC$

thus if  $t_M = 2.48 RC$  is used, the variation will be +9.3%, -0% due to variations in transfer voltage.

#### Note:

In the astable mode, the first positive half cycle has a duration of  $t_M$ ; succeeding durations are  $t_A/2$ .

In addition to variations from unit to unit, the monostable pulse width varies with  $V_{DD}$  and temperature. These variations are presented in graphical form in Fig. 19 to 26 with 10 V as reference for voltage-variation curves and 25°C as reference for temperature-variation curves.

## CD4047B Types

### III. Retrigger Mode Operation

The CD4047B can be used in the retrigger mode to extend the output-pulse duration, or to compare the frequency of an input signal with that of the internal oscillator. In the retrigger mode the input pulse is applied to terminal 12, and the output is taken from terminal 10 or 11. As shown in Fig. 34 normal monostable action is obtained when one retrigger pulse is applied. Extended pulse duration is obtained when more than one pulse is applied.




Fig. 34—Retrigger-mode waveforms.

For two input pulses,  $t_{RE} = t_1' + t_1 + 2t_2$ . For more than two pulses, the output pulse width is an integral number of time periods, with the first time period being  $t_1' + t_2$ , typically,  $2.48RC$ , and all subsequent time periods being  $t_1 + t_2$ , typically,  $2.2RC$ .

### IV. External Counter Option

Time  $t_M$  can be extended by any amount with the use of external counting cir-

cuitry. Advantages include digitally controlled pulse duration, small timing capacitors for long time periods, and extremely fast recovery time. A typical implementation is shown in Fig. 35. The pulse duration at the output is

$$t_{ext} = (N - 1)(t_A) + (t_M + t_A/2)$$

where  $t_{ext}$  = pulse duration of the circuitry, and  $N$  is the number of counts used.




Fig. 35—Implementation of external counter option.

### V. Timing-Component Limitations

The capacitor used in the circuit should be non-polarized and have low leakage (i.e. the parallel resistance of the capacitor should be at least an order of magnitude greater than the external resistor used). There is no upper or lower limit for either  $R$  or  $C$  value to maintain oscillation.

However, in consideration of accuracy,  $C$  must be much larger than the inherent stray capacitance in the system (unless this capacitance can be measured and taken into account).  $R$  must be much

larger than the CMOS "ON" resistance in series with it, which typically is hundreds of ohms. In addition, with very large values of  $R$ , some short-term instability with respect to time may be noted.

The recommended values for these components to maintain agreement with

tion of leakage current in the circuit, as shown in the static electrical characteristics. For dynamic operation, the power needed to charge the external timing capacitor  $C$  is given by the following formulae:

Astable Mode:

$$P = 2CV^2f. \text{ (Output at terminal No. 13)}$$

$$P = 4CV^2f. \text{ (Output at terminal Nos. 10 and 11)}$$


Monostable Mode:

$$P = \frac{(2.9CV^2) (\text{Duty Cycle})}{T}$$

(Output at terminal Nos. 10 and 11)

The circuit is designed so that most of the total power is consumed in the external components. In practice, the lower the values of frequency and voltage used, the closer the actual power dissipation will be to the calculated value.

Because the power dissipation does not depend on  $R$ , a design for minimum power dissipation would be a small value of  $C$ . The value of  $R$  would depend on the desired period (within the limitations discussed above). See Figs. 27, 28, and 29 for typical power consumption in astable mode.



Chip dimensions and pad layout for CD4047B

Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils (10<sup>-3</sup> inch).

## PACKAGING INFORMATION

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)     |
|------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-------------------------|
| <a href="#">8102001CA</a>    | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8102001CA<br>CD4047BF3A |
| <a href="#">CD4047BD3</a>    | Active        | Production           | CDIP SB (JD)   14 | 24   TUBE             | No          | AU                                   | N/A for Pkg Type                  | -55 to 125   | CD4047BD/3              |
| CD4047BD3.A                  | Active        | Production           | CDIP SB (JD)   14 | 24   TUBE             | No          | AU                                   | N/A for Pkg Type                  | -55 to 125   | CD4047BD/3              |
| <a href="#">CD4047BE</a>     | Active        | Production           | PDIP (N)   14     | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD4047BE                |
| CD4047BE.A                   | Active        | Production           | PDIP (N)   14     | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD4047BE                |
| CD4047BEE4                   | Active        | Production           | PDIP (N)   14     | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD4047BE                |
| <a href="#">CD4047BF</a>     | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD4047BF                |
| CD4047BF.A                   | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD4047BF                |
| <a href="#">CD4047BF3A</a>   | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8102001CA<br>CD4047BF3A |
| CD4047BF3A.A                 | Active        | Production           | CDIP (J)   14     | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8102001CA<br>CD4047BF3A |
| <a href="#">CD4047BM</a>     | Obsolete      | Production           | SOIC (D)   14     | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | CD4047BM                |
| <a href="#">CD4047BM96</a>   | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CD4047BM                |
| CD4047BM96.A                 | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CD4047BM                |
| CD4047BM96G4                 | Active        | Production           | SOIC (D)   14     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CD4047BM                |
| <a href="#">CD4047BMT</a>    | Obsolete      | Production           | SOIC (D)   14     | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | CD4047BM                |
| <a href="#">CD4047BNSR</a>   | Active        | Production           | SOP (NS)   14     | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CD4047B                 |
| CD4047BNSR.A                 | Active        | Production           | SOP (NS)   14     | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CD4047B                 |
| <a href="#">CD4047BPW</a>    | Obsolete      | Production           | TSSOP (PW)   14   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | CM047B                  |
| <a href="#">CD4047BPWR</a>   | Active        | Production           | TSSOP (PW)   14   | 2000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | CM047B                  |
| CD4047BPWR.A                 | Active        | Production           | TSSOP (PW)   14   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CM047B                  |
| <a href="#">CD4047BPWRG4</a> | Active        | Production           | TSSOP (PW)   14   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | CM047B                  |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD4047B, CD4047B-MIL :**

- Catalog : [CD4047B](#)
- Military : [CD4047B-MIL](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD4047BM96   | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| CD4047BNSR   | SOP          | NS              | 14   | 2000 | 330.0              | 16.4               | 8.1     | 10.4    | 2.5     | 12.0    | 16.0   | Q1            |
| CD4047BPWR   | TSSOP        | PW              | 14   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD4047BPWR   | TSSOP        | PW              | 14   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD4047BPWRG4 | TSSOP        | PW              | 14   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD4047BM96   | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| CD4047BNSR   | SOP          | NS              | 14   | 2000 | 353.0       | 353.0      | 32.0        |
| CD4047BPWR   | TSSOP        | PW              | 14   | 2000 | 356.0       | 356.0      | 35.0        |
| CD4047BPWR   | TSSOP        | PW              | 14   | 2000 | 353.0       | 353.0      | 32.0        |
| CD4047BPWRG4 | TSSOP        | PW              | 14   | 2000 | 356.0       | 356.0      | 35.0        |

## TUBE




\*All dimensions are nominal

| Device     | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD4047BE   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD4047BE.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD4047BEE4 | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |


JD (R-CDIP-T14)

CERAMIC SIDE-BRAZE DUAL-IN-LINE




- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - Controlling dimension: inch.
  - Leads within 0.005 (0,13) radius of true position (TP) at gage plane with maximum material condition and unit installed.
  - Angle applies to spread leads prior to installation.
  - Outlines on which the seating plane is coincident with the plane (standoff = 0), terminals lead standoffs are not required, and lead shoulder may equal lead width along any part of the lead above the seating/base plane.

- Body width does not include particles of packing materials.
- A visual index feature must be located within the cross-hatched area.

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4220718/A 09/2016

**NOTES:**


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
5. Reference JEDEC registration MS-012, variation AB.

# EXAMPLE BOARD LAYOUT



D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN




- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

**J 14**

## GENERIC PACKAGE VIEW


**CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE




Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G

**J0014A****PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

**NOTES:**

1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.




**TEXAS  
INSTRUMENTS**  
www.ti.com

# EXAMPLE BOARD LAYOUT



J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X




4214771/A 05/2017


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE





| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.



4220202/B 12/2023

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT



PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4220202/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220202/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated