

# DACx3004W 12-Bit and 10-Bit, Ultra-Low-Power, Quad Voltage and Current Output Smart DACs With Auto-Detected I<sup>2</sup>C, SPI, or PMBus Interface

## 1 Features

- Programmable voltage or current outputs with flexible configuration:
  - Voltage outputs:
    - 1LSB DNL
    - Gains of 1 ×, 1.5 ×, 2 ×, 3 ×, and 4 ×
    - Current outputs:
      - 1 LSB INL and DNL (8-bit)
      - Unipolar and bipolar output range options from 25µA to 250µA
- 35µA/channel I<sub>DD</sub> in voltage-output mode
- · Programmable comparator mode for all channels
- High-impedance output when VDD is off
- High-impedance and resistive pulldown powerdown modes
- 50MHz SPI-compatible interface
- Automatically detected I<sup>2</sup>C, SPI, or PMBus<sup>™</sup> interface
  - 1.62V V<sub>IH</sub> with V<sub>DD</sub> = 5.5V
- General-purpose input/output (GPIO) configurable as multiple functions
- Predefined waveform generation: sine wave, triangular, sawtooth
- User-programmable nonvolatile memory (NVM)
- Internal, external, or power-supply as reference
- Wide operating range:
  - Power supply: 1.8V to 5.5V
  - Temperature range: -40°C to +125°C
- Tiny package: 16-pin DSBGA (1.76mm × 1.76mm)

## 2 Applications

- Optical module
- Pulse oximeter
- Standard notebook PC

### **3 Description**


The 12-bit DAC63004W and 10-bit DAC53004W (DACx3004W) are a pin-compatible family of quadchannel, buffered, voltage-output and current-output smart digital-to-analog converters (DACs). These DACx3004W support Hi-Z power-down mode and Hi-Z output during power-off condition. The DAC outputs provide a force-sense option for use as a programmable comparator and current sink. The multifunction GPIO, function generation, and NVM enable these smart DACs for processor-less applications and design reuse. These devices automatically detect I<sup>2</sup>C, SPI, and PMBus interfaces, and contain an internal reference.

The feature set combined with the tiny package and low power make these smart DACs an excellent choice for applications such as voltage margining and scaling, dc set-point for biasing and calibration, and waveform generation.

#### **Device Information**

PART NUMBER	RESOLUTION	PACKAGE <sup>(1)</sup>
DAC63004W	12-bit	YBH (DSBGA, 16)
DAC53004W	10-bit	YBH (DSBGA, 16)

(1) For more information, see Section 10.



Simplified Block Diagram



## **Table of Contents**

1 Features	1
2 Applications	
3 Description	
4 Pin Configuration and Functions	3
5 Specifications	4
5.1 Absolute Maximum Ratings	4
5.2 ESD Ratings	4
5.3 Recommended Operating Conditions	4
5.4 Thermal Information	4
5.5 Electrical Characteristics: Voltage Output	5
5.6 Electrical Characteristics: Current Output	7
5.7 Electrical Characteristics: Comparator Mode	
5.8 Electrical Characteristics: General	10
5.9 Timing Requirements: I <sup>2</sup> C Standard Mode	
5.10 Timing Requirements: I <sup>2</sup> C Fast Mode	
5.11 Timing Requirements: I <sup>2</sup> C Fast Mode Plus	11
5.12 Timing Requirements: SPI Write Operation	12
5.13 Timing Requirements: SPI Read and Daisy	
Chain Operation (FSDO = 0)	12
5.14 Timing Requirements: SPI Read and Daisy	
Chain Operation (FSDO = 1)	
5.15 Timing Requirements: GPIO	
5.16 Timing Diagrams	
5.17 Typical Characteristics: Voltage Output	15

5.18 Typical Characteristics: Current Output	. 20
5.19 Typical Characteristics: Comparator	25
5.20 Typical Characteristics: General	. 26
6 Detailed Description	
6.1 Overview	
6.2 Functional Block Diagram	27
6.3 Feature Description.	28
6.4 Device Functional Modes	
6.5 Programming	. 47
6.6 Register Map	55
7 Application and Implementation	73
7.1 Application Information	
7.2 Typical Application	. 73
7.3 Power Supply Recommendations	76
7.4 Layout	. 76
8 Device and Documentation Support	77
8.1 Receiving Notification of Documentation Updates	77
8.2 Support Resources	. 77
8.3 Trademarks	77
8.4 Electrostatic Discharge Caution	77
8.5 Glossary	
9 Revision History	. 77
10 Mechanical, Packaging, and Orderable	
Information	. 77



## **4** Pin Configuration and Functions




Figure 4-1. YBH Package, 16-pin DSBGA (Top View)

#### **Table 4-1. Pin Functions**

	PIN		DESCRIPTION	
NO.	NAME	ITPE	DESCRIPTION	
A1	VREF	Power	External reference input. Connect a capacitor (approximately 0.1 $\mu$ F) between VREF and AGND. Use a pullup resistor to VDD when the external reference is not used. Do not ramp up this pin before VDD. In case an external reference is used, make sure the reference ramps up after VDD.	
A2	OUT3	Output	Analog output voltage from DAC channel 3.	
A3	OUT2	Output	Analog output voltage from DAC channel 2.	
A4	GPIO/SDO	Input/Output	General-purpose input/output configurable as <u>LDAC</u> , <u>PD</u> , <u>PROTECT</u> , <u>RESET</u> , SDO, and <u>STATUS</u> . For <u>STATUS</u> and SDO, connect the pin to the IO voltage with an external pullup resistor. If unused, connect the GPIO pin to VDD or AGND using an external resistor. This pin can ramp up before VDD.	
B1	VDD	Power	Supply voltage.	
B2	FB3	Input	Voltage feedback pin for channel 3. In voltage-output mode, connect to OUT3 for closed-loop amplifier output. In current-output mode, keep the FB3 pin unconnected to minimize leakage current.	
В3	FB2	Input	Voltage feedback pin for channel 2. In voltage-output mode, connect to OUT2 for closed-loop at output. In current-output mode, keep the FB2 pin unconnected to minimize leakage current.	
B4	SCL/SYNC	Output	I <sup>2</sup> C serial interface clock or SPI chip select input. Connect this to the IO voltage using an external pullup resistor. This pin can ramp up before VDD.	
C1	AGND	Ground	Ground reference point for all circuitry on the device.	
C2	FB0	Input	Voltage feedback pin for channel 0. In voltage-output mode, connect to OUT0 for closed-loop amplifier output. In current-output mode, keep the FB0 pin unconnected to minimize leakage current.	
C3	FB1	Input	Voltage feedback pin for channel 1. In voltage-output mode, connect to OUT1 for closed-loop amplifier output. In current-output mode, keep the FB1 pin unconnected to minimize leakage current.	
C4	A0/SDI	Input	Address configuration pin for I <sup>2</sup> C or serial data input for SPI. For A0, connect this pin to VDD, AGND, SDA, or SCL for address configuration (Section 6.5.2.2.1). For SDI, this pin need not be pulled up or pulled down. This pin can ramp up before VDD.	
D1	CAP	Power	External bypass capacitor for the internal LDO. Connect a capacitor (approximately 1.5 $\mu F)$ between CAP and AGND.	
D2	OUT0	Output	Analog output voltage from DAC channel 0.	
D3	OUT1	Output	Analog output voltage from DAC channel 1.	
D4	SDA/SCLK	Input/Output	Bidirectional I <sup>2</sup> C serial data bus or SPI clock input. Connect this pinto the IO voltage using an external pullup resistor in I <sup>2</sup> C mode. This pin can ramp up before VDD.	



## **5** Specifications

### 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
V <sub>DD</sub>	Supply voltage, V <sub>DD</sub> to AGND	-0.3	6	V
	Digital inputs to AGND	-0.3	V <sub>DD</sub> + 0.3	V
	V <sub>FBX</sub> to AGND	-0.3	V <sub>DD</sub> + 0.3	V
	V <sub>OUTX</sub> to AGND	-0.3	V <sub>DD</sub> + 0.3	V
V <sub>REF</sub>	External reference, V <sub>REF</sub> to AGND	-0.3	V <sub>DD</sub> + 0.3	V
	Current into any pin except the OUTx, VDD, and AGND pins	-10	10	mA
TJ	Junction temperature	-40	150	°C
T <sub>stg</sub>	Storage temperature	-65	150	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

### 5.2 ESD Ratings

			VALUE	UNIT	
	Electrostatic	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>	±2000	V	
V <sub>(ESD)</sub>	discharge	Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002, all pins <sup>(2)</sup>	±500	v	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

#### **5.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM MAX	UNIT
V <sub>DD</sub>	Positive supply voltage to ground (AGND)	1.7	5.5	V
V <sub>REF</sub>	External reference to ground (AGND)	1.7	V <sub>DD</sub>	V
VIH	Digital input high voltage, 1.7 V < $V_{DD} \le 5.5$ V	1.62		V
VIL	Digital input low voltage		0.4	V
C <sub>CAP</sub>	External capacitor on CAP pin	0.5	15	μF
T <sub>A</sub>	Ambient temperature	-40	125	°C

### 5.4 Thermal Information

		DACx3004W	
	THERMAL METRIC <sup>(1)</sup>	YBH (DSBGA)	UNIT
		16 PINS	
R <sub>θJA</sub>	Junction-to-ambient thermal resistance	81.2	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	0.3	°C/W
R <sub>θJB</sub>	Junction-to-board thermal resistance	20.3	°C/W
$\Psi_{JT}$	Junction-to-top characterization parameter	0.2	°C/W
$\Psi_{JB}$	Junction-to-board characterization parameter	20.3	°C/W

(1) For information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



### 5.5 Electrical Characteristics: Voltage Output

all minimum/maximum specifications at  $T_A = -40^{\circ}$ C to +125°C and typical specifications at  $T_A = 25^{\circ}$ C, 1.7 V  $\leq V_{DD} \leq 5.5$  V, DAC reference tied to VDD, gain = 1 ×, DAC output pin (OUT) loaded with resistive load ( $R_L = 5 \text{ k}\Omega$  to AGND) and capacitive load ( $C_L = 200 \text{ pF}$  to AGND), and digital inputs at VDD or AGND (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
STAT	IC PERFORMANCE	· · ·				
	Deschation	DAC63004W	12			Dite
	Resolution	DAC53004W	10			Bits
1.5.11	Internel mentione with (1)	DAC63004W	-5		5	
INL	Integral nonlinearity <sup>(1)</sup>	DAC53004W	-1.25		1.25	LSB
DNL	Differential nonlinearity <sup>(1)</sup>		-1		1	LSB
		Code 0d into DAC, external reference, $V_{DD}$ = 5.5 V		6	12	
	Zero-code error <sup>(4)</sup>	Code 0d into DAC, internal V <sub>REF</sub> , gain = 4 ×, V <sub>DD</sub> = 5.5 V		6	15	mV
	Zero-code error temperature coefficient <sup>(4)</sup>			±10		µV/°C
	Offset error <sup>(4) (6)</sup>	1.7 V $\leq$ V <sub>DD</sub> $<$ 2.7 V, V <sub>FB</sub> pin shorted to V <sub>OUT</sub> , DAC code: 32d for 12-bit resolution	-0.75	0.3	0.75	%FSR
		2.7 V $\leq$ V <sub>DD</sub> $\leq$ 5.5 V, V <sub>FB</sub> pin shorted to V <sub>OUT</sub> , DAC code: 32d for 12-bit resolution	-0.5	0.25	0.5	
	$\begin{array}{l} \text{Offset-error temperature} \\ \text{coefficient}^{(4)} \end{array}$	$V_{\text{FB}}$ pin shorted to $V_{\text{OUT}},$ DAC code: 32d for 12-bit resolution, 8d for 10-bit resolution		±0.0003		%FSR/°C
	Gain error <sup>(4)</sup>	Between end-point codes: 32d to 4064d for 12-bit resolution, 8d to 1016d for 10-bit resolution	-0.5	0.25	0.5	%FSR
	Gain-error temperature coefficient <sup>(4)</sup>	Between end-point codes: 32d to 4064d for 12-bit resolution, 8d to 1016d for 10-bit resolution		±0.0008		%FSR/°C
	Full-scale error <sup>(4)</sup> (6)	$1.7 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$ , DAC at full-scale	-1		1	%FSR
		2.7 V $\leq$ V <sub>DD</sub> $\leq$ 5.5 V, DAC at full-scale	-0.5		0.5	70F SIX
	Full-scale-error temperature coefficient <sup>(4)</sup>	DAC at full-scale		±0.0008		%FSR/°C
ουτι	PUT					
	Output voltage	Reference tied to V <sub>DD</sub>	0		$V_{DD}$	V
CL	Capacitive load <sup>(2)</sup>	R <sub>L</sub> = infinite, phase margin = 30°			200	pF
ΟĽ		Phase margin = 30°			1000	Pi
		$V_{\text{DD}}$ = 1.7 V, full-scale output shorted to AGND or zero-scale output shorted to $V_{\text{DD}}$		15		
	Short-circuit current	$V_{\text{DD}}$ = 2.7 V, full-scale output shorted to AGND or zero-scale output shorted to $V_{\text{DD}}$		50		mA
		$V_{\text{DD}}$ = 5.5 V, full-scale output shorted to AGND or zero-scale output shorted to $V_{\text{DD}}$		60		
		To V <sub>DD</sub> (DAC output unloaded, internal reference = 1.21 V), V <sub>DD</sub> $\ge$ 1.21 V $\times$ gain + 0.2 V	0.2			V
	Output-voltage headroom <sup>(2)</sup>	To $V_{DD}$ and to AGND (DAC output unloaded, external reference at $V_{DD}$ (gain = 1 ×), the $V_{REF}$ pin is not shorted to $V_{DD}$ )	0.8			
		To V <sub>DD</sub> and to AGND ( $I_{LOAD}$ = 10 mA at V <sub>DD</sub> = 5.5 V, $I_{LOAD}$ = 3 mA at V <sub>DD</sub> = 2.7 V, $I_{LOAD}$ = 1 mA at V <sub>DD</sub> = 1.8 V), external reference at V <sub>DD</sub> (gain = 1 ×), the V <sub>REF</sub> pin is not shorted to V <sub>DD</sub> )	10			%FSR
Z <sub>O</sub>	V <sub>FB</sub> dc output impedance <sup>(3)</sup>	DAC output enabled, internal reference (gain = $1.5 \times$ or $2 \times$ ) or external reference at V <sub>DD</sub> (gain = $1 \times$ ), the V <sub>REF</sub> pin is not shorted to V <sub>DD</sub>	400	500	600	kΩ
		DAC output enabled, internal $V_{REF}$ , gain = 3 × or 4 ×	325	400	485	

Copyright © 2025 Texas Instruments Incorporated

## 5.5 Electrical Characteristics: Voltage Output (continued)

all minimum/maximum specifications at  $T_A = -40^{\circ}$ C to +125°C and typical specifications at  $T_A = 25^{\circ}$ C, 1.7 V  $\leq V_{DD} \leq 5.5$  V, DAC reference tied to VDD, gain = 1 ×, DAC output pin (OUT) loaded with resistive load ( $R_L = 5 \text{ k}\Omega$  to AGND) and capacitive load ( $C_L = 200 \text{ pF}$  to AGND), and digital inputs at VDD or AGND (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
	Power supply rejection ratio (dc)	Internal V <sub>REF</sub> , gain = 2 ×, DAC at midscale, V <sub>DD</sub> = 5 V ±10%		0.25		mV/V
DYN	AMIC PERFORMANCE					
+	Output voltage settling time	1/4 to 3/4 scale and 3/4 to 1/4 scale settling to 10%FSR, $V_{\text{DD}}$ = 5.5 V		20		110
t <sub>sett</sub>	Output voltage setting time	1/4 to 3/4 scale and 3/4 to 1/4 scale settling to 10%FSR, $V_{DD}$ = 5.5 V, internal $V_{REF}$ , gain = 4 ×		25		μs
	Slew rate	V <sub>DD</sub> = 5.5 V		0.3		V/µs
	Power-on glitch magnitude	At start-up (DAC output disabled)		75		mV
	Fower-on glitch magnitude	At start-up (DAC output disabled), $R_L$ = 100 k $\Omega$		200		IIIV
	Output-enable glitch magnitude	DAC output disabled to enabled (DAC registers at zero scale), R <sub>L</sub> = 100 k $\Omega$	·	250		mV
	Output poice voltage (peek to	f = 0.1 Hz to 10 Hz, DAC at midscale, $V_{DD}$ = 5.5 V		50		
Vn	Output noise voltage (peak to peak)	Internal V <sub>REF</sub> , gain = 4 ×, f = 0.1 Hz to 10 Hz, DAC at midscale, V <sub>DD</sub> = 5.5 V		90		μV <sub>PP</sub>
		f = 1 kHz, DAC at midscale, V <sub>DD</sub> = 5.5 V		0.35		
	Output noise density	Internal V <sub>REF,</sub> gain = 4 ×, f = 1 kHz, DAC at midscale, V <sub>DD</sub> = 5.5 V	·	0.9		µV/√ <del>Hz</del>
	Power supply rejection ratio (ac) <sup>(3)</sup>	Internal V <sub>REF</sub> , gain = 4 ×, 200-mV 50-Hz or 60-Hz sine wave superimposed on power supply voltage, DAC at midscale		-68		dB
	Code change glitch impulse	±1 LSB change around midscale (including feedthrough)	·	10		nV-s
	Code change glitch impulse magnitude	±1 LSB change around midscale (including feedthrough)		15		mV
POW	/ER					
I <sub>DD</sub>	Current flowing into VDD <sup>(4) (5)</sup>	Normal operation, DACs at full scale, digital pins static, external reference at $V_{\text{DD}}$ but the $V_{\text{REF}}$ pin is not shorted to $V_{\text{DD}}$		35	50	µA/ch

(1) Measured with DAC output unloaded. For external reference and internal reference V<sub>DD</sub> ≥ 1.21 × gain + 0.2 V, between end-point codes: 32d to 4064d for 12-bit resolution, 8d to 1016d for 10-bit resolution.

(2) Specified by design and characterization, not production tested.

(3) Specified with 200-mV headroom with respect to reference value when internal reference is used.

(4) Measured with DAC output unloaded.

(5) The total power consumption is calculated by I<sub>DD</sub> × (total number of channels powered on) + (sleep-mode current).

(6) When a DAC channel is configured in IOUT mode for long term and then switched to VOUT mode, the VOUT mode can show parametric drift.

## 5.6 Electrical Characteristics: Current Output

all minimum/maximum specifications at  $T_A = -40$ °C to +125°C and typical specifications at  $T_A = 25$ °C, 1.7 V  $\leq V_{DD} \leq 5.5$  V, ±250-µA output range, and digital inputs at VDD or AGND (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
STAT	IC PERFORMANCE					
	Resolution		8			Bits
INL	Integral nonlinearity	DAC codes between 10d and 255d for current output range of 0 $\mu A$ to 25 $\mu A,$ DAC codes between 0d and 255d for other ranges	-1		1	LSB
DNL	Differential nonlinearity	DAC codes between 10d and 255d for current output range of 0 $\mu A$ to 25 $\mu A,$ DAC codes between 0d and 255d for other ranges	-1		1	LSB
	Offset error	DAC output range: 0 µA to 25 µA, DAC at code 10d		±1.5		%FSR
	Offset error	DAC output ranges: 0 $\mu A$ to 50 $\mu A,$ 0 $\mu A$ to 125 $\mu A,$ and 0 $\mu A$ to 250 $\mu A;$ DAC at zero-scale	·	5		%FSR
	Offset error	all unipolar negative ranges, DAC at zero-scale		-5		%FSR
	Offset error	DAC output ranges: ±25 μA, ±50 μA, ±125 μA, and ±250 μA; DAC at midscale		±1		%FSR
	Gain error	DAC output range: 0 µA to 25 µA, DAC codes between 10d and 255d		±1.5		%FSR
	Gain error	DAC output ranges: 0 $\mu$ A to 50 $\mu$ A, 0 $\mu$ A to 125 $\mu$ A, and 0 $\mu$ A to 250 $\mu$ A; DAC codes between 0d and 255d		±1.5		%FSR
	Gain error	all unipolar negative ranges, DAC codes between 0d and 255d		±5		%FSR
	Gain error	DAC output ranges: ±25 $\mu$ A, ±50 $\mu$ A, ±125 $\mu$ A, and ±250 $\mu$ A; DAC codes between 0d and 255d		±1.3		%FSR
ουτι	PUT					
	Output compliance voltage <sup>(1)</sup>	DAC output range: 0 $\mu A$ to 25 $\mu A,$ to $V_{DD}$ and to $A_{GND}$	200			mV
	Output compliance voltage <sup>(1)</sup>	DAC output ranges: 0 $\mu A$ to 50 $\mu A,$ 0 $\mu A$ to 125 $\mu A,$ and 0 $\mu A$ to 250 $\mu A;$ to $V_{DD}$	400			mV
	Output compliance voltage <sup>(1)</sup>	all unipolar negative ranges, to V <sub>DD</sub>	400			mv
	Output compliance voltage <sup>(1)</sup>	DAC output ranges: ±25 $\mu A,$ ±50 $\mu A,$ ±125 $\mu A,$ and ±250 $\mu A;$ to $V_{DD}$ and to AGND	400			mV
Zo	I <sub>OUT</sub> dc output impedance <sup>(2)</sup>	DAC at midscale, DAC output kept at $V_{DD}/2$	60			MΩ
	Power supply rejection ratio (dc)	DAC at midscale, output range: 0 $\mu A$ to 25 $\mu A,$ $V_{DD}$ changed from 4.5 V to 5.5 V		0.28		LSB/V
	Power supply rejection ratio (dc)	DAC at midscale, all unipolar positive ranges, $V_{\text{DD}}$ changed from 4.5 V to 5.5V		0.33		LSB/V
	Power supply rejection ratio (dc)	DAC at midscale, all unipolar negative ranges, $V_{\text{DD}}$ changed from 4.5 V to 5.5V		0.83		LSB/V
	Power supply rejection ratio (dc)	DAC at midscale, all bipolar ranges, $V_{\text{DD}}$ changed from 4.5V to 5.5V	·	0.23		LSB/V
DYN	AMIC PERFORMANCE					
t <sub>sett</sub>	Output current settling time	1/4 to 3/4 scale and 3/4 to 1/4 scale settling to 1 LSB at 8-bit resolution, $V_{DD}$ = 5.5 V, common-mode voltage at OUTx pin is $V_{DD}/2$		60		μs
Vn	Output noise current (peak to peak)	0.1 Hz to 10 Hz, DAC at midscale, $V_{DD}$ = 5.5 V, ±250-µA output range		150		nA <sub>PP</sub>
	Output noise density	f = 1 kHz, DAC at midscale, $V_{DD}$ = 5.5 V, ±250- $\mu$ A output range		1		nA/√Hz
	Power supply rejection ratio (ac) <sup>(3)</sup>	±250 µA output range, 200-mV 50-Hz or 60-Hz sine wave superimposed on power-supply voltage, DAC at midscale		0.65		LSB/V



## 5.6 Electrical Characteristics: Current Output (continued)

all minimum/maximum specifications at  $T_A = -40^{\circ}$ C to +125°C and typical specifications at  $T_A = 25^{\circ}$ C, 1.7 V  $\leq V_{DD} \leq 5.5$  V, ±250-µA output range, and digital inputs at VDD or AGND (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
POWER							
I <sub>DD</sub>	Current flowing into VDD <sup>(3) (4)</sup>	Normal operation, DACs at midscale, all unipolar output ranges, digital pins static		18	24	µA/ch	
I <sub>DD</sub>	Current flowing into VDD <sup>(3) (4)</sup>	Normal operation, DACs at full scale, ±25-µA output range, digital pins static		42	50		
		Normal operation, DACs at full scale, ±50-µA output range, digital pins static		56	70		
		Normal operation, DACs at full scale, ±125-µA output range, digital pins static		98	120	µA/ch	
		Normal operation, DACs at full scale, ±250-µA output range, digital pins static		167	200		

(1) Measured between DAC codes 0d and 255d.

(2) Specified by design and characterization, not production tested.

(3) The current flowing into  $V_{DD}$  does not account for the load current sourced or sunk on the OUTx pins. The  $V_{REF}$  pin is connected to  $V_{DD}$ .

(4) The total power consumption is calculated by I<sub>DD</sub> × (total number of channels powered on) + (sleep-mode current).



### 5.7 Electrical Characteristics: Comparator Mode

all minimum/maximum specifications at  $T_A = -40^{\circ}$ C to +125°C and typical specifications at  $T_A = 25^{\circ}$ C, 1.7 V  $\leq$  V<sub>DD</sub>  $\leq$  5.5 V, DAC reference tied to VDD, gain = 1 × in voltage output mode, DAC output pin (OUT) loaded with resistive load (R<sub>L</sub> = 5 k $\Omega$  to AGND) and capacitive load (C<sub>L</sub> = 200 pF to AGND), and digital inputs at VDD or AGND (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
STAT	IC PERFORMANCE	·				
	Offset error <sup>(1) (2)</sup>	1.7 V $\leq$ V <sub>DD</sub> $\leq$ 5.5 V; DAC at midscale, comparator input at Hi-Z, and DAC operating with external reference.	-6	0	6	mV
	Offset error time drift <sup>(1)</sup>	$V_{DD}$ = 5.5 V, external reference, $T_A$ = 125°C, FB in Hi-Z mode, DAC at full scale and $V_{FB}$ at 0 V or DAC at zero scale and $V_{FB}$ at 1.84 V, drift specified for 10 years of continuous operation		4		mV
OUT	PUT	· · · ·				
		$V_{\text{REF}}$ connected to $V_{\text{DD}}, V_{\text{FB}}$ resistor network connected to ground	0		V <sub>DD</sub>	V
	Input voltage	$V_{\text{REF}}$ connected to $V_{\text{DD}}, V_{\text{FB}}$ resistor network disconnected from ground	0		V <sub>DD</sub> × (1/3 – 1/100)	v
V <sub>OL</sub>	Logic low output voltage	I <sub>LOAD</sub> = 100 μA, output in open-drain mode		0.1		V
DYN	AMIC PERFORMANCE					
t <sub>resp</sub>	Output response time	DAC at midscale with 10-bit resolution, FB input at Hi-Z, and transition step at FB node is $(V_{DAC} - 2 LSB)$ to $(V_{DAC} + 2 LSB)$ , transition time measured between 10% and 90% of output, output current of 100 µA, comparator output configured in push-pull mode, load capacitor at DAC output is 25 pF		10		μs

(1) Specified by design and characterization, not production tested.

(2) This specification does not include the total unadjusted error (TUE) of the DAC.



### **5.8 Electrical Characteristics: General**

all minimum/maximum specifications at  $T_A = -40^{\circ}$ C to +125°C and typical specifications at  $T_A = 25^{\circ}$ C, 1.7 V  $\leq V_{DD} \leq 5.5$  V, DAC reference tied to VDD, gain = 1 × in voltage output mode or ±250-µA output range in current output mode, DAC output pin (OUT) loaded with resistive load ( $R_L = 5 \text{ k}\Omega$  to AGND) in voltage-output mode and capacitive load ( $C_L = 200 \text{ pF}$  to AGND), and digital inputs at VDD or AGND (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
NTE	RNAL REFERENCE						
	Initial accuracy	T <sub>A</sub> = 25°C	1.1979	1.212	1.224	V	
	Reference output temperature coefficient <sup>(1)</sup> <sup>(2)</sup>				50	ppm/°C	
EXTE	RNAL REFERENCE						
	V <sub>REF</sub> input impedance <sup>(1) (3)</sup>			192		kΩ-ch	
EPF	ROM						
	Endurance <sup>(1)</sup>	$-40^{\circ}C \le T_A \le +85^{\circ}C$	20000				
	Endurance	T <sub>A</sub> = 125°C		1000		Cycles	
	Data retention <sup>(1)</sup>	T <sub>A</sub> = 25°C		50		Years	
	EEPROM programming write cycle time <sup>(1)</sup>				200	ms	
	Device boot-up time <sup>(1)</sup>	Time taken from power valid ( $V_{DD} \ge 1.7 \text{ V}$ ) to output valid state (output state as programmed in EEPROM), 0.5-µF capacitor on the CAP pin		5		ms	
DIGIT	TAL INPUTS	· · · · · ·					
	Digital feedthrough	Voltage output mode, DAC output static at midscale, fast mode plus, SCL toggling	20			nV-s	
	Pin capacitance	Per pin		10		pF	
POW	ER-DOWN MODE	l I			I		
DD	Current flowing into VDD	DAC in deep-sleep mode, internal reference powered down, SDO mode disabled		1.5	3	μA	
DD	Current flowing into VDD	DAC in sleep mode, internal reference powered down, external reference at 5.5 V			28	μA	
DD	Current flowing into VDD <sup>(1)</sup>	DAC in sleep mode, internal reference enabled, additional current through internal reference		10		μA	
DD	Current flowing into VDD <sup>(1)</sup>	DAC channels enabled, internal reference enabled, additional current through internal reference per DAC channel in voltage-output mode		12.5		μA	
HIGH	-IMPEDANCE OUTPUT						
		DAC in Hi-Z output mode, 1.7 V $\leq$ V <sub>DD</sub> $\leq$ 5.5 V		10		nA	
		$V_{DD}$ = 0 V, $V_{OUT}$ ≤ 1.5 V, decoupling capacitor between $V_{DD}$ and AGND = 0.1 $\mu F$		200		nA	
LEAK	Current flowing into $V_{OUTX}$ and $V_{FBX}$	$V_{DD}$ = 0 V, 1.5 V < $V_{OUT}$ ≤ 5.5 V, decoupling capacitor between $V_{DD}$ and AGND = 0.1 $\mu$ F		500		nA	
		100 kΩ between V <sub>DD</sub> and AGND, V <sub>OUT</sub> ≤ 1.25 V, series resistance of 10 kΩ at OUT pin		±2		μA	

(1) Specified by design and characterization, not production tested.

(2) Measured at  $-40^{\circ}$ C and  $+125^{\circ}$ C and calculated the slope.

(3) Impedances for the DAC channels are connected in parallel.



### 5.9 Timing Requirements: I<sup>2</sup>C Standard Mode

all input signals are timed from VIL to 70% of  $V_{pull-up}$ , 1.7 V  $\leq V_{DD} \leq 5.5$  V,  $-40^{\circ}C \leq T_A \leq +125^{\circ}C$ , and 1.7 V  $\leq V_{pull-up} \leq V_{DD}$  V

		MIN	NOM MAX	UNIT
f <sub>SCL</sub>	SCL frequency		100	kHz
t <sub>BUF</sub>	Bus free time between stop and start conditions	4.7		μs
t <sub>HDSTA</sub>	Hold time after repeated start	4		μs
t <sub>SUSTA</sub>	Repeated start setup time	4.7		μs
t <sub>SUSTO</sub>	Stop condition setup time	4		μs
t <sub>HDDAT</sub>	Data hold time	0		ns
t <sub>SUDAT</sub>	Data setup time	250		ns
t <sub>LOW</sub>	SCL clock low period	4700		ns
t <sub>HIGH</sub>	SCL clock high period	4000		ns
t <sub>F</sub>	Clock and data fall time		300	ns
t <sub>R</sub>	Clock and data rise time		1000	ns
t <sub>VDDAT</sub>	Data valid time, R = 360 $\Omega$ , C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF		3.45	μs
t <sub>VDACK</sub>	Data valid acknowledge time, R = 360 $\Omega$ , C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF		3.45	μs

## 5.10 Timing Requirements: I<sup>2</sup>C Fast Mode

all input signals are timed from VIL to 70% of  $V_{pull-up}$ , 1.7 V  $\leq V_{DD} \leq 5.5$  V,  $-40^{\circ}C \leq T_A \leq +125^{\circ}C$ , and 1.7 V  $\leq V_{pull-up} \leq V_{DD}$  V

		MIN	NOM	MAX	UNIT
f <sub>SCL</sub>	SCL frequency			400	kHz
t <sub>BUF</sub>	Bus free time between stop and start conditions	1.3			μs
t <sub>HDSTA</sub>	Hold time after repeated start	0.6			μs
t <sub>SUSTA</sub>	Repeated start setup time	0.6			μs
t <sub>SUSTO</sub>	Stop condition setup time	0.6			μs
t <sub>HDDAT</sub>	Data hold time	0			ns
t <sub>SUDAT</sub>	Data setup time	100			ns
t <sub>LOW</sub>	SCL clock low period	1300			ns
t <sub>HIGH</sub>	SCL clock high period	600			ns
t <sub>F</sub>	Clock and data fall time			300	ns
t <sub>R</sub>	Clock and data rise time			300	ns
t <sub>VDDAT</sub>	Data valid time, R = 360 $\Omega$ , C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF			0.9	μs
t <sub>VDACK</sub>	Data valid acknowledge time, R = 360 $\Omega$ , C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF			0.9	μs

## 5.11 Timing Requirements: I<sup>2</sup>C Fast Mode Plus

all input signals are timed from VIL to 70% of  $V_{pull-up}$ , 1.7 V  $\leq V_{DD} \leq 5.5$  V,  $-40^{\circ}C \leq T_A \leq +125^{\circ}C$ , and 1.7 V  $\leq V_{pull-up} \leq V_{DD}$  V

		MIN	NOM	MAX	UNIT
f <sub>SCL</sub>	SCL frequency			1	MHz
t <sub>BUF</sub>	Bus free time between stop and start conditions	0.5			μs
t <sub>HDSTA</sub>	Hold time after repeated start	0.26			μs
t <sub>SUSTA</sub>	Repeated start setup time	0.26			μs
t <sub>susto</sub>	Stop condition setup time	0.26			μs
t <sub>HDDAT</sub>	Data hold time	0			ns
t <sub>SUDAT</sub>	Data setup time	50			ns
t <sub>LOW</sub>	SCL clock low period	0.5			μs
t <sub>HIGH</sub>	SCL clock high period	0.26			μs
t <sub>F</sub>	Clock and data fall time			120	ns
t <sub>R</sub>	Clock and data rise time			120	ns
t <sub>VDDAT</sub>	Data valid time, R = 360 Ω, C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF			0.45	μs
t <sub>VDACK</sub>	Data valid acknowledge time, R = 360 $\Omega$ , C <sub>trace</sub> = 23 pF, C <sub>probe</sub> = 10 pF			0.45	μs



### 5.12 Timing Requirements: SPI Write Operation

all input signals are specified with  $t_r = t_f = 1$  V/ns (10% to 90% of  $V_{IO}$ ) and timed from a voltage level of (VIL + VIH) / 2, 1.7 V  $\leq V_{IO} \leq 5.5$  V, 1.7 V  $\leq V_{DD} \leq 5.5$  V, and  $-40^{\circ}C \leq T_A \leq +125^{\circ}C$ 

		MIN	NOM	MAX	UNIT
f <sub>SCLK</sub>	Serial clock frequency			50	MHz
t <sub>SCLKHIGH</sub>	SCLK high time	9			ns
t <sub>SCLKLOW</sub>	SCLK low time	9			ns
t <sub>SDIS</sub>	SDI setup time	8			ns
t <sub>SDIH</sub>	SDI hold time	8			ns
t <sub>CSS</sub>	CS to SCLK falling edge setup time	18			ns
t <sub>CSH</sub>	SCLK falling edge to CS rising edge	10			ns
t <sub>CSHIGH</sub>	CS high time	50			ns
t <sub>DACWAIT</sub>	Sequential DAC update wait time (time between subsequent LDAC falling edges) for same channel	2			μs
t <sub>BCASTWAIT</sub>	Broadcast DAC update wait time (time between subsequent LDAC falling edges)	2			μs

### 5.13 Timing Requirements: SPI Read and Daisy Chain Operation (FSDO = 0)

all input signals are specified with  $t_r = t_f = 1$  V/ns (10% to 90% of V<sub>IO</sub>) and timed from a voltage level of (VIL + VIH) / 2, 1.7 V  $\leq$  V<sub>IO</sub>  $\leq$  5.5 V, 1.7 V  $\leq$  V<sub>DD</sub>  $\leq$  5.5 V, -40°C  $\leq$  T<sub>A</sub>  $\leq$  +125°C, and FSDO = 0

		MIN	NOM MAX	UNIT
f <sub>SCLK</sub>	Serial clock frequency		1.25	6 MHz
t <sub>SCLKHIGH</sub>	SCLK high time	350		ns
t <sub>SCLKLOW</sub>	SCLK low time	350		ns
t <sub>SDIS</sub>	SDI setup time	8		ns
t <sub>SDIH</sub>	SDI hold time	8		ns
t <sub>CSS</sub>	SYNC to SCLK falling edge setup time	400		ns
t <sub>CSH</sub>	SCLK falling edge to SYNC rising edge	400		ns
t <sub>CSHIGH</sub>	SYNC high time	1		μs
t <sub>SDODLY</sub>	SCLK rising edge to SDO falling edge, $I_{OL} \le 5$ mA, $C_L = 20$ pF.		300	ns

### 5.14 Timing Requirements: SPI Read and Daisy Chain Operation (FSDO = 1)

all input signals are specified with  $t_r = t_f = 1$  V/ns (10% to 90% of V<sub>IO</sub>) and timed from a voltage level of (VIL + VIH) / 2, 1.7 V  $\leq$  V<sub>IO</sub>  $\leq$  5.5 V, 1.7 V  $\leq$  V<sub>DD</sub>  $\leq$  5.5 V, -40°C  $\leq$  T<sub>A</sub>  $\leq$  +125°C, and FSDO = 1

		MIN	NOM	MAX	UNIT
f <sub>SCLK</sub>	Serial clock frequency			2.5	MHz
t <sub>SCLKHIGH</sub>	SCLK high time	175			ns
t <sub>SCLKLOW</sub>	SCLK low time	175			ns
t <sub>SDIS</sub>	SDI setup time	8			ns
t <sub>SDIH</sub>	SDI hold time	8			ns
t <sub>CSS</sub>	SYNC to SCLK falling edge setup time	300			ns
t <sub>CSH</sub>	SCLK falling edge to SYNC rising edge	300			ns
t <sub>CSHIGH</sub>	SYNC high time	1			μs
t <sub>SDODLY</sub>	SCLK rising edge to SDO falling edge, $I_{OL} \le 5$ mA, $C_L = 20$ pF.			300	ns




### 5.15 Timing Requirements: GPIO


all input signals are specified with  $t_r = t_f = 1$  V/ns (10% to 90% of V<sub>IO</sub>) and timed from a voltage level of (VIL + VIH) / 2, 1.7 V  $\leq$  V<sub>IO</sub>  $\leq$  5.5 V, 1.7 V  $\leq$  V<sub>DD</sub>  $\leq$  5.5 V, and  $-40^{\circ}C \leq$  T<sub>A</sub>  $\leq$  +125°C

		MIN	NOM	MAX	UNIT
t <sub>GPIHIGH</sub>	GPI high time	2			μs
t <sub>GPILOW</sub>	GPI low time	2			μs
t <sub>GPAWGD</sub>	LDAC falling edge to DAC update delay			2	μs
t <sub>CS2LDAC</sub>	SYNC rising edge to LDAC falling edge	1			μs
t <sub>STP2LDAC</sub>	I <sup>2</sup> C stop bit rising edge to LDAC falling edge	1			μs
t <sub>LDACW</sub>	LDAC low time	2			μs

## 5.16 Timing Diagrams










Figure 5-3. SPI Read Timing Diagram

DAC53004W, DAC63004W

SLASF72A - MARCH 2023 - REVISED JULY 2025

t<sub>CSHIGH</sub>

1 t<sub>C</sub>

**EXAS** 


 $t_{\text{CSH}}$ 

INSTRUMENTS


www.ti.com




## 5.17 Typical Characteristics: Voltage Output






















## 5.18 Typical Characteristics: Current Output

























### 5.19 Typical Characteristics: Comparator





### 5.20 Typical Characteristics: General

at T<sub>A</sub> = 25°C, V<sub>DD</sub> = 5.5 V, and DAC outputs unloaded (unless otherwise noted)






## 6 Detailed Description

### 6.1 Overview

The 12-bit DAC63004W and 10-bit DAC53004W (DACx3004W) are a pin-compatible family of quad-channel, buffered, voltage-output and current-output, smart digital-to-analog converters (DACs). The DAC channels are independently configurable as voltage or current output. The DAC outputs change to Hi-Z when VDD is off. This feature is useful in voltage-margining applications. These smart DACs contain nonvolatile memory (NVM), an internal reference, automatically detectable SPI or I<sup>2</sup>C interface, PMBus-compatibility in I<sup>2</sup>C mode, force-sense output, and a general-purpose input. These devices support Hi-Z power-down modes by default, which can be configured to 10 k $\Omega$ -GND or 100 k $\Omega$ -GND using the NVM. The DACx3004W have a power-on-reset (POR) circuit that makes sure all the registers start with default or user-programmed settings using NVM. The DACx3004W operate with either an internal reference, external reference, or with a power supply as the reference, and provide a full-scale output of 1.8 V to 5.5 V.

The DACx3004W devices support I<sup>2</sup>C standard mode (100Kbps), fast mode (400Kbps), and fast mode plus (1Mbps). The I<sup>2</sup>C interface can be configured with four target addresses using the A0 pin. These devices also support specific PMBus commands such as *turn on/off, margin high or low*, and more. The SPI mode supports a three-wire interface by default with up to a 50-MHz SCLK input. The GPIO input can be configured as SDO in the NVM for SPI read capability. The GPIO input can alternatively be configured as the LDAC, PD, STATUS, FAULT-DUMP, RESET, or PROTECT function.

The DACx3004W also include digital slew rate control, and support standard waveform generation such as *sine and cosine, triangular*, and *sawtooth* waveforms. These devices can generate pulse-width modulation (PWM) output with the combination of the triangular or sawtooth waveform and the FB pin. The force-sense outputs of the DAC channels can be used as programmable comparators. The comparator mode allows programmable hysteresis, latching comparator, window comparator, and fault-dump to the NVM. These features enable the DACx3004W to go beyond the limitations of a conventional DAC that depends on a processor to function. As a result of *processor-less* operation and the *smart* feature set, the DACx3004W are called smart DACs.



## 6.2 Functional Block Diagram

Figure 6-1. Functional Block Diagram



### 6.3 Feature Description

### 6.3.1 Smart Digital-to-Analog Converter (DAC) Architecture

The DACx3004W devices consist of string architecture with a voltage-output amplifier and an external FB pin and voltage-to-current converter for each channel. Section 6.2 shows the DAC architecture within the block diagram, which operates from a 1.8-V to 5.5-V power supply. The DAC has an internal voltage reference of 1.21 V. There is an option to select an external reference on the VREF pin or the power supply as a reference. The voltage output mode uses one of these three reference options. The current output mode uses an internal band gap to generate the current outputs. Both the voltage- and current-output modes support multiple programmable output ranges.

The DACx3004W devices support Hi-Z output when VDD is off, maintaining very low leakage current at the output pins with up to 1.25 V of forced voltage. The DAC output pin also starts up in high-impedance mode by default, making these devices an excellent choice for voltage margining and scaling applications. To change the power-up mode to 10 k $\Omega$ -GND or 100 k $\Omega$ -GND, program the corresponding VOUT-PDN-X field in the COMMON-CONFIG register and load these bits in the device NVM.

The DACx3004W devices support an independent comparator mode for each channel. The respective FBx pins act as the inputs for the comparator. The DAC architecture supports inversion of the comparator output using register settings. The comparator outputs can be push-pull or open-drain. The comparator mode supports programmable hysteresis using *margin-high* and *margin-low* register fields, latching comparator, and window comparator. The comparator outputs are accessible internally by the device.

The DACx3004W devices include a *smart* feature set to enable processor-less operation and high-integration. The NVM enables a predictable start-up. The GPIO triggers the DAC output without the I<sup>2</sup>C interface in the absence of a processor or when the processor or software fails. The integrated functions and the FBx pin enable PWM output for control applications. The FBx pin enables this device to be used as a programmable comparator. The digital slew-rate control and the Hi-Z power-down modes enable a hassle-free voltage margining and scaling function.

#### 6.3.2 Digital Input/Output

The DACx3004W have four digital IO pins that include I<sup>2</sup>C, SPI, PMBus, and GPIO interfaces. These devices automatically detect I<sup>2</sup>C and SPI protocols at the first successful communication after power-on, and then connect to the detected interface. After an interface protocol is connected, any change in the protocol is ignored. The I<sup>2</sup>C interface uses the A0 pin to select from among four address options. The SPI interface is a 3-wire interface by default. No readback capability is available in this mode. The GPIO pin can be configured in the register map and then programmed in to the NVM as the SDO pin. The SPI readback mode is slower than the write mode. The programming interface pins are:

- I<sup>2</sup>C: SCL, SDA, A0
- SPI: SCLK, SDI, <u>SYNC</u>, SDO/GPIO

The GPIO can be configured as multiple functions other than SDO. These are LDAC, PD, STATUS, PROTECT, FAULT-DUMP, and RESET. All the digital pins are open-drain when used as outputs. Therefore, all the output pins must be pulled up to the desired IO voltage using external resistors.



#### 6.3.3 Nonvolatile Memory (NVM)

The DACx3004W contain nonvolatile memory (NVM) bits. These memory bits are user programmable and erasable, and retain the set values in the absence of a power supply. All the register bits, as shown in the highlighted gray cells in the *Register Map* section, can be stored in the NVM by setting NVM-PROG = 1 in the COMMON-TRIGGER register. The NVM-PROG is an autoresetting bit. The default values for all the registers in the DACx3004W are loaded from NVM as soon as a POR event is issued.

The DACx3004W also implement NVM-RELOAD bit in the COMMON-TRIGGER register. Set this bit to 1 for the device to start an NVM-reload operation. After completion, the device autoresets the NVM-RELOAD bit to 0. During the NVM write or reload operation, all read/write operations to the device are blocked. The *Electrical Characteristics: General* section provides the timing specification for the NVM write cycle. The processor must wait for the specified duration before resuming any read or write operation on the SPI or I<sup>2</sup>C interface.

#### 6.3.4 Power Consumption

The power consumption of the DACx3004W in sleep mode and deep-sleep mode are provided in the *Typical Characteristics: General* section. In normal operation, the total power consumption of the device depends on the number of channels powered on and the output mode of each channel (voltage or current). In current-output mode, the  $I_{DD}$  also depends on the output range. The  $I_{DD}$  calculation excludes the load current. For example, in the ±250 µA output mode with a DAC setting of +125 µA, the total current drawn through the VDD pin is the total  $I_{DD}$  plus 125 µA. The total  $I_{DD}$  in normal operation can be calculated using Equation 1.

$$P_{\text{NORMAL}_MODE} = V_{\text{DD}} \times (I_{\text{DD}_S\text{LEEP}} + I_{\text{DD}_R\text{EF}}) + \sum_{X}^{3} = 0 (V_{\text{DD}} \times I_{\text{DD}_X})$$
(1)

where:

- I<sub>DD\_SLEEP</sub> is the current through V<sub>DD</sub> in sleep mode when all the channels and internal reference are powered down.
- I<sub>DD REF</sub> is the reference current, which is:
  - either the current drawn by the reference input impedance when V<sub>DD</sub> is used as reference
  - or the current drawn by the internal reference, if enabled
- I<sub>DD X</sub> is the current through V<sub>DD</sub> for every powered-on channel-X.

### Note

When an external reference is used, the current is calculated mainly as the current sourced from the external reference, which is equal to the reference voltage divided by the input impedance of the VREF pin.



### 6.4 Device Functional Modes

#### 6.4.1 Voltage-Output Mode

The voltage-output mode for each DAC channel can be entered by selecting the power-up option in the VOUT-PDN-X fields in the COMMON-CONFIG register and simultaneously powering down the current output option for the respective channels using the IOUT-PDN-X bits in the same register. Short the OUTx and FBx pins of respective channels externally for closed-loop amplifier output. An open FBx pin saturates the amplifier output. To achieve the desired voltage output, select the correct reference option, select the amplifier gain for the required output range, and program the DAC code in the DAC-X-DATA register of the respective channels.

#### 6.4.1.1 Voltage Reference and DAC Transfer Function

There are three voltage reference options possible with the DACx3004W: internal reference, external reference, and the power supply as reference, as shown in Figure 6-2. The DAC transfer function in the voltage-output and comparator modes changes based on the voltage reference selection.




Figure 6-2. Voltage Reference Selection and Power-Down Logic

#### 6.4.1.1.1 Internal Reference

The DACx3004W contain an internal reference that is disabled by default. To enable the internal reference, write 1 to bit EN-INT-REF in the COMMON-CONFIG register. The internal reference generates a fixed 1.21-V voltage (typical). Use the VOUT-GAIN-X bit in the DAC-X-VOUT-CMP-CONFIG register to achieve gains of  $1.5 \times 2 \times 3 \times 10^{-4} \times 10^{-4}$  for the DAC output voltage (V<sub>OUT</sub>). Equation 2 shows DAC transfer function using the internal reference.

$$V_{OUT} = \frac{DAC_DATA}{2^N} \times V_{REF} \times GAIN$$

(2)

where:

- N is the resolution in bits, 10 (DAC53004W) or 12 (DAC63004W).
- DAC\_DATA is the decimal equivalent of the binary code that is loaded to the DAC-X-DATA bit in the DAC-X-DATA register. DAC\_DATA ranges from 0 to 2<sup>N</sup> – 1.
- V<sub>REF</sub> is the internal reference voltage = 1.21 V (typical).
- GAIN = 1.5 ×, 2 ×, 3 ×, or 4 ×, based on VOUT-GAIN-X bits.



(3)

(4)

#### 6.4.1.1.2 External Reference

By default, the DACx3004W operate from an external reference input. The external reference option can also be selected by configuring the VOUT-GAIN-X field in the DAC-X-VOUT-CMP-CONFIG register appropriately. Write 1 to the DIS-MODE-IN bit in the DEVICE-MODE-CONFIG register to minimize  $I_{DD}$ . The external reference can be between 1.7 V and VDD. Equation 3 shows DAC transfer function when the external reference is used. The gain at the output stage of the DAC is always 1 × in the external reference mode.

#### Note

The external reference must be less than VDD in both transient and steady-state conditions. Therefore, the external reference must ramp up after VDD and ramp down before VDD.

$$V_{OUT} = \frac{DAC_DATA}{2^N} \times V_{REF}$$

where:

- N is the resolution in bits, 10 (DAC53004W) or 12 (DAC63004W).
- DAC\_DATA is the decimal equivalent of the binary code that is loaded to the DAC-X-DATA field in the DAC-X-DATA register. DAC\_DATA ranges from 0 to 2<sup>N</sup> – 1.
- V<sub>REF</sub> is the external reference voltage.

#### 6.4.1.1.3 Power-Supply as Reference

The DACx3004W can operate with the power-supply pin (VDD) as a reference. Equation 4 shows DAC transfer function when the power-supply pin is used as reference. The gain at the output stage is always 1x.

$$V_{OUT} = \frac{DAC_DATA}{2^N} \times V_{DD}$$

where:

- N is the resolution in bits, 10 (DAC53004W) or 12 (DAC63004W).
- DAC\_DATA is the decimal equivalent of the binary code that is loaded to the DAC-X-DATA bit in the DAC-X-DATA register.
- DAC\_DATA ranges from 0 to 2<sup>N</sup> 1.
- V<sub>DD</sub> is used as the DAC reference voltage.

#### 6.4.2 Current-Output Mode

To enter current-output mode for each DAC channel, disable the respective IOUT-PDN-X bits in the COMMON-CONFIG register, and set the respective VOUT-PDN-X bits in the same register to Hi-Z power-down mode. Select the desired current-output range by writing to the IOUT-RANGE-X bit in the DAC-X-IOUT-MISC-CONFIG register. To minimize leakage in current-output mode, disconnect the FBx pin. For the best power-on glitch performance, program the NVM with IOUT mode using the smallest output range before powering on the output channel, and then immediately program the DAC code and desired output range. The transfer function of the output current is shown in the following equation:

$$I_{OUT} = \frac{DAC_DATA \times (I_{MAX} - I_{MIN})}{2^8} + I_{MIN}$$
(5)

where:

- DAC\_DATA is the decimal equivalent of the binary code that is loaded to the DAC-X-DATA bits specified in Section 6.6.8 or the DAC-X-DATA-8BIT bits specified in Section 6.6.19. DAC\_DATA ranges from 0 to 255.
- I<sub>MAX</sub> is the signed maximum current in the IOUT-RANGE-X setting specified in Section 6.6.5.
- I<sub>MIN</sub> is the signed minimum current in the IOUT-RANGE-X setting specified in Section 6.6.5.



#### 6.4.3 Comparator Mode

All the DAC channels can be configured as programmable comparators in the voltage-output mode. To enter the comparator mode for a channel, write 1 to the CMP-X-EN bit in the respective DAC-X-VOUT-CMP-CONFIG register. The comparator output can be configured as push-pull or open-drain using the CMP-X-OD-EN bit. To enable the comparator output on the output pin, write 1 to the CMP-X-OUT-EN bit. To invert the comparator output, write 1 to the CMP-X-INV-EN bit. The FBx pin has a finite impedance. By default, the FBx pin is in the high-impedance mode. To disable high-impedance on the FBx pin, write 1 to the CMP-X-HIZ-IN-DIS bit. Table 6-1 shows the comparator output at the pin for different bit settings.

#### Note

In the Hi-Z input mode, the comparator input range is limited to:


- For GAIN = 1x, 1.5x, or 2x: V<sub>FB</sub> ≤ (V<sub>REF</sub> × GAIN) / 3
- For GAIN = 3x, or 4x:  $V_{FB} \le (V_{REF} \times GAIN) / 6$

Any higher input voltage is clipped.

Table 0-1: Comparator Output Comparation								
CMP-X-EN	CMP-X-OUT-EN	CMP-X-OD-EN	CMP-X-INV-EN	CMPX-OUT PIN				
0	Х	Х	Х	Comparator not enabled				
1	0	Х	Х	No output				
1	1	0	0	Push-pull output				
1	1	0	1	Push-pull and inverted output				
1	1	1	0	Open-drain output				
1	1	1	1	Open-drain and inverted output				

#### Table 6-1. Comparator Output Configuration

Figure 6-3 shows the interface circuit when all the DAC channels are configured as comparators. The programmable comparator operation is as shown in Figure 6-4. Individual comparator channels can be configured in no-hysteresis, with-hysteresis, and window-comparator modes using the CMP-X-MODE bit in the respective DAC-X-CMP-MODE-CONFIG register, as shown in Table 6-2.










Figure 6-4. Programmable Comparator Operation

### Table 6-2. Comparator Mode Selection

CMP-X-MODE BIT FIELD	COMPARATOR CONFIGURATION
00	Normal comparator mode. No hysteresis or window operation.
01	Hysteresis comparator mode. DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW registers set the hysteresis.
10	Window comparator mode. DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW registers set the window bounds.
11	Invalid setting



#### 6.4.3.1 Programmable Hysteresis Comparator

Comparator mode provides hysteresis when the CMP-X-MODE bit is set to 01b, as shown in Table 6-2. The hysteresis is provided by the DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW registers, as shown in Figure 6-5.

When the DAC-X-MARGIN-HIGH is set to full-code or the DAC-X-MARGIN-LOW is set to zero-code, the comparator works as a latching comparator that is, the output is latched after the threshold is crossed. The latched output can be reset by writing to the corresponding RST-CMP-FLAG-X bit in the COMMON-DAC-TRIG register. Figure 6-6 shows the behavior of a latching comparator with active low output and Figure 6-7 shows the behavior of a latching comparator with active high output.

Note The value of the DAC-X-MARGIN-HIGH register must be greater than the value of the DAC-X-MARGIN-LOW register. The comparator output in the hysteresis mode can only be noninverting that is, the CMP-X-INV-EN bit in the DAC-X-VOUT-CMP-CONFIG register must be set to 0. In latching mode, for the reset to take effect, the input voltage must be within DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW. DAC-X-MARGIN-HIGH Hysteresis FBx/AINx DAC-X-MARGIN-LOW OUT-X CMP-X-INV-EN = 0 Figure 6-5. Programmable Hysteresis Without Latching Output DAC-X-MARGIN-HIGH FBx/AINx DAC-X-MARGIN-LOW (ZERO-CODE) OUT-X CMP-X-INV-EN = 0 RST-CMP-FLAG-X Figure 6-6. Latching Comparator With Active Low Output DAC-X-MARGIN-HIGH (FULL-CODE) FBx/AINx DAC-X-MARGIN-LOW OUT-X CMP-X-INV-EN = 0 RST-CMP-FLAG-X





#### 6.4.3.2 Programmable Window Comparator

Window comparator mode is enabled by setting the CMP-X-MODE bit to 10b, as shown in Table 6-2. The window bounds are set by the DAC-X-MARGIN-HIGH and the DAC-X-MARGIN-LOW registers, as shown in Figure 6-8. The output of the window comparator for a given channel is indicated by the respective WIN-CMP-X bit in the CMP-STATUS register. The comparator output (WIN-CMP-X) can be latched by writing 1 to the WIN-LATCH-EN bit in the COMMON-CONFIG register. After being latched, the comparator output can be reset using the corresponding RST-CMP-FLAG-X bit in the COMMON-DAC-TRIG register. For the reset to take effect, the input must be within the window bounds.




Figure 6-8. Window Comparator Operation

A single comparator is used per channel to check both the *margin-high* and *margin-low* limits of the window. Therefore, the window comparator function has a finite response time as specified in the *Electrical Characteristics: Comparator Mode* section. Also, the static behavior of the WIN-CMP-X bit is not reflected at the output pins. Set the CMP-X-OUT-EN bit to 0. The WIN-CMP-X bit must be read digitally using the communication interface. This bit can also be mapped to the GPIO pin, as shown in Table 6-19.

#### Note

- The value of the DAC-X-MARGIN-HIGH register must be greater than that of the DAC-X-MARGIN-LOW register.
- Set the SLEW-RATE-X bit to 0000b (no-slew) and LOG-SLEW-EN-X bit to 0b in the DAC-X-FUNC-CONFIG register to get the best response time from the window comparator.
- The CMP-X-OUT-EN bit in the DAC-X-VOUT-CMP-CONFIG register can be set to 0b to eliminate undesired toggling of the OUT pin.

#### 6.4.4 Fault-Dump Mode

The DACx3004W provides a feature to save a few registers into the NVM when the FAULT-DUMP bit is triggered or the GPIO mapped to fault-dump (as shown in Table 6-18) is triggered. This feature is useful in system-level fault management to capture the state of the device or system just before a fault is triggered, to allow diagnosis after the fault has occurred. The registers saved when fault-dump is triggered, are:

- CMP-STATUS[7:0]
- DAC-0-DATA[15:8]
- DAC-1-DATA[15:8]
- DAC-2-DATA[15:8]
- DAC-3-DATA[15:8]

#### Note

When the fault-dump cycle is in progress, any change in the data can corrupt the final outcome. Make sure the comparator and the DAC codes are stable during the NVM write cycle.

Table 6-3 shows the storage format of the registers in the NVM.

Copyright © 2025 Texas Instruments Incorporated



#### Table 6-3. Fault-Dump NVM Storage Format

NVM ROWS	B31-B24	B23-B16 B15-B8		B7-B0	
Row1	CMP-STATUS[7:0]	Don't care			
Row2	DAC-0-DATA[15:8]	DAC-1-DATA[15:8] DAC-2-DATA[15:8]		DAC-3-DATA[15:8]	

The data captured in the NVM after the fault dump can be read in a specific sequence:

- 1. Set the EE-READ-ADDR bit to 0b in the COMMON-CONFIG register, to select row1 of the NVM.
- 2. Trigger the read of the selected NVM row by writing 1 to the READ-ONE-TRIG in the COMMON-TRIGGER register; this bit autoresets. This action copies that data from the selected NVM row to SRAM addresses 0x9D (LSB 16 bits from the NVM) and 0x9E (MSB 16 bits from the NVM).
- 3. To read the SRAM data:
  - a. Write 0x009D to the SRAM-CONFIG register.
  - b. Read the data from the SRAM-DATA register to get the LSB 16 bits.
  - c. Write 0x009E to the SRAM-CONFIG register.
  - d. Read the data from the SRAM-DATA register again to get the MSB bits.
- 4. Set the EE-READ-ADDR bit to 1b in the COMMON-CONFIG register, to select row2 of the NVM. Repeat steps 2 and 3.

### 6.4.5 Application-Specific Modes

This section provides the details of application-specific functional modes available in DACx3004W.

#### 6.4.5.1 Voltage Margining and Scaling

Voltage margining or scaling is a primary application for DACx3004W. This section provides specific features available for this application such as Hi-Z output, slew-rate control, **PROTECT** input, and PMBus compatibility.

### 6.4.5.1.1 High-Impedance Output and PROTECT Input

All the DAC output channels remain in high-impedance (Hi-Z) when VDD is off. Figure 6-9 shows a simplified schematic of DACx3004W used in a voltage-margining application. The series resistor  $R_S$  is needed in voltage-output mode, but is optional in current-output mode. Almost all linear regulators and DC/DC converters have a feedback voltage of  $\leq 1.25$  V. The low-leakage currents at the outputs are maintained for  $V_{FB}$  of  $\leq 1.25$  V. Thus, for all practical purposes, the DAC outputs appear as Hi-Z when VDD of the DAC is off in voltage margining and scaling applications. This feature allows for seamless integration of the DACx3004W into a system without any need for additional power-supply sequencing for the DAC.




Figure 6-9. High-Impedance (Hi-Z) Output and PROTECT Input

The DAC channels power down to Hi-Z at boot up. The outputs can power up with a preprogrammed code that corresponds to the nominal output of the DC/DC converter or the linear regulator. This feature allows for smooth power up and power down of the DAC without impacting the feedback loop of the DC/DC converter or the linear regulator.

The GPIO pin of the DACx3004W can be configured as a **PROTECT** function, as shown in **Table 6-18**. **PROTECT** takes the DAC outputs to a predictable state with a slewed or direct transition. This function is useful in systems where a fault condition (such as a brownout), a subsystem failure, or a software crash requires



that the DAC outputs reach a predefined state without the involvement of a processor. The detected event can be fed to the GPIO pin that is configured as the PROTECT input. The PROTECT function can also be triggered using the PROTECT bit in the COMMON-TRIGGER register. Configure the behavior of the PROTECT function in the PROTECT-CONFIG field in the DEVICE-MODE-CONFIG register, as shown in Table 6-4.

#### Note

- After the **PROTECT** function is triggered, the write functionality is disabled on the communication interface until the function is completed.
- The PROTECT-FLAG bit in the CMP-STATUS register is set to 1 when the PROTECT function is triggered. This bit can be polled by reading the CMP-STATUS register. After the PROTECT function is complete, a read command on the CMP-STATUS register resets the PROTECT-FLAG bit.

Tabl	e 6-4. PROTECT Function Configuration
PROTECT-CONFIG FIELD	FUNCTION
00	Switch to Hi-Z power-down (no slew).
01	Switch to DAC code stored in NVM (no slew) and then switch to Hi-Z power-down.
10	Slew to margin-low code and then switch to Hi-Z power-down.
11	Slew to margin-high code and then switch to Hi-Z power-down.

#### 6.4.5.1.2 Programmable Slew-Rate Control

When the DAC data registers are written, the voltage on DAC output ( $V_{OUT}$ ) immediately transitions to the new code following the slew rate and settling time specified in the *Electrical Characteristics*.

The slew rate control feature allows the user to control the rate at which the output voltage ( $V_{OUT}$ ) changes. When this feature is enabled (using the SLEW-RATE-X[3:0] bits), the DAC output changes from the current code to the code in the DAC-X-MARGIN-HIGH or DAC-X-MARGIN-LOW registers (when margin high or low commands are issued to the DAC) using the step size and time-period per step set in CODE-STEP-X and SLEW-RATE-X bits in the DAC-X-FUNC-CONFIG register:

- SLEW-RATE-X defines the time-period per step at which the digital slew updates.
- CODE-STEP-X defines the number of LSBs by which the output value changes at each update, for the corresponding channels.

Table 6-5 and Table 6-6 show different settings available for CODE-STEP-X and SLEW-RATE-X. With the default slew rate control setting of no-slew, the output changes immediately at a rate limited by the output drive circuitry and the attached load.

When the slew rate control feature is used, the output changes happen at the programmed slew rate. This configuration results in a staircase formation at the output as shown in Figure 6-10. Do not write to CODE-STEP-X, SLEW-RATE-X, or DAC-X-DATA during the output slew operation. Equation 6 provides the equation for the calculating the slew time ( $t_{SLEW}$ ).






Figure 6-10. Programmable Slew-Rate Control

$$t_{SLEW} = SLEW_RATE \times CEILING\left(\frac{MARGIN_HIGH - MARGIN_LOW}{CODE_STEP} + 1\right)$$
(6)

where:

- SLEW\_RATE is the SLEW-RATE-X setting as specified in Table 6-6.
- CODE\_STEP is the CODE-STEP-X setting as specified in Table 6-5.
- MARGIN\_HIGH is the decimal value of the DAC-X-MAGIN-HIGH bits specified in the DAC-X-MARGIN-HIGH register.
- MARGIN\_LOW is the decimal value of the DAC-X-MAGIN-LOW bits specified in the DAC-X-MARGIN-LOW register.

		Table 6-5. Code Step		
REGISTER	CODE-STEP-X[2]	CODE-STEP-X[1]	CODE-STEP-X[0]	CODE STEP SIZE
	0	0	0	1 LSB (default)
	0	0	1	2 LSB
	0	1	0	3 LSB
DAC-X-FUNC-CONFIG	0	1	1	4 LSB
DAC-X-FUNC-CUNFIG	1	0	0	6 LSB
	1	0	1	8 LSB
	1	1	0	16 LSB
	1	1	1	32 LSB

## Table 6-6. Slew Rate

REGISTER	SLEW-RATE-X[3]	SLEW-RATE-X[2]	SLEW-RATE-X[1]	SLEW-RATE-X[0]	TIME PERIOD (PER STEP)
	0	0	0	0	No slew (default)
	0	0	0	1	4 µs
	0	0	1	0	8 µs
	0	0	1	1	12 µs
	0	1	0	0	18 µs
	0	1	0	1	27.04 μs
	0	1	1	0	40.48 µs
DAC-X-FUNC-CONFIG	0	1	1	1	60.72 μs
DAC-X-FUNC-CONFIG	1	0	0	0	91.12 μs
	1	0	0	1	136.72 µs
	1	0	1	0	239.2 µs
	1	0	1	1	418.64 µs
	1	1	0	0	732.56 µs
	1	1	0	1	1282 µs
	1	1	1	0	2563.96 µs
	1	1	1	1	5127.92 µs



#### 6.4.5.1.3 PMBus Compatibility Mode

The PMBus protocol is an I<sup>2</sup>C-based communication standard for power-supply management. PMBus contains standard command codes tailored to power supply applications. The DACx3004W implement some PMBus commands such as *Turn Off, Turn On, Margin Low, Margin High, Communication Failure Alert Bit (CML)*, as well as *PMBUS revision*. Figure 6-11 shows typical PMBus connections. The EN-PMBUS bit in the INTERFACE-CONFIG register must be set to 1 to enable the PMBus protocol.




Figure 6-11. PMBus Connections



Similar to I<sup>2</sup>C, PMBus is a variable length packet of 8-bit data bytes, each with a receiver acknowledge, wrapped between a start and stop bit. The first byte is always a 7-bit *target address* followed by a *write* bit, sometimes called the *even address* that identifies the intended receiver of the packet. The second byte is an 8-bit *command* byte, identifying the PMBus command being transmitted using the respective command code. After the command byte, the transmitter either sends data associated with the command to write to the receiver command register (from least significant byte to most significant byte, as shown in Table 6-7), or sends a new start bit indicating the desire to read the data associated with the command register from the receiver. Then the receiver transmits the data following the same least significant byte first format (see Table 6-8).

MSB		LSB	ACK	MSB		LSB	ACK	MSB		LSB	ACK	MSB		LSB	ACK
	ress (A) tion 6.5.2	,			mmand b tion 6.5.2	,		Data	ı byte - L	SDB			byte - M Optional		
0	OB [31:24	4]		0	DB [23:16	6]			DB [15:8	]			DB [7:0]		

### Table 6-7. PMBus Update Sequence

### Table 6-8. PMBus Read Sequence

s	MSB		R/W (0)	АСК	MSB		LSB	АСК	Sr	MSB		R/W (1)	ACK	MSB		LSB	ACK	MSB		LSB	ACK
	ADDR Sectio				COMN Sectio		BYTE 5.2.2.2		Sr	1	DRESS BYTE tion 6.5.2.2.1			LSDB		3		MSDE	(Op	tional)	
	From Co	ontrol	ler	Target	From	Con	troller	Target		From C	Controller Target		Target	Fro	m Ta	rget	Controller	Fro	n Ta	rget	Controller

The DACx3004W I<sup>2</sup>C interface implements some of the PMBus commands. Table 6-9 shows the supported PMBus commands that are implemented in DACx3004W. The DAC uses DAC-X-MARGIN-LOW, DAC-X-MARGIN-HIGH bits, SLEW-RATE-X, and CODE-STEP-X bits for PMBUS-OPERATION-CMD-X. To access multiple channels, write the PMBus page address as specified in the *Register Names* table in the *Register Map* section to the PMBUS-PAGE register first, followed by a write to the channel-specific register.

#### 

The DACx3004W also implement PMBus features such as group command protocol and communication timeout failure. The CML bit in the PMBUS-CML register indicates a communication fault in the PMBus. This bit is reset by writing 1.

To get the PMBus version, read the PMBUS-VERSION register.

Copyright © 2025 Texas Instruments Incorporated



### 6.4.5.2 Function Generation

The DACx3004W implement a continuous function or waveform generation feature. These devices can generate a triangular wave, sawtooth wave, and sine wave independently for every channel.

#### 6.4.5.2.1 Triangular Waveform Generation

Figure 6-12 shows that the triangular waveform uses the DAC-X-MARGIN-LOW (FUNCTION-MIN) and DAC-X-MARGIN-HIGH (FUNCTION-MAX) registers for minimum and maximum levels, respectively. The frequency of the waveform depends on the min and max levels, CODE-STEP and SLEW-RATE settings as shown in Equation 7. An external RC load with a time-constant larger than the slew-rate settings can be dominant over the internal frequency calculation. The CODE-STEP-X and SLEW-RATE-X settings are available in the DAC-X-FUNC-CONFIG register. Writing 0b000 to the FUNC-CONFIG-X bit field in the DAC-X-FUNC-CONFIG register selects triangular waveform.

$$f_{\text{TRIANGLE}} = \frac{1}{2 \times \text{TIME}_{\text{STEP}} \times \text{CEILING}\left(\frac{\text{FUNCTION}_{\text{MAX}} - \text{FUNCTION}_{\text{MIN}}}{\text{CODE}_{\text{STEP}}}\right)}$$
(7)

where:

- TIME\_STEP is the SLEW-RATE-X setting as specified in Table 6-6.
- CODE\_STEP is the CODE-STEP-X setting as specified in Table 6-5.
- FUNCTION\_MAX is the decimal value of DAC-X-MAGIN-HIGH bits specified in the DAC-X-MARGIN-HIGH register.
- FUNCTION\_MIN is the decimal value of the DAC-X-MAGIN-LOW bits specified in the DAC-X-MARGIN-LOW register.




Figure 6-12. Triangle Waveform



### 6.4.5.2.2 Sawtooth Waveform Generation

Figure 6-13 shows the sawtooth and the inverse sawtooth waveforms use the DAC-X-MARGIN-LOW (FUNCTION-MIN) and DAC-X-MARGIN-HIGH (FUNCTION-MAX) registers for minimum and maximum levels, respectively. The frequency of the waveform depends on the min and max levels, CODE-STEP and SLEW-RATE settings as shown in Equation 8. An external RC load with a time constant larger than the slew-rate settings can be dominant over the internal frequency calculation. The CODE-STEP-X and SLEW-RATE-X settings are available in the DAC-X-FUNC-CONFIG register. Write 0b001 to the FUNC-CONFIG-X bit field in the DAC-X-FUNC-CONFIG register to select sawtooth waveform, and write 0b010 to select inverse sawtooth waveform.

$$f_{SAWTOOTH} = \frac{1}{TIME\_STEP \times CEILING(\frac{FUNCTION\_MAX - FUNCTION\_MIN}{CODE\_STEP} + 1)}$$
(8)

where:

- TIME\_STEP is the SLEW-RATE-X setting as specified in Table 6-6.
- CODE\_STEP is the CODE-STEP-X setting as specified in Table 6-5.
- FUNCTION\_MAX is the decimal value of the DAC-X-MAGIN-HIGH bits specified in the DAC-X-MARGIN-HIGH register.
- FUNCTION\_MIN is the decimal value of the DAC-X-MAGIN-LOW bits specified in the DAC-X-MARGIN-LOW.




Figure 6-13. Sawtooth Waveform



(9)

#### 6.4.5.2.3 Sine Waveform Generation

The sine wave function uses 24 preprogrammed points per cycle. The frequency of the sine wave depends on the SLEW-RATE settings as shown in Equation 9:


# $f_{SINE_WAVE} = \frac{1}{24 \times SLEW_RATE}$

where SLEW RATE is the SLEW-RATE-X setting as specified in Table 6-6.

An external RC load with a time constant larger than the slew-rate settings can be dominant over the internal frequency calculation. The SLEW-RATE-X setting is available in the DAC-X-FUNC-CONFIG register. Writing 0b100 to the FUNC-CONFIG-X bit field in the DAC-X-FUNC-CONFIG register selects sine wave. The codes for the sine wave are fixed. Use the gain settings at the output amplifier for changing the full-scale output using the internal reference option. The gain settings are accessible through the VOUT-GAIN-X bits in the DAC-X-VOUT-CMP-CONFIG register. Table 6-10 shows the list of hard-coded discrete points for the sine wave with 12-bit resolution and Figure 6-14 shows the pictorial representation of the sine wave. There are four phase settings available for the sine wave that are selected using the PHASE-SEL-X bit in the DAC-X-FUNC-CONFIG register.

SEQUENCE	12-BIT VALUE	SEQUENCE	12-BIT VALUE
0 (0° phase start)	0x800	12	0x800
1	0x9A8	13	0x658
2	0xB33	14	0x4CD
3	0xC87	15	0x379
4	0xD8B	16 (240° phase start)	0x275
5	0xE2F	17	0x1D1
6 (90° phase start)	0xE66	18	0x19A
7	0xE2F	19	0x1D1
8 (120° phase start)	0xD8B	20	0x275
9	0xC87	21	0x379
10	0xB33	22	0x4CD
11	0x9A8	23	0x658

### Table 6-10. Sine Wave Data Points



### Figure 6-14. Sine Wave Generation



## 6.4.6 Device Reset and Fault Management

This section provides the details of power-on-reset (POR), software reset, and other diagnostics and fault-management features of the DACx3004W.

#### 6.4.6.1 Power-On Reset (POR)

The DACx3004W family of devices includes a power-on reset (POR) function that controls the output voltage at power up. After the  $V_{DD}$  supply has been established, a POR event is issued. The POR causes all registers to initialize to default values, and communication with the device is valid only after a POR (boot-up) delay. The default value for all the registers in the DACx3004W is loaded from NVM as soon as the POR event is issued.

When the device powers up, a POR circuit sets the device to the default mode. The POR circuit requires specific  $V_{DD}$  levels, as indicated in Figure 6-15, to make sure that the internal capacitors discharge and reset the device at power up. To make sure that a POR occurs,  $V_{DD}$  must be less than 0.7 V for at least 1 ms. When  $V_{DD}$  drops to less than 1.65 V, but remains greater than 0.7 V (shown as the undefined region), the device may or may not reset under all specified temperature and power-supply conditions. In this case, initiate a POR. When  $V_{DD}$  remains greater than 1.65 V, a POR does not occur.




Figure 6-15. Threshold Levels for V<sub>DD</sub> POR Circuit

#### 6.4.6.2 External Reset

An external reset to the device can be triggered through the GPIO pin or through the register map. To initiate a device software reset event, write the reserved code 1010b to the RESET field in the COMMON-TRIGGER register. A software reset initiates a POR event. The GPIO pin can be configured as a RESET pin as shown in Table 6-18. This configuration must be programmed into the NVM so that the setting is not cleared after the device reset. The RESET input must be a low pulse. The device starts the boot-up sequence after the falling edge of the RESET input. The rising edge of the RESET input does not have any effect.

### 6.4.6.3 Register-Map Lock

The DACx3004W implement a register-map lock feature that prevents an accidental or unintended write to the DAC registers. The device locks all the registers when the DEV-LOCK bit in the COMMON-CONFIG register is set to 1. However, the software reset function through the COMMON-TRIGGER register is not blocked when using I<sup>2</sup>C interface. To bypass the DEV-LOCK setting, write 0101b to the DEV-UNLOCK bits in the COMMON-TRIGGER register.



### 6.4.6.4 NVM Cyclic Redundancy Check (CRC)

The DACx3004W implement a cyclic redundancy check (CRC) feature for the NVM to make sure that the data stored in the NVM is uncorrupted. There are two types of CRC alarm bits implemented in DACx3004W:

- NVM-CRC-FAIL-USER
- NVM-CRC-FAIL-INT

The NVM-CRC-FAIL-USER bit indicates the status of user-programmable NVM bits, and the NVM-CRC-FAIL-INT bit indicates the status of internal NVM bits The CRC feature is implemented by storing a 16-Bit CRC (CRC-16-CCITT) along with the NVM data each time NVM program operation (write or reload) is performed and during the device start up. The device reads the NVM data and validates the data with the stored CRC. The CRC alarm bits (NVM-CRC-FAIL-USER and NVM-CRC-FAIL-INT in the GENERAL-STATUS register) report any errors after the data are read from the device NVM. The alarm bits are set only at boot-up.

### 6.4.6.4.1 NVM-CRC-FAIL-USER Bit

A logic 1 on NVM-CRC-FAIL-USER bit indicates that the user-programmable NVM data are corrupt. During this condition, all registers in the DAC are initialized with factory reset values, and any DAC registers can be written to or read from. To reset the alarm bits to 0, issue a software reset (see *Section 6.4.6.2*) command, or cycle power to the DAC. A software reset or power-cycle also reloads the user-programmable NVM bits. In case the failure persists, reprogram the NVM.

## 6.4.6.4.2 NVM-CRC-FAIL-INT Bit

A logic 1 on NVM-CRC-FAIL-INT bit indicates that the internal NVM data are corrupt. During this condition, all registers in the DAC are initialized with factory reset values, and any DAC registers can be written to or read from. In case of a temporary failure, to reset the alarm bits to 0, issue a software reset (see Section 6.4.6.2) command or cycle power to the DAC. A permanent failure in the NVM makes the device unusable.



## 6.4.7 Power-Down Mode

The DACx3004W output amplifier and internal reference can be independently powered down through the EN-INT-REF, VOUT-PDN-X, and IOUT-PDN-X bits in the COMMON-CONFIG register, as shown in Figure 6-2. At power up, the DAC output and the internal reference are disabled by default. In power-down mode, the DAC outputs (OUTx pins) are in a high-impedance state. To change this state to 10 k $\Omega$ -AGND or 100 k $\Omega$ -AGND in the voltage-output mode (at power up), use the VOUT-PDN-X bits. The power-down state for current-output mode is always high-impedance.

The DAC power-up state can be programmed to any state (power-down or normal mode) using the NVM. Table 6-11 shows the DAC power-down bits. The individual channel power-down bits or the global device power-down function can be mapped to the GPIO pin using the GPIO-CONFIG register.

REGISTER	VOUT-PDN-X[1]	VOUT-PDN-X[0]	IOUT-PDN-X	DESCRIPTION
	0	0	1	Power up VOUT-X.
	0	1	1	Power down VOUT-X with 10 k $\Omega$ to AGND. Power down IOUT-X to Hi-Z.
COMMON-CONFIG	1	0	1	Power down VOUT-X with 100 k $\Omega$ to AGND. Power down IOUT-X to Hi-Z.
	1	1	1	Power down VOUT-X to Hi-Z. Power down IOUT-X to Hi-Z (default).
	1	1	0	Power down VOUT-X to Hi-Z. Power up IOUT-X.

### Table 6-11. DAC Power-Down Bits



## 6.5 Programming

The DACx3004W are programmed through either a 3-wire SPI or 2-wire I<sup>2</sup>C interface. A 4-wire SPI mode is enabled by mapping the GPIO pin as SDO. The SPI readback operates at a lower SCLK than the standard SPI write operation. The type of interface is determined based on the first protocol to communicate after device power up. After the interface type is determined, the device ignores any change in the type while the device is on. The interface type can be changed after a power cycle.

## 6.5.1 SPI Programming Mode

To initiate an SPI access cycle for DACx3004W, assert the SYNC pin low. The serial clock, SCLK, is a continuous or gated clock. SDI data are clocked on SCLK falling edges. The SPI frame for DACx3004W is 24 bits long. Therefore, ensure that the SYNC pin is low for at least 24 SCLK falling edges. The access cycle ends when the SYNC pin is deasserted high. If the access cycle contains less than the minimum clock edges, the communication is ignored. By default, the SDO pin is not enabled (three-wire SPI). In three-wire SPI mode, if the access cycle contains more than the minimum clock edges, only the first 24 bits are used by the device. When SYNC is high, the SCLK and SDI signals are blocked, and SDO becomes Hi-Z to allow data readback from other devices connected on the bus.

Table 6-12 and Figure 6-16 describe the format for the 24-bit SPI access cycle. The first byte input to SDI is the instruction cycle. The instruction cycle identifies the request as a read or write command and the 7-bit address that is to be accessed. The last 16 bits in the cycle form the data cycle.

BIT	FIELD		DESCRI	PTION	
23	R/W	Identifies the communication as a operation. $R/W$ = 1 sets a read op		and to the address register	∵ R/₩ = 0 sets a write
22-16	A[6:0]	Register address: specifies the re-	gister to be accessed	d during the read or write o	operation
15-0	DI[15:0]	Data cycle bits: If a write comman address A[6:0]. If a read comman			en to the register with
SYNC					
SCLK	1 8	9 24		8 9	24
•	Write comm	and	•	Any command	
SDI	D23 D16	D15 D0	D23	D16 D15	D0
HiZ		HIZ	<u>الم</u>	- Write command echo	
SDO			D23	D16 D15	D0

### Table 6-12. SPI Read/Write Access Cycle

Figure 6-16. SPI Write Cycle

Read operations require that the SDO pin is first enabled by setting the SDO-EN bit in the INTERFACE-CONFIG register. This configuration is called four-wire SPI. A read operation is initiated by issuing a read command access cycle. After the read command, a second access cycle must be issued to get the requested data. The output data format is shown in Table 6-13 and Figure 6-17. Data are clocked out on the SDO pin either on the falling edge or rising edge of SCLK according to the FSDO bit, as shown in Figure 5-3.


BIT	FIELD	DESCRIPTION
23	R/W	Echo R/W from previous access cycle
22-16	A[6:0]	Echo register address from previous access cycle
15-0	DI[15:0]	Readback data requested on previous access cycle

#### Table 6-13. SDO Output Access Cycle

		<b>, <mark>DAC6300</mark></b> RCH 2023 – F	AW REVISED JULY 2025						TEXAS INSTRUMENTS www.ti.com
- SYNC									
SCLK			8	9	24		8	9	24
		•	Read comma	and		•	Any comm	and ———	
SDI		D23	D16	D15	D0	D23	D16	D15	D0
	HiZ				Hi2	<u></u>		←	Read Data ——— HiZ
SDO -						D23	D16	D15	D0

Figure 6-17. SPI Read Cycle

The daisy-chain operation is also enabled with the SDO pin. In daisy-chain mode, multiple devices are connected in a *chain* with the SDO pin of one device is connected to SDI pin of the following device, as shown in Figure 6-18. The SPI host drives the SDI pin of the first device in the chain. The SDO pin of the last device in the chain is connected to the POCI pin of the SPI host. In four-wire SPI mode, if the access cycle contains multiples of 24 clock edges, only the last 24 bits are used by the device first device in the chain. If the access cycle contains clock edges that are not in multiples of 24, the SPI packet is ignored by the device. Figure 6-19 describes the packet format for the daisy-chain write cycle.



.



## 6.5.2 I<sup>2</sup>C Programming Mode

The DACx3004W devices have a 2-wire serial interface (SCL and SDA), and one address pin (A0), as shown in the pin diagram in the *Pin Configuration and Functions* section. The  $I^2C$  bus consists of a data line (SDA) and a clock line (SCL) with pullup structures. When the bus is idle, both SDA and SCL lines are pulled high. All the  $I^2C$ -compatible devices connect to the  $I^2C$  bus through the open drain I/O pins, SDA and SCL.

The I<sup>2</sup>C specification states that the device that controls communication is called a *controller*, and the devices that are controlled by the controller are called *targets*. The controller generates the SCL signal. The controller also generates special timing conditions (start condition, repeated start condition, and stop condition) on the bus to indicate the start or stop of a data transfer. Device addressing is completed by the controller. The controller on an I<sup>2</sup>C bus is typically a microcontroller or digital signal processor (DSP). The DACx3004W family operates as a target on the I<sup>2</sup>C bus. A target acknowledges controller commands, and upon controller control, receives or transmits data.


Typically, the DACx3004W family operates as a target receiver. A controller writes to the DACx3004W, a target receiver. However, if a controller requires the DACx3004W internal register data, the DACx3004W operate as a target transmitter. In this case, the controller reads from the DACx3004W. According to I<sup>2</sup>C terminology, read and write refer to the controller.

The DACx3004W family supports the following data transfer modes:

- Standard mode (100Kbps)
- Fast mode (400Kbps)
- Fast mode plus (1.0Mbps)

The data transfer protocol for standard and fast modes is exactly the same; therefore, both modes are referred to as *F/S-mode* in this document. The fast mode plus protocol is supported in terms of data transfer speed, but not output current. The low-level output current is 3 mA; similar to the case of standard and fast modes. The DACx3004W family supports 7-bit addressing. The 10-bit addressing mode is not supported. The device supports the general call reset function. Sending the following sequence initiates a software reset within the device: start or repeated start, 0x00, 0x06, stop. The reset is asserted within the device on the rising edge of the ACK bit, following the second byte.

Other than specific timing signals, the I<sup>2</sup>C interface works with serial bytes. At the end of each byte, a ninth clock cycle generates and detects an acknowledge signal. An acknowledge is when the SDA line is pulled low during the high period of the ninth clock cycle. A not-acknowledge is when the SDA line is left high during the high period of the ninth clock cycle, as shown in Figure 6-20.







### 6.5.2.1 F/S Mode Protocol

The following steps explain a complete transaction in F/S mode.

- 1. The controller initiates data transfer by generating a start condition. The start condition is when a high-to-low transition occurs on the SDA line while SCL is high, as shown in Figure 6-21. All I<sup>2</sup>C-compatible devices recognize a start condition.
- 2. The controller then generates the SCL pulses, and transmits the 7-bit address and the read/write direction bit (R/W) on the SDA line. During all transmissions, the controller makes sure that data are valid. A valid data condition requires the SDA line to be stable during the entire high period of the clock pulse, as shown in Figure 6-22. All devices recognize the address sent by the controller and compare the address to the respective internal fixed address. Only the target device with a matching address generates an acknowledge by pulling the SDA line low during the entire high period of the 9th SCL cycle, as shown in Figure 6-20. When the controller detects this acknowledge, the communication link with a target has been established.
- 3. The controller generates further SCL cycles to transmit (R/W bit 0) or receive (R/W bit 1) data to the target. In either case, the receiver must acknowledge the data sent by the transmitter. The acknowledge signal can be generated by the controller or by the target, depending on which is the receiver. The 9-bit valid data sequences consists of eight data bits and one acknowledge-bit, and can continue as long as necessary.
- 4. To signal the end of the data transfer, the controller generates a stop condition by pulling the SDA line from low-to-high while the SCL line is high, as shown in Figure 6-21. This action releases the bus and stops the communication link with the addressed target. All I<sup>2</sup>C-compatible devices recognize the stop condition. Upon receipt of a stop condition, the bus is released, and all target devices then wait for a start condition followed by a matching address.




Figure 6-21. Start and Stop Conditions




Figure 6-22. Bit Transfer on the I<sup>2</sup>C Bus



## 6.5.2.2 I<sup>2</sup>C Update Sequence

For a single update, the DACx3004W require a start condition, a valid I<sup>2</sup>C address byte, a command byte, and two data bytes, as listed in Table 6-14.

							· · ·		· ·						
MSB		LSB	ACK	MSB		LSB	ACK	MSB		LSB	ACK	MSB		LSB	ACK
	Iress (A) tion 6.5.2				mmand b tion 6.5.2	,		Data byte - MSDB Data by		a byte - L	SDB				
[	OB [31:24	1]		[	DB [23:16	6]			DB [15:8	]			DB [7:0]		

Table 0-14. Opuale Sequence	. Update Sequence	e 6-14. l	Table
-----------------------------	-------------------	-----------	-------

After each byte is received, the DACx3004W family acknowledges the byte by pulling the SDA line low during the high period of a single clock pulse, as shown in Figure 6-23. These four bytes and acknowledge cycles make up the 36 clock cycles required for a single update to occur. A valid I<sup>2</sup>C address byte selects the DACx3004W.




Figure 6-23. I<sup>2</sup>C Bus Protocol

The command byte sets the operating mode of the selected DACx3004W device. For a data update to occur when the operating mode is selected by this byte, the DACx3004W device must receive two data bytes: the most significant data byte (MSDB) and least significant data byte (LSDB). The DACx3004W device performs an update on the falling edge of the acknowledge signal that follows the LSDB.

When using fast mode (clock = 400 kHz), the maximum DAC update rate is limited to 10 kSPS. Using fast mode plus (clock = 1 MHz), the maximum DAC update rate is limited to 25 kSPS. When a stop condition is received, the DACx3004W device releases the  $I^{2}C$  bus and awaits a new start condition.



## 6.5.2.2.1 Address Byte

The address byte, as shown in Table 6-15, is the first byte received from the controller device following the start condition. The first four bits (MSBs) of the address are factory preset to 1001. The next three bits of the address are controlled by the A0 pin. The A0 pin input can be connected to VDD, AGND, SCL, or SDA. The A0 pin is sampled during the first byte of each data frame to determine the address. The device latches the value of the address pin, and consequently responds to that particular address according to Table 6-16.

COMMENT				LSB										
—	AD6	AD5	AD4	AD3	AD2	AD1	AD0	R/W						
General address	1	0	0	1	See Table 6-16 (target address column)			0 or 1						
Broadcast address	1	0	0	0	1	1	1	0						

## Table 6-15. Address Byte

Table 6-16. Address Format											
TARGET ADDRESS	A0 PIN										
000	AGND										
001	VDD										
010	SDA										
011	SCL										

## Table 6-16. Address Format

The DACx3004W supports broadcast addressing, which is used for synchronously updating or powering down multiple DACx3004W devices. When the broadcast address is used, the DACx3004W responds regardless of the address pin state. Broadcast is supported only in write mode.

#### 6.5.2.2.2 Command Byte

The Register Names table in the Register Map section lists the command byte in the ADDRESS column.



#### 6.5.2.3 I<sup>2</sup>C Read Sequence

To read any register the following command sequence must be used:

- 1. Send a start or repeated start command with a target address and the R/W bit set to 0 for writing. The device acknowledges this event.
- 2. Send a command byte for the register to be read. The device acknowledges this event again.
- 3. Send a repeated start with the target address and the R/W bit set to 1 for reading. The device acknowledges this event.
- 4. The device writes the MSDB byte of the addressed register. The controller must acknowledge this byte.
- 5. Finally, the device writes out the LSDB of the register.

The broadcast address cannot be used for reading.

s	MSB		R/W (0)	АСК	MSB		LSB	ACK	Sr	MSB		R/W (1)	ACK	MSB		LSB	ACK	MSB		LSB	ACK
	ADDR Sectio						BYTE 5.2.2.2		Sr	Sr ADDRESS BYTE Section 6.5.2.2.1			MSDB			L	SDE	3			
	From Co	ontro	ller	Target	From	Con	troller	Target	From Controller		From Controller Target From Target Controller From Target		From Target Control		rget	Controller					

#### Table 6-17. Read Sequence

## 6.5.3 General-Purpose Input/Output (GPIO) Modes

Together with I<sup>2</sup>C and SPI, the DACx3004W also support a GPIO that can be configured in the NVM for multiple functions. This pin allows for updating the DAC output channels and reading status bits without using the programming interface, thus enabling processor-less operation. In the GPIO-CONFIG register, write 1 to the GPI-EN bit to set the GPIO pin as an input, or write 1 to the GPO-EN bit to set the pin as output. There are global and channel-specific functions mapped to the GPIO pin. For channel-specific functions, select the channels using the GPI-CH-SEL field in the GPIO-CONFIG register. Table 6-18 lists the functional options available for the GPIO as input and Table 6-19 lists the options for the GPIO as output. Some of the GP input operations are edge-triggered after the device boots up. After the power supply ramps up, the device registers the GPI level and executes the associated command. This feature allows the user to configure the initial output state at power-on. By default, the GPIO pin is not mapped to any operation. When the GPIO pin is mapped to a specific input function, the corresponding software bit functionality is disabled to avoid a race condition. When used as a RESET input, the GPIO pin must transmit an active-low pulse for triggering a device reset. All other constraints of the functions are applied to the GPIO-based trigger.

#### Note

Pull the GPIO pin to high or low when not used. When the GPIO pin is used as RESET, the configuration must be programmed into the NVM. Otherwise, the setting is cleared after the device resets.

#### DAC53004W, DAC63004W SLASF72A – MARCH 2023 – REVISED JULY 2025



	Table 6-18. General-Purpose Input Function Map													
REGISTER	BIT FIELD	VALUE	CHANNELS	GPIO EDGE / LEVEL	FUNCTION									
		0000	All	Falling-edge	Trigger DEEP-SLEEP mode.									
		0000	All	Rising-edge	Bring the device out of deep-sleep.									
		0010	All	Falling-edge	Trigger FAULT-DUMP									
		0010	All	Rising-edge	No effect									
		0011		Falling-edge	IOUT power-down									
		0011	As per GPI-CH-SEL	Rising-edge	IOUT power-up									
		0100	As per GPI-CH-SEL	Falling-edge	VOUT power-down. Pulldown resistor as per the VOUT-PDN-X setting									
				Rising-edge	VOUT power-up									
		0101	All	Falling-edge	Trigger PROTECT function									
		0101		Rising-edge	No effect									
		0111	All	Falling-edge	Trigger CLR function									
		UIII		Rising-edge	No effect									
			As per GPI-CH-SEL. Both	Falling-edge	Trigger LDAC function									
GPIO-CONFIG	GPI-CONFIG	1000	the SYNC-CONFIG-X and the GPI-CH-SEL must be configured for every channel.	Rising-edge	No effect									
		1001	As per GPI-CH-SEL	Falling-edge	Stop function generation									
		1001	AS per GPI-CH-SEL	Rising-edge	Start function generation									
		1010		Falling-edge	Trigger margin-low									
		1010	As per GPI-CH-SEL	Rising-edge	Trigger margin-high									
		1011	All	Low pulse	Trigger device RESET. The RESET configuration must be programmed into the NVM.									
				Rising-edge	No effect									
		1100	Δ11	Falling-edge	Allows NVM programming									
		1100	All	Rising-edge	Blocks NVM programming									
				Falling-edge	Allows register map update									
		1101	All	rising-edge	Blocks register map write except a write to the DEV-UNLOCK field through I <sup>2</sup> C or SPI and to the RESET field through I <sup>2</sup> C									
		Others	NA	NA	Not applicable									

## Table 6-18. General-Purpose Input Function Map

 Table 6-19. General-Purpose Output (STATUS) Function Map

•														
REGISTER	BIT FIELD	VALUE	FUNCTION											
		0001	NVM-BUSY											
		0100	DAC-0-BUSY											
		0101	DAC-1-BUSY											
	GPO-CONFIG	0110	DAC-2-BUSY											
GPIO-CONFIG		0111	DAC-3-BUSY											
GPIO-CONFIG		GPO-CONFIG	1000	WIN-CMP-0										
			1001	WIN-CMP-1										
		1010	WIN-CMP-2											
		1011	WIN-CMP-3											
		Others	Not applicable											



## 6.6 Register Map

			MOST	SIGNIFICANT	DATA BYTE				LEAST SIGNIFICANT DATA BYTE (LSDB)								
REGISTER <sup>(1)</sup> <sup>(2)</sup>	BIT15	BIT14	BIT13	BIT12	BIT11	BIT10	BIT9	BIT8	BIT7	BIT6	BIT5	BIT4	BIT3	BIT2	BIT1	BIT0	
NOP								N	OP								
DAC-X-MARGIN- HIGH						DAC-X-MA	RGIN-HIGH					x					
DAC-X-MARGIN- LOW						DAC-X-MA	RGIN-LOW					х					
DAC-X-VOUT- CMP-CONFIG		х			Vout-gain->	(			х			CMP-X-OD- EN	CMP-X- OUT-EN	CMP-X-HIZ- IN-DIS	CMP-X-INV- EN	CMP-X-EN	
DAC-X-IOUT-MISC- CONFIG		х			IOUT-X	-RANGE	1					х					
DAC-X-CMP- MODE-CONFIG			x		CMP-X	-MODE		x									
DAC-X-FUNC- CONFIG	CLR-SEL-X	SYNC- CONFIG-X	BRD- CONFIG-X						FUNC-G	EN-CONFIG-	BLOCK-X						
DAC-X-DATA						DAC->	K-DATA								х		
COMMON-CONFIG	WIN- LATCH-EN	DEV-LOCK	EE-READ- ADDR	EN-INT-REF	VOUT	-PDN-3	IOUT-PDN-3	VOUT	-PDN-2	DN-2 IOUT-PDN-2 VOUT-PDI			IOUT-PDN-1	IOUT-PDN-1 VOUT-		IOUT-PDN-0	
COMMON- TRIGGER		DEV-U	NLOCK			RE	SET		LDAC	CLR	х	FAULT- DUMP	PROTECT	READ-ONE- TRIG	NVM-PROG	NVM- RELOAD	
COMMON-DAC- TRIG	RST-CMP- FLAG-0	TRIG-MAR- LO-0	TRIG-MAR- HI-0	START- FUNC-0	RST-CMP- FLAG-1	TRIG-MAR- LO-1	TRIG-MAR- HI-1	START- FUNC-1	RST-CMP- FLAG-2	TRIG-MAR- LO-2	TRIG-MAR- HI-2	START- FUNC-2	RST-CMP- FLAG-3	TRIG-MAR- LO-3	TRIG-MAR- HI-3	START- FUNC-3	
GENERAL-STATUS	NVM-CRC- FAIL-INT	NVM-CRC- FAIL-USER	X	DAC- BUSY-3	DAC- BUSY-2	DAC- BUSY-1	DAC- BUSY-0	NVM-BUSY				DEVI	/ICE-ID				
CMP-STATUS				Х				PROTECT- FLAG	WIN-CMP-3	WIN-CMP-2	WIN-CMP-1	WIN-CMP-0	CMP- FLAG-3	CMP- FLAG-2	CMP- FLAG-1	CMP- FLAG-0	
GPIO-CONFIG	GF-EN	DEEP- SLEEP-EN	GPO-EN		GPO-0	CONFIG			GPI-C	H-SEL			GPI-CONFIG GP				
DEVICE-MODE- CONFIG	RESE	RVED	DIS-MODE- IN		RESERVED		PROTEC	T-CONFIG		RESERVED				х			
INTERFACE- CONFIG		Х		TIMEOUT- EN		х		EN-PMBUS			х			FSDO-EN	Х	SDO-EN	
SRAM-CONFIG				>	<							SRAM	1-ADDR				
SRAM-DATA								SRAM	I-DATA								
DAC-X-DATA-8BIT	DAC-X-DATA-8BIT												Х				
BRDCAST-DATA						BRDCA	ST-DATA	T-DATA X									
PMBUS-PAGE				PMBUS	-PAGE							١	NA				
PMBUS-OP-CMD				PMBUS-OPER	ATION-CMD->	x	NA										
PMBUS-CML			2	x			CML	Х				١	NA				
PMBUS-VERSION				PMBUS-	VERSON							١	NA				

Table 6-20. Register Map

(1) The highlighted gray cells indicate the register bits or fields that are stored in the NVM.
 (2) X = Don't care.



## Table 6-21. Register Names

I <sup>2</sup> C/SPI ADDRESS	PMBUS PAGE ADDR	PMBUS REGISTER ADDR	REGISTER NAME	SECTION
00h	FFh	D0h	NOP	Section 6.6.1
01h	00h	25h	DAC-0-MARGIN-HIGH	Section 6.6.2
02h	00h	26h	DAC-0-MARGIN-LOW	Section 6.6.3
03h	FFh	D1h	DAC-0-VOUT-CMP-CONFIG	Section 6.6.4
04h	FFh	D2h	DAC-0-IOUT-MISC-CONFIG	Section 6.6.5
05h	FFh	D3h	DAC-0-CMP-MODE-CONFIG	Section 6.6.6
06h	FFh	D4h	DAC-0-FUNC-CONFIG	Section 6.6.7
07h	01h	25h	DAC-1-MARGIN-HIGH	Section 6.6.2
08h	01h	26h	DAC-1-MARGIN-LOW	Section 6.6.3
09h	FFh	D5h	DAC-1-VOUT-CMP-CONFIG	Section 6.6.4
0Ah	FFh	D6h	DAC-1-IOUT-MISC-CONFIG	Section 6.6.5
0Bh	FFh	D7h	DAC-1-CMP-MODE-CONFIG	Section 6.6.6
0Ch	FFh	D8h	DAC-1-FUNC-CONFIG	Section 6.6.7
0Dh	02h	25h	DAC-2-MARGIN-HIGH	Section 6.6.2
0Eh	02h	26h	DAC-2-MARGIN-LOW	Section 6.6.3
0Fh	FFh	D9h	DAC-2-VOUT-CMP-CONFIG	Section 6.6.4
10h	FFh	DAh	DAC-2-IOUT-MISC-CONFIG	Section 6.6.5
11h	FFh	DBh	DAC-2-CMP-MODE-CONFIG	Section 6.6.6
12h	FFh	DCh	DAC-2-FUNC-CONFIG	Section 6.6.7
13h	03h	25h	DAC-3-MARGIN-HIGH	Section 6.6.2
14h	03h	26h	DAC-3-MARGIN-LOW	Section 6.6.3
15h	FFh	DDh	DAC-3-VOUT-CMP-CONFIG	Section 6.6.4
16h	FFh	DEh	DAC-3-IOUT-MISC-CONFIG	Section 6.6.5
17h	FFh	DFh	DAC-3-CMP-MODE-CONFIG	Section 6.6.6
18h	FFh	E0h	DAC-3-FUNC-CONFIG	Section 6.6.7
19h	00h	21h	DAC-0-DATA	Section 6.6.8
1Ah	01h	21h	DAC-1-DATA	Section 6.6.8
1Bh	02h	21h	DAC-2-DATA	Section 6.6.8
1Ch	03h	21h	DAC-3-DATA	Section 6.6.8
1Fh	FFh	E3h	COMMON-CONFIG	Section 6.6.9
20h	FFh	E4h	COMMON-TRIGGER	Section 6.6.10
21h	FFh	E5h	COMMON-DAC-TRIG	Section 6.6.11

56 Submit Document Feedback

TEXAS INSTRUMENTS www.ti.com

## Table 6-21. Register Names (continued)

I <sup>2</sup> C/SPI ADDRESS	PMBUS PAGE ADDR	PMBUS REGISTER ADDR	REGISTER NAME	SECTION
22h	FFh	E6h	GENERAL-STATUS	Section 6.6.12
23h	FFh	E7h	CMP-STATUS	Section 6.6.13
24h	FFh	E8h	GPIO-CONFIG	Section 6.6.14
25h	FFh	E9h	DEVICE-MODE-CONFIG	Section 6.6.15
26h	FFh	EAh	INTERFACE-CONFIG	Section 6.6.16
2Bh	FFh	EFh	SRAM-CONFIG	Section 6.6.17
2Ch	FFh	F0h	SRAM-DATA	Section 6.6.18
40h	NA	NA	DAC-0-DATA-8BIT	Section 6.6.19
41h	NA	NA	DAC-1-DATA-8BIT	Section 6.6.19
42h	NA	NA	DAC-2-DATA-8BIT	Section 6.6.19
43h	NA	NA	DAC-3-DATA-8BIT	Section 6.6.19
50h	FFh	F1h	BRDCAST-DATA	Section 6.6.20
NA	All pages	00h	PMBUS-PAGE	Section 6.6.21
NA	00h	01h	PMBIS-OP-CMD-0	Section 6.6.22
NA	01h	01h	PMBUS-OP-CMD-1	Section 6.6.22
NA	02h	01h	PMBUS-OP-CMD-2	Section 6.6.22
NA	03h	01h	PMBUS-OP-CMD-3	Section 6.6.22
NA	All pages	78h	PMBUS-CML	Section 6.6.23
NA	All pages	98h	PMBUS-VERSION	Section 6.6.24

## Table 6-22. Access Type Codes

Access Type	Code	Description
Х	Х	Don't care
Read Type		
R	R	Read
Write Type	-	
W	W	Write
Reset or Default Value		
-n		Value after reset or the default value

## 6.6.1 NOP Register (address = 00h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = D0h

	Figure 6-24. NOP Register														
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	NOP														
	R-0h														

....

- - -

#### Table 6-23. NOP Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-0	NOP	R	0000h	No operation

### 6.6.2 DAC-X-MARGIN-HIGH Register (address = 01h, 07h, 0Dh, 13h) [reset = 0000h]

### PMBus page address = 00h, 01h, 02h, 03h, PMBus register address = 25h

#### Figure 6-25. DAC-X-MARGIN-HIGH Register (X = 0, 1, 2, 3)

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	DAC-X-MARGIN-HIGH[11:0] DAC-X-MARGIN-HIGH[9:0]											>	<		
R/W-000h											Х-	0h			

### Table 6-24. DAC-X-MARGIN-HIGH Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-4	DAC-X-MARGIN-HIGH[11:0]	R/W	000h	Margin-high code for DAC output
	DAC-X-MARGIN-HIGH[9:0]			Data are in straight-binary format. MSB left-aligned.
				Use the following bit-alignment:
				DAC63004W VOUT: {DAC-X-MARGIN-HIGH[11:0]} DAC53004W VOUT: {DAC-X-MARGIN-HIGH[9:0], X, X}
				X = Don't care bits.
3-0	x	Х	0	Don't care

## 6.6.3 DAC-X-MARGIN-LOW Register (address = 02h, 08h, 0Eh, 14h) [reset = 0000h]

#### PMBus page address = 00h, 01h, 02h, 03h, PMBus register address = 26h

#### Figure 6-26. DAC-X-MARGIN-LOW Register (X = 0, 1, 2, 3)

				•					<u> </u>			,			
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
					-X-MARG -X-MARG								>	K	
					R/W-	000h							Х-	0h	

#### Table 6-25. DAC-X-MARGIN-LOW Register Field Descriptions

Bit	Field	Туре	Reset	Description			
15-4	DAC-X-MARGIN-LOW[11:0]	R/W	000h	Margin-low code for DAC output			
	DAC-X-MARGIN-LOW[9:0]			Data are in straight-binary format. MSB left-aligned.			
				Use the following bit-alignment:			
				DAC63004W VOUT: {DAC-X-MARGIN-LOW[11:0]} DAC53004W VOUT: {DAC-X-MARGIN-LOW[9:0], X, X}			
				X = Don't care bits.			
3-0	х	Х	0	Don't care			



## 6.6.4 DAC-X-VOUT-CMP-CONFIG Register (address = 03h, 09h, 0Fh, 15h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = D1h, D5h, D9h, DDh

			riguie	· 0-27.	DAC-/			-0014	110 14	egiste	i (x = 0	', I, <b>∠</b> , J	)		
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	Х		VOL	IT-GAIN-	-X			Х			CMP- X-OD- EN	CMP- X-OUT- EN	CMP-X- HIZ-IN- DIS	CMP- X-INV- EN	CMP- X-EN
	X-0h		F	R/W-0h				X-0h			R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h

## Figure 6-27. DAC-X-VOUT-CMP-CONFIG Register (X = 0, 1, 2, 3)

#### Table 6-26. DAC-X-VOUT-CMP-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-13	x	Х	0h	Don't care
12-10	VOUT-GAIN-X	R/W	Oh	000: Gain = 1x, external reference on VREF pin 001: Gain = 1x, VDD as reference 010: Gain = 1.5x, internal reference 011: Gain = 2x, internal reference 100: Gain = 3x, internal reference 101: Gain = 4x, internal reference Others: Invalid
9-5	X	Х	0h	Don't care
4	CMP-X-OD-EN	R/W	0	0: Set OUTx pin as push-pull 1: Set OUTx pin as open-drain in comparator mode (CMP-X-EN = 1 and CMP-X-OUT-EN = 1)
3	CMP-X-OUT-EN	R/W	0	<ul><li>0: Generate comparator output but consume internally</li><li>1: Bring comparator output to the respective OUTx pin</li></ul>
2	CMP-X-HIZ-IN-DIS	R/W	0	<ul> <li>0: FBx input has high-impedance. Input voltage range is limited.</li> <li>1: FBx input is connected to resistor divider and has finite impedance. Input voltage range is same as full-scale.</li> </ul>
1	CMP-X-INV-EN	R/W	0	0: Don't invert the comparator output 1: Invert the comparator output
0	CMP-X-EN	R/W	0	<ul><li>0: Disable comparator mode</li><li>1: Enable comparator mode. Current-output must be in power- down. Voltage-output mode must be enabled.</li></ul>



## 6.6.5 DAC-X-IOUT-MISC-CONFIG Register (address = 04h, 0Ah, 10h, 16h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = D2h, D6h, DAh, DEh

			Figur	re 6-28	. DAC->	K-IOUT	-MISC-	CONFI	G Reg	ister (X	( = 0, 1 <sub>,</sub>	2, 3)			
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	Х			IOUT-RANGE-X				X							
	X-0h			R/W-0h							X-0h				

#### Table 6-27. DAC-X-IOUT-MISC-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-13	X	Х	0h	Don't care
12-9	IOUT-RANGE-X	R/W	0000	0000: 0 μA to 25 μA 0001: 0 μA to 50 μA 0010: 0 μA to 125 μA 0011: 0 μA to 250 μA 0100: 0 μA to -24 μA 0101: 0 μA to -48 μA 0110: 0 μA to -120 μA 0111: 0 μA to -240 μA 1000: -25 μA to +25 μA 1001: -50 μA to +50 μA 1010: -125 μA to +125 μA 1011: -250 μA to +250 μA 0thers: Invalid
8-0	x	Х	000h	Don't care

## 6.6.6 DAC-X-CMP-MODE-CONFIG Register (address = 05h, 0Bh, 11h, 17h) [reset = 0000h]

### PMBus page address = FFh, PMBus register address = D3h, D7h, DBh, DFh

### Figure 6-29. DAC-X-CMP-MODE-CONFIG Register (X = 0, 1, 2, 3)

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	>	X		CMP-X	-MODE					)	<				
	Х-	0h		R/W	/-0h					X-	0h				

## Table 6-28. DAC-X-CMP-MODE-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-12	x	Х	00h	Don't care
11-10	CMP-X-MODE	R/W	00	<ul> <li>00: No hysteresis or window function</li> <li>01: Hysteresis provided using DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW registers</li> <li>10: Window comparator mode with DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW registers setting window bounds</li> <li>11: Invalid</li> </ul>
9-0	x	Х	000h	Don't care



## 6.6.7 DAC-X-FUNC-CONFIG Register (address = 06h, 0Ch, 12h, 18h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = D4h, D8h, DCh, E0h

## Figure 6-30. DAC-X-FUNC-CONFIG Register (X = 0, 1, 2, 3)

		J · · ·			-	-	-		<b>\</b>	- , ,	, .,				
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
CLR-SEL-X	SYNC- CONFIG-X	BRD- CONFIG-X					FUI	NC-GEN	N-CONF	FIG-BLC	CK				
R/W-0h	R/W-0h	R/W-0h						F	R/W-000	)h					

#### Table 6-29. DAC-X-FUNC-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15	CLR-SEL-X	R/W	0	0: Clear DAC-X to zero-scale 1: Clear DAC-X to mid-scale
14	SYNC-CONFIG-X	R/W	0	0: DAC-X output updates immediately after a write command 1: DAC-X output updates with LDAC pin falling-edge or when the LDAC bit in the COMMON-TRIGGER register is set to 1
13	BRD-CONFIG-X	R/W	0	0: Don't update DAC-X with broadcast command 1: Update DAC-X with broadcast command

## Table 6-30. Linear-Slew Mode: FUNC-GEN-CONFIG-BLOCK Field Descriptions

Bit	Field	Туре	Reset	Description
12-11	PHASE-SEL-X	R/W	0	00: 0° 01: 120° 10: 240° 11: 90°
10-8	FUNC-CONFIG-X	R/W	0	000: Triangular wave 001: Sawtooth wave 010: Inverse sawtooth wave 100: Sine wave 111: Disable function generation Others: Invalid
7	LOG-SLEW-EN-X	R/W	0	0: Enable linear slew
6-4	CODE-STEP-X	R/W	0	CODE-STEP for linear slew mode: 000: 1-LSB 001: 2-LSB 010: 3-LSB 011: 4-LSB 100: 6-LSB 101: 8-LSB 110: 16-LSB 111: 32-LSB
3-0	SLEW-RATE-X	R/W	0	SLEW-RATE for linear slew mode:         0000: No slew for margin-high and margin-low. Invalid for         waveform generation.         0001: 4 µs/step         0010: 8 µs/step         0101: 12 µs/step         0101: 12 µs/step         0101: 12 µs/step         0101: 27.04 µs/step         0111: 40.48 µs/step         0111: 60.72 µs/step         1000: 91.12 µs/step         1001: 136.72 µs/step         1001: 136.72 µs/step         1011: 239.2 µs/step         1011: 239.2 µs/step         1011: 418.64 µs/step         1102: 732.56 µs/step         1101: 1282 µs/step         1111: 2563.96 µs/step         1111: 5127.92 µs/step



Bit         Field         Type         Reset         Description           12-11         PHASE-SEL-X         R/W         0         00: 0°         01: 120°           10-8         FUNC-CONFIG-X         R/W         0         000: Triangular wave         001: Sawtooth wave           10-8         FUNC-CONFIG-X         R/W         0         000: Triangular wave         001: Sawtooth wave           10: Inverse sawtooth wave         01: Sawtooth wave         01: Issue sawtooth wave         000: Triangular wave           7         LOG-SLEW-EN-X         R/W         0         1: Enable logarithmic slew.           10 logarithmic slew.         In logarithmic slew.         In logarithmic slew.         In logarithmic slew.           7         LOG-SLEW-EN-X         R/W         0         1: Enable logarithmic slew.         In logarithmic slew.           10 logarithmic slew.         In logarithmic slew.         In logarithmic slew.         In logarithmic slew.         In logarithmic slew.           10 logarithmic slew.         In logarithmic slew.         In logarithmic slew.         In logarithmic slew.           10 logarithmic slew.         In logarithmic slew.         In logarithmic slew.         In logarithmic slew.           10.03125) times the current step.         When slewing in the negative direction, the next step is (	le, or
01: 120°         10 - 8       FUNC-CONFIG-X         R/W       0       000: Triangular wave 001: Sawtooth wave 010: Inverse sawtooth wave 100: Sine wave 111: Disable function generation Others: Invalid         7       LOG-SLEW-EN-X       R/W       0       1: Enable logarithmic slew. In logarithmic slew mode, the DAC output moves from th X-MARGIN-LOW code to the DAC-X-MARGIN-HIGH cod vice versa, in 3.125% steps. When slewing in the positive direction, the next step is (1 0.03125) times the current step. When slewing in the negative direction, the next step is ( 0.03125) times the current step. When DAC-X-MARGIN-LOW is 0, the slew starts from co The time interval for each step is defined by RISE-SLEW FALL-SLEW-X.         6-4       RISE-SLEW-X       R/W       0       SLEW-RATE for logarithmic slew mode (DAC-X-MARGIN DAC-X-MARGIN-HIGH): 000: 4 µs/step	le, or
6-4       RISE-SLEW-X       R/W       0       Substrational state of the set	le, or
6-4       RISE-SLEW-X       R/W       0       SLEW-RATE for logarithmic slew mode (DAC-X-MARGIN-HIGH control of the	le, or
DAC-X-MARGIN-HIGH): 000: 4 µs/step	1 – ode 1.
010: 27.04 µs/step 011: 60.72 µs/step 100: 136.72 µs/step 101: 418.64 µs/step 110: 1282 µs/step 111: 5127.92 µs/step	N-LOW to
3-1       FALL-SLEW-X       R/W       0       SLEW-RATE for logarithmic slew mode (DAC-X-MARGII to DAC-X-MARGIN-LOW):         000: 4 µs/step       001: 12 µs/step       001: 12 µs/step         010: 27.04 µs/step       011: 60.72 µs/step         100: 136.72 µs/step       101: 418.64 µs/step         111: 5127.92 µs/step       111: 5127.92 µs/step	N-HIGH
0 X X 0 Don't care	



## 6.6.8 DAC-X-DATA Register (address = 19h, 1Ah, 1Bh, 1Ch) [reset = 0000h]

## PMBus page address = 00h, 01h, 02h, 03h, PMBus register address = 21h

## Figure 6-31. DAC-X-DATA Register (X = 0, 1, 2, 3)

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
					DAC-X-D DAC-X-D								>	<	
	R/W-000h													0h	

#### Table 6-32. DAC-X-DATA Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-4	DAC-X-DATA[11:0] DAC-X-DATA[9:0]	R/W	000h	Data for DAC output Data are in straight-binary format. MSB left-aligned. Use the following bit-alignment: DAC63004W VOUT: {DAC-X-DATA[11:0]} DAC53004W VOUT: {DAC-X-DATA[9:0], X, X} X = Don't care bits.
3-0	X	Х	0h	Don't care

## 6.6.9 COMMON-CONFIG Register (address = 1Fh) [reset = 0FFFh]

## PMBus page address = FFh, PMBus register address = E3h

#### Figure 6-32. COMMON-CONFIG Register

				<u> </u>						•					
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
WIN- LATCH- EN	DEV- LOCK	EE-READ- ADDR	EN-INT- REF	VOUT-	PDN-3	IOUT- PDN-3	VOUT-F	PDN-2	IOUT- PDN-2	VOUT-	PDN-1	IOUT- PDN-1	VOUT-I	PDN-0	IOUT- PDN-0
R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W	-11b	R/W-1b	R/W-	·11b	R/W-1b	R/W-	-11b	R/W-1b	R/W-	-11b	R/W-1b

#### Table 6-33. COMMON-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15	WIN-LATCH-EN	R/W	0	0: Non-latching window-comparator output 1: Latching window-comparator output
14	DEV-LOCK	R/W	0	0: Device not locked. 1: Device locked, the device locks all the registers. To set this bit back to 0 (unlock device), write to the unlock code to the DEV- UNLOCK field in the COMMON-TRIGGER register first, followed by a write to the DEV-LOCK bit as 0.
13	EE-READ-ADDR	R/W	0	0: Fault-dump read enable at address 0x00 1: Fault-dump read enable at address 0x01
12	EN-INT-REF	R/W	0	0: Disable internal reference. 1: Enable internal reference. This bit must be set before using internal reference gain settings.
11-10, 8-7, 5-4, 2-1	VOUT-PDN-X	R/W	11	00: Power-up VOUT-X 01: Power-down VOUT-X with 10 KΩ to AGND 10: Power-down VOUT-X with 100 KΩ to AGND 11: Power-down VOUT-X with Hi-Z to AGND
9, 6, 3, 0	IOUT-PDN-X	R/W	1	0: Power-up IOUT-X 1: Power-down IOUT-X



## 6.6.10 COMMON-TRIGGER Register (address = 20h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = E4h

## Figure 6-33. COMMON-TRIGGER Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	DEV-UN	NLOCK			RES	SET		LDAC	CLR	х	FAULT- DUMP	PROTECT	READ- ONE- TRIG	NVM- PROG	NVM- RELOAD
	R/W	/-0h			R/W	/-0h		R/W-0h	R/W-0h	X-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h	R/W-0h

## Table 6-34. COMMON-TRIGGER Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-12	DEV-UNLOCK	R/W	0000	0101: Device unlocking password. To unlock device, write this unlock password first, followed by a write 0 to the DEV-LOCK bit in the COMMON-CONFIG register. Others: Don't care
11 - 8	RESET	W	0000	1010: POR reset triggered. This bit self-resets. Others: Don't care
7	LDAC	R/W	0	0: LDAC operation not triggered 1: LDAC operation triggered if the respective SYNC-CONFIG-X bit in the DAC-X-FUNC-CONFIG register is 1. This bit self-resets.
6	CLR	R/W	0	0: DAC registers and outputs unaffected 1: DAC registers and outputs set to zero-code or mid-code based on the respective CLR-SEL-X bit in the DAC-X-FUNC-CONFIG register. This bit self-resets.
5	X	Х	0	Don't care
4	FAULT-DUMP	R/W	0	0: Fault-dump is not triggered 1: Triggers fault-dump sequence. This bit self-resets.
3	PROTECT	R/W	0	0: PROTECT function not triggered 1: Trigger PROTECT function. This bit is self-resetting.
2	READ-ONE-TRIG	R/W	0	0: Fault-dump read not triggered 1: Read one row of NVM for fault-dump. This bit self-resets.
1	NVM-PROG	R/W	0	0: NVM write not triggered 1: NVM write triggered. This bit self-resets.
0	NVM-RELOAD	R/W	0	0: NVM reload not triggered 1: Reload data from NVM to register map. This bit self-resets.



## 6.6.11 COMMON-DAC-TRIG Register (address = 21h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = E5h

				1 19	juie o-	34.00		I-DAC-	ING F	registe	71				
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
RESET- CMP- FLAG-0	TRIG- MAR- LO-0	TRIG- MAR- HI-0	START- FUNC-0	RESET- CMP- FLAG-1	TRIG- MAR- LO-1	TRIG- MAR- HI-1	START- FUNC-1	RESET- CMP- FLAG-2	TRIG- MAR- LO-2	TRIG- MAR- HI-2	START- FUNC-2		TRIG- MAR- LO-3	TRIG- MAR- HI-3	START- FUNC-3
W-0h	W-0h	W-0h	R/W-0h	W-0h	W-0h	W-0h	R/W-0h	W-0h	W-0h	W-0h	R/W-0h	W-0h	W-0h	W-0h	R/W-0h

## Figure 6-34. COMMON-DAC-TRIG Register

### Table 6-35. COMMON-DAC-TRIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15, 11, 7, 3	RESET-CMP-FLAG-X	W	0	0: Latching-comparator output unaffected 1: Reset latching-comparator and window-comparator output. This bit self-resets.
14, 10, 6, 2	TRIG-MAR-LO-X	W	0	0: Don't care 1: Trigger margin-low command. This bit self-resets.
13, 9, 5, 1	TRIG-MAR-HI-X	W	0	0: Don't care 1: Trigger margin-high command. This bit self-resets.
12, 8, 4, 0	START-FUNC-X	R/W	0	0: Stop function generation 1: Start function generation as per FUNC-GEN-CONFIG-X in the DAC-X-FUNC-CONFIG register.



## 6.6.12 GENERAL-STATUS Register (address = 22h) [reset = 00h, DEVICE-ID, VERSION-ID]

## PMBus page address = FFh, PMBus register address = E6h

## Figure 6-35. GENERAL-STATUS Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
NVM- CRC- FAIL-INT	NVM- CRC- FAIL- USER	х	DAC-3- BUSY	DAC-2- BUSY	DAC-1- BUSY	DAC-0- BUSY	х			DEVI	CE-ID			VERS	ION-ID
R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	X-0h			F	र			R-	0h

Bit	Field	Туре	Reset	Description
15	NVM-CRC-FAIL-INT	R	0	0: No CRC error in OTP 1: Indicates a failure in OTP loading. A software reset or power-cycle can bring the device out of this condition in case of temporary failure.
14	NVM-CRC-FAIL-USER	R	0	0: No CRC error in NVM loading 1: Indicates a failure in NVM loading. The register settings are corrupted. The device allows all operations during this error condition. Reprogram the NVM to get original state. A software reset brings the device out of this temporary error condition.
13	X	R	0	Don't care
12	DAC-3-BUSY	R	0	0: DAC-3 channel can accept commands 1: DAC-3 channel does not accept commands
11	DAC-2-BUSY	R	0	0: DAC-2 channel can accept commands 1: DAC-2 channel does not accept commands
10	DAC-1-BUSY	R	0	0: DAC-1 channel can accept commands 1: DAC-1 channel does not accept commands
9	DAC-0-BUSY	R	0	0: DAC-0 channel can accept commands 1: DAC-0 channel does not accept commands
8	X	R	0	Don't care
7-2	DEVICE-ID	R	DAC53004W: 05h DAC63004W: 04h	Device identifier
1-0	VERSION-ID	R	00	Version identifier

## Table 6-36. GENERAL-STATUS Register Field Descriptions

## 6.6.13 CMP-STATUS Register (address = 23h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = E7h

	Figure 6-36. CMP-STATUS Register														
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			х				PROTECT- FLAG	WIN- CMP-3	WIN- CMP-2	WIN- CMP-1	WIN- CMP-0	CMP- FLAG- 3	CMP- FLAG- 2		CMP- FLAG- 0
			X-0h				R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h	R-0h

#### Table 6-37. CMP-STATUS Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-9	x	х	0	Don't care
8	PROTECT-FLAG	R	0	0: PROTECT operation not triggered. 1: PROTECT function is completed or in progress. This bit resets to 0 when read.
7, 6, 5, 4	WIN-CMP-X	R	0	Window comparator output from respective channels. The output is latched or unlatched based on the WINDOW-LATCH-EN setting in the COMMON-CONFIG register.
3, 2, 1, 0	CMP-FLAG-X	R	0	Synchronized comparator output from respective channels.

## 6.6.14 GPIO-CONFIG Register (address = 24h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = E8h

#### Figure 6-37. GPIO-CONFIG Register

							U								
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
GF-EN	DEEP- SLEEP- EN	GPO-EN		GPO-CO	ONFIG			GPI-C	H-SEL			GPI-C	ONFIG		GPI-EN
R/W-0h	R/W-0h	R/W-0h		R/W-0h			R/W-0h				R/V	V-0h		R/W-0h	

#### Table 6-38. GPIO-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15	GF-EN	R/W	0	<ol> <li>O: Glitch filter disabled for GP input. This setting provides faster response.</li> <li>1: Glitch filter enabled for GP input. This setting introduces additional propagation delay but provides robustness.</li> </ol>
14	DEEP-SLEEP-EN	R/W	0	0: Deep-sleep mode disabled 1: Deep-sleep mode enabled for GP input
13	GPO-EN	R/W	0	0: Disable output mode for GPIO pin 1: Enable output mode for GPIO pin
12-9	GPO-CONFIG	R/W	0000	STATUS function setting. The GPIO pin is mapped to thefollowing register bits as output:0001: NVM-BUSY0100: DAC-0-BUSY0101: DAC-1-BUSY0111: DAC-2-BUSY0111: DAC-3-BUSY1010: WIN-CMP-01001: WIN-CMP-11010: WIN-CMP-21011:WIN-CMP-3Others: Invalid



	Table 6-38. GPIO-CONFIG Register Field Descriptions (continued)												
Bit	Field	Туре	Reset	Description									
8-5	GPI-CH-SEL	R/₩	0000	Each bit corresponds to a DAC channel. 0b is <i>disabled</i> and 1b is <i>enabled</i> . GPI-CH-SEL[0]: Channel 0 GPI-CH-SEL[1]: Channel 1 GPI-CH-SEL[2]: Channel 2 GPI-CH-SEL[3]: Channel 3									
				Example: when GPI-CH-SEL is 0101, both channel-0 and channel-2 are enabled and both channel-1 and channel-3 are disabled.									
4-1	GPI-CONFIG	R/W	0000	GPIO pin input configuration. Global settings act on the entire device. Channel-specific settings depend on the channel selection by the GPI-CH-SEL bits:									
				0000: DEEP-SLEEP (global). GPIO falling-edge triggers deep- sleep mode, GPIO rising-edge takes the device out of deep-sleep mode.									
				0010: FAULT-DUMP (global). GPIO falling-edge triggers fault- dump, GPIO = 1 has no effect.									
				0011: IOUT power-up, down (channel-specific). GPIO falling-edge triggers power-down, GPIO rising-edge triggers power-up.									
				0100: VOUT power-up/down (channel-specific). The output load is as per the VOUT-PDN-X setting. GPIO falling-edge triggers power-down, GPIO rising-edge triggers power-up.									
				0101: PROTECT input (global). GPIO falling-edge asserts PROTECT function, GPIO = 1 has no effect.									
				0111: $\overline{\text{CLR}}$ input (global). GPIO = 0 asserts $\overline{\text{CLR}}$ function, GPIO = 1 has no effect.									
				1000: $\overline{\text{LDAC}}$ input (channel-specific). GPIO falling-edge asserts $\overline{\text{LDAC}}$ function, GPIO = 1 has no effect. Both the SYNC-CONFIG-X and the GPI-CH-SEL must be configured for every channel.									
				1001: Start, stop function generation (channel-specific). GPIO falling-edge stops function generation. GPIO rising-edge starts function generation.									
				1010: Trigger margin-high, low (channel-specific). GPIO falling- edge triggers margin-low. GPIO rising-edge triggers margin-high.									
				1011: RESET input (global). The falling-edge of the GPIO pin asserts the RESET function. The RESET input must be a pulse. The GPIO rising-edge brings the device out of reset. The RESET configuration must be programmed into the NVM. Otherwise, the setting is cleared after the device reset.									
				1100: NVM write-protection (global). GPIO falling-edge allows NVM programming. GPIO rising-edge blocks NVM programming.									
				1101: Register-map lock (global). GPIO falling-edge allows update to the register map. GPIO rising-edge blocks any register map update except a write to the DEV-UNLOCK field through I <sup>2</sup> C or SPI and to the RESET field through I <sup>2</sup> C.									
				Others: Not applicable									
0	GPI-EN	R/W	0	0: Disable input mode for GPIO pin 1: Enable input mode for GPIO pin									

## Table 6-38. GPIO-CONFIG Register Field Descriptions (continued)



## 6.6.15 DEVICE-MODE-CONFIG Register (address = 25h) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = E9h

### Figure 6-38. DEVICE-MODE-CONFIG Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
RESE	RVED	DIS- MODE-IN	RE	SERVED	)	PROT CON	TECT- IFIG	R	ESERVE	ED			х		
R/W	/-0h	R/W-0h	I	R/W-0h		R/W	/-0h		R/W-0h				X-0h		

#### Table 6-39. DEVICE-MODE-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-14	RESERVED	R/W	00	Always write 0b00
13	DIS-MODE-IN	R/W	0	Write 1 to this bit for low-power consumption.
12-10	RESERVED	R/W	0	Always write 0b000
9-8	PROTECT-CONFIG	R/W	00	<ul> <li>00: Switch to Hi-Z power-down (no slew)</li> <li>01: Switch to DAC code stored in NVM (no slew) and then switch to Hi-Z power-down</li> <li>10: Slew to margin-low code and then switch to Hi-Z power-down</li> <li>11: Slew to margin-high code and then switch to Hi-Z power-down</li> </ul>
7-5	RESERVED	R/W	0	Always write 0b000
4-0	X	R/W	00h	Don't care

## 6.6.16 INTERFACE-CONFIG Register (address = 26h) [reset = 0000h]

#### Figure 6-39. INTERFACE-CONFIG Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	Х		TIMEOUT- EN		Х		EN-PMBUS			Х			FSDO- EN	Х	SDO- EN
	X-0h		R/W-0h		X-0h		R/W-0h			X-0h			R/W-0h	X-0h	R/W-0h

### Table 6-40. INTERFACE-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-13	X	X	0h	Don't care
12	TIMEOUT-EN	R/W	0	0: I <sup>2</sup> C timeout disabled 1: I <sup>2</sup> C timeout enabled
11-9	X	X	0h	Don't care
8	EN-PMBUS	R/W	0	0: PMBus disabled 1: Enable PMBus
7-3	X	X	00h	Don't care
2	FSDO-EN	R/W	0	0: Fast SDO (FSDO) disabled 1: Fast SDO enabled
1	X	X	0	Don't care
0	SDO-EN	R/W	0	0: SDO disabled 1: SDO enabled on GPIO pin

## 6.6.17 SRAM-CONFIG Register (address = 2Bh) [reset = 0000h]

## PMBus page address = FFh, PMBus register address = EFh

### Figure 6-40. SRAM-CONFIG Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			Х								SRA	M-ADDR			
	X-00h										R/\	N-00h			

### Table 6-41. SRAM-CONFIG Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-8	х	Х	00h	Don't care
7-0	SRAM-ADDR	R/W		8-bit SRAM address. Writing to this register field configures the SRAM address to be accessed next. This address automatically increments after a write to the SRAM.

## 6.6.18 SRAM-DATA Register (address = 2Ch) [reset = 0000h]

### PMBus page address = FFh, PMBus register address = F0h

#### Figure 6-41. SRAM-DATA Register

					•				•						
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	SRAM-DATA														
						I	R/W-000	00h							

### Table 6-42. SRAM-DATA Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-0	SRAM-DATA	R/W		16-bit SRAM data. Data are written to or read from the address configured in the SRAM-CONFIG register.



## 6.6.19 DAC-X-DATA-8BIT Register (address = 40h, 41h, 42h, 43h) [reset = 0000h]

## PMBus page address = Not applicable, PMBus register address = Not applicable

#### Figure 6-42. DAC-X-DATA-8BIT Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		DAC	-X-DATA-8	BIT[7:0]								х			
			R/W-00ł	ı							Х	-00h			

#### Table 6-43. DAC-X-DATA-8BIT Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-8	DAC-X-DATA-8BIT[7:0]	R/W		8-bit data for current output. This register provides faster update rate in the I <sup>2</sup> C mode. Data are in straight-binary format.
7-0	x	Х	00h	Not applicable

#### 6.6.20 BRDCAST-DATA Register (address = 50h) [reset = 0000h]

### PMBus page address = FFh, PMBus register address = F1h

#### Figure 6-43. BRDCAST-DATA Register

15	14	13	12	11	10	9	8	4	3	2	1	0			
					AST-DAT AST-DAT								Х	(	
				R/W-000h X-0h											

#### Table 6-44. BRDCAST-DATA Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-4	BRDCAST-DATA[11:0] BRDCAST-DATA[9:0]	R/W	000h	Broadcast code for all DAC channels Data are in straight-binary format. MSB left-aligned. Use the following bit-alignment: DAC63004W VOUT: {BRDCAST-DATA[11:0]} DAC53004W VOUT: {BRDCAST-DATA[9:0], X, X} X = Don't care bits. The BRD-CONFIG-X bit in the DAC-X-FUNC-CONFIG register must be enabled for the respective channels.
3-0	x	Х	0h	Don't care.

### 6.6.21 PMBUS-PAGE Register [reset = 0300h]

### PMBus page address = X, PMBus register address = 00h

#### Figure 6-44. PMBUS-PAGE Register

1	5	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
				PMBUS	S-PAGE							>	×			
				R/W	-03h							X-0	)0h			

#### Table 6-45. PMBUS-PAGE Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-8	PMBUS-PAGE	R/W		8-bit PMBus page address as specified in the <i>Register Names</i> table in the <i>Register Map</i> section.
7-0	x	Х	00h	Not applicable



## 6.6.22 PMBUS-OP-CMD-X Register [reset = 0000h]

## PMBus page address = 00h, 01h, 02h, 03h, PMBus register address = 01h

## Figure 6-45. PMBUS-OP-CMD-X Register (X = 0, 1, 2, 3)

				•					•	•		,			
15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
		PMBU	IS-OPER	ATION-0	CMD-X						>	<			
			R/W	-00h							X-0	)0h			

### Table 6-46. PMBUS-OP-CMD-X Register Field Descriptions

Bit	Field	Туре	Reset	Description
15-8	PMBUS-OPERATION-CMD-X	R/W	00h	PMBus operation commands: 00h: Turn off 80h: Turn on A4h: Margin high, DAC output margins high to DAC-X-MARGIN- HIGH code 94h: Margin low, DAC output margins low to DAC-X-MARGIN- LOW code
7-0	x	Х	00h	Not applicable

## 6.6.23 PMBUS-CML Register [reset = 0000h]

## PMBus page address = X, PMBus register address = 78h

#### Figure 6-46. PMBUS-CML Register

1	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			)	x			CML	Х				N	/A			
			X-(	00h			R/W-0h	X-0h				X-0	)0h			

#### Table 6-47. PMBUS-CML Register Field Descriptions

				/ 1
Bit	Field	Туре	Reset	Description
15-10	X	Х	00h	Don't care
9	CML	R/W	0	0: No communication fault 1: PMBus communication fault for write with incorrect number of clocks, read before write command, invalid command address, and invalid or unsupported data value; reset this bit by writing 1.
8	x	X	0h	Don't care
7-0	x	Х	00h	Not applicable

#### 6.6.24 PMBUS-VERSION Register [reset = 2200h]

#### PMBus page address = X, PMBus register address =98h

### Figure 6-47. PMBUS-VERSION Register

15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
			PMBUS-\	/ERSIO	N						>	<			
			R-2	22h							X-0	)0h			

### Table 6-48. PMBUS-VERSION Register Field Descriptions

	Bit	Field	Туре	Reset	Description
	15-8	PMBUS-VERSION	R	22h	PMBus version
Γ	7-0	х	х	00h	Not applicable



# 7 Application and Implementation

#### Note


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 7.1 Application Information

The DACx3004W are quad-channel buffered, force-sense output, voltage-output and current-output smart DACs that include an NVM and internal reference, and are available in a tiny 1.76-mm × 1.76-mm DSBGA package. The external reference must not exceed  $V_{DD}$ , either during transient or steady-state conditions. For the best Hi-Z output performance, use a pullup resistor on the VREF pin to VDD. In case the VDD pin remains floating during the off condition, place a 100-k $\Omega$  resistor to AGND for proper detection of the VDD pin *off* condition. All the digital outputs are open drain; use external pullup resistors on these pins. The interface protocol is detected at power-on, and the device locks to the protocol as long as  $V_{DD}$  is on. In I<sup>2</sup>C mode, when allocating the I<sup>2</sup>C addresses in the system, also consider the broadcast address. I<sup>2</sup>C timeout can be enabled for robustness. SPI mode is three-wire by default. Configure the GPIO pin as SDO in the NVM for SPI readback capability. The SPI clock speed in readback mode is slower than in write mode. Power-down mode sets the DAC outputs in Hi-Z by default. Change the configuration appropriately for different power-down settings. The DAC channels can also power-up with a programmed DAC code in the NVM.

### 7.2 Typical Application

The DACx3004W can be used as a programmable current source using an external MOSFET for current values greater than 250  $\mu$ A. The force-sense outputs of DACx3004W can be used to compensate for the gate-source voltage drop caused by temperature, drain current, and aging of the MOSFET. The GPIO pin can be used to switch the output current on or off without the need for run-time software. The slew between the on and off values can be programmed. Figure 7-1 shows how the DACx3004W is used as a programmable current source. A resistor, R<sub>SET</sub>, connected to the source of the MOSFET sets the output current range. This circuit can be used in optical modules that require a high current output with a small size.







#### 7.2.1 Design Requirements

Table 7-1. Design 1 arameters						
PARAMETER	VALUE					
Current output range	0 mA to 200 mA					
DAC range	0 V to 0.6 V					
R <sub>SET</sub>	3 Ω					

#### Table 7-1. Design Parameters

#### 7.2.2 Detailed Design Procedure

 $V_{\text{SET}}$  is controlled by the DACx3004W to adjust the current output.  $R_{\text{SET}}$  sets the output range of the current source. Choose a small  $V_{\text{SET}}$  so that the power dissipation across  $R_{\text{SET}}$  is minimum. Equation 10 calculates  $R_{\text{SET}}$ .

$$R_{SET} = \frac{V_{SET}}{I_{OUT}}$$
(10)

A 0.6-V max V<sub>SET</sub> is used in this example. Equation 11 shows that  $R_{SET}$  is calculated to be 3  $\Omega$ . Choose an  $R_{SET}$  with a power rating of at least 120 mW.

$$R_{SET} = \frac{0.6 \, V}{200 \, \text{mA}} = 3 \, \Omega \tag{11}$$

Equation 12 shows how to calculate the DAC code for a given output voltage, reference, and gain setting.

$$DAC_DATA = \frac{V_{OUT} \times 2^{N}}{V_{REF} \times GAIN}$$
(12)

Equation 13 calculates the DAC code for an output voltage,  $V_{SET}$ , of 0.6 V, the internal 1.21-V reference, and the 1.5 × gain setting.

$$DAC_DATA = \frac{0.6 \text{ V} \times 2^{12}}{1.21 \text{ V} \times 1.5} = 1354 \text{d}$$
(13)

The GPIO pin can be configured as an input to trigger the DACx3x04W output to turn on and off, which turns the current source on and off. Configure the GPIO in the GPIO-CONFIG register. The GPI-EN bit enables the GPIO pin as an input. The GPI-CH-SEL field selects which channels are controlled by the GPI. The GPI-CONFIG field selects the GPI function. Table 6-18 defines the functions for the GPI-CONFIG field. Choose the trigger margin-high or margin-low function if programmable slew is needed, or VOUT power up or down if programmable slew is not needed.

The programmable slew is configured by the CODE-STEP and SLEW-RATE fields in the DAC-X-FUNC-CONFIG Register. The programmable slew is only available when toggling between two values stored in the DAC-X-MARGIN-HIGH and DAC-X-MARGIN-LOW Registers. Section 6.4.5.1.2 discusses how to set the programmable slew. This application example uses a SLEW-RATE of 8  $\mu$ V/s and a CODE-STEP of 8-LSB to achieve a 1.36-ms slew time.



The pseudo code for this application example is as follows:

//SYNTAX: WRITE <REGISTER NAME (Hex code)>, <MSB DATA>, <LSB DATA> //Set gain setting to 1.5x internal reference (1.8 V) (repeat for all channels) WRITE DAC-0-VOUT-CMP-CONFIG(0x3), 0x08, 0x00 //Power-up voltage output on all channels and enable the internal reference WRITE COMMON-CONFIG(0x1F),0x12, 0x49 //Configure GPI for Margin-High, Low trigger for all channels WRITE GPIO-CONFIG(0x24), 0x01, 0xF5 //Set slew rate and code step (repeat for all channels) //CODE\_STEP: 8 LSB, SLEW\_RATE: 8 µs/step WRITE DAC-0-FUNC-CONFIG(0x06), 0x00, 0x52 //Write DAC margin high code (repeat for all channels) //For a 1.8-V output range, the 12-bit hex code for 0.6 V is 0x54A. With 16-bit left alignment, this becomes 0x54A0 WRITE DAC-0-MARGIN-HIGH(0x01), 0x54, 0xA0 //Write DAC margin low code (repeat for all channels) //The 12-bit hex code for 0 V is 0x000. With 16-bit left alignment, this becomes 0x0000 WRITE DAC-0-MARGIN-LOW(0x02), 0x00, 0x00 //Save settings to NVM WRITE COMMON-TRIGGER(0x20), 0x00, 0x02

#### 7.2.3 Application Curve




Figure 7-2. IOUT and VFB On-to-Off Transition



#### 7.3 Power Supply Recommendations

The DACx3004W family of devices does not require specific power-supply sequencing. These devices require a single power supply,  $V_{DD}$ . However, make sure the external voltage reference is applied after VDD. Use a 0.1- $\mu$ F decoupling capacitor for the V<sub>DD</sub> pin. Use a bypass capacitor with a value approximately 1.5  $\mu$ F for the CAP pin.

#### 7.4 Layout

#### 7.4.1 Layout Guidelines

The DACx3004W pin configuration separates the analog, digital, and power pins for an optimized layout. For signal integrity, separate the digital and analog traces, and place decoupling capacitors close to the device pins.

#### 7.4.2 Layout Example




Figure 7-3. Layout Example

Note: The ground and power planes have been omitted for clarity.



# 8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

#### 8.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 8.2 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 8.3 Trademarks

PMBus<sup>™</sup> is a trademark of SMIF, Inc.. TI E2E<sup>™</sup> is a trademark of Texas Instruments. All trademarks are the property of their respective owners.

#### 8.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 8.5 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

#### **9 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

С	hanges from Revision * (March 2023) to Revision A (July 2025)	Page
•	Changed package dimensions from 1.75mm × 1.75mm to 1.76mm × 1.76mm in last bullet in Features	1
•	Changed package dimensions from 1.75mm × 1.75mm to 1.76mm × 1.76mm in Application Information	n <mark>73</mark>
•	Updated YBH package outline with corrected dimensions	77

# 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.


YBH0016-C03



# **PACKAGE OUTLINE**

DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



NOTES:

All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.






# YBH0016-C03

# EXAMPLE BOARD LAYOUT

#### DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



NOTES: (continued)

3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. See Texas Instruments Literature No. SNVA009 (www.ti.com/lit/snva009).






# YBH0016-C03

# **EXAMPLE STENCIL DESIGN**

#### DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.





## **PACKAGING INFORMATION**

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
	(1)	(2)			(3)	(4)	(5)		(0)
DAC53004YBHR	Active	Production	DSBGA (YBH)   16	3000   LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 125	DAC 53004
DAC53004YBHR.A	Active	Production	DSBGA (YBH)   16	3000   LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 125	DAC 53004
DAC63004YBHR	Active	Production	DSBGA (YBH)   16	3000   LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 125	DAC 63004
DAC63004YBHR.A	Active	Production	DSBGA (YBH)   16	3000   LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 125	DAC 63004

<sup>(1)</sup> **Status:** For more details on status, see our product life cycle.

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

# PACKAGE OPTION ADDENDUM


11-Jun-2025



www.ti.com

# TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DAC53004YBHR	DSBGA	YBH	16	3000	180.0	8.4	1.94	1.94	0.69	4.0	8.0	Q1
DAC63004YBHR	DSBGA	YBH	16	3000	180.0	8.4	1.94	1.94	0.69	4.0	8.0	Q1



www.ti.com

# PACKAGE MATERIALS INFORMATION

11-Jun-2025



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DAC53004YBHR	DSBGA	YBH	16	3000	182.0	182.0	20.0
DAC63004YBHR	DSBGA	ҮВН	16	3000	182.0	182.0	20.0

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated