







SN65C1167, SN75C1167, SN65C1168, SN75C1168 SLLS159G - MARCH 1993 - REVISED FEBRUARY 2024

SNx5C116x Dual Differential Drivers and Receivers

1 Features

- Meet or exceed standards TIA/EIA-422-B and ITU recommendation V.11
- BiCMOS process technology
- Low supply-current requirements: 9mA maximum
- Low pulse skew
- Receiver input impedance: 17kΩ typical
- Receiver input sensitivity: ±200mV
- Receiver common-mode input voltage range of -7V to7 V
- Operate from single 5V power supply
- Glitch-free power-up and power-down protection
- Receiver 3-state outputs active-low enable for SN65C1167 and SN75C1167 only
- Improved replacements for the MC34050 and MC34051

2 Applications

- **Motor Drives**
- **Factory Automation**
- **Building Automation**

3 Description

The SN65C1167, SN75C1167, SN65C1168, SN75C1168 dual drivers and receivers integrated circuits designed for balanced transmission lines. The devices meet TIA/EIA-422-B and ITU recommendation V.11.


The SN65C1167 and SN75C1167 combine dual 3state differential line drivers and 3-state differential line receivers, both of which operate from a single 5V power supply. The driver and receiver have activehigh and active-low enables, respectively, which can be connected together externally to function as direction control. The SN65C1168 and SN75C1168 drivers have individual active-high enables.


Package Information


rackage information									
PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾							
SN65C1167	DB (SSOP)	6.2mm x 5.30mm							
SNOSCTION	NS (SOP)	10.3mm x 5.30mm							
	DB (SSOP)	6.2mm x 5.30mm							
SN75C1167	N (PDIP)	19.3mm x 6.35mm							
	NS (SOP)	10.3mm x 5.30mm							
	N (PDIP)	19.3mm x 6.35mm							
SN65C1168	NS (SOP)	10.3mm x 5.30mm							
	PW (TSSOP)	5mm x 4.40mm							
	DB (SSOP)	6.2mm x 5.30mm							
SN75C1168	N (PDIP)	19.3mm x 6.35mm							
3117301100	NS (SOP)	10.3mm x 5.30mm							
	PW (TSSOP)	5mm x 4.4mm							

- For more information, see Section 10.
- The package size (length × width) is a nominal value and includes pins, where applicable.

SN65C1168, SN75C1168







Logic Diagram (Positive Logic)



Table of Contents

1 Features	7 Detailed Description11
2 Applications1	7.1 Functional Block Diagram11
3 Description	7.2 Device Functional Modes12
4 Pin Configuration and Functions3	8 Device and Documentation Support13
5 Specifications5	8.1 Documentation Support13
5.1 Absolute Maximum Ratings5	8.2 Receiving Notification of Documentation Updates13
5.2 ESD Ratings5	8.3 Support Resources13
5.3 Recommended Operating Conditions5	8.4 Trademarks13
5.4 Thermal Information6	8.5 Electrostatic Discharge Caution13
5.5 Electrical Characteristics, Driver Section ⁽²⁾ 6	8.6 Glossary13
5.6 Switching Characteristics7	9 Revision History13
5.7 Electrical Characteristics, Receiver Section	10 Mechanical, Packaging, and Orderable
5.8 Switching Characteristics8	Information13
6 Parameter Measurement Information9	



4 Pin Configuration and Functions




Figure 4-1. SN65C1167: DB or NS Package SN75C1167: DB, N, or NS Package (Top View)

Table 4-1. Pin Functions, SNx5C1167

PIN		TYPE ⁽¹⁾	DESCRIPTION
NAME	NO.	ITPE(")	DESCRIPTION
1B	1	I	Inverting Input of Channel 1 Differential Receiver
1A	2	I	Non-Inverting Input of Channel 1 Differential Receiver
1R	3	0	Single Ended Receiver Output for Channel 1
RE	4	I	Receiver Active Low Enable Input for Channel 1 and 2
2R	5	0	Single Ended Receiver Output for Channel 2
2A	6	I	Non-Inverting Input of Channel 1 Differential Receiver
2B	7	I	Inverting Input of Channel 2 Differential Receiver
GND	8	G	Device Ground
2D	9	I	Single Ended Driver Input for Channel 2
2Y	10	0	Non-Inverting Output of Channel 2 Differential Driver
2Z	11	0	Inverting Output of Channel 2 Differential Driver
DE	12	Į	Driver Active High Enable Input for Channel 1 and 2
1Z	13	0	Inverting Output of Channel 1 Differential Driver
1Y	14	0	Non-Inverting Output of Channel 1 Differential Driver
1D	15	I	Single Ended Driver Input for Channel 1
V _{CC}	16	Р	Device VCC, connect 4.5V to 5.5V Source between this Pin and Device Ground

⁽¹⁾ I = Input, O = Output, I/O = Input or Output, G = Ground, P = Power.






Figure 4-2. SN65C1168: N, NS, or PW Package SN75C1168: DB, N, NS, or PW Package (Top View)

Table 4-2. Pin Functions, SNx5C1168

	PIN						
		TYPE ⁽¹⁾	DESCRIPTION				
NAME	NO.						
1B	1	1	Inverting Input of Channel 1 Differential Receiver				
1A	2	1	Non-Inverting Input of Channel 1 Differential Receiver				
1R	3	0	Single Ended Receiver Output for Channel 1				
1DE	4	I	Driver Active High Enable Input for Channel 1				
2R	5	0	Single Ended Receiver Output for Channel 2				
2A	6	I	Non-Inverting Input of Channel 1 Differential Receiver				
2B	7	I	Inverting Input of Channel 2 Differential Receiver				
GND	8	G	Device Ground				
2D	9	I	Single Ended Driver Input for Channel 2				
2Y	10	0	Non-Inverting Output of Channel 2 Differential Driver				
2Z	11	0	Inverting Output of Channel 2 Differential Driver				
2DE	12	I	Driver Active High Enable Input for Channel 2				
1Z	13	0	Inverting Output of Channel 1 Differential Driver				
1Y	14	0	Non-Inverting Output of Channel 1 Differential Driver				
1D	15	I	Single Ended Driver Input for Channel 1				
V _{CC}	16	Р	Device VCC, connect 4.5V to 5.5V Source between this Pin and Device Ground				

(1) I = Input, O = Output, I/O = Input or Output, G = Ground, P = Power.



5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V _{CC}	Supply voltage range ⁽²⁾		-0.5	7	V
\/	lanut voltage range	Driver	-0.5	V _{CC} + 0.5	V
V _I	Input voltage range	A or B, Receiver	-11	14	V
V_{ID}	Differential input voltage range ⁽³⁾	Receiver	-14	14	V
Vo	Output voltage range	Driver	-0.5	7	V
I _{IK} or I _{OK}	Clamp current range	Driver		±20	mA
	Output ourrent range	Driver		±150	m Λ
I _O	Output current range	Receiver		±25	mA
Icc	Supply current	·		200	mA
	GND current			-200	mA
TJ	Operating virtual junction temperature	Operating virtual junction temperature			°C
T _{stg}	Storage temperature range		-65	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

5.2 ESD Ratings

			VALUE	UNIT
V _(ESD) Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	± 8kV	W	
V _(ESD)	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	± 1kV	V

⁽¹⁾ JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
V _{CC}	Supply voltage		4.5	5	5.5	V
V _{IC}	Common-mode input voltage ⁽¹⁾	Receiver			±7	V
V _{ID}	Differential input voltage	Receiver			±7	V
V _{IH}	High-level input voltage	Except A, B	2			V
V _{IL}	Low-level input voltage	Except A, B			0.8	V
	High lovel output ourrent	Receiver			-6	mA
I _{OH}	High-level output current	Driver			-20	IIIA
	Low-level output current	Receiver			6	mA
I _{OL}	Low-level output current	Driver			20	IIIA

⁽²⁾ All voltages values except differential input voltage are with respect to the network GND.

⁽³⁾ Differential input voltage is measured at the noninverting terminal with respect to the inverting terminal.

⁽²⁾ JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process. .



5.3 Recommended Operating Conditions (continued)

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	MAX	UNIT
T _A	Operating free air temperature	SN75C1167, SN75C1168	0		70	°C
	Operating free-air temperature	SN65C1167, SN65C1168	-40		85	C

(1) Refer to TIA/EIA-422-B for exact conditions.

5.4 Thermal Information

	THERMAL METRIC ⁽¹⁾	DB (SSOP)	N (PDIP)	NS (SOP)	PW (TSSOP)	UNIT
	I HERWAL METRIC	16 PINS	16 PINS	16 PINS	16 PINS	UNII
$R_{\theta JA}$	Junction-to-ambient thermal resistance	102.6	60.6	88.5	107.5	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	48.7	48.1	46.2	38.4	°C/W
R _{0JB}	Junction-to-board thermal resistance	54.3	40.6	50.7	53.7	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	11.8	27.5	13.5	3.2	°C/W
ΨЈВ	Junction-to-board characterization parameter	53.5	40.3	50.3	53.1	°C/W
R ₀ JC(bot)	Junction-to-case (bottom) thermal resistance	N/A	N/A	N/A	N/A	°C/W

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

5.5 Electrical Characteristics, Driver Section⁽²⁾

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

	PARAMETER	TE	EST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
V _{IK}	Input clamp voltage	I _I = −18mA				-1.5	V
V _{OH}	High-level output voltage	$V_{IH} = 2V$,	$V_{IL} = 0.8V$, $I_{OH} = -20mA$	2.4	3.4		V
V _{OL}	Low-level output voltage	V _{IH} = 2V,	V _{IL} = 0.8V, I _{OL} = 20mA		0.2	0.4	V
V _{OD1}	Differential output voltage	I _O = 0mA		2		6	V
V _{OD2}	Differential output voltage (2)			2	3.1		V
Δ V _{OD}	Change in magnitude of differential output voltage	D = 1000 S	aa Figura 6 1			±0.4	V
V _{oc}	Common-mode output voltage	$R_L = 100\Omega$, So	ee rigure 6-1			±3	V
Δ V _{OC}	Change in magnitude of common-mode output voltage					±0.4	V
	Out to the second of the secon	V _{CC} = 0V	V _O = 6V			100	^
I _{O(OFF)}	Output current with power off	$V_{\rm CC} = 0.00$ $V_{\rm O} = -0.25$ V				-100	μA
	High impedance state output ourrent	V _O = 2.5				20	^
I _{OZ}	High-impedance-state output current	V _O = 5				-20	μA
I _{IH}	High-level input current	$V_I = V_{CC}$ or V_I	Н			1	μΑ
I _{IL}	Low-level input current	V _I = GND or \	/ _{IL}			-1	μΑ
I _{OS}	Short-circuit output current ⁽³⁾	$V_O = V_{CC}$ or GND,		-30		-150	mA
	Supply ourrent (total package)(4)	No load,	V _I = V _{CC} or GND		4	6	mA
Icc	Supply current (total package) ⁽⁴⁾	Enabled V _I = 2.4 or 0.5V		5	9	IIIA	
Ci	Input capacitance				6		pF

- (1) All typical values are at V_{CC} = 5V, and T_A = 25°C.
- (2) Refer to TIA/EIA-422-B for exact conditions.
- (3) Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.
- (4) This parameter is measured per input, while the other inputs are at V_{CC} or GND.



5.6 Switching Characteristics

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST CONI	TEST CONDITIONS			MAX	UNIT
t _{PHL}	Propagation delay time, high- to low-level output	R1 = R2 = 50Ω , C1 = C2 = C3 = $40pF$,	R3 = $500Ω$, S1 is open,		7	12	ns
t _{PLH}	Propagation delay time, low- to high-level output	See Figure 6-2			7	12	ns
t _{sk(p)}	Pulse skew				0.5	4	ns
t _r	Rise time	R1 = R2 = 50Ω,	R3 = 500Ω,		5	10	ns
t _f	Fall time	C1 = C2 = C3 = 40pF, SeeFigure 6-3	S1 is open,		5	10	ns
t _{PZH}	Output enable time to high level	$R1 = R2 = 50\Omega$,	R3 = 500Ω,		10	19	ns
t _{PZL}	Output enable time to low level	C1 = C2 = C3 = 40pF, See Figure 6-4	S1 is closed,		10	19	ns
t _{PHZ}	Output disable time from low level	$R1 = R2 = 50\Omega$,	$R3 = 500\Omega$,		7	16	ns
t _{PLZ}	Output disable time from high level	C1 = C2 = C3 = 40pF, See Figure 6-4	S1 is closed,		7	16	ns

⁽¹⁾ All typical values are at V_{CC} = 5V, and T_A = 25°C.

5.7 Electrical Characteristics, Receiver Section

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

	PARAMETER		TEST C	CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
V _{IT+}	Positive-going input threshold volta input	age, differential					0.2	V
V _{IT}	Negative-going input threshold voltage input	age, differential			-0.2 ⁽²⁾			V
V _{hys}	Input hysteresis (V _{IT+} - V _{IT-})					60		mV
V _{IK}	Input clamp voltage, RE	SN75C1167	I _I = −18 mA				-1.5	V
V _{OH}	High-level output voltage		V _{ID} = 200 mV,	I _{OH} = −6 mA	3.8	4.2		V
V _{OL}	Low-level output voltage		V _{ID} = −200 mV,	I _{OL} = 6 mA		0.1	0.3	V
I _{OZ}	High-impedance-state output current	SN75C1167	V _O = VCC or GND			±0.5	±5	μΑ
	Line input current		Other input at 0.1/	V _I = 10 V			1.5	т Л
l ₁	Line input current		Other input at 0 V	V _I = −10 V			-2.5	mA
I _I	Enable input current, RE	SN75C1167	V _I = V _{CC} or GND				±1	μA
r _i	Input resistance		$V_{IC} = -7 \text{ V to } 7 \text{ V},$	Other input at 0 V	4	17		kΩ
	0 1 1/11 1 1		No lood Engblod	V _I = V _{CC} or GND		4	6	т Л
Icc	Supply current (total package)	No load, Enabled	$V_{IH} = 2.4 \text{ V or } 0.5 \text{ V}^{(3)}$		5	9	mA	

⁽¹⁾ All typical values are at V_{CC} = 5V and T_A = 25°C.

⁽²⁾ The algebraic convention, where the less positive (more negative) limit is designated as minimum, is used in this data sheet for common-mode input voltage and threshold voltage levels only.

⁽³⁾ Refer to TIA/EIA-422-B for exact conditions.



5.8 Switching Characteristics

over operating free-air temperature range (unless otherwise noted) (2)

	PARAMETER	TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
t _{PLH}	Propagation delay time, low- to high-level output	See Figure 6-5	9	17	27	ns
t _{PHL}	Propagation delay time, high- to low-level output	See Figure 0-5	9	17	27	ns
t _{TLH}	Transition time, low- to high-level output	V = 0\/ See Figure 6 F		4	9	ns
t _{THL}	Transition time, high- to low-level output	V _{IC} = 0V, See Figure 6-5		4	9	ns
t _{PZH}	Output enable time to high level			13	22	ns
t _{PZL}	Output enable time to low level	D = 1kW See Figure 6.6		13	22	ns
t _{PHZ}	Output disable time from high level	R _L = 1kW, See Figure 6-6		13	22	ns
t _{PLZ}	Output disable time from low level			13	22	ns

⁽¹⁾ All typical values are at V_{CC} = 5V and T_A = 25°C. (2) Measured per input while the other inputs are at V_{CC} or GND



6 Parameter Measurement Information






Figure 6-1. Driver Test Circuit, V_{OD} and V_{OC}



- A. C1, C2, and C3 include probe and jig capacitance.
- B. The input pulse is supplied by a generator having the following characteristics: PRR = 1MHz, 50% duty cycle, $t_r = t_f \le 6$ ns.


Figure 6-2. Driver Test Circuit and Voltage Waveforms



- A. C1, C2, and C3 include probe and jig capacitance.
- B. The input pulse is supplied by a generator having the following characteristics: PRR = 1MHz, 50% duty cycle, $t_r = t_f \le 6$ ns.


Figure 6-3. Driver Test Circuit and Voltage Waveforms






- A. C1, C2, and C3 include probe and jig capacitance.
- B. The input pulse is supplied by a generator having the following characteristics: PRR = 1MHz, 50% duty cycle, t_r = t_f ≤ 6ns.

Figure 6-4. Driver Test Circuit and Voltage Waveforms



- A. C_L includes probe and jig capacitance.
- B. The input pulse is supplied by a generator having the following characteristics: PRR = 1MHz, 50% duty cycle, t_r = t_f ≤6ns.

Figure 6-5. Receiver Test Circuit and Voltage Waveforms



- C_L includes probe and jig capacitance.
- B. The input pulse is supplied by a generator having the following characteristics: PRR = 1MHz, 50% duty cycle, $t_r = t_f \le 6$ ns.

Figure 6-6. Receiver Test Circuit and Voltage Waveforms



7 Detailed Description

7.1 Functional Block Diagram




Figure 7-1. Schematic of Inputs




Figure 7-2. Schematic of Outputs



7.2 Device Functional Modes

7.2.1 Functions Table

Table 7-1. Each Driver(1)

INPUT	ENABLE	OUTPUTS					
D	DE	Υ	Z				
Н	Н	Н	L				
L	Н	L	Н				
X	L	Z	Z				

(1) H = high level, L = low level, X = irrelevant, Z = high impedance

Table 7-2. Each Receiver(1)

DIFFERENTIAL INPUTS A - B	ENABLE RE	OUTPUT R
V _{ID} ≥ 0.2 V	L	Н
-0.2V < V _{ID} < 0.2V	L	?
V _{ID} ≤ −0.2V	L	L
X	Н	Z
Open	L	Н

(1) H = high level, L = low level, ? = indeterminate, X = irrelevant, Z = high impedance (off), Open = input disconnected or connected driver off



8 Device and Documentation Support

8.1 Documentation Support

8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision F (November 2009) to Revision G (February 2024) Changed the numbering format for tables, figures, and cross references throughout the

Pag

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com

9-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
	()	()			(-)	(4)	(5)		(-)
SN65C1167NSR	Obsolete	Production	SOP (NS) 16	-	-	Call TI	Call TI	-40 to 85	65C1167
SN65C1168N	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	SN65C1168N
SN65C1168N.A	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	-40 to 85	SN65C1168N
SN65C1168NSR	Obsolete	Production	SOP (NS) 16	-	-	Call TI	Call TI	-40 to 85	65C1168
SN65C1168PW	Obsolete	Production	TSSOP (PW) 16	-	-	Call TI	Call TI	-40 to 85	CB1168
SN65C1168PWR	Obsolete	Production	TSSOP (PW) 16	-	-	Call TI	Call TI	-40 to 85	CB1168
SN75C1167DB	Obsolete	Production	SSOP (DB) 16	-	-	Call TI	Call TI	-	CA1167
SN75C1167DBR	Active	Production	SSOP (DB) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	CA1167
SN75C1167DBR.A	Active	Production	SSOP (DB) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	CA1167
SN75C1167N	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75C1167N
SN75C1167N.A	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75C1167N
SN75C1167NSR.B	Obsolete	Production	SOP (NS) 16	-	-	Call TI	Call TI	0 to 70	
SN75C1168DBR	Active	Production	SSOP (DB) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	CA1168
SN75C1168DBR.A	Active	Production	SSOP (DB) 16	2000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	CA1168
SN75C1168N	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75C1168N
SN75C1168N.A	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75C1168N
SN75C1168NE4	Active	Production	PDIP (N) 16	25 TUBE	Yes	NIPDAU	N/A for Pkg Type	0 to 70	SN75C1168N
SN75C1168NS	Active	Production	SOP (NS) 16	50 TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	75C1168
SN75C1168NS.A	Active	Production	SOP (NS) 16	50 TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	75C1168
SN75C1168NSR	Obsolete	Production	SOP (NS) 16	-	-	Call TI	Call TI	0 to 70	75C1168
SN75C1168PW	Obsolete	Production	TSSOP (PW) 16	-	-	Call TI	Call TI	0 to 70	CA1168

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.



PACKAGE OPTION ADDENDUM

www.ti.com 9-Nov-2025

(4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN75C1167DBR	SSOP	DB	16	2000	330.0	16.4	8.35	6.6	2.4	12.0	16.0	Q1
SN75C1168DBR	SSOP	DB	16	2000	330.0	16.4	8.35	6.6	2.4	12.0	16.0	Q1

www.ti.com 24-Jul-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN75C1167DBR	SSOP	DB	16	2000	353.0	353.0	32.0
SN75C1168DBR	SSOP	DB	16	2000	353.0	353.0	32.0

PACKAGE MATERIALS INFORMATION

www.ti.com 24-Jul-2025

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
SN65C1168N	N	PDIP	16	25	506	13.97	11230	4.32
SN65C1168N.A	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1167N	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1167N.A	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1168N	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1168N.A	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1168NE4	N	PDIP	16	25	506	13.97	11230	4.32
SN75C1168NS	NS	SOP	16	50	530	10.5	4000	4.1
SN75C1168NS.A	NS	SOP	16	50	530	10.5	4000	4.1





NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
 4. Reference JEDEC registration MO-150.





- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SOP



NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.



SOF



- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOF



- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.







NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.





- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025