

# LMK3H0102 Reference-Less 2-Differential or 5-Single-Ended Output PCIe Gen 1-7 **Compliant Programmable BAW Clock Generator**

#### 1 Features

- Integrated BAW resonator, no need for external reference
- Flexible frequency generation:
  - Two channel dividers: up to three unique output frequencies from 2.5MHz to 400MHz
  - LVCMOS outputs supported up to 200MHz: 1.8V, 2.5V, or 3.3V
  - Combination of AC-LVDS, DC-LVDS, LP-HCSL, and LVCMOS on OUT0 and OUT1 pins
  - Additional LVCMOS output for generation of up to 5 LVCMOS clocks
- Total output frequency stability: ±25ppm
- 2 functional modes: I<sup>2</sup>C or preprogrammed OTP
  - Fully configurable I<sup>2</sup>C address
- PCIe Gen 1 to Gen 7 compliant: Common Clock with or without SSC, SRNS, and SRIS
- Very low PCIe jitter with SSC:
  - PCle Gen 3 Common Clock jitter: 135.3fs maximum (PCIe limit is 1ps)
  - PCIe Gen 4 Common Clock jitter: 135.3fs maximum (PCIe limit is 500fs)
  - PCle Gen 5 Common Clock jitter: 57.5fs maximum (PCIe limit is 150fs)
  - PCIe Gen 6 Common Clock jitter: 34.5fs maximum (PCIe limit is 100fs)
  - PCIe Gen 7 Common Clock jitter: 29.6fs maximum (PCIe limit is 67fs)
- Programmable SSC modulation depth
  - Preprogrammed: -0.1%, -0.25%, -0.3%, and -0.5% down spread
  - Register programmable: –0.1% to –3% down spread or ±0.05% to ±1.5% center spread
- 1.8V to 3.3V supply voltage
- Internal LDOs with -93.1dBc PSNR at 500kHz switching noise for LP-HCSL outputs
- Start-up time: <1.5ms
- Output-to-output skew: <50ps
- Fail-safe digital input pins

## 2 Applications

- PCIe Gen 1 to Gen 7 clock generation
- Server Motherboard
- NIC, SmartNIC
- Hardware Accelerator
- **Multifunction Printer**
- PCIe SSD
- Add-In Card, PCIe Expansion Card

## 3 Description

The LMK3H0102 is a 2-output PCIe Gen 1 to Gen 7 compliant reference-less clock generator with Spread Spectrum Clocking (SSC) support. The part is based on TI proprietary Bulk Acoustic Wave (BAW) technology and provides ±25ppm clock outputs without any crystal or external clock reference. The device can provide two SSC clocks, two non-SSC clocks, or one SSC clock and one non-SSC clock at the same time. The device meets the full PCIe compliance from Gen 1 to Gen 7, including Common Clock with or without SSC, Separate Reference No Spread (SRNS), and Separate Reference Independent Spread (SRIS).


The device can be easily configured through either GPIO pins or I<sup>2</sup>C interface. An external DC/DC can be used to power the device. Refer to Power Supply Recommendations for detailed guidelines on power supply filtering and sourcing from DC/DC.

For OTP default settings for each LMK3H0102Axxx configuration, refer to the LMK3H0102 Configuration Guide.

**Package Information** 

| PART NUMBER | PACKAGE <sup>(1)</sup> | PACKAGE SIZE <sup>(2)</sup> |  |  |
|-------------|------------------------|-----------------------------|--|--|
| LMK3H0102   | RER (TQFN, 16)         | 3.0mm × 3.0mm               |  |  |

- For all available packages, see the section Mechanical, Packaging, and Orderable Information.
- The package size (length × width) is a nominal value and includes pins, where applicable.



Simplified Block Diagram



## **Table of Contents**

| 1 Features1   | 7.5 Programming2                                       |
|---|--|
| 2 Applications 1                                    | 8 Device Registers32                                   |
| 3 Description                                       | 8.1 Register Maps32                                    |
| 4 Pin Configuration and Functions3                  | 9 Application and Implementation42                     |
| 5 Specifications5                                   | 9.1 Application Information42                          |
| 5.1 Absolute Maximum Ratings5                       | 9.2 Typical Applications42                             |
| 5.2 ESD Ratings5                                    | 9.3 Power Supply Recommendations50                     |
| 5.3 Recommended Operating Conditions5               | 9.4 Layout5  |
| 5.4 Thermal Information6                            | 10 Device and Documentation Support52                  |
| 5.5 Electrical Characteristics6                     | 10.1 Documentation Support52                           |
| 5.6 I2C Interface Specification12                   | 10.2 Receiving Notification of Documentation Updates52 |
| 6 Parameter Measurement Information14               | 10.3 Support Resources52                               |
| 6.1 Output Format Configurations14                  | 10.4 Trademarks52                                      |
| 6.2 Differential Voltage Measurement Terminology 15 | 10.5 Electrostatic Discharge Caution52                 |
| 7 Detailed Description16                            | 10.6 Glossary52  |
| 7.1 Overview  | 11 Revision History52                                  |
| 7.2 Functional Block Diagram17                      | 12 Mechanical, Packaging, and Orderable                |
| 7.3 Feature Description17                           | Information53  |
| 7.4 Device Functional Modes22                       | 12.1 Tape and Reel Information5                        |



## **4 Pin Configuration and Functions**




Figure 4-1. LMK3H0102 16-Pin TQFN Top View

**Table 4-1. Pin Functions** 

| PIN NAME NO.          |   | TYPE <sup>(1)</sup> | DESCRIPTION  |
|-----------------------|---|---------------------|--|
| NAME                  | NO.   | ITPE                | DESCRIPTION  |
| OUT0_P, OUT0_N        | 8, 7  | 0                   | Clock output 0. Supports LP-HCSL (85 $\Omega$ or 100 $\Omega$ ), LVDS or 1.8-V/2.5-V/3.3-V LVCMOS.   |
| OUT1_P, OUT1_N        | 12, 11  | 0                   | Clock output 1. Supports LP-HCSL (85 $\Omega$ or 100 $\Omega$ ), LVDS or 1.8-V/2.5-V/3.3-V LVCMOS.   |
| REF_CTRL<br>(REF_CLK) | Pin 2, Pin 3 and Pin 4. Pull low or leave floating for I2C mode or high for O1 to power-up. After power-up, this pin can be programmed as an additional L (REF_CLK), active-high CLK_READY signal, or disabled.  See REF_CTRL Operation for more details. This pin has an 880-kΩ internal pulldown resistor.  Output Enable. Active low. 2-state logic input pin. |                     | See REF_CTRL Operation for more details.   |
| OE                    | 1   | I                   | Output Enable. Active low. 2-state logic input pin. This pin has a 75-kΩ internal pulldown resistor. This pin can control either OUT0 alone or OUT0 and OUT1. See Output Enable for more details.  Low/Floating: OUT0 and OUT1 enabled High: OUT0 and OUT1 disabled                        |
| FMT_ADDR              | DDR  2 Multifunctional pin. Functionality is determined OTP Mode and I2C Mode for more details. This pin has an 880-kΩ internal pulldown resident of the I2C Mode: This pin can select the I2C address OUT1, or have no function.   |                     | <ul> <li>This pin has an 880-kΩ internal pulldown resistor.</li> <li>I2C Mode: This pin can select the I2C address, function as the output enable for OUT1, or have no function.</li> <li>OTP Mode: This pin can set the output format, function as the output enable for OUT1,</li> </ul> |



## **Table 4-1. Pin Functions (continued)**

| PIN                           |           | TYPE(1) | DESCRIPTION  |
|-------------------------------|-----------|---------|--|
| NAME                          | NO.       | ITPE(') | DESCRIPTION  |
| OTP_SEL0/SCL,<br>OTP_SEL1/SDA | 3, 4      | I, I/O  | Multifunctional pin. Functionality is determined by REF_CTRL (pin 15) at power up. See OTP Mode and I2C Mode for details. These pins have 880-kΩ internal pulldown resistors.  • I2C Mode: These pins are the I2C clock and data connections.  • OTP Mode: These pins select the OTP page. |
| VDD                           | 5, 14, 16 | Р       | 1.8-V, 2.5-V or 3.3-V device power supply. A 0.1-μF capacitor must be placed as close to each of the pins as possible. For LMK3H0102V18, only provide 1.8 V to this pin.   |
| VDDO_0, VDDO_1                | 10, 13    | Р       | 1.8-V, 2.5-V or 3.3-V OUT0 and OUT1 power supply. If VDD is 1.8 V or 2.5 V, the VDDO pins must be the same voltage as VDD. A 0.1-µF capacitor must be placed as close to each of the pins as possible.   |
| NC                            | 6, 9      | N/A     | No connect. Pins can be connected to GND, VDD, or otherwise tied to any potential within the Supply Voltage range stated in the <i>Absolute Maximum Ratings</i> .  |
| DAP                           | 17        | G       | GND  |

<sup>(1)</sup> I = Input, O = Output, I/O = Input or Output, G = Ground, P = Power.

## **5 Specifications**

## 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

|                  |  | MIN  | MAX                      | UNIT |
|------------------|--|------|--------------------------|------|
| $V_{DD}$         | Device supply voltage  | -0.3 | 3.9                      | V    |
| $V_{DDO}$        | Output supply voltage  | -0.3 | 3.9                      | V    |
| V <sub>IN</sub>  | Logic input voltage (V <sub>DD</sub> = V <sub>DDO</sub> = -0.3 to 3.9 V)               | -0.3 | 3.9                      | V    |
|                  | Voltage applied to OUTx_P and OUTx_N pins (when outputs are high or low)               | -0.3 | V <sub>DDO_x</sub> + 0.3 | V    |
| V <sub>OUT</sub> | Voltage applied to OUTx_P and OUTx_N pins (when outputs are LVCMOS tri-state)          | -0.3 | 1.89                     | V    |
|                  | Voltage applied to OUTx_P and OUTx_N pins (when outputs are LP-HCSL or LVDS tri-state) | -0.3 | 1.5                      | V    |
| T <sub>J</sub>   | Junction temperature   |      | 105                      | °C   |

<sup>(1)</sup> Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

## 5.2 ESD Ratings

|                    |                         |   | VALUE | UNIT    |
|--------------------|-------------------------|---|-------|---------|
| V(ESD)             | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/<br>JEDEC JS-001, all pins <sup>(1)</sup>     | ±2000 | V       |
| V <sub>(ESD)</sub> | Electrostatic discharge | Charged device model (CDM), per JEDEC specification JS-002, all pins <sup>(2)</sup> | ±500  | ±2000 V |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## **5.3 Recommended Operating Conditions**

 $V_{DD}$  =  $V_{DDO}$  = 1.8 V, 2.5 V or 3.3 V ± 5%,  $T_A$  =  $T_{A,min}$  to  $T_{A,max}$ 

|                   |  | MIN   | NOM | MAX   | UNIT |
|-------------------|--|-------|-----|-------|------|
|                   |  | 1.71  | 1.8 | 1.89  | V    |
| $V_{DD}$          | Device supply voltage                                    | 2.375 | 2.5 | 2.625 | V    |
|                   |  | 3.135 | 3.3 | 3.465 | V    |
|                   |  | 1.71  | 1.8 | 1.89  | V    |
| $V_{DDO}$         | Output supply voltage                                    | 2.375 | 2.5 | 2.625 | V    |
|                   |  | 3.135 | 3.3 | 3.465 | V    |
| T <sub>A</sub>    | Ambient temperature                                      | -40   |     | 85    | °C   |
| TJ                | Junction temperature                                     | -40   |     | 105   | °C   |
| t <sub>ramp</sub> | Power supply ramp time. V <sub>DD</sub> = 1.8 V          | 0.05  |     | 5     | ms   |
| t <sub>ramp</sub> | Power supply ramp time. V <sub>DD</sub> = 2.5 V or 3.3 V | 0.05  |     | 5     | ms   |



## **5.4 Thermal Information**

|                        |  | LMK3H0102 |      |
|------------------------|--|-----------|------|
|                        | THERMAL METRIC(1)                            | RER (QFN) | UNIT |
|                        |  | 16 PINS   |      |
| R <sub>0JA</sub>       | Junction-to-ambient thermal resistance       | 69.8      | °C/W |
| R <sub>0</sub> JC(top) | Junction-to-case (top) thermal resistance    | 56.5      | °C/W |
| R <sub>θJB</sub>       | Junction-to-board thermal resistance         | 38.6      | °C/W |
| $\Psi_{JT}$            | Junction-to-top characterization parameter   | 2.1       | °C/W |
| $\Psi_{JB}$            | Junction-to-board characterization parameter | 38.5      | °C/W |
| R <sub>0</sub> JC(bot) | Junction-to-case (bottom) thermal resistance | 10.3      | °C/W |

<sup>(1)</sup> For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application note.

## **5.5 Electrical Characteristics**

 $V_{DD}$  =  $V_{DDO}$  = 1.8 V, 2.5 V or 3.3 V ± 5%,  $T_A$  =  $T_{A,min}$  to  $T_{A,max}$ 

|                        | PARAMETER   | TEST CONDITIONS   | MIN | TYP | MAX  | UNIT |
|------------------------|---|---|-----|-----|------|------|
| FREQUE                 | NCY STABILITY   |   |     |     |      |      |
| $\Delta f_total$       | Total frequency stability                             | All factors included: temperature variation, 10-year aging at 25°C, solder shift, hysteresis and initial frequency accuracy | -25 |     | 25   | ppm  |
| LP-HCSL                | CLOCK OUTPUT CHARACTERISTICS                          |   |     |     |      |      |
| f <sub>out</sub>       | Output frequency                                      |   | 2.5 |     | 400  | MHz  |
| V <sub>min</sub>       | Output low voltage (undershoot included)              |   | -60 |     | 25   | mV   |
| V <sub>overshoot</sub> | Overshoot voltage. V <sub>max</sub> - V <sub>OH</sub> |   |     |     | 150  | mV   |
|                        |   | code = 0  | 563 | 625 | 688  | mV   |
|                        |   | code = 1  | 582 | 647 | 712  | mV   |
|                        |   | code = 2  | 601 | 668 | 735  | mV   |
|                        |   | code = 3  | 621 | 690 | 759  | mV   |
|                        |   | code = 4  | 641 | 712 | 783  | mV   |
|                        |   | code = 5  | 660 | 733 | 806  | mV   |
|                        |   | code = 6 (default)  | 680 | 755 | 831  | mV   |
| V <sub>OH,2.5/3.</sub> | Output high voltage, VDD = 2.5 V or 2.2 V             | code = 7  | 699 | 777 | 855  | mV   |
| 3                      | Output high voltage. VDD = 2.5 V or 3.3 V             | code = 8  | 718 | 798 | 878  | mV   |
|                        |   | code = 9  | 738 | 820 | 902  | mV   |
|                        |   | code = 10   | 758 | 842 | 926  | mV   |
|                        |   | code = 11   | 777 | 863 | 949  | mV   |
|                        |   | code = 12   | 797 | 885 | 974  | mV   |
|                        |   | code = 13   | 816 | 907 | 998  | mV   |
|                        |   | code = 14   | 835 | 928 | 1021 | mV   |
|                        |   | code = 15   | 855 | 950 | 1045 | mV   |
|                        |   |   |     |     |      |      |

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

 $V_{DD}$  =  $V_{DDO}$  = 1.8 V, 2.5 V or 3.3 V ± 5%,  $T_{A}$  =  $T_{A,min}$  to  $T_{A,max}$ 

|                        | PARAMETER  | TEST CONDITIONS   | MIN   | TYP | MAX   | UNIT |
|------------------------|--|---|-------|-----|-------|------|
|                        |  | code = 0  | 563   | 625 | 688   | mV   |
|                        |  | code = 1  | 582   | 647 | 712   | mV   |
|                        |  | code = 2  | 601   | 668 | 735   | mV   |
|                        |  | code = 3  | 621   | 690 | 759   | mV   |
|                        |  | code = 4  | 641   | 712 | 783   | mV   |
|                        |  | code = 5  | 660   | 733 | 806   | mV   |
|                        |  | code = 6 (default)  | 680   | 755 | 831   | mV   |
|                        |  | code = 7  | 699   | 777 | 855   | mV   |
| $V_{OH,1.8}$           | Output high voltage. VDD = 1.8 V                     | code = 8  | 718   | 798 | 878   | mV   |
|                        |  | code = 9  | 738   | 820 | 902   | mV   |
|                        |  | code = 10   | 758   | 842 | 926   | mV   |
|                        |  | code = 11   | 777   | 863 | 949   | mV   |
|                        |  | code = 12   | 797   | 885 | 974   | mV   |
|                        |  | code = 13   | 816   | 907 | 998   | mV   |
|                        |  | code = 14   | 835   | 928 | 1021  | mV   |
|                        |  | code = 15   | 855   | 950 | 1045  | mV   |
|                        |  |   | 80.75 | 85  | 91.25 | Ω    |
| $Z_{diff}$             | LP-HCSL static differential impedance                |   | 95    | 100 | 105   | Ω    |
|                        | Output slew rate (rising and falling edge)           | Measured from –150 mV to +150 mV on the differential waveform, centered on the zero crossing point. OUTx_SLEW_RATE = 0 <sup>(1)</sup> | 2.1   |     | 3.1   | V/ns |
|                        |  | Measured from –150 mV to +150 mV on the differential waveform, centered on the zero crossing point. OUTx_SLEW_RATE = 0                | 2.3   |     | 3.5   | V/ns |
| dV/dt                  |  | Measured from -150 mV to +150 mV on the differential waveform, centered on the zero crossing point. OUTx_SLEW_RATE = 1                | 2     |     | 3.2   | V/ns |
|                        |  | Measured from –150 mV to +150 mV on the differential waveform, centered on the zero crossing point. OUTx_SLEW_RATE = 2                | 1.7   |     | 2.8   | V/ns |
|                        |  | Measured from –150 mV to +150 mV on the differential waveform, centered on the zero crossing point. OUTx_SLEW_RATE = 3                | 1.4   |     | 2.7   | V/ns |
| ∆dV/dt                 | Rising edge rate to falling edge rate matching       | See <sup>(1)</sup>  |       |     | 3     | %    |
|                        |  | See <sup>(1)</sup>  | 47    |     | 53    | %    |
| ODC                    | Output duty cycle                                    | f <sub>out</sub> ≤ 325 MHz  | 47    |     | 53    | %    |
|                        |  | 325 MHz < f <sub>out</sub> ≤ 400 MHz  | 47    |     | 53    | %    |
| t <sub>skew</sub>      | Output to output skew                                | Same FOD, LP-HCSL output  |       |     | 50    | ps   |
| V <sub>cross</sub>     | Absolute crossing point voltage                      | See <sup>(1)</sup>  | 280   |     | 480   | mV   |
| $\Delta V_{cross}$     | Variation of V <sub>cross</sub> over all clock edges | See <sup>(1)</sup>  |       |     | 30    | mV   |
| V <sub>RB</sub>        | Absolute value of ring back voltage                  | See <sup>(1)</sup>  | 100   |     |       | mV   |
| stable                 | Time before V <sub>RB</sub> is allowed               | See <sup>(1)</sup>  | 500   |     |       | ps   |
| J <sub>cycle-to-</sub> | Cycle to cycle jitter, Common Clock no SSC           | See <sup>(1)</sup>  |       |     | 20    | ps   |



 $V_{DD} = V_{DDO} = 1.8 \text{ V}, 2.5 \text{ V or } 3.3 \text{ V} \pm 5\%, T_A = T_{A,min} \text{ to } T_{A,max}$ 

|                                   | PARAMETER   | TEST CONDITIONS   | MIN                       | TYP | MAX        | UNIT |
|-----------------------------------|---|---|---------------------------|-----|------------|------|
| J <sub>cycle-to-</sub><br>cycle   | Cycle to cycle jitter, Common Clock, -0.5% SSC  | See <sup>(1)</sup>  |                           |     | 25         | ps   |
| t <sub>period_abs</sub>           | Absolute period including jitter and SSC  | See <sup>(1)</sup>  | 9.949                     | 10  | 10.101     | ns   |
| t <sub>period_avg</sub><br>_CC    | Average clock period accuracy, Common Clock   | See <sup>(1)</sup>  | -100                      |     | 2600       | ppm  |
| t <sub>period_avg</sub><br>_SRIS  | Average clock period accuracy, SRIS   | See <sup>(1)</sup>  | -100                      |     | 1600       | ppm  |
| LVDS CL                           | OCK OUTPUT CHARACTERISTICS  |   |                           |     |            |      |
| f <sub>out</sub>                  | Output frequency  |   | 2.5                       |     | 400        | MHz  |
| V <sub>OD</sub>                   | Steady-state magnitude of the differential output voltage  V <sub>OUTP</sub> - V <sub>OUTN</sub>                                | 100 Ω external termination                                      | 250                       | 350 | 450        | mV   |
| $\Delta V_{pp	ext{-diff}}$        | Change in differential output voltage swing between complementary output states   | 100 Ω external termination                                      |                           |     | 50         | mV   |
|                                   |   | $V_{DDO}$ = 3.3 V, 100 Ω external termination                   | 1.12                      | 1.2 | 1.365      | V    |
| Vos                               | Output offset voltage (common mode voltage)   | $V_{DDO}$ = 2.5 V, 100 Ω external termination                   | 1.1                       | 1.2 | 1.345      | V    |
|                                   |   | V <sub>DDO</sub> = 1.8 V, 100 Ω external termination            | 0.8                       |     | 0.97       | V    |
| ΔV <sub>OS</sub>                  | Change in V <sub>OS</sub> between complementary output states   |   |                           |     | 50         | mV   |
| I <sub>SA</sub> , I <sub>SB</sub> | Short-circuit current. Magnitude of current with the generator output terminals short-circuited to the generator circuit common |   | -24                       |     | 24         | mA   |
| I <sub>SAB</sub>                  | Short-circuit current. Magnitude of current with generator output terminals short-circuited to each other                       |   | -12                       |     | 12         | mA   |
|                                   |   | OUTx_SLEW_RATE = 0  | 195                       |     | 323        | ps   |
| t <sub>R</sub> , t <sub>F</sub>   | 20% to 80% differential rise/fall time  | OUTx_SLEW_RATE = 1  | 250                       |     | 454        | ps   |
| K, 4                              | 2070 to 0070 differential fiberial affice   | OUTx_SLEW_RATE = 2  | 270                       |     | 635<br>792 | ps   |
|                                   |   | OUTx_SLEW_RATE = 3  | 280                       |     |            | ps   |
| t <sub>skew</sub>                 | Output to output skew   | Same FOD, LVDS output   |                           |     | 50         | ps   |
| ODC                               | Output duty cycle   |   | 47                        |     | 53         | %    |
| LVCMOS                            | CLOCK OUTPUT CHARACTERISTICS  |   |                           |     |            |      |
| f <sub>out</sub>                  | Output frequency  |   | 2.5                       |     | 200        | MHz  |
|                                   |   | $V_{DDO}$ = 3.3 V ± 5%, measured from 20% to 80%, 4.7 pF load   | 2.6                       |     | 4.7        | V/ns |
| dV/dt                             | Output slew rate  | $V_{DDO}$ = 2.5 V ± 5%, measured from 20% to 80%, 4.7 pF load   | 2.6                       |     | 3.7        | V/ns |
|                                   |   | $V_{DDO}$ = 1.8 V ± 5%, measured from 20% to 80%, 4.7 pF load   | 1.5                       |     | 3.2        | V/ns |
|                                   |   | I <sub>OH</sub> = -15 mA at 3.3 V                               | • •                       |     |            |      |
| $V_{OH}$                          | Output high voltage   | I <sub>OH</sub> = -12 mA at 2.5 V                               | 0.8 x<br>V <sub>DDO</sub> |     | $V_{DDO}$  | V    |
|                                   |   | I <sub>OH</sub> = -8 mA at 1.8 V                                | - 5550                    |     |            |      |
|                                   |   | I <sub>OL</sub> = 15 mA at 3.3 V                                |                           |     |            |      |
| $V_{OL}$                          | Output low voltage  | I <sub>OL</sub> = 12 mA at 2.5 V                                |                           |     | 0.4        | V    |
|                                   |   | I <sub>OL</sub> = 8 mA at 1.8 V                                 |                           |     |            |      |
| I <sub>leak</sub>                 | Output leakage current  | Output tri-stated. V <sub>DD</sub> = V <sub>DDO</sub> = 3.465 V | -5                        | 0   | 5          | μΑ   |
| R <sub>out</sub>                  | Output impedance  |   |                           | 17  |            | Ω    |
| 000                               | Outrout duty must   | f <sub>out</sub> ≤ 156.25 MHz                                   | 45                        |     | 55         | %    |
| ODC                               | Output duty cycle   | f <sub>out</sub> > 156.25 MHz                                   | 40                        |     | 60         | %    |

 $V_{DD}$  =  $V_{DDO}$  = 1.8 V, 2.5 V or 3.3 V ± 5%,  $T_A$  =  $T_{A,min}$  to  $T_{A,max}$ 

|                                   | PARAMETER   | TEST CONDITIONS  | MIN                 | TYP   | MAX   | UNIT   |
|-----------------------------------|---|--|---------------------|-------|-------|--------|
| t <sub>skew</sub>                 | Output-to-output skew   | Same FOD, LVCMOS output  |                     |       | 50    | ps     |
| C <sub>load</sub>                 | Maximum load capacitance  |  |                     |       | 15    | pF     |
| LVCMOS                            | REFCLK CHARATERISTICS   |  |                     |       | '     |        |
| f <sub>out</sub>                  | Output frequency  | See <sup>(2)</sup>   | 12.5 <sup>(3)</sup> |       | 200   | MHz    |
|                                   |   | $V_{DDO}$ = 3.3 V ± 5%, measured from 20% to 80%, 4.7 pF load <sup>(2)</sup>   | 2.6                 |       | 6.7   | V/ns   |
| dV/dt                             | Output slew rate  | $V_{DDO}$ = 2.5 V ± 5%, measured from 20% to 80%, 4.7 pF load <sup>(2)</sup>   | 1.8                 |       | 4.5   | V/ns   |
|                                   |   | $V_{DDO}$ = 1.8 V ± 5%, measured from 20% to 80%, 4.7 pF load <sup>(2)</sup>   | 1                   |       | 3.2   | V/ns   |
| I <sub>leak</sub>                 | Output leakage current  | Output tri-stated. V <sub>DD</sub> = V <sub>DDO</sub> = 3.465 V <sup>(2)</sup> | -5                  |       | 5     | μΑ     |
| R <sub>out</sub>                  | Output impedance  |  |                     | 17    |       | Ω      |
| ODC                               | Output duty cycle   | f <sub>out</sub> ≤ 156.25 MHz <sup>(2)</sup>                                   | 45                  |       | 55    | %      |
| ODC                               | Output duty cycle   | f <sub>out</sub> > 156.25 MHz <sup>(2)</sup>                                   | 40                  |       | 60    | %      |
| C <sub>load</sub>                 | Maximum load capacitance  | See <sup>(2)</sup>   |                     |       | 15    | pF     |
| RJ                                | Random jitter   | 12 kHz to 20 MHz integrated jitter at 50 MHz <sup>(2)</sup>                    |                     |       | 0.5   | ps     |
| SSC CHA                           | ARACTERISTICS   |  |                     |       | '     |        |
| f <sub>out</sub>                  | Output frequency range that supports SSC (any output format)              |  | 2.5                 |       | 200   | MHz    |
| f <sub>SSC</sub>                  | SSC modulation frequency  |  | 30                  | 31.5  | 33    | kHz    |
| f <sub>SSC-</sub>                 |   | Down spread (programmable)   | -3                  |       | -0.1  | %      |
| deviation                         | SSC deviation (modulation depth)  | Center spread (programmable)   | ±0.05               |       | ±1.5  | %      |
|                                   |   | f <sub>out</sub> ≤ 100 MHz, down spread  | 0                   |       | 0.01  | %      |
| f <sub>SSC-</sub>                 |   | 100 MHz < f <sub>out</sub> ≤ 200 MHz, down spread                              | 0                   |       | 0.05  | %      |
| deviation-                        | SSC deviation accuracy  | f <sub>out</sub> ≤ 100 MHz, center spread                                      | 0                   |       | 0.01  | %      |
| accuracy                          |   | 100 MHz < f <sub>out</sub> ≤ 200 MHz, center spread                            | 0                   |       | 0.05  | %      |
| df/dt                             | max SSC frequency slew rate   | 0 < f <sub>SSC-deviation</sub> ≤ −0.5%   |                     |       | 1250  | ppm/µs |
| JITTER C                          | CHARACTERISTICS   |  |                     |       |       |        |
| J <sub>PCle1-cc-</sub><br>SSC_off | PCIe Gen 1 Common Clock jitter, SSC is off (jitter limit = 86 ps)         | SSC disabled on both outputs   |                     |       | 0.8   | ps     |
| J <sub>PCle1-cc-</sub><br>SSC_on  | PCIe Gen 1 Common Clock jitter, −0.5% ≤ SSC < 0% (jitter limit = 86 ps)   | SSC enabled on both outputs  |                     |       | 1.4   | ps     |
| J <sub>PCle2-cc-</sub><br>SSC_off | PCIe Gen 2 Common Clock jitter, SSC is off (jitter limit = 3 ps)          | SSC disabled on both outputs   |                     | 0.2   | 0.3   | ps     |
| J <sub>PCle2-cc-</sub><br>SSC_on  | PCIe Gen 2 Common Clock jitter, –0.5% ≤ SSC < 0% (jitter limit = 3 ps)    | SSC enabled on both outputs  |                     | 0.3   | 0.5   | ps     |
| J <sub>PCle2-</sub><br>SRNS       | PCle Gen 2 SRNS jitter  | SSC disabled on both outputs   |                     | 0.2   | 0.3   | ps     |
| J <sub>PCle2</sub> -<br>SRIS      | PCIe Gen 2 SRIS jitter, −0.3% ≤ SSC < 0%                                  | SSC enabled on both outputs  |                     | 0.3   | 0.5   | ps     |
| J <sub>PCle3-cc-</sub><br>SSC_off | PCIe Gen 3 Common Clock jitter, SSC is off (jitter limit = 1 ps)          | SSC disabled on both outputs   |                     | 42.8  | 84.2  | fs     |
| J <sub>PCle3-cc-</sub><br>SSC_on  | PCIe Gen 3 Common Clock jitter, −0.5%<br>≤ SSC < 0% (jitter limit = 1 ps) | SSC enabled on both outputs  |                     | 63.1  | 135.3 | fs     |
| J <sub>PCle3-</sub><br>SRNS       | PCIe Gen 3 SRNS jitter  | SSC disabled on both outputs   |                     | 48.8  | 97.5  | fs     |
| J <sub>PCle3-</sub><br>SRIS       | PCIe Gen 3 SRIS jitter, -0.3% ≤ SSC < 0%                                  | SSC enabled on both outputs  |                     | 194.1 | 418.5 | fs     |
|                                   | <u> </u>  | 1  |                     |       |       |        |



 $V_{DD} = V_{DDO} = 1.8 \text{ V}, 2.5 \text{ V or } 3.3 \text{ V} \pm 5\%, T_A = T_{A,min} \text{ to } T_{A,max}$ 

| PCIe Gen 4 Common Clock jitter, SSC is                                      |  |   |  |   |   |
|---|--|---|--|---|---|
| off (jitter limit = 500 fs)   | SSC disabled on both outputs   |   | 42.8   | 84.2  | fs  |
| PCIe Gen 4 Common Clock jitter, –0.5%<br>≤ SSC < 0% (jitter limit = 500 fs) | SSC enabled on both outputs  |   | 63.1   | 135.3   | fs  |
| PCIe Gen 4 SRNS jitter  | SSC disabled on both outputs   |   | 48.8   | 97.5  | fs  |
| PCIe Gen 4 SRIS jitter, –0.3% ≤ SSC < 0%                                    | SSC enabled on both outputs  |   | 98.5   | 205.4   | fs  |
| PCIe Gen 5 Common Clock jitter, SSC is off (jitter limit = 150 fs)          | SSC disabled on both outputs   |   | 17.8   | 35.6  | fs  |
| PCIe Gen 5 Common Clock jitter, –0.5%<br>≤ SSC < 0% (jitter limit = 150 fs) | SSC enabled on both outputs  |   | 26.4   | 57.5  | fs  |
| PCIe Gen 5 SRNS jitter  | SSC disabled on both outputs   |   | 19.8   | 39  | fs  |
| PCIe Gen 5 SRIS jitter, –0.3% ≤ SSC < 0%                                    | SSC enabled on both outputs  |   | 30.2   | 63.9  | fs  |
| PCIe Gen 6 Common Clock jitter, SSC is off (jitter limit = 100 fs)          | SSC disabled on both outputs   |   | 11   | 22  | fs  |
| PCIe Gen 6 Common Clock jitter, –0.5% ≤ SSC < 0% (jitter limit = 100 fs)    | SSC enabled on both outputs  |   | 16   | 34.5  | fs  |
| PCIe Gen 6 SRNS jitter  | SSC disabled on both outputs   |   | 14.8   | 27.9  | fs  |
| PCIe Gen 6 SRIS jitter, –0.3% ≤ SSC < 0%                                    | SSC enabled on both outputs  |   | 22.2   | 45.9  | fs  |
| PCIe Gen 7 Common Clock jitter, SSC is off (jitter limit = 67 fs)           | SSC disabled on both outputs   |   | 7.7  | 15.4  | fs  |
| PCIe Gen 7 Common Clock jitter, –0.5% ≤ SSC < 0% (jitter limit = 67 fs)     | SSC enabled on both outputs  |   | 12.1   | 29.6  | fs  |
| PCIe Gen 7 SRNS jitter  | SSC disabled on both outputs   |   | 10.4   | 19.6  | fs  |
| PCIe Gen 7 SRIS jitter, –0.1% ≤ SSC < 0%                                    | SSC enabled on both outputs  |   | 12.2   | 25.5  | fs  |
| 12 kHz to 20 MHz RMS jitter   | f <sub>out</sub> = 156.25MHz   |   | 105  | 144   | fs  |
| HARACTERISTICS  |  |   |  |   |   |
| Chart up time   | $V_{DD}$ = 2.5 V or 3.3 V. Time elapsed from all $V_{DD}$ pins reach 2.1 V until first output clock rising edge. Output clock is always within specification   |   |  | 1   | ms  |
| Start-up time   | $V_{DD}$ = 1.8 V. Time elapsed from all $V_{DD}$ pins reach 1.6 V until first output clock rising edge. Output clock is always within specification  |   |  | 1.5   | ms  |
| Output enable time.   | After CLOCK_READY status is '1', time elapsed between OE assertion and first output clock rising edge. Output is not tristated when disabled.  |   |  | 7   | output<br>clock<br>cycles   |
| Output disable time.  | Time elapsed between OE deassertion and last output clock falling edge.  |   |  | 7   | output<br>clock<br>cycles   |
|   | PCIe Gen 4 SRIS jitter, -0.3% ≤ SSC < 0%  PCIe Gen 5 Common Clock jitter, SSC is off (jitter limit = 150 fs)  PCIe Gen 5 Common Clock jitter, -0.5% ≤ SSC < 0% (jitter limit = 150 fs)  PCIe Gen 5 SRNS jitter  PCIe Gen 6 Common Clock jitter, SSC is off (jitter limit = 100 fs)  PCIe Gen 6 Common Clock jitter, -0.5% ≤ SSC < 0% (jitter limit = 100 fs)  PCIe Gen 6 SRNS jitter  PCIe Gen 6 SRNS jitter  PCIe Gen 6 SRIS jitter, -0.3% ≤ SSC < 0% (pitter limit = 100 fs)  PCIe Gen 7 Common Clock jitter, SSC is off (jitter limit = 67 fs)  PCIe Gen 7 SRNS jitter  PCIE Gen 8 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 9 SRNS jitter  PCIE Gen 9 SRNS jitter  PCIE Gen 10 SRNS jitter  PCIE Gen 10 SRNS jitter  PCIE Gen 11 SRNS jitter  PCIE Gen 12 SRNS jitter  PCIE Gen 13 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 14 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 15 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 16 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 17 SRNS jitter  PCIE Gen 17 SRNS jitter  PCIE Gen 17 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs)  PCIE Gen 17 SRIS jitter, -0.1% ≤ SSC < 0% (pitter limit = 67 fs) | PCIe Gen 4 SRIS jitter, -0.3% ≤ SSC < SSC enabled on both outputs  PCIe Gen 5 Common Clock jitter, SSC is off (jitter limit = 150 fs)  PCIe Gen 5 Common Clock jitter, -0.5% SSC enabled on both outputs  SSC -0% (jitter limit = 150 fs)  PCIe Gen 5 SRNS jitter  PCIe Gen 5 SRNS jitter, -0.3% ≤ SSC < SSC enabled on both outputs  SSC disabled on both outputs  PCIe Gen 6 SRNS jitter, -0.3% ≤ SSC < SSC enabled on both outputs  SSC disabled on both outputs  SSC enabled on both output | PCIe Gen 4 SRIS jitter, −0.3% ≤ SSC<br>0%<br>PCIe Gen 5 Common Clock jitter, SSC is off (jitter limit = 150 fs)<br>PCIe Gen 5 Common Clock jitter, −0.5%<br>≤ SSC < 0% (jitter limit = 150 fs)<br>PCIe Gen 5 SRNS jitter<br>PCIe Gen 5 SRNS jitter<br>PCIe Gen 5 SRNS jitter<br>PCIe Gen 6 Common Clock jitter, −0.3% ≤ SSC<br>0%<br>PCIe Gen 6 Common Clock jitter, SSC is off (jitter limit = 100 fs)<br>PCIe Gen 6 Common Clock jitter, −0.5%<br>≤ SSC disabled on both outputs<br>SSC disabled on both outputs<br>SSC enabled on both outputs<br>PCIe Gen 6 Common Clock jitter, −0.5%<br>≤ SSC < 0% (jitter limit = 100 fs)<br>PCIe Gen 6 SRNS jitter<br>PCIe Gen 6 SRNS jitter<br> | PCIe Gen 4 SRIS jitter, −0.3% ≤ SSC < SSC enabled on both outputs 98.5  PCIe Gen 5 Common Clock jitter, SSC is off (jitter limit = 150 fs)  PCIe Gen 5 Common Clock jitter, −0.5% SSC enabled on both outputs 26.4  SSC 0% (jitter limit = 150 fs)  PCIe Gen 5 SRNS jitter SSC disabled on both outputs 19.8  PCIe Gen 5 SRNS jitter SSC disabled on both outputs 19.8  PCIe Gen 5 SRIS jitter, −0.3% ≤ SSC < SSC enabled on both outputs 19.8  PCIe Gen 6 Common Clock jitter, SSC is off (jitter limit = 100 fs)  PCIe Gen 6 Common Clock jitter, −0.5% SSC enabled on both outputs 11.  PCIe Gen 6 Common Clock jitter, −0.5% SSC enabled on both outputs 11.  PCIE Gen 6 SRNS jitter SSC is off (jitter limit = 100 fs)  PCIE Gen 6 SRNS jitter SSC ≤ SSC enabled on both outputs 14.8  PCIE Gen 6 SRNS jitter, −0.3% ≤ SSC < SSC enabled on both outputs 14.8  PCIE Gen 6 SRNS jitter, −0.3% ≤ SSC < SSC enabled on both outputs 14.8  PCIE Gen 7 Common Clock jitter, −0.5% SSC enabled on both outputs 14.8  PCIE Gen 7 Common Clock jitter, −0.5% SSC disabled on both outputs 14.8  PCIE Gen 7 Common Clock jitter, −0.5% SSC disabled on both outputs 14.8  PCIE Gen 7 SRNS jitter SSC is off (jitter limit = 67 fs)  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 12.1  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 12.1  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outputs 10.4  PCIE Gen 7 SRNS jitter SSC disabled on both outpu | PCIe Gen 4 SRIS jitter, -0.3% ≤ SSC < SSC enabled on both outputs |

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

 $V_{DD} = V_{DDO} = 1.8 \text{ V}, 2.5 \text{ V or } 3.3 \text{ V} \pm 5\%, T_A = T_{A,min} \text{ to } T_{A,max}$ 

|                    | PARAMETER  | TEST CONDITIONS  | MIN | TYP MA          | X UNIT |
|--------------------|--|--|-----|-----------------|--------|
|                    |  | One FOD enabled, 100 MHz ≤ f <sub>FOD</sub> ≤ 200 MHz  | ţ   | 57.5 79         | .9 mA  |
|                    | Core supply current, not including output drivers              | One FOD enabled, 200 MHz < f <sub>FOD</sub> ≤ 400 MHz  |     | 67 90           | .7 mA  |
| I <sub>DD</sub>    |  | Two FODs enabled, 100 MHz ≤ f <sub>FOD</sub> ≤ 200 MHz | 8   | 31.1 105        | .8 mA  |
|                    |  | Two FODs enabled, 200 MHz < f <sub>FOD</sub> ≤ 400 MHz | 9   | 97.8 125        | .8 mA  |
|                    |  | LP-HCSL. f <sub>out</sub> ≤ 100 MHz                    | •   | 10.1 10.        | .8 mA  |
|                    |  | LP-HCSL. 100 MHz < f <sub>out</sub> ≤ 200 MHz          |     | 13.2 14         | .1 mA  |
|                    |  | LP-HCSL. 200 MHz < f <sub>out</sub> ≤ 300 MHz          |     | 13.7 15         | .1 mA  |
|                    |  | LP-HCSL. 300 MHz < f <sub>out</sub> ≤ 400 MHz          |     | 14.4 16         | .4 mA  |
|                    |  | LVDS. f <sub>out</sub> ≤ 100 MHz                       |     | 6               | 8 mA   |
|                    |  | LVDS. 100 MHz < f <sub>out</sub> ≤ 200 MHz             |     | 6.8 9           | .2 mA  |
|                    |  | LVDS. 200 MHz < f <sub>out</sub> ≤ 300 MHz             |     | 7.6 10          | .2 mA  |
| I <sub>DDO</sub>   | Output supply current, per output channel                      | LVDS. 300 MHz < f <sub>out</sub> ≤ 400 MHz             |     | 8.4 11          | .3 mA  |
|                    |  | 1.8 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 4.2             | 5 mA   |
|                    |  | 1.8 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 11.7 13         | .4 mA  |
|                    |  | 2.5 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 5.6 6           | .4 mA  |
|                    |  | 2.5 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 15.3 17.        | .3 mA  |
|                    |  | 3.3 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 6.8 7.          | .7 mA  |
|                    |  | 3.3 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 19.2 21         | .7 mA  |
|                    |  | 1.8 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 3.4 3.          | .9 mA  |
|                    |  | 1.8 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 9.5 11          | .7 mA  |
|                    |  | 2.5 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 4.7 5.          | .3 mA  |
| I <sub>DDREF</sub> | REFCLK supply current  | 2.5 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 12.8 15         | .8 mA  |
|                    |  | 3.3 V LVCMOS. f <sub>out</sub> = 50 MHz                |     | 5.9 6.          | .6 mA  |
|                    |  | 3.3 V LVCMOS. f <sub>out</sub> = 200 MHz               |     | 16.6 20         | .2 mA  |
| PSNR CH            | ARACTERISTICS  |  |     |                 |        |
|                    |  | 10 kHz   | -7  | 76.7 -58        | .1 dBc |
|                    |  | 50 kHz   | -8  | 30.9 -57        | .9 dBc |
|                    |  | 100 kHz  | -8  | 31.8 -5         | 7 dBc  |
|                    | Power Supply Noise Rejection for LVCMOS outputs <sup>(4)</sup> | 500 kHz  | -8  | 34.3 -61.       | .7 dBc |
| MOS                | LVCIMOS outputs(**)  | 1 MHz  | _(  | 97.6 -78.       | .1 dBc |
|                    |  | 5 MHz  | -10 | 04.3 -7         | 9 dBc  |
|                    |  | 10 MHz   | -10 | 08.7 -89        | .5 dBc |
|                    |  | 10 kHz   |     | 79.5 -70        |        |
|                    |  | 50 kHz   |     | 33.5 -73.       |        |
|                    |  | 100 kHz  |     | _83 <b>-</b> 71 |        |
|                    | Power Supply Noise Rejection for LVDS                          | 500 kHz  |     |                 | 9 dBc  |
| S                  | outputs <sup>(4)</sup>   | 1 MHz  |     | 23.4 -101.      |        |
|                    |  | 5 MHz  |     | -115 -87        |        |
|                    |  | 10 MHz   |     | 23.7 -103       |        |



 $V_{DD}$  =  $V_{DDO}$  = 1.8 V, 2.5 V or 3.3 V ± 5%,  $T_A$  =  $T_{A,min}$  to  $T_{A,max}$ 

|  | PARAMETER   | TEST CONDITIONS | MIN                       | TYP    | MAX                      | UNIT |
|--|---|-----------------|---------------------------|--------|--------------------------|------|
|  |   | 10 kHz          |                           | -80.1  | -70.8                    | dBc  |
|  |   | 50 kHz          |                           | -84.7  | -72.9                    | dBc  |
|  |   | 100 kHz         |                           | -84.6  | -70.1                    | dBc  |
| PSNR <sub>LP</sub>                         | Power Supply Noise Rejection for LP-HCSL outputs <sup>(4)</sup>   | 500 kHz         |                           | -93.1  | -78.8                    | dBc  |
| HUSL                                       | Tiooz da.pato   | 1 MHz           |                           | -124.6 | -101.5                   | dBc  |
|  |   | 5 MHz           |                           | -114.3 | -88.3                    | dBc  |
|  |   | 10 MHz          |                           | -123   | -103.7                   | dBc  |
| 2-STATE                                    | LOGIC INPUT CHARACTERISTICS                                       | ·               |                           |        |                          |      |
| V <sub>IH-Pin2</sub>                       | Input high voltage for Pin 2                                      |                 | 0.7<br>× V <sub>DD</sub>  |        | V <sub>DD</sub> + 0.3    | V    |
| V <sub>IL-Pin2</sub>                       | Input low voltage for Pin 2                                       |                 | GND -<br>0.3              |        | 0.3<br>× V <sub>DD</sub> | V    |
| V <sub>IH-Pin1</sub>                       | Input high voltage for Pin 1                                      |                 | 1.15                      |        | V <sub>DD</sub> + 0.3    | V    |
| V <sub>IL-Pin1</sub>                       | Input low voltage for Pin 1                                       |                 | -0.3                      |        | 0.65                     | V    |
| V <sub>IH-Pin3,4</sub>                     | Input voltage high for OTP_SEL[1:0]                               |                 | 0.7 ×<br>V <sub>DD</sub>  |        | V <sub>DD</sub> + 0.3    | V    |
| V <sub>IL-Pin3,4</sub>                     | Input voltage low for OTP_SEL[1:0]                                |                 | GND -<br>0.3              |        | 0.8                      | V    |
| V <sub>IH-Pin15</sub>                      | Input voltage high for Pin 15                                     |                 | 0.65 ×<br>V <sub>DD</sub> |        | V <sub>DD</sub> + 0.3    | V    |
| V <sub>IL-Pin15</sub>                      | Input voltage low for Pin 15                                      |                 | -0.3                      |        | 0.4                      | V    |
| R <sub>ext-up/</sub><br>down-Pin1,2        | Recommended external pullup or pulldown resistor for Pin 1, 2     |                 | 0                         | 1      | 10                       | kΩ   |
| R <sub>ext-up/</sub><br>down-<br>Pin3,4,15 | Recommended external pullup or pulldown resistor for Pin 3, 4, 15 |                 | 0                         | 10     | 60                       | kΩ   |
| t <sub>R</sub> /t <sub>F</sub>             | OE signal rise or fall time                                       |                 |                           |        | 10                       | ns   |
| C <sub>in</sub>                            | Input capacitance   |                 |                           |        | 3                        | pF   |

- PCIe test load, 15 dB loss at 4 GHz,  $f_{out}$  = 100 MHz,  $Z_{diff}$  = 100  $\Omega$  Tested with 10 k $\Omega$  external pullup or pulldown resistor
- (2)
- REFCLK can be /2, /4, /8 from either FOD0 or FOD1. Both FODs support 100 to 400 MHz. (3)
- All power supply pins are tied together. 0.1 µF capacitor placed close to each power supply pin. Apply 50 mVpp ripple and measure the spur level at the clock output

## **5.6 I2C Interface Specification**

All timing requirements referred to  $V_{IH-min}$  and  $V_{IL-max}$ . Chip  $V_{DD}$  =  $I^2C$   $V_{DD}$ .

|                  | PARAMETER                           | R TEST CONDITIONS                           |                          | STANDARD<br>MODE         |                           | FAST MODE                |   |
|------------------|-------------------------------------|---|--------------------------|--------------------------|---------------------------|--------------------------|---|
|                  |                                     |   | MIN                      | MAX                      | MIN                       | MAX                      |   |
| V <sub>IL</sub>  | Input low voltage                   |   | -0.3                     | 0.3 ×<br>V <sub>DD</sub> | -0.3                      | 0.3 ×<br>V <sub>DD</sub> | V |
| V <sub>IH</sub>  | Input high voltage                  |   | 0.7 ×<br>V <sub>DD</sub> | V <sub>DD</sub> + 0.3    | 0.7<br>× V <sub>DD</sub>  | V <sub>DD</sub> + 0.3    | V |
| V <sub>hys</sub> | Hysteresis of Schmitt trigger input |   |                          |                          | 0.05 ×<br>V <sub>DD</sub> |                          | V |
| V <sub>OL1</sub> | Low level output voltage 1          | At 3 mA sink current. V <sub>DD</sub> > 2 V | 0                        | 0.4                      | 0                         | 0.4                      | V |
| V <sub>OL2</sub> | Low level output voltage 2          | At 2 mA sink current. V <sub>DD</sub> ≤ 2 V |                          |                          | 0                         | 0.2 x<br>V <sub>DD</sub> | V |

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

All timing requirements referred to  $V_{IH-min}$  and  $V_{IL-max}$ . Chip  $V_{DD}$  =  $I^2C$   $V_{DD}$ .

| PARAMETER           |   | TEST CONDITIONS                                       | STANDARD<br>MODE         |      | FAST MODE                            |     | UNIT |
|---------------------|---|---|--------------------------|------|--------------------------------------|-----|------|
|                     |   |   | MIN                      | MAX  | MIN                                  | MAX |      |
|                     | Low lovel output ourrent  | V <sub>OL</sub> = 0.4 V                               | 3                        |      | 3                                    |     | mA   |
| I <sub>OL</sub>     | Low level output current  | V <sub>OL</sub> = 0.6 V                               |                          |      | 6                                    |     | mA   |
| t <sub>OF</sub>     | Output fall time from VIHmin to VILmax                            |   |                          | 250  | 20 ×<br>(V <sub>DD</sub> /<br>5.5 V) | 250 | ns   |
| t <sub>SP</sub>     | Pulse width of spikes that must be suppressed by the input filter |   |                          |      | 0                                    | 50  | ns   |
| li                  | Input current each I/O pin  | $0.1 \times V_{DD} < V_{IN} < 0.9 \times V_{DDmax}$   | -10                      | 10   | -10                                  | 10  | μA   |
| Ci                  | Capacitance for each I/O pin                                      |   |                          | 10   |                                      | 10  | pF   |
| f <sub>SCL</sub>    | SCL clock frequency   |   | 0                        | 100  | 0                                    | 400 | kHz  |
| t <sub>HD-STA</sub> | Hold time (repeated) START condition                              | After this period, the first clock pulse is generated | 4                        |      | 0.6                                  |     | μs   |
| tlow                | Low period of the SCL clock                                       |   | 4.7                      |      | 1.3                                  |     | μs   |
| thigh               | High period of the SCL clock                                      |   | 4                        |      | 0.6                                  |     | μs   |
| t <sub>SU-STA</sub> | Set-up time for a repeated START condition                        |   | 4.7                      |      | 0.6                                  |     | μs   |
| t <sub>HD-DAT</sub> | Data hold time  | I <sup>2</sup> C bus devices                          | 0                        |      | 0                                    |     | μs   |
| t <sub>SU-DAT</sub> | Data set-up time  |   | 0.25                     |      | 0.1                                  |     | μs   |
| t <sub>R</sub>      | Rise time of both SDA and SCL signals <sup>(1)</sup>              |   |                          | 300  | 20                                   | 300 | ns   |
| t <sub>F</sub>      | Fall time of both SDA and SCL signals <sup>(1)</sup>              |   |                          | 300  | 20 ×<br>(V <sub>DD</sub> /<br>5.5 V) | 300 | ns   |
| t <sub>SU-STO</sub> | Set-up time for STOP condition                                    |   | 4                        |      | 0.6                                  |     | μs   |
| t <sub>BUF</sub>    | Bus free time between a STOP and START condition                  |   | 4.7                      |      | 1.3                                  |     | μs   |
| C <sub>B</sub>      | Capacitive load for each bus line                                 |   |                          | 400  |                                      | 400 | pF   |
| t <sub>VD-DAT</sub> | Data valid time   |   |                          | 3.45 |                                      | 0.9 | μs   |
| t <sub>VD-ACK</sub> | Data valid acknowledge time                                       |   |                          | 3.45 |                                      | 0.9 | μs   |
| V <sub>NL</sub>     | Noise margin at the low level                                     | For each connected device, including hysteresis       | 0.1 x<br>V <sub>DD</sub> |      | 0.1 ×<br>V <sub>DD</sub>             |     | V    |
| V <sub>NH</sub>     | Noise margin at the high level                                    | For each connected device, including hysteresis       | 0.2 x<br>V <sub>DD</sub> |      | 0.2 ×<br>V <sub>DD</sub>             |     | V    |



### **6 Parameter Measurement Information**

## **6.1 Output Format Configurations**

This section describes the characterization test setup of each output format option in the LMK3H0102.




Figure 6-1. LVCMOS Output Configuration During Device Test




Figure 6-2. AC-LVDS Output Configuration During Device Test




Figure 6-3. DC-LVDS Output Configuration During Device Test




Figure 6-4. LP-HCSL Output Configuration During Non-PCle Device Test




Figure 6-5. LP-HCSL Output Configuration During PCIe Device Test

Product Folder Links: LMK3H0102

Figure 6-6. PCle Test Configuration Using Phase Noise Analyzer

## 6.2 Differential Voltage Measurement Terminology

The differential voltage of a differential signal can be described by two different definitions, causing confusion when reading data sheets or communicating with other engineers. This section addresses the measurement and description of a differential signal so that the reader is able to understand and distinguish between the two different definitions when used.

The first definition used to describe a differential signal is the absolute value of the voltage potential between the inverting and noninverting signal. The symbol for this first measurement is typically  $V_{ID}$  or  $V_{OD}$  depending on if an input or output voltage is being described.

The second definition used to describe a differential signal is to measure the potential of the noninverting signal with respect to the inverting signal. The symbol for this second measurement is  $V_{SS}$  and is a calculated parameter. Nowhere in the IC does this signal exist with respect to ground, the signal only exists in reference to the differential pair.  $V_{SS}$  can be measured directly by oscilloscopes with floating references, otherwise this value can be calculated as twice the value of  $V_{OD}$  as described in the first description.

Figure 6-7 shows the two different definitions side-by-side for inputs and Figure 6-8 shows the two different definitions side-by-side for outputs. The  $V_{ID}$  and  $V_{OD}$  definitions show  $V_A$  and  $V_B$  DC levels that the noninverting and inverting signals toggle between with respect to ground.  $V_{SS}$  input and output definitions show that if the inverting signal is considered the voltage potential reference, the noninverting signal voltage potential is now increasing and decreasing above and below the noninverting reference. Thus the peak-to-peak voltage of the differential signal can be measured.

 $V_{ID}$  and  $V_{OD}$  are often defined as volts (V) and  $V_{SS}$  is often defined as volts peak-to-peak ( $V_{PP}$ ).




Figure 6-7. Two Different Definitions for Differential Input Signals




Figure 6-8. Two Different Definitions for Differential Output Signals

Copyright © 2025 Texas Instruments Incorporated

## 7 Detailed Description

#### 7.1 Overview

The LMK3H0102 is a dual-channel clock generator primarily used for PCle Gen 1 to Gen 7 clock generation, either with or without Spread Spectrum Clocking (SSC). The device has an integrated Bulk Acoustic Wave (BAW) resonator and does not require any external crystal or clock reference. The device has four selectable pages of memory, referred to as OTP pages. The collection of these pages in memory is referred to as the EFUSE.

The default output configuration is two 100MHz clocks, each with a  $100\Omega$  LP-HCSL output format, both disabled at startup. The LMK3H0102 supports  $100\Omega$  LP-HCSL,  $85\Omega$  LP-HCSL, LVDS and 1.8V, 2.5V, or 3.3V LVCMOS output formats, as well as programmable output frequencies up to 200MHz for single-ended outputs and 400MHz for differential outputs. The LMK3H0102V33 is the part number for the default configuration with a 3.3V supply voltage. The LMK3H0102V18 is the part number for the default configuration with a 1.8V supply voltage. Additional configuration part numbers are LMK3H0102 Axxx, where xxx denotes the configuration number. LMK3H0102 Configuration Guide details the critical device settings and default register settings for each LMK3H0102Axxx OTP configuration.

The LMK3H0102 supports two functional modes determined by the REF\_CTRL pin at power-up: One-Time Programming (OTP) mode or I<sup>2</sup>C mode.

- In OTP mode, one out of four OTP pages is selected by pins OTP\_SEL0 and OTP\_SEL1. The default output frequency across all OTP pages is 100MHz.
- 2. In I<sup>2</sup>C mode, the LMK3H0102 is configured by modifying the active registers. If a configuration other than the default operation is desired, the registers must be written every time at start-up.

Refer to *Pin Configuration and Functions* for the detailed descriptions of the device pins.

The LMK3H0102 has flexible SSC configurations, including:

- 1. SSC disabled on both outputs
- 2. SSC enabled on both outputs
- 3. SSC enabled on a single output

The SSC specifications and jitter performance are fully compliant to PCIe Gen 1 to Gen 7. Refer to *Spread-Spectrum Clocking* for SSC and jitter performance details.

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

#### 7.2 Functional Block Diagram




Figure 7-1. LMK3H0102 Functional Block Diagram

#### 7.3 Feature Description

### 7.3.1 Device Block-Level Description

The LMK3H0102 is a reference-less clock generator with an integrated BAW oscillator. The BAW frequency, nominally 2467MHz, is divided down by two fractional output dividers (FODs), each of which is capable of generating frequencies between 100MHz and 400MHz. Each FOD can be routed to one of two channel dividers, which divides the FOD frequency down to generate frequencies from 2.5MHz to 200MHz. For generating frequencies above 200MHz, the edge combiner, which utilizes both FODs, must be used. In this case, the channel divider is bypassed, resulting in generated frequencies from 200MHz to 400MHz. An additional LVCMOS clock, with a voltage corresponding with VDD, can be optionally generated on the REF CTRL pin.

#### 7.3.2 Device Configuration Control

Figure 7-2 shows the relationships between device states, the configuration pins, device initialization, and device operational modes. OTP mode is entered when the REF\_CTRL pin is pulled high at start-up. I<sup>2</sup>C mode is entered when the REF\_CTRL pin is pulled low at start-up. In OTP mode, the state of the OTP\_SEL0/SCL and OTP\_SEL1/SDA pins determines the OTP page that is loaded into the active registers. The device is one-time programmable, meaning that the register settings stored into the internal EFUSE can not be changed. The device can be transitioned from OTP to I<sup>2</sup>C mode, or reciprocally, by changing the state of the REF\_CTRL pin, then triggering a device power cycle by pulling VDD low, then high again. In OTP mode, a change in the level of the OTP\_SEL0 or OTP\_SEL1 pins, while keeping the REF\_CTRL pin high, dynamically changes the active OTP



page. The device waits for 350 μs for the OTP\_SEL0 and OTP\_SEL1 pins to settle before loading the new OTP page.

In I<sup>2</sup>C mode, the state of the FMT\_ADDR pin can determine the I<sup>2</sup>C address of the device, with the OTP\_SEL0/SCL and OTP\_SEL1/SDA pins re-purposed as I<sup>2</sup>C clock and data pins, respectively. In I<sup>2</sup>C mode, the host can update the active device registers. If using a configuration different than the programmed configuration, the registers must be written after each power cycle.

The device can be placed into a low power state by setting the PDN bit (R10[1]) to '1'. Clearing the PDN bit takes the device out of the low power state. If DEV\_IDLE\_STATE\_SEL bit (R10[4]) is a '0' and the outputs are disabled, the device enters the low power state. Entering the low power state is required for changing the frequency of the FOD used by Channel 0, changing the SSC configuration, and changing the output format. TI recommends performing register writes within this low power state. Set the OTP\_AUTOLOAD\_DIS (R10[2]) bit to a '1' to prevent automatic loading of OTP Page 0 prior to setting PDN to '0'.

There are two fields that determine the state of the device when coming out of the low power state. PIN\_RESAMPLE\_DIS (R10[3]) controls whether or not the FMT\_ADDR, OTP\_SEL0/SCL, OTP\_SEL1/SDA, and REF\_CTRL pins are resampled when exiting the low power state. If the pins are resampled, the device can be transitioned into OTP mode if the REF\_CTRL pin is pulled high. Set this bit to a '1' to disable this functionality. OTP\_AUTOLOAD\_DIS controls whether or not the contents of OTP Page 0 are loaded into the device registers when exiting the low power state. If OTP\_AUTOLOAD\_DIS bit is a '1' and PIN\_RESAMPLE\_DIS is a '1', then the register contents do not change. If OTP\_AUTOLOAD\_DIS bit is a '0' and PIN\_RESAMPLE\_DIS is a '1', then the contents of OTP Page 0 are loaded to the registers. If PIN\_RESAMPLE\_DIS is a '0' and REF\_CTRL is pulled high, then the device enters OTP Mode. In this case, OTP\_SEL0/SCL and OTP\_SEL1/SDA control the OTP page loaded into the device registers.

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated




Figure 7-2. LMK3H0102 Device Mode Diagram

In I<sup>2</sup>C Mode, the device registers are from the contents of OTP Page 0. In OTP mode, these values come from one of the four OTP pages, selectable based on the state of the OTP\_SELx pins on start-up. Figure 7-3 shows interface and control blocks within the LMK3H0102, with the arrows referring to read and write access from the different embedded memories.






Figure 7-3. LMK3H0102 Interface and Control Blocks

### **7.3.3 OTP Mode**

In this mode, the configuration pins allow for selection of one of four one-time programmable (OTP) pages, as well as output format selection.  $I^2C$  is not enabled in this mode, as the  $I^2C$  pins are repurposed for OTP page selection. Table 7-1 shows the OTP page selected based on the state of the OTP\_SEL0 and OTP\_SEL1 pins.

Table 7-1. OTP Page Selection in OTP Mode

| OTP_SEL1 Pin | OTP_SEL0 Pin | OTP Page |
|--------------|--------------|----------|
| Low          | Low          | 0        |
| Low          | High         | 1        |
| High         | Low          | 2        |
| High         | High         | 3        |

The EFUSE of the devices is permanently programmed and has  $OTP_BURNT(R0[0]) = 1$ . If a new configuration is desired, the configuration must be loaded through  $I^2C$  on each start-up. OTP configurations can be created using the Wizard in TICS Pro. Contact TI for creation of a custom OTP configuration orderable part number.

The following fields can be unique between the four OTP pages. All other register settings are shared between the OTP pages:

- · SSC EN: Enable or disable SSC.
- OE 0: Enable or disable OUT0.
- · OE 1: Enable or disable OUT1.
- OP TYPE CH0: OUT0 output format type, see Output Format Types.
- OP TYPE CH1: OUT1 output format type, see Output Format Types.
- SSC SETTING: SSC modulation type, see Spread Spectrum Clocking.

When OTP\_SEL1 or OTP\_SEL0 pin state changes, the device automatically goes through a power cycle and reloads the new OTP page. The time elapsed from when pins 3 and 4 change to a stable state in the new OTP is no more than 1.5ms.

#### 7.3.4 I<sup>2</sup>C Mode

In this mode, I<sup>2</sup>C is enabled and the SCA and SDL pins function as the I<sup>2</sup>C clock and I<sup>2</sup>C data pins, respectively. Table 7-2 shows the four default I<sup>2</sup>C addresses selectable by the FMT\_ADDR pin. The 5 MSBs of the I<sup>2</sup>C address are set in the upper five bits of I<sup>2</sup>C ADDR (R12[14:8]).

If I2C\_ADDR\_LSB\_SEL (R12[15]) = 0, then the FMT\_ADDR pin is ignored, and the I $^2$ C address is solely determined by I2C\_ADDR. If using the FMT\_ADDR pin for I $^2$ C LSB selection, then the pin must not be configured for individual output enable control.

| Table 1-2:1 0 Address delection |              |                              |  |  |  |
|---------------------------------|--------------|------------------------------|--|--|--|
| REF_CTRL PIN (1)                | FMT_ADDR PIN | I <sup>2</sup> C ADDRESS (2) |  |  |  |
| High                            | X            | N/A                          |  |  |  |
|                                 |              | (I2C disabled)               |  |  |  |
| Low                             | 0            | 0x68 / 0xD0                  |  |  |  |
| Low                             | 1            | 0x69 / 0xD2                  |  |  |  |
| Low                             | Tied to SDA  | 0x6A / 0xD4                  |  |  |  |
| Low                             | Tied to SCL  | 0x6B / 0xD8                  |  |  |  |

Table 7-2. I<sup>2</sup>C Address Selection

- (1) This is the state of the REF\_CTRL pin at power-up, not the live pin state.
- (2) The 0xD0, 0xD2, 0xD4, and 0xD8 addresses are with the R/W bit included set to '0'.

When changing the registers of the device, first set PDN to '1', write to the device registers, then set PDN to '0'.Figure 7-4 shows this process.






Figure 7-4. LMK3H0102 Programming Sequence

#### 7.4 Device Functional Modes

#### 7.4.1 Fail-Safe Inputs

The LMK3H0102 digital input pins are designed to support fail-safe input operation, with the exception of the REF\_CTRL pin. This feature allows the user to drive the digital inputs before VDD is applied without damaging the device. Refer to Section 5.1 for more information on the maximum input voltages supported by the device.

#### 7.4.2 Fractional Output Dividers

The LMK3H0102 contains two fractional output dividers. If all outputs are able to be generated by a single FOD, TI recommends disabling FOD1 to conserve power and improve performance. If no output channels select FOD1, then FOD1 is disabled.

## 7.4.2.1 FOD Operation

The internal BAW resonator is divided down by one or two Fractional Output Dividers (FODs). FOD0 has an SSC generator and FOD1 does not have an SSC generator. If both OUT0 and OUT1 must be SSC clocks, the two clocks must be sourced by FOD0. If one SSC clock and one non-SSC clock are required at the same time, then FOD0 is enabled for the SSC clock and FOD1 is enabled for the non-SSC clock. If neither output clock requires SSC, then either FOD can be used.

#### Note

TI recommends that FOD0 be used as the default FOD if only one FOD is needed for an application. If both FODs are in use, TI recommends using FOD0 with OUT0 and FOD1 with OUT1.

The maximum frequency that can be generated at the clock outputs by a single FOD is 200 MHz, as the minimum channel divider value is a divide by two. To generate a greater than 200 MHz output, the edge combiner is used, bypassing the channel dividers. This requires that both FODs are enabled and have the same integer divider and fractional numerator values, and the same gain calibration values. When one of the outputs exceeds 200 MHz, the other output can only select the shared FOD frequency divided by one of the channel divider values, or be the FOD frequency. Below 200 MHz, the two FODs can be configured independently so that OUT0 and OUT1 can have different frequencies. TI recommends sourcing from a single FOD whenever possible to make sure that OUT0 and OUT1 have a deterministic phase relationship.

The FODs in the LMK3H0102 can be configured to accommodate various output frequencies through I2C programming, or in the absence of programming, the one-time programmed (OTP) settings. The FODs can be configured by setting the integer (FODx\_N\_DIV) and fractional (FODx\_NUM) divide values. Table 7-3 shows the register locations for these fields for each FOD.

Table 7-3. FOD Integer and Numerator Divide Locations

| Field           | Register |
|-----------------|----------|
| FOD0_N_DIV      | R0[9:3]  |
| FOD0_NUM[23:16] | R1[15:8] |
| FOD0_NUM[15:0]  | R2[15:0] |
| FOD1_N_DIV      | R3[15:9] |
| FOD1_NUM[23:16] | R6[12:5] |
| FOD1_NUM[15:0]  | R8[15:0] |

An example of how to set the integer and numerator divide values is shown in Equation 1 and Equation 2.

$$FODx_N_DIV = floor(F_{BAW}/F_{FOD})$$
 (1)

#### where:

- FODx\_N\_DIV: Integer portion of the FOD divide value (7 bits, 6 to 24)
- F<sub>BAW</sub>: BAW frequency, 2467 MHz plus offset, described in further detail below
- F<sub>FOD</sub>: Desired FOD frequency (100 MHz to 400 MHz)

$$FODx_NUM = int(((F_{BAW}/F_{FOD}) - FODx_N_DIV) \times 2^{24})$$
(2)

where FODx NUM is the fractional portion of the FOD divide value (24 bits, that is 0 to 16777215).

The output frequency ( $F_{OUT}$ ) is related to the FOD frequency as given in Equation 3, or is equal to the FOD frequency when the edge combiner is enabled. OUTDIV can be 2, 4, 6, 8, 10, 20, or 40.

$$F_{OUT} = F_{FOD}/OUTDIV$$
 (3)

Use Equation 4 to calculate the actual value of the BAW frequency for a device. Users can find the value of BAWFREQ\_OFFSET\_FIXEDLUT by reading R238, which is a signed 16-bit value.

$$F_{BAW} = 2467 \text{ MHz} \times (1 + (BAWFREQ OFFSET FIXEDLUT \times 128E-9))$$
 (4)

## 7.4.2.2 Edge Combiner

Use the edge combiner to generate output frequencies greater than 200 MHz. To use the Edge Combiner, set CH0\_EDGE\_COMB\_EN (R3[3]) or CH1\_EDGE\_COMB\_EN (R3[7]) to '1'. When using the edge combiner, both FODs must operate at the same exact frequency (that is, the divide values must match). The device handles this by automatically loading the divider values from FOD0 into FOD1 when either CHx\_EDGE\_COMB\_EN bit is set to a '1'. SSC on FOD0 is not supported when using the edge combiner, and must not be enabled. Either of the FODs can still generate the LVCMOS REF\_CLK output.

For proper edge combiner operation, the following conditions must be true:

- The gain calibration codes for both FODs must be averaged. For example, if DTC1\_GAIN\_RT = 200, and DTC2\_GAIN\_RT = 220, then both of these fields must be written to 210. The gain calibration codes are in the protected register space. Unlock the protected registers using R12[7:0] = 0x5B, write only the averaged gain calibration codes, and then lock the protected registers by setting R12[7:0] = 0x00. See R146, R147, and R148 for more information.
- If the edge combiner is used for OUT1 **only**, CH0\_FOD\_SEL (R3[4]) must **always** be set to '0' (FOD0), regardless of the disable state of OUT0.

Copyright © 2025 Texas Instruments Incorporated

#### 7.4.2.3 Digital State Machine

The digital state machine of the LMK3H0102 has a clock that originates from one of the FODs. The FOD selected by CH0\_FOD\_SEL (R3[4]) drives the input to the state machine clock divider. The total divide value is the DIG\_CLK\_N\_DIV (R0[9:3]) field plus two. Set DIG\_CLK\_N\_DIV such that the FOD frequency divided by the total state machine clock divide value is between 40MHz and 50MHz. The divider value used to set this clock is equal to the value stored in . As an example, if the frequency of FOD0 is 200MHz, and CH0\_FOD\_SEL is a '0', then DIG\_CLK\_N\_DIV must be set to '2', as 200MHz divided by 4 is 50MHz.

#### 7.4.2.4 Spread-Spectrum Clocking

FOD0 supports spread-spectrum clocking (SSC). SSC can be used to reduce peak radiated emissions by modulating the output frequency. When SSC\_EN (R4[0]) = '1', any outputs that are sourced from FOD0 have SSC. SSC\_MOD\_TYPE (R4[1]) selects between down-spread modulation (SSC\_MOD\_TYPE = 0) or center-spread modulation (SSC\_MOD\_TYPE = 1). The LMK3H0102 has four built-in down-spread SSC options, as well as a custom SSC option. SSC\_CONFIG\_SEL (R9[11:9]) selects between the custom or preconfigured options. The preconfigured options are optimized for a 200MHz output from FOD0. Table 7-4 details the register settings for the preconfigured SSC options. The preconfigured SSC options are optimized for 200MHz outputs from FOD0. If the edge combiner is used, then spread-spectrum clocking must be disabled.

Table 7-4. Predefined SSC Configurations

| SSC_CONFIG_SEL   | Down-spread SSC Depth                        |
|------------------|--|
| 0x0              | Custom, based on SSC_STEPS and SSC_STEP_SIZE |
| 0x1              | -0.10%                                       |
| 0x2              | -0.25%                                       |
| 0x3              | -0.30%                                       |
| 0x4              | -0.50%                                       |
| All other values | Reserved                                     |

If Custom SSC is selected, then SSC\_STEPS (R4[14:2]) and SSC\_STEP\_SIZE (R5) must be configured to set the modulation depth. Use Equation 5 and Equation 6 to determine the SSC\_STEPS (R4[14:2]) register settings, and use Equation 7 or Equation 8 to determine the SSC\_STEP\_SIZE (R5) settings. Equation 7 is for down-spread SSC and Equation 8 is for center-spread SSC.

Down-spread: SSC\_STEPS = 
$$int((F_{FOD0}/F_{MOD})/2)$$
 (5)

Center-spread: 
$$SSC\_STEPS = int((F_{FODO}/F_{MOD})/4)$$
 (6)

#### where:

- F<sub>FOD0</sub>: FOD0 Frequency
- F<sub>MOD</sub>: Modulation frequency, use 31.5kHz for PCIe applications

$$SSC\_STEP\_SIZE = floor((F\_BAW/F\_FOD0*(1/(1 - SSC\_DEPTH) - 1))/(SSC\_STEPS)*DEN)$$
(7)

$$SSC\_STEP\_SIZE = floor((F\_BAW/F\_FOD0*(1/(1-SSC\_DEPTH)-1/(1+SSC\_DEPTH))))/(2*SSC\_STEPS)*DEN) \tag{8}$$

#### where:

- SSC\_STEP\_SIZE: Numerator increment value per step for SSC
- F<sub>BAW</sub>: BAW frequency, 2467MHz. Note that the F<sub>BAW</sub> value varies from device to device.
- SSC DEPTH: Modulation depth, expressed as a positive value. If -0.5% depth is used, this value is 0.005
- SSC STEPS: Result from Equation 5 for down-spread or Equation 6 for center-spread
- DEN: Fractional denominator, 2<sup>24</sup>

If using a mix of SSC on one output and no SSC on a different output, there can be crosstalk between the two outputs. Contact TI to request measurement data for a specific configuration when configuring SSC on only a single output.

When modifying the SSC settings, do not set SSC\_EN to a '1' until the other SSC settings have been configured. Perform the following steps for configuring the SSC:

- 1. Set PDN to a '1'.
- 2. Set OTP AUTOLOAD DIS to a '1'.
- 3. Modify SSC\_MOD\_TYPE, SSC\_STEP\_SIZE, and SSC\_STEPS as necessary.
- 4. Set SSC EN to a '1'.
- 5. Set PDN to a '0'.

### 7.4.2.5 Integer Boundary Spurs

When the decimal portion of the FOD divide value is near an integer boundary, integer boundary spurs can occur. In general, this "integer boundary" is when the decimal portion is between 0.9 and 1, or 0 and 0.1. For example, if the BAW frequency is 2467 MHz, and an output of 122.88 MHz, then the FOD must run at 245.76 MHz. 2467 MHz divided by 245.76 MHz is approximately 10.038. The decimal portion of the divide value is 0.038, which falls between 0 and 0.1, and thus means that generating a 122.88 MHz output can result in spurs in the 12 kHz to 20 MHz band on the output clock. In some cases, proper frequency planning can account for this by increasing the FOD frequency and the channel divider value. For any concerns about integer boundary spurs for a specific frequency plan, contact TI.

#### 7.4.3 Output Behavior

#### 7.4.3.1 Output Format Selection

This device supports LP-HCSL (both  $85\Omega$  and  $100\Omega$  internal termination), LVDS, and LVCMOS. For LVCMOS outputs, VDDO can be 1.8V, 2.5V or 3.3V if the VDD is 3.3V. Otherwise, the VDDO must be the same voltage as VDD. When OUT0 and OUT1 use different formats, DC-LVDS and differential LVCMOS are 180 degrees out of phase from all other formats.

**Table 7-5. Output Format Using Registers** 

| OUT0_FMT /<br>OUT1_FMT | Description  |
|------------------------|--|
| 0x0                    | LP-HCSL 100Ω Termination   |
| 0x1                    | LP-HCSL 85Ω Termination  |
| 0x2                    | AC-coupled LVDS  |
| 0x3                    | DC-coupled LVDS  |
| 0x4                    | LVCMOS enabled on OUTx_P<br>LVCMOS disabled on OUTx_N                            |
| 0x5                    | LVCMOS disabled on OUTx_P LVCMOS enabled on OUTx_N                               |
| 0x6                    | LVCMOS enabled on OUTx_P<br>LVCMOS enabled on OUTx_N<br>180 degrees out of phase |
| 0x7                    | LVCMOS enabled on OUTx_P LVCMOS enabled on OUTx_N OUTx_P and OUTx_N in phase     |

For best output performance, TI recommends using 180 degree out of phase LVCMOS if both OUTx\_P and OUTx\_N traces are required.

Copyright © 2025 Texas Instruments Incorporated



In OTP mode, the FMT\_ADDR pin function can be determined by OUT\_FMT\_SRC\_SEL (R9[8]). Table 7-6 describes the output format settings available using the OUT\_FMT\_SRC\_SEL field. If using the FMT\_ADDR pin for output format selection, the pin must not be configured for individual output enable.

Table 7-6. FMT\_ADDR Output Format Options

| OUT_FMT_SR<br>C_SEL | FMT_ADDR<br>Pin | Output Format                                     |
|---------------------|-----------------|---|
| 0                   | Х               | Set by OUT0_FMT (R6[2:0] )/<br>OUT1_FMT (R7[4:2]) |
| 1                   | GND             | LP-HCSL 100Ω Termination                          |
| 1                   | VDD             | LP-HCSL 85Ω Termination                           |

#### 7.4.3.1.1 Output Format Types

Figure 7-5 through Figure 7-8 display how to connect the LMK3H0102 outputs based on the output format selected.




Figure 7-5. Interfacing LMK3H0102 LVCMOS Output With an LVCMOS Receiver




Figure 7-6. Interfacing LMK3H0102 LVCMOS Output With an AC-LVDS Receiver




Figure 7-7. Interfacing LMK3H0102 LVCMOS Output With a DC-LVDS Receiver




Figure 7-8. Interfacing LMK3H0102 LVCMOS Output With an LP-HCSL Receiver

#### 7.4.3.1.1.1 LP-HCSL Termination

For LP-HCSL outputs, the LMK3H0102 uses internal  $50-\Omega$  termination resistors for the termination to GND. External termination resistors are not required.

#### 7.4.3.2 Output Slew Rate Control

For all LVDS and LP-HCSL outputs, the slew rate can be configured. OUT0\_SLEW\_RATE (R6[4:3]) and OUT1\_SLEW\_RATE (R7[6:5]) can be used to slow down output slew rate to reduce EMI for OUT0 and OUT1, respectively. Table 7-7 shows the slew rate options available.

Table 7-7. Slew Rate Settings

| OUT0_SLEW_RATE OUT1_SLEW_RATE | Slew Rate                |
|-------------------------------|--------------------------|
| 0x0                           | Between 2.3 and 3.5 V/ns |
| 0x1                           | Between 2.0 and 3.2 V/ns |
| 0x2                           | Between 1.7 and 2.8 V/ns |
| 0x3                           | Between 1.4 and 2.7 V/ns |

#### 7.4.3.3 REF\_CTRL Operation

At start-up, the REF\_CTRL pin selects I<sup>2</sup>C mode when low, and OTP mode when high. After start-up, REF\_CTRL can be programmed to output an LVCMOS REF\_CLK, which is derived from either FOD0 or FOD1 followed by an integer divider (/2, /4, /8). Alternatively, this pin can be disabled, or function as a "clock ready" signal. REF\_CTRL\_PIN\_FUNC (R7[14:13]) controls the function of the REF\_CTRL pin. Table 7-8 shows these options.

Table 7-8. REF\_CTRL Function After Startup

|                   | · · · · · · · · · · · · · · · · · · · |
|-------------------|---------------------------------------|
| REF_CTRL_PIN_FUNC | REF_CTRL Function                     |
| 0x0               | Disabled, forced low                  |
| 0x1               | Disabled, tri-state                   |
| 0x2               | REF_CLK LVCMOS output                 |
| 0x3               | CLK_READY output                      |

#### 7.4.4 Output Enable

#### 7.4.4.1 Output Enable Control

This device supports synchronous Output Enable (OE). Synchronous OE means there is no glitch on the outputs when OE signal is asserted or deasserted.

The following table shows the enabling and disabling outputs through pin configuration and I<sup>2</sup>C. Note that the OE pin must be low **and** OE bit must be "1" for the output to be active. The output enable bits are OUT0\_EN (R7[1]) and OUT1\_EN (R7[8]).

**Table 7-9. OE Functionality** 

| OE Pin | OE Pin Polarity | Software Output Enable<br>OUTx_EN | OUTx    |
|--------|-----------------|-----------------------------------|---------|
| High   | Active low      | 0                                 | Off     |
| High   | Active low      | 1                                 | Off     |
| Low    | Active low      | 0                                 | Off     |
| Low    | Active low      | 1                                 | Running |
| High   | Active high     | 0                                 | Off     |
| High   | Active high     | 1                                 | Running |
| Low    | Active high     | 0                                 | Off     |

Copyright © 2025 Texas Instruments Incorporated

| OE Pin | OE Pin Polarity | Software Output Enable<br>OUTx_EN | OUTx |
|--------|-----------------|-----------------------------------|------|
| Low    | Active high     | 1                                 | Off  |

#### 7.4.4.2 Output Enable Polarity

OE pin polarity is programmable. When the OE pin is active low, the internal pulldown resistor is automatically enabled, and the internal pullup resistor is disabled. When the OE pin is active high, the internal pullup resistor is automatically enabled, and the internal pulldown resistor is disabled. By default, clock outputs are enabled when the OE pin is floating. The OE pin polarity is set by OE\_PIN\_POLARITY (R7[0]) as '1' for active-low (default), or '0' for active-high.

#### 7.4.4.3 Individual Output Enable

The FMT\_ADDR pin can be reconfigured as a second output enable pin. Set SEPARATE\_OE\_EN (R11[14]) to enable this functionality. This bit is OTP programmable. When FMT\_ADDR is used as an output enable pin, the OE pin controls OUT0, and the FMT\_ADDR pin controls OUT1. The OE\_PIN\_POLARITY (R7[0]) bit applies to the OE and FMT\_ADDR pins in this case. If using the FMT\_ADDR pin for individual output enable control, the pin must not be configured for I<sup>2</sup>C LSB selection or output format selection.

#### 7.4.4.4 Output Disable Behavior

When the outputs are disabled, the outputs can be either tri-state or set to the levels in Table 7-10, determined by OUT0 DISABLE STATE (R3[5]) for OUT0 and OUT1 DISABLE STATE (R3[6]) for OUT1.

Table 7-10. Output Disable Behavior

| Output Format          | OUTx_P | OUTx_N |
|------------------------|--------|--------|
| LP-HCSL                | LOW    | LOW    |
| AC-LVDS (1)            | N/A    | N/A    |
| DC-LVDS (2)            | HIGH   | LOW    |
| LVCMOS, P Only         | LOW    | LOW    |
| LVCMOS, N Only         | LOW    | LOW    |
| LVCMOS, Opposite Phase | HIGH   | LOW    |
| LVCMOS, In Phase       | LOW    | LOW    |

<sup>(1)</sup> DC-LVDS assumes that the outputs are DC terminated with 100Ohms.

### 7.4.5 Device Default Settings

Table 7-11 summarizes the default settings of the LMK3H0102V33 and LMK3H0102V18 at start-up for the four OTP pages. In I<sup>2</sup>C mode, the Page 0 settings are loaded. For a full list of every default register setting, see *Device Registers*.

Table 7-11. LMK3H0102 Start-up Settings

| Parameter          | OTP Page 0  | OTP Page 1  | OTP Page 2  | OTP Page 3  |
|--------------------|---|---|---|---|
| VDD supply voltage |   | 3.3V (LMK3<br>1.8V (LMK3  | ,   |   |
| OUT0 Frequency     | 100MHz  | 100MHz  | 100MHz  | 100MHz  |
| OUT0 Output Format | 100Ω LP-HCSL in I2C mode. Set by Pin 2 in OTP mode: • Pin 2 = Low: 100Ω LP-HCSL • Pin 2 = High: 85Ω LP-HCSL | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL |

Table 7-11. LMK3H0102 Start-up Settings (continued)

| Parameter   | OTP Page 0  | OTP Page 1  | OTP Page 2  | OTP Page 3  |
|---|---|---|---|---|
| OUT0 Enable   | Enable  | Enable  | Enable  | Enable  |
| OUT0 Differential Slew Rate   | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  |
| OUT0 LP-HCSL Amplitude  | 755mV (typical)   | 755mV (typical)   | 755mV (typical)   | 755mV (typical)   |
| OUT0_P/N Disable Behavior   | Low/Low   | Low/Low   | Low/Low   | Low/Low   |
| OUT1 Frequency  | 100MHz  | 100MHz  | 100MHz  | 100MHz  |
| OUT1 Output Format  | 100Ω LP-HCSL in I2C mode. Set by Pin 2 in OTP mode: • Pin 2 = Low: 100Ω LP-HCSL • Pin 2 = High: 85Ω LP-HCSL | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL                             | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL                             | Set by Pin 2: Pin 2 = Low: 100Ω LP-HCSL Pin 2 = High: 85Ω LP-HCSL                             |
| OUT1 Enable   | Enable  | Enable  | Enable  | Enable  |
| OUT1 Differential Slew Rate   | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  | 2.3V/ns to 3.5V/ns  |
| OUT1 LP-HCSL Amplitude  | 755mV (typical)   | 755mV (typical)   | 755mV (typical)   | 755mV (typical)   |
| OUT1_P/N Disable Behavior   | Low/Low   | Low/Low   | Low/Low   | Low/Low   |
| REF_CTRL Behavior   | CLK_READY   | CLK_READY   | CLK_READY   | CLK_READY   |
| FOD0 Frequency  | 200MHz  | 200MHz  | 200MHz  | 200MHz  |
| FOD1 Frequency  | 200MHz  | 200MHz  | 200MHz  | 200MHz  |
| SSC Enable  | Disable   | Enable  | Enable  | Enable  |
| SSC Modulation Type   | N/A   | Down-spread   | Down-spread   | Down-spread   |
| SSC Modulation Depth  | N/A   | -0.1%   | -0.3%   | -0.5%   |
| Pin 2 Function  Pin 2 Function  Pin 2 Function  Pin 2 Function  Output Format  Selection (OTP Mode  Only) |   | I2C Address LSB Selection (I <sup>2</sup> C Mode Only Output Format Selection (OTP Mode Only) | I2C Address LSB Selection (I <sup>2</sup> C Mode Only Output Format Selection (OTP Mode Only) | I2C Address LSB Selection (I <sup>2</sup> C Mode Only Output Format Selection (OTP Mode Only) |

## 7.5 Programming

The host (DSP, Microcontroller, FPGA, and so forth) configures and monitors the LMK3H0102 through the I<sup>2</sup>C port. The host reads and writes to a collection of control bits called the register set. The device blocks can be controlled and monitored through a specific grouping of bits located within the register space. In the absence of the host, the LMK3H0102 can be configured to operate in OTP mode from one of four of the on-chip OTP pages, stored in the internal EFUSE, depending on the state of REF\_CTRL and OTP\_SELx pins. The EFUSE is one-time programmed by TI, and is not rewritable. This means that the values of the registers that are automatically loaded from the EFUSE at power-up can not be customized. However, the values of the registers can be changed subsequently via the I<sup>2</sup>C register interface. Within the device registers, there are certain bits that have read/write access. Other bits are read-only (an attempt to write to a read only bit does not change the state of the bit). Certain device registers and bits are reserved meaning that the fields must not be changed from the default reset state.

#### 7.5.1 I<sup>2</sup>C Serial Interface

The I<sup>2</sup>C port on the LMK3H0102 works as a peripheral device and supports both the 100-kHz standard mode and 400-kHz fast-mode operations. Fast mode imposes a glitch tolerance requirement on the control signals. Therefore, the input receivers ignore pulses of less than 50-ns duration. The I<sup>2</sup>C timing requirements are provided in the I<sup>2</sup>C Interface Specification. Figure 7-9 shows the timing diagram.






Figure 7-9. I<sup>2</sup>C Timing Diagram

The LMK3H0102 is accessed through a 7-bit peripheral address transmitted as part of an  $I^2C$  packet. Only the device with a matching peripheral address responds to subsequent  $I^2C$  commands. In  $I^2C$  mode, the LMK3H0102 allows up to four unique peripheral devices to occupy the I2C bus based on the pin strapping of FMT\_ADDR (tied to VDD, GND, SDA, or SCL). By default, the device peripheral address is 0b11010xx (the two LSBs are determined by the FMT\_ADDR pin). The full address can be configured through  $I^2C$ .

During the data transfer through the I<sup>2</sup>C interface, one clock pulse is generated for each data bit transferred. The data on the SDA line must be stable during the high period of the clock. The high or low state of the data line can change only when the clock signal on the SCL line is low. The start data transfer condition is characterized by a high-to-low transition on the SDA line while SCL is high. The stop data transfer condition is characterized by a low-to-high transition on the SDA line while SCL is high. The start and stop conditions are always initiated by the controller. Every byte on the SDA line must be eight bits long. Each byte must be followed by an acknowledge bit and bytes are sent MSB first. The LMK3H0102 has an 8-bit register address, followed by a 16-bit data word.

The acknowledge bit (A) or non-acknowledge bit (A') is the 9th bit attached to any 8-bit data byte and is always generated by the receiver to inform the transmitter that the byte has been received (when A = 0) or not (when A' = 0). A = 0 is done by pulling the SDA line low during the 9th clock pulse and A' = 0 is done by leaving the SDA line high during the 9th clock pulse.

The I<sup>2</sup>C controller initiates the data transfer by asserting a start condition which initiates a response from all peripheral devices connected to the serial bus. Based on the 8-bit address byte sent by the controller over the SDA line (consisting of the 7-bit peripheral address (MSB first) and an R/W' bit), the device whose address corresponds to the transmitted address responds by sending an acknowledge bit. All other devices on the bus remain idle while the selected device waits for data transfer with the controller.

After the data transfer occurs, stop conditions are established. In write mode, the controller asserts a stop condition to end data transfer during the 10th clock pulse following the acknowledge bit for the last data byte from the peripheral. In read mode, the controller receives the last data byte from the peripheral but does not pull SDA low during the 9th clock pulse. This is known as a non-acknowledge bit. By receiving the non-acknowledge bit, the peripheral knows the data transfer is finished and enters the idle mode. The controller then takes the data line low during the low period before the 10th clock pulse, and high during the 10th clock pulse to assert a stop condition. Figure 7-10 and Figure 7-11 show the sequence for block writes and block reads using the LMK3H0102, respectively.




Figure 7-11. Generic Block Read Sequence

#### 7.5.2 One-Time Programming Sequence

The upper register space includes all registers from R13 onward, as well as I2C\_ADDR (R12[15:8]). Unlocking the upper register space is performed by writing 0x5B to UNLOCK\_PROTECTED\_REG (R12[7:0]), leaving I2C\_ADDR unchanged. If using the edge combiner, performing the unlock first is required before modifying R146, R147, and R148.

There are six fields that can have different values depending on the EFUSE page loaded at device start-up.

- OUT0 Output Format
- OUT0 Enable
- OUT1 Output Format
- OUT1 Enable
- SSC Enable
- SSC Configuration (either preconfigured or custom)

All other fields retain the same value across all four EFUSE pages. For generating custom configurations, contact TI.



## **8 Device Registers**

## 8.1 Register Maps

Table 8-1 lists the LMK3H0102 Device registers. All register offset address not listed in Table 8-1 can be considered as reserved locations and the register contents must not be modified.

Table 8-1. LMK3H0102 Registers

| Address | Acronym | Section |
|---------|---------|---------|
| 0x0     | R0      | Go      |
| 0x1     | R1      | Go      |
| 0x2     | R2      | Go      |
| 0x3     | R3      | Go      |
| 0x4     | R4      | Go      |
| 0x5     | R5      | Go      |
| 0x6     | R6      | Go      |
| 0x7     | R7      | Go      |
| 0x8     | R8      | Go      |
| 0x9     | R9      | Go      |
| 0xA     | R10     | Go      |
| 0xB     | R11     | Go      |
| 0xC     | R12     | Go      |
| 0x92    | R146    | Go      |
| 0x93    | R147    | Go      |
| 0x94    | R148    | Go      |
| 0xEE    | R238    | Go      |

Complex bit access types are encoded to fit into small table cells. Table 8-2 shows the codes that are used for access types in this section.

Table 8-2. LMK3H0102 Access Type Codes

| 100.00 -11. | 14515 5 21 21111 (5115 102 ) (500 50 1) po 50465 |                     |  |  |  |  |
|-------------|--|---------------------|--|--|--|--|
| Access Type | Code   | Description         |  |  |  |  |
|             | Read Type  |                     |  |  |  |  |
| R           | R  | Read                |  |  |  |  |
|             | Write Type                                       |                     |  |  |  |  |
| W           | W  | Write               |  |  |  |  |
| WL          | W  | Write               |  |  |  |  |
|             | L  | Locked, requires    |  |  |  |  |
|             |  | UNLOCK_PROTECT      |  |  |  |  |
|             |  | ED_REG (R12[7:0]) = |  |  |  |  |
|             |  | 0x5B to unlock and  |  |  |  |  |
|             |  | write successfully  |  |  |  |  |
|             |  |                     |  |  |  |  |

#### 8.1.1 R0 Register (Address = 0x0) [reset = 0x0861/0x0863]

R0 is shown in Table 8-3.

Return to the Summary Table.

Table 8-3. R0 Register Field Descriptions

| Bit   | Field         | Туре | Reset                        | Description   |
|-------|---------------|------|------------------------------|---|
| 15:10 | DIG_CLK_N_DIV | R/W  | 0x02                         | Digital State Machine clock rate. Derived from the FOD frequency sourced by the CH0_FOD_SEL multiplexer. The target for the frequency is 50MHz maximum. The actual divide value is the DIG_CLK_N_DIV value plus 2. This field is stored in the EFUSE.                                 |
| 9:3   | FOD0_N_DIV    | R/W  | 0x0C                         | Integer Ratio of BAW frequency to FOD0 frequency. This field is stored in the EFUSE.  |
| 2:1   | SUP_LVL_SEL   | R/W  | 0x0<br>(V33)<br>0x1<br>(V18) | Operating voltage for core supply LDO. This field is factory programmed, and <b>must not</b> be overwritten with a different value than the programmed value. Supply voltage on VDD and VDDO pins <b>must not</b> exceed the selected voltage value + 10%.  0: 3.3V  1: 1.8V  2: 2.5V |
| 0     | OTP_BURNT     | R/WL | 0x1                          | Indicates that the EFUSE has been programmed. If this field is '1', the EFUSE is programmed.  |

#### 8.1.2 R1 Register (Address = 0x1) [reset = 0x5599]

R1 is shown in Table 8-4.

Return to the Summary Table.

Table 8-4. R1 Register Field Descriptions

| Bit  | Field           | Туре | Reset | Description  |
|------|-----------------|------|-------|--|
| 15:8 | FOD0_NUM[23:16] | R/W  | 0x55  | High byte of the FOD0 fractional divide value. The value of this field changes from device to device. This field is stored in the EFUSE. |
| 7:0  | ADC_CLK_N_DIV   | R/W  | 0x99  | ADC clock frequency in MHz, derived directly from BAW. Default is ceil(2467 / 16) - 2  |
|      |                 |      |       | = 0x99. This field is stored in the EFUSE.   |
|      |                 |      |       | TI does not recommend modifying the value of this field.   |

## 8.1.3 R2 Register (Address = 0x2) [reset = 0xC28F]

R2 is shown in Table 8-5.

Return to the Summary Table.

## Table 8-5. R2 Register Field Descriptions

| Bit  | Field          | Туре | Reset | Description  |
|------|----------------|------|-------|--|
| 15:0 | FOD0_NUM[15:0] | R/W  |       | Lower two bytes of the FOD0 fractional divide value. The value of this field changes from device to device. This field is stored in the EFUSE. |

## 8.1.4 R3 Register (Address = 0x3) [reset = 0x1801]

R3 is shown in Table 8-6.

Return to the Summary Table.

## Table 8-6. R3 Register Field Descriptions

| Bit  | Field       | Туре | Reset | Description  |  |  |
|------|-------------|------|-------|--|--|--|
| 15:9 | FOD1_N_DIV  | R/W  | 0x0C  | Integer Ratio of BAW frequency to FOD1 frequency. This field is stored in the EFUSE.                                       |  |  |
| 8    | CH1_FOD_SEL | R/W  | 0x0   | Selects the FOD to use as the input source for Channel Divider 1. This field is stored in the EFUSE.  Oh: FOD0.  1h: FOD1. |  |  |

Copyright © 2025 Texas Instruments Incorporated



### Table 8-6. R3 Register Field Descriptions (continued)

| Bit | Field              | Туре | Reset | Description (continued)  |
|-----|--------------------|------|-------|--|
| 7   | CH1_EDGE_COMB_EN   | R/W  | 0x0   | Selects between using Channel Divider 1 or using the Edge Combiner as the input source for Output Driver 1. This field is stored in the EFUSE.  Oh: Channel Divider 1 input  1h: Edge Combiner input   |
| 6   | OUT1_DISABLE_STATE | R/W  | 0x0   | When OUT1 is disabled, this bit selects whether the OUT1_P and OUT1_N pins are forced to GND or tri-state. This field is stored in the EFUSE.  Oh: Forced to GND on disable.  1h: Tri-state on disable.  |
| 5   | OUT0_DISABLE_STATE | R/W  | 0x0   | When OUT0 is disabled, this bit selects whether the OUT0_P and OUT0_N pins are forced to GND or tri-state. This field is stored in the EFUSE.  Oh: Forced to GND on disable.  1h: Tri-state on disable.  |
| 4   | CH0_FOD_SEL        | R/W  | 0x0   | Selects the FOD to use as the input source for Channel Divider 0. This field is stored in the EFUSE.  0h: FOD0.  1h: FOD1.   |
| 3   | CH0_EDGE_COMB_EN   | R/W  | 0x0   | Selects between using Channel Divider 0 or using the Edge Combiner as the input source for Output Driver 0. This field is stored in the EFUSE.  Oh: Channel Divider 0 input  1h: Edge Combiner input   |
| 2:0 | CH0_DIV            | R/W  | 0x1   | Divider value for Channel Divider 0. This field is stored in the EFUSE.  0h: Channel Divider disabled. Set CH0_DIV to '0' when using the edge combiner for OUT0.  1h: FOD / 2  2h: FOD / 4  3h: FOD / 6  4h: FOD / 8  5h: FOD / 10  6h: FOD / 20  7h: FOD / 40 |

## 8.1.5 R4 Register (Address = 0x4) [reset = 0x0000]

R4 is shown in Table 8-7.

Return to the Summary Table.

## Table 8-7. R4 Register Field Descriptions

| Bit  | Field        | Туре | Reset  | Description   |
|------|--------------|------|--------|---|
| 15   | Reserved     | R    | N/A    | Reserved, do not write to this field.   |
| 14:2 | SSC_STEPS    | R/W  | 0x0000 | Number of steps in each segment of the triangular profile for SSC. See Spread Spectrum Clocking for instructions to calculate this value. This field is stored in the EFUSE.          |
| 1    | SSC_MOD_TYPE | R/W  | 0x0    | Selects between down-spread or center-spread modulation for custom SSC configurations. This field is stored in the EFUSE.  Oh: Down-spread modulation.  1h: Center-spread modulation. |
| 0    | SSC_EN       | R/W  | 0x0    | Enable SSC. This field is stored in the EFUSE.  0h: SSC Disabled.  1h: SSC Enabled.   |

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

## 8.1.6 R5 Register (Address = 0x5) [reset = 0x0000]

R5 is shown in Table 8-8.

Return to the Summary Table.

## Table 8-8. R5 Register Field Descriptions

| Bit  | Field         | Туре | Reset | Description   |
|------|---------------|------|-------|---|
| 15:0 | SSC_STEP_SIZE | R/W  |       | Numerator increment value per step for SSC. See Spread Spectrum Clocking for instructions to calculate this value. This field is stored in the EFUSE. |

## 8.1.7 R6 Register (Address = 0x6) [reset = 0x0AA0]

R6 is shown in Table 8-9.

Return to the Summary Table.

## Table 8-9. R6 Register Field Descriptions

| Bit   | Field           | Туре | Reset | Description  |
|-------|-----------------|------|-------|--|
| 15:13 | CH1_DIV         | R/W  | 0x0   | Divider value for Channel Divider 1. This field is stored in the EFUSE.  Oh: Channel Divider disabled. Set CH1_DIV to '0' when using the edge combiner for OUT1. |
|       |                 |      |       | 1h: FOD / 2  |
|       |                 |      |       | 2h: FOD / 4  |
|       |                 |      |       | 3h: FOD / 6  |
|       |                 |      |       | 4h: FOD / 8  |
|       |                 |      |       | 5h: FOD / 10   |
|       |                 |      |       | 6h: FOD / 20   |
|       |                 |      |       | 7h: FOD / 40   |
| 12:5  | FOD1_NUM[23:16] | R/W  | 0x55  | High byte of the FOD1 fractional divide value. The value of this field changes from device to device. This field is stored in the EFUSE.                         |
| 4:3   | OUT0_SLEW_RAT   | R/W  | 0x0   | Slew rate control for OUT0. This field is stored in the EFUSE.   |
|       | E               |      |       | Only applies to differential output formats.   |
|       |                 |      |       | 0h: Between 2.3V/ns and 3.5V/ns.   |
|       |                 |      |       | 1h: Between 2.0V/ns and 3.2V/ns.   |
|       |                 |      |       | 2h: Between 1.7V/ns and 2.8V/ns.   |
|       |                 |      |       | 3h: Between 1.4V/ns and 2.7V/ns.   |
| 2:0   | OUT0_FMT        | R/W  | 0x0   | Selects the output format for OUT0. This field is stored in the EFUSE.   |
|       |                 |      |       | 0h: LP-HCSL 100Ω Termination.  |
|       |                 |      |       | 1h: LP-HCSL 85Ω Termination.   |
|       |                 |      |       | 2h: AC-coupled LVDS.   |
|       |                 |      |       | 3h: DC-coupled LVDS.   |
|       |                 |      |       | 4h: LVCMOS, OUTx_P enabled, OUTx_N disabled.   |
|       |                 |      |       | 5h: LVCMOS, OUTx_P disabled, OUTx_N enabled.   |
|       |                 |      |       | 6h: LVCMOS, OUTx_P enabled, OUTx_N enabled, 180 degrees out of phase.  |
|       |                 |      |       | 7h: LVCMOS, OUTx_P enabled, OUTx_N enabled, OUTx_P and OUTx_N in phase.  |

## 8.1.8 R7 Register (Address = 0x7) [reset = 0x6503]

R7 is shown in Table 8-10.

Return to the Summary Table.

### Table 8-10. R7 Register Field Descriptions

| Bit | Field    | Туре | Reset | Description                           |
|-----|----------|------|-------|---------------------------------------|
| 15  | Reserved | N/A  | 0x0   | Reserved, do not write to this field. |

Copyright © 2025 Texas Instruments Incorporated



## Table 8-10. R7 Register Field Descriptions (continued)

| D:4   | Field                 |      |       | Register Field Descriptions (continued)   |
|-------|-----------------------|------|-------|---|
| Bit   | Field                 | Туре | Reset | Description   |
| 14:13 | REF_CTRL_PIN_F<br>UNC | R/W  | 0x3   | Sets the function of the REF_CTRL pin. This field is stored in the EFUSE.  Oh: REF_CTRL pin disabled, pulled to GND.  1h: REF_CTRL pin disabled, tri-state.  2h: REF_CTRL pin functions as an additional LVCMOS REF_CLK output.  3h: REF_CTRL pin functions as "clock ready" signal.  |
| 12:11 | REF_CLK_DIV           | R/W  | 0x0   | REF_CLK output divisor value when REF_CTRL is used as REF_CLK. This field is stored in the EFUSE.  0h: REF_CLK disabled.  1h: FOD / 2.  2h: FOD / 4.  3h: FOD / 8.  |
| 10    | Reserved              | R/W  | 0x1   | Reserved. Do not write any value other than '1' to this field.  |
| 9     | REF_CLK_FOD_S<br>EL   | R/W  | 0x0   | Select the FOD used to generate the REF_CLK output. This field is stored in the EFUSE.  0h: FOD0.  1h: FOD1.  |
| 8     | OUT1_EN               | R/W  | 0x1   | Output Enable bit for OUT1. This field is stored in the EFUSE.  0h: OUT1 is disabled.  1h: OUT1 is enabled.   |
| 7     | OUT1_CH_SEL           | R/W  | 0x0   | Selects the source for OUT1. If the Edge Combiner is enabled, then this bit is ignored. This field is stored in the EFUSE.  0h: OUT1 is sourced from Channel Divider 0 if CH0_EDGE_COMB_EN is a '0', or the Edge Combiner if CH0_EDGE_COMB_EN is a '1'.  1h: OUT1 is sourced from Channel Divider 1 if CH1_EDGE_COMB_EN is a '0', or the Edge Combiner if CH1_EDGE_COMB_EN is a '1'.  |
| 6:5   | OUT1_SLEW_RAT<br>E    | R/W  | 0x0   | Slew rate control for OUT1. This field is stored in the EFUSE.  Only applies to differential output formats.  0h: Between 2.3V/ns and 3.5V/ns.  1h: Between 2.0V/ns and 3.2V/ns.  2h: Between 1.7V/ns and 2.8V/ns.  3h: Between 1.4V/ns and 2.7V/ns.  |
| 4:2   | OUT1_FMT              | R/W  | 0x0   | Selects the output format for OUT1. This field is stored in the EFUSE.  0h: LP-HCSL 100Ω Termination.  1h: LP-HCSL 85Ω Termination.  2h: AC-coupled LVDS.  3h: DC-coupled LVDS.  4h: LVCMOS, OUTx_P enabled, OUTx_N disabled.  5h: LVCMOS, OUTx_P disabled, OUTx_N enabled.  6h: LVCMOS, OUTx_P enabled, OUTx_N enabled, 180 degrees out of phase.  7h: LVCMOS, OUTx_P enabled, OUTx_N enabled, OUTx_P and OUTx_N in phase. |
| 1     | OUT0_EN               | R/W  | 0x1   | Output Enable bit for OUT0. This field is stored in the EFUSE. 0h: OUT0 is disabled. 1h: OUT0 is enabled.   |
| 0     | OE_PIN_POLARIT<br>Y   | R/W  | 0x1   | OE pin polarity selection. This bit does not affect the polarity of the OUTx_EN bits, only the OE pin. This field is stored in the EFUSE.  Oh: OE is active high (OE tied to VDD enables outputs).  1h: OE is active low (OE tied to GND enables outputs).  |

# 8.1.9 R8 Register (Address = 0x8) [reset = 0xC28F]

R8 is shown in Table 8-11.

Return to the Summary Table.

## Table 8-11. R8 Register Field Descriptions

| Bit  | Field          | Туре | Reset | Description  |
|------|----------------|------|-------|--|
| 15:0 | FOD1_NUM[15:0] | R/W  |       | Lower two bytes of the FOD1 fractional divide value. The value of this field changes from device to device. This field is stored in the EFUSE. |

# 8.1.10 R9 Register (Address = 0x9) [reset = 0x3166]

R9 is shown in Table 8-12.

Return to the Summary Table.

# Table 8-12. R9 Register Field Descriptions

| Bit   | Field               | Туре | Reset                        | Description  |
|-------|---------------------|------|------------------------------|--|
| 15:12 | OTP_ID              | R/W  | 0x3<br>(V33)<br>0x1<br>(V18) | Configurable field for identifying the OTP configuration. Can be used in I2C mode as a 4-bit spare field. This field is stored in the EFUSE.   |
| 11:9  | SSC_CONFIG_SEL      | R/W  | 0x0                          | SSC modulation configuration. If center-spread modulation is desired, then custom SSC configuration is required. Four preconfigured down-spread modulation depths are also available. Any other modulation depths require custom SSC configuration. This field is stored in the EFUSE.  The preconfigured SSC options are specifically for 100MHz clock outputs. For other output frequencies, TI recommends creating a custom SSC configuration.  0h: Custom SSC Configuration - see Spread Spectrum Clocking for details on creating a custom configuration.  1h: -0.10% preconfigured down-spread.  2h: -0.25% preconfigured down-spread.  3h: -0.30% preconfigured down-spread.  4h: -0.50% preconfigured down-spread.  All other values: Reserved |
| 8     | OUT_FMT_SRC_S<br>EL | R/W  | 0x1                          | Forces the FMT_ADDR pin to override the output format register settings in OTP Mode. When in I2C mode, the FMT_ADDR pin is never used for this purpose. This field is stored in the EFUSE.  Oh: FMT_ADDR pin is ignored in OTP mode for output format selection.  1h: FMT_ADDR pin overrides the register settings in OTP mode. The output format is LP-HCSL, and the termination resistor values are based on the FMT_ADDR pin state on start-up.   |

Copyright © 2025 Texas Instruments Incorporated

Submit Document Feedback



#### Table 8-12. R9 Register Field Descriptions (continued)

| Bit | Field                   | Туре | Reset | Description  Description  |
|-----|-------------------------|------|-------|---|
| 7:4 |                         | R/W  | 0x6   | -   |
| 7:4 | OUT1_LPHSCL_A<br>MP_SEL | R/VV | UXO   | OUT1 output swing level when using LP-HCSL output format. This field is stored in |
|     | WII _OLL                |      |       | the EFUSE.  |
|     |                         |      |       | 0h: 625mV.  |
|     |                         |      |       | 1h: 647mV.  |
|     |                         |      |       | 2h: 668mV.  |
|     |                         |      |       | 3h: 690mV.  |
|     |                         |      |       | 4h: 712mV.  |
|     |                         |      |       | 5h: 733mV.  |
|     |                         |      |       | 6h: 755mV.  |
|     |                         |      |       | 7h: 777mV.  |
|     |                         |      |       | 8h: 798mV.  |
|     |                         |      |       | 9h: 820mV.  |
|     |                         |      |       | Ah: 842mV.  |
|     |                         |      |       | Bh: 863mV.  |
|     |                         |      |       | Ch: 885mV.  |
|     |                         |      |       | Dh: 907mV.  |
|     |                         |      |       | Eh: 928mV.  |
|     |                         |      |       | Fh: 950mV.  |
| 3:0 | OUT0_LPHSCL_A           | R/W  | 0x6   | OUT0 output swing level when using LP-HCSL output format. This field is stored in |
|     | MP_SEL                  |      |       | the EFUSE.  |
|     |                         |      |       | 0h: 625mV.  |
|     |                         |      |       | 1h: 647mV.  |
|     |                         |      |       | 2h: 668mV.  |
|     |                         |      |       | 3h: 690mV.  |
|     |                         |      |       | 4h: 712mV.  |
|     |                         |      |       | 5h: 733mV.  |
|     |                         |      |       | 6h: 755mV.  |
|     |                         |      |       | 7h: 777mV.  |
|     |                         |      |       | 8h: 798mV.  |
|     |                         |      |       | 9h: 820mV.  |
|     |                         |      |       | Ah: 842mV.  |
|     |                         |      |       | Bh: 863mV.  |
|     |                         |      |       | Ch: 885mV.  |
|     |                         |      |       | Dh: 907mV.  |
|     |                         |      |       | Eh: 928mV.  |
|     |                         |      |       | Fh: 950mV.  |
|     |                         |      |       | 1   |

# 8.1.11 R10 Register (Address = 0xA) [reset = 0x0010]

R10 is shown in Table 8-13.

Return to the Summary Table.

# Table 8-13. R10 Register Field Descriptions

| Bit   | Field      | Туре | Reset | Description   |
|-------|------------|------|-------|---|
| 15    | Reserved   | R/W  | 0x0   | Reserved. Only write '0' to this bit.   |
| 14:11 | PROD_REVID | R    | N/A   | Product revision identifier.  |
| 10    | CLK_READY  | R    | N/A   | CLK_READY status. The REF_CTRL pin mirrors this status signal when the pin functions as a "clock ready" signal. |
| 9     | Reserved   | R    | N/A   | Reserved, do not write to this field.   |
| 8     | RB_PIN_15  | R    | N/A   | Readback of the REF_CTRL pin.   |
| 7     | RB_PIN_4   | R    | N/A   | Readback of the OTP_SEL1/SDA pin.   |

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

# **INSTRUMENTS** www.ti.com

## Table 8-13. R10 Register Field Descriptions (continued)

| Bit | Field                  | Туре | Reset | Description (continued)  |
|-----|------------------------|------|-------|--|
| 6   | RB_PIN_3               | R    | N/A   | Readback of the OTP_SEL0/SCL pin.  |
| 5   | RB_PIN_2               | R    | N/A   | Readback of the FMT_ADDR pin.  |
| 4   | DEV_IDLE_STATE_<br>SEL | R/W  | 0x1   | This bit controls the behavior of the device when both outputs are disabled. Placing the device into a low-power state is not recommended for PCIe applications, as the time to re-enable the clocks is extended. This field is stored in the EFUSE.  Oh: When both outputs are disabled, the outputs are muted, and the device is placed into a low-power state.  1h: When both outputs are disabled, the outputs are muted. The device does not enter a low-power state.   |
| 3   | PIN_RESAMPLE_D<br>IS   | R/W  | 0x0   | This bit controls the resampling of the device pins when exiting the low power mode. Write this bit while in the low power mode. TI recommends keeping this bit as a '1' unless the functionality is explicitly desired.  Oh: Pin resampling is enabled. When exiting the low power mode, the FMT_ADDR, OTP_SEL0/SCL, OTP_SEL1/SDA, and FMT_ADDR pins are resampled. If FMT_ADDR is high, the device enters OTP Mode.  1h: Pin resampling is disabled. When exiting the low power mode, the FMT_ADDR, OTP_SEL0/SCL, OTP_SEL1/SDA, and FMT_ADDR pins are not resampled. The device remains in I2C Mode. |
| 2   | OTP_AUTOLOAD_<br>DIS   | R/W  | 0x0   | This bit controls the behavior of the device when exiting the low power mode. Write this bit while in the low power mode. TI recommends keeping this bit as a '1' unless the functionality is explicitly desired.  Oh: OTP autoload is enabled. When exiting the low power mode, the contents of OTP Page 0 are written to the device registers.  1h: OTP autoload is disabled. When exiting the low power mode, the contents of OTP Page 0 are not written to the device registers.   |
| 1   | PDN                    | R/W  | 0x0   | Writing a '1' to this bit puts the device into a low power state.  |
| 0   | Reserved               | R/W  | 0x0   | Reserved. Only write '0' to this bit.  |

# 8.1.12 R11 Register (Address = 0xB) [reset = 0x0000]

R11 is shown in Table 8-14.

Return to the Summary Table.

#### Table 8-14. R11 Register Field Descriptions

| Bit  | Field              | Туре | Reset  | Description   |
|------|--------------------|------|--------|---|
| 15   | Reserved           | R/W  | 0x0    | Reserved. Only write '0' to this bit.   |
| 14   | SEPARATE_OE_E<br>N | R/W  |        | This bit enables the separate output enable functionality of the device. If this bit is a '1', then OUT_FMT_SRC_SEL and I2C_ADDR_LSB_SEL must be set to '0'. This field is stored in the EFUSE.  Oh: Pin 1 is the output enable for OUT0 and OUT1.  1h: Pin 1 is the output enable for OUT0, Pin 2 is the output enable for OUT1. |
| 13:0 | Reserved           | R/W  | 0x0000 | Reserved, do not write to this field.   |

## 8.1.13 R12 Register (Address = 0xC) [reset = 0xE800]

R12 is shown in Table 8-15.

Return to the Summary Table.



Table 8-15. R12 Register Field Descriptions

| Bit  | Field                    | Туре | Reset | Description  |
|------|--------------------------|------|-------|--|
| 15   | I2C_ADDR_LSB_S<br>EL     | R/WL | 0x1   | I2C peripheral address source. If this bit is a '1', SEPARATE_OE_EN must be '0'. This field is stored in the EFUSE.  Oh: I2C peripheral address comes entirely from the I2C_ADDR field.  1h: The two lowest bits of the I2C peripheral address come from the FMT_ADDR pin, all other bits come from R12[14:10].  |
| 14:8 | I2C_ADDR                 | R/WL | 0x68  | I2C peripheral address. After writing to this field, the device responds to the new I2C address. This field is stored in the EFUSE.  |
| 7:0  | UNLOCK_PROTEC<br>TED_REG | R/W  | 0x00  | This field locks all registers from R13 onward, in addition to R12[15:8]. Registers R13 onward are largely device calibration registers, and the contents modified if not described in this document. These registers can be read from normally regardless of the unlock status.  5Bh: Unlocks register writes for R12[15:8] and above.  Any other value: R12[15:8] and above ignore all writes. |

# 8.1.14 R146 Register (Address = 0x92) [reset = 0x0000]

R146 is shown in Table 8-16.

Return to the Summary Table.

## Table 8-16. R146 Register Field Descriptions

| Bit   | Field                  | Туре | Reset | Description   |
|-------|------------------------|------|-------|---|
| 15:13 | Reserved               | R/WL | 0x0   | Reserved, do not write to this field.   |
| 12:5  | DTC1_GAIN_RT           | R/WL | 0x00  | Room temperature gain calibration code for FOD0. The value of this field varies from device to device. This must be averaged with DTC2_GAIN_RT when using the edge combiner. This field is stored in the EFUSE.       |
| 4:0   | DTC1_GAIN_DELT<br>A_CT | R/WL | 0x00  | Cold temperature gain calibration code for FOD0. The value of this field varies from device to device. This must be averaged with DTC2_GAIN_DELTA_CT when using the edge combiner. This field is stored in the EFUSE. |

## 8.1.15 R147 Register (Address = 0x93) [reset = 0x0000]

R147 is shown in Table 8-17.

Return to the Summary Table.

#### Table 8-17, R147 Register Field Descriptions

|       | Table 6 111 Kt 41 Regioter Flora Becomptions |      |       |   |  |  |
|-------|--|------|-------|---|--|--|
| Bit   | Field  | Туре | Reset | Description   |  |  |
| 15:11 | Reserved                                     | R/WL | 0x00  | Reserved, do not write to this field.   |  |  |
| 13:8  | DTC2_GAIN_DELT<br>A_CT                       | R/WL | 0x00  | Cold temperature gain calibration code for FOD1. The value of this field varies from device to device. This must be averaged with DTC1_GAIN_DELTA_CT when using the edge combiner. This field is stored in the EFUSE. |  |  |
| 7:0   | DTC1_GAIN_DELT<br>A_HT                       | R/WL | 0x00  | Hot temperature gain calibration code for FOD0. The value of this field varies from device to device. This must be averaged with DTC2_GAIN_DELTA_HT when using the edge combiner. This field is stored in the EFUSE.  |  |  |

## 8.1.16 R148 Register (Address = 0x94) [reset = 0x0000]

R148 is shown in Table 8-18.

Return to the Summary Table.

# Table 8-18. R148 Register Field Descriptions

|       | Table 6 161 171 16 1769 letter 1 1614 2 5061 ptions |      |       |                                       |  |
|-------|---|------|-------|---------------------------------------|--|
| Bit   | Field   | Туре | Reset | Description                           |  |
| 15:14 | Reserved  | R/WL | 0x0   | Reserved, do not write to this field. |  |

Product Folder Links: LMK3H0102

#### www.ti.com

## Table 8-18. R148 Register Field Descriptions (continued)

| Bit  | Field                  | Туре | Reset | Description  |
|------|------------------------|------|-------|--|
| 13:8 | DTC2_GAIN_DELT<br>A_HT | R/WL | 0x00  | Hot temperature gain calibration code for FOD1. The value of this field varies from device to device. This must be averaged with DTC1_GAIN_DELTA_HT when using the edge combiner. This field is stored in the EFUSE. |
| 7:0  | DTC2_GAIN_RT           | R/WL | 0x00  | Room temperature gain calibration code for FOD1. The value of this field varies from device to device. This must be averaged with DTC1_GAIN_RT when using the edge combiner. This field is stored in the EFUSE.      |

# 8.1.17 R238 Register (Address = 0xEE) [reset = 0x0000]

R246 is shown in Table 8-19.

Return to the Summary Table.

# Table 8-19. R246 Register Field Descriptions

| Bit  | Field                       | Туре | Reset  | Description   |
|------|-----------------------------|------|--------|---|
| 15:0 | BAWFREQ_OFFSE<br>T_FIXEDLUT | R/WL | 0x0000 | Offset value from 2467MHz for the BAW frequency. Signed 16-bit integer value. This field is stored in the EFUSE.  Each bit of this fields corresponds to 128ppm of frequency deviation. <b>This field varies from part to part.</b> This field is for calculation purposes only, the device does not use this register for any internal calculation. Do <b>NOT</b> write to this field. |



# 9 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

## 9.1 Application Information

The LMK3H0102 is a reference-less BAW-based clock generator that can be used to provide reference clocks for various applications, including PCIe reference clocking and XTAL/XO replacement.

#### 9.2 Typical Applications

#### 9.2.1 Application Block Diagram Examples




Figure 9-1. PCIe Applications




Figure 9-2. Five XO Replacement

#### 9.2.2 Design Requirements

Consider a typical PCle application. In a system such as this, the clocks are expected to be available upon request without the need for any additional device-level programming. A typical output clock requirement in this application is two 100MHz LP-HCSL clocks. A 25MHz clock is added to show how to configure the REF\_CLK output as well. The section below describes the detailed design procedure to generate the required output frequencies for the above PCle scenario using the LMK3H0102.

Product Folder Links: LMK3H0102

## 9.2.3 Detailed Design Procedure

Design of all aspects of the LMK3H0102 is straightforward, and software support is available to assist in frequency planning and part programming. This design procedure gives a straightforward outline of the process.

#### 1. Frequency Planning

- a. The first step of designing an LMK3H0102 configuration is to determine the FOD frequencies that are required to generate the required output frequencies. The process is as such:
  - i. If the output frequencies are greater than 200MHz, the frequencies must both be the same, and can not use SSC. If the frequencies are different, or require SSC, then this frequency plan can not be supported by the device.
    - In the case of two identical frequencies greater than 200MHz, the edge combiner must be enabled, the FOD divider values must match, and REF\_CLK, if used, can be sourced from either FOD.
  - ii. If both output frequencies are the same, and have the same SSC settings (that is, both use SSC or both do not use SSC), only one FOD is required.
  - iii. If both output frequencies are different, but have the same SSC settings, the outputs can share an FOD to conserve current. If both frequencies can be generated from dividing a single valid FOD frequency by the channel divider options, then the second FOD can be disabled. Otherwise, both FODs must be used. If both outputs require SSC, then this frequency plan can not be supported by the LMK3H0102 device.
  - iv. If one output requires SSC and the other does not, then the SSC output must use FOD0 and the non-SSC output must use FOD1.
- b. If SSC is being used, determine whether or not a preconfigured down-spread modulation, a custom down-spread modulation, or a center-spread modulation is required for the application. If a custom configuration is required, follow the steps outlined in *Spread-Spectrum Clocking*.
- c. Set the digital clock divider such that the digital clock frequency is as close to 50MHz as possible.
- d. Determine the REF\_CTRL pin functionality. If this is used as an additional LVCMOS reference clock, verify that the desired frequency can be generated based on the FOD0 and FOD1 frequencies, as the divider range for the REF\_CLK output is /2, /4, or /8 only.
  - Keep in mind that if SSC is used on FOD0, and the REF\_CLK source is FOD0, this output now has SSC as well.

#### 2. Setting the Output Formats

- a. The output formats that are required are based upon the clock format needed in the system. For PCIe applications, this is most often a 100MHz LP-HCSL clock. The internal termination resistance value must be chosen such that the impedance matches the input impedance of the receiver. Note that the termination scheme is different for AC-LVDS and DC-LVDS an AC-LVDS receiver requires an AC-LVDS output from the LMK3H0102.
- b. For differential outputs, the slew rate is selectable, from the slowest range (1.4V/ns to 2.7V/ns) to the fastest range (2.3V/ns to 3.5V/ns).
- c. For LP-HCSL outputs of either termination scheme, the amplitude is selectable between 625mV and 950mV.
- d. For LVCMOS outputs, the P and N phases can be in phase, opposite, or individually enabled or disabled. This allows for the generation of up to five LVCMOS clocks between OUT0, OUT1, and the REF\_CTRL pin.
  - i. For LVCMOS outputs, the VDDO\_x voltage MUST match the VDD voltage if VDD is 1.8V or 2.5V.

#### 3. Output Enable Behavior

a. The output enable pin is active low by default, with an internal pulldown resistor to GND. If this functionality is not desired, then OE\_PIN\_POLARITY can be set to '0' to change the behavior of the OE pin to active-high. If this is done, the internal pulldown is disabled, and an internal pullup to VDD is used.

Copyright © 2025 Texas Instruments Incorporated

b. Determine whether or not both outputs being disabled means that the device enters low-power mode. While this is able to conserve current, low-power mode is not recommended for any applications where the clocks must turn back on quickly, such as PCIe clocking.

For the PCle example, the following settings are required:

- 1. One FOD can be used to generate both LP-HCSL outputs. As such, FOD0 can be set to have an output frequency of 200MHz, with Channel Divider 0 set to divide by two. Alternatively, FOD0 can be set to 400MHz with a divider by four. Both configurations are valid. Both output drivers select Channel Divider 0, and are both set to LP-HCSL.
  - a. DIG CLK N DIV must be set to two to set the state machine clock properly. The state machine clock must be as close to 50MHz as possible without exceeding this frequency. Equation 9 shows the relationship between the digital state machine frequency, the frequency selected by the CH0 FOD SEL multiplexer, and the DIG CLK N DIV field. Write the DIG CLK N DIV field only while the device is in the low power state.
- 2. FOD0 can be used to generate the 25MHz LVCMOS clock, 200MHz / 8 = 25MHz. The REF CLK divider options are divides by two, four, or eight. Therefore, REF CLK DIV must be set to 3 for achieving a divide by 8.

$$F_{DIG} = \frac{F_{CH0\_FOD\_SEL}}{2 + DIG\_CLK\_N\_DIV}$$
 (9)

where F<sub>DIG</sub> is the digital state machine clock frequency and F<sub>CH0 FOD SEL</sub> is the frequency selected by the CH0 FOD SEL multiplexer

#### 9.2.4 Example: Changing Output Frequency

If the user wants to change the output from 100-MHz LP-HCSL on OUT0 and OUT1 to 24-MHz differential LVCMOS clocks on OUT0 and OUT1- with an additional LVCMOS clock on the REF CTRL pin, the value of the BAWFREQ OFFSET FIXEDLUT field for this example is 0x3701. The steps for changing the frequency are as follows:

- 1. Determine the BAW frequency of the device. This is critical for all following calculations. From Equation 4, if BAWFREQ OFFSET FIXEDLUT is 0x3701, then the BAW frequency of this device is approximately 2471.446441856.
- 2. Determine the channel divider settings and required FOD frequency. If the output frequency is 24 MHz, and the range of the FODs is from 100 MHz to 400 MHz, then a channel divider value of at least 5 is required to generate the output. As there is not a divide by 5 option, and REF CLK must also have a clock (see CH0 DIV, CH1 DIV, and REF CLK DIV), a divide by 8 is required. From here, 24 MHz times 8 yields an FOD output frequency of 192 MHz. If OUT1 were a different frequency, then using FOD1 can be required if both frequencies can not be generated by dividing down from the same FOD frequency.
- 3. Set the FOD divide values. Use Equation 1 to calculate the integer divide value FOD0 N DIV = floor(2471.446441856/192) = 12. From Equation 2, the numerator divide value FOD0 NUM =  $int(((2471.446441856/192) - 12) \times 2^{24}) = 14631693$
- 4. Write the desired settings to the device registers. This includes the divider settings listed above, as well as the output driver settings. Follow the procedure outlined in Figure 7-4:
  - a. Set PDN = 1.
  - b. Set FOD0 N DIV = 12 and FOD0 NUM = 14631693.
  - c. Set CH0 DIV, and REF CLK DIV to divide by 8 (by default, OUT1 CH SEL is set to select Channel Divider 0).
  - d. Set OUT0 FMT and OUT1 FMT to select Differential LVCMOS as the output format.
  - e. Set REF CTRL PIN FUNC to output REF CLK.
  - f. Set OTP\_AUTOLOAD\_DIS to 1 (disable the OTP Page 0 autoload feature).
  - g. Set DIG CLK N DIV = 2 to set the digital state machine clock to 48 MHz, based on Equation 9

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated



#### h. Set PDN = 0

The time required for the frequency change to take affect is typically on the order of 1 ms between issuing PDN = 0 and the output clocks starting at the desired frequency.

#### 9.2.5 Crosstalk

Performance degradation can occur in the LMK3H0102 due to crosstalk in the device when the outputs are operating at different frequencies. Table 9-1 displays the performance of the LMK3H0102 outputs for common LVCMOS frequencies. Contact TI for measurement of additional combinations for impact of crosstalk on output performance.

Table 9-1. LMK3H0102 LVCMOS Output Crosstalk (1)

| FOD0 Frequency<br>(MHz) | FOD1 Frequency<br>(MHz)s | OUT0 Frequency<br>(MHz) (2) | OUT1 Frequency<br>(MHz) (2) | Typical OUT0 RMS<br>Jitter (fs) (3) | Typical OUT1 RMS<br>Jitter (fs) (3) |
|-------------------------|--------------------------|-----------------------------|-----------------------------|-------------------------------------|-------------------------------------|
| 240                     | 250                      | 24                          | 25                          | 852                                 | 716                                 |
| 240                     | 270                      | 24                          | 27                          | 457                                 | 371                                 |
| 240                     | 200                      | 24                          | 50                          | 832                                 | 779                                 |
| 250                     | 240                      | 25                          | 24                          | 784                                 | 717                                 |
| 250                     | 270                      | 25                          | 27                          | 757                                 | 787                                 |
| 270                     | 240                      | 27                          | 24                          | 429                                 | 367                                 |
| 270                     | 250                      | 27                          | 25                          | 913                                 | 641                                 |
| 270                     | 200                      | 27                          | 50                          | 865                                 | 930                                 |
| 200                     | 240                      | 50                          | 24                          | 806                                 | 548                                 |
| 200                     | 270                      | 50                          | 27                          | 913                                 | 704                                 |


<sup>(1)</sup> Measured over 25°C to 105°C using differential LVCMOS output formats using VDD = VDDO x = 3.3V, no SSC.

<sup>(2)</sup> OUT0 and OUT1 are generated using FOD0 and FOD1, respectively.

<sup>(3)</sup> RMS Jitter measured over the 12kHz to 5MHz integration bandwidth.




#### 9.2.6 Application Curves



OUT0: 100 MHz LP-HCSL OUT1: 100 MHz LP-HCSL Temperature: 25 °C 12k – 20M RMS Jitter: 125 fs


Figure 9-3. 100-MHz LP-HCSL Output for PCle Application, Measured on OUT0



OUT1: 125 MHz LP-HCSL Temperature: 25 °C 12k – 20M RMS Jitter: 107 fs


Figure 9-4. 125-MHz LP-HCSL Output, Measured on OUT0





OUT0: 156.25 MHz LP-HCSL OUT1: 156.25 MHz LP-HCSL Temperature: 25 °C 12k – 20M RMS Jitter: 99 fs


Figure 9-5. 156.25-MHz LP-HCSL Output, Measured on OUT0



OUT1: 156.25 MHz LP-HCSL Temperature: 25 °C 12k – 20M RMS Jitter: 167 fs

Figure 9-6. 125-MHz LP-HCSL on OUT0 With 156.25-MHz LP-HCSL on OUT1





OUT0: 125 MHz LP-HCSL OUT1: 156.25 MHz LP-HCSL Temperature: 25 °C 12k – 20M RMS Jitter: 186 fs

Figure 9-7. 156.25-MHz LP-HCSL on OUT1 With 125 MHz-LP-HCSL on OUT0

#### 9.3 Power Supply Recommendations

#### 9.3.1 Power-Up Sequencing

The LMK3H0102 provides multiple power supply pins. Each power supply supports 1.8V, 2.5V, or 3.3V. Internal low-dropout regulators (LDO) source the internal blocks and allow each pin to be supplied with individual supply voltages. The VDD pin supplies the control pins, the serial interface, and the REF\_CTRL pin. Therefore, any pullup resistors must be connected to the same domain as VDD.

If an output is not used, connect the corresponding VDDO\_x rail to VDD. If the VDD and VDDO\_x rails are the same voltage, TI recommends connecting these together directly. If VDD and the VDDO\_x rails differ, VDD must ramp first, with VDDO x no more than 5ms after.

#### 9.3.2 Decoupling Power Supply Inputs

Do not tie VDD and VDDO pins to ground. Use a separate ferrite bead to isolate the VDD and the VDDO supplies. If OUT0 and OUT1 are different frequencies, a separate ferrite bead must be used for each VDDO supply. For each supply voltage pin, a 0.1-µF or 1-µF capacitor must be placed very close to the pin.

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated

#### 9.4 Layout

#### 9.4.1 Layout Guidelines

For this example, follow these guidelines:

- · Isolate outputs using a GND shield. Route all outputs as differential pairs.
- Isolate outputs to adjacent outputs when generating multiple frequencies.
- · Avoid impedance jumps in the fan-in and fan-out areas when possible.
- Use five vias to connect the thermal pad to a solid GND plane. Full-through vias are preferred.
- Place decoupling capacitors with small capacitance values very close to the supply pins. Place the
  decoupling capacitors on the same layer or on the bottom layer directly underneath the device. Larger values
  can be placed farther away. Ferrite beads are recommended to isolate the different output supplies and the
  VDD supply.
- Use multiple vias to connect wide supply traces to the respective power planes.

#### 9.4.2 Layout Example

Below are printed circuit board (PCB) layout examples that show the application of thermal design practices and a low-inductance ground connection between the device DAP and the PCB.




Figure 9-8. PCB Layout Example for LMK3H0102, Top Layer




Figure 9-9. PCB Layout Example for LMK3H0102, Bottom Layer



# 10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

#### **10.1 Documentation Support**

#### 10.1.1 Related Documentation

For documentation related to the evaluation module, refer to the *LMK3H0102EVM* user's guide.

For documentation related to the configuration details of LMK3H0102Axxx devices, refer to the LMK3H0102 Configuration Guide

## 10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

# 10.3 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 10.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

## 10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 10.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

#### 11 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| C | hanges from Revision C (October 2024) to Revision D (March 2025)   | Page   |
|---|--|--------|
| • | Added PCIe Gen 7   | 1      |
| • | Updated PCIe Gen 6 to PCIe Gen 7   | 1      |
| • | Updated the numbering format for tables, figures, and cross-references throughout the document                         | 1      |
| • | Added reference to LMK3H0102 Configuration Guide   | 1      |
| • | Updated PCIe compliance to Gen 7 throughout the document   | 1      |
| • | Added margin to the following specifications: LP-HCSL high level for 2.5V/3.3V from +/-5% to +/-10%,                   | LP-    |
|   | HCSL duty cycle from $49.9\%$ - $50.3\%$ for $100MHz$ / $48.8\%$ - $50.8\%$ for f ≤ $325MHz$ / $48.6\%$ - $51.8\%$ for |        |
|   | 325MHz < f ≤ 400MHz to 47% - 53% for all cases, LVDS duty cycle from 49% - 51.1% to 47% - 53%, L                       | .VDS   |
|   | 20% to 80% differential rise/fall time maximum increased by 5%, PSNR maximum limits increased by 5                     | 5%. No |
|   | SSC cycle-to-cycle maximum jitter reduced from 150ps to 20ps. Updated PADCAP_x to OUTx_SLEW_                           | _RATE  |
|   | for LVDS rise/fall time  | 5      |
|   |  |        |

Submit Document Feedback

www.ti.com

| •  | Updated image for LP-HCSL configuration during PCIe Test to reflect correct device name  | 14    |
|----|--|-------|
| •  | Added reference to LMK3H0102 Configuration Guide, updated units to latest standards, added PCIe Ger  | 1 7   |
|    | support  |       |
| •  | Clarified behavior for switching OTP pages in OTP Mode   |       |
| •  | Added clarification on requesting OTP configurations from TI   | 20    |
| •  | Updated <i>Programming Sequence</i> image to reflect OTP_AUTOLOAD_DIS = 1 instead of   | 0.4   |
|    | OTP_AUTOLOAD_DIS = 0   |       |
| •  | Corrected description of ADC_CLK_N_DIV to show 0x99 instead of 0x9B  |       |
|    | 0x0AA0   |       |
| •  | Updated default value of REF_CTRL_PIN_FUNC from 0x1 to 0x3. Updated default value of OUT0_EN from 0x0 to 0x1. Updated default value of OUT1_EN from 0x0 to 0x1 | om    |
| •  | Updated default value of OUT1_LPHSCL_AMP_SEL from 0x3 to 0x6. Removed extra period in the  |       |
|    | description of OUT_FMT_SRC_SEL. Added note that OTP_ID is 1 for the V18 configuration  | 37    |
| •  | Updated default value of R12 from 0x6800 to 0xE800. Updated default value of I2C_ADDR_LSB_SEL from 0x6800 to 0xE800.   |       |
|    | 0x0 to 0x1   |       |
| •  | Updated instances of REF_CLK to REF_CTRL to align with pin names   |       |
| •  | Changed REF_CLK frequency from 33MHz to 25MHz to match diagram   |       |
| •  | Updated instance of CHO_FOD_SEL to CH0_FOD_SEL. Updated REF_CLK to 25MHz in place of 33MH example calculation  |       |
|    | Changed "more far away" to "farther away"  |       |
|    | Added reference to LMK3H0102 Configuration Guide   |       |
|    | Added reference to LMK3H0102 Configuration Guide   |       |
|    |  |       |
| CI | hanges from Revision B (June 2024) to Revision C (October 2024)  | Page  |
| -  | Changed data sheet status from Advanced Information to Production Data   |       |
|    | Updated the number formatting for tables, figures, and cross-references throughout the document  |       |
| _  | opulated the number formatting for tables, figures, and cross-references throughout the document   | ····· |
|    |  |       |
| CI | hanges from Revision A (December 2023) to Revision B (June 2024)   | age   |
| •  | Updated the number formatting for tables, figures, and cross-references throughout the document  | 1     |
| -  |  |       |
| ۵. | hanna fann Barisian t (Namarka 2000) ta Barisia (Barisia 2000)   |       |
|    | · · · · · · · · · · · · · · · · · · ·  | Page  |
| •  | Updated the number formatting for tables, figures, and cross-references throughout the document  | - 1   |

# 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

RER0016A






## PACKAGE OUTLINE

# TQFN - 1.2 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.



Submit Document Feedback


Copyright © 2025 Texas Instruments Incorporated

# **EXAMPLE BOARD LAYOUT**

# RER0016A

## TQFN - 1.2 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)



This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
 Vias are optional depending on application, refer to device data sheet. It is recommended that vias under paste be filled, plugged or tented.




## **EXAMPLE STENCIL DESIGN**

# **RER0016A**

# TQFN - 1.2 mm max height

PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.




# 12.1 Tape and Reel Information



# TAPE DIMENSIONS K0 P1 B0 W Cavity A0


| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |
|    |   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



| Device                | Package<br>Type | Package<br>Drawing | Pins | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width W1<br>(mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|-----------------------|-----------------|--------------------|------|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| LMK3H0102V33RERR      | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102V18RERR      | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A001RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A006RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A014RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A015RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A016RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A018RERR     | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |
| LMK3H0102A01ERER<br>R | TQFN            | RER0016A           | 16   | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.1        | 8.0        | 12.0      | Q1               |





| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LMK3H0102V33RERR  | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102V18RERR  | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A001RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A006RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A014RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A015RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A016RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A018RERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |
| LMK3H0102A01ERERR | TQFN         | RER0016A        | 16   | 3000 | 346         | 346        | 33          |

For documentation related to the configuration details of LMK3H0102Axxx devices, refer to the LMK3H0102 Configuration Guide

www.ti.com

18-Jul-2025

#### **PACKAGING INFORMATION**

| Orderable part number | Status | Material type | Package   Pins  | Package qty   Carrier | RoHS | Lead finish/<br>Ball material | MSL rating/<br>Peak reflow | Op temp (°C) | Part marking |
|-----------------------|--------|---------------|-----------------|-----------------------|------|-------------------------------|----------------------------|--------------|--------------|
|                       | (1)    | (2)           |                 |                       | (3)  | (4)                           | (5)                        |              | (0)          |
| LMK3H0102A001RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA001       |
| LMK3H0102A001RERR.A   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA001       |
| LMK3H0102A001RERR.B   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |
| LMK3H0102A002RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA002       |
| LMK3H0102A006RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA006       |
| LMK3H0102A006RERR.A   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA006       |
| LMK3H0102A006RERR.B   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |
| LMK3H0102A014RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA014       |
| LMK3H0102A014RERR.A   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA014       |
| LMK3H0102A014RERR.B   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |
| LMK3H0102A015RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA015       |
| LMK3H0102A015RERR.A   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA015       |
| LMK3H0102A015RERR.B   | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |
| LMK3H0102A016RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA016       |
| LMK3H0102A018RERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA018       |
| LMK3H0102A01ERERR     | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HA01E       |
| LMK3H0102V18RERR      | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HV18        |
| LMK3H0102V18RERR.A    | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HV18        |
| LMK3H0102V18RERR.B    | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |
| LMK3H0102V33RERR      | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HV33        |
| LMK3H0102V33RERR.A    | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | Yes  | Call TI                       | Level-2-260C-1 YEAR        | -40 to 85    | 3HV33        |
| LMK3H0102V33RERR.B    | Active | Production    | TQFN (RER)   16 | 3000   LARGE T&R      | -    | Call TI                       | Call TI                    | -40 to 85    |              |

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

# PACKAGE OPTION ADDENDUM

www.ti.com 18-Jul-2025

(4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF LMK3H0102:

Automotive: LMK3H0102-Q1

NOTE: Qualified Version Definitions:

Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects



www.ti.com 14-Aug-2025

## TAPE AND REEL INFORMATION



# TAPE DIMENSIONS + K0 - P1 - B0 W Cavity - A0 -

| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

| Device            | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|-------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| LMK3H0102A001RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A002RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A006RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A014RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A015RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A016RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A018RERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102A01ERERR | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102V18RERR  | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |
| LMK3H0102V33RERR  | TQFN            | RER                | 16 | 3000 | 330.0                    | 12.4                     | 3.3        | 3.3        | 1.35       | 8.0        | 12.0      | Q1               |



www.ti.com 14-Aug-2025



\*All dimensions are nominal

| 7 til dilitionorono di o mominar |              |                 |      |      |             |            |             |
|----------------------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| Device                           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
| LMK3H0102A001RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A002RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A006RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A014RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A015RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A016RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A018RERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102A01ERERR                | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102V18RERR                 | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |
| LMK3H0102V33RERR                 | TQFN         | RER             | 16   | 3000 | 346.0       | 346.0      | 33.0        |

#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated