





LMX2582 SNAS680E - DECEMBER 2015 - REVISED AUGUST 2022

# LMX2582 High Performance, Wideband PLLatinum™ RF Synthesizer With Integrated **VCO**

#### 1 Features

- Output Frequency Range from 20 to 5500 MHz
- Industry Leading Phase Noise Performance
  - VCO Phase Noise: –144.5 dBc/Hz at 1-MHz Offset for 1.8-GHz Output
  - Normalized PLL Noise Floor: –231 dBc/Hz
  - Normalized PLL Flicker Noise: –126 dBc/Hz
  - 47-fs RMS Jitter (12 kHz to 20 MHz) for 1.8 **GHz Output**
- Input Clock Frequency Up to 1400 MHz
- Phase Detector Frequency Up to 200 MHz, and Up to 400 MHz in Integer-N Mode
- Supports Fractional-N and Integer-N Modes
- **Dual Differential Outputs**
- Innovative Solution to Reduce Spurs
- Programmable Phase Adjustment
- Programmable Charge Pump Current
- Programmable Output Power Level
- SPI or uWire (4-Wire Serial Interface)
- Single Power Supply Operation: 3.3 V

# 2 Applications

- Test and Measurement Equipment
- Cellular Base-Station
- Microwave Backhaul
- High-Performance Clock Source for High-Speed **Data Converters**
- Software Defined Radio

### 3 Description

The LMX2582 device is a low-noise, wideband RF PLL with integrated VCO that supports a frequency range from 20 MHz to 5.5 GHz. The device supports both fractional-N and integer-N modes, with a 32-bit fractional divider allowing fine frequency selection. Integrated noise of 47 fs for 1.8-GHz output makes it an ideal low-noise source. Combining best-in-class PLL and integrated VCO noise with integrated LDOs, this device removes the need for multiple discrete devices in high performance systems.


The device accepts input frequencies up to 1.4 GHz, which combined with frequency dividers and programmable low noise multiplier allows flexible frequency planning. The additional programmable low-noise multiplier lets users mitigate the impact of integer boundary spurs. In Fractional-N mode, the device can adjust the output phase by a 32-bit resolution. For applications that need fast frequency changes, the device supports a fast calibration option which takes less than 25 µs.

This performance is achieved by using single 3.3-V supply. It supports 2 flexible differential outputs that can be configured as single-ended outputs as well. Users can choose to program one output from the VCO and the second from the channel divider. When not being used, each output can be muted separately.

#### Package Information (1)

PART NUMBER	DESCRIPTION	BODY SIZE (NOM)
LMX2582RHAT LMX2582RHAR	VQFN (40)	6.00 mm × 6.00 mm

For all available packages, see the orderable addendum at (1) the end of the data sheet.



Simplified Schematic



•	Table of	Contents	
1 Features	1	7.5 Programming	18
2 Applications		7.6 Register Maps	
3 Description	1		
4 Revision History	2		
5 Pin Configuration and Functions	4		
6.1 Absolute Maximum Ratings	6	8.4 Layout	38
		9 Device and Documentation Support	39
6.3 Recommended Operating Conditions	6		
6.4 Thermal Information	6		
6.5 Electrical Characteristics	<mark>7</mark>	9.3 Receiving Notification of Documentation Upda	tes <mark>39</mark>
6.6 Timing Requirements	8		
6.7 Typical Characteristics	10	9.5 Trademarks	39
		9.6 Electrostatic Discharge Caution	39
7.1 Overview	13	9.7 Glossary	39
		10 Mechanical, Packaging, and Orderable	
7.3 Functional Description	13	Information	39
4 Revision History Changes from Revision D (October 2017) t	o Revisior	n E (August 2022)	Page
			<u></u>
Description18 Application and Implementation25Revision History28.1 Application Information25Pin Configuration and Functions48.2 Typical Application36Specifications68.3 Power Supply Recommendations376.1 Absolute Maximum Ratings68.4 Layout366.2 ESD Ratings69 Device and Documentation Support366.3 Recommended Operating Conditions69.1 Device Support366.4 Thermal Information69.2 Documentation Support366.5 Electrical Characteristics79.3 Receiving Notification of Documentation Updates366.6 Timing Requirements89.4 Support Resources366.7 Typical Characteristics109.5 Trademarks36Detailed Description139.6 Electrostatic Discharge Caution367.1 Overview139.7 Glossary397.2 Functional Block Diagram139.7 Glossary397.3 Functional Description1310 Mechanical, Packaging, and Orderable Information36Information3617			
<ul> <li>Unanged the position of register field, PFD</li> </ul>	CIL, IN TO	egister K13	18

# 

Added additional information for register MUXOUT\_HDRV in Table 7-44
 Added a new register field, VTUNE\_ADJ, in Table 7-25
 Changed the register R0 FCAL\_LPFD\_ADJ configurable values
 Changed the register R13 PFD\_CTL position

Added the R68, R69 and R70 register field descriptions.
 Added External Loop Filter section.

Moved the Power Supply Recommendations and Layout sections to the Application and Implementation section.

# Changes from Revision C (July 2017) to Revision D (October 2017)

# Changes from Revision B (February 2017) to Revision C (July 2017)

• Changed Channel Divider Setting as a Function of the Desired Output Frequency table......15

# Changes from Revision A (December 2015) to Revision B (February 2017)

Submit Document Feedback

Copyright © 2022 Texas Instruments Incorporated

Page

### www.ti.com

•	Removed charge pump current TYP range '0 to 12' and split range into MIN (0) and MAX (12) columns	
•	Added 10 kHz test conditions for the PN <sub>open loop</sub> parameter	7
•	Added HD2, HD3, and Spur_PFD parameters to the <i>Electrical Characteristics</i> table	
•	Changed the high level input voltage minimum value of from: 1.8 to: 1.4	
•	Moved all typical values in the Timing Requirements table to minimum column	
•	Changed text from: the rising edge of the LE signal to: the rising edge of the last CLK signal	8
•	Changed text from: the shift registers to an actual counter to: the shift registers to a register bank	8
•	Changed high input value from: 700 to: 200	14
•	Changed high input value from: 1400 to: 400	
•	Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN to: Fpd × PLL_N_PRE / PLL_DEN / [Changed minimum output frequency step from: Fpd / PLL_DEN frequency step from: Fpd / P	
	Added content to the Voltage Controlled Oscillator section	15
	Changed text from: output dividers to: channel dividers	
	Changed Channel Divider Setting as a Function of the Desired Output Frequency table	
	Changed output frequency from: 3600 to: 3550	
	Changed VCO frequency from: 7200 to: 7100	
	Changed Phase shift (degrees) from: 360 × MASH_SEED / PLL_N_DEN / [Channel divider value] to: 36	
	MASH_SEED x PLL_N_PRE / PLL_N_DEN / [Channel divider value]"	
	Changed register 7, 8, 19, 23, 32, 33, 34, 46, and 64 descriptions	
	Added registers 20, 22, 25, 59, and 61	
	Added registers 2, 4, and 62 to <i>Register Table</i>	18
	Changed register 38 in <i>Register Table</i>	
	Changed register descriptions from: Program to default to: Program to Register Map default values	
	Added R2 Register Field Descriptions	
	Added R4 Register Field Descriptions	
	Added R62 Register Field Descriptions	
	Updated content in the <i>Decreasing Lock Time</i> section	34
	Changed typical application image	
	Changed charge pump value from: 4.8 to: 20	
	Changed R2 value from: 0.068 to: 68	
_	Ondriged 112 value from: 0.000 to. 00	01
CI	hanges from Revision * (December 2015) to Revision A (December 2015)	Page
•	Changed device status from product preview to production data, and released full data sheet	1



# **5 Pin Configuration and Functions**




Figure 5-1. RHA Package 40-Pin VQFN Top View

Table 5-1. Pin Functions

PIN NAME NO.		TVDE	DESCRIPTION	
		TYPE	DESCRIPTION	
CE	1	Input	Chip Enable input. Active high powers on the device.	
CPout	12	Output	Charge pump output. Recommend connecting C1 of loop filter close to pin.	
CSB	24	Input	SPI chip select bar or uWire latch enable (abbreviated as LE in Figure 6-1). High impedance CMOS input. 1.8 to 3.3-V logic.	
DAP	GND	Ground	RFout ground.	
GND	2, 4, 6, 13, 14, 25, 31, 34, 39, 40	Ground	VCO ground.	
MUXout 20 Outp		Output	Programmable with register MUXOUT_SEL to be readback SDO or lock detect indicator (active high).	
NC	5, 28, 30, 32	_	Not connected.	
OSCinP	8	Input	Differential reference input clock (+). High input impedance. Requires connecting series capacitor (0.1-μF recommended).	
OSCinM	9	Input	Differential reference input clock (–). High input impedance. Requires connecting series capacitor (0.1-µF recommended).	
RFoutAM	22	Output	Differential output A (–). This output requires a pullup component for proper biasing. A 50-Ω resistor or inductor may be used. Place as close to output as possible.	
RFoutAP	23	Output	Differential output A (+). This output requires a pullup component for proper biasing. A 50-Ω resistor or inductor may be used. Place as close to output as possible.	
RFoutBP	19	Output	Differential output B (+). This output requires a pullup component for proper biasing. A 50-Ω resistor or inductor may be used. Place as close to output as possible.	
RFoutBM	18	Output	Differential output B (–). This output requires a pullup component for proper biasing. A 50-Ω resistor or inductor may be used. Place as close to output as possible.	
SCK	16	Input	SPI or uWire clock (abbreviated as CLK in Figure 6-1). High impedance CMOS input. 1.8 to 3.3-V logic.	
SDI	17	Input	SPI or uWire data (abbreviated as DATA in Figure 6-1). High impedance CMOS input. 1.8 to 3.3-V logic.	

Submit Document Feedback

Copyright © 2022 Texas Instruments Incorporated

**Table 5-1. Pin Functions (continued)** 

PIN		TYPE	DESCRIPTION	
NAME	NO.	ITPE	DESCRIPTION	
VbiasVARAC	33	Bypass	VCO varactor internal voltage, access for bypass. Requires connecting 10-μF capacitor to VCO ground.	
VbiasVCO	3	Bypass	VCO bias internal voltage, access for bypass. Requires connecting 10-μF capacitor to VCO ground. Place close to pin.	
VbiasVCO2	27	Bypass	VCO bias internal voltage, access for bypass. Requires connecting 1-μF capacitor to VCO ground.	
V <sub>CC</sub> BUF	21	Supply	Output buffer supply. Requires connecting 0.1-µF capacitor to RFout ground.	
V <sub>CC</sub> CP	11	Supply	Charge pump supply. Recommend connecting 0.1-µF capacitor to charge pump ground.	
V <sub>CC</sub> DIG	7	Supply	Digital supply. Recommend connecting 0.1-μF capacitor to digital ground.	
V <sub>CC</sub> MASH	15	Supply	Digital supply. Recommend connecting 0.1-μF and 10-μF capacitor to digital ground.	
V <sub>CC</sub> VCO	37	Supply	VCO supply. Recommend connecting 0.1-μF and 10-μF capacitor to ground.	
V <sub>CC</sub> VCO2	26	Supply	VCO supply. Recommend connecting 0.1-μF and 10-μF capacitor to VCO ground.	
VrefVCO	36	Bypass	VCO supply internal voltage, access for bypass. Requires connecting 10-μF capacitor to ground.	
VrefVCO2	29	Bypass	VCO supply internal voltage, access for bypass. Requires connecting 10-μF capacitor to VCO ground.	
VregIN	10	Bypass	Input reference path internal voltage, access for bypass. Requires connecting 1-μF capacitor to ground. Place close to pin.	
VregVCO	38	Bypass	VCO supply internal voltage, access for bypass. Requires connecting 1-μF capacito ground.	
Vtune	35	Input	VCO tuning voltage input. This signal should be kept away from noise sources. Connect a 3.3-nF or more capacitor to VCO ground.	



## **6 Specifications**

# **6.1 Absolute Maximum Ratings**

over operating free-air temperature range (unless otherwise noted)(1)

		MIN	MAX	UNIT
V <sub>CC</sub>	Power supply voltage	-0.3	3.6	V
V <sub>IN</sub>	Input voltage to pins other than V <sub>CC</sub> pins	-0.3	V <sub>CC</sub> + 0.3	V
V <sub>OSCin</sub>	Voltage on OSCin (pin 8 and pin 9)	≤1.8 with V <sub>CC</sub> Applied	≤1 with V <sub>CC</sub> = 0	Vpp
TL	Lead temperature (solder 4 s)		260	°C
TJ	Junction temperature	-40	150	°C
T <sub>stg</sub>	Storage temperature	-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 6.2 ESD Ratings

			VALUE	UNIT
		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2500	
V <sub>(ESD)</sub>	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±750	V
		Machine model (MM) ESD stress voltage	±250	

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 500-V HBM is possible with the necessary precautions. Pins listed as ±2500 V may actually have higher performance.

### **6.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V <sub>CC</sub>	Power supply voltage	3.15		3.45	V
T <sub>A</sub>	Ambient temperature	-40		85	°C
TJ	Junction temperature			125	°C

### 6.4 Thermal Information

		LMX2582	
	THERMAL METRIC <sup>(1)</sup>	RHA (VQFN)	UNIT
		40 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	30.5	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	15.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	5.4	°C/W
ΨЈТ	Junction-to-top characterization parameter	0.2	°C/W
ΨЈВ	Junction-to-board characterization parameter	5.3	°C/W
R <sub>0</sub> JC(bot)	Junction-to-case (bottom) thermal resistance	0.9	°C/W

For more information about traditional and new thermal metrics, see the <u>Semiconductor and IC Package Thermal Metrics</u> application report.

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 250-V CDM is possible with the necessary precautions. Pins listed as ±1250 V may actually have higher performance.

# **6.5 Electrical Characteristics**

 $3.15~V \le V_{CC} \le 3.45~V, -40^{\circ}C \le T_{A} \le 85^{\circ}C.$  Typical values are at  $V_{CC} = 3.3~V, 25^{\circ}C$  (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
POWER SUI	PPLY				
V <sub>CC</sub>	Supply voltage		3.3		V
Icc	Supply current	Single 5.4-GHz, 0-dBm output <sup>(1)</sup>	250		mA
I <sub>PD</sub>	Powerdown current		3.7		mA
OUTPUT CH	IARACTERISTICS				
F <sub>out</sub>	Output frequency		20	5500	MHz
P <sub>out</sub>	Typical high output power	Output = 3 GHz, $50-\Omega$ pullup, single-ended <sup>(2)</sup>	8		dBm
INPUT SIGN	IAL PATH				
REFin	Reference input frequency		5	1400	MHz
REFv	Reference input voltage	AC-coupled, differential <sup>(3)</sup>	0.2	2	Vppd
MULin	Input signal path multiplier input frequency		40	70	MHz
MULout	Input signal path multiplier output frequency		180	250	MHz
PHASE DET	ECTOR AND CHARGE PUMP				
DDE	Discount data stanto		5	200	MHz
PDF	Phase detector frequency	Extended range mode <sup>(4)</sup>	0.25	400	MHz
CPI	Charge pump current	Programmable	0	12	mA
PLL PHASE	NOISE				
PLL_flicker_Nor	Normalized PLL Flicker Noise <sup>(5)</sup>		-126		dBc/H
PLL_FOM	Normalized PLL Noise Floor (PLL Figure of Merit) <sup>(5)</sup>		-231		dBc/H
VCO					
ΔT <sub>CL</sub>	Allowable temperature drift <sup>(6)</sup>	VCO not being recalibrated		125	°C
		10 kHz	-105.7		
		100 kHz	-129.8		1
	Output = 900 MHz	1 MHz	-150.4		
		10 MHz	-160.6		
		100 MHz	-161.1		
		10 kHz	-99.5		
		100 kHz	-123.6		
PN <sub>open loop</sub>	Output = 1.8 GHz	1 MHz	-144.5		dBc/H
		10 MHz	-157.2		
		100 MHz	-157.7		
		10 kHz	-89.7		
		100 kHz	-114.0		1
	Output = 5.5 GHz	1 MHz	-134.9		
		10 MHz	-151.3		
		100 MHz	-153.3		
HD2	2nd Order Harmonic Distortion <sup>(7)</sup>	Testing output A, output at 5 GHz, output	-27		dBc
HD3	3rd Order Harmonic Distortion <sup>(7)</sup>	power level at 8.5-dBm, single-ended output, other end terminated with 50 $\Omega$ .	-25		dBc
DIGITAL INT	ERFACE				

### $3.15~\textrm{V} \leq \textrm{V}_{\textrm{CC}} \leq 3.45~\textrm{V}, -40^{\circ}\textrm{C} \leq \textrm{T}_{\textrm{A}} \leq 85^{\circ}\textrm{C}.$

Typical values are at V<sub>CC</sub> = 3.3 V, 25°C (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V <sub>IH</sub>	High level input voltage		1.4		V <sub>CC</sub>	V
V <sub>IL</sub>	Low level input voltage		0		0.4	V
I <sub>IH</sub>	High level input current		-25		25	μA
I <sub>IL</sub>	Low level input current		-25		25	μA
V <sub>OH</sub>	High level output voltage	Load/Source Current of –350 μA		V <sub>CC</sub> – 0.4		V
V <sub>OL</sub>	Low level output voltage	Load/Sink Current of 500 μA		0.4		V
SPIW	Highest SPI write speed			75		MHz
SPIR	SPI read speed			50		MHz
Spur_PFD	Phase frequency detector spur	PFD = 20 MHz, output = 5.4 GHz		-93		dBc

- (1) For typical total current consumption of 250 mA: 100-MHz input frequency, OSCin doubler bypassed, pre-R divider bypassed, multiplier bypassed, post-R divider bypassed, 100-MHz phase detector frequency, 0.468-mA charge pump current, channel divider off, one output on, 5.4GHz output frequency, 50-Ω output pullup, 0-dBm output power (differential). See the Application and Implementation section for more information.
- (2) For a typical high output power for a single-ended output, with 50-Ω pullup on both M and P side, register OUTx\_POW = 63. Un-used side terminated with 50-Ω load.
- (3) There is internal voltage biasing so the OSCinM and OSCinP pins must always be AC-coupled (capacitor in series). Vppd is differential peak-to-peak voltage swing. If there is a differential signal (two are negative polarity of each other), the total swing is one subtracted by the other, each should be 0.1 to 1-Vppd. If there is a single-ended signal, it can have 0.2 to 2 Vppd. See the *Application and Implementation* section for more information.
- (4) To use phase detector frequencies lower than 5-MHz set register FCAL\_LPFD\_ADJ = 3. To use phase detector frequencies higher than 200 MHz, you must be in integer mode, set register PFD\_CTL = 3 (to use single PFD mode), set FCAL\_HPFD\_ADJ = 3. For more information, see the *Detailed Description* section.
- (5) The PLL noise contribution is measured using a clean reference and a wide loop bandwidth and is composed into flicker and flat components. PLL\_flat = PLL\_FOM + 20 × log(Fvco/Fpd) + 10 × log(Fpd / 1Hz). PLL\_flicker (offset) = PLL\_flicker\_Norm + 20 × log(Fvco / 1GHz) 10 × log(offset / 10kHz). Once these two components are found, the total PLL noise can be calculated as PLL\_Noise = 10 × log(10<sup>PLL\_Flat / 10</sup> + 10<sup>PLL\_flicker / 10</sup>).
- (6) Not tested in production. Ensured by characterization. Allowable temperature drift refers to programming the device at an initial temperature and allowing this temperature to drift without reprogramming the device, and still have the device stay in lock. This change could be up or down in temperature and the specification does not apply to temperatures that go outside the recommended operating temperatures of the device.
- (7) This parameter is verified by characterization on evaluation board, not tested in production.

### 6.6 Timing Requirements

 $3.15 \text{ V} \le \text{V}_{CC} \le 3.45 \text{ V}, -40^{\circ}\text{C} \le \text{T}_{A} \le 85^{\circ}\text{C}$ , except as specified. Typical values are at  $\text{V}_{CC} = 3.3 \text{ V}, \text{T}_{A} = 25^{\circ}\text{C}$ 

			MIN	TYP	MAX	UNIT
MICROV	VIRE TIMING					
tES	Clock to enable low time		5			ns
tCS	Data to clock setup time		2			ns
tCH	Data to clock hold time		2			ns
tCWH	Clock pulse width high	See Figure 6-1	5			ns
tCWL	Clock pulse width low		5			ns
tCES	Enable to clock setup time		5			ns
tEWH	Enable pulse width high		2			ns




Figure 6-1. Serial Data Input Timing Diagram


There are several considerations for programming:

- A slew rate of at least 30 V/µs is recommended for the CLK, DATA, LE
- The DATA is clocked into a shift register on each rising edge of the CLK signal. On the rising edge of the last CLK signal, the data is sent from the shift registers to a register bank
- · The LE pin may be held high after programming and clock pulses are ignored
- When CLK and DATA lines are shared between devices, TI recommends diving down the voltage to the CLK, DATA, and LE pins closer to the minimum voltage. This provides better noise immunity
- If the CLK and DATA lines are toggled while the VCO is in lock, as is sometimes the case when these lines are shared with other parts, the phase noise may be degraded during the time of this programming




### **6.7 Typical Characteristics**

T<sub>A</sub> = 25°C (unless otherwise noted)



### 6.7 Typical Characteristics (continued)


T<sub>A</sub> = 25°C (unless otherwise noted)





# **6.7 Typical Characteristics (continued)**

T<sub>A</sub> = 25°C (unless otherwise noted)



## 7 Detailed Description

#### 7.1 Overview

The LMX2582 is a high performance wideband synthesizer (PLL with integrated VCO). The output frequency range is from 20 MHz to 5.5 GHz. The VCO core covers an octave from 3.55 to 7.1 GHz. The output channel divider covers the frequency range from 20 MHz to the low bound of the VCO core.


The input signal frequency has a wide range from 5 to 1400 MHz. Following the input, there is an programmable OSCin doubler, a pre-R divider (previous to multiplier), a multiplier, and then a post-R divider (after multiplier) for flexible frequency planning between the input (OSCin) and the phase detector.

The phase detector (PFD) can take frequencies from 5 to 200 MHz, but also has extended modes down to 0.25 MHz and up to 400 MHz. The phase-lock loop (PLL) contains a Sigma-Delta modulator (1st to 4th order) for fractional N-divider values. The fractional denominator is programmable to 32-bit long, allowing a very fine resolution of frequency step. There is a phase adjust feature that allows shifting of the output phase in relation to the input (OSCin) by a fraction of the size of the fractional denominator.

The output power is programmable and can be designed for high power at a specific frequency by the pullup component at the output pin.

The digital logic is a standard 4-wire SPI or uWire interface and is 1.8-V and 3.3-V compatible.

### 7.2 Functional Block Diagram



#### 7.3 Functional Description

#### 7.3.1 Input Signal

An input signal is required for the PLL to lock. The input signal is also used for the VCO calibration, so a proper signal needs to be applied before the start of programming. The input signal goes to the OSCinP and OSCinM pins of the device (there is internal biasing which requires AC-coupling caps in series before the pin). This is a differential buffer so the total swing is the OSCinM signal subtracted by the OSCinP signal. Both differential signals and single-ended signal can be used. Below is an example of the max signal level in each mode. It is important to have proper termination and matching on both sides (see *Application and Implementation*).




Figure 7-1. Differential vs. Single-Ended Mode

#### 7.3.2 Input Signal Path

The input signal path contains the components between the input (OSCin) buffer and the phase detector. The best PLL noise floor is achieved with a 200-MHz input signal for the highest dual-phase detector frequency. To address a wide range of applications, the input signal path contains the below components for flexible configuration before the phase detector. Each component can be bypassed. See Table 7-1 for usage boundaries if engaging a component.

- OSCin doubler: This is low noise frequency doubler which can be used to multiply input frequencies by two. The doubler uses both the rising and falling edge of the input signal so the input signal must have 50% duty cycle if enabling the doubler. The best PLL noise floor is achieved with 200-MHz PFD, thus the doubler is useful if, for example, a very low-noise, 100-MHz input signal is available instead.
- Pre-R divider: This is a frequency divider capable of very high frequency inputs. Use this to divide any input frequency up to 1400-MHz, and then the post-R divider if lower frequencies are needed.
- Multiplier: This is a programmable, low noise multiplier. In combination with the Pre-R and Post-R dividers, the multiplier offers the flexibility to set a PFD away from frequencies that may create critical integer boundary spurs with the VCO and output frequencies. See the *Application and Implementation* section for an example. The user should not use the doubler while using the low noise programmable multiplier.
- Post-R divider: Use this divider to divide down to frequencies below 5 MHz in extended PFD mode.

	I abio i ii bo	anaanoo ioi inpati at	ii Goiiiboiig	
	IN	PUT	OU	TPUT
	LOW (MHz)	HIGH (MHz)	LOW (MHz)	HIGH (MHz)
Input signal	5	1400		
OSCin doubler	5	200	10	400
Pre-R divider	10	1400	5	700
Multiplier	40	70	180	250
Post-R divider	5	250	0.25	125
PFD	0.25	400		

**Table 7-1. Boundaries for Input Path Components** 

### 7.3.3 PLL Phase Detector and Charge Pump

The PLL phase detector, also known as phase frequency detector (PFD), compares the outputs of the post-R divider and N divider and generates a correction current with the charge pump corresponding to the phase error until the two signals are aligned in phase (the PLL is locked). The charge pump output goes through external components (loop filter) which turns the correction current pulses into a DC voltage applied to the tuning voltage (Vtune) of the VCO. The charge pump gain level is programmable and allow to modify the loop bandwidth of the PLL.

The default architecture is a dual-loop PFD which can operate between 5 to 200 MHz. To use it in extended range mode the PFD has to be configured differently:

- Extended low phase detector frequency mode: For frequencies between 250 kHz and 5 MHz, low PFD mode can be activated (FCAL\_LPFD\_ADJ = 3). PLL\_N\_PRE also needs to be set to 4.
- Extended high phase detector frequency mode: For frequencies between 200 and 400 MHz, high PFD mode can be activated (FCAL\_HPFD\_ADJ = 3). The PFD also has to be set to single-loop PFD mode (PFD\_CTL = 3). This mode only works if using integer-N, and PLL noise floor will be about 6-dB higher than in dual-loop PFD mode.

### 7.3.4 N Divider and Fractional Circuitry

The N divider (12 bits) includes a multi-stage noise shaping (MASH) sigma-delta modulator with programmable order from 1st to 4th order, which performs fractional compensation and can achieve any fractional denominator from 1 to  $(2^{32} - 1)$ . Using programmable registers, PLL\_N is the integer portion and PLL\_NUM / PLL\_DEN is the fractional portion, thus the total N divider value is determined by PLL\_N + PLL\_NUM / PLL\_DEN. This allows the output frequency to be a fractional multiplication of the phase detector frequency. The higher the denominator the finer the resolution step of the output. There is a N divider prescaler (PLL\_N\_PRE) between the VCO and

Submit Document Feedback

Copyright © 2022 Texas Instruments Incorporated

the N divider which performs a division of 2 or 4. 2 is selected typically for higher performance in fractional mode and 4 may be desirable for lower power operation and when N is approaching max value.

Minimum output frequency step = Fpd × PLL\_N\_PRE / PLL\_DEN / [Channel divider value]

Typically, higher modulator order pushes the noise out in frequency and may be filtered out with the PLL. However, several tradeoff needs to be made. Table 7-2 shows the suggested minimum N value while in fractional mode as a function of the sigma-delta modulator order. It also describe the recommended register setting for the PFD delay (register PFD DLY SEL).

<b>Table 7-2.</b>	MASH	Order	and N	Divider
-------------------	------	-------	-------	---------

	INTEGER-N	1st ORDER	2nd ORDER	3rd ORDER	4th ORDER
Minimum N divider (low bound)	9	11	16	18	30
PFD delay recommended setting (PFD_DLY_SEL)	1	1	2	2	8

#### 7.3.5 Voltage Controlled Oscillator

The voltage controlled oscillator (VCO) is fully integrated. The frequency range of the VCO is from 3.55 to 7.1 GHz so it covers one octave. Channel dividers allow the generation of all other lower frequencies. The VCO-doubler allow the generation of all other higher frequencies. The output frequency of the VCO is inverse proportional to the DC voltage present at the tuning voltage point on pin Vtune. The tuning range is 0 V to 2.5 V. 0 V generates the maximum frequency and 2.5 V generates the minimum frequency. This VCO requires a calibration procedure for each frequency selected to lock on. Each VCO calibration will force the tuning voltage to mid value and calibrate the VCO circuit. Any frequency setting in fast calibration occurs in the range of Vtune pin 0 V to 2.5 V. The VCO is designed to remained locked over the entire temperature range the device can support. Table 7-3 shows the VCO gain as a function of frequency.

Table 7-3. Typical kVCO

VCO FREQUENCY (MHz)	kVCO (MHz/V)
3700	28
4200	30
4700	33
5200	36
5700	41
6200	47
6800	51

#### 7.3.6 VCO Calibration

The VCO calibration is responsible of setting the VCO circuit to the target frequency. The frequency calibration routine is activated any time that the R0 register is programmed with the FCAL\_EN = 1. A valid input (OSCin) signal to the device must present before the VCO calibration begins. To see how to reduce the calibration time, refer to the *Application and Implementation* section.

#### 7.3.7 Channel Divider




Figure 7-2. Channel Divider Diagram

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback

To go below the VCO lower bound, the channel divider must be used. The channel divider consists of three programmable dividers controlled by the registers CHDIV\_SEG1, CHDIV\_SEG2, CHDIV\_SEG3. The Multiplexer (programmed with register CHDIV\_SEG\_SEL) selects which divider is included in the path. The minimum division is 2 while the maximum division is 192. Un-used dividers can be powered down to save current consumption. The entire channel divider can be powered down with register CHDIV\_EN = 0 or selectively setting registers CHDIV\_SEG1\_EN = 0, CHDIV\_SEG2\_EN = 0, CHDIV\_SEG3\_EN = 0. Unused buffers may also be powered down with registers CHDIV\_DISTA\_EN and CHDIV\_DIST\_EN. There are restrictions on the maximum VCO frequency when channel divider is engaged.

OUTPUT FRE	QUENCY (MHz)		CHDIV SEGMENT	Г	TOTAL	VCO FREQU	JENCY (MHz)
MIN	MAX	SEG1	SEG2	SEG3	DIVISION	MIN	MAX
1775	3550	2	1	1	2	3550	7100
1184	2200	3	1	1	3	3552	6600
888	1184	2	2	1	4	3552	4736
592	888	3	2	1	6	3552	5328
444	592	2	4	1	8	3552	4736
296	444	2	6	1	12	3552	5328
222	296	2	8	1	16	3552	4736
148	222	3	8	1	24	3552	5328
111	148	2	8	2	32	3552	4736
99	111	3	6	2	36	3564	3996
74	99	3	8	2	48	3552	4752
56	74	2	8	4	64	3584	4736
37	56	2	8	6	96	3552	5376
28	37	2	8	8	128	3584	4736
20	20 28 3 8		8	192	3840	5376	

### 7.3.8 Output Distribution




Figure 7-3. Output Distribution Diagram

For each output A or B, there is a mux which select the VCO output directly or the channel divider output. Before these selection MUX there are several buffers in the distribution path which can be configured depending on the route selected. By disabling unused buffers, unwanted signals can be isolated and unneeded current consumption can be eliminated.

### 7.3.9 Output Buffer

Each output buffer (A and B) have programmable gain with register OUTA\_POW and OUTB\_POW. The RF output buffer configuration is open-collector and requires an external pullup from RFout pin to  $V_{CC}$ . There are two pullup options that can be used with either resistor or inductor. Refer to the *Application and Implementation* section for design considerations.

- 1. Resistor pullup: placing a  $50-\Omega$  resistor pullup matches the output impedance to  $50-\Omega$ . However, maximum output power is limited. Output buffer current settings should be set to a value before output power is saturated (output power increases less for every step increase in output current value).
- 2. Inductor pullup: placing an inductor pullup creates a resonance at the frequency of interest. This offers higher output power for the same current and higher maximum output power. However, the output impedance is higher and additional matching may be required..

### 7.3.10 Phase Adjust

In fractional mode, the phase relationship between the output and the input can be changed with very fine resolution. Every time MASH\_SEED register is written, it will trigger a phase shift of the amount described in Equation 1. The seed value should be less then the fractional-N denominator register PLL\_N\_DEN. The actual phase shift can be obtained with the following equation:

#### 7.4 Device Functional Modes

#### 7.4.1 Power Down

Power up and down can be achieved using the CE pin (logic HIGH or LOW voltage) or the POWERDOWN register bit (0 or 1). When the device comes out of the powered-down state, either by pulling back CE pin HIGH (if it was powered down by CE pin) or by resuming the POWERDOWN bit to 0 (if it was powered down by register write), it is required that register R0 be programmed again to re-calibrate the device.

#### 7.4.2 Lock Detect

The MUXout pin can be configured to output a signal that gives an indication for the PLL being locked. If lock detect is enabled (LD\_EN = 1) and the MUXout pin is configured as lock detect output (MUXOUT\_SEL = 1), when the device is locked, the MUXout pin output is a logic HIGH voltage, and when the device is unlocked, MUXout output is a logic LOW voltage.

#### 7.4.3 Register Readback

The MUXout pin can be programmed (MUXOUT\_SEL = 0) to use register readback serial data output. To read back a certain register value, use the following steps:

- 1. Set the R/W bit to 1; the data field contents are ignored.
- 2. Program this register to the device, readback serial data will be output starting at the 9th clock.




Figure 7-4. Register Readback Timing Diagram

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback

### 7.5 Programming

The programming using 24-bit shift registers. The shift register consists of a R/W bit (MSB), followed by a 7-bit address field and a 16-bit data field. For the R/W (bit 23), 1 is read and 0 is write. The address field ADDRESS (bits 22:16) is used to decode the internal register address. The remaining 16 bits form the data field DATA (bits 15:0). While CSB is low, serial data is clocked into the shift register upon the rising edge of clock (data is programmed MSB first). When CSB goes high, data is transferred from the data field into the selected register bank.

#### 7.5.1 Recommended Initial Power on Programming Sequence

When the device is first powered up, the device needs to be initialized and the ordering of this programming is very important. After this sequence is completed, the device should be running and locked to the proper frequency.

- 1. Apply power to the device and ensure the V<sub>CC</sub> pins are at the proper levels
- 2. Ensure that a valid reference is applied to the OSCin pin
- 3. Soft reset the device (write R0[1] = 1)
- 4. Program the remaining registers
- 5. Frequency calibrate (write R0[3] = 1)

### 7.5.2 Recommended Sequence for Changing Frequencies

The recommended sequence for changing frequencies is as follows:

- 1. Set the new N divider value (write R38[12:1])
- 2. Set the new PLL numerator (R45 and R44) and denominator (R41 and R40)
- 3. Frequency calibrate (write R0[3] = 1)

## 7.6 Register Maps

### 7.6.1 LMX2582 Register Map - Default Values

Figure 7-5. Register Table

		Figure 7-5. Register Table																						
REG	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	R/ W		,	ADDF	RESS	[6:0]										DAT	A [15:0]							
0	R/ W	0	0	0	0	0	0	0	0	0	LD_EN	0	0	0	1		_HPFD ADJ		_LPFD_ ADJ	ACA L_E N	FCAL_EN	MUXO UT_S EL	RES ET	POWE RDOW N
1	R/ W	0	0	0	0	0	0	1	0	0	0	0	1	0	0	0	0	0	0	0	1	CA	L_CLK	_DIV
2	R/ W	0	0	0	0	0	1	0	0	0	0	0	0	1	0	1	0	0	0	0	0	0	0	0
4	R/ W	0	0	0	0	1	0	0			F	ACAL_CN	ИР_DLY	,			0	1	0	0	0	0	1	1
7	R/ W	0	0	0	0	1	1	1	0	0	1	0	1	0	0	0	1	0	1	1	0	0	1	0
8	R/ W	0	0	0	1	0	0	0	0	0	VCO_ID AC_OV R	1	0	VCO_ CAPC TRL_ OVR	0	0	1	0	0	0	0	1	0	0
9	R/ W	0	0	0	1	0	0	1	0	0	0	0	OSC _2X	0	REF_E N	1	0	0	0	0	0	0	1	0
10	R/ W	0	0	0	1	0	1	0	0	0	0	1			MULT			1	0	1	1	0	0	0
11	R/ W	0	0	0	1	0	1	1	0	0	0	0				PLI	R				1	0	0	0
12	R/ W	0	0	0	1	1	0	0	0	1	1	1						PL	L_R_PRE					
13	R/ W	0	0	0	1	1	0	1	0	CP_E N	0	0	0	0	0	0	0	0	0	0	0	0	PFI	D_CTL
14	R/ W	0	0	0	1	1	1	0	0	0	0	0			CP_IDN					CP_II	UP		CP_IC	COARSE
19	R/ W	0	0	1	0	0	1	1	0	0	0	0					VCO_ID	AC				1	0	1
20	R/ W	0	0	1	0	1	0	0	0	0	0	0	0	0	0				ACAL_	_vco_i	IDAC_STR1			

Submit Document Feedback

Copyright © 2022 Texas Instruments Incorporated

www.ti.com

	Figure 7-5. Register Table (continued)																							
REG	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	R/ W			ADDI	RESS	6:0]										DAT	A [15:0]							
22	R/ W	0	0	1	0	1	1	0	0	0	1	0	0	0	1	1				VCO_	_CAPCTRL			
23	R/ W	0	0	1	0	1	1	1	1	FCAL _VC O_S EL_S TRT	V	CO_SEL		VCO_ SEL_ FORC E	0	0	0	1	0	0	0	0	1	0
24	R/ W	0	0	1	1	0	0	0	0	0	0	0	0	1	0	1	0	0	0	0	1	0	0	1
25	R/ W	0	0	1	1	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
28	R/ W	0	0	1	1	1	0	0	0	0	1	0	1	0	0	1	0	0	1	0	0	1	0	0
29	R/ W	0	0	1	1	1	0	1	0	0	0	0	0	0	0	0	1	0	0	0	0	1	0	0
30	R/ W	0	0	1	1	1	1	0	0	0	0 0 0 0 MASH 0 0 VTUNE_ADJ 1 1 0 O CONTROL OF THE O								0	1	0	0		
31	R/ W	0	0	1	1	1	1	1	0	0	0	0	0	VCO_ DIST B_PD	VCO_D ISTA_P D	0	CHDIV _DIST _PD	0	0	0	0	0	0	1
32	R/ W	0	1	0	0	0	0	0	0	0	1	0	0	0	0	1	0	0	0	0	1	0	1	0
33	R/ W	0	1	0	0	0	0	1	0	0	1	0	1	0	1	0	0	0	0	0	1	0	1	0
34	R/ W	0	1	0	0	0	1	0	1	1	0	0	0	0	1	1	1	1	CHDIV _EN	0	1	0	1	0
35	R/ W	0	1	0	0	0	1	1	0									1						
36	R/ W	0	1	0	0	1	0	0	0	0	0	0	CHDI V_DI STB_ EN	CHDI V_DIS TA_E N	0	0	0	CHE	DIV_SEG_	SEL		CHDIV_S	SEG3	
37	R/ W	0	1	0	0	1	0	1	0	1	0	PLL_N _PRE	0	0	0	0	0	0	0	0	0	0	0	0
38	R/ W	0	1	0	0	1	1	0	0	0	0						PL	L_N						0
39	R/ W	0	1	0	0	1	1	1	1	0			PFD_	DLY			0	0	0	0	0	1	0	0
40	R/ W	0	1	0	1	0	0	0								PLL_D	EN[31:16	5]						
41	R/ W	0	1	0	1	0	0	1								PLL_[	DEN[15:0	]						
42	R/ W	0	1	0	1	0	1	0							M	IASH_S	SEED[31:	16]						
43	R/ W	0	1	0	1	0	1	1							N	/ASH_	SEED[15	:0]						
44	R/ W	0	1	0	1	1	0	0								PLL_N	UM[31:16	6]						
45	R/ W	0	1	0	1	1	0	1								PLL_N	NUM[15:0	]						
46	R/ W	0	1	0	1	1	1	0	0	0 0 OUTA_POW OUTB OUT 1 0 0 MASH_ORDER PD A_P D														
47	R/ W	0	1	0	1	1	1	1	0	0	0	OUTA	_MUX	0	0	0	1	1			OUTB_	POW		
48	R/ W	0	1	1	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1	1	1	OUT	B_MUX	
59	R/ W	0	1	1	1	0	1	1	0	0	0	0	0	0	0	0	0	0	MUXO UT_HD RV	0	0	0	0	0
61	R/ W	0	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	LD_TY PE
62	R/ W	0	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	<u> </u>	1		1		1						1	1	L	Ĭ	1	1					1		L



Figure 7-5. Register Table (continued)

													J		•			,						
REG	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	R/ W			ADDF	RESS	[6:0]										DATA	A [15:0]							
64	R/ W	1	0	0	0	0	0	0	0	0	0	0	0	0 ACAL FCA AJUMP_SIZE 1 FJUN FAST L_FA ST					FJUMP_	SIZE				
68	R	1	0	0	0	1	0	0	0	0	0	0	0	rb_LD	VTUNE	0	rb_	vco_	SEL	0	0	0	0	0
69	R	1	0	0	0	1	0	1	0	0	0	0	0	0	0	0 rb_VCO_CAPCTRL								
70	R	1	0	0	0	1	1	0	0	0	0	0	0	0	0 0 rb_VCO_DACISET									

# 7.6.1.1 Register Descriptions

Table 7-5, R0 Register Field Descriptions

Table 7-5. R0 Register Field Descriptions											
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION							
15:14		R/W		Program to Register Map default values							
13	LD_EN	R/W	1	Lock detect enable 1: enable 0: disable							
12:9		R/W		Program to Register Map default values							
8:7	FCAL_HPFD_ADJ	R/W	0	Used for when PFD freq is high 3: PFD > 200 MHz 2: PFD > 150 MHz 1: PFD > 100 MHz 0: not used							
6:5	FCAL_LPFD_ADJ	R/W	0	Used for when PFD freq is low 3: PFD < 2.5 MHz 2: 2.5 MHz ≤ PFD < 5 MHz 1: 5 MHz ≤ PFD < 10 MHz 0: PFD ≥ 10 MHz							
4	ACAL_EN	R/W	1	Enable amplitude calibration  1: enable (calibration algorithm will set VCO amplitude. For manual mode set register VCO_IDAC_OVR=1, and then set the VCO amplitude by register VCO_IDAC)  0: disable							
3	FCAL_EN	R/W	1	Enable frequency calibration 1: enable (writing 1 to this register triggers the calibration sequence) 0: disable							
2	MUXOUT_SEL	R/W	1	Signal at MUXOUT pin 1: Lock Detect (3.3 V if locked, 0 V if unlocked) 0: Readback (3.3-V digital output)							
1	RESET	R/W	0	Reset Write with a value of 1 to reset device (this register will self-switch back to 0)							
0	POWERDOWN	R/W	0	Powerdown whole device 1: power down 0: power up							

Table 7-6. R1 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:3		R/W		Program to Register Map default values
2:0	CAL_CLK_DIV	R/W		Divides down the OSCin signal for calibration clock Calibration Clock = OSCin / 2^CAL_CLK_DIV Set this value so that calibration clock is less than but as close to 200MHz as possible if fast calibration time is desired.

Table 7-7. R2 Register Field Descriptions

_					
	BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
	15:0		R/W		Program to Register Map default values

Table 7-8. R4 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:8	ACAL_CMP_DLY	R/W	25	VCO amplitude calibration delay. Lowering this value can speed calibration time. The guideline for this register is 2 x [ACAL_CMP_DLY value] x [calibration clock period] > 200ns. As described in CAL_CLK_DIV, the calibration clock is defined as OSCin / 2^CAL_CLK_DIV. For example, with the fastest calibration clock of 200MHz (OSCin=200MHz and CAL_CLK_DIV=0), the period is 5ns. So ACAL_CMP_DLY should be > 20. With the same derivation, an example of a OSCin=100MHz, ACAL_CMP_DLY should be > 10. This register is left at a default value of 25 if there is no need to shorten calibration time.
7:0		R/W		Program to Register Map default values

### Table 7-9. R7 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

### Table 7-10. R8 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:14		R/W		Program to Register Map default values
13	VCO_IDAC_OVR	R/W	0	This is the override bit for VCO amplitude (or IDAC value). When this is enabled, the VCO amplitude calibration function (ACAL_EN) is not used. VCO_IDAC register can be programmed to set the amplitude. Keep the VCO_IDAC value within 250 and 450.
12:11		R/W		Program to Register Map default values
10	VCO_CAPCTRL_OVR	R/W	0	This is the override bit for VCO capacitor bank code (or CAPCTRL value). When this is enabled, the VCO frequency calibration function (FCAL_EN) is not used. the VCO_CAPCTRL register can be programmed to set the VCO frequency within the selected VCO core. The VCO core is selected by setting VCO_SEL_FORCE=1 and then selecting the core with VCO_SEL=1,2,3,4,5,6, or 7
9:0		R/W		Program to Register Map default values

### Table 7-11. R9 Register Field Descriptions

	Table 7-11. Na Register Field Descriptions								
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION					
15:12		R/W		Program to Register Map default values					
11	OSC_2X	R/W	0	Reference path doubler 1: enable 0: disable					
10		R/W		Program to Register Map default values					
9	REF_EN	R/W	1	Enable reference path 1: enable 0: disable					
8:0		R/W		Program to Register Map default values					

#### Table 7-12. R10 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION			
15:12		R/W		Program to Register Map default values			
11:7	MULT	R/W		Input signal path multiplier (input range from 40 - 70 MHz, output range from 180 - 250 MHz)			



### **Table 7-12. R10 Register Field Descriptions (continued)**

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
6:0		R/W		Program to Register Map default values

### Table 7-13. R11 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:12		R/W		Program to Register Map default values
11:4	PLL_R	R/W	1	R divider after multiplier and before PFD
3:0		R/W		Program to Register Map default values

# Table 7-14. R12 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:12		R/W		Program to Register Map default values
11:0	PLL_R_PRE	R/W	1	R divider after OSCin doubler and before multiplier

### Table 7-15. R13 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15		R/W		Program to Register Map default values
14	CP_EN	R/W	1	Enable charge pump 1: enable 0: disable
13:2		R/W		Program to Register Map default values
1:0	PFD_CTL	R/W	0	PFD mode 0: Dual PFD (default) 3: Single PFD (ONLY use if PFD freq is higher than 200MHz)

### Table 7-16. R14 Register Field Descriptions

	10.010		ricia Descriptions	
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:12		R/W		Program to Register Map default values
11:7	CP_IDN	R/W	3	Charge pump current (DN) – must equal to charge pump current (UP). Can activate any combination of bits.   <b< td=""></b<>
6:2	CP_IUP	R/W	3	Charge pump current (UP) – must equal to charge pump current (DN). Can activate any combination of bits.   <b< td=""></b<>
1:0	CP_ICOARSE	R/W	1	Charge pump gain multiplier - multiplies charge pump current by a given factor: 3: multiply by 2.5 2: multiply by 1.5 1: multiply by 2 0: no multiplication For optimal accuracy of the lock detect circuit over temperature, it is recommended that only set this register to either 0 or 2.

# Table 7-17. R19 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:12		R/W		Program to Register Map default values

### Table 7-17. R19 Register Field Descriptions (continued)

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION				
11:3	VCO_IDAC	R/W	300	This is the VCO amplitude (or IDAC value). When VCO_IDAC is overridden with VCO_IDAC_OVR=1, VCO amplitude calibration function (ACAL_EN) is not used. VCO_IDAC register can be programmed to set the amplitude. VCO_IDAC value must be kept within 250 and 450.				
2:0		R/W		Program to Register Map default values				

# Table 7-18. R20 Register Field Descriptions

			•	•
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:9		R/W		Program to Register Map default values
8:0	ACAL_VCO_IDAC_STRT	R/W	300	This register is used to aid the VCO amplitude calibration function (ACAL_EN). By default the amplitude calibration function searches from the low end of VCO_IDAC until it reaches the target value. Like the VCO_IDAC, this must be kept within 250 and 450. This can be set to a value closer to the target value, then the amplitude calibration time can be shortened typically final VCO_IDAC is somewhere around 300.

# Table 7-19. R22 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:8		R/W		Program to Register Map default values
7:0	VCO_CAPCTRL	R/W	0	This is the VCO capacitor bank code (or CAPCTRL value). When VCO_CAPCTRL is overridden with VCO_CAPCTRL_OVR=1, VCO frequency calibration function (FCAL_EN) is not used. VCO_CAPCTRL register can be programmed to set the frequency in that core. VCO_SEL_FORCE=1 has to be set and VCO_SEL to select the VCO core, then CAPCTRL values between 0 to 183 will produce frequencies within this core (0 being the highest frequency and 183 the lowest).

### Table 7-20. R23 Register Field Descriptions

	10.0.0		Ticia Descriptions	
BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15		R/W		Program to Register Map default values
14	FCAL_VCO_SEL_STRT	R/W	0	This is a register that aids the frequency calibration function. When this is enabled, a VCO core can be selected for the frequency calibration to start at, set by register VCO_SEL. By default the frequency calibration starts from VCO core 7 and works its way down. If you want for example to lock to a frequency in VCO core 1, you can set VCO_SEL to 2, so the calibration will start at VCO core 2 and end at target frequency at VCO core 1 faster.
13:11	VCO_SEL	R/W	1	This is the register used to select VCO cores. It works for VCO_CAPCTRL when VCO_CAPCTRL_OVR=1 and VCO_SEL_FORCE=1. It also aids the frequency calibration function with FCAL_VCO_SEL_STRT.
10	VCO_SEL_FORCE	R/W	0	This register works to force selection of VCO cores. If VCO_CAPTRL_OVR=1 and this register is enabled, you can select the VCO core to use with VCO_SEL.
9:0		R/W		Program to Register Map default values

# Table 7-21. R24 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to default

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



### Table 7-22. R25 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

## Table 7-23. R28 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

### Table 7-24. R29 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

### Table 7-25. R30 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:11		R/W		Program to Register Map default values
10	MASH_DITHER	R/W	0	MASH dithering: toggle on/off to randomize
9:8		R/W		Program to Register Map default values
7:6	VTUNE_ADJ	R/W		Change this register field according to the VCO frequency 0: f <sub>VCO</sub> < 6500 MHz 3: f <sub>VCO</sub> ≥ 6500 MHz
5:0		R/W		Program to Register Map default values

### Table 7-26. R31 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:11		R/W		Program to Register Map default values
10	VCO_DISTB_PD	R/W	1	Power down buffer between VCO and output B 1: power down 0: power up
9	VCO_DISTA_PD	R/W	0	Power down buffer between VCO and output A 1: power down 0: power up
8		R/W		Program to Register Map default values
7	CHDIV_DIST_PD	R/W	0	Power down buffer between VCO and channel divider
6:0		R/W		Program to Register Map default values

# Table 7-27. R32 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

# Table 7-28. R33 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

### Table 7-29. R34 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:6		R/W		Program to Register Map default values
5	CHDIV_EN	R/W		Enable entire channel divider  1: enable 0: power down
4:0		R/W		Program to Register Map default values

### Table 7-30. R35 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:13		R/W		Program to Register Map default values

Table 7-30. R35 Register Field Descriptions (continued)

DIT		TYPE	DEFAULT	Descriptions (continued)
BIT	FIELD	ITPE	DEFAULI	DESCRIPTION
12:9	CHDIV_SEG2	R/W	1	Channel divider segment 2 8: divide-by-8 4: divide-by-6 2: divide-by-4 1: divide-by-2 0: PD
8	CHDIV_SEG3_EN	R/W	0	Channel divider segment 3 1: enable 0: power down (power down if not needed)
7	CHDIV_SEG2_EN	R/W	0	Channel divider segment 2 1: enable 0: power down (power down if not needed)
6:3		R/W		Program to Register Map default values
2	CHDIV_SEG1	R/W	1	Channel divider segment 1 1: divide-by-3 0: divide-by-2
1	CHDIV_SEG1_EN	R/W	0	Channel divider segment 1 1: enable 0: power down (power down if not needed)
0		R/W		Program to Register Map default values

### Table 7-31. R36 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:12		R/W		Program to Register Map default values
11	CHDIV_DISTB_EN	R/W	0	Enable buffer between channel divider and output B 1: enable 0: disable
10	CHDIV_DISTA_EN	R/W	1	Enable buffer between channel divider and output A 1: enable 0: disable
9:7		R/W		Program to Register Map default values
6:4	CHDIV_SEG_SEL	R/W	1	Channel divider segment select 4: includes channel divider segment 1,2 and 3 2: includes channel divider segment 1 and 2 1: includes channel divider segment 1 0: PD
3:0	CHDIV_SEG3	R/W	1	Channel divider segment 3 8: divide-by-8 4: divide-by-6 2: divide-by-4 1: divide-by-2 0: PD

# Table 7-32. R37 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:13		R/W		Program to Register Map default values
12	PLL_N_PRE	R/W		N-divider pre-scalar 1: divide-by-4 0: divide-by-2
11:0		R/W		Program to Register Map default values

### Table 7-33. R38 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:13		R/W		Program to Register Map default values
12:1	PLL_N	R/W	27	Integer part of N-divider

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



### Table 7-33. R38 Register Field Descriptions (continued)

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
0		R/W		Program to Register Map default values

### Table 7-34. R39 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:14		R/W		Program to Register Map default values
13:8	PFD_DLY	R/W	2	PFD Delay 32: Not used 16: 16 clock cycle delay 8: 12 clock cycle delay 4: 8 clock cycle delay 2: 6 clock cycle delay 1: 4 clock cycle delay
7:0		R/W		Program to Register Map default values

# Table 7-35. R40 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	PLL_DEN[31:16]	R/W	1000	Denominator MSB of N-divider fraction

### Table 7-36. R41 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	PLL_DEN[15:0]	R/W	1000	Denominator LSB of N-divider fraction

### Table 7-37. R42 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	MASH_SEED[31:16]	R/W	0	MASH seed MSB

### Table 7-38. R43 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	MASH_SEED[15:0]	R/W	0	MASH seed LSB

### Table 7-39. R44 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	PLL_NUM[31:16]	R/W	0	Numerator MSB of N-divider fraction

### Table 7-40. R45 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0	PLL_NUM[15:0]	R/W	0	Numerator LSB of N-divider fraction

### Table 7-41. R46 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15		R/W		Program to Register Map default values
13:8	OUTA_POW	R/W	15	Output buffer A power increase power from 0 to 31 extra boost from 48 to 63
7	OUTB_PD	R/W	1	Output buffer B power down 1: power down 0: power up
6	OUTA_PD	R/W	0	Output buffer A power down 1: power down 0: power up
5:3		R/W		Program to Register Map default values

Table 7-41. R46 Register Field Descriptions (continued)

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
2:0	MASH_ORDER	R/W		Sigma-delta modulator order 4: fourth order 3: third order 2: second order 1: first order 0: integer mode

### Table 7-42. R47 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:13		R/W		Program to Register Map default values
12:11	OUTA_MUX	R/W	0	Selects signal to the output buffer 2,3: reserved 1: Selects output from VCO 0: Selects the channel divider output
10:6		R/W		Program to Register Map default values
5:0	OUTB_POW	R/W	0	Output buffer B power increase power from 0 to 31 extra boost from 48 to 63

## Table 7-43. R48 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:2		R/W		Program to Register Map default values
1:0	ОИТВ_МИХ	R/W		Selects signal to the output buffer 2,3: reserved 1: Selects output from VCO 0: Selects the channel divider output

### Table 7-44. R59 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:6		R/W		Program to Register Map default values
5	MUXOUT_HDRV	R/W	0	This bit enables higher current output (approximately 3 mA) at MUXOUT pin if value is 1.
4:0		R/W		Program to Register Map default values

### Table 7-45. R61 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:1		R/W		Program to Register Map default values
0	LD_TYPE	R/W	1	To use lock detect, set MUXOUT_SEL=1. Use this register to select type of lock detect:  0: Calibration status detect (this indicates if the auto-calibration process has completed successfully and will output from MUXout pin a logic HIGH when successful). 1: vtune detect (this checks if vtune is in the expected range of voltages and outputs from MUXout pin a logic HIGH if device is locked and LOW if unlocked).

# Table 7-46. R62 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:0		R/W		Program to Register Map default values

### Table 7-47. R64 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
15:10		R/W		Program to Register Map default values

Product Folder Links: LMX2582

Copyright © 2022 Texas Instruments Incorporated



Table 7-47. R64 Register Field Descriptions (continued)

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
9	ACAL_FAST	R/W	0	Enable fast amplitude calibration 1: enable 0: disable
8	FCAL_FAST	R/W	0	Enable fast frequency calibration 1: enable 0: disable
7:5	AJUMP_SIZE	R/W	3	When ACAL_FAST=1, use this register to select the jump increment
4		R/W		Program to Register Map default values
3:0	FJUMP_SIZE	R/W	15	When FCAL_FAST=1, use this register to select the jump increment

### Table 7-48. R68 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
10:9	rb_LD_VTUNE	R	-	Readback of Vtune detect (LD_TYPE = 1). 0: Unlocked 1: Invalid 2: Locked 3: Unlocked
7:5	rb_VCO_SEL	R	_	Reads back the actual VCO that the calibration has selected.  1: VCO1  2: VCO2  7: VCO7

# Table 7-49. R69 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
7:0	rb_VCO_CAPCTRL	R	_	Reads back the actual CAPCTRL value that the VCO calibration has chosen.

# Table 7-50. R70 Register Field Descriptions

BIT	FIELD	TYPE	DEFAULT	DESCRIPTION
8:0	rb_VCO_DACISET	R		Reads back the actual DACISET value that the VCO calibration has chosen.

## 8 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### **8.1 Application Information**

### 8.1.1 Optimization of Spurs

### 8.1.1.1 Understanding Spurs by Offsets

The first step in optimizing spurs is to be able to identify them by offset. Figure 8-1 gives a good example that can be used to isolate the following spur types.




Figure 8-1. Spur Offset Frequency Example

Based on Figure 8-1, the most common spurs can be calculated from the frequencies. Note that the % is the modulus operator and is meant to mean the difference to the closest integer multiple. Some examples of how to use this operator are: 36 % 11 = 3, 1000.1 % 50 = 0.1, and 5023.7 % 122.88 = 14.38. Applying this concept, the spurs at various offsets can be identified from Figure 8-1.

**Table 8-1. Spur Definition Table** 

SPUR TYPE	OFFSET	OFFSET IN Figure 8-1	COMMENTS	
OSCin	fosc	40 MHz	This spur occurs at harmonics of the OSCin frequency.	
Fpd	f <sub>PD</sub>	120 MHz	The phase detector spur has many possible mechanisms and occurs at multiples of the phase detector frequency.	
f <sub>OUT</sub> % f <sub>OSC</sub>	f <sub>OUT</sub> % f <sub>OSC</sub>	606.25 % 40 = 6.25 MHz	This spur is caused by mixing between the output and input frequencies.	
f <sub>VCO</sub> % f <sub>OSC</sub>	f <sub>VCO</sub> % f <sub>OSC</sub>	4850 % 40 = 10 MHz	This spur is caused by mixing between the VCO and input frequencies.	
f <sub>VCO</sub> % f <sub>PD</sub>	f <sub>VCO</sub> % f <sub>PD</sub>	4850 % 120 = 50 MHz	This spur would be the same offset as the integer boundary spur if PLL_N_PRE=1, but can be different if this value is greater than one.	
Integer Boundary	f <sub>PD</sub> *(Fnum%Fden)/ Fden)	120 × (5%24)/24 = 25 MHz	This is a single spur	
Primary Fractional	f <sub>PD</sub> / Fden	120 / 24 = 5 MHz	The primary fractional	

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



**Table 8-1. Spur Definition Table (continued)** 

SPUR TYPE	OFFSET	OFFSET IN Figure 8-1	COMMENTS
Sub-Fractional	f <sub>PD</sub> / Fden / k k=2,3, or 6	First Order Modulator: None 2nd Order Modulator: 120/24/2 = 2.5 MHz 3rd Order Modulator: 120/24/6 = 0.83333 MHz 4th Order Modulator: 120/24/12 = 0.416666 MHz	To Calculate k:  1st Order Modulator: k=1  2nd Order Modulator: k=1 if Fden is odd, k=2 if Fden is even  3rd Order Modulator: k=1 if Fden not divisible by 2 or 3, k=2 if Fden divisible by 2 not 3, k=3 if Fden divisible by 3 but not 2, Fden = 6 if Fden divisible by 2 and 3  4th Order Modulator: k=1 if Fden not divisible by 2 or 3. k=3 if Fden divisible by 3 but not 2, k=4 if Fden divisible by 2 but not 3, k=12 if Fden divisible by 2 and 3  Sub-Fractional Spurs exist if k>1

In the case that two different spur types occur at the same offset, either name would be correct. Some may name this by the more dominant cause, while others would simply name by choosing the name that is near the top of Table 8-1.

### 8.1.1.2 Spur Mitigation Techniques

Once the spur is identified and understood, there will likely be a desire to try to minimize them. Spurs and Mitigation Techniques gives some common methods.

**Spurs and Mitigation Techniques** 

SPUR TYPE	WAYS TO REDUCE	TRADE-OFF
OSCin	Use PLL_N_PRE = 2     Use an OSCin signal with low amplitude and high slew rate (like LVDS).	
Phase Detector	<ol> <li>Decrease PFD_DLY</li> <li>To pin 11, use a series ferrite bead and a shunt 0.1-μF capacitor.</li> </ol>	
f <sub>OUT</sub> % f <sub>OSC</sub>	Use an OSCin signal with low amplitude and high slew rate (like LVDS)	
f <sub>VCO</sub> % f <sub>OSC</sub>	<ol> <li>To pin 7, use a series ferrite bead and a shunt 0.1-µF capacitor.</li> <li>Increase the offset of this spur by shifting the VCO frequency</li> <li>If multiple VCO frequencies are possible that yield the same spur offset, choose the higher VCO frequency.</li> </ol>	
f <sub>VCO</sub> % f <sub>PD</sub>	Avoid this spur by shifting the phase detector frequency (with the programmable input multiplier or R divider) or shifting the VCO frequency. This spur is better at higher VCO frequency.	
Integer Boundary	<ol> <li>Methods for PLL Dominated Spurs</li> <li>Avoid the worst case VCO frequencies if possible.</li> <li>Strategically choose which VCO core to use if possible.</li> <li>Ensure good slew rate and signal integrity at the OSCin pin</li> <li>Reduce the loop bandwidth or add more filter poles for out of band spurs</li> <li>Experiment with modulator order and PFD_DLY</li> </ol>	Reducing the loop bandwidth may degrade the total integrated noise if the bandwidth is too narrow.
	<ol> <li>Methods for VCO Dominated Spurs</li> <li>Avoid the worst case VCO frequencies if possible.</li> <li>Reduce Phase Detector Frequency</li> <li>Ensure good slew rate and signal integrity at the OSCin pin</li> <li>Make the impedance looking outwards from the OSCin pin close to 50 Ω.</li> </ol>	Reducing the phase detector may degrade the phase noise and also reduce the capacitance at the Vtune pin.

Submit Document Feedback

Product Folder Links: LMX2582

Spurs and Mitigation Techniques (continued)

SPUR TYPE	WAYS TO REDUCE	TRADE-OFF
Primary Fractional	<ol> <li>Decrease Loop Bandwidth</li> <li>Change Modulator Order</li> <li>Use Larger Unequivalent Fractions</li> </ol>	Decreasing the loop bandwidth too much may degrade in-band phase noise. Also, larger unequivalent fractions only sometimes work
Sub-Fractional	<ol> <li>Use Dithering</li> <li>Use MASH seed</li> <li>Use Larger Equivalent Fractions</li> <li>Use Larger Unequivalent Fractions</li> <li>Reduce Modulator Order</li> <li>Eliminate factors of 2 or 3 in denominator (see AN-1879 Fractional N Frequency Synthesis (SNAA062)</li> </ol>	Dithering and larger fractions may increase phase noise. MASH_SEED can be set between values 0 and Fden, which changes the sub-fractional spur behavior. This is a deterministic relationship and there will be one seed value that will give best result for this spur.

### 8.1.2 Configuring the Input Signal Path

The input path is considered the portion of the device between the OSCin pin and the phase detector, which includes the input buffer, R dividers, and programmable multipliers. The way that these are configured can have a large impact on phase noise and fractional spurs.

### 8.1.2.1 Input Signal Noise Scaling

The input signal noise scales by 20 × log(output frequency / input signal frequency), so always check this to see if the noise of the input signal scaled to the output frequency is close to the PLL in-band noise level. When that happens, the input signal noise is the dominant noise source, not the PLL noise floor.




Figure 8-2. Phase Noise of 5.4-GHz Output With Low-Noise Input Signal




Figure 8-3. Phase Noise of 5.4-GHz Output With High-Noise Input Signal

## 8.1.3 Input Pin Configuration

The OSCinM and OSCinP can be used to support both a single-ended or differential clock. In either configuration, the termination on both sides should match for best common-mode noise rejection. The slew rate and signal integrity of this signal can have an impact on both the phase noise and fractional spurs. Standard clocking types, LVDS, LVPECL, HCSL, and CMOS can all be used.

#### 8.1.4 Using the OSCin Doubler

The lowest PLL flat noise is achieved with a low-noise 200-MHz input signal. If only a low-noise input signal with lower frequency is available (for example a 100-MHz source), you can use the low noise OSCin doubler to attain 200-MHz phase detector frequency. Because PLL\_flat = PLL\_FOM +  $20 \times \log(\text{Fvco/Fpd}) + 10 \times \log(\text{Fpd} / 1\text{Hz})$ , doubling Fpd theoretically gets –6 dB from the  $20 \times \log(\text{Fvco/Fpd})$  component, +3 dB from the  $10 \times \log(\text{Fpd} / 1\text{Hz})$  component, and cumulatively a –3-dB improvement.




Figure 8-4. 100-MHz Input With OSCin Doubler

#### 8.1.5 Using the Input Signal Path Components

The ideal input is a low-noise, 200-MHz (or multiples of it) signal and 200-MHz phase detector frequency (highest dual PFD frequency). However, if spur mechanisms are understood, certain combinations of the R-divider and Multiplier can help. Refer to the *Optimization of Spurs* section for understanding spur types and their mechanisms first, then try this section for these specific spurs.

### 8.1.5.1 Moving Phase Detector Frequency

Engaging the multiplier in the reference path allows more flexibility in setting the PFD frequency. One example use case of this is if Fvco % Fpd is the dominant spur. This method can move the PFD frequency and thus the Fvco % Fpd.

Example: Fvco = 3720.12 MHz, Fosc = 300 MHz, Pre-R divider = 5, Fpd = 60 MHz, Fvco%Fosc = 120.12 MHz (Far out), Fvco%Fpd = 120 kHz (dominant). There is a Fvco%Fpd spur at 120 kHz (refer to Figure 8-5).




Figure 8-5. Fvco % Fpd Spur

Then second case, using divider and multiplier, is Fpd = 53.57 MHz away from 120-kHz spur. Fvco = 3720.12MHz, Fosc = 300MHz, Pre-R divider = 7, Multiplier = 5, Post-R divider = 4, Fpd = 53.57 MHz, Fvco%Fosc = 120.12 MHz (Far out). Fvco % Fpd = 23.79 MHz (far out). There is a 20-dB reduction for the Fvco % Fpd spur at 120 kHz (refer to Figure 8-6).




Figure 8-6. Moving Away From Fvco % Fpd Spur

#### 8.1.5.2 Multiplying and Dividing by the Same Value

Although it may not seem like the first thing to try, the Fvco%Fosc and Fout%Fosc spur can sometimes be improved engaging the OSC\_2X bit and then dividing by 2. Although this gives the same phase detector frequency, the spur can be improved.

# 8.1.6 Designing for Output Power

If there is a desired frequency for highest power, use an inductor pullup and design for the value so that the resonance is at that frequency. Use the formula SRF =  $1 / (2\pi \times \text{sqrt}[L \times C])$ .

Example: C = 1.4 pF (characteristic). If maximum power is targeted at 1 GHz, L = 18 nH. If maximum power is targeted at 3.3 GHz, L = 1.6 nH




Figure 8-7. Output Power vs Pullup Type

#### **8.1.7 Current Consumption Management**

The starting point is the typical total current consumption of 250 mA: 100-MHz input frequency, OSCin doubler bypassed, Pre-R divider bypassed, multiplier bypassed, post-R divider bypassed, 100-MHz phase detector frequency, 0.468-mA charge pump current, channel divider off, one output on, 5400-MHz output frequency,  $50-\Omega$  output pullup, 0-dBm output power (differential). To understand current consumption changes due to engaging different functional blocks , refer to Table 8-2.

Copyright © 2022 Texas Instruments Incorporated



**Table 8-2. Typical Current Consumption Impact By Function** 

ACTION	STEPS	PROGRAMMING	INCREASE IN CURRENT (mA)
Use input signal path	Enable OSCin doubler	OSC_2X = 1	7
	Enable multiplier	MULT = 3,4,5, or 6	10
Add an output	Route VCO to output B	VCO_DISTB_PD = 0	8
	Enable output B buffer	OUTB_PD = 0	54
Increase output power from 0 to +10dBm (differential)	Set highest output buffer current	OUTA_POW = 63	53
Use channel divider	Route channel divider to output	CHDIV_DISTA_EN = 1	5
	Enable channel divider	CHDIV_EN = 1	18
	Enable chdiv_seg1	CHDIV_SEG1_EN = 1	2
	Enable chdiv_seg2	CHDIV_SEG2_EN = 1	5
	Enable chdiv_seg3	CHDIV_SEG3_EN = 1	5

#### 8.1.8 Decreasing Lock Time

A calibration time of 590 µs typically to lock to 7-GHz VCO can be achieved with default settings as specified in the *Electrical Characteristics* table. There are several registers that can be programmed to speed up this time. Lock time consists of the calibration time (time required to calibrate the VCO to the correct frequency range) plus the analog settling time (time lock the PLL in phase and frequency). For fast calibration set registers FCAL FAST = 1 and ACAL FAST = 1. Also set the calibration clock frequency [input reference frequency] / 2^CAL CLK DIV) to 200 MHz. The 20-us range lock time can be achieved if the amplitude comparator delay is low, set by register ACAL CMP DLY (5 in this example). If this is too low there is not enough time to make the decision of VCO amplitude to use and may result in non-optimal phase noise. The other approach is to turn off amplitude calibration with ACAL EN=0, then manually choose the amplitude with VCO IDAC (350 for example). This will also result in 20-µs range calibration time. There are many other registers that can aid calibration time, for example ACAL VCO IDAC STRT lets the user choose what VCO amplitude to start with during amplitude calibration. Setting this value to around 350 will give faster times because it is close to the final amplitude for most final frequencies. FCAL VCO SEL START allows you to choose the VCO core to start with for the calibration instead of starting from core 7 by default. If you know you are locking to a frequency around VCO core 1, you can start from VCO 2 by setting VCO SEL=2, which should give faster lock times. Go to the Register Maps section for detailed information of these registers and their related registers. For fast analog settling time, design loop filter for very wide loop bandwidth (MHz range).




Figure 8-8. Lock Time Screenshot

The calibration sweeps from the top of the VCO frequency range to the bottom. This example does a calibration to lock at 3.7 GHz (which is the worst case). For the left screenshot (Wideband Frequency view), see the

Submit Document Feedback

sweeping from top to bottom of the VCO range. On the right screenshot (Narrowband Frequency view), see the analog settling time to the precise target frequency.

### 8.1.9 Modeling and Understanding PLL FOM and Flicker Noise

Follow these recommended settings to design for wide loop bandwidth and extract FOM and flicker noise. The flat model is the PLL noise floor modeled by: PLL\_flat = PLL\_FOM +  $20 \times log(Fvco/Fpd)$  +  $10 \times log(Fpd / 1 Lz)$ . The flicker noise (also known as 1/f noise) which changes by -10dB / decade, is modeled by: PLL\_flicker (offset) = PLL\_flicker\_Norm +  $20 \times log(Fvco / 1 GHz)$  -  $10 \times log(offset / 10k Hz)$ . The cumulative model is the addition of both components: PLL\_Noise =  $10 \times log(10PLL_Flat / 10 + 10PLL_flicker / 10)$ . This is adjusted to fit the measured data to extract the PLL\_FOM and PLL\_flicker\_Norm spec numbers.

Table 8-3. Wide Loop Filter Design

PARAMETER	VALUE
PFD (MHz)	200
Charge pump (mA)	12
VCO frequency (MHz)	5400
Loop bandwidth (kHz)	2000
Phase margin (degrees)	30
Gamma	1.4
Loop filter (2nd order)	
C1 (nF)	0.01
C2 (nF)	0.022
R2 (kΩ)	4.7




Figure 8-9. FOM and Flicker Noise Modeling

#### 8.1.10 External Loop Filter

The LMX2582 requires an external loop filter that is application-specific and can be configured by the PLLatinum<sup>™</sup> simulation tool found here. For the LMX2582, it matters what impedance is seen from the Vtune pin looking outwards. This impedance is dominated by the component C3 for a third order filter or C1 for a second order filter. If there is at least 3.3 nF for the capacitance that is shunt with this pin, the VCO phase noise will be close to the best it can be. If there is less, the VCO phase noise in the 100-kHz to 1-MHz region will degrade. This capacitor should be placed close to the Vtune pin.

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback







Figure 8-10. External Loop Filter

# 8.2 Typical Application

# 8.2.1 Design for Low Jitter



Copyright © 2016, Texas Instruments Incorporated

Figure 8-11. Typical Application Schematic

## 8.2.1.1 Design Requirements

Refer to the design parameters shown in Table 8-4.

**Table 8-4. Design Information** 

PARAMETER	VALUE						
PFD (MHz)	200						
Charge pump (mA)	20						
VCO frequency (MHz)	1800						
Loop bandwidth (kHz)	210						
Phase margin (degrees)	70						
Gamma	3.8						
Loop filter (2nd order)							
C1 (nF)	4.7						
C2 (nF)	100						
R2 (Ω)	68						

### 8.2.1.2 Detailed Design Procedure

The integration of phase noise over a certain bandwidth (jitter) is an performance specification that translates to signal-to-noise ratio. Phase noise inside the loop bandwidth is dominated by the PLL, while the phase noise outside the loop bandwidth is dominated by the VCO. As a rule of thumb, jitter is lowest if loop bandwidth is designed to the point where the two intersect. A higher phase margin loop filter design has less peaking at the loop bandwidth and thus lower jitter. The tradeoff with this as longer lock times and spurs should be considered in design as well.

## 8.2.1.3 Application Curve




Figure 8-12. Typical Jitter

## 8.3 Power Supply Recommendations

TI recommends placing 100-nF spurs close to each of the power supply pins. If fractional spurs are a large concern, using a ferrite bead to each of these power supply pins can reduce spurs to a small degree.



# 8.4 Layout

## 8.4.1 Layout Guidelines

See EVM instructions for details. In general, the layout guidelines are similar to most other PLL devices. The followings are some outstanding guidelines.

- · Place output pull up components close to the pin.
- · Place capacitors close to the pins.
- Make sure input signal trace is well matched.
- Do not route any traces that carrying switching signal close to the charge pump traces and external VCO.

## 8.4.2 Layout Example




Figure 8-13. Recommended Layout

Submit Document Feedback

Copyright © 2022 Texas Instruments Incorporated

# 9 Device and Documentation Support

# 9.1 Device Support

# 9.1.1 Development Support

Texas Instruments has several software tools to aid in the development at www.ti.com. Among these tools are:

- Codeloader to understand how to program the EVM board.
- · Clock Design Tool for designing loop filters, simulating phase noise, and simulating spurs.
- EVM board instructions for seeing typical measured data with detailed measurement conditions and a complete design.
- Clock Architect for designing and simulating the device and understanding how it might work with other devices.

## 9.2 Documentation Support

### 9.2.1 Related Documentation

The following are recommended reading.

- AN-1879 Fractional N Frequency Synthesis (SNAA062)
- PLL Performance, Simulation, and Design Handbook (SNAA106)
- 9.8 GHz RF High Performance Synthesizer Operating From a Buck Converter Reference Design (TIDUC22)
- RF Sampling S-Band Radar Receiver Reference Design (TIDUBS6)
- 9.8GHz RF CW Signal Generator Using Integrated Synthesizer With Spur Reduction Reference Design (TIDUBM1)
- 2-GHz Complex Bandwidth DC-Coupled 14-bit Digitizer Reference Design (TIDRLM6)

# 9.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 9.4 Support Resources

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 9.5 Trademarks

PLLatinum<sup>™</sup> and TI E2E<sup>™</sup> are trademarks of Texas Instruments.

All trademarks are the property of their respective owners.

#### 9.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

# 9.7 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2022 Texas Instruments Incorporated

www.ti.com 9-Nov-2025

#### PACKAGING INFORMATION

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
LMX2582RHAR	Active	Production	VQFN (RHA)   40	2500   LARGE T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582
LMX2582RHAR.A	Active	Production	VQFN (RHA)   40	2500   LARGE T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582
LMX2582RHAR.B	Active	Production	VQFN (RHA)   40	2500   LARGE T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582
LMX2582RHAT	Active	Production	VQFN (RHA)   40	250   SMALL T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582
LMX2582RHAT.A	Active	Production	VQFN (RHA)   40	250   SMALL T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582
LMX2582RHAT.B	Active	Production	VQFN (RHA)   40	250   SMALL T&R	Yes	NIPDAUAG	Level-3-260C-168 HR	-40 to 85	LMX2582

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 9-Nov-2025

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 1-Aug-2025

## TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LMX2582RHAR	VQFN	RHA	40	2500	330.0	16.4	6.3	6.3	1.5	12.0	16.0	Q1
LMX2582RHAT	VQFN	RHA	40	250	178.0	16.4	6.3	6.3	1.5	12.0	16.0	Q1

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 1-Aug-2025



## \*All dimensions are nominal

	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ı	LMX2582RHAR	VQFN	RHA	40	2500	356.0	356.0	36.0
ı	LMX2582RHAT	VQFN	RHA	40	250	208.0	191.0	35.0

6 x 6, 0.5 mm pitch


PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





PLASTIC QUAD FLATPACK - NO LEAD




# NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025