





## Table of Contents

|                                                                               |          |                                                                  |           |
|-------------------------------------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                                                       | <b>1</b> | 6.2 Functional Block Diagram.....                                | <b>8</b>  |
| <b>2 Description</b> .....                                                    | <b>1</b> | 6.3 Device Functional Modes.....                                 | <b>8</b>  |
| <b>3 Pin Configuration and Functions</b> .....                                | <b>3</b> | <b>7 Application and Implementation</b> .....                    | <b>9</b>  |
| <b>4 Specifications</b> .....                                                 | <b>4</b> | 7.1 Power Supply Recommendations.....                            | <b>9</b>  |
| 4.1 Absolute Maximum Ratings.....                                             | <b>4</b> | 7.2 Layout.....                                                  | <b>9</b>  |
| 4.2 Recommended Operating Conditions.....                                     | <b>4</b> | <b>8 Device and Documentation Support</b> .....                  | <b>10</b> |
| 4.3 Thermal Information.....                                                  | <b>4</b> | 8.1 Documentation Support.....                                   | <b>10</b> |
| 4.4 Electrical Characteristics.....                                           | <b>5</b> | 8.2 Receiving Notification of Documentation Updates....          | <b>10</b> |
| 4.5 Timing Requirements, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ .....       | <b>5</b> | 8.3 Support Resources.....                                       | <b>10</b> |
| 4.6 Timing Requirements, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....         | <b>5</b> | 8.4 Trademarks.....                                              | <b>10</b> |
| 4.7 Switching Characteristics, $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ ..... | <b>6</b> | 8.5 Electrostatic Discharge Caution.....                         | <b>10</b> |
| 4.8 Switching Characteristics, $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$ .....   | <b>6</b> | 8.6 Glossary.....                                                | <b>10</b> |
| 4.9 Operating Characteristics.....                                            | <b>6</b> | <b>9 Revision History</b> .....                                  | <b>10</b> |
| <b>5 Parameter Measurement Information</b> .....                              | <b>7</b> | <b>10 Mechanical, Packaging, and Orderable Information</b> ..... | <b>11</b> |
| <b>6 Detailed Description</b> .....                                           | <b>8</b> |                                                                  |           |
| 6.1 Overview.....                                                             | <b>8</b> |                                                                  |           |

## 3 Pin Configuration and Functions



**Figure 3-1. SN54AC373 J or W Package;  
SN74AC373 DB, DW, N, NS, or PW Package (Top  
View)**



**Figure 3-2. SN54AC373 FK Package (Top View)**

**Table 3-1. Pin Functions**

| NO. | PIN                                |                 | TYPE | DESCRIPTION                       |
|-----|------------------------------------|-----------------|------|-----------------------------------|
|     | SSOP, TVSOP, SOIC,<br>SO, or TSSOP | VQFN            |      |                                   |
| 1   | $\overline{OE}$                    | $\overline{OE}$ | I    | Output Enable                     |
| 2   | 1Q                                 | 1Q              | O    | 1Q Output                         |
| 3   | 1D                                 | 1D              | I    | 1D Input                          |
| 4   | 2D                                 | 2D              | I    | 2D Input                          |
| 5   | 2Q                                 | 2Q              | O    | 2Q Output                         |
| 6   | 3Q                                 | 3Q              | O    | 3Q Output                         |
| 7   | 3D                                 | 3D              | I    | 3D Input                          |
| 8   | 4D                                 | 4D              | I    | 4D Input                          |
| 9   | 4Q                                 | 4Q              | O    | 4Q Output                         |
| 10  | GND                                | GND             | —    | Ground Pin                        |
| 11  | LE                                 | LE              | I    | Latch Enable                      |
| 12  | 5Q                                 | 5Q              | O    | 5Q Output                         |
| 13  | 5D                                 | 5D              | I    | 5D Input                          |
| 14  | 6D                                 | 6D              | I    | 6D Input                          |
| 15  | 6Q                                 | 6Q              | O    | 6Q Output                         |
| 16  | 7Q                                 | 7Q              | O    | 7Q Output                         |
| 17  | 7D                                 | 7D              | I    | 7D Input                          |
| 18  | 8D                                 | 8D              | I    | 8D Input                          |
| 19  | 8Q                                 | 8Q              | O    | 8Q Output                         |
| 20  | V <sub>CC</sub>                    | V <sub>CC</sub> | —    | Power Pin                         |
| —   | —                                  | Thermal Pad     | —    | Thermal Pad, normally tied to GND |

## 4 Specifications

### 4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>1</sup>

|                    |                                            | MIN                                  | MAX            | UNIT    |
|--------------------|--------------------------------------------|--------------------------------------|----------------|---------|
| $V_{CC}$           | Supply voltage range                       | -0.5                                 | 7              | V       |
| $V_I$ <sup>1</sup> | Input voltage range                        | -0.5                                 | $V_{CC} + 0.5$ | V       |
| $V_O$ <sup>1</sup> | Output voltage range                       | -0.5                                 | $V_{CC} + 0.5$ | V       |
| $I_{IK}$           | Input clamp current                        | $(V_I < 0 \text{ or } V_I > V_{CC})$ |                | ±20 mA  |
| $I_{OK}$           | Output clamp current                       | $(V_O < 0 \text{ or } V_O > V_{CC})$ |                | ±20 mA  |
| $I_O$              | Continuous output current                  | $(V_O = 0 \text{ to } V_{CC})$       |                | ±50 mA  |
|                    | Continuous current through $V_{CC}$ or GND |                                      |                | ±200 mA |
| $T_{stg}$          | Storage temperature range                  | -65                                  | 150            | °C      |

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

### 4.2 Recommended Operating Conditions

over recommended operating free-air temperature range (unless otherwise noted)<sup>1</sup>

|                 |                                    |                         | SN54AC373 |                 | SN74AC373 |                 | UNIT |
|-----------------|------------------------------------|-------------------------|-----------|-----------------|-----------|-----------------|------|
|                 |                                    |                         | MIN       | MAX             | MIN       | MAX             |      |
| V <sub>CC</sub> | Supply voltage                     |                         | 2         | 6               | 2         | 6               | V    |
| V <sub>IH</sub> | High-level input voltage           | V <sub>CC</sub> = 3 V   | 2.1       |                 | 2.1       |                 | V    |
|                 |                                    | V <sub>CC</sub> = 4.5 V | 3.15      |                 | 3.15      |                 |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V | 3.85      |                 | 3.85      |                 |      |
| V <sub>IL</sub> | Low-level input voltage            | V <sub>CC</sub> = 3 V   |           | 0.9             |           | 0.9             | V    |
|                 |                                    | V <sub>CC</sub> = 4.5V  |           | 1.35            |           | 1.35            |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V |           | 1.65            |           | 1.65            |      |
| V <sub>I</sub>  | Input voltage                      |                         | 0         | V <sub>CC</sub> | 0         | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                     |                         | 0         | V <sub>CC</sub> | 0         | V <sub>CC</sub> | V    |
| I <sub>OH</sub> | High-level output current          | V <sub>CC</sub> = 3 V   |           | -12             |           | -12             | mA   |
|                 |                                    | V <sub>CC</sub> = 4.5 V |           | -24             |           | -24             |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V |           | -24             |           | -24             |      |
| I <sub>OL</sub> | Low-level output current           | V <sub>CC</sub> = 3 V   |           | 12              |           | 12              | mA   |
|                 |                                    | V <sub>CC</sub> = 4.5 V |           | 24              |           | 24              |      |
|                 |                                    | V <sub>CC</sub> = 5.5 V |           | 24              |           | 24              |      |
| Δt/Δv           | Input transition rise or fall rate |                         |           | 8               |           | 8               | ns/V |
| T <sub>A</sub>  | Operating free-air temperature     |                         | -55       | 125             | -40       | 85              | °C   |

- (1) All unused inputs of the device must be held at  $V_{CC}$  or GND to for proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

### 4.3 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                        | SNx4AC373 |           |    |         |            | UNIT |
|-------------------------------|----------------------------------------|-----------|-----------|----|---------|------------|------|
|                               |                                        | DB (SSOP) | DW (SOIC) | N  | NS (SO) | PW (TSSOP) |      |
|                               |                                        | 20 PINS   |           |    |         |            |      |
| R <sub>θJA</sub>              | Junction-to-ambient thermal resistance | 70        | 101.2     | 69 | 60      | 126.2      | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 4.4 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER       | TEST CONDITIONS                                             | V <sub>CC</sub> | T <sub>A</sub> = 25°C |     |       | SN54AC373 |     | SN74AC373 |      | UNIT |
|-----------------|-------------------------------------------------------------|-----------------|-----------------------|-----|-------|-----------|-----|-----------|------|------|
|                 |                                                             |                 | MIN                   | TYP | MAX   | MIN       | MAX | MIN       | MAX  |      |
| V <sub>OH</sub> | I <sub>OH</sub> = -50μA                                     | 3 V             | 2.9                   |     |       | 2.9       |     | 2.9       |      | V    |
|                 |                                                             | 4.5 V           | 4.4                   |     |       | 4.4       |     | 4.4       |      |      |
|                 |                                                             | 5.5 V           | 5.4                   |     |       | 5.4       |     | 5.4       |      |      |
|                 | I <sub>OH</sub> = -12 mA                                    | 3 V             | 2.56                  |     |       | 2.4       |     | 2.46      |      |      |
|                 |                                                             | 4.5 V           | 3.86                  |     |       | 3.7       |     | 3.76      |      |      |
|                 |                                                             | 5.5 V           | 4.86                  |     |       | 4.7       |     | 4.76      |      |      |
| V <sub>OL</sub> | I <sub>OL</sub> = 50μA                                      | 3 V             |                       |     | 0.1   |           | 0.1 |           | 0.1  | V    |
|                 |                                                             | 4.5 V           |                       |     | 0.1   |           | 0.1 |           | 0.1  |      |
|                 |                                                             | 5.5 V           |                       |     | 0.1   |           | 0.1 |           | 0.1  |      |
|                 | I <sub>OL</sub> = 12 mA                                     | 3 V             |                       |     | 0.36  |           | 0.5 |           | 0.44 |      |
|                 |                                                             | 4.5 V           |                       |     | 0.36  |           | 0.5 |           | 0.44 |      |
|                 |                                                             | 5.5 V           |                       |     | 0.36  |           | 0.5 |           | 0.44 |      |
| I <sub>I</sub>  | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5.5 V           |                       |     | ±0.1  |           | ±1  |           | ±1   | μA   |
| I <sub>OZ</sub> | V <sub>O</sub> = V <sub>CC</sub> or GND                     | 5.5 V           |                       |     | ±0.25 |           | ±5  |           | ±2.5 | μA   |
| I <sub>CC</sub> | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0 | 5.5 V           |                       |     | 4     |           | 80  |           | 40   | μA   |
| C <sub>i</sub>  | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5 V             |                       | 4.5 |       |           |     |           |      | pF   |

## 4.5 Timing Requirements, V<sub>CC</sub> = 3.3 V ± 0.3 V

over recommended operating free-air temperature range, V<sub>CC</sub> = 3.3 V ± 0.3 V (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

|                 |                             | T <sub>A</sub> = 25°C |     | SN54AC373 |     | SN74AC373 |     | UNIT |
|-----------------|-----------------------------|-----------------------|-----|-----------|-----|-----------|-----|------|
|                 |                             | MIN                   | MAX | MIN       | MAX | MIN       | MAX |      |
| t <sub>w</sub>  | Pulse duration, LE high     | 5.5                   |     | 6.5       |     | 6         |     | ns   |
| t <sub>su</sub> | Setup time, data before LE↓ | 5.5                   |     | 6.5       |     | 6         |     | ns   |
| t <sub>h</sub>  | Hold time, data after LE↓   | 1                     |     | 1         |     | 1         |     | ns   |

## 4.6 Timing Requirements, V<sub>CC</sub> = 5 V ± 0.5 V

over recommended operating free-air temperature range, V<sub>CC</sub> = 5 V ± 0.5 V (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

|                 |                             | T <sub>A</sub> = 25°C |     | SN54AC373 |     | SN74AC373 |     | UNIT |
|-----------------|-----------------------------|-----------------------|-----|-----------|-----|-----------|-----|------|
|                 |                             | MIN                   | MAX | MIN       | MAX | MIN       | MAX |      |
| t <sub>w</sub>  | Pulse duration, LE high     | 4                     |     | 5         |     | 4.5       |     | ns   |
| t <sub>su</sub> | Setup time, data before LE↓ | 4                     |     | 5         |     | 4.5       |     | ns   |
| t <sub>h</sub>  | Hold time, data after LE↓   | 1                     |     | 1         |     | 1         |     | ns   |

**SN54AC373, SN74AC373**

SCAS540F – OCTOBER 1995 – REVISED FEBRUARY 2024

**4.7 Switching Characteristics,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$** 

over recommended operating free-air temperature range,  $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | TO (INPUT)      | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ |     |      | SN54AC373 |      | SN74AC373 |      | UNIT |
|-----------|-----------------|-------------|--------------------------|-----|------|-----------|------|-----------|------|------|
|           |                 |             | MIN                      | TYP | MAX  | MIN       | MAX  | MIN       | MAX  |      |
| $t_{PLH}$ | D               | Q           | 1.5                      | 10  | 13.5 | 1         | 16.5 | 1.5       | 15   | ns   |
| $t_{PHL}$ |                 |             | 1.5                      | 9.5 | 13.0 | 1         | 16   | 1.5       | 14.5 |      |
| $t_{PLH}$ | LE              | Q           | 1.5                      | 10  | 13.5 | 1         | 16.5 | 1.5       | 15   | ns   |
| $t_{PHL}$ |                 |             | 1.5                      | 9.5 | 12.5 | 1         | 15   | 1.5       | 14   |      |
| $t_{PZH}$ | $\overline{OE}$ | Q           | 1.5                      | 9   | 11.5 | 1         | 14   | 1         | 13   | ns   |
| $t_{PZL}$ |                 |             | 1.5                      | 8.5 | 11.5 | 1         | 13.5 | 1         | 13   |      |
| $t_{PHZ}$ | $\overline{OE}$ | Q           | 1.5                      | 10  | 12.5 | 1         | 16   | 1         | 14.5 | ns   |
| $t_{PLZ}$ |                 |             | 1.5                      | 8   | 11.5 | 1         | 13   | 1         | 12.5 |      |

**4.8 Switching Characteristics,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$** 






over recommended operating free-air temperature range,  $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see [Load Circuit and Voltage Waveforms](#))

| PARAMETER | TO (INPUT)      | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ |     |     | SN54AC373 |      | SN74AC373 |      | UNIT |
|-----------|-----------------|-------------|--------------------------|-----|-----|-----------|------|-----------|------|------|
|           |                 |             | MIN                      | TYP | MAX | MIN       | MAX  | MIN       | MAX  |      |
| $t_{PLH}$ | D               | Q           | 1.5                      | 7   | 9.5 | 1         | 11.5 | 1.5       | 10.5 | ns   |
| $t_{PHL}$ |                 |             | 1.5                      | 7   | 9.5 | 1         | 11.5 | 1.5       | 10.5 |      |
| $t_{PLH}$ | LE              | Q           | 1.5                      | 7.5 | 9.5 | 1         | 12   | 1.5       | 10.5 | ns   |
| $t_{PHL}$ |                 |             | 1.5                      | 7   | 9.5 | 1         | 11   | 1.5       | 10.5 |      |
| $t_{PZH}$ | $\overline{OE}$ | Q           | 1.5                      | 7   | 8.5 | 1         | 10.5 | 1         | 9.5  | ns   |
| $t_{PZL}$ |                 |             | 1.5                      | 6.5 | 8.5 | 1         | 10   | 1         | 9.5  |      |
| $t_{PHZ}$ | $\overline{OE}$ | Q           | 1.5                      | 8   | 11  | 1         | 13.5 | 1         | 12.5 | ns   |
| $t_{PLZ}$ |                 |             | 1.5                      | 6.5 | 8.5 | 1         | 10.5 | 1         | 10   |      |

**4.9 Operating Characteristics**
 $V_{CC} = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$ 

| PARAMETER |                               | TEST CONDITIONS      |                    | TYP | UNIT |
|-----------|-------------------------------|----------------------|--------------------|-----|------|
| $C_{pd}$  | Power dissipation capacitance | $C_L = 50\text{ pF}$ | $f = 1\text{ MHz}$ | 40  | pF   |

## 5 Parameter Measurement Information



- A.  $C_L$  includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r \leq 2.5 \text{ ns}$ ,  $t_f \leq 2.5 \text{ ns}$ .
- D. The outputs are measured one at a time with one input transition per measurement.

**Figure 5-1. Load Circuit and Voltage Waveforms**

| TEST              | S1                |
|-------------------|-------------------|
| $t_{PLH}/t_{PHL}$ | Open              |
| $t_{PLZ}/t_{PZL}$ | $2 \times V_{CC}$ |
| $t_{PHZ}/t_{PZH}$ | Open              |

## 6 Detailed Description

## 6.1 Overview


The eight latches are D-type transparent latches. When the latch-enable (LE) input is high, the Q outputs follow the data (D) inputs. When LE is taken low, the Q outputs are latched at the logic levels set up at the D inputs.

A buffered output-enable ( $\overline{OE}$ ) input can be used to place the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines in bus-organized systems without need for interface or pullup components.

$\overline{\text{OE}}$  does not affect the internal operations of the latches. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

For specified high-impedance state during power up or power down,  $\overline{\text{OE}}$  must be tied to  $V_{\text{CC}}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

## 6.2 Functional Block Diagram



### Figure 6-1. Logic Diagram (Positive Logic)

## 6.3 Device Functional Modes

### Table 6-1. Function Table (Each Latch)

| INPUTS |    |   | OUTPUT Q       |
|--------|----|---|----------------|
| OE     | LE | D |                |
| L      | H  | H | H              |
| L      | H  | L | L              |
| L      | L  | X | Q <sub>0</sub> |
| H      | X  | X | Z              |

## 7 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 7.1 Power Supply Recommendations


### 7.2 Layout

#### 7.2.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states.

Specified in [Layout Diagram](#) are rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or  $V_{CC}$ , whichever makes more sense or is more convenient. It is acceptable to float outputs unless the part is a transceiver. If the transceiver has an output enable pin, it will disable the outputs section of the part when asserted. This will not disable the input section of the I/Os so they also cannot float when disabled.

#### 7.2.2 Layout Example



**Figure 7-1. Layout example for the SNx4AC373**

## 8 Device and Documentation Support

### 8.1 Documentation Support

#### 8.1.1 Related Documentation

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**Table 8-1. Related Links**

| PARTS     | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|-----------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| SN54AC373 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| SN74AC373 | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |

### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 8.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 8.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

### 8.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision E (August 2023) to Revision F (February 2024)                 | Page |
|-------------------------------------------------------------------------------------|------|
| • Updated RθJA values: DW = 58 to 101.2, PW = 83 to 126.2, all values in °C/W ..... | 4    |
| • Added <i>Application and Implementation</i> section.....                          | 9    |

| Changes from Revision D (October 2003) to Revision E (August 2023)                                                                                                                                                                                           | Page |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Added <i>Device Information</i> table, <i>Pin Functions</i> table, <i>Thermal Information</i> table, <i>Device Functional Modes</i> , <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section | 1    |

## 10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                    |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|----------------------------------------|
| <a href="#">5962-87555012A</a>  | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87555012A<br>SNJ54AC<br>373FK |
| <a href="#">5962-8755501RA</a>  | Active        | Production           | CDIP (J)   20   | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501RA<br>SNJ54AC373J          |
| <a href="#">5962-8755501SA</a>  | Active        | Production           | CFP (W)   20    | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501SA<br>SNJ54AC373W          |
| <a href="#">5962-8755501VSA</a> | Active        | Production           | CFP (W)   20    | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501VS<br>A<br>SNV54AC373W     |
| 5962-8755501VSA.A               | Active        | Production           | CFP (W)   20    | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501VS<br>A<br>SNV54AC373W     |
| <a href="#">SN74AC373DBR</a>    | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| SN74AC373DBR.A                  | Active        | Production           | SSOP (DB)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| <a href="#">SN74AC373DW</a>     | Obsolete      | Production           | SOIC (DW)   20  | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | AC373                                  |
| <a href="#">SN74AC373DWR</a>    | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| SN74AC373DWR.A                  | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| SN74AC373DWRE4                  | Active        | Production           | SOIC (DW)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| <a href="#">SN74AC373N</a>      | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74AC373N                             |
| SN74AC373N.A                    | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74AC373N                             |
| SN74AC373NE4                    | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | SN74AC373N                             |
| <a href="#">SN74AC373NSR</a>    | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| SN74AC373NSR.A                  | Active        | Production           | SOP (NS)   20   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| <a href="#">SN74AC373PW</a>     | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | AC373                                  |
| <a href="#">SN74AC373PWR</a>    | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| SN74AC373PWR.A                  | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | AC373                                  |
| <a href="#">SNJ54AC373FK</a>    | Active        | Production           | LCCC (FK)   20  | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>87555012A<br>SNJ54AC<br>373FK |

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|------------------------------------|
| SNJ54AC373FK.A              | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-87555012A<br>SNJ54AC<br>373FK |
| <a href="#">SNJ54AC373J</a> | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501RA<br>SNJ54AC373J      |
| SNJ54AC373J.A               | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501RA<br>SNJ54AC373J      |
| <a href="#">SNJ54AC373W</a> | Active        | Production           | CFP (W)   20   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501SA<br>SNJ54AC373W      |
| SNJ54AC373W.A               | Active        | Production           | CFP (W)   20   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8755501SA<br>SNJ54AC373W      |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF SN54AC373, SN54AC373-SP, SN74AC373 :**

- Catalog : [SN74AC373](#), [SN54AC373](#)
- Enhanced Product : [SN74AC373-EP](#), [SN74AC373-EP](#)
- Military : [SN54AC373](#)
- Space : [SN54AC373-SP](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications
- Space - Radiation tolerant, ceramic packaging and qualified for use in Space-based application

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AC373DBR | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74AC373DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.9    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74AC373DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74AC373NSR | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74AC373PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |
| SN74AC373PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AC373DBR | SSOP         | DB              | 20   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74AC373DWR | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74AC373DWR | SOIC         | DW              | 20   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74AC373NSR | SOP          | NS              | 20   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74AC373PWR | TSSOP        | PW              | 20   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74AC373PWR | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |

**TUBE**



\*All dimensions are nominal

| Device            | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-87555012A    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| 5962-8755501SA    | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| 5962-8755501VSA   | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| 5962-8755501VSA.A | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SN74AC373N        | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74AC373N.A      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74AC373NE4      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SNJ54AC373FK      | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ54AC373FK.A    | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| SNJ54AC373W       | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |
| SNJ54AC373W.A     | W            | CFP          | 20   | 25  | 506.98 | 26.16  | 6220   | NA     |



## SSOP - 2 mm max height

## SMALL OUTLINE PACKAGE



4214851/B 08/2019

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



SOLDER MASK DETAILS

4214851/B 08/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE




| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).  
 The 20 pin end lead shoulder width is a vendor option, either half or full width.




## NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.



**DW0020A**

### SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



## SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.  
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER


This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229370VA\

W (R-GDFP-F20)

CERAMIC DUAL FLATPACK



## NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within Mil-Std 1835 GDFP2-F20



## TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated