











SN74LVC1G373

SCES528F - DECEMBER 2003 - REVISED MAY 2017

SN74LVC1G373 Single D-Type Latch With 3-State Output

Features

- Available in the Texas Instruments NanoFree™ Package
- Supports 5-V V_{CC} Operation
- Inputs Accept Voltages to 5.5 V
- Provides Down Translation to V_{CC}
- Max t_{pd} of 4 ns at 3.3 V
- Low Power Consumption: 10-µA Maximum I_{CC}
- ±24-mA Output Drive at 3.3 V
- Ioff Supports Partial-Power-Down Mode and Back **Drive Protection**
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II

Applications

- Servers
- **Printers**
- Telecom and Grid Infrastructure
- Memory Addressing
- **Buffer Registers**
- Electronic Point of Sale

3 Description

The SN74LVC1G373 device is a single D-type latch designed for 1.65-V to 5.5-V V_{CC} operation.

This device is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers. While the latch-enable (LE) input is high, the Q outputs follow the data (D) inputs. When LE is taken low, the Q outputs are latched at the logic levels set up at the D inputs.

NanoFree™ package technology is a major breakthrough in IC packaging concepts, using the die as the package.

OE does not affect the internal operations of the latch. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

Device Information(1)

· · · · · · · · · · · · · · · · · · ·				
PACKAGE NUMBER	PACKAGE	BODY SIZE (NOM)		
SN74LVC1G373DBV	SOT-23 (6)	2.90 mm × 1.60 mm		
SN74LVC1G373DCK	SC70 (6)	2.00 mm × 1.25 mm		
SN74LVC1G373YZP	DSBGA (6)	1.41 mm × 0.91 mm		

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Logic Diagram (Positive Logic)






Table of Contents

1	Features 1		8.1 Overview	12
2	Applications 1		8.2 Functional Block Diagram	12
3	Description 1		8.3 Feature Description	12
4	Revision History2		8.4 Device Functional Modes	13
5	Pin Configuration and Functions	9	Application and Implementation	
6	Specifications4			
	6.1 Absolute Maximum Ratings 4	40	- 71 11	
	6.2 ESD Ratings 4	10	Power Supply Recommendations	
	6.3 Recommended Operating Conditions 5	11	Layout	
	6.4 Thermal Information5		11.1 Layout Guidelines	
	6.5 Electrical Characteristics6		11.2 Layout Example	16
	6.6 Timing Requirements: $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$	12	Device and Documentation Support	17
	6.7 Timing Requirements: $T_{\Delta} = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$ 6		12.1 Documentation Support	17
	6.8 Switching Characteristics: $T_A = -40^{\circ}\text{C}$ to +85°C 7		12.2 Receiving Notification of Documentation Update	es 17
	6.9 Switching Characteristics: T _A = -40°C to +85°C 7		12.3 Community Resource	17
	6.10 Switching Characteristics: $T_A = -40^{\circ}\text{C}$ to +125°C 8		12.4 Trademarks	17
	6.11 Operating Characteristics 8		12.5 Electrostatic Discharge Caution	17
	6.12 Typical Characteristics9		12.6 Glossary	17
7	Parameter Measurement Information	13	Mechanical, Packaging, and Orderable	
8	Detailed Description 12		Information	17
	-			

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Ch	anges from Revision E (September 2016) to Revision F	Page
•	Changed YZP Package pinout diagram and added YZP pin numbers in <i>Pin Functions</i> table	3
•	Added Balanced High-Drive CMOS Push-Pull Outputs, Standard CMOS Inputs, Clamp Diodes, Partial Power Dov (I _{off}), Over-voltage Tolerant Inputs	
•	Added Trace Example in Layout Example section	16
	Added Documentation Support section	17
<u> </u>	Added Documentation Support Section	17
- Ch	anges from Revision D (December 2013) to Revision E	Page
Ch		

 Changes from Revision C (May 2007) to Revision D
 Page

 • Updated document to new TI data sheet format.
 1

 • Deleted Ordering Information table; see POA at the end of the data sheet.
 1


 • Updated operating temperature range.
 5

Submit Documentation Feedback


Copyright © 2003–2017, Texas Instruments Incorporated




5 Pin Configuration and Functions



See mechanical drawings for dimensions.



YZP Package 6-Pin DSBGA Bottom View



Pin Functions

PIN			1/0	DESCRIPTION
NAME	DCK, DBV	YZP	I/O	DESCRIPTION
LE	1	A1	I	Latch Enable; output follows D input when high
GND	2	B1	_	Ground
D	3	C1	I	D latch input
Q	4	C2	0	Q latch output
V _{CC}	5	B2	_	Positive supply
ŌĒ	6	A2	I	Active low output enable; Hi-Z output when high



Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V _{CC}	Supply voltage		-0.5	6.5	V
VI	Input voltage ⁽²⁾		-0.5	6.5	V
Vo	Voltage range applied to any output in the high-impedance of	or power-off state (2)(3)	-0.5	6.5	V
Vo	Voltage range applied to any output in the high or low state	2)(3)	-0.5	V _{CC} + 0.5	V
I _{IK}	Input clamp current	V _I < 0		-50	mA
I _{OK}	Output clamp current	V _O < 0		-50	mA
Io	Continuous output current			±50	mA
	Continuous current through V _{CC} or GND			±100	mA
T_{J}	Absolute maximum Junction temperature			150	°C
T _{stg}	Storage temperature		-65	150	°C

⁽¹⁾ Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended* Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

			VALUE	UNIT
.,		Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±2000	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \
V _(ESD) Electrostatic dischar	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 (2)	±1500	V

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed. The value of V_{CC} is provided in the *Recommended Operating Conditions*.

JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. CDM tested on DBV package



6.3 Recommended Operating Conditions

See (1)

			MIN	MAX	UNIT
V	Supply voltage	Operating	1.65	5.5	V
V _{CC}		Data retention only	1.5		V
		V _{CC} = 1.65 V to 1.95 V	0.65 × V _{CC}	5.5	
.,	I limb lavel in a strong to a	V _{CC} = 2.3 V to 2.7 V	1.7	5.5	V
V_{IH}	High-level input voltage	V _{CC} = 3 V to 3.6 V	2	5.5	V
		V _{CC} = 4.5 V to 5.5 V	0.7 × V _{CC}	5.5	
		V _{CC} = 1.65 V to 1.95 V	0	0.35 × V _{CC}	
. ,	Law band Sandon Name	V _{CC} = 2.3 V to 2.7 V	0	0.7	
V_{IL}	Low-level input voltage	V _{CC} = 3 V to 3.6 V	0	0.8	V
		V _{CC} = 4.5 V to 5.5 V	0	$0.3 \times V_{CC}$	
Vo	Output voltage	•	0	V _{CC}	V
		V _{CC} = 1.65 V		-4	
		V _{CC} = 2.3 V		-8	mA
I _{OH}	High-level output current			-16	
	-			-24	
		V _{CC} = 4.5 V		-32	
		V _{CC} = 1.65 V		4	
		V _{CC} = 2.3 V		8	
l _{OL}	Low-level output current			16	mA
		V _{CC} = 3 V		24	
		V _{CC} = 4.5 V		32	
		V _{CC} = 1.8 V ± 0.15 V, 2.5 V ± 0.2 V		20	
Δt/Δν	Input transition rise or fall rate	V _{CC} = 3.3 V ± 0.3 V		10	ns/V
		$V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$		5	
_		DSBGA package	-40	85	0.0
T _A	Operating free-air temperature	All other packages	-40	125	°C

⁽¹⁾ All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. See *Implications of Slow or Floating CMOS Inputs* (SCBA004).

6.4 Thermal Information

		SN74LVC1G373			
THERMAL METRIC ⁽¹⁾		DBV (SOT-23)	DCK (SC70)	YZP (DSBGA)	UNIT
		6 PINS	6 PINS	6 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	219.8	255.2	131	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	189	121.9	1.3	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	65.8	58	22.6	°C/W
ΨЈТ	Junction-to-top characterization parameter	67.3	7.2	5.2	°C/W
ΨЈВ	Junction-to-board characterization parameter	65.2	57.3	22.6	°C/W

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



6.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST COI	NDITIONS	V _{cc}	MIN	TYP ⁽¹⁾	MAX	UNIT
	I _{OH} = -100 μA	1.65 V to 5.5 V	V _{CC} - 0.1				
V _{OH}	$I_{OH} = -4 \text{ mA}$	1.65 V	1.2				
	I _{OH} = -8 mA		2.3 V	1.9			V
	I _{OH} = -16 mA		2.1/	2.4			V
	I _{OH} = -24 mA		3 V	2.3			
	I _{OH} = -32 mA		4.5 V	3.8			
	I _{OL} = 100 μA		1.65 V to 5.5 V			0.1	
	I _{OL} = 4 mA		1.65 V			0.45	
	I _{OL} = 8 mA	2.3 V			0.3	V	
	I _{OL} = 16 mA						0.4
V _{OL}		$T_A = -40$ °C to 85°C	3 V			0.55	V
	I _{OL} = 24 mA	$T_A = -40^{\circ}C$ to 125°C				0.65	
	I _{OL} = 32 mA	$T_A = -40$ °C to 85°C	45.77			0.55	
		$T_A = -40^{\circ}C$ to 125°C	4.5 V			0.65	
I _I	V _I = 5.5 V or GND		0 V to 5.5 V			±1	
I _{OZ}	V _O = 0 to 5.5 V		3.6 V			±5	
I _{off}	V_I or $V_O = 5.5 \text{ V}$		0			±10	μA
I _{CC}	V _I = 5.5 V or GND, I _O = 0		1.65 V to 5.5 V			10	μΛ
Δl _{CC}	One input at V _{CC} – 0.6 V, Other inputs at V _{CC} or GND	3 V to 5.5 V			500		
C _i	$V_I = V_{CC}$ or GND	$T_A = -40$ °C to 85°C	3.3 V		3.5		
C _o	$V_O = V_{CC}$ or GND	$T_A = -40$ °C to 85°C	3.3 V		6		pF

⁽¹⁾ All typical values are at V_{CC} = 3.3 V, T_A = 25°C.

6.6 Timing Requirements: $T_A = -40^{\circ}C$ to $+85^{\circ}C$

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2)

			MIN	MAX	UNIT
t _w	Pulse duration, LE high		3		
		$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2.4		
	Cotus time data hafara LEL	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	2		
t _{su}	Setup time, data before LE↓	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1.5		
		V _{CC} = 5 V ± 0.5 V	1.5		ns
		$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2.5		
	Light time data after LE	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5		
t _h	Hold time, data after LE↓	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1.5		
		$V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$	1.5		

6.7 Timing Requirements: $T_A = -40^{\circ}C$ to $+125^{\circ}C$

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2)

			MIN	MAX	UNIT
t _w	Pulse duration, LE high		3		
t _{su} Setup time, data before LE↓		$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2.9		
	Catua time data batara I C	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	2.1		
	Setup time, data before LEJ	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1.5		
		$V_{CC} = 5 V \pm 0.5 V$	1.5		ns
		$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	3		
	Hold time data after LC	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5		
t _h	Hold time, data after LE↓	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1.5		
		$V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$	1.5		



6.8 Switching Characteristics: $T_A = -40$ °C to +85°C

over recommended operating free-air temperature range, $C_L = 15 \text{ pF}$ (unless otherwise noted) (see Figure 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	MAX	UNIT
			V _{CC} = 1.8 V ± 0.15 V	2	15	
	D		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	15	5	
	D		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	4	
		Q	$V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$	1	3.5	
t _{pd}		Q	$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	15	
	LE		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	5	
			$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	4	
			V _{CC} = 5 V ± 0.5 V	1	3.5	
	<u> </u>	ŌĒ Q	$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	12.5	ns
			$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	4.5	
t _{en}	OE	Q	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	4	1
			V _{CC} = 5 V ± 0.5 V	1	2.5	
			$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	14	
	or	OE Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	7	
t _{dis}	OE		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	7.9	
			$V_{CC} = 5 \text{ V} \pm 0.5 \text{ V}$	1	5.3	

6.9 Switching Characteristics: $T_A = -40^{\circ}C$ to +85°C

over recommended operating free-air temperature range, $C_L = 30 \text{ pF}$ or 50 pF (unless otherwise noted) (see Figure 3)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	MAX	UNIT	
			V _{CC} = 1.8 V ± 0.15 V	2	16		
	D		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	7.3		
	D		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	5.4		
		Q	V _{CC} = 5 V ± 0.5 V	1	4		
t _{pd}		Q	V _{CC} = 1.8 V ± 0.15 V	2	16.3		
	LE		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	7.4		
	LL		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	5.5		
			V _{CC} = 5 V ± 0.5 V	1	4	ns	
			V _{CC} = 1.8 V ± 0.15 V	2	13	115	
	ŌĒ	Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	6.3	7	
t _{en}	OE	Q	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	5.1		
			$V_{CC} = 5 V \pm 0.5 V$	1	3.7		
			$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	17.4		
	ŌĒ	Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1	5.9		
t _{dis}	OE .		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	6.5		
			V _{CC} = 5 V ± 0.5 V	1	4.6		



6.10 Switching Characteristics: $T_A = -40$ °C to +125°C

over recommended operating free-air temperature range, $C_L = 30 \text{ pF}$ or 50 pF (unless otherwise noted) (see Figure 3)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	MAX	UNIT	
			V _{CC} = 1.8 V ± 0.15 V	2	17		
	D		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	8		
	Ь		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	6		
		Q	$V_{CC} = 5 V \pm 0.5 V$	1	4.5		
od		Q	$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	17		
	LE		$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	8		
	LC		$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	6		
			$V_{CC} = 5 V \pm 0.5 V$	1	4.5		
			$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	13.5		
	ŌĒ	Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	7		
n OE	Q	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	5.5			
			$V_{CC} = 5 V \pm 0.5 V$	1	4		
			$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	18.4	ns	
	ŌĒ	Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1	6.2		
dis	OE .	Q	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	1	6.8		
			$V_{CC} = 5 V \pm 0.5 V$	1	5		
			$V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$	2	14		
	ŌĒ	Q	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$	1.5	8.3		
en	OE .	Q	$V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$	0.9	6.5		
		V _{CC} = 5 V ± 0.5 V	0.7	5.5			
			V _{CC} = 1.8 V ± 0.15 V	2	16		
	ŌĒ		V _{CC} = 2.5 V ± 0.2 V	1.1	7.3		
lis	UE	Q	V _{CC} = 3.3 V ± 0.3 V	1.4	6	1	
			V _{CC} = 5 V ± 0.5 V	0.8	5.1	1	

6.11 Operating Characteristics

 $T_A = 25^{\circ}C$

	PARAMETER	₹	TEST C	TYP	UNIT	
			V _{CC} = 1.8 V	19		
	Outputs enabled		$V_{CC} = 2.5 \text{ V}$	19		
		Outputs enabled		$V_{CC} = 3.3 \text{ V}$	19	
Power dissipation		f 40 MH-	$V_{CC} = 5 V$	20	~F	
C _{pd}	capacitance		f = 10 MHz	V _{CC} = 1.8 V	3	pF
		Outputs disabled		$V_{CC} = 2.5 \text{ V}$	3	
	Outputs disabled		$V_{CC} = 3.3 \text{ V}$	3		
				$V_{CC} = 5 V$	4	

Product Folder Links: SN74LVC1G373

Submit Documentation Feedback



6.12 Typical Characteristics





Figure 1. Propagation delay vs V_{CC}

Copyright © 2003–2017, Texas Instruments Incorporated

Submit Documentation Feedback




7 Parameter Measurement Information



TEST	S1
t _{PLH} /t _{PHL}	Open
t _{PLZ} /t _{PZL}	V _{LOAD}
t _{PHZ} /t _{PZH}	GND

LOAD CIRCUIT

.,	INI	PUTS		.,			.,
V _{cc}	V,	t,/t,	V _M	V _{LOAD}	C _L	R _∟	V _A
1.8 V ± 0.15 V	V _{cc}	≤2 ns	V _{cc} /2	2 × V _{cc}	15 pF	1 M Ω	0.15 V
$2.5~\textrm{V}~\pm~0.2~\textrm{V}$	V _{cc}	≤2 ns	V _{cc} /2	2 × V _{cc}	15 pF	1 M Ω	0.15 V
$3.3~V~\pm~0.3~V$	3 V	≤2.5 ns	1.5 V	6 V	15 pF	1 M Ω	0.3 V
5 V ± 0.5 V	V _{cc}	≤2.5 ns	V _{cc} /2	2 × V _{cc}	15 pF	1 M Ω	0.3 V



NOTES: A. C, includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_o = 50 \Omega$.
- D. The outputs are measured one at a time, with one transition per measurement.
- E. t_{PLZ} and \dot{t}_{PHZ} are the same as t_{dis} .
- F. $t_{\mbox{\tiny PZL}}$ and $t_{\mbox{\tiny PZH}}$ are the same as $t_{\mbox{\tiny en}}.$
- G. t_{PlH} and t_{PHl} are the same as t_{pd} .
- H. All parameters and waveforms are not applicable to all devices.


Figure 2. Load Circuit and Voltage Waveforms

Submit Documentation Feedback

Copyright © 2003–2017, Texas Instruments Incorporated




Parameter Measurement Information (continued)



TEST	S1
t _{PLH} /t _{PHL}	Open
t _{PLZ} /t _{PZL}	V _{LOAD}
t _{PHZ} /t _{PZH}	GND

LOAD CIRCUIT

,,	INI	PUTS		V			.,
V _{cc}	V,	t,/t,	V _M	V _{LOAD}	C _L	R _⊾	V _Δ
1.8 V ± 0.15 V	V _{cc}	≤2 ns	V _{cc} /2	2 × V _{cc}	30 pF	1 k Ω	0.15 V
$2.5~\textrm{V}~\pm~0.2~\textrm{V}$	V _{cc}	≤2 ns	V _{cc} /2	2 × V _{cc}	30 pF	500 Ω	0.15 V
$3.3~V~\pm~0.3~V$	3 V	≤2.5 ns	1.5 V	6 V	50 pF	500 Ω	0.3 V
5 V ± 0.5 V	V _{cc}	≤2.5 ns	V _{cc} /2	2 × V _{cc}	50 pF	500 Ω	0.3 V



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_0 = 50 \,\Omega$.
- D. The outputs are measured one at a time, with one transition per measurement.
- E. t_{PLZ} and \dot{t}_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. $t_{\text{PLH}}^{\text{F2L}}$ and $t_{\text{PHL}}^{\text{F2L}}$ are the same as $t_{\text{pd}}^{\text{eff}}$
- H. All parameters and waveforms are not applicable to all devices.

Figure 3. Load Circuit and Voltage Waveforms



8 Detailed Description

8.1 Overview

A buffered output-enable (\overline{OE}) input can be used to place the output in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the output neither loads nor drives the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines without interface or pullup components. To ensure the high-impedance state during power up or power down, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver. This device is fully specified for partial-power-down applications using I_{off} . The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

8.2 Functional Block Diagram




Figure 4. Logic Diagram (Positive Logic)

8.3 Feature Description

8.3.1 Balanced High-Drive CMOS Push-Pull Outputs

A balanced output allows the device to sink and source similar currents. The high drive capability of this device creates fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the power output of the device to be limited to avoid thermal runaway and damage due to over-current. The electrical and thermal limits defined the in the *Absolute Maximum Ratings* must be followed at all times.

8.3.2 Standard CMOS Inputs

Standard CMOS inputs are high impedance and are typically modelled as a resistor in parallel with the input capacitance given in the *Electrical Characteristics*. The worst case resistance is calculated with the maximum input voltage, given in the *Absolute Maximum Ratings*, and the maximum input leakage current, given in the *Electrical Characteristics*, using ohm's law $(R = V \div I)$.

Signals applied to the inputs need to have fast edge rates, as defined by $\Delta t/\Delta v$ in *Recommended Operating Conditions* to avoid excessive currents and oscillations. If a slow or noisy input signal is required, a device with a Schmitt-trigger input should be utilized to condition the input signal prior to the standard CMOS input.

Submit Documentation Feedback



Feature Description (continued)

8.3.3 Clamp Diodes

The inputs and outputs to this device have negative clamping diodes.

CAUTION

Voltages beyond the values specified in the *Absolute Maximum Ratings* table can cause damage to the device. The input negative-voltage and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




Figure 5. Electrical Placement of Clamping Diodes for Each Input and Output

8.3.4 Partial Power Down (I_{off})

The inputs and outputs for this device enter a high impedance state when the supply voltage is 0 V. The maximum leakage into or out of any input or output pin on the device is specified by I_{off} in the *Electrical Characteristics*.

8.3.5 Over-voltage Tolerant Inputs

Input signals to this device can be driven above the supply voltage so long as they remain below the maximum input voltage value specified in the *Absolute Maximum Ratings*.

8.4 Device Functional Modes

Table 1 lists the functions of this device.

Table 1. Function Table

	INPUTS						
ŌĒ	LE	D	Q				
L	Н	L	L				
L	Н	Н	Н				
L	L	Х	Q_0				
Н	Х	Х	Hi-Z				



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The SN74LVC1G373 latches can be used to store one bit of data. Figure 6 shows a typical application. The multiplexer is used to convert parallel data coming in from the latch into serial data using the A, B, and C select pins moving up in a sequence. With latch input low by a trigger event, the output Q holds the previous Q_0 data entered until the LE pin is cleared.

9.2 Typical Application




Figure 6. Latch Used With Multiplexer for Parallel to Serial Conversion

9.2.1 Design Requirements

This device uses CMOS technology and has balanced output drive. Take care to avoid bus contention because it can drive currents that would exceed maximum limits. The high drive also creates fast edges into light loads, so routing and load conditions must be considered to prevent ringing.

Submit Documentation Feedback



Typical Application (continued)

9.2.2 Detailed Design Procedure

- 1. Recommended Input Conditions
 - For rise time and fall time specifications, see $\Delta t/\Delta V$ in Recommended Operating Conditions.
 - For specified High and low levels, see V_{IH} and V_{IL} in Recommended Operating Conditions.
 - Inputs are overvoltage tolerant allowing them to go as high as 5.5 V at any valid V_{CC} .
- 2. Recommended Output Conditions
 - Load currents should not exceed 32 mA per output and 100 mA total through the part.
 - Outputs must not be pulled above V_{CC}.

9.2.3 Application Curve




Figure 7. Enable Time vs V_{CC}



10 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in Recommended Operating Conditions.

Each V_{CC} pin should have a good bypass capacitor to prevent power disturbance. For devices with a single supply, TI recommends a 0.1-µF bypass capacitor. If there are multiple V_{CC} pins, TI recommends 0.01-µF or 0.022-µF bypass capacitor for each power pin. It is acceptable to parallel multiple bypass capacitors to reject different frequencies of noise. 0.1-µF and 1-µF capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power pin as possible for best results.

11 Layout

11.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such input pins should not be left unconnected because the undefined voltages at the outside connections result in undefined operational states.

Specified in Figure 8 are rules that must be observed under all circumstances. All unused inputs of digital logic devices must be connected to a high or low bias to prevent them from floating. The logic level that should be applied to any particular unused input depends on the function of the device. Generally they will be tied to GND or VCC, whichever makes more sense or is more convenient.

Even low data rate digital signals can have high frequency signal components due to fast edge rates. When a PCB trace turns a corner at a 90° angle, a reflection can occur. A reflection occurs primarily because of the change of width of the trace. At the apex of the turn, the trace width increases to 1.414 times the width. This increase upsets the transmission-line characteristics, especially the distributed capacitance and self-inductance of the trace which results in the reflection. Not all PCB traces can be straight and therefore some traces must turn corners. Figure 9 shows progressively better techniques of rounding corners. Only the last example (BEST) maintains constant trace width and minimizes reflections.

11.2 Layout Example




Figure 8. Proper Multiple Input Termination Diagram




Figure 9. Trace Example

Submit Documentation Feedback Product Folder Links: SN74LVC1G373



12 Device and Documentation Support

12.1 Documentation Support

12.1.1 Related Documentation

For related documentation see the following:

Implications of Slow or Floating CMOS Inputs (SCBA004)

12.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

12.3 Community Resource

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.4 Trademarks

NanoFree, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

12.5 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 7-Oct-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
74LVC1G373DBVR1G4	Active	Production	SOT-23 (DBV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	(CA35, CA3R)
74LVC1G373DBVR1G4.B	Active	Production	SOT-23 (DBV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	(CA35, CA3R)
74LVC1G373DBVRE4	Active	Production	SOT-23 (DBV) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	(CA35, CA3R)
74LVC1G373DCKRE4	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	D35
74LVC1G373DCKRG4	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	D35
74LVC1G373DCKRG4.B	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	D35
SN74LVC1G373DBVR	Active	Production	SOT-23 (DBV) 6	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	(CA35, CA3R)
SN74LVC1G373DBVR.B	Active	Production	SOT-23 (DBV) 6	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	(CA35, CA3R)
SN74LVC1G373DCKR	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	(D35, D3J, D3R)
SN74LVC1G373DCKR.B	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	(D35, D3J, D3R)
SN74LVC1G373YZPR	Active	Production	DSBGA (YZP) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 85	D3N
SN74LVC1G373YZPR.B	Active	Production	DSBGA (YZP) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 85	D3N

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



PACKAGE OPTION ADDENDUM

www.ti.com 7-Oct-2025

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

www.ti.com 1-Nov-2025

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
74LVC1G373DBVR1G4	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
74LVC1G373DBVR1G4	SOT-23	DBV	6	3000	178.0	9.2	3.3	3.23	1.55	4.0	8.0	Q3
74LVC1G373DCKRG4	SC70	DCK	6	3000	178.0	9.2	2.4	2.4	1.22	4.0	8.0	Q3
SN74LVC1G373DBVR	SOT-23	DBV	6	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
SN74LVC1G373DCKR	SC70	DCK	6	3000	178.0	8.4	2.25	2.45	1.2	4.0	8.0	Q3
SN74LVC1G373DCKR	SC70	DCK	6	3000	180.0	8.4	2.3	2.5	1.2	4.0	8.0	Q3
SN74LVC1G373YZPR	DSBGA	YZP	6	3000	178.0	9.2	1.02	1.52	0.63	4.0	8.0	Q1



www.ti.com 1-Nov-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
74LVC1G373DBVR1G4	SOT-23	DBV	6	3000	202.0	201.0	28.0
74LVC1G373DBVR1G4	SOT-23	DBV	6	3000	180.0	180.0	18.0
74LVC1G373DCKRG4	SC70	DCK	6	3000	180.0	180.0	18.0
SN74LVC1G373DBVR	SOT-23	DBV	6	3000	208.0	191.0	35.0
SN74LVC1G373DCKR	SC70	DCK	6	3000	208.0	191.0	35.0
SN74LVC1G373DCKR	SC70	DCK	6	3000	210.0	185.0	35.0
SN74LVC1G373YZPR	DSBGA	YZP	6	3000	220.0	220.0	35.0





NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.25 per side.

- 4. Leads 1,2,3 may be wider than leads 4,5,6 for package orientation.
- 5. Refernce JEDEC MO-178.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





DIE SIZE BALL GRID ARRAY



NOTES:

NanoFree Is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.
- 3. NanoFree[™] package configuration.



DIE SIZE BALL GRID ARRAY



NOTES: (continued)

Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.
 For more information, see Texas Instruments literature number SBVA017 (www.ti.com/lit/sbva017).



DIE SIZE BALL GRID ARRAY



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.







NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.

 4. Falls within JEDEC MO-203 variation AB.





NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025