

# Single 3-Input Positive-XOR Gate

Check for Samples: SN74LVC1G386

### **FEATURES**


- Available in the Texas Instruments NanoStar <sup>™</sup> and NanoFree<sup>™</sup> Packages
- Supports 5-V V<sub>CC</sub> Operation
- Inputs Accept Voltages to 5.5 V
- Supports Down Translation to V<sub>CC</sub>
- I<sub>off</sub> Supports Live Insertion, Partial-Power-Down Mode, Back-Drive Protection
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

### DESCRIPTION

The SN74LVC1G386 device performs the Boolean function  $Y = A \times B \times C$  in positive logic.

NanoStar $^{\text{TM}}$  and NanoFree $^{\text{TM}}$  package technology is a major breakthrough in IC packaging concepts, using the die as the package.

This device is fully specified for partial-power-down applications using  $I_{\text{off}}$ . The  $I_{\text{off}}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.



See mechanical drawings for dimensions.

M

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.





These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### **Function Table**

|   | INPUTS |   | OUTPUT |
|---|--------|---|--------|
| Α | В      | С | Υ      |
| L | L      | L | L      |
| L | L      | Н | Н      |
| L | Н      | L | Н      |
| L | Н      | Н | L      |
| Н | L      | L | Н      |
| Н | L      | Н | L      |
| Н | Н      | L | L      |
| Н | Н      | Н | Н      |

### **Logic Diagram (Positive Logic)**



# Absolute Maximum Ratings(1)

over operating free-air temperature range (unless otherwise noted)

|                  |  |                                 | MIN  | MAX                   | UNIT |
|------------------|--|---------------------------------|------|-----------------------|------|
| $V_{CC}$         | Supply voltage range                               |                                 | -0.5 | 6.5                   | V    |
| VI               | Input voltage range <sup>(2)</sup>                 |                                 | -0.5 | 6.5                   | V    |
| Vo               | Voltage range applied to any output in the high-im | npedance or power-off state (2) | -0.5 | 6.5                   | V    |
| Vo               | Voltage range applied to any output in the high or | low state (2)(3)                | -0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>  | Input clamp current                                | V <sub>I</sub> < 0              |      | -50                   | mA   |
| I <sub>OK</sub>  | Output clamp current                               | V <sub>O</sub> < 0              |      | -50                   | mA   |
| Io               | Continuous output current                          |                                 |      | ±50                   | mA   |
|                  | Continuous current through V <sub>CC</sub> or GND  |                                 |      | ±100                  | mA   |
|                  |  | DBV package                     |      | 165                   |      |
| $\theta_{JA}$    | Package thermal impedance <sup>(4)</sup>           | DCK package                     |      | 259                   | °C/W |
|                  |  | YEP or YZP package              |      | 123                   |      |
| T <sub>stg</sub> | Storage temperature range                          |                                 | -65  | 150                   | °C   |

<sup>(1)</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

Submit Documentation Feedback

<sup>(2)</sup> The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

<sup>(3)</sup> The value of V<sub>CC</sub> is provided in the recommended operating conditions table.

<sup>(4)</sup> The package thermal impedance is calculated in accordance with JESD 51-7.



# **Recommended Operating Conditions**(1)

|                 |                                    |  | MIN  | MAX                    | UNIT |
|-----------------|------------------------------------|--|--|------------------------|------|
| .,              | Cumply walte no                    | Operating  | 1.65   | 5.5                    | V    |
| V <sub>CC</sub> | Supply voltage                     | Data retention only  | 1.5  |                        | V    |
|                 |                                    | V <sub>CC</sub> = 1.65 V to 1.95 V   | 0.65 × V <sub>CC</sub>                       |                        |      |
| . ,             | Lifeth James Computer of France    | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.7  |                        | .,   |
| V <sub>IH</sub> | High-level input voltage           | V <sub>CC</sub> = 3 V to 3.6 V   | 2  |                        | V    |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V   | 1.65<br>1.5<br>0.65 × V <sub>CC</sub><br>1.7 |                        |      |
|                 |                                    | V <sub>CC</sub> = 1.65 V to 1.95 V   |  | 0.35 × V <sub>CC</sub> |      |
| . ,             | Law law Paratasta                  | V <sub>CC</sub> = 2.3 V to 2.7 V   |  | 0.7                    | .,   |
| $V_{IL}$        | Low-level input voltage            | V <sub>CC</sub> = 3 V to 3.6 V   |  | 0.8                    | V    |
|                 |                                    | V <sub>CC</sub> = 4.5 V to 5.5 V   |  | 0.3 × V <sub>CC</sub>  |      |
| VI              | Input voltage                      |  | 0  | 5.5                    | V    |
| V <sub>O</sub>  | Output voltage                     |  | 0  | V <sub>CC</sub>        | V    |
|                 |                                    | V <sub>CC</sub> = 1.65 V   |  | -4                     |      |
|                 | High-level input voltage           | V <sub>CC</sub> = 2.3 V  |  | -8                     |      |
| l <sub>он</sub> |                                    | V 0.V  |  | -16                    | mA   |
|                 |                                    |  | -24  |                        |      |
|                 |                                    | V <sub>CC</sub> = 4.5 V  |  | -32                    |      |
|                 |                                    | V <sub>CC</sub> = 1.65 V   |  | 4                      |      |
|                 |                                    | V <sub>CC</sub> = 2.3 V  |  | 8                      |      |
| loL             | Low-level output current           | V 0.V  |  | 16                     | mA   |
|                 |                                    | V <sub>CC</sub> = 3 V  |  | 24                     |      |
|                 |                                    | V <sub>CC</sub> = 4.5 V  |  | 32                     |      |
|                 |                                    | $V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}, 2.5 \text{ V} \pm 0.2 \text{ V}$ |  | 20                     |      |
| Δt/Δv           | Input transition rise or fall rate | $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$                                   |  | 10                     | ns/V |
|                 |                                    |  |  | 5                      |      |
| T <sub>A</sub>  | Operating free-air temperature     | ,  | -40  | 125                    | °C   |

<sup>(1)</sup> All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

Product Folder Links: SN74LVC1G386



## **Electrical Characteristics**

over recommended operating free-air temperature range (unless otherwise noted)

| DADAMETED                 | TEST COMPLETIONS  | .,                 | -40°                  | C to 85°C          |      | –40°0                 | C to 125°C         |      |      |
|---------------------------|---|--------------------|-----------------------|--------------------|------|-----------------------|--------------------|------|------|
| PARAMETER                 | TEST CONDITIONS   | V <sub>cc</sub>    | MIN                   | TYP <sup>(1)</sup> | MAX  | MIN                   | TYP <sup>(1)</sup> | MAX  | UNIT |
|                           | I <sub>OH</sub> = -100 μA   | 1.65 V to<br>5.5 V | V <sub>CC</sub> - 0.1 |                    |      | V <sub>CC</sub> - 0.1 |                    |      |      |
|                           | $I_{OH} = -4 \text{ mA}$  | 1.65 V             | 1.2                   |                    |      | 1.2                   |                    |      |      |
| V <sub>OH</sub>           | $I_{OH} = -8 \text{ mA}$  | 2.3 V              | 1.9                   |                    |      | 1.9                   |                    |      | V    |
| <b></b>                   | I <sub>OH</sub> = -16 mA  | 2.1/               | 2.4                   |                    |      | 2.4                   |                    |      |      |
|                           | $I_{OH} = -24 \text{ mA}$   | 3 V                | 2.3                   |                    |      | 2.3                   |                    |      |      |
|                           | $I_{OH} = -32 \text{ mA}$   | 4.5 V              | 3.8                   |                    |      | 3.8                   |                    |      |      |
|                           | I <sub>OL</sub> = 100 μA  | 1.65 V to<br>5.5 V |                       |                    | 0.1  |                       |                    | 0.1  |      |
|                           | I <sub>OL</sub> = 4 mA  | 1.65 V             |                       |                    | 0.45 |                       |                    | 0.45 |      |
| V <sub>OL</sub>           | I <sub>OL</sub> = 8 mA  | 2.3 V              |                       |                    | 0.3  |                       |                    | 0.3  | V    |
|                           | I <sub>OL</sub> = 16 mA   | 3 V                |                       |                    | 0.4  |                       |                    | 0.4  |      |
|                           | I <sub>OL</sub> = 24 mA   | 3 V                |                       |                    | 0.55 |                       |                    | 0.55 |      |
|                           | I <sub>OL</sub> = 32 mA   | 4.5 V              |                       |                    | 0.55 |                       |                    | 0.55 |      |
| I <sub>I</sub> All inputs | V <sub>I</sub> = 5.5 V or GND   | 0 to 5.5 V         |                       |                    | ±5   |                       |                    | ±5   | μΑ   |
| I <sub>off</sub>          | $V_I$ or $V_O = 5.5 \text{ V}$  | 0                  |                       |                    | ±10  |                       |                    | ±10  | μΑ   |
| Icc                       | V <sub>I</sub> = 5.5 V or GND, I <sub>O</sub> = 0                               | 1.65 V to<br>5.5 V |                       |                    | 10   |                       |                    | 10   | μA   |
| ΔI <sub>CC</sub>          | One input at V <sub>CC</sub> - 0.6 V,<br>Other inputs at V <sub>CC</sub> or GND | 3 V to 5.5 V       |                       |                    | 500  |                       |                    | 500  | μA   |
| Ci                        | V <sub>I</sub> = V <sub>CC</sub> or GND   | 3.3 V              |                       | 3.5                |      |                       |                    |      | pF   |

<sup>(1)</sup> All typical values are at  $V_{CC}$  = 3.3 V,  $T_A$  = 25°C.



## **Switching Characteristics**

over recommended operating free-air temperature range, C<sub>L</sub> = 15 pF (unless otherwise noted) (see Figure 1)

|                 |                 | TO<br>(OUTPUT) | -40°C to 85°C                       |     |                                    |     |                                    |     |                                  |     |      |
|-----------------|-----------------|----------------|-------------------------------------|-----|------------------------------------|-----|------------------------------------|-----|----------------------------------|-----|------|
| PARAMETER       | FROM<br>(INPUT) |                | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | V <sub>CC</sub> = 5 V<br>± 0.5 V |     | UNIT |
|                 |                 |                | MIN                                 | MAX | MIN                                | MAX | MIN                                | MAX | MIN                              | MAX |      |
| t <sub>pd</sub> | A, B, or C      | Y              | 3                                   | 9.4 | 1.3                                | 5   | 0.8                                | 4.5 | 0.5                              | 3.5 | ns   |

## **Switching Characteristics**

over recommended operating free-air temperature range,  $C_L = 30 \text{ pF}$  or 50 pF (unless otherwise noted) (see Figure 2)

|                 |                 |                | −40°C to 85°C                       |     |                                    |     |     |     |                                  |     |      |
|-----------------|-----------------|----------------|-------------------------------------|-----|------------------------------------|-----|-----|-----|----------------------------------|-----|------|
| PARAMETER       | FROM<br>(INPUT) | TO<br>(OUTPUT) | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     |     |     | V <sub>CC</sub> = 5 V<br>± 0.5 V |     | UNIT |
|                 |                 |                | MIN                                 | MAX | MIN                                | MAX | MIN | MAX | MIN                              | MAX |      |
| t <sub>pd</sub> | A, B, or C      | Υ              | 3.5                                 | 12  | 1.8                                | 5.5 | 1.3 | 5   | 1                                | 4   | ns   |

# **Switching Characteristics**

over recommended operating free-air temperature range,  $C_L = 30 \text{ pF}$  or 50 pF (unless otherwise noted) (see Figure 2)

|                 |                 | TO<br>(OUTPUT) |                                     | -40°C to 125°C |                                    |     |                                    |     |                                  |     |      |
|-----------------|-----------------|----------------|-------------------------------------|----------------|------------------------------------|-----|------------------------------------|-----|----------------------------------|-----|------|
| PARAMETER       | FROM<br>(INPUT) |                | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |                | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | V <sub>CC</sub> = 5 V<br>± 0.5 V |     | UNIT |
|                 |                 |                | MIN                                 | MAX            | MIN                                | MAX | MIN                                | MAX | MIN                              | MAX |      |
| t <sub>pd</sub> | A, B, or C      | Y              | 3.5                                 | 14.8           | 1.8                                | 7.2 | 1.3                                | 6.4 | 1                                | 5.1 | ns   |

# **Operating Characteristics**


 $T_A = 25^{\circ}C$ 

| PARAMETER |                               | TEST CONDITIONS | V <sub>CC</sub> = 1.8 V | V <sub>CC</sub> = 1.8 V V <sub>CC</sub> = 2.5 V |     | $V_{CC} = 5 V$ | UNIT |  |
|-----------|-------------------------------|-----------------|-------------------------|---|-----|----------------|------|--|
|           | FARAMETER                     | TEST CONDITIONS | TYP                     | TYP   | TYP | TYP            | UNII |  |
| $C_{pd}$  | Power dissipation capacitance | f = 10 MHz      | 17.5                    | 18  | 19  | 22             | pF   |  |

Product Folder Links: SN74LVC1G386




#### **Parameter Measurement Information**



| TEST                                 | S1                       |
|--------------------------------------|--------------------------|
| t <sub>PZL</sub> (see Notes E and F) | V <sub>LOAD</sub>        |
| t <sub>PLZ</sub> (see Notes E and G) | $V_{LOAD}$               |
| t <sub>PHZ</sub> /t <sub>PZH</sub>   | <b>V</b> <sub>LOAD</sub> |

LOAD CIRCUIT

| .,                | INPUTS          |         | .,                                     | .,                  |                | _              |                |
|-------------------|-----------------|---------|--|---------------------|----------------|----------------|----------------|
| V <sub>cc</sub>   | V,              | t,/t,   | t,/t, V <sub>M</sub> V <sub>LOAD</sub> |                     | C <sub>∟</sub> | R <sub>⊾</sub> | V <sub>Δ</sub> |
| 1.8 V ± 0.15 V    | V <sub>cc</sub> | ≤2 ns   | V <sub>cc</sub> /2                     | 2 × V <sub>cc</sub> | 15 pF          | <b>1 M</b> Ω   | 0.15 V         |
| 2.5 V $\pm$ 0.2 V | V <sub>cc</sub> | ≤2 ns   | V <sub>cc</sub> /2                     | 2 × V <sub>cc</sub> | 15 pF          | <b>1 M</b> Ω   | 0.15 V         |
| 3.3 V $\pm$ 0.3 V | 3 V             | ≤2.5 ns | 1.5 V                                  | 6 V                 | 15 pF          | <b>1 Μ</b> Ω   | 0.3 V          |
| 5 V $\pm$ 0.5 V   | V <sub>cc</sub> | ≤2.5 ns | V <sub>cc</sub> /2                     | 2 × V <sub>cc</sub> | 15 pF          | <b>1 Μ</b> Ω   | 0.3 V          |



NOTES: A. C<sub>⊥</sub> includes probe and jig capacitance.


- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators have the following characteristics: PRR  $\leq$  10 MHz,  $Z_o$  = 50  $\Omega$ .
- D. The outputs are measured one at a time, with one transition per measurement.
- E. Because this device has open-drain outputs,  $t_{\tiny PLZ}$  and  $t_{\tiny PZL}$  are the same as  $t_{\tiny PD}$ .
- F.  $t_{PZL}$  is measured at  $V_{M}$ .
- G.  $t_{PLZ}$  is measured at  $V_{OL}$  +  $V_{\Delta}$ .
- H. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms

Submit Documentation Feedback




#### **Parameter Measurement Information**



| TEST                                      | S1                       |
|---|--------------------------|
| t <sub>PLH</sub> /t <sub>PHL</sub>        | Open                     |
| $t_{_{\mathrm{PLZ}}}/t_{_{\mathrm{PZL}}}$ | <b>V</b> <sub>LOAD</sub> |
| t <sub>PHZ</sub> /t <sub>PZH</sub>        | GND                      |

**LOAD CIRCUIT** 

| V               | INPUTS   |         | V                  | V                   |                |                | \ \ \  |
|-----------------|--|---------|--------------------|---------------------|----------------|----------------|--------|
| V <sub>cc</sub> | V <sub>1</sub> t <sub>r</sub> /t <sub>r</sub> V <sub>M</sub> V <sub>LOAD</sub> |         | V <sub>LOAD</sub>  | C <sub>L</sub>      | R <sub>⊾</sub> | V <sub>Δ</sub> |        |
| 1.8 V ± 0.15 V  | V <sub>cc</sub>  | ≤2 ns   | V <sub>cc</sub> /2 | 2 × V <sub>cc</sub> | 30 pF          | <b>1 k</b> Ω   | 0.15 V |
| 2.5 V ± 0.2 V   | $V_{cc}$   | ≤2 ns   | V <sub>cc</sub> /2 | 2 × V <sub>cc</sub> | 30 pF          | 500 Ω          | 0.15 V |
| 3.3 V ± 0.3 V   | 3 V  | ≤2.5 ns | 1.5 V              | 6 V                 | 50 pF          | 500 Ω          | 0.3 V  |
| 5 V ± 0.5 V     | $V_{cc}$   | ≤2.5 ns | V <sub>cc</sub> /2 | 2 × V <sub>cc</sub> | 50 pF          | 500 Ω          | 0.3 V  |



NOTES: A.  $C_L$  includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_o$  = 50  $\Omega$ .
- D. The outputs are measured one at a time, with one transition per measurement.
- E.  $t_{\mbox{\tiny PLZ}}$  and  $\dot{t}_{\mbox{\tiny PHZ}}$  are the same as  $t_{\mbox{\tiny dis}}.$
- F.  $t_{\mbox{\tiny PZL}}$  and  $t_{\mbox{\tiny PZH}}$  are the same as  $t_{\mbox{\tiny en}}.$
- G.  $t_{\text{PLH}}$  and  $t_{\text{PHL}}$  are the same as  $t_{\text{pd}}$ .
- H. All parameters and waveforms are not applicable to all devices.

Figure 2. Load Circuit and Voltage Waveforms

Submit Documentation Feedback

### SCES439E -APRIL 2003-REVISED DECEMBER 2013



## **REVISION HISTORY**

| Changes from Revision D (July 2006) to Revision E |   |   |  |  |
|---|---|---|--|--|
| •   | Updated document to new TI data sheet format. | 1 |  |  |
| •   | Updated Features.                             | 1 |  |  |
| •   | Added ESD warning.                            | 2 |  |  |
| •   | Updated operating temperature range.          | 3 |  |  |

www.ti.com 11-Nov-2025

#### PACKAGING INFORMATION

| Orderable part number | Status | Material type | Package   Pins   | Package qty   Carrier | RoHS | Lead finish/<br>Ball material | MSL rating/<br>Peak reflow | Op temp (°C) | Part marking (6) |
|-----------------------|--------|---------------|------------------|-----------------------|------|-------------------------------|----------------------------|--------------|------------------|
|                       |        | ``            |                  |                       |      | (4)                           | (5)                        |              |                  |
| 74LVC1G386DCKRG4      | Active | Production    | SC70 (DCK)   6   | 3000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8R              |
| 74LVC1G386DCKRG4.B    | Active | Production    | SC70 (DCK)   6   | 3000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8R              |
| SN74LVC1G386DBVR      | Active | Production    | SOT-23 (DBV)   6 | 3000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | CC6R             |
| SN74LVC1G386DBVR.B    | Active | Production    | SOT-23 (DBV)   6 | 3000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | CC6R             |
| SN74LVC1G386DCKR      | Active | Production    | SC70 (DCK)   6   | 3000   LARGE T&R      | Yes  | NIPDAU   SN                   | Level-1-260C-UNLIM         | -40 to 125   | (C8J, C8R)       |
| SN74LVC1G386DCKR.B    | Active | Production    | SC70 (DCK)   6   | 3000   LARGE T&R      | Yes  | SN                            | Level-1-260C-UNLIM         | -40 to 125   | (C8J, C8R)       |
| SN74LVC1G386DRYR      | Active | Production    | SON (DRY)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386DRYR.B    | Active | Production    | SON (DRY)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386DSFR      | Active | Production    | SON (DSF)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386DSFR.B    | Active | Production    | SON (DSF)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386DSFRG4    | Active | Production    | SON (DSF)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386DSFRG4.B  | Active | Production    | SON (DSF)   6    | 5000   LARGE T&R      | Yes  | NIPDAU                        | Level-1-260C-UNLIM         | -40 to 125   | C8               |
| SN74LVC1G386YZPR      | Active | Production    | DSBGA (YZP)   6  | 3000   LARGE T&R      | Yes  | SNAGCU                        | Level-1-260C-UNLIM         | -40 to 85    | C8N              |
| SN74LVC1G386YZPR.B    | Active | Production    | DSBGA (YZP)   6  | 3000   LARGE T&R      | Yes  | SNAGCU                        | Level-1-260C-UNLIM         | -40 to 85    | C8N              |

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 11-Nov-2025

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 18-Jun-2025

### TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

| Device             | Package<br>Type | Package<br>Drawing |   | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|--------------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| 74LVC1G386DCKRG4   | SC70            | DCK                | 6 | 3000 | 180.0                    | 8.4                      | 2.47       | 2.3        | 1.25       | 4.0        | 8.0       | Q3               |
| SN74LVC1G386DBVR   | SOT-23          | DBV                | 6 | 3000 | 180.0                    | 8.4                      | 3.23       | 3.17       | 1.37       | 4.0        | 8.0       | Q3               |
| SN74LVC1G386DCKR   | SC70            | DCK                | 6 | 3000 | 178.0                    | 9.0                      | 2.4        | 2.5        | 1.2        | 4.0        | 8.0       | Q3               |
| SN74LVC1G386DRYR   | SON             | DRY                | 6 | 5000 | 180.0                    | 9.5                      | 1.15       | 1.6        | 0.75       | 4.0        | 8.0       | Q1               |
| SN74LVC1G386DSFR   | SON             | DSF                | 6 | 5000 | 180.0                    | 9.5                      | 1.16       | 1.16       | 0.5        | 4.0        | 8.0       | Q2               |
| SN74LVC1G386DSFRG4 | SON             | DSF                | 6 | 5000 | 180.0                    | 9.5                      | 1.16       | 1.16       | 0.5        | 4.0        | 8.0       | Q2               |
| SN74LVC1G386YZPR   | DSBGA           | YZP                | 6 | 3000 | 178.0                    | 9.2                      | 1.02       | 1.52       | 0.63       | 4.0        | 8.0       | Q1               |



www.ti.com 18-Jun-2025



\*All dimensions are nominal

| Device             | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| 74LVC1G386DCKRG4   | SC70         | DCK             | 6    | 3000 | 183.0       | 183.0      | 20.0        |
| SN74LVC1G386DBVR   | SOT-23       | DBV             | 6    | 3000 | 202.0       | 201.0      | 28.0        |
| SN74LVC1G386DCKR   | SC70         | DCK             | 6    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74LVC1G386DRYR   | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G386DSFR   | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G386DSFRG4 | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G386YZPR   | DSBGA        | YZP             | 6    | 3000 | 220.0       | 220.0      | 35.0        |





### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.

  4. Falls within JEDEC MO-203 variation AB.





NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.





Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.









#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.





NOTES: (continued)

3. For more information, see QFN/SON PCB application report in literature No. SLUA271 (www.ti.com/lit/slua271).





NOTES: (continued)

Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.







### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. Reference JEDEC registration MO-287, variation X2AAF.





NOTES: (continued)

4. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).





4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.







### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.25 per side.

- 4. Leads 1,2,3 may be wider than leads 4,5,6 for package orientation.
- 5. Refernce JEDEC MO-178.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





DIE SIZE BALL GRID ARRAY



#### NOTES:

NanoFree Is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.
- 3. NanoFree<sup>™</sup> package configuration.



DIE SIZE BALL GRID ARRAY



NOTES: (continued)

Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.
 For more information, see Texas Instruments literature number SBVA017 (www.ti.com/lit/sbva017).



DIE SIZE BALL GRID ARRAY



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025