

# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

- Complete PWM Power Control
- 3.6-V to 40-V Operation
- Internal Undervoltage-Lockout Circuit
- Internal Short-Circuit Protection
- Oscillator Frequency . . . 20 kHz to 500 kHz
- Variable Dead Time Provides Control Over Total Range
- $\pm 3\%$  Tolerance on Reference Voltage (TL5001A)
- Available in Q-Temp Automotive HighRel Automotive Applications Configuration Control / Print Support Qualification to Automotive Standards

## description

The TL5001 and TL5001A incorporate on a single monolithic chip all the functions required for a pulse-width-modulation (PWM) control circuit. Designed primarily for power-supply control, the TL5001/A contains an error amplifier, a regulator, an oscillator, a PWM comparator with a dead-time-control input, undervoltage lockout (UVLO), short-circuit protection (SCP), and an open-collector output transistor. The TL5001A has a typical reference voltage tolerance of  $\pm 3\%$  compared to  $\pm 5\%$  for the TL5001.


The error-amplifier common-mode voltage ranges from 0 V to 1.5 V. The noninverting input of the error amplifier is connected to a 1-V reference. Dead-time control (DTC) can be set to provide 0% to 100% dead time by connecting an external resistor between DTC and GND. The oscillator frequency is set by terminating RT with an external resistor to GND. During low  $V_{CC}$  conditions, the UVLO circuit turns the output off until  $V_{CC}$  recovers to its normal operating range.

The TL5001C and TL5001AC are characterized for operation from  $-20^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ . The TL5001I and TL5001AI are characterized for operation from  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ . The TL5001Q and TL5001AQ are characterized for operation from  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The TL5001M and TL5001AM are characterized for operation from  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

### AVAILABLE OPTIONS

| T <sub>A</sub>                                 | PACKAGED DEVICES  |                 |                  |                   |
|------------------------------------------------|-------------------|-----------------|------------------|-------------------|
|                                                | SMALL OUTLINE (D) | PLASTIC DIP (P) | CERAMIC DIP (JG) | CHIP CARRIER (FK) |
| $-20^{\circ}\text{C}$ to $85^{\circ}\text{C}$  | TL5001CD          | TL5001CP        | —                | —                 |
|                                                | TL5001ACD         | TL5001ACP       | —                | —                 |
| $-40^{\circ}\text{C}$ to $85^{\circ}\text{C}$  | TL5001ID          | TL5001IP        | —                | —                 |
|                                                | TL5001AID         | TL5001AIP       | —                | —                 |
| $-40^{\circ}\text{C}$ to $125^{\circ}\text{C}$ | TL5001QD          | —               | —                | —                 |
|                                                | TL5001AQD         | —               | —                | —                 |
| $-55^{\circ}\text{C}$ to $125^{\circ}\text{C}$ | —                 | —               | TL5001MJG        | TL5001MFK         |
|                                                | —                 | —               | TL5001AMJG       | TL5001AMFK        |

The D package is available taped and reeled. Add the suffix R to the device type (e.g., TL5001CDR).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**


POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2002, Texas Instruments Incorporated  
On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.


# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

## schematic for typical application



## functional block diagram



## detailed description


### voltage reference

A 2.5-V regulator operating from  $V_{CC}$  is used to power the internal circuitry of the TL5001 and TL5001A and as a reference for the error amplifier and SCP circuits. A resistive divider provides a 1-V reference for the error amplifier noninverting input which typically is within 2% of nominal over the operating temperature range.

### error amplifier

The error amplifier compares a sample of the dc-to-dc converter output voltage to the 1-V reference and generates an error signal for the PWM comparator. The dc-to-dc converter output voltage is set by selecting the error-amplifier gain (see Figure 1), using the following expression:

$$V_O = (1 + R1/R2) (1 \text{ V})$$



**Figure 1. Error-Amplifier Gain Setting**

The error-amplifier output is brought out as COMP for use in compensating the dc-to-dc converter control loop for stability. Because the amplifier can only source 45  $\mu$ A, the total dc load resistance should be 100 k $\Omega$  or more.

### oscillator/PWM

The oscillator frequency ( $f_{osc}$ ) can be set between 20 kHz and 500 kHz by connecting a resistor between RT and GND. Acceptable resistor values range from 15 k $\Omega$  to 250 k $\Omega$ . The oscillator frequency can be determined by using the graph shown in Figure 5.

The oscillator output is a triangular wave with a minimum value of approximately 0.7 V and a maximum value of approximately 1.3 V. The PWM comparator compares the error-amplifier output voltage and the DTC input voltage to the triangular wave and turns the output transistor off whenever the triangular wave is greater than the lesser of the two inputs.

### dead-time control (DTC)

DTC provides a means of limiting the output-switch duty cycle to a value less than 100%, which is critical for boost and flyback converters. A current source generates a reference current ( $I_{DT}$ ) at DTC that is nominally equal to the current at the oscillator timing terminal, RT. Connecting a resistor between DTC and GND generates a dead-time reference voltage ( $V_{DT}$ ), which the PWM/DTC comparator compares to the oscillator triangle wave as described in the previous section. Nominally, the maximum duty cycle is 0% when  $V_{DT}$  is 0.7 V or less and 100% when  $V_{DT}$  is 1.3 V or greater. Because the triangle wave amplitude is a function of frequency and the source impedance of RT is relatively high (1250  $\Omega$ ), choosing  $R_{DT}$  for a specific maximum duty cycle, D, is accomplished using the following equation and the voltage limits for the frequency in question as found in Figure 11 ( $V_{osc,max}$  and  $V_{osc,min}$  are the maximum and minimum oscillator levels):

# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

### dead-time control (DTC) (continued)

$$R_{DT} = (R_t + 1250) [D(V_{oscmax} - V_{oscmin}) + V_{oscmin}]$$

Where

$R_{DT}$  and  $R_t$  are in ohms,  $D$  in decimal

Soft start can be implemented by paralleling the DTC resistor with a capacitor ( $C_{DT}$ ) as shown in Figure 2. During soft start, the voltage at DTC is derived by the following equation:

$$V_{DT} \approx I_{DT} R_{DT} \left( 1 - e^{-t/R_{DT} C_{DT}} \right)$$




Figure 2. Soft-Start Circuit

If the dc-to-dc converter must be in regulation within a specified period of time, the time constant,  $R_{DT}C_{DT}$ , should be  $t_0/3$  to  $t_0/5$ . The TL5001/A remains off until  $V_{DT} \approx 0.7$  V, the minimum ramp value.  $C_{DT}$  is discharged every time UVLO or SCP becomes active.

### undervoltage-lockout (UVLO) protection

The undervoltage-lockout circuit turns the output transistor off and resets the SCP latch whenever the supply voltage drops too low (approximately 3 V at 25°C) for proper operation. A hysteresis voltage of 200 mV eliminates false triggering on noise and chattering.

### short-circuit protection (SCP)

The TL5001/A includes short-circuit protection (see Figure 3), which turns the power switch off to prevent damage when the converter output is shorted. When activated, the SCP prevents the switch from being turned on until the internal latching circuit is reset. The circuit is reset by reducing the input voltage until UVLO becomes active or until the SCP terminal is pulled to ground externally.

When a short circuit occurs, the error-amplifier output at COMP rises to increase the power-switch duty cycle in an attempt to maintain the output voltage. SCP comparator 1 starts an RC timing circuit when COMP exceeds 1.5 V. If the short is removed and the error-amplifier output drops below 1.5 V before time out, normal converter operation continues. If the fault is still present at the end of the time-out period, the timer sets the latching circuit and turns off the TL5001/A output transistor.

## short-circuit protection (SCP) (continued)




Figure 3. SCP Circuit

The timer operates by charging an external capacitor ( $C_{SCP}$ ), connected between the SCP terminal and ground, towards 2.5 V through a 185-k $\Omega$  resistor ( $R_{SCP}$ ). The circuit begins charging from an initial voltage of approximately 185 mV and times out when the capacitor voltage reaches 1 V. The output of SCP comparator 2 then goes high, turns on Q2, and latches the timer circuit. The expression for setting the SCP time period is derived from the following equation:

$$V_{SCP} = (2.5 - 0.185)(1 - e^{-t/\tau}) + 0.185$$

Where

$$\tau = R_{SCP}C_{SCP}$$

The end of the time-out period,  $t_{SCP}$ , occurs when  $V_{SCP} = 1$  V. Solving for  $C_{SCP}$  yields:

$$C_{SCP} = 12.46 \times t_{SCP}$$

Where

$t$  is in seconds,  $C$  in  $\mu$ F.

$t_{SCP}$  must be much longer (generally 10 to 15 times) than the converter start-up period or the converter will not start.

## output transistor

The output of the TL5001/A is an open-collector transistor with a maximum collector current rating of 21 mA and a voltage rating of 51 V. The output is turned on under the following conditions: the oscillator triangle wave is lower than both the DTC voltage and the error-amplifier output voltage, the UVLO circuit is inactive, and the short-circuit protection circuit is inactive.

# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                              |                              |
|--------------------------------------------------------------|------------------------------|
| Supply voltage, $V_{CC}$ (see Note 1)                        | 41 V                         |
| Amplifier input voltage, $V_{I(FB)}$                         | 20 V                         |
| Output voltage, $V_{O, OUT}$                                 | 51 V                         |
| Output current, $I_{O, OUT}$                                 | 21 mA                        |
| Output peak current, $I_{O(peak), OUT}$                      | 100 mA                       |
| Continuous total power dissipation                           | See Dissipation Rating Table |
| Operating ambient temperature range, $T_A$ :                 |                              |
| TL5001C, TL5001AC                                            | –20°C to 85°C                |
| TL5001I, TL5001AI                                            | –40°C to 85°C                |
| TL5001Q, TL5001AQ                                            | –40°C to 125°C               |
| TL5001M, TL5001AM                                            | –55°C to 125°C               |
| Storage temperature range, $T_{stg}$                         | –65°C to 150°C               |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds | 260°C                        |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: All voltage values are with respect to network ground terminal.

DISSIPATION RATING TABLE

| PACKAGE | $T_A \leq 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A = 25^\circ\text{C}$ | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 85^\circ\text{C}$<br>POWER RATING | $T_A = 125^\circ\text{C}$<br>POWER RATING |
|---------|---------------------------------------------|---------------------------------------------------|------------------------------------------|------------------------------------------|-------------------------------------------|
| D       | 725 mW                                      | 5.8 mW/°C                                         | 464 mW                                   | 377 mW                                   | 145 mW                                    |
| FK      | 1375 mW                                     | 11.0 mW/°C                                        | 880 mW                                   | 715 mW                                   | 275 mW                                    |
| JG      | 1050 mW                                     | 8.4 mW/°C                                         | 672 mW                                   | 546 mW                                   | 210 mW                                    |
| P       | 1000 mW                                     | 8.0 mW/°C                                         | 640 mW                                   | 520 mW                                   | 200 mW                                    |

### recommended operating conditions

|                                      | MIN               | MAX | UNIT    |
|--------------------------------------|-------------------|-----|---------|
| Supply voltage, $V_{CC}$             | 3.6               | 40  | V       |
| Amplifier input voltage, $V_{I(FB)}$ | 0                 | 1.5 | V       |
| Output voltage, $V_{O, OUT}$         |                   | 50  | V       |
| Output current, $I_{O, OUT}$         |                   | 20  | mA      |
| COMP source current                  |                   | 45  | μA      |
| COMP dc load resistance              | 100               |     | kΩ      |
| Oscillator timing resistor, $R_t$    | 15                | 250 | kΩ      |
| Oscillator frequency, $f_{osc}$      | 20                | 500 | kHz     |
| Operating ambient temperature, $T_A$ | TL5001C, TL5001AC |     | –20 85  |
|                                      | TL5001I, TL5001AI |     | –40 85  |
|                                      | TL5001Q, TL5001AQ |     | –40 125 |
|                                      | TL5001M, TL5001AM |     | –55 125 |

# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f_{osc} = 100\text{ kHz}$  (unless otherwise noted)

## reference

| PARAMETER                              | TEST CONDITIONS                                          | TL5001C, TL5001I |      |      | TL5001AC, TL5001AI |      |      | UNIT |
|----------------------------------------|----------------------------------------------------------|------------------|------|------|--------------------|------|------|------|
|                                        |                                                          | MIN              | TYP† | MAX  | MIN                | TYP† | MAX  |      |
| Output voltage                         | COMP connected to FB                                     | 0.95             | 1    | 1.05 | 0.97               | 1    | 1.03 | V    |
| Input regulation                       | $V_{CC} = 3.6\text{ V to }40\text{ V}$                   |                  | 2    | 12.5 |                    | 2    | 12.5 | mV   |
| Output voltage change with temperature | $T_A = -20^\circ\text{C to }25^\circ\text{C}$ (C suffix) | -10              | -1   | 10   | -10                | -1   | 10   | mV/V |
|                                        | $T_A = -40^\circ\text{C to }25^\circ\text{C}$ (I suffix) | -10              | -1   | 10   | -10                | -1   | 10   |      |
|                                        | $T_A = 25^\circ\text{C to }85^\circ\text{C}$             | -10              | -2   | 10   | -10                | -2   | 10   |      |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

## undervoltage lockout

| PARAMETER               | TEST CONDITIONS          | TL5001C, TL5001I |      |     | TL5001AC, TL5001AI |      |     | UNIT |
|-------------------------|--------------------------|------------------|------|-----|--------------------|------|-----|------|
|                         |                          | MIN              | TYP† | MAX | MIN                | TYP† | MAX |      |
| Upper threshold voltage | $T_A = 25^\circ\text{C}$ |                  | 3    |     |                    | 3    |     | V    |
| Lower threshold voltage | $T_A = 25^\circ\text{C}$ |                  | 2.8  |     |                    | 2.8  |     | V    |
| Hysteresis              | $T_A = 25^\circ\text{C}$ | 100              | 200  |     | 100                | 200  |     | mV   |
| Reset threshold voltage | $T_A = 25^\circ\text{C}$ | 2.1              | 2.55 |     | 2.1                | 2.55 |     | V    |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

## short-circuit protection

| PARAMETER                          | TEST CONDITIONS          | TL5001C, TL5001I |      |      | TL5001AC, TL5001AI |      |      | UNIT          |
|------------------------------------|--------------------------|------------------|------|------|--------------------|------|------|---------------|
|                                    |                          | MIN              | TYP† | MAX  | MIN                | TYP† | MAX  |               |
| SCP threshold voltage              | $T_A = 25^\circ\text{C}$ | 0.95             | 1.00 | 1.05 | 0.97               | 1.00 | 1.03 | V             |
| SCP voltage, latched               | No pullup                | 140              | 185  | 230  | 140                | 185  | 230  | mV            |
| SCP voltage, UVLO standby          | No pullup                |                  | 60   | 120  |                    | 60   | 120  | mV            |
| Input source current               | $T_A = 25^\circ\text{C}$ | -10              | -15  | -20  | -10                | -15  | -20  | $\mu\text{A}$ |
| SCP comparator 1 threshold voltage |                          |                  | 1.5  |      |                    | 1.5  |      | V             |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

## oscillator

| PARAMETER                         | TEST CONDITIONS                               | TL5001C, TL5001I |      |     | TL5001AC, TL5001AI |      |     | UNIT |
|-----------------------------------|-----------------------------------------------|------------------|------|-----|--------------------|------|-----|------|
|                                   |                                               | MIN              | TYP† | MAX | MIN                | TYP† | MAX |      |
| Frequency                         | $R_t = 100\text{ k}\Omega$                    |                  | 100  |     |                    | 100  |     | kHz  |
| Standard deviation of frequency   |                                               |                  | 15   |     |                    | 15   |     | kHz  |
| Frequency change with voltage     | $V_{CC} = 3.6\text{ V to }40\text{ V}$        |                  | 1    |     |                    | 1    |     | kHz  |
| Frequency change with temperature | $T_A = -40^\circ\text{C to }25^\circ\text{C}$ | -4               | -0.4 | 4   | -4                 | -0.4 | 4   | kHz  |
|                                   | $T_A = -20^\circ\text{C to }25^\circ\text{C}$ | -4               | -0.4 | 4   | -4                 | -0.4 | 4   | kHz  |
|                                   | $T_A = 25^\circ\text{C to }85^\circ\text{C}$  | -4               | -0.2 | 4   | -4                 | -0.2 | 4   | kHz  |
| Voltage at RT                     |                                               |                  | 1    |     |                    | 1    |     | V    |

† All typical values are at  $T_A = 25^\circ\text{C}$ .



# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f_{osc} = 100\text{ kHz}$  (unless otherwise noted) (continued)

### dead-time control

| PARAMETER               |         | TEST CONDITIONS           | TL5001C, TL5001I               |                  |                     | TL5001AC, TL5001AI             |                  |                     | UNIT          |
|-------------------------|---------|---------------------------|--------------------------------|------------------|---------------------|--------------------------------|------------------|---------------------|---------------|
|                         |         |                           | MIN                            | TYP <sup>†</sup> | MAX                 | MIN                            | TYP <sup>†</sup> | MAX                 |               |
| Output (source) current | TL5001C | $V_{(DT)} = 1.5\text{ V}$ | $0.9 \times I_{RT}^{\ddagger}$ |                  | $1.1 \times I_{RT}$ | $0.9 \times I_{RT}^{\ddagger}$ |                  | $1.1 \times I_{RT}$ | $\mu\text{A}$ |
|                         | TL5001I | $V_{(DT)} = 1.5\text{ V}$ | $0.9 \times I_{RT}^{\ddagger}$ |                  | $1.2 \times I_{RT}$ | $0.9 \times I_{RT}^{\ddagger}$ |                  | $1.2 \times I_{RT}$ |               |
| Input threshold voltage |         | Duty cycle = 0%           | 0.5                            | 0.7              |                     | 0.5                            | 0.7              |                     | V             |
|                         |         | Duty cycle = 100%         |                                | 1.3              | 1.5                 |                                | 1.3              | 1.5                 |               |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .

<sup>‡</sup> Output source current at RT

### error amplifier

| PARAMETER                       |          | TEST CONDITIONS                         | TL5001C, TL5001I |                  |      | TL5001AC, TL5001AI |                  |      | UNIT          |
|---------------------------------|----------|-----------------------------------------|------------------|------------------|------|--------------------|------------------|------|---------------|
|                                 |          |                                         | MIN              | TYP <sup>†</sup> | MAX  | MIN                | TYP <sup>†</sup> | MAX  |               |
| Input voltage                   |          | $V_{CC} = 3.6\text{ V to }40\text{ V}$  | 0                |                  | 1.5  | 0                  |                  | 1.5  | V             |
| Input bias current              |          |                                         | –160             |                  | –500 | –160               |                  | –500 | nA            |
| Output voltage swing            | Positive |                                         | 1.5              | 2.3              |      | 1.5                | 2.3              |      | V             |
|                                 | Negative |                                         |                  | 0.3              | 0.4  |                    | 0.3              | 0.4  | V             |
| Open-loop voltage amplification |          |                                         |                  | 80               |      |                    | 80               |      | dB            |
| Unity-gain bandwidth            |          |                                         |                  | 1.5              |      |                    | 1.5              |      | MHz           |
| Output (sink) current           |          | $V_{I(FB)} = 1.2\text{ V}$ , COMP = 1 V | 100              | 600              |      | 100                | 600              |      | $\mu\text{A}$ |
| Output (source) current         |          | $V_{I(FB)} = 0.8\text{ V}$ , COMP = 1 V | –45              | –70              |      | –45                | –70              |      | $\mu\text{A}$ |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .

### output

| PARAMETER                    | TEST CONDITIONS                                 | TL5001C, TL5001I |      | TL5001AC, TL5001AI |     | UNIT |      |     |
|------------------------------|-------------------------------------------------|------------------|------|--------------------|-----|------|------|-----|
|                              |                                                 | MIN              | TYP† | MAX                | MIN |      | TYP† | MAX |
| Output saturation voltage    | I <sub>O</sub> = 10 mA                          | 1.5              |      | 2                  | 1.5 |      | 2    | V   |
| Off-state current            | V <sub>O</sub> = 50 V,      V <sub>CC</sub> = 0 |                  |      | 10                 |     |      | 10   | μA  |
|                              | V <sub>O</sub> = 50 V                           |                  |      | 10                 |     |      | 10   |     |
| Short-circuit output current | V <sub>O</sub> = 6 V                            | 40               |      |                    | 40  |      |      | mA  |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .

### total device

| PARAMETER              |           | TEST CONDITIONS            | TL5001C, TL5001I |                  |     | TL5001AC, TL5001AI |                  |     | UNIT |
|------------------------|-----------|----------------------------|------------------|------------------|-----|--------------------|------------------|-----|------|
|                        |           |                            | MIN              | TYP <sup>†</sup> | MAX | MIN                | TYP <sup>†</sup> | MAX |      |
| Standby supply current | Off state |                            |                  | 1                | 1.5 |                    | 1                | 1.5 | mA   |
| Average supply current |           | $R_t = 100\text{ k}\Omega$ |                  | 1.4              | 2.1 |                    | 1.4              | 2.1 | mA   |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .



# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f_{osc} = 100\text{ kHz}$  (unless otherwise noted)

### reference

| PARAMETER                              | TEST CONDITIONS           |                                        | TL5001Q,<br>TL5001M |      |      | TL5001AQ,<br>TL5001AM |      |      | UNIT |
|----------------------------------------|---------------------------|----------------------------------------|---------------------|------|------|-----------------------|------|------|------|
|                                        |                           |                                        | MIN                 | TYP† | MAX  | MIN                   | TYP† | MAX  |      |
| Output voltage                         | $T_A = 25^\circ\text{C}$  | COMP connected to FB                   | 0.95                | 1.00 | 1.05 | 0.97                  | 1.00 | 1.03 | V    |
|                                        | $T_A = \text{MIN to MAX}$ |                                        | 0.93                | 0.98 | 1.07 | 0.94                  | 0.98 | 1.06 |      |
| Input regulation                       | $T_A = \text{MIN to MAX}$ | $V_{CC} = 3.6\text{ V to }40\text{ V}$ |                     | 2    | 12.5 |                       | 2    | 12.5 | mV   |
| Output voltage change with temperature | $T_A = \text{MIN to MAX}$ |                                        | *-6                 | 2    | *6   | *-6                   | 2    | *6   | %    |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

\*Not production tested.

### undervoltage lockout

| PARAMETER               | TEST CONDITIONS                      | TL5001Q,<br>TL5001M |      |     | TL5001AQ,<br>TL5001AM |      |     | UNIT |
|-------------------------|--------------------------------------|---------------------|------|-----|-----------------------|------|-----|------|
|                         |                                      | MIN                 | TYP† | MAX | MIN                   | TYP† | MAX |      |
| Upper threshold voltage | $T_A = \text{MIN}, 25^\circ\text{C}$ |                     | 3.00 |     |                       | 3.00 |     | V    |
|                         | $T_A = \text{MAX}$                   |                     | 2.55 |     |                       | 2.55 |     |      |
| Lower threshold voltage | $T_A = \text{MIN}, 25^\circ\text{C}$ |                     | 2.8  |     |                       | 2.8  |     | V    |
|                         | $T_A = \text{MAX}$                   |                     | 2.0  |     |                       | 2.0  |     |      |
| Hysteresis              | $T_A = \text{MIN to MAX}$            | 100                 | 200  |     | 100                   | 200  |     | mV   |
| Reset threshold voltage | $T_A = \text{MIN}, 25^\circ\text{C}$ | 2.10                | 2.55 |     | 2.10                  | 2.55 |     | V    |
|                         | $T_A = \text{MAX}$                   | 0.35                | 0.63 |     | 0.35                  | 0.63 |     |      |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

### short-circuit protection

| PARAMETER                          | TEST CONDITIONS                      |           | TL5001Q,<br>TL5001M |      |      | TL5001AQ,<br>TL5001AM |      |      | UNIT       |
|------------------------------------|--------------------------------------|-----------|---------------------|------|------|-----------------------|------|------|------------|
|                                    |                                      |           | MIN                 | TYP† | MAX  | MIN                   | TYP† | MAX  |            |
| SCP threshold voltage              | $T_A = \text{MIN}, 25^\circ\text{C}$ |           | 0.95                | 1.00 | 1.05 | 0.97                  | 1.00 | 1.03 | V          |
|                                    | $T_A = \text{MAX}$                   |           | 0.93                | 0.98 | 1.07 | 0.94                  | 0.98 | 1.06 |            |
| SCP voltage, latched               | $T_A = \text{MIN to MAX}$            | No pullup | 140                 | 185  | 230  | 140                   | 185  | 230  | mV         |
| SCP voltage, UVLO standby          | $T_A = \text{MIN to MAX}$            | No pullup |                     | 60   | 120  |                       | 60   | 120  | mV         |
| Equivalent timing resistance       | $T_A = \text{MIN to MAX}$            |           |                     | 185  |      |                       | 185  |      | k $\Omega$ |
| SCP comparator 1 threshold voltage | $T_A = \text{MIN to MAX}$            |           |                     | 1.5  |      |                       | 1.5  |      | V          |

† All typical values are at  $T_A = 25^\circ\text{C}$ .



# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f_{osc} = 100\text{ kHz}$  (unless otherwise noted) (continued)

### oscillator

| PARAMETER                         | TEST CONDITIONS           |                                        | TL5001Q, TL5001M |      |     | TL5001AQ, TL5001AM |      |     | UNIT |
|-----------------------------------|---------------------------|----------------------------------------|------------------|------|-----|--------------------|------|-----|------|
|                                   |                           |                                        | MIN              | TYP† | MAX | MIN                | TYP† | MAX |      |
| Frequency                         | $T_A = \text{MIN to MAX}$ | $R_t = 100\text{ k}\Omega$             |                  | 100  |     |                    | 100  |     | kHz  |
| Standard deviation of frequency   | $T_A = \text{MIN to MAX}$ |                                        |                  | 2    |     |                    | 2    |     | kHz  |
| Frequency change with voltage     | $T_A = \text{MIN to MAX}$ | $V_{CC} = 3.6\text{ V to }40\text{ V}$ |                  | 1    |     |                    | 1    |     | kHz  |
| Frequency change with temperature | $T_A = \text{MIN to MAX}$ | Q suffix                               | *-6              | 3    | *6  | *-6                | 3    | *6  | kHz  |
|                                   |                           | M suffix                               | *-9              | 5    | *9  | *-9                | 5    | *9  |      |
| Voltage at RT                     | $T_A = \text{MIN to MAX}$ |                                        |                  | 1    |     |                    | 1    |     | V    |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

\*Not production tested.

### dead-time control

| PARAMETER               | TEST CONDITIONS           |                           | TL5001Q, TL5001M             |      |                     | TL5001AQ, TL5001AM           |      |                     | UNIT          |
|-------------------------|---------------------------|---------------------------|------------------------------|------|---------------------|------------------------------|------|---------------------|---------------|
|                         |                           |                           | MIN                          | TYP† | MAX                 | MIN                          | TYP† | MAX                 |               |
| Output (source) current | $T_A = \text{MIN to MAX}$ | $V_{(DT)} = 1.5\text{ V}$ | $0.9 \times I_{RT}^\ddagger$ |      | $1.1 \times I_{RT}$ | $0.9 \times I_{RT}^\ddagger$ |      | $1.1 \times I_{RT}$ | $\mu\text{A}$ |
| Input threshold voltage | $T_A = 25^\circ\text{C}$  | Duty cycle = 0%           | 0.5                          | 0.7  |                     | 0.5                          | 0.7  |                     | V             |
|                         |                           | Duty cycle = 100%         |                              | 1.3  | 1.5                 |                              | 1.3  | 1.5                 |               |
|                         | $T_A = \text{MIN to MAX}$ | Duty cycle = 0%           | 0.4                          | 0.7  |                     | 0.4                          | 0.7  |                     |               |
|                         |                           | Duty cycle = 100%         |                              | 1.3  | 1.7                 |                              | 1.3  | 1.7                 |               |

† All typical values are at  $T_A = 25^\circ\text{C}$ .

‡ Output source current at RT

### error amplifier

| PARAMETER                       |                                      | TEST CONDITIONS                         | TL5001Q, TL5001M           |      |      | TL5001AQ, TL5001AM         |      |      | UNIT          |
|---------------------------------|--------------------------------------|-----------------------------------------|----------------------------|------|------|----------------------------|------|------|---------------|
|                                 |                                      |                                         | MIN                        | TYP† | MAX  | MIN                        | TYP† | MAX  |               |
| Input bias current              |                                      | $T_A = \text{MIN to MAX}$               |                            | -160 | -500 |                            | -160 | -500 | nA            |
| Output voltage swing            | Positive                             | $T_A = \text{MIN to MAX}$               | 1.5                        | 2.3  |      | 1.5                        | 2.3  |      | V             |
|                                 | Negative                             |                                         |                            | 0.3  | 0.4  |                            | 0.3  | 0.4  | V             |
| Open-loop voltage amplification |                                      | $T_A = \text{MIN to MAX}$               |                            | 80   |      |                            | 80   |      | dB            |
| Unity-gain bandwidth            |                                      | $T_A = \text{MIN to MAX}$               |                            | 1.5  |      |                            | 1.5  |      | MHz           |
| Output (sink) current           |                                      | $T_A = \text{MIN to MAX}$               | $V_{I(FB)} = 1.2\text{ V}$ | 100  | 600  | $V_{I(FB)} = 1.2\text{ V}$ | 100  | 600  | $\mu\text{A}$ |
| Output (source) current         | $T_A = \text{MIN}, 25^\circ\text{C}$ | $V_{I(FB)} = 0.8\text{ V}$ , COMP = 1 V | -45                        | -70  |      | -45                        | -70  |      | $\mu\text{A}$ |
|                                 | $T_A = \text{MAX}$                   |                                         | -30                        | -45  |      | -30                        | -45  |      |               |

† All typical values are at  $T_A = 25^\circ\text{C}$ .



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

electrical characteristics over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f_{osc} = 100\text{ kHz}$  (unless otherwise noted) (continued)

## output

| PARAMETER                    | TEST CONDITIONS           |                                 | TL5001Q,<br>TL5001M |                  |     | TL5001AQ,<br>TL5001AM |                  |     | UNIT          |
|------------------------------|---------------------------|---------------------------------|---------------------|------------------|-----|-----------------------|------------------|-----|---------------|
|                              |                           |                                 | MIN                 | TYP <sup>†</sup> | MAX | MIN                   | TYP <sup>†</sup> | MAX |               |
| Output saturation voltage    | $T_A = \text{MIN to MAX}$ | $I_O = 10\text{ mA}$            |                     | 1.5              | 2   |                       | 1.5              | 2   | V             |
| Off-state current            | $T_A = \text{MIN to MAX}$ | $V_O = 50\text{ V}, V_{CC} = 0$ |                     |                  | 10  |                       |                  | 10  | $\mu\text{A}$ |
|                              |                           | $V_O = 50\text{ V}$             |                     |                  | 10  |                       |                  | 10  |               |
| Short-circuit output current | $T_A = \text{MIN to MAX}$ | $V_O = 6\text{ V}$              |                     | 40               |     |                       | 40               |     | mA            |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .

## total device

| PARAMETER              |           | TEST CONDITIONS           |                            | TL5001Q,<br>TL5001M |                  |     | TL5001AQ,<br>TL5001AM |                  |     | UNIT |
|------------------------|-----------|---------------------------|----------------------------|---------------------|------------------|-----|-----------------------|------------------|-----|------|
|                        |           |                           |                            | MIN                 | TYP <sup>†</sup> | MAX | MIN                   | TYP <sup>†</sup> | MAX |      |
| Standby supply current | Off state | $T_A = \text{MIN to MAX}$ |                            |                     | 1                | 1.5 |                       | 1                | 1.5 | mA   |
| Average supply current |           | $T_A = \text{MIN to MAX}$ | $R_t = 100\text{ k}\Omega$ |                     | 1.4              | 2.1 |                       | 1.4              | 2.1 | mA   |

<sup>†</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .




# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

### PARAMETER MEASUREMENT INFORMATION



NOTE A: The waveforms show timing characteristics for an intermittent short circuit and a longer short circuit that is sufficient to activate SCP.

**Figure 4. PWM Timing Diagram**

# TYPICAL CHARACTERISTICS




Figure 5




Figure 6




Figure 7




Figure 8

# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

### TYPICAL CHARACTERISTICS




Figure 9




Figure 10




Figure 11




Figure 12

# TYPICAL CHARACTERISTICS




Figure 13




Figure 14




Figure 15




Figure 16

# TL5001, TL5001A

## PULSE-WIDTH-MODULATION CONTROL CIRCUITS

SLVS084F – APRIL 1994 – REVISED JANUARY 2002

### TYPICAL CHARACTERISTICS




Figure 17




Figure 18




Figure 19





Figure 20



### APPLICATION INFORMATION



#### Partial Bill of Materials:

|     |                                                                       |                   |
|-----|-----------------------------------------------------------------------|-------------------|
| U1  | TL5001/A                                                              | Texas Instruments |
| Q1  | TPS1101                                                               | Texas Instruments |
| LI  | CTX20-1 or<br>23 turns of #28 wire on<br>Micrometals No. T50-26B core | Coiltronics       |
| C1  | TPSD107M010R0100                                                      | AVX               |
| C2  | TPSD107M010R0100                                                      | AVX               |
| CR1 | MBRS140T3                                                             | Motorola          |

- NOTES: A. Frequency = 200 kHz  
 B. Duty cycle = 90% max  
 C. Soft-start time constant (TC) = 5.6 ms  
 D. SCP TC = 70 msA

**Figure 21. Step-Down Converter**

# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS


SLVS084F – APRIL 1994 – REVISED JANUARY 2002

## MECHANICAL DATA

D (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14 PIN SHOWN



- NOTES: B. All linear dimensions are in inches (millimeters).  
C. This drawing is subject to change without notice.  
D. Body dimensions do not include mold flash or protrusion, not to exceed 0.006 (0,15).  
E. Falls within JEDEC MS-012

# TL5001, TL5001A PULSE-WIDTH-MODULATION CONTROL CIRCUITS


SLVS084F – APRIL 1994 – REVISED JANUARY 2002

## MECHANICAL DATA

FK (S-CQCC-N\*\*)

LEADLESS CERAMIC CHIP CARRIER

28 TERMINALS SHOWN



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package can be hermetically sealed with a metal lid.
  - D. The terminals are gold-plated.
  - E. Falls within JEDEC MS-004

**PACKAGING INFORMATION**

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                    |
|---------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|----------------------------------------|
| <a href="#">5962-9958301QPA</a> | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958301QPA<br>TL5001M                  |
| <a href="#">5962-9958302Q2A</a> | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>9958302Q2A<br>TL5001<br>AMFKB |
| <a href="#">5962-9958302QPA</a> | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958302QPA<br>TL5001AM                 |
| <a href="#">TL5001ACD</a>       | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -20 to 85    | 5001AC                                 |
| TL5001ACD.A                     | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AC                                 |
| <a href="#">TL5001ACDR</a>      | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -20 to 85    | 5001AC                                 |
| TL5001ACDR.A                    | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AC                                 |
| <a href="#">TL5001AID</a>       | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 5001AI                                 |
| TL5001AID.A                     | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AI                                 |
| TL5001AIDG4                     | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 5001AI                                 |
| <a href="#">TL5001AIDR</a>      | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 5001AI                                 |
| TL5001AIDR.A                    | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AI                                 |
| <a href="#">TL5001AIP</a>       | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TL5001AIP                              |
| TL5001AIP.A                     | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | TL5001AIP                              |
| <a href="#">TL5001AMFKB</a>     | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>9958302Q2A<br>TL5001<br>AMFKB |
| TL5001AMFKB.A                   | Active        | Production           | LCCC (FK)   20 | 55   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-<br>9958302Q2A<br>TL5001<br>AMFKB |
| <a href="#">TL5001AMJGB</a>     | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958302QPA<br>TL5001AM                 |
| TL5001AMJGB.A                   | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958302QPA<br>TL5001AM                 |
| <a href="#">TL5001AQD</a>       | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ                                 |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TL5001AQD.A                  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ              |
| <a href="#">TL5001AQDG4</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | 5001AQ              |
| TL5001AQDG4.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ              |
| <a href="#">TL5001AQDR</a>   | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ              |
| TL5001AQDR.A                 | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ              |
| <a href="#">TL5001AQDRG4</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | 5001AQ              |
| TL5001AQDRG4.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001AQ              |
| <a href="#">TL5001CD</a>     | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | 5001C               |
| TL5001CD.A                   | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001C               |
| TL5001CDG4                   | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | 5001C               |
| <a href="#">TL5001CDR</a>    | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | 5001C               |
| TL5001CDR.A                  | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001C               |
| TL5001CDRG4                  | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | 5001C               |
| <a href="#">TL5001CP</a>     | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -25 to 85    | TL5001CP            |
| TL5001CP.A                   | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | TL5001CP            |
| <a href="#">TL5001CPS</a>    | Active        | Production           | SO (PS)   8    | 80   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | T5001               |
| TL5001CPS.A                  | Active        | Production           | SO (PS)   8    | 80   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | T5001               |
| <a href="#">TL5001CPSR</a>   | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -25 to 85    | T5001               |
| TL5001CPSR.A                 | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | T5001               |
| <a href="#">TL5001ID</a>     | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 5001I               |
| TL5001ID.A                   | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001I               |
| <a href="#">TL5001IDR</a>    | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | 5001I               |
| TL5001IDR.A                  | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001I               |
| <a href="#">TL5001IP</a>     | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TL5001IP            |
| TL5001IP.A                   | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 125   | TL5001IP            |
| TL5001IPE4                   | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TL5001IP            |
| <a href="#">TL5001IPSR</a>   | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | Z5001               |
| TL5001IPSR.A                 | Active        | Production           | SO (PS)   8    | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | Z5001               |
| <a href="#">TL5001MJG</a>    | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | TL5001MJG           |
| TL5001MJG.A                  | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | TL5001MJG           |

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)   |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-----------------------|
| <a href="#">TL5001MJGB</a>  | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958301QPA<br>TL5001M |
| TL5001MJGB.A                | Active        | Production           | CDIP (JG)   8  | 50   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 9958301QPA<br>TL5001M |
| <a href="#">TL5001QD</a>    | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |
| TL5001QD.A                  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |
| <a href="#">TL5001QDG4</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | 5001Q                 |
| TL5001QDG4.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |
| <a href="#">TL5001QDR</a>   | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |
| TL5001QDR.A                 | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |
| <a href="#">TL5001QDRG4</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -            | 5001Q                 |
| TL5001QDRG4.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 5001Q                 |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**OTHER QUALIFIED VERSIONS OF TL5001, TL5001A, TL5001AM, TL5001M :**

- Catalog : [TL5001A](#), [TL5001](#)
- Automotive : [TL5001A-Q1](#), [TL5001A-Q1](#)
- Military : [TL5001M](#), [TL5001AM](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION




\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TL5001ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001AIDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001AQDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001AQDRG4 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001CDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001CPSR   | SO           | PS              | 8    | 2000 | 330.0              | 16.4               | 8.35    | 6.6     | 2.5     | 12.0    | 16.0   | Q1            |
| TL5001IDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001IPSR   | SO           | PS              | 8    | 2000 | 330.0              | 16.4               | 8.35    | 6.6     | 2.5     | 12.0    | 16.0   | Q1            |
| TL5001QDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TL5001QDRG4  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |




## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TL5001ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| TL5001AIDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| TL5001AQDR   | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TL5001AQDRG4 | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TL5001CDR    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| TL5001CPSR   | SO           | PS              | 8    | 2000 | 356.0       | 356.0      | 35.0        |
| TL5001IDR    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| TL5001IPSR   | SO           | PS              | 8    | 2000 | 356.0       | 356.0      | 35.0        |
| TL5001QDR    | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TL5001QDRG4  | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |

**TUBE**


\*All dimensions are nominal


| Device          | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-9958302Q2A | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| TL5001ACD       | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001ACD.A     | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001AID       | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001AID.A     | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001AIDG4     | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001AIP       | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001AIP.A     | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001AMFKB     | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| TL5001AMFKB.A   | FK           | LCCC         | 20   | 55  | 506.98 | 12.06  | 2030   | NA     |
| TL5001AQD       | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001AQD.A     | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001AQDG4     | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001AQDG4.A   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001CD        | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001CD.A      | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001CDG4      | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001CP        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001CP.A      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001CPS       | PS           | SOP          | 8    | 80  | 530    | 10.5   | 4000   | 4.1    |
| TL5001CPS.A     | PS           | SOP          | 8    | 80  | 530    | 10.5   | 4000   | 4.1    |
| TL5001ID        | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001ID.A      | D            | SOIC         | 8    | 75  | 507    | 8      | 3940   | 4.32   |
| TL5001IP        | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001IP.A      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001IPE4      | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| TL5001QD        | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001QD.A      | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TL5001QDG4      | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |

---

| Device       | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|--------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TL5001QDG4.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |

**JG0008A****PACKAGE OUTLINE****CDIP - 5.08 mm max height**

CERAMIC DUAL IN-LINE PACKAGE



4230036/A 09/2023

**NOTES:**


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package can be hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification.
5. Falls within MIL STD 1835 GDIP1-T8

# EXAMPLE BOARD LAYOUT

JG0008A

CDIP - 5.08 mm max height

CERAMIC DUAL IN-LINE PACKAGE



LAND PATTERN EXAMPLE  
NON SOLDER MASK DEFINED  
SCALE: 9X

4230036/A 09/2023

## GENERIC PACKAGE VIEW


**FK 20**

**LCCC - 2.03 mm max height**

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4229370VA\



## PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT





1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

# EXAMPLE BOARD LAYOUT

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019


NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## MECHANICAL DATA

PS (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE




4040063/C 03/03

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

P (R-PDIP-T8)

PLASTIC DUAL-IN-LINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MS-001 variation BA.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated