











SNVSAV1A - JUNE 2017-REVISED OCTOBER 2017

**TLV760** 

# TLV760 100-mA, 30-V, Fixed-Output, Linear-Voltage Regulator

#### **Features**

- Wide Input Voltage Range up to 30 V
- Output Current up to 100 mA
- Available in Fixed Output Voltage 3.3-V, 5-V, 12-V and 15-V Versions
- Operating Junction Temperature -40°C to +125°C
- Stable With Ceramic Capacitors Greater Than or Equal to 0.1 µF
- Active Thermal Protection and Current Limit

# **Applications**

- Post Regulator for Switching DC-DC Converter
- Bias Supply for Digital and Analog Circuits
- Home Appliances
- **Power Tools**
- Factory and Building Automation

# 3 Description

The TLV760 is an integrated linear-voltage regulator featuring operation from an input as high as 30 V. The TLV760 has a maximum dropout of 1.2 V at the full 100-mA load across operating temperature. Standard packaging for the TLV760 is the 3-pin SOT-23 package.

The TLV760 is available in 3.3 V, 5 V, 12 V and 15 V. The SOT-23 packaging of the TLV760 series allows the device to be used in space-constrained applications. The TLV760 is a small size alternative to LM78Lxx series and similar devices.


The TLV760 is designed to bias digital and analog circuits in applications that are subject to voltage transients and spikes up to 30 V — for example, appliances and automation applications. The device has robust internal thermal protection, which protects itself from potential damage caused by conditions like short to ground, increases in ambient temperature, high load, or high dropout events.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
TLV760	SOT-23 (3)	2.92 mm × 1.30 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### **Typical Application Circuit**



Copyright © 2017, Texas Instruments Incorporated



# **Table of Contents**

1	Features 1	7.4 Device Functional Modes	10
2	Applications 1	8 Application and Implementation	. 11
3	Description 1	8.1 Application Information	
4	Revision History2	8.2 Typical Application	12
5	Pin Configuration and Functions	9 Power Supply Recommendations	. 14
6	Specifications4	10 Layout	. 14
•	6.1 Absolute Maximum Ratings	10.1 Layout Guidelines	14
	6.2 ESD Ratings	10.2 Layout Example	14
	6.3 Recommended Operating Conditions	11 Device and Documentation Support	. 15
	6.4 Thermal Information	11.1 Device Support	
	6.5 Electrical Characteristics	11.2 Receiving Notification of Documentation Update	s 15
	6.6 Typical Characteristics	11.3 Community Resources	15
7	Detailed Description9	11.4 Trademarks	15
-	7.1 Overview 9	11.5 Electrostatic Discharge Caution	15
	7.2 Functional Block Diagram9	11.6 Glossary	15
	7.3 Feature Description	12 Mechanical, Packaging, and Orderable Information	. 16

# 4 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

# Changes from Original (June 2017) to Revision A

Page



# 5 Pin Configuration and Functions



**Pin Functions** 

PIN		1/0	1/0	1/0	1/0	1/0	DESCRIPTION
NO.	NAME	1/0	DESCRIPTION				
1	OUT	0	Output voltage, a ceramic capacitor greater than or equal to 0.1 $\mu F$ is need for the stability of the device. (1)				
2	IN	1	Input voltage supply — TI recommends a capacitor of value greater than 0.1 µF at the input. (1)				
3	GND	_	Common ground				

(1) See External Capacitors for more details.



# 6 Specifications

# 6.1 Absolute Maximum Ratings<sup>(1)</sup>

	MIN	MAX	UNIT
Input voltage (IN to GND)	-0.3	35	V
Output Voltage (OUT)		V <sub>IN</sub> + 0.3	V
Output Current		Internally limited (2)	mA
Junction temperature	-40	150	°C
Storage temperature, T <sub>stg</sub>	-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings<sup>(1)</sup> may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) See Recommended Operating Conditions section for more details.

## 6.2 ESD Ratings

			VALUE	UNIT
, Elec	Electrostatic	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±2000	\/
V <sub>(ESD)</sub>	discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 (2)	±500	V

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	MIN	MAX	UNIT
Maximum input voltage (IN to GND)		30	V
Output current (I <sub>OUT</sub> )		100	mA
Input and output capacitor (C <sub>OUT</sub> )	0.1		μF
Junction temperature, T <sub>J</sub>	-40	125	°C

#### 6.4 Thermal Information

		TLV760	
	THERMAL METRIC <sup>(1)</sup>	DBZ (SOT-23)	UNIT
		3 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	275.2	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	92.8	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	56.8	°C/W
ΨЈТ	Junction-to-top characterization parameter	2.9	°C/W
ΨЈВ	Junction-to-board characterization parameter	55.6	°C/W

 For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

Product Folder Links: *TLV760* 

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



# 6.5 Electrical Characteristics

Typical and other limits apply for  $T_A = T_J = 25$ °C,  $V_{OUT(NOM)} = 3.3$  V, 5 V, 12 V, and 15 V, unless otherwise specified.


	PARAMETER	TEST CONDI	TIONS	MIN	TYP	MAX	UNIT
	Output voltage	$V_{IN} = V_{OUT(NOM)} + 1.5 V,$ 1 mA \leq I <sub>OUT</sub> \leq 100 mA		-4%		4%	
V <sub>OUT</sub>	accuracy	$V_{IN} = V_{OUT(NOM)} + 1.5 \text{ V},$ 1 mA \leq I <sub>OUT</sub> \leq 100 mA, -40°C \leq T_J \leq 125°C		-5%		5%	V
		$V_{OUT(NOM)} + 1.5 \text{ V} \le V_{IN} \le 30 \text{ V}$	V <sub>OUT(NOM)</sub> = 3.3 V, 5 V		10	30	.,
$\Delta V_{(\Delta VIN)}$ Line regulation		I <sub>OUT</sub> = 1 mA , -40°C ≤ T <sub>J</sub> ≤ 125°C	V <sub>OUT(NOM)</sub> = 12 V, 15 V		14	45	mV
		$V_{IN} = V_{OUT(NOM)} + 1.5 V$ ,	V <sub>OUT(NOM)</sub> = 3.3 V, 5 V		20	45	
$\Delta V_{(\Delta IOUT)}$	Load regulation	10 mA ≤ $I_{OUT}$ ≤ 100 mA, -40°C ≤ $T_J$ ≤ 125°C	V <sub>OUT(NOM)</sub> = 12 V, 15 V		45	80	mV
I <sub>GND</sub>	Ground pin current	$V_{OUT(NOM)} + 1.5 \text{ V} \le V_{IN} \le 30 \text{ V},$ -40°C \le T <sub>J</sub> \le 125°C	no load,		2	5	mA
		I <sub>OUT</sub> = 10 mA			0.7	0.9	
V	Dropout voltage	I <sub>OUT</sub> = 10 mA , −40°C ≤ T <sub>J</sub> ≤ 125°C				1	V
$V_{DO}$		I <sub>OUT</sub> = 100 mA			0.9	1.1	v
		I <sub>OUT</sub> = 100 mA, −40°C ≤ T <sub>J</sub> ≤ 125°C				1.2	
T <sub>SD</sub>	Thermal shutdown temperature				150		°C

Copyright © 2017, Texas Instruments Incorporated



# 6.6 Typical Characteristics


Unless indicated otherwise,  $V_{IN} = V_{NOM} + 1.5 \text{ V}$ ,  $C_{IN} = 0.1 \mu\text{F}$ ,  $C_{OUT} = 0.1 \mu\text{F}$ , and  $T_A = 25^{\circ}\text{C}$ .





# **Typical Characteristics (continued)**

Unless indicated otherwise,  $V_{IN} = V_{NOM} + 1.5 \text{ V}$ ,  $C_{IN} = 0.1 \mu\text{F}$ ,  $C_{OUT} = 0.1 \mu\text{F}$ , and  $T_A = 25 ^{\circ}\text{C}$ .




Copyright © 2017, Texas Instruments Incorporated

# TEXAS INSTRUMENTS

# **Typical Characteristics (continued)**

Unless indicated otherwise,  $V_{IN} = V_{NOM} + 1.5 \text{ V}$ ,  $C_{IN} = 0.1 \mu\text{F}$ ,  $C_{OUT} = 0.1 \mu\text{F}$ , and  $T_A = 25^{\circ}\text{C}$ .



Submit Documentation Feedback

Copyright © 2017, Texas Instruments Incorporated




# 7 Detailed Description

#### 7.1 Overview

The TLV760 is an integrated linear-voltage regulator with inputs that can be as high as 30 V. The TLV760 features quasi LDO architecture, which allows the usage of low ESR capacitors at the output. A ceramic capacitor with a capacitance value greater than or equal to 0.1 µF is adequate to keep the linear regulator in stable operation. The device has a rugged active junction thermal protection mechanism.

## 7.2 Functional Block Diagram



Copyright © 2017, Texas Instruments Incorporated

## 7.3 Feature Description

#### 7.3.1 Thermal Protection

The TLV760 contains an active thermal protection mechanism, which limits the junction temperature to 150°C. This protection comes into action when the thermal junction temperature of the device tries to exceed 150°C. The output current of the device is limited or folded back to maintain the junction temperature.

The thermal protection follows Equation 1

$$P_D = (T_J - T_A) / R_{\theta JA}$$

where

•  $P_D = (V_{IN} - V_{OUT})I_{OUT}$ 

Copyright © 2017, Texas Instruments Incorporated

- T<sub>J</sub> is the junction temperature
- $R_{\theta JA}$  is the junction-to-ambient thermal resistance

When a high drop out condition occurs resulting in higher power dissipation across the device the output current is limited to maintain a constant junction temperature of 150°C. This rugged feature protects the device from higher power dissipation applications as well as the short to ground at the output.

This internal protection circuitry of TLV760 is intended to protect the devices against thermal overload conditions. The circuitry is not intended to replace proper heat sinking. Continuously running the TLV760 into thermal protection degrades device reliability.

For reliable operation, limit junction temperature to a maximum of 125°C. To estimate the thermal margin in a given layout, increase the ambient temperature until the thermal protection is triggered using worst case load and highest input voltage conditions.

Droduct Folder Linker

(1)



## **Feature Description (continued)**

## 7.3.2 Dropout Voltage

The TLV760 is a bipolar device with quasi LDO architecture. Being a bipolar device the dropout voltage of the device does not change significantly with output load current. The device has a maximum dropout across temperature of 1.2 V at 100-mA load current, which is a significant improvement over the traditional LM78Lxx devices.

#### 7.4 Device Functional Modes

#### 7.4.1 Normal Operation

The TLV760 operates with an input up to 30 V. Its tiny SOT-23 package and quasi-LDO architecture makes it suitable for providing a very tiny 100-mA bias supply. The device regulates to the nominal output voltage when all of the following conditions are met.

- The input voltage is greater than the nominal output voltage plus the dropout voltage  $(V_{OUT(NOM)} + V_{DO})$ .
- The output current is less than or equal to 100 mA.
- The device junction temperature is less than the thermal protection temperature of 150°C.

Submit Documentation Feedback

Copyright © 2017, Texas Instruments Incorporated



# 8 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 8.1 Application Information

The TLV760 is a fixed output device which need only input and output capacitors to function. This section discusses the key aspects to implement this linear regulator in typical applications.

#### 8.1.1 Fixed Output

TLV760 comes in fixed output voltage options, 3.3 V, 5 V, 12 V and 15 V. To ensure the proper regulated output, the input voltage should be greater than  $V_{OUT(nom)} + V_{DO}$ .

#### 8.1.2 External Capacitors

#### 8.1.2.1 Input and Output Capacitor Requirements

A minimum input and output capacitance value of  $0.1~\mu F$  is required for stability and adequate transient performance. There is no specific equivalent series resistance (ESR) limitation, although excessively high ESR compromises transient performance. There is no specific limitation on a maximum capacitance value on the input or the output. However while selecting a capacitor, derating factors on the capacitance value should be considered. Use C0G, X7R, or X5R-type ceramic capacitors because these capacitors have minimal variation in capacitance value and ESR over temperature.

## 8.1.2.2 Load-Step Transient Response

The load-step transient response is the output voltage response by the linear regulator to a step change in load current. The depth of charge depletion immediately after the load step is directly proportional to the amount of output capacitance. However, larger output capacitances decrease any voltage dip or peak occurring during a load step, the control-loop bandwidth is also decreased, thereby slowing the response time. TI recommends to optimally scale output capacitors for a specific application and test for the output load transients.

#### 8.1.3 Power Dissipation

Proper consideration should be given to device power dissipation, location of the circuit on the printed circuit board (PCB), and correct sizing of the thermal plane to ensure the device reliability. The PCB area around the regulator must be as free as possible of other heat-generating devices that cause added thermal stresses. To first-order approximation, power dissipation in the regulator depends on the input-to-output voltage difference and load conditions. Power dissipation can be calculated using The thermal protection follows Equation 1:

$$P_D = (T_J - T_A) / R_{\theta JA}$$

where

•  $P_D = (V_{IN} - V_{OUT})I_{OUT}$ 

Copyright © 2017, Texas Instruments Incorporated

- T<sub>J</sub> is the junction temperature
- $R_{\theta JA}$  is the junction-to-ambient thermal resistance

Thus, at a given load current, input and output voltage, maximum power dissipation determines the maximum allowable ambient temperature  $(T_A)$  for the device, and vice versa. Power dissipation and junction temperature are most often related by the junction-to-ambient thermal resistance  $(R_{\theta JA})$  of the combined PCB and device package and the temperature of the ambient air  $(T_A)$ .

 $R_{\theta JA}$  is highly dependent on the heat-spreading capability built into the particular PCB design, and therefore varies according to the total copper area, copper weight, and location of the planes. The  $R_{\theta JA}$  recorded in *Thermal Information* is determined by the JEDEC standard, PCB, and copper-spreading area and is only used as a relative measure of package thermal performance.

Product Folder Links: TI


(2)



# **Application Information (continued)**

TLV760 integrates a rugged protection where the  $T_J$  is limited to 150°C. The maximum power dissipation depends on the ambient temperature and can be calculated using  $P_D = (T_J - T_A) / R_{\theta JA}$ , for example, substituting the absolute maximum junction temperature, 150°C for  $T_J$ , 50°C for  $T_A$ , and 275.2 °C/W for  $R_{\theta JA}$ , the maximum power that can be dissipated is 363 mW. More power can be safely dissipated at lower ambient temperatures. Less power can be safely dissipated at higher ambient temperatures. The power dissipation can be increased by 3.6 mW for each °C below 50°C ambient. It must be derated by 3.6 mW for each °C above 50°C ambient. Proper heat sinking enables the safe dissipation of more power.

## 8.2 Typical Application



Copyright © 2017, Texas Instruments Incorporated

Figure 18. Typical Application for the 5-V Option

#### 8.2.1 Design Requirements

For typical TLV760 applications, use the parameters in Table 1.

**Table 1. Design Parameters** 

DESIGN PARAMETER	EXAMPLE VALUE
Input voltage	6.5 V
Output voltage	5 V
Output current	100 mA

#### 8.2.2 Detailed Design Procedure


The output for TLV76050 is internally set to 5 V. Input and output capacitors can be selected in accordance with the *External Capacitors*. Ceramic capacitances of 0.1 µF for both input and output are selected.

See the *Layout* section for an example of how to PCB layout the TLV760 to achieve best performance.



#### 8.2.3 Application Curves

Unless indicated otherwise,  $V_{IN}$  = 6.5 V,  $V_{OUT}$  = 5 V,  $C_{OUT}$  = 0.1  $\mu F$ , and  $T_A$  = 25°C.



# 9 Power Supply Recommendations

The TLV760 is designed to operate from input voltage up to 30 V. If the input power supply has ripples, additional input and output capacitors with low ESR can help improve the PSRR at higher frequencies.

## 10 Layout

## 10.1 Layout Guidelines

General guidelines for linear regulator designs are to place all circuit components on the same side of the circuit board and as near as practical to the respective TLV760 pin connections. Place ground return connections to the input and output capacitors, and to the TLV760 ground pin as close as possible to each other, connected by a wide, component-side, copper surface. The use of vias and long traces to create TLV760 circuit connections is strongly discouraged and negatively affects system performance.

Use a ground reference plane, either embedded in the PCB itself or located on the bottom side of the PCB opposite the components. This reference plane serves to assure accuracy of the output voltage and to shield noise; it behaves similarly to a thermal plane to spread heat from the linear regulator. In most applications, this ground plane is necessary to meet thermal requirements.

#### 10.2 Layout Example




Figure 25. Layout Guideline for TLV760



# 11 Device and Documentation Support

## 11.1 Device Support

#### 11.1.1 Related Documentation

For related documentation see the following:

AN-1148 Linear Regulators: Theory of Operation and Compensation

#### 11.1.2 Spice Models

Computer simulation of circuit performance using SPICE is often useful when analyzing the performance of analog circuits and systems. A SPICE model for the TLV760 is available through the TLV760 product folder under simulation models.

#### 11.1.3 Device Nomenclature

Table 2. Ordering Information<sup>(1)</sup>

PRODUCT	DESCRIPTION
TLV760 <b>XXYYYZ</b>	XX is the voltage designator YYY is the package designator. Z is the package quantity.

<sup>(1)</sup> For the most current package and ordering information see the Package Option Addendum at the end of this document, or see the device product folder at www.ti.com.

## 11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 11.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 11.4 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

## 11.5 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

# 11.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

Product Folder Links: TLV760



# 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





www.ti.com 23-May-2025

#### PACKAGING INFORMATION

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	RoHS	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking
	(-)	(=)			(-)	(4)	(5)		(5)
TLV76012DBZR	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18G
TLV76012DBZR.B	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18G
TLV76012DBZT	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18G
TLV76012DBZT.B	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18G
TLV76015DBZR	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18C
TLV76015DBZR.B	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18C
TLV76015DBZT	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18C
TLV76015DBZT.B	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18C
TLV76033DBZR	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18H
TLV76033DBZR.B	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18H
TLV76033DBZT	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18H
TLV76033DBZT.B	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	18H
TLV76050DBZR	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	181
TLV76050DBZR.B	Active	Production	SOT-23 (DBZ)   3	3000   LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	181
TLV76050DBZT	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	181
TLV76050DBZT.B	Active	Production	SOT-23 (DBZ)   3	250   SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	181

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 23-May-2025

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com 9-Aug-2022

## TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLV76012DBZR	SOT-23	DBZ	3	3000	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76012DBZT	SOT-23	DBZ	3	250	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76015DBZR	SOT-23	DBZ	3	3000	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76015DBZT	SOT-23	DBZ	3	250	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76033DBZR	SOT-23	DBZ	3	3000	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76033DBZT	SOT-23	DBZ	3	250	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76050DBZR	SOT-23	DBZ	3	3000	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3
TLV76050DBZT	SOT-23	DBZ	3	250	178.0	8.4	3.3	2.9	1.22	4.0	8.0	Q3



www.ti.com 9-Aug-2022




\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLV76012DBZR	SOT-23	DBZ	3	3000	208.0	191.0	35.0
TLV76012DBZT	SOT-23	DBZ	3	250	208.0	191.0	35.0
TLV76015DBZR	SOT-23	DBZ	3	3000	208.0	191.0	35.0
TLV76015DBZT	SOT-23	DBZ	3	250	208.0	191.0	35.0
TLV76033DBZR	SOT-23	DBZ	3	3000	208.0	191.0	35.0
TLV76033DBZT	SOT-23	DBZ	3	250	208.0	191.0	35.0
TLV76050DBZR	SOT-23	DBZ	3	3000	208.0	191.0	35.0
TLV76050DBZT	SOT-23	DBZ	3	250	208.0	191.0	35.0



SMALL OUTLINE TRANSISTOR




## NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
   This drawing is subject to change without notice.
   Reference JEDEC registration TO-236, except minimum foot length.

- 4. Support pin may differ or may not be present.
- 5. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



SMALL OUTLINE TRANSISTOR




NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated