









TLV9361-Q1, TLV9362-Q1, TLV9364-Q1 SBOSAD6B - APRIL 2023 - REVISED AUGUST 2024

TLV936x-Q1 Automotive, 10MHz, 40V, Rail-to-Rail Output, Operational Amplifier for **Cost-Sensitive Systems**

1 Features

- AEC-Q100 qualified for automotive applications
 - Temperature grade 1: –40°C to +125°C
 - Human-body model (HBM) Electrostatic discharge (ESD) classification level: 2A
 - Charged-device model (CDM) ESD classification level: C6
- Low offset voltage: ±400µV
- Low offset voltage drift: ±1.25µV/°C
- Low noise: $8.5 \text{nV}/\sqrt{\text{Hz}}$ at 1 kHz, $6 \text{nV}/\sqrt{\text{Hz}}$ broadband
- High common-mode rejection: 110dB
- Low bias current: ±10pA
- Rail-to-rail output
- Wide bandwidth: 10.6MHz GBW, unity-gain stable
- High slew rate: 25V/µs
- Low quiescent current: 2.6mA per amplifier
- Wide supply: ±2.25V to ±20V, 4.5V to 40V
- Robust EMIRR performance

2 Applications

- Automotive head unit
- Digital cockpit processing unit
- Telematics control unit
- Emergency call (eCall)
- Automotive active noise cancellation
- Automotive external amplifier

3 Description

The TLV936x-Q1 family (TLV9361-Q1, TLV9362-Q1, and TLV9364-Q1) is a family of AEC-Q100 automotive qualified, 40V cost-optimized operational amplifiers.

These devices offer strong DC and AC specifications, including rail-to-rail output, low input voltage noise density (6 nV/ $\sqrt{\text{Hz}}$), low offset (±400 μ V, typical), low offset drift (±1.25µV/°C, typical), and 10.6MHz bandwidth.


Features such as EMIRR filtering, high output current (±60mA), and high slew rate (25V/µs) make the TLV936x-Q1 a robust operational amplifier for highvoltage, cost-sensitive applications.

The TLV936x-Q1 family of op amps is available in standard packages and is specified from -40°C to 125°C.

Package Information

| PART NUMBER ⁽¹⁾ | PACKAGE | PACKAGE SIZE(2) |
|----------------------------|-----------------|-----------------|
| TLV9361-Q1 | DBV (SOT-23, 5) | 2.9mm × 2.8mm |
| 1LV9301-Q1 | DCK (SC70, 5) | 2mm × 2.1mm |
| | D (SOIC, 8) | 4.9mm × 6mm |
| TLV9362-Q1 | DGK (VSSOP, 8) | 3mm × 4.9mm |
| | PW (TSSOP, 8) | 3mm × 6.4mm |
| TLV9364-Q1 | D (SOIC, 14) | 8.65mm × 6mm |
| 1 LV 3304-Q1 | PW (TSSOP, 14) | 5mm × 6.4mm |

- For all available packages, see the orderable addendum at the end of the data sheet.
- The package size (length × width) is a nominal value and includes pins, where applicable.



$$\frac{V_{OUT}}{V_{IN}} = \left(1 + \frac{R_F}{R_G}\right) \left(\frac{1}{1 + sR_1C_1}\right)$$

TLV936x-Q1 in a Single-Pole, Low-Pass Filter



Table of Contents

| 1 Features1 | 6.4 Device Functional Modes | .22 |
|---|---|-----|
| 2 Applications1 | 7 Application and Implementation | 23 |
| 3 Description1 | 7.1 Application Information | 23 |
| 4 Pin Configuration and Functions3 | 7.2 Typical Applications | |
| 5 Specifications6 | 7.3 Power Supply Recommendations | |
| 5.1 Absolute Maximum Ratings6 | 7.4 Layout | 25 |
| 5.2 ESD Ratings6 | 8 Device and Documentation Support | .27 |
| 5.3 Recommended Operating Conditions6 | 8.1 Device Support | 27 |
| 5.4 Thermal Information for Single Channel6 | 8.2 Documentation Support | 27 |
| 5.5 Thermal Information for Dual Channel7 | 8.3 Receiving Notification of Documentation Updates | .27 |
| 5.6 Thermal Information for Quad Channel7 | 8.4 Support Resources | 27 |
| 5.7 Electrical Characteristics8 | 8.5 Trademarks | 27 |
| 5.8 Typical Characteristics10 | 8.6 Electrostatic Discharge Caution | .28 |
| 6 Detailed Description17 | 8.7 Glossary | .28 |
| 6.1 Overview17 | 9 Revision History | 28 |
| 6.2 Functional Block Diagram17 | 10 Mechanical, Packaging, and Orderable | |
| 6.3 Feature Description18 | Information | 28 |
| | | |



4 Pin Configuration and Functions




Figure 4-1. TLV9361-Q1 DBV Package 5-Pin SOT-23 (Top View)




Figure 4-2. TLV9361-Q1 DCK Package 5-Pin SC70 (Top View)

Table 4-1. Pin Functions: TLV9361-Q1

| | PIN | | TYPE(1) | DESCRIPTION | |
|------|--------|------|---------|---------------------------------|--|
| NAME | SOT-23 | SC70 | ITPE\/ | DESCRIPTION | |
| IN+ | 3 | 1 | I | Non-inverting input | |
| IN- | 4 | 3 | ı | Inverting input | |
| OUT | 1 | 4 | 0 | Dutput | |
| V+ | 5 | 5 | _ | Positive (highest) power supply | |
| V- | 2 | 2 | _ | Negative (lowest) power supply | |

(1) I = input, O = output






Figure 4-3. TLV9362-Q1 D, DGK, and PW Package 8-Pin SOIC, VSSOP, and TSSOP (Top View)

Table 4-2. Pin Functions: TLV9362-Q1

| P | IN | TYPE ⁽¹⁾ | DESCRIPTION | |
|------|-----|---------------------|---------------------------------|--|
| NAME | NO. | 1175(1) | DESCRIPTION | |
| IN1+ | 3 | I | Non-inverting input, channel 1 | |
| IN1- | 2 | I | Inverting input, channel 1 | |
| IN2+ | 5 | I | Non-inverting input, channel 2 | |
| IN2- | 6 | I | Inverting input, channel 2 | |
| OUT1 | 1 | 0 | Output, channel 1 | |
| OUT2 | 7 | 0 | Output, channel 2 | |
| V+ | 8 | _ | Positive (highest) power supply | |
| V- | 4 | _ | Negative (lowest) power supply | |

(1) I = input, O = output






Figure 4-4. TLV9364-Q1 D and PW Package, SOIC and TSSOP (Top View)

Table 4-3. Pin Functions: TLV9364-Q1

| P | IN | | | | |
|------|-----|---------------------|---------------------------------|--|--|
| | | TYPE ⁽¹⁾ | DESCRIPTION | | |
| NAME | NO. | | | | |
| IN1+ | 3 | I | Non-inverting input, channel 1 | | |
| IN1- | 2 | I | Inverting input, channel 1 | | |
| IN2+ | 5 | I | Non-inverting input, channel 2 | | |
| IN2- | 6 | I | Inverting input, channel 2 | | |
| IN3+ | 10 | I | Non-inverting input, channel 3 | | |
| IN3- | 9 | I | Inverting input, channel 3 | | |
| IN4+ | 12 | I | Non-inverting input, channel 4 | | |
| IN4- | 13 | I | Inverting input, channel 4 | | |
| OUT1 | 1 | 0 | Output, channel 1 | | |
| OUT2 | 7 | 0 | Output, channel 2 | | |
| OUT3 | 8 | 0 | Output, channel 3 | | |
| OUT4 | 14 | 0 | Output, channel 4 | | |
| V+ | 4 | _ | Positive (highest) power supply | | |
| V- | 11 | _ | Negative (lowest) power supply | | |

(1) I = input, O = output



5 Specifications

5.1 Absolute Maximum Ratings

over operating ambient temperature range (unless otherwise noted)(1)

| | 1 3 (| MIN | MAX | UNIT |
|---------------------------------------|-------------------------------------|------------|----------------------|------|
| Supply voltage, V _S = (V+) |) – (V–) | 0 | 42 | V |
| | Common-mode voltage ⁽³⁾ | (V-) - 0.5 | (V+) + 0.5 | V |
| Signal input pins | Differential voltage ⁽³⁾ | | V _S + 0.2 | V |
| | Current ⁽³⁾ | -10 | 10 | mA |
| Output short-circuit ⁽²⁾ | | Continuous | us | |
| Operating ambient tempe | erature, T _A | -55 | 150 | °C |
| Junction temperature, T _J | | | 150 | °C |
| Storage temperature, T _{stg} | | -65 | 150 | °C |

- (1) Operating the device beyond the ratings listed under Absolute Maximum Ratings causes permanent damage to the device. These are stress ratings only, based on process and design limitations, and this device has not been designed to function outside the conditions indicated under Recommended Operating Conditions. Exposure to any condition outside Recommended Operating Conditions for extended periods, including absolute-maximum-rated conditions, can affect device reliability and performance.
- (2) Short-circuit to ground, one amplifier per package. Extended short-circuit current, especially with higher supply voltage, can cause excessive heating and eventual destruction.
- (3) Input pins are diode-clamped to the power-supply rails. Input signals that can swing more than 0.5V beyond the supply rails must be current limited to 10mA or less.

5.2 ESD Ratings

| | | | VALUE | UNIT | | |
|--|---|---|-------|------|--|--|
| TLV9361-C | TLV9361-Q1 | | | | | |
| V _(ESD) Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±2000 | V | | | |
| | Electrostatic discharge | Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 ⁽²⁾ | ±1500 | V | | |
| TLV9362-C | 1 and TLV9364-Q1 | | | | | |
| V _(ESD) Electrostatic discharge | | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±2500 | V | | |
| V _(ESD) | Electrostatic discharge | Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 ⁽²⁾ | ±1500 | , V | | |

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

| | | MIN | MAX | UNIT |
|----------------|-----------------------------|------|----------|------|
| Vs | Supply voltage, (V+) – (V–) | 4.5 | 40 | V |
| VI | Common mode voltage range | (V-) | (V+) – 2 | V |
| T _A | Specified temperature | -40 | 125 | °C |

5.4 Thermal Information for Single Channel

| | | TLV93 | 361-Q1 | |
|-----------------------|--|-----------------|---------------|------|
| | THERMAL METRIC(1) | DBV (SOT-23) | DCK (SC70) | UNIT |
| | | 5 PINS | 5 PINS | |
| R _{0JA} | Junction-to-ambient thermal resistance | 189.3 | 202.4 | °C/W |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 86.8 | 111.6 | °C/W |
| $R_{\theta JB}$ | Junction-to-board thermal resistance | 55.9 | 51.6 | °C/W |
| ΨЈТ | Junction-to-top characterization parameter | 23.6 | 25.8 | °C/W |
| ΨЈВ | Junction-to-board characterization parameter | 55.5 | 51.4 | °C/W |

Submit Document Feedback



| | | TLV93 | | |
|-----------------------|--|-----------------|---------------|------|
| | THERMAL METRIC(1) | DBV (SOT-23) | DCK (SC70) | UNIT |
| | | 5 PINS | 5 PINS | |
| R _{θJC(bot)} | Junction-to-case (bottom) thermal resistance | N/A | N/A | °C/W |

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

5.5 Thermal Information for Dual Channel

| | | | TLV9362-Q1 | | |
|-----------------------|--|-------------|----------------|---------------|------|
| THERMAL METRIC(1) | | D (SOIC) | DGK (VSSOP) | PW (TSSOP) | Unit |
| | | 8 PINS | 8 PINS | 8 PINS | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 130.8 | 173.9 | 159.1 | °C/W |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 74.0 | 65.7 | 67.9 | °C/W |
| $R_{\theta JB}$ | Junction-to-board thermal resistance | 74.3 | 95.6 | 98.1 | °C/W |
| ΨЈТ | Junction-to-top characterization parameter | 25.8 | 10.9 | 9.1 | °C/W |
| ΨЈВ | Junction-to-board characterization parameter | 73.5 | 94.1 | 96.7 | °C/W |
| R _{0JC(bot)} | Junction-to-case (bottom) thermal resistance | N/A | N/A | N/A | °C/W |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

5.6 Thermal Information for Quad Channel

| | | TLV9 | TLV9364-Q1 | | | |
|-----------------------|--|-------------|---------------|------|--|--|
| THERMAL METRIC(1) | | D (SOIC) | PW (TSSOP) | UNIT | | |
| | | 14 PINS | 14 PINS | | | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 94.9 | 120.0 | °C/W | | |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 51.1 | 50.4 | °C/W | | |
| $R_{\theta JB}$ | Junction-to-board thermal resistance | 51.4 | 63.1 | °C/W | | |
| ΨЈТ | Junction-to-top characterization parameter | 15.3 | 8.1 | °C/W | | |
| ΨЈВ | Junction-to-board characterization parameter | 51.0 | 62.5 | °C/W | | |
| R _{0JC(bot)} | Junction-to-case (bottom) thermal resistance | N/A | N/A | °C/W | | |

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.



5.7 Electrical Characteristics

For $V_S = (V+) - (V-) = 4.5 \text{ V}$ to 40 V (±2.25 V to ±20 V) at $T_A = 25^{\circ}\text{C}$, $R_L = 10 \text{ k}\Omega$ connected to $V_S / 2$, $V_{CM} = V_S / 2$, and $V_{CHT} = V_S / 2$, unless otherwise noted.

| | ' _S / 2, unless otherwise n | | ONDITIONS | MIN | TYP | MAX | UNIT | |
|----------------------|--|---|---|---------------------------------|----------|----------|--------------------|----|
| OFFSET V | OLTAGE | | | | | | | |
| | | | | | ±0.4 | ±1.7 | | |
| V _{OS} | Input offset voltage | V _{CM} = V- | T _A = -40°C to 125°C | | | ±2 | mV | |
| dV _{OS} /dT | Input offset voltage drift | V _{CM} = V- | T _A = -40°C to 125°C | | ±1.25 | | μV/°C | |
| PSRR | Input offset voltage versus | $V_{CM} = V_{-}, V_{S} = 5 \text{ V to } 40 \text{ V}^{(1)}$ | | | ±1.5 | ±7.5 | μV/V | |
| | power supply | V _{CM} - V-, V _S - 5 V to 40 V V | 1A = -40 C to 125 C | | | ±1.5 | | |
| | DC channel separation | | | | 1 | | μV/V | |
| | AS CURRENT | Г | | T | | | | |
| l _B | Input bias current | | | | ±10 | | pA | |
| los | Input offset current | | | | ±10 | | pA | |
| NOISE | | | | | | | | |
| E _N | Input voltage noise | f = 0.1 Hz to 10 Hz | | | 6 | | μV_{PP} | |
| ⊢IN | imput voltago noiso | 0.1112.0 10112 | | | 1 | | μV_{RMS} | |
| 0 | Input voltage noise density | f = 1 kHz | | | 8.5 | | nV/√ Hz | |
| e _N | input voltage noise density | f = 10 kHz | | | 6 | | IIV/ VIIZ | |
| i _N | Input current noise density | f = 1 kHz | | | 100 | | fA/√Hz | |
| INPUT VO | LTAGE RANGE | | | | | | | |
| V _{CM} | Common-mode voltage range | | | (V-) | | (V+) - 2 | V | |
| | Common-mode rejection | Common-mode rejection | $V_S = 40 \text{ V}, V < V_{CM} < (V+) - 2 \text{ V}$ | T 4000 / 40500 | 95 | 110 | | dВ |
| CMRR | ratio | $V_S = 5 \text{ V}, \text{ V} - < V_{CM} < (\text{V+}) - 2$ | - 1 _A = -40°C to 125°C | 75 | 75 85 | | dB | |
| INPUT IMP | PEDANCE | I | | | | | | |
| Z _{ID} | Differential | | | | 100 9 | | MΩ pF | |
| Z _{ICM} | Common-mode | | | | 6 1 | | TΩ pF | |
| OPEN-LO | OP GAIN | 1 | | | , | | | |
| | Open-loop voltage gain | $V_S = 40 \text{ V}, V_{CM} = V_S / 2,$ $(V-) + 0.1 \text{ V} < V_O < (V+) -$ 0.1 V | | 115 | 130 | | | |
| A _{OL} | | Open-loop voltage gain (| V _S = 40 V, V _{CM} = V _S / 2, (V–) + 0.12 V < V _O < (V+) – 0.12 V | T _A = -40°C to 125°C | | 130 | | dB |
| | | $V_S = 5 \text{ V}, V_{CM} = V_S / 2,$ | | 100 | 120 | | | |
| | | $(V-) + 0.1 V < V_O < (V+) - 0.1 V(1)$ | T _A = -40°C to 125°C | | 120 | | | |
| FREQUEN | LCY RESPONSE | | | | | | | |
| | Gain-bandwidth product | | | | 10.6 | | MHz | |
| | Slew rate | V _S = 40 V, G = +1, V _{STEP} = 10 |) V. C ₁ = 20 pF ⁽³⁾ | | 25 | | V/µs | |
| | | To 0.1%, $V_S = 40 \text{ V}$, $V_{STEP} = 10 \text{ V}$ | | | 0.65 | | -740 | |
| | | To 0.1%, $V_S = 40 \text{ V}$, $V_{STEP} = 20 \text{ V}$ | | | 0.03 | | | |
| t _S | Settling time | To 0.01%, $V_S = 40 \text{ V}$, $V_{STEP} = 20 \text{ V}$ | | | 0.86 | | μs | |
| | | To 0.01%, $V_S = 40 \text{ V}$, $V_{STEP} =$ | | | | + | | |
| | Dhago marain | | | | 0.44 | | 0 | |
| | Phase margin | $G = +1, R_L = 10 k\Omega, C_L = 20 p$ | DF | | 64 | | | |
| | Overload recovery time | V _{IN} × gain > V _S | | | 170 | | ns | |
| | | $V_S = 40 \text{ V}, V_O = 3 \text{ V}_{RMS}, G = 1, f = 1 \text{ kHz}, R_L = 10 \text{ k}\Omega$ | | | 0.0001% | | | |
| | | | | | 120 | | dB | |
| THD+N | Total harmonic distortion + | $V_S = 10 \text{ V}, V_O = 3 V_{RMS}, G = 10 \text{ V}$ | 1, f = 1 kHz, R ₁ = 128 Ω | | 0.0056% | | | |
| | noise | - , - U RIVIO, 9 | | 85 | | dB | | |
| | | V _S = 10 V, V _O = 0.4 V _{RMS} , G = | | 0.00056% | | | | |
| | | VS - 10 V, VO - 0.4 VRMS, G - | | 105 | | dB | | |



For V_S = (V+) – (V–) = 4.5 V to 40 V (±2.25 V to ±20 V) at T_A = 25°C, R_L = 10 k Ω connected to V_S / 2, V_{CM} = V_S / 2, and V_{OUT} = V_S / 2, unless otherwise noted.

| | PARAMETER | TEST | CONDITIONS | MIN | TYP | MAX | UNIT |
|-------------------|----------------------------|-------------------------------------|---|-----------|--------------------|-----|------|
| OUTPUT | | | | | | ' | |
| | | | V _S = 40 V, R _L = no load | | 10 | | mV |
| | 0 | Positive and negative rail headroom | $V_S = 40 \text{ V}, R_L = 10 \text{ k}\Omega$ | 60 250 | | 100 | |
| | | Tail Hodaroom | $V_S = 40 \text{ V}, R_L = 2 \text{ k}\Omega$ | | | 400 | |
| I _{SC} | Short-circuit current | | ' | | ±60 ⁽²⁾ | | mA |
| C _{LOAD} | Capacitive Load Drive | | | See | Figure 5-28 | | pF |
| Z _O | Open-loop output impedance | I _O = 0 A | | See | Figure 5-25 | | Ω |
| POWER S | SUPPLY | 1 | | | | ' | |
| | Quiescent current per | I _O = 0 A | | | 2.6 | | mA |
| IQ | amplifier | 10 - U A | T _A = -40°C to 125°C | | | 3.2 | IIIA |


Specified by characterization only. (1)

At high supply voltage, placing the TLV936x in a sudden short to mid-supply or ground will lead to rapid thermal shutdown. Output current greater than I_{SC} can be achieved if rapid thermal shutdown is avoided as per Figure 5-12.


See Figure 5-11 for more information.




5.8 Typical Characteristics

































6 Detailed Description


6.1 Overview

The TLV936x-Q1 family (TLV9361-Q1, TLV9362-Q1, and TLV9364-Q1) is a family of 40V, cost-optimized operational amplifiers. These devices offer strong general-purpose DC and AC specifications, including rail-to-rail output, low offset (±400µV, typical), low offset drift (±1.25µV/°C, typical), and 10.6MHz bandwidth.

Convenient features such as wide differential input-voltage range, high output current (±60mA), and high slew rate (25V/µs) make the TLV936x-Q1 a robust operational amplifier for high-voltage, cost-sensitive applications.

The TLV936x-Q1 family of op amps is available in standard packages and is specified from -40°C to 125°C.

6.2 Functional Block Diagram





6.3 Feature Description

6.3.1 EMI Rejection

The TLV936x-Q1 uses integrated electromagnetic interference (EMI) filtering to reduce the effects of EMI from sources such as wireless communications and densely-populated boards with a mix of analog signal chain and digital components. EMI immunity can be improved with circuit design techniques; the TLV936x-Q1 benefits from these design improvements. Texas Instruments has developed the ability to accurately measure and quantify the immunity of an operational amplifier over a broad frequency spectrum extending from 10MHz to 6GHz. Figure 6-1 shows the results of this testing on the TLV936x-Q1. Table 6-1 lists the EMIRR IN+ values for the TLV936x-Q1 at particular frequencies commonly encountered in real-world applications. Table 6-1 lists applications that can be centered on or operated near the particular frequency shown. The EMI Rejection Ratio of Operational Amplifiers application report contains detailed information on the topic of EMIRR performance as relates to op amps and is available for download from www.ti.com.




Figure 6-1. EMIRR Testing

Table 6-1. TLV936x-Q1 EMIRR IN+ for Frequencies of Interest

| FREQUENCY | APPLICATION OR ALLOCATION | EMIRR IN+ |
|-----------|--|-----------|
| 400MHz | Mobile radio, mobile satellite, space operation, weather, radar, ultra-high frequency (UHF) applications | 50.0dB |
| 900MHz | Global system for mobile communications (GSM) applications, radio communication, navigation, GPS (to 1.6GHz), GSM, aeronautical mobile, UHF applications | 56.3dB |
| 1.8GHz | GSM applications, mobile personal communications, broadband, satellite, L-band (1GHz to 2GHz) | 65.6dB |
| 2.4GHz | 802.11b, 802.11g, 802.11n, Bluetooth®, mobile personal communications, industrial, scientific and medical (ISM) radio band, amateur radio and satellite, S-band (2GHz to 4GHz) | 70.0dB |
| 3.6GHz | Radiolocation, aero communication and navigation, satellite, mobile, S-band | 78.9dB |
| 5GHz | 802.11a, 802.11n, aero communication and navigation, mobile communication, space and satellite operation, C-band (4GHz to 8GHz) | 91.0dB |

6.3.2 Thermal Protection

The internal power dissipation of any amplifier causes the internal (junction) temperature to rise. This phenomenon is called self heating. The absolute maximum junction temperature of the TLV936x-Q1 is 150°C. Exceeding this temperature causes damage to the device. The TLV936x-Q1 has a thermal protection feature that reduces damage from self heating. The protection works by monitoring the temperature of the device and turning off the op amp output drive for temperatures above 170°C. Figure 6-2 shows an application example for the TLV9362-Q1 that has significant self heating because of the power dissipation (0.954W). In this example, both channels have a quiescent power dissipation while one of the channels has a significant load. Thermal calculations indicate that for an ambient temperature of 55°C, the device junction temperature reaches 180°C. The actual device, however, turns off the output drive to recover towards a safe junction temperature. Figure 6-2



shows how the circuit behaves during thermal protection. During normal operation, the device acts as a buffer so the output is 3V.

When self heating causes the device junction temperature to increase above the internal limit, the thermal protection forces the output to a high-impedance state and the output is pulled to ground through resistor R_L . If the condition that caused excessive power dissipation is not removed, the amplifier oscillates between a shutdown and enabled state until the output fault is corrected. Please note that thermal performance can vary greatly depending on the package selected and the PCB layout design. This example uses the thermal performance of the SOIC (8) package.





Figure 6-2. Thermal Protection

6.3.3 Capacitive Load and Stability

The TLV936x-Q1 features an output stage capable of driving moderate capacitive loads, and by leveraging an isolation resistor, the device can easily be configured to driver large capacitive loads. Increasing the gain enhances the ability of the amplifier to drive greater capacitive loads; see Figure 6-3 and Figure 6-4. The particular op amp circuit configuration, layout, gain, and output loading are some of the factors to consider when establishing whether an amplifier is stable in operation.



For additional drive capability in unity-gain configurations, improve capacitive load drive by inserting a small resistor, $R_{\rm ISO}$, in series with the output, as shown in Figure 6-5. This resistor significantly reduces ringing and maintains DC performance for purely capacitive loads. However, if a resistive load is in parallel with the capacitive load, then a voltage divider is created, thus introducing a gain error at the output and slightly reducing the output swing. The error introduced is proportional to the ratio $R_{\rm ISO}$ / $R_{\rm L}$, and is generally negligible at low output levels. A high capacitive load drive makes the TLV936x-Q1 an excellent choice for applications such as reference buffers, MOSFET gate drives, and cable-shield drives. The circuit shown in Figure 6-5 uses an



isolation resistor, R_{ISO} , to stabilize the output of an op amp. R_{ISO} modifies the open-loop gain of the system for increased phase margin.




Figure 6-5. Extending Capacitive Load Drive With the TLV9361-Q1

6.3.4 Electrical Overstress

Designers often ask questions about the capability of an operational amplifier to withstand electrical overstress (EOS). These questions tend to focus on the device inputs, but can involve the supply voltage pins or even the output pin. Each of these different pin functions have electrical stress limits determined by the voltage breakdown characteristics of the particular semiconductor fabrication process and specific circuits connected to the pin. Additionally, internal electrostatic discharge (ESD) protection is built into these circuits to protect them from accidental ESD events both before and during product assembly.

Having a good understanding of this basic ESD circuitry and relevance to an electrical overstress event is helpful. Figure 6-6 shows an illustration of the ESD circuits contained in the TLV936x-Q1 (indicated by the dashed line area). The ESD protection circuitry involves several current-steering diodes connected from the input and output pins and routed back to the internal power-supply lines, where the diodes meet at an absorption device or the power-supply ESD cell, internal to the operational amplifier. This protection circuitry is intended to remain inactive during normal circuit operation.




Figure 6-6. Equivalent Internal ESD Circuitry Relative to a Typical Circuit Application



An ESD event is very short in duration and very high voltage (for example; 1kV, 100ns), whereas an EOS event is long duration and lower voltage (for example; 50V, 100ms). The ESD diodes are designed for out-of-circuit ESD protection (that is; during assembly, test, and storage of the device before being soldered to the PCB). During an ESD event, the ESD signal is passed through the ESD steering diodes to an absorption circuit (labeled ESD power-supply circuit). The ESD absorption circuit clamps the supplies to a safe level.

Although this behavior is necessary for out-of-circuit protection, excessive current and damage is caused if activated in-circuit. A transient voltage suppressors (TVS) can be used to prevent against damage caused by turning on the ESD absorption circuit during an in-circuit ESD event. Using the appropriate current limiting resistors and TVS diodes allows for the use of device ESD diodes to protect against EOS events.

6.3.5 Overload Recovery

Overload recovery is defined as the time required for the op amp output to recover from a saturated state to a linear state. The output devices of the op amp enter a saturation region when the output voltage exceeds the rated operating voltage, either due to the high input voltage or the high gain. After the device enters the saturation region, the charge carriers in the output devices require time to return back to the linear state. After the charge carriers return back to the linear state, the device begins to slew at the specified slew rate. Thus, the propagation delay in case of an overload condition is the sum of the overload recovery time and the slew time. The overload recovery time for the TLV936x-Q1 is approximately 170ns.

6.3.6 Typical Specifications and Distributions

Designers often have questions about a typical specification of an amplifier to design a more robust circuit. Due to natural variation in process technology and manufacturing procedures, every specification of an amplifier exhibits some amount of deviation from the ideal value, like the input offset voltage of an amplifier. These deviations often follow *Gaussian* (*bell curve*), or *normal* distributions, and circuit designers leverage this information to guard band systems, even when there are no minimum or maximum specifications in the *Electrical Characteristics* table.




Figure 6-7. Ideal Gaussian Distribution

Figure 6-7 shows an example distribution, where μ , or mu, is the mean of the distribution, and σ , or sigma, is the standard deviation of a system. For a specification that exhibits this kind of distribution, approximately two-thirds (68.26%) of all units can be expected to have a value within one standard deviation, or one sigma, of the mean (from $\mu - \sigma$ to $\mu + \sigma$).



Depending on the specification, values listed in the *typical* column of the *Electrical Characteristics* table are represented in different ways. As a general rule, if a specification naturally has a nonzero mean (for example, like gain bandwidth), then the typical value is equal to the mean (μ). However, if a specification naturally has a mean near zero (like input offset voltage), then the typical value is equal to the mean plus one standard deviation (μ + σ) to most accurately represent the typical value.

Use this chart to calculate approximate probability of a specification in a unit; for example, for TLV936x-Q1, the typical input voltage offset is $400\mu\text{V}$, so 68.2% of all TLV936x-Q1 devices are expected to have an offset from $-400\mu\text{V}$ to $400\mu\text{V}$. At 4σ ($\pm 1600\mu\text{V}$), 99.9937% of the distribution has an offset voltage less than $\pm 1600\mu\text{V}$, which means 0.0063% of the population is outside of these limits, which corresponds to about 1 in 15,873 units.

Specifications with a value in the minimum or maximum column are specified by TI, and units outside these limits are removed from production material. For example, the TLV936x-Q1 family has a maximum offset voltage of 1.7mV at 125°C, and even though this corresponds to about 4.25σ (≈2 in 100,000 units), which is unlikely, TI verifies that any unit with larger offset than 1.7mV is removed from production material.

For specifications with no value in the minimum or maximum column, consider selecting a sigma value of sufficient guardband for your application, and design worst-case conditions using this value. For example, the 6σ value corresponds to about 1 in 500 million units, which is an extremely unlikely chance, and can be an option as a wide guardband to design a system around. In this case, the TLV936x-Q1 family does not have a maximum or minimum for offset voltage drift, but based on the typical value of $1.25\mu\text{V/°C}$ in the *Electrical Characteristics* table, the 6σ value is calculated for offset voltage drift is about $7.5\mu\text{V/°C}$. When designing for worst-case system conditions, use this value to estimate the worst possible offset across temperature without having an actual minimum or maximum value.

However, process variation and adjustments over time can shift typical means and standard deviations, and unless there is a value in the minimum or maximum specification column, TI cannot verify the performance of a device. This information must be used only to estimate the performance of a device.

6.4 Device Functional Modes

The TLV936x-Q1 has a single functional mode and is operational when the power-supply voltage is greater than 4.5V (±2.25V). The maximum power supply voltage for the TLV936x-Q1 is 40V (±20V).

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

7 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

7.1 Application Information

The TLV936x-Q1 family offers excellent DC precision and DC performance. These devices operate up to 40V supply rails and offer true rail-to-rail output, low offset voltage and offset voltage drift, as well as 10.6MHz bandwidth and high output drive. These features make the TLV936x-Q1 a robust, high-performance operational amplifier for high-voltage cost-sensitive applications.

7.2 Typical Applications

7.2.1 Low-Side Current Measurement

Figure 7-1 shows the TLV936x-Q1 configured in a low-side current sensing application. For a full analysis of the circuit shown in Figure 7-1 including theory, calculations, simulations, and measured data, see TI Precision Design TIPD129, *OA to 1A Single-Supply Low-Side Current-Sensing Solution*.




Figure 7-1. TLV936x-Q1 in a Low-Side, Current-Sensing Application

7.2.2 Design Requirements

The design requirements for this design are:

Load current: 0A to 1AMax output voltage: 4.9V

Maximum shunt voltage: 100mV

7.2.3 Detailed Design Procedure

The transfer function of the circuit in Figure 7-1 is given in Equation 1:

$$V_{OUT} = I_{LOAD} \times R_{SHUNT} \times Gain$$
 (1)



The load current (I_{LOAD}) produces a voltage drop across the shunt resistor (R_{SHUNT}). The load current is set from 0A to 1A. To keep the shunt voltage below 100mV at maximum load current, the largest shunt resistor is defined using Equation 2:

$$R_{SHUNT} = \frac{V_{SHUNT_MAX}}{I_{LOAD\ MAX}} = \frac{100\ mV}{1\ A} = 100\ m\Omega \tag{2}$$

Using Equation 2, R_{SHUNT} is calculated to be $100m\Omega$. The voltage drop produced by I_{LOAD} and R_{SHUNT} is amplified by the TLV936x-Q1 to produce an output voltage of 0V to 4.9V. The gain needed by the TLV936x-Q1 to produce the necessary output voltage is calculated using Equation 3:

$$Gain = \frac{(V_{OUT_MAX} - V_{OUT_MIN})}{(V_{IN MAX} - V_{IN MIN})}$$
(3)

Using Equation 3, the required gain is calculated to be 49V/V, which is set with resistors R_F and R_G. Equation 4 is used to size the resistors, R_F and R_G, to set the gain of the TLV936x-Q1 to 49V/V.

$$Gain = 1 + \frac{(R_F)}{(R_G)}$$
 (4)

Choosing R_F as 5.76k $\!\Omega,\,R_G$ is calculated to be 120 $\!\Omega.\,R_F$ and R_G were chosen as 5.76k $\!\Omega$ and 120 $\!\Omega$ because the values are standard value resistors that create a 49:1 ratio. Other resistors that create a 49:1 ratio can also be used. However, excessively large resistors generate thermal noise that exceeds the intrinsic noise of the op amp. Figure 7-2 shows the measured transfer function of the circuit shown in Figure 7-1.

7.2.4 Application Curves




Figure 7-2. Low-Side, Current-Sense, Transfer Function

7.3 Power Supply Recommendations

The TLV936x-Q1 is specified for operation from 4.5V to 40V (±2.25V to ±20V); many specifications apply from -40°C to 125°C.

CAUTION

Supply voltages larger than 40V can permanently damage the device; see the Absolute Maximum Ratings table.

Place 0.1µF bypass capacitors close to the power-supply pins to reduce errors coupling in from noisy or high-impedance power supplies. For more detailed information on bypass capacitor placement, refer to the Layout section.



7.4 Layout

7.4.1 Layout Guidelines

For best operational performance of the device, use good PCB layout practices, including:

- Noise can propagate into analog circuitry through the power pins of the circuit as a whole and op amp itself.
 Bypass capacitors are used to reduce the coupled noise by providing low-impedance power sources local to the analog circuitry.
 - Connect low-ESR, 0.1-µF ceramic bypass capacitors between each supply pin and ground, placed as close to the device as possible. A single bypass capacitor from V+ to ground is applicable for singlesupply applications.
- Separate grounding for analog and digital portions of circuitry is one of the simplest and most-effective
 methods of noise suppression. One or more layers on multilayer PCBs are usually devoted to ground planes.
 A ground plane helps distribute heat and reduces EMI noise pickup. Make sure to physically separate digital
 and analog grounds paying attention to the flow of the ground current.
- To reduce parasitic coupling, run the input traces as far away from the supply or output traces as possible. If these traces cannot be kept separate, crossing the sensitive trace perpendicular is much better as opposed to in parallel with the noisy trace.
- Place the external components as close to the device as possible. As shown in Figure 7-4, keeping RF and RG close to the inverting input minimizes parasitic capacitance.
- Keep the length of input traces as short as possible. Always remember that the input traces are the most sensitive part of the circuit.
- Consider a driven, low-impedance guard ring around the critical traces. A guard ring can significantly reduce leakage currents from nearby traces that are at different potentials.
- Cleaning the PCB following board assembly is recommended for best performance.
- Any precision integrated circuit can experience performance shifts due to moisture ingress into the plastic package. Following any aqueous PCB cleaning process, baking the PCB assembly is recommended to remove moisture introduced into the device packaging during the cleaning process. A low temperature, post cleaning bake at 85°C for 30 minutes is sufficient for most circumstances.

Copyright © 2024 Texas Instruments Incorporated



7.4.2 Layout Example




Figure 7-3. Schematic for Non-inverting Configuration Layout Example




Figure 7-4. Operational Amplifier Board Layout for Non-inverting Configuration - SC70 (DCK) Package

8 Device and Documentation Support

8.1 Device Support

8.1.1 Development Support

8.1.1.1 TINA-TI™ (Free Software Download)

TINA™ is a simple, powerful, and easy-to-use circuit simulation program based on a SPICE engine. TINA-TI is a free, fully-functional version of the TINA software, preloaded with a library of macro models in addition to a range of both passive and active models. TINA-TI provides all the conventional dc, transient, and frequency domain analysis of SPICE, as well as additional design capabilities.

Available as a free download from the Analog eLab Design Center, TINA-TI offers extensive post-processing capability that allows users to format results in a variety of ways. Virtual instruments offer the ability to select input waveforms and probe circuit nodes, voltages, and waveforms, creating a dynamic quick-start tool.

Note

These files require that either the TINA software (from DesignSoft[™]) or TINA-TI software be installed. Download the free TINA-TI software from the TINA-TI folder.

8.1.1.2 TI Precision Designs

The TLV936x-Q1 is featured in several TI Precision Designs, available online at http://www.ti.com/ww/en/analog/precision-designs/. TI Precision Designs are analog solutions created by TI's precision analog applications experts and offer the theory of operation, component selection, simulation, complete PCB schematic and layout, bill of materials, and measured performance of many useful circuits.

8.2 Documentation Support

8.2.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, Analog Engineer's Circuit Cookbook: Amplifiers
- Texas Instruments, AN31 amplifier circuit collection application report
- · Texas Instruments, EMI Rejection Ratio of Operational Amplifiers application report
- Texas Instruments, Capacitive Load Drive Solution using an Isolation Resistor reference design.

8.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.4 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.5 Trademarks

TINA-TI™ is a trademark of Texas Instruments, Inc and DesignSoft, Inc.

TINA[™] and DesignSoft[™] are trademarks of DesignSoft, Inc.

TI E2E[™] is a trademark of Texas Instruments.

Bluetooth® is a registered trademark of Bluetooth SIG, Inc.

All trademarks are the property of their respective owners.



8.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.7 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision A (May 2023) to Revision B (August 2024) | Page |
|---|------|
| Added the TLV9362-Q1 PW package to the Package Information table | 1 |
| • Changed the Package Information measurements from: Body Size (Nom) to: Package Size | 1 |
| Added the TLV9362-Q1 PW package to Pin Configuration and Functions | 3 |
| Added 8-pin TSSOP (PW) package to Thermal Information for Dual Channel table | |
| Changes from Revision * (April 2023) to Revision A (May 2023) | Page |
| Changed the status of the D and DGK packages from: preview to: active | |
| • Changed the status of the D and DGK packages from: preview to: active | |

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Document Feedback

www.ti.com 7-Oct-2025

PACKAGING INFORMATION

| Orderable part number | Status | Material type | Package Pins | Package qty Carrier | RoHS | Lead finish/ Ball material | MSL rating/ Peak reflow | Op temp (°C) | Part marking (6) |
|-----------------------|--------|---------------|------------------|-----------------------|------|-------------------------------|----------------------------|--------------|------------------|
| | | | | | | (4) | (5) | | |
| TLV9361QDBVRQ1 | Active | Production | SOT-23 (DBV) 5 | 3000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | 2W1H |
| TLV9361QDBVRQ1.A | Active | Production | SOT-23 (DBV) 5 | 3000 LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | 2W1H |
| TLV9361QDCKRQ1 | Active | Production | SC70 (DCK) 5 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 1NL |
| TLV9361QDCKRQ1.A | Active | Production | SC70 (DCK) 5 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 1NL |
| TLV9362QDGKRQ1 | Active | Production | VSSOP (DGK) 8 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 2S6T |
| TLV9362QDGKRQ1.A | Active | Production | VSSOP (DGK) 8 | 2500 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 2S6T |
| TLV9362QDRQ1 | Active | Production | SOIC (D) 8 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T9362D |
| TLV9362QDRQ1.A | Active | Production | SOIC (D) 8 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T9362D |
| TLV9362QPWRQ1 | Active | Production | TSSOP (PW) 8 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 9362PW |
| TLV9362QPWRQ1.A | Active | Production | TSSOP (PW) 8 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | 9362PW |
| TLV9364QDRQ1 | Active | Production | SOIC (D) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | TLV9364QD |
| TLV9364QDRQ1.A | Active | Production | SOIC (D) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | TLV9364QD |
| TLV9364QPWRQ1 | Active | Production | TSSOP (PW) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T9364PW |
| TLV9364QPWRQ1.A | Active | Production | TSSOP (PW) 14 | 3000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T9364PW |

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

PACKAGE OPTION ADDENDUM

www.ti.com 7-Oct-2025

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TLV9361-Q1, TLV9362-Q1, TLV9364-Q1:

Catalog: TLV9361, TLV9362, TLV9364

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

www.ti.com 24-Jul-2025

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| TLV9361QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 180.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| TLV9361QDCKRQ1 | SC70 | DCK | 5 | 3000 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| TLV9362QDGKRQ1 | VSSOP | DGK | 8 | 2500 | 330.0 | 12.4 | 5.25 | 3.35 | 1.25 | 8.0 | 12.0 | Q1 |
| TLV9362QDRQ1 | SOIC | D | 8 | 3000 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| TLV9362QPWRQ1 | TSSOP | PW | 8 | 3000 | 330.0 | 12.4 | 7.0 | 3.6 | 1.6 | 8.0 | 12.0 | Q1 |
| TLV9364QDRQ1 | SOIC | D | 14 | 3000 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| TLV9364QPWRQ1 | TSSOP | PW | 14 | 3000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |



www.ti.com 24-Jul-2025



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLV9361QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 210.0 | 185.0 | 35.0 |
| TLV9361QDCKRQ1 | SC70 | DCK | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TLV9362QDGKRQ1 | VSSOP | DGK | 8 | 2500 | 366.0 | 364.0 | 50.0 |
| TLV9362QDRQ1 | SOIC | D | 8 | 3000 | 353.0 | 353.0 | 32.0 |
| TLV9362QPWRQ1 | TSSOP | PW | 8 | 3000 | 353.0 | 353.0 | 32.0 |
| TLV9364QDRQ1 | SOIC | D | 14 | 3000 | 353.0 | 353.0 | 32.0 |
| TLV9364QPWRQ1 | TSSOP | PW | 14 | 3000 | 353.0 | 353.0 | 32.0 |



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
- 5. Reference JEDEC registration MS-012, variation AB.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-203.

- 4. Support pin may differ or may not be present.5. Lead width does not comply with JEDEC.
- 6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side





NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.





- 9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 10. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE INTEGRATED CIRCUIT



- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.



SMALL OUTLINE INTEGRATED CIRCUIT



- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.





- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153, variation AA.






NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.





- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.





NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.





- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.







PowerPAD is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-187.





- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- 8. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.
- 9. Size of metal pad may vary due to creepage requirement.





- 11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 12. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated