





SLAS345 - DECEMBER 2001

# 5-V, LOW POWER, 14-BIT, 200-KSPS SERIAL ANALOG-TO-DIGITAL CONVERTERS WITH AUTO-POWER DOWN

### **FEATURES**

- 200-KSPS Sampling Rate
- Built-In Conversion Clock
- INL: ±1 LSB Max DNL: ±1 LSB Max
- SINAD = 81.5 dB, SFDR = 95 dB
   THD = 94 dB at 15 kHz f<sub>in</sub>, 200 KSPS
- SPI/DSP-Compatible Serial Interfaces With SCLK Input up to 15 MHz
- Single 5-V Supply
- Rail-to-Rail Analog Input With 500 kHz BW
- Two Input Options Available:
  - TLC3541 Single Channel Input
  - TLC3545 Single Channel,
     Pseudo-Differential Input
- (TLC3541) Optimized DSP Interface Requires FS Input Only
- Low Power With Auto-Power Down
  - Operating Current: 3.5 mA
  - Auto-Powerdown Current: 5 μA
- Pin Compatible 12-/14-/16-Bit Family in 8-Pin SOIC and MSOP Packages


### **APPLICATIONS**


- ATE System
- Industrial Process Control
- Measurement
- Motor Control

### **DESCRIPTION**

The TLC3541 and TLC3545 are a family of high performance, 14-bit, low power, miniature CMOS analog-to-digital converters (ADCs). These devices operate from a single 5-V supply. Devices are available with single, dual, or single pseudo-differential inputs. All of these devices have a chip select  $(\overline{CS})$ , serial clock (SCLK), and serial data output (SDO) that provides a direct 3-wire interface to the serial port of most popular host microprocessors (SPI interface). When interfaced with a DSP, a frame sync signal (FS) is used to indicate the start of a serial data frame on either pin 1  $(\overline{CS})$  or pin 7 (FS) for the TLC3541. The TLC3545 ADC connects to the DSP via pin 1 only  $(\overline{CS})$ .

The TLC3541 and TLC3545 are designed to operate with low power consumption. The power saving feature is further enhanced with an auto-power down mode. This product family features a high-speed serial link to modern host processors with an external SCLK up to 15 MHz. Both families use a built-in oscillator as the conversion clock, providing a 2.67  $\mu$ s maximum conversion time.








Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




### **AVAILABLE OPTIONS**

_	PACKAGED DEVICES					
ТД	8-MSOP (DGK)	8-SOIC (D)				
	TLC3541IDGK (PKG Code = AMG)	TLC3541ID				
-40°C to 85°C	TLC3545IDGK (PKG Code = AMM)	TLC3545ID				

### functional block diagram





### **Terminal Functions**

### TLC3541 single channel unipolar ADCs

TERMIN	AL	1/0	DESCRIPTION
NAME	NO.	1/0	DESCRIPTION
AIN	4	I	Analog input channel
CS	1	I	Chip select. A high-to-low transition on the $\overline{\text{CS}}$ input removes SDO from a high-impedance state within a maximum delay time. If the TLC3541 is attached to a dedicated TMS320 DSP serial port using the FS input, $\overline{\text{CS}}$ can be grounded.
FS	7	I	DSP frame sync input. Indication of a start of a serial data frame. A low-to-high transition removes SDO from the high-impedance state and the MSB is presented. Tie this pin to V <sub>DD</sub> if not used.
GND	3	I	Ground return for the internal circuitry. Unless otherwise noted, all voltage measurements are with respect to GND.
SDO	8	0	$\frac{\text{The 3-state serial data output for the A/D conversion result. SDO is kept in the high-impedance state when }{\text{CS}} \text{ is high. The output format is MSB first. Remaining data bits are presented on the rising edge of SCLK.}$
			When FS is not active (FS = 1 at the falling edge of $\overline{CS}$ ): The MSB is presented on the SDO pin on the falling edge of $\overline{CS}$ after a maximum delay time. Data is valid on each falling edge of SCLK until all data is read.
			When FS is active (FS = 0 at the falling edge of $\overline{\text{CS}}$ ): The MSB is presented to the SDO output on the rising edge of FS. Data is valid on the falling edge SCLK and changes on the rising edge SCLK (this is typically used with an active FS from a DSP).
			SDO returns to the high-impedance state after the 17th rising edge on SCLK. If a 17th SCLK cycle is not presented, as is the case when using an SPI host, SDO returns to the high-impedance state on the rising edge of $\overline{\text{CS}}$ .
SCLK	5	I	Serial clock. This terminal receives the serial SCLK from the host processor.
REF	2	I	External voltage reference input
$V_{DD}$	6	Ι	Positive supply voltage

### TLC3545 single channel pseudo-differential ADCs

TERMIN	AL	1/0	DESCRIPTION
NAME	NO.	1/0	DESCRIPTION
AIN0 (+)	4	I	Positive analog input for the TLC3545.
AIN1 (-)	5	- 1	Inverted analog input for the TLC3545.
CS	1	I	Chip select. A high-to-low transition on $\overline{\text{CS}}$ removes SDO from the high-impedance state within a maximum delay time. The $\overline{\text{CS}}$ input can be connected to a DSP frame sync (FS) output when a dedicated TMS320 DSP serial port is used.
GND	3	I	Ground return for the internal circuitry. Unless otherwise noted, all voltage measurements are with respect to GND.
SDO	8	0	The 3-state serial data output for the A/D conversion result. SDO is kept in the high-impedance state when $\overline{\text{CS}}$ is high and presents output data after the $\overline{\text{CS}}$ falling edge until the LSB is presented. The output format is MSB first. The remaining data bits are presented on the rising edge of SCLK. Output data is valid on each falling edge of SCLK until all data is read. SDO returns to the high-impedance state after the 17th rising edge on SCLK. If a 17th SCLK cycle is not presented, as is the case when using an SPI host, SDO returns to the high-impedance state on the rising edge of $\overline{\text{CS}}$ .
SCLK	7	I	Serial clock. This terminal receives the serial SCLK from the host processor.
REF	2	I	External voltage reference input
$V_{DD}$	6	I	Positive supply voltage

SLAS345 - DECEMBER 2001

### absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>

Supply voltage, GND to V <sub>DD</sub>	0.3 V to 6.5V
Analog input voltage range	0.3 V to V <sub>DD</sub> +0.3 V
Reference input voltage	V <sub>DD</sub> +0.3 V
Digital input voltage range	
Operating virtual junction temperature range, T <sub>J</sub>	–40°C to 150°C
Operating free-air temperature range: T <sub>A</sub> (I suffix)	–40°C to 85°C
Storage temperature range, T <sub>Stq</sub>	
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### recommended operating conditions

		MIN	NOM	MAX	UNIT
Supply voltage, V <sub>DD</sub>		4.5	5	5.5	V
Frequency, SCLK	V <sub>DD</sub> = 4.5 V to 5.5 V	100		15000	kHz
Tolerable clock jitter, SCLK	V <sub>DD</sub> = 4.5 V to 5.5 V			97	ps
Aperature jitter	V <sub>DD</sub> = 4.5 V to 5.5 V		100		ps
External reference voltage input, V <sub>REF</sub>	External reference voltage input, V <sub>REF</sub>	4		$V_{DD}$	V
	$V_{DD} = 5 \text{ V}, \overline{CS} = 1, \text{ SCLK} = 0$	100			МΩ
V <sub>REF</sub> input impedance	$V_{DD} = 5 \text{ V},  \overline{CS} = 0,  \text{SCLK} = 15 \text{ MHz}$	20	25		kΩ
External reference input current	$V_{DD} = V_{REF} = 4.5 \text{ V}, \overline{CS} = 0, \text{ SCLK} = 15 \text{ MHz}$		0.02	1	mA
	AIN, AIN(+)	0		$V_{DD}$	.,
Analog input voltage	AIN(-)	-0.2		0.2	V
High level control input voltage, V <sub>IH</sub>		2.1			V
Low level control input voltage, V <sub>IL</sub>				0.8	V
Operating free-air temperature, T <sub>A</sub>	TLC3541/45I	-40		85	°C



# electrical characteristics over recommended operating free-air temperature range, $V_{DD} = 5 \text{ V}$ , $V_{REF} = 4.096 \text{ V}$ , SCLK frequency = 15 MHz (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
Vон	High-level output voltage	$V_{DD} = 4.5 \text{ V}, \qquad I_{OH} = -0.2 \text{ mA}$	3.9			V
VOL	Low-level output voltage	$V_{DD} = 4.5 \text{ V}$ $I_{OL} = 0.8 \text{ mA}$			0.4	V
	Off-state output current	$V_O = V_{DD}$ , $\overline{CS} = V_{DD}$		1	2.5	
loz	(high-impedance-state)	$V_O = 0$ , $\overline{CS} = V_{DD}$		-1	-2.5	μΑ
lн	High-level input current	$V_I = V_{DD}$		0.005	2.5	μΑ
IIL	Low-level input current	V <sub>I</sub> = 0	-	-0.005	2.5	μΑ
ICC	Operating supply current	<del>CS</del> at 0 V, V <sub>DD</sub> = 4.5 V to 5.5 V			3.5	mA
ICC(PD)	Power-down supply current	For all digital inputs, $0 \le V_I \le 0.3 \text{ V}$ or $V_I \ge V_{DD} - 0.3 \text{ V}$ , SCLK= $V_{DD}$ , $V_{DD} = 4.5 \text{ V}$ to $5.5 \text{ V}$		3	5	μА
	Selected analog input channel leakage	Selected channel at V <sub>DD</sub>			1	
	current	Selected channel at 0 V			-1	μΑ
	Land and all the second	Analog inputs		11	14	
Ci	Input capacitance	Control Inputs		20	25	рF
Zi	Input resistance	V <sub>DD</sub> = 5.5 V			500	Ω

### ac specifications (TLC3541/45)

PARAMETER			TEST CONDITIONS	MIN	TYP	MAX	UNIT
SINAD	Signal-to-noise ratio +distortion		f <sub>I</sub> = 15 kHz at 200 KSPS		81.5		dB
SNR	Signal-to-noise ratio		f <sub>I</sub> = 15 kHz at 200 KSPS		82		dB
		TLC3541	f <sub>I</sub> = 15 kHz at 200 KSPS		-94	-87	-10
THD	THD Total harmonic distortion		f <sub>I</sub> = 15 kHz at 200 KSPS		-94	-89	dB
ENOB	B Effective number of bits		f <sub>I</sub> = 15 kHz at 200 KSPS		13.2		Bits
OFDD			f <sub>I</sub> = 15 kHz at 200 KSPS		-95	-87	10
SFDR	Spurious free dynamic range	TLC3545	f <sub>I</sub> = 15 kHz at 200 KSPS		-95	-89	dB
	Full-power bandwidth, -3 dB, and	alog input			1		MHz
	Full-power bandwidth, -1 dB, analog input				500		kHz
Crosstal	k		0.25 LSB	80			dB

### dc specifications (TLC3541/45)

	,					
	PARAMETER	TEST CONDITIONS	MIN	TYP <sup>†</sup>	MAX	UNIT
INL	Integral linearity error (see Note 1)		-1		1	LSB
DNL	Differential linearity error		-1	0.75	1	LSB
_	E <sub>O</sub> Offset error (see Note 2)	TLC3541	-3.5		3.5	
FO		TLC3545	-1		1	mV
_	0 : ( )   ( )	TLC3541	-2		2	
E <sub>G</sub> Gain error (see Note 2)		TLC3545	-1.8		1.8	mV

<sup>†</sup> All typical values are at  $V_{DD} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

NOTES: 1. Linear error is the maximum deviation from the best straight line through the A/D transfer characteristics.



<sup>2.</sup> Zero error is the difference between 0000h and the converted output for zero input voltage: full-scale error is the difference between ideal full-scale and the converted output for full-scale input voltage.

## TLC3541, TLC3545

### SLAS345 - DECEMBER 2001

# timing requirements, $V_{DD}$ = 5 V, $V_{REF}$ = 4.096 V, SCLK frequency = 15 MHz (unless otherwise specified)

		MIN	TYP	MAX	UNIT
tcyc(SCLK)	SCLK cycle time, V <sub>DD</sub> = 4.5 V to 5.5 V (see Note 3)	66		10000	ns
t <sub>w1</sub>	Pulse duration, SCLK low	27		5000	ns
t <sub>w2</sub>	Pulse duration, SCLK high	27		5000	ns
t <sub>h1</sub>	Hold time, CS high after SCLK falling edge	3			ns
t <sub>su1</sub>	Setup time, CS falling edge before the first SCLK falling edge	15			ns
t <sub>h2</sub>	Hold time, CS low after 16th SCLK falling edge	5			ns
t <sub>W3</sub>	Pulse duration, CS high	0.5			SCLKs
<sup>t</sup> d1	Delay time, $\overline{\text{CS}}$ falling edge to SDO MSB valid, $V_{DD} = V_{REF} = 4.5 \text{ V}$ , 20 pF		12	17	ns
t <sub>d2</sub>	Delay time, SCLK rising edge to next SDO data bit valid, V <sub>DD</sub> = V <sub>REF</sub> = 4.5 V, 20 pF			15	ns
t <sub>d3</sub>	Delay time, 17 <sup>th</sup> SCLK rising edge to 3-stated SDO, V <sub>DD</sub> = V <sub>REF</sub> = 4.5 V, 20 pF (see Note 4)			20	ns
t <sub>su3</sub>	Setup time, CS falling edge before FS rising edge (TLC3541 only)	0.5	1		SCLKs
t <sub>W4</sub>	Pulse duration, FS high (TLC3541 only)	0.5	1		SCLKs
t <sub>su4</sub>	Setup time, FS rising edge before SCLK falling edge (TLC3541 only)	12.5			ns
t <sub>h4</sub>	Hold time, FS high after SCLK falling edge (TLC3541 only)	5			ns
t <sub>su5</sub>	Setup time, FS falling edge before 1st SCLK falling edge (TLC3541 only)	12			ns
t <sub>d4</sub>	Delay time, FS rising edge to SDO MSB valid, (V <sub>DD</sub> = V <sub>REF</sub> = 4.5 V, 20 pF TLC3541 only)			15	ns
th6	Hold time, CS low after 1st SCLK falling edge	5			ns
t <sub>su6</sub>	Setup time, CS rising edge before 9th (or the last) SCLK falling edge	5			ns
t <sub>h7</sub>	Hold time, FS low after 1st SCLK falling edge (TLC3541 only)	5			ns
t <sub>su7</sub>	Setup time, FS rising edge before 9th (or the last) SCLK falling edge	5			ns
tcyc(reset)	Active CS/FS cycle time, SCLK falling edges required to initialize ADC	1		8	SCLKs
tconv	Conversion time (20 conversion clocks based on 7.5 MHz to 12 MHz OSC)	1.67		2.67	μs
t <sub>S</sub>	Sample time, 20 SCLKs, SCLK up to 15 MHz	1.33		200	μs

NOTES: 3. Timing specifications given for 40/60 to 60/40 duty cycle



<sup>4.</sup> SDO goes into the high impedance state after detection of the 17th rising SCLK edge or a rising  $\overline{\text{CS}}$  edge if a 17th SCLK is not presented.




Figure 1




Figure 2





Figure 3



# UNTEGRAL NONLINEARITY 1.5 0.5 -0.5 -1 -1.5 0 5000 10000 15000 Code

Figure 4



# INPUT FREQUENCY -80 VDD = VREF = 5 V -90 -90 20 40 60 80 100 120

fi - Input Frequency - kHz

TOTAL HARMONIC DISTORTION

Figure 5 Figure 6

### **TOTAL HARMONIC DISTORTION** FREE-AIR TEMPERATURE -82 -84 THD - Total Harmonic Distortion - dB -86 f<sub>i</sub> = 100 kHz -88 -90 -92 $f_i = 15 \text{ kHz}$ -94 -96 $f_i = 1 \text{ kHz}$ -98 -40 25 80 $T_A$ – Free-Air Temperature – $^{\circ}C$

Figure 7








Figure 8











### control and timing

### device initialization/RESET cycle

The TLC3541/45 each require one RESET cycle after power-on for initialization in order to operate properly. The RESET cycle is initiated by asserting the  $\overline{CS}$  pin (pin 1) low for a minimum duration of at least one SCLK falling edge but no more than 8 SCLK falling edges in length. The RESET cycle is terminated by asserting  $\overline{CS}$  high. If a valid RESET cycle is issued, the data presented on the SDO output during the following cycle is 3FC0h. This output code is useful in determining when a valid reset/initialization has occurred.

The TLC3541 has separate  $\overline{CS}$  and FS pins. In this case, it is also possible to initiate the RESET cycle by asserting FS low if  $\overline{CS}$  is already asserted low. The RESET cycle can be terminated by either asserting  $\overline{CS}$  high (as shown in the first RESET cycle in Figure 14), or by asserting FS high (as shown in the second RESET cycle in Figure 14), whichever happens first.




Figure 14. TLC3541/45 Initialization Timing

### sampling

The converter sample time is 20 SCLKs in duration, beginning on the 5th SCLK received during an active signal on the  $\overline{\text{CS}}$  input (or FS input for the TLC3541.)

### conversion

Each device completes a conversion in the following manner. The conversion is started after the 24th falling SCLK edge. The  $\overline{\text{CS}}$  input can be released at this point or at any time during the remainder of the conversion cycle. The conversion takes a maximum of 2.67  $\mu$ s to complete. Enough time (for conversion) should be allowed before the next falling edge on the  $\overline{\text{CS}}$  input (or rising edge on the FS input for the TLC3541) so that no conversion is terminated prematurely. If the conversion cycle is terminated early, the data presented on SDO during the following cycle is 3FC0h. This predefined output code is helpful in determining if the cycle time is not long enough to complete the conversion. The same code is also used to determine if a reset cycle is valid.

For all devices, the SDO data presented during a cycle is the result of the conversion of the sample taken during the previous cycle. The output data format is shown in the following table.

SERIAL OUTPUT DATA FORMAT							
	MSB [D15:D2] LSB [D1:D0]						
TLC3541/45	Conversion result (OD13-OD0)	Don't care					



### control and timing (continued)

### sampling and conversion cycle

### TLC3541:

Control via pin  $\underline{1}$ ,  $\overline{CS}$  (FS = 1 at the falling edge of  $\overline{CS}$ ) – The falling edge of  $\overline{CS}$  is the start of the cycle. Transitions on  $\overline{CS}$  can occur when SCLK is high or low. The MSB may be read on the first falling SCLK edge after  $\overline{CS}$  is low. Output data changes on the rising edge of SCLK. This control method is typically used for a microcontroller with an SPI interface, although it can also be used for a DSP. The microcontroller SPI interface should be programmed for CPOL = 0 (serial clock inactive low) and CPHA = 1 (data valid on the falling edge of serial clock).

Control via pin 7, FS  $\overline{\text{CS}}$  is tied/held low) – The rising edge of FS is the start of the cycle. Transitions on FS can occur when SCLK is high or low. The MSB is presented on SDO after the rising edge of FS. The MSB may be read on the first falling edge of SCLK after the FS falling edge. Output data changes on the rising edge of SCLK. This is the typical configuration when the ADC is the only device on the TMS320 DSP serial port.

Control via pin 1 and pin 7,  $\overline{\text{CS}}$  and FS – Transitions on  $\overline{\text{CS}}$  and FS can occur when SCLK is high or low. The MSB is presented after the rising edge of FS. The falling edge of FS is the start of the sampling cycle. The MSB may be read on the first falling edge of SCLK after the FS falling edge. Output data changes on the rising edge of SCLK. This is typically used for multiple devices connected to a single TMS320 DSP serial port.

### TLC3545:

All control is provided using the  $\overline{CS}$  input (pin 1) on the TLC3545. Transitions on  $\overline{CS}$  can occur when SCLK is high or low. The cycle is started on the falling edge transition on the  $\overline{CS}$  input. This signal can be provided by either a  $\overline{CS}$  signal (when interfacing with an SPI microcontroller) or FS signal (when interfacing with a TMS320 DSP). The MSB is presented to SDO on the falling edge of the signal applied to pin 1 and may be read on the first falling SCLK edge after this input is low. Output data changes on the rising edge of SCLK.

### control modes

### control via pin 1 (CS, SPI interface)

All devices are compatible with this mode of operation. A falling edge on the  $\overline{CS}$  input initiates the cycle. (For the TLC3541, the FS input is tied to  $V_{DD}$ ). The  $\overline{CS}$  input remains low for the entire sampling time plus 4 SCLK decoding time (24 falling SCLK edges) and can then be released at any point during the remainder of the conversion. Enough time should be allowed before the next falling  $\overline{CS}$  edge so that the conversion cycle is not terminated prematurely. The microcontroller SPI interface should be programmed for CPOL = 0 (serial clock inactive low) and CPHA = 1 (data is valid on the falling edge of serial clock).




Figure 15. SPI Cycle Timing Using the CS Input (FS = 1 for TLC3541)



### control via pin 1 (CS, DSP interface)

All devices are compatible with this mode of operation. The FS signal from a DSP is connected directly to the  $\overline{\text{CS}}$  input of the ADC. A falling edge on the  $\overline{\text{CS}}$  input while SCLK is high or low initiates the cycle. (For TLC3541 in this configuration, the FS input is tied to  $V_{DD}$ .) Enough time should be allowed before the next rising  $\overline{\text{CS}}$  edge so that the conversion cycle is not terminated prematurely.




Figure 16. DSP Cycle Timing Using the CS Input (FS = 1 for TLC3541 only)

### control via pin 1 and pin 7 (CS and FS or FS only, DSP interface)

Only TLC3541 is compatible with this mode of operation. The  $\overline{\text{CS}}$  input to the ADC can be controlled via a general-purpose I/O pin from the DSP or tied to ground. The FS signal from the DSP is connected directly to the FS input of the ADC. A rising FS edge releases the MSB to the SDO output. The falling edge on the FS input while SCLK is high or low initiates the cycle. The  $\overline{\text{CS}}$  input should remain low for the entire sampling time plus 4 SCLK decoding time after falling FS (24 falling SCLK edges) and can then be released at any time during the remainder of the conversion cycle. The optimum DSP interface is achieved when tying  $\overline{\text{CS}}$  to ground and using only the FS input to control the ADC.




Figure 17. DSP Cycle Timing Using FS Only (or Using Both CS and FS for TLC3541)






Figure 18. Critical Timing: Control Via CS Input (FS = 1 for TLC3541)




Figure 19. Critical Timing: Control Via CS and FS Inputs (TLC3541 Only)




Figure 20. Critical Timing: Reset/Initialization Cycle (FS =1 for TLC3541)






Figure 21. Critical Timing: Initialization Cycle (TLC3541 Only)

### detailed description

The TLC3541/5 are successive approximation (SAR) ADCs utilizing a charge-redistribution DAC. Figure 22 shows a simplified version of the ADC. The sampling capacitor acquires the signal on AIN (or the AIN(+) pin for TLC3545) during the sampling period. When the conversion process starts, the SAR control logic and charge redistribution DAC are used to add and subtract fixed amounts of charge from the sampling capacitor to bring the comparator into a balanced condition. When the comparator is balanced, the conversion is complete and the ADC output code is generated.




Figure 22. Simplified SAR Circuit

### pseudo-differential inputs

The TLC3545 operates in pseudo-differential mode. The inverted input is available on pin 5. The inverted input can tolerate a maximum input ripple of  $\pm 0.2$  V. It is normally used for zero-scale offset cancellation or ground noise rejection.

### serial interface

Output data format is binary (unipolar straight binary).

### binary

- Zero-Scale Code = 0000h, V<sub>AIN</sub> = GND
- Full-Scale Code = 3FFFh, V<sub>AIN</sub> = V<sub>REF</sub> 1 LSB

### reference voltage


An external reference must be applied via pin 2,  $V_{REF}$ . The voltage level applied to this pin establishes the upper limit of the analog inputs to produce a full-scale reading. The value of  $V_{REF}$ , and the analog input should not exceed the positive supply or be less than GND, consistent with the specified absolute maximum ratings. The digital output is at full scale when the input signal is equal to or higher than  $V_{REF}$  and at zero when the input signal is equal to or less than GND.


### auto-power down and power up

Auto-power down is built into the devices in order to reduce power consumption. The wake-up time is fast enough to provide power down between each conversion cycle. The power-down state is initiated at the end of conversion and wakes up on a falling  $\overline{CS}$  edge (or rising FS edge, whichever occurs first, for TLC3541 only).



### **APPLICATION INFORMATION**





### **DSP to Multiple TLC3541s**




Figure 23. Typical ADC Interface to a TMS320 DSP







www.ti.com

23-May-2025

### PACKAGING INFORMATION

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	RoHS	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
						(4)	(5)		
TLC3541ID	Active	Production	SOIC (D)   8	75   TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3541ID.B	Active	Production	SOIC (D)   8	75   TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3541IDG4	Active	Production	SOIC (D)   8	75   TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3541IDGK	Active	Production	VSSOP (DGK)   8	80   TUBE	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	AMG
TLC3541IDGK.B	Active	Production	VSSOP (DGK)   8	80   TUBE	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	AMG
TLC3541IDGKR	Active	Production	VSSOP (DGK)   8	2500   LARGE T&R	Yes	Call TI   Nipdauag	Level-1-260C-UNLIM	-40 to 85	AMG
TLC3541IDGKR.B	Active	Production	VSSOP (DGK)   8	2500   LARGE T&R	Yes	Call TI	Level-1-260C-UNLIM	-40 to 85	AMG
TLC3541IDR	Active	Production	SOIC (D)   8	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3541IDR.B	Active	Production	SOIC (D)   8	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3541IDRG4	Active	Production	SOIC (D)   8	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35411
TLC3545ID	Active	Production	SOIC (D)   8	75   TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35451
TLC3545ID.B	Active	Production	SOIC (D)   8	75   TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35451
TLC3545IDGK	Active	Production	VSSOP (DGK)   8	80   TUBE	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	AMM
TLC3545IDGK.B	Active	Production	VSSOP (DGK)   8	80   TUBE	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	AMM
TLC3545IDR	Active	Production	SOIC (D)   8	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35451
TLC3545IDR.B	Active	Production	SOIC (D)   8	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	35451

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.



### **PACKAGE OPTION ADDENDUM**

www.ti.com 23-May-2025

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

### **PACKAGE MATERIALS INFORMATION**

www.ti.com 23-May-2025

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLC3541IDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLC3545IDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1



www.ti.com 23-May-2025



### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLC3541IDR	SOIC	D	8	2500	350.0	350.0	43.0
TLC3545IDR	SOIC	D	8	2500	350.0	350.0	43.0

### **PACKAGE MATERIALS INFORMATION**

www.ti.com 23-May-2025

### **TUBE**



\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
TLC3541ID	D	SOIC	8	75	505.46	6.76	3810	4
TLC3541ID.B	D	SOIC	8	75	505.46	6.76	3810	4
TLC3541IDG4	D	SOIC	8	75	505.46	6.76	3810	4
TLC3541IDGK	DGK	VSSOP	8	80	331.47	6.55	3000	2.88
TLC3541IDGK.B	DGK	VSSOP	8	80	331.47	6.55	3000	2.88
TLC3545ID	D	SOIC	8	75	505.46	6.76	3810	4
TLC3545ID.B	D	SOIC	8	75	505.46	6.76	3810	4
TLC3545IDGK	DGK	VSSOP	8	80	331.47	6.55	3000	2.88
TLC3545IDGK.B	DGK	VSSOP	8	80	331.47	6.55	3000	2.88



SMALL OUTLINE PACKAGE



### NOTES:

PowerPAD is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-187.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- 8. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.
- 9. Size of metal pad may vary due to creepage requirement.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 12. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE INTEGRATED CIRCUIT



### NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



### NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated