

Table of Contents

1 Features	1	7.7 Register 06H: CHGR_SET3.....	55
2 Applications	1	7.8 Register 07H: CHGR_SET4.....	56
3 Description	1	7.9 Register 08H: CHGR_STATUS.....	57
4 Pin Configuration and Functions	3	7.10 Register 09H: SOH_SET1.....	58
5 Specifications	5	7.11 Register 0AH: SOH_SET2.....	59
5.1 Absolute Maximum Ratings.....	5	7.12 Register 0BH: CONTROL_STATUS.....	60
5.2 ESD Ratings.....	5	7.13 Register 0CH: FAULT_CONDITION.....	61
5.3 Recommended Operating Conditions.....	5	7.14 Register 0DH: STATUS_PIN_SET.....	62
5.4 Thermal Information.....	5	7.15 Register 0EH: SW_RST.....	63
5.5 Electrical Characteristics.....	6	8 Application and Implementation	64
5.6 I2C Timing Characteristics.....	9	8.1 Application Information.....	64
5.7 Typical Characteristics.....	10	8.2 Typical Application.....	64
6 Detailed Description	14	8.3 Power Supply Recommendations.....	76
6.1 Overview.....	14	8.4 Layout.....	76
6.2 Functional Block Diagram.....	15	9 Device and Documentation Support	80
6.3 Feature Description.....	16	9.1 Device Support.....	80
6.4 Device Functional Modes.....	19	9.2 Documentation Support.....	80
6.5 I ² C Serial Interface.....	43	9.3 Receiving Notification of Documentation Updates.....	80
7 Register Maps	48	9.4 Support Resources.....	80
7.1 Register 00H: CHIP_ID.....	49	9.5 Trademarks.....	80
7.2 Register 01H: BOOST_SET1.....	50	9.6 Electrostatic Discharge Caution.....	80
7.3 Register 02H: BOOST_SET2.....	51	9.7 Glossary.....	80
7.4 Register 03H: BOOST_SET3.....	52	10 Revision History	80
7.5 Register 04H: CHGR_SET1.....	53	11 Mechanical, Packaging, and Orderable Information	81
7.6 Register 05H: CHGR_SET2.....	54		

4 Pin Configuration and Functions




Figure 4-1. TPS61382Q1 QFN with Wettable Flank Package, 24-Pin (Top View)

TERMINAL		I/O	DESCRIPTION
NAME	RAV		
BUB	1	I	Back up battery voltage sensing pin. Connect BUB as close as possible to the positive terminal of the battery for the most accurate voltage sense.
COMP	2	O	External compensation pin. This pin is the output of the transconductance amplifier. Connect a compensation network from the COMP pin to AGND.
AVI	3	O	Analog voltage output pin for battery State of Health (SOH) detection function. AVI pin outputs back-up battery voltage, discharge current or back up battery temperature according to I2C setting. The pin has internal 125kΩ pulldown resistance to AGND when AVI output is disabled.
SCL	4	I	Clock pin for I2C interface.
SDA	5	I/O	Data pin for I2C interface.
AGND	6	G	Signal ground pin. Connect with PGND (Low side MOSFET source) through 20mil wire or 0Ω resistor. View Section 8.4.2 for detailed GND connection.
EN_CHGR	7	I	Charger function enable pin. Drive this pin high / low to enable / disable the charger function.
STATUS	8	O	STATUS indication output pin. Open drain output for STATUS indication function. Output low when entering boost mode by default. Selectable by I2C to output other signals.
VCC	9	O	Internal regulator output. Used as supply to internal control circuits. Do not connect this pin to any external loads. Connect 2.2-4.7μF capacitor from this pin to AGND.
LO	10	O	Gate driver pin for low-side MOSFET.
VOUT	11, 12, 13, 14	P	Boost converter output pin.

TERMINAL		I/O	DESCRIPTION
NAME	RAV		
SW	15, 16, 17	P	Device switch pins and the switch node of the regulator. Connect to the low side MOSFET drain.
IL	18, 19, 20, 21	P	Boost converter input pin. Connect to the inductor.
BOOT	22	O	Power supply for the high-side MOSFET gate driver. Connect a 100nF-470nF capacitor between the SW node and BOOT. An internal diode charges the capacitor while SW node is low.
EN_BST	23	I	Boost function enable pin. Drive this pin high / low to enable / disable the boost function.
TS	24	I	Temperature qualification voltage input pin. Connect a negative temperature coefficient (NTC) thermistor directly from TS to GND (AT103-2 recommended). Charge suspends when the TS pin voltage is out of range.
EP	25	G	Thermal pad. Connect with AGND.

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
Voltage range at terminals	SW, VOUT	−0.3	40	V
	IL	−0.3	18	V
	BUB, EN_BST, EN_CHGR, STATUS	−0.3	15	V
	LO, TS, AVI, SDA, SCL, VCC, COMP	−0.3	6	V
	BOOT to SW	−0.3	6	V
T _J	Junction temperature	−40	150	°C
T _{stg}	Storage temperature	−65	150	°C

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

5.2 ESD Ratings

			VALUE	UNIT
V _(ESD) ⁽¹⁾	Electrostatic discharge	Human-body model (HBM), per AEC Q100-002 ⁽²⁾	±2000	V
		Charged-device model (CDM), per AEC Q100-011, all pins ⁽³⁾	±500	
V _(ESD) ⁽¹⁾	Electrostatic discharge	Charged-device model (CDM), per AEC Q100-011, corner pins ⁽³⁾	±750	V

- (1) Electrostatic discharge (ESD) to measure device sensitivity and immunity to damage caused by assembly line electrostatic discharges in to the device.
- (2) Level listed above is the passing level per ANSI, ESDA, and JEDEC JS-001. JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 500-V HBM is possible with the necessary precautions.
- (3) Level listed above is the passing level per EIA-JEDEC JESD22-C101. JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process. Manufacturing with less than 250-V CDM is possible with the necessary precautions.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V _{BUB}	Back-up battery voltage range	0		3.8	V
V _{OUT}	Output voltage range	V _{in}		20	V
L	Effective inductance range for 400kHz frequency	1	2.2		μH
C _I	Effective input capacitance range, (enable buck charger)	10	30	220	μF
C _I	Effective input capacitance range, (enable BuB voltage loop), BUB IR<100mohm			10	μF
C _I	Effective input capacitance range, (enable BuB voltage loop), BUB IR<400mohm			5	μF
C _O	Effective output capacitance range	30	220		μF
T _A	Ambient temperature	−40		125	°C
T _J	Junction temperature	−40		150	°C

5.4 Thermal Information

THERMAL METRIC ⁽¹⁾		RAV (24 PINS)	RAV (24 PINS)	UNIT
		Standard	EVM	
R _{θJA}	Junction-to-ambient thermal resistance	40.4	25.49	°C/W

5.4 Thermal Information (continued)

THERMAL METRIC ⁽¹⁾		RAV (24 PINS)	RAV (24 PINS)	UNIT
		Standard	EVM	
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	12.0	N/A	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	6.9	N/A	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	0.2	2.4	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	6.9	13.05	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	23.6	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

5.5 Electrical Characteristics

$T_J = -40^{\circ}\text{C}$ to 150°C , $V_{BUB} = 3.6\text{V}$ and $V_{OUT} = 12\text{V}$ (buck mode), $V_{OUT} = 10\text{V}$ (boost mode). Typical values are at $T_J = 25^{\circ}\text{C}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER SUPPLY						
V_{BUB}	Back-up battery voltage range		0		3.8	V
V_{BUB_UVLO}	Undervoltage lockout threshold	V_{BUB} rising with $V_{OUT} = 0\text{V}$			3	V
V_{BUB_UVLO}	Undervoltage lockout threshold	V_{BUB} rising with $V_{out} > 5\text{V}$ or $V_{CC} > 4.5\text{V}$, boost mode active			1	V
V_{BUB_UVLO}	Undervoltage lockout threshold	V_{BUB} falling with $V_{OUT} > V_{VOUT_UVLO}$, boost mode active		0.5	0.6	V
V_{VOUT_UVLO}	Undervoltage lockout threshold	V_{OUT} rising			3.5	V
$V_{VOUT_UVLO_HYS}$	V_{VOUT_UVLO} hysteresis				300	mV
$I_{Q_BOOST_STANDBY}$	Quiescent current into BUB pin at standby mode	$V_{OUT} = 11\text{V}$ to 18V , T_J up to 85°C .		0.01	0.1	μA
$I_{Q_BOOST_STANDBY}$	Quiescent current into VOUT pin at standby mode	$V_{OUT} = 11\text{V}$ to 18V , T_J up to 85°C .		20	30	μA
$I_{Q_CHG_DONE}$	Quiescent current into BUB pin at charge done state	$V_{out} = 12\text{V}$, $V_{BUB} > \text{target}$, T_J up to 85°C		0.01	0.1	μA
$I_{Q_BUCK_STANDBY}$	Quiescent current into VOUT pin at charge done state	$V_{out} = 12\text{V}$, $V_{BUB} > \text{target}$, T_J up to 85°C		20	30	μA
I_{SD}	Shutdown current into BUB pin	$EN_BST=0$ and $EN_CHGR=0$, T_J up to 85°C		0.2	1	μA
I_{SD}	Shutdown current into VOUT pin	$EN_BST=0$ and $EN_CHGR=0$, T_J up to 85°C		0.2	1	μA
I_{VOUT_LKG}	Leakage current into VOUT pin, Q2 leakage current	$V_{SW} = V_{IL} = 0\text{V}$ and $V_{OUT} = 10\text{V}$ to 18V , IC disabled, T_J up to 85°C		0.1	10	μA
I_{IL_LKG}	Leakage current into IL pin, Q leakage current	$V_{SW} = V_{OUT} = 0\text{V}$ and $V_{IL} = 0\text{V}$ to 4.8V , IC disabled, T_J up to 85°C		0.1	10	μA
V_{CC}	Internal regulator output	$I_{CC}=20\text{mA}$	5	5.2	5.35	V
BOOST OUTPUT						
V_{OUT}	Output voltage setting range	Programmable by I2C	5		12	V
$V_{OUT_PWM_ACY}$	Output voltage accuracy	PWM or FPWM	-2.5		2.5	%
$V_{OUT_PFM_ACY}$		PFM		1.5		%

5.5 Electrical Characteristics (continued)

$T_J = -40^{\circ}\text{C}$ to 150°C , $V_{BUB} = 3.6\text{V}$ and $V_{OUT} = 12\text{V}$ (buck mode), $V_{OUT} = 10\text{V}$ (boost mode). Typical values are at $T_J = 25^{\circ}\text{C}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
$V_{OUT_STANDBY}$	Boost standby threshold	Vout rising		6		%
$V_{OUT_OV_P}$	Buck charger and boost output overvoltage protection, rising			23		V
$V_{OUT_OV_P}$	Buck charger and boost output overvoltage protection, falling			21		V
t_{OFF_min}	Min. off time	Boost mode, low side		100	157	ns
Duty_min_down_mode	Min. duty at boost mode			6	11	%
I_{LIM_boost}	Average current limit accuracy in boost mode	$I_{LIM_boost} = 5\text{A}$	4	5	6	A
I_{LIM_boost}	Average current limit accuracy in boost mode	$I_{LIM_boost} = 10\text{A}$	8	10	12	A
I_{LIM_boost}	Average current limit accuracy in boost mode	$I_{LIM_boost} = 15\text{A}$	11	15	18	A
I_{peak_boost}	Absolute peak current limit range in boost mode	$I_{LIM_boost} = 5\text{A}$ or 10A		15		A
I_{peak_boost}	Absolute peak current limit range in boost mode	$I_{LIM_boost} = 15\text{A}$		30		A
POWER SWITCH						
$R_{DS(on)}$	High-side MOSFET on resistance	$V_{CC} = 5.0\text{V}$		20		mΩ
$R_{DS(on)}$	Isolation MOSFET on resistance	$V_{CC} = 5.0\text{V}$		6		mΩ
f_{SW}	Switching frequency		360	400	440	kHz
GATE DRIVER						
V_{DRV_L}	Low-state voltage drop	100-mA sinking		0.08		V
V_{DRV_H}	High-state voltage drop	$V_{CC} - V_{DRV}$, 100-mA sourcing		0.18		V
BUCK CC/CV						
V_{BUB}	BUB CV setting voltage range		1.7		3.8	V
	V_{BUB} accuracy	For Li-ion and LiFePO4, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	-1		1	%
	V_{BUB} accuracy	For super capacitor, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	-2		2	%
I_{CC}	Charging current setting range	LDO charger	50		100	mA
I_{CC}	Charging current setting range	Buck charger	0.5		3	A
D_{Fault_max}	Minimum duty fault logic threshold	$f_s=400\text{kHz}$		1		V
D_{Fault_min}	Maximum duty fault logic threshold	$f_s=400\text{kHz}$		92.5		%
I_{CC_ACC}	I_{CC} accuracy	$I_{CC} = 1\text{A}$, Buck Charger, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	750		1300	mA
		$I_{CC} = 3\text{A}$, Buck Charger, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	2500		3420	mA
		$50\text{mA} \leq I_{CC} < 100\text{mA}$, LDO Charger, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	-20		20	%
$V_{BUB_SHORT_RT}$	BUB short circuit voltage rising threshold, per cell for Li-ion battery	V_{BUB} rising, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	2.1	2.2	2.3	V
$V_{BUB_SHORT_RT}$	BUB short circuit voltage rising threshold, per cell for LiFePO4 battery	V_{BUB} rising, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	1.1	1.2	1.3	V
$V_{BUB_SHORT_RT_HYS}$	Hysteresis			170		mV

5.5 Electrical Characteristics (continued)

$T_J = -40^{\circ}\text{C}$ to 150°C , $V_{BUB} = 3.6\text{V}$ and $V_{OUT} = 12\text{V}$ (buck mode), $V_{OUT} = 10\text{V}$ (boost mode). Typical values are at $T_J = 25^{\circ}\text{C}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I_{SHORT}	BUB short current			15		mA
$V_{BUB_LO_WV}$	Pre-charge to fast-charge transient threshold, per cell for Li-ion battery	V_{BUB} rising, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	2.7	2.8	3	V
$V_{BUB_LO_WV}$	Pre-charge to fast-charge transient threshold, per cell for LiFePO4 battery	V_{BUB} rising, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	1.9	2	2.1	V
$V_{BUB_LO_WV_HYS}$	Hysteresis, per cell	V_{BUB} falling		90		mV
V_{RECHG_HYS}	Battery recharge threshold, per cell for Li-ion battery	V_{BUB} falling, $V_{BUB_CV} - V_{BUB}$, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	50	100	200	mV
V_{RECHG_HYS}	Battery recharge threshold, per cell for LiFePO4 battery	V_{BUB} falling, $V_{BUB_CV} - V_{BUB}$, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	150	200	285	mV
V_{RECHG_HYS}	Battery recharge threshold, per cell for super capacitor	V_{BUB} falling, $V_{BUB_CV} - V_{BUB}$, $V_{BUB} = 2.5\text{V}$, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	110	150	200	mV
V_{CHG_NIMH}	Battery charge threshold, per cell for NiMH battery	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	1.31	1.34	1.365	V
V_{BUB_OVP}	BUB overvoltage threshold for Li-ion / LiFePO4 / super capacitor	Rising, As percentage of V_{BUB} , $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	101	104	106	%
V_{BUB_OVP}	BUB overvoltage threshold, per cell for NiMH battery	Rising, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	1.65	1.7	1.75	V
t_{CHARGE}	Charging timer accuracy		7	8	9	hr
t_{SAFETY}	Safety timer accuracy		9	10	11.5	hr
$t_{ON_INTERMITTENT}$	On time in intermittent charge			2		s
$t_{OFF_INTERMITTENT}$	Off time in intermittent charge			58		s
BATTERY-PACK NTC MONITOR						
I_{TS_BIAS}	TS nominal bias current	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	35.5	38	40.2	uA
V_{COLD}	Cold temperature threshold	TS pin voltage rising (approx. 0°C)	0.99	1.04	1.09	V
	Cold temperature exit threshold	TS pin voltage falling (approx. 4°C)	0.83	0.88	0.93	V
V_{HOT}	Hot temperature threshold	TS pin voltage falling (approx. 45°C)	176	188	200	mV
	Hot temperature exit threshold	TS pin voltage rising (approx. 40°C)	208	220	232	mV
V_{TS_CLAMP}	TS maximum voltage clamp	TS pin open circuit(float)	2.3	2.6	2.9	V
BATTERY HEALTH DETECTION						
$I_{DISCHARGE}$	Discharge current range		0		1.5	A
$I_{DISCHARGE_ACC}$	Discharge current accuracy	$T_J = 25^{\circ}\text{C}$	480	500	520	mA
$I_{DISCHARGE_ACC}$	Discharge current accuracy	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	470	500	520	mA
$V_{DISCHARGE_AVI}$	Discharge current measurement voltage range		0		3.3	V
$V_{DISCHARGE_AVI_ACC}$	Discharge current measurement voltage accuracy	$I_{DISCHARGE} = 500\text{mA}$, ratio=2, $T_J = 25^{\circ}\text{C}$	-3.2		3.2	%
$V_{DISCHARGE_AVI_ACC}$	Discharge current measurement voltage accuracy	$I_{DISCHARGE} = 500\text{mA}$, ratio=2, $T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	-4		4	%
V_{BUB_AVI}	BUB voltage measurement range		0		3.3	V

5.5 Electrical Characteristics (continued)

$T_J = -40^{\circ}\text{C}$ to 150°C , $V_{BUB} = 3.6\text{V}$ and $V_{OUT} = 12\text{V}$ (buck mode), $V_{OUT} = 10\text{V}$ (boost mode). Typical values are at $T_J = 25^{\circ}\text{C}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{BUB_AVI}	BUB voltage measurement accuracy	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$, ratio = 0.5	-0.3		0.15	%
V_{BUB_AVI}	BUB voltage measurement accuracy	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$, ratio = 1	-0.1		0.1	%
V_{TEMP_AVI}	BUB temperature measurement range		0		3.3	V
$V_{TEMP_AVI_ACC}$	BUB measurement accuracy	$T_J = -20^{\circ}\text{C} \sim 85^{\circ}\text{C}$	-0.46		0.69	%
LOGIC INTERFACE						
V_{I2C_IO}	IO voltage range for I2C		1.7		5.5	V
V_{I2C_H}	I ² C input high threshold	$V_{CC} = 2.7\text{V}$ to 5.5V			1.2	V
V_{I2C_L}	I ² C input low threshold	$V_{CC} = 2.7\text{V}$ to 5.5V	0.4			V
V_{EN_H}	EN_BST and EN_CHG logic high threshold	$V_{CC} = 2.7\text{V}$ to 5.5V			1.2	V
V_{EN_L}	EN_BST and EN_CHG logic low threshold	$V_{CC} = 2.7\text{V}$ to 5.5V	0.4			V
THERMAL PROTECTION						
T_{SD}	Thermal shutdown	T_J rising		175		$^{\circ}\text{C}$
T_{SD_HYS}	Thermal shutdown hysteresis			15		$^{\circ}\text{C}$

5.6 I2C Timing Characteristics

$T_J = -40^{\circ}\text{C}$ to 150°C , $V_{CC} = 5\text{V}$. Typical values are at $T_J = 25^{\circ}\text{C}$, unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I2C TIMING						
f_{SCL}	SCL clock frequency		100		1000	kHz
t_{BUF}	Bus free time between a STOP and START condition	Fast mode plus	0.5			μs
$t_{HD(STA)}$	Hold time (repeated) START condition		260			ns
t_{LOW}	Low period of the SCL clock		0.5			μs
t_{HIGH}	High period of the SCL clock		260			ns
$t_{SU(STA)}$	Setup time for a repeated START condition		260			ns
$t_{SU(DAT)}$	Data setup time		50			ns
$t_{HD(DAT)}$	Data hold time		0			μs
t_{RCL}	Rise time of SCL signal				120	ns
t_{RCL1}	Rise time of SCL signal after a repeated START condition and after an ACK bit				120	ns
t_{FCL}	Fall time of SCL signal				120	ns
t_{RDA}	Rise time of SDA signal				120	ns
t_{FDA}	Fall time of SDA signal				120	ns
$t_{SU(STO)}$	Setup time of STOP condition		260			ns
C_B	Capacitive load for SDA and SCL				200	pF

5.7 Typical Characteristics




Figure 5-1. Boost Efficiency vs Output Current, $V_{OUT} = 6.2V$, PFM




Figure 5-2. Boost Efficiency vs Output Current, $V_{OUT} = 6.2V$, FPWM




Figure 5-3. Boost Efficiency vs Output Current, $V_{OUT} = 8V$, PFM




Figure 5-4. Boost Efficiency vs Output Current, $V_{OUT} = 8V$, FPWM




Figure 5-5. Boost Efficiency vs Output Current, $V_{OUT} = 10V$, PFM




Figure 5-6. Boost Efficiency vs Output Current, $V_{OUT} = 10V$, FPWM

5.7 Typical Characteristics (continued)




Figure 5-7. Output Voltage vs Output Current, $V_{OUT} = 6.2V$, PFM




Figure 5-8. Output Voltage vs Output Current, $V_{OUT} = 8V$, PFM




Figure 5-9. Output Voltage vs Output Current, $V_{OUT} = 10V$, PFM




Figure 5-10. Charger Efficiency vs BUB Voltage, LiFePO4 Battery, 1Cell




Figure 5-11. Charger Efficiency vs BUB Voltage, LiFePO4 Battery, 1Cell




Figure 5-12. Switching Frequency Accuracy vs Temperature, FPWM, $V_{BUB} = 3.6V$, $V_{OUT} = 10V$

5.7 Typical Characteristics (continued)




Figure 5-13. Output Voltage Accuracy vs Temperature, FPWM, $V_{BUB} = 3.6V$, $V_{OUT} = 10V$




Figure 5-14. Quiescent Current into BUB vs BUB Voltage, $V_{OUT} = 12V$




Figure 5-15. Quiescent Current into VOUT vs VOUT Voltage, $V_{BUB} = 3.6V$




Figure 5-16. Shutdown Current into BUB vs BUB Voltage, $V_{OUT} = 12V$




Figure 5-17. Shutdown Current into VOUT vs VOUT Voltage, $V_{BUB} = 3.6V$




Figure 5-18. Battery Regulation Voltage Accuracy vs Temperature, $I_{charge} = 100mA$

5.7 Typical Characteristics (continued)




Figure 5-19. Charge Current Accuracy vs Temperature, $I_{\text{charge}} = 100\text{mA}$




Figure 5-20. Precharge Current Accuracy vs Temperature




Figure 5-21. Discharge Current Accuracy vs Temperature, $I_{\text{discharge}} = 500\text{mA}$




Figure 5-22. AVI Pin Discharge Current Output Accuracy vs Temperature, $I_{\text{discharge}} = 500\text{mA}$, Ratio = 2




Figure 5-23. AVI Pin BUB Voltage Output Accuracy vs Temperature, Ratio = 1

6 Detailed Description

6.1 Overview

The TPS61382Q1 is a bi-directional boost converter / buck charger with battery State-of Health (SOH) detection function. The device provides integrated topology for back-up power system like TBOX and e-Call applications. The converter supports 40V voltage rating on VOUT pin to withstand load-dump condition and support direct connection with 12V car battery. The converter supports boost function for back up power system. The IC automatically switch to boost mode when car battery malfunction occurs and voltage drop on the system side is detected.

The TPS61382Q1 integrates boost function that operates over a wide range of 0.5V to 3.8V BUB voltage and 5V to 12V programmable output voltage in boost mode. The device uses fix frequency peak current mode control scheme which provides simplified loop compensation, rapid response to load transients and inherent line voltage rejection. An error amplifier compares the feedback voltage with the internal reference voltage. The output of the error amplifier determines the peak inductor current. The IC also supports 5A-15A selectable average current limit.


The TPS61382Q1 integrates an I2C configurable constant-current / constant-voltage (CC/CV) buck / LDO charger to charge the battery. The charger function supports 1 to 2cell NiMH, 1cell Li-Ion, LiFePO4 and 1cell super capacitor. The device supports battery temperature monitor function which connects TS pin to battery NTC to detect battery temperature and pauses charging when high/low temperature is detected.

The TPS61382Q1 integrates battery State-of Health (SOH) detection feature which discharge the battery with a constant current and detect the voltage drop across the battery internal resistance. By controlling back-up battery discharge current by I2C interface and output the detected BUB voltage to MCU, the MCU calculates the internal resistance and diagnose the battery health.

An internal oscillator operates with fixed 400kHz and provide clock for the IC switching cycle. To minimize EMI, TPS61382Q1 dithers the switching frequency at $\pm 7\%$ of the 400kHz switching frequency.

The TPS61382Q1 is available in a 3mm $\times$ 4mm QFN package with wettable flank.

6.2 Functional Block Diagram



6.3 Feature Description

6.3.1 VCC Power Supply and UVLO Logic

An internal VCC_LDO sinks current from either BUB or VOUT pin to power VCC to 5.2V target depending on BUB and VOUT voltage and operating mode. The IC is enabled only when at least one of its EN pins is high and VCC voltage > 2.8V.

A ceramic capacitor is connected between the VCC pin and AGND pin to stabilize the VCC voltage and also decouple the noise on the VCC pin. Keep the effective capacitance of this ceramic capacitor is above 1μF. A ceramic capacitor with an X7R or X5R grade dielectric with a voltage rating higher than 6.3V is recommended.

TPS61382Q1 applies undervoltage lockout (UVLO) logic on BUB, VOUT and VCC pin depending on different operating mode. Apply sufficient voltage to so that the IC is powered correctly.

Table 6-1. UVLO Logic

Operating Mode	VBUB	VOUT	VCC
Boost Mode	>V _{BUB_UVLO}	>0V	>2.8V
Charger Mode	>0V	>V _{VOUT_UVLO}	>2.8V
SOH Mode	>0V	>V _{VOUT_UVLO}	>2.8V
Standby Mode	>0V	>V _{VOUT_UVLO}	>2.8V

6.3.2 Enable or Shutdown

TPS61382Q1 applies two EN pins to configure operating modes of the device. The I2C interface function is enabled by either EN_BST pin or EN_CHGR pin. After device is enabled, the IC enters its operating mode depending on EN pins, I2C configuration and VOUT voltage. Check [Section 6.4](#) for details about operation modes.

Table 6-2. Enable or Shutdown Logic

EN pins configuration	I2C EN bits configuration	Device State	I2C Interface	Device Current Consumption
EN_CHGR pin = 0 AND EN_BST pin = 0	X	Shutdown	Disabled Register Reset	<1μA(typ)
EN_CHGR pin = 1 AND EN_BST pin = 0	CHGR_SOH_EN bit = 00b	Standby	Enabled	20μA(typ)
EN_CHGR pin = 0 AND EN_BST pin = 1	CHGR_SOH_EN bit = 00b	Standby	Enabled	20μA(typ)
EN_CHGR pin = 1	CHGR_SOH_EN bit = 01b/10b	Device Active	Enabled	According to working condition
EN_BST pin = 1	BST_EN bit = 1	Device Active	Enabled	According to working condition

When TPS61382Q1 is disabled by EN pin (EN_BST=0 AND EN_CHGR=0), the device is completely Shutdown. Under shutdown state, the device consumes less than 1μA shutdown current, I2C registers are reset to default and I2C interface is disabled. When the device is disabled by EN bit (BST_EN = 0 AND CHGR_SOH_EN = 0), the device enters standby state. Current consumption under this state is 20μA, I2C register contents are kept and I2C interface is active.

During shutdown and standby state, TPS61382Q1 supports true disconnection function and the backup battery is completely disconnected from the output.

6.3.3 STATUS Pin

TPS61382Q1 supports status indication function or external PMOS load disconnect switch driver function by multiplexing its STATUS pin (Pin 8). Configure Register 0DH (STATUS_PIN_SET), to configure pin8 as open-drain status indicator output or external PMOS driver.

6.3.3.1 Status Indicator IO (STATUS Pin)

TPS61382Q1 supports status indication function with its STATUS pin. The STATUS pin operates as an open-drain digital output to indicate the IC status or trigger interrupt of your system MCU.

TPS61382Q1 STATUS pin supports indicating multiple items by configuring I2C register 0DH (Bit 3 to Bit 7). The pin is set to indicate BST_ACTIVE (boost active) status by default. When the device enters boost mode, the STATUS pin is pulled low to indicate a boost active status. The pin outputs charge done, thermal shutdown or TS fault signal depending on I2C setting. If multiple status items are selected, the pin output the NOR logic of all items (Pull low if any of the status is triggered).

Table 6-3. STATUS Pin Indication Items

Register 0DH Bit	Selected Item	Description
[7]	INC_BST	BST_ACTIVE status is included in the STATUS pin. Output low when entering boost mode.
[6]	INC_ABST	ALRT_BST_ACTIVE status is included in the STATUS pin. Output low when boost mode has been entered since last read.
[5]	INC_ADN	ALRT_CHGR_DONE status is included in the STATUS pin. Output low when charge done has been triggered since last read.
[4]	INC_TSD	THRM_SD status is included in the STATUS pin. Output low when thermal shutdown protection is triggered.
[3]	INC_TSFAULT	TS_FAULT status is included in the STATUS pin. Output low when TS pin detects cold/hot temperature over range.

6.3.3.2 Configured as External PMOS Driver

TPS61382Q1 supports external PMOS driver function with its STATUS pin. The STATUS pin operates as an 70µA pull down current source to drive the ISO switch connected to the car main battery. (Shown in Figure 6-1).




Figure 6-1. DRV Pin Control External P-MOSFET

Set DRV_CONTROL bit (Register 0DH, Bit 1) 0 to apply automatic control over the PMOS driver. When the device Vout drops to its wake up threshold and the device enters boost mode, the DRV pin becomes open and the ISO switch is turned off to prevent reverse current into car main battery. As the device quits boost mode, the DRV pin sinks 70µA to drive the ISO switch open.

Set DRV_CONTROL bit (Register 0DH, Bit 1) 1 to apply manual control over the PMOS driver. The driver output follows the I2C DRV_OUT bit (Register 0DH, Bit 0). Set DRV_OUT bit high when you need to turn on the ISO FET, the STATUS pin sink 70µA to turn on the PMOS.

The resistance on R_{GS} is calculated as below to turn on PMOS:

$$R_{GS} = \frac{V_{GSon}}{70\mu A} \quad (1)$$

The PMOS driver turn off speed could be over 50µs depending on PMOS Qg parameter and R_{GS} value. So check whether your 12V battery is robust enough to withstand temporary reverse current before PMOS fully turns off.

6.3.4 Thermal Shutdown

Thermal shutdown limits total power dissipation by turning off the internal switches when the IC junction temperature exceeds 175°C (typical). After thermal shutdown occurs, hysteresis prevents the device from toggling until the junction temperature drops to approximately 160°C. When the junction temperature falls below 160°C (typical), TPS61382Q1 attempts to re-start.

6.4 Device Functional Modes

TPS61382Q1 supports four operating modes for its main functions: charger mode, boost mode, State-of-Health (SOH) mode and standby mode. The power structure of each modes are depicted by figures below:




Figure 6-2. Standby Mode




Figure 6-3. Boost Mode




Figure 6-4. Charger Mode




Figure 6-5. SOH Mode

TPS61382Q1 applies AND logic on its EN pins and I2C EN bits. The boost function is enabled when EN_BST pin and BST_EN bit is both high. Charger is enabled when EN_CHGR pin is high and CHGR_SOH_EN bit is 01b. SOH is enabled when EN_CHGR pin is high and CHGR_SOH_EN bit is 10b.

Table 6-4. Operating Modes Control Logic

Boost enable: EN_BST pin AND BST_EN bit	Charger/SOH enable: EN_CHGR AND CHGR_SOH_EN bit	Device State	Device Operation
EN_BST = 0 or BST_EN = 0	EN_CHGR = 1 and CHGR_SOH_EN = 01b	Pure charger	Charger Active.
EN_BST = 0 or BST_EN = 0	EN_CHGR = 1 and CHGR_SOH_EN = 10b	Pure SOH	SOH Active.
EN_BST = 1 and BST_EN = 1	EN_CHGR = 0 or CHGR_SOH_EN=00b	Automatic boost and standby	- Boost Active: $V_{OUT} < BST_WAKE$ - Standby Active: $V_{OUT} > V_{OUT_STANDBY}(106\%V_{OUT_TARGET})$
EN_BST = 1 and BST_EN = 1	EN_CHGR = 1 and CHGR_SOH_EN = 01b	Automatic boost and charger mode	- Boost Active: $V_{OUT} < BST_WAKE$ - Charger Active: $V_{OUT} > V_{OUT_STANDBY}(106\%V_{OUT_TARGET})$
EN_BST = 1 and BST_EN = 1	EN_CHGR = 1 and CHGR_SOH_EN = 10b	Automatic boost and SOH mode	- Boost Active: $V_{OUT} < BST_WAKE$ - SOH Active: $V_{OUT} > V_{OUT_STANDBY}(106\%V_{OUT_TARGET})$

When multiple functions are enabled, TPS61382Q1 monitors system voltage by VOUT pin to decide which function mode to enter. The IC stays in standby/ charger or SOH mode (depending on which function is enabled) when system voltage is sufficient and automatically transition into boost mode when car battery malfunction occurs and voltage drop on system voltage is detected. The different operation modes are shown in the Functional State Diagram.




Figure 6-6. Functional State Diagram




Figure 6-7. Automatic Boost and Standby/Charger/SOH Transition Logic

6.4.1 Charger Mode Description

TPS61382Q1 integrates buck/LDO charger function with integrated charging strategy for multiple types of back up battery. By setting the battery type, cell number, charging current, charging voltage and charging timer, TPS61382Q1 automatically applies corresponding charging strategy for the selected battery chemistry.

- Supports multiple types of back up battery: NiMH(1S 2S), LiFePO4(1S), Li-ion(1S), super capacitor(1S)
- Optional charging current: 50mA to 100mA (LDO mode), 150mA to 3A (Buck mode, NiMH battery), 500mA to 3A (Buck mode, lithium battery or super capacitor)
- Support charger status indication by I2C interface: Register 08H (CHGR_STATUS)

TPS61382Q1 supports multiple safety protection and monitor functions for both battery charging and system operations. Charging safety timer, back up battery overvoltage protection, charger anti-reverse protection and battery cold/hot temperature protections are applied to protect battery safety during charger operation. Also, TPS61382Q1 indicates the charger status and fault condition by CHGR_STATUS and FAULT_CONDITION registers.

6.4.1.1 Charger Enable

TPS61382Q1 charger function is enabled when:

- EN_CHGR pin is high
- CHGR_SOH_EN=01b (I2C Register 0BH: CONTROL_STATUS, Bit [6:5])
- $V_{OUT} < V_{OUT_OVP}$
- $V_{CC} > 2.8V$

After charger function is enabled, the IC enters charger mode when $V_{OUT} >$ boost wake-up threshold (Set by I2C BST_WAKE bits).

When charger mode is active, TPS61382Q1 charge the back-up battery (BUB pin). The charger only support step down operation. So if V_{OUT} drops below 100mV+BUB Voltage, the charger turn off all power MOSFETs to protect itself.

6.4.1.2 LDO Charger and Buck Charger Description

TPS61382Q1 supports two charging topologies for different applications. Set I2C CHGR_TO bit (Register 06H: CHGR_SET3, Bit 7) to select topology. Select buck charger for better efficiency or LDO charger for better EMI performance.

6.4.1.2.1 Buck Charger

TPS61382Q1 integrates buck charger function with I2C selectable charging current from 150mA to 3A. The buck charger applies 400kHz fix frequency average current control scheme. In buck charger mode, Q2 and Q1 switches as buck leg while Q3 is fully turned on.




Figure 6-8. Buck Charger Structure

TPS61382Q1 supports multiple battery chemistry including NiMH battery, Li-ion battery, LiFePO4 battery and super capacitor. By setting I2C BUB_TYP bits (Register 04H: CHGR_SET1 bit [6:7]), TPS61382Q1 charges back up battery with the integrated charging profile for the selected battery type.

For buck charger, the device available duty range is limited by minimum on-time of the Q1 and Q2, so buck operation is only available when BUB voltage is between 1V and 92.6% VOUT. If BUB voltage is below 1V or above 92.6% VOUT, TPS61382Q1 triggers its duty fault logic.




Figure 6-9. 400kHz Buck Charging Operation

TPS61382Q1 enters LDO mode when BUB voltage drops below 1V and the minimum duty fault threshold is triggered. When minimum duty fault is triggered, the TPS61382Q1 switch to linear charge and the charging current decreases to 100mA. When BUB voltage is higher than maximum duty fault threshold, the TPS61382Q1 also switch to LDO charger mode. For $I_{CC} < 750\text{mA}$, charging current decreases to 100mA, for $I_{CC} \geq 750\text{mA}$, charging current decreases to 660mA.

6.4.1.2.2 LDO Charger

TPS61382Q1 supports LDO charger function with 50mA or 100mA charging current. In LDO charger mode, Q_2 is regulated in saturation region to control the charging current while Q_3 is fully turned on. Keep VOUT voltage over $0.6V + V_{BUB}$ Voltage to keep Q_2 in saturation region.




Figure 6-10. Linear Charger Structure

6.4.1.3 NiMH Battery Charging Profile

In NiMH charging mode, TPS61382Q1 charges batteries with a time-controlled charging profile consisting of two phases: continuous charge and intermittent charge (optional).

Before initiating a NiMH charging cycle, the device checks the battery status. If backup battery voltage (VBUB) is above $1.34V \times \text{cell number}$ (Set by I2C bit BUB_CELL, Register 05H: CHGR_SET2), the device consider backup battery as fully charged. The device does not start charging and I2C CHG_DONE bit (Register 08H: CHGR_STATUS) sets 1 to indicate that the charging cycle is done.

If the initial backup battery voltage is below $1.34V \times \text{cell number}$, TPS61382Q1 enters continuous charge phase. The backup battery is charged with constant current controlled by a pre-set timer. Charging current and the duration for continuous charging phase is be programmed by I2C interface (Register 04H to 05H: BUB_CC, BUB_NIMH_TIMER). After timer is done and the continuous charge phase finishes, TPS61382Q1 sets I2C bit CHG_DONE bit (Register 08H: CHGR_STATUS) to 1 to indicate the charging cycle is done.

If the re-charge function is disabled (Set by I2C bit BUB_TER, Register 06H: CHGR_SET3), the IC stops charging after continuous charging phase is finished. Restart charging by toggling the $\overline{\text{EN_CHGR}}$ pin or I2C CHGR_EN bit, this clears the CHGR_MODE_DONE bit and restart the continuous charge phase.




Figure 6-11. NiMH Battery Charging Profile, Re-charge Disabled

If the re-charge is enabled (Set by I2C bit BUB_TER, Register 06H: CHGR_SET3), the device enters intermittent charging phase after continuous charging phase is finished. In this phase, the IC replenishes the natural self-discharge of NiMH by charging the battery intermittently with pulse charge cycle (2s on and 58s off).




Figure 6-12. NiMH Battery Charging Profile , Re-charge Enabled

TPS61382Q1 monitors the battery voltage during all charging phases, if the battery voltage is above $1.70V \times \text{cell number}$, the device stops charging and set I2C bit BUB_OVP (Register 0CH: FAULT_CONDITION) to 1 to indicate a overvoltage protection.

6.4.1.4 Lithium Battery Charging Profile

In Lithium charging mode, TPS61382Q1 charges batteries with a voltage-controlled charging profile consisting of four phases: trickle charge, pre-charge, CC charge and CV charge.

When the backup battery voltage is below V_{BUB_SHORT} threshold, the device enters trickle charge phase. In this phase, the device charges the battery by 12.5mA LDO mode to protect the safety of Lithium battery.

When the battery voltage is charged to V_{BUB_SHORT} threshold but still below V_{BUB_LOWV} threshold, the device enters pre-charge phase. In this phase, the device charges the battery with 20% of the CC current set in I2C BUB_CC bits (Register 05H: CHGR_SET2). Lithium battery within this voltage range is considered as normal but low battery, so charging current is limited at 20% of CC current to protect battery life.

If the battery voltage does not reach V_{BUB_LOWV} threshold within 30 minutes. The battery is considered damaged and internal short-circuit. The IC terminates charging and I2C bit BUB_SHORT (Register 0CH: FAULT_CONDITION) is set to 1 to indicate a battery short situation.

After battery voltage reaches V_{BUB_LOWV} threshold, the device enters CC charge phase. In this phase, the device charges the battery by CC current (Set by I2C Register 05H: CHGR_SET2, BUB_CC bits).

After battery is charged to its target voltage (Set by I2C bits BUB_CV), TPS61382Q1 enters CV charge phase. The device decrease charging current to regulate battery voltage until the charging current drops below termination threshold I_{TERM} (Set by Register 06H: CHGR_SET3, CHG_TEM_CURRENT bit), then the device terminate charging.

If configured as recharge disabled (By I2C bits BUB_TER), the device does not re-charge after terminated unless the EN_CHGR pin or CHGR_EN bit is toggled.




Figure 6-13. Lithium-Based Battery Charging Profile, Re-Charge Disabled

If configured as recharge enabled, the device pause charging temporary and automatically re-charge when BUB voltage drops below V_{RECHG} threshold.




Figure 6-14. Lithium-based Battery Charging Profile, Re-Charge Enabled

6.4.1.5 Super Capacitor Charging Profile

In super capacitor charging mode, TPS61382Q1 charges batteries with a voltage-controlled charging profile consisting of two phases: CC Charge, CV Charge.

When the backup super capacitor voltage is below target voltage (Set by I2C bits BUB_CV), the device enters CC charge phase. In this phase, the device charges the super capacitor by CC current configured by BUB_CC bits. Note that buck operation range is limited by minimum duty, so the IC works in 100mA LDO mode when BUB voltage is below 1V.

After super capacitor is charged to its target voltage, TPS61382Q1 enters CV charge phase. The device decrease charging current to regulate the super capacitor voltage until the current drops below a pre-set threshold, then the device terminates charging.

If configured as recharge disabled (By I2C bits BUB_TER), the device does not re-charge after terminated unless the EN_CHGR pin or CHGR_EN bit is toggled.




Figure 6-15. Super Capacitor Charging Profile, Re-Charge Disabled

If configured as recharge enabled, the device pauses charging temporary and automatically re-charges when BUB voltage drops below V_{RECHG} threshold.




Figure 6-16. Super Capacitor Charging Profile, Re-Charge Enabled

6.4.1.6 Battery Cold, Hot Temperature (TS Pin)

TPS61382Q1 supports battery low, high temperature monitoring function by sensing the voltage on TS pin. The negative temperature coefficient (NTC) thermistor in battery is connected within a resistor network (Shown in Figure 6-17). TS pin sources 38uA into the resistor network and generate voltage on TS pin during charger and SOH mode. Battery charging is allowed only when the TS pin voltage stays between V_{COLD} and V_{HOT} thresholds (188mV~1.04V). If the battery temperature exceeds normal range and TS pin voltage goes beyond the thresholds, the device stops charging and set the TS_FAULT bit to 1 (Register 0CH: FAULT_CONDITION). Once battery temperature returns to normal range and TS pin voltage returns between threshold, charging operation resumes automatically.

The temperature window is modified by the resistance of the resistor network:

$$R_p = \frac{-1.23(R_{HT} - R_{LT}) + \sqrt{0.73(R_{LT} - R_{HT})(R_{LT} - R_{HT} + 24156)}}{7.6 \times 10^{-5} \cdot (R_{LT} - R_{HT}) - 1.704} \quad (2)$$

$$R_s = \frac{1.23(R_{LT} - R_{HT}) + \sqrt{0.73(R_{LT} - R_{HT})(R_{LT} - R_{HT} + 24156)}}{1.704} - 1.22R_{LT} + 0.22R_{HT} \quad (3)$$

Where R_{HT} & R_{LT} are the NTC resistance under your highest & lowest temperature




Figure 6-17. TS Resistor Network for Modified Temperature Window

Taking 103AT-2 as an example, the recommended resistor values for different temperature charging windows are given below:

Table 6-5. Recommended Resistor Values for Different Temperature Charging Windows

TEMPERATURE CHARGING WINDOW	R_s	R_p
0°C to 60°C	2.1kΩ	488kΩ
-10°C to 60°C	2.5kΩ	70kΩ
-10°C to 50°C	1.3kΩ	74kΩ

If temperature sensing is not required in the application, connect a fixed 10kΩ resistor from TS to GND to disable temperature sensing and protection.

6.4.1.7 Charger Protection and Fault Condition Indication

TPS61382Q1 applies multiple fault protection function to protect battery life and safety during charging operation. Fault conditions of the charger operation is monitored through I2C register (Register 0CH: FAULT_CONDITION). When these fault condition occurs, the device pauses charging operation and set the corresponding I2C register bit high to indicate the fault condition.

Fault Item	Description	Fault Indication	Device Behavior
CHGR_RVS	- Charger reverse current protection. - Triggered when $V_{OUT} < V_{BUB} + 100\text{mV}$.	No Flag	- Pause charging - Pause charger timer. - Recover automatically when fault condition is removed
SYSTEM_OVP	- System overvoltage protection fault. - Triggered when $V_{OUT} > 23\text{V}$.	Indicated by Register 0CH: FAULT_CONDITION, SYSTEM_OVP bit	
TS_FAULT	- Battery out of cold/hot temperature range - Triggered when TS pin voltage $> 1.04\text{V}$ or $< 188\text{mV}$	Indicated by Register 0CH: FAULT_CONDITION, TS_FAULT bit	
BUB_SHORT	- Battery short-circuit fault for Li-ion/LiFePO4 battery - Triggered when BUB voltage is still $< V_{BUB_LOWV}$ after 30 minutes charging - Only available for Li-ion and Li-FePO4 battery	Indicated by Register 0CH: FAULT_CONDITION, BUB_SHORT bit	- Stop charging. - Does not recover automatically - Toggle EN_CHGR pin or CHGR_EN bit to reset fault status
BUB_OVP	- Battery overvoltage fault - NiMH battery: Triggered when BUB voltage $> 1.7\text{V}$ per cell - Other battery type: Triggered when BUB voltage is 4% over target voltage	Indicated by Register 0CH: FAULT_CONDITION, BUB_OVP bit	
TIMER_FAULT	- Charger safety timer fault for Li-ion and Li-FePO4 - Triggered when charging time out of safety timer range	Indicated by Register 0CH: FAULT_CONDITION, TIMER_FAULT bit	
THRM_SD	- Thermal shutdown - Triggered when junction temperature $> 175^{\circ}\text{C}$	Indicated by Register 0CH: FAULT_CONDITION, THRM_SD bit	- Pause charging. - Reset charger timer - Recover automatically when fault condition is removed

6.4.2 Boost Mode Description

The TPS61382Q1 integrates synchronous boost converter with load disconnect function. The boost function supports input voltage from 0.5V to 3.8V and output voltage up to 12V with 5-15A programmable average input current limit. The boost function operates with fixed 400kHz switching frequency with optional spread spectrum to achieve EMI performance for automotive applications.

6.4.2.1 Enable and Start up

TPS61382Q1 enable its boost function when EN_BST pin is high and I2C BST_EN bit is also 1. After boost function is enabled, the TPS61382Q1 keeps monitoring VOUT voltage and enters boost mode when VOUT drops below wake up voltage threshold.

When entering boost mode, TPS61382Q1 checks its BUB pin voltage for undervoltage lockout (UVLO) function. If $V_{out} > 2.8V$, the UVLO threshold is 1V. If $V_{out} < 2.8V$, the UVLO threshold is 3V. The IC starts boosting only when BUB voltage is over UVLO threshold.

TPS61382Q1 applies 30us start-up time so that its boost mode starts up quickly when power interruption of 12V main battery system is detected. So the boost start up current reaches up to its input current limit (default 15A). Set I2C current limit to 5A before enable boost if the system requires smaller start up current and slower start up.

6.4.2.1.1 Automatic Transition into Boost Mode

For back-up power application, when boost operation is enabled, TPS61382Q1 detects system voltage with VOUT pin (Connected to your system power rail) and automatically transition into boost mode when a power interruption of the system is detected. Taking automatic boost and standby mode as an example, the device works in standby mode when Vout is normal. When the power failure occurs and Vout drops below than $\min\{V_{BST_WAKEUP}(\text{Set by I2C bits } BST_WAKE), V_{BST_STANDBY} (BST_VOUT \times 106\%)\}$, the device enters boost mode to maintain the output voltage.

When the 12V main battery recovers and Vout rises higher than $V_{BST_STANDBY}$, the device enter standby mode.

The V_{BST_WAKEUP} is configured to $BST_VOUT \times 103\%$ ($BST_WAKE = 111b$) by default to achieve smaller voltage drop during transition into boost mode. But TPS61382Q1 also allows configuring V_{BST_WAKEUP} lower than boost output voltage to avoid entering boost mode at temporary voltage drop like cold crank conditions. Choose higher V_{BST_WAKEUP} for smaller voltage drop or choose lower V_{BST_WAKEUP} to avoid entering boost mode at cold crank condition and improve back up battery life.




Figure 6-18. Case1: $V_{BST_WAKEUP} > BST_VOUT$




Figure 6-19. Case2: $V_{BST_WAKEUP} < BST_VOUT$

6.4.2.1.2 Manual Transition into Boost Mode

TPS61382Q1 also supports manual transition into boost mode by controlling external EN pins. Manual transition by EN pins allows user to shutdown the IC when 12V battery voltage is normal and saves quiescent current. But external voltage detection circuit and MCU are required to control EN pins.

The device requires $50\mu\text{s}$ ($t_{\text{EN_delay1}}$) delay time to initialize its internal circuit from shutdown mode. After initialized, the device takes approximately $20\mu\text{s}$ ($t_{\text{EN_delay2}}$) delay time from standby mode to boost mode.

For backup power applications, TI suggests setting up two threshold to enable our device. Use the $V_{\text{Pre-ENABLE}}$ threshold to control EN_CHGR pin and initialize the device in advance. And use the $V_{\text{BST_EN}}$ threshold to control EN_BST pin. This EN sequence reduces the delay time entering boost mode (Only $t_{\text{EN_delay2}}$).




Figure 6-20. Manual Transition into Boost Mode

6.4.2.2 Down Mode

The TPS61382Q1 enters down mode when BUB voltage is higher than output voltage during boost mode. During downmode TPS61382Q1 high-side and low-side FETs works the same way as in boost operation, while the isolation FET Q₃ is regulated in saturation region during high side on phase. This downmode operation allows the device to regulate its output voltage at target value even when $V_{BUB} > V_{OUT}$.

With its Q₃ operates in saturation region, downmode generates a lot of loss and heat compared to normal boost operation. Therefore current limit threshold is reduced in downmode to avoid overheating. When BUB-VOUT is over 8V, the peak inductor current is limited to 2.33A. When BUB-VOUT is between 4-8V, the peak current limit is 2.95A. When BUB-VOUT is between 0-4V, the peak current limit is 4.41A. Also, because of the high loss and low efficiency, this mode is only for start up and output short protection. Avoid $V_{BUB} > V_{OUT}$ condition during normal operation.

6.4.2.3 Output Short- to-Ground Protection

TPS61382Q1 applies optional output short protection to protect the IC from damage during output short-circuit condition. The short circuit protection is disabled by default and is enabled by I2C BST_SCP bits. If the output short occurred and the output voltage is pulled below the BUB voltage, the device enters short circuit protection operation in which downmode is applied to control inductor current.

For system safety, TI recommends enabling short circuit protection function.

TPS61382Q1 applies hiccup control for short circuit protection to avoid overheating in downmode, the device keeps switching for 2ms, stopping for 65ms and repeats this cycle to reduce the average current and power consumption.

6.4.2.4 Boost Control Loop

TPS61382Q1 applies fix-frequency peak current control scheme, the internal oscillator supports 400kHz switching frequency.

The TPS61382Q1 operates with fixed-frequency pulse width modulation (PWM) from medium to heavy load. At the beginning of each switching cycle, the low-side N-MOSFET switch is turned on. The inductor current ramps up to a peak current that is determined by the output of the internal error amplifier (V_{EA}). Once the switching peak current triggers the output of the EA, the low-side N-MOSFET is turned off and the high-side N-MOSFET is turned on after a short dead time. The high-side N-MOSFET switch is not turned off until the next cycle as determined by the internal oscillator. The low-side switch turns on again after a short dead time and the switching cycle is repeated.

6.4.2.5 Current Limit Operation

TPS61382Q1 implements both peak current and average inductor current limit function to protect the device from overload and back up battery from over-discharging. The average current limit is programmed by I2C BST_ILIM bits.

Besides the average current limit, peak current limit protection is applied to protect the device against overcurrent conditions. In boost operation, the peak current limit threshold is determined by average current limit. With the average current limit set to 5A or 10A, the peak current is limited to 15A, otherwise the peak current is limited to 30A. The peak current limit is enabled or disabled by I2C BST_ILIM_EN bit. In downmode operation, the peak current limit is reduced depending on VOUT and BUB voltage to avoid IC overheating.

6.4.2.6 Functional Modes at Light Load

In light load condition, the TPS61382Q1 works in either auto PFM or forced PWM (FPWM) mode to meet different application requirements. Auto PFM mode decreases switching frequency under light load. This strategy reduces switching loss and improves higher efficiency at light load condition. FPWM mode force the converter to keep switching with fixed frequency under light load. FPWM improves EMI performance and reduces output ripple, but sacrifices light load efficiency compared to PFM mode.

TPS61382Q1 is configured to auto PFM mode by default. Write I2C BST_PFM bit (Register 01H, BOOST_SET1) as 1 to switch to FPWM mode.

Care needs to be taken for backup power applications, FPWM allows reverse current into backup battery when VOUT is higher than boost output target. Reverse current into BUB is usually not favorable for the back up battery. So TI recommend PFM mode during transition into boost mode.

6.4.2.6.1 Auto PFM Mode

The TPS61382Q1 applies auto PFM operation to improve efficiency at light load. Auto PFM mode is applied by enabling the PFM function in the internal register. When the TPS61382Q1 operates at light load condition, the output of the internal error amplifier decreases to make the inductor peak current down and deliver less power to the load. When the inductor current decreases to I_{CLAMP_LOW} (peak current approximately 4A), the output voltage of the error amplifier is clamped by the internal circuit and does not further reduce. If the load current reduces further, the inductor current is clamped and V_{OUT} increases. When the output voltage hits the PFM reference voltage (101.5% V_{out_target}), the device pauses switching. The load is supplied by the output capacitor, and the output voltage declines. When the output voltage falls below 100.5% V_{out_target} , the device starts switching again to ramp up the output voltage.




Figure 6-21. PFM Operation

6.4.2.6.2 Forced PWM Mode

TPS61382Q1 applies force PWM (FPWM) operation to reduce output ripple and improve EMI performance. In the FPWM mode, the TPS61382Q1 keeps the switching frequency constant in light load condition. When the load current decreases, the output of the internal error amplifier decreases as well to keep the inductor current down and deliver less power from input to output. When the output current further reduces, the current through the inductor decreases to zero during the off-time. The high-side MOSFET is not turned off even if the current through the MOSFET is zero. Thus, the inductor current changes its direction after it runs to zero. The power flow is from output side to input side. The efficiency is low in this mode. But with the fixed switching frequency, there is no audible noise and other problems caused by low switching frequency in light load condition.




Figure 6-22. FPWM Operation

6.4.2.7 Duty Cycle Limitation

TPS61382Q1 triggers maximum duty cycle limitation when the low-side MOS off time reaches its minimum limit (100ns typical). When V_{BUB} is too low and the max duty cycle is met, the device clamps its duty and output voltage goes out of regulation. TPS61382Q1 also triggers minimum duty cycle limitation when the low-side MOS on time reaches its minimum limit (120ns typical). So the available V_{BUB} range is limited by:

$$V_{BUB} < (1 - D_{min})V_{OUT} \quad (4)$$

$$V_{BUB} > t_{OFFmin}V_{OUT}f_{sw} \quad (5)$$

6.4.2.8 BUB Voltage Loop

The TPS61382Q1 applies BUB voltage loop to protect back up battery with high internal impedance. like batteries at low battery, cold temperature or the end of its life. This function allows the battery to output its maximum power and maintain its voltage over boost UVLO threshold when the battery has high internal resistance that limits its output power. This function is enabled by I2C BST_VINLOOP_EN bits and the input target voltage is programmed by BST_VINLOOP bits.

When the BUB voltage is higher than input target voltage, the BUB voltage loop is not activated. When the BUB voltage is lower than input target voltage, the BUB voltage loop takes over the controlling loop and try decreasing its inductor current to maintain its input voltage. So by allowing the V_{OUT} to drop below V_{OUT_TARGET} , TPS61382Q1 turns to control its input voltage by which the battery matches its output impedance with internal impedance and output its maximum power.

6.4.2.9 Spread Spectrum

TPS61382Q1 implements optional switching frequency dithering for boost function to improve the EMI performance. The device uses a triangle jitter to spread the switching frequency by $\pm 7\%$. The modulation frequency of the spread spectrum is optional programmable by I2C BST_SS bits.

Table 6-6. Spread Spectrum and Optional Modulation Frequency

BST_SS Bits	Spread Spectrum	Modulation Frequency
00	No Spread Spectrum	No Spread Spectrum
01	$\pm 7\%$ Spread Spectrum	6.5kHz
10	$\pm 7\%$ Spread Spectrum	3.2kHz
11	$\pm 7\%$ Spread Spectrum	1.6kHz

6.4.3 Battery State-of-Health (SOH) Detection Mode Description

The battery state-of-health (SOH) detection function allows TPS6138Q1 to detect the internal resistance of the backup battery (BUB). When the EN_CHGR pin is high and CHGR_SOH_EN=10b, the SOH function is enabled. After enabled, the device enters SOH mode when VOUT > wake up voltage.

In SOH mode, the backup battery is discharged by a constant current programmed by I2C SOH_I bits. During the test, the TPS61382Q1 AVI pin outputs the voltage of the backup battery, discharge current or the battery temperature depending on I2C settings. Connect AVI pin to your MCU ADC to acquire and calculate internal resistance.

The ISO FET Q3 is turned on during SOH mode. So TI suggests the output voltage is higher than BUB voltage during SOH operation to avoid inrush current through high side body diode.

6.4.3.1 SOH Mode Operation

During SOH mode, the TPS61382Q1 fully turns on its isolation MOSFET Q3 and regulate the gate voltage of the low-side MOSFET Q2 with LO pin. In this way, low side MOSFET operates in saturation area and discharge the backup battery by constant current. TI recommend 500mA discharge current to achieve best accuracy. By sensing the battery open voltage, voltage with discharge current and discharge current, the battery internal resistance R_{bat} is given by:

$$R_{bat} = \frac{V_{open} - V_{dischg}}{I_{dischg}} \quad (6)$$

where:

- V_{open} is the battery voltage without discharge current
- V_{dischg} is the battery voltage with discharge current
- I_{dischg} is the discharge current

According to the recommendation from battery manufacturer , it is recommended to discharge battery with 500mA I_{dischg} for 500ms and then read V_{dischg}




Figure 6-23. Typical Operation of SOH

6.4.3.2 Multi-Signal Output in AVI Pin

The AVI pin outputs three optional signals depending on I2C settings: battery voltage, battery discharge current and battery temperature. The output item is selected by I2C SOH_AVI_EN bits. So MCU uses one ADC channel to read all signals.

The AVI pin voltage is limited to <3.3V to protect MCU ADC pin. The ratio from measured item to AVI output is selected by I2C AVI_I_RATIO or AVI_V_RATIO bits. TI recommend AVI_I_RATIO = 2 with 500mA discharge current to achieve best accuracy




Figure 6-24. AVI Pin Connection

6.4.3.3 Calculate Impedance of Back up Battery

Steps below gives an example on how to calculate the internal impedance of the backup battery with your system MCU :

- Set SOH discharge current to 0A (Register 0x09: SOH_SET1, SOH_I bits).
- Set AVI pin ratio to the backup battery voltage as 1 (Register 0x0A: SOH_SET2, SOH_V_RATIO bits).
- Set AVI pin ratio to the discharge current as 2 (Register 0x0A: SOH_SET2, SOH_I_RATIO bits).
- Select AVI pin output as battery voltage (Register 0x0A: SOH_SET2, SOH_AVI_EN bits).
- Enable SOH function (Register 0x0B: CONTROL_STATUS, CHGR_SOH_EN bits).
- Wait for approximately 1ms for AVI output voltage to stabilize.
- Read the backup battery voltage at AVI pin with the MCU ADC (V_{BUB1}).
- Set SOH discharge current to 500mA (Register 0x09: SOH_SET1, SOH_I bits).
- Discharge for 500ms (depending on battery characteristic, NiMH usually requires 500ms).
- Read the backup battery voltage at AVI pin with the MCU ADC (V_{BUB2}).
- Select AVI pin output as discharge current (Register 0x0A: SOH_SET2, SOH_AVI_EN bits).
- Wait for approximately 1ms for AVI output voltage to stabilize.
- Read the discharge current at AVI pin with the MCU ADC (I_{BUB2}).

MCU uses the below equation to calculate the internal impedance of the back-up battery and detect the battery state of health.

$$R_{BUB} = (V_{BUB1} - V_{BUB2}) / I_{BUB} \quad (7)$$

6.5 I²C Serial Interface

I²C is a 2-wire serial interface developed by Philips Semiconductor, now NXP Semiconductors (see [NXP Semiconductors, UM10204 – I²C-Bus Specification and User Manual](#)). The bus consists of a data line (SDA) and a clock line (SCL) with pullup structures. When the bus is idle, both SDA and SCL lines are pulled high. All the I²C-compatible devices connect to the I²C bus through open-drain I/O pins, SDA, and SCL. A controller device, usually a microcontroller or a digital signal processor, controls the bus. The controller is responsible for generating the SCL signal and device addresses. The controller also generates specific conditions that indicate the START and STOP of data transfer. A target device receives and transmits data on the bus under control of the controller device.

The device works as a target and supports the following data transfer modes, as defined in the I²C-Bus Specification:

- Standard-mode (100 kbps)
- Fast-mode (400 kbps)
- Fast-mode Plus (1 Mbps)


The interface adds flexibility to the power supply solution, enabling most functions to be programmed to new values, depending on the instantaneous application requirements.

The data transfer protocol for standard and fast modes is exactly the same, therefore, it is referred to as F/S-mode in this document. The device supports only 7-bit addressing; 10-bit addressing and general call address are not supported. The device 7-bit address is 31h (0110001b).

To make sure that the I²C function in the device is correctly reset, it is recommended that the I²C controller initiates a STOP condition on the I²C bus after the initial power up of SDA and SCL pullup voltages.

6.5.1 Data Validity

During all transmissions, the controller checks that data is valid. A valid data condition requires the SDA line to be stable during the entire high period of the clock pulse. The high level or low level state of the data line only changes when the clock signal on the SCL line is low level. One clock pulse is generated for each data bit transferred.

**Figure 6-25. I²C Data Validity**

6.5.2 START and STOP Conditions

All transactions begin with a START (S) and is terminated by a STOP (P). A high level to low level transition on the SDA line while SCL is at high level defines a START condition. A low level to high level transition on the SDA line when the SCL is at high level defines a STOP condition.

START and STOP conditions are always generated by the controller. The bus is considered busy after the START condition, and free after the STOP condition.




Figure 6-26. I²C START and STOP Conditions

6.5.3 Byte Format

Every byte on the SDA line needs to be eight bits long. The number of bytes to be transmitted per transfer is unrestricted. Each byte has to be followed by an acknowledge bit. Data is transferred with the most significant bit (MSB) first. If a target doesn't receive or transmit another complete byte of data until it has performed some other function, it holds the clock line SCL low to force the controller into a wait state (clock stretching). Data transfer then continues when the target is ready for another byte of data and release the clock line SCL.




Figure 6-27. Byte Format

6.5.4 Acknowledge (ACK) and Not Acknowledge (NACK)

The acknowledge takes place after every byte. The acknowledge bit allows the receiver to signal the transmitter that the byte was successfully received and another byte may be sent. All clock pulses, including the acknowledge 9th clock pulse, are generated by the controller.

The transmitter releases the SDA line during the acknowledge clock pulse so the receiver pulls the SDA line to low level and it remains stable low level during the high level period of this clock pulse.

The Not Acknowledge signal is when SDA remains high level during the 9th clock pulse. The controller then generate either a STOP to abort the transfer or a repeated START to start a new transfer.

6.5.5 Target Address and Data Direction Bit

After the START, a target address is sent. This address is seven bits long followed by the eighth bit as a data direction bit (bit R/W). A zero indicates a transmission (WRITE) and a one indicates a request for data (READ).




Figure 6-28. Target Address and Data Direction

6.5.6 Single Read and Write

Figure 6-29 and Figure 6-30 show the single-byte write and single-byte read format of the I²C communication.



Figure 6-29. Single-byte Write




Figure 6-30. Single-byte Read

If the register address is not defined, the device sends back NACK and goes back to the idle state.

6.5.7 Multi-Read and Multi-Write

The TPS61382Q1 supports multi-read and multi-write.




Figure 6-31. Multi-byte Write




Figure 6-32. Multi-byte Read

7 Register Maps

Table 7-1 lists the memory-mapped registers for the device registers. All register offset addresses not listed in Table 7-1 is considered as reserved locations, and do not modify the register contents.

Table 7-1. Device Registers

Address	Register Name	Type	Description	Section
00H	CHIP_ID	R	DIE_TYPE provides information on the chip and silicon revision	
01H	BOOST_SET1	R/W	Boost set1: frequency, PFM or FPWM, spread spectrum, short protection, output discharge	
02H	BOOST_SET2	R/W	Boost set2: Vout, current limit	
03H	BOOST_SET3	R/W	Boost set2: BUB voltage loop, boost wake up threshold.	
04H	CHGR_SET1	R/W	Charger set1: battery type, CV voltage, NiMH timer.	
05H	CHGR_SET2	R/W	Charger set2: cell number, CC current	
06H	CHGR_SET3	R/W	Charger set3: termination current	
07H	CHGR_SET4	R/W	Charger set4: safety timer	
08H	CHGR_STATUS	R	Charger status: pre-charge, CC phase, CV phase, charge done,	
09H	SOH_SET1	R/W	SOH set1: discharge current	
0AH	SOH_SET2	R/W	SOH set2: AVI pin to current ratio, AVI pin to voltage ratio, AVI output selection.	
0BH	CONTROL_STATUS	R/W or R	Control status: Boost enable, charger or SOH enable, boost active, charger active, SOH active, standby active.	
0CH	FAULT_CONDITION	R	Fault flag: Vout OVP, battery is OVP, thermal shutdown signal, short, out of safety time and out of temperature and device thermal shutdown	
0DH	STATUS_PIN_SET	R/W	STATUS pin output selection: including boost, charger done and thermal shutdown	
0EH	SW_RST	W	Software reset: resets the entire part to its original default conditions	

7.1 Register 00H: CHIP_ID

Figure 7-1. CHIP_ID

7	6	5	4	3	2	1	0
CHIP_ID							
R-00110000b							

Table 7-2. CHIP_ID Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:0]	CHIP_ID	R	0x30	Provides information on the chip and silicon version.

7.2 Register 01H: BOOST_SET1

Figure 7-2. BOOST_SET1

7	6	5	4	3	2	1	0
Reserved	BST_PFM	BST_SS		BST_SCP	Reserved		
R/W-0b	R/W-0b	R/W-01b		R/W-0b	R-000b		

Table 7-3. BOOST_SET1 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	Reserved	R	0	Reserved
[6]	BST_PFM	R/W	0	0 = PFM, auto PFM at light load 1 = FPWM, force PWM at light load TI recommend PFM for bi-directional application.
[5:4]	BST_SS	R/W	01b	Boost mode spread spectrum 00b = no spread spectrum 01b = 6.5kHz modulation frequency 10b = 3.2kHz modulation frequency 11b = 1.6kHz modulation frequency
[3]	BST_SCP	R/W	0	0 = Boost output short circuit protection disabled 1 = Boost output short circuit protection enabled TI recommend enabling short circuit protection for system safety.
[2:0]	Reserved	R	000b	Reserved

7.3 Register 02H: BOOST_SET2

Figure 7-3. BOOST_SET2

7	6	5	4	3	2	1	0
BST_VOUT				Reserved	BST_ILIM		BST_ILIM_EN
R/W-1100b				R-0b	R/W-10b		R/W-1b

Table 7-4. BOOST_SET2 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:4]	BST_VOUT	R/W	1100b	Set output target voltage 0000b=5V 0001b=5.5V 0010b=6V 0011b=6.2V 0100b=6.5V 0101b=6.8V 0110b=7.1V 0111b=7.5V 1000b=8V 1001b=8.5V 1010b=9V 1011b=9.5V 1100b=10V 1101b=10.5V 1110b=11V 1111b=12V
[3]	Reserved	R	0	Reserved
[2:1]	BST_ILIM	R/W	10b	Boost average current limit 00b=5A 01b=10A 10b=15A
[0]	BST_ILIM_EN	R/W	1	0=disable boost peak current limit 1=enable boost peak current limit If average current=5A or 10A, the peak current limit is 15A; otherwise the peak current limit is 30A.

7.4 Register 03H: BOOST_SET3

Figure 7-4. BOOST_SET3

7	6	5	4	3	2	1	0
BST_VINLOOP		BST_VINLOOP_EN	BST_WAKE			Reserved	
R/W-10b		R/W-0b	R/W-111b			R-00b	

Figure 7-5. BOOST_SET3 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:6]	BST_VINLOOP	R/W	10b	Set input voltage regulation voltage 00b=1V 01b=1.2V 10b=1.5V 11b=2V
[5]	BST_VINLOOP_EN	R/W	0	0=disable input voltage loop 1=enable input voltage loop
[4:2]	BST_WAKE	R/W	111b	Set boost automatically wake-up threshold, VOUT falling 000b=4.5V 001b=5V 010b=5.5V 011b=6V 100b=6.5V 101b= 7.5V 110b=8V 111b=Vout_target+3%
[1:0]	Reserved	R	00b	Reserved

7.5 Register 04H: CHGR_SET1

Figure 7-6. CHGR_SET1

7	6	5	4	3	2	1	0
BUB_TYP		BUB_CV				BUB_NIMH_TIMER	
R/W-00b		R/W-0000b				R/W-00b	

Figure 7-7. CHGR_SET1 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:6]	BUB_TYP	R/W	00b	Set the back-up battery charging strategy 00b=Li-ion charging profile, precharge+CC+CV 01b=LiFePO4 charging profile, precharge+CC+CV 10b=NiMH charging profile, CC + timer 11b=Super capacitor charging profile, CC+CV
[5:2]	BUB_CV	R/W	0000b	Set CV voltage 0000b=1.7V (Super capacitor) 0001b=2.0V (Super capacitor) 0010b=2.2V (Super capacitor) 0011b=2.4V (Super capacitor) 0100b=2.5V (Super capacitor) 0101b=2.7V (Super capacitor) 0110b=3.0V (Super capacitor) 0111b=3.5V (LiFePO4) 1000b=3.6V (LiFePO4) 1001b=3.7V (LiFePO4) 1010b=3.8V (Li-ion) Note: this register is inactive for NiMH battery.
[1:0]	BUB_NIMH_TIMER	R/W	00b	Set the NiMH battery charging time 00b=4h 01b=8h 10b=16h 11b=32h

7.6 Register 05H: CHGR_SET2

Figure 7-8. CHGR_SET2

7	6	5	4	3	2	1	0
Reserved		BUB_CELL	BUB_CC				
R-00b		R/W-0b	R/W-00000b				

Figure 7-9. CHGR_SET2 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:6]	Reserved	R	00b	Reserved
[5]	BUB_CELL	R/W	0b	The number cell of back-up battery Li-ion supports up to 1s NiMH supports up to 2s Super capacitor supports up to 1s 0b=1 1b=2
[4:0]	BUB_CC	R/W	00000b	Set CC current LDO charger supports 50mA-100mA Buck charger supports 150mA-3A 00000b=50mA 00001b=100mA 00010b=150mA (Only for NiMH battery) 00011b=200mA (Only for NiMH battery) 00100b=250mA (Only for NiMH battery) 00101b=300mA (Only for NiMH battery) 00110b=350mA (Only for NiMH battery) 00111b=400mA (Only for NiMH battery) 01000b=450mA (Only for NiMH battery) 01001b=500mA 01010b=550mA 01011b=600mA 01100b=650mA 01101b=700mA 01110b=750mA 01111b=800mA 10000b=850mA 10001b=900mA 10010b=950mA 10011b=1A 10100b=1.5A 10101b=2A 10110b=2.5A 10111b=3A

7.7 Register 06H: CHGR_SET3

Figure 7-10. CHGR_SET3

7	6	5	4	3	2	1	0
CHGR_TO	Reserved		BUCK_SS		BUB_TER	CHG_TEM_CUR RRENT	Reserved
R/W-0b	R-00b		R/W-01b		R/W-0b	R/W-0b	R-0b

Figure 7-11. CHGR_SET3 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	CHGR_TO	R/W	0	Charger topology 0=LDO charger 1=buck charger
[6:5]	Reserved	R	00b	Reserved
[4:3]	BUCK_SS	R/W	01b	Buck mode spread spectrum 00b = no spread spectrum 01b = 6.5kHz modulation frequency 10b = 3.2kHz modulation frequency 11b = 1.6kHz modulation frequency
[2]	BUB_TER	R/W	0	After fully charged, re-charge or not. For NiMH battery, enable intermittent charging For Li-ion, LiFePO4 or super capacitor battery, start recharge when battery voltage is lower than recharge voltage. 0=disable re-charge 1=enable re-charge
[1]	CHG_TEM_CURRENT	R/W	0	0= 10% * I _{cc} 1=20% * I _{cc} Note: this bit is active for Li-ion, LiFePO4 and super capacitor.
[0]	Reserved	R	0	Reserved

7.8 Register 07H: CHGR_SET4

Figure 7-12. CHGR_SET4

7	6	5	4	3	2	1	0
SAFT_TIMER_EN	SAFT_TIMER	Reserved					
R/W-1b	R/W-1b	R-00000b					

Figure 7-13. CHGR_SET4 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	SAFT_TIMER_EN	R/W	1	0=disable the safety time of Li-ion charger 1= enable the safety time of Li-ion charger
[6]	SAFT_TIMER	R/W	1	0=5hr 0=10hr
[5:0]	Reserved	R	00000b	Reserved

7.9 Register 08H: CHGR_STATUS

Figure 7-14. CHGR_STATUS

7	6	5	4	3	2	1	0
CHGR_MODE_ PRE	CHGR_MODE_ CC	CHGR_MODE_ CV	CHGR_MODE_ DONE	ALRT_CHGR_ MODE_DO NE	Reserved		
R-0b	R-0b	R-0b	R-0b	R-0b	R-000b		

Figure 7-15. CHGR_STATUS Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	CHGR_MODE_PRE	R	0	Read only that provides information on the charger operation mode 0=Charger is not operating in pre-charge stage 1=Charger is operating in pre-charge stage
[6]	CHGR_MODE_CC	R	0	Read only that provides information on the charger operation mode 0=Charger is not operating in CC stage 1=Charger is operating in CC stage
[5]	CHGR_MODE_CV	R	0	Read only that provides information on the charger operation mode 0=Charger is not operating in CV stage 1=Charger is operating in CV stage
[4]	CHGR_MODE_DONE	R	0	Read only that provides information on the charger operation mode 0= Charge done not triggered. 1= Charge done triggered.
[3]	ALRT_CHGR_MODE_DO NE	R	0	Read only that provides information on the charger operation mode. 0= Charging has not done since the last read 1= Charging has done since the last read Latch after set, clear-on-read
[2:0]	Reserved	R	000b	Reserved

7.10 Register 09H: SOH_SET1

Figure 7-16. SOH_SET1

7	6	5	4	3	2	1	0
SOH_I			Reserved				
R/W-000b			R-00000b				

Figure 7-17. SOH_SET1 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:5]	SOH_I	R/W	000b	Set SOH discharge current 000b=0A 001b=100mA (Recommend AVI_I_RATIO=2) 010b=200mA (Recommend AVI_I_RATIO=2) 011b=300mA (Recommend AVI_I_RATIO=2) 100b=500mA (Recommend AVI_I_RATIO=2) 101b=800mA (Recommend AVI_I_RATIO=2) 110b=1A (Recommend AVI_I_RATIO=2) 111b=1.5A (Recommend AVI_I_RATIO=1)
[4:0]	Reserved	R	00000b	Reserved

7.11 Register 0AH: SOH_SET2

Figure 7-18. SOH_SET2

7	6	5	4	3	2	1	0
AVI_I_RATIO		AVI_V_RATIO		Reserved		SOH_AVI_EN	
R/W-01b		R/W-10b		R-00b		R/W-00b	

Figure 7-19. SOH_SET2 Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:6]	AVI_I_RATIO	R/W	01b	AVI pin ratio to the discharge current. The voltage of AVI pin = AVI_I_RATIO × discharge current 00b=1/2 01b=1 10b=2
[5:4]	AVI_V_RATIO	R/W	10b	AVI pin ratio to the back-up battery voltage. The voltage of AVI pin = AVI_V_RATIO × back-up battery voltage 00b=1/4 01b=1/2(Recommended for 1S Lithium, 2S NiMH) 10b=1 (Recommended for 1S NiMH, 1S super capacitor)
[3:2]	Reserved	R	00b	Reserved
[1:0]	SOH_AVI_EN	R/W	00b	Enable AVI pin output and choose I, V or T output signal 00b=disable AVI pin output, internal 125kΩ pulldown to AGND. 01b=Enable back-up battery voltage output 10b=Enable discharge current output 11b=Enable battery temperature output

7.12 Register 0BH: CONTROL_STATUS

Figure 7-20. CONTROL_STATUS

7	6	5	4	3	2	1	0
BST_EN	CHGR_SOH_EN		ALRT_BST_ACTIVE	BST_ACTIVE	CHGR_ACTIVE	SOH_ACTIVE	STANDBY_ACTIVE
R/W-1b	R/W-00b		R-0b	R-0b	R-0b	R-0b	R-0b

Figure 7-21. CONTROL_STATUS Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	BST_EN	R/W	1	0= Disable boost function 1= Enable boost function
[6:5]	CHGR_SOH_EN	R/W	00b	00b= Disable charger and SOH function 01b= Enable charger function 10b= Enable SOH function
[4]	ALRT_BST_ACTIVE	R	0	Read only. Provides information about the system operating mode 0= Boost mode has not been activated since the last read 1= Boost mode has been activated since the last read Latch after set, clear-on-read
[3]	BST_ACTIVE	R	0	Read only. Provides information about the system operating mode 0= Boost mode is not active 1= Boost mode is active
[2]	CHGR_ACTIVE	R	0	Read only. Provides information about the system operation mode 0= Charger mode is not active 1= Charger mode is active
[1]	SOH_ACTIVE	R	0	Read only. Provides information about the system operation mode 0= SOH mode is not active 1= SOH mode is active
[0]	STANDBY_ACTIVE	R	0	Read only. Provides information about the system operation mode 0= Standby mode is not active 1= Standby mode is active

7.13 Register 0CH: FAULT_CONDITION

Figure 7-22. FAULT_CONDITION

7	6	5	4	3	2	1	0
SYSTEM_OVP	TS_FAULT	BUB_SHORT	TIMER_FAULT	BUB_OVP	THRM_SD	Reserved	
R-0b	R-0b	R-0b	R-0b	R-0b	R-0b	R-00b	

Figure 7-23. FAULT_CONDITION Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	SYSTEM_OVP	R	0	0=No overvoltage on VOUT pin 1=Overvoltage on VOUT pin
[6]	TS_FAULT	R	0	0= TS pin voltage is within cold/hot temperature threshold 1= TS pin voltage is out of cold/hot temperature threshold
[5]	BUB_SHORT	R	0	0= No short circuit on Li-ion/LiFePO4 battery 1= Short circuit on Li-ion/LiFePO4 battery Note: this bit only active for Li-ion/LiFePO4 battery
[4]	TIMER_FAULT	R	0	0= Within safety time 1= Out of safety time
[3]	BUB_OVP	R	0	0= No overvoltage on battery 1= Overvoltage on battery
[2]	THRM_SD	R	0	0=no thermal shutdown 1= thermal shutdown ($T_j > 175^{\circ}\text{C}$)
[1:0]	Reserved	R	00b	Reserved

7.14 Register 0DH: STATUS_PIN_SET

Figure 7-24. STATUS_PIN_SET

7	6	5	4	3	2	1	0
INC_BST	INC_ABST	INC_ADN	INC_TSD	INC_TSFAULT	STATUS_OR_D RV	DRV_CONTRO L	DRV_OUT
R-1b	R-0b	R-0b	R-0b	R-0b	R/W-0b	R/W-0b	R/W-0b

Figure 7-25. STATUS_PIN_SET Register Field Descriptions

Bit	Field	Type	Reset	Description
[7]	INC_BST	R/W	1	0= BST_ACTIVE status is not included in the STATUS pin output, STATUS pin pulls low when entering boost mode 1= BST_ACTIVE status is included in the STATUS pin output Check Section 7.12 for descriptions of BST_ACTIVE signal
[6]	INC_ABST	R/W	0	0= ALRT_BST_ACTIVE status is not included in the STATUS pin output, STATUS pin pulls low when boost mode is entered since last read 1= ALRT_BST_ACTIVE status is included in the STATUS pin output Check Section 7.12 for descriptions of ALRT_BST_ACTIVE signal
[5]	INC_ADN	R/W	0	0= ALRT_CHGR_MODE_DONE status is not included in the STATUS pin output, STATUS pin pulls low when charger operation is done since last read 1= ALRT_CHGR_MODE_DONE status is included in the STATUS pin output Check Section 7.9 for descriptions of ALRT_CHGR_MODE_DONE signal
[4]	INC_TSD	R/W	0	0= THRM_SD status is not included in the STATUS pin output, STATUS pin pulls low when thermal shutdown is triggered 1= THRM_SD status is included in the STATUS pin output Check Section 7.13 for descriptions of THRM_SD signal
[3]	INC_TSFAULT	R/W	0	0= TS_FAULT status is not included in the STATUS pin output, STATUS pin pulls low when TS_FAULT is triggered 1= TS_FAULT status is included in the STATUS pin output Check Section 7.13 for descriptions of TS_FAULT signal
[2]	STATUS_OR_DRV	R/W	0b	Configure function of STATUS pin (Pin 8) 0= STATUS pin operates as status indicator IO 1= STATUS pin operates as external PMOS driver
[1]	DRV_CONTROL	R/W	0b	External PMOS driver logic. Only available when STATUS_OR_DRV bit is 1. 0= Automatic control. The IC turns off external PMOS when entering boost mode. Turns on PMOS when entering charger, SOH or standby mode. 1= Manual control. The external PMOS driver is controlled by I2C DRV_OUT bit. Write DRV_OUT bit to turn on or off the external PMOS
[0]	DRV_OUT	R/W	0b	External PMOS driver manual control. Only available when STATUS_OR_DRV bit and DVR_CONTROL bit is 1. 0= Turn off external PMOS 1= Turn on external PMOS

7.15 Register 0EH: SW_RST

SW_RST (software reset) is a write-only register/command that resets the entire part to its original default conditions at the end of the I2C SW_RST transaction (that is, the data-byte ACK). Execution only occurs if DIN[7:0]=0x00. The effect of a SW_RST is identical to power-cycling the part.

TPS61382Q1 also support hardware reset, when the two EN pins are both low(EN_BST=0 AND EN_CHGR=0), the entire registers are reset to its original default conditions.

Figure 7-26. SW_RST

7	6	5	4	3	2	1	0
CHIP_ID							
W-00000000b							

Table 7-5. SW_RST Register Field Descriptions

Bit	Field	Type	Reset	Description
[7:0]	SW_RST	W	00000000b	Resets the entire part to its original default conditions

8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

TPS61382Q1 is a bi-directional boost converter with CC/CV charger and battery health detection function. The device provides integrated power structure in back-up power system, like T-box and e-call applications. The following design procedure is used to design TBOX system with TPS61382Q1.

8.2 Typical Application

Figure 8-1 shows a typical application circuit for the TPS61382Q1. This device is designed to charge BUB when VBAT is normal and boost BUB energy to Vsystem when VBAT is disconnected.




Figure 8-1. Typical TBOX Application

8.2.1 Design Requirements

The following table provides the parameters for our detailed design procedure example:

Table 8-1. Design Requirements

PARAMETERS	VALUES
Car Battery Input Voltage:	Typical: 6~18V, load damp: up to 40V
Back-up Battery	1s LiFePO4
Back-up Battery Voltage:	2.5 ~ 3.6V
Charging Current:	1A
Charging Voltage	3.6V
Battery Health Detection Current:	500mA
Boost Output Voltage:	10V
Boost Output Current:	2A
Mode Selection	Automatic Charger and Boost Mode
Voltage Drop during Mode Transient	<=200mV

8.2.2 Detailed Design Procedure

8.2.2.1 Selecting the External MOSFET

TPS61382Q1 requires an external MOSFET (Q1) as its boost low side switch and SOH discharge switch. The external MOSFET is selected depending on its thermal performance, V_{DS} voltage and I_d current.

- TPS61382Q1 supports only n-channel MOSFET as Q1.
- Recommend $Q_{gd} < 5nC$. Q_{gd} does not exceed 10nC at most.
- Recommend $V_{plateau}$ 2-3V. Do not exceed 3.5V at most.
- R_{dson} low as possible. Recommend R_{dson} less than 15mohm at most
- The drain-source breakdown voltage, $V_{(BR)DSS} \geq 30V$
- The continuous drain current is larger than the maximum peak current in the boost mode:

$$I_{peak} = \frac{I_{OUT}}{(1-D) \cdot eff} + \frac{V_{BUB} \cdot D}{2L \cdot f_{sw}} \quad (8)$$

where

- I_{OUT} is the maximum load current in boost mode.
- D is the duty cycle of boost operation
- eff is the boost mode efficiency
- L is the boost inductance
- f_{sw} is the switching frequency in boost mode
- V_{BUB} is the input voltage on BUB pin

8.2.2.2 Inductor Selection

A boost converter normally requires two main passive components for storing energy during power conversion: an inductor and an output capacitor. The inductor affects the steady state efficiency (including the ripple and efficiency), transient behavior, and loop stability, which makes the inductor the most critical component in application.

When selecting the inductor and the inductance, the other important parameters are:

- The maximum current rating (RMS and peak current needs to be considered)
- The series resistance
- Operating temperature

The TPS61382Q1 has built-in slope compensation to avoid subharmonic oscillation associated with current mode control. If the inductor value is too low and makes the inductor peak-to-peak ripple higher than 7A, the slew rate of its slope compensation is not adequate, and the loop is unstable. Therefore, it is recommended to make the peak-to-peak current ripple between 2A to 5A when selecting the inductor.

The inductance is calculated by:

$$L = \frac{V_{BUB} \left(1 - \frac{V_{BUB} \cdot \text{eff}}{V_{OUT}} \right)}{\Delta I_L \cdot f_{sw}} \quad (9)$$

So, TI suggests 2.2μH for 400kHz switching frequency.

The current flowing through the inductor is the inductor ripple current plus the average input current. During power up, load faults, or transient load conditions, the inductor current increases above the peak inductor current calculated.

Inductor values has ±20%, or even ±30% tolerance with no current bias. When the inductor current approaches the saturation level, the inductance decreases 20% to 35% from the value at 0A bias current, depending on how the inductor vendor defines saturation. When selecting an inductor, make sure the rated current, especially the saturation current, is larger than its peak current during the operation.

The inductor peak current varies as a function of the load, switching frequency, and input and output voltages. The peak current is calculated by:

$$I_{peak} = \frac{I_{OUT}}{(1-D) \cdot \text{eff}} + \frac{V_{BUB} \cdot D}{2L \cdot f_{sw}} \quad (10)$$

Select the inductor with a saturation current rating higher than the maximum inductor current.

where

- I_{peak} is the peak current of the inductor
- I_{OUT} is the output current
- D is the duty cycle
- eff is the efficiency
- V_{BUB} is the input voltage
- L is the inductance
- f_{sw} is the switching frequency

The heat rating current (RMS) is calculated with:

$$I_{LRMS} = \sqrt{(I_{BUB}^2 + \Delta I_L^2) / 12} \quad (11)$$

where

- I_{LRMS} is the RMS current of the inductor
- I_{BUB} is the input current of the inductor
- ΔI_L is the ripple current of the inductor

It is important that the peak current does not exceed the inductor saturation current and the RMS current is not over the temperature-related rating current of the inductors.

For a given physical inductor size, increasing inductance usually results in an inductor with lower saturation current. The total losses of the coil consists of the DC resistance (DCR) loss and the following frequency-dependent loss:

- The losses in the core material (magnetic hysteresis loss, especially at high switching frequencies)
- Additional losses in the conductor from the skin effect (current displacement at high frequencies)
- Magnetic field losses of the neighboring windings (proximity effect)

For a certain inductor, the larger current ripple (smaller inductor) generates the higher DC and also the frequency-dependent loss. An inductor with lower DCR is basically recommended for higher efficiency. However, it is usually a tradeoff between the loss and foot print. [Table 8-2](#) lists some recommended inductors. In this application example, the Coilcraft inductor XGL6060-222 is selected for its small size, high saturation current, and small DCR.

Table 8-2. Recommended Inductors for the TPS61382Q1

PART NUMBER	L (μH)	DCR TYPICAL(mΩ)	SATURATION CURRENT (A)	HEAT RATING CURRENT (A)	SIZE (L × W × H)	VENDOR ⁽¹⁾
XGL6060-222MED	2.2	4.3	12.1 (20% Drop)	20.7 (ΔT 40K)	6.51 × 6.71 × 6.1	Coilcraft
XGL1060-222MED	2.2	3.8	21.5 (20% Drop)	25.3 (ΔT 40K)	10.0 × 11.3 × 6.0	Coilcraft
IHLP-4040DZ-ER2R2	2.2	8.2	25.6 (20% Drop)	12.0 (ΔT 40K)	10.16 × 10.195 × 4.0	Vishay
IHLP-6767DZ-ER2R2	2.2	4.57	17.5 (20% Drop)	26 (ΔT 40K)	17.15 × 11.94 × 4.0	Vishay
B82464D6222M000	2.2	9	11.8 (10% Drop) 13.85 (30% Drop)	6 (ΔT 40K)	10.4 × 10.4 × 6.3	TDK
7843340220	2.2	10	14.7 (30% Drop)	8.4 (ΔT 50K)	8.1 × 8.1 × 9.0	Würth Elektronik
784373680022	2.2	7.8	25.7 (30% Drop)	13.6 (ΔT 50K)	10 × 10.85 × 3.8	Würth Elektronik

(1) See the [Third-Party Products](#) disclaimer

8.2.2.3 Capacitor in Back-Up Battery Side

The capacitance in the back-up battery side-affects BUB loop stability. Select the effective capacitance between 5μF to 10μF if BUB loop functions needs to be applied. If BUB loop function is not required, then the capacitance in BUB side does not have upper limit.

Care needs to be taken when evaluating effective capacitance of a ceramic capacitor. For ceramic capacitors, the derating under dc bias voltage, aging, and ac signal needs to be taken into consideration. Taking Murata GCM21BR71C475KA73K as an example, the effective capacitance reduces by 56% when 8V DC voltage is applied.

If back up battery is connected to the IC through long cable, TI recommend adding extra 100-200uF electrolytic capacitors on BUB side. This capacitor helps suppress LC ringing caused by parasite inductance on back up battery cable. Note that the electrolytic capacitor does not replace ceramic capacitor and 5μF to 10μF ceramic capacitor still needs to be placed near the IC.

8.2.2.4 Selecting the Output Capacitor

Main consideration for designing the output capacitor is the requirements for the output voltage drop when main battery fails and the device transition into boost mode. The minimum C_{out} is calculated by:

$$C_{out} > \frac{I_{outmax} \times 20\mu s}{\Delta V_{outmax}} \quad (12)$$

Where

- C_{OUT} is the output capacitance
- I_{OUTMAX} is the maximum output current
- ΔV_{OUTMAX} is the maximum output voltage drop allowed when transition into boost mode

20 μ s is the maximum transition time for the device to enter boost mode and start switching

The output ripple voltage another factor that affects the C_{out} selection. Assuming a capacitor with zero ESR, the minimum capacitance needed for a given ripple is calculated by

$$C_{out} > \frac{I_{outmax} \times (V_{out} - V_{BUB})}{f_{sw} \times \Delta V \times V_{out}} \quad (13)$$

Where

- I_{OUT} is the output current
- V_{OUT} is the output DC voltage
- V_{BUB} is the backup battery voltage
- ΔV is the output voltage ripple required
- f_{sw} is the switching frequency

Typically, a combination of ceramic capacitors and bulk electrolytic capacitors is needed to provide low ESR, high ripple current, and small output voltage ripple.

Ceramic capacitors has DC-bias derating that significantly reduce the effective capacitance when a DC-voltage is applied. So check the DC-bias curve at Boost V_{out} target voltage when calculating the capacitance.

Electrolytic capacitors has large ESR and the ESR of electrolytic capacitor increases by over 10 times under low temperature condition and seriously affect loop stability. So make sure low temperature ESR is considered when calculating loop stability. Poly-hybrid capacitors usually has smaller ESR under low temperature and is therefore more recommended.

Based on the application requirement, this application choose 100 μ F electrolytic capacitor with four 10 μ F ceramic capacitors in parallel.

8.2.2.5 Loop Stability and Compensation Design

The TPS61382Q1 requires external compensation, which allows the loop response to be optimized for each application. The COMP pin is the output of the internal error amplifier. An external compensation network, comprised of resistor R5, and ceramic capacitors C8 and C9, is connected to the COMP pin. Compensation parameter need to be calculated case by case. Following section gives an example about how to calculate the compensation network parameters with the selected inductor and output capacitor.




Figure 8-2. TPS61382Q1 Compensation Design

8.2.2.5.1 Small Signal Analysis

The TPS61382Q1 uses the fixed frequency peak current mode control with an internal adaptive slope compensation to avoid subharmonic oscillation. With the inductor current information sensed, the small-signal model of the power stage reduces from a two-pole system, created by L and C_{OUT} , to a single-pole system, created by R_{OUT} and C_{OUT} . The single-pole system is easily used with the loop compensation. The image below shows the equivalent small signal elements of a boost converter.




Figure 8-3. TPS61382Q1 Control Equivalent Circuitry Model

The small signal of power stage is given by:

$$K_{PS}(s) = \frac{R_{out}(1-D)}{2R_{sense}} \times \frac{\left(1 + \frac{s}{2\pi \times f_{zESR}}\right) \left(1 - \frac{s}{2\pi \times f_{zRHP}}\right)}{\left(1 + \frac{s}{2\pi \times f_{pPS}}\right)} \quad (14)$$

where

- D is the duty cycle
- R_{out} is the output load resistance
- R_{sense} is the equivalent internal current sense resistor, which is typically 6mΩ

The single pole of the power stage is given by:

$$f_{pPS} = \frac{2}{2\pi \times C_{out} \times R_{out}} \quad (15)$$

where

- C_{out} is the output capacitance. For a boost converter having multiple identical output capacitors in parallel, simply combine the capacitors with the equivalent capacitance

The zero created by the ESR of the output capacitor is given by:

$$f_{zESR} = \frac{1}{2\pi \times C_{out} \times R_{ESR}} \quad (16)$$

where

- R_{ESR} is the equivalent resistance in series of the output capacitor

The right-hand plane zero is given by:

$$f_{zRHP} = \frac{R_{out}(1-D)^2}{2\pi \times L} \quad (17)$$

where

- D is the duty cycle
- R_{out} is the output load resistor
- L is the inductance

Equation 18 shows the equation for feedback resistor network and the compensation network.

$$H_{COMP}(s) = G_{comp} \times R_{EA} \times \frac{R_{up} + R_{down}}{R_{down}} \times \frac{\left(1 + \frac{s}{2\pi \times f_{zCOMP}}\right)}{\left(s1 + \frac{s}{2\pi \times f_{pCOMP1}}\right)\left(1 + \frac{s}{2\pi \times f_{pCOMP2}}\right)} \quad (18)$$

where

- G_{COMP} is the gain of the error amplifier, typically $G_{EA} = 24\mu S$
- R_{EA} is the output impedance of the error amplifier, typically $R_{EA} = 5M\Omega$
- f_{pCOMP1} , f_{pCOMP2} is the frequency of the pole generated by compensation
- f_{zCOMP} is the zero's frequency of the compensation network

f_{pCOMP1} is given by:

$$f_{pCOMP1} = \frac{1}{2\pi \times R_{EA} \times C_{COMP}} \quad (19)$$

where

- C_{COMP} is the compensation capacitor

f_{pCOMP2} is given by:

$$f_{pCOMP2} = \frac{1}{2\pi \times R_{COMP} \times C_{HF}} \quad (20)$$

where

- C_{HF} is the high frequency bypass capacitor on COMP pin
- R_{COMP} is the resistor of the compensation network

f_{zCOMP} is given by:

$$f_{zCOMP} = \frac{1}{2\pi \times R_{COMP} \times C_{COMP}} \quad (21)$$

where

- C_{COMP} is the zero capacitor compensation
- R_{COMP} is the resistor of the compensation network

8.2.2.5.2 Loop Compensation Design

With the previous analysis on small signal models, calculate the compensation network parameters with the given inductor and output capacitor parameters. This section gives an example on calculating loop compensation.

1. Set the Crossover Frequency, f_C .

The first step is to set the loop crossover frequency, f_C . The higher the crossover frequency, the faster the loop response is. It is generally accepted that the loop gain crosses over no higher than the lower of either 1/10 of the switching frequency, f_{SW} , or 1/5 of the RHPZ frequency, f_{zRHP} .

2. Set the Compensation Resistance, R_{COMP} .

For a well-compensated boost system, the f_c is determined by R_{COMP} . For a properly designed boost system, f_{zCOMP} is placed below f_c to keep phase margin. And for common R_{COMP} range, R_{COMP} is far smaller than the amplifier output resistance R_{EA} , which makes $R_{COMP} \parallel R_{EA} \approx R_{COMP}$. Therefore, in the equation below, the initial gain $R_{COMP} \times G_{COMP} \times K_{FB}$ is determined by R_{COMP} . Therefore the f_c is calculated by the equation that the close loop total gain $T(s) = K_{PS}(s) + H_{COMP}(s)$ is zero at f_c .

$$H_{COMP} = 20 \lg \left(G_{COMP} \times R_{COMP} \times \frac{R_{down}}{R_{up} + R_{down}} \right) = -K_{PS}(f_c) \quad (22)$$

where

- K_{PS} is the gain of the power stage
- G_{EA} is the transconductance of the amplifier, the typical value of $G_{EA} = 24\mu S$

3. Set the Compensation Zero capacitor, C_{COMP} .

The compensation zero is placed at the power stage pole f_{pPS} to compensate the phase drop near f_{pPS} . Set $f_z = f_p$, the C_{COMP} is calculated as:

$$C_{COMP} = \frac{R_{out} \times C_{out}}{2R_{COMP}} \quad (23)$$

4. Set the Compensation Pole Capacitor, C_{HF} .

The compensation pole is placed to eliminate the ESR zero produced by R_{ESR} and C_{out} . Set $f_{pCOMP2} = f_{zESR}$, and get:

$$C_{HF} = \frac{R_{ESR} \times C_{out}}{R_{COMP}} \quad (24)$$

5. Check Phase Margin and Gain Margin

The calculated compensation parameters does not always means stability. Especially when the C_{out} has big ESR which bring f_{zESR} into bandwidth. TI provide excel calculation tool which generates bode plot after all compensation parameters are selected. So check the bode plot for stability after step 1-4. TI recommend Phase margin $> 60\text{deg}$ and gain margin $> 10\text{db}$. Reduce desired f_c and re-calculate compensation in step1-4 if the margin does not meet requirement.




Figure 8-4. Evaluate Loop Stability

8.2.3 Application Curves




Figure 8-5. Boost Switching at Heavy Load




Figure 8-6. Boost Switching at Light Load




Figure 8-7. Load Transient at Boost Mode




Figure 8-8. Load Sweep at Boost Mode




Figure 8-9. Line Transient at Boost Mode




Figure 8-10. Line Sweep at Boost Mode




Figure 8-11. Boost Output Short Protection












Figure 8-12. Boost Output Short Hiccup

**Figure 8-13. Boost Output Short Recovery****Figure 8-14. BUB Loop****Figure 8-15. Standby Mode Transition into Boost Mode (12V Battery Interruption)****Figure 8-16. Boost Mode Transition into Standby Mode (12V Battery Recovery)****Figure 8-17. Charger Mode Transition into Boost Mode (12V Battery Interruption)****Figure 8-18. Boost Mode Transition into Charger Mode (12V Battery Recovery)****Figure 8-19. LDO Charger Start up****Figure 8-20. LDO Charger Steady State**




Figure 8-21. Buck Charger Start up




Figure 8-22. Buck Charger Steady State




Figure 8-23. NiMH Intermittent Charge




Figure 8-24. SOH Steady State




Figure 8-25. 12V Battery Load Dump




Figure 8-26. 12V Battery Cold Crank

8.3 Power Supply Recommendations

The characteristics of the input supply needs to be capable of delivering the required input current to the loaded regulator. The average input current is estimated with the following equation.

$$I_{BUB} = \frac{V_{out} \times I_{out}}{V_{BUB} \times \eta} \quad (25)$$

where

- η is the efficiency

If the regulator is connected to the input supply through long wires or PCB traces, special care is required to achieve good performance. The parasitic inductance and resistance of the input cables has an adverse effect on the operation of the regulator. The parasitic inductance, in combination with the low-ESR ceramic input capacitors, resulting in LC resonant circuit. This LC ring results in overvoltage transients at the input to the regulator or tripping UVLO. Consider that the supply voltage dips when a load transient is applied to the output depending on the parasitic resistance and inductance of the harness and characteristics of the supply. If the application is operating close to the minimum input voltage, this dip causes the regulator to momentarily shut down and reset. The best way to solve these kinds of issues is to reduce the distance from the input supply to the regulator. Additionally, use an aluminum input capacitor in parallel with the ceramics. The moderate ESR of this type of capacitor helps damp the input resonant circuit and reduce any overshoots or undershoots. A value in the range of 47 μ F to 100 μ F is usually sufficient to provide input damping and help hold the input voltage steady during large load transients.

8.4 Layout

8.4.1 Layout Guidelines

The PCB layout of any DC-DC converter is critical to the excellent performance of the design. Bad PCB layout generates external noise and therefore disrupts the operation of an otherwise good schematic design. Even if the converter regulates correctly in some preliminary tests, bad PCB layout still affects reliability and increases risk under mass production. Furthermore, the EMI performance of the regulator is dependent on the PCB layout to a great extent.

In a boost converter, the most EMI-critical PCB feature is the loop formed by the output capacitor and low side MOSFET ground. This loop carries discontinuous currents with high di/dt which generates high voltage spikes on layout parasitic inductance. Excessive transient voltages disrupts the proper operation of the converter, affect EMI and even damage the MOSFET. In order to reduce parasitic inductance on layout, ceramic Cout need to be placed as close to Vout pin as possible (within 1mm) and low side MOSFET Q1 is placed as close to SW pin as possible. TI also recommend a smaller Cout (100nF-1uF, 0603 package) closest to the Vout pin to bypass the high frequency noise. Avoid connecting this smaller Cout through vias.

Besides Cout loop, GND connection is also very important to avoid switching noise form affecting the IC. There are risks that the IC internal circuit get out of control or even damage if AGND is not connected correctly. Make sure that there is a separate AGND from PGND and connect VCC, COMP, AGND pin, thermal pad to AGND. AGND need to be connected to PGND by single point (net-tie, 0ohm resistor or 10-20mil width trace). The net-tie is connected by a separate, short trace between low side MOSFET source (PGND) and AGND pad of VCC capacitor. View [Section 8.4.2](#) for detailed routing example on GND connection.

Place the VCC capacitor close to the VCC pin and AGND pin: This capacitor needs to be routed with short, wide traces to the VCC pin and AGND pin.

Make layer 2 of the PCB a ground plane: This plane operates as a noise shield and as a heat dissipation path. Using layer 2 as GND plane reduces the enclosed area of the Cout loop and reduces parasitic inductance.

Provide wide polygon pour for IL, SW, VOUT, and PGND(Low side MOSFET source): These paths needs to be as wide and direct as possible to reduce any voltage drops on the input or output paths of the converter to maximize efficiency.

Provide enough copper plane for proper heat sinking: Enough copper area needs to be applied to keep low $R_{\theta JA}$ under heavy load and high temperature. Apply at least 4-layer board with two-ounce copper the top and bottom PCB layers. If the PCB design uses multiple copper layers (recommended), thermal vias also connects to the inner layer heat-spreading ground planes. Note that the package of this device dissipates heat through all pins. Wide traces is used for all pins except where noise considerations dictate minimization of area

8.4.2 Layout Example

According to the previous analysis on GND connection. The net-tie between AGND and PGND is connected between source of the low side MOSFET and AGND pad of VCC capacitor. Driver current return path is cut out from PGND copper and routed separately in parallel with the gate trace as differential pairs so that their mutual inductance eliminates parasite inductance. Also, VCC Cap is placed closed to the IC as possible.




Figure 8-27. GND Connection Layout Example




Figure 8-28. TPS61382Q1 Typical Layout Top Layer




Figure 8-29. TPS61382Q1 Typical Layout Bottom Layer

9 Device and Documentation Support

9.1 Device Support

9.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

9.2 Documentation Support

9.2.1 Related Documentation

For related documentation see the following:

- Texas Instruments, [Performing Accurate PFM Mode Efficiency Measurements Application Report](#)
- Texas Instruments, [Accurately Measuring Efficiency of Ultra-low-IQ Devices Technical Brief](#)
- Texas Instruments, [IQ: What it is, What it isn't, and How to Use it Technical Brief](#)

9.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

9.4 Support Resources

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

9.5 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

9.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

9.7 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision * (September 2025) to Revision A (September 2025)	Page
• Changed Test Conditions for VOUT from '10V to 18V' to '11V to 18V'.....	6
• Changed Test Conditions for VOUT from '10V to 18V' to '11V to 18V'.....	6
• Added 'TJ = -20°C ~ 85°C' in Test Conditions.....	6

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPS613821QRAVRQ1	Active	Production	WQFN-FCRLF (RAV) 24	3000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 150	613821Q

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS613821QRAVRQ1	WQFN-FCRLF	RAV	24	3000	330.0	12.4	3.3	4.3	0.85	8.0	12.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS613821QRAVRQ1	WQFN-FCRLF	RAV	24	3000	346.0	346.0	33.0




4229510/D 04/2025

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



LAND PATTERN EXAMPLE
SCALE: 20X



4229510/D 04/2025

NOTES: (continued)


- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sluea271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

RAV0024A

WQFN-FCRLF - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE
 BASED ON 0.125 mm THICK STENCIL
 SCALE: 20X

PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE
 FUSED PAD 11 - 14 & 18-20: 62%
 FUSED PAD 15-17: 68%
 PAD 25: 79%

4229510/D 04/2025

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated