

TLV770 50mA, Small-Size, High-PSRR, Low-Dropout Regulator

1 Features

High PSRR: 55dB (1MHz) V_{IN} range: 1.4V to 5.5V

Fixed output voltage range: 0.6V to 3.3V

Output voltage accuracy: 2%

Low dropout voltage:

45mV at 50mA (3.3V_{OUT})

Active output pulldown resistor

Packages:

1mm × 1mm, 4-pin X2SON (DQN)

5-pin SOT-23 (DBV)

2 Applications

- **Smartphones**
- **Tablets**
- Gaming consoles
- **Notebooks**
- Streaming media players
- Set-top boxes
- Camera modules

3 Description


The TLV770 is a small, low-dropout (LDO) linear regulator that sources 50mA of output current. This LDO is designed to provide a voltage source with high PSRR. The device also provides load and line transient performance that meets the requirements of a variety of circuits. With a 1.4V to 5.5V input voltage range and a 0.6V to 3.3V output voltage range, the TLV770 is flexible enough to support multiple applications.

The TLV770 features an internal soft-start circuit to avoid excessive inrush current, thus minimizing the input voltage drop during start-up. An active pulldown circuit quickly discharges the output when the LDO is disabled and provides a known start-up state. The EN input allows an external logic signal to enable or disable the regulated output. The LDO is stable with small ceramic capacitors, allowing for a small overall package size. The operating junction temperature range is from -40°C to +125°C. This LDO is available in standard SOT-23 (DBV) and 1mm × 1mm X2SON (DQN) packages.

Package Information

PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾
TI V770	DQN (X2SON, 4)	1mm × 1mm
ILV//U	DBV (SOT-23, 5)	2.9mm × 2.8mm

- For more information, see the Mechanical, Packaging, and Orderable Information.
- The package size (length × width) is a nominal value and includes pins, where applicable.



Typical Application Circuit



Table of Contents

1 Features	1	7 Application and Implementation	13
2 Applications		7.1 Application Information	13
3 Description		7.2 Typical Application	
4 Pin Configuration and Functions	3	7.3 Power Supply Recommendations	
5 Specifications	4	7.4 Layout	15
5.1 Absolute Maximum Ratings		8 Device and Documentation Support	
5.2 ESD Ratings		8.1 Device Support	16
5.3 Recommended Operating Conditions		8.2 Documentation Support	16
5.4 Thermal Information	5	8.3 Receiving Notification of Documentation Updates.	16
5.5 Electrical Characteristics	<mark>5</mark>	8.4 Support Resources	16
5.6 Switching Characteristics	6	8.5 Trademarks	
5.7 Typical Characteristics	7	8.6 Electrostatic Discharge Caution	16
6 Detailed Description	10	8.7 Glossary	16
6.1 Overview		9 Revision History	17
6.2 Functional Block Diagram	10	10 Mechanical, Packaging, and Orderable	
6.3 Feature Description	10	Information	17
6.4 Device Functional Modes	12		



4 Pin Configuration and Functions




Figure 4-1. DQN Package, 1mm × 1mm, 4-Pin X2SON (Top View)




Figure 4-2. DBV Package, 5-Pin SOT-23 (Top View)

Table 4-1. Pin Functions

	PIN	TYPE ⁽¹⁾		DESCRIPTION
NAME	X2SON	SOT-23	ITPE	DESCRIPTION
EN	3	3	I	Enable input. A low voltage ($< V_{EN(LOW)}$) on this pin turns the regulator off and discharges the output pin to GND. A high voltage ($> V_{EN(HI)}$) on this pin enables the regulator output.
GND	2	2	G	Common ground.
IN	4	1	ı	Input voltage supply. For best transient response and to minimize input impedance, use the nominal value or larger capacitor from IN to ground; see the <i>Recommended Operating Conditions</i> table. Place the input capacitor as close to the IN and GND pins of the device as possible.
N/C	_	4	_	No internal electrical connection. Connect to GND for improved thermal performance.
OUT	1	5	0	Regulated output voltage. A low equivalent series resistance (ESR) capacitor is required from OUT to ground for stability. For best transient response, use the nominal recommended value or larger capacitor, as listed in the <i>Recommended Operating Conditions</i> table. Place the output capacitor as close to the OUT and GND pins of the device as possible. An internal pulldown resistor prevents a charge from remaining on V_{OUT} when the regulator is in shutdown mode (V_{EN} < $V_{EN(LOW)}$).
Thermal Pad	5	_	_	Thermal pad for the X2SON package. Connect this pad to GND or leave floating. Do not connect to any potential other than GND. Connect the thermal pad to a large-area ground plane for best thermal performance.

⁽¹⁾ I = input, O = output, I/O = input or output, and G = ground.



5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)(1) (3)

		MIN	MAX	UNIT
	Input, V _{IN}	-0.3	6.5	
Voltage	Output, V _{OUT}	-0.3	6.0 or V _{IN} + 0.3 ⁽²⁾	V
	Enable, V _{EN}	-0.3	6.5	
Current	Maximum output, I _{OUT} ⁽⁴⁾	Internally	y limited	Α
Temperature	Operating junction, T _J	-55	150	°C
	Storage, T _{stg}	-65	150	C

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) The maximum value of V_{OUT} is the lesser of 6.0V or $(V_{IN} + 0.3V)$.
- (3) All voltages are with respect to the GND pin.
- (4) Internal thermal shutdown circuitry protects the device from permanent damage.

5.2 ESD Ratings

			VALUE	UNIT
V _(ESD) Ele	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±1000	V
	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±500	V

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)(1)

		MIN	NOM	MAX	UNIT
V _{IN}	Input supply voltage	1.4		5.5	V
V _{EN}	Enable input voltage	0		5.5	V
V _{OUT}	Nominal output voltage range	0.6		3.3	V
I _{OUT}	Output current	0		50	mA
C _{IN}	Input capacitor ⁽²⁾		1		μF
C _{OUT}	Output capacitance ⁽³⁾	0.47		40	μF
ESR	Output capacitor effective series resistance			100	mΩ
TJ	Operating junction temperature	-40		125	°C

- (1) All voltages are with respect to GND.
- (2) An input capacitor is not required for LDO stability. However, an input capacitor with an effective value of 0.47µF minimum is recommended to counteract the effect of source resistance and inductance, which in some cases causes symptoms of system-level instability such as ringing or oscillation, especially in the presence of load transients. If needed use a larger input capacitance, depending on the characteristics of the input voltage source.
- (3) Effective output capacitance of 0.47μF minimum and 40μF maximum is required for stability. The effective output capacitance accounts for tolerance, temperature, voltage, and any other factors that affect the value, and is often 50% smaller than the capacitors specified value.

Product Folder Links: TLV770



5.4 Thermal Information

		TLV	/770	
	THERMAL METRIC(1)	DBV (SOT-23)	DQN (X2SON)	UNIT
		5 PINS	4 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	242.5	236.2	°C/W
R _{θJC(top)}	Junction-to-case (top) thermal resistance	140.9	218.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	109.4	180.8	°C/W
Ψлт	Junction-to-top characterization parameter	76.1	16.1	°C/W
ΨЈВ	Junction-to-board characterization parameter	108.8	179.6	°C/W
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	N/A	157.2	°C/W

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application note.

5.5 Electrical Characteristics

specifications apply for T_J = 25°C, V_{IN} = $V_{OUT(NOM)}$ + 0.5V or 1.4V, whichever is greater, V_{EN} = V_{IN} , I_{OUT} = 1mA, C_{IN} = 1 μ F, and C_{OUT} = 1 μ F (unless otherwise noted); all typical values are at T_J = 25°C

	PARAMETER	TEST CO	NDITIONS	MIN	TYP	MAX	UNIT
			1.2V ≤ V _{OUT} < 1.8V	-2.5		2.5	
			1.8V ≤ V _{OUT} ≤ 3.3V	-2		2	
ΔV _{OUT}	Output voltage tolerance		1.2V ≤ V _{OUT} < 1.8V	-3		3	%
		$T_J = -40$ °C to 85°C	1.8V ≤ V _{OUT} < 2.5V	-2.75		2.75	
			2.5V ≤ V _{OUT} ≤ 3.3V	-2.5		2.5	
ΔV _{OUT}	Line regulation	$V_{IN} = (V_{OUT(NOM)} + 0.5V)$ to	5.5V		0.01	0.1	%/V
ΔV _{OUT}	Load regulation	I _{OUT} = 1mA to 50mA			85	110	μV/mA
I _{GND}	Quiescent ground current	V _{EN} = V _{IN} = 5.5V, I _{OUT} = 0m.	A, T _J = -40°C to 85°C		80	120	μA
I _{SHDN}	Shutdown ground current	$V_{EN} < V_{EN(LOW)}, V_{IN} = 5.5V,$	T _J = -40°C to 85°C		0.01	2	μA
	Dropout voltage	I _{OUT} = 50mA,	$1.2V \le V_{OUT} < 1.8V^{(1)}$ (2)			220	mV
		V _{IN} = 95% × V _{OUT(NOM)}	1.8V ≤ V _{OUT} < 2.5V			60	
V _{DO}			2.5V ≤ V _{OUT} ≤ 3.3V			45	
V _{DO}		$I_{OUT} = 50 \text{mA},$ $V_{IN} = 95\% \times V_{OUT(NOM)}, T_{J}$	$1.2V \le V_{OUT} < 1.8V^{(1)}$ (2)			230	
			1.8V ≤ V _{OUT} < 2.5V			65	
		= -40°C to 85°C	2.5V ≤ V _{OUT} ≤ 3.3V			50	
I _{CL}	Output current limit	V _{OUT} = 0.9 x V _{OUT(NOM)} , T _J =	= -40°C to 85°C	80		210	mA
PSRR	Power-supply rejection ratio	I _{OUT} = 50mA,	f = 100kHz		56		dB
FORK	Fower-supply rejection ratio	$V_{IN} = V_{OUT} + 1.0V$	f = 1MHz		55		uБ
V _N	Output noise voltage	BW = 10Hz to 100kHz, V _{OU} -	_r = 1.2V, I _{OUT} = 50mA		90		μV _{RMS}
R _{PULLDOWN}	Output automatic discharge pulldown resistance	V _{EN} < V _{EN(LOW)} (output disal	bled), V _{IN} = 3.3V		135		Ω
_	T	T _J rising			160		°C
T _{SD}	Thermal shutdown	T _J falling			140		3.0
V _{EN(LOW)}	Low input threshold	V _{EN} falling until the output is 85°C	V_{EN} falling until the output is disabled, $T_J = -40$ °C to 85°C			0.3	V
V _{EN(HI)}	High input threshold	V _{EN} rising until the output is	enabled, T _J = –40°C to 85°C	0.9			V
I _{EN}	EN input leakage current	V _{EN} = 5.5V and V _{IN} = 5.5V			0.01	1	μΑ

For V_{OUT} < 1.5V, dropout is tested with V_{IN} = 1.4V.

⁽²⁾ For V_{OUT} = 0.6V, Dropout voltage < Headroom voltage. At V_{IN} = 1.4V, a 0.6V output device will not be in dropout. Headroom voltage = V_{IN} - V_{OUT}.



5.6 Switching Characteristics


specifications apply for T_J = 25°C, V_{IN} = $V_{OUT(NOM)}$ + 0.5V or 1.4V, whichever is greater, V_{EN} = V_{IN} , I_{OUT} = 1mA, C_{IN} = 1 μ F, and C_{OUT} = 1 μ F (unless otherwise noted); all typical values are at T_J = 25°C

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{ST}	Start-up time (V _{EN})	From $V_{EN} > V_{EN(HI)}$ to V_{OUT} = 95% of $V_{OUT(NOM)}$, V_{IN} rise time = 1V/ μ s		320		μs

Product Folder Links: TLV770

5.7 Typical Characteristics

at operating temperature T_J = 25°C, V_{IN} = $V_{OUT(NOM)}$ + 0.5V, I_{OUT} = 1mA, V_{EN} = V_{IN} , and C_{IN} = C_{OUT} = 1 μ F (unless otherwise noted)







Figure 5-1. Line Regulation vs V_{IN}

Figure 5-2. Load Regulation vs I_{OUT}







Figure 5-3. Output Voltage Accuracy vs VIN

Figure 5-4. Output Voltage Accuracy vs I_{OUT}







Figure 5-5. Dropout Voltage vs I_{OUT}

Figure 5-6. Quiescent Current vs VIN



5.7 Typical Characteristics (continued)


at operating temperature T_J = 25°C, V_{IN} = $V_{OUT(NOM)}$ + 0.5V, I_{OUT} = 1mA, V_{EN} = V_{IN} , and C_{IN} = C_{OUT} = 1 μ F (unless otherwise noted)



80 60 -50°C 0°C 85°C 125°C 1

Figure 5-7. Ground Current vs I_{OUT}

Figure 5-8. Shutdown Current vs V_{IN}








Figure 5-9. Current Limit

Figure 5-10. Enable Logic Threshold vs Temperature






 $V_{IN} = V_{OUT(nom)} + 1.0V$, $I_{OUT} = 50$ mA to 0mA, $t_{FALLING} = 10$ µs

Figure 5-11. Load Transient

Figure 5-12. Load Transient

5.7 Typical Characteristics (continued)

at operating temperature T_J = 25°C, V_{IN} = $V_{OUT(NOM)}$ + 0.5V, I_{OUT} = 1mA, V_{EN} = V_{IN} , and C_{IN} = C_{OUT} = 1 μ F (unless otherwise noted)






6 Detailed Description

6.1 Overview

The TLV770 provides high PSRR and good transient response in a small, 50mA LDO.

This LDO is designed to operate with a single 1µF input capacitor and a single 1µF ceramic output capacitor.

6.2 Functional Block Diagram



6.3 Feature Description

6.3.1 Dropout Voltage

Dropout voltage (V_{DO}) is defined as $V_{IN} - V_{OUT}$ at the rated output current (I_{RATED}), where the pass transistor is fully on. VIN is the input voltage, VOUT is the output voltage, and IRATED is the maximum IOUT listed in the Recommended Operating Conditions table. At this operating point, the pass transistor is driven fully on. Dropout voltage indirectly specifies a minimum input voltage greater than the nominal programmed output voltage where the output voltage is expected to stay in regulation. If the input voltage falls to less than the nominal output regulation, then the output voltage falls as well.

For a CMOS regulator, the dropout voltage is determined by the drain-source, on-state resistance (R_{DS(ON)}) of the pass transistor. Therefore, if the linear regulator operates at less than the rated current, the dropout voltage for that current scales accordingly. The following equation calculates the R_{DS(ON)} of the device.

$$R_{DS(ON)} = \frac{V_{DO}}{I_{RATED}}$$
 (1)

6.3.2 Active Discharge

The regulator has an internal MOSFET that connects a pulldown resistor between the output and ground when the device is disabled. This connection actively discharges the output voltage. The active discharge circuit is activated by the enable pin or by the voltage on IN falling below the undervoltage lockout (UVLO) threshold.

Product Folder Links: TLV770

Do not rely on the active discharge circuit for discharging a large amount of output capacitance after the input supply collapses. Reverse current flow from the output to the input potentially causes damage to the device. Limit reverse current to no more than 5% of the device rated current for a short period of time.

6.3.3 Brick-Wall Current Limit

The device has an internal current limit circuit that protects the device during overcurrent or shorting conditions. The current-limit circuit, as shown in Figure 6-1, is a brick-wall scheme. When the device is in current limit, the device sources the output current limit (I_{CL}) and the output voltage is unregulated. In this scenario, the output voltage depends on the load impedance.




Figure 6-1. Brick-Wall Current Limit Scheme

During a current-limit event, the potential for high power dissipation exists because of the elevated current level and increased input-to-output differential voltage $(V_{IN} - V_{OUT})$. If the device heats enough, the device enters thermal shutdown. If the current-limit condition is not removed when the device turns back on after cooling, the device reenters thermal shutdown. This cycle continues until the current-limit condition is removed. The device survives this fault, but repeatedly operating in this mode degrades long-term reliability.

6.3.4 Thermal Shutdown

The device contains a thermal shutdown protection circuit to disable the device when the junction temperature (T_J) of the pass transistor rises to $T_{SD(shutdown)}$ (typical). Thermal shutdown hysteresis makes sure that the device resets (turns on) when the temperature falls to $T_{SD(reset)}$ (typical).

The thermal time-constant of the semiconductor die is fairly short. Thus the device cycles on and off when thermal shutdown is reached until power dissipation is reduced. Power dissipation during start-up is high from large $V_{\text{IN}} - V_{\text{OUT}}$ voltage drops across the device or from high inrush currents charging large output capacitors. Under some conditions, the thermal shutdown protection disables the device before start-up completes.

For reliable operation, limit the junction temperature to the maximum listed in the *Recommended Operating Conditions* table. Operation above this maximum temperature causes the device to exceed operational specifications. Although the device internal protection circuitry is designed to protect against thermal overload conditions, this circuitry is not intended to replace proper heat sinking. Continuously running the device into thermal shutdown or above the maximum recommended junction temperature reduces long-term reliability.



6.4 Device Functional Modes

Table 6-1 shows the conditions that lead to the different modes of operation. See the *Electrical Characteristics* table for parameter values.

Table 6-1. Device Functional Mode Comparison

OPERATING MODE				
OPERATING WIDDE	V _{IN}	V _{EN}	I _{OUT}	T _J
Normal operation	$V_{IN} > V_{OUT(nom)} + V_{DO}$ and $V_{IN} > V_{IN(min)}$	$V_{EN} > V_{EN(HI)}$	$I_{OUT} < I_{OUT(max)}$	$T_J < T_{SD(shutdown)}$
Dropout operation	$V_{IN(min)} < V_{IN} < V_{OUT(nom)} + V_{DO}$	$V_{EN} > V_{EN(HI)}$	$I_{OUT} < I_{OUT(max)}$	$T_J < T_{SD(shutdown)}$
Disabled (any true condition disables the device)	V _{IN} < V _{UVLO}	V _{EN} < V _{EN(LOW)}	Not applicable	$T_{J} > T_{SD(shutdown)}$

6.4.1 Normal Operation

The device regulates to the nominal output voltage when the following conditions are met:

- The input voltage is greater than the nominal output voltage plus the dropout voltage (V_{OUT(nom)} + V_{DO})
- The output current is less than the current limit (I_{OUT} < I_{CL})
- The device junction temperature is less than the thermal shutdown temperature (T_J < T_{SD})
- The enable voltage has previously exceeded the enable rising threshold voltage and has not yet decreased to less than the enable falling threshold

6.4.2 Dropout Operation

If the input voltage is lower than the nominal output voltage plus the specified dropout voltage, the device operates in dropout mode. In this mode, the output voltage tracks the input voltage. In this mode, the transient performance of the device becomes significantly degraded. During this mode, the pass transistor is driven fully on. Line or load transients in dropout potentially result in large output voltage deviations.

When the device is in a steady dropout state, the pass transistor is driven fully on. This state is defined as when the device is in dropout, directly after being in a normal regulation state, but *not* during start-up. Dropout occurs when $V_{IN} < V_{OUT(NOM)} + V_{DO}$. When the regulator exits dropout, the input voltage returns to a value $\geq V_{OUT(NOM)} + V_{DO}$. During this time, the output voltage potentially overshoots for a short period of time. $V_{OUT(NOM)}$ is the nominal output voltage and V_{DO} is the dropout voltage. During dropout exit, the device pulls the pass transistor back from being driven fully on.

6.4.3 Disabled

Shutdown the device output by forcing the enable pin voltage to less than the maximum EN pin low-level input voltage (see the *Electrical Characteristics* table). When disabled, the pass transistor turns off and internal circuits shut down. The output voltage is also actively discharged to ground by an internal discharge circuit from the output to ground.

Copyright © 2025 Texas Instruments Incorporated Product Folder Links: *TLV770*



7 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

7.1 Application Information

7.1.1 Recommended Capacitor Types

The device is designed to be stable using low equivalent series resistance (ESR) ceramic capacitors at the input and output. Multilayer ceramic capacitors have become the industry standard for these types of applications and are recommended, but use good judgment. Ceramic capacitors that employ X7R-, X5R-, and C0G-rated dielectric materials provide relatively good capacitive stability across temperature. However, using Y5V-rated capacitors is discouraged because of large variations in capacitance.

Regardless of the ceramic capacitor type selected, the effective capacitance varies with operating voltage and temperature. Generally, expect the effective capacitance to decrease by as much as 50%. The input and output capacitors listed in the *Recommended Operating Conditions* table account for an effective capacitance of approximately 50% of the nominal value.

7.1.2 Input and Output Capacitor Requirements

Although an input capacitor is not required for stability, good analog design practice is to connect a capacitor from IN to GND. This capacitor counteracts reactive input sources and improves transient response, input ripple, and PSRR. Use an input capacitor if the source impedance is more than 0.5Ω . For typical operation of the TLV770, connect a $1\mu F$ capacitor to the input. Use a higher value capacitor if large, fast rise-time, load, or line transients are anticipated. Additionally, use a higher-value capacitor if the device is located several inches from the input power source.

Dynamic performance of the device is improved by using an output capacitor. Use an output capacitor within the range specified in the *Recommended Operating Conditions* table for stability. Make sure that the minimum derated output capacitance is equal to or greater than 0.47µF. When the output voltage is ramping up, the inrush current depends on the size of the output capacitance. During start-up, the output current is potentially as high as the current limit value for larger output capacitors.



7.2 Typical Application

7.2.1 Application

Figure 7-1 shows a typical application circuit for the TLV770.




Figure 7-1. TLV770 Typical Application

7.2.2 Design Requirements

Table 7-1 summarizes the design requirements for Figure 7-1.

 PARAMETER
 VALUE

 Input voltage range
 4.0V ± 5%

 Output voltage
 3.3V

 Output current
 50mA


 Maximum ambient temperature
 125°C

Table 7-1. Design Parameters

7.2.3 Detailed Design Procedure

For this design example, the 3.3V output version (TLV77033) is selected. A nominal 4.0V input supply is assumed. Use a minimum $1\mu F$ input capacitor to minimize the effect of resistance and inductance between the 4.0V source and LDO input. Use a minimum $0.47\mu F$ output capacitance for stability and good load transient response. The dropout voltage (V_{DO}) is less than 50mV maximum at a 3.3V output voltage and 50mA output current. There are no dropout issues with a minimum 3.8V input voltage (4.0V - 5%) and a maximum 50mA output current.

7.2.4 Application Curves



Product Folder Links: TLV770

7.3 Power Supply Recommendations

This device is designed to operate from an input supply voltage range of 1.4V to 5.5V. Make sure input supply is well regulated and free of spurious noise. To make sure that the output voltage is well regulated and dynamic performance is optimum, set the input supply to at least $V_{OUT(nom)} + 0.5V$ or 1.4V, whichever is greater.

Use a 1µF or greater input capacitor to reduce the impedance of the input supply, especially during transients.

7.4 Layout

7.4.1 Layout Guidelines

- Place input and output capacitors as close to the device as possible.
- Use copper planes for device connections to optimize thermal performance.
- · Place thermal vias around the device to distribute the heat.
- Do not place a thermal via directly beneath the thermal pad of the DQN package. A via wicks solder or solder
 paste away from the thermal pad joint during the soldering process. Thus, leading to a compromised solder
 joint on the thermal pad.

7.4.2 Layout Examples




Figure 7-4. DBV Package (SOT-23) Typical Layout




Figure 7-5. DQN Package (X2SON) Typical Layout



8 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed in this section.

8.1 Device Support

8.1.1 Device Nomenclature

Table 8-1. Device Nomenclature

PRODUCT ⁽¹⁾	DESCRIPTION
TLV770xx(x)Pyyyz	 xx(x) is the nominal output voltage. For output voltages with a resolution of 100mV, two digits are used in the ordering number. Otherwise, three digits are used (for example, 28 = 2.8V; 125 = 1.25V). P indicates an active output discharge feature. yyy is the package designator. z is the package quantity. R is for reel (3000 pieces).

⁽¹⁾ For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder on www.ti.com.

8.2 Documentation Support

8.2.1 Related Documentation

For related documentation, see the following:

Texas Instruments, Know Your Limits application note

8.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.4 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.5 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

8.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.7 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

Product Folder Links: TLV770



9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision * (May 2024) to Revision A (April 2025)	Page
•	Changed Functional Block Diagram: Deleted 500kΩ resistor from EN trace	10

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com

7-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
						(4)	(5)		
TLV77012PDBVR	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F5F
TLV77012PDBVR.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F5F
TLV77012PDQNR	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PG
TLV77012PDQNR.A	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PG
TLV77018PDBVR	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F6F
TLV77018PDBVR.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F6F
TLV77018PDQNR	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PH
TLV77018PDQNR.A	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PH
TLV77025PDBVR	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F7F
TLV77025PDBVR.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F7F
TLV77025PDQNR	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PI
TLV77025PDQNR.A	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PI
TLV77028PDBVR	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F8F
TLV77028PDBVR.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F8F
TLV77028PDQNR	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PJ
TLV77028PDQNR.A	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PJ
TLV77033PDBVR	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F9F
TLV77033PDBVR.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	3F9F
TLV77033PDQNR	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PK
TLV77033PDQNR.A	Active	Production	X2SON (DQN) 4	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	PK

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.



PACKAGE OPTION ADDENDUM

www.ti.com 7-Nov-2025

(4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com 20-Feb-2025

TAPE AND REEL INFORMATION



TAPE DIMENSIONS KO P1 BO W Cavity A0

A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLV77012PDBVR	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TLV77012PDQNR	X2SON	DQN	4	3000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2
TLV77018PDBVR	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TLV77018PDQNR	X2SON	DQN	4	3000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2
TLV77025PDBVR	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TLV77025PDQNR	X2SON	DQN	4	3000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2
TLV77028PDBVR	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TLV77028PDQNR	X2SON	DQN	4	3000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2
TLV77033PDBVR	SOT-23	DBV	5	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
TLV77033PDQNR	X2SON	DQN	4	3000	180.0	8.4	1.16	1.16	0.5	4.0	8.0	Q2



www.ti.com 20-Feb-2025



*All dimensions are nominal

dimensione are neminal								
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
TLV77012PDBVR	SOT-23	DBV	5	3000	210.0	185.0	35.0	
TLV77012PDQNR	X2SON	DQN	4	3000	210.0	185.0	35.0	
TLV77018PDBVR	SOT-23	DBV	5	3000	210.0	185.0	35.0	
TLV77018PDQNR	X2SON	DQN	4	3000	210.0	185.0	35.0	
TLV77025PDBVR	SOT-23	DBV	5	3000	210.0	185.0	35.0	
TLV77025PDQNR	X2SON	DQN	4	3000	210.0	185.0	35.0	
TLV77028PDBVR	SOT-23	DBV	5	3000	210.0	185.0	35.0	
TLV77028PDQNR	X2SON	DQN	4	3000	210.0	185.0	35.0	
TLV77033PDBVR	SOT-23	DBV	5	3000	210.0	185.0	35.0	
TLV77033PDQNR	X2SON	DQN	4	3000	210.0	185.0	35.0	




Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4210367/F



PLASTIC SMALL OUTLINE - NO LEAD




NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.
- 4. Features may not exist. Recommend use of pin 1 marking on top of package for orientation purposes.
- 5. Shape of exposed side leads may differ.
- 6. Number and location of exposed tie bars may vary.



PLASTIC SMALL OUTLINE - NO LEAD




NOTES: (continued)

- 7. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 8. If any vias are implemented, it is recommended that vias under paste be filled, plugged or tented.



PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate
design recommendations.





SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025