

Technical documentation





TEXAS INSTRUMENTS

TMP235-Q1, TMP236-Q1 SBOS939D – APRIL 2019 – REVISED JUNE 2022


TMP23x-Q1 Automotive Grade, High-Accuracy Analog Output Temperature Sensors

1 Features

- AEC-Q100 qualified for automotive applications
 TMP235-Q1 grade 0: -40°C to +150°C
 - TMP235-QT grade 0: -40 C to +150 C
 TMP236-Q1 grade 1: -40°C to +125°C
 - TMP230-QT grade 1. -40 C to +1
- Functional Safety-Capable
 - Documentation available to aid functional safety system design
- Tight accuracy across a wide temperature range:
 - ±2.5°C (maximum): -40°C to +150°C (TMP235-Q1)
 - ±2.5°C (maximum): -10°C to +125°C (TMP236-Q1)
- Positive slope sensor gain, offset (typical):
 - 10 mV/°C, 500 mV at 0°C (TMP235-Q1)
 - 19.5 mV/°C, 400 mV at 0°C (TMP236-Q1)
- Wide operating supply voltage range:
 - 2.3 V to 5.5 V (TMP235-Q1)
 - 3.1 V to 5.5 V (TMP236-Q1)
- Short-circuit protected output
- Low power: 9 µA (typical)
- · Strong output for driving loads up to 1000 pF
- Available package options:
 - 5-pin SC70 (DCK) surface mount
 - 3-pin SOT-23 (DBZ) surface mount
 - Footprint compatible with industry-standard LMT8x-Q1, LM50-Q1, and LM20 temperature sensors
- Cost-effective alternative to thermistors

2 Applications

- Automotive head unit
- Electric power steering (EPS)
- Shifter system
- Battery management system (BMS)
- Gasoline engine



3 Description


The TMP23x-Q1 devices are family of а automotive grade precision CMOS integrated-circuit analog temperature sensors linear with an output voltage proportional to temperature, serving various automotive applications from powertrain to infotainment. These temperature sensors have a typical accuracy from 0°C to +70°C of ±0.5°C. The TMP235-Q1 device provides a positive slope output of 10 mV/°C over the full –40°C to +150°C temperature range and a supply range from 2.3 V to 5.5 V. The higher gain TMP236-Q1 sensor provides a positive slope output of 19.5 mV/°C from -10°C to +125°C and a supply range from 3.1 V to 5.5 V.

The 9-µA typical quiescent current and 800-µs typical power-on time enable effective power-cycling architectures to minimize power consumption for battery-powered devices. A class-AB output driver provides a strong 500-µA maximum output to drive capacitive loads up to 1000 pF and is designed to directly interface to analog-to-digital converter sample and hold inputs. With excellent accuracy and a strong linear output driver, the TMP23x-Q1 analog output temperature sensors are cost-effective alternatives to passive thermistors.

Device Information⁽¹⁾

PART NUMBER	PACKAGE	BODY SIZE (NOM)
TMP235-Q1,	SC70 (5)	2.00 mm × 1.25 mm
TMP236-Q1	SOT-23 (3)	2.92 mm × 1.30 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.



An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.



Table of Contents

1 Features	1
2 Applications	1
3 Description	1
4 Revision History	
5 Pin Configuration and Functions	3
6 Specifications	4
6.1 Absolute Maximum Ratings	4
6.2 ESD Ratings	4
6.3 Recommended Operating Conditions	4
6.4 Thermal Information	4
6.5 Electrical Characteristics	5
6.6 Typical Characteristics	6
7 Detailed Description	
7.1 Overview	
7.2 Functional Block Diagram	
7.3 Feature Description	<mark>8</mark>

7.4 Device Functional Modes	.10
8 Application and Implementation	. 11
8.1 Application Information	.11
8.2 Typical Application	
9 Power Supply Recommendations	.12
10 Layout	
10.1 Layout Guidelines	
10.2 Layout Examples	
11 Device and Documentation Support	
11.1 Receiving Notification of Documentation Updates.	
11.2 Support Resources	13
11.3 Trademarks	
11.4 Electrostatic Discharge Caution	
11.5 Glossary	
12 Mechanical, Packaging, and Orderable	
Information	13


4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision C (November 2019) to Revision D (June 2	2022) Page	
 Updated the numbering format for tables, figures, and cross-references throughout the document Added Functional Safety bullets to the <i>Features</i> section 		
Changes from Revision B (October 2019) to Revision C (Novemb	er 2019) Page	
 Added temperature accuracy specs for the TMP236-Q1 SOT-23 p 	ackage5	
Changes from Revision A (May 2019) to Revision B (October 2019	9) Page	
Changed document status from Advance Information to Production	n Data1	
Changes from Revision * (April 2019) to Revision A (May 2019)	Page	
 Changed recommended operating temperature range from: –50°C 	to 150°C to: -40°C to 150°C4	



5 Pin Configuration and Functions






Figure 5-1. DBZ Package 3-Pin SOT-23 Top View

NC- no internal connection Figure 5-2. DCK Package 5-Pin SC70 Top View

Table 5-1. Pin Functions

NAME				DESCRIPTION	
	SOT-23	SC70		DESCRIPTION	
GND	3	2	Ground	Power supply ground.	
NC	—	5	—	No internal connection. This pin may be left floating or connected to GND.	
NC	—	1	_	No internal connection. This pin may be left floating or connected to GND.	
V _{OUT}	2	3	0	Outputs voltage proportional to temperature	
V _{DD}	1	4	I	Positive supply input	



6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

	MIN	MAX	UNIT	
Supply voltage, V _{DD}		+6	6 V	
Output voltage, V _{OUT}	-0.3	(V _{DD} + 0.3)		
Output current	-30	+30	mA	
Latch-up current, each pin	-200	+200	ШA	
Junction temperature (T _J)		+150	°C	
Storage temperature (T _{stg})	-65	+150	C	

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or anyother conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

				VALUE	UNIT
V _(ESD) Electrostatic discharge	Human body model (HBM), per AEC Q100-002 ⁽¹⁾ HBM ESD Classification Level 2		±2000	V	
	Charged device model (CDM), per AEC Q100-011	All Pins	±500	V	
		CDM ESD Classification Level C4B	Corner Pins	±750	V

(1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM MAX	UNIT
V.	Input voltage (TMP235-Q1)	2.3	5.5	V
V _{DD}	Input voltage (TMP236-Q1)	3.1	5.5	v
T _A	Operating free-air temperature	-40	150	°C

6.4 Thermal Information

THERMAL METRIC ⁽¹⁾ ⁽²⁾		TMP	TMP23X-Q1		
		DCK (SC70)	DBZ (SOT-23)	UNIT	
		5 PINS	3 PINS		
R _{θJA}	Junction-to-ambient thermal resistance ^{(3) (4)}	275	167	°C/W	
R _{0JC(top)}	Junction-to-case (top) thermal resistance	84	90	°C/W	
R _{θJB}	Junction-to-board thermal resistance	56	146	°C/W	
Ψ_{JT}	Junction-to-top characterization parameter	1.2	35	°C/W	
Ψ _{JB}	Junction-to-board characterization parameter	55	146	°C/W	

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

(2) For information on self-heating and thermal response time see Layout Guidelines section.

(3) The junction to ambient thermal resistance (R_{θJA}) under natural convection is obtained in a simulation on a JEDEC-standard, High-K board as specified in JESD51-7, in an environment described in JESD51-2. Exposed pad packages assume that thermal vias are included in the PCB, per JESD 51-5.

(4) Changes in output due to self heating can be computed by multiplying the internal dissipation by the thermal resistance.



6.5 Electrical Characteristics

TMP235-Q1: V_{DD} = 2.3 V to 5.5 V, GND = Ground, T_A = -40°C to +125°C and no load (unless otherwise noted) TMP236-Q1: V_{DD} = 3.1 V to 5.5 V, GND = Ground, T_A = -10°C to +125°C and no load (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
POWEF	R SUPPLY							
			T _A = 25°C, V _{DD} = 2.3 V, TMP235-Q1		9			
			T _A = 25°C, V _{DD} = 3.1 V, TMP236-Q1		10			
I _{DD}	Operating current		T _A = -40°C to +125°C, TMP235-Q1			14.5	μA	
			T _A = -10°C to +125°C, TMP236-Q1			15		
			T _A = 150°C, TMP235-Q1			17		
Δ°C/ ΔV _{DD}	Line regulation			-0.1	0.02	0.1	°C/V	
SENSO	RACCURACY					1		
			T _A = 25°C		±0.5			
T _{ACY}			T _A = 0°C to 70°C (SC70 Package) (TMP235-Q1)	-1.5	±0.5	+1.2		
	Temperature accuracy ⁽¹⁾		T _A = 0°C to 70°C (SOT-23 Package) (TMP235-Q1)	-1.5	±0.5	+1.2	O°	
			T _A = -40°C to 125°C (TMP235-Q1)	-2.5	±0.5	+2.5		
			T _A = -40°C to 150°C (TMP235-Q1)	-2.5	±0.5	+2.5		
			T _A = -10°C to 125°C (TMP236-Q1)	-2.5	±0.5	+2.5		
T _{ACY}	Temperature accuracy ⁽¹⁾		T _A = 0°C to 70°C (SOT-23 Package) (TMP236-Q1)	-1.5	±0.5	+1.5	°C	
SENSO	ROUTPUT					1		
			TMP235-Q1		500			
V _{0°C}	Output voltage offset at 0 °C		TMP236-Q1	400		mV		
-	Townshing a finite to the second second	\ \	TMP235-Q1		10			
т _с	Temperature coefficient (sensor gain)	TMP236-Q1		19.5		mV/°C	
V _{ONL}	Output nonlinearity ⁽²⁾		T _A = 0 °C to 70 °C, no load		±0.5		°C	
I _{OUT}	Output current					500	μA	
7	Outrut importance		IOUT = 100 μA, f = 100 Hz		20		0	
Z _{OUT}	Output impedance		IOUT = 100 μA, f = 500 Hz		50		Ω	
	Output load regulation		$T_{A} = 0^{\circ}C \text{ to } 70^{\circ}C, \text{ IOUT} = 100 \mu\text{A}, \\ \Delta V_{OUT} / \Delta I_{OUT}$		1		Ω	
t _{ON}	Turn on time		Time to reach accuracy within ±0.5°C		800		μs	
C _{LOAD}	Typical load capacitance					1000	pF	
t _{RES}	Thermal response to 63%	SC70	30°C (Air) to +125°C (Fluid Bath)		1.3		s	


(1) Accuracy is defined as the error between the measured and reference output voltages, tabulated in the TMP235-Q1 Transfer Table and TMP236-Q1 Transfer Table at the specified conditions of supply voltage and temperature (expressed in °C). Accuracy limits include line regulation within the specified conditions. Accuracy limits do not include load regulation; they assume no DC load.

(2) Nonlinearity is defined as the deviation of the output-voltage-versus-temperature curve from the best-fit straight line, over the device's rated temperature range.




6.6 Typical Characteristics

at T_A = 25°C, (unless otherwise noted)










7 Detailed Description

7.1 Overview

The TMP23x-Q1 devices are a family of linear analog temperature sensors with an output voltage proportional to temperature. These temperature sensors have an accuracy from 0°C to 70°C of ±1.5°C. The TMP235-Q1 device provides a positive slope output of 10 mV/°C over the full -40°C to +150°C temperature range and a supply range from 2.3 V to 5.5 V. The higher gain TMP236-Q1 sensor provides a positive slope output of 19.5 mV/°C from -10°C to +125°C and a supply range from 3.1 V to 5.5 V. A class-AB output driver provides a maximum output of 500 µA to drive capacitive loads up to 1000 pF.

7.2 Functional Block Diagram



7.3 Feature Description

As shown in Figure 6-2, the TMP23x-Q1 devices are linear. A small V_{OUT} gain shift, however, is present at temperatures above 100°C. When small shifts are expected, a piecewise linear function provides the best accuracy and is used for the device accuracy specifications (see Specifications). Typical output voltages of the TMP23x-Q1 devices across the full operating temperature range are listed in Table 7-3 and Table 7-4. The ideal linear columns represent the ideal linear V_{OUT} output response with respect to temperature, while the piecewise linear columns indicate the small voltage shift at elevated temperatures.

The piecewise linear function uses three temperature ranges listed in Table 7-1 and Table 7-2. In equation form, the voltage output V_{OUT} of the TMP23x-Q1 is calculated by Equation 1:

$$V_{OUT} = (T_A - T_{INFL}) \times T_C + V_{OFFS}$$
(1)

where

- V_{OUT} is the TMP23x-Q1 voltage output for a given temperature
- T_A is the ambient temperature in °C
- T_{INFI} is the temperature inflection point for a piecewise segment in °C
- T_C is the TMP23x-Q1 temperature coefficient or gain
- V_{OFFS} is the TMP23x-Q1 voltage offset

Therefore, the T_A temperature for a given V_{OUT} voltage output within a piecewise voltage range (V_{RANGE}) is calculated in Equation 2. For applications where the accuracy enhancement above 100°C is not required, use the first row of Table 7-1 and Table 7-2 for all voltages.

Table 7-1. TMP235-Q1 Piecewise Linear Function Summary							
T _A RANGE (°C)	V _{RANGE} (mV) T _{INFL} (°C) T _C (mV/°C) V _{OFFS} (mV)						
-40 to +100	< 1500	0	10	500			
100 to 125	1500 to 1752.5	100	10.1	1500			
125 to 150	> 1752.5	125	10.6	1752.5			

 $T_A = (V_{OUT} - V_{OFFS}) / T_C + T_{INFL}$

e	Linear	Function	Summarv	

(2)



Table 7-2. TMP236-Q1 Piecewise Linear Function Summary									
T _A RANGE (°C)	V _{RANGE} (mV)	T _{INFL} (°C)	T _C (mV/°C)	V _{OFFS} (mV)					
-40 to +100	≤ 2350	0	19.5	400					
100 to 125	> 2350	100	19.7	2350					
125 to 150	—			—					

Table 7-3. TMP235-Q1 Transfer Table

TEMPERATURE (°C)	V _{OUT} (mV) IDEAL LINEAR VALUES	V _{OUT} (mV) PIECEWISE LINEAR VALUES
-40	100	100
-35	150	150
-30	200	200
-25	250	250
-20	300	300
-15	350	350
-10	400	400
-5	450	450
0	500	500
5	550	550
10	600	600
15	650	650
20	700	700
25	750	750
30	800	800
35	850	850
40	900	900
45	950	950
50	1000	1000
55	1050	1050
60	1100	1100
65	1150	1150
70	1200	1200
75	1250	1250
80	1300	1300
85	1350	1350
90	1400	1400
95	1450	1450
100	1500	1500
105	1550	1550.5
110	1600	1601
115	1650	1651.5
120	1700	1702
125	1750	1752.5
130	1800	1805.5
135	1850	1858.5
140	1900	1911.5
145	1950	1964.5
150	2000	2017.5



Table 7-4. TMP236-Q1 Transfer Table

TEMPERATURE (°C)	V _{OUT} (mV) IDEAL LINEAR VALUES	V _{OUT} (mV) PIECEWISE LINEAR VALUES		
-40	_	_		
-35	_	_		
-30	_	_		
-25	_	_		
-20	_	_		
-15	_	_		
-10	205	205		
-5	303	303		
0	400	400		
5	498	498		
10	595	595		
15	693	693		
20	790	790		
25	888	888		
30	985	985		
35	1083	1083		
40	1180	1180		
45	1278	1278		
50	1375	1375		
55	1473	1473		
60	1570	1570		
65	1668	1668		
70	1765	1765		
75	1863	1863		
80	1960	1960		
85	2058	2058		
90	2155	2155		
95	2253	2253		
100	2350	2350		
105	2448	2448.5		
110	2545	2547		
115	2643	2645.4		
120	2740	2743.9		
125	2838	2842.4		
130	_	_		
135	_	_		
140	_	_		
145	_	_		
150	_	_		

7.4 Device Functional Modes

The singular functional mode of the TMP23x-Q1 is an analog output directly proportional to temperature.



8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

The features of the TMP235-Q1 make the series of devices designed for various general temperature-sensing applications. The TMP235-Q1 and TMP236-Q1 devices can operate down to a 2.3-V and a 3.1-V supply with $9-\mu A$ power consumption, respectively. The TMP23x-Q1 series is mounted in two surface mount technology packages (SC70 and SOT-23.)

8.2 Typical Application

8.2.1 Connection to an ADC




Figure 8-1. Suggested Connections to an ADC Input Stage

8.2.1.1 Design Requirements

See Figure 8-1 for suggested connections to an ADC input stage. Most CMOS-based ADCs have a sampled data comparator input structure. When the ADC charges the sampling capacitor (C_{SAMPLE}), the capacitor requires instantaneous charge from the output of the analog source temperature sensor, such as the TMP235-Q1. Therefore, the output impedance of the temperature sensor can affect ADC performance. In most cases, adding an external capacitor (C_{FILTER}) mitigates design challenges. The TMP235-Q1 is specified and characterized with a 1000-pF maximum capacitive load (C_{LOAD}). Figure 8-1 shows C_{LOAD} as the sum of C_{FILTER} + C_{MUX} + C_{SAMPLE} . TI recommends maximizing the C_{FILTER} value while allowing for the maximum specified ADC input capacitance (C_{MUX} + C_{SAMPLE}) to limit the total C_{LOAD} at 1000 pF. In most cases, a 680-pF C_{FILTER} provides a reasonable allowance for ADC input capacitance to minimize ADC sampling error and reduce noise coupling. An optional series resistor (R_{FILTER}) and C_{FILTER} provides additional low-pass filtering to reject system level noise. TI recommends placing R_{FILTER} and C_{FILTER} as close as possible to the ADC input for optimal performance.

8.2.1.2 Detailed Design Procedure

Depending on the input characteristics of the ADC, an external C_{FILTER} may be required. The value of C_{FILTER} depends on the size of the sampling capacitor (C_{SAMPLE}) and the sampling frequency while observing a maximum C_{LOAD} of 1000 pF. The capacitor requirements can vary because the input stages of all ADCs are not identical. Figure 8-1 shows a general ADC application as an example only.



8.2.1.3 Application Curve




Figure 8-2. Output Voltage vs. Ambient

9 Power Supply Recommendations

The low supply current and supply range of the TMP23x-Q1 allow the device to be easily powered from many sources.


Power supply bypassing is strongly recommended. In noisy environments, TI recommends to add a filter with 0.1- μ F capacitor and 100- Ω resistor between external supply and V_{DD} to limit the power supply noise. Larger capacitances may be required and are dependent on the noise of the power supply.


10 Layout

10.1 Layout Guidelines

The layout of the TMP23x-Q1 series is simple. If a power supply bypass capacitor is used, the capacitor must be connected as *Layout Examples* shows.

10.2 Layout Examples







11 Device and Documentation Support

11.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.2 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

11.3 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

11.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.5 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking
	(1)	(2)			(3)	(4)	(5)		(6)
TMP235AEDBZRQ1	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	235E
TMP235AEDBZRQ1.A	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	235E
TMP235AEDBZTQ1	Obsolete	Production	SOT-23 (DBZ) 3	-	-	Call TI	Call TI	-40 to 150	235E
TMP235AEDCKRQ1	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1CF
TMP235AEDCKRQ1.A	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 150	1CF
TMP235AQDBZRQ1	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	235Q
TMP235AQDBZRQ1.A	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	235Q
TMP235AQDBZTQ1	Obsolete	Production	SOT-23 (DBZ) 3	-	-	Call TI	Call TI	-40 to 125	235Q
TMP235AQDCKRQ1	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	1CG
TMP235AQDCKRQ1.A	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	1CG
TMP235AQDCKTQ1	Obsolete	Production	SC70 (DCK) 5	-	-	Call TI	Call TI	-40 to 125	1CG
TMP236AQDBZRQ1	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	NIPDAUAG SN	Level-2-260C-1 YEAR	-40 to 125	236Q
TMP236AQDBZRQ1.A	Active	Production	SOT-23 (DBZ) 3	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 125	236Q
TMP236AQDBZTQ1	Obsolete	Production	SOT-23 (DBZ) 3	-	-	Call TI	Call TI	-40 to 125	236Q

⁽¹⁾ **Status:** For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



www.ti.com

PACKAGE OPTION ADDENDUM

30-Jun-2025

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TMP235-Q1, TMP236-Q1 :

• Catalog : TMP235, TMP236

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product



Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal												t.
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMP235AEDBZRQ1	SOT-23	DBZ	3	3000	180.0	8.4	3.15	2.77	1.22	4.0	8.0	Q3
TMP235AEDCKRQ1	SC70	DCK	5	3000	180.0	8.4	2.47	2.3	1.25	4.0	8.0	Q3
TMP235AQDBZRQ1	SOT-23	DBZ	3	3000	180.0	8.4	3.15	2.77	1.22	4.0	8.0	Q3
TMP235AQDCKRQ1	SC70	DCK	5	3000	180.0	8.4	2.47	2.3	1.25	4.0	8.0	Q3
TMP236AQDBZRQ1	SOT-23	DBZ	3	3000	180.0	8.4	3.2	2.85	1.3	4.0	8.0	Q3



www.ti.com

PACKAGE MATERIALS INFORMATION

22-Apr-2025



*All dimensions are nominal	
-----------------------------	--

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TMP235AEDBZRQ1	SOT-23	DBZ	3	3000	213.0	191.0	35.0
TMP235AEDCKRQ1	SC70	DCK	5	3000	213.0	191.0	35.0
TMP235AQDBZRQ1	SOT-23	DBZ	3	3000	213.0	191.0	35.0
TMP235AQDCKRQ1	SC70	DCK	5	3000	213.0	191.0	35.0
TMP236AQDBZRQ1	SOT-23	DBZ	3	3000	210.0	185.0	35.0

DBZ0003A



PACKAGE OUTLINE

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.
 Reference JEDEC registration TO-236, except minimum foot length.

- 4. Support pin may differ or may not be present.
- 5. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side




DBZ0003A

EXAMPLE BOARD LAYOUT

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




DBZ0003A

EXAMPLE STENCIL DESIGN

SOT-23 - 1.12 mm max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

8. Board assembly site may have different recommendations for stencil design.



DCK0005A



PACKAGE OUTLINE

SOT - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 This drawing is subject to change without notice.
 Reference JEDEC MO-203.

- 4. Support pin may differ or may not be present.5. Lead width does not comply with JEDEC.
- 6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



DCK0005A

EXAMPLE BOARD LAYOUT

SOT - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

Publication IPC-7351 may have alternate designs.
 Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DCK0005A

EXAMPLE STENCIL DESIGN

SOT - 1.1 max height

SMALL OUTLINE TRANSISTOR



NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

10. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated