

Technical documentation



Support & training



TVS3301

SLVSEG2B – SEPTEMBER 2018 – REVISED SEPTEMBER 2022

# **TVS3301 33-V Bidirectional Flat-Clamp Surge Protection Device**

## 1 Features

- Functional Safety-Capable
  - Documentation available to aid functional safety system design
- Protection against 1-kV, 42-Ω IEC 61000-4-5 surge test for industrial signal lines
- Bidirectional polarity enables protection against bipolar signaling or miswiring conditions
- Clamping voltage of 40 V at 27-A of 8/20-µs surge current
- Standoff voltage: ±33 V
- Small 3 mm × 3 mm SON footprint
- Survives over 5,000 repetitive strikes of 25-A 8/20-µs surge current
- Robust surge protection
  - IEC61000-4-5 (8/20 μs): 27 A
  - IEC61643-321 (10/1000 μs): 3 A
- Low leakage current
- 2.5-nA typical at 27°C
- 450-nA maximum at 85°C
- Low capacitance: 54 pF
- Integrated level 4 IEC 61000-4-2 ESD protection

### 2 Applications

- Industrial sensor I/O
- PLC I/O modules
- Analog inputs
- Appliances
- Medical equipment
- Building automation

## **3 Description**

The TVS3301 device shunts up to 27 A of IEC 61000-4-5 fault current to protect systems from highpower transients or lightning strikes. The device survives the common industrial signal line EMC requirement of 1-kV IEC 61000-4-5 open circuit voltage coupled through a  $42-\Omega$  impedance. The TVS3301 uses a feedback mechanism to ensure precise flat clamping during a fault, keeping system exposure lower than traditional TVS diodes. The tight voltage regulation allows designers to confidently select system components with a lower voltage tolerance, lowering system costs and complexity without sacrificing robustness. The TVS3301 has a ±33-V operating range to enable operation in systems that require protection against reverse wiring conditions.


In addition, the TVS3301 is available in a small SON footprint designed for space constrained applications, offering a significant size reduction compared to standard SMA and SMB packages. Low device leakage and capacitance ensure a minimal effect on the protected line. To ensure robust protection over the lifetime of the product, TI tests the TVS3301 against 5000 repetitive surge strikes at 125°C with no shift in device performance.

#### Package Information<sup>(1) (2)</sup>


PART NUMBER	PACKAGE	BODY SIZE (NOM)
TVS3301	SON (DRB, 8)	3.00 mm × 3.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

(2) For related products, see the *Device Comparison Table*.



Voltage Clamp Response to 8/20-µs Surge Event



**Functional Block Diagram** 

An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.



# **Table of Contents**

1 Features	1
2 Applications	1
3 Description	1
4 Revision History	
5 Description (continued)	3
6 Device Comparison Table	
7 Pin Configuration and Functions	4
8 Specifications	
8.1 Absolute Maximum Ratings	5
8.2 ESD Ratings - JEDEC	5
8.3 ESD Ratings - IEC	<mark>5</mark>
8.4 Recommended Operating Conditions	5
8.5 Thermal Information	5
8.6 Electrical Characteristics	6
8.7 Typical Characteristics	7
9 Detailed Description	9
9.1 Overview	
9.2 Functional Block Diagram	

9.3 Feature Description	9
9.4 Device Functional Modes	9
10 Application and Implementation	. 11
10.1 Application Information	.11
10.2 Typical Application	. 11
11 Power Supply Recommendations	.13
12 Layout	.13
12.1 Layout Guidelines	. 13
12.2 Layout Example	
13 Device and Documentation Support	
13.1 Documentation Support	
13.2 Receiving Notification of Documentation Updates.	
13.3 Support Resources	
13.4 Trademarks	
13.5 Electrostatic Discharge Caution	
13.6 Glossary	.14
14 Mechanical, Packaging, and Orderable	
Information	. 14

# **4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (December 2018) to Revision B (September 2022)	Page
Updated the numbering format for tables, figures, and cross-references throughout the doc	
Updated the <i>Features</i> section to include Functional Safety-Capable text	1
Changes from Revision * (September 2018) to Revision A (December 2018)	Page
Changed from Advance Information to Production Data	1



# **5** Description (continued)

The TVS3301 is part of TI's Flat-Clamp family of surge devices. For a deeper look at the Flat-Clamp family, refer to the *Flat-Clamp Surge Protection Technology for Efficient System Protection* white paper.

### 6 Device Comparison Table

DEVICE	V <sub>rwm</sub>	V <sub>clamp</sub> at I <sub>pp</sub>	l <sub>pp</sub> (8/20 μs)	Leakage at V <sub>rwm</sub>	POLARITY	Package
TVS0500	5	9.2 V	43 A	0.07 nA	Unidirectional	DRV (SON-6)
TVS0701	7	11 V	30 A	0.25 nA	Bidirectional	DRB (SON-8)
TVS1400	14	18.6 V	43 A	2 nA	Unidirectional	DRV (SON-6)
TVS1401	14	20.5 V	30 A	1.1 nA	Bidirectional	DRB (SON-8)
TVS1800	18	22.8 V	40 A	0.3 nA	Unidirectional	DRV (SON-6)
TVS1801	18	27.4 V	30 A	0.4 nA	Bidirectional	DRB (SON-8)
TVS2200	22	27.7 V	40 A	3.2 nA	Unidirectional	DRV (SON-6)
TVS2201	22	29.6 V	30 A	2 nA	Bidirectional	DRB (SON-8)
TVS2700	27	32.5 V	40 A	1.7 nA	Unidirectional	DRV (SON-6)
TVS2701	27	34 V	27 A	0.8 nA	Bidirectional	DRB (SON-8)
TVS3300	33	38 V	35 A	19 nA	Unidirectional	DRV (SON-6), YZF (WCSP)
TVS3301	33	40 V	27 A	2.5 nA	Bidirectional	DRB (SON-8)



# 7 Pin Configuration and Functions




Figure 7-1. DRB Package, 8-Pin SON (Top View)

#### Table 7-1. Pin Functions

	PIN	TYPE <sup>(1)</sup>	DESCRIPTION
NAME	NAME DRB		DESCRIPTION
IN	1, 2, 3, 4	IN	Surge protected channel
GND	GND 5, 6, 7, 8		Ground
FLOAT	FLOAT Exposed Thermal Pad		Exposed thermal pad must be floating.

(1) IN = input, GND = ground, NC = no connection.



### 8 Specifications

#### 8.1 Absolute Maximum Ratings

 $T_A = 27^{\circ}C$  (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
	IEC 61000-4-5 Current (8/20 μs)		±27	A
Maximum Surge	IEC 61000-4-5 Power (8/20 μs)		1100	W
Maximum Surge	IEC 61643-321 Current (10/1000 μs)		±3	А
	IEC 61643-321 Power (10/1000 μs)		120	W
EFT	IEC 61000-4-4 EFT Protection		±80	A
I <sub>BR</sub>	DC Current		20	mA
T <sub>A</sub>	Ambient Operating Temperature	-40	125	°C
T <sub>stg</sub>	Storage Temperature	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Rating may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Condition. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### 8.2 ESD Ratings - JEDEC

			VALUE	UNIT	
M	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/ JEDEC JS-001, all pins <sup>(1)</sup>	±2000	V	
V <sub>(ESD)</sub>		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup>	±500	V	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

#### 8.3 ESD Ratings - IEC

			VALUE	UNIT
V	Electrostatic discharge	IEC 61000-4-2 contact discharge	±8	kV
V <sub>(ESD)</sub>		IEC 61000-4-2 air-gap discharge	±15	ΓV

#### 8.4 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V <sub>RWM</sub>	Reverse Stand-Off Voltage		±33		V

#### 8.5 Thermal Information

		TVS3301	
	THERMAL METRIC <sup>(1)</sup> DRB (SON) UNIT   B PINS 8 PINS 0°C/W   Junction-to-ambient thermal resistance 52.0 °C/W   Junction-to-case (top) thermal resistance 56.1 °C/W   Junction-to-board thermal resistance 24.9 °C/W   Junction-to-top characterization parameter 2.1 °C/W   Junction-to-board characterization parameter 24.8 °C/W	UNIT	
		8 PINS	
R <sub>qJA</sub>	Junction-to-ambient thermal resistance	52.0	°C/W
R <sub>qJC(top)</sub>	Junction-to-case (top) thermal resistance	56.1	°C/W
R <sub>qJB</sub>	Junction-to-board thermal resistance	24.9	°C/W
Y <sub>JT</sub>	Junction-to-top characterization parameter	2.1	°C/W
Y <sub>JB</sub>	Junction-to-board characterization parameter	24.8	°C/W
R <sub>qJC(bot)</sub>	Junction-to-case (bottom) thermal resistance	9.8	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.




#### **8.6 Electrical Characteristics**

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
1	Lookago Current	Measured at $V_{IN}$ = ± $V_{RWM}$ , $T_A$ = 27°C		2.5	110	nA
ILEAK	Leakage Current	Measured at $V_{IN} = \pm V_{RWM}$ , $T_A = 85^{\circ}C$			450	ΠA
V <sub>BR</sub>	Break-down Voltage	I <sub>IN</sub> = ±1 mA	34.4	37.5		V
M	Clamp Voltage	$\pm I_{pp}$ IEC 61000-4-5 Surge (8/20 µs), V <sub>IN</sub> = 0 V before surge, T <sub>A</sub> = 27°C		40	42.5	V
V <sub>CLAMP</sub>	Clamp Voltage	21 A IEC 61000-4-5 Surge (8/20 $\mu$ s), V <sub>IN</sub> =±V <sub>RWM</sub> before surge, T <sub>A</sub> = 125°C			43.2	v
R <sub>DYN</sub>	8/20 μs surge dynamic resistance	Calculated from V <sub>CLAMP</sub> at .5*I <sub>PP</sub> and I <sub>PP</sub> surge current, T <sub>A</sub> = 25°C		35		mΩ
C <sub>IN</sub>	Input pin capacitance	$V_{IN} = V_{RWM}$ , f = 1 MHz, 30 mV <sub>pp</sub> , IO to GND		54		pF
SR	Mayimum Claur Data	0- $\pm$ V <sub>RWM</sub> rising edge, sweep rise time and measure slew rate when I <sub>PEAK</sub> = 1 mA, T <sub>A</sub> = 27°C		2.5		
	Maximum Slew Rate	$0-\pm V_{RWM}$ rising edge, sweep rise time and measure slew rate when $I_{PEAK}$ = 1 mA, $T_A$ = 85°C		1.0		V/µs




### 8.7 Typical Characteristics



7



# 8.7 Typical Characteristics (continued)






## 9 Detailed Description

#### 9.1 Overview

The TVS3301 is a bidirectional precision clamp with two integrated FETs driven by a feedback loop to tightly regulate the input voltage during an overvoltage event. This feedback loop leads to a very low dynamic resistance, giving a flat clamping voltage during transient overvoltage events like a surge.

#### 9.2 Functional Block Diagram



#### 9.3 Feature Description

The TVS3301 is a precision clamp that handles 27 A of IEC 61000-4-5 8/20- $\mu$ s surge pulse. The flat clamping feature helps keep the clamping voltage very low to keep the downstream circuits from being stressed. The flat clamping feature can also help end-equipment designers save cost by opening up the possibility to use lower-cost, lower voltage tolerant downstream ICs. This device provides a bidirectional operating range, with a symmetrical V<sub>RWM</sub> of ±33 V designed for applications that have bipolar input signals or that must withstand reverse wiring conditions. The TVS3301 has minimal leakage at V<sub>RWM</sub>, designed for applications where low leakage and power dissipation is a necessity. Built-in IEC 61000-4-2 and IEC 61000-4-4 ratings make it a robust protection solution for ESD and EFT events and the TVS3301 wide ambient temperature range of  $-40^{\circ}$ C to +125°C enables usage in harsh industrial environments.

#### 9.4 Device Functional Modes

#### 9.4.1 Protection Specifications

The TVS3301 is specified according to both the IEC 61000-4-5 and IEC 61643-321 standards. This enables usage in systems regardless of which standard is required by relevant product standards or best matches measured fault conditions. The IEC 61000-4-5 standard requires protection against a pulse with a rise time of 8  $\mu$ s and a half-length of 20  $\mu$ s, while the IEC 61643-321 standard requires protection against a much longer pulse with a rise time of 10  $\mu$ s and a half-length of 1000  $\mu$ s.

The positive and negative surges are imposed to the TVS3301 by a combination wave generator (CWG) with a 2- $\Omega$  coupling resistor at different peak voltage levels. For powered-on transient tests that need power supply bias, inductances are used to decouple the transient stress and protect the power supply. The TVS3301 is post-tested by assuring that there is no shift in device breakdown or leakage at V<sub>RWM</sub>.



In addition, the TVS3301 has been tested according to IEC 61000-4-5 to pass a  $\pm$ 1-kV surge test through a 42- $\Omega$  coupling resistor and a 0.5- $\mu$ F capacitor. This test is a common test requirement for industrial signal I/O lines and the TVS3301 precision clamp can be used in applications that have that requirement.

The TVS3301 integrates IEC 61000-4-2 level 4 ESD Protection and 80 A of IEC 61000-4-4 EFT Protection. These combine to ensure that the device can protect against most common transient test requirements.

For more information on TI's test methods for Surge, ESD, and EFT testing, refer to the *IEC 61000-4-x Tests for TI's Protection Devices* application report.

#### 9.4.2 Reliability Testing

To ensure device reliability, the TVS3301 is characterized against 5000 repetitive pulses of 25-A IEC 61000-4-5 8/20-µs surge pulses at 125°C. The test is performed with less than 10 seconds between each pulse at high temperature to simulate worst-case scenarios for fault regulation. After each surge pulse, the TVS3301 clamping voltage, breakdown voltage, and leakage are recorded to ensure that there is no variation or performance degradation. By ensuring robust, reliable, high temperature protection, the TVS3301 enables fault protection in applications that must withstand years of continuous operation with no performance change.

#### 9.4.3 Minimal Derating

Unlike traditional diodes, the TVS3301 has very little derating of maximum power dissipation and ensures robust performance up to 125°C, shown in Figure 8-6. Traditional TVS diodes lose up to 50% of their current carrying capability when at high temperatures, so a surge pulse above 85°C ambient can cause failures that are not seen at room temperature. The TVS3301 prevents this so the designer can see the surge protection regardless of temperature. Because of this, Flat-Clamp devices can provide robust protection against surge pulses that occur at high ambient temperatures, as shown in TI's *TVS Surge Protection in High-Temperature Environments* application report.

#### 9.4.4 Bidirectional Operation

The TVS3301 is a bidirectional TVS with a symmetrical operating region. This allows for operation with positive and negative voltages, rather than just positive voltages like the unidirectional TVS3300. This allows for single chip protection for applications where the signal is expected to operate below 0 V or where there is a need to withstand a large common-mode voltage. In addition, there is a system requirement to be able to withstand reverse wiring conditions, in many cases where a high voltage signal is accidentally applied to the system ground and a ground is accidentally applied to the input terminal. This causes a large reverse voltage on the TVS diode that the device must be able to withstand. The TVS3301 is designed to not break down or see failures under reverse wiring conditions for applications that must withstand these miswiring issues.

#### Note

If the applied signal is not expected to go below 0 V, a unidirectional device will clamp much lower in the reverse direction and should be used. In this case, the recommended device would be the TVS3300.

#### 9.4.5 Transient Performance

During large transient swings, the TVS3301 will begin clamping the input signal to protect downstream conditions. While this prevents damage during fault conditions, it can cause leakage when the intended input signal has a fast slew rate. To keep power dissipation low and remove the chance of signal distortion, TI recommendeds that the designer keep the slew rate of any input signal on the TVS3301 below 2.5 V/µs at room temperature and below 1.0 V/µs at 85°C shown in Figure 8-7. Faster slew rates will cause the device to clamp the input signal and draw current through the device for a few microseconds, increasing the rise time of the signal. This will not cause any harm to the system or to the device, however, it can cause device overheating if the fast input voltage swings occur regularly.



### 10 Application and Implementation

#### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

#### **10.1 Application Information**

The TVS3301 can be used to protect any power, analog, or digital signal from transient fault conditions caused by the environment or other electrical components. One common example is using the TVS3301 to protect both sides of a PLC module and a sensor transmitter, as shown in the following figure. The transmitter side of this will be examined in more detail in the following section.




Figure 10-1. TVS3301 Application Example

#### **10.2 Typical Application**




Figure 10-2. TVS3301 Application Schematic



#### **10.2.1 Design Requirements**

A typical operation for the TVS3301 would be protecting an analog output module on a PLC similar to Figure 10-2. In this example, the TVS3301 is protecting a 4-20 mA transmitter that uses the XTR115, a standard transmitter that has a nominal voltage of 24 V and a maximum input voltage of 40 V. Most industrial interfaces such as this require protection against  $\pm 1$  kV surge test through a 42- $\Omega$  coupling resistor and a 0.5- $\mu$ F capacitor, equaling roughly 24 A of surge current. The system also requires protection from reverse wiring conditions. Without any input protection, this input voltage will rise to hundreds of volts for multiple microseconds, and violate the absolute maximum input voltage and harn the device if a surge event is caused by lightning, coupling, ringing, or any other fault condition. TI's Flat-Clamp technology provides surge protection diodes that can maximize the useable voltage range and clamp at a safe level for the system.

#### **10.2.2 Detailed Design Procedure**

If the TVS3301 is in place to protect the device, the voltage will rise to the breakdown of the diode at 37.5 V, during a surge event. The TVS3301 will then turn on to shunt the surge current to ground. With the low dynamic resistance of the TVS3301, large amounts of surge current will have minimal impact on the clamping voltage. The dynamic resistance of the TVS3301 is around 35 m $\Omega$ , which means a 24-A surge current will cause a voltage raise of 24 A × 35 m $\Omega$  = 0.84 V. Because the device turns on at 37.5 V, this means the XTR115 input will be exposed to a maximum of 37.5 V + 0.84 V = 38.34 V during surge pulses, well within the absolute maximum input voltage to ensure robust protection of the circuit.

Because the TVS3301 is a bidirectional device, it also satisfies the condition for withstanding reverse wiring. In this case, if  $V_{LOOP}$  is wired in reverse, the input terminal of the TVS3301 will see –24 V, which is below the negative  $V_{RWM}$ . The leakages will be the same as if the battery is wired properly.

The small size of the device also improves fault protection by lowering the effect of fault current coupling onto neighboring traces. The small form factor of the TVS3301 allows the device to be placed extremely close to the input connector, which lowers the length of the path fault current going through the system compared to larger protection solutions. Finally, the low leakage of the TVS3301 will have low input power losses. At 33 V, the device will see typical 2.5-nA leakage for a constant power dissipation of less than 100  $\mu$ W, a small quantity that will minimally effect overall efficiency metrics and heating concerns.

#### **10.2.3 Application Curves**

As shown in Figure 10-3, the TVS3301 will clamp when exposed to a surge.




Figure 10-3. TVS3301 Clamping Waveform (27-A, 8/20-µs Surge)

#### 10.2.4 PLC Surge Protection Reference Design

For a detailed description of the Flat-Clamp devices advantages in a PLC Analog Input Module, reference TI's *Surge Protection Reference Design for PLC Analog Input Module*. This document describes the considerations and performance of the TVS3300 in a common industrial application. While the document does not reference the TVS3301 specifically, performance between the devices should be similar.



### **11 Power Supply Recommendations**

The TVS3301 is a clamping device so there is no need to power it. To ensure the device functions properly do not violate the recommended  $V_{IN}$  voltage range (-33 V to 33 V).

#### 12 Layout

#### **12.1 Layout Guidelines**

The optimum placement is close to the connector. EMI during an ESD event can couple from the tested trace to other nearby unprotected traces, which could result in system failures. The PCB designer must minimize the possibility of EMI coupling by keeping all unprotected traces away from protected traces between the TVS and the connector. Route the protected traces straight. Use rounded corners with the largest radii possible to eliminate any sharp corners on the protected traces between the TVS3301 and the connector. Electric fields tend to build up on corners, which could increase EMI coupling.

Ensure that the thermal pad on the layout is floating rather than grounded. Grounding the thermal pad will impede the operating range of the TVS3301, and can cause failures when the applied voltage is negative. A floating thermal pad allows the maximum operating range without sacrificing any transient performance.

#### 12.2 Layout Example




Figure 12-1. TVS3301 Layout



## 13 Device and Documentation Support

#### **13.1 Documentation Support**

#### 13.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, Flat-Clamp Surge Protection Technology for Efficient System Protection white papers
- Texas Instruments, IEC 61000-4-x Tests for TI's Protection Devices application reports
- Texas Instruments, Surge Protection Reference Design for PLC Analog Input Module
- Texas Instruments, TVS Surge Protection in High-Temperature Environments application reports
- Texas Instruments, TVS3301 Functional Safety, FIT Rate, Failure Mode Distribution and Pin FMA

#### **13.2 Receiving Notification of Documentation Updates**

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### **13.3 Support Resources**

TI E2E<sup>™</sup> support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

#### 13.4 Trademarks

TI E2E<sup>™</sup> is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

#### 13.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

#### 13.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

#### 14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



#### PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	<b>RoHS</b> (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
TVS3301DRBR	Active	Production	SON (DRB)   8	3000   LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	1PQP
TVS3301DRBR.A	Active	Production	SON (DRB)   8	3000   LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	1PQP

<sup>(1)</sup> **Status:** For more details on status, see our product life cycle.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

# TAPE AND REEL INFORMATION





#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal
-----------------------------

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TVS3301DRBR	SON	DRB	8	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2



www.ti.com

# PACKAGE MATERIALS INFORMATION

17-Apr-2023



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TVS3301DRBR	SON	DRB	8	3000	338.0	355.0	50.0

# **GENERIC PACKAGE VIEW**

# VSON - 1 mm max height PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4203482/L



# DRB0008A



# **PACKAGE OUTLINE**

# VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.

3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



# **DRB0008A**

# **EXAMPLE BOARD LAYOUT**

# VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



# **DRB0008A**

# **EXAMPLE STENCIL DESIGN**

# VSON - 1 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated