

# Single-Event-Effects Test Report of the TPS7H2211-SEP eFuse



## ABSTRACT

The purpose of this study is to characterize the single-event effects (SEE) performance due to heavy-ion irradiation of the TPS7H2211-SEP. Heavy-ions with  $LET_{EFF}$  (Effective Linear Energy Transfer) of 48 MeV·cm<sup>2</sup>/mg were used to irradiate 5 devices. A flux of  $\approx 10^5$  ions/(cm<sup>2</sup>·s) and fluence of  $\approx 10^7$  ions/cm<sup>2</sup> per run were used for the characterization. The results demonstrated that the TPS7H2211-SEP is single event latch-up, single-event burnout and single-event gate rupture (EN = high/low)-free at T = 125°C and 25°C, respectively, using <sup>109</sup>Ag across the full electrical specifications. A single transient was not observed. See [Section 8](#) for more details.

## Table of Contents

<b>1 Introduction</b> .....	4
<b>2 Single-Event Effects</b> .....	5
<b>3 Device and Test Board Information</b> .....	6
<b>4 Irradiation Facility and Setup</b> .....	8
<b>5 Depth, Range, and <math>LET_{EFF}</math> Calculation</b> .....	10
<b>6 Test Setup and Procedures</b> .....	11
<b>7 Destructive Single-Event Effects (DSEE)</b> .....	13
7.1 Single-Event Latch-Up (SEL) Results.....	13
7.2 Single-Event Burnout (SEB) and Single-Event Gate Rupture (SEGR) Results.....	13
<b>8 Single-Event Transients (SET)</b> .....	16
8.1 Single Event Transients.....	16
<b>9 Event Rate Calculations</b> .....	17
<b>10 Summary</b> .....	18
<b>B References</b> .....	20

## List of Figures

Figure 3-1. Photograph of Delidded TPS7H2211-SEP (Left) and Pin Out Diagram (Right).....	6
Figure 3-2. TPS7H2211-SEP Board Top View.....	6
Figure 3-3. TPS7H2211-SEP EVM Schematic.....	7
Figure 4-1. Photograph of the TPS7H2211-SEP Evaluation Board Mounted in Front of the Heavy-Ion Beam Exit Port at the Texas A&M Cyclotron.....	9
Figure 5-1. Generalized Cross-Section of the LBC7 Technology BEOL Stack on the TPS7H2211-SEP (Left) and SEUSS 2020 Application Used to Determine Key Ion Parameters (Right).....	10
Figure 6-1. Block Diagram of SEE Test Setup With the TPS7H2211-SP.....	12
Figure 7-1. Current vs Time for Run # 1 of the TPS7H2211-SEP at T = 125°C.....	13
Figure 7-2. Current vs Time for Run # 4 (Enabled) for the TPS7H2211-SEP at T = 25°C.....	14
Figure 7-3. Current vs Time for Run # 5 (Disabled) for the TPS7H2211-SEP at T = 25°C.....	15

## List of Tables

Table 1-1. Overview Information.....	4
Table 5-1. Praseodymium and Homium Ion $LET_{EFF}$ Depth and Range in Silicon.....	10
Table 6-1. Equipment Set and Parameters Used for SEE Testing the TPS7H2211-SP.....	11
Table 7-1. Summary of TPS7H2211-SEP SEL Test Condition and Results.....	13
Table 7-2. Summary of TPS7H2211-SEP SEB Test Condition and Results.....	14
Table 8-1. Summary of TPS7H2211-SEP SET Test Condition and Results.....	16
Table 9-1. SEL Event Rate Calculations for Worst-Week LEO and GEO Orbits.....	17
Table 9-2. SEB/SEGR Event Rate Calculations for Worst-Week LEO and GEO Orbits.....	17

Table 9-3. SET Event Rate Calculations for Worst-Week LEO and GEO Orbits.....	17
---	----

## Trademarks

National Instruments™ and LabVIEW™ are trademarks of National Instruments.

HP-Z4™ is a trademark of Hewlett-Packard.

All trademarks are the property of their respective owners.

## 1 Introduction

The TPS7H2211-SEP is a radiation tolerant, 4.5-V to 14-V input, 3.5-A, eFuse. The device provides reverse current protection, overvoltage protection, and a configurable rise time. The device contains a P-channel MOSFET which operates over the full input range and supports the maximum 3.5 A of continuous current. The switch is controlled through the active-high Enable (EN) input pin, which is capable of interfacing directly with low-voltage control signals.

Other protection features include thermal shutdown, internal current limiting (Fast Trip), and an overvoltage detection pin.

The device is offered in a 32-pin plastic package (HTSSOP). [Table 1-1](#) lists general device information and test conditions. For more detailed technical specifications, user's guides, and application notes, see the [TPS7H2211-SEP](#) product page

**Table 1-1. Overview Information**

Description <sup>(1)</sup>	Device Information
TI part number	TPS7H2211-SP
Orderable number	TPS7H2211MDAPTSEP
Device function	Integrated single channel eFuse
Technology	250-nm linear BiCMOS 7 (LBC7)
Exposure facility	Radiation Effects Facility, Cyclotron Institute, Texas A&M University (15 MeV/nucleon)
Heavy ion fluence per run	$\approx 1 \times 10^7$ ions/cm <sup>2</sup>
Irradiation temperature	25°C (for SEB testing), 25°C (for SET testing), and 125°C (for SEL testing)

- (1) TI may provide technical applications or design advice, quality characterization, and reliability data or service. Providing these items shall not expand or otherwise affect TI's warranties as set forth in the Texas Instruments Incorporated Standard Terms and Conditions of Sale for Semiconductor Products. No obligation or liability shall arise from Semiconductor Products, and no obligation or liability shall arise from TI's provision of such items.

## 2 Single-Event Effects

The primary concern of interest for the TPS7H2211-SEP is the robustness against the Destructive Single-Event Effects (DSEE) named as:

- Single-Event Latch-up (SEL)
- Single-Event Burn-out (SEB)
- Single-Event Gate Rupture (SEGR)

In mixed technologies, such as the Linear BiCMOS 7 process used on the TPS7H2211-SEP, the CMOS circuitry introduces a potential for SEL susceptibility. SEL can occur if excess current injection caused by the passage of an energetic ion is high enough to trigger the formation of a parasitic cross-coupled PNP and NPN bipolar structure (formed between the p-sub and n-well and n+ and p+ contacts) [1, 2]. The parasitic bipolar structure initiated by a single-event creates a high-conductance path (inducing a steady-state current that is typically orders-of-magnitude higher than the normal operating current). This current between power and ground persists or is *latched* until power is removed, the device is reset, or until the device is destroyed by the high-current state. The TPS7H2211-SEP was tested for SEL at the maximum recommended voltage of 14 V and maximum load current of 3.5 A. The device exhibits no-SEL with heavy-ions of  $LET_{EFF} = 48 \text{ MeV}\cdot\text{cm}^2/\text{mg}$  at Flux  $\approx 10^5$  ions/cm<sup>2</sup>·s, fluences of  $\approx 10^7$  ions/cm<sup>2</sup>, and a die temperature of 125°C, using <sup>109</sup>Ag.

DMOS are susceptible to SEB/SEGR while in the off state. However, the device was also evaluated on all possible cases (Enable and Disable). SEB is similar to the SEL and occurs when the parasitic BJT of the DMOSFET is turned on by the heavy ion strike. When a heavy ion with sufficient energy hits the p body, it creates an excess charge inducing a voltage drop. This voltage drop forward biases the emitter-base junction of the parasitic NPN (formed by the N+ source, the P base region, and the N-drift region). If this happens when the DMOSFET is under a high drain bias, a secondary breakdown of the parasitic npn BJT can occur, creating permanent damage of the DMOS.

When the heavy-ion hits the neck region of the DMOS (under the gate), the heavy-ion creates electron hole-pairs on the oxide and silicon. Drift separates the excess electrons and holes due to the positive bias field on the drain to source of the DMOS. Holes are driven upward to the dioxide while the electrons are transported toward the drain. The collected holes on the dioxide create an equal image of electrons on the opposite side of the gate dioxide. Since the charge injection and collection after an event is faster than the transport and recombination of the e-h pairs, a voltage transient can be developed across the gate oxide. If this build-up voltage is higher than the oxide breakdown, permanent damage can be induced on the oxide, creating a destructive gate rupture [3, 4]. The TPS7H2211-SEP was evaluated for SEB/SEGR at full load conditions (3.5 A), enabled and disabled modes and  $LET_{EFF}$  of  $48 \text{ MeV}\cdot\text{cm}^2/\text{mg}$  using <sup>109</sup>Ag (at angle of incidence of 0°). A flux of  $\approx 10^5$  ions/cm<sup>2</sup>·s, fluence of  $\approx 10^7$  ions/cm<sup>2</sup>, and a die temperature of  $\approx 25^\circ\text{C}$  per run was used during the SEB/SEGR characterization. The device is SEB/SEGR-free up to 14 V.


The TPS7H2211-SP was characterized for SET at flux of  $\approx 10^5$  ions/cm<sup>2</sup>·s, fluences of  $\approx 10^7$  ions/cm<sup>2</sup>, and room temperature. The device was characterized at input voltages ranging from 4.5 V (minimum recommended voltage) to 14 V (maximum recommended voltage), at  $I_{LOAD}$  of 3.5 A and under no-load conditions. The TPS7H2211-SP is SET-free. For more details, see the [Single-Event Transients \(SET\)](#) section.

### 3 Device and Test Board Information


The TPS7H2211-SP is packaged in a 32-pin (HTSSOP) plastic package as shown in [Figure 3-1](#). A TPS7H2211EVM evaluation board was used to evaluate the performance and characteristics of the TPS7H2211-SEP under heavy-ions.

[Figure 3-2](#) shows the top view of the evaluation board used for the radiation testing. [Figure 3-3](#) shows the EVM board schematics for dual site testing. For more information about the evaluation board, see the [TPS7H2211-SEP Evaluation Module User's Guide](#).

The package was delidded to reveal the die face for all heavy-ion testing.



**Figure 3-1. Photograph of Delidded TPS7H2211-SEP (Left) and Pin Out Diagram (Right)**



**Figure 3-2. TPS7H2211-SEP Board Top View**




## 4 Irradiation Facility and Setup

The heavy-ion species used for the SEE studies on this product were provided and delivered by the TAMU Cyclotron Radiation Effects Facility using a superconducting cyclotron and an advanced Electron Cyclotron Resonance (ECR) ion source. At the fluxes used, ion beams had good flux stability and high irradiation uniformity over a 1-in diameter circular cross-sectional area for the in-air station. Uniformity is achieved by magnetic de-focusing. The flux of the beam is regulated over a broad range spanning several orders of magnitude. For the bulk of these studies, ion flux of  $\approx 10^5$  ions/cm<sup>2</sup>·s were used to provide heavy-ion fluences of  $\approx 10^7$  ions/cm<sup>2</sup> per run.


For the experiments conducted on this report, <sup>109</sup>Ag ions were used to achieve LET<sub>EFF</sub> 48 MeV·cm<sup>2</sup>/mg. Ion uniformity for these experiments was between 94 and 98%.

Figure 4-1 shows the TPS7H2211-SEP test board used for the experiments at the TAMU facility. Although not visible in this photo, the beam port has a 1-mil Aramica window to allow in-air testing while maintaining the vacuum within the accelerator with only minor ion energy loss. A 40-mm in-air gap between the device and the ion beam port window was maintained at these distances for all runs respective to the ion that was tested.



**Figure 4-1. Photograph of the TPS7H2211-SEP Evaluation Board Mounted in Front of the Heavy-Ion Beam Exit Port at the Texas A&M Cyclotron**

### 5 Depth, Range, and LET<sub>EFF</sub> Calculation



**Figure 5-1. Generalized Cross-Section of the LBC7 Technology BEOL Stack on the TPS7H2211-SEP (Left) and SEUSS 2020 Application Used to Determine Key Ion Parameters (Right)**

The TPS7H2211-SEP is fabricated in the TI Linear BiCMOS 7 (LBC7, 250-nm process with a Back-End-Of-Line (BEOL) stack consisting of four levels of standard thickness aluminum metal. The total stack height from the surface of the passivation to the silicon surface is 13.5 μm based on nominal layer thickness as shown in Figure 5-1. Accounting for energy loss through the 1-mil thick Aramica beam port window, the 40-mm air gap and the BEOL stack over the TPS7H2211-SEP, the effective LET (LET<sub>EFF</sub>) at the surface of the silicon substrate, the depth, and the ion range was determined with the SEUSS 2020 Software (provided by the Texas A&M Cyclotron Institute and based on the latest SRIM-2013 (7) models). Table 5-1 lists the results. The stack was modeled as a homogeneous layer of silicon dioxide (valid since SiO<sub>2</sub> and aluminum density are similar).

**Table 5-1. Praseodymium and Homium Ion LET<sub>EFF</sub> Depth and Range in Silicon**

Ion Type	Angle of Incidence (°)	Range <sub>EFF</sub> in Silicon (μm)	LET <sub>EFF</sub> (MeV·cm <sup>2</sup> /mg)
<sup>109</sup> Ag	0	91.6	48

## 6 Test Setup and Procedures

SEE testing was performed on a TPS7H2211-SP device mounted on a modified TPS7H2211EVM. The device power was provided by using the J3 (VIN-1) and J8 (GND) inputs with the N6765A precision power supply in a 4-wire configuration mounted on a N6705 rack. A Chroma E-Load (Electronic Load) in the Constant-Resistance (CR) modes were used to load the device to 3.5 A for the SEE testing campaign.

For the SEL, SEB, and SEGR, the device was powered up to the maximum recommended operating voltage of 14 V and loaded with the maximum load of 3.5 A. For the SEB/SEGR characterization, the device was tested under enabled and disabled modes. The device was disabled by using the TP 7 connecting EN to GND. The E-Load was connected even when the device was disabled to help differentiate if an SET momentarily activated the device under the heavy-ion irradiation. During the SEB and SEGR testing not a single input current event was observed when testing with  $^{109}\text{Ag}$ .

For the SET characterization, the TPS7H2211-SEP was evaluated at input voltages ranging from 4.5 V (minimum recommended voltage) to 14 V (maximum recommended voltage), at  $I_{\text{LOAD}}$  of 3.5 A and under no-load conditions. The SET events were monitored using two National Instruments™ (NI) PXIe-5172 scope card. The first 5172 scope was used to monitor and trigger from  $V_{\text{OUT}}$  using a window trigger around  $\pm 3\%$  from the nominal output voltage. The second 5172 scope was used to monitor and trigger from the Soft-Start (SS) at VIN-0.3 V, using a edge/positive trigger. Both scopes were mounted on a NI PXIe-1095 chassis. During SET testing, no  $V_{\text{OUT}}$  or SS transients or SS SETs were observed.

All equipment was controlled and monitored using a custom-developed LabVIEW™ program (PXI-RadTest) running on a HP-Z4™ desktop computer. The computer communicates with the PXI chassis through an MXI-Express cable and a NI PXIe-8381 remote control module. [Figure 6-1](#) shows a block diagram of the setup used for SEE testing of the TPS7H2211-SP. [Table 6-1](#) shows the connections, limits, and compliance values used during the testing. During the SEL testing the device was heated to 125°C by using a Closed-Loop PID controlled heat gun (MISTRAL 6 System (120-V, 2400-W)). For the SEB and SEGR testing, the device was tested at room temperature  $\approx 25^\circ\text{C}$ . For SET testing, the device was tested at room temperature (no cooling or heating was applied to the DUT). Die temperature was verified using a FLIR IR-camera prior to the SEE test campaign.

**Table 6-1. Equipment Set and Parameters Used for SEE Testing the TPS7H2211-SP**

Pin Name	Equipment Used	Capability	Compliance	Range of Values Used
VIN	Agilent N6766A PS (Channel #1)	50 A	10 A	4.5 to 14 V
EN	E36311A	—	0.1 A	4.5 and 5 V
Oscilloscope Card on SS	NI-PXIe 5172	100 MS/s	—	5 MS/s
Oscilloscope Card on $V_{\text{OUT}}$	NI-PXIe 5172	100 MS/s	—	5 MS/s

All boards used for SEE testing were fully checked for functionality. Dry runs were also performed to make sure that the test system was stable under all bias and load conditions prior to being taken to the TAMU facility. During the heavy-ion testing, the LabVIEW control program powered up the TPS7H2211-SP device and set the external sourcing and monitoring functions of the external equipment. After functionality and stability had been confirmed, the beam shutter was opened to expose the device to the heavy-ion beam. The shutter remained open until the target fluence was achieved (determined by external detectors and counters). During irradiation, the NI scope cards continuously monitored the signals. When the output voltage exceeds the pre-defined  $\pm 3\%$  window trigger, or when the PG signal changed from high to low (using a negative edge trigger), a data capture was initiated. In addition to monitoring the voltage levels of the two scopes, VIN current and the 5-V (beam on and off) signal from TAMU were monitored at all times. No sudden increases in current were observed (outside of normal fluctuations) on any of the test runs and indicated that no SEL events occurred during any of the tests.




Figure 6-1. Block Diagram of SEE Test Setup With the TPS7H2211-SP

## 7 Destructive Single-Event Effects (DSEE)

### 7.1 Single-Event Latch-Up (SEL) Results

During SEL characterization, the device was heated using forced hot air, maintaining the DUT temperature at 125°C. The die temperature was monitored prior to radiation using a FLIR IR-camera.

The species used for the SEL testing was Silver (<sup>109</sup>Ag) ion with an angle-of-incidence of 0° for an LET<sub>EFF</sub> = 48 MeV·cm<sup>2</sup>/mg. For more details, see [Depth, Range, and LET<sub>EFF</sub> Calculation](#). The kinetic energy in the vacuum is 1.634 GeV (15-MeV/amu line). Flux of approximately 10<sup>5</sup> ions/cm<sup>2</sup>·s and a fluence of approximately 10<sup>7</sup> ions/cm<sup>2</sup> were used for the three runs. Run duration to achieve this fluence was approximately 2 minutes (per 1 × 10<sup>7</sup> ions·cm<sup>2</sup>). The three devices were powered up and exposed to the heavy-ions using the maximum recommended voltage of 14 V and maximum load of 3.5 A. No SEL events were observed during all three runs, indicating that the TPS7H2211-SP is SEL-free. [Table 7-1](#) shows the SEL test conditions and results. [Figure 7-1](#) shows a typical plot of current versus time for an SEL testing.


**Table 7-1. Summary of TPS7H2211-SEP SEL Test Condition and Results**

For all runs, the device was loaded with a ≈ 3.5 amps load.

Run Number	Unit Number	Ion	LET <sub>EFF</sub> (MeV·cm <sup>2</sup> /mg)	Flux (ions·cm <sup>2</sup> /s)	Fluence (ions·cm <sup>2</sup> )	V <sub>IN</sub> (V)
1	1	<sup>109</sup> Ag	48	1.05 × 10 <sup>5</sup>	1.00 × 10 <sup>7</sup>	14
2	2	<sup>109</sup> Ag	48	1.00 × 10 <sup>5</sup>	1.00 × 10 <sup>7</sup>	14
3	3	<sup>109</sup> Ag	48	7.17 × 10 <sup>4</sup>	1.00 × 10 <sup>7</sup>	14

Using the MFTF method described in [SLVK047](#) and combining (or summing) the fluences of the eight runs at 125°C (7.99 × 10<sup>7</sup> ions·cm<sup>2</sup>), the upper-bound cross-section (using a 95% confidence level) is calculated as:

$$\sigma_{SEL} \leq 1.23 \times 10^{-7} \frac{cm^2}{device} \text{ for } LET_{EFF} = 48 \text{ MeV} \cdot \frac{cm^2}{mg} \text{ and } T = 125^\circ C \quad (1)$$



**Figure 7-1. Current vs Time for Run # 1 of the TPS7H2211-SEP at T = 125°C**

### 7.2 Single-Event Burnout (SEB) and Single-Event Gate Rupture (SEGR) Results

During the SEB/SEGR characterization, the device was tested at room temperature ≈ 25°C. The die temperature was verified using a FLIR IR-camera.

The species used for the SEB testing was a Silver (<sup>109</sup>Ag) ion with an angle-of-incidence of 0° for an LET<sub>EFF</sub> = 48 MeV·cm<sup>2</sup>/mg (for more details, see [Depth, Range, and LET<sub>EFF</sub> Calculation](#)). The kinetic energy in the vacuum for these ions is 1.634 GeV (15-MeV/amu line). Flux of approximately 10<sup>5</sup> ions/cm<sup>2</sup>·s and a fluence of

approximately  $10^7$  ions/cm<sup>2</sup> were used for the 6 runs. Run duration to achieve this fluence was approximately 2 minutes (per  $1 \times 10^7$  ions·cm<sup>2</sup>). The TPS7H2211-SP was tested under enabled and disabled modes. The device was disabled by forcing 0 V on the EN pin with an SMU. The E-Load was connected, even when the device was disabled, to help differentiate if an SET momentarily activated the device under the heavy-ion irradiation. During SEB and SEGR testing using the <sup>109</sup>Ag ion with the device *disabled/enabled* no V<sub>OUT</sub> transient or input current event was observed. This indicates that the TPS7H2211-SP is SEB and SEGR On-free, up to LET<sub>EFF</sub> = 48 MeV·cm<sup>2</sup>/mg. Table 7-2 shows the SEB test conditions and results. Figure 7-2 shows a plot of the current vs time for run 4 (enabled) and Figure 7-3 for run 5 (disabled).


**Table 7-2. Summary of TPS7H2211-SEP SEB Test Condition and Results**

For all runs the device was loaded with  $\approx 3.5$  amps.


Run Number	Unit Number	Ion	LET <sub>EFF</sub> (MeV·cm <sup>2</sup> /mg)	Flux (ions·cm <sup>2</sup> /s)	Fluence(ions·cm <sup>2</sup> )	V <sub>IN</sub> (V)	EN?
4	1	<sup>109</sup> Ag	48	$1.11 \times 10^5$	$1.00 \times 10^7$	14	Yes
5	1	<sup>109</sup> Ag	48	$1.00 \times 10^5$	$1.00 \times 10^7$	14	No
6	2	<sup>109</sup> Ag	48	$1.02 \times 10^5$	$1.00 \times 10^7$	14	Yes
7	2	<sup>109</sup> Ag	48	$1.03 \times 10^5$	$1.00 \times 10^7$	14	No
8	3	<sup>109</sup> Ag	48	$8.57 \times 10^4$	$1.00 \times 10^7$	14	Yes
9	3	<sup>109</sup> Ag	48	$1.20 \times 10^5$	$1.00 \times 10^7$	14	No

Using the MFTF method described in SLVK047 and combining (or summing) the fluences of the runs with the same categories as described on the columns the SEB/SEGR upper-bound cross-section (using a 95% confidence level) is calculated as:

$$\sigma_{SEB} \leq 6.15 \times 10^{-8} \frac{cm^2}{device} \text{ for } LET_{EFF} = 48 \text{ MeV} \cdot \frac{cm^2}{mg} \text{ and } T = 25^\circ C$$



**Figure 7-2. Current vs Time for Run # 4 (Enabled) for the TPS7H2211-SEP at T = 25°C**



**Figure 7-3. Current vs Time for Run # 5 (Disabled) for the TPS7H2211-SEP at T = 25°C**

## 8 Single-Event Transients (SET)

### 8.1 Single Event Transients

SETs are defined as heavy-ion-induced transients upsets on the  $V_{OUT}$  and the Soft-Start (SS) flag of the TPS7H2211-SP. SET testing was performed at room temperature (no external temperature control applied). The species used for the SET testing was Silver ( $^{109}\text{Ag}$ ) ion with an angle-of-incidence of  $0^\circ$  for an  $\text{LET}_{\text{EFF}} = 48$   $\text{MeV}\cdot\text{cm}^2/\text{mg}$  respectively, for more details, see [Depth, Range, and  \$\text{LET}\_{\text{EFF}}\$  Calculation](#). Flux of approximately  $10^5$  ions/ $\text{cm}^2\cdot\text{s}$  and a fluence of approximately  $10^7$  ions/ $\text{cm}^2$  were used for the 12 SET runs.

$V_{OUT}$  SETs were characterized using a window trigger of  $\pm 3\%$  around the nominal output voltage ( $\approx 4.5$  V and 14 V). The devices were characterized with input voltages ranging from  $V_{IN} = 4.5$  V (minimum) to  $V_{IN} = 14$  V (maximum). The output load was set to 3.5 Amps for each run by using a Chroma Load in Constant-Resistance (CR) mode. To capture the two NI-PXI-5172 scope cards of the SET, continuously monitoring the  $V_{OUT}$  and the SS were used, respectively. Each scope was operated independently. The output voltage was monitored by using the TP4 and the TP6 test points on the EVM, while the SS was monitored using the TP8 test point.

The scope triggering from  $V_{OUT}$  was programmed to record 20 k samples with a sample rate of 5-M samples per second (S/s) in case of a event (trigger). The scope triggering from SS was programmed with 30 ks and 5 MS/s. Both scopes were programmed to record 20% of the data before (pre) the trigger happened.

Not a single upset on  $V_{OUT}$  or SS was observed. [Table 8-1](#) lists the SET test condition and results for all the data.

**Table 8-1. Summary of TPS7H2211-SEP SET Test Condition and Results**

Run Number	Unit Number	Ion	$\text{LET}_{\text{EFF}}$ ( $\text{MeV}\cdot\text{cm}^2/\text{mg}$ )	Flux (ions· $\text{cm}^2/\text{s}$ )	Fluence (ions· $\text{cm}^2$ )	$V_{IN}$ (V)	Enabled	$V_{OUT_{\text{SET}} \geq  3\% }$ (Number) at 25 °C	$\text{SS}_{\text{SET}}$ (Number) at 25 °C	Load Type (Chroma)	Load Value
10	4	$^{109}\text{Ag}$	48	$6.91 \times 10^4$	$1.00 \times 10^7$	14	Yes	0	0	CR	3.5
11	4	$^{109}\text{Ag}$	48	$5.80 \times 10^4$	$1.00 \times 10^7$	14	Yes	0	0	N/A	0
12	4	$^{109}\text{Ag}$	48	$6.29 \times 10^4$	$1.00 \times 10^7$	12	Yes	0	0	CR	3.5
13	4	$^{109}\text{Ag}$	48	$5.51 \times 10^4$	$1.00 \times 10^7$	12	Yes	0	0	N/A	0
14	4	$^{109}\text{Ag}$	48	$5.10 \times 10^4$	$1.00 \times 10^7$	4.5	Yes	0	0	CR	3.5
15	4	$^{109}\text{Ag}$	48	$5.15 \times 10^4$	$1.00 \times 10^7$	4.5	Yes	0	0	N/A	0
16	5	$^{109}\text{Ag}$	48	$1.13 \times 10^5$	$1.00 \times 10^7$	14	Yes	0	0	CR	3.5
17	5	$^{109}\text{Ag}$	48	$1.13 \times 10^5$	$1.00 \times 10^7$	14	Yes	0	0	N/A	0
18	5	$^{109}\text{Ag}$	48	$1.18 \times 10^5$	$1.00 \times 10^7$	12	Yes	0	0	CR	3.5
19	5	$^{109}\text{Ag}$	48	$1.16 \times 10^5$	$1.00 \times 10^7$	12	Yes	0	0	N/A	0
20	5	$^{109}\text{Ag}$	48	$1.11 \times 10^5$	$1.00 \times 10^7$	4.5	Yes	0	0	CR	3.5
21	5	$^{109}\text{Ag}$	48	$1.37 \times 10^5$	$1.00 \times 10^7$	4.5	Yes	0	0	N/A	0

The upper-bound cross-section (using a 95% confidence level) is calculated by combining all runs above as:

$\sigma_{\text{SET}} \leq 3.07 \times 10^{-8}$   $\text{cm}^2/\text{device}$  for  $\text{LET}_{\text{EFF}} = 48$   $\text{MeV}\cdot\text{cm}^2/\text{mg}$  and  $T = 25^\circ\text{C}$ . Since no  $V_{OUT}$  or SS SETs were observed, this cross section is valid for both cases.

## 9 Event Rate Calculations

Event rates were calculated for LEO (ISS) and GEO environments by combining CREME96 orbital integral flux estimations and simplified SEE cross-sections according to methods described in [SLVK046](#). A minimum shielding configuration of 100 mils (2.54 mm) of aluminum, and *worst-week* solar activity (this is similar to a 99% upper bound for the environment) is assumed. Using the 95% upper-bounds for the SEL, SET, and the SEB and SEGR, is shown in [Table 9-1](#) and [Table 9-2](#) show the event rate calculation for the SEL, SET, and the SEB/SEGR, respectively.

**Table 9-1. SEL Event Rate Calculations for Worst-Week LEO and GEO Orbits**

The SEL Event Rate is for reference only as not a Single Unit during any Run showed a Latch-up event.

Orbit Type	Onset LET <sub>EFF</sub> (MeV-cm <sup>2</sup> /mg)	CREME96 Integral FLUX (/day/cm <sup>2</sup> )	σSAT (cm <sup>2</sup> )	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO (ISS)	48	4.50 × 10 <sup>-4</sup>	1.23 × 10 <sup>-7</sup>	5.54 × 10 <sup>-11</sup>	2.31 × 10 <sup>-3</sup>	4.95 × 10 <sup>7</sup>
GEO		1.48 × 10 <sup>-3</sup>		1.82 × 10 <sup>-10</sup>	7.56 × 10 <sup>-3</sup>	1.51 × 10 <sup>7</sup>

**Table 9-2. SEB/SEGR Event Rate Calculations for Worst-Week LEO and GEO Orbits**

The SEB Event Rate is for reference only as not a Single Unit during any Run showed a burnout event.

Orbit Type	Onset LET <sub>EFF</sub> (MeV-cm <sup>2</sup> /mg)	CREME96 Integral FLUX (/day/cm <sup>2</sup> )	σSAT (cm <sup>2</sup> )	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO (ISS)	48	4.50 × 10 <sup>-4</sup>	6.15 × 10 <sup>-8</sup>	2.77 × 10 <sup>-11</sup>	1.15 × 10 <sup>-3</sup>	9.90 × 10 <sup>7</sup>
GEO		1.48 × 10 <sup>-3</sup>		9.08 × 10 <sup>-11</sup>	3.78 × 10 <sup>-3</sup>	3.02 × 10 <sup>7</sup>

**Table 9-3. SET Event Rate Calculations for Worst-Week LEO and GEO Orbits**

Orbit Type	Onset LET <sub>EFF</sub> (MeV-cm <sup>2</sup> /mg)	CREME96 Integral FLUX (/day/cm <sup>2</sup> )	σSAT (cm <sup>2</sup> )	Event Rate (/day)	Event Rate (FIT)	MTBE (Years)
LEO (ISS)	48	4.50 × 10 <sup>-4</sup>	3.07 × 10 <sup>-8</sup>	1.38 × 10 <sup>-11</sup>	5.77 × 10 <sup>-4</sup>	1.98 × 10 <sup>8</sup>
GEO		1.48 × 10 <sup>-3</sup>		4.54 × 10 <sup>-11</sup>	1.89 × 10 <sup>-3</sup>	6.04 × 10 <sup>7</sup>

## 10 Summary

The purpose of this study was to characterize the effect of heavy-ion irradiation on the Single-Event-Effect (SEE) performance of the TPS7H2211-SEP load switch. Heavy-ions with  $LET_{EFF} = 48 \text{ MeV}\cdot\text{cm}^2/\text{mg}$  were used for the SEE test campaign. Flux of  $10^5 \text{ ions}/\text{cm}^2\cdot\text{s}$  and fluences  $10^7 \text{ ions}/\text{cm}^2$  per run were used for the characterization. The SEE results demonstrated that the TPS7H2211-SEP is SEL and SEB and SEGR (enable)-free up to  $LET_{EFF} = 48 \text{ MeV}\cdot\text{cm}^2/\text{mg}$ . The device is SET-free up to  $LET_{EFF} = 48 \text{ MeV}\cdot\text{cm}^2/\text{mg}$ . CREME96-based worst-week event-rate calculations for LEO (ISS) and GEO orbits are presented for reference.

**A**

## B References

1. M. Shoga and D. Binder, "Theory of Single Event Latchup in Complementary Metal-Oxide Semiconductor Integrated Circuits", *IEEE Trans. Nucl. Sci.*, Vol. 33(6), Dec. 1986, pp. 1714-1717.
2. G. Bruguier and J. M. Palau, "Single particle-induced latchup", *IEEE Trans. Nucl. Sci.*, Vol. 43(2), Mar. 1996, pp. 522-532.
3. G. H. Johnson, J. H. Hohl, R. D. Schrimpf and K. F. Galloway, "Simulating single-event burnout of n-channel power MOSFET's," in IEEE Transactions on Electron Devices, vol. 40, no. 5, pp. 1001-1008, May 1993.
4. J. R. Brews, M. Allenspach, R. D. Schrimpf, K. F. Galloway, J. L. Titus and C. F. Wheatley, "A conceptual model of a single-event gate-rupture in power MOSFETs," in IEEE Transactions on Nuclear Science, vol. 40, no. 6, pp. 1959-1966, Dec. 1993.
5. Texas Instruments, [Radiation Handbook for Electronics](#), e-book.
6. G. H. Johnson, R. D. Schrimpf, K. F. Galloway, and R. Koga, "Temperature dependence of single event burnout in n-channel power MOSFETs [for space application]," *IEEE Trans. Nucl. Sci.*, 39(6), Dec. 1992, pp. 1605-1612.
7. Cyclotron Institute, Texas A&M University, [Texas A&M University Cyclotron Institute Radiation Effects Facility](#), webpage.
8. James F. Ziegler, [SRIM- The Stopping and Range of Ions in Matter](#), webpage.
9. D. Kececioglu, "Reliability and Life Testing Handbook", Vol. 1, PTR Prentice Hall, New Jersey, 1993, pp. 186-193.
10. ISDE CRÈME-MC, Vanderbilt University, [ISDE CRÈME-MC](#), webpage.
11. A. J. Tylka, J. H. Adams, P. R. Boberg, et al., "CREME96: A Revision of the Cosmic Ray Effects on Micro-Electronics Code", *IEEE Trans. on Nucl. Sci.*, Vol. 44(6), Dec. 1997, pp. 2150-2160.
12. A. J. Tylka, W. F. Dietrich, and P. R. Boberg, "Probability distributions of high-energy solar-heavy-ion fluxes from IMP-8: 1973-1996", *IEEE Trans. on Nucl. Sci.*, Vol. 44(6), Dec. 1997, pp. 2140-2149.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2023, Texas Instruments Incorporated