LM317A-337N-EVM

User's Guide



Literature Number: SNLU193 January 2016



Contents

1	Introduction					
	1.1	Features	3			
2	Setu	ıp	4			
	2.1	Input/Output Connector Description				
	2.2	Test Point Description	4			
	2.3	Board Setup	3 4 4 4 4 4 6 6 8 10			
		2.3.1 How to Set the Output Voltage				
		2.3.2 Evaluation	4			
3	Operation					
	3.1	•				
	3.2	Negative Input Power-Up and Power-Down (SOT-223)	8			
4	Boa	rd Layout 1	0			
5	Sch	ematic 1				
6	Rela	ted Documentation	4			



Introduction

The Texas Instruments LM317A-337N-EVM evaluation module (EVM) helps designers operate and understand the LM317A 3-Terminal Adjustable Regulator and LM337-N 3-Terminal Adjustable Negative Regulator. The board is assembled with the SOT-223 package option for both devices. This user guide is meant to provide guidance and examples in order to understand how the EVM can be used to test the LM317A and LM337-N. For more information about the functional and electrical characteristics of these devices, consult the LM317A (SNVSAC2) and LM337-N (SNVS778) data sheets.

The EVM contains footprints for two package options of the LM317A adjustable positive regulator and the LM337-N adjustable negative regulator. (See Table 1-1.)

REF DESIGNATOR IC PACKAGE **OUTPUT CURRENT** U1 LM317AEMP/NOPB SOT-223 1.0 A U2 LM317AT/NOPB TO-220 1.5 A U3 LM337T/NOPB TO-220 – 1.5 A SOT-223 U4 LM337IMP/NOPB – 1.5 A

Table 1-1. Device and Package Configurations

1.1 Features

- Output voltage adjustable from 1.2 V to 37 V for LM317A and −1.2 V to −37 V for LM337-N
- U2 and U3 footprints for TO-220 option evaluation
- Heat sink footprint space for TO-220
- Large input/output capacitor footprints for customization
- Board size: 3.5" x 3.5"



Setup

This section describes the connectors and test points on the EVM as well as how to properly connect, set up, and use the LM317A-337N-EVM. Ensure the external power supply is turned off while making connections on the board.

2.1 Input/Output Connector Description

- **VBAT+** is the positive input voltage supply for the LM317A.
- VBAT- is the negative input voltage supply for the LM337-N.
- **VOUT+** is the positive output voltage regulated by the LM317A.
- **VOUT-** is the negative output voltage regulated by the LM337-N.
- **GND** is the ground in which all other voltages on the EVM are referenced to. Ground banana jacks are placed on both the input and output side of the EVM.

2.2 Test Point Description

- **TP1 VIN+** is the input to the LM317A.
- TP2 ADJ+ is the adjustment pin of the LM317A.
- TP3 VOUT+ is the output of the LM317A.
- **TP4 VIN-** is the input to the LM337-N.
- TP5 ADJ- is the adjustment pin of the LM337-N.
- TP6 VOUT- is the output of the LM337-N.
- **TP7 GND** is the ground rail of the EVM.

2.3 Board Setup

2.3.1 How to Set the Output Voltage

Both the LM317A and LM337-N are designed to sustain a nominal 1.25-V reference voltage VREF. Details can be found on the data sheets, but most importantly the output voltage for the LM317A is given by Equation 1.

$$V_{OIIT+} = V_{RFF} (1 + R3/R1) + (I_{ADI} \times R3)$$
 (1)

The output voltage for the LM337-N is given by Equation 2.

$$V_{OUT} = -V_{REF} (1 + R4/R2) + (-I_{ADJ} \times R4)$$
 (2)

 I_{ADJ} is the current flowing out of the adjustment pin. The EVM will be populated according to a ± 5 -V output voltage, but the user can change this according to their needs.

It should be carefully noted that a minimum load current should be established to keep the device under regulation.

2.3.2 Evaluation

Before applying power to the LM317A-337N-EVM, all external connections should be verified. The nominal operating conditions that have been tested for the purpose of evaluation are shown in Table 2-1.



Board Setup www.ti.com

Important Note: If operation outside Table 2-1 is tested, then proper care should be taken to limit the power dissipation across the LM317A and LM337-N so that its absolute maximum ratings are not exceeded. Thermal management techniques such as heatsinks and airflow should be used in cases of high power dissipation.

CONNECTOR NAME	VOLTAGE
VBAT+	8 V

Table 2-1. Nominal Operating Conditions

VOLTAGE
8 V
-8 V
5 V
–5 V
500 mA
–500 mA
1.5 W

To begin evaluation of the LM317A, an external power supply should be turned off and connected with proper polarity to the VBAT+ and GND connectors. The VIN+ (TP1) test point can be used to measure the positive input while the VOUT+ (TP3) test point can be measure the positive output. The ADJ+ (TP2) test point can be used to measure the adjustment pin of the LM317A.

To evaluate the LM337-N, an external power supply should be turned off and connected with proper polarity to VBAT- and GND. The VIN- (TP4) test point is used to measure the negative input, while the VOUT- (TP6) test point is used to measure the negative output. The ADJ- (TP5) test point can be used to measure the adjustment pin of the LM337-N.

Furthermore, the LM317A-337N-EVM provides solder space for a wide range of input and output capacitors. Specifically, there is space for electrolytic and ceramic capacitors. At the output, R5 and R6 resistor footprints are provided to add ESR for ceramics. Stock component values can be found on the schematic (Figure 5-1).

The board also contains footprint space for a TO-220 heat sink, which will aid in heat dissipation for high power applications. A recommended heat sink is provided in the Bill of Materials section.

Once all connections and components on the LM317A-337N-EVM have been verified, power can be applied to VBAT+ and/or VBAT-, and evaluation can begin.



Operation

For the following operation examples, we use the Nominal Operating Conditions as described in Table 2-1, with only stock components populated:

- Input capacitors C1 and C2 with a value of 22 µF
- Resistors R1 and R2 with a value of 240 Ω
- Resistors R3 and R4 with a value of 715 Ω
- Adjustment capacitors C5 and C6 with a value of 10 µF
- Output capacitors C3 and C4 with a value of 22 µF

3.1 Positive Input Power-Up and Power-Down (SOT-223)

In a typical application of the LM317A, a desired positive output voltage is set by selecting the resistor divider, and the linear regulator will regulate the output to a constant voltage. Linear regulators like the LM317A span a wide range of applications, all including some form of power management. In this section, the following conditions are used: input voltage = 8 V, output voltage = 5 V, load = 500 mA, and IC power dissipation = 1.5 W.




Figure 3-1. Positive Input Power-Up

6






Figure 3-2. Positive Input Power-Down




Figure 3-3. LM317A Thermal Image (After 5-min Run Time at 1.5 W)



3.2 Negative Input Power-Up and Power-Down (SOT-223)

The LM337-N provides regulation of a negative voltage at the output if the input-output differential is above the dropout voltage, and the input is within the operating range. The LM337-N finds use in applications that involve providing a reliable negative rail, such as in bipolar amplifier circuits and op amps. In this section, the following conditions are used: input voltage = -8 V, output voltage = -5 V, load = -500 mA, and IC power dissipation = 1.5 W.




Figure 3-4. Negative Input Power-Up




Figure 3-5. Negative Input Power-Down





Figure 3-6. LM337-N Thermal Image (after 5 min run time @ 1.5W)



Board Layout

Figure 4-1, Figure 4-2 and Figure 5-1 show the board layout for the LM317A-337N-EVM. Please note C7, C8, R5, R6, S1, and S2 will be left unpopulated. If the TO-220 package options for the LM317A and LM337-N are to be evaluated, then remove U1 and U4, and populate U3 and U2 along with the heatsinks.




Figure 4-1. Top Layer Layout






Figure 4-2. Bottom Layer Layout



Schematic




Figure 5-1. LM317N-LM337N10EVM Schematic



www.ti.com

Table 5-1. LM317N-LM337N10EVM Bill of Materials

DESIGNATOR	QTY	VALUE	DESCRIPTION	PACKAGE REFERENCE	PART NUMBER	MANUFACTURER
!PCB	1		Printed Circuit Board		SV601211	Any
C1, C2, C3, C4	4	22 μF	CAP, AL, 22 μF, 50 V, ±20%, 0.88 ohm, SMD	SMT Radial D	EEE- FK1H220P	Panasonic
C5, C6	2	10 μF	CAP, CERM, 10 μF, 50 V, ±10%, X7R, 1210	1210	GRM32ER7 1H106KA12 L	MuRata
D1, D2, D3, D4	4	400 V	Diode, Ultrafast, 400 V, 1 A, SMB	SMB	MURS140- 13-F	Diodes Inc.
H1, H2, H3, H4	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw	NY PMS 440 0025 PH	B&F Fastener Supply
H5, H6, H7, H8	4		Standoff, Hex, 0.5"L #4-40 Nylon	Standoff	1902C	Keystone
J1, J2, J3, J4	4		Standard Banana Jack, Insulated, Red	6091	6091	Keystone
J5, J6	2		Standard Banana Jack, Insulated, Black	6092	6092	Keystone
LBL1	1		Thermal Transfer Printable Labels, 1.250" W x 0.250" H - 10,000 per roll	PCB Label 1.25"H x 0.250"W	THT-13- 457-10	Brady
R1, R2	2		RES, 240, 5%, 0.25 W, 1206	1206	CRCW1206 240RJNEA	Vishay-Dale
R3, R4	2		RES, 715, 1%, 0.25 W, 1206	1206	CRCW1206 715RFKEA	Vishay-Dale
TP1, TP2, TP3, TP4, TP5, TP6, TP7	7	White	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint	5012	Keystone
U1	1		3-Terminal Adjustable Regulator, 4- pin SOT-223, Pb-Free	MP04A	LM317AEM P/NOPB	Texas Instruments
U4	1		3-Terminal Adjustable Negative Regulator, 4-pin SOT-223, Pb-Free	MP04A	LM337IMP/ NOPB	Texas Instruments
C7, C8, C9, C10	0	10 μF	CAP, CERM, 10 μF, 50 V, ±20%, X7R, 2220	2220	C5750X7R1 H106M	TDK
FID1, FID2, FID3	0		Fiducial mark. There is nothing to buy or mount.	Fiducial	_	_
R5, R6	0	1	RES, 1.0, 5%, 0.25 W, 1206	1206	CRCW1206 1R00JNEA	Vishay-Dale
S1, S2	0		Heat Sink, TO-220, Vertical	Heat Sink, TO- 220, Vertical	FA-T220- 38E	Ohmite
U2	0		3-Terminal Adjustable Regulator, 3- pin TO-220, Pb-Free	T03B	LM317AT/N OPB	Texas Instruments
U3	0		3-Terminal Adjustable Negative Regulator, 3-pin TO-220, Pb-Free	T03B	LM337T/NO PB	Texas Instruments



Related Documentation

- LM317A 3-Terminal Adjustable Positive Regulator data sheet (SNVSAC2)
- LM337-N 3-Terminal Adjustable Negative Regulator data sheet (SNVS778)

STANDARD TERMS AND CONDITIONS FOR EVALUATION MODULES

- 1. Delivery: TI delivers TI evaluation boards, kits, or modules, including any accompanying demonstration software, components, or documentation (collectively, an "EVM" or "EVMs") to the User ("User") in accordance with the terms and conditions set forth herein. Acceptance of the EVM is expressly subject to the following terms and conditions.
 - 1.1 EVMs are intended solely for product or software developers for use in a research and development setting to facilitate feasibility evaluation, experimentation, or scientific analysis of TI semiconductors products. EVMs have no direct function and are not finished products. EVMs shall not be directly or indirectly assembled as a part or subassembly in any finished product. For clarification, any software or software tools provided with the EVM ("Software") shall not be subject to the terms and conditions set forth herein but rather shall be subject to the applicable terms and conditions that accompany such Software
 - 1.2 EVMs are not intended for consumer or household use. EVMs may not be sold, sublicensed, leased, rented, loaned, assigned, or otherwise distributed for commercial purposes by Users, in whole or in part, or used in any finished product or production system.
- 2 Limited Warranty and Related Remedies/Disclaimers:
 - 2.1 These terms and conditions do not apply to Software. The warranty, if any, for Software is covered in the applicable Software License Agreement.
 - 2.2 TI warrants that the TI EVM will conform to TI's published specifications for ninety (90) days after the date TI delivers such EVM to User. Notwithstanding the foregoing, TI shall not be liable for any defects that are caused by neglect, misuse or mistreatment by an entity other than TI, including improper installation or testing, or for any EVMs that have been altered or modified in any way by an entity other than TI. Moreover, TI shall not be liable for any defects that result from User's design, specifications or instructions for such EVMs. Testing and other quality control techniques are used to the extent TI deems necessary or as mandated by government requirements. TI does not test all parameters of each EVM.
 - 2.3 If any EVM fails to conform to the warranty set forth above, Tl's sole liability shall be at its option to repair or replace such EVM, or credit User's account for such EVM. Tl's liability under this warranty shall be limited to EVMs that are returned during the warranty period to the address designated by Tl and that are determined by Tl not to conform to such warranty. If Tl elects to repair or replace such EVM, Tl shall have a reasonable time to repair such EVM or provide replacements. Repaired EVMs shall be warranted for the remainder of the original warranty period. Replaced EVMs shall be warranted for a new full ninety (90) day warranty period.
- 3 Regulatory Notices:
 - 3.1 United States
 - 3.1.1 Notice applicable to EVMs not FCC-Approved:

This kit is designed to allow product developers to evaluate electronic components, circuitry, or software associated with the kit to determine whether to incorporate such items in a finished product and software developers to write software applications for use with the end product. This kit is not a finished product and when assembled may not be resold or otherwise marketed unless all required FCC equipment authorizations are first obtained. Operation is subject to the condition that this product not cause harmful interference to licensed radio stations and that this product accept harmful interference. Unless the assembled kit is designed to operate under part 15, part 18 or part 95 of this chapter, the operator of the kit must operate under the authority of an FCC license holder or must secure an experimental authorization under part 5 of this chapter.

3.1.2 For EVMs annotated as FCC - FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant:

CAUTION

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- · Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

3.2 Canada

3.2.1 For EVMs issued with an Industry Canada Certificate of Conformance to RSS-210

Concerning EVMs Including Radio Transmitters:

This device complies with Industry Canada license-exempt RSS standard(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concernant les EVMs avec appareils radio:

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes: (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concerning EVMs Including Detachable Antennas:

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication. This radio transmitter has been approved by Industry Canada to operate with the antenna types listed in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotrope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante. Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur

3.3 Japan

- 3.3.1 Notice for EVMs delivered in Japan: Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_01.page 日本国内に輸入される評価用キット、ボードについては、次のところをご覧ください。
 http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_01.page
- 3.3.2 Notice for Users of EVMs Considered "Radio Frequency Products" in Japan: EVMs entering Japan may not be certified by TI as conforming to Technical Regulations of Radio Law of Japan.

If User uses EVMs in Japan, not certified to Technical Regulations of Radio Law of Japan, User is required by Radio Law of Japan to follow the instructions below with respect to EVMs:

- Use EVMs in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
- 2. Use EVMs only after User obtains the license of Test Radio Station as provided in Radio Law of Japan with respect to EVMs, or
- 3. Use of EVMs only after User obtains the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to EVMs. Also, do not transfer EVMs, unless User gives the same notice above to the transferee. Please note that if User does not follow the instructions above, User will be subject to penalties of Radio Law of Japan.

【無線電波を送信する製品の開発キットをお使いになる際の注意事項】 開発キットの中には技術基準適合証明を受けていないものがあります。 技術適合証明を受けていないもののご使用に際しては、電波法遵守のため、以下のいずれかの措置を取っていただく必要がありますのでご注意ください。

- 1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用 いただく。
- 2. 実験局の免許を取得後ご使用いただく。
- 3. 技術基準適合証明を取得後ご使用いただく。
- なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。 上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。 日本テキサス・イ

東京都新宿区西新宿6丁目24番1号

西新宿三井ビル

ンスツルメンツ株式会社

- 3.3.3 Notice for EVMs for Power Line Communication: Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_02.page
 電力線搬送波通信についての開発キットをお使いになる際の注意事項については、次のところをご覧ください。http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_02.page
- 4 EVM Use Restrictions and Warnings:
 - 4.1 EVMS ARE NOT FOR USE IN FUNCTIONAL SAFETY AND/OR SAFETY CRITICAL EVALUATIONS, INCLUDING BUT NOT LIMITED TO EVALUATIONS OF LIFE SUPPORT APPLICATIONS.
 - 4.2 User must read and apply the user guide and other available documentation provided by TI regarding the EVM prior to handling or using the EVM, including without limitation any warning or restriction notices. The notices contain important safety information related to, for example, temperatures and voltages.
 - 4.3 Safety-Related Warnings and Restrictions:
 - 4.3.1 User shall operate the EVM within TI's recommended specifications and environmental considerations stated in the user guide, other available documentation provided by TI, and any other applicable requirements and employ reasonable and customary safeguards. Exceeding the specified performance ratings and specifications (including but not limited to input and output voltage, current, power, and environmental ranges) for the EVM may cause personal injury or death, or property damage. If there are questions concerning performance ratings and specifications, User should contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may also result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM user guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, even with the inputs and outputs kept within the specified allowable ranges, some circuit components may have elevated case temperatures. These components include but are not limited to linear regulators, switching transistors, pass transistors, current sense resistors, and heat sinks, which can be identified using the information in the associated documentation. When working with the EVM, please be aware that the EVM may become very warm.
 - 4.3.2 EVMs are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems. User assumes all responsibility and liability for proper and safe handling and use of the EVM by User or its employees, affiliates, contractors or designees. User assumes all responsibility and liability to ensure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard. User assumes all responsibility and liability for any improper or unsafe handling or use of the EVM by User or its employees, affiliates, contractors or designees.
 - 4.4 User assumes all responsibility and liability to determine whether the EVM is subject to any applicable international, federal, state, or local laws and regulations related to User's handling and use of the EVM and, if applicable, User assumes all responsibility and liability for compliance in all respects with such laws and regulations. User assumes all responsibility and liability for proper disposal and recycling of the EVM consistent with all applicable international, federal, state, and local requirements.
- 5. Accuracy of Information: To the extent TI provides information on the availability and function of EVMs, TI attempts to be as accurate as possible. However, TI does not warrant the accuracy of EVM descriptions, EVM availability or other information on its websites as accurate, complete, reliable, current, or error-free.

6. Disclaimers:

- 6.1 EXCEPT AS SET FORTH ABOVE, EVMS AND ANY WRITTEN DESIGN MATERIALS PROVIDED WITH THE EVM (AND THE DESIGN OF THE EVM ITSELF) ARE PROVIDED "AS IS" AND "WITH ALL FAULTS." TI DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, REGARDING SUCH ITEMS, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF ANY THIRD PARTY PATENTS, COPYRIGHTS, TRADE SECRETS OR OTHER INTELLECTUAL PROPERTY RIGHTS.
- 6.2 EXCEPT FOR THE LIMITED RIGHT TO USE THE EVM SET FORTH HEREIN, NOTHING IN THESE TERMS AND CONDITIONS SHALL BE CONSTRUED AS GRANTING OR CONFERRING ANY RIGHTS BY LICENSE, PATENT, OR ANY OTHER INDUSTRIAL OR INTELLECTUAL PROPERTY RIGHT OF TI, ITS SUPPLIERS/LICENSORS OR ANY OTHER THIRD PARTY, TO USE THE EVM IN ANY FINISHED END-USER OR READY-TO-USE FINAL PRODUCT, OR FOR ANY INVENTION, DISCOVERY OR IMPROVEMENT MADE, CONCEIVED OR ACQUIRED PRIOR TO OR AFTER DELIVERY OF THE EVM
- 7. USER'S INDEMNITY OBLIGATIONS AND REPRESENTATIONS. USER WILL DEFEND, INDEMNIFY AND HOLD TI, ITS LICENSORS AND THEIR REPRESENTATIVES HARMLESS FROM AND AGAINST ANY AND ALL CLAIMS, DAMAGES, LOSSES, EXPENSES, COSTS AND LIABILITIES (COLLECTIVELY, "CLAIMS") ARISING OUT OF OR IN CONNECTION WITH ANY HANDLING OR USE OF THE EVM THAT IS NOT IN ACCORDANCE WITH THESE TERMS AND CONDITIONS. THIS OBLIGATION SHALL APPLY WHETHER CLAIMS ARISE UNDER STATUTE, REGULATION, OR THE LAW OF TORT, CONTRACT OR ANY OTHER LEGAL THEORY, AND EVEN IF THE EVM FAILS TO PERFORM AS DESCRIBED OR EXPECTED.
- 8. Limitations on Damages and Liability:
 - 8.1 General Limitations. IN NO EVENT SHALL TI BE LIABLE FOR ANY SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL, OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THESE TERMS ANDCONDITIONS OR THE USE OF THE EVMS PROVIDED HEREUNDER, REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. EXCLUDED DAMAGES INCLUDE, BUT ARE NOT LIMITED TO, COST OF REMOVAL OR REINSTALLATION, ANCILLARY COSTS TO THE PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES, RETESTING, OUTSIDE COMPUTER TIME, LABOR COSTS, LOSS OF GOODWILL, LOSS OF PROFITS, LOSS OF SAVINGS, LOSS OF USE, LOSS OF DATA, OR BUSINESS INTERRUPTION. NO CLAIM, SUIT OR ACTION SHALL BE BROUGHT AGAINST TI MORE THAN ONE YEAR AFTER THE RELATED CAUSE OF ACTION HAS OCCURRED.
 - 8.2 Specific Limitations. IN NO EVENT SHALL TI'S AGGREGATE LIABILITY FROM ANY WARRANTY OR OTHER OBLIGATION ARISING OUT OF OR IN CONNECTION WITH THESE TERMS AND CONDITIONS, OR ANY USE OF ANY TI EVM PROVIDED HEREUNDER, EXCEED THE TOTAL AMOUNT PAID TO TI FOR THE PARTICULAR UNITS SOLD UNDER THESE TERMS AND CONDITIONS WITH RESPECT TO WHICH LOSSES OR DAMAGES ARE CLAIMED. THE EXISTENCE OF MORE THAN ONE CLAIM AGAINST THE PARTICULAR UNITS SOLD TO USER UNDER THESE TERMS AND CONDITIONS SHALL NOT ENLARGE OR EXTEND THIS LIMIT.
- 9. Return Policy. Except as otherwise provided, TI does not offer any refunds, returns, or exchanges. Furthermore, no return of EVM(s) will be accepted if the package has been opened and no return of the EVM(s) will be accepted if they are damaged or otherwise not in a resalable condition. If User feels it has been incorrectly charged for the EVM(s) it ordered or that delivery violates the applicable order, User should contact TI. All refunds will be made in full within thirty (30) working days from the return of the components(s), excluding any postage or packaging costs.
- 10. Governing Law: These terms and conditions shall be governed by and interpreted in accordance with the laws of the State of Texas, without reference to conflict-of-laws principles. User agrees that non-exclusive jurisdiction for any dispute arising out of or relating to these terms and conditions lies within courts located in the State of Texas and consents to venue in Dallas County, Texas. Notwithstanding the foregoing, any judgment may be enforced in any United States or foreign court, and TI may seek injunctive relief in any United States or foreign court.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity