

# Implementing a Direct Thermocouple Interface With the MSP430F4xx and ADS1240

MSP430 Applications

#### **ABSTRACT**

This application report describes how to implement a direct thermocouple interface without using the signal conditioning circuitry normally required for thermocouples. The thermocouple interfaces directly to the ADS1240 24-bit analog-to-digital converter (ADC). An MSP430F413 ultra-low-power microcontroller (MCU) is used to communicate with the ADC, read the conversion values, convert them to temperature, and display them on an LCD. Although an MSP430F413 is used for this application report, any MSP430<sup>™</sup> MCU could be used to implement this application.

This document includes a complete schematic and code listing. The code can also be downloaded from <a href="http://www.ti.com/lit/zip/slaa125">http://www.ti.com/lit/zip/slaa125</a>.

#### Contents

1		duction	
2	Theri	mocouples	2
3	Appli	cation Circuit	3
4		ementation and Code Details	
	4.1	Initialization and Setup	5
	4.2	Mainloop	
	4.3	ReadTC and ReadTR Routines	
	4.4	Get_TR_Temp – Determining the Thermistor Temperature	6
	4.5	Get_TC_Temp – Determining the Thermocouple's Relative Temperature	
	4.6	Get_ABS_Temp – Determining the Absolute Temperature	
	4.7	DISPLCD – Display the Absolute Temperature on the LCD	
5	Circu	iit Schematic	8
6	Application Code		
7	Conclusion		
8	References		

#### **Trademarks**

MSP430 is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.



Introduction www.ti.com

#### 1 Introduction

Thermocouples typically require signal conditioning to amplify the thermocouple voltage into the ADC range and to provide any offset that is required. This application report describes how a high-resolution ADC, such as the 24-bit ADS1240, can be used to implement a direct thermocouple interface without the need for signal conditioning. The thermocouple is connected directly to the inputs of the ADC. An MSP430F413 MCU communicates with the ADS1240 to read the ADC values, convert the ADC values into temperature, and display the temperature on the LCD. For this application report, a type K thermocouple was used, and the temperature range was limited to 0°C to 99.9°C.

#### 2 Thermocouples

Thermocouples are constructed of two dissimilar metals welded at one end. They produce a voltage at the nonwelded end that is relative to the temperature difference between the two ends of the thermocouple. There are many types of thermocouples and much has been written on thermocouples and thermocouple usage. A simple search on the Internet can provide a host of useful information for anyone wanting to learn the intricate details of thermocouples and thermocouple usage that are not covered in this report.

The voltage produced by thermocouples depends on the temperature difference between the ends of the thermocouple. It is not enough to simply measure the voltage to determine the temperature. That measurement gives only the temperature difference between the two ends of the thermocouple. The temperature of the cold junction (the connection of the thermocouple to the measuring device) affects the voltage produced at the thermocouple end. As a result, some type of cold junction compensation is required. Often, circuits are employed to produce a voltage proportional to the cold junction temperature. This voltage is injected into the circuit and is part of the typical thermocouple signal conditioning circuitry.

Another technique of cold junction compensation involves measuring the temperature of the junction with a thermistor or some other type of temperature sensor. This is the technique employed in this report. In this technique, the temperature of the welded end of the thermocouple can be determined from knowing the cold junction temperature and measuring the thermocouple voltage. For accurate results, this technique requires the use of an isothermal block to assure the temperature of the cold junction temperature sensor is the same as the temperature of the cold junction.

The voltage that thermocouples produce is standardized by the National Institute of Standards and Technology. Data tables for thermocouple voltages are available from the NIST.



www.ti.com Application Circuit

## 3 Application Circuit

Figure 1 shows the circuit diagram for the circuit used in this application report. Section 5 includes a complete schematic.




Figure 1. Circuit Diagram

- A thermistor is used to provide cold junction compensation.
- Several pins from port P1 on the MSP430F413 are used to implement serial communication with the ADS1240.
- A voltage divider is used to bias the negative terminal of the thermocouple.
- The ADS1240 is clocked from the MCLK output of the MSP430F413.
- The clock frequency is set at 1.5 MHz.



## 4 Implementation and Code Details

Figure 2 shows the program flow. The following sections describe this program flow.




Figure 2. Program Flow



## 4.1 Initialization and Setup

The MSP430F413 and the ADS1240 are both initialized after a reset. On the MSP430F413, the watchdog timer is disabled. The FLL+ and DCO are configured to generate an MCLK of 1.507 MHz. This frequency is used for the CPU and is used externally to clock the ADS1240. This frequency was chosen for the ADS1240 because it is fast enough for the application but allows some power savings over the nominal 2.4576-MHz reference in the ADS1240 data sheet. The Basic Timer and LCD modules are configured for the LCD, and the LCD memory is cleared. The I/O ports are configured for desired function, direction and interrupt edge. The unused I/O ports are set to the output direction. A delay is implemented before calling the ADC setup routine. The delay allows the FLL+ time to adjust the DCO to the desired frequency of 1.507 MHz. For more information on the FLL+, DCO, or any other MSP430F413 peripheral, refer to the MSP430x4xx Family User's Guide. For more information on the MSP430F41x devices, see the MSP430x41x Mixed-Signal Microcontrollers data sheet.

To setup the ADS1240, a reset command is issued first. Then the input multiplexer is set for channel 0 and 1 for the plus and minus inputs, respectively. These are for the plus and minus sides of the thermocouple. The data rate is selected for the ADS1240 as the slowest it offers. This results in approximately 2.3 conversions per second, rather than the 3.75 listed in the data sheet, because the values in the data sheet assume a clock of 2.4576 MHz, but this application uses a clock of 1.5 MHz. When writing to successive registers of the ADS1240, it is not necessary to send the WREG command each time (see the ADS1240 24-Bit Analog-to-Digital Converters data sheet for more details).

Interrupts are enabled on the MSP430F413, and the SELFGCAL command is issued to the ADS1240. The SELFGCAL command works best when the PGA = 1, and it requires some time to complete. The DRDY line of the ADS1240 goes low to signal the completion of the SELFGCAL process. Interrupts are enabled on the MSP430F413 to allow the MSP430F413 to enter low-power mode 0 (LPM0) while the SELFGCAL process is being executed and to be interrupted by the ADS1240 when the process completes. Finally, the programmable gain amplifier (PGA) is set to a gain of 16 and the SELFOCAL command is issued. For more information on the ADS1240, refer to the ADS1240 24-Bit Analog-to-Digital Converters data sheet.

#### 4.2 Mainloop

The mainloop is a succession of calls to other routines with a statements to enter LPM0. The first instruction of the mainloop puts the MSP430F413 into LPM0. The MSP430F413 stays in LPM0 until the DRDY line from the ADS1240 goes low, signaling that data is ready to be read. When the DRDY line goes low, the MSP430F413 receives the P1.0 interrupt and awakens to service it. The interrupt service routine then clears the appropriate status register bits so the MSP430F413 returns from the interrupt in active mode. Next, a call is made to the routine that reads the ADS1240. This value is for the thermocouple. Upon return from that routine, the MSP430F413 is again put into LPM0 to wait for the next DRDY. After the next DRDY, the ADS1240 is ready to be read again, so a call is made to the routine to read the thermistor value (see Figure 2). Upon return from reading the thermistor value, the MSP430F413 is ready to determine the temperature. Interrupts are disabled and calls are made to routines that convert the thermistor and thermocouple ADC values into their respective temperatures and then a call is made to determine the absolute temperature based on the thermistor and thermocouple temperatures. After the temperatures are determined, interrupts are re-enabled and a call is made to display the absolute temperature on the LCD. Then the mainloop starts over.

## 4.3 ReadTC and ReadTR Routines

The ReadTC and ReadTR routines read the thermocouple and thermistor values, respectively, from the ADS1240. Each routine sends the RDATA command and then clocks the data out of the ADS1240. Then, each routine sets up the PGA and multiplexer settings of the ADS1240 for the next conversion. The routine to read the thermocouple value sets up the ADS1240 to perform a conversion on the thermistor. The thermistor ADC value is then available at the next assertion of DRDY. Likewise, the routine to read the thermistor value sets up the ADS1240 to perform a conversion on the thermocouple.



## 4.4 Get\_TR\_Temp - Determining the Thermistor Temperature

To read the thermistor in this application a resistor divider is formed with a  $10\text{-k}\Omega$  resistor and  $10\text{-k}\Omega$  thermistor. The top of divider is connected to the reference and bottom to ground. This provides a voltage input to the ADC that varies with temperature. Thermistor values decrease as temperature increases, so the voltage from this divider decreases with temperature as well (see Figure 1). Perhaps a more common way of measuring a thermistor is with a slope analog-to-digital conversion. A slope conversion was not employed in this application, because a high-performance precision ADC was already available, and performing the slope analog-to-digital conversion would have unnecessarily complicated the application and the code. A complete application report with code examples are available to show how to perform a slope analog-to-digital conversion with the MSP430F4xx MCUs (see the MSP430 Based Digital Thermometer application report).

To determine the thermistor temperature from the ADC value, first a table lookup is performed to determine the temperature to the nearest degree. Then, an interpolation is done to determine the temperature to the nearest tenth of a degree. To do this, first the nearest whole degree temperature is multiplied by 10 and saved to RAM. Then, the tenths are determined from Equation 1.

$$\frac{\text{(higher - ADC value)} \times 10}{\text{higher - lower}}$$

where

- ADCvalue = ADC conversion value of thermistor voltage
- higher = the next higher value in the table
- lower = the next lower value in the table (1)

After the tenths are interpolated, they are added to the nearest whole temperature that was multiplied by ten previously. Now the thermistor temperature is stored in the form of XX.X in binary format.

The table of thermistor values shown in the code in Section 6 is specific to this application. This table uses measured values for the  $10-k\Omega$  resistor and for the ADC reference and uses only 16 of the 24 ADC bits. Equation 2 shows the general formula for computing the table.

ADC value = 
$$hex \left( 2^{N} \times \frac{voltage}{2 \times Vref} \right)$$

where

- N = Desired resolution of the analog-to-digital conversion (the ADS1240 is a 24-bit ADC, but for this application only the upper 16 bits are used, so in this case, N is 16).
- voltage = Resulting voltage from the voltage divider

For this application, Equation 3 shows the equation for the voltage divider.

$$voltage = \frac{V \times Rt}{Rt + 10k}$$

where

- Rt = Thermistor resistance
- V = Voltage source for the divider Vref in this application

Combining the two equations results in Equation 4.

ADC value = hex 
$$\left[ \left( \frac{2^{N}}{2 \times \text{Vref}} \right) \left( \frac{\text{Vref} \times \text{Rt}}{\text{Rt} + 10 \text{k}} \right) \right]$$
 (4)

Which reduces to Equation 5.

ADC value = hex 
$$\left(\frac{2^{N-1} \times Rt}{Rt + 10k}\right)$$
 (5)

(3)



## 4.5 Get TC Temp – Determining the Thermocouple's Relative Temperature

Converting a thermocouple voltage measurement into temperature can sometimes be a difficult task, depending on the application, because of the nonlinearity of thermocouples. However, this application report simplifies the task by limiting the measurable temperature range and by using a table lookup rather than a mathematical calculation. A type K thermocouple was used for this application report.

Determining the thermocouple relative temperature is done with a lookup table and tenths interpolation, the same as was described in Section 4.4 for the thermistor temperature. If the temperature of the thermocouple tip is less than the cold junction temperature, the voltage from the thermocouple will be negative and the ADC value will be negative. At the completion of the routine, the thermocouple temperature is stored in RAM in the form of XXX.X and has the appropriate sign.

As with the thermistor, the table of values used for the thermocouple temperature lookup is specific to this application and incorporates measured values. Equation 6 shows the general formula for computing the table

ADC value = hex 
$$\left(\frac{2^{N} \times PGA \times Vtc}{2 \times Vref}\right)$$

#### where

- N = Desired resolution of the analog-to-digital conversion (the ADS1240 is a 24-bit ADC, but for this application only the upper 16 bits are used, so in this case N is 16)
- PGA = Gain from the programmable gain amplifier
- Vref = Reference for the ADC
- Vtc = Thermocouple voltage

(6)

## 4.6 Get\_ABS\_Temp - Determining the Absolute Temperature

The Get\_ABS\_Temp routine adds the thermistor (cold junction) temperature to the relative thermocouple measurement to produce the absolute temperature of the thermocouple tip. After adding, the result is checked to determines if it is negative. If so, it falls outside of the range of this application report (0°C to 99.9°C). However, the range checking is performed in the display routine, not in this routine. Therefore, if the absolute temperature is negative, then it is simply stored in RAM as a negative value. If the temperature is positive, it is converted to the BCD format and stored in RAM in BCD format.

#### 4.7 DISPLCD – Display the Absolute Temperature on the LCD

The DISPLCD routine checks the absolute temperature to make sure it is within the specified range. If it is not, either an L or an H is displayed on the LCD to indicate the out-of-range temperature. If the measured temperature is within range, the bits are manipulated appropriately for display on the LCD. The code in this application report is written for demonstration purposes and must be modified for the LCD of your choice.



Circuit Schematic www.ti.com

#### 5 Circuit Schematic

Figure 3 shows a schematic of the circuit used in this application.




Figure 3. Circuit Schematic

Implementing a Direct Thermocouple Interface With the MSP430F4xx and ADS1240



#### 6 Application Code

```
; THIS PROGRAM IS PROVIDED "AS IS". TI MAKES NO WARRANTIES OR
; REPRESENTATIONS, EITHER EXPRESS, IMPLIED OR STATUTORY,
; INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS
; FOR A PARTICULAR PURPOSE, LACK OF VIRUSES, ACCURACY OR
; COMPLETENESS OF RESPONSES, RESULTS AND LACK OF NEGLIGENCE.
; TI DISCLAIMS ANY WARRANTY OF TITLE, QUIET ENJOYMENT, QUIET
; POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY
; INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO THE PROGRAM OR
; YOUR USE OF THE PROGRAM.
; IN NO EVENT SHALL TI BE LIABLE FOR ANY SPECIAL, INCIDENTAL,
; CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY
; THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED
; OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT
; OF THIS AGREEMENT, THE PROGRAM, OR YOUR USE OF THE PROGRAM.
; EXCLUDED DAMAGES INCLUDE, BUT ARE NOT LIMITED TO, COST OF
; REMOVAL OR REINSTALLATION, COMPUTER TIME, LABOR COSTS, LOSS
; OF GOODWILL, LOSS OF PROFITS, LOSS OF SAVINGS, OR LOSS OF
; USE OR INTERRUPTION OF BUSINESS. IN NO EVENT WILL TI'S
; AGGREGATE LIABILITY UNDER THIS AGREEMENT OR ARISING OUT OF
; YOUR USE OF THE PROGRAM EXCEED FIVE HUNDRED DOLLARS
; (U.S.$500).
; Unless otherwise stated, the Program written and copyrighted
; by Texas Instruments is distributed as "freeware". You may,
; only under TI's copyright in the Program, use and modify the
; Program without any charge or restriction. You may
; distribute to third parties, provided that you transfer a
; copy of this license to the third party and the third party
; agrees to these terms by its first use of the Program. You
; must reproduce the copyright notice and any other legend of
; ownership on each copy or partial copy, of the Program.
; You acknowledge and agree that the Program contains
; copyrighted material, trade secrets and other TI proprietary
; information and is protected by copyright laws,
; international copyright treaties, and trade secret laws, as
; well as other intellectual property laws. To protect TI's
; rights in the Program, you agree not to decompile, reverse
; engineer, disassemble or otherwise translate any object code
; versions of the Program to a human-readable form. You agree
; that in no event will you alter, remove or destroy any
; copyright notice included in the Program. TI reserves all
; rights not specifically granted under this license. Except
; as specifically provided herein, nothing in this agreement
; shall be construed as conferring by implication, estoppel,
; or otherwise, upon you, any license or other right under any
; TI patents, copyrights or trade secrets.
; You may not use the Program in non-TI devices.
#include "msp430x41x.h"
            Implement a direct thermocouple interface with the ADS1240 and
           MSP430.
           Mike Mitchell
           MSP430 Applications
```



```
;
          May 10, 2001
; Other Definitions
       ADC_HI R14
#define
#define
       ADC_LO R10
#define
        TXBUF
               R7
#define
       RXBUF
               R6
#define
       BITCNT R5
; LCD segment Definitions
        EQU
              001h
b
        EQU
               002h
       EOU
               010h
C
d
       EQU
               004h
        EQU
               080h
е
f
        EQU
               020h
        EQU
               008h
g
h
        EQU
               040h
; ADS1240 serial communication definitions
Dout.
       EOU
               004h
               008h
Din
        EQU
SCLK
       EQU
               010h
CS
        EQU
               040h
; ADS1240 Register Definitions (Not complete list, see ADS1240 data sheet)
SETUP
       EOU
               000h
               001h
MUX
        EQU
ACR
        EQU
               002h
; ADS1240 Commands (Not complete list, see ADS1240 data sheet)
            001h
RDATA EQU
               050h
                      ; The opcode for WREG is <0101 reg xxxx number>
WREG
        EQU
              010h
                       ; The opcode for RREG is <0001 reg xxxx number>
RREG
       EQU
SELFCAL EQU
              0F0h
SELFOCAL EQU
              0F1h
SELFGCAL EOU
               0F2h
SYSOCAL EQU
               0F3H
SYSGCAL EQU
               0F4h
RST
        EQU
               0FEh
RSEG
               UDATA0
                        ; RAM Locations
TC_ADC_HI
               DS
                     2
                         ; Thermocouple ADC reading, high word
TC_ADC_LO
               DS
                      1
                          ; Thermocouple ADC reading, low byte
TR ADC LO
               DS
                      1
                          ; Thermistor ADC reading, low byte
TR_ADC_HI
               DS
                     2
                          ; Thermistor ADC reading, high word
                          ; Thermocouple temperature
TC_TMP
               DS
                      2
TR_TMP
                      2
               DS
                          ; Thermistor temperature
ABS_TMP
               DS
                      2
                           ; Absolute temperature (TR_TMP+TC_TMP)
TC_NEG
               DS
                      1
                          ; Used for keeping track of negative TC value
          RSEG CSTACK
```



```
*************************
         RSEG
                CODE
; Setup uC and ADC
RESET
         mov
                #SFE(CSTACK),SP
                                ; define stackpointer
SetupWDT
         mov
                #WDTPW+WDTHOLD, &WDTCTL ; Stop Watchdog Timer
SetupFLL
         mov.b
                #02Dh,&SCFQCTL
                                ; Set N=45. 46x32KHz = 1.5Mhz
                                 ; Set clock for ADS1240 to be above
                                 ; min of 1MHz for some margin.
SetupLCD
         mov.b
                #LCDON+LCD4MUX+LCDP2,&LCDCTL
                                         ; LCD 4Mux, S0-S17
SetupBT
         mov.b
                #BTDIV+BTFRFQ1,&BTCTL ; LCD freq.
                         ; Clear 15 bytes of LCD RAM
ClearLCD
                #15,R15
         mov
                                ; Clear LCD RAM
         clr.b LCDMEM-1(R15)
Clear1
                                ; All 15 bytes of LCD RAM?
          dec
                R15
          jnz
                Clear1
                                ; Not done?
SetupIO
         mov.b
                #0ffh,&P5SEL
                                ; Select LCD functions
         mov.b
                #BIT0+BIT1,&P5DIR ; Set output direction
         mov.b
                #BIT1,&P1SEL ; Select MCLK output for pin
         mov.b
                #BIT0,&P1IES
                                ; Select H/L transition for interrupt
                                 ; DRDY\ is connected pin P1.0.
         mov.b
                #0,&P1IFG
                                 ; The previous instruction could have
                                 ; set the P1.0 IFG, so clear it.
         mov.b
                #BIT0,&P1IE
                                 ; Enable interrupt on P1.0
         mov.b
                #BIT1+Din+SCLK+CS,&P1DIR
                                 ; Set direction for serial comm. pins
                                 ; MCLK used as OSC input to ADS1240
         mov.b
                #CS,&P1OUT
                                 ; Set CS High, everything else low
SetupIO2 ; Set all unused IO ports to output direction
         bis.b #BIT5+BIT6+BIT7,&P1DIR
         bis.b #0FFh,&P2DIR
         bis.b
                #BIT0+BIT1+BIT2,&P3DIR
         bis.b #0FFh,&P6DIR
Delay1
         mov
               #0fffh,R15
                                ; Delay to allow FLL+ to
loop1
         dec
               R15
                                 ; sync up MCLK
          jnz
               loop1
          Call
               #SetupADC
                                 ; Call setup routine for ADC
Mainloop
         bis.w
                #LPM0,SR
                                ; Enter LPMO
          call
                #ReadTC
                                 ; Read Thermocouple
         bis.w
                #LPM0,SR
                                ; Enter LPM0
          call
                #ReadTR
                                ; Read Thermistor
          call
                #Get_TR_temp
                                ; Determine temperature with tables
                                ; and interpolation
                                 ; Determine temperature with tables
          call
                #Get_TC_temp
                                 ; and interpolation
                                 ; Determine absolute temperature
          call
                #Get_ABS_temp
          call
                #DISPLCD
                                 ; Display
          jmp
                Mainloop
                                 ; Return to low power mode
SetupADC
          ; Routine to setup the ADS1240 ADC
```



```
bic.b
                 #CS,&P1OUT
                                   ; Take CS\ low to select the ADC.
; Issue reset command
          mov.b
                 #RST,TXBUF
                                  ; Move Reset command to TX buffer (R15)
                                  ; Set bit count value
          mov.b
                 #08h,BITCNT
                                  ; Shift out the Reset command
          call
                 #TXLoop
          call
                 #SCLKdlay
                                  ; Delay for SCLK
; Set PGA to 16X to amplify thermocouple voltage
          mov.b
                 #WREG+SETUP,TXBUF ; Move write register command plus reg
                 #08h,BITCNT ; Set bit count value
          mov.b
          call
                 #TXLoop
                                  ; Shift out command
          mov.b
                 #02h,TXBUF
                                  ; Second part of write reg command
                                   ; Denotes going to write 3 registers total:
                                   ; Setup, Mux, and ACR
          mov.b
                 #08h,BITCNT
                                  ; Set bit count value
                                  ; Shift out command
          call
                 #TXLoop
                                  ; Set PGA to 16X
          mov.b
                 #004h,TXBUF
                                  ; Set bit count value
          mov.b
                 #08h,BITCNT
          call
                 #TXLoop
                                   ; Shift out command
          call
                 #SCLKdlay
                                   ; Delay for SCLK
; Select channels 0,1,common for +,- inputs. This is for the thermocouple
                               ; Select analog channels for conversion
                #01h,TXBUF
          mov.b
          mov.b
                 #08h,BITCNT
                                  ; Set bit count value
          call
                 #TXLoop
                                  ; Shift out command
          call
                 #SCLKdlay
                                  ; Delay for SCLK
; Setup up Data rate with ACR register
                             ; Select Slowes:
; Set bit count value
; Shift out command
                #002h,TXBUF
                                  ; Select slowest data rate for DRDY\.
          mov.b
          mov.b
                 #08h,BITCNT
                 #TXLoop
          call
          call
                 #SCLKdlay
                                   ; Delay for SCLK
; enable interrupts
          eint
                                   ; Enable interrupts
                                   ; Interrupts needed at this point to
                                   ; delay for SELFCAL command.
; Issue SELFCAL command
                                  ; Move Self cal command to TX buffer
          mov.b
                #SELFCAL,TXBUF
          mov.b
                 #08h,BITCNT
                                   ; Set bit count value
          call
                 #TXLoop
                                   ; Shift out the command
          bis
                 #LPM0,SR
                                   ; Go to sleep until DRDY\ goes low.
                                   ; At that point the selfcal is done.
                 #CS,&P1OUT
          bis.b
                                   ; Take CS\ back high again
          ret
                                   ; Done setting up ADC.
; Routine to read thermocouple value
ReadTC
bic.b #CS,&P1OUT
                                  ; Take CS\ low to select ADC.
; Transfer read data command
          mov
                #RDATA,TXBUF
                                   ; Move read command to TX buffer
          mov.b
                 #08h,BITCNT
                                   ; Set Bit count value
          call
                 #TXLoop
                                   ; Shift out the read command
                                   ; Delay for SCLK
          call
                 #SCLKdlay
```



```
; Get the data from the ADC
           mov
                   #10h,BITCNT
                                     ; Set bit counter to 16 bits to shift
                                     ; in the upper 16 bits of ADC value.
           call
                   #RXI,oop
                                     ; Call shift routine
                   RXBUF,TC_ADC_HI
           mov.
                                     ; Save off high word of data.
                                     ; Set bit counter to 8 to shift in
           mov
                   #08h,BITCNT
                                      ; lower 8 bits of ADC data.
           call
                   #RXLoop
                                      ; Call shift routine
           mov.b
                  RXBUF,TC_ADC_LO
                                     ; Save off low byte of ADC data
; Now set mux and gain for thermistor for next ADC read.
           mov.b #WREG+SETUP,TXBUF ; Move write register command plus reg
           mov.b
                   #08h,BITCNT
                                    ; Set bit count value
           call
                   #TXLoop
                                     ; Shift out command
           mov.b
                   #01h,TXBUF
                                    ; Second part of write reg command
           mov.b
                   #08h,BITCNT
                                    ; Set bit count value
                                     ; Shift out command
           call
                   #TXLoop
                                     ; delay for SCLK
           call
                   #SCLKdlay
; Set PGA to 1X. The Thermistor needs no amp.
                                  ; Set PGA to 1X
           mov.b
                  #00h,TXBUF
                                    ; Set bit count value
           mov.b
                   #08h,BITCNT
           call
                   #TXLoop
                                     ; Shift out command
                                     ; Delay for SCLK
           call
                   #SCLKdlay
; Select channels 2, common for +, - inputs.
                                 ; Select analog channels for conversion
           mov.b
                 #028h,TXBUF
           mov.b
                   #08h,BITCNT
                                     ; Set bit count value
           call
                   #TXLoop
                                     ; Shift out command
                                     ; Delay for SCLK
           call
                   #SCLKdlay
; Done reading values, set CS\ high and return
           bis.b
                   #CS,&P1OUT
                                      ; Take CS\ back high.
           ret
ReadTR
          ; Routine to read thermistor value
           bic.b #CS,&P1OUT
                                     ; Take CS\ low to select ADC.
; First read the data for the thermistor
; Transfer read data command
           mov
                   #RDATA, TXBUF
                                     ; Move read command to TX buffer
           mov.b
                   #08h,BITCNT
                                      ; Set Bit count value
           call
                   #TXLoop
                                      ; Shift out the read command
           call
                   #SCLKdlay
                                     ; Delay for SCLK;
; Get the data from the ADC
           mov
                   #10h,BITCNT
                                     ; Set bit counter to 16 bits to shift
                                      ; in the upper 16 bits of ADC value.
           call
                   #RXLoop
                                     ; Call shift routine
           mov
                  RXBUF, TR_ADC_HI
                                     ; Save off high word of data.
           mov
                   #08h,BITCNT
                                     ; Set bit counter to 8 to shift in
                                      ; lower 8 bits of ADC data.
           call
                   #RXLoop
                                      ; Call shift routine
           mov.b
                  RXBUF,TR_ADC_LO
                                     ; Save off low byte of ADC data
; Now set mux and gain for thermocouple for next ADC read.
           mov.b
                   #WREG+SETUP, TXBUF
                                     ; Move write register command plus reg
```



```
; Set bit count value
        mov.b
              #08h,BITCNT
        call
              #TXLoop
                             ; Shift out command
        mov.b
              #01h,TXBUF
                             ; Second part of write reg command.
        mov.b
              #08h,BITCNT
                             ; Set bit count value
         call
              qooJXT#
                             ; Shift out command
; Set PGA to 16X to amplify thermocouple voltage.
        mov.b
             #004h,TXBUF
                             ; Set PGA to 16X
                             ; Set bit count value
        mov.b
              #08h,BITCNT
                            ; Shift out command
         call
              qooJXT#
         call
              #SCLKdlay
                             ; Delay for SCLK
; Select channels 0,1,common for +,- inputs.
                          ; Select analog channels for conversion
        mov.b #01h,TXBUF
        mov.b
              #08h,BITCNT
                            ; Set bit count value
         call
              #TXLoop
                            ; Shift out command
         call
              #SCLKdlay
                            ; Delay for SCLK
; Done reading values, set CS\ high and return
        bis.b #CS,&P10UT
                             ; Take CS\ back high.
        ret
; Routine to transmit to the ADS1240 ADC
bis.b
              #SCLK,&P1OUT
                             ; Set SCLK high
        rla.b TXBUF
                            ; Rotate TXBUF through C
         iс
              Set H
                             ; Jump if C is High
        bic.b
Set_L
              #Din,&P1OUT
                             ; Set Dout Low
        jmp
        bis.b #Din,&P10UT
                             ; Set Dout High
Set_H
             #SCLK,&P1OUT
        bic.b
                             ; Set SCLK Low to latch data into ADC
                             ; Decrement Bit counter
        dec.b BITCNT
         jnz
              TXLoop
                             ; Continue if not done
        ret
; Routine to shift in ADC data
#0,RXBUF
                             ; Clear buffer
        mov
                            ; Set SCLK high.
Ь1
        bis.b
             #SCLK,&P1OUT
        nop
                             ; Short delay
        bic.b
              #SCLK,&P1OUT
                             ; Set SCLK low
                             ; Latch data into Carry bit
        bit.b
              #Dout,&P1IN
        rlc
              RXBUF
                             ; C -> Receive buffer
                             ; Decrement bit counter
        dec
              BITCNT
              L1
         jnz
                             ; Continue if not done
        ret
; Delay loop to meet spec. for SCLK inactive
              #0Fh,R7
                             ; load delay value
        mov
L2
         dec
              R7
                             ; decrement
         jnz
              L2
                             ; repeat until zero
        ret.
Get_TR_temp
             ; Determine temperature of thermistor
```



```
;
                  ; using tables and interpolation
                 *****************
            dint
                                            ; Disable interrupts.
                    TR_ADC_HI,R14
                                            ; Move high word of TR data to R14
           mov
                                            ; Not using low byte in this app.
                                            ; Only using upper 16-bits.
            mov
                    #0h,R5
                                            ; Use R5 as table pointer
            mov
                    #0h,R13
                                            ; Use R13 for temperature value
                    TR_Temps(R5),R14
                                            ; Compare A/D high word to table
            cmp
                    End_TR_Temp
                                            ; If Thermistor value is greater than
            jge
                                            ; first value in table, then it's temp
                                            ; is too low, so end. If equal, then
                                            ; then temp is = 0.
            incd
                                            ; Point to second value in table
CMPloop1
                    TR\_Temps(R5),R14
                                            ; Compare again
            cmp
                    End_LU_1
                                            ; If equal, need to add one to temp
            jeq
                                            ; value then end.
            jge
                    End_TR_lookup
                                            ; If greater, then end routine
            incd
                    R5
                                            ; Point to next value in table
            inc
                    R13
                                            ; Add one to temp value
            jmp
                    CMPloop1
                                            ; Repeat loop
End_LU_1
            inc
                    R13
                                            ; Add one to temp value
            incd
                    R5
                                            ; Also need to increment pointer
End_TR_lookup
; Resolved to nearest degree, now multiply by 10 and interpolate tenths.
; After tenths are determined, simply add it. Then will have temp to nearest
; tenth in binary format.
            rla
                    R13
                                            ; rotate left
            mov
                    R13,R12
                                            ; copy
            rla
                    R12
                                            ; rotate the copy two more times
            rla
                    R12
            add
                    R12.R13
                                            ; then add.
            mov
                    R13,TR_TMP
                                            ; Save off to RAM
; Interpolate to tenths. Tenths = ((higher-ADCvalue)x10)/(higher-lower)
            mov
                                            ; Move table value to R13
                    TR_Temps(R5),R13
            decd
                                            ; Point to previous value in table
           mov
                    TR\_Temps(R5),R15
                                            ; Now, the higher is in R15
                                            ; the ADC value is in R14
                                            ; and the lower is in R13
            sub
                    R13,R15
                                            ; Get delta between lower and higher
            mov
                    TR_Temps(R5),R13
                                            ; Move higher table value to R13
            sub
                    R14,R13
                                            ; Get delta between ADC value and higher
; Multiply delta between ADC value and higher table value by 10
            rla
                    R13
                                            ; rotate left
                    R13,R12
            mov
                                            ; copy
            rla
                    R12
                                            ; rotate the copy two more times
            rla
                    R12
                                            ; then add.
            add
                    R12,R13
                                            ; Done with x10. Now need to divide
; Divide (higher-ADCvalue)x10 by delta between lower and upper to get tenths
     Dividend = (higher-ADCvalue)x10, which is in R13
     Divisor = (higher-lower), which is in R15
                                            ; Use R12 as counter for subtractions
           mov
                    #0,R12
            cmp
                    R15,R13
                                            ; Compare to see if R13>R15.
```



```
jl
                   remainder
                                          ; If not, no division, just remainder
Divide1
           sub
                   R15,R13
                                          ; Dividend-Divisor -> dividend
           inc.b
                   R12
                   R15,R13
                                           ; Is Dividend>Divisor?
           cmp
                   Divide1
                                           ; Yes, subtract and increment again
           jge
remainder
           rla
                   R13
                                           ; Multiply remainder by two
                                           ; Is Dividend>Divisor?
           cmp
                   R15,R13
           jl
                   EndDiv1
                                           ; If not, return
           inc.b
                   R12
                                           ; If so, incrment counter to round up
EndDiv1
           ;
                Division now done, so Add tenths (R12) to the whole number (TR_TMP)
                  R12,TR_TMP
                                           ; Now have xx.x (in binary) for the
           add
                                           ; thermistor temperature.
           ret
                                           ; Done with TR temp. Note interrupts not
                                           ; re-enabled until end of Get_ABS_temp
End_TR_Temp
                  #0h,TR_TMP
                                           ; If get here, TR temp is 0 or too low
           mov
                                           ; So store 00.0 as the temp.
           ret
                                           ; Return. Note interrupts not re-
                                           ; enabled until end of Get_ABS_temp
                  *****************
                 ; Determine temperature of thermocouple
                 ; using tables and interpolation
    *******************
           mov
                   TC_ADC_HI,R14
                                           ; Move high word of TC data to R14
                                           ; Not using low byte in this app.
                                           ; Only using upper 16-bits.
           mov
                   #0h,R5
                                           ; Use R5 as table pointer
                   #0FFD7h,R13
                                           ; Use R13 for temperature value
           mov
                                           ; Preload it with -41 deg C.
                   TC_Temps(R5),R14
                                           ; Compare to table
           cmp
           jl
                   End_TC2
                                           ; Jump if A/D < 1st table value
                   End_TC1
                                           ; Jump if A/D = 1st table value
           jeq
CMPloop2
           incd
                   R5
                                          ; Point to next value in table
           inc
                   R13
                                           ; Add one to temp value
           cmp
                   TC_Temps(R5),R14
                                          ; Compare again
                   CMPloop2
                                           ; If R14 greater or equal, loop
           jge
End_TC_lookup ;
; Resolved to nearest degree, now multiply by 10 and interpolate tenths.
; After tenths are determined, simply add it. Then will have temp to nearest
; tenth in binary format.
           rla
                   R13
                                           ; rotate left
           mov
                   R13.R12
                                           ; copy
           rla
                   R12
                                           ; rotate the copy two more times
           rla
                   R12
           add
                   R12,R13
                                           ; then add.
           mov
                   R13,TC_TMP
                                           ; Save off to RAM
; Interpolate to tenths. Tenths = ((ADCvalue-lower)x10)/(higher-lower)
                   TC_Temps(R5),R15
                                           ; Move table value to register
           mov
           decd
                   R5
                                           ; decrement table pointer
           mov
                   TC_Temps(R5),R13
                                           ; Now, the higher is in R15
                                           ; the ADC value is in R14
                                           ; and the lower is in R13
           sub
                   R13,R15
                                           ; Get delta between lower and higher
                                           ; Get delta between ADC value and lower
           sub
                   R13,R14
```



```
;
; Multiply delta between ADC value and lower table value (which is in R14) by 10
                  R14
                                         ; rotate left
           mov
                  R14,R12
                                         ; сору
           rla
                  R12
                                         ; rotate the copy two more times
           rla
                  R12
                                         ; then add.
           add
                  R12,R14
                                         ; Done with x10. Now need to divide.
; Divide (ADC-lower)x10 by delta between lower and upper to get tenths
    Dividend = (ADC-lower)x10, which is in R14
    Divisor = (higher-lower), which is in R15
           mov
                  #0,R12
                                         ; Use R12 as counter for subtractions
           cmp
                  R15,R14
                                         ; Compare R14, R15
           jl
                  remain
                                         ; jump if R14<R15 - no division
Divide2
           sub
                  R15,R14
                                         ; Dividend-Divisor -> dividend
           inc.b
                  R12
                  R15,R14
                                        ; Is Dividend>Divisor?
           cmp
                                         ; Yes, subtract and increment again
                  Divide2
           jge
                                         ; Multiply remainder by two
remain
           rla
                  R14
           cmp
                  R15,R14
                                         ; Is Dividend>Divisor?
           jl
                  EndDiv2
                                         ; If not, return
           inc.b
                  R12
                                         ; If so, increment counter to round up
EndDiv2
           ;
               Division now done, so Add tenths (R12) to the whole number (TC_TMP)
                 R12,TC_TMP
                                        ; Now have xx.x (in binary) in TC_TMP
           add
           ret
                                         ; Done so return
End TC1
           inc
                  R13
                                         ; Increment R13 to -40 deg C.
End_TC2
           mov
                  R13,TC_TMP
                                         ; Move to RAM.
           ret
                                         ; Return
;End_TC_Temp ret
                                          ; Done
Get_ABS_temp
                ; Calculate absolute temperature by adding the TC and TR
;
                ; temps.
; Add TR_TMP and TC_TMP to get ABS_TMP
Add_temps
                  TC_TMP,R14
                                        ; Put TC_TMP in R14
           mov
           add
                  TR_TMP,R14
                                         ; Add TR_TMP to it
           bit
                  #08000h,R14
                                        ; Test if result is negative
           jge
                  Bin_Dec
                                         ; If not, proceed with conversion
           mov
                  R14,ABS_TMP
                                         ; If so, store the negative temp
           jmp
                  End_Get_ABS_Temp
                                         ; and jump to end
; Now convert to BCD format
Bin_Dec
          rla
                   R14
                                         ; Shift out upper nibble,
           rla
                   R14
                                         ; not used for this
           rla
                   R14
                                         ; conversion
           rla
                   R14
                   #0Ch,R15
                                         ; Loop counter
           mov
           clr
                   R12
                                        ; Result goes into R12
L3
           rla
                   R14
                                        ; Shift MSB into C
           dadd
                   R12,R12
                                         ; Add R14 to itself, plus C
           dec
                   R15
           jnz
                   L3
                                         ; Jump if not done
; Done converting to BCD
```



```
mov
                  R12,ABS_TMP
                                         ; Save absolute temp in BCD to RAM.
End_Get_ABS_Temp
                                         ; re-enable interrupts
           eint.
           ret
DISPLCD
                 ; Display temp on LCD.
ABS_TMP,R14
                                        ; Get temperature from RAM
           mov
                   #08000h,R14
           bit.
                                        ; Test if temp is negative
           jn
                   Disp_L
                                        ; If so, display "low" on LCD
           cmp
                   #01000h,R14
                                        ; Test if temp >= 100
           jge
                   Disp_H
                                         ; If so, display "high" on LCD
; display temp on LCD
           mov.b
                   R14,R11
                                         ; Copy lower byte
           mov.b
                   R14,R12
                                         ; copy lower byte
           rra.b
                   R12
           rra.b
                   R12
           rra.b
                   R12
                                         ; Rotate right to expose nibble
           rra.b
                   R12
           swpb
                   R14
                                         ; Swap high and low bytes of data
           mov.b
                   R14,R13
                                         ; Copy again
           and
                   #0Fh,R13
           and
                   #0Fh,R12
                                         ;
           and
                   #0Fh,R11
                                         ;
           mov.b
                   LCD_Tab(R11), &LCDM1
           mov.b
                   LCD_Tab(R12),&LCDM2
           bis.b
                   #040h,&LCDM2
                                         ; Turn on decimal point
           mov.b
                   LCD_Tab(R13),&LCDM3
           mov.b
                   #0h,&LCDM4
                                         ; Clear upper digit
           ret
; Display "L" on LCD
Disp_L
           mov.b
                   #0h, &LCDM4
           mov.b
                   #0h, &LCDM3
           mov.b
                   #0h,&LCDM2
           mov.b
                   #d+e+f,&LCDM1
           ret
; Display "H" on LCD
Disp_H
           mov.b
                   #0h, &LCDM4
           mov.b
                   #0h, &LCDM3
           mov.b
                   #0h,&LCDM2
           mov.b
                   #b+c+e+f+g,&LCDM1
           ret
; * * * * * * * * *
          *******************
TR_Temps
           DW
                  05DDEh
                           ; 0C
           DW
                  05CE1h
                         ; 1C
           DW
                  05BD5h
                          ; 2C
           DW
                  05AB9h
                          ; 3C
           DW
                  0598Ah
                          ; 4C
           DW
                  05848h
                          ; 5C
           DW
                  0573Dh
                           ; 6C
           DW
                  05624h
                          ; 7C
           DW
                  054FBh
                          ; 8C
           DW
                  053C1h
                           ; 9C
           DW
                  05274h
                           ; 10C
```



```
; 11C
             DW
                      0515Ch
             DW
                      05035h
                                ; 12C
             DW
                      04EFFh
                                ; 13C
             DW
                      04DB9h
                                ; 14C
             DW
                      04C62h
                                ; 15C
             DW
                      04B46h
                                ; 16C
             DW
                      04A1Dh
                                ; 17C
             DW
                      048E7h
                                ; 18C
             DW
                      047A3h
                                ; 19C
             DW
                      0464Fh
                                ; 20C
             DW
                      04531h
                                ; 21C
             DW
                      04408h
                                ; 22C
             DW
                      042D3h
                                ; 23C
             DW
                      04191h
                                ; 24C
                                ; 25C
             DW
                      04042h
             DW
                      03F28h
                                ; 26C
             DW
                      03E05h
                                ; 27C
             DW
                      03CD8h
                                ; 28C
                                ; 29C
             DW
                      03BA0h
             DW
                      03A5Ch
                                ; 30C
             DW
                      0394Bh
                                ; 31C
             DW
                      03832h
                                ; 32C
             DW
                      03711h
                                ; 33C
             DW
                      035E6h
                                ; 34C
                                ; 35C
             DW
                      034B1h
             DW
                      033AFh
                                ; 36C
             DW
                      032A5h
                                ; 37C
             DW
                      03195h
                                ; 38C
             DW
                      0307Ch
                                ; 39C
             DW
                      02F5Ch
                                ; 40C
             DW
                      00000h
                                ; Too High
TC_Temps
             DW
                      0FD78h
                                ; -40C
                                ; -39C
             DW
                      0FD87h
                      0FD97h
                                ; -38C
             DW
             DW
                      0FDA6h
                                ; -37C
                                ; -36C
             DW
                      0FDB6h
             DW
                      0FDC6h
                                ; -35C
             DW
                      0FDD6h
                                ; -34C
                                ; -33C
             DW
                      0FDE6h
             DW
                      0FDF5h
                                ; -32C
             DW
                      0FE05h
                                ; -31C
             DW
                      0FE15h
                                ; -30C
             DW
                      0FE25h
                                ; -29C
             DW
                      0FE35h
                                ; -28C
                                ; -27C
             DW
                      0FE45h
                                ; -26C
             DW
                      0FE55h
             DW
                      0FE65h
                                ; -25C
             DW
                      0FE75h
                                ; -24C
             DW
                      0FE85h
                                ; -23C
             DW
                      0FE95h
                                ; -22C
             DW
                      0FEA6h
                                ; -21C
             DW
                      0FEB6h
                                ; -20C
             DW
                      0FEC6h
                                ; -19C
             DW
                      0FED6h
                                ; -18C
             DW
                      0FEE7h
                                ; -17C
                                ; -16C
             DW
                      0FEF7h
             DW
                      0FF07h
                                ; -15C
```



DW	0FF18h	;	-140
DW	0FF28h	;	-13C
DW	0FF38h	;	-120
DW	0FF49h	;	-110
DW	0FF5Ah	;	-10C
DW	0FF6Ah	;	-9C
DW	0FF7Bh	;	-8C
DW	0FF8Bh	;	-7C
DW	0FF9Ch	;	-6C
DW	0FFACh	;	-5C
DW	0FFBDh	;	-4C
DW	0FFCEh	;	-3C
DW	0FFDEh	;	-2C
DW	0FFEFh	;	-1C
DW	00000h	;	0C
DW	00011h	;	1C
DW	00022h	;	2C
DW	00033h	;	3C
DW	00043h	;	4C
DW	00013h	;	5C
DW	00051h	;	6C
DW	00076h	;	7C
DW	00070H	;	8C
DW	0000711 00098h	;	9C
DW	00056H	;	10C
DW DW	000A3H	;	11C
DW DW	000BAII 000CAh	;	12C
DW	000CAN 000DBh		13C
	000DBH 000ECh	;	14C
DW		;	
DW	000FDh	;	15C
DW	0010Eh	;	16C
DW	0011Fh	;	17C
DW	00131h	;	18C
DW	00142h	;	19C
DW	00153h	;	20C
DW	00164h	;	21C
DW	00175h	;	22C
DW	00186h	;	23C
DW	00198h	;	24C
DW	001A9h	;	25C
DW	001BAh	;	26C
DW	001CBh	;	27C
DW	001DCh	;	28C
DW	001EEh	;	29C
DW	001FFh	;	30C
DW	00210h	;	31C
DW	00222h	;	32C
DW	00233h	;	33C
DW	00244h	;	34C
DW	00255h	;	35C
DW	00267h	;	36C
DW	00278h	;	37C
DW	0028Ah	;	38C
DW	0029Bh	;	39C
DW	002ACh	;	40C
DW	002BEh	;	41C
DW	002CFh	;	42C
DW	002E1h	;	43C
DW	002F2h	;	44C
DW	00303h	;	45C



```
DW
         00315h
                   ; 46C
DW
         00326h
                   ; 47C
DW
         00338h
                   ; 48C
DW
         00349h
                   ; 49C
DW
         0035Bh
                   ; 50C
DW
         0036Ch
                   ; 51C
DW
         0037Eh
                     52C
DW
         0038Fh
                   ; 53C
DW
         003A1h
                   ; 54C
DW
         003B3h
                   ; 55C
DW
         003C4h
                   ; 56C
DW
         003D5h
                   ; 57C
DW
         003E7h
                   ; 58C
DW
         003F9h
                   ; 59C
DW
         0040Ah
                   ; 60C
DW
         0041Ch
                   ; 61C
DW
         0042Dh
                   ; 62C
DW
         0043Fh
                   ; 63C
DW
         00451h
                   ; 64C
DW
         00462h
                   ; 65C
DW
         00474h
                   ; 66C
DW
         00486h
                   ; 67C
DW
         00497h
                   ; 68C
DW
         004A9h
                   ; 69C
DW
         004BAh
                   ; 70C
DW
         004CCh
                   ; 71C
DW
         004DEh
                   ; 72C
DW
         004EFh
                   ; 73C
DW
         00501h
                   ; 74C
                   ; 75C
DW
         00513h
DW
         00524h
                     76C
DW
         00536h
                     77C
DW
         00548h
                   ; 78C
DW
         00559h
                   ; 79C
                   ; 80C
DW
         0056Bh
DW
         0057Ch
                   ; 81C
DW
         0058Eh
                   ; 82C
DW
         005A0h
                   ; 83C
                   ; 84C
DW
         005B1h
DW
         005C3h
                   ; 85C
DW
         005D5h
                   ; 86C
DW
         005E6h
                   ; 87C
DW
         005F8h
                   ; 88C
DW
         00609h
                   ; 89C
DW
         0061Bh
                   ; 90C
DW
         0062Ch
                   ; 91C
DW
         0063Eh
                   ; 92C
DW
         00650h
                   ; 93C
DW
         00662h
                   ; 94C
DW
         00673h
                   ; 95C
DW
         00685h
                   ; 96C
DW
         00696h
                   ; 97C
DW
         006A8h
                   ; 98C
DW
         006B9h
                   ; 99C
DW
         006CBh
                     100C
DW
         07 FFFh
                   ; Too high
```

<sup>;</sup> LCD Table of definitions

<sup>;</sup> These use the bit definitions defined above



Conclusion www.ti.com

```
; for each segment to turn on the appropriate
; segments to form each numeral
LCD_Tab
             DB
                  a+b+c+d+e+f
                                            ; displays "0"
             DB b+c

      b+c
      ; displays
      "1"

      a+b+d+e+g
      ; displays
      "2"

      a+b+c+d+g
      ; displays
      "3"

      b+c+f+g
      ; displays
      "4"

      a+c+d+f+g
      ; displays
      "5"

      a+b+c
      ; displays
      "6"

      a+b+c+d+e+f+g
      ; displays
      "8"

      a+b+c+d+f+g
      ; displays
      "9"

      a+b+c+e+f+g
      ; displays
      "A"

      c+d+e+f+g
      ; displays
      "C"

      b+c+d+e+g
      ; displays
      "d"

      a+d+e+f+g
      ; displays
      "E"

      a+e+f+g
      ; displays
      "F"

                                           ; displays "1"
             DB a+b+d+e+g
             DB
                                             ; displays "F"
             DB
                   a+e+f+g
Exit LPM0
P1 ISR;
bic.b #BIT0,&P1IFG ; Clear P1.0 IFG
                                           ; Clear LPMO bits to exit LPMO
             bic.w #LPM0,0(SP)
             reti
                                            ; on return from interrupt
*******************************
             COMMON INTVEC
                                              ; MSP430x41x Interrupt vectors
 ************************
             ORG
                     PORT1_VECTOR
             DW
                      P1_ISR
                                            ; P1 ISR
                      RESET_VECTOR
             ORG
             DW
                      RESET
                                            ; POR, ext. Reset, Watchdog
             END
```

#### 7 Conclusion

While traditional thermocouple circuits can be complex to design and implement, this report shows how new high-resolution ADCs and microcontrollers can simplify the task.

#### 8 References

- 1. MSP430x4xx Family User's Guide
- 2. MSP430x41x Mixed-Signal Microcontrollers data sheet
- 3. ADS1240 24-Bit Analog-to-Digital Converters data sheet
- 4. MSP430 Based Digital Thermometer



www.ti.com Revision History

## **Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from October 4, 2001 to May 29, 2018		
•	Editorial changes and format updates throughout document	1

#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<a href="www.ti.com/legal/termsofsale.html">www.ti.com/legal/termsofsale.html</a>) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated