TPS54KB20EVM Step-Down Converter Evaluation Module



ABSTRACT

This user's guide contains information for the TPS54KB20EVM evaluation module and the TPS54KB20 DC/DC converter. Also included are the performance characteristics, schematic, and bill of materials for the TPS54KB20EVM.

Table of Contents

1 Introduction	3
1.1 Background	3
1.2 Before You Begin	
1.3 Performance Characteristics Summary	
2 Configurations and Modifications	
2.1 Output Voltage	5
2.2 Frequency and Operation Mode Setting (MSEL Pin)	
3 Test Setup and Results	
3.1 Input/Output Connections	
3.2 Efficiency	
3.3 Output Voltage Regulation	
3.4 Load Transient and Loop Response	
3.5 Output Voltage Ripple	
3.6 Start-up and Shutdown with EN	
3.7 Thermal Performance	
4 Board Layout	
4.1 Layout	
5 Schematic and Bill of Materials	
5.1 Schematic	
5.2 Bill of Materials	20
1 · 4 · 6 PP ·	
List of Figures	
Figure 3-1. TPS54KB20EVM	
Figure 3-2. U1 Efficiency – Skip-Mode (Default)	9
Figure 3-3. U2 Efficiency – Skip-Mode (Default)	
Figure 3-4. U2 Efficiency – FCCM	
Figure 3-5. U1 Load Regulation	
Figure 3-6. U1 Line Regulation	
Figure 3-7. U2 Load Regulation.	
Figure 3-8. U2 Line Regulation	
Figure 3-9. U1 Transient Response.	
Figure 3-10. U2 Transient Response	
Figure 3-11. U1 Bode Plot – 10-A Load	
Figure 3-12. U2 Bode Plot – 10-A Load	
Figure 3-13. U1 Output Ripple – 10-mA Load, Skip-Mode	
Figure 3-15. U2 Output Ripple – 10-mA Load, Skip-Mode	
Figure 3-16. U2 Output Ripple – 25-A Load	
Figure 3-17. U2 Start-up with EN – 25-A Load Figure 3-18. U2 Shutdown with EN – 25-A Load	
Figure 3-19. U1 Thermal Performance – 25-A Load and U2 off	
Figure 3-20. U2 Thermal Performance – 25-A Load and U1 off	
Figure 4-1. Top-Side Composite View	I 🔾
	1/
Figure 4-1. Top-Side Composite View. Figure 4-2. Bottom-Side Composite View (Viewed From Bottom)	

Trademarks

Figure 4-3 Top Layer Layout	15
Figure 4-3. Top Layer LayoutFigure 4-4. Mid Layer 1 Layout	15
Figure 4-5. Mid Layer 2 Layout	15
Figure 4-6. Mid Layer 3 Layout	15
Figure 4-7. Mid Layer 4 Layout	16
Figure 4-8. Bottom Layer Layout	16
Figure 5-1. U1 Schematic	18
Figure 5-2. U2 Schematic	19
List of Tables Table 1-1. Input Voltage and Output Current Summary	3
Table 1-2. TPS54KB20EVM Small Size (U1) Performance Characteristics Summary	
Table 1-3. TPS54KB20EVM High Efficiency (U2) Performance Characteristics Summary	
Table 2-1. MSEL Pin Selection	5
Table 3-1. Connectors and Jumpers	7
Table 3-2. Test Points	
14510 0 2. 10011 01110	7
Table 3-3. Efficiency Measurement Test Points	

Trademarks

All trademarks are the property of their respective owners.

www.ti.com Introduction

1 Introduction

1.1 Background

The TPS54KB20 DC/DC converter are synchronous buck converters designed to provide up to a 25-A output. Rated input voltage and output current range for the evaluation module are given in Table 1-1.

The high-side and low-side MOSFETs are incorporated inside the TPS54KB20 package along with the gate-drive circuitry. The low drain-to-source on-resistance of the MOSFET allows the TPS54KB20 to achieve high efficiencies and helps to keep the junction temperature low at the rated output current. An external divider allows for an adjustable output voltage. The TPS54KB20 MSEL pin provides selectable switching frequency, light load operation mode, and internal compensation. Current limit setting and soft start configuration are set via ILIM and SS pins respectively. Lastly, the TPS54KB20 includes an enable pin and a power good output which can be used for sequencing multiple regulators.

This evaluation module includes two designs with the TPS54KB20. The first design (U1) is designed to demonstrate the small printed-circuit-board areas that can be achieved when designing with the TPS54KB20 regulator. The small area design fits within 250 mm². The second design (U2) is designed to demonstrate the high efficiency that can be achieved when designing with the TPS54KB20 regulator. The second design also includes jumpers that can be used to easily evaluate the features of the TPS54KB20.

Table 1-1. Input Voltage and Output Current Summary

EVM	RELATED IC	INPUT VOLTAGE RANGE	OUTPUT CURRENT RANGE
TPS54KB20EVM	U1	V _{IN} = 8 V to 16 V	0 A to 25 A
TPS54KB20EVM	U2	V _{IN} = 4.5 V to 16 V	0 A to 25 A

1.2 Before You Begin

The following warnings and cautions are noted for the safety of anyone using or working close to the TPS54KB20EVM. Observe all safety precautions.





The TPS54KB20EVM can become hot during operation due to dissipation of power in some operating conditions. Avoid contact with the board. Follow all applicable safety procedures applicable to your laboratory.

WARNING

The circuit module has signal traces, components, and component leads on the bottom of the board and can result in exposed voltages, hot surfaces or sharp edges. Do not reach under the board during operation.

CAUTION

Some power supplies can be damaged by application of external voltages. If using more than 1 power supply, check your equipment requirements and use blocking diodes or other isolation techniques, as needed, to prevent damage to your equipment.

Introduction www.ti.com

1.3 Performance Characteristics Summary

A summary of the TPS54KB20EVM performance characteristics is provided in Table 1-2 and Table 1-3. The TPS54KB20EVM is designed and tested for V_{IN} = 8 V to 16 V for U1 and V_{IN} = 4.5 V to 16 V for U2. Characteristics are given for an input voltage of V_{IN} = 12 V and output voltage of 3.3 V, unless otherwise specified. The ambient temperature is room temperature (20°C to 25°C) for all measurements, unless otherwise noted.

Table 1-2. TPS54KB20EVM Small Size (U1) Performance Characteristics Summary

SPECIFICATION	TEST C	ONDITIONS	MIN	TYP	MAX	UNIT
V _{IN} voltage range			8	12	16 ⁽¹⁾	V
Input current	V _{IN} = 8 V, I _O = 25 A			11.2		Α
V _{IN} start voltage	Set by EN pin resistor	divider		7.18		V
V _{IN} stop voltage	Set by EN pin resistor	divider		5.98		V
Output voltage setpoint				3.310		V
Output current range	V _{IN} = 8 V to 16 V		0		25	Α
Line and load regulation	V _{IN} = 8 V to 16 V, I _{OUT}	= 0 A to 25 A		±0.15		%
	I _{OUT} = 5 A to 15 A	Voltage change		-17		mV
		Recovery time		22		μs
Load transient response	I _{OUT} = 15 A to 5 A	Voltage change		14		mV
		Recovery time		22		μs
Input ripple voltage	I _{OUT} = 25 A			780		mVPP
Output ripple voltage	I _{OUT} = 25 A			26		mVPP
Output rise time	Set by SS pin capacito	r		550		μs
Current limit	Set by ILIM pin resistor	•		27.5		Α
Switching frequency (f _{SW})	Set by MSEL pin resist	Set by MSEL pin resistor		1400		kHz
Peak efficiency	I _{OUT} = 10 A			94.2		%
IC case temperature	I _{OUT} = 25 A, 15-minute	soak		113		°C

(1) Max V_{IN} limited by minimum on-time

Table 1-3. TPS54KB20EVM High Efficiency (U2) Performance Characteristics Summary

SPECIFICATION	TEST C	TEST CONDITIONS		TYP	MAX	UNIT
V _{IN} voltage range			4.5	12	16	V
Input current	V _{IN} = 4.5 V, I _{OUT} = 25 A	4		19.9		Α
V _{IN} start voltage	Set by EN pin resistor	divider		3.84		V
V _{IN} stop voltage	Set by EN pin resistor	divider		3.20		V
Output voltage setpoint				3.310		V
Output current range	V _{IN} = 4.5 V to 16 V		0		25	Α
Line and load regulation	$V_{IN} = 4.5 \text{ V to } 16 \text{ V, } I_{OU}$	_{IT} = 0 A to 25 A		±0.03%		
Load transient response	I _{OUT} = 5 A to 15 A	Voltage change		-34		mV
		Recovery time		40		μs
	I _{OUT} = 15 A to 5 A	Voltage change		53		mV
		Recovery time		42		μs
Input ripple voltage	I _{OUT} = 25 A			340		mVPP
Output ripple voltage	I _{OUT} = 25 A			16.4		mVPP
Output rise time	Set by SS pin capacito	r		975		μs
Current limit	Set by ILIM pin resistor	Set by ILIM pin resistor		27.5		Α
Switching frequency (f _{SW})	Set by MSEL pin resist	Set by MSEL pin resistor, J8 short pins 3 and 4		800		kHz
Peak efficiency	I _{OUT} = 7.5 A		96.3%			
IC case temperature	I _{OUT} = 25 A, 15-minute	soak		97.2		°C



2 Configurations and Modifications

These evaluation modules are designed to provide access to the features of the TPS54KB20. The U2 design provides jumpers for testing different configurations. Jumper selections must be made prior to enabling the TPS54KB20.

If a desired configuration is not available, then some modifications can be made to this module. When modifications are made to the components on the EVM, the internal compensation option selected with the MSEL pin resistor needs to be changed. Changes to the f_{SW}, output voltage, output inductor, and output capacitors can require a change in the compensation. TPS54KB20 data sheet equations or WEBENCH can be used to calculate the output capacitor value, compensation, f_{SW}, and inductance. Verify that all components have sufficient voltage and current ratings.

2.1 Output Voltage

In the U1 design, the output voltage is set by the resistor divider network of R2 (R_{FBT}) and R6 (R_{FBB}). R6 is fixed at 10.0 k Ω to set the FB divider current at approximately 90 μ A. The output voltage is set to 3.3V as default. To change the output voltage of the EVM, the value of resistor R2 must change. Changing the value of R2 can change the output voltage above the 0.9-V reference voltage (V_{REF}). The value of R2 for a specific output voltage can be calculated using Equation 1.

In the U2 design, the output voltage is set by the resistor divider network of R12 (R_{FBT}) and R15 (R_{FBB}). R15 is fixed at 3.01 k Ω to set the FB divider current at approximately 299 μ A. The output voltage is set to 3.3V as default. To change the output voltage of the EVM, the value of resistor R12 must change. Changing the value of R12 can change the output voltage above the 0.9-V reference voltage (V_{REF}). The value of R12 for a specific output voltage can be calculated using Equation 1. After changing R12, the feed forward capacitor (C51) also needs to be changed.

$$R_{FBT} = R_{FBB} \times \left(\frac{V_{OUT}}{V_{REF}} - 1\right) \tag{1}$$

2.2 Frequency and Operation Mode Setting (MSEL Pin)

In the U2 design, jumper J8 can change between MSEL pin selections shown in Table 2-1. If the desired option is unavailable, then change one of the resistors to the value that sets the desired option.

In the U1 design, change the MSEL resistor to the value which sets the desired option.

SWITCHING MSEL RESISTOR OPERATION UNDER ZERO FREQUENCY RAMP AMPLITUDE JUMPER SETTING FREQUENCY (f_{SW}) **LIGHT LOAD** (kHz) $(k\Omega)$ (kHz) 0 **FCCM** 800 2.2x 53 1 to 2 pin shorted 3 to 4 pin shorted 4.99 **FCCM** 800 1.6x 53 5 to 6 pin shorted 7.50 **FCCM** 800 1 3x 10.5 **FCCM** 800 32 7 to 8 pin shorted 1x 54.9 2.2x 53 9 to 10 pin shorted Skip-mode 800 11 to 12 pin shorted 63.4 Skip-mode 800 1.6x 53 13 to 14 pin shorted(1) 73.2 Skip-mode 800 1.3x 32 86 6 32 15 to 16 pin shorted Skip-mode 800 1x

Table 2-1. MSEL Pin Selection

⁽¹⁾ Default Setting

Test Setup and Results www.ti.com

3 Test Setup and Results

This section describes how to properly connect, set up, and use the TPS54KB20EVM evaluation module. The section also includes test results typical for the evaluation module and covers efficiency, output voltage regulation, load transients, loop response, output ripple, input ripple, start-up, and current limit modes. Measurements are taken with the following conditions unless otherwise noted.

- 12-V input
- Room temperature (20°C to 25°C)
- U1 with the default setting output voltage of 3.310 V, switching frequency of 1400 kHz, and maximum current limit setting
- U2 with the default setting output voltage of 3.310 V, switching frequency of 800 kHz, and maximum current limit setting
- With the other converter disabled




Figure 3-1. TPS54KB20EVM

www.ti.com Test Setup and Results

3.1 Input/Output Connections

The TPS54KB20EVM is provided with input connectors, output connectors, and test points as shown in Table 3-1 and Table 3-2.

To support the minimum input voltage with the full rated load on both outputs with the default EVM, a power supply capable of supplying greater than 20 A must be connected to the VIN and PGND terminal blocks (J1 for U1, and J3 for U2) through a pair of 12-AWG wires or better.

For U1, the load must be connected to J2 and for U2, the load must be connected to J4. A pair of 10-AWG wires or better must be used for each connection. With the maximum current limit setting, the maximum load current capability is near 30 A before the TPS54KB20 goes into current limit. Wire lengths must be minimized to reduce losses in the wires.

Table 3-1. Connectors and Jumpers

Table 6 in Connections and Campore						
REFERENCE DESIGNATOR	NAME	RELATED IC	FUNCTION			
J1	VIN1	U1	VIN screw terminal to connect input voltage (see Table 1-1 for VIN range)			
J2	VOUT1	U1	VOUT screw terminal to connect load to output			
J3	VIN2	U2	VIN screw terminal to connect input voltage (see Table 1-1 for VIN range)			
J4	VOUT2	U2	VOUT screw terminal to connect load to output			
J5	-	U2	For Tl's internal use only. Do not change the default jumper position.			
J6	-	U2	For Tl's internal use only. Do not change the default jumper position.			
J7	-	U2	For Tl's internal use only. Do not change the default jumper position.			
J8	-	U2	MSEL selection header. Use shunt to select MSEL resistor (see Table 2-1 for MSEL pin selection)			

Table 3-2. Test Points

REFERENCE DESIGNATOR	NAME	RELATED IC	FUNCTION
TP1	VIN1	U1	VIN test point. Use this for efficiency measurements.
TP2	SW1	U1	SW node test point
TP3	VOUT1	U1	VOUT test point
TP4	PGND1	U1	PGND test point. Use this for efficiency measurements.
TP5	VCC1	U1	VCC test point
TP6	PG1	U1	PGOOD output test point (pulled up to VCC pin through a 10-kΩ resistor)
TP7	BODE1-	U1	Test point between voltage divider network and output voltage. Used for Bode plot measurements.
TP8	REG_VOUT1	U1	VOUT test point. Use this for efficiency, output regulation, and bode plot measurements.
TP9	PGND1	U1	PGND test point. Use this for efficiency measurements.
TP10	AGND1	U1	AGND test point
TP11	VOUT_U1	U1	SMB connector to measure output voltage. When using this test point, set the scope for 1-M Ω termination. When using 50- Ω termination, a 2:1 divider is created.
TP12	VIN2	U2	VIN test point
TP13	VOUT2	U2	VOUT test point
TP14	SW2	U2	SW test point
TP15	EN2	U2	EN test point
TP16	VCC2	U2	VCC test point
TP17	REG_GND	U2	PGND test point. Use this for efficiency measurements.
TP18	PG2	U2	PGOOD output test point (pulled up to VCC pin through a 10-kΩ resistor)
TP19	BODE2-	U2	Test point between voltage divider network and output voltage. Used for Bode plot measurements.

Test Setup and Results www.ti.com

Table 3-2. Test Points (continued)

	144010 0 = 1 10011 0 11100 (0 0 11111140 4)						
REFERENCE DESIGNATOR	NAME	RELATED IC	FUNCTION				
TP20	REG_VOUT2	U2	VOUT test point. Use this for efficiency, output regulation, and bode plot measurements.				
TP21	SS2	U2	SS test point				
TP22	ILIM2	U2	ILIM test point				
TP23	MSEL2	U2	MSEL test point				
TP24	PGND2	U2	PGND test point. Use this for efficiency measurements.				
TP25	AGND2	U2	AGND test point				
TP28	SW_U2	U2	SMB connector to measure SW node. When using this test point, set the scope for 50 - Ω termination. The combination of 50 - Ω termination and 450 - Ω series resistance creates a 10 :1 attenuation.				
TP29	VOUT_U2	U2	SMB connector to measure output voltage. When using this test point, set the scope for 1-M Ω termination. When using 50- Ω termination, a 2:1 divider is created.				

www.ti.com Test Setup and Results

3.2 Efficiency


Figure 3-2 through Figure 3-4 show the efficiency for both designs on the TPS54KB20EVM. The test points listed in Table 3-3 are used for the efficiency measurement. Use these test points to minimize the contribution of PCB parasitic power loss to the measured power loss.

The following are some additional test setup considerations to minimize external sources of power dissipation.

- Disable the other regulator to avoid including the switching quiescent current of the other regulator in the
 efficiency measurement.
- Do not measure the SW pin of U2 with TP28 while measuring the efficiency of U2. Measuring the SW pin with this test point loads this node with 500 Ω and the efficiency measurement includes the power lost in this external resistance.

Table 3-3. Efficiency Measurement Test Points


RELATED IC	TEST POINT NAME	REFERENCE DESIGNATOR	FUNCTION
	VIN1	TP1	Input voltage test point connected near pins of U1
U1	PGND1	TP9	PGND reference test point for input voltage
UI	REG_VOUT1	TP8	Output voltage test point near output inductor of U1
	PGND1	TP4	PGND reference test point for output voltage
	VIN2	TP12	Input voltage test point connected near pins of U2
U2	PGND2	TP24	PGND reference test point for input voltage
02	REG_VOUT2	TP20	Output voltage test point near output inductor of U2
	REG_GND	TP17	PGND reference test point for output voltage





3.3 Output Voltage Regulation

Figure 3-5 and Figure 3-6 show the load and line regulation for U1. Figure 3-7 and Figure 3-8 show the load and line regulation for U2.




www.ti.com Test Setup and Results

3.4 Load Transient and Loop Response

Figure 3-9 and Figure 3-10 show the response to load transients for both designs. The current step is from 5 A to 15 A and the current step slew rate is 1 A/µs. An electronic load is used to provide a DC 5-A load and the load transient circuit on the EVM is used to provide a 10-A step. The VOUT voltage is measured using TP11 for U1 and TP29 for U2.


Figure 3-11 and Figure 3-12 show the loop characteristics for both designs. Gain and phase plots are shown for V_{IN} voltage of 12 V and a 10-A load.





3.5 Output Voltage Ripple


Figure 3-13 through Figure 3-16 show the TPS54KB20EVM output voltage ripple. The load currents are no load and 6 A. V_{IN} = 12 V. The VOUT voltage is measured using TP10 for U1 and TP29 for U2.



www.ti.com Test Setup and Results

3.6 Start-up and Shutdown with EN

Figure 3-17 and Figure 3-18 show the start-up and shutdown waveforms for U2 with EN. In Figure 3-17, the input voltage is initially applied and the output is inhibited by pulling EN to GND using an external function generator. When the EN voltage is increased above the enable-threshold voltage, the start-up sequence begins and the output voltage ramps up to the externally set value. In Figure 3-18, the external function generator pulls EN to ground and the TPS54KB20 shuts down.



3.7 Thermal Performance

Figure 3-19 through Figure 3-20 show the temperature rise of the TPS54KB20 ICs at full 25-A load. Figure 3-19 and Figure 3-20 have only one TPS54KB20 on and loaded. A minimum of 10 minutes for soak time was used before taking each measurement.




Figure 3-19. U1 Thermal Performance – 25-A Load and U2 off




Figure 3-20. U2 Thermal Performance – 25-A Load and U1 off

INSTRUMENTS Board Layout www.ti.com

4 Board Layout

This section provides a description of the TPS54KB20EVM board layout and layer illustrations.

4.1 Layout

The board layout for the TPS54KB20EVM is shown in Figure 4-1 through Figure 4-8. The top-side layer of the EVM is laid out in a manner typical of a user application. The top, bottom, and internal layers are 2-oz. copper. The small size U1 circuit takes up an area of only approximately 250 mm² as shown on the silkscreen.




Figure 4-1. Top-Side Composite View




Figure 4-2. Bottom-Side Composite View (Viewed From Bottom)

www.ti.com Board Layout




Figure 4-3. Top Layer Layout




Figure 4-5. Mid Layer 2 Layout




Figure 4-4. Mid Layer 1 Layout




Figure 4-6. Mid Layer 3 Layout

Board Layout w




Figure 4-7. Mid Layer 4 Layout




Figure 4-8. Bottom Layer Layout




5 Schematic and Bill of Materials

This section presents the TPS54KB20EVM schematic and bill of materials.



5.1 Schematic

Figure 5-1 is the schematic for U1. Figure 5-2 is the schematic for U2.






Figure 5-1. U1 Schematic






Figure 5-2. U2 Schematic



5.2 Bill of Materials

Table 5-1 presents the bill of materials for the TPS54KB20EVM.

Table 5-1. TPS54KB20EVM Bill of Materials

DESIGNATOR	QTY	VALUE	DESCRIPTION	PACKAGE REFERENCE	PART NUMBER	MANUFACTURER
!PCB1	1		Printed Circuit Board		BSR225	Any
C1, C32	2	330 μF	Cap Aluminum Polymer 330 uF 25 V 20% Solder Cylindrical 19 m Ohm 2325 mA 2000 hr 125°C T/R	SMT_CAP_8MM3_8MM3	A768KS337M1ELAE019	KEMET
C2, C3, C17, C18, C19, C33, C34, C35	8	10uF	CAP, CERM, 10 μF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206	CGA5L1X7R1E106K160A E	TDK
C4, C5, C20, C36	4	1uF	CAP, CERM, 1 μF, 25 V,+/- 20%, X5R, 0402	402	GRM155R61E105MA12D	MuRata
C6, C7, C12, C22, C38, C48	6	0.1uF	CAP, CERM, 0.1 uF, 35 V, +/- 10%, X5R, 0402	402	GMK105BJ104KV-F	Taiyo Yuden
C8, C9, C10, C11	4	47uF	CAP, CERM, 47 µF, 10 V,+/- 20%, X5R, 0805	805	GRM21BR61A476ME15L	MuRata
C14, C50	2	1uF	CAP, CERM, 1 uF, 16 V, +/- 10%, X6S, 0402	402	C1005X6S1C105K050BC	TDK
C15	1	0.022uF	CAP, CERM, 0.022 uF, 50 V, +/- 10%, C0G/NP0, 0402	402	GCM155R71H223KA55D	MuRata
C24, C25, C26, C27, C40, C41, C42	7	22uF	CAP, CERM, 22 μF, 10 V,+/- 20%, X6S, 0805	805	GRM21BC81A226ME44	MuRata
C30, C46	2	220 μF	Molded Tantalum Polymer Capacitor 220uF 20% 6.3V life 1000Hours SMD 2917	2917	6TCF220M5L	Panasonic
C52	1	0.039uF	CAP, CERM, 0.039 uF, 10 V, +/- 10%, X7R, 0402	402	GRM155R71A393KA01D	MuRata
FID1, FID2, FID3, FID4	4		Fiducial mark. There is nothing to buy or mount.	N/A	N/A	N/A
H1, H2, H3, H4	4		Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon	SJ-5303 (CLEAR)	ЗМ
J1, J2, J3, J4	4		Terminal Block, 60 A, 10.16mm Pitch, 2-Pos, TH	21.8x30x19 mm	399100102	Molex
J5, J6, J7	3		Header, 100mil, 3x1, Gold, TH	3x1 Header	TSW-103-07-G-S	Samtec
J8	1		Header, 2.54 mm, 8x2, Tin, Vertical, TH	Header, 2.54 mm, 8x2, TH	PEC08DAAN	Sullins Connector Solutions
J9	1		Card Edge Socket, 0.8mm, 10x2, SMT	Card Edge Socket, 0.8mm, 10x2, SMT	HSEC8-110-01-S-DV-A	Samtec
J_PGND1, J_PGND2	2		1 mm Uninsulated Shorting Plug, 10.16mm spacing, TH	Shorting Plug, 10.16mm spacing, TH	D3082-05	Harwin
L1	1	0.22uH	220 nH Shielded Inductor 29 A 1.3mOhm Max Nonstandard	SMT_IND_6MM51_6MM71	XGL6060-221MEC	Coilcraft
L2	1	0.47uH	SMT High Current Cube Inductor 0.47 μH ±20% 26 A 1.85 mΩ	SMT2_12MM1_11MM4	7443320047	Wurth Electronics
LBL1	1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch	THT-14-423-10	Brady
R1	1	453k	RES, 453 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402453KFKED	Vishay-Dale
R2	1	26.7k	RES, 26.7 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW040226K7FKED	Vishay-Dale
R3, R13	2	10	RES, 10.0, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW040210R0FKED	Vishay-Dale
R4, R6, R14	3	10.0k	RES, 10.0 k, 1%, 0.1 W, 0402	402	ERJ-2RKF1002X	Panasonic
R5, R16	2	100k	RES, 100 k, 1%, 0.1 W, 0402	402	ERJ-2RKF1003X	Panasonic
R7, R17	2	4.32k	RES, 4.32 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04024K32FKED	Vishay-Dale
R8	1	174k	RES, 174 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402174KFKED	Vishay-Dale
R10, R34	2	49.9	RES, 49.9, 1%, 0.1 W, 0603	603	RC0603FR-0749R9L	Yageo
R11	1	200k	RES, 200 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402200KFKED	Vishay-Dale
R12	1	8.06k	RES, 8.06 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04028K06FKED	Vishay-Dale
R15	1	3.01k	RES, 3.01 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04023K01FKED	Vishay-Dale
R19	1	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603	CRCW06030000Z0EA	Vishay-Dale
R20	1	4.99k	RES, 4.99 k, 0.1%, 0.1 W, 0603	603	RT0603BRD074K99L	Yageo America



	Table 5-1. TPS54KB20EVM Bill of Materials (continued)								
DESIGNATOR	QTY	VALUE	DESCRIPTION	PACKAGE REFERENCE	PART NUMBER	MANUFACTURER			
R21	1	7.50k	RES, 7.50 k, 1%, 0.1 W, 0603	603	ERJ-3EKF7501V	Panasonic			
R22	1	10.5k	RES, 10.5 k, 0.1%, 0.1 W, 0603	603	RG1608P-1052-B-T5	Susumu Co Ltd			
R23	1	54.9k	RES, 54.9 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0754K9L	Yageo America			
R24	1	63.4k	RES, 63.4 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0763K4L	Yageo America			
R25	1	73.2k	RES, 73.2 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0773K2L	Yageo America			
R26	1	84.5k	RES, 84.5 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0784K5L	Yageo America			
R29	1	453	RES, 453, 1%, 0.1 W, 0603	603	RC0603FR-07453RL	Yageo			
R33	1	66.5k	RES, 66.5 k, 1%, 0.1 W, 0603	603	RC0603FR-0766K5L	Yageo			
SH-J1, SH-J2, SH-J3, SH-J4	4	1x2	Shunt, 100mil, Gold plated, Black	Shunt	SNT-100-BK-G	Samtec			
TP1, TP2, TP3, TP5, TP6, TP7, TP8, TP12, TP13, TP14, TP15, TP16, TP18, TP19, TP20, TP21, TP22, TP23	18		Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint	5010	Keystone			
TP4, TP9, TP10, TP17, TP24, TP25	6		Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint	5011	Keystone Electronics			
TP11, TP28, TP29	3		Connector, Receptacle, 50 ohm, TH	SMB Connector	SMBR004D00	JAE Electronics			
U1, U2	2		4-V to 16-V Input, 25-A, Remote Sense, D-CAP4 Synchronous Buck Converter	WQFN-FCRLF16	TPS54KB20RZRR	Texas Instruments			
C13	0	0.01uF	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X5R, 0402	402	GRM155R61C103KA01D	MuRata			
C16, C53	0	560 pF	CAP, CERM, 560 pF, 100 V, +/- 10%, X7R, 0603	603	GRM188R72A561KA01D	MuRata			
C21, C37	0	1uF	CAP, CERM, 1 µF, 25 V,+/- 20%, X5R, 0402	402	GRM155R61E105MA12D	MuRata			
C23, C39	0	0.1uF	CAP, CERM, 0.1 uF, 35 V, +/- 10%, X5R, 0402	402	GMK105BJ104KV-F	Taiyo Yuden			
C28, C29, C43, C44, C45	0	100uF	CAP, CERM, 100 μF, 6.3 V,+/- 20%, X6T, 1206	1206	GRM31CD80J107ME39L	MuRata			
C31, C47	0	220 µF	Molded Tantalum Polymer Capacitor 220uF 20% 6.3V life 1000Hours SMD 2917	2917	6TCF220M5L	Panasonic			
C49	0	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	402	CGA2B3X7R1H103K050 BB	TDK			
C51	0	15 pF	CAP, CERM, 15 pF, 50 V,+/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	402	CGA2B2C0G1H150J050 BA	TDK			
C54	0	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0402	402	C1005X7R1H104K050BB	TDK			
D1	0	Green	LED, Green, SMD	LED_0603	150060GS75000	Wurth Elektronik			
J10	0		Header(Shrouded), 2.54mm, 5x2, Gold, TH	Header, 2.54mm, 5x2, TH	AWHW-10G-0202-T	Assman WSW			
R9, R18	0	5.1	RES, 5.10, 1%, 0.5 W, 1210	1210	RC1210FR-075R1L	Yageo			
R27	0	0	RES, 0, 5%, 0.1 W, 0603	603	RC0603JR-070RL	Yageo			
R28, R32	0	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603	CRCW06030000Z0EA	Vishay-Dale			
R30	0	2.2k	RES, 2.2 k, 5%, 0.1 W, 0603	603	RC0603JR-072K2L	Yageo			
R31	0	49.9	RES, 49.9, 1%, 0.1 W, 0603	603	RC0603FR-0749R9L	Yageo			
R35, R36	0	10.0Meg	RES, 10.0 M, 1%, 0.1 W, AEC- Q200 Grade 0, 0603	603	CRCW060310M0FKEA	Vishay-Dale			
TP26, TP27	0		Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint	5010	Keystone			
U3	0		250 MHz, Rail-to-Rail I/O, CMOS Single Operational Amplifier, 2.5 to 5.5 V, -40 to 125 degC, 5-pin SOT23 (DBV5), Green (RoHS & no Sb/Br)	DBV0005A	OPA354AIDBVR	Texas Instruments			



5.2 Bill of Materials

Table 5-1 presents the bill of materials for the TPS54KB20EVM.

Table 5-1. TPS54KB20EVM Bill of Materials

DESIGNATOR	QTY	VALUE	DESCRIPTION	PACKAGE REFERENCE	PART NUMBER	MANUFACTURER
!PCB1	1	VALUE	Printed Circuit Board	FACRAGE REI ERENCE	BSR225	
		ļ				Any
C1, C32	2	330 μF	Cap Aluminum Polymer 330 uF 25 V 20% Solder Cylindrical 19 m Ohm 2325 mA 2000 hr 125°C T/R	SMT_CAP_8MM3_8MM3	A768KS337M1ELAE019	KEMET
C2, C3, C17, C18, C19, C33, C34, C35	8	10uF	CAP, CERM, 10 µF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206	CGA5L1X7R1E106K160A E	TDK
C4, C5, C20, C36	4	1uF	CAP, CERM, 1 µF, 25 V,+/- 20%, X5R, 0402	402	GRM155R61E105MA12D	MuRata
C6, C7, C12, C22, C38, C48	6	0.1uF	CAP, CERM, 0.1 uF, 35 V, +/- 10%, X5R, 0402	402	GMK105BJ104KV-F	Taiyo Yuden
C8, C9, C10, C11	4	47uF	CAP, CERM, 47 µF, 10 V,+/- 20%, X5R, 0805	805	GRM21BR61A476ME15L	MuRata
C14, C50	2	1uF	CAP, CERM, 1 uF, 16 V, +/- 10%, X6S, 0402	402	C1005X6S1C105K050BC	TDK
C15	1	0.022uF	CAP, CERM, 0.022 uF, 50 V, +/- 10%, C0G/NP0, 0402	402	GCM155R71H223KA55D	MuRata
C24, C25, C26, C27, C40, C41, C42	7	22uF	CAP, CERM, 22 μF, 10 V,+/- 20%, X6S, 0805	805	GRM21BC81A226ME44	MuRata
C30, C46	2	220 µF	Molded Tantalum Polymer Capacitor 220uF 20% 6.3V life 1000Hours SMD 2917	2917	6TCF220M5L	Panasonic
C52	1	0.039uF	CAP, CERM, 0.039 uF, 10 V, +/- 10%, X7R, 0402	402	GRM155R71A393KA01D	MuRata
FID1, FID2, FID3, FID4	4		Fiducial mark. There is nothing to buy or mount.	N/A	N/A	N/A
H1, H2, H3, H4	4		Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon	SJ-5303 (CLEAR)	зм
J1, J2, J3, J4	4		Terminal Block, 60 A, 10.16mm Pitch, 2-Pos, TH	21.8x30x19 mm	399100102	Molex
J5, J6, J7	3		Header, 100mil, 3x1, Gold, TH	3x1 Header	TSW-103-07-G-S	Samtec
J8	1		Header, 2.54 mm, 8x2, Tin, Vertical, TH	Header, 2.54 mm, 8x2, TH	PEC08DAAN	Sullins Connector Solutions
J9	1		Card Edge Socket, 0.8mm, 10x2, SMT	Card Edge Socket, 0.8mm, 10x2, SMT	HSEC8-110-01-S-DV-A	Samtec
J_PGND1, J_PGND2	2		1 mm Uninsulated Shorting Plug, 10.16mm spacing, TH	Shorting Plug, 10.16mm spacing, TH	D3082-05	Harwin
L1	1	0.22uH	220 nH Shielded Inductor 29 A 1.3mOhm Max Nonstandard	SMT_IND_6MM51_6MM71	XGL6060-221MEC	Coilcraft
L2	1	0.47uH	SMT High Current Cube Inductor 0.47 μH ±20% 26 A 1.85 mΩ	SMT2_12MM1_11MM4	7443320047	Wurth Electronics
LBL1	1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch	THT-14-423-10	Brady
R1	1	453k	RES, 453 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402453KFKED	Vishay-Dale
R2	1	26.7k	RES, 26.7 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW040226K7FKED	Vishay-Dale
R3, R13	2	10	RES, 10.0, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW040210R0FKED	Vishay-Dale
R4, R6, R14	3	10.0k	RES, 10.0 k, 1%, 0.1 W, 0402	402	ERJ-2RKF1002X	Panasonic
R5, R16	2	100k	RES, 100 k, 1%, 0.1 W, 0402	402	ERJ-2RKF1003X	Panasonic
R7, R17	2	4.32k	RES, 4.32 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04024K32FKED	Vishay-Dale
R8	1	174k	RES, 174 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402174KFKED	Vishay-Dale
R10, R34	2	49.9	RES, 49.9, 1%, 0.1 W, 0603	603	RC0603FR-0749R9L	Yageo
R11	1	200k	RES, 200 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW0402200KFKED	Vishay-Dale
R12	1	8.06k	RES, 8.06 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04028K06FKED	Vishay-Dale
R15	1	3.01k	RES, 3.01 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	402	CRCW04023K01FKED	Vishay-Dale
R19	1	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603	CRCW06030000Z0EA	Vishay-Dale
R20	1	4.99k	RES, 4.99 k, 0.1%, 0.1 W, 0603	603	RT0603BRD074K99L	Yageo America

Table 5-1. TPS54KB20EVM Bill of Materials (continued)						
DESIGNATOR	QTY	VALUE	DESCRIPTION	PACKAGE REFERENCE	PART NUMBER	MANUFACTURER
R21	1	7.50k	RES, 7.50 k, 1%, 0.1 W, 0603	603	ERJ-3EKF7501V	Panasonic
R22	1	10.5k	RES, 10.5 k, 0.1%, 0.1 W, 0603	603	RG1608P-1052-B-T5	Susumu Co Ltd
R23	1	54.9k	RES, 54.9 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0754K9L	Yageo America
R24	1	63.4k	RES, 63.4 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0763K4L	Yageo America
R25	1	73.2k	RES, 73.2 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0773K2L	Yageo America
R26	1	84.5k	RES, 84.5 k, 0.1%, 0.1 W, 0603	603	RT0603BRD0784K5L	Yageo America
R29	1	453	RES, 453, 1%, 0.1 W, 0603	603	RC0603FR-07453RL	Yageo
R33	1	66.5k	RES, 66.5 k, 1%, 0.1 W, 0603	603	RC0603FR-0766K5L	Yageo
SH-J1, SH-J2, SH-J3, SH-J4	4	1x2	Shunt, 100mil, Gold plated, Black	Shunt	SNT-100-BK-G	Samtec
TP1, TP2, TP3, TP5, TP6, TP7, TP8, TP12, TP13, TP14, TP15, TP16, TP18, TP19, TP20, TP21, TP22, TP23	18		Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint	5010	Keystone
TP4, TP9, TP10, TP17, TP24, TP25	6		Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint	5011	Keystone Electronics
TP11, TP28, TP29	3		Connector, Receptacle, 50 ohm, TH	SMB Connector	SMBR004D00	JAE Electronics
U1, U2	2		4-V to 16-V Input, 25-A, Remote Sense, D-CAP4 Synchronous Buck Converter	WQFN-FCRLF16	TPS54KB20RZRR	Texas Instruments
C13	0	0.01uF	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X5R, 0402	402	GRM155R61C103KA01D	MuRata
C16, C53	0	560 pF	CAP, CERM, 560 pF, 100 V, +/- 10%, X7R, 0603	603	GRM188R72A561KA01D	MuRata
C21, C37	0	1uF	CAP, CERM, 1 μF, 25 V,+/- 20%, X5R, 0402	402	GRM155R61E105MA12D	MuRata
C23, C39	0	0.1uF	CAP, CERM, 0.1 uF, 35 V, +/- 10%, X5R, 0402	402	GMK105BJ104KV-F	Taiyo Yuden
C28, C29, C43, C44, C45	0	100uF	CAP, CERM, 100 µF, 6.3 V,+/- 20%, X6T, 1206	1206	GRM31CD80J107ME39L	MuRata
C31, C47	0	220 µF	Molded Tantalum Polymer Capacitor 220uF 20% 6.3V life 1000Hours SMD 2917	2917	6TCF220M5L	Panasonic
C49	0	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	402	CGA2B3X7R1H103K050 BB	TDK
C51	0	15 pF	CAP, CERM, 15 pF, 50 V,+/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	402	CGA2B2C0G1H150J050 BA	TDK
C54	0	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0402	402	C1005X7R1H104K050BB	TDK
D1	0	Green	LED, Green, SMD	LED_0603	150060GS75000	Wurth Elektronik
J10	0		Header(Shrouded), 2.54mm, 5x2, Gold, TH	Header, 2.54mm, 5x2, TH	AWHW-10G-0202-T	Assman WSW
R9, R18	0	5.1	RES, 5.10, 1%, 0.5 W, 1210	1210	RC1210FR-075R1L	Yageo
R27	0	0	RES, 0, 5%, 0.1 W, 0603	603	RC0603JR-070RL	Yageo
R28, R32	0	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603	CRCW06030000Z0EA	Vishay-Dale
R30	0	2.2k	RES, 2.2 k, 5%, 0.1 W, 0603	603	RC0603JR-072K2L	Yageo
R31	0	49.9	RES, 49.9, 1%, 0.1 W, 0603	603	RC0603FR-0749R9L	Yageo
R35, R36	0	10.0Meg	RES, 10.0 M, 1%, 0.1 W, AEC- Q200 Grade 0, 0603	603	CRCW060310M0FKEA	Vishay-Dale
TP26, TP27	0		Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint	5010	Keystone
U3	0		250 MHz, Rail-to-Rail I/O, CMOS Single Operational Amplifier, 2.5 to 5.5 V, -40 to 125 degC, 5-pin SOT23 (DBV5), Green (RoHS & no Sb/Br)	DBV0005A	OPA354AIDBVR	Texas Instruments

STANDARD TERMS FOR EVALUATION MODULES

- Delivery: TI delivers TI evaluation boards, kits, or modules, including any accompanying demonstration software, components, and/or
 documentation which may be provided together or separately (collectively, an "EVM" or "EVMs") to the User ("User") in accordance
 with the terms set forth herein. User's acceptance of the EVM is expressly subject to the following terms.
 - 1.1 EVMs are intended solely for product or software developers for use in a research and development setting to facilitate feasibility evaluation, experimentation, or scientific analysis of TI semiconductors products. EVMs have no direct function and are not finished products. EVMs shall not be directly or indirectly assembled as a part or subassembly in any finished product. For clarification, any software or software tools provided with the EVM ("Software") shall not be subject to the terms and conditions set forth herein but rather shall be subject to the applicable terms that accompany such Software
 - 1.2 EVMs are not intended for consumer or household use. EVMs may not be sold, sublicensed, leased, rented, loaned, assigned, or otherwise distributed for commercial purposes by Users, in whole or in part, or used in any finished product or production system.
- 2 Limited Warranty and Related Remedies/Disclaimers:
 - 2.1 These terms do not apply to Software. The warranty, if any, for Software is covered in the applicable Software License Agreement.
 - 2.2 TI warrants that the TI EVM will conform to TI's published specifications for ninety (90) days after the date TI delivers such EVM to User. Notwithstanding the foregoing, TI shall not be liable for a nonconforming EVM if (a) the nonconformity was caused by neglect, misuse or mistreatment by an entity other than TI, including improper installation or testing, or for any EVMs that have been altered or modified in any way by an entity other than TI, (b) the nonconformity resulted from User's design, specifications or instructions for such EVMs or improper system design, or (c) User has not paid on time. Testing and other quality control techniques are used to the extent TI deems necessary. TI does not test all parameters of each EVM. User's claims against TI under this Section 2 are void if User fails to notify TI of any apparent defects in the EVMs within ten (10) business days after the defect has been detected.
 - 2.3 Tl's sole liability shall be at its option to repair or replace EVMs that fail to conform to the warranty set forth above, or credit User's account for such EVM. Tl's liability under this warranty shall be limited to EVMs that are returned during the warranty period to the address designated by Tl and that are determined by Tl not to conform to such warranty. If Tl elects to repair or replace such EVM, Tl shall have a reasonable time to repair such EVM or provide replacements. Repaired EVMs shall be warranted for the remainder of the original warranty period. Replaced EVMs shall be warranted for a new full ninety (90) day warranty period.

WARNING

Evaluation Kits are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems.

User shall operate the Evaluation Kit within TI's recommended guidelines and any applicable legal or environmental requirements as well as reasonable and customary safeguards. Failure to set up and/or operate the Evaluation Kit within TI's recommended guidelines may result in personal injury or death or property damage. Proper set up entails following TI's instructions for electrical ratings of interface circuits such as input, output and electrical loads.

NOTE:

EXPOSURE TO ELECTROSTATIC DISCHARGE (ESD) MAY CAUSE DEGREDATION OR FAILURE OF THE EVALUATION KIT; TI RECOMMENDS STORAGE OF THE EVALUATION KIT IN A PROTECTIVE ESD BAG.

3 Regulatory Notices:

3.1 United States

3.1.1 Notice applicable to EVMs not FCC-Approved:

FCC NOTICE: This kit is designed to allow product developers to evaluate electronic components, circuitry, or software associated with the kit to determine whether to incorporate such items in a finished product and software developers to write software applications for use with the end product. This kit is not a finished product and when assembled may not be resold or otherwise marketed unless all required FCC equipment authorizations are first obtained. Operation is subject to the condition that this product not cause harmful interference to licensed radio stations and that this product accept harmful interference. Unless the assembled kit is designed to operate under part 15, part 18 or part 95 of this chapter, the operator of the kit must operate under the authority of an FCC license holder or must secure an experimental authorization under part 5 of this chapter.

3.1.2 For EVMs annotated as FCC – FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant:

CAUTION

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- · Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

3.2 Canada

3.2.1 For EVMs issued with an Industry Canada Certificate of Conformance to RSS-210 or RSS-247

Concerning EVMs Including Radio Transmitters:

This device complies with Industry Canada license-exempt RSSs. Operation is subject to the following two conditions:

(1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concernant les EVMs avec appareils radio:

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes: (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concerning EVMs Including Detachable Antennas:

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication. This radio transmitter has been approved by Industry Canada to operate with the antenna types lated in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotrope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante. Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur

3.3 Japan

- 3.3.1 Notice for EVMs delivered in Japan: Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_01.page 日本国内に輸入される評価用キット、ボードについては、次のところをご覧ください。
 - https://www.ti.com/ja-jp/legal/notice-for-evaluation-kits-delivered-in-japan.html
- 3.3.2 Notice for Users of EVMs Considered "Radio Frequency Products" in Japan: EVMs entering Japan may not be certified by TI as conforming to Technical Regulations of Radio Law of Japan.

If User uses EVMs in Japan, not certified to Technical Regulations of Radio Law of Japan, User is required to follow the instructions set forth by Radio Law of Japan, which includes, but is not limited to, the instructions below with respect to EVMs (which for the avoidance of doubt are stated strictly for convenience and should be verified by User):

- 1. Use EVMs in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
- 2. Use EVMs only after User obtains the license of Test Radio Station as provided in Radio Law of Japan with respect to EVMs, or
- 3. Use of EVMs only after User obtains the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to EVMs. Also, do not transfer EVMs, unless User gives the same notice above to the transferee. Please note that if User does not follow the instructions above. User will be subject to penalties of Radio Law of Japan.

【無線電波を送信する製品の開発キットをお使いになる際の注意事項】 開発キットの中には技術基準適合証明を受けていないものがあります。 技術適合証明を受けていないもののご使用に際しては、電波法遵守のため、以下のいずれかの 措置を取っていただく必要がありますのでご注意ください。

- 1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用 いただく。
- 2. 実験局の免許を取得後ご使用いただく。
- 3. 技術基準適合証明を取得後ご使用いただく。
- なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。 上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。 日本テキサス・イ

ンスツルメンツ株式会社

東京都新宿区西新宿6丁目24番1号

西新宿三井ビル

- 3.3.3 Notice for EVMs for Power Line Communication: Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_02.page 電力線搬送波通信についての開発キットをお使いになる際の注意事項については、次のところをご覧ください。https://www.ti.com/ja-jp/legal/notice-for-evaluation-kits-for-power-line-communication.html
- 3.4 European Union
 - 3.4.1 For EVMs subject to EU Directive 2014/30/EU (Electromagnetic Compatibility Directive):

This is a class A product intended for use in environments other than domestic environments that are connected to a low-voltage power-supply network that supplies buildings used for domestic purposes. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

- 4 EVM Use Restrictions and Warnings:
 - 4.1 EVMS ARE NOT FOR USE IN FUNCTIONAL SAFETY AND/OR SAFETY CRITICAL EVALUATIONS, INCLUDING BUT NOT LIMITED TO EVALUATIONS OF LIFE SUPPORT APPLICATIONS.
 - 4.2 User must read and apply the user guide and other available documentation provided by TI regarding the EVM prior to handling or using the EVM, including without limitation any warning or restriction notices. The notices contain important safety information related to, for example, temperatures and voltages.
 - 4.3 Safety-Related Warnings and Restrictions:
 - 4.3.1 User shall operate the EVM within TI's recommended specifications and environmental considerations stated in the user guide, other available documentation provided by TI, and any other applicable requirements and employ reasonable and customary safeguards. Exceeding the specified performance ratings and specifications (including but not limited to input and output voltage, current, power, and environmental ranges) for the EVM may cause personal injury or death, or property damage. If there are questions concerning performance ratings and specifications, User should contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may also result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM user guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, even with the inputs and outputs kept within the specified allowable ranges, some circuit components may have elevated case temperatures. These components include but are not limited to linear regulators, switching transistors, pass transistors, current sense resistors, and heat sinks, which can be identified using the information in the associated documentation. When working with the EVM, please be aware that the EVM may become very warm.
 - 4.3.2 EVMs are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems. User assumes all responsibility and liability for proper and safe handling and use of the EVM by User or its employees, affiliates, contractors or designees. User assumes all responsibility and liability to ensure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard. User assumes all responsibility and liability for any improper or unsafe handling or use of the EVM by User or its employees, affiliates, contractors or designees.
 - 4.4 User assumes all responsibility and liability to determine whether the EVM is subject to any applicable international, federal, state, or local laws and regulations related to User's handling and use of the EVM and, if applicable, User assumes all responsibility and liability for compliance in all respects with such laws and regulations. User assumes all responsibility and liability for proper disposal and recycling of the EVM consistent with all applicable international, federal, state, and local requirements.
- 5. Accuracy of Information: To the extent TI provides information on the availability and function of EVMs, TI attempts to be as accurate as possible. However, TI does not warrant the accuracy of EVM descriptions, EVM availability or other information on its websites as accurate, complete, reliable, current, or error-free.

6. Disclaimers:

- 6.1 EXCEPT AS SET FORTH ABOVE, EVMS AND ANY MATERIALS PROVIDED WITH THE EVM (INCLUDING, BUT NOT LIMITED TO, REFERENCE DESIGNS AND THE DESIGN OF THE EVM ITSELF) ARE PROVIDED "AS IS" AND "WITH ALL FAULTS." TI DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, REGARDING SUCH ITEMS, INCLUDING BUT NOT LIMITED TO ANY EPIDEMIC FAILURE WARRANTY OR IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF ANY THIRD PARTY PATENTS, COPYRIGHTS, TRADE SECRETS OR OTHER INTELLECTUAL PROPERTY RIGHTS.
- 6.2 EXCEPT FOR THE LIMITED RIGHT TO USE THE EVM SET FORTH HEREIN, NOTHING IN THESE TERMS SHALL BE CONSTRUED AS GRANTING OR CONFERRING ANY RIGHTS BY LICENSE, PATENT, OR ANY OTHER INDUSTRIAL OR INTELLECTUAL PROPERTY RIGHT OF TI, ITS SUPPLIERS/LICENSORS OR ANY OTHER THIRD PARTY, TO USE THE EVM IN ANY FINISHED END-USER OR READY-TO-USE FINAL PRODUCT, OR FOR ANY INVENTION, DISCOVERY OR IMPROVEMENT, REGARDLESS OF WHEN MADE, CONCEIVED OR ACQUIRED.
- 7. USER'S INDEMNITY OBLIGATIONS AND REPRESENTATIONS. USER WILL DEFEND, INDEMNIFY AND HOLD TI, ITS LICENSORS AND THEIR REPRESENTATIVES HARMLESS FROM AND AGAINST ANY AND ALL CLAIMS, DAMAGES, LOSSES, EXPENSES, COSTS AND LIABILITIES (COLLECTIVELY, "CLAIMS") ARISING OUT OF OR IN CONNECTION WITH ANY HANDLING OR USE OF THE EVM THAT IS NOT IN ACCORDANCE WITH THESE TERMS. THIS OBLIGATION SHALL APPLY WHETHER CLAIMS ARISE UNDER STATUTE, REGULATION, OR THE LAW OF TORT, CONTRACT OR ANY OTHER LEGAL THEORY, AND EVEN IF THE EVM FAILS TO PERFORM AS DESCRIBED OR EXPECTED.

- 8. Limitations on Damages and Liability:
 - 8.1 General Limitations. IN NO EVENT SHALL TI BE LIABLE FOR ANY SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL, OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THESE TERMS OR THE USE OF THE EVMS, REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. EXCLUDED DAMAGES INCLUDE, BUT ARE NOT LIMITED TO, COST OF REMOVAL OR REINSTALLATION, ANCILLARY COSTS TO THE PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES, RETESTING, OUTSIDE COMPUTER TIME, LABOR COSTS, LOSS OF GOODWILL, LOSS OF PROFITS, LOSS OF SAVINGS, LOSS OF USE, LOSS OF DATA, OR BUSINESS INTERRUPTION. NO CLAIM, SUIT OR ACTION SHALL BE BROUGHT AGAINST TIMORE THAN TWELVE (12) MONTHS AFTER THE EVENT THAT GAVE RISE TO THE CAUSE OF ACTION HAS OCCURRED.
 - 8.2 Specific Limitations. IN NO EVENT SHALL TI'S AGGREGATE LIABILITY FROM ANY USE OF AN EVM PROVIDED HEREUNDER, INCLUDING FROM ANY WARRANTY, INDEMITY OR OTHER OBLIGATION ARISING OUT OF OR IN CONNECTION WITH THESE TERMS, , EXCEED THE TOTAL AMOUNT PAID TO TI BY USER FOR THE PARTICULAR EVM(S) AT ISSUE DURING THE PRIOR TWELVE (12) MONTHS WITH RESPECT TO WHICH LOSSES OR DAMAGES ARE CLAIMED. THE EXISTENCE OF MORE THAN ONE CLAIM SHALL NOT ENLARGE OR EXTEND THIS LIMIT.
- 9. Return Policy. Except as otherwise provided, TI does not offer any refunds, returns, or exchanges. Furthermore, no return of EVM(s) will be accepted if the package has been opened and no return of the EVM(s) will be accepted if they are damaged or otherwise not in a resalable condition. If User feels it has been incorrectly charged for the EVM(s) it ordered or that delivery violates the applicable order, User should contact TI. All refunds will be made in full within thirty (30) working days from the return of the components(s), excluding any postage or packaging costs.
- 10. Governing Law: These terms and conditions shall be governed by and interpreted in accordance with the laws of the State of Texas, without reference to conflict-of-laws principles. User agrees that non-exclusive jurisdiction for any dispute arising out of or relating to these terms and conditions lies within courts located in the State of Texas and consents to venue in Dallas County, Texas. Notwithstanding the foregoing, any judgment may be enforced in any United States or foreign court, and TI may seek injunctive relief in any United States or foreign court.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated