

# TPS659039-Q1 User's Guide to Power DRA74x, DRA75x, TDA2x, and AM572x

This User's Guide can be used as a guide for integrating the TPS659039-Q1 power-management integrated circuit (PMIC) into a system powering the DRA74x, DRA75x, TDA2x, or AM572x device.

#### **Contents**

1	Introd	uction	3
2	Device	e Versions	3
3	Platfo	rm Connection	4
4		OTP Configuration	
5		Platform Settings	
	5.1	System Voltage Monitoring	
	5.2	SMPS	
	5.3	LDO	
	5.4	Interrupts	
	5.5	GPIO	
	5.6	MISC	
	5.7	SWOFF_HWRST	
^	5.8	Shutdown_ColdReset	
6	•	ence Platform Settings	
	6.1 6.2	OFF2ACT Sequences	
	6.3	ACT2OFF Sequences	
	6.4	Warm Reset Sequences	
	0.4	Walli Nesel Sequelices	20
		List of Figures	
1	Proces	ssor Connection With O9039A387IZWSRQ1	4
2	Proces	ssor Connection With O9039A385IZWSRQ1	5
3	Proces	ssor Connection With O9039A389IZWSRQ1	6
4	Reset	Connections With POWERHOLD Configuration	7
5	Reset	Connections With PWRON Configuration	7
6	PMIC	Comparators	8
7	State	Transitions	8
8	Reset	Levels versus Registers	13
9	OFF2	ACT Sequence of O9039A387IZWSRQ1	16
10	OFF2	ACT Sequence of O9039A385IZWSRQ1	17
11	OFF2	ACT Sequence of O9039A389IZWSRQ1	18
12	ACT2	SLP and SLP2ACT Sequences of O9039A387IZWSRQ1	20
13	ACT2	SLP and SLP2ACT Sequences of O9039A385IZWSRQ1	21
14	ACT2	SLP and SLP2ACT Sequences of O9039A389IZWSRQ1	22
15	Warm	Reset Sequence of O9039A387IZWSRQ1	24
16	Warm	Reset Sequence of O9039A385IZWSRQ1	25
17	Warm	Reset Sequence of O9039A389IZWSRQ1	26





1	TPS659039-Q1 OTP Settings Differentiation	. 3
2	Differences from Older OTP Versions	3
3	System Voltage Monitoring OTP Settings	8
4	SMPS OTP Settings	ę
5	LDO OTP Settings	10
6	INT1 OTP Settings	
7	INT2 OTP Settings	10
8	INT3 OTP Settings	11
9	INT4 OTP Settings	11
10	GPIO OTP Settings	
11	MISC1 OTP Settings	12
12	MISC2 OTP Settings	12
13	SWOFF_HWRST OTP Settings	13
14	Shutdown_ColdReset OTP Settings	14
	3 4 5 6 7 8 9 10 11 12 13	Differences from Older OTP Versions  System Voltage Monitoring OTP Settings  LDO OTP Settings  INT1 OTP Settings  INT2 OTP Settings  INT3 OTP Settings  INT4 OTP Settings  MISC1 OTP Settings  SWOFF_HWRST OTP Settings

# **Trademarks**

All trademarks are the property of their respective owners.

2



www.ti.com Introduction

#### 1 Introduction

This user's guide can be used as a guide for connectivity between the TPS659039-Q1 PMIC and a processor. This guide describes the platform connections as well as the power-up, power-down, and sleep entry and exit sequences along with the OTP configurations. In addition, this user's guide describes the initialization software and advises how to get started with the TPS659039-Q1 PMIC. This document does not provide details about the power resources, external components, or the functionality of the device. For such information, see the TPS659038-Q1 and TPS659039-Q1 data sheet, *TPS65903x-Q1 Automotive Power Management Unit (PMU) for Processor*.

In the event of any inconsistency between the official specification and any user's guide, application report, or other referenced material, the data sheet specification will be the definitive source.

#### 2 Device Versions

Three different versions of the TPS659039-Q1 device are available and the OTP settings for each version are described in this document. The three different versions of the device can be used to power the DRA74x, DRA75x, TDA2x, and AM572x processor devices. The OTP version can be read from the SW\_REVISION register. In this user's guide, each device version is distinguished either by the part number or the SW\_REVISION value which are both listed in Table 1.

In addition, the TPS65917-Q1 device can be used to power the DRA74x, DRA75x, and TDA2x devices as described in the *TPS65917-Q1 User's Guide to Power DRA7xx and TDA2x/TDA2Ex*. See Table 1 to determine the recommended part number based on the load current requirements of the MPU, DSPEVE, GPU, and IVA domains of the processor.

Texas Instruments recommends having 15% margin in the load current. Therefore the current requirements listed in Table 1 are 15% lower than the maximum capability of the regulator. If the load currents in the application are unknown, select the O9039A385IZWSRQ1 because it supports the maximum performance of the processors.

CONTENT OF ORDERABI E PART LOAD CURRENT REQUIREMENT SLEEP MODE POWERGOOD SPECIAL FEATURES NUMBER REGISTER MPU > 3 A or DSPEVE + GPU + IVA > 3.4 A Yes O9039A385IZWSRQ1 0x85 Yes Integrated DDR regulator MPU > 3 A or DSPEVE + GPU + IVA > 3.4 A Same configuration as DRA74x EVM External DDR regulator Yes Yes O9039A387IZWSRQ1 MPU > 3 A or 3 A < DSPEVE + GPU + IVA < 3.4 A 2 SMPS regulators for external use Integrated DDR regulator Yes Yes O9039A389IZWSRQ1 0x89 MPU < 3 A and No Yes Smaller, lower-power solution O917A132TRGZRQ1 DSPEVE + GPU + IVA < 3 A See User's Guide MPU < 3 A and Yes No Smaller, lower-power solution O917A133TRGZRQ1 DSPEVE + GPU + IVA < 3 A

Table 1. TPS659039-Q1 OTP Settings Differentiation

Table 2 lists the older OTP versions and the differences compared to the current OTP versions. The older versions are not recommended for new designs (NRND). The newer versions should be used instead because they meet the latest specifications of the processor, and are pin-to-pin replacements for the older versions with no schematic or layout change required.

Table 2. Differences from Older OTP Versions

OLDER OTP VERSION	NEWER OTP VERSION	CHANGES IMPLEMENTED IN NEWER VERSION
O9039A344IZWSRQ1	O9039A387IZWSRQ1	SMPS123 voltage increased from 1.10 V to 1.15 V SMPS7 voltage increased from 1.06 V to 1.15 V
O9039A360IZWSRQ1	O9039A385IZWSRQ1	SMPS12 voltage increased from 1.10 V to 1.15 V SMPS7 voltage increased from 1.06 V to 1.15 V
O9039A36BIZWSRQ1	O9039A389IZWSRQ1	SMPS12 voltage increased from 1.10 V to 1.15 V SMPS6 voltage increased from 1.06 V to 1.15 V

<sup>(1)</sup> TI only recommends 0x87 if copying the DRA74x EVM reference design.



Platform Connection www.ti.com

#### 3 Platform Connection

Figure 1 shows the detailed connections between a processor and the O9039A387IZWSRQ1 (0x87). In this configuration, the VIO\_IN of the PMIC is supplied by SMPS9 at 1.8 V. If the VIO\_IN of the PMIC is supplied by 3.3 V, it can be supplied by an externally switched 3.3-V rail enabled by SMPS9.




Figure 1. Processor Connection With O9039A387IZWSRQ1

Figure 2 shows the detailed connections between the processor and the O9039A385IZWSRQ1 (0x85). The main difference between 0x85 and 0x87 is that the DDR voltage is supplied by the SMPS3 of the PMIC instead of an external regulator. The configuration allows selection between a 1.35-V output on SMPS3 supporting DDR3L and a 1.5-V output supporting DDR3. Additionally, this PMIC device does not use an external crystal. In this configuration, VIO\_IN of the PMIC is driven by the 3.3-V output of the load switch, TPS22965-Q1.



www.ti.com Platform Connection




Figure 2. Processor Connection With O9039A385IZWSRQ1

Figure 3 shows the detailed connections between the processor and O9039A389IZWSRQ1 (0x89). This configuration uses a different power mapping where the DSPEVE, GPU, and IVAHD domains of the processor are powered from the single output SMPS45. The core domain of the processor is powered by SMPS6. The VDD\_1V8 domain of the processor is powered by SMPS8. This configuration allows selection between a 1.35-V output on SMPS3 supporting DDR3L and a 1.5-V output supporting DDR3. Additionally, this PMIC device does not use an external crystal. In this configuration, VIO\_IN of the PMIC is driven by the 3.3-V output of the load switch, TPS22965-Q1.



Platform Connection www.ti.com




Figure 3. Processor Connection With O9039A389IZWSRQ1

Figure 4 and Figure 5 show the reset connections required between the TPS659039-Q1 and the processor. All of the OTP configurations have the same reset connections to the processor, along with one of the two options for enabling the power supply; either POWERHOLD or PWRON. Enabling either of these signals turns on the TPS659039-Q1 device and starts the startup sequence for the processor. Figure 4 shows the POWERHOLD configuration for the TPS659039-Q1 and the processor. GPIO\_7 is configured as POWERHOLD in the OTP memory. To turn on the TPS659039-Q1, GPIO\_7 must be set to a high logic level. When using POWERHOLD, the PWRON signal can be left floating.



www.ti.com Platform Connection




Figure 4. Reset Connections With POWERHOLD Configuration

Figure 5 shows the PWRON configuration for the TPS659039-Q1 and the processor. This configuration is used when a push button enables the system. As shown, PWRON is connected to a switch that pulls PWRON to a low logic level when the switch is pressed on.

In some applications, a warm reset is required. This allows for the TPS659039-Q1 to reset to its default settings without turning off first. To complete a warm reset correctly, POWERHOLD must be kept at a high logic level so the TPS659039-Q1 does not turn off. One solution for this scenario is that GPIO\_5 is tied to GPIO\_7 and pulled up to VDDS1V8 from the processor. Pulling GPIO\_7 to VDDS1V8 ensures that POWERHOLD is kept high during a warm reset. Tying GPIO\_5 to POWERHOLD provides a method to set POWERHOLD low, which is necessary to turn off the device.

For this solution to work, a few software writes must occur:

- 1. First, enable the TPS659039-Q1 by the push button.
- Second, set GPIO\_5 to a high logic level.
- 3. Third, set GPIO\_5 as an output.

When ready to disable the TPS659039-Q1, set GPIO 5 to a low logic level.




Figure 5. Reset Connections With PWRON Configuration



#### 4 BOOT OTP Configuration

All TPS659039-Q1 resource settings are stored in the form of registers. Therefore, all platform-related settings are linked to an action altering these registers. This action can be a static update (register initialization value) or a dynamic update of the register (either from the user or from a power sequence).

Resources and platform settings are stored in nonvolatile memory (OTP). These settings are defined as follows:

**Static platform settings** — These settings define, for example, SMPS or LDO default voltages, and GPIO functionality. Most static platform settings can be overwritten by a power sequence or by the user.

**Sequence platform settings** —These settings define the TPS659039-Q1 power sequences between state transitions, such as the OFF2ACT sequence when transitioning from OFF mode to ACTIVE mode. The power sequence is composed of several register accesses that define which resources (and the corresponding registers) must be updated during the respective state transition. The state of these resources can be overwritten by the user after the power sequence completes execution.

# 5 Static Platform Settings

Each device has predefined values stored in OTP which control the default configuration of the device. The tables in this section list the OTP-programmed values for each device, distinguished by the SW\_REVISION.

#### 5.1 System Voltage Monitoring

**Table 3. System Voltage Monitoring OTP Settings** 

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE	UNIT
VSYS_MON	VSYS_HI	System voltage rising-edge threshold		3.1		V
VSYS_LO	VSYS_LO	System voltage falling-edge threshold		2.75		V

The power state-machine of the TPS659039-Q1 device is controlled by comparators monitoring the voltage on the VCC SENSE and VCCx pins. For electrical parameters refer to the data sheet.

VSYS\_LO —When the voltage on the VCC1 pin rises above VSYS\_LO, the device enters from the BACKUP to the OFF state. When the device is in the ACTIVE, SLEEP, or OFF state and the voltage on the VCC1 pin decreases below VSYS\_LO, the device enters BACKUP mode. The VSYS\_LO level is OTP programmable.

VSYS\_HI — During power up, the VSYS\_HI OTP value is used as a threshold for the VSYS\_MON comparator which is gating the PMIC startup (as a threshold for transition from the OFF to ACTIVE state). The VSYS\_MON comparator monitors the VCC\_SENSE pin. After power up, the user can use software to configure the comparator threshold in the VSYS\_MON register.



www.ti.com Static Platform Settings




Figure 6. PMIC Comparators

Figure 7. State Transitions

NOTE: The maximum input voltage of the VCC\_SENSE and VCC\_SENSE2 pins depend on the OTP setting of PMU\_CONFIG [HIGH\_VCC\_SENSE] as listed in the *Recommended Operating Conditions* table of the TPS659039-Q1 data sheet. This configuration is set as HIGH\_VCC\_SENSE = 0 with the VCC\_SENSE and VCC\_SENSE2 pins are connected to VCC1.

For the recommended operating conditions of the electrical parameters, see the TPS659038-Q1 and TPS659039-Q1 data sheet, *TPS65903x-Q1 Automotive Power Management Unit (PMU) for Processor.* 

#### 5.2 SMPS

This section describes the default voltage for each SMPS. The 0x87 OTP uses SMPS123 in triple phase. Therefore, SMPS12 and SMPS3 are combined and always output the same voltage programmed in to the SMPS12\_VOLTAGE register. The 0x85 and 0x89 OTP have two default voltages for SMPS3 based on the connection of the BOOT0 pin. If the BOOT0 pin is connected to 0 V, then SMPS3 defaults to 1.35 V. If the BOOT0 pin is connected to 1.8 V, then SMPS3 outputs 1.5 V.

By default, SMPS7 and SMPS9 remain off in OTP 0x89. SMPS7 and SMPS9 can be enabled after startup through I<sup>2</sup>C by setting the appropriate SMPSx\_CTRL and SMPSx\_VOLTAGE registers.

			J				
BIT	DESCRIPTION <sup>(1)</sup>	0x87 VALUE	0x85 VALUE		0x89 VALUE		LIMIT
DII	DESCRIPTION	UX87 VALUE	BOOT0 = 0	BOOT0 = 1	BOOT0 = 0	BOOT0 = 1	UNIT
SMPS12_VOLTAGE	Default output voltage for the regulator			1.15			V
SMPS3_VOLTAGE	Default output voltage for the regulator	N/A	1.35	1.5	1.35	1.5	V
SMPS45_VOLTAGE	Default output voltage for the regulator			1.06			V
SMPS6_VOLTAGE	Default output voltage for the regulator		1.06		1	.15	V
SMPS7_VOLTAGE	Default output voltage for the regulator	1.15 0		1.15		0	V
SMPS8_VOLTAGE	Default output voltage for the regulator	1.06 1.8		1.06		1.8	V
SMPS9_VOLTAGE	Default output voltage for the regulator	1.8		r 1.8 0		0	V
SMPS12_SMPS123_EN	SMPS3 configuration	SMPS123 triple SMPS3 single phase		phase		NA	

**Table 4. SMPS OTP Settings** 

<sup>(1)</sup> The regulator output voltage cannot be modified while active from one (0.7 to 1.65 V) voltage range to the other (1 to 3.3 V) voltage range or the other way around. The regulator must be turned off to do so.



Static Platform Settings www.ti.com

#### 5.3 **LDO**

This section describes the default output voltage for each LDO.

**Table 5. LDO OTP Settings** 

BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE	UNIT
LDO1_VOLTAGE	Default output voltage for the regulator		3.3		V
LDO2_VOLTAGE	Default output voltage for the regulator		3.3		V
LDO3_VOLTAGE	Default output voltage for the regulator		1.8		V
LDO9_VOLTAGE	Default output voltage for the regulator		1.05		V
LDOLN_VOLTAGE	Default output voltage for the regulator		1.8		V
LDOUSB_VOLTAGE	Default output voltage for the regulator		3.3		V

NOTE: LDO1 and LDO2 share a single input LDO12\_IN and must by supplied by the same voltage. Refer to the input voltage parameter in the data sheet.

#### 5.4 Interrupts

The interrupts are split into four register groups (INT1, INT2, INT3, and INT4). All interrupts are logically combined on a single output line, INT (default active-low). This line is used as an external interrupt line to warn the host processor of any interrupt event that has occurred within the device. The OTP settings in this section show whether each interrupt is enabled or disabled by default.

**Table 6. INT1 OTP Settings** 

REGISTER	BIT	DESCRIPTION	0x87 VALUE 0x85 VALUE 0x89 V		0x89 VALUE	
	VSYS_MON	Enable and disable interrupt from the VSYS_MON comparator		d		
	PWRDOWN	Enable and disable interrupt from the PWRDOWN pin	0: Interrupt generated			
	PWRON	Enable and disable interrupt from PWRON pin. A PWRON event is always an ON request.	1: Interrupt generation disabled		i	
INT1_MASK	LONG_PRESS_KEY	Enable and disable interrupt from long key press on the PWRON pin	1: Interrupt generation disabled			
	RPWRON	Enable and disable interrupt from RPWRON pin. A RPWRON event is always an ON request.	0: Interrupt generated			
	HOTDIE	Enable and disable interrupt from device hot-die detection. The interrupt can be used as a pre-warning for processor to limit the PMIC load, before increasing die temperature forces shutdown.	0: Interrupt generated			

**Table 7. INT2 OTP Settings** 

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE
	SHORT	Triggered from internal event of SMPS or LDO outputs failing. If an interrupt is enabled, it is an ON request.			
	WDT	Enable and disable interrupt from watchdog expiration	0: Interrupt generated		
INT2_MASK	RTC_TIMER	Enable and disable RTC timer interrupt. Timer period preprogrammed. If an interrupt is enabled, it is an ON request.	1: Interrupt generation disabled		
	RTC_ALARM	Enable and disable RTC alarm interrupt. The alarm is preprogrammed for certain date or time. If an interrupt is enabled, it is an ON request.			
	RESET_IN	Enable and disable interrupt from the RESET_IN pin	0: Interrupt generated		



www.ti.com Static Platform Settings

# **Table 8. INT3 OTP Settings**

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE	
	GPADC_EOC_SW	GPADC result ready from software- initiated conversion	1: Interrupt generation disabled			
INT3_MASK	GPADC_AUTO_1	GPADC automatic conversion result 1 above or below the reference threshold	0: Interrupt generated			
	GPADC_AUTO_0	GPADC automatic conversion result 0 above or below the reference threshold	0: Interrupt generated			

# **Table 9. INT4 OTP Settings**

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE		
	GPIO_7	Enable and disable interrupt from the GPIO7 pin rising or falling edge	1: Interrupt generation disabled				
	GPIO_6	Enable and disable interrupt from the GPIO6 pin rising or falling edge		1: Interrupt generation disabled			
	GPIO_5	Enable and disable interrupt from the GPIO5 pin rising or falling edge	1: Interrupt generation disabled		i		
INT4 MASK	GPIO_4	Enable and disable interrupt from the GPIO4 pin rising or falling edge	1: Interrupt generation disabled				
INT4_MASK	GPIO_3	Enable and disable interrupt from the GPIO3 pin rising or falling edge	1: Interrupt generation disabled				
	GPIO_2	Enable and disable interrupt from the GPIO2 pin rising or falling edge	1: Interrupt generation disabled		1		
	GPIO_1	Enable and disable interrupt from the GPIO1 pin rising or falling edge	1: Interrupt generation disabled		i		
	GPIO_0	Enable and disable interrupt from the GPIO0 pin rising or falling edge		1: Interrupt generation disabled	i		

#### 5.5 **GPIO**

TPS659039-Q1 integrates eight configurable general-purpose I/Os (GPIOs) that are multiplexed with alternative features. This section describes the default configuration of each GPIO, as well as the configuration of internal pullup or pulldown resistors on the GPIOs.

**Table 10. GPIO OTP Settings** 

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE		
	GPIO_7 Select pin function		10: POWERHOLD				
PRIMARY SECONDARY PAD2	GPIO_6	Select pin function		1: SYSEN2			
PRIMART_SECONDART_PAD2	GPIO_5	Select pin function		00: GPIO_5			
	GPIO_4	Select pin function		1: SYSEN1			
PRIMARY SECONDARY PAD1	GPIO_2	Select pin function		00: GPIO_2			
PRIMARY_SECONDARY_PADI	GPIO_1	Select pin function		00: GPIO_1			
PU_PD_GPIO_CTRL2  GPIO_7_PD  Enable and disable pulldown for GPIO_7. Applies if GPIO mode is selected		0: Pulldown not enabled					
	GPIO_3_PD	Enable and disable pulldown for GPIO_3. Applies if GPIO mode is selected	1: Pulldown enabled				
	GPIO_2_PU	Enable and disable pullup for GPIO_2. Applies if GPIO mode is selected	0: Pullup not enabled				
PU PD GPIO CTRL1	GPIO_2_PD	Enable and disable pulldown for GPIO_2. Applies if GPIO mode is selected	1: Pulldown enabled				
PO_PD_GPIO_CIRCI	GPIO_1_PU	Enable and disable pullup for GPIO_1. Applies if GPIO mode is selected		0: Pullup not enabled			
	GPIO_1_PD	Enable and disable pulldown for GPIO_1. Applies if GPIO mode is selected	1: Pulldown enabled				
	GPIO_0_PD	Enable and disable pulldown for GPIO_0. Applies if GPIO mode is selected	0: Pulldown not enabled				



Static Platform Settings www.ti.com

# 5.6 MISC

This section describes miscellaneous device configuration settings including pulldowns, polarity of signals, communication settings, and other functionality.

# Table 11. MISC1 OTP Settings

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE
PRIMARY SECONDARY PAD2	RESET_IN_PD	Enable and disable internal pulldown for the RESET_IN pin		1: Pulldown enabled	
PRIMART_SECONDART_PAD2	PWRDOWN_PD	Enable and disable internal pulldown for the PWRDOWN pin		1: Pulldown enabled	
	PWRGOOD_USB_ PSELPOLARITY_	Select polarity, applies to PWRGOOD and USB_PSEL selection		0: Active high	
POLARITY_CTRL	PWRDOWN_POLARITY	Select PWRDOWN pin polarity: 0: Device is switched off when PWRDOWN is high. 1: Device is switched off when PWRDOWN is low.		0: Active high	
	RESET_IN_POLARITY	Select RESET_IN pin polarity: 0: Device is switched off when RESET_IN is low. 1: Device is switched off when RESET_IN is high.		0: Active low	
	GPIO_3_POLARITY	Select polarity for GPIO3 pin:		0: Active high	

# **Table 12. MISC2 OTP Settings**

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE
LONG_PRESS_KEY	PWRON_DEBOUNCE	Debounce time selection for PWRON pin	00: 15 ms		
I2C_SPI	I2C_SPI	Selection of control interface, I <sup>2</sup> C, or SPI	0: I <sup>2</sup> C		
	ID_I2C2	I2C_2 address for page access versus initial address (0H12)	0: Address is 0x12		
	ID_I2C1	I2C_1 address for I <sup>2</sup> C register access	12C_1[0] = 1: 0x58 12C_1[1] = 1: 0x59 12C_1[2] = 1: 0x5A 12C_1[3] = 1: 0x5B		
PMU_CONFIG	HIGH_VCC_SENSE	Enable internal buffers on VCC_SENSE to allow voltage sensing above 5.25 V	0: High VCC sense not enabled		
	GATE_RESET_OUT	Gating of RESET_OUT until crystal oscillator is stable.	0: Not gated		
	AUTODEVON	Automatically set DEV_ON bit after startup sequence completes	0: AUTODEVON disabled		
	SWOFF_DLY	Delay before switch-off to allow host processor to save context. Device is maintained as ACTIVE until delay expiration then switches off.	00: No delay		
SPARE	REGEN2_OD	Configures REGEN2 to be open drain or push-pull.	0: Push-pull mode		
	REGEN1_OD	Configures REGEN1 to be open drain or push-pull.	0: Push-pull mode		
	OSC16M_CFG	16-MHz crystal is disabled and the 32K bypass is Enable	0: 16-MHz oscillator enabled	1: 16-MHz oscilla	tor disabled



www.ti.com Static Platform Settings

#### 5.7 SWOFF HWRST

This section describes whether each reset type is configured to generate a HWRST or SWORST.

**Hardware reset (HWRST)** —A hardware reset occurs when any OFF request is configured to generate a hardware reset. This reset triggers a transition to the OFF state from either the ACTIVE or SLEEP state (execute either the ACT2OFF or SLP2OFF sequence).

**Switch-off reset (SWORST)** —A switch-off reset occurs when any OFF request is configured to not generate a hardware reset. This reset acts as the HWRST, except only the SWO registers are reset. The device enters the OFF state, from either ACTIVE or SLEEP, and therefore executes the ACT2OFF or SLP2OFF sequence.

The power resource control registers for SMPS and LDO voltage levels and operating mode control are in SWORST domain. Additionally some registers control the 32-kHz, REGENx and SYSENx, watchdog, and VSYS MON comparator. This list is indicative only.




Figure 8. Reset Levels versus Registers

#### Table 13. SWOFF\_HWRST OTP Settings

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE
SWOFF_HWRST	PWRON_LPK	Define if PWRON long key press is causing HWRST or SWORST		1: HWRST	
	PWRDOWN	Define if PWRDOWN pin is causing HWRST or SWORST		0: SWORST	
	WTD	Define if watchdog expiration is causing HWRST or SWORST		1: HWRST	
	TSHUT	Define if thermal shutdown is causing HWRST or SWORST		1: HWRST	
	RESET_IN	Define if RESET_IN pin is causing HWRST or SWORST		1: HWRST	
	SW_RST	Define if register bit is causing HWRST or SWORST		1: HWRST	
	VSYS_LO	Define if VSYS_LO is causing HWRST or SWORST		1: HWRST	
	GPADC_SHUTDOWN	Define if GPADC event is causing HWRST or SWORST	0: SWORST		



Static Platform Settings www.ti.com

#### 5.8 Shutdown ColdReset

These OTP settings show whether each OFF request is configured to generate a shutdown request (SD) or cold reset request (CR).

- When configured to generate an SD, the embedded power controller (EPC) executes a transition to the OFF state (SLP2OFF or ACT2OFF power sequence) and remains in the OFF state.
- When configured to generate a CR, the EPC executes a transition to the OFF state (SLP2OFF or ACT2OFF power sequence) and restarts, transitioning to the ACTIVE state (OFF2ACT power sequence) if none of the ON request gating conditions are present.

Table 14. Shutdown\_ColdReset OTP Settings

REGISTER	BIT	DESCRIPTION	0x87 VALUE	0x85 VALUE	0x89 VALUE
	PWRON_LPK	Define if PWRON long key press causes shutdown or cold reset	0: Shutdown		
	PWRDOWN	Define if PWRDOWN pin causes shutdown or cold reset	1: Cold reset		
	WTD	Define if watchdog timer expiration causes shutdown or cold reset	1: Cold reset		
SWOFF COLDRST	TSHUT	Define if thermal shutdown causes shutdown or cold reset	0: Shutdown		
SWOFF_COLDR31	RESET_IN	Define if RESET_IN pin causes shutdown or cold reset	1: Cold reset		
	SW_RST	Define if SW_RST register bit causes shutdown or cold reset	1: Cold reset		
	VSYS_LO	Define if VSYS_LO causes shutdown or cold reset	0: Shutdown		
	GPADC_SHUTDOWN	Define if GPADC shutdown causes shutdown or cold reset	0: Shutdown		



# 6 Sequence Platform Settings

A power sequence is an automatic preprogrammed sequence handled by the TPS659039-Q1 device to configure the device resources: SMPSs, LDOs, part of GPIOs, and REGEN signals into ON, OFF, or SLEEP state.

# 6.1 OFF2ACT Sequences

When an ON request occurs in the OFF state, the device is switched on and each resource is enabled based on the programmed OFF2ACT sequence.



Figure 9 shows the OFF2ACT sequence of the O9039A387IZWSRQ1. If the BOOT0 pin is connected to 1.8 V, then RESET\_OUT generates a high pulse of 3.4 ms, a low pulse of 3.4 ms, and then transitions high. If the BOOT0 pin is connected to 0 V, then RESET\_OUT generates only one positive edge.




Figure 9. OFF2ACT Sequence of O9039A387IZWSRQ1



Figure 10 shows the OFF2ACT sequence of O9039A385IZWSRQ1. If the BOOT1 pin is connected to 1.8 V, then RESET\_OUT generates a high pulse of 3.4 ms, a low pulse of 3.4 ms, and then transitions high. If the BOOT1 pin is connected to 0 V, then RESET\_OUT generates one positive edge.




Figure 10. OFF2ACT Sequence of O9039A385IZWSRQ1



Figure 11 shows the OFF2ACT sequence of O9039A389IZWSRQ1. If the BOOT1 pin is connected to 1.8 V, then RESET\_OUT generates a high pulse of 3.4 ms, a low pulse of 3.4 ms, and then transitions high. If the BOOT1 pin is connected to 0 V, then RESET\_OUT generates one positive edge.




Figure 11. OFF2ACT Sequence of O9039A389IZWSRQ1



#### 6.2 ACT2OFF Sequences

When an OFF request occurs during active mode, each resource is disabled based on the programmed ACT2OFF sequence. The ACT2OFF sequence of each device is the reverse of the OFF2ACT sequence, with the exception of the RESET\_OUT pulse, which does not appear in any ACT2OFF sequence.

#### 6.3 ACT2SLP and SLP2ACT Sequences

When a SLEEP request occurs during active mode, each resource transitions to the sleep operating mode (MODE\_SLEEP bits of the corresponding CTRL register) based on the programmed ACT2SLP sequence. When a WAKE request occurs during sleep mode, each resource transitions to the active operating mode (MODE\_ACTIVE bits of the corresponding CTRL register) based on the programmed SLP2ACT sequence.

The following five steps must occur before a resource shuts off in sleep mode.


- Step 1. The NSLEEP pin must be unmasked through the POWER\_CTRL.NSLEEP\_MASK register bit
- Step 2. Each resource must be assigned to NSLEEP through the appropriate NSLEEP\_xxxx\_ASSIGN registers. For example, the NSLEEP\_SMPS\_ASSIGN register.
- Step 3. Each resource must be set to be OFF in sleep mode by clearing the MODE\_SLEEP bits of the appropriate xxxx\_CTRL register. For example, SMPS12\_CTRL register.
- Step 4. All interrupts must be cleared, because any pending interrupt prevents the PMIC from going to sleep mode.
- Step 5. A SLEEP request is generated through the NSLEEP pin.

OTP 0x89 automatically has the first three steps configured after startup. The user must only clear all interrupts and assert the NSLEEP pin low to transition the device to sleep mode with this OTP. For the other OTP versions, these commands must be sent to the PMIC through I<sup>2</sup>C before the device goes to SLEEP mode.

Note that RESET\_OUT and CLK32KGO are on the VIO domain, and therefore output the same voltage as VIO\_IN. When VIO\_IN is connected to SMPS9 or a switched 3.3V rail, then both RESET\_OUT and CLK32KGO will be shut off during sleep mode at the same time as VIO\_IN of the PMIC. If VIO\_IN remains supplied during sleep mode, then both RESET\_OUT and CLK32KGO will remain on.



Sequence Platform Settings www.ti.com






Figure 12. ACT2SLP and SLP2ACT Sequences of O9039A387IZWSRQ1





www.ti.com

Figure 13 shows the ACT2SLP and SLP2ACT sequences of O9039A385IZWSRQ1.





Figure 13. ACT2SLP and SLP2ACT Sequences of O9039A385IZWSRQ1



Sequence Platform Settings www.ti.com






Figure 14. ACT2SLP and SLP2ACT Sequences of O9039A389IZWSRQ1



#### 6.4 Warm Reset Sequences

A warm reset is triggered by the NRESWARM pin. During a warm reset, the OFF2ACT sequence is executed regardless of the actual state (ACTIVE, SLEEP) and the device returns to or remains in the ACTIVE state. Resources that are part of power-up sequence go to ACTIVE mode and the output voltage level is reloaded from OTP or kept in the previous value depending on the WR\_S bit in the SMPSx\_CTRL register or the LDOx\_CTRL register. Resources that are not part of the OFF2ACT sequence are not impacted by a warm reset and maintain the previous state. Depending on OTP version, if BOOT0 = 1 or BOOT1 = 1, then RESET\_OUT is asserted low during the warm reset sequence. If BOOT0 = 0 or BOOT1 = 0, RESET\_OUT is not asserted low.

If RESET\_OUT is asserted low during warm reset, then the PMIC must be enabled by the POWERHOLD (GPIO\_7) pin. If the PMIC will be enabled by the PWRON pin and kept on using the DEV\_ON bit, then RESET\_OUT must not be asserted low during warm reset. If POWERHOLD is set to GND and RESET\_OUT is asserted low during warm reset, the PMIC will shut off during the warm reset sequence.



Figure 15 shows the warm reset sequence of O9039A387IZWSRQ1. If any resource is on when NRESWARM is asserted, the resource remains on as shown by the solid **black** lines. The dashed **red** lines show the timing in case any resource is off before the warm reset. If VIO\_IN is switched off before the warm reset sequence, then GPIO\_4, GPIO\_6, and RESET\_OUT will be off because they are in the VIO domain. In this example, VIO\_IN is supplied by SMPS9, so RESET\_OUT follows the SMPS9 timing.




Figure 15. Warm Reset Sequence of O9039A387IZWSRQ1



Figure 16 shows the warm reset sequence of O9039A385IZWSRQ1. If any resource is on when NRESWARM is asserted, the resource remains on as shown by the solid **black** lines. The dashed **red** lines show the timing in case any resource is off before the warm reset. If VIO\_IN is switched off before the warm reset sequence, then RESET\_OUT will be off because it is in the VIO domain. In this example, VIO\_IN is supplied by SMPS9, so RESET\_OUT follows the SMPS9 timing.




Figure 16. Warm Reset Sequence of O9039A385IZWSRQ1



Figure 17 shows the warm reset sequence of O9039A389IZWSRQ1. If any resource is on when NRESWARM is asserted, the resource remains on as shown by the solid **black** lines. The dashed **red** lines show the timing in case any resource is off before the warm reset. If VIO\_IN is switched off before the warm reset sequence, then RESET\_OUT will be off because it is in the VIO domain. In this example, VIO\_IN is supplied by SMPS8, so RESET\_OUT follows the SMPS8 timing.




Figure 17. Warm Reset Sequence of O9039A389IZWSRQ1



www.ti.com Revision History

# **Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

CI	hanges from B Revision (March 2017) to C Revision	Page
•	Added TPS65917-Q1 configurations and link to TPS65917-Q1 user's guide	3
CI	hanges from A Revision (December 2015) to B Revision	Page
•	First public release of document	3
CI	hanges from Original (January 2015) to A Revision	Page
•	Updated OTP versions from 0x44, 0x60, and 0x6B OTP versions to 0x87, 0x85, and 0x89 respectively with updated and CORE boot voltages	
•	Deleted external charger control from SWORST registers	. 13
•	Changed CLK32KGAO to CLK32KGO	. 16
•	Changed CLK32KGO domain to VIO domain	. 16
•	Changed the method of setting each resource to OFF in sleep mode from setting to clearing in the ACT2SLP and	
	SLP2ACT Sequences section	
•	Added a description of the VIO signals in sleep mode when using a sequenced VIO supply	19
•	Added Warm Reset Sequences section with description of warm reset behavior	. 23

#### IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated