

TEXAS INSTRUMENTS INCORPORATED

PMP10896 Rev B.

Power Design Services Test Report

Ryan Manack

3/9/2015

PMP10896 Rev B is a power evaluation module consisting of eight power supplies, an input hot-swap and a 24-channel sequencer and supervisor. The board is intended to showcase TI's PMBus power solutions in addition to analog point-of-load converters. The test report documents the various power supply waveforms.

PMP10896 Rev B Test Results



Table of Contents

1	PMP10896 REV B	4
1.1	Board Photo	4
2	LM25066A 12V at 27.6A Hot Swap.....	5
2.1	Board Photo	5
2.2	Startup	5
2.3	Overcurrent Protection.....	6
2.4	Thermal.....	6
3	TPS62153 5V_STBY at 1A.....	7
3.1	Board Photo	7
3.2	Load Regulation	7
3.3	Startup and Shutdown	8
3.4	Output Ripple.....	9
3.5	Transient Response.....	10
3.6	Frequency Jitter	10
3.7	Thermal Image	11
4	TPS53319 3.3V at 14A.....	12
4.1	Board Photo	12
4.2	Load Regulation	12
4.3	Startup and Shutdown	13
4.4	Output Ripple.....	14
4.5	Transient Response.....	15
4.6	Frequency Jitter	15
4.7	Switch Node Peak	16
4.8	Loop Response	16
4.9	Thermal Image	17
5	TPS53355 5V at 10A.....	18
5.1	Board Photo	18
5.2	Load Regulation	18
5.3	Startup and Shutdown	19
5.4	Output Ripple.....	20
5.5	Load Transient.....	21

PMP10896 Rev B Test Results



5.6	Frequency Jitter	21
5.7	Switch Node Peak	22
5.8	Loop Response	22
5.9	Thermal Image	23
6	TPS53515 1.2V at 12A.....	24
6.1	Board Photo	24
6.2	Load Regulation	24
6.3	Startup and Shutdown	25
6.4	Output Ripple.....	26
6.5	Load Transient.....	27
6.6	Frequency Jitter	27
6.7	Switch Node Peak	28
6.8	Loop Response	28
6.9	Thermal Image	29
7	TPS53513 1.5V at 8A.....	30
7.1	Board Photo	30
7.2	Load Regulation	30
7.3	Startup and Shutdown	31
7.4	Output Ripple.....	32
7.5	Load Transient.....	33
7.6	Frequency Jitter	33
7.7	Switch Node Peak	34
7.8	Loop Response	34
7.9	Thermal Image	35
8	TPS544C25 1V at 30A.....	36
8.1	Board Photo	36
8.2	Load Regulation	36
8.3	Startup and Shutdown	37
8.4	Output Ripple.....	38
8.5	Load Transient.....	39
8.6	On Time Jitter.....	39
8.7	Switch Node Peak	40

PMP10896 Rev B Test Results




8.8	Loop Response	40
8.9	Thermal Image	41
9	TPS544C25 0.85V at 30A.....	42
9.1	Board Photo	42
9.2	Load Regulation	42
9.3	Startup and Shutdown	43
9.4	Output Ripple.....	44
9.5	Load Transient.....	45
9.6	On Time Jitter.....	45
9.7	Switch Node Peak	46
9.8	Loop Response	46
9.9	Thermal Image	47
10	TPS40428 1V at 60A.....	48
10.1	Board Photo	48
10.2	Load Regulation	48
10.3	Startup and Shutdown	49
10.4	Output Ripple.....	50
10.5	Load Transient.....	51
10.6	On-Time Jitter	51
10.7	Switch Node Peak	52
10.8	Loop Response	53
10.9	Thermal Image	53

PMP10896 Rev B Test Results


1 PMP10896 REV B

1.1 Board Photo




2 LM25066A 12V at 27.6A Hot Swap

2.1 Board Photo



2.2 Startup


The hot-swap startup into no load is shown below.



PMP10896 Rev B Test Results


2.3 Overcurrent Protection

The overcurrent protection is shown below. R_Isense is 2mΩ. Steady-state OCP is 27.6A.




2.4 Thermal

The hot-swap thermal image at 25A is shown below.



3 TPS62153 5V_STBY at 1A

3.1 Board Photo



3.2 Load Regulation



The output regulation for load currents listed in Amps is below.

5V_STBY Load Regulation	
Measured at TP65 and TP70	
0	5.02 V
0.25	5.02 V
0.5	5.02 V

PMP10896 Rev B Test Results



3.3 Startup and Shutdown

The startup at 0A and shutdown at 500mA are shown below.



3.4 Output Ripple


The 5V_STBY output ripple at 0A and 500mA are shown in persistence below.



PMP10896 Rev B Test Results


3.5 Transient Response

The transient response due to a 100mA to 500mA load step is shown in persistence below.




3.6 Frequency Jitter

The switch node frequency jitter is shown in persistence at 500mA load current. Fsw = 1.25MHz.




3.7 Thermal Image

The thermal image for 5V_STBY at 500mA load current is shown below.



4.1 Board Photo



4.2 Load Regulation



The 3.3V output regulation for load currents listed in Amps is below.

3.3V Load Regulation		
Measured at TP9 and TP14		
0	3.296	V
5	3.287	V
14	3.282	V

PMP10896 Rev B Test Results

4.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

4.4 Output Ripple


The 3.3V output ripple at 0A and 14A are shown in persistence below.



PMP10896 Rev B Test Results


4.5 Transient Response

The transient response due to a 5A to 10A load step is shown in persistence below.



4.6 Frequency Jitter


The switch node frequency jitter is shown in persistence at 14A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


4.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 14A.




4.8 Loop Response

The loop response of the power supply at 14A load current is shown below.




4.9 Thermal Image

The thermal image of the power supply operating with 14A load current is shown below.



5.1 Board Photo



5.2 Load Regulation



The 5V output regulation for load currents listed in Amps is below.

5V Load Regulation		
Measured at TP16 and TP21		
0	5.09	V
5	5.07	V
10	5.07	V

PMP10896 Rev B Test Results

5.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

5.4 Output Ripple

The 5V output ripple at 0A and 10A are shown in persistence below.



PMP10896 Rev B Test Results


5.5 Load Transient

The transient response due to a 5A to 10A load step is shown in persistence below.



5.6 Frequency Jitter


The switch node frequency jitter is shown in persistence at 10A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


5.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 10A.




5.8 Loop Response

The loop response of the power supply at 10A load current is shown below.




5.9 Thermal Image

The thermal image of the power supply operating with 10A load current is shown below.



6 TPS53515 1.2V at 12A

6.1 Board Photo



6.2 Load Regulation



The 1.2V output regulation for load currents listed in Amps is below.

1.2V Load Regulation		
Measured at TP25 and TP30		
0	1.198	V
6	1.193	V
12	1.187	V

PMP10896 Rev B Test Results

6.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

6.4 Output Ripple


The 1.2V output ripple at 0A and 12A are shown in persistence below.



PMP10896 Rev B Test Results


6.5 Load Transient

The transient response due to a 1A to 6A load step is shown in persistence below.



6.6 Frequency Jitter


The switch node frequency jitter is shown in persistence at 12A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


6.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 12A.




6.8 Loop Response

The loop response of the power supply at 12A load current is shown below.




6.9 Thermal Image

The thermal image of the power supply operating with 12A load current is shown below.



7 TPS53513 1.5V at 8A

7.1 Board Photo



7.2 Load Regulation



The 1.5V output regulation for load currents listed in Amps is below.

1.5V Load Regulation		
Measured at TP32 and TP37		
0	1.499	V
4	1.495	V
8	1.492	V

PMP10896 Rev B Test Results

7.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

7.4 Output Ripple


The 1.5V output ripple at 0A and 8A are shown in persistence below.



PMP10896 Rev B Test Results


7.5 Load Transient

The transient response due to a 4A to 8A load step is shown in persistence below.



7.6 Frequency Jitter


The switch node frequency jitter is shown in persistence at 8A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


7.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 8A.




7.8 Loop Response

The loop response of the power supply at 8A load current is shown below.




7.9 Thermal Image

The thermal image of the power supply operating with 8A load current is shown below.



8.1 Board Photo



8.2 Load Regulation



The 1V output regulation for load currents listed in Amps is below.

1V Load Regulation		
Measured at TP41 and TP43		
0	1	V
15	0.999	V
20	0.999	V

PMP10896 Rev B Test Results

8.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

8.4 Output Ripple


The 1V output ripple at 0A and 20A are shown in persistence below.



PMP10896 Rev B Test Results


8.5 Load Transient

The transient response due to a 1A to 10A load step is shown in persistence below.



8.6 On Time Jitter


The switch node on-time jitter is shown in persistence at 20A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


8.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 20A.




8.8 Loop Response

The loop response of the power supply at 15A load current is shown below.




8.9 Thermal Image

The thermal image of the power supply operating with 30A load current is shown below.



9.1 Board Photo



9.2 Load Regulation



The 0.85V output regulation for load currents listed in Amps is below.

0.85V Load Regulation		
Measured at TP53 and TP55		
	0	0.849 V
15	0.848	V
30	0.848	V

PMP10896 Rev B Test Results

9.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

9.4 Output Ripple

The 0.85V output ripple at 0A and 30A are shown in persistence below.



PMP10896 Rev B Test Results


9.5 Load Transient

The transient response due to a 1A to 10A load step is shown in persistence below.



9.6 On Time Jitter


The switch node on-time jitter is shown in persistence at 30A below. Fsw = 500kHz.



PMP10896 Rev B Test Results


9.7 Switch Node Peak

The maximum switch node voltage is shown in persistence below at 30A.




9.8 Loop Response

The loop response of the power supply at 15A load current is shown below.




9.9 Thermal Image

The thermal image of the power supply operating with 30A load current is shown below.



10.1 Board Photo



10.2 Load Regulation



The 1V output regulation for load currents listed in Amps is below.

1VA Load Regulation		
Measured at TP66 and TP74		
0	1.003	V
15	1.003	V
30	1.003	V
45	1.003	V
60	1.004	V

PMP10896 Rev B Test Results

10.3 Startup and Shutdown



The startup at 0A and shutdown at 1A are shown below.



PMP10896 Rev B Test Results

10.4 Output Ripple


The 1V output ripple at 0A and 60A are shown in persistence below. Two phase switching at 500kHz per phase.



PMP10896 Rev B Test Results


10.5 Load Transient

The transient response due to a 30A to 45A load step is shown in persistence below.



10.6 On-Time Jitter

The switch node on-time jitter is shown in persistence at 60A below. Fsw = 500kHz/phase.





PMP10896 Rev B Test Results



10.7 Switch Node Peak


The maximum switch node voltages for U11 and U13 are shown in persistence below at 60A load current.



PMP10896 Rev B Test Results


10.8 Loop Response

The loop response of the power supply at 15A load current is shown below.



10.9 Thermal Image

The thermal image of the power supply operating with 60A load current is shown below.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated