

# Design Guide: TIDC-HYBRID-RF-PLC

## Hybrid RF and PLC Reference Design to Extend Network Coverage and Reliability



### Description

The importance of on-time response and monitoring in advanced metering infrastructure (AMI) and distribution automation networks increases demands on reliable communications. This reference design addresses this issue by implementing a solution with both radio frequency (RF) and power line communication (PLC). This design can help improve network performance, reliability, capacity, and scalability. The CC13xx wireless microcontroller (MCU) acts as both the RF protocol processor and the host for the PLC processor, which results in additional cost-savings for the system design. This design is based on a proprietary RF solution to provide a reference for choosing various RF protocols and frequency bands as required in different markets. The *Hybrid Wireless M-Bus and G3-PLC Reference Design (TIDC-HYBRID-WMBUS-PLC)* implements a specific version of the hybrid RF plus PLC concept.

### Resources

<a href="#">TIDC-HYBRID-RF-PLC</a>	Design Folder
<a href="#">CC1310</a>	Product Folder
<a href="#">F28PLC84</a>	Product Folder
<a href="#">F28375S</a>	Product Folder
<a href="#">F28M35H52C</a>	Product Folder
<a href="#">AFE031</a>	Product Folder
<a href="#">AFE032</a>	Product Folder
<a href="#">TMDSPCKITV4-CEN</a>	Tools Folder
<a href="#">LAUNCHXL-CC1310</a>	Tools Folder
<a href="#">TI-PLC-G3-CENELEC-SN</a>	Tools Folder
<a href="#">SIMPLELINK-CC13X0-SDK</a>	Tools Folder

### Features



- Improves network reliability through simultaneous transmissions over wireless and PLC networks
- Improves network capacity through spatial multiplexing by using RF and PLC networks to simultaneously transmit independent data
- Improves network scalability by acting as a bridge between RF and PLC networks, extending the area covered within a territory
- Fully Programmable Protocol Design Provides Various Options for RF and PLC Communication Protocols and Frequency Bands
  - PLC Protocols (PRIME, G3-PLC, and PLC-Lite) Over CENELEC, ARIB, and FCC Frequency Bands
  - RF Protocols (Wireless M-Bus, IEEE 802.15.4g FSK, and Long Range Mode) Over Sub-1 GHz (CC1310 or CC1350) and 2.4-GHz Frequency Bands (CC1350)

### Applications

- Distribution Automation
- Electricity Meters
- Smart Plugs
- Smart Grid Communications



[Search Our E2E™ support forums](#)



An IMPORTANT NOTICE at the end of this TI reference design addresses authorized use, intellectual property matters and other important disclaimers and information.

## 1 System Description

This TI Design provides a reliable communication system solution with dual RF and PLC communications for end equipment of smart grid applications. This design is built on top of the existing TI PLC and RF solutions, which target at improving network performance and providing more features by combining the communication modems while keeping the advantages inherited from the existing PLC and RF solutions.

The programmable PLC design allows two options for the system design: one uses RF with a PLC full-stack based design (Figure 1), and one uses RF with a PLC lower-MAC stack based design (Figure 2). The former design takes full advantage of the embedded PLC network stacks, allowing multi-hop communications without additional effort in addition to the new features such as simultaneous transmissions, spatial multiplexing, PLC and RF repeaters, and support for two independent networks. The latter design allows the lower stacks (MAC or network layer) to control which physical layer (wireless or PLC) is used for each link over multi-hop networks. This capability cannot be supported by the former design.

Figure 1 shows the RF with a PLC full-stack based system architecture. The ARM® Cortex®-M3 processor in the CC1310 (or CC1350) Simplelink™ Wireless MCU is the CPU controlling both the RF and PLC links. For this design, the CC1310 Wireless MCU is connected to the C2000™ PLC MCU through UART to act as the PLC modem's external host processor. The PLC MCU is loaded with the complete PRIME or G3-PLC software stack. The wireless MCU also runs the system's host applications; for example, it simultaneously transmits packets on both networks or acts as a bridge between the different physical networks. The hybrid RF/PLC example project described in Section 4 implements this architecture with the full G3-PLC stack.

**Figure 1. System Architecture (RF With PLC Full-Stack)**





Figure 2 shows the RF with a PLC lower-MAC based system architecture. The only difference in this architecture is that the C2000 PLC device is loaded with PLC lower-MAC stack binary instead of full PLC stack. The benefit of this architecture is to allow building a single network layer to control both RF and PLC MAC or PHYs, which enables the network layer to select one of RF and PLC channels on a per-link basis over an entire multi-hop path. The decision algorithm of how to select one of the links (wireless or PLC) at the network layer can be implementation-specific. Note that this design is capable of building this type of architecture, but the software coming with this design does not provide any specific examples to work with this architecture.

The lower-MAC PLC software binary can be obtained from the G3-PLC DC or PRIME DC software package[5][6]. The PLCLite, TI's proprietary PLC solution, includes MAC and PHY only, which can be downloaded from the TI-PLC-PLCLITE product page[8].

**Figure 2. System Architecture (RF With PLC Lower-MAC Stack)**




## 2 Block Diagram

Figure 3 shows the block diagram of the design. The primary devices for this design are the CC1310, TMS320F28PLC84, and AFE031. The CC1310 includes two core processors: ARM Cortex-M0 for RF communication, and ARM Cortex-M3 for applications, network stacks, and host-level RF and PLC communication drivers. The TMS320F28PLC84 with the AFE031 (PLC analog front-end) is for PLC communication.

For this design, these devices were chosen because of the following:

- The CC1310 combines a flexible, ultralow-power RF transceiver with a powerful 48-MHz ARM Cortex-M3 microcontroller in a platform supporting multiple PHY (physical) layers and RF standards.
- The TMS320F28PLC84 provides optimized PLC OFDM performance with VCU and allows a programmable, flexible PLC design upgradable to different PLC solutions without hardware modification.
- The AFE031 analog front-end provides high reliability in PLC applications by monolithic integrated circuit with thermal and overcurrent protection.


**Figure 3. Block Diagram**



## 2.1 CC1310

The CC1310 is a member of the CC26xx and CC13xx family of cost-effective, ultralow-power, 2.4-GHz and Sub-1GHz RF devices. Its very low active RF, MCU current, and low-power mode current consumption provide excellent battery lifetime and allow operation on small coin-cell batteries and in energy-harvesting applications. The device is the first part in a Sub-1 GHz family of cost-effective, ultralow power wireless MCUs. The CC1310 combines a flexible, very low power RF transceiver with a powerful 48-MHz Cortex-M3 microcontroller in a platform supporting multiple physical layers and RF standards. A dedicated radio controller (Cortex-M0) handles low-level RF protocol commands that are stored in ROM or RAM, thus ensuring ultralow power and flexibility. The low-power consumption of the CC1310 does not come at the expense of RF performance; the CC1310 has excellent sensitivity and robustness (selectivity and blocking) performance. The CC1310 is a highly integrated, true single-chip solution incorporating a complete RF system and an on-chip DC-DC converter. Sensors can be handled in a very low-power manner by a dedicated autonomous ultralow-power MCU that can be configured to handle analog and digital sensors; thus, the main MCU (Cortex-M3) is able to maximize sleep time. The CC1310 power and clock management and radio systems require specific configuration and handling by software to operate correctly. This has been implemented in the TI RTOS, and it is therefore recommended that this software framework is used for all application development on the device. The complete TI-RTOS and device drivers are offered in source code free of charge. Figure 4 shows the CC1310 functional block diagram[1].


**Figure 4. CC1310 Functional Block Diagram[1]**



## 2.2 TMS320F28PLC84

The TMS320F28PLC84 PLC processors are optimized to meet the requirements for AMI networks in smart grid installations that use narrowband PLC in the CENELEC frequency band. The CENELEC band is defined to be 35 to 90 kHz. The F28PLC84 processor is designed to execute the entire PLC protocol stack for the supported industry standards. TI supplies these firmware libraries to execute on the F28PLC84 processor with no additional license fees or royalties. The F28PLC84 processor is also used in PLC data concentrators, which act as neighborhood-area collectors of electricity usage information from multiple end nodes. The F28PLC84 processors are optimized to work with the AFE031 analog front-end for PLCs. The AFE031 is an integrated analog front-end for narrowband PLCs that are capable of driving a transformer-coupled connection to the AC mains power line. It is ideal for driving high-current, low-impedance lines driving up to 1.9 A into reactive loads. The AFE031 is compliant to CENELEC A, B, C, and D (EN50065-1, EN50065-2, EN50065-3, EN50065-7) frequency bands. Figure 5 shows the TMS320F28PLC84 functional block diagram[2].

Figure 5. TMS320F28PLC84 Functional Block Diagram[2]




### 2.3 AFE031

The AFE031 is a low-cost, integrated, PLC analog front-end device that is capable of capacitive- or transformer-coupled connections to the power line while under the control of a DSP or microcontroller. It is ideal for driving low-impedance lines that require up to 1.5 A into reactive loads. The integrated receiver is able to detect signals down to  $20 \mu\text{V}_{\text{RMS}}$  and is capable of a wide range of gain options to adapt to varying input signal conditions. This monolithic integrated circuit provides high reliability in demanding PLC applications.

The AFE031 transmit power amplifier operates from a single supply in the range of 7 to 24 V. At maximum output current, a wide output swing provides a  $12\text{-V}_{\text{PP}}$  ( $I_{\text{OUT}} = 1.5 \text{ A}$ ) capability with a nominal 15-V supply. The analog and digital signal processing circuitry operates from a single 3.3-V power supply.

The AFE031 is internally protected against over temperature and short-circuit conditions. It also provides an adjustable current limit. An interrupt output is provided that indicates both current limit and thermal limit. There is also a shutdown pin that can be used to quickly put the device into its lowest power state. Through the four-wire serial peripheral interface, or SPI, each functional block can be enabled or disabled to optimize power dissipation. The AFE031 is housed in a thermally-enhanced, surface-mount Power PAD package (QFN-48). Operation is specified over the extended industrial junction temperature range of  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . Figure 6 shows the AFE031 functional block diagram[3].

**Figure 6. AFE031 Functional Block Diagram[3]**



### 3 Getting Started Hardware

The hybrid RF and PLC communications design is built with two standard EVMs: the LAUNCHXL-CC1310 (<http://www.ti.com/tool/launchxl-cc1310>) and the TMDSPCKITV4-CEN (<http://www.ti.com/tool/tmdsplckitv4-cen>), shown in [Figure 7](#) and [Figure 8](#), respectively. For PLC, this reference design is configured as CENELEC-A band in software with the TMDSPCKITV4-CEN platform. Depending on user applications, the TIDM-SOMPLC-FCC (<http://www.ti.com/tool/TIDM-SOMPLC-FCC>) or the TMDSPCKITV4-ARIB (<http://www.ti.com/tool/TIDM-SOMPLC-ARIB>) can be also used with the LAUNCHXL-CC1310 EVM. Similarly, the CC1310 can be replaced with the CC1350 or other CC wireless MCUs with some modification on the example software provided with the reference design.

**Figure 7. LAUNCHXL-CC1310**




**Figure 8. TMDSPCKITV4-CEN**



### 3.1 Hybrid RF/PLC EVM Configuration


The major hardware modification to build the hybrid RF and PLC module is to connect UART pins between RF and PLC EVM: UART\_TX, UART\_RX, and GND. Figure 9 shows UART pin connections between the TMDSPCKITV4 and LAUNCHXL-CC1310. The M3:P2-12 (PLC\_SCIA\_TX) pin (Figure 9) is connected to the UART RX pin (DIO 2) on the LAUNCHXL-CC1310, and M3:P2-14 (PLC\_SCIA\_RX) (Figure 9) to the UART TX pin (DIO 3) on the LAUNCHXL-CC1310 EVM. One of the GND pins in the TMDSPCKITV4 EVM, shown in Figure 9, is connected to a GND pin on the LAUNCHXL-CC1310.

**Figure 9. UART Pins on TMDSPCKITV4**



As shown in Figure 10, additional configuration change is SW2 position to OFF. Turning off the SW2 blocks UART communication with the mini-USB port in TMDSPCKITV4. Thus, it allows the M3 module to communicate with external device through UART without any interrupts.


**Figure 10. SW2 Position in TMDSPCKITV4 EVM**




## 4 Getting Started Firmware

This reference design provides a HYBRID-RF-PLC software example which includes applications for simultaneous transmissions, RF and PLC repeaters, and RF and PLC communication drivers. This section covers details of the example software architecture, followed by how to build and flash the example project using Code Composer Studio™ (CCS). The software example can be built with Code Composer Studio™ (CCS) v9.0.1 (or above). [Figure 11](#) and [Figure 12](#) show the compiler and CC1310 SDK versions (SIMPLELINK-CC13X0-SDK v3.10.0.11) used to compile the software example.

**Figure 11. Software Example Compiler Version**



**Figure 12. Software Example SDK Version**



#### 4.1 TIDC-HYBRID-RF-PLC Software Example

The example software runs based on TI-RTOS in the ARM Cortex-M3. For PLC communication, the default configuration in the example is set to CENELEC-A, TMR ON, and the TX level of 0x20 (maximum). For RF communication, the example is set to a 50-kbps FSK mode over a 868-MHz frequency band.

To run the software example in different frequency bands of FCC or ARIB, the following code line needs to be updated in the `init_plcHandler()` to `TONEMASK_FCC_FULL_BAND` or `TONEMASK_FCC_ARIB_54`. The TX power level and TMR configuration can be changed in the same function.

```
plcHandle.g3ToneMaskSelection = TONEMASK_CENELEC_A_36;
```

The software example runs simultaneous transmissions (sending data to RF and PLC channels). In addition, the RF and PLC repeater feature (passing received RF (or PLC) data to PLC (or RF) link) can be supported on top of the simultaneous transmissions by enabling `RF_PLC_REPEATER` macro definition in the software.

Figure 13 shows the overall software architecture of the hybrid RF/PLC example, which consists of five tasks: `uartRxTask`, `PLCStateMachineTask`, `RFTxTask`, `PLCTxTask`, and `applicationTask`. This project is provided as a working example to be used for baseline software on customer-specific application development.

Figure 13. Hybrid RF/PLC Example Software Architecture




Figure 14.

#### 4.1.1 uartRxTask

The uartRXTask processes PLC host messages received from the C2000 PLC device. The task waits for a 6-byte PLC host message header that contains the host message type, payload length, and header CRC. If the CRC passes, the task extracts remaining bytes including payload CRC, payload sub-header, and payload. If the payload CRC passes, then the task passes the received data to the corresponding tasks through mailbox.

#### 4.1.2 PLCStateMachineTask

The PLCStateMachineTask maintains G3-PLC service node state machine. When power is on, the PLCStateMachine task starts to initialize G3-PLC with the default configuration and to join the G3-PLC network once G3-PLC DC is detected. Once all steps are successful, the task changes the state machine to NORMAL state, which allows the PLCTxTask to start data transmissions.

The details of the G3-PLC host message sequences can be found in [Section 4.2](#), and this example is implemented in all procedures except for the keep-alive mechanism and firmware upgrade.

#### 4.1.3 RFTxTask

The RFTxTask waits for the mailbox message of "SEND\_RF\_DATA". Once the task receives the mailbox message, it sends the data over the RF transmission path with a given configuration and then changes back to the receive state.

#### 4.1.4 PLCTxTask

The PLCTxTask wait for the mailbox message of "SEND\_PLC\_DATA". If the task receives the mailbox message, it sends the data over UART to the PLC C2000 device for PLC transmissions, and then copies the data into PLC\_HoldQueue to handle re-transmissions. When retransmission happens, the task simply sends the data in the PLC\_HoldQueue through UART.

#### 4.1.5 applicationTask

The applicationTask emulates application data source. This task creates 100B random data and sends a mailbox message with data to RFTxTask and PLCTxTask every 5 seconds for simultaneous transmissions. The application data size and interval can be configurable in application/app.c.

#### 4.1.6 LED Configuration

The example project has activated two LEDs on LAUNCHXL-CC1310 to trace software activities. [Table 1](#) summarizes the LED pin mapping to the specific software activity.

**Table 1. LED Mapping**

LED NUMBER	BEHAVIOR MAPPING TO SOFTWARE ACTIVITY
DIO6	PLC TX/RX activities
DIO7	RF TX/RX activities

## 4.2 G3-PLC Service Node Host Message Sequences

This section details the G3-PLC host message sequences to run as G3-PLC service node.

### 4.2.1 Initialization State

**Table 2. Host Message Sequence (Initialization)**

SEQ	HOST MSG	MSG TYPE	PARAMETERS
1	Load system configuration (Port configuration)	0x0C	Config type: 0x0001 Diag port/host port: SCI-A (0x00)
2	Load system configuration (System configuration)	0x0C	Config type: 0x0003 Device mode: 0x0000 (G3 normal mode)
3	Load system configuration (G3 configuration)	0x0C	Config type: 0x0008 COH: 0 (OFF) TMR: 1 (ON if TMR is used) G3 long address: unique ID* Note that the G3 long address should be little-endian order. As an example, 0x11 22 33 44 55 66 77 88 if your long address is 0x88 77 66 55 44 33 22 11.
4	SHUT_DOWN	0x05	Reset type: soft reset
2-second delay after receiving SHUT_DOWN.confirm			
5	SET_INFO (G3 PHY TX parameters)	0x04	Info type: 0x0002 Band selection: CENELEC/FCC/ARIB TX level: 0x20 (maximum) Modulation: Any value in [4] Tonemask: CEN A 36 (for CENELEC)
6	SET_INFO (G3 PHY RX parameters)	0X04	Info type: 0x0003 Band selection: CENELEC/FCC/ARIB COH/BLI: 0 AGC: 1 Gain value: 0 (ignored if AGC is set to 1) Tonemask: CEN A 36 (for CENELEC) The tonemask value should be the same as TX.
7	SET_MAC_PIB		adpLOADNGSequenceNumber (= (previous value + offset1)%0xFFFF) macFrameCounter (= (previous value + offset2)%0xFFFFFFFF) Note that the initial values are set to 0, and the offset calculation is given in <a href="#">Section 4.2.2</a> .
8	Discover	0x12	Discover type: 0x00 - Network discover Duration: 12 (in seconds)
Choose one from a list of PAN Descriptors in Discover.confirm (based on LQI, fixed PAN ID searching and so on)			
9	Attach	0x10	PAN ID: CoordPANId from the PAN Descriptor LBA address: CoordAddr from the PAN descriptor

**NOTE:** All reserved fields should be set to zero.

To avoid collisions between multiple nodes in the discovery stage, it is strongly recommended to add random back-off before sending Discover.request.

Step 7 is required when the DC assigns static short address for each service node.

## 4.2.2 Normal State

After the host receives ATTACH.confirm (SUCCESS), it is ready state to send and receive data.

### 4.2.2.1 Data Transfer

**Table 3. Data Transfer Message Configuration**

SEQ	HOST MSG	MSG TYPE	PARAMETERS
1	DATA_TRANSFER	0x00	NSDU Handle: random value SEC: 1 QoS: 0 D-route:1 (This will automatically set up route to the destination whenever it is needed.) L_SDU data: IPv6 packet

Set D-route flag to 1, which allows the DSP to find a route to the destination if the route is not valid. The L\_SDU data should be IPv6 packet. An example of UDP over IPv6 packet is given below.

```

60 00 00 00 00 23 11 08 FE 80 00 00 00 00 00 00 74 55 00 FF FE 00 00 00 FE 80 00 00 00 00 00 74
55 00 FF FE 00 00 01 00 00 00 00 00 23 13 43 A0 AA 00 00 00 00 00 00 01 00 00 00 01 00 00 00 01 00
00 00 03 00 00 00 31 31 31
    
```

- IPv6 header (40-byte in red-color with underline)
  - Next header: 17 (=UDP)
  - Payload length: 35
  - Hop limit: 8
  - Source address: FE80:0000:0000:0000:7455:00FF:FE00:0000
  - Destination address: FE80:0000:0000:0000:7455:00FF:FE00:0001
- UDP header (8-byte in blue-color with italic)
  - Source port: 0x0000
  - Destination port: 0x0000
  - Length: 35 (Note that the length should be the same as that of the IPv6 header)
  - CRC: 0x0000 (If the CRC is zero, UDP checksum will be ignored)
- Application payload
  - A0 AA 00 00 00 00 00 00 00 01 00 00 00 01 00 00 00 01 00 00 00 01 00 00 00 03 00 00 00 31 31 31

### 4.2.2.2 Keep-Alive Mechanism


The keep-alive mechanism is for the host to check if the DSP is alive or not. For this purpose, probe the PIBs given in Table 4. The host requires tracking of the PIB values and setting updated values (= the previous PIB value + offset) to the PIBs in the initialization routine when reset happens.

The ping interval can be implementation specific. The offset value depends on the ping interval. As an example, if the host set the ping interval to 2 minutes for macFrameCounter and the last update for the value is 100, then the macFrameCounter should be set to 1300 (= 2 minutes × 600 per minute + 100) when reset happens.

**Table 4. PIB for Keep-Alive**

ATTRIBUTE	PIB ID	LENGTH	OFFSET
adpLOADNGSequenceNumber	0xa5	2	10 per minute
macFrameCounter	0x77	4	600 per minute

**Figure 15. Keep-Alive Mechanism**



### 4.2.3 Error Handling


If the host does not receive confirmation from the DSP within the timeout given in [Table 5](#), the host needs to retry until it reaches MaxRetryCnt (implementation-specific). If all the trials fail, hard reset to recover from the stage. The details are given in [Figure 16](#).

**NOTE:** The host application has to wait until it receives a confirmation message to transmit the next message. The timeout value given in [Table 5](#) can be used to indicate that the confirmation is lost.

**Table 5. Timeout Values for PLC Host Messages**

MESSAGE	TIMEOUT
Attach.request	$T1 = \text{adpLBAMAXAttempts} \times \text{adpJoinWaitTime}$ (for example, 360 seconds with the default PIB setting) Note that changing the PIB values should apply to the timeout calculation.
Data transfer	T2 = 150 seconds (GENELEC) or 90 seconds (FCC)
Other messages	T3 = 5 seconds

**Figure 16. Recovery and Timeout Mechanism**




### 4.2.4 Firmware Upgrade

The details of host message exchanges for a firmware upgrade are described in Section 2.4 of the TI-PLC-G3-GENELC-SN software package [TI\\_G3\\_host\\_msg.pdf](#) [4].

### 4.3 Build HYBRID-RF-PLC Software Example Using CCS

The example project can be built with CCS IDE v9.0.1 (or above). The two CCS projects of HybridRfPlcExample\_CC1310\_LAUNCHXL\_tirtos\_ccs and tirtos\_builds\_CC1310\_LAUNCHXL\_release\_ccs need to be opened to compile the project. The screen capture of the project view is shown in Figure 17. Once successfully compiled, the binary file (HybridRfPlcExample\_CC1310\_LAUNCHXL\_tirtos\_ccs.out) will be generated in the directory of *debug*.

**Figure 17. Build TIDC-HYBRID-RF-PLC CCS Project**



### 4.4 Flashing Binaries Using CCS

This section presents a step-by-step procedure to flash software binary to F28PLC84 (for G3-PLC) and CC1310 (for Hybrid RF/PLC application) devices, which is required to run the Hybrid RF/PLC node.

#### 4.4.1 Flashing Hybrid RF/PLC Example Binary to CC1310 Using CCS

This section covers how to flash the Hybrid RF/PLC example binary on the CC1310 using CCS.

1. Connect the USB cable to LAUNCHXL-CC1310 EVM..
2. Launch the target configuration for CC1310 and connect to the device in hte CCS debug mode.
3. Select Run → Load → Load Program and flash the "HybridRfPlcExample\_CC1310\_LAUNCHXL\_tirtos\_ccs.out" binary in the directory of *debug*.

#### 4.4.2 Flashing PLC Binary to TMS320F28PLC84

Find the step-by-step procedure in Section 7.1 (if using the XDS100 and CodeSkin to program the F28PLC84 MCU) or Section 7.2 (if using CCS and JTAG emulator to program the F28PLC84 MCU) in the TIDM-SOMPLC-G3-CENELEC reference design guide[7]. The latest G3-PLC software can be obtained from TI-PLC-G3-CENELEC-SN-F28PLC84 (<http://www.ti.com/tool/ti-plc-g3-cenelec-sn>).

## 5 Hybrid RF/PLC Test

The goal of the Hybrid RF/PLC test is to show simultaneous transmissions and RF-to-PLC repeater features with a 3-node set-up: one RF only, one PLC only, and one Hybrid RF/PLC node.

### 5.1 Test Setup

To run the Hybrid RF/PLC test, it is required to have the [LAUNCHXL-CC1310](#) and the [TMDSPCKITV4-CEN](#). Find both EVMs in the TI store (<https://store.ti.com/>). In addition, [Table 6](#) summarizes the additional tools and software required to run the Hybrid RF/PLC test.

**Table 6. Required Tools for Hybrid RF/PLC Test Setup**

DEVICE	EVM	HW MODIFICATION?	FLASH FIRMWARE?	GUI TOOL?
RF only	LAUNCHXL-CC1310	No	Yes <sup>(1)</sup>	No (or SmartRF studio without flashing the firmware)
PLC only	TMDSPCKITV4-CEN	No	Yes ( <a href="#">Section 4.4.2</a> )	Yes (Zero-configuration GUI <sup>(2)</sup> )
Hybrid RF/PLC	CC1310DK TMDSPCKITV4-CEN	No	Yes ( <a href="#">Section 4.4.1</a> and <a href="#">Section 4.4.2</a> )	No


<sup>(1)</sup> The pre-built RF only standalone binary can be found in the debug\_RF\_only directory. This example echo back data received from the HYBRID-RF-PLC node.

<sup>(2)</sup> Zero-configuration GUI is use to run PLC node as mini-DC to start G3-PLC network. The G3-PLC software package (<http://www.ti.com/tool/ti-plc-g3-cenelec-sn>) installs the GUI automatically.

### 5.2 Running Hybrid RF/PLC Test

[Figure 18](#) shows the 3-node test setup. The RF only node runs with the SmartRF™ software tool and the PLC only node runs with zero-configuration graphical user interface (GUI) tool. The Hybrid RF/PLC node runs in standalone mode.

**Figure 18. Hybrid RF/PLC Test Setup**



For the Hybrid RF/PLC test, the PLC only node is configured as the G3-PLC mini-DC node. The RF only node can run as the PACKET\_RX mode to capture RF packets or the PACKET\_TX mode to transmit RF packets. The PACKET\_RX mode shows simultaneous transmissions from the Hybrid RF/PLC node, and the PACKET\_TX mode shows RF-to-PLC repeater functionality on the Hybrid RF/PLC node.

When the Hybrid RF/PLC node starts, it will try to join to the PLC mini-DC (PLC only node) as the G3-PLC service node. The RF is running only PHY, so no joining is required. Once joined to the PLC network, the Hybrid RF/PLC node starts to send out 10B data to both RF and PLC nodes every 5 seconds. The PLC only and RF only node can capture the packet receptions through the GUI. In addition, the RF only or the PLC only nodes can generate data to show the RF-to-PLC repeater functionality on the Hybrid RF/PLC node. The Hybrid RF/PLC node can forward data received from one end (the RF only or PLC only node) to the other end. The receptions on the other end can be captured with the GUI tool.

### 5.2.1 Test Procedure

This section covers the step-by-step procedure to run the Hybrid RF/PLC test.

1. Start the PLC only node as mini-DC (Steps 1 to 5 in Section 5.2.2).
2. Start the RF only node in a standalone mode. (or use SmartRF studio to capture the RF packet RX.)
3. Once the Hybrid RF/PLC node is joined to the PLC network, an indication will show up in the mini-DC pop-up window (Step 6 in Section 5.2.2).
4. Check the simultaneous transmissions from Hybrid RF/PLC node on the GUI for the PLC(Step 7 in Section 5.2.2 for PLC). The RF only node can monitor the packet reception via the CCS debug window or SmartRF studio.

### 5.2.2 PLC Only Node Setup

This section covers how to run the PLC only node as mini-DC with the GUI.

1. Connect the PLC only node to the PC and open intermediate GUI.
2. Set a unique long address for each device by using "Set System Config."

**Figure 19. Set System Configuration**






Figure 20. G3-PLC System Configuration




3. Turn on "Log Raw Message Data" to see all the raw data exchanged between the GUI and C2000 PLC.

Figure 21. Log Raw Message Data




4. Start the device as mini-DC by selecting Functions → Start Base Node.

**Figure 22. Start Base Node**




5. In the pop-up window of the G3 base node, click "Start Network".

**Figure 23. Start Network With the G3 Base Node Window**




- Once the Hybrid RF/PLC node is joined, the IPv6 information for the joined node is visible.

**Figure 24. Joining Node Information in the G3 Base Node Window**




- Go to the log window to trace all the received data (G3 Data Transfer Indication).

**Figure 25. G3 Data Transfer Indication on the Log Window**



8. Set both "Min Data Packet Size" and "Max Data Packet Size" to less than 70B and with "Cycle" to 1 as shown in [Figure 26](#). In this capture, the packet size is set to 50B with cycles of 1. Then, send PLC data by selecting "Start Test."

**Figure 26. Start Test in the G3 Base Node Window**



### 5.3 Hybrid RF/PLC Test Results

This section shows the Hybrid RF/PLC test results to verify simultaneous transmissions and RF-to-PLC repeater functionality.

Figure 27 shows the simultaneous transmission test results with a 3-node setup. The Hybrid RF/PLC node starts to send 10B packets with intervals of 5 seconds to both RF and PLC nodes once PLC completely joins the process. The zero-configuration GUI on the PLC only node shows 10B packet reception (G3 Data Transfer.Indication) in the log window (top of Figure 27), and at the same time the RF only node receives the same packet (10B packet with RF sub-header information).

**Figure 27. Simultaneous Transmissions**




Figure 28 shows test results for PLC-to-RF repeater functionality. For the test, the PLC node sent a 50B UDP/IPV6 packet, meaning that the total packet size is 98B (50B payload + 40B IPv6 header + 8B UDP header). The zero-configuration GUI shows the packet transmission (G3 Data Transfer.Request) in the GUI. As a result, the Hybrid RF/PLC node forwarded the received PLC data to the RF link. Finally, the RF node shows the packet reception on the Packet RX window at the timestamp of 15:32:38.905. Note that, for this testing, the packet size sent by the PLC should be limited up to 70B because of the size limitation by the pre-programmed RF software. The RX packet size can be increased by flashing a new RF RX example binary with the increased maximum RX packet size.

Figure 28. PLC-to-RF Repeater





Figure 29 shows test results of the RF-to-PLC repeater. For the test, the RF node sent a 5B text message. Once the 5B packet is received at the Hybrid RF/PLC node, the node passes the received data to the PLC link. The zero-configuration GUI shows the packet reception (in forms of G3 Data Transfer Indication) in the zero-configuration GUI (top in Figure 29). The received packet at PLC includes 6B of information (5B message + 1B sub-header inserted by the RF transmitter).

**Figure 29. RF-to-PLC Repeater**



## 6 Design Files

### 6.1 Schematics

To download the schematics, see the design files at [TIDC-HYBRID-RF-PLC](#).

### 6.2 Bill of Materials

To download the bill of materials (BOM), see the design files at [TIDC-HYBRID-RF-PLC](#).

### 6.3 Layout Prints

To download the layer plots, see the design files at [TIDC-HYBRID-RF-PLC](#).

### 6.4 Gerber Files

To download the Gerber files, see the design files at [TIDC-HYBRID-RF-PLC](#).

### 6.5 Assembly Drawings

To download the assembly drawings, see the design files at [TIDC-HYBRID-RF-PLC](#).

## 7 Software Files

To download the software files, see the design files at [TIDC-HYBRID-RF-PLC](#).

## 8 References

1. Texas Instruments, *CC1310 SimpleLink™ Ultralow Power Sub-1-GHz Wireless MCU*, CC1310 Datasheet ([SWRS181](#))
2. Texas Instruments, *TMS320F28PLC8x Power Line Communications (PLC) Processors*, TMS320F28PLC8x Datasheet ([SPRS802](#))
3. Texas Instruments, *Powerline Communications Analog Front-End*, AFE031 Datasheet ([SBOS531](#))
4. Texas Instruments, *TI\_G3\_host\_msg.pdf*, TI-PLC-G3-CENELEC-SN Software Package (<http://www.ti.com/tool/ti-plc-g3-cenelec-sn>)
5. Texas Instruments, *G3 Data Concentrator Power-Line Communication Modem*, TI-PLC-G3-DC Software Package (<http://www.ti.com/tool/ti-plc-g3-dc>)
6. Texas Instruments, *PRIME Data Concentrator Power-Line Communication Modem*, TI-PLC-PRIME-DC Software Package (<http://www.ti.com/tool/ti-plc-prime-dc>)
7. Texas Instruments, *System on Module for G3 Power Line Communication (CENELEC Frequency Band)*, TIDM-SOMPLC-G3-CENELEC Design Guide ([TIDU442](#))
8. Texas Instruments, *PLCLite Industrial Power-Line Communication Modem*, TI-PLC-PLCLITE Software Package (<http://www.ti.com/tool/ti-plc-plclite>)

### 8.1 Trademarks

E2E is a trademark of Texas Instruments.

## 9 Terminology

**PLC**— Power line communication

**RF**— Radio frequency

**TMR**— ToneMap request

**DC**— Data concentrator

**VCU**— Viterbi/complex math unit

**AMI**— Advanced metering infrastructure

**AFE**— Analog front-end

## 10 About the Author

**WONSOO KIM** is a system engineer at Texas Instruments, where he is responsible for driving system solutions for Smart Grid applications, defining future requirements in TI's product roadmap, and providing system-level support and training focusing on communication software and systems for Smart Grid customers. He received the Ph.D. degree in electrical and computer engineering from the University of Texas at Austin, Austin, TX.

## Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

---

### Changes from Original (April 2016) to A Revision Page

- Changed from preview page..... 1
- 

### Changes from A Revision (May2016) to B Revision Page

- Changed LAUNCHXL-CC1310CC1310DK to LAUNCHXL-CC1310 ..... 1
  - Changed SIMPLELINK-CC13X0-SKDCC13XX to SIMPLELINK-CC13X0-SDK ..... 1
  - Changed CC13xx to CC1310..... 2
  - Changed CC1310DK to LAUNCHXL-CC1310 ..... 9
  - Changed hyperlink ..... 9
  - Changed CC1310DK to LAUNCHXL-CC1310 EVM..... 9
  - Changed title from CC1310DK to LAUNCHXL-CC1310 ..... 9
  - Changed paragraph text ..... 10
  - Changed paragraph text ..... 11
  - Changed title from Hybrid\_RF-PLC-project to TIDC-HYBRID-RF-PLC Software Example..... 12
  - Changed paragraph text ..... 12
  - Changed paragraph text ..... 12
  - Changed paragraph text ..... 14
  - Changed 10 byte to 100 B..... 14
  - Added sentence..... 14
  - Changed paragraph text ..... 14
  - Changed text in table..... 14
  - Changed title from Build Hybrid\_RF\_PLC\_Project Example Using CCS to Build HYBRID-RF-PLC Software Example Using CCS ..... 19
  - Changed paragraph text ..... 19
  - Changed title from Build Hybrid\_RF\_PLC Project to Build TIDC-HYBRID-RF-PLC CCS Project ..... 19
  - Changed CC1310DK to LAUNCHXL-CC1310 EVM ..... 19
  - Changed paragraph text ..... 19
  - Changed paragraph text ..... 19
  - Changed CC1310DK to LAUNCHXL-CC1310 ..... 20
  - Changed hyperlink name ..... 20
  - Changed table text ..... 20
  - Added note 1 ..... 20
  - Changed paragraph text ..... 21
  - Changed paragraph text ..... 21
  - Changed paragraph text ..... 26
-

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2022, Texas Instruments Incorporated